

Scaled data based on original data using  
LM-79-08 Approved Method: Electrical and Photometric Measurements of Solid-  
State Lighting Products

Test Report Prepared for  
Cooper Lighting Solutions  
(formerly Eaton)

Brand: STREETWORKS

Report Number: P147569

Luminaire Tested: **AVS-E02-LED-E-U-5MQ-7030**

Issue Date: 3/3/2020

**Test Information**

Test Method: LM-79-08  
Report Number: P147569  
REPORT IS SCALED FROM IESNA LM-79-08 TEST DATA (P33674)  
Test Lab: INNOVATION CENTER-P3  
Issue Date: 3/3/2020  
Manufacturer: COOPER LIGHTING SOLUTIONS (FORMERLY EATON)  
Product Line: STREETWORKS  
Catalog Number: AVS-E02-LED-E-U-5MQ-7030  
Description: VISION SITE SMALL LED LUMINAIRE  
(2) LIGHTBARS WITH AccuLED OPTICS - TYPE 5 SQUARE MEDIUM  
Light Source: (42) 3000K CCT, 70 CRI LEDs  
Ballast/Driver: -

**Summary**

Lumens per Lamp: N/A  
Luminaire Lumens: 5888.8 lumens  
Efficiency: N/A  
Efficacy: 113.0 lumens/watt  
Luminous Opening: Rectangular (W 0.33' x L: 1' x H: 0')  
IES Classification: Type V - Short - Full Cutoff  
BUG Rating: B3 - U0 - G1


Input Watts (W): 52.1  
Input Voltage (V): NR  
Input Current (Ain): NR  
Voltage Rise (V): NR  
Power Factor: NR  
Total Harmonic Distortion (THDi): NR  
Frequency (hertz): 60  
Stabilization Time: NR  
Operation Time: NR  
Ambient Temperature (°C): NR  
Test Distance: 28.75 FT



REPORT NUMBER: P147569  
 CATALOG NUMBER: AVS-E02-LED-E-U-5MQ-7030

### Iso-Footcandle Lines of Horizontal Illumination


✕ Max cd  
 - - - 1/2 Max cd



Based on 10 foot mounting height. Maximum calculated value = 4.4 fc  
 Type V - Short - Full Cutoff

REPORT NUMBER: P147569  
CATALOG NUMBER: AVS-E02-LED-E-U-5MQ-7030

### Luminous Intensity Polar Plot



— Vertical Plane Through 45-Deg Lateral    - - - Horizontal Cone Through 62.5-Deg Vertical

REPORT NUMBER: P147569

CATALOG NUMBER: AVS-E02-LED-E-U-5MQ-7030

**FLUX DISTRIBUTION:**

		Downward	Upward	Total
<b>House Side</b>	Lumens	2944.4	0.0	2944.4
	% Fixture	50.0	0.0	50.0
<b>Street Side</b>	Lumens	2944.4	0.0	2944.4
	% Fixture	50.0	0.0	50.0
<b>Total</b>	Lumens	5888.8	0.0	5888.8
	% Fixture	100.0	0.0	100.0

**ZONAL LUMENS:**

Zone	Lumens	% Fixture
0°-10°	39.2	0.7
10°-20°	132.4	2.2
20°-30°	256.0	4.3
30°-40°	495.7	8.4
40°-50°	895.1	15.2
50°-60°	1556.5	26.4
60°-70°	1767.0	30.0
70°-80°	685.0	11.6
80°-90°	61.8	1.0
90°-100°	0.0	0.0
100°-110°	0.0	0.0
110°-120°	0.0	0.0
120°-130°	0.0	0.0
130°-140°	0.0	0.0
140°-150°	0.0	0.0
150°-160°	0.0	0.0
160°-170°	0.0	0.0
170°-180°	0.0	0.0
0°-90°	5888.8	100.0
0°-180°	5888.8	100.0

**Coefficient of Utilization**



REPORT NUMBER: P147569


CATALOG NUMBER: AVS-E02-LED-E-U-5MQ-7030

**LUMINAIRE CLASSIFICATION SYSTEM LUMEN TABLE AND BUG RATING:**

Zone	Lumens	% Fixture	Zone Rating/Lumen Limit		
			B	U	G
FL (0°-30°)	213.8	3.6			
FM (30°-60°)	1473.7	25.0			
FH (60°-80°)	1226.0	20.8			G1/1800
FVH (80°-90°)	30.9	0.5			G1/100
BL (0°-30°)	213.8	3.6	B1/500		
BM (30°-60°)	1473.7	25.0	B2/2500		
BH (60°-80°)	1226.0	20.8	B3/2500		G1/1800
BVH (80°-90°)	30.9	0.5			G1/100
UL (90°-100°)	0.0	0.0		U0/0	
UH (100°-180°)	0.0	0.0		U0/0	

**BUG Rating: B3-U0-G1**

Type V Short





REPORT NUMBER: P147569

CATALOG NUMBER: AVS-E02-LED-E-U-5MQ-7030

**CANDELA DISTRIBUTION (FULL):**

	0°	5°	10°	15°	20°	25°	30°	35°	40°	45°	50°
0°	390.9	390.9	390.9	390.9	390.9	390.9	390.9	390.9	390.9	390.9	390.9
2.5°	393.4	394.6	394.2	393.6	393.6	393.6	393.4	392.4	392.1	392.7	393.4
5°	402.5	402.5	402.5	402.5	401.9	401.9	401.2	400.6	401.0	400.4	400.0
7.5°	416.5	415.5	415.5	415.2	415.3	414.7	413.8	412.5	412.8	412.5	412.2
10°	433.0	433.2	432.3	433.2	431.7	431.4	430.3	429.6	429.2	428.4	428.4
12.5°	452.6	451.8	451.8	451.2	450.6	449.9	448.1	447.9	446.6	446.0	445.2
15°	471.3	471.0	469.8	468.6	468.3	467.6	465.5	464.2	464.0	462.4	461.2
17.5°	489.8	489.2	487.7	487.2	485.9	485.0	483.1	481.3	480.4	479.8	478.3
20°	509.6	509.0	507.6	506.3	504.8	503.5	500.8	499.3	498.3	497.4	496.3
22.5°	534.3	533.1	530.6	528.5	525.2	523.9	520.3	518.1	516.7	515.4	514.8
25°	561.0	561.5	558.1	555.2	551.4	548.0	543.4	540.9	539.5	538.2	537.9
27.5°	594.6	594.9	591.9	587.9	581.8	578.1	572.0	569.0	568.1	566.8	566.6
30°	647.6	644.8	639.7	633.3	627.8	619.9	611.0	608.0	605.0	603.9	604.0
32.5°	745.0	743.4	739.2	723.3	716.1	699.6	684.1	675.2	665.3	660.3	657.3
35°	813.3	812.6	809.2	803.7	799.2	795.9	786.7	785.2	783.3	783.3	785.8
37.5°	863.4	859.8	859.2	860.1	858.9	859.5	866.7	876.8	885.4	889.5	889.0
40°	937.7	932.5	935.5	933.5	930.8	930.2	932.5	936.5	940.4	940.4	939.5
42.5°	1034.8	1037.3	1038.5	1029.6	1023.8	1022.4	1028.1	1026.9	1030.9	1029.4	1025.4
45°	1179.1	1177.6	1175.5	1164.8	1155.6	1148.4	1149.8	1147.8	1148.1	1145.7	1142.6
47.5°	1324.7	1329.7	1321.0	1315.9	1305.5	1300.3	1304.6	1300.9	1308.0	1295.1	1289.0
50°	1465.9	1469.6	1466.5	1459.3	1459.3	1466.5	1471.7	1478.4	1488.2	1473.6	1451.6
52.5°	1581.6	1584.7	1589.2	1595.3	1610.3	1625.7	1647.7	1671.1	1689.7	1686.9	1662.1
55°	1652.2	1656.0	1663.5	1684.6	1711.3	1752.1	1801.7	1856.2	1898.9	1919.6	1901.3
57.5°	1676.0	1678.8	1699.5	1724.8	1766.4	1826.9	1910.1	2004.1	2086.1	2138.2	2129.9
60°	1670.6	1670.5	1691.6	1726.2	1784.7	1865.1	1982.6	2112.8	2238.3	2316.3	2304.7
62.5°	1613.0	1616.0	1646.2	1687.9	1758.5	1854.7	1994.8	2161.2	2311.4	2408.3	2398.8
65°	1486.9	1489.0	1521.7	1571.3	1650.2	1763.9	1917.1	2101.6	2273.6	2366.8	2349.1
67.5°	1283.3	1285.4	1311.9	1367.9	1451.3	1570.4	1735.6	1938.8	2107.2	2180.7	2127.8
70°	1020.8	1026.9	1043.9	1103.3	1166.6	1283.3	1435.4	1638.5	1797.5	1867.2	1808.7
72.5°	695.8	711.2	731.8	784.6	845.2	942.0	1063.1	1234.3	1361.9	1442.5	1390.5
75°	391.8	413.7	420.1	460.0	509.9	586.3	675.0	797.6	926.4	991.9	929.1
77.5°	169.2	187.3	195.1	213.7	252.6	284.7	338.5	421.3	520.9	566.8	491.6
80°	83.4	87.7	91.0	96.8	107.8	118.1	143.7	179.9	220.7	231.1	183.8
82.5°	64.5	67.6	73.4	77.9	80.6	83.4	85.9	90.8	94.7	96.8	91.3
85°	45.4	49.3	55.8	60.9	63.9	66.1	68.2	69.7	66.1	60.3	63.3
87.5°	11.8	15.5	21.7	23.4	26.4	28.0	27.4	28.3	25.6	18.7	20.7
90°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0



REPORT NUMBER: P147569

CATALOG NUMBER: AVS-E02-LED-E-U-5MQ-7030

**CANDELA DISTRIBUTION (continued):**

	55°	60°	65°	70°	75°	80°	85°	90°
0°	390.9	390.9	390.9	390.9	390.9	390.9	390.9	390.9
2.5°	393.0	392.7	393.1	393.1	393.1	392.7	392.7	392.7
5°	400.0	400.0	400.3	399.8	399.8	400.0	399.8	399.5
7.5°	412.0	411.6	411.6	411.3	411.6	411.3	411.4	411.0
10°	427.8	427.2	427.5	426.5	426.5	426.2	426.3	426.2
12.5°	444.8	443.9	444.1	443.3	441.8	442.1	442.3	442.1
15°	461.2	460.3	459.5	458.9	457.8	458.2	458.2	457.9
17.5°	477.9	476.2	475.9	474.9	474.6	474.6	474.6	474.9
20°	495.3	494.1	493.9	492.8	492.6	493.5	493.9	493.2
22.5°	514.0	513.4	513.9	513.4	514.2	514.8	515.1	514.5
25°	537.4	536.8	537.6	539.8	541.0	541.7	543.2	542.5
27.5°	567.5	566.8	569.0	572.0	573.9	577.0	578.4	579.1
30°	606.4	609.1	610.4	616.6	617.8	622.6	622.6	624.8
32.5°	663.1	668.2	677.4	686.8	699.9	709.4	709.4	714.2
35°	787.4	789.4	796.5	797.9	800.7	803.7	800.7	803.1
37.5°	882.6	873.2	866.5	857.0	851.2	851.2	851.8	851.2
40°	931.4	927.7	924.6	916.7	915.4	915.2	915.1	916.4
42.5°	1018.4	1009.5	1004.7	998.0	995.9	995.2	994.9	995.5
45°	1131.6	1117.3	1104.2	1097.6	1091.8	1086.2	1088.1	1088.1
47.5°	1263.4	1241.2	1219.9	1208.4	1198.3	1193.7	1190.8	1189.7
50°	1423.8	1392.8	1365.4	1343.8	1329.2	1328.9	1330.4	1320.7
52.5°	1620.5	1571.6	1537.5	1508.2	1494.5	1493.1	1488.1	1482.7
55°	1838.5	1780.4	1724.1	1692.7	1674.8	1665.1	1659.3	1650.2
57.5°	2063.2	1985.1	1904.0	1853.8	1822.2	1800.2	1788.6	1783.4
60°	2236.5	2129.5	2022.8	1942.1	1889.4	1856.8	1836.8	1828.5
62.5°	2304.7	2159.8	2022.8	1916.8	1840.7	1795.6	1768.5	1756.7
65°	2223.4	2051.6	1895.8	1778.9	1694.0	1643.7	1614.2	1601.5
67.5°	1996.3	1844.7	1675.0	1558.8	1471.4	1421.8	1389.8	1380.4
70°	1673.6	1518.5	1356.7	1252.7	1174.9	1134.3	1101.1	1097.2
72.5°	1257.6	1124.0	985.2	899.4	836.6	769.6	752.6	761.1
75°	806.2	681.0	557.5	480.1	422.9	359.0	334.3	340.4
77.5°	381.8	295.6	213.5	165.0	138.4	118.4	113.3	110.3
80°	141.6	114.8	101.3	96.2	92.6	89.2	86.8	84.0
82.5°	91.6	89.5	86.7	85.8	83.1	78.9	70.9	67.6
85°	68.5	68.5	64.9	65.2	63.0	57.6	50.3	46.3
87.5°	20.1	18.0	16.4	15.2	14.9	13.5	9.7	8.5
90°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0

(END OF REPORT)