

Scaled data based on original data using  
LM-79-08 Approved Method: Electrical and Photometric Measurements of Solid-  
State Lighting Products

Test Report Prepared for  
Cooper Lighting Solutions  
(formerly Eaton)

Brand: STREETWORKS

Report Number: P152034

Luminaire Tested: **AVS-F02-LED-E-U-SL4-HSS-7030**

Issue Date: 3/3/2020

**Test Information**

Test Method: LM-79-08  
Report Number: P152034  
REPORT IS SCALED FROM IESNA LM-79-08 TEST DATA (P33728)  
Test Lab: INNOVATION CENTER-P3  
Issue Date: 3/3/2020  
Manufacturer: COOPER LIGHTING SOLUTIONS (FORMERLY EATON)  
Product Line: STREETWORKS  
Catalog Number: AVS-F02-LED-E-U-SL4-HSS-7030  
Description: VISION SITE SMALL LED LUMINAIRE  
(2) LIGHTBARS WITH AccuLED OPTICS - TYPE 4 W/ SPILL LIGHT CONTROL AND HOUSE SIDE SHIELD  
Light Source: (14) 3000K CCT, 70 CRI LEDs  
Ballast/Driver: -

**Summary**


Lumens per Lamp: N/A  
Luminaire Lumens: 3068.5 lumens  
Efficiency: N/A  
Efficacy: 55.8 lumens/watt  
Luminous Opening: Rectangular (W 0.33' x L: 1' x H: 0')  
IES Classification: Type IV - Short - Semi-Cutoff  
BUG Rating: B0 - U0 - G1  
  
Input Watts (W): 55  
Input Voltage (V): NR  
Input Current (Ain): NR  
Voltage Rise (V): NR  
Power Factor: NR  
Total Harmonic Distortion (THDi): NR  
Frequency (hertz): 60  
Stabilization Time: NR  
Operation Time: NR  
Ambient Temperature (°C): NR  
Test Distance: 28.75 FT



REPORT NUMBER: P152034  
 CATALOG NUMBER: AVS-F02-LED-E-U-SL4-HSS-7030

### Iso-Footcandle Lines of Horizontal Illumination


✕ Max cd  
 - - - 1/2 Max cd



Based on 10 foot mounting height. Maximum calculated value = 6.9 fc  
 Type IV - Short - Semi-Cutoff

REPORT NUMBER: P152034  
CATALOG NUMBER: AVS-F02-LED-E-U-SL4-HSS-7030

### Luminous Intensity Polar Plot



— Vertical Plane Through 40-Deg Lateral    - - - Horizontal Cone Through 69-Deg Vertical

REPORT NUMBER: P152034

CATALOG NUMBER: AVS-F02-LED-E-U-SL4-HSS-7030

**FLUX DISTRIBUTION:**

		Downward	Upward	Total
<b>House Side</b>	Lumens	91.4	0.0	91.4
	% Fixture	3.0	0.0	3.0
<b>Street Side</b>	Lumens	2977.1	0.0	2977.1
	% Fixture	97.0	0.0	97.0
<b>Total</b>	Lumens	3068.5	0.0	3068.5
	% Fixture	100.0	0.0	100.0

**Coefficient of Utilization**

**ZONAL LUMENS:**

Zone	Lumens	% Fixture
0°-10°	23.8	0.8
10°-20°	82.1	2.7
20°-30°	157.2	5.1
30°-40°	261.4	8.5
40°-50°	353.7	11.5
50°-60°	553.1	18.0
60°-70°	1137.2	37.1
70°-80°	457.6	14.9
80°-90°	42.3	1.4
90°-100°	0.0	0.0
100°-110°	0.0	0.0
110°-120°	0.0	0.0
120°-130°	0.0	0.0
130°-140°	0.0	0.0
140°-150°	0.0	0.0
150°-160°	0.0	0.0
160°-170°	0.0	0.0
170°-180°	0.0	0.0
0°-90°	3068.5	100.0
0°-180°	3068.5	100.0



REPORT NUMBER: P152034


CATALOG NUMBER: AVS-F02-LED-E-U-SL4-HSS-7030

**LUMINAIRE CLASSIFICATION SYSTEM LUMEN TABLE AND BUG RATING:**

Zone	Lumens	% Fixture	Zone Rating/Lumen Limit		
			B	U	G
FL (0°-30°)	228.4	7.4			
FM (30°-60°)	1126.5	36.7			
FH (60°-80°)	1581.5	51.5			G1/1800
FVH (80°-90°)	40.8	1.3			G1/100
BL (0°-30°)	34.8	1.1	B0/110		
BM (30°-60°)	41.7	1.4	B0/220		
BH (60°-80°)	13.3	0.4	B0/110		G0/110
BVH (80°-90°)	1.6	0.1			G0/10
UL (90°-100°)	0.0	0.0		U0/0	
UH (100°-180°)	0.0	0.0		U0/0	

**BUG Rating: B0-U0-G1**

Type IV Short





REPORT NUMBER: P152034

CATALOG NUMBER: AVS-F02-LED-E-U-SL4-HSS-7030

**CANDELA DISTRIBUTION (FULL):**

	0°	5°	10°	15°	20°	25°	30°	35°	40°	45°	50°
0°	231.7	231.7	231.7	231.7	231.7	231.7	231.7	231.7	231.7	231.7	231.7
2.5°	309.1	305.6	301.6	301.6	296.6	296.6	293.6	285.5	284.5	280.0	275.4
5°	394.6	391.6	386.5	382.1	378.0	371.0	365.9	356.4	345.8	335.8	326.7
7.5°	478.0	476.5	467.5	466.0	459.5	447.9	437.8	423.7	405.7	391.6	375.0
10°	555.4	551.9	549.9	541.3	531.8	519.3	503.6	486.5	465.5	443.3	419.7
12.5°	616.8	614.7	605.7	602.2	592.1	579.6	560.0	537.8	516.8	488.1	460.4
15°	662.5	659.0	653.0	647.5	635.3	624.4	606.2	582.1	556.5	525.3	492.1
17.5°	700.7	694.2	692.6	684.1	671.6	658.4	638.3	616.3	586.1	554.9	518.8
20°	752.0	742.9	739.9	727.4	712.7	694.7	671.6	643.9	612.2	578.0	540.8
22.5°	812.3	805.8	799.3	788.2	769.5	743.9	710.3	680.1	639.9	602.2	562.0
25°	897.7	892.2	881.7	866.6	843.4	812.8	772.1	727.9	680.6	632.3	585.1
27.5°	980.7	975.6	968.1	956.6	930.5	896.8	846.5	790.2	730.4	672.0	619.8
30°	1058.7	1054.1	1046.5	1035.0	1011.8	978.7	921.9	861.6	787.2	719.3	656.5
32.5°	1142.6	1141.0	1132.5	1116.0	1095.9	1051.1	989.2	924.4	849.0	770.6	697.2
35°	1237.5	1226.0	1217.9	1201.3	1167.2	1119.4	1047.0	976.2	896.8	816.4	734.4
37.5°	1318.0	1306.9	1296.9	1275.8	1234.0	1173.3	1091.3	1013.4	931.4	849.5	766.0
40°	1376.8	1371.3	1359.2	1331.5	1284.8	1212.4	1123.9	1039.0	956.6	874.1	791.7
42.5°	1420.5	1412.0	1398.4	1369.7	1314.5	1232.0	1137.0	1049.5	968.1	889.2	808.3
45°	1436.6	1429.5	1417.0	1385.8	1326.0	1237.5	1136.5	1046.5	968.6	893.8	819.4
47.5°	1427.0	1420.0	1408.9	1379.8	1321.0	1231.0	1127.5	1038.0	963.6	895.2	829.4
50°	1395.4	1391.4	1382.8	1358.2	1305.4	1218.4	1119.4	1033.5	962.6	902.8	843.4
52.5°	1392.3	1389.8	1379.3	1354.7	1300.9	1214.4	1118.4	1036.0	971.2	912.3	853.5
55°	1701.6	1665.8	1585.9	1518.0	1406.4	1273.8	1169.2	1076.7	1007.4	950.1	908.8
57.5°	2418.3	2365.1	2260.0	2130.8	1874.4	1622.6	1421.0	1275.2	1203.4	1177.2	1192.8
60°	2754.1	2744.6	2728.0	2666.6	2535.4	2318.8	2077.5	1816.6	1712.0	1703.0	1734.7
62.5°	2913.5	2907.4	2912.4	2904.9	2864.1	2800.8	2731.5	2618.9	2515.3	2448.5	2306.7
65°	2986.8	2990.9	3019.5	3042.1	3047.2	3063.7	3114.5	3254.7	3357.3	3184.9	2791.3
67.5°	2800.3	2823.9	2889.8	2972.2	3068.7	3162.3	3313.1	3608.6	3819.3	3616.7	3057.7
69°	2318.2	2329.8	2490.7	2646.0	2881.8	3046.6	3265.3	3652.8	3889.6	3660.9	3036.6
70°	1825.2	1835.8	2008.2	2219.3	2617.8	2829.9	3116.0	3577.9	3823.7	3602.1	2928.0
72.5°	823.3	808.3	869.1	982.2	1415.5	1752.3	2252.4	2898.9	3154.7	2885.8	2190.6
75°	575.0	568.5	575.0	575.5	642.9	829.4	1046.5	1571.3	1943.3	1676.9	1046.5
77.5°	445.4	440.8	436.3	431.3	439.4	492.1	513.3	557.4	723.8	684.7	399.1
80°	352.3	348.4	359.4	355.9	355.9	361.9	357.9	341.3	310.2	287.6	257.4
82.5°	163.8	164.9	164.9	179.0	215.6	251.8	263.4	246.8	219.2	186.5	150.3
85°	15.5	17.6	29.6	45.7	91.0	102.6	103.0	85.5	85.5	67.4	54.3
87.5°	0.0	0.5	0.5	0.5	4.6	12.5	10.6	3.0	1.6	1.6	2.5
90°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0



REPORT NUMBER: P152034

CATALOG NUMBER: AVS-F02-LED-E-U-SL4-HSS-7030

**CANDELA DISTRIBUTION (continued):**

	55°	60°	65°	70°	75°	80°	85°	90°	95°	100°	105°
0°	231.7	231.7	231.7	231.7	231.7	231.7	231.7	231.7	231.7	231.7	231.7
2.5°	267.5	265.9	259.9	253.9	248.3	242.3	236.8	231.2	225.2	220.6	215.1
5°	312.6	301.6	289.0	277.0	264.9	252.3	239.3	227.7	215.6	204.6	194.0
7.5°	358.4	336.8	319.7	298.0	278.4	258.9	240.7	222.2	205.1	189.0	173.9
10°	397.1	371.0	344.4	316.7	288.5	262.4	237.3	215.1	192.5	173.0	154.3
12.5°	428.8	395.5	362.9	328.3	296.6	263.4	232.2	205.6	179.0	156.8	137.7
15°	457.4	419.2	380.0	339.8	299.6	261.9	227.3	194.0	166.8	141.8	120.1
17.5°	480.5	436.8	392.5	347.4	304.1	259.9	220.6	186.0	154.3	128.2	107.0
20°	500.6	454.9	407.2	356.4	307.2	259.4	215.1	176.0	143.2	115.6	95.0
22.5°	519.3	473.5	422.3	368.0	311.6	258.9	210.2	168.4	133.7	106.0	85.5
25°	540.3	492.1	438.3	380.0	319.7	260.9	207.0	162.4	125.2	97.0	77.9
27.5°	563.9	513.3	457.4	395.1	330.3	264.9	206.1	155.9	117.6	88.5	71.9
30°	597.2	538.3	476.5	410.2	339.8	269.4	205.1	151.8	110.1	82.0	65.8
32.5°	626.3	563.0	497.6	425.8	350.4	274.0	204.6	146.3	103.0	75.4	61.3
35°	657.0	585.6	515.8	440.8	359.4	279.0	204.0	142.3	96.5	68.9	56.8
37.5°	683.6	604.7	529.8	453.9	369.4	283.5	204.6	138.8	90.5	63.3	52.7
40°	706.2	624.4	545.4	466.0	380.0	290.6	205.1	135.2	84.5	58.3	49.2
42.5°	726.3	642.9	562.0	479.6	392.1	298.5	208.1	132.2	79.4	53.8	45.7
45°	742.0	660.0	580.1	498.7	411.7	311.6	213.7	130.2	74.4	49.7	42.7
47.5°	758.0	685.1	610.8	528.8	440.3	332.2	223.2	129.6	70.4	46.7	40.2
50°	780.1	710.3	637.9	559.5	466.4	353.4	234.7	130.2	65.4	43.7	37.7
52.5°	796.2	735.9	673.1	612.7	528.8	417.7	279.5	139.3	62.8	41.2	34.7
55°	891.2	880.6	882.2	892.2	827.4	710.8	467.5	201.0	73.9	46.7	34.2
57.5°	1256.7	1293.9	1315.4	1314.9	1207.9	1001.8	627.9	258.3	82.5	54.3	40.7
60°	1737.2	1709.0	1669.3	1571.3	1429.1	1143.5	702.2	277.9	71.4	43.2	37.2
62.5°	2162.0	1997.1	1850.8	1691.9	1505.5	1192.8	717.3	276.5	62.3	32.6	26.1
65°	2426.8	2130.3	1894.0	1695.0	1475.3	1151.6	678.5	253.9	52.7	26.6	21.7
67.5°	2490.2	2058.4	1724.1	1470.3	1232.5	896.3	498.1	191.0	41.2	22.1	19.1
69°	2351.9	1829.7	1428.6	1140.5	896.8	594.6	308.1	120.6	31.7	20.1	17.6
70°	2163.4	1591.4	1163.6	915.3	664.0	417.7	215.6	85.0	25.6	18.5	16.1
72.5°	1391.9	836.0	572.0	398.1	274.0	166.4	84.5	38.2	19.6	15.5	13.1
75°	539.9	309.1	224.1	170.4	133.2	92.5	51.3	24.7	16.6	13.1	10.1
77.5°	265.9	203.6	166.4	114.1	66.3	41.2	27.7	19.1	13.6	9.5	6.5
80°	210.2	139.7	83.4	51.8	39.2	29.6	21.1	15.5	10.1	6.0	4.6
82.5°	107.6	58.9	43.2	35.2	29.1	23.1	17.1	11.1	6.5	4.0	3.5
85°	33.7	24.7	22.1	21.7	20.1	16.6	12.0	7.0	4.0	2.5	2.5
87.5°	2.5	3.5	4.6	3.5	4.0	3.5	4.6	3.0	2.0	2.0	1.6
90°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0





REPORT NUMBER: P152034

CATALOG NUMBER: AVS-F02-LED-E-U-SL4-HSS-7030

**CANDELA DISTRIBUTION (continued):**

	110°	115°	120°	125°	130°	135°	140°	145°	150°	155°	160°
0°	231.7	231.7	231.7	231.7	231.7	231.7	231.7	231.7	231.7	231.7	231.7
2.5°	211.1	205.1	199.6	196.1	189.5	186.9	184.5	183.5	179.0	180.0	176.0
5°	184.5	173.9	165.9	157.8	150.3	144.8	140.2	134.7	130.2	128.2	124.1
7.5°	160.3	146.7	136.3	127.7	118.7	111.6	105.6	101.6	97.5	93.5	91.5
10°	139.3	124.7	112.6	104.0	95.5	89.4	85.0	82.0	79.4	77.9	77.4
12.5°	119.6	105.6	94.5	86.9	80.4	77.4	75.4	73.9	73.4	72.8	72.8
15°	104.6	90.5	82.0	76.4	73.4	71.9	71.4	70.4	69.3	68.9	68.9
17.5°	90.5	79.9	73.9	70.9	69.3	68.4	67.4	66.3	65.4	64.9	64.9
20°	80.9	72.3	69.3	67.4	65.8	64.9	63.3	62.3	61.9	61.3	60.8
22.5°	73.4	67.9	65.8	64.4	62.3	60.8	59.8	58.9	57.8	57.3	56.8
25°	67.9	64.4	62.8	60.8	58.9	57.3	55.8	54.3	53.3	52.7	51.8
27.5°	63.8	61.3	59.3	56.8	54.8	53.3	51.8	50.3	49.2	48.3	47.8
30°	60.3	57.8	55.3	53.3	50.8	49.2	47.3	45.7	45.3	44.2	43.2
32.5°	56.8	54.3	51.8	49.2	46.7	44.8	43.7	41.8	40.7	40.2	39.2
35°	52.7	50.3	47.3	45.3	42.7	40.7	39.2	37.7	36.7	35.6	35.2
37.5°	49.2	46.2	43.2	40.7	38.8	36.7	35.2	33.7	32.6	31.7	31.2
40°	45.3	42.2	39.2	36.7	34.7	33.2	31.7	30.2	29.1	28.6	28.6
42.5°	41.8	38.2	35.2	33.2	31.7	29.6	28.2	26.6	26.1	25.6	26.1
45°	38.2	34.7	32.1	30.2	28.6	26.6	25.2	24.1	23.6	24.1	24.7
47.5°	35.2	31.7	29.1	27.7	26.1	24.7	23.1	22.1	22.1	23.1	24.1
50°	32.1	28.6	26.6	25.6	24.1	22.6	20.6	20.1	20.6	21.7	22.6
52.5°	29.1	25.2	23.6	23.1	21.7	20.1	18.5	18.1	18.5	19.6	19.1
55°	26.1	22.1	21.7	21.1	19.6	17.6	16.1	16.1	16.1	15.5	14.6
57.5°	25.2	19.6	19.1	18.5	17.1	15.1	14.1	13.1	12.5	11.1	10.6
60°	26.1	17.6	17.6	16.6	15.1	13.1	11.6	10.1	9.0	8.1	8.1
62.5°	21.1	16.1	15.5	14.6	12.5	10.6	9.0	7.6	7.0	6.5	6.5
65°	17.1	14.6	13.6	12.0	10.6	8.5	7.0	6.0	5.5	5.5	6.0
67.5°	15.5	13.1	11.6	10.1	8.5	6.5	5.5	5.1	5.1	5.5	5.5
69°	14.6	12.0	10.6	9.0	7.6	6.0	5.1	5.1	5.1	5.1	5.5
70°	13.6	11.6	10.1	8.5	6.5	5.1	4.6	4.6	5.1	5.1	5.5
72.5°	10.6	9.0	8.5	7.0	5.1	4.6	4.0	4.6	4.6	5.1	5.1
75°	8.1	6.5	6.5	5.5	4.0	3.5	3.5	4.0	4.0	4.6	4.6
77.5°	5.5	4.6	4.6	4.0	3.5	3.0	3.0	3.5	4.0	4.0	4.6
80°	4.0	3.5	3.0	3.5	3.0	2.5	3.0	3.5	3.5	4.0	4.0
82.5°	3.0	3.0	3.0	3.0	2.5	2.5	3.0	3.0	3.5	4.0	4.0
85°	2.5	2.5	2.5	2.5	2.5	2.5	2.5	3.0	3.0	3.5	3.5
87.5°	1.6	1.6	1.6	2.0	2.0	2.5	2.5	2.5	2.5	3.0	3.0
90°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0



REPORT NUMBER: P152034

CATALOG NUMBER: AVS-F02-LED-E-U-SL4-HSS-7030

**CANDELA DISTRIBUTION (continued):**

	165°	170°	175°	180°
0°	231.7	231.7	231.7	231.7
2.5°	174.9	174.4	172.4	173.0
5°	122.7	119.6	121.7	121.1
7.5°	89.9	89.4	89.0	89.9
10°	76.9	76.9	76.4	76.9
12.5°	72.3	72.3	72.3	72.3
15°	68.9	68.9	68.4	68.4
17.5°	64.9	64.9	64.9	64.4
20°	60.8	60.3	60.3	60.3
22.5°	56.3	55.8	55.8	55.8
25°	51.8	51.3	51.3	51.3
27.5°	47.3	46.7	46.2	46.2
30°	42.7	42.2	41.8	41.8
32.5°	38.2	37.7	37.2	37.2
35°	34.2	34.2	33.7	33.2
37.5°	30.7	30.7	30.7	30.7
40°	28.2	28.6	28.6	28.6
42.5°	26.6	27.2	27.7	28.2
45°	25.6	26.6	27.2	27.2
47.5°	25.2	25.6	26.1	26.1
50°	23.1	22.6	22.6	22.6
52.5°	18.5	17.6	17.1	16.6
55°	13.6	13.1	12.0	12.0
57.5°	9.5	9.5	9.0	9.0
60°	7.6	7.6	7.0	7.6
62.5°	6.5	6.5	6.5	6.5
65°	6.0	6.0	6.0	6.0
67.5°	6.0	6.0	6.0	6.0
69°	5.5	5.5	5.5	5.5
70°	5.5	5.5	5.5	5.5
72.5°	5.1	5.1	5.1	5.1
75°	4.6	5.1	5.1	5.1
77.5°	4.6	4.6	4.6	4.6
80°	4.0	4.0	4.6	4.6
82.5°	4.0	4.0	4.0	4.0
85°	3.5	3.5	4.0	4.0
87.5°	3.0	3.0	3.5	3.5
90°	0.0	0.0	0.0	0.0

(END OF REPORT)