

Scaled data based on original data using  
LM-79-08 Approved Method: Electrical and Photometric Measurements of Solid-  
State Lighting Products

Test Report Prepared for  
Cooper Lighting Solutions  
(formerly Eaton)

Brand: STREETWORKS

Report Number: P153191

Luminaire Tested: **AVS-E04-LED-E-U-SLL-7050**

Issue Date: 3/3/2020

**Test Information**

Test Method: LM-79-08  
Report Number: P153191  
REPORT IS SCALED FROM IESNA LM-79-08 TEST DATA (P33681)  
Test Lab: INNOVATION CENTER-P3  
Issue Date: 3/3/2020  
Manufacturer: COOPER LIGHTING SOLUTIONS (FORMERLY EATON)  
Product Line: STREETWORKS  
Catalog Number: AVS-E04-LED-E-U-SLL-7050  
Description: VISION SITE SMALL LED LUMINAIRE  
(4) LIGHTBARS WITH AccuLED OPTICS - 90° SPILL LIGHT ELIMINATOR LEFT  
Light Source: (84) 5000K CCT, 70 CRI LEDs  
Ballast/Driver: -

**Summary**

Lumens per Lamp: N/A  
Luminaire Lumens: 11420.4 lumens  
Efficiency: N/A  
Efficacy: 117.5 lumens/watt  
Luminous Opening: Rectangular (W 0.67' x L: 1' x H: 0')  
IES Classification: Type IV - Short - Non-Cutoff  
BUG Rating: B2 - U0 - G3


Input Watts (W): 97.2  
Input Voltage (V): NR  
Input Current (Ain): NR  
Voltage Rise (V): NR  
Power Factor: NR  
Total Harmonic Distortion (THDi): NR  
Frequency (hertz): 60  
Stabilization Time: NR  
Operation Time: NR  
Ambient Temperature (°C): NR  
Test Distance: 28.75 FT



REPORT NUMBER: P153191  
 CATALOG NUMBER: AVS-E04-LED-E-U-SLL-7050

### Iso-Footcandle Lines of Horizontal Illumination


✕ Max cd  
 - - - 1/2 Max cd



Based on 20 foot mounting height. Maximum calculated value = 7.1 fc  
 Type IV - Short - Non-Cutoff

REPORT NUMBER: P153191  
CATALOG NUMBER: AVS-E04-LED-E-U-SLL-7050

### Luminous Intensity Polar Plot



— Vertical Plane Through 60-Deg Lateral      - - - Horizontal Cone Through 63-Deg Vertical

REPORT NUMBER: P153191

CATALOG NUMBER: AVS-E04-LED-E-U-SLL-7050

**FLUX DISTRIBUTION:**

		Downward	Upward	Total
<b>House Side</b>	Lumens	2476.5	0.0	2476.5
	% Fixture	21.7	0.0	21.7
<b>Street Side</b>	Lumens	8943.9	0.0	8943.9
	% Fixture	78.3	0.0	78.3
<b>Total</b>	Lumens	11420.4	0.0	11420.4
	% Fixture	100.0	0.0	100.0

**ZONAL LUMENS:**

Zone	Lumens	% Fixture
0°-10°	139.7	1.2
10°-20°	435.1	3.8
20°-30°	773.0	6.8
30°-40°	1217.3	10.7
40°-50°	1791.4	15.7
50°-60°	2379.5	20.8
60°-70°	2621.1	23.0
70°-80°	1644.4	14.4
80°-90°	418.8	3.7
90°-100°	0.0	0.0
100°-110°	0.0	0.0
110°-120°	0.0	0.0
120°-130°	0.0	0.0
130°-140°	0.0	0.0
140°-150°	0.0	0.0
150°-160°	0.0	0.0
160°-170°	0.0	0.0
170°-180°	0.0	0.0
0°-90°	11420.4	100.0
0°-180°	11420.4	100.0

**Coefficient of Utilization**



REPORT NUMBER: P153191


CATALOG NUMBER: AVS-E04-LED-E-U-SLL-7050

**LUMINAIRE CLASSIFICATION SYSTEM LUMEN TABLE AND BUG RATING:**

Zone	Lumens	% Fixture	Zone Rating/Lumen Limit		
			B	U	G
FL (0°-30°)	731.3	6.4			
FM (30°-60°)	4150.4	36.3			
FH (60°-80°)	3694.7	32.4			G2/5000
FVH (80°-90°)	367.5	3.2			G3/500
BL (0°-30°)	616.5	5.4	B2/1000		
BM (30°-60°)	1237.8	10.8	B2/2500		
BH (60°-80°)	570.8	5.0	B2/1000		G2/1000
BVH (80°-90°)	51.3	0.4			G1/100
UL (90°-100°)	0.0	0.0		U0/0	
UH (100°-180°)	0.0	0.0		U0/0	

**BUG Rating: B2-U0-G3**

Type IV Short





REPORT NUMBER: P153191  
 CATALOG NUMBER: AVS-E04-LED-E-U-SLL-7050

**CANDELA DISTRIBUTION (FULL):**

	0°	5°	10°	15°	20°	25°	30°	35°	40°	45°	50°
0°	1435.1	1435.1	1435.1	1435.1	1435.1	1435.1	1435.1	1435.1	1435.1	1435.1	1435.1
2.5°	1416.1	1418.8	1418.8	1417.4	1417.4	1420.1	1418.8	1417.4	1413.3	1418.8	1418.8
5°	1405.1	1407.8	1407.8	1410.6	1413.3	1416.1	1416.1	1418.8	1417.4	1422.9	1426.9
7.5°	1418.8	1421.5	1426.9	1433.8	1437.9	1447.5	1447.5	1454.3	1457.1	1461.1	1459.8
10°	1436.6	1443.4	1455.8	1466.6	1474.8	1485.8	1494.0	1503.6	1503.6	1507.7	1510.5
12.5°	1468.0	1474.8	1488.5	1502.2	1514.5	1528.2	1540.5	1550.1	1559.7	1562.4	1567.9
15°	1520.0	1528.2	1548.7	1567.9	1582.9	1600.7	1617.1	1636.3	1654.1	1658.1	1660.9
17.5°	1598.0	1614.4	1629.4	1663.6	1685.6	1708.8	1734.8	1762.2	1767.7	1796.4	1803.2
20°	1708.8	1729.3	1743.0	1785.4	1822.4	1852.4	1890.8	1922.3	1934.5	1961.9	1989.3
22.5°	1900.3	1896.3	1916.8	1959.2	1986.5	2046.7	2079.6	2112.4	2128.8	2169.8	2191.7
25°	2157.5	2179.5	2224.6	2228.7	2254.7	2324.5	2366.8	2399.7	2401.0	2413.4	2436.7
27.5°	2410.7	2500.9	2572.1	2610.4	2680.2	2744.5	2741.8	2788.3	2715.8	2730.8	2752.7
30°	2717.1	2867.7	3001.7	3092.0	3163.1	3238.3	3275.3	3301.3	3269.8	3256.2	3230.2
32.5°	3004.5	3215.1	3421.8	3581.8	3714.5	3839.0	3921.1	3958.0	4001.8	4112.6	4152.3
35°	3201.5	3499.7	3756.9	3988.1	4209.7	4408.2	4551.8	4633.9	4602.4	4587.4	4579.2
37.5°	3319.1	3683.0	4004.6	4331.5	4586.0	4882.9	5105.9	5322.1	5371.3	5285.1	5242.7
40°	3393.0	3823.9	4237.1	4622.9	4952.6	5335.8	5612.1	5936.4	6182.6	6215.4	6114.2
42.5°	3428.6	3918.3	4399.9	4836.4	5282.4	5751.7	6101.9	6494.6	6862.6	7115.6	7052.7
45°	3434.0	3979.9	4519.0	5029.3	5560.1	6117.0	6568.4	7003.5	7496.1	7929.7	7942.1
47.5°	3434.0	4026.4	4601.0	5168.8	5809.1	6434.4	6926.9	7441.3	8044.7	8557.7	8715.0
50°	3436.8	4057.9	4677.7	5278.2	5999.3	6702.5	7259.4	7866.8	8501.7	9059.8	9363.5
52.5°	3449.1	4081.1	4737.8	5356.3	6122.4	6891.3	7517.9	8218.4	8850.5	9423.7	9816.4
55°	3476.5	4114.0	4781.7	5404.1	6204.6	7014.5	7705.4	8459.2	9076.3	9657.7	10206.3
57.5°	3553.1	4171.5	4835.0	5446.5	6249.6	7095.1	7836.7	8563.2	9162.5	9768.5	10413.0
60°	3706.3	4293.3	4926.6	5531.4	6324.9	7244.4	7899.7	8493.4	9099.5	9735.6	10459.5
62.5°	3951.2	4483.4	5053.9	5675.0	6539.7	7475.5	7851.7	8285.5	8851.9	9545.5	10293.9
63°	4036.1	4524.5	5082.6	5706.5	6598.5	7517.9	7831.2	8223.9	8801.2	9485.3	10235.0
65°	4272.7	4706.4	5219.5	5865.2	6840.7	7560.3	7671.2	7903.7	8451.0	9141.9	9887.6
67.5°	4714.6	5148.3	5513.6	6133.4	7044.6	7393.5	7174.5	7203.2	7775.1	8490.7	9161.0
70°	4993.7	5510.9	5701.0	6167.6	7007.6	7145.8	6531.5	6151.2	6609.5	7424.9	8011.8
72.5°	4921.2	5515.0	5494.4	5712.0	6268.8	6397.4	5761.2	5162.0	5434.3	6043.1	6423.4
75°	4215.2	4925.3	4774.8	4731.0	4926.6	5011.5	4534.0	4442.4	4785.8	5123.7	5129.1
77.5°	3034.5	3815.8	3639.3	3386.1	3372.4	3568.1	3632.4	4233.1	4740.6	5007.4	4889.7
80°	1933.2	2780.1	2596.7	2154.8	2148.0	2402.5	2967.5	3784.2	4322.0	4471.1	4164.7
82.5°	1009.6	1819.6	1889.4	1617.1	1851.1	2272.4	2823.8	3049.5	3253.5	3274.0	2912.7
85°	629.3	1119.2	1316.2	1358.5	1671.9	2015.2	2011.2	1931.8	1841.6	1576.1	1425.6
87.5°	71.2	140.9	213.5	202.5	272.2	381.8	476.1	279.1	195.6	71.2	98.5
90°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0



REPORT NUMBER: P153191

CATALOG NUMBER: AVS-E04-LED-E-U-SLL-7050

**CANDELA DISTRIBUTION (continued):**

	55°	60°	65°	70°	75°	80°	85°	90°	95°	100°	105°
0°	1435.1	1435.1	1435.1	1435.1	1435.1	1435.1	1435.1	1435.1	1435.1	1435.1	1435.1
2.5°	1421.5	1422.9	1424.2	1424.2	1431.1	1429.7	1431.1	1433.8	1437.9	1440.6	1443.4
5°	1432.4	1432.4	1437.9	1442.0	1450.3	1455.8	1458.4	1466.6	1476.3	1473.5	1481.7
7.5°	1468.0	1466.6	1472.1	1474.8	1481.7	1491.3	1489.9	1496.8	1505.0	1507.7	1514.5
10°	1515.9	1511.8	1511.8	1509.0	1510.5	1507.7	1507.7	1507.7	1513.2	1511.8	1517.3
12.5°	1565.2	1563.8	1561.0	1552.8	1552.8	1541.9	1536.4	1529.5	1528.2	1518.7	1520.0
15°	1666.4	1666.4	1660.9	1644.5	1630.8	1621.2	1607.6	1598.0	1584.4	1566.5	1557.0
17.5°	1814.2	1795.0	1788.2	1785.4	1763.5	1755.3	1725.2	1693.8	1678.8	1654.1	1640.4
20°	1994.7	1990.7	1963.3	1949.6	1922.3	1883.9	1845.6	1804.6	1780.0	1749.8	1733.5
22.5°	2198.7	2168.5	2154.8	2134.3	2091.9	2048.1	1990.7	1936.0	1897.6	1877.1	1864.8
25°	2436.7	2406.5	2392.8	2365.5	2313.6	2267.0	2195.9	2131.6	2097.4	2063.1	2044.0
27.5°	2752.7	2723.9	2707.6	2636.4	2618.7	2542.0	2454.4	2366.8	2321.8	2271.1	2238.2
30°	3224.7	3226.1	3141.2	3055.0	2966.1	2833.4	2741.8	2643.2	2569.3	2496.9	2424.4
32.5°	4022.4	3818.4	3661.1	3476.5	3283.5	3142.6	3029.0	2911.4	2808.8	2703.4	2583.0
35°	4509.4	4410.9	4207.0	3869.1	3674.8	3503.8	3377.9	3235.6	3109.7	2923.7	2740.4
37.5°	5059.4	4830.9	4583.3	4395.9	4175.5	3977.2	3766.5	3605.1	3387.6	3137.1	2877.2
40°	5862.5	5535.5	5237.2	4985.5	4700.9	4493.0	4257.6	4023.7	3735.0	3372.4	3015.3
42.5°	6701.1	6363.2	5969.2	5642.2	5307.0	5063.5	4772.1	4443.7	4019.6	3570.9	3134.4
45°	7580.8	7129.4	6657.4	6257.8	5909.0	5606.6	5245.5	4810.4	4293.3	3748.7	3245.2
47.5°	8448.3	7929.7	7367.5	6937.8	6483.6	6114.2	5671.0	5120.9	4506.6	3917.0	3356.1
50°	9213.1	8713.7	8036.5	7490.6	7030.9	6575.2	6022.6	5360.4	4674.9	4062.0	3456.0
52.5°	9872.5	9442.9	8730.2	8040.5	7511.1	6999.4	6305.8	5553.3	4844.6	4196.1	3538.0
55°	10356.8	10070.9	9414.2	8559.1	7933.9	7323.6	6545.2	5739.4	5004.7	4302.8	3591.4
57.5°	10722.1	10563.4	9999.7	9047.6	8322.4	7638.3	6792.8	5962.4	5163.3	4394.5	3616.0
60°	10921.9	10965.6	10443.0	9474.4	8665.8	7901.0	7040.4	6152.5	5281.0	4447.9	3602.3
62.5°	10902.7	11170.9	10775.4	9737.1	8865.6	8057.0	7207.4	6241.5	5264.6	4363.0	3477.8
63°	10865.8	11177.7	10812.4	9754.8	8877.8	8062.5	7211.5	6229.1	5230.4	4322.0	3428.6
65°	10547.0	11020.4	10780.9	9674.1	8768.4	7959.8	7125.3	6051.3	4989.6	4101.7	3175.4
67.5°	9693.3	10285.7	10217.3	9103.6	8249.8	7535.8	6684.8	5478.0	4394.5	3559.9	2691.1
70°	8282.7	8839.6	8851.9	7917.4	7204.7	6504.1	5796.8	4457.4	3483.3	2759.6	2007.0
72.5°	6348.2	6706.6	6831.1	6215.4	5738.0	5245.5	4610.7	3235.6	2483.2	1877.1	1306.5
75°	4915.8	4817.2	4815.9	4556.0	4361.7	4120.8	3423.1	2183.5	1630.8	1220.4	799.0
77.5°	4419.1	3981.2	3557.2	3245.2	3089.2	3008.5	2245.1	1316.2	961.8	701.9	459.7
80°	3644.8	2999.0	2423.0	2086.4	1952.3	2045.4	1251.8	711.4	526.7	399.5	298.2
82.5°	2513.3	2086.4	1585.7	1313.4	1127.4	1179.4	640.3	363.9	243.5	223.0	184.7
85°	1309.3	1147.9	968.6	831.8	734.7	645.8	332.4	173.8	101.2	88.9	80.7
87.5°	0.0	1.3	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
90°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0





REPORT NUMBER: P153191  
 CATALOG NUMBER: AVS-E04-LED-E-U-SLL-7050

**CANDELA DISTRIBUTION (continued):**

	110°	115°	120°	125°	130°	135°	140°	145°	150°	155°	160°
0°	1435.1	1435.1	1435.1	1435.1	1435.1	1435.1	1435.1	1435.1	1435.1	1435.1	1435.1
2.5°	1447.5	1446.1	1448.9	1450.3	1454.3	1457.1	1458.4	1455.8	1459.8	1463.9	1461.1
5°	1485.8	1495.3	1496.8	1500.8	1500.8	1509.0	1509.0	1509.0	1507.7	1509.0	1506.3
7.5°	1518.7	1531.0	1532.3	1537.8	1539.2	1548.7	1544.7	1547.4	1547.4	1540.5	1537.8
10°	1522.7	1535.0	1541.9	1548.7	1558.3	1570.7	1570.7	1577.5	1577.5	1572.0	1570.7
12.5°	1524.1	1533.7	1540.5	1550.1	1563.8	1581.6	1591.2	1600.7	1604.9	1603.4	1599.4
15°	1552.8	1552.8	1554.2	1562.4	1572.0	1593.9	1607.6	1618.5	1625.4	1622.6	1615.8
17.5°	1628.1	1617.1	1608.9	1595.2	1598.0	1608.9	1617.1	1626.7	1628.1	1625.4	1614.4
20°	1715.6	1702.0	1681.5	1659.6	1648.6	1640.4	1634.9	1634.9	1630.8	1617.1	1599.4
22.5°	1840.1	1822.4	1793.7	1760.8	1738.9	1713.0	1681.5	1651.3	1618.5	1585.7	1547.4
25°	2012.5	1987.9	1957.8	1907.2	1860.6	1805.9	1741.7	1674.6	1596.6	1528.2	1472.1
27.5°	2186.3	2131.6	2053.6	1983.8	1897.6	1815.5	1723.8	1641.8	1541.9	1459.8	1398.2
30°	2329.9	2226.0	2113.8	2003.0	1889.4	1778.5	1669.1	1570.7	1461.1	1377.7	1317.5
32.5°	2440.7	2297.1	2141.1	1996.2	1856.6	1721.1	1595.2	1485.8	1375.0	1288.8	1224.5
35°	2543.4	2343.6	2145.3	1966.0	1793.7	1652.7	1510.5	1391.4	1273.8	1183.4	1113.7
37.5°	2620.0	2365.5	2120.6	1909.9	1711.5	1554.2	1409.2	1287.5	1167.0	1068.5	989.1
40°	2669.2	2351.8	2067.3	1829.2	1614.4	1448.9	1301.1	1175.2	1059.0	950.9	855.1
42.5°	2708.9	2334.1	2013.9	1755.3	1537.8	1357.2	1205.3	1069.8	952.2	834.6	729.2
45°	2767.8	2347.8	1990.7	1703.3	1469.4	1279.2	1112.3	971.4	848.3	733.4	632.1
47.5°	2825.2	2354.6	1956.5	1639.1	1383.2	1198.4	1028.8	892.0	766.1	660.8	567.8
50°	2877.2	2350.5	1903.1	1557.0	1299.7	1117.7	953.6	816.8	692.2	595.1	507.6
52.5°	2901.9	2327.3	1837.4	1477.6	1232.7	1046.6	879.7	747.0	623.8	532.2	451.5
55°	2899.1	2267.0	1751.2	1402.4	1158.9	971.4	807.3	675.9	565.1	480.2	410.5
57.5°	2858.0	2174.0	1659.6	1318.9	1061.7	878.3	722.4	595.1	502.1	431.0	372.1
60°	2771.8	2054.9	1539.2	1197.1	939.9	763.4	617.0	507.6	432.3	377.6	339.3
62.5°	2610.4	1883.9	1388.7	1027.5	775.8	614.3	487.0	416.0	359.8	326.9	309.2
63°	2562.5	1837.4	1324.4	986.4	737.4	580.1	459.7	385.8	344.8	316.1	299.6
65°	2324.5	1608.9	1108.2	796.3	573.3	447.4	369.4	313.3	288.7	276.4	275.0
67.5°	1882.6	1265.5	783.9	545.9	389.9	322.9	283.2	259.9	249.0	246.2	249.0
70°	1321.7	799.0	498.0	362.6	288.7	259.9	242.2	232.5	225.7	227.2	229.8
72.5°	842.8	478.9	342.1	275.0	243.5	228.5	220.3	217.5	216.2	214.8	214.8
75°	480.2	318.8	262.7	238.0	221.7	209.3	202.5	199.8	201.1	202.5	199.8
77.5°	317.4	262.7	234.0	217.5	202.5	188.8	184.7	183.3	186.1	188.8	188.8
80°	250.4	234.0	217.5	201.1	176.5	166.9	169.6	171.0	169.6	171.0	166.9
82.5°	176.5	173.8	177.8	171.0	146.4	138.1	135.4	136.8	134.1	134.1	131.3
85°	82.1	82.1	86.2	86.2	83.4	84.9	91.7	99.9	103.9	99.9	94.4
87.5°	0.0	0.0	0.0	0.0	0.0	12.3	24.7	35.5	38.3	47.9	46.5
90°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0



REPORT NUMBER: P153191

CATALOG NUMBER: AVS-E04-LED-E-U-SLL-7050

**CANDELA DISTRIBUTION (continued):**

	165°	170°	175°	180°	185°	190°	195°	200°	205°	210°	215°
0°	1435.1	1435.1	1435.1	1435.1	1435.1	1435.1	1435.1	1435.1	1435.1	1435.1	1435.1
2.5°	1457.1	1459.8	1458.4	1457.1	1459.8	1457.1	1458.4	1457.1	1457.1	1455.8	1455.8
5°	1503.6	1507.7	1499.5	1498.1	1495.3	1488.5	1488.5	1485.8	1485.8	1480.3	1476.3
7.5°	1533.7	1535.0	1528.2	1526.8	1520.0	1513.2	1507.7	1502.2	1500.8	1496.8	1488.5
10°	1562.4	1559.7	1554.2	1547.4	1540.5	1531.0	1524.1	1517.3	1515.9	1509.0	1499.5
12.5°	1587.0	1585.7	1574.7	1567.9	1557.0	1547.4	1539.2	1531.0	1526.8	1518.7	1505.0
15°	1603.4	1595.2	1581.6	1569.2	1557.0	1546.0	1536.4	1526.8	1522.7	1513.2	1499.5
17.5°	1596.6	1581.6	1563.8	1548.7	1532.3	1518.7	1510.5	1500.8	1494.0	1488.5	1469.4
20°	1572.0	1550.1	1522.7	1505.0	1483.1	1465.3	1459.8	1450.3	1444.8	1424.2	1399.6
22.5°	1507.7	1476.3	1442.0	1416.1	1391.4	1373.6	1359.9	1350.4	1336.7	1324.4	1286.0
25°	1426.9	1391.4	1355.9	1324.4	1291.5	1264.1	1239.6	1216.3	1209.4	1183.4	1146.5
27.5°	1349.0	1309.3	1273.8	1236.8	1194.4	1160.2	1117.7	1085.0	1063.0	1035.6	1001.5
30°	1265.5	1225.8	1177.9	1128.7	1079.5	1042.5	994.6	954.9	927.6	898.9	867.4
32.5°	1160.2	1112.3	1054.8	1000.1	954.9	911.2	863.3	825.0	797.6	771.6	741.6
35°	1039.8	976.9	915.3	855.1	807.3	770.3	727.9	699.2	680.0	656.7	625.3
37.5°	901.6	830.5	764.8	718.2	675.9	640.3	610.2	592.4	571.9	559.6	540.4
40°	762.1	692.2	628.0	585.6	549.9	529.4	513.1	508.9	495.2	478.9	466.5
42.5°	639.0	571.9	508.9	474.7	451.5	446.0	437.8	437.8	431.0	418.7	410.5
45°	555.4	485.7	431.0	406.3	394.0	392.6	388.6	388.6	387.2	381.8	372.1
47.5°	495.2	432.3	389.9	374.9	372.1	369.4	365.3	363.9	362.6	358.4	353.0
50°	440.5	387.2	359.8	353.0	354.3	350.3	346.1	342.1	340.6	336.6	331.1
52.5°	389.9	351.6	333.8	329.7	329.7	329.7	326.9	326.9	324.2	322.9	317.4
55°	361.1	332.4	322.9	321.6	320.1	318.8	316.1	316.1	313.3	311.9	305.1
57.5°	336.6	318.8	313.3	310.6	309.2	306.4	305.1	305.1	305.1	305.1	296.9
60°	317.4	309.2	307.9	305.1	303.7	298.2	295.5	294.2	295.5	296.9	288.7
62.5°	296.9	295.5	294.2	291.4	290.1	284.6	280.5	277.7	280.5	283.2	281.9
63°	291.4	290.1	290.1	288.7	287.4	280.5	276.4	273.7	276.4	279.1	279.1
65°	272.2	273.7	273.7	272.2	270.9	266.7	261.3	258.5	259.9	264.0	265.4
67.5°	251.7	253.1	251.7	253.1	251.7	249.0	244.9	242.2	240.8	242.2	243.5
70°	232.5	235.3	234.0	232.5	231.2	231.2	228.5	224.4	223.0	221.7	221.7
72.5°	216.2	216.2	213.5	213.5	212.0	212.0	209.3	205.2	203.8	203.8	201.1
75°	198.3	198.3	194.3	194.3	191.5	193.0	190.2	186.1	184.7	184.7	183.3
77.5°	187.5	183.3	176.5	175.1	173.8	173.8	172.4	168.3	166.9	166.9	165.6
80°	165.6	157.3	150.5	149.1	150.5	153.3	153.3	150.5	150.5	150.5	150.5
82.5°	128.6	125.9	121.8	119.1	119.1	123.1	128.6	131.3	134.1	136.8	136.8
85°	94.4	95.8	94.4	90.3	88.9	93.1	98.5	103.9	105.4	110.8	109.4
87.5°	50.6	52.0	47.9	46.5	50.6	53.4	58.9	60.2	62.9	64.4	65.7
90°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0



REPORT NUMBER: P153191

CATALOG NUMBER: AVS-E04-LED-E-U-SLL-7050

**CANDELA DISTRIBUTION (continued):**

	220°	225°	230°	235°	240°	245°	250°	255°	260°	265°	270°
0°	1435.1	1435.1	1435.1	1435.1	1435.1	1435.1	1435.1	1435.1	1435.1	1435.1	1435.1
2.5°	1454.3	1453.0	1454.3	1451.6	1451.6	1448.9	1446.1	1444.8	1442.0	1440.6	1437.9
5°	1479.0	1474.8	1470.8	1469.4	1463.9	1458.4	1454.3	1447.5	1442.0	1432.4	1429.7
7.5°	1495.3	1485.8	1480.3	1479.0	1470.8	1466.6	1457.1	1448.9	1440.6	1428.3	1424.2
10°	1502.2	1492.6	1483.1	1479.0	1469.4	1462.6	1453.0	1440.6	1433.8	1421.5	1418.8
12.5°	1510.5	1492.6	1477.6	1466.6	1453.0	1437.9	1428.3	1421.5	1411.9	1405.1	1402.4
15°	1495.3	1472.1	1448.9	1428.3	1406.4	1390.1	1380.4	1369.5	1358.5	1354.5	1354.5
17.5°	1454.3	1424.2	1384.6	1358.5	1335.3	1317.5	1305.2	1294.3	1292.8	1287.5	1290.2
20°	1369.5	1329.8	1291.5	1272.3	1258.7	1247.8	1235.4	1229.9	1225.8	1217.6	1214.9
22.5°	1251.8	1219.0	1191.6	1177.9	1167.0	1153.4	1142.4	1126.0	1121.9	1113.7	1109.5
25°	1121.9	1095.9	1072.6	1063.0	1056.2	1037.1	1030.3	1008.3	993.3	983.7	989.1
27.5°	991.9	972.7	950.9	938.5	934.4	916.7	909.8	885.2	872.8	872.8	859.2
30°	857.8	840.0	826.3	812.6	809.9	788.1	770.3	760.7	747.0	741.6	731.9
32.5°	731.9	714.2	703.2	696.4	685.4	667.7	649.8	633.5	611.6	603.3	599.3
35°	615.6	602.0	588.3	582.8	567.8	548.6	526.7	513.1	487.0	477.5	473.4
37.5°	526.7	510.4	500.7	485.7	470.7	450.2	433.7	421.3	411.8	407.7	407.7
40°	455.5	443.3	432.3	420.0	407.7	396.8	388.6	385.8	384.5	384.5	387.2
42.5°	402.3	391.3	385.8	379.0	374.9	374.9	373.5	374.9	376.3	377.6	381.8
45°	366.6	359.8	357.1	355.8	358.4	361.1	362.6	365.3	370.8	373.5	374.9
47.5°	347.5	342.1	340.6	342.1	346.1	351.6	357.1	361.1	365.3	366.6	368.0
50°	328.4	321.6	318.8	321.6	326.9	335.2	339.3	346.1	348.9	351.6	348.9
52.5°	311.9	306.4	305.1	305.1	310.6	316.1	321.6	326.9	328.4	328.4	326.9
55°	298.2	294.2	290.1	292.7	296.9	302.4	310.6	314.7	317.4	318.8	318.8
57.5°	287.4	283.2	279.1	281.9	285.9	291.4	299.6	303.7	306.4	310.6	311.9
60°	279.1	273.7	269.5	273.7	277.7	285.9	292.7	296.9	303.7	305.1	305.1
62.5°	270.9	265.4	258.5	262.7	262.7	266.7	273.7	279.1	285.9	288.7	288.7
63°	269.5	264.0	257.2	259.9	259.9	262.7	268.2	273.7	281.9	284.6	283.2
65°	258.5	257.2	250.4	250.4	247.7	250.4	254.5	259.9	264.0	268.2	268.2
67.5°	240.8	239.4	238.0	238.0	238.0	240.8	243.5	247.7	251.7	254.5	253.1
70°	220.3	220.3	220.3	221.7	221.7	224.4	225.7	224.4	228.5	231.2	229.8
72.5°	202.5	201.1	199.8	202.5	201.1	201.1	203.8	202.5	206.6	206.6	208.0
75°	183.3	182.0	182.0	183.3	180.6	177.8	179.3	179.3	180.6	180.6	183.3
77.5°	166.9	166.9	166.9	165.6	162.8	161.5	160.1	160.1	160.1	160.1	161.5
80°	151.8	151.8	151.8	150.5	147.8	145.0	142.3	140.9	139.6	132.7	132.7
82.5°	136.8	136.8	136.8	136.8	135.4	132.7	128.6	117.6	112.2	106.7	108.1
85°	108.1	110.8	113.6	117.6	116.3	116.3	108.1	94.4	86.2	80.7	82.1
87.5°	69.7	61.6	61.6	60.2	57.5	54.7	54.7	46.5	38.3	34.2	35.5
90°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0



REPORT NUMBER: P153191  
 CATALOG NUMBER: AVS-E04-LED-E-U-SLL-7050

REPORT N  
 CATALOG

**CANDELA DISTRIBUTION (continued):**

**CANDELA**

	275°	280°	285°	290°	295°	300°	305°	310°	315°	320°	325°	
0°	1435.1	1435.1	1435.1	1435.1	1435.1	1435.1	1435.1	1435.1	1435.1	1435.1	1435.1	0°
2.5°	1437.9	1435.1	1432.4	1432.4	1428.3	1428.3	1425.6	1431.1	1425.6	1421.5	1421.5	2.5°
5°	1426.9	1424.2	1416.1	1414.6	1409.2	1409.2	1409.2	1406.4	1406.4	1403.7	1402.4	5°
7.5°	1420.1	1413.3	1406.4	1402.4	1402.4	1399.6	1405.1	1402.4	1403.7	1403.7	1405.1	7.5°
10°	1414.6	1409.2	1406.4	1405.1	1405.1	1409.2	1413.3	1414.6	1413.3	1414.6	1414.6	10°
12.5°	1400.9	1403.7	1405.1	1410.6	1417.4	1425.6	1435.1	1436.6	1439.3	1439.3	1442.0	12.5°
15°	1357.2	1364.0	1372.2	1385.9	1403.7	1421.5	1439.3	1454.3	1468.0	1474.8	1480.3	15°
17.5°	1295.6	1302.5	1317.5	1332.5	1355.9	1381.9	1411.9	1437.9	1466.6	1492.6	1518.7	17.5°
20°	1212.1	1223.1	1227.3	1254.6	1282.0	1317.5	1353.1	1394.1	1443.4	1492.6	1543.2	20°
22.5°	1104.0	1116.4	1135.5	1157.4	1186.2	1229.9	1272.3	1336.7	1402.4	1472.1	1551.5	22.5°
25°	983.7	997.4	1013.8	1037.1	1065.8	1112.3	1173.9	1242.3	1323.0	1414.6	1513.2	25°
27.5°	859.2	872.8	886.5	903.0	935.9	985.1	1057.6	1128.7	1217.6	1317.5	1432.4	27.5°
30°	734.7	736.1	744.2	764.8	799.0	863.3	916.7	1005.6	1098.7	1203.9	1336.7	30°
32.5°	597.9	596.5	606.1	623.8	656.7	718.2	783.9	870.2	961.8	1094.5	1231.3	32.5°
35°	476.1	476.1	493.9	511.7	548.6	592.4	649.8	726.5	834.6	957.7	1094.5	35°
37.5°	411.8	421.3	432.3	450.2	478.9	513.1	563.6	630.7	715.5	833.2	959.1	37.5°
40°	391.3	396.8	406.3	422.8	447.4	478.9	515.8	566.4	632.1	726.5	841.5	40°
42.5°	383.1	384.5	389.9	402.3	424.1	455.5	493.9	539.1	588.3	655.3	755.2	42.5°
45°	374.9	373.5	376.3	385.8	403.6	439.2	483.0	532.2	581.5	637.5	719.7	45°
47.5°	368.0	368.0	368.0	372.1	388.6	424.1	474.7	532.2	591.1	654.0	734.7	47.5°
50°	348.9	347.5	347.5	350.3	362.6	400.8	461.0	530.9	607.5	689.5	781.2	50°
52.5°	326.9	326.9	328.4	329.7	340.6	379.0	446.0	530.9	626.6	736.1	851.0	52.5°
55°	320.1	321.6	322.9	321.6	329.7	362.6	429.6	522.6	634.8	773.0	926.2	55°
57.5°	314.7	317.4	317.4	316.1	321.6	348.9	413.2	506.2	628.0	786.6	979.6	57.5°
60°	306.4	306.4	306.4	302.4	305.1	329.7	388.6	480.2	606.1	774.4	987.8	60°
62.5°	288.7	288.7	285.9	284.6	283.2	302.4	355.8	441.9	566.4	741.6	967.3	62.5°
63°	284.6	283.2	283.2	279.1	279.1	296.9	348.9	436.5	555.4	733.4	959.1	63°
65°	269.5	269.5	269.5	266.7	265.4	279.1	321.6	398.1	513.1	695.0	918.0	65°
67.5°	253.1	254.5	251.7	250.4	249.0	257.2	290.1	350.3	447.4	614.3	841.5	67.5°
70°	229.8	231.2	231.2	229.8	228.5	234.0	254.5	301.0	370.8	511.7	716.9	70°
72.5°	209.3	212.0	212.0	214.8	214.8	218.9	227.2	250.4	296.9	399.5	563.6	72.5°
75°	187.5	188.8	191.5	194.3	191.5	190.2	191.5	209.3	232.5	295.5	402.3	75°
77.5°	168.3	172.4	172.4	171.0	166.9	164.1	164.1	172.4	191.5	224.4	287.4	77.5°
80°	139.6	146.4	147.8	143.6	139.6	139.6	142.3	147.8	160.1	184.7	217.5	80°
82.5°	112.2	119.1	120.4	121.8	120.4	124.5	124.5	125.9	132.7	151.8	177.8	82.5°
85°	86.2	91.7	95.8	97.1	98.5	99.9	98.5	91.7	95.8	108.1	120.4	85°
87.5°	38.3	39.7	36.9	38.3	36.9	38.3	39.7	32.8	31.5	42.4	43.7	87.5°
90°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	90°



NUMBER: P153191

NUMBER: AVS-E04-LED-E-U-SLL-7050

**DISTRIBUTION (continued):**

330°	335°	340°	345°	350°	355°	360°
1435.1	1435.1	1435.1	1435.1	1435.1	1435.1	1435.1
1420.1	1420.1	1421.5	1418.8	1418.8	1420.1	1416.1
1398.2	1403.7	1403.7	1403.7	1400.9	1403.7	1405.1
1403.7	1407.8	1410.6	1410.6	1409.2	1414.6	1418.8
1410.6	1417.4	1420.1	1420.1	1420.1	1426.9	1436.6
1436.6	1442.0	1446.1	1446.1	1448.9	1457.1	1468.0
1484.5	1491.3	1491.3	1489.9	1498.1	1507.7	1520.0
1537.8	1557.0	1566.5	1565.2	1572.0	1584.4	1598.0
1588.4	1641.8	1665.1	1681.5	1688.3	1704.7	1708.8
1630.8	1719.8	1784.0	1838.8	1864.8	1881.2	1900.3
1615.8	1736.2	1851.1	1963.3	2042.6	2123.3	2157.5
1554.2	1704.7	1855.2	2019.4	2163.0	2306.7	2410.7
1479.0	1659.6	1862.1	2094.6	2321.8	2542.0	2717.1
1392.7	1617.1	1877.1	2164.4	2462.7	2751.3	3004.5
1284.7	1536.4	1840.1	2171.2	2522.9	2873.1	3201.5
1147.9	1426.9	1754.0	2122.0	2525.6	2926.4	3319.1
1011.1	1288.8	1644.5	2050.9	2490.1	2938.8	3393.0
915.3	1165.7	1533.7	1960.5	2432.5	2919.6	3428.6
849.6	1076.7	1435.1	1878.4	2371.0	2885.4	3434.0
844.1	1038.4	1370.9	1818.2	2321.8	2855.3	3434.0
890.7	1059.0	1349.0	1788.2	2301.2	2845.7	3436.8
978.2	1141.0	1388.7	1811.4	2317.6	2858.0	3449.1
1083.5	1265.5	1495.3	1892.1	2387.4	2899.1	3476.5
1179.4	1409.2	1677.3	2048.1	2514.6	3003.1	3553.1
1235.4	1532.3	1870.3	2267.0	2732.2	3209.6	3706.3
1242.3	1600.7	2041.2	2505.1	2996.3	3446.3	3951.2
1236.8	1606.2	2063.1	2550.3	3052.3	3505.2	4036.1
1206.7	1607.6	2124.8	2708.9	3246.6	3752.8	4272.7
1130.1	1563.8	2146.6	2833.4	3491.5	4078.4	4714.6
997.4	1439.3	2082.3	2836.2	3585.9	4260.4	4993.7
801.8	1202.6	1804.6	2580.3	3336.9	4081.1	4921.2
586.9	883.8	1364.0	1998.9	2722.6	3397.1	4215.2
389.9	571.9	919.4	1424.2	1952.3	2444.9	3034.5
268.2	354.3	537.7	856.5	1194.4	1433.8	1933.2
197.0	234.0	298.2	437.8	574.6	707.4	1009.6
123.1	134.1	149.1	216.2	309.2	417.3	629.3
32.8	34.2	31.5	42.4	67.0	64.4	71.2
0.0	0.0	0.0	0.0	0.0	0.0	0.0

(END OF REPORT)