

Scaled data based on original data using
LM-79-08 Approved Method: Electrical and Photometric Measurements of Solid-
State Lighting Products

Test Report Prepared for
Cooper Lighting Solutions
(formerly Eaton)

Brand: STREETWORKS

Report Number: P152036

Luminaire Tested: **AVS-F02-LED-E-U-SL4-HSS-7050**

Issue Date: 3/3/2020

Test Information

Test Method: LM-79-08
Report Number: P152036
REPORT IS SCALED FROM IESNA LM-79-08 TEST DATA (P33728)
Test Lab: INNOVATION CENTER-P3
Issue Date: 3/3/2020
Manufacturer: COOPER LIGHTING SOLUTIONS (FORMERLY EATON)
Product Line: STREETWORKS
Catalog Number: AVS-F02-LED-E-U-SL4-HSS-7050
Description: VISION SITE SMALL LED LUMINAIRE
(2) LIGHTBARS WITH AccuLED OPTICS - TYPE 4 W/ SPILL LIGHT CONTROL AND HOUSE SIDE SHIELD
Light Source: (14) 5000K CCT, 70 CRI LEDs
Ballast/Driver: -

Summary

Lumens per Lamp: N/A
Luminaire Lumens: 3447.3 lumens
Efficiency: N/A
Efficacy: 62.7 lumens/watt
Luminous Opening: Rectangular (W 0.33' x L: 1' x H: 0')
IES Classification: Type IV - Short - Semi-Cutoff
BUG Rating: B0 - U0 - G1


Input Watts (W): 55
Input Voltage (V): NR
Input Current (Ain): NR
Voltage Rise (V): NR
Power Factor: NR
Total Harmonic Distortion (THDi): NR
Frequency (hertz): 60
Stabilization Time: NR
Operation Time: NR
Ambient Temperature (°C): NR
Test Distance: 28.75 FT



REPORT NUMBER: P152036
 CATALOG NUMBER: AVS-F02-LED-E-U-SL4-HSS-7050

Iso-Footcandle Lines of Horizontal Illumination


✕ Max cd
 - - - 1/2 Max cd



Based on 10 foot mounting height. Maximum calculated value = 7.7 fc
 Type IV - Short - Semi-Cutoff

REPORT NUMBER: P152036
CATALOG NUMBER: AVS-F02-LED-E-U-SL4-HSS-7050

Luminous Intensity Polar Plot



— Vertical Plane Through 40-Deg Lateral - - - Horizontal Cone Through 69-Deg Vertical

REPORT NUMBER: P152036

CATALOG NUMBER: AVS-F02-LED-E-U-SL4-HSS-7050


FLUX DISTRIBUTION:

		Downward	Upward	Total
House Side	Lumens	102.7	0.0	102.7
	% Fixture	3.0	0.0	3.0
Street Side	Lumens	3344.6	0.0	3344.6
	% Fixture	97.0	0.0	97.0
Total	Lumens	3447.3	0.0	3447.3
	% Fixture	100.0	0.0	100.0

Coefficient of Utilization

ZONAL LUMENS:

Zone	Lumens	% Fixture
0°-10°	26.8	0.8
10°-20°	92.3	2.7
20°-30°	176.6	5.1
30°-40°	293.6	8.5
40°-50°	397.4	11.5
50°-60°	621.4	18.0
60°-70°	1277.6	37.1
70°-80°	514.1	14.9
80°-90°	47.6	1.4
90°-100°	0.0	0.0
100°-110°	0.0	0.0
110°-120°	0.0	0.0
120°-130°	0.0	0.0
130°-140°	0.0	0.0
140°-150°	0.0	0.0
150°-160°	0.0	0.0
160°-170°	0.0	0.0
170°-180°	0.0	0.0
0°-90°	3447.3	100.0
0°-180°	3447.3	100.0



REPORT NUMBER: P152036


CATALOG NUMBER: AVS-F02-LED-E-U-SL4-HSS-7050

LUMINAIRE CLASSIFICATION SYSTEM LUMEN TABLE AND BUG RATING:

Zone		Lumens	% Fixture	Zone Rating/Lumen Limit		
				B	U	G
FL	(0°-30°)	256.5	7.4			
FM	(30°-60°)	1265.5	36.7			
FH	(60°-80°)	1776.7	51.5			G1/1800
FVH	(80°-90°)	45.8	1.3			G1/100
BL	(0°-30°)	39.0	1.1	B0/110		
BM	(30°-60°)	46.9	1.4	B0/220		
BH	(60°-80°)	15.0	0.4	B0/110		G0/110
BVH	(80°-90°)	1.8	0.1			G0/10
UL	(90°-100°)	0.0	0.0		U0/0	
UH	(100°-180°)	0.0	0.0		U0/0	

BUG Rating: B0-U0-G1

Type IV Short





REPORT NUMBER: P152036

CATALOG NUMBER: AVS-F02-LED-E-U-SL4-HSS-7050

CANDELA DISTRIBUTION (FULL):

	0°	5°	10°	15°	20°	25°	30°	35°	40°	45°	50°
0°	260.3	260.3	260.3	260.3	260.3	260.3	260.3	260.3	260.3	260.3	260.3
2.5°	347.3	343.3	338.9	338.9	333.2	333.2	329.8	320.7	319.6	314.5	309.4
5°	443.3	439.9	434.3	429.2	424.7	416.8	411.1	400.4	388.5	377.2	367.0
7.5°	537.0	535.3	525.2	523.5	516.2	503.2	491.9	476.1	455.8	439.9	421.2
10°	624.0	620.1	617.8	608.2	597.5	583.3	565.8	546.6	522.9	498.0	471.5
12.5°	693.0	690.7	680.5	676.6	665.3	651.1	629.1	604.2	580.5	548.3	517.3
15°	744.2	740.3	733.6	727.4	713.8	701.3	681.0	654.0	625.2	590.2	552.8
17.5°	787.3	779.9	778.1	768.6	754.5	739.8	717.2	692.3	658.4	623.4	582.8
20°	844.8	834.6	831.3	817.1	800.7	780.4	754.5	723.4	687.9	649.4	607.7
22.5°	912.5	905.3	897.9	885.5	864.6	835.8	797.9	764.0	718.9	676.6	631.4
25°	1008.6	1002.4	990.5	973.6	947.6	913.2	867.4	817.7	764.7	710.4	657.3
27.5°	1101.8	1096.2	1087.7	1074.6	1045.3	1007.5	951.0	887.8	820.5	755.0	696.3
30°	1189.3	1184.2	1175.8	1162.8	1136.8	1099.5	1035.6	967.9	884.4	808.1	737.5
32.5°	1283.6	1281.9	1272.3	1253.7	1231.1	1180.8	1111.4	1038.5	953.8	865.7	783.2
35°	1390.4	1377.3	1368.3	1349.6	1311.3	1257.6	1176.3	1096.7	1007.5	917.1	825.1
37.5°	1480.7	1468.3	1457.0	1433.3	1386.4	1318.0	1226.0	1138.4	1046.4	954.4	860.6
40°	1546.7	1540.5	1527.0	1496.0	1443.4	1362.1	1262.7	1167.3	1074.6	982.1	889.4
42.5°	1595.9	1586.3	1571.1	1538.9	1476.7	1384.1	1277.4	1179.2	1087.7	999.0	908.1
45°	1614.0	1606.0	1591.9	1556.9	1489.7	1390.4	1276.8	1175.8	1088.2	1004.0	920.5
47.5°	1603.2	1595.3	1582.9	1550.2	1484.0	1383.0	1266.6	1166.1	1082.6	1005.8	931.8
50°	1567.7	1563.1	1553.6	1525.9	1466.5	1368.9	1257.6	1161.0	1081.5	1014.2	947.6
52.5°	1564.2	1561.5	1549.5	1521.9	1461.5	1364.4	1256.5	1163.8	1091.0	1025.0	958.9
55°	1911.6	1871.5	1781.7	1705.5	1580.1	1431.0	1313.6	1209.6	1131.7	1067.4	1021.0
57.5°	2716.9	2657.0	2539.0	2393.9	2105.8	1822.9	1596.5	1432.6	1351.9	1322.6	1340.1
60°	3094.1	3083.3	3064.8	2995.9	2848.4	2605.1	2334.0	2040.9	1923.4	1913.3	1948.8
62.5°	3273.1	3266.3	3272.0	3263.5	3217.7	3146.6	3068.7	2942.2	2825.8	2750.8	2591.5
65°	3355.5	3360.1	3392.2	3417.6	3423.3	3442.0	3499.0	3656.6	3771.7	3578.0	3135.9
67.5°	3146.0	3172.5	3246.5	3339.2	3447.6	3552.6	3722.1	4054.1	4290.7	4063.1	3435.1
69°	2604.5	2617.5	2798.1	2972.6	3237.5	3422.8	3668.4	4103.8	4369.7	4112.8	3411.5
70°	2050.5	2062.4	2256.1	2493.3	2941.0	3179.4	3500.7	4019.7	4295.8	4046.7	3289.4
72.5°	925.0	908.1	976.4	1103.4	1590.3	1968.6	2530.5	3256.7	3544.1	3242.1	2461.0
75°	646.0	638.7	646.0	646.6	722.3	931.8	1175.8	1765.3	2183.2	1883.9	1175.8
77.5°	500.3	495.2	490.2	484.6	493.6	552.8	576.6	626.3	813.2	769.1	448.4
80°	395.9	391.4	403.7	399.8	399.8	406.6	402.1	383.4	348.4	323.0	289.1
82.5°	184.1	185.2	185.2	201.0	242.3	282.9	296.0	277.3	246.2	209.5	168.8
85°	17.5	19.8	33.4	51.4	102.2	115.2	115.8	96.0	96.0	75.6	61.0
87.5°	0.0	0.5	0.5	0.5	5.1	14.1	11.8	3.4	1.7	1.7	2.8
90°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0



REPORT NUMBER: P152036

CATALOG NUMBER: AVS-F02-LED-E-U-SL4-HSS-7050

CANDELA DISTRIBUTION (continued):

	55°	60°	65°	70°	75°	80°	85°	90°	95°	100°	105°
0°	260.3	260.3	260.3	260.3	260.3	260.3	260.3	260.3	260.3	260.3	260.3
2.5°	300.4	298.8	291.9	285.2	279.0	272.2	266.0	259.8	253.0	247.9	241.7
5°	351.3	338.9	324.7	311.2	297.6	283.5	268.8	255.9	242.3	229.8	218.0
7.5°	402.7	378.3	359.2	334.9	312.8	290.9	270.5	249.6	230.4	212.3	195.4
10°	446.1	416.8	386.8	355.8	324.1	294.8	266.5	241.7	216.3	194.3	173.4
12.5°	481.7	444.5	407.8	368.8	333.2	296.0	260.9	231.0	201.0	176.2	154.7
15°	513.9	471.0	426.9	381.8	336.6	294.2	255.2	218.0	187.5	159.3	134.9
17.5°	539.9	490.8	441.0	390.3	341.7	291.9	247.9	208.9	173.4	144.0	120.3
20°	562.5	511.1	457.4	400.4	345.1	291.4	241.7	197.6	160.9	129.8	106.7
22.5°	583.3	531.9	474.4	413.4	350.2	290.9	236.1	189.2	150.3	119.2	96.0
25°	607.0	552.8	492.4	426.9	359.2	293.1	232.6	182.4	140.6	109.0	87.6
27.5°	633.6	576.6	513.9	443.8	371.0	297.6	231.5	175.0	132.1	99.4	80.7
30°	670.9	604.8	535.3	460.8	381.8	302.7	230.4	170.6	123.6	92.0	74.0
32.5°	703.6	632.4	559.1	478.3	393.6	307.8	229.8	164.4	115.8	84.7	68.9
35°	738.1	657.9	579.4	495.2	403.7	313.4	229.3	159.8	108.4	77.4	63.8
37.5°	768.0	679.4	595.2	509.9	415.0	318.5	229.8	155.9	101.7	71.2	59.3
40°	793.5	701.3	612.7	523.5	426.9	326.4	230.4	151.9	94.9	65.5	55.3
42.5°	816.1	722.3	631.4	538.8	440.5	335.4	233.8	148.5	89.2	60.4	51.4
45°	833.5	741.5	651.7	560.2	462.5	350.2	240.0	146.2	83.6	56.0	48.0
47.5°	851.6	769.7	686.1	594.1	494.7	373.3	250.8	145.7	79.1	52.5	45.2
50°	876.5	797.9	716.6	628.5	524.0	397.0	263.7	146.2	73.4	49.1	42.4
52.5°	894.5	826.7	756.2	688.4	594.1	469.3	314.0	156.5	70.6	46.3	39.0
55°	1001.2	989.4	991.1	1002.4	929.5	798.5	525.2	225.9	83.0	52.5	38.4
57.5°	1411.8	1453.6	1477.8	1477.3	1357.0	1125.5	705.3	290.3	92.6	61.0	45.7
60°	1951.7	1920.0	1875.4	1765.3	1605.5	1284.8	788.9	312.3	80.2	48.6	41.8
62.5°	2428.8	2243.6	2079.3	1900.8	1691.3	1340.1	805.8	310.6	70.1	36.7	29.3
65°	2726.4	2393.3	2127.9	1904.2	1657.4	1293.8	762.4	285.2	59.3	29.9	24.2
67.5°	2797.6	2312.5	1937.0	1651.8	1384.7	1006.8	559.6	214.6	46.3	24.9	21.5
69°	2642.3	2055.5	1605.0	1281.3	1007.5	668.1	346.2	135.5	35.5	22.6	19.8
70°	2430.6	1787.9	1307.4	1028.4	746.0	469.3	242.3	95.4	28.8	20.9	18.0
72.5°	1563.7	939.2	642.7	447.3	307.8	186.9	94.9	42.9	22.1	17.5	14.7
75°	606.5	347.3	251.8	191.4	149.6	103.9	57.6	27.7	18.7	14.7	11.3
77.5°	298.8	228.7	186.9	128.2	74.5	46.3	31.1	21.5	15.2	10.8	7.4
80°	236.1	157.0	93.8	58.1	44.0	33.4	23.7	17.5	11.3	6.7	5.1
82.5°	120.8	66.1	48.6	39.5	32.7	26.0	19.2	12.4	7.4	4.6	3.9
85°	37.8	27.7	24.9	24.2	22.6	18.7	13.6	7.9	4.6	2.8	2.8
87.5°	2.8	3.9	5.1	3.9	4.6	3.9	5.1	3.4	2.3	2.3	1.7
90°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0



REPORT NUMBER: P152036

CATALOG NUMBER: AVS-F02-LED-E-U-SL4-HSS-7050

CANDELA DISTRIBUTION (continued):

	110°	115°	120°	125°	130°	135°	140°	145°	150°	155°	160°
0°	260.3	260.3	260.3	260.3	260.3	260.3	260.3	260.3	260.3	260.3	260.3
2.5°	237.2	230.4	224.1	220.2	212.8	210.1	207.3	206.1	201.0	202.2	197.6
5°	207.3	195.4	186.3	177.3	168.8	162.6	157.5	151.3	146.2	144.0	139.5
7.5°	180.1	164.9	153.1	143.4	133.3	125.4	118.5	114.1	109.5	105.1	102.8
10°	156.5	140.0	126.5	116.9	107.3	100.5	95.4	92.0	89.2	87.6	86.9
12.5°	134.4	118.5	106.2	97.7	90.4	86.9	84.7	83.0	82.5	81.9	81.9
15°	117.5	101.7	92.0	85.8	82.5	80.7	80.2	79.1	77.9	77.4	77.4
17.5°	101.7	89.7	83.0	79.6	77.9	76.8	75.6	74.5	73.4	72.8	72.8
20°	90.9	81.3	77.9	75.6	74.0	72.8	71.2	70.1	69.4	68.9	68.3
22.5°	82.5	76.3	74.0	72.3	70.1	68.3	67.2	66.1	65.0	64.4	63.8
25°	76.3	72.3	70.6	68.3	66.1	64.4	62.7	61.0	59.9	59.3	58.1
27.5°	71.7	68.9	66.6	63.8	61.6	59.9	58.1	56.5	55.3	54.2	53.7
30°	67.8	65.0	62.1	59.9	57.0	55.3	53.1	51.4	50.8	49.7	48.6
32.5°	63.8	61.0	58.1	55.3	52.5	50.3	49.1	46.8	45.7	45.2	44.0
35°	59.3	56.5	53.1	50.8	48.0	45.7	44.0	42.4	41.2	40.1	39.5
37.5°	55.3	51.9	48.6	45.7	43.5	41.2	39.5	37.8	36.7	35.5	35.0
40°	50.8	47.5	44.0	41.2	39.0	37.3	35.5	33.9	32.7	32.2	32.2
42.5°	46.8	42.9	39.5	37.3	35.5	33.4	31.6	29.9	29.3	28.8	29.3
45°	42.9	39.0	36.2	33.9	32.2	29.9	28.2	27.2	26.5	27.2	27.7
47.5°	39.5	35.5	32.7	31.1	29.3	27.7	26.0	24.9	24.9	26.0	27.2
50°	36.2	32.2	29.9	28.8	27.2	25.4	23.1	22.6	23.1	24.2	25.4
52.5°	32.7	28.2	26.5	26.0	24.2	22.6	20.9	20.3	20.9	22.1	21.5
55°	29.3	24.9	24.2	23.7	22.1	19.8	18.0	18.0	18.0	17.5	16.4
57.5°	28.2	22.1	21.5	20.9	19.2	16.9	15.9	14.7	14.1	12.4	11.8
60°	29.3	19.8	19.8	18.7	16.9	14.7	13.0	11.3	10.2	9.0	9.0
62.5°	23.7	18.0	17.5	16.4	14.1	11.8	10.2	8.5	7.9	7.4	7.4
65°	19.2	16.4	15.2	13.6	11.8	9.6	7.9	6.7	6.2	6.2	6.7
67.5°	17.5	14.7	13.0	11.3	9.6	7.4	6.2	5.6	5.6	6.2	6.2
69°	16.4	13.6	11.8	10.2	8.5	6.7	5.6	5.6	5.6	5.6	6.2
70°	15.2	13.0	11.3	9.6	7.4	5.6	5.1	5.1	5.6	5.6	6.2
72.5°	11.8	10.2	9.6	7.9	5.6	5.1	4.6	5.1	5.1	5.6	5.6
75°	9.0	7.4	7.4	6.2	4.6	3.9	3.9	4.6	4.6	5.1	5.1
77.5°	6.2	5.1	5.1	4.6	3.9	3.4	3.4	3.9	4.6	4.6	5.1
80°	4.6	3.9	3.4	3.9	3.4	2.8	3.4	3.9	3.9	4.6	4.6
82.5°	3.4	3.4	3.4	3.4	2.8	2.8	3.4	3.4	3.9	4.6	4.6
85°	2.8	2.8	2.8	2.8	2.8	2.8	2.8	3.4	3.4	3.9	3.9
87.5°	1.7	1.7	1.7	2.3	2.3	2.8	2.8	2.8	2.8	3.4	3.4
90°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0



REPORT NUMBER: P152036

CATALOG NUMBER: AVS-F02-LED-E-U-SL4-HSS-7050

CANDELA DISTRIBUTION (continued):

	165°	170°	175°	180°
0°	260.3	260.3	260.3	260.3
2.5°	196.5	196.0	193.7	194.3
5°	137.8	134.4	136.7	136.1
7.5°	101.0	100.5	100.0	101.0
10°	86.4	86.4	85.8	86.4
12.5°	81.3	81.3	81.3	81.3
15°	77.4	77.4	76.8	76.8
17.5°	72.8	72.8	72.8	72.3
20°	68.3	67.8	67.8	67.8
22.5°	63.2	62.7	62.7	62.7
25°	58.1	57.6	57.6	57.6
27.5°	53.1	52.5	51.9	51.9
30°	48.0	47.5	46.8	46.8
32.5°	42.9	42.4	41.8	41.8
35°	38.4	38.4	37.8	37.3
37.5°	34.4	34.4	34.4	34.4
40°	31.6	32.2	32.2	32.2
42.5°	29.9	30.5	31.1	31.6
45°	28.8	29.9	30.5	30.5
47.5°	28.2	28.8	29.3	29.3
50°	26.0	25.4	25.4	25.4
52.5°	20.9	19.8	19.2	18.7
55°	15.2	14.7	13.6	13.6
57.5°	10.8	10.8	10.2	10.2
60°	8.5	8.5	7.9	8.5
62.5°	7.4	7.4	7.4	7.4
65°	6.7	6.7	6.7	6.7
67.5°	6.7	6.7	6.7	6.7
69°	6.2	6.2	6.2	6.2
70°	6.2	6.2	6.2	6.2
72.5°	5.6	5.6	5.6	5.6
75°	5.1	5.6	5.6	5.6
77.5°	5.1	5.1	5.1	5.1
80°	4.6	4.6	5.1	5.1
82.5°	4.6	4.6	4.6	4.6
85°	3.9	3.9	4.6	4.6
87.5°	3.4	3.4	3.9	3.9
90°	0.0	0.0	0.0	0.0

(END OF REPORT)