

Scaled data based on original data using
LM-79-08 Approved Method: Electrical and Photometric Measurements of Solid-
State Lighting Products

Test Report Prepared for
Cooper Lighting Solutions
(formerly Eaton)

Brand: STREETWORKS

Report Number: P156866

Luminaire Tested: **AVS-F02-LED-E-U-T4-7050**

Issue Date: 3/3/2020

Test Information

Test Method: LM-79-08
Report Number: P156866
REPORT IS SCALED FROM IESNA LM-79-08 TEST DATA (P33673)
Test Lab: INNOVATION CENTER-P3
Issue Date: 3/3/2020
Manufacturer: COOPER LIGHTING SOLUTIONS (FORMERLY EATON)
Product Line: STREETWORKS
Catalog Number: AVS-F02-LED-E-U-T4-7050
Description: VISION SITE SMALL LED LUMINAIRE
(2) LIGHTBARS WITH AccuLED OPTICS - TYPE 4 SHORT
Light Source: (14) 5000K CCT, 70 CRI LEDs
Ballast/Driver: -

Summary

Lumens per Lamp: N/A
Luminaire Lumens: 5119.8 lumens
Efficiency: N/A
Efficacy: 93.1 lumens/watt
Luminous Opening: Rectangular (W 0.33' x L: 1' x H: 0')
IES Classification: Type IV - Short - Semi-Cutoff
BUG Rating: B1 - U0 - G2

Input Watts (W): 55
Input Voltage (V): NR
Input Current (Ain): NR
Voltage Rise (V): NR
Power Factor: NR
Total Harmonic Distortion (THDi): NR
Frequency (hertz): 60
Stabilization Time: NR
Operation Time: NR
Ambient Temperature (°C): NR
Test Distance: 28.75 FT




REPORT NUMBER: P156866

CATALOG NUMBER: AVS-F02-LED-E-U-T4-7050

Iso-Footcandle Lines of Horizontal Illumination

✕ Max cd
 - - - 1/2 Max cd




Based on 10 foot mounting height. Maximum calculated value = 7.1 fc
 Type IV - Short - Semi-Cutoff

REPORT NUMBER: P156866

CATALOG NUMBER: AVS-F02-LED-E-U-T4-7050

Luminous Intensity Polar Plot



— Vertical Plane Through 47.5-Deg Lateral - - - Horizontal Cone Through 66-Deg Vertical

REPORT NUMBER: P156866

CATALOG NUMBER: AVS-F02-LED-E-U-T4-7050

FLUX DISTRIBUTION:

		Downward	Upward	Total
House Side	Lumens	1092.4	0.0	1092.4
	% Fixture	21.3	0.0	21.3
Street Side	Lumens	4027.4	0.0	4027.4
	% Fixture	78.7	0.0	78.7
Total	Lumens	5119.8	0.0	5119.8
	% Fixture	100.0	0.0	100.0

ZONAL LUMENS:

Zone	Lumens	% Fixture
0°-10°	65.5	1.3
10°-20°	199.0	3.9
20°-30°	342.7	6.7
30°-40°	518.5	10.1
40°-50°	672.0	13.1
50°-60°	926.5	18.1
60°-70°	1439.5	28.1
70°-80°	837.1	16.3
80°-90°	119.0	2.3
90°-100°	0.0	0.0
100°-110°	0.0	0.0
110°-120°	0.0	0.0
120°-130°	0.0	0.0
130°-140°	0.0	0.0
140°-150°	0.0	0.0
150°-160°	0.0	0.0
160°-170°	0.0	0.0
170°-180°	0.0	0.0
0°-90°	5119.8	100.0
0°-180°	5119.8	100.0

Coefficient of Utilization



REPORT NUMBER: P156866


CATALOG NUMBER: AVS-F02-LED-E-U-T4-7050

LUMINAIRE CLASSIFICATION SYSTEM LUMEN TABLE AND BUG RATING:

Zone		Lumens	% Fixture	Zone Rating/Lumen Limit		
				B	U	G
FL	(0°-30°)	314.8	6.1			
FM	(30°-60°)	1643.5	32.1			
FH	(60°-80°)	1977.8	38.6			G2/5000
FVH	(80°-90°)	91.3	1.8			G1/100
BL	(0°-30°)	292.4	5.7	B1/500		
BM	(30°-60°)	473.6	9.2	B1/1000		
BH	(60°-80°)	298.8	5.8	B1/500		G1/500
BVH	(80°-90°)	27.7	0.5			G1/100
UL	(90°-100°)	0.0	0.0		U0/0	
UH	(100°-180°)	0.0	0.0		U0/0	

BUG Rating: B1-U0-G2

Type IV Short





REPORT NUMBER: P156866

CATALOG NUMBER: AVS-F02-LED-E-U-T4-7050

CANDELA DISTRIBUTION (FULL):

	0°	5°	10°	15°	20°	25°	30°	35°	40°	45°	47.5°
0°	674.8	674.8	674.8	674.8	674.8	674.8	674.8	674.8	674.8	674.8	674.8
2.5°	662.4	664.7	663.0	663.5	663.5	664.1	664.1	664.7	664.1	665.8	666.9
5°	650.6	651.7	651.1	652.2	653.4	655.6	655.0	657.9	658.4	660.1	663.0
7.5°	646.0	644.9	645.5	647.2	648.3	649.4	650.6	652.8	654.5	658.4	660.7
10°	650.6	649.9	650.6	651.7	651.7	652.2	651.1	653.4	654.5	657.9	660.1
12.5°	669.2	669.2	668.1	668.1	666.9	665.8	663.0	661.2	660.7	661.2	662.4
15°	699.2	698.0	695.8	694.0	691.8	687.9	683.8	680.5	678.2	674.8	673.7
17.5°	728.5	726.8	724.6	722.3	719.5	715.5	709.3	705.3	699.2	695.1	693.0
20°	762.4	759.0	756.2	753.4	747.7	746.5	740.3	733.6	726.2	717.2	716.1
22.5°	806.4	800.7	797.4	795.6	790.1	788.4	778.1	768.6	759.6	747.7	744.9
25°	851.0	845.4	843.7	841.5	837.5	835.2	825.6	814.9	803.0	786.6	783.2
27.5°	894.5	895.0	890.6	892.2	891.1	887.2	877.6	866.8	857.8	838.7	834.6
30°	948.7	945.3	943.1	946.4	942.5	943.1	934.6	928.9	914.3	903.0	895.0
32.5°	1005.2	1004.7	1008.0	1010.3	1009.7	1008.6	1001.8	996.2	983.2	966.8	963.4
35°	1082.6	1085.9	1088.8	1099.0	1099.0	1106.3	1099.5	1092.7	1077.5	1057.7	1051.0
37.5°	1135.1	1136.2	1147.5	1161.0	1178.0	1193.8	1198.3	1200.0	1193.8	1179.2	1169.0
40°	1183.1	1185.4	1203.4	1224.4	1249.1	1280.2	1298.9	1307.4	1309.0	1302.3	1280.2
42.5°	1231.1	1234.5	1253.1	1283.6	1318.0	1357.6	1390.4	1411.2	1423.1	1423.1	1410.1
45°	1286.9	1291.5	1311.8	1345.2	1385.3	1434.9	1480.1	1520.2	1539.4	1540.5	1528.1
47.5°	1353.1	1357.0	1380.7	1414.6	1455.9	1506.1	1563.1	1608.9	1644.5	1646.7	1636.6
50°	1438.3	1443.9	1463.7	1494.2	1536.6	1587.5	1644.5	1708.3	1745.5	1754.6	1743.8
52.5°	1551.3	1552.4	1568.8	1597.0	1638.2	1686.8	1747.3	1816.7	1865.8	1873.2	1855.6
55°	1707.2	1705.5	1716.2	1746.6	1777.7	1815.5	1878.2	1956.2	2011.0	2022.3	2004.1
57.5°	1918.9	1917.2	1926.2	1933.6	1991.7	2028.5	2090.1	2164.6	2217.6	2250.4	2219.4
60°	2247.0	2245.3	2260.0	2302.9	2346.4	2400.0	2459.9	2549.1	2623.6	2633.3	2602.8
62.5°	2484.8	2493.3	2525.4	2575.6	2663.7	2768.8	2878.3	2995.9	3148.9	3197.4	3182.7
65°	2401.8	2418.7	2463.3	2539.5	2657.0	2802.2	2973.8	3186.7	3391.7	3506.3	3502.9
66°	2327.2	2345.8	2400.6	2474.0	2598.2	2757.0	2944.5	3176.6	3405.8	3532.3	3540.2
67.5°	2191.7	2212.5	2266.2	2353.2	2474.0	2642.9	2844.5	3096.9	3356.1	3503.5	3524.4
70°	1928.0	1951.7	1990.7	2062.4	2181.5	2332.3	2544.7	2770.5	3042.2	3211.0	3236.4
72.5°	1611.7	1632.6	1676.1	1734.8	1832.5	1927.4	2094.0	2260.5	2454.8	2647.4	2628.8
75°	1157.1	1166.1	1192.1	1256.0	1308.5	1393.7	1527.6	1664.2	1796.9	1885.0	1897.4
77.5°	601.5	625.2	661.9	732.4	789.4	866.3	953.3	1056.1	1153.2	1233.9	1211.9
80°	393.6	403.7	436.5	472.6	514.5	563.6	621.8	660.1	672.5	667.5	672.5
82.5°	227.0	245.7	289.1	316.8	347.9	364.8	411.1	455.1	480.0	448.9	437.6
85°	28.8	37.3	117.5	148.0	169.4	194.8	208.9	235.4	219.7	196.5	239.5
87.5°	6.2	5.6	7.9	16.9	17.5	14.7	27.7	29.3	18.0	9.0	11.3
90°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0



REPORT NUMBER: P156866

CATALOG NUMBER: AVS-F02-LED-E-U-T4-7050

CANDELA DISTRIBUTION (continued):

	50°	55°	60°	65°	70°	75°	80°	85°	90°	95°	100°
0°	674.8	674.8	674.8	674.8	674.8	674.8	674.8	674.8	674.8	674.8	674.8
2.5°	668.1	668.6	669.7	671.4	672.5	673.7	674.8	676.6	677.6	678.8	681.0
5°	665.3	667.5	669.7	672.0	674.8	679.4	682.2	684.5	686.7	691.2	693.0
7.5°	663.5	667.5	670.9	674.8	679.4	683.3	688.4	691.2	694.6	697.4	700.8
10°	662.4	668.1	671.4	677.1	682.2	686.1	691.8	695.1	699.2	702.5	704.2
12.5°	664.7	667.5	670.9	676.6	682.7	688.4	694.6	697.4	700.8	703.6	704.2
15°	674.3	674.3	674.8	679.4	685.6	690.1	695.1	698.0	699.7	701.3	701.3
17.5°	691.8	687.9	685.0	685.6	689.5	692.3	695.1	695.1	694.0	693.5	692.3
20°	712.1	707.0	701.3	697.4	696.3	694.0	692.3	686.7	682.2	678.2	675.4
22.5°	741.5	733.6	725.7	718.3	711.5	703.1	693.5	682.2	671.4	664.1	659.6
25°	777.6	771.4	761.8	750.5	742.1	726.2	713.8	697.4	683.8	674.3	666.3
27.5°	829.0	821.7	812.6	802.5	790.1	772.5	757.3	738.1	721.7	707.6	697.4
30°	892.8	883.2	876.5	864.0	855.5	835.8	820.5	796.8	765.2	742.6	728.5
32.5°	958.3	947.6	942.0	932.3	922.8	910.9	887.8	851.0	810.4	773.7	749.4
35°	1045.9	1034.6	1024.4	1016.0	1001.8	979.8	959.5	915.4	859.5	808.1	767.5
37.5°	1156.0	1137.3	1111.9	1090.5	1065.6	1034.0	1002.9	957.7	894.0	827.4	773.1
40°	1273.5	1240.7	1204.6	1164.5	1121.6	1075.8	1040.2	994.5	922.8	843.7	769.1
42.5°	1396.0	1344.0	1293.8	1237.3	1177.4	1123.2	1076.9	1026.6	944.2	848.2	753.4
45°	1517.4	1459.3	1383.0	1309.0	1233.4	1166.1	1114.2	1057.7	963.9	849.9	732.4
47.5°	1617.9	1558.0	1471.1	1378.4	1288.7	1212.4	1151.5	1090.5	990.5	861.8	727.4
50°	1724.0	1651.2	1554.7	1445.1	1343.4	1258.2	1193.3	1129.9	1027.8	892.2	743.7
52.5°	1839.9	1756.3	1643.3	1520.8	1409.5	1314.1	1243.5	1178.5	1075.2	935.1	774.8
55°	1981.0	1878.9	1756.3	1617.9	1498.8	1393.2	1315.2	1238.4	1131.7	986.0	813.8
57.5°	2196.8	2071.4	1933.6	1776.1	1643.9	1519.1	1425.9	1337.2	1219.3	1061.7	866.8
60°	2586.9	2453.2	2274.1	2083.2	1928.0	1782.3	1645.6	1535.4	1390.4	1210.8	984.4
62.5°	3146.0	2968.2	2729.3	2462.2	2258.9	2048.8	1894.6	1730.9	1550.7	1357.0	1122.7
65°	3456.7	3240.9	2921.2	2611.3	2349.7	2121.7	1925.7	1736.0	1536.1	1350.8	1154.8
66°	3495.0	3270.3	2938.2	2611.8	2337.4	2103.0	1896.9	1700.4	1496.0	1319.2	1141.2
67.5°	3479.2	3249.4	2907.2	2562.7	2283.7	2031.8	1819.0	1615.1	1411.2	1246.3	1096.2
70°	3220.0	3002.1	2666.0	2332.3	2067.5	1819.0	1615.6	1415.1	1228.3	1087.0	976.4
72.5°	2673.9	2487.6	2195.6	1933.6	1725.8	1520.8	1348.5	1157.1	999.0	894.5	829.0
75°	1930.2	1817.3	1551.3	1401.0	1218.7	1082.6	915.4	801.9	688.4	637.6	626.3
77.5°	1219.3	1067.4	898.4	739.8	608.2	504.2	392.4	333.2	277.8	272.2	328.7
80°	617.2	555.6	428.1	341.1	286.8	232.1	183.5	139.0	97.1	116.9	140.0
82.5°	404.4	337.1	264.2	217.4	189.2	157.0	122.0	84.7	62.1	70.1	96.0
85°	218.5	186.3	150.3	118.5	96.0	85.8	57.6	40.6	40.1	42.9	54.8
87.5°	15.9	15.9	12.4	11.3	13.6	11.3	10.2	10.2	9.6	10.2	13.6
90°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0



REPORT NUMBER: P156866

CATALOG NUMBER: AVS-F02-LED-E-U-T4-7050

CANDELA DISTRIBUTION (continued):

	105°	110°	115°	120°	125°	130°	135°	140°	145°	150°	155°
0°	674.8	674.8	674.8	674.8	674.8	674.8	674.8	674.8	674.8	674.8	674.8
2.5°	682.2	683.8	684.5	687.3	688.9	690.1	691.2	691.2	691.8	693.5	694.0
5°	695.1	698.0	701.3	703.6	704.8	708.2	709.3	709.3	710.4	712.6	714.4
7.5°	703.1	707.0	710.4	711.5	713.8	714.9	716.6	717.7	717.7	720.0	721.1
10°	705.9	708.2	711.5	711.5	713.8	713.8	715.5	716.1	716.1	718.3	720.0
12.5°	705.9	707.0	709.8	709.8	711.5	712.1	714.4	716.1	716.6	719.5	721.7
15°	702.5	703.6	705.9	706.4	710.4	712.6	717.7	721.1	721.1	723.9	725.1
17.5°	693.0	695.8	700.2	704.8	712.1	717.2	723.4	726.2	723.9	722.3	720.6
20°	677.1	682.2	693.0	704.2	717.2	723.9	727.4	724.6	716.6	708.7	703.6
22.5°	661.2	671.4	689.5	706.4	721.1	725.7	723.9	713.8	700.8	691.2	684.5
25°	668.6	680.5	698.0	713.3	722.8	721.7	714.9	700.8	686.7	674.3	663.0
27.5°	699.2	712.1	721.7	726.8	725.7	717.7	707.0	691.2	674.3	657.9	642.1
30°	727.9	734.7	737.0	733.0	723.9	711.0	697.4	679.4	656.8	636.5	618.3
32.5°	740.9	734.1	723.4	712.6	698.0	686.7	668.1	648.3	620.1	595.8	577.7
35°	740.9	713.8	686.7	664.1	642.1	628.0	606.5	580.0	554.0	533.7	519.6
37.5°	724.6	672.5	628.0	591.3	563.6	548.3	516.2	492.4	470.4	463.6	454.6
40°	694.6	617.8	553.5	505.4	470.4	447.8	415.6	399.3	390.8	387.4	385.7
42.5°	654.5	556.8	471.0	411.7	373.9	348.4	326.9	316.8	316.3	315.6	315.6
45°	611.6	491.3	390.8	320.2	286.8	264.2	254.1	250.2	253.6	253.0	253.6
47.5°	585.1	441.7	317.4	242.3	216.9	202.2	197.1	198.8	201.6	200.5	200.5
50°	581.7	416.2	268.3	188.6	169.4	162.1	160.9	160.9	162.6	161.6	160.9
52.5°	594.1	412.2	242.8	162.1	146.8	140.6	139.5	139.0	138.3	134.9	132.1
55°	615.5	421.2	235.4	155.3	139.5	132.7	131.0	129.8	127.7	123.1	118.0
57.5°	658.4	449.5	242.3	158.7	141.8	136.1	134.4	134.4	129.8	122.6	115.2
60°	761.8	521.2	269.9	171.7	152.4	146.8	148.0	147.4	140.6	129.8	118.5
62.5°	895.0	615.0	306.1	189.7	166.0	164.9	170.6	169.4	158.1	141.8	125.4
65°	956.6	659.1	316.3	193.7	168.8	173.9	185.2	184.1	169.9	147.4	126.5
66°	957.7	659.1	311.7	190.3	164.9	171.1	182.4	181.9	167.8	145.2	124.2
67.5°	934.6	640.9	298.8	183.5	157.0	161.6	171.7	171.1	158.1	139.5	119.7
70°	847.7	573.8	265.4	171.7	146.2	144.0	147.4	145.2	136.7	123.6	110.2
72.5°	726.2	481.7	231.5	162.6	139.0	129.8	127.7	125.9	119.2	111.8	103.3
75°	572.0	381.1	203.3	155.9	132.1	120.3	116.4	114.1	109.5	104.5	97.7
77.5°	353.0	272.7	177.3	146.8	127.0	115.2	112.3	109.0	102.2	96.0	90.9
80°	157.5	168.8	145.7	128.2	113.5	102.8	98.2	93.2	86.4	82.5	79.6
82.5°	105.1	109.0	105.6	96.0	85.8	77.4	70.6	70.6	69.4	66.1	65.0
85°	67.2	67.8	65.5	59.3	55.3	50.3	47.5	48.0	50.3	49.7	49.1
87.5°	15.2	15.2	18.0	16.9	19.8	20.9	22.6	24.2	27.7	27.7	29.3
90°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0



REPORT NUMBER: P156866

CATALOG NUMBER: AVS-F02-LED-E-U-T4-7050

CANDELA DISTRIBUTION (continued):

	160°	165°	170°	175°	180°
0°	674.8	674.8	674.8	674.8	674.8
2.5°	694.6	695.8	696.9	695.1	695.8
5°	714.4	713.8	716.6	714.9	716.1
7.5°	720.6	721.1	723.4	723.4	723.9
10°	721.1	722.3	725.1	726.8	727.9
12.5°	723.9	726.2	730.8	731.9	731.9
15°	726.2	727.4	730.2	731.3	732.4
17.5°	718.3	716.1	717.2	717.7	717.2
20°	698.5	696.3	695.8	693.5	694.6
22.5°	677.1	670.9	666.9	662.4	662.4
25°	651.1	641.6	633.6	625.7	627.4
27.5°	626.8	614.4	606.5	601.5	600.3
30°	603.1	590.2	582.8	576.6	576.6
32.5°	563.6	554.5	545.0	541.0	540.4
35°	508.8	503.2	495.2	493.6	490.8
37.5°	447.3	445.6	438.8	438.2	435.4
40°	382.9	384.0	381.8	380.6	379.0
42.5°	318.5	324.1	323.0	322.5	321.3
45°	257.0	260.9	261.5	263.1	266.0
47.5°	202.2	203.3	204.5	203.8	204.5
50°	158.1	155.3	154.7	153.1	154.7
52.5°	127.7	123.1	120.8	118.5	117.5
55°	112.3	107.9	105.6	104.5	103.3
57.5°	108.4	103.9	100.5	98.2	97.7
60°	109.5	102.8	98.2	95.4	94.9
62.5°	112.3	103.3	97.1	94.3	93.8
65°	111.8	102.2	96.6	93.2	92.6
66°	110.2	101.0	95.4	92.6	92.0
67.5°	107.3	99.4	94.3	92.0	90.9
70°	102.2	97.1	93.2	90.4	89.2
72.5°	97.7	93.8	90.4	87.6	86.9
75°	92.6	89.2	85.8	83.6	83.0
77.5°	86.4	83.0	80.7	79.1	78.4
80°	76.3	74.0	71.7	69.4	69.4
82.5°	63.2	61.6	59.3	57.6	57.0
85°	48.6	48.6	46.8	45.2	44.7
87.5°	28.8	28.2	28.2	26.5	26.5
90°	0.0	0.0	0.0	0.0	0.0

(END OF REPORT)