

Scaled data based on original data using
LM-79-08 Approved Method: Electrical and Photometric Measurements of Solid-
State Lighting Products

Test Report Prepared for
Cooper Lighting Solutions
(formerly Eaton)

Brand: STREETWORKS

Report Number: P152056

Luminaire Tested: **AVS-F04-LED-E-U-SL4-HSS-7050**

Issue Date: 3/3/2020

Test Information

Test Method: LM-79-08
Report Number: P152056
REPORT IS SCALED FROM IESNA LM-79-08 TEST DATA (P33728)
Test Lab: INNOVATION CENTER-P3
Issue Date: 3/3/2020
Manufacturer: COOPER LIGHTING SOLUTIONS (FORMERLY EATON)
Product Line: STREETWORKS
Catalog Number: AVS-F04-LED-E-U-SL4-HSS-7050
Description: VISION SITE SMALL LED LUMINAIRE
(4) LIGHTBARS WITH AccuLED OPTICS - TYPE 4 W/ SPILL LIGHT CONTROL AND HOUSE SIDE SHIELD
Light Source: (28) 5000K CCT, 70 CRI LEDs
Ballast/Driver: -

Summary

Lumens per Lamp: N/A
Luminaire Lumens: 6894.5 lumens
Efficiency: N/A
Efficacy: 67.5 lumens/watt
Luminous Opening: Rectangular (W 0.67' x L: 1' x H: 0')
IES Classification: Type IV - Short - Semi-Cutoff
BUG Rating: B0 - U0 - G2


Input Watts (W): 102.2
Input Voltage (V): NR
Input Current (Ain): NR
Voltage Rise (V): NR
Power Factor: NR
Total Harmonic Distortion (THDi): NR
Frequency (hertz): 60
Stabilization Time: NR
Operation Time: NR
Ambient Temperature (°C): NR
Test Distance: 28.75 FT



REPORT NUMBER: P152056
 CATALOG NUMBER: AVS-F04-LED-E-U-SL4-HSS-7050

Iso-Footcandle Lines of Horizontal Illumination


✕ Max cd
 - - - 1/2 Max cd



Based on 10 foot mounting height. Maximum calculated value = 15.4 fc
 Type IV - Short - Semi-Cutoff

REPORT NUMBER: P152056
CATALOG NUMBER: AVS-F04-LED-E-U-SL4-HSS-7050

Luminous Intensity Polar Plot



— Vertical Plane Through 40-Deg Lateral - - - Horizontal Cone Through 69-Deg Vertical

REPORT NUMBER: P152056

CATALOG NUMBER: AVS-F04-LED-E-U-SL4-HSS-7050


FLUX DISTRIBUTION:

		Downward	Upward	Total
House Side	Lumens	205.3	0.0	205.3
	% Fixture	3.0	0.0	3.0
Street Side	Lumens	6689.2	0.0	6689.2
	% Fixture	97.0	0.0	97.0
Total	Lumens	6894.5	0.0	6894.5
	% Fixture	100.0	0.0	100.0

Coefficient of Utilization

ZONAL LUMENS:

Zone	Lumens	% Fixture
0°-10°	53.5	0.8
10°-20°	184.5	2.7
20°-30°	353.1	5.1
30°-40°	587.3	8.5
40°-50°	794.7	11.5
50°-60°	1242.8	18.0
60°-70°	2555.2	37.1
70°-80°	1028.2	14.9
80°-90°	95.1	1.4
90°-100°	0.0	0.0
100°-110°	0.0	0.0
110°-120°	0.0	0.0
120°-130°	0.0	0.0
130°-140°	0.0	0.0
140°-150°	0.0	0.0
150°-160°	0.0	0.0
160°-170°	0.0	0.0
170°-180°	0.0	0.0
0°-90°	6894.5	100.0
0°-180°	6894.5	100.0



REPORT NUMBER: P152056


CATALOG NUMBER: AVS-F04-LED-E-U-SL4-HSS-7050

LUMINAIRE CLASSIFICATION SYSTEM LUMEN TABLE AND BUG RATING:

Zone		Lumens	% Fixture	Zone Rating/Lumen Limit		
				B	U	G
FL	(0°-30°)	513.1	7.4			
FM	(30°-60°)	2531.1	36.7			
FH	(60°-80°)	3553.5	51.5			G2/5000
FVH	(80°-90°)	91.6	1.3			G1/100
BL	(0°-30°)	78.1	1.1	B0/110		
BM	(30°-60°)	93.7	1.4	B0/220		
BH	(60°-80°)	29.9	0.4	B0/110		G0/110
BVH	(80°-90°)	3.5	0.1			G0/10
UL	(90°-100°)	0.0	0.0		U0/0	
UH	(100°-180°)	0.0	0.0		U0/0	

BUG Rating: B0-U0-G2

Type IV Short





REPORT NUMBER: P152056

CATALOG NUMBER: AVS-F04-LED-E-U-SL4-HSS-7050

CANDELA DISTRIBUTION (FULL):

	0°	5°	10°	15°	20°	25°	30°	35°	40°	45°	50°
0°	520.6	520.6	520.6	520.6	520.6	520.6	520.6	520.6	520.6	520.6	520.6
2.5°	694.6	686.7	677.6	677.6	666.3	666.3	659.6	641.6	639.3	629.1	619.0
5°	886.6	879.8	868.5	858.3	849.3	833.5	822.3	800.7	777.1	754.5	734.1
7.5°	1074.1	1070.7	1050.4	1046.9	1032.3	1006.3	983.7	952.1	911.5	879.8	842.6
10°	1248.0	1240.1	1235.6	1216.4	1194.9	1166.7	1131.7	1093.3	1045.9	996.2	943.1
12.5°	1385.8	1381.3	1360.9	1353.1	1330.5	1302.3	1258.2	1208.5	1161.0	1096.7	1034.6
15°	1488.6	1480.7	1467.2	1454.7	1427.6	1402.8	1362.1	1307.9	1250.3	1180.2	1105.7
17.5°	1574.4	1559.8	1556.4	1537.2	1508.9	1479.6	1434.4	1384.7	1316.9	1246.9	1165.6
20°	1689.6	1669.3	1662.5	1634.3	1601.6	1560.8	1508.9	1446.8	1375.6	1298.9	1215.2
22.5°	1825.2	1810.5	1795.8	1771.0	1729.1	1671.6	1595.9	1528.1	1437.7	1353.1	1262.7
25°	2017.2	2004.8	1981.0	1947.2	1895.2	1826.3	1734.8	1635.4	1529.2	1420.8	1314.6
27.5°	2203.5	2192.2	2175.3	2149.3	2090.6	2014.9	1902.0	1775.4	1641.0	1510.1	1392.6
30°	2378.5	2368.4	2351.5	2325.5	2273.6	2199.0	2071.4	1935.9	1768.7	1616.3	1475.0
32.5°	2567.3	2563.8	2544.7	2507.4	2462.2	2361.7	2222.7	2077.0	1907.6	1731.4	1566.5
35°	2780.6	2754.7	2736.6	2699.4	2622.6	2515.2	2352.6	2193.4	2014.9	1834.2	1650.1
37.5°	2961.3	2936.6	2914.0	2866.5	2772.7	2636.1	2452.0	2276.9	2092.8	1908.7	1721.2
40°	3093.5	3081.1	3054.0	2991.9	2886.8	2724.1	2525.4	2334.5	2149.3	1964.0	1778.9
42.5°	3191.8	3172.5	3142.1	3077.7	2953.5	2768.3	2554.8	2358.2	2175.3	1997.9	1816.2
45°	3227.9	3212.1	3183.8	3113.9	2979.5	2780.6	2553.7	2351.5	2176.4	2008.1	1840.9
47.5°	3206.4	3190.7	3165.8	3100.3	2968.2	2766.0	2533.4	2332.3	2165.1	2011.5	1863.5
50°	3135.3	3126.3	3107.0	3051.7	2933.2	2737.7	2515.2	2322.1	2162.9	2028.5	1895.2
52.5°	3128.5	3122.9	3099.2	3043.8	2923.0	2728.7	2513.0	2327.8	2182.1	2049.9	1917.8
55°	3823.1	3742.9	3563.3	3410.9	3160.2	2862.0	2627.0	2419.3	2263.4	2134.6	2042.0
57.5°	5433.7	5314.0	5077.9	4787.7	4211.7	3645.8	3193.0	2865.4	2703.8	2645.2	2680.1
60°	6188.2	6166.7	6129.4	5991.6	5696.9	5210.1	4668.0	4081.8	3846.8	3826.5	3897.7
62.5°	6546.2	6532.6	6543.9	6527.0	6435.5	6293.2	6137.3	5884.4	5651.7	5501.5	5183.0
65°	6711.1	6720.1	6784.6	6835.3	6846.6	6883.9	6997.9	7313.1	7543.5	7156.1	6271.7
67.5°	6292.1	6345.2	6493.2	6678.3	6895.2	7105.3	7444.1	8108.2	8581.5	8126.3	6870.4
69°	5208.9	5234.9	5596.4	5945.4	6475.0	6845.5	7336.8	8207.6	8739.6	8225.7	6822.9
70°	4100.9	4124.7	4512.1	4986.4	5882.1	6358.8	7001.3	8039.3	8591.6	8093.6	6579.0
72.5°	1850.1	1816.2	1952.7	2206.9	3180.5	3937.2	5061.0	6513.5	7088.3	6484.0	4922.1
75°	1292.1	1277.4	1292.1	1293.2	1444.6	1863.5	2351.5	3530.6	4366.4	3767.8	2351.5
77.5°	1000.7	990.5	980.3	969.0	987.2	1105.7	1153.2	1252.5	1626.4	1538.2	896.8
80°	791.7	782.7	807.6	799.7	799.7	813.2	804.1	766.8	696.9	646.0	578.2
82.5°	368.2	370.5	370.5	402.1	484.6	565.8	591.8	554.5	492.4	419.1	337.7
85°	35.0	39.5	66.6	102.8	204.5	230.4	231.5	192.0	192.0	151.3	122.0
87.5°	0.0	1.1	1.1	1.1	10.2	28.2	23.7	6.7	3.4	3.4	5.6
90°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0



REPORT NUMBER: P152056
 CATALOG NUMBER: AVS-F04-LED-E-U-SL4-HSS-7050

CANDELA DISTRIBUTION (continued):

	55°	60°	65°	70°	75°	80°	85°	90°	95°	100°	105°
0°	520.6	520.6	520.6	520.6	520.6	520.6	520.6	520.6	520.6	520.6	520.6
2.5°	600.8	597.5	583.9	570.4	557.9	544.4	531.9	519.6	506.0	495.9	483.4
5°	702.5	677.6	649.4	622.3	595.2	566.9	537.6	511.6	484.6	459.7	436.0
7.5°	805.3	756.7	718.3	669.7	625.7	581.7	541.0	499.2	460.8	424.7	390.8
10°	892.2	833.5	773.7	711.5	648.3	589.5	533.1	483.4	432.5	388.5	346.7
12.5°	963.4	888.9	815.4	737.5	666.3	591.8	521.8	462.0	402.1	352.4	309.4
15°	1027.8	942.0	853.9	763.5	673.2	588.4	510.5	436.0	374.9	318.5	269.9
17.5°	1079.7	981.5	882.1	780.4	683.3	583.9	495.9	417.9	346.7	288.0	240.5
20°	1124.9	1022.2	914.8	800.7	690.1	582.8	483.4	395.3	321.9	259.8	213.5
22.5°	1166.7	1063.9	948.7	826.7	700.2	581.7	472.1	378.3	300.4	238.3	192.0
25°	1214.1	1105.7	984.9	853.9	718.3	586.2	465.3	364.8	281.2	218.0	175.0
27.5°	1267.3	1153.2	1027.8	887.8	742.1	595.2	463.1	350.2	264.2	198.8	161.6
30°	1341.8	1209.6	1070.7	921.7	763.5	605.4	460.8	341.1	247.4	184.1	148.0
32.5°	1407.3	1265.0	1118.1	956.6	787.3	615.5	459.7	328.7	231.5	169.4	137.8
35°	1476.2	1315.8	1158.8	990.5	807.6	626.8	458.5	319.6	216.9	154.7	127.7
37.5°	1536.1	1358.8	1190.5	1019.9	830.2	637.0	459.7	311.7	203.3	142.3	118.5
40°	1586.8	1402.8	1225.4	1046.9	853.9	652.8	460.8	303.8	189.7	131.0	110.7
42.5°	1632.0	1444.6	1262.7	1077.5	880.9	670.9	467.6	297.0	178.4	120.8	102.8
45°	1667.0	1482.9	1303.3	1120.4	925.0	700.2	480.0	292.5	167.2	111.8	96.0
47.5°	1703.2	1539.4	1372.2	1188.2	989.4	746.5	501.5	291.4	158.1	105.1	90.4
50°	1752.8	1595.9	1433.3	1257.1	1048.1	794.0	527.5	292.5	146.8	98.2	84.7
52.5°	1789.0	1653.5	1512.3	1376.8	1188.2	938.5	628.0	312.8	141.1	92.6	77.9
55°	2002.5	1978.8	1982.2	2004.8	1859.1	1597.0	1050.4	451.8	166.0	105.1	76.8
57.5°	2823.6	2907.2	2955.8	2954.6	2714.0	2251.0	1410.7	580.5	185.2	122.0	91.5
60°	3903.3	3840.1	3750.9	3530.6	3211.0	2569.4	1577.8	624.6	160.4	97.1	83.6
62.5°	4857.7	4487.3	4158.5	3801.7	3382.7	2680.1	1611.7	621.1	140.0	73.4	58.8
65°	5453.0	4786.5	4255.8	3808.5	3314.9	2587.6	1524.8	570.4	118.5	59.9	48.6
67.5°	5595.2	4625.1	3874.0	3303.6	2769.3	2013.8	1119.3	429.2	92.6	49.7	42.9
69°	5284.7	4111.2	3209.8	2562.7	2014.9	1336.2	692.3	271.1	71.2	45.2	39.5
70°	4861.0	3575.8	2614.6	2056.7	1492.0	938.5	484.6	190.9	57.6	41.8	36.2
72.5°	3127.4	1878.2	1285.3	894.5	615.5	373.9	189.7	85.8	44.0	35.0	29.3
75°	1213.1	694.6	503.7	382.9	299.3	207.8	115.2	55.3	37.3	29.3	22.6
77.5°	597.5	457.4	373.9	256.4	149.1	92.6	62.1	42.9	30.5	21.5	14.7
80°	472.1	314.0	187.5	116.4	88.1	66.6	47.5	35.0	22.6	13.6	10.2
82.5°	241.7	132.1	97.1	79.1	65.5	51.9	38.4	24.9	14.7	9.0	7.9
85°	75.6	55.3	49.7	48.6	45.2	37.3	27.2	15.9	9.0	5.6	5.6
87.5°	5.6	7.9	10.2	7.9	9.0	7.9	10.2	6.7	4.6	4.6	3.4
90°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0



REPORT NUMBER: P152056

CATALOG NUMBER: AVS-F04-LED-E-U-SL4-HSS-7050

CANDELA DISTRIBUTION (continued):

	110°	115°	120°	125°	130°	135°	140°	145°	150°	155°	160°
0°	520.6	520.6	520.6	520.6	520.6	520.6	520.6	520.6	520.6	520.6	520.6
2.5°	474.4	460.8	448.4	440.5	425.8	420.1	414.5	412.2	402.1	404.4	395.3
5°	414.5	390.8	372.7	354.6	337.7	325.3	315.1	302.7	292.5	288.0	279.0
7.5°	360.3	329.8	306.1	286.8	266.5	250.8	237.2	228.2	219.1	210.1	205.6
10°	312.8	280.1	253.0	233.8	214.6	201.0	190.9	184.1	178.4	175.0	173.9
12.5°	268.8	237.2	212.3	195.4	180.7	173.9	169.4	166.0	164.9	163.7	163.7
15°	234.9	203.3	184.1	171.7	164.9	161.6	160.4	158.1	155.9	154.7	154.7
17.5°	203.3	179.6	166.0	159.3	155.9	153.6	151.3	149.1	146.8	145.7	145.7
20°	181.9	162.6	155.9	151.3	148.0	145.7	142.3	140.0	139.0	137.8	136.7
22.5°	164.9	152.4	148.0	144.6	140.0	136.7	134.4	132.1	129.8	128.7	127.7
25°	152.4	144.6	141.1	136.7	132.1	128.7	125.4	122.0	119.7	118.5	116.4
27.5°	143.4	137.8	133.3	127.7	123.1	119.7	116.4	113.0	110.7	108.4	107.3
30°	135.5	129.8	124.2	119.7	114.1	110.7	106.2	102.8	101.7	99.4	97.1
32.5°	127.7	122.0	116.4	110.7	105.1	100.5	98.2	93.8	91.5	90.4	88.1
35°	118.5	113.0	106.2	101.7	96.0	91.5	88.1	84.7	82.5	80.2	79.1
37.5°	110.7	103.9	97.1	91.5	86.9	82.5	79.1	75.6	73.4	71.2	70.1
40°	101.7	94.9	88.1	82.5	77.9	74.5	71.2	67.8	65.5	64.4	64.4
42.5°	93.8	85.8	79.1	74.5	71.2	66.6	63.2	59.9	58.8	57.6	58.8
45°	85.8	77.9	72.3	67.8	64.4	59.9	56.5	54.2	53.1	54.2	55.3
47.5°	79.1	71.2	65.5	62.1	58.8	55.3	51.9	49.7	49.7	51.9	54.2
50°	72.3	64.4	59.9	57.6	54.2	50.8	46.3	45.2	46.3	48.6	50.8
52.5°	65.5	56.5	53.1	51.9	48.6	45.2	41.8	40.6	41.8	44.0	42.9
55°	58.8	49.7	48.6	47.5	44.0	39.5	36.2	36.2	36.2	35.0	32.7
57.5°	56.5	44.0	42.9	41.8	38.4	33.9	31.6	29.3	28.2	24.9	23.7
60°	58.8	39.5	39.5	37.3	33.9	29.3	26.0	22.6	20.3	18.0	18.0
62.5°	47.5	36.2	35.0	32.7	28.2	23.7	20.3	16.9	15.9	14.7	14.7
65°	38.4	32.7	30.5	27.2	23.7	19.2	15.9	13.6	12.4	12.4	13.6
67.5°	35.0	29.3	26.0	22.6	19.2	14.7	12.4	11.3	11.3	12.4	12.4
69°	32.7	27.2	23.7	20.3	16.9	13.6	11.3	11.3	11.3	11.3	12.4
70°	30.5	26.0	22.6	19.2	14.7	11.3	10.2	10.2	11.3	11.3	12.4
72.5°	23.7	20.3	19.2	15.9	11.3	10.2	9.0	10.2	10.2	11.3	11.3
75°	18.0	14.7	14.7	12.4	9.0	7.9	7.9	9.0	9.0	10.2	10.2
77.5°	12.4	10.2	10.2	9.0	7.9	6.7	6.7	7.9	9.0	9.0	10.2
80°	9.0	7.9	6.7	7.9	6.7	5.6	6.7	7.9	7.9	9.0	9.0
82.5°	6.7	6.7	6.7	6.7	5.6	5.6	6.7	6.7	7.9	9.0	9.0
85°	5.6	5.6	5.6	5.6	5.6	5.6	5.6	6.7	6.7	7.9	7.9
87.5°	3.4	3.4	3.4	4.6	4.6	5.6	5.6	5.6	5.6	6.7	6.7
90°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0



REPORT NUMBER: P152056

CATALOG NUMBER: AVS-F04-LED-E-U-SL4-HSS-7050

CANDELA DISTRIBUTION (continued):

	165°	170°	175°	180°
0°	520.6	520.6	520.6	520.6
2.5°	393.1	391.9	387.4	388.5
5°	275.5	268.8	273.4	272.2
7.5°	202.2	201.0	199.9	202.2
10°	172.8	172.8	171.7	172.8
12.5°	162.6	162.6	162.6	162.6
15°	154.7	154.7	153.6	153.6
17.5°	145.7	145.7	145.7	144.6
20°	136.7	135.5	135.5	135.5
22.5°	126.5	125.4	125.4	125.4
25°	116.4	115.2	115.2	115.2
27.5°	106.2	105.1	103.9	103.9
30°	96.0	94.9	93.8	93.8
32.5°	85.8	84.7	83.6	83.6
35°	76.8	76.8	75.6	74.5
37.5°	68.9	68.9	68.9	68.9
40°	63.2	64.4	64.4	64.4
42.5°	59.9	61.0	62.1	63.2
45°	57.6	59.9	61.0	61.0
47.5°	56.5	57.6	58.8	58.8
50°	51.9	50.8	50.8	50.8
52.5°	41.8	39.5	38.4	37.3
55°	30.5	29.3	27.2	27.2
57.5°	21.5	21.5	20.3	20.3
60°	16.9	16.9	15.9	16.9
62.5°	14.7	14.7	14.7	14.7
65°	13.6	13.6	13.6	13.6
67.5°	13.6	13.6	13.6	13.6
69°	12.4	12.4	12.4	12.4
70°	12.4	12.4	12.4	12.4
72.5°	11.3	11.3	11.3	11.3
75°	10.2	11.3	11.3	11.3
77.5°	10.2	10.2	10.2	10.2
80°	9.0	9.0	10.2	10.2
82.5°	9.0	9.0	9.0	9.0
85°	7.9	7.9	9.0	9.0
87.5°	6.7	6.7	7.9	7.9
90°	0.0	0.0	0.0	0.0

(END OF REPORT)