

Scaled data based on original data using  
LM-79-08 Approved Method: Electrical and Photometric Measurements of Solid-  
State Lighting Products

Test Report Prepared for  
Cooper Lighting Solutions  
(formerly Eaton)

Brand: STREETWORKS

Report Number: P150902

Luminaire Tested: **AVS-E03-LED-E-U-SL3-HSS-7060**

Issue Date: 3/3/2020

**Test Information**

Test Method: LM-79-08  
Report Number: P150902  
REPORT IS SCALED FROM IESNA LM-79-08 TEST DATA (P33727)  
Test Lab: INNOVATION CENTER-P3  
Issue Date: 3/3/2020  
Manufacturer: COOPER LIGHTING SOLUTIONS (FORMERLY EATON)  
Product Line: STREETWORKS  
Catalog Number: AVS-E03-LED-E-U-SL3-HSS-7060  
Description: VISION SITE SMALL LED LUMINAIRE  
(3) LIGHTBARS WITH AccuLED OPTICS - TYPE 3 W/ SPILL LIGHT CONTROL AND HOUSE SIDE SHIELD  
Light Source: (63) 5700K CCT, 70 CRI LEDs  
Ballast/Driver: -

**Summary**


Lumens per Lamp: N/A  
Luminaire Lumens: 5337.3 lumens  
Efficiency: N/A  
Efficacy: 71.0 lumens/watt  
Luminous Opening: Rectangular (W 0.5' x L: 1' x H: 0')  
IES Classification: Type III - Short - Non-Cutoff  
BUG Rating: B0 - U0 - G2  
  
Input Watts (W): 75.2  
Input Voltage (V): NR  
Input Current (Ain): NR  
Voltage Rise (V): NR  
Power Factor: NR  
Total Harmonic Distortion (THDi): NR  
Frequency (hertz): 60  
Stabilization Time: NR  
Operation Time: NR  
Ambient Temperature (°C): NR  
Test Distance: 28.75 FT



REPORT NUMBER: P150902  
 CATALOG NUMBER: AVS-E03-LED-E-U-SL3-HSS-7060

### Iso-Footcandle Lines of Horizontal Illumination


✕ Max cd  
 - - - 1/2 Max cd



Based on 10 foot mounting height. Maximum calculated value = 8.8 fc  
 Type III - Short - Non-Cutoff

REPORT NUMBER: P150902  
CATALOG NUMBER: AVS-E03-LED-E-U-SL3-HSS-7060

### Luminous Intensity Polar Plot



— Vertical Plane Through 65-Deg Lateral    - - - Horizontal Cone Through 66-Deg Vertical

REPORT NUMBER: P150902

CATALOG NUMBER: AVS-E03-LED-E-U-SL3-HSS-7060


**FLUX DISTRIBUTION:**

		Downward	Upward	Total
<b>House Side</b>	Lumens	115.7	0.0	115.7
	% Fixture	2.2	0.0	2.2
<b>Street Side</b>	Lumens	5221.6	0.0	5221.6
	% Fixture	97.8	0.0	97.8
<b>Total</b>	Lumens	5337.3	0.0	5337.3
	% Fixture	100.0	0.0	100.0

**ZONAL LUMENS:**

Zone	Lumens	% Fixture
0°-10°	18.0	0.3
10°-20°	76.5	1.4
20°-30°	164.9	3.1
30°-40°	352.2	6.6
40°-50°	778.9	14.6
50°-60°	1320.0	24.7
60°-70°	1761.4	33.0
70°-80°	775.9	14.5
80°-90°	89.4	1.7
90°-100°	0.0	0.0
100°-110°	0.0	0.0
110°-120°	0.0	0.0
120°-130°	0.0	0.0
130°-140°	0.0	0.0
140°-150°	0.0	0.0
150°-160°	0.0	0.0
160°-170°	0.0	0.0
170°-180°	0.0	0.0
0°-90°	5337.3	100.0
0°-180°	5337.3	100.0

**Coefficient of Utilization**



REPORT NUMBER: P150902


CATALOG NUMBER: AVS-E03-LED-E-U-SL3-HSS-7060

**LUMINAIRE CLASSIFICATION SYSTEM LUMEN TABLE AND BUG RATING:**

Zone		Lumens	% Fixture	Zone Rating/Lumen Limit		
				B	U	G
FL	(0°-30°)	222.9	4.2			
FM	(30°-60°)	2400.3	45.0			
FH	(60°-80°)	2512.5	47.1			G2/5000
FVH	(80°-90°)	85.8	1.6			G1/100
BL	(0°-30°)	36.5	0.7	B0/110		
BM	(30°-60°)	50.8	1.0	B0/220		
BH	(60°-80°)	24.8	0.5	B0/110		G0/110
BVH	(80°-90°)	3.6	0.1			G0/10
UL	(90°-100°)	0.0	0.0		U0/0	
UH	(100°-180°)	0.0	0.0		U0/0	

**BUG Rating: B0-U0-G2**

Type III Short





REPORT NUMBER: P150902  
 CATALOG NUMBER: AVS-E03-LED-E-U-SL3-HSS-7060

**CANDELA DISTRIBUTION (FULL):**

	0°	5°	15°	25°	35°	45°	55°	65°	66°	67°	68°
0°	161.1	161.1	161.1	161.1	161.1	161.1	161.1	161.1	161.1	161.1	161.1
2.5°	203.2	202.2	198.0	198.0	191.9	187.8	182.7	177.5	177.5	176.5	175.4
5°	268.8	262.7	261.7	250.4	241.1	227.8	215.4	199.1	197.0	194.9	193.9
7.5°	341.7	340.6	331.4	318.1	299.6	275.0	250.4	223.7	219.6	217.5	213.5
10°	436.1	431.0	418.7	396.1	368.4	335.5	295.5	253.5	248.3	244.2	242.2
12.5°	526.4	517.2	509.9	481.2	446.3	398.1	349.9	289.3	285.3	280.1	271.9
15°	610.6	602.3	590.1	565.4	526.4	465.8	409.4	335.5	325.3	318.1	311.9
17.5°	676.2	671.1	656.7	629.0	586.9	533.6	465.8	382.7	374.5	365.3	354.0
20°	738.8	731.6	709.0	671.1	625.9	584.9	532.5	444.4	433.1	421.8	409.4
22.5°	798.3	791.1	754.2	691.6	643.4	625.9	607.5	514.1	496.7	487.4	475.1
25°	881.5	866.0	808.6	709.0	644.4	657.7	689.5	604.4	588.0	574.6	555.1
27.5°	993.3	972.7	882.5	734.7	648.5	692.6	783.9	714.2	696.7	681.3	659.8
30°	1119.5	1106.1	998.4	796.3	678.2	743.9	889.6	853.7	833.2	814.7	789.1
32.5°	1246.7	1228.3	1121.6	913.3	758.3	843.4	1022.0	1015.9	989.1	971.7	944.0
35°	1358.5	1349.3	1270.4	1105.1	940.9	1017.9	1198.4	1205.7	1182.1	1163.6	1132.8
37.5°	1434.5	1434.5	1419.1	1311.4	1231.3	1288.8	1458.1	1459.2	1435.5	1393.5	1378.0
40°	1473.5	1484.8	1540.2	1560.7	1556.6	1630.5	1798.8	1780.3	1760.8	1739.3	1688.0
42.5°	1553.6	1563.8	1681.8	1823.4	1915.8	2013.3	2129.1	2123.0	2099.4	2060.4	2013.3
45°	1689.0	1702.3	1842.9	2067.6	2257.4	2396.0	2469.8	2441.1	2417.5	2380.5	2356.0
47.5°	1861.3	1887.0	2046.0	2324.1	2553.0	2781.8	2858.8	2782.8	2762.3	2733.6	2693.6
50°	2045.1	2069.6	2239.0	2557.1	2815.6	3088.6	3216.9	3088.6	3058.9	3049.5	3004.5
52.5°	2204.0	2224.6	2387.8	2736.6	3016.8	3336.9	3523.6	3354.3	3332.7	3302.0	3269.2
55°	2298.4	2314.9	2467.8	2822.8	3153.3	3560.6	3820.2	3671.4	3639.6	3627.3	3580.1
57.5°	2330.3	2346.7	2484.2	2834.1	3227.2	3764.8	4180.3	4185.5	4147.6	4103.4	4089.0
60°	2330.3	2348.7	2464.7	2806.4	3299.0	3982.3	4660.6	5088.5	5006.3	4998.1	4945.8
62.5°	2233.8	2251.3	2368.3	2721.2	3395.3	4275.8	5329.6	6084.8	6061.2	6007.9	5921.7
65°	2024.5	2034.8	2149.7	2503.7	3358.4	4545.6	5909.3	6747.7	6709.7	6605.1	6494.2
66°	1930.2	1938.3	2046.0	2379.6	3237.4	4582.6	6011.9	6830.8	6768.2	6679.9	6554.7
67.5°	1793.7	1808.0	1883.9	2148.7	2946.9	4454.3	5947.4	6772.3	6717.9	6611.2	6486.0
70°	1197.5	1187.3	1455.0	1648.9	2245.1	3629.3	5335.8	6080.7	6081.8	6031.4	5981.1
72.5°	568.5	574.6	652.6	1014.8	1469.4	2424.7	4247.0	4853.5	4923.2	4833.0	4770.4
75°	408.4	417.6	464.9	620.8	876.3	1455.0	2753.1	3394.4	3396.4	3236.4	3093.7
77.5°	119.1	124.1	174.4	382.7	656.7	982.0	1581.2	1887.0	1842.9	1728.0	1620.2
80°	49.2	49.2	51.3	122.1	263.7	666.9	1106.1	1453.0	1447.9	1403.7	1340.1
82.5°	18.4	19.5	24.7	50.3	62.6	164.1	737.7	1261.0	1258.0	1195.4	1150.3
85°	2.1	2.1	6.1	21.6	23.6	30.8	147.8	556.2	553.1	556.2	487.4
87.5°	0.0	0.0	1.0	2.1	3.1	4.1	6.1	21.6	23.6	22.6	20.5
90°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0



REPORT NUMBER: P150902

CATALOG NUMBER: AVS-E03-LED-E-U-SL3-HSS-7060

**CANDELA DISTRIBUTION (continued):**

	69°	70°	71°	72°	73°	74°	75°	76°	77°	78°	79°
0°	161.1	161.1	161.1	161.1	161.1	161.1	161.1	161.1	161.1	161.1	161.1
2.5°	175.4	173.4	173.4	172.4	172.4	172.4	171.4	170.4	170.4	169.3	168.3
5°	191.9	189.8	188.8	186.7	185.7	184.7	182.7	181.7	179.6	178.5	177.5
7.5°	211.4	207.3	206.2	203.2	200.1	198.0	196.0	193.0	190.9	186.7	185.7
10°	236.0	230.9	226.7	222.7	219.6	214.5	211.4	207.3	203.2	200.1	197.0
12.5°	267.8	260.6	254.5	250.4	243.2	237.0	230.9	227.8	219.6	215.4	210.4
15°	302.7	294.5	287.4	279.1	274.0	263.7	255.5	246.2	242.2	235.0	226.7
17.5°	347.9	334.5	323.2	315.0	304.8	294.5	285.3	276.1	263.7	255.5	245.3
20°	396.1	384.8	369.4	355.0	342.7	330.4	317.1	304.8	293.5	280.1	267.8
22.5°	457.6	441.2	422.8	408.4	392.0	378.7	360.2	343.7	325.3	307.9	293.5
25°	535.6	514.1	496.7	476.1	456.6	436.1	413.5	393.0	369.4	353.0	328.4
27.5°	632.1	611.6	588.0	561.2	541.8	511.0	481.2	455.5	427.9	402.3	374.5
30°	755.2	725.5	700.8	675.1	636.2	606.4	571.5	536.7	498.7	473.1	431.0
32.5°	903.0	871.2	834.2	797.3	761.3	719.3	676.2	633.1	591.1	543.8	500.7
35°	1083.5	1045.6	1003.5	963.5	908.1	863.0	808.6	749.0	701.9	647.5	593.1
37.5°	1322.7	1260.1	1223.1	1181.0	1106.1	1044.6	984.0	924.6	841.5	783.9	706.9
40°	1622.3	1585.3	1524.8	1457.1	1389.3	1308.3	1226.2	1147.2	1050.8	970.7	881.5
42.5°	1974.2	1919.8	1858.2	1760.8	1692.0	1596.6	1503.2	1398.5	1280.6	1177.9	1073.3
45°	2304.7	2240.0	2192.7	2095.3	2023.5	1910.6	1797.7	1686.9	1550.5	1418.0	1297.0
47.5°	2661.8	2608.4	2530.4	2451.4	2378.5	2251.3	2129.1	1994.7	1851.1	1694.1	1537.1
50°	2975.8	2933.7	2880.3	2784.9	2703.8	2597.1	2453.4	2306.7	2125.1	1969.1	1790.6
52.5°	3242.5	3209.6	3134.7	3067.0	2994.2	2893.6	2765.4	2624.8	2428.8	2257.4	2054.3
55°	3557.5	3533.9	3468.2	3426.2	3361.6	3265.1	3145.0	3014.7	2807.5	2620.6	2390.8
57.5°	4073.7	4055.1	3997.7	3980.3	3916.7	3832.5	3684.8	3545.2	3303.0	3071.1	2808.5
60°	4928.4	4891.4	4807.3	4764.2	4629.7	4516.9	4325.1	4133.2	3840.7	3545.2	3229.1
62.5°	5843.6	5740.0	5580.0	5442.5	5251.6	5055.6	4799.1	4505.6	4162.9	3812.0	3448.7
65°	6337.2	6160.7	5958.5	5740.0	5492.7	5204.5	4881.1	4529.2	4160.8	3790.5	3406.6
66°	6393.7	6194.6	5980.1	5737.0	5462.0	5155.1	4826.8	4457.4	4074.7	3713.5	3329.7
67.5°	6322.9	6114.6	5887.8	5617.9	5320.3	5002.3	4657.5	4273.7	3905.4	3539.1	3165.5
70°	5827.3	5620.0	5417.8	5133.6	4816.6	4496.4	4170.1	3741.1	3392.3	3055.8	2723.3
72.5°	4653.4	4512.8	4312.7	4069.5	3760.7	3385.1	3113.2	2729.4	2426.7	2100.4	1842.9
75°	2908.0	2709.9	2462.7	2152.7	1916.8	1612.0	1453.0	1161.6	989.1	838.3	692.6
77.5°	1486.8	1338.0	1164.7	990.2	822.9	656.7	507.9	359.2	242.2	168.3	125.2
80°	1228.3	1096.9	953.3	794.2	646.4	501.8	361.1	246.2	157.0	102.6	80.0
82.5°	1014.8	904.0	775.8	628.0	499.7	394.0	274.0	178.5	110.8	71.8	56.5
85°	432.0	392.0	302.7	240.1	180.6	133.4	93.4	62.6	44.1	36.0	32.8
87.5°	18.4	20.5	19.5	15.4	11.3	11.3	10.3	8.2	8.2	8.2	8.2
90°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0





REPORT NUMBER: P150902

CATALOG NUMBER: AVS-E03-LED-E-U-SL3-HSS-7060

**CANDELA DISTRIBUTION (continued):**

	80°	81°	82°	83°	84°	85°	95°	105°	115°	125°	135°
0°	161.1	161.1	161.1	161.1	161.1	161.1	161.1	161.1	161.1	161.1	161.1
2.5°	168.3	167.3	166.2	166.2	165.2	164.1	158.0	152.8	146.7	142.6	138.5
5°	175.4	174.4	172.4	171.4	169.3	168.3	154.9	143.6	134.4	127.3	122.1
7.5°	182.7	181.7	178.5	175.4	174.4	172.4	150.9	136.5	124.1	116.0	110.8
10°	191.9	188.8	185.7	181.7	178.5	175.4	146.7	128.3	114.9	107.8	102.6
12.5°	205.2	200.1	194.9	189.8	185.7	180.6	144.7	121.0	107.8	99.5	94.4
15°	220.6	213.5	207.3	201.1	193.9	188.8	140.6	114.9	101.6	93.4	87.3
17.5°	235.0	226.7	217.5	208.3	201.1	193.9	136.5	108.8	95.4	87.3	81.0
20°	255.5	243.2	231.9	220.6	210.4	201.1	130.4	102.6	90.3	81.0	74.9
22.5°	278.0	263.7	249.3	234.0	220.6	208.3	125.2	97.5	85.2	76.0	68.7
25°	306.8	289.3	269.8	250.4	235.0	218.5	120.1	92.3	80.0	70.8	63.6
27.5°	346.8	322.2	300.6	276.1	252.4	234.0	116.0	88.3	74.9	65.7	58.4
30°	401.2	365.3	331.4	304.8	277.1	250.4	111.8	83.1	70.8	60.5	52.3
32.5°	461.8	419.7	380.7	340.6	305.8	275.0	107.8	79.0	65.7	55.4	48.2
35°	536.7	483.3	431.0	384.8	342.7	301.7	103.6	74.9	61.6	50.3	43.1
37.5°	644.4	577.7	508.9	449.4	395.0	340.6	100.5	70.8	56.5	45.2	37.9
40°	792.1	706.0	621.9	540.7	469.9	402.3	96.5	66.7	52.3	41.0	33.9
42.5°	952.2	847.6	736.8	645.4	548.0	462.8	92.3	62.6	48.2	36.9	29.7
45°	1151.3	1020.9	886.5	762.4	643.4	533.6	88.3	58.4	43.1	32.8	25.7
47.5°	1368.8	1202.6	1050.8	894.7	753.2	621.9	83.1	55.4	39.0	28.7	22.6
50°	1592.5	1417.1	1225.2	1047.7	879.4	710.1	78.0	50.3	34.9	25.7	18.4
52.5°	1833.7	1626.4	1430.4	1209.7	1013.8	826.0	72.8	46.2	31.8	22.6	15.4
55°	2140.4	1908.6	1678.8	1431.4	1195.4	960.4	67.8	41.0	27.7	19.5	12.3
57.5°	2526.3	2251.3	1969.1	1689.9	1403.7	1136.9	63.6	36.0	23.6	16.4	10.3
60°	2890.6	2569.3	2227.7	1906.5	1583.3	1272.3	57.5	31.8	20.5	13.4	10.3
62.5°	3079.4	2713.1	2344.7	1990.7	1645.9	1320.6	51.3	26.6	17.4	11.3	9.2
65°	3033.2	2659.7	2302.6	1945.5	1607.9	1289.8	45.2	23.6	15.4	10.3	9.2
66°	2966.4	2597.1	2237.9	1898.3	1576.1	1257.0	42.1	22.6	14.4	10.3	8.2
67.5°	2820.7	2463.7	2120.9	1804.9	1488.9	1194.4	37.9	20.5	13.4	9.2	8.2
70°	2409.3	2085.1	1811.1	1529.9	1272.3	1006.6	30.8	17.4	11.3	8.2	8.2
72.5°	1594.6	1374.0	1191.3	1025.1	856.8	664.9	25.7	14.4	9.2	8.2	7.2
75°	601.3	543.8	466.8	419.7	366.3	321.1	20.5	9.2	7.2	7.2	7.2
77.5°	106.7	98.5	87.3	80.0	73.9	67.8	16.4	6.1	6.1	7.2	7.2
80°	71.8	66.7	60.5	55.4	51.3	46.2	11.3	5.2	6.1	6.1	7.2
82.5°	51.3	48.2	45.2	41.0	37.9	33.9	7.2	5.2	6.1	6.1	6.1
85°	30.8	28.7	26.6	24.7	21.6	20.5	5.2	5.2	5.2	6.1	6.1
87.5°	8.2	7.2	8.2	8.2	6.1	7.2	4.1	4.1	4.1	5.2	5.2
90°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0



REPORT NUMBER: P150902

CATALOG NUMBER: AVS-E03-LED-E-U-SL3-HSS-7060

**CANDELA DISTRIBUTION (continued):**

	145°	155°	165°	175°	180°
0°	161.1	161.1	161.1	161.1	161.1
2.5°	136.5	136.5	134.4	137.5	137.5
5°	118.0	118.0	117.0	118.0	118.0
7.5°	107.8	106.7	106.7	106.7	107.8
10°	98.5	97.5	97.5	97.5	97.5
12.5°	90.3	89.2	88.3	89.2	89.2
15°	83.1	81.0	81.0	81.0	81.0
17.5°	77.0	74.9	73.9	73.9	73.9
20°	70.8	67.8	67.8	67.8	67.8
22.5°	64.7	61.6	61.6	61.6	61.6
25°	58.4	55.4	55.4	55.4	55.4
27.5°	53.4	50.3	50.3	50.3	50.3
30°	47.2	45.2	45.2	46.2	45.2
32.5°	43.1	40.0	40.0	41.0	41.0
35°	37.9	36.0	36.0	36.0	36.0
37.5°	32.8	30.8	30.8	30.8	30.8
40°	28.7	26.6	25.7	26.6	26.6
42.5°	24.7	22.6	21.6	21.6	21.6
45°	21.6	18.4	17.4	18.4	18.4
47.5°	17.4	15.4	15.4	16.4	16.4
50°	13.4	13.4	14.4	16.4	16.4
52.5°	12.3	12.3	14.4	16.4	16.4
55°	11.3	12.3	14.4	15.4	16.4
57.5°	10.3	12.3	14.4	15.4	15.4
60°	10.3	11.3	13.4	15.4	15.4
62.5°	9.2	10.3	12.3	14.4	14.4
65°	9.2	10.3	12.3	14.4	14.4
66°	9.2	10.3	12.3	14.4	14.4
67.5°	9.2	10.3	12.3	14.4	14.4
70°	9.2	10.3	12.3	13.4	13.4
72.5°	8.2	9.2	11.3	13.4	13.4
75°	8.2	9.2	11.3	13.4	13.4
77.5°	8.2	9.2	11.3	13.4	13.4
80°	8.2	9.2	11.3	12.3	13.4
82.5°	7.2	9.2	10.3	12.3	12.3
85°	7.2	8.2	10.3	11.3	12.3
87.5°	6.1	7.2	8.2	10.3	10.3
90°	0.0	0.0	0.0	0.0	0.0

(END OF REPORT)