

Scaled data based on original data using
LM-79-08 Approved Method: Electrical and Photometric Measurements of Solid-
State Lighting Products

Test Report Prepared for
Cooper Lighting Solutions
(formerly Eaton)

Brand: STREETWORKS

Report Number: P154778

Luminaire Tested: **AVS-E02-LED-E-U-T2-8030**

Issue Date: 3/3/2020

Test Information

Test Method: LM-79-08
Report Number: P154778
REPORT IS SCALED FROM IESNA LM-79-08 TEST DATA (P33671)
Test Lab: INNOVATION CENTER-P3
Issue Date: 3/3/2020
Manufacturer: COOPER LIGHTING SOLUTIONS (FORMERLY EATON)
Product Line: STREETWORKS
Catalog Number: AVS-E02-LED-E-U-T2-8030
Description: VISION SITE SMALL LED LUMINAIRE
(2) LIGHTBARS WITH AccuLED OPTICS - TYPE 2 AREA
Light Source: (42) 3000K CCT, 80 CRI LEDs
Ballast/Driver: -

Summary

Lumens per Lamp: N/A
Luminaire Lumens: 5171.7 lumens
Efficiency: N/A
Efficacy: 99.3 lumens/watt
Luminous Opening: Rectangular (W 0.33' x L: 1' x H: 0')
IES Classification: Type II - Short - Semi-Cutoff
BUG Rating: B2 - U0 - G2

Input Watts (W): 52.1
Input Voltage (V): NR
Input Current (Ain): NR
Voltage Rise (V): NR
Power Factor: NR
Total Harmonic Distortion (THDi): NR
Frequency (hertz): 60
Stabilization Time: NR
Operation Time: NR
Ambient Temperature (°C): NR
Test Distance: 28.75 FT




REPORT NUMBER: P154778

CATALOG NUMBER: AVS-E02-LED-E-U-T2-8030

Iso-Footcandle Lines of Horizontal Illumination

× Max cd
 - - - 1/2 Max cd




Based on 10 foot mounting height. Maximum calculated value = 6.3 fc
 Type II - Short - Semi-Cutoff

REPORT NUMBER: P154778

CATALOG NUMBER: AVS-E02-LED-E-U-T2-8030

Luminous Intensity Polar Plot



— Vertical Plane Through 76-Deg Lateral - - - Horizontal Cone Through 65-Deg Vertical

REPORT NUMBER: P154778

CATALOG NUMBER: AVS-E02-LED-E-U-T2-8030

FLUX DISTRIBUTION:

		Downward	Upward	Total
House Side	Lumens	1811.0	0.0	1811.0
	% Fixture	35.0	0.0	35.0
Street Side	Lumens	3360.7	0.0	3360.7
	% Fixture	65.0	0.0	65.0
Total	Lumens	5171.7	0.0	5171.7
	% Fixture	100.0	0.0	100.0

Coefficient of Utilization

ZONAL LUMENS:

Zone	Lumens	% Fixture
0°-10°	51.8	1.0
10°-20°	177.8	3.4
20°-30°	349.4	6.8
30°-40°	580.6	11.2
40°-50°	853.1	16.5
50°-60°	1181.1	22.8
60°-70°	1409.7	27.3
70°-80°	498.5	9.6
80°-90°	69.7	1.3
90°-100°	0.0	0.0
100°-110°	0.0	0.0
110°-120°	0.0	0.0
120°-130°	0.0	0.0
130°-140°	0.0	0.0
140°-150°	0.0	0.0
150°-160°	0.0	0.0
160°-170°	0.0	0.0
170°-180°	0.0	0.0
0°-90°	5171.7	100.0
0°-180°	5171.7	100.0



REPORT NUMBER: P154778


CATALOG NUMBER: AVS-E02-LED-E-U-T2-8030

LUMINAIRE CLASSIFICATION SYSTEM LUMEN TABLE AND BUG RATING:

Zone		Lumens	% Fixture	Zone Rating/Lumen Limit		
				B	U	G
FL	(0°-30°)	299.2	5.8			
FM	(30°-60°)	1646.5	31.8			
FH	(60°-80°)	1367.3	26.4			G1/1800
FVH	(80°-90°)	47.6	0.9			G1/100
BL	(0°-30°)	279.8	5.4	B1/500		
BM	(30°-60°)	968.2	18.7	B1/1000		
BH	(60°-80°)	541.0	10.5	B2/1000		G2/1000
BVH	(80°-90°)	22.1	0.4			G1/100
UL	(90°-100°)	0.0	0.0		U0/0	
UH	(100°-180°)	0.0	0.0		U0/0	

BUG Rating: B2-U0-G2

Type II Short





REPORT NUMBER: P154778

CATALOG NUMBER: AVS-E02-LED-E-U-T2-8030

CANDELA DISTRIBUTION (FULL):

	0°	5°	15°	25°	35°	45°	55°	60°	61°	62°	64°
0°	517.1	517.1	517.1	517.1	517.1	517.1	517.1	517.1	517.1	517.1	517.1
2.5°	539.6	540.1	539.1	538.4	536.8	534.0	531.7	529.4	529.4	529.4	527.8
5°	563.2	564.4	562.1	560.4	555.3	552.5	548.6	545.8	544.7	544.0	542.4
7.5°	593.1	591.4	588.0	586.8	582.9	576.7	569.4	563.8	563.8	563.2	563.8
10°	622.9	618.3	616.7	615.0	608.8	600.9	592.4	586.3	585.7	585.2	583.5
12.5°	652.6	651.0	649.3	643.1	636.9	624.6	615.0	608.8	608.2	608.8	606.5
15°	692.1	688.1	686.4	675.8	662.3	648.7	636.9	631.3	629.6	630.2	628.5
17.5°	722.5	722.5	718.5	706.7	689.2	670.7	658.3	654.9	654.4	654.4	654.9
20°	746.6	746.1	742.2	732.5	711.8	693.2	687.0	685.9	685.3	685.3	687.0
22.5°	760.1	759.1	757.3	746.6	730.4	717.9	718.5	721.9	723.0	724.1	726.4
25°	766.9	765.2	764.7	757.3	745.5	743.8	754.0	763.0	765.2	767.5	770.3
27.5°	778.1	775.3	776.5	773.7	770.9	776.0	796.7	806.3	808.0	810.8	812.4
30°	809.1	808.0	812.4	813.6	815.9	823.2	842.3	851.3	855.2	855.2	863.1
32.5°	868.2	868.7	869.8	881.7	885.6	890.7	900.8	908.1	908.7	909.2	916.6
35°	947.6	950.9	960.4	970.6	980.1	979.6	973.4	977.3	974.5	977.9	978.4
37.5°	1047.7	1043.2	1057.2	1080.3	1094.9	1091.0	1063.4	1045.4	1050.5	1048.2	1046.5
40°	1124.8	1129.8	1156.8	1187.3	1198.4	1210.9	1174.8	1143.9	1139.4	1131.0	1125.9
42.5°	1231.1	1231.7	1253.6	1276.2	1308.7	1335.8	1312.6	1268.2	1254.7	1244.6	1222.7
45°	1329.5	1327.9	1345.9	1373.5	1412.2	1451.1	1459.6	1411.2	1406.1	1388.1	1359.4
47.5°	1395.4	1393.2	1405.5	1441.6	1504.6	1568.2	1603.0	1588.4	1578.9	1571.5	1526.5
50°	1439.9	1435.3	1449.4	1487.7	1558.0	1656.0	1747.0	1759.5	1755.5	1755.5	1726.8
52.5°	1473.1	1473.1	1483.2	1514.1	1585.6	1707.7	1870.9	1933.3	1938.3	1944.0	1942.3
55°	1454.5	1457.3	1482.6	1527.7	1603.0	1743.7	1973.3	2109.9	2138.1	2161.8	2188.7
57.5°	1390.9	1400.4	1434.2	1508.0	1607.6	1770.7	2086.9	2357.5	2436.9	2505.5	2612.4
60°	1298.0	1310.5	1359.4	1453.4	1574.3	1726.8	2126.8	2566.8	2692.8	2842.6	3121.7
62.5°	1138.9	1151.2	1199.1	1293.0	1396.5	1558.5	1961.5	2597.8	2799.3	3011.4	3433.4
65°	806.8	787.2	842.3	926.7	1045.4	1202.4	1585.0	2390.2	2680.0	2967.5	3488.5
67.5°	449.5	447.9	481.7	544.7	658.3	827.2	1092.1	1833.2	2099.9	2425.6	3065.4
70°	310.1	313.4	334.8	402.9	496.8	642.6	778.1	1151.2	1343.1	1564.1	2193.3
72.5°	217.7	225.1	236.9	277.4	373.6	541.2	795.0	688.1	783.8	934.6	1318.9
75°	127.8	132.7	141.2	160.9	212.6	361.8	823.2	604.9	604.9	640.3	797.8
77.5°	78.8	78.8	83.8	91.7	113.1	177.2	586.3	679.7	660.5	640.3	642.0
80°	40.5	43.3	50.7	54.6	63.0	81.0	263.3	634.1	695.4	736.5	707.9
82.5°	18.5	20.8	31.0	33.2	36.6	42.8	90.6	360.6	483.3	636.4	795.0
85°	9.5	9.5	16.3	20.2	22.0	19.7	33.2	145.7	220.5	336.5	526.6
87.5°	1.7	1.7	2.8	3.4	5.1	4.5	5.6	8.4	14.1	15.2	15.8
90°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0



REPORT NUMBER: P154778

CATALOG NUMBER: AVS-E02-LED-E-U-T2-8030

CANDELA DISTRIBUTION (continued):

	65°	66°	67°	68°	69°	70°	71°	72°	73°	74°	75°
0°	517.1	517.1	517.1	517.1	517.1	517.1	517.1	517.1	517.1	517.1	517.1
2.5°	527.3	527.8	527.3	526.6	525.5	525.5	525.5	525.0	525.0	525.0	524.4
5°	542.4	540.1	540.7	539.6	539.1	538.4	539.1	537.9	536.8	537.3	536.8
7.5°	561.6	560.4	558.1	558.1	557.6	556.5	556.5	554.8	554.2	553.1	552.5
10°	582.9	580.1	581.2	580.1	580.6	578.4	577.3	576.2	575.0	575.0	575.6
12.5°	604.9	604.2	602.6	601.5	601.5	599.8	600.3	599.8	598.1	597.5	595.9
15°	627.4	627.4	625.7	626.2	625.7	624.6	623.4	623.4	622.3	621.1	621.8
17.5°	653.8	653.8	653.8	653.8	654.4	652.6	653.3	652.1	651.0	653.3	653.3
20°	688.1	690.4	690.4	689.8	692.6	691.0	690.4	693.2	690.4	694.3	693.8
22.5°	727.6	729.7	729.7	732.0	732.5	734.3	735.4	734.3	736.5	738.8	738.8
25°	771.4	773.7	775.3	778.8	780.4	779.3	779.9	782.7	783.8	786.0	788.3
27.5°	817.5	818.1	820.3	824.2	827.2	828.2	828.8	833.3	833.9	835.0	837.2
30°	862.6	868.2	867.0	872.1	873.8	875.5	878.9	880.5	884.5	886.7	886.7
32.5°	915.4	914.3	918.9	922.8	925.6	928.4	931.2	933.5	935.8	936.8	942.5
35°	981.2	983.5	983.5	984.1	990.9	991.4	993.7	998.8	1000.4	1003.8	1006.0
37.5°	1046.5	1042.6	1042.1	1042.1	1039.8	1041.5	1042.1	1042.6	1044.9	1045.4	1047.7
40°	1119.7	1114.6	1110.2	1107.4	1102.8	1096.6	1095.5	1092.6	1094.4	1093.8	1094.4
42.5°	1219.9	1205.8	1195.1	1187.3	1178.2	1171.5	1166.4	1159.1	1154.0	1147.9	1146.7
45°	1347.6	1321.1	1303.1	1290.2	1277.2	1258.7	1248.0	1236.7	1226.6	1216.5	1208.1
47.5°	1515.2	1487.2	1458.4	1434.8	1414.5	1384.7	1354.3	1337.4	1317.7	1300.3	1288.0
50°	1712.7	1679.0	1665.5	1632.2	1606.9	1562.0	1524.2	1496.7	1457.3	1430.9	1407.8
52.5°	1914.7	1906.3	1899.0	1870.9	1841.0	1815.1	1782.0	1733.6	1693.6	1663.2	1616.0
55°	2189.8	2193.8	2191.0	2175.9	2165.1	2140.3	2126.8	2084.7	2066.6	2022.8	1973.3
57.5°	2653.0	2684.5	2724.4	2740.2	2761.6	2741.2	2764.9	2793.6	2722.2	2746.9	2702.5
60°	3244.4	3388.9	3475.0	3580.7	3649.9	3746.7	3764.2	3789.5	3782.2	3796.3	3825.0
62.5°	3605.5	3777.1	3942.0	4061.9	4190.2	4261.0	4346.5	4406.2	4468.1	4509.7	4497.9
65°	3711.9	3888.5	4038.2	4169.3	4284.1	4370.8	4450.1	4524.9	4581.8	4621.7	4645.3
67.5°	3321.3	3552.1	3709.6	3863.2	4011.2	4102.4	4168.7	4241.3	4324.6	4393.8	4407.4
70°	2499.4	2845.4	3068.7	3252.7	3426.6	3549.2	3642.1	3709.6	3774.3	3823.8	3877.8
72.5°	1563.1	1865.8	2121.2	2359.8	2544.4	2713.2	2791.4	2941.0	2921.3	2959.1	2999.6
75°	936.8	1084.2	1224.9	1393.2	1489.9	1630.6	1656.0	1680.6	1667.8	1625.5	1657.0
77.5°	651.0	675.2	674.1	664.5	654.4	629.6	597.5	580.1	568.3	551.4	558.1
80°	654.9	602.6	522.7	439.5	362.9	312.2	292.0	292.0	312.8	342.7	372.4
82.5°	782.7	726.9	648.2	542.4	429.8	349.9	296.5	275.1	279.1	309.4	347.8
85°	527.8	540.1	473.8	433.3	343.2	267.3	223.9	181.8	160.9	166.0	188.0
87.5°	19.2	23.1	8.4	11.3	7.9	6.7	6.7	7.4	5.1	6.2	5.6
90°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0



REPORT NUMBER: P154778

CATALOG NUMBER: AVS-E02-LED-E-U-T2-8030

CANDELA DISTRIBUTION (continued):

	76°	77°	78°	79°	80°	81°	82°	83°	84°	85°	86°
0°	517.1	517.1	517.1	517.1	517.1	517.1	517.1	517.1	517.1	517.1	517.1
2.5°	523.8	523.3	523.3	522.2	522.2	521.6	521.6	521.0	520.4	520.4	519.9
5°	536.2	535.6	534.5	534.0	532.8	532.8	532.2	531.2	531.2	530.1	529.4
7.5°	553.7	552.5	551.4	550.9	550.3	548.6	548.6	547.5	547.5	546.3	545.8
10°	574.5	573.4	572.2	572.7	571.1	570.6	569.4	569.4	567.8	567.2	567.2
12.5°	597.0	596.4	596.4	594.7	594.2	593.6	591.4	591.4	591.4	590.3	590.8
15°	621.1	621.8	620.1	621.8	621.1	619.5	619.5	619.5	617.2	620.1	617.8
17.5°	653.8	655.5	654.4	654.9	653.8	653.8	654.4	653.8	654.9	654.9	658.3
20°	694.3	694.9	697.7	696.6	696.6	696.1	697.1	697.7	700.0	698.9	701.0
22.5°	738.8	741.6	742.2	744.4	744.4	743.8	745.0	747.3	748.3	750.1	749.4
25°	789.4	791.1	793.4	790.6	795.0	795.0	796.2	799.0	799.6	799.6	803.5
27.5°	836.7	841.1	841.8	844.6	842.9	844.0	848.0	849.6	851.9	851.9	853.0
30°	890.2	891.8	893.0	896.3	895.8	896.3	896.9	899.7	899.7	902.5	905.3
32.5°	945.3	946.4	947.6	950.9	952.0	954.3	953.2	955.4	958.2	958.8	960.4
35°	1011.1	1012.2	1013.4	1018.4	1019.0	1022.9	1024.0	1022.9	1027.5	1024.6	1027.5
37.5°	1049.3	1054.4	1055.5	1059.0	1057.8	1060.6	1062.3	1064.6	1065.7	1068.0	1072.4
40°	1096.1	1097.7	1101.1	1102.8	1105.1	1105.6	1107.9	1109.5	1111.3	1116.3	1121.3
42.5°	1143.9	1146.1	1147.9	1150.1	1152.8	1155.1	1156.8	1161.9	1163.0	1166.4	1176.0
45°	1201.9	1200.7	1201.2	1201.9	1203.0	1205.8	1210.9	1216.0	1219.3	1227.2	1235.0
47.5°	1273.9	1266.5	1263.7	1259.3	1260.3	1266.5	1267.7	1276.2	1282.9	1290.2	1299.8
50°	1383.0	1363.3	1351.5	1339.7	1338.5	1342.0	1346.4	1355.4	1363.3	1372.8	1386.4
52.5°	1566.4	1528.7	1505.1	1472.4	1463.5	1461.8	1458.4	1463.5	1465.7	1478.7	1504.0
55°	1937.8	1868.1	1823.0	1772.3	1725.1	1711.1	1684.0	1689.6	1684.0	1691.9	1729.6
57.5°	2713.2	2657.4	2613.6	2548.8	2467.9	2381.8	2360.3	2272.0	2289.4	2340.1	2307.5
60°	3839.1	3818.8	3787.3	3756.4	3645.5	3583.0	3481.1	3469.9	3398.4	3399.1	3352.3
62.5°	4469.2	4495.1	4476.0	4466.9	4460.7	4441.0	4390.5	4329.6	4238.5	4172.6	4076.0
65°	4649.2	4627.4	4606.5	4603.7	4602.0	4634.1	4641.3	4598.7	4516.0	4413.5	4302.1
67.5°	4439.4	4427.0	4428.2	4404.5	4419.2	4474.8	4513.7	4501.9	4425.9	4302.1	4160.3
70°	3939.8	3915.5	3940.3	3971.3	3993.2	4025.3	4064.1	4073.7	4004.5	3877.3	3732.6
72.5°	2950.1	2954.0	2977.6	2986.0	3074.4	3065.4	3100.3	2986.6	2936.5	2815.5	2741.2
75°	1552.3	1527.0	1592.8	1453.4	1396.0	1436.0	1323.9	1216.5	1239.0	1257.5	1123.6
77.5°	548.6	513.2	453.0	428.7	356.7	302.2	247.0	222.8	209.8	203.1	194.7
80°	393.9	405.1	392.7	363.5	308.9	247.6	195.2	154.2	132.2	120.4	112.5
82.5°	398.3	442.8	462.5	454.1	404.6	306.1	202.0	128.8	95.6	79.9	74.3
85°	213.8	234.1	225.1	189.6	170.5	101.9	69.7	46.7	39.4	36.0	33.2
87.5°	8.4	6.7	5.6	5.6	6.2	6.7	5.6	6.2	5.6	5.6	5.6
90°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0



REPORT NUMBER: P154778

CATALOG NUMBER: AVS-E02-LED-E-U-T2-8030

CANDELA DISTRIBUTION (continued):

	87°	88°	89°	90°	95°	105°	115°	125°	135°	145°	155°
0°	517.1	517.1	517.1	517.1	517.1	517.1	517.1	517.1	517.1	517.1	517.1
2.5°	518.8	518.8	518.8	518.2	517.1	514.3	511.5	509.2	507.6	505.8	503.6
5°	528.9	527.8	527.8	527.8	523.3	518.8	514.8	510.9	507.6	504.7	502.5
7.5°	545.8	545.2	543.0	542.4	539.1	531.7	527.3	520.4	516.5	512.5	511.5
10°	566.0	565.5	564.9	564.4	559.9	552.5	546.9	540.7	535.1	529.4	523.8
12.5°	589.6	589.1	588.5	586.8	585.2	581.2	575.0	568.3	561.6	549.7	543.5
15°	619.0	620.1	619.0	618.3	617.2	617.8	613.9	604.2	593.6	578.4	565.5
17.5°	657.7	656.6	656.1	658.3	657.7	660.5	659.5	647.0	630.8	606.5	584.0
20°	700.5	700.5	702.8	704.5	709.5	716.8	713.5	698.2	668.4	634.7	605.4
22.5°	751.7	752.8	755.1	754.0	761.9	773.7	774.8	753.4	714.6	667.9	626.8
25°	805.2	806.3	804.0	807.5	820.3	837.2	840.6	810.3	759.1	698.2	644.8
27.5°	855.9	856.9	856.9	861.5	873.8	902.5	905.9	872.1	804.0	724.7	657.7
30°	905.3	909.8	911.0	912.1	930.7	970.6	977.9	928.9	843.4	744.4	666.7
32.5°	967.8	969.4	971.7	974.5	996.0	1044.9	1044.9	977.9	868.7	756.8	668.4
35°	1034.7	1035.3	1040.3	1040.9	1071.3	1120.2	1110.7	1018.4	886.7	754.0	656.1
37.5°	1075.2	1077.5	1082.6	1089.3	1121.3	1190.6	1168.6	1053.3	890.2	735.4	628.0
40°	1125.3	1129.8	1134.9	1141.7	1189.4	1262.1	1217.6	1075.2	876.1	698.9	585.7
42.5°	1179.4	1185.5	1193.4	1205.8	1262.6	1325.1	1254.7	1078.7	844.0	657.7	535.6
45°	1240.1	1251.4	1260.3	1275.0	1339.2	1379.7	1277.2	1059.0	803.5	603.7	482.2
47.5°	1310.5	1319.5	1335.2	1351.0	1415.1	1416.8	1279.5	1020.6	748.3	549.7	425.4
50°	1397.1	1402.7	1426.3	1436.0	1496.2	1455.6	1263.2	968.9	690.4	488.9	362.4
52.5°	1512.4	1520.3	1550.7	1565.3	1608.1	1508.5	1240.1	912.6	624.0	420.8	297.6
55°	1740.3	1774.6	1796.1	1821.3	1848.9	1628.3	1229.9	852.4	549.1	342.1	235.8
57.5°	2380.1	2368.8	2416.1	2473.5	2472.8	1902.4	1290.8	800.6	460.8	261.7	181.1
60°	3333.2	3343.9	3319.7	3354.0	3244.9	2242.2	1374.0	746.1	361.2	194.7	138.4
62.5°	4041.6	3979.7	3945.4	3904.9	3664.6	2279.4	1313.3	634.1	262.8	136.7	106.3
65°	4209.2	4136.7	4063.0	3985.9	3623.5	2054.8	1077.5	465.3	169.9	94.0	84.4
67.5°	4043.8	3927.4	3833.4	3754.1	3320.3	1703.2	787.8	285.8	97.3	76.0	72.0
70°	3615.1	3486.2	3334.3	3245.4	2795.9	1255.3	504.7	154.2	74.8	67.6	65.8
72.5°	2646.2	2540.4	2374.4	2272.5	2007.6	763.0	281.9	86.6	69.7	64.7	62.5
75°	1030.8	975.6	906.4	912.1	814.2	337.6	127.8	74.8	68.1	63.6	61.3
77.5°	177.2	172.7	159.8	159.8	181.8	123.2	85.0	75.4	67.6	62.5	58.5
80°	106.3	104.0	99.1	97.9	94.5	86.6	81.6	76.5	66.4	59.1	54.0
82.5°	69.7	66.9	65.3	64.7	70.4	76.0	76.5	76.0	63.0	51.2	43.9
85°	29.8	29.8	29.8	30.4	40.5	61.3	63.0	67.6	51.8	40.0	31.5
87.5°	5.1	6.2	6.2	6.7	7.4	13.5	16.9	22.0	17.4	16.9	15.2
90°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0



REPORT NUMBER: P154778

CATALOG NUMBER: AVS-E02-LED-E-U-T2-8030

CANDELA DISTRIBUTION (continued):

	165°	175°	180°
0°	517.1	517.1	517.1
2.5°	503.0	501.9	501.9
5°	501.3	500.2	500.7
7.5°	508.1	505.8	506.4
10°	520.4	518.2	517.1
12.5°	536.2	533.4	533.4
15°	552.5	545.8	545.2
17.5°	566.0	557.6	556.5
20°	581.2	569.9	568.3
22.5°	595.3	580.1	577.8
25°	605.4	586.8	584.0
27.5°	609.9	588.0	585.7
30°	613.3	588.5	585.2
32.5°	609.9	583.5	580.6
35°	591.4	562.7	560.9
37.5°	559.3	527.3	525.0
40°	517.1	483.3	477.7
42.5°	463.1	431.6	425.4
45°	410.8	374.7	371.9
47.5°	354.5	320.1	321.9
50°	295.4	264.5	263.9
52.5°	239.2	212.1	210.5
55°	188.5	169.3	167.7
57.5°	149.1	139.0	137.3
60°	121.6	116.5	114.8
62.5°	97.9	96.2	95.6
65°	81.6	81.6	81.6
67.5°	70.9	71.5	71.5
70°	65.3	65.8	65.3
72.5°	63.0	64.7	64.7
75°	61.3	62.5	60.2
77.5°	60.2	60.7	56.8
80°	59.7	59.1	51.8
82.5°	51.8	50.1	43.9
85°	47.3	36.0	30.4
87.5°	24.1	16.9	13.0
90°	0.0	0.0	0.0

(END OF REPORT)