

Scaled data based on original data using  
LM-79-08 Approved Method: Electrical and Photometric Measurements of Solid-  
State Lighting Products

Test Report Prepared for  
Cooper Lighting Solutions  
(formerly Eaton)

Brand: STREETWORKS

Report Number: P691187

Luminaire Tested: **CRTK2-C013-D-U-T5R-7050-U0**

Issue Date: 6/13/2023

**Test Information**

Test Method: LM-79-08  
Report Number: P691187  
TEST IS SCALED FROM IESNA LM-79-08 TEST DATA (G2-2301-903-19)  
Test Lab: INNOVATION CENTER  
Issue Date: 6/13/2023  
Manufacturer: COOPER LIGHTING SOLUTIONS (FORMERLY EATON)  
Product Line: STREETWORKS  
Catalog Number: CRTK2-C013-D-U-T5R-7050-U0  
Description: CARETAKER AREA AND ROADWAY LUMINAIRE  
(1) 70 CRI, 5000K LED WITH TYPE V ROUND OPTIC AND UO SHIELD  
Light Source: -  
Ballast/Driver: ELECTRONIC DRIVER

**Summary**

Lumens per Lamp: N/A  
Luminaire Lumens: 3204 lumens  
Efficiency: N/A  
Efficacy: 157.1 lumens/watt  
Luminous Opening: Circular (Dia: 0.33' x H: 0')  
IES Classification: Type V - Short  
BUG Rating: B2 - U0 - G1


Input Watts (W): 20.4  
Input Voltage (V): NR  
Input Current (Ain): NR  
Voltage Rise (V): NR  
Power Factor: NR  
Total Harmonic Distortion (THDi): NR  
Frequency (hertz): 60  
Stabilization Time: NR  
Operation Time: NR  
Ambient Temperature (°C): NR  
Test Distance: 24 FT



REPORT NUMBER: P691187  
 CATALOG NUMBER: CRTK2-C013-D-U-T5R-7050-U0

### Iso-Footcandle Lines of Horizontal Illumination


× Max cd  
 - - - 1/2 Max cd



Based on 25 foot mounting height. Maximum calculated value = 0.5 fc  
 Type V - Short - N/A

REPORT NUMBER: P691187  
CATALOG NUMBER: CRTK2-C013-D-U-T5R-7050-U0

### Luminous Intensity Polar Plot



— Vertical Plane Through 0-Deg Lateral      - - - Horizontal Cone Through 67.5-Deg Vertical

REPORT NUMBER: P691187  
 CATALOG NUMBER: CRTK2-C013-D-U-T5R-7050-U0


**FLUX DISTRIBUTION:**

		Downward	Upward	Total
<b>House Side</b>	Lumens	1602.0	0.0	1602.0
	% Fixture	50.0	0.0	50.0
<b>Street Side</b>	Lumens	1602.0	0.0	1602.0
	% Fixture	50.0	0.0	50.0
<b>Total</b>	Lumens	3204.0	0.0	3204.0
	% Fixture	100.0	0.0	100.0

**ZONAL LUMENS:**

Zone	Lumens	% Fixture
0°-10°	27.9	0.9
10°-20°	75.6	2.4
20°-30°	130.3	4.1
30°-40°	221.2	6.9
40°-50°	390.4	12.2
50°-60°	665.3	20.8
60°-70°	956.9	29.9
70°-80°	695.8	21.7
80°-90°	40.6	1.3
90°-100°	0.0	0.0
100°-110°	0.0	0.0
110°-120°	0.0	0.0
120°-130°	0.0	0.0
130°-140°	0.0	0.0
140°-150°	0.0	0.0
150°-160°	0.0	0.0
160°-170°	0.0	0.0
170°-180°	0.0	0.0
0°-90°	3204.0	100.0
0°-180°	3204.0	100.0

**Coefficient of Utilization**




REPORT NUMBER: P691187  
 CATALOG NUMBER: CRTK2-C013-D-U-T5R-7050-U0

**LUMINAIRE CLASSIFICATION SYSTEM LUMEN TABLE AND BUG RATING:**

Zone	Lumens	% Fixture	Zone Rating/Lumen Limit		
			B	U	G
FL (0°-30°)	116.9	3.6			
FM (30°-60°)	638.4	19.9			
FH (60°-80°)	826.3	25.8			G1/1800
FVH (80°-90°)	20.3	0.6			G1/100
BL (0°-30°)	116.9	3.6	B1/500		
BM (30°-60°)	638.4	19.9	B1/1000		
BH (60°-80°)	826.3	25.8	B2/1000		G1/1800
BVH (80°-90°)	20.3	0.6			G1/100
UL (90°-100°)	0.0	0.0		U0/0	
UH (100°-180°)	0.0	0.0		U0/0	

**BUG Rating: B2-U0-G1**

Type V Short



REPORT NUMBER: P691187  
CATALOG NUMBER: CRTK2-C013-D-U-T5R-7050-U0

**CANDELA DISTRIBUTION (FULL):**

	0°
0°	311.6
2.5°	306.6
5°	300.5
7.5°	289.4
10°	277.2
12.5°	269.1
15°	265.1
17.5°	264.1
20°	265.1
22.5°	270.1
25°	278.2
27.5°	289.4
30°	302.5
32.5°	320.7
35°	346.0
37.5°	377.4
40°	409.7
42.5°	449.2
45°	495.7
47.5°	550.4
50°	610.1
52.5°	673.8
55°	740.6
57.5°	803.3
60°	867.0
62.5°	925.7
65°	994.5
67.5°	1022.9
70°	952.0
72.5°	842.8
75°	702.1
77.5°	506.9
80°	226.6
82.5°	29.3
85°	6.1
87.5°	1.0
90°	0.0

(END OF REPORT)