

Scaled data based on original data using  
LM-79-08 Approved Method: Electrical and Photometric Measurements of Solid-  
State Lighting Products

Test Report Prepared for  
Cooper Lighting Solutions  
(formerly Eaton)

Brand: STREETWORKS

Report Number: P320525

Luminaire Tested: **GAN-SA1C-722-U-SLL**

Issue Date: 3/3/2020

**Test Information**

Test Method: LM-79-08  
Report Number: P320525  
TEST IS SCALED FROM IESNA LM-79-08 TEST DATA (G2-1903-205-26)  
Test Lab: INNOVATION CENTER  
Issue Date: 3/3/2020  
Manufacturer: COOPER LIGHTING SOLUTIONS (FORMERLY EATON)  
Product Line: STREETWORKS  
Catalog Number: GAN-SA1C-722-U-SLL  
Description: GALLEON AREA AND ROADWAY LUMINAIRE  
(1) 70 CRI, 2200K, 1050mA LIGHTSQUARE WITH 16 LEDS AND SPILL LIGHT  
ELIMINATOR LEFT OPTICS  
Light Source: -  
Ballast/Driver: ELECTRONIC DRIVER

**Summary**

Lumens per Lamp: N/A  
Luminaire Lumens: 4786 lumens  
Efficiency: N/A  
Efficacy: 81.1 lumens/watt  
Luminous Opening: Rectangular (W 0.5' x L: 0.5' x H: 0')  
IES Classification: Type III - Medium  
BUG Rating: B1 - U0 - G2


Input Watts (W): 59  
Input Voltage (V): NR  
Input Current (Ain): NR  
Voltage Rise (V): NR  
Power Factor: NR  
Total Harmonic Distortion (THDi): NR  
Frequency (hertz): 60  
Stabilization Time: NR  
Operation Time: NR  
Ambient Temperature (°C): NR  
Test Distance: 24 FT



REPORT NUMBER: P320525  
 CATALOG NUMBER: GAN-SA1C-722-U-SLL

### Iso-Footcandle Lines of Horizontal Illumination


✕ Max cd  
 - - - 1/2 Max cd



Based on 25 foot mounting height. Maximum calculated value = 2.9 fc  
 Type III - Medium - N/A

REPORT NUMBER: P320525  
CATALOG NUMBER: GAN-SA1C-722-U-SLL

### Luminous Intensity Polar Plot



— Vertical Plane Through 75-Deg Lateral      - - - Horizontal Cone Through 67.5-Deg Vertical

REPORT NUMBER: P320525  
 CATALOG NUMBER: GAN-SA1C-722-U-SLL


**FLUX DISTRIBUTION:**

		Downward	Upward	Total
<b>House Side</b>	Lumens	842.9	0.0	842.9
	% Fixture	17.6	0.0	17.6
<b>Street Side</b>	Lumens	3943.1	0.0	3943.1
	% Fixture	82.4	0.0	82.4
<b>Total</b>	Lumens	4786.0	0.0	4786.0
	% Fixture	100.0	0.0	100.0

**ZONAL LUMENS:**

Zone	Lumens	% Fixture
0°-10°	112.5	2.4
10°-20°	233.8	4.9
20°-30°	332.5	6.9
30°-40°	479.1	10.0
40°-50°	675.2	14.1
50°-60°	938.6	19.6
60°-70°	1135.1	23.7
70°-80°	697.7	14.6
80°-90°	181.6	3.8
90°-100°	0.0	0.0
100°-110°	0.0	0.0
110°-120°	0.0	0.0
120°-130°	0.0	0.0
130°-140°	0.0	0.0
140°-150°	0.0	0.0
150°-160°	0.0	0.0
160°-170°	0.0	0.0
170°-180°	0.0	0.0
0°-90°	4786.0	100.0
0°-180°	4786.0	100.0

**Coefficient of Utilization**




REPORT NUMBER: P320525  
 CATALOG NUMBER: GAN-SA1C-722-U-SLL

**LUMINAIRE CLASSIFICATION SYSTEM LUMEN TABLE AND BUG RATING:**

Zone	Lumens	% Fixture	Zone Rating/Lumen Limit		
			B	U	G
FL (0°-30°)	475.2	9.9			
FM (30°-60°)	1710.3	35.7			
FH (60°-80°)	1596.5	33.4			G1/1800
FVH (80°-90°)	161.2	3.4			G2/225
BL (0°-30°)	203.6	4.3	B1/500		
BM (30°-60°)	382.6	8.0	B1/1000		
BH (60°-80°)	236.3	4.9	B1/500		G1/500
BVH (80°-90°)	20.4	0.4			G1/100
UL (90°-100°)	0.0	0.0		U0/0	
UH (100°-180°)	0.0	0.0		U0/0	

**BUG Rating: B1-U0-G2**  
 Type III Medium





REPORT NUMBER: P320525

CATALOG NUMBER: GAN-SA1C-722-U-SLL

**CANDELA DISTRIBUTION (FULL):**

	0°	5°	10°	15°	20°	25°	30°	35°	40°	45°	50°
0°	1458.1	1458.1	1458.1	1458.1	1458.1	1458.1	1458.1	1458.1	1458.1	1458.1	1458.1
2.5°	1554.1	1574.6	1588.8	1602.7	1613.6	1624.4	1640.0	1655.7	1658.8	1661.7	1655.5
5°	1544.9	1594.9	1637.4	1679.7	1718.9	1758.1	1781.6	1805.2	1810.0	1814.8	1800.0
7.5°	1446.0	1519.7	1593.4	1667.0	1734.6	1802.1	1843.3	1884.2	1893.6	1902.8	1878.7
10°	1333.5	1419.2	1509.7	1600.2	1689.2	1778.2	1837.7	1897.2	1909.1	1920.9	1890.9
12.5°	1248.0	1341.5	1438.2	1534.8	1628.8	1722.5	1784.1	1845.7	1860.5	1875.2	1853.4
15°	1215.1	1317.6	1408.5	1499.4	1581.3	1663.0	1713.5	1763.9	1770.0	1775.9	1772.5
17.5°	1248.0	1361.1	1443.3	1525.4	1570.0	1614.4	1634.7	1654.8	1661.5	1668.0	1676.8
20°	1344.2	1466.3	1524.3	1582.1	1580.2	1578.1	1568.3	1558.3	1556.6	1554.9	1579.8
22.5°	1481.6	1623.4	1646.6	1669.5	1615.7	1562.0	1529.3	1496.3	1489.8	1483.1	1509.6
25°	1642.9	1793.9	1789.7	1785.3	1682.9	1580.3	1518.0	1455.6	1448.3	1441.0	1463.6
27.5°	1818.4	1962.7	1935.1	1907.6	1768.4	1629.3	1538.8	1448.3	1441.0	1433.8	1453.7
30°	1955.6	2086.5	2042.3	1998.1	1840.6	1683.1	1575.6	1468.0	1456.2	1444.1	1468.6
32.5°	2071.7	2183.1	2123.8	2064.5	1899.1	1733.8	1617.5	1501.1	1482.6	1464.0	1496.7
35°	2192.7	2279.5	2196.1	2112.5	1951.4	1790.1	1667.0	1543.8	1521.0	1498.3	1543.2
37.5°	2328.7	2400.9	2281.1	2161.1	2010.1	1859.1	1741.3	1623.2	1599.9	1576.5	1633.9
40°	2472.4	2532.5	2372.7	2212.9	2074.4	1935.9	1844.0	1752.0	1729.8	1707.4	1777.1
42.5°	2598.1	2642.0	2458.1	2274.2	2151.9	2029.4	1964.8	1899.9	1899.7	1899.3	1969.9
45°	2692.9	2730.9	2529.2	2327.4	2227.5	2127.4	2093.7	2060.1	2087.0	2114.0	2177.9
47.5°	2771.5	2797.3	2588.9	2380.4	2314.0	2247.6	2252.6	2257.5	2312.4	2367.4	2408.5
50°	2861.4	2840.6	2643.1	2445.4	2425.0	2404.5	2449.3	2493.8	2557.0	2619.9	2647.9
52.5°	2958.8	2903.5	2716.6	2529.4	2552.4	2575.4	2666.4	2757.5	2821.2	2885.0	2895.5
55°	3133.9	3049.1	2851.7	2654.0	2698.2	2742.2	2876.0	3009.5	3059.3	3109.0	3112.9
57.5°	3331.2	3256.0	3040.9	2825.8	2873.3	2920.7	3075.2	3229.4	3283.2	3336.7	3329.3
60°	3407.2	3410.8	3220.6	3030.2	3078.0	3125.9	3276.3	3426.7	3488.5	3550.1	3533.6
62.5°	3330.6	3420.4	3318.8	3217.0	3260.4	3303.6	3451.0	3598.3	3661.6	3725.0	3696.3
65°	3179.3	3268.2	3313.8	3359.3	3373.7	3388.0	3525.6	3663.0	3711.6	3760.0	3745.5
67.5°	2986.8	3058.7	3226.7	3394.5	3365.6	3336.7	3401.2	3465.7	3515.7	3565.6	3557.4
70°	2763.8	2849.6	3073.6	3297.7	3155.7	3013.6	2987.0	2960.4	3014.3	3068.1	3034.8
72.5°	2364.1	2493.5	2732.5	2971.3	2709.7	2448.1	2357.2	2266.3	2334.6	2403.0	2350.0
75°	1785.7	1957.3	2221.4	2485.2	2173.1	1861.1	1739.7	1618.4	1677.2	1735.9	1699.6
77.5°	1241.9	1457.1	1717.2	1977.2	1660.0	1342.5	1252.4	1162.1	1179.7	1197.1	1191.0
80°	846.7	988.3	1169.7	1350.9	1139.7	928.4	935.5	942.4	934.2	925.7	938.0
82.5°	531.0	630.7	770.8	910.6	798.5	686.4	750.7	815.0	783.4	751.6	763.5
85°	299.1	359.9	496.9	633.7	590.7	547.4	585.1	622.6	573.7	524.7	546.3
87.5°	57.0	94.9	275.0	454.8	412.9	371.0	322.4	273.8	209.0	144.1	210.5
90°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
92.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
95°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
97.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
100°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
102.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
105°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
107.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
110°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0



REPORT NUMBER: P320525  
 CATALOG NUMBER: GAN-SA1C-722-U-SLL

**CANDELA DISTRIBUTION (continued):**

	0°	5°	10°	15°	20°	25°	30°	35°	40°	45°	50°
112.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
115°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
117.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
120°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
122.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
125°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
127.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
130°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
132.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
135°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
137.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
140°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
142.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
145°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
147.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
150°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
152.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
155°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
157.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
160°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
162.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
165°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
167.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
170°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
172.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
175°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
177.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
180°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0





REPORT NUMBER: P320525

CATALOG NUMBER: GAN-SA1C-722-U-SLL

**CANDELA DISTRIBUTION (continued):**

	55°	60°	65°	70°	75°	80°	85°	90°	95°	100°	105°
0°	1458.1	1458.1	1458.1	1458.1	1458.1	1458.1	1458.1	1458.1	1458.1	1458.1	1458.1
2.5°	1649.4	1646.2	1642.9	1631.2	1619.4	1601.8	1587.2	1562.0	1548.2	1527.3	1506.5
5°	1785.1	1764.4	1743.8	1708.2	1672.4	1632.6	1586.9	1536.1	1497.9	1448.1	1398.4
7.5°	1854.6	1806.3	1757.9	1689.6	1621.1	1559.5	1487.2	1419.8	1362.4	1297.7	1233.1
10°	1860.9	1788.5	1716.0	1627.2	1538.3	1463.4	1380.2	1305.4	1236.5	1162.3	1087.8
12.5°	1831.4	1754.5	1677.4	1579.6	1481.6	1396.7	1307.1	1223.3	1146.9	1065.2	983.3
15°	1769.0	1707.6	1646.0	1554.3	1462.7	1376.9	1290.1	1190.8	1104.5	1020.8	937.0
17.5°	1685.4	1656.3	1627.0	1560.8	1494.4	1420.2	1336.0	1219.5	1118.4	1027.5	936.7
20°	1604.5	1615.2	1625.7	1599.3	1572.9	1513.4	1439.9	1309.0	1180.0	1061.2	942.2
22.5°	1535.8	1587.2	1638.5	1659.0	1679.3	1643.5	1586.1	1434.7	1264.0	1108.9	953.7
25°	1486.0	1571.4	1656.7	1724.8	1792.7	1776.9	1732.7	1587.4	1375.4	1177.6	979.5
27.5°	1473.6	1578.2	1682.9	1788.5	1894.0	1908.7	1896.5	1748.4	1508.2	1262.9	1017.4
30°	1493.1	1599.1	1704.9	1833.5	1961.9	2020.6	2037.1	1882.5	1660.0	1362.4	1064.7
32.5°	1529.5	1633.4	1737.3	1877.3	2017.2	2106.0	2158.4	2005.1	1765.8	1437.4	1108.9
35°	1588.2	1685.4	1782.6	1928.4	2074.2	2189.0	2284.7	2131.8	1859.7	1489.8	1119.8
37.5°	1691.1	1774.8	1858.4	1993.1	2127.6	2276.5	2420.2	2271.3	1961.3	1540.4	1119.2
40°	1846.7	1905.8	1964.8	2078.6	2192.3	2379.6	2573.6	2426.9	2073.6	1595.1	1116.5
42.5°	2040.5	2071.0	2101.2	2191.3	2281.5	2487.3	2712.9	2579.0	2180.8	1646.0	1111.2
45°	2241.7	2249.7	2257.7	2314.6	2371.2	2572.7	2807.9	2693.2	2274.4	1690.2	1105.8
47.5°	2449.5	2421.9	2394.3	2416.9	2439.5	2638.1	2875.6	2779.9	2368.3	1739.2	1109.8
50°	2675.8	2599.1	2522.4	2510.5	2498.6	2703.6	2955.4	2890.1	2481.2	1810.5	1139.9
52.5°	2905.8	2779.3	2652.9	2606.0	2558.9	2781.6	3061.2	3027.3	2642.3	1921.1	1199.8
55°	3116.7	2955.8	2794.8	2731.7	2668.5	2901.0	3190.4	3228.8	2848.8	2062.5	1276.1
57.5°	3321.6	3139.3	2956.9	2898.4	2839.8	3076.5	3354.0	3409.6	3057.4	2198.2	1338.9
60°	3517.2	3336.7	3156.1	3109.2	3062.2	3294.6	3530.8	3490.2	3164.9	2261.7	1358.4
62.5°	3667.6	3524.1	3380.6	3355.9	3331.0	3515.3	3666.6	3458.8	3096.6	2199.2	1301.7
65°	3730.9	3649.2	3567.3	3590.5	3613.4	3682.1	3700.5	3367.0	2881.9	2023.9	1165.9
67.5°	3548.9	3565.6	3582.2	3679.4	3776.5	3729.2	3599.8	3186.0	2576.3	1775.5	974.7
70°	3001.3	3101.2	3200.9	3430.9	3660.7	3555.8	3330.2	2861.0	2208.5	1489.5	770.2
72.5°	2296.8	2409.1	2521.2	2862.6	3203.8	3107.1	2830.8	2350.0	1770.7	1189.4	607.9
75°	1663.0	1789.9	1916.5	2293.1	2669.7	2535.6	2117.5	1682.5	1345.0	907.9	470.7
77.5°	1184.6	1269.6	1354.6	1726.5	2098.3	1879.8	1409.5	1132.2	930.9	631.1	331.0
80°	950.2	924.2	898.2	1105.4	1312.7	1276.3	932.3	727.1	644.3	422.9	201.5
82.5°	775.2	711.6	648.1	745.7	843.3	837.9	647.0	533.5	479.5	293.9	108.3
85°	567.7	542.3	516.8	603.1	689.4	615.8	438.2	339.1	373.9	216.4	58.9
87.5°	276.9	316.3	355.5	457.3	558.9	419.6	133.0	65.8	91.1	59.9	28.5
90°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
92.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
95°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
97.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
100°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
102.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
105°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
107.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
110°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0



REPORT NUMBER: P320525  
 CATALOG NUMBER: GAN-SA1C-722-U-SLL

**CANDELA DISTRIBUTION (continued):**

	55°	60°	65°	70°	75°	80°	85°	90°	95°	100°	105°
112.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
115°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
117.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
120°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
122.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
125°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
127.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
130°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
132.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
135°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
137.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
140°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
142.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
145°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
147.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
150°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
152.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
155°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
157.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
160°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
162.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
165°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
167.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
170°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
172.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
175°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
177.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
180°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0



REPORT NUMBER: P320525  
 CATALOG NUMBER: GAN-SA1C-722-U-SLL

**CANDELA DISTRIBUTION (continued):**

	110°	115°	120°	125°	130°	135°	140°	145°	150°	155°	160°
0°	1458.1	1458.1	1458.1	1458.1	1458.1	1458.1	1458.1	1458.1	1458.1	1458.1	1458.1
2.5°	1491.0	1475.3	1457.5	1439.7	1419.4	1399.0	1386.9	1374.6	1361.4	1348.2	1333.3
5°	1365.5	1332.6	1295.2	1257.9	1221.0	1184.1	1164.2	1144.3	1123.2	1102.0	1083.6
7.5°	1185.2	1137.2	1085.5	1033.7	987.7	941.6	913.1	884.4	858.4	832.2	810.2
10°	1026.6	965.4	913.5	861.5	826.8	792.2	766.0	739.8	714.5	689.0	664.7
12.5°	922.1	860.9	828.0	795.1	766.4	737.6	707.4	677.0	642.4	607.5	582.1
15°	881.4	825.7	789.1	752.4	713.9	675.3	638.1	601.0	560.1	519.1	490.2
17.5°	863.7	790.8	739.8	688.5	637.8	587.1	544.0	501.0	456.2	411.4	382.1
20°	845.2	748.2	679.7	611.0	545.9	480.9	432.1	383.3	343.3	303.3	280.9
22.5°	828.3	702.8	616.9	530.8	453.9	377.0	329.1	281.1	256.6	232.1	223.1
25°	821.5	663.2	557.6	452.0	370.8	289.5	255.5	221.4	212.0	202.4	197.9
27.5°	822.6	627.8	507.6	387.3	314.2	241.1	217.8	194.4	188.7	182.7	179.9
30°	827.0	589.4	460.6	331.8	271.5	211.2	196.1	180.8	174.7	168.6	164.9
32.5°	832.0	554.9	424.2	293.3	244.2	194.8	182.4	169.7	163.8	157.9	154.2
35°	823.4	526.8	399.3	271.9	226.6	181.0	170.5	159.8	153.3	146.8	143.3
37.5°	808.8	498.5	380.0	261.4	215.1	168.6	160.9	153.1	146.4	139.5	136.2
40°	795.6	474.5	365.7	256.6	208.8	160.7	154.2	147.7	140.8	133.8	129.9
42.5°	784.9	458.5	351.5	244.5	203.0	161.3	152.1	142.7	136.0	129.4	125.1
45°	776.9	447.9	340.4	232.9	197.7	162.5	150.8	139.1	132.4	125.5	120.5
47.5°	776.1	442.4	332.6	222.7	187.5	152.1	147.3	142.6	132.8	122.8	117.1
50°	786.6	433.4	323.4	213.2	177.8	142.4	148.9	155.2	138.5	121.7	114.4
52.5°	808.6	417.5	308.8	200.2	165.9	131.5	141.6	151.5	137.2	122.7	113.3
55°	835.2	394.2	286.8	179.3	150.2	120.9	129.9	138.7	129.7	120.5	109.3
57.5°	851.9	364.7	259.1	153.5	132.6	111.7	116.9	121.9	118.3	114.6	103.1
60°	841.9	325.5	227.9	130.1	117.1	104.1	103.1	102.0	107.3	112.7	99.5
62.5°	793.3	284.9	200.3	115.8	106.0	96.1	94.0	91.7	100.5	109.1	95.1
65°	711.2	256.6	182.9	109.3	98.4	87.4	85.2	82.9	85.5	88.2	81.7
67.5°	607.0	239.2	173.0	106.8	93.6	80.2	77.5	74.8	74.2	73.7	71.4
70°	499.4	228.5	166.5	104.5	88.4	72.1	69.7	67.2	66.4	65.4	63.7
72.5°	417.5	227.1	165.7	104.3	84.2	64.1	61.8	59.5	58.6	57.4	56.1
75°	341.9	213.2	157.3	101.4	78.5	55.3	53.2	51.1	50.3	49.4	48.2
77.5°	253.7	176.4	132.2	88.0	67.2	46.3	44.2	41.9	41.7	41.3	40.4
80°	164.6	127.6	94.5	61.4	49.0	36.4	34.6	32.7	32.9	33.1	32.3
82.5°	91.5	74.4	57.8	41.1	33.5	25.8	25.1	24.1	24.7	25.1	24.1
85°	48.2	37.5	31.0	24.5	19.3	14.2	14.2	14.0	14.7	15.5	14.7
87.5°	20.9	13.2	11.3	9.2	5.2	1.0	1.1	1.1	1.5	1.9	1.7
90°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
92.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
95°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
97.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
100°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
102.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
105°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
107.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
110°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0



REPORT NUMBER: P320525  
 CATALOG NUMBER: GAN-SA1C-722-U-SLL

**CANDELA DISTRIBUTION (continued):**

	110°	115°	120°	125°	130°	135°	140°	145°	150°	155°	160°
112.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
115°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
117.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
120°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
122.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
125°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
127.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
130°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
132.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
135°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
137.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
140°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
142.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
145°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
147.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
150°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
152.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
155°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
157.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
160°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
162.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
165°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
167.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
170°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
172.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
175°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
177.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
180°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0



REPORT NUMBER: P320525  
 CATALOG NUMBER: GAN-SA1C-722-U-SLL

**CANDELA DISTRIBUTION (continued):**

	165°	170°	175°	180°	185°	190°	195°	200°	205°	210°	215°
0°	1458.1	1458.1	1458.1	1458.1	1458.1	1458.1	1458.1	1458.1	1458.1	1458.1	1458.1
2.5°	1318.2	1304.2	1290.1	1274.6	1277.4	1265.6	1253.7	1246.3	1238.8	1236.5	1234.2
5°	1065.2	1049.4	1033.3	1018.9	1031.4	1023.0	1014.5	1013.4	1012.0	1012.0	1011.9
7.5°	788.2	771.1	753.9	742.1	754.3	752.8	751.2	759.5	767.7	774.4	780.9
10°	640.4	619.8	598.9	581.3	578.3	569.5	560.5	562.4	564.1	571.4	578.6
12.5°	556.6	531.9	507.3	486.6	477.2	462.7	447.9	438.8	429.6	430.5	431.3
15°	461.2	437.2	413.1	395.3	389.4	378.1	366.8	355.3	343.7	338.9	333.9
17.5°	352.7	333.5	314.2	302.3	302.3	299.1	295.8	290.1	284.2	279.4	274.4
20°	258.5	248.4	238.0	233.1	234.6	234.8	234.8	237.7	240.5	239.0	237.5
22.5°	213.9	210.3	206.7	204.6	205.3	205.5	205.7	208.4	210.9	212.8	214.5
25°	193.1	190.8	188.5	187.7	189.4	189.6	189.6	191.3	193.1	195.0	196.9
27.5°	176.8	175.8	174.9	173.6	175.3	175.3	175.1	177.0	178.7	180.4	182.0
30°	161.3	161.7	161.9	161.5	162.6	163.4	164.0	165.3	166.5	167.8	169.2
32.5°	150.4	149.8	149.3	148.9	151.4	152.7	154.0	155.4	156.5	157.1	157.7
35°	139.9	138.5	137.2	136.2	138.5	140.3	142.0	144.5	146.8	147.1	147.5
37.5°	132.8	131.1	129.4	128.2	129.2	129.9	130.7	133.4	136.0	137.6	138.9
40°	126.1	124.4	122.7	121.7	122.3	122.5	122.7	124.0	125.1	128.0	130.7
42.5°	120.7	118.6	116.5	115.4	115.8	116.1	116.3	116.1	116.0	118.6	121.3
45°	115.4	113.1	110.8	109.5	109.6	109.6	109.6	109.3	108.7	110.0	111.4
47.5°	111.2	108.5	105.8	104.5	104.1	103.7	103.3	103.1	102.8	103.7	104.5
50°	107.0	104.1	101.0	99.5	98.5	98.2	97.8	97.6	97.2	98.2	98.9
52.5°	103.7	100.3	96.8	94.3	93.4	92.8	92.2	92.4	92.4	92.8	93.0
55°	98.0	94.9	91.7	89.9	88.2	87.8	87.4	88.0	88.4	88.4	88.4
57.5°	91.7	88.8	85.7	84.6	83.0	83.0	82.9	83.6	84.2	84.6	85.0
60°	86.1	82.9	79.6	78.6	78.1	77.9	77.7	78.6	79.4	80.2	80.9
62.5°	80.9	77.5	74.1	72.9	72.7	72.9	72.9	73.9	74.6	75.4	76.2
65°	75.2	71.8	68.1	67.0	67.4	67.9	68.5	69.3	69.8	70.6	71.4
67.5°	68.9	66.0	63.0	61.8	62.0	62.8	63.5	64.1	64.5	65.2	66.0
70°	62.0	59.5	57.0	56.3	56.1	57.0	57.8	58.2	58.6	59.5	60.3
72.5°	54.5	52.4	50.3	49.8	49.9	50.5	51.1	51.7	52.0	53.0	53.8
75°	46.9	45.0	43.1	42.7	43.1	43.6	44.2	44.6	45.0	46.1	47.1
77.5°	39.4	37.3	35.0	34.8	35.4	36.0	36.4	36.9	37.5	39.0	40.6
80°	31.6	29.3	26.8	26.6	27.2	27.7	28.3	28.9	29.5	31.4	33.1
82.5°	23.2	20.5	17.8	17.4	19.3	19.9	20.5	21.4	22.2	23.9	25.6
85°	14.0	11.3	8.6	8.4	10.1	11.1	12.1	13.2	14.2	15.7	17.2
87.5°	1.5	0.8	0.0	0.0	0.2	1.0	1.7	2.7	3.6	5.2	6.5
90°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
92.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
95°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
97.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
100°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
102.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
105°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
107.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
110°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0



REPORT NUMBER: P320525  
 CATALOG NUMBER: GAN-SA1C-722-U-SLL

**CANDELA DISTRIBUTION (continued):**

	165°	170°	175°	180°	185°	190°	195°	200°	205°	210°	215°
112.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
115°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
117.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
120°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
122.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
125°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
127.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
130°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
132.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
135°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
137.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
140°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
142.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
145°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
147.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
150°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
152.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
155°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
157.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
160°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
162.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
165°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
167.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
170°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
172.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
175°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
177.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
180°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0



REPORT NUMBER: P320525  
 CATALOG NUMBER: GAN-SA1C-722-U-SLL

**CANDELA DISTRIBUTION (continued):**

	220°	225°	230°	235°	240°	245°	250°	255°	260°	265°	270°
0°	1458.1	1458.1	1458.1	1458.1	1458.1	1458.1	1458.1	1458.1	1458.1	1458.1	1458.1
2.5°	1225.8	1217.2	1226.0	1234.6	1238.2	1241.9	1232.5	1222.9	1237.8	1252.6	1256.4
5°	1004.2	996.4	1002.3	1008.0	995.2	982.4	981.0	979.5	990.6	1001.7	1003.4
7.5°	778.4	775.9	781.5	787.0	770.8	754.3	746.3	738.2	740.9	743.6	743.2
10°	580.4	581.9	588.8	595.5	582.8	570.2	564.7	559.1	565.2	571.2	576.7
12.5°	434.7	438.0	445.3	452.3	447.2	441.8	442.4	443.0	450.1	456.9	463.1
15°	337.7	341.6	346.7	351.7	351.9	351.9	356.9	361.6	361.1	360.5	364.7
17.5°	279.6	284.5	285.1	285.7	285.9	286.1	285.7	285.3	282.4	279.6	282.8
20°	239.4	241.1	242.6	244.0	242.2	240.3	235.6	230.8	228.9	226.9	230.0
22.5°	217.8	220.8	219.3	217.6	214.1	210.5	206.8	203.0	202.8	202.4	204.2
25°	199.6	202.1	199.4	196.7	194.2	191.7	189.2	186.8	186.6	186.4	187.1
27.5°	184.5	186.8	184.3	181.8	179.7	177.6	175.7	173.7	173.4	173.0	173.2
30°	171.4	173.6	171.4	169.2	167.6	165.9	164.6	163.2	163.0	162.8	162.8
32.5°	159.8	161.9	160.4	158.8	157.5	156.1	155.2	154.2	153.3	152.3	150.2
35°	149.6	151.7	150.8	149.6	148.1	146.6	144.9	142.9	140.4	137.8	136.6
37.5°	141.0	143.1	142.2	141.2	139.1	137.0	133.9	130.7	129.9	129.0	128.8
40°	134.1	137.4	135.5	133.4	130.1	126.9	125.3	123.8	123.4	123.0	122.7
42.5°	126.5	131.5	128.0	124.6	121.5	118.4	118.1	117.7	117.5	117.3	117.3
45°	116.9	122.3	118.8	115.2	113.5	111.7	111.7	111.7	111.9	111.9	112.3
47.5°	107.9	111.2	109.5	107.7	106.8	105.8	106.0	106.2	106.8	107.2	108.1
50°	100.3	101.4	101.8	102.0	101.4	100.8	101.2	101.4	102.0	102.4	103.1
52.5°	94.7	96.4	96.4	96.2	96.2	96.2	96.6	97.0	97.6	98.2	98.9
55°	91.1	93.6	92.8	92.0	92.2	92.2	92.6	93.0	93.6	94.0	95.1
57.5°	87.6	90.3	89.6	88.8	88.8	88.8	89.0	89.2	89.7	90.1	90.9
60°	83.6	86.3	85.5	84.6	84.8	85.0	85.2	85.2	85.5	85.7	85.7
62.5°	78.8	81.5	80.7	79.8	80.4	80.7	80.7	80.7	81.1	81.3	80.7
65°	73.9	76.3	75.6	74.8	75.6	76.2	76.5	76.7	76.5	76.3	75.8
67.5°	68.5	71.0	70.2	69.3	70.2	71.0	71.8	72.3	71.8	71.2	70.4
70°	62.8	65.2	64.3	63.3	64.3	65.2	66.0	66.8	66.0	65.2	65.1
72.5°	56.6	59.5	58.4	57.2	58.4	59.5	59.9	60.3	59.7	59.1	58.7
75°	49.9	52.8	51.9	50.7	51.7	52.6	52.8	53.0	53.0	52.8	51.7
77.5°	42.9	45.2	44.6	44.0	44.6	45.2	45.2	45.2	45.3	45.3	43.8
80°	34.4	35.8	36.0	36.2	36.4	36.5	36.4	36.2	35.8	35.4	34.4
82.5°	25.6	25.6	27.2	28.5	28.5	28.3	28.1	27.7	27.0	26.0	23.9
85°	16.3	15.3	17.8	20.1	20.1	19.9	19.5	18.9	17.4	15.7	14.0
87.5°	5.5	4.6	7.1	9.6	9.8	9.8	9.4	9.0	7.5	5.7	4.4
90°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
92.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
95°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
97.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
100°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
102.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
105°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
107.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
110°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0



REPORT NUMBER: P320525  
 CATALOG NUMBER: GAN-SA1C-722-U-SLL

**CANDELA DISTRIBUTION (continued):**

	220°	225°	230°	235°	240°	245°	250°	255°	260°	265°	270°
112.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
115°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
117.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
120°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
122.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
125°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
127.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
130°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
132.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
135°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
137.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
140°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
142.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
145°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
147.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
150°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
152.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
155°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
157.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
160°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
162.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
165°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
167.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
170°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
172.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
175°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
177.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
180°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0





REPORT NUMBER: P320525  
 CATALOG NUMBER: GAN-SA1C-722-U-SLL

**CANDELA DISTRIBUTION (continued):**

	275°	280°	285°	290°	295°	300°	305°	310°	315°	320°	325°
0°	1458.1	1458.1	1458.1	1458.1	1458.1	1458.1	1458.1	1458.1	1458.1	1458.1	1458.1
2.5°	1262.1	1264.6	1266.9	1285.7	1304.2	1326.0	1347.9	1364.5	1381.0	1398.0	1415.0
5°	1009.4	1012.4	1015.5	1038.3	1060.8	1091.3	1121.7	1147.9	1174.1	1204.9	1235.7
7.5°	748.2	754.9	761.4	785.7	809.8	842.5	875.0	909.3	943.3	983.5	1023.7
10°	587.6	600.3	612.7	637.6	662.4	694.8	726.9	762.7	798.5	838.1	877.5
12.5°	475.7	492.5	509.2	539.0	568.9	607.5	646.0	685.8	725.4	760.2	795.1
15°	375.8	394.2	412.4	443.9	475.5	518.0	560.3	603.7	647.0	688.7	730.4
17.5°	293.1	308.3	323.2	350.0	376.6	417.7	458.9	504.4	549.9	600.8	651.5
20°	236.5	242.8	249.1	268.5	287.6	321.1	354.4	400.9	447.4	508.2	569.1
22.5°	207.2	210.5	213.5	222.9	232.1	253.7	275.2	316.3	357.2	423.6	489.9
25°	189.6	192.1	194.6	200.7	206.8	217.2	227.5	256.4	285.3	350.6	415.6
27.5°	173.7	177.6	181.2	184.1	186.8	193.8	200.7	219.7	238.6	299.5	360.1
30°	162.3	163.6	164.9	169.3	173.6	180.8	188.1	201.3	214.5	266.0	317.3
32.5°	148.9	150.8	152.7	157.3	161.9	168.6	175.3	186.0	196.5	240.5	284.3
35°	136.8	138.7	140.6	145.2	149.6	156.9	164.0	173.0	181.8	220.1	258.3
37.5°	129.4	131.3	133.2	137.2	141.0	148.3	155.4	162.5	169.3	204.7	240.1
40°	123.0	125.0	126.9	130.7	134.3	141.4	148.3	154.2	160.2	193.3	226.4
42.5°	117.5	119.6	121.7	125.5	129.2	135.5	141.8	149.6	157.3	183.3	209.1
45°	112.9	115.0	116.9	121.1	125.3	131.5	137.6	148.5	159.4	178.1	196.9
47.5°	108.7	111.0	113.1	117.7	122.3	129.9	137.4	146.6	155.6	174.1	192.7
50°	104.7	107.3	110.0	115.6	120.9	133.8	146.4	147.7	148.9	170.9	192.7
52.5°	100.8	103.9	107.0	113.9	120.5	135.5	150.4	145.6	140.6	164.8	188.9
55°	97.0	99.7	102.2	110.6	119.0	129.9	140.8	134.5	128.0	153.3	178.5
57.5°	91.8	94.7	97.4	106.4	115.4	123.0	130.5	124.8	118.8	140.3	161.5
60°	86.5	89.7	93.0	104.5	115.8	114.4	112.9	111.7	110.4	125.7	141.0
62.5°	81.7	85.2	88.6	103.5	118.4	109.3	100.1	101.0	101.8	113.1	124.4
65°	76.9	80.4	83.6	91.1	98.5	94.9	91.3	92.8	94.1	105.2	116.3
67.5°	71.6	74.6	77.5	80.0	82.5	82.9	83.2	84.8	86.3	99.5	112.5
70°	65.6	68.1	70.6	72.3	73.9	74.6	75.2	77.1	79.0	93.4	107.7
72.5°	58.9	61.0	63.0	64.5	66.0	66.6	67.0	68.9	70.8	86.1	101.4
75°	51.7	53.4	54.9	56.3	57.6	58.4	59.1	60.5	61.8	78.5	94.9
77.5°	43.6	45.3	46.9	48.0	49.0	49.8	50.3	52.0	53.8	67.7	81.5
80°	34.1	36.2	38.1	39.0	39.8	40.0	40.0	41.5	43.1	53.0	62.8
82.5°	24.1	26.4	28.5	29.3	30.0	30.0	30.0	31.8	33.5	40.2	46.7
85°	14.2	16.6	18.9	19.7	20.5	20.9	21.0	21.8	22.4	27.2	31.8
87.5°	4.4	6.5	8.4	8.8	9.2	10.0	10.7	10.9	10.9	14.2	17.4
90°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
92.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
95°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
97.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
100°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
102.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
105°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
107.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
110°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0



REPORT NUMBER: P320525  
 CATALOG NUMBER: GAN-SA1C-722-U-SLL

**CANDELA DISTRIBUTION (continued):**

	275°	280°	285°	290°	295°	300°	305°	310°	315°	320°	325°
112.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
115°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
117.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
120°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
122.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
125°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
127.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
130°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
132.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
135°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
137.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
140°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
142.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
145°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
147.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
150°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
152.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
155°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
157.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
160°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
162.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
165°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
167.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
170°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
172.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
175°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
177.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
180°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0



REPORT NUMBER: P320525

CATALOG NUMBER: GAN-SA1C-722-U-SLL

**CANDELA DISTRIBUTION (continued):**

	330°	335°	340°	345°	350°	355°	360°
0°	1458.1	1458.1	1458.1	1458.1	1458.1	1458.1	1458.1
2.5°	1434.5	1454.1	1476.8	1499.4	1518.7	1538.1	1554.1
5°	1275.0	1314.2	1362.2	1410.0	1452.7	1495.4	1544.9
7.5°	1074.4	1125.1	1187.3	1249.5	1309.8	1369.9	1446.0
10°	929.2	980.7	1046.5	1112.1	1179.9	1247.4	1333.5
12.5°	837.0	878.7	942.4	1006.1	1085.7	1165.1	1248.0
15°	776.1	821.7	883.6	945.6	1032.7	1119.8	1215.1
17.5°	711.2	770.8	850.2	929.6	1032.7	1135.7	1248.0
20°	643.3	717.4	820.3	923.3	1062.2	1200.9	1344.2
22.5°	575.6	661.3	793.3	925.2	1106.8	1288.2	1481.6
25°	514.5	613.5	776.9	940.1	1171.6	1403.0	1642.9
27.5°	468.2	576.2	770.2	964.0	1253.9	1543.8	1818.4
30°	427.1	536.9	762.1	987.4	1333.1	1678.7	1955.6
32.5°	391.5	498.7	746.6	994.4	1388.4	1782.4	2071.7
35°	363.6	468.8	720.6	972.4	1423.1	1873.7	2192.7
37.5°	339.5	438.8	691.0	943.2	1453.9	1964.6	2328.7
40°	316.5	406.6	665.5	924.2	1496.3	2068.5	2472.4
42.5°	294.7	380.2	645.0	909.9	1535.8	2161.5	2598.1
45°	278.4	359.9	626.9	893.6	1561.2	2228.8	2692.9
47.5°	270.4	347.9	617.1	886.1	1586.7	2287.0	2771.5
50°	269.2	345.8	628.2	910.6	1641.8	2372.7	2861.4
52.5°	269.0	349.2	660.2	971.1	1744.1	2517.0	2958.8
55°	265.0	351.3	698.2	1045.0	1881.5	2717.9	3133.9
57.5°	252.8	344.0	737.5	1130.7	2026.8	2922.7	3331.2
60°	233.8	326.4	769.8	1213.0	2124.4	3035.6	3407.2
62.5°	210.1	295.6	780.5	1265.2	2121.7	2978.2	3330.6
65°	189.8	263.3	745.3	1227.1	2014.3	2801.3	3179.3
67.5°	171.8	231.0	657.3	1083.4	1821.3	2558.9	2986.8
70°	158.8	209.7	543.8	877.9	1579.6	2281.1	2763.8
72.5°	150.6	199.6	443.4	686.9	1281.8	1876.6	2364.1
75°	139.3	183.7	347.9	511.9	981.0	1450.2	1785.7
77.5°	118.3	154.8	262.1	369.5	719.9	1070.0	1241.9
80°	91.3	119.6	180.3	240.9	495.4	749.9	846.7
82.5°	65.1	83.4	109.3	135.1	329.1	523.0	531.0
85°	40.2	48.6	62.6	76.5	217.8	359.0	299.1
87.5°	21.6	25.8	33.1	40.2	69.7	99.1	57.0
90°	0.0	0.0	0.0	0.0	0.0	0.0	0.0
92.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0
95°	0.0	0.0	0.0	0.0	0.0	0.0	0.0
97.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0
100°	0.0	0.0	0.0	0.0	0.0	0.0	0.0
102.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0
105°	0.0	0.0	0.0	0.0	0.0	0.0	0.0
107.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0
110°	0.0	0.0	0.0	0.0	0.0	0.0	0.0



REPORT NUMBER: P320525  
CATALOG NUMBER: GAN-SA1C-722-U-SLL

**CANDELA DISTRIBUTION (continued):**

	330°	335°	340°	345°	350°	355°	360°
112.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0
115°	0.0	0.0	0.0	0.0	0.0	0.0	0.0
117.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0
120°	0.0	0.0	0.0	0.0	0.0	0.0	0.0
122.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0
125°	0.0	0.0	0.0	0.0	0.0	0.0	0.0
127.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0
130°	0.0	0.0	0.0	0.0	0.0	0.0	0.0
132.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0
135°	0.0	0.0	0.0	0.0	0.0	0.0	0.0
137.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0
140°	0.0	0.0	0.0	0.0	0.0	0.0	0.0
142.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0
145°	0.0	0.0	0.0	0.0	0.0	0.0	0.0
147.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0
150°	0.0	0.0	0.0	0.0	0.0	0.0	0.0
152.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0
155°	0.0	0.0	0.0	0.0	0.0	0.0	0.0
157.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0
160°	0.0	0.0	0.0	0.0	0.0	0.0	0.0
162.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0
165°	0.0	0.0	0.0	0.0	0.0	0.0	0.0
167.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0
170°	0.0	0.0	0.0	0.0	0.0	0.0	0.0
172.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0
175°	0.0	0.0	0.0	0.0	0.0	0.0	0.0
177.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0
180°	0.0	0.0	0.0	0.0	0.0	0.0	0.0

(END OF REPORT)