

Scaled data based on original data using  
LM-79-08 Approved Method: Electrical and Photometric Measurements of Solid-  
State Lighting Products

Test Report Prepared for  
Cooper Lighting Solutions  
(formerly Eaton)

Brand: STREETWORKS

Report Number: P324123

Luminaire Tested: **GAN-SA9B-730-U-SLL-HSS**

Issue Date: 3/3/2020

**Test Information**

Test Method: LM-79-08  
Report Number: P324123  
TEST IS SCALED FROM IESNA LM-79-08 TEST DATA (G2-1903-205-27)  
Test Lab: INNOVATION CENTER  
Issue Date: 3/3/2020  
Manufacturer: COOPER LIGHTING SOLUTIONS (FORMERLY EATON)  
Product Line: STREETWORKS  
Catalog Number: GAN-SA9B-730-U-SLL-HSS  
Description: GALLEON AREA AND ROADWAY LUMINAIRE  
(9) 70 CRI, 3000K, 800mA LIGHTSQUARES WITH 16 LEDS EACH AND SPILL LIGHT  
ELIMINATOR LEFT OPTICS WITH HOUSE SIDE SHIELD  
Light Source: -  
Ballast/Driver: ELECTRONIC DRIVER

**Summary**

Lumens per Lamp: N/A  
Luminaire Lumens: 34493 lumens  
Efficiency: N/A  
Efficacy: 92.2 lumens/watt  
Luminous Opening: Rectangular (W 2.5' x L: 1' x H: 0')  
IES Classification: Type III - Medium  
BUG Rating: B3 - U0 - G4


Input Watts (W): 374  
Input Voltage (V): NR  
Input Current (Ain): NR  
Voltage Rise (V): NR  
Power Factor: NR  
Total Harmonic Distortion (THDi): NR  
Frequency (hertz): 60  
Stabilization Time: NR  
Operation Time: NR  
Ambient Temperature (°C): NR  
Test Distance: 24 FT



REPORT NUMBER: P324123  
 CATALOG NUMBER: GAN-SA9B-730-U-SLL-HSS

### Iso-Footcandle Lines of Horizontal Illumination


✕ Max cd  
 - - - 1/2 Max cd



Based on 25 foot mounting height. Maximum calculated value = 24 fc  
 Type III - Medium - N/A

REPORT NUMBER: P324123  
CATALOG NUMBER: GAN-SA9B-730-U-SLL-HSS

### Luminous Intensity Polar Plot



— Vertical Plane Through 75-Deg Lateral      - - - Horizontal Cone Through 67.5-Deg Vertical

REPORT NUMBER: P324123  
 CATALOG NUMBER: GAN-SA9B-730-U-SLL-HSS

**FLUX DISTRIBUTION:**

		Downward	Upward	Total
<b>House Side</b>	Lumens	5176.0	0.0	5176.0
	% Fixture	15.0	0.0	15.0
<b>Street Side</b>	Lumens	29317.0	0.0	29317.0
	% Fixture	85.0	0.0	85.0
<b>Total</b>	Lumens	34493.0	0.0	34493.0
	% Fixture	100.0	0.0	100.0

**ZONAL LUMENS:**

Zone	Lumens	% Fixture
0°-10°	877.8	2.5
10°-20°	1728.4	5.0
20°-30°	2445.1	7.1
30°-40°	3595.0	10.4
40°-50°	5167.2	15.0
50°-60°	7274.1	21.1
60°-70°	8495.5	24.6
70°-80°	4334.1	12.6
80°-90°	575.8	1.7
90°-100°	0.0	0.0
100°-110°	0.0	0.0
110°-120°	0.0	0.0
120°-130°	0.0	0.0
130°-140°	0.0	0.0
140°-150°	0.0	0.0
150°-160°	0.0	0.0
160°-170°	0.0	0.0
170°-180°	0.0	0.0
0°-90°	34493.0	100.0
0°-180°	34493.0	100.0

**Coefficient of Utilization**




REPORT NUMBER: P324123  
 CATALOG NUMBER: GAN-SA9B-730-U-SLL-HSS

**LUMINAIRE CLASSIFICATION SYSTEM LUMEN TABLE AND BUG RATING:**

Zone	Lumens	% Fixture	Zone Rating/Lumen Limit		
			B	U	G
FL (0°-30°)	3697.7	10.7			
FM (30°-60°)	13575.8	39.4			
FH (60°-80°)	11485.2	33.3			G4/12000
FVH (80°-90°)	558.3	1.6			G4/750
BL (0°-30°)	1353.6	3.9	B3/2500		
BM (30°-60°)	2460.5	7.1	B2/2500		
BH (60°-80°)	1344.5	3.9	B3/2500		G3/2500
BVH (80°-90°)	17.5	0.1			G1/100
UL (90°-100°)	0.0	0.0		U0/0	
UH (100°-180°)	0.0	0.0		U0/0	

**BUG Rating: B3-U0-G4**  
 Type III Medium





REPORT NUMBER: P324123  
 CATALOG NUMBER: GAN-SA9B-730-U-SLL-HSS

**CANDELA DISTRIBUTION (FULL):**

	0°	1°	5°	15°	25°	35°	45°	55°	65°	75°	85°
0°	11571.8	11571.8	11571.8	11571.8	11571.8	11571.8	11571.8	11571.8	11571.8	11571.8	11571.8
2.5°	12544.0	12563.6	12664.9	12900.2	13156.8	13176.4	13349.6	13171.5	13111.0	12823.4	12526.1
5°	12638.8	12714.0	13062.0	13753.2	14352.8	14545.6	14682.9	14333.2	13965.6	13263.0	12513.0
7.5°	11875.7	12001.5	12548.9	13846.3	14918.2	15392.0	15481.9	14934.5	14034.2	12877.4	11749.9
10°	10898.6	11042.4	11702.5	13297.3	14769.5	15581.6	15705.8	14988.5	13694.3	12253.2	10924.8
12.5°	10107.8	10276.1	10950.9	12679.6	14258.1	15156.8	15401.8	14807.1	13400.2	11810.4	10361.0
15°	9743.4	9936.2	10645.3	12281.0	13691.1	14398.6	14601.2	14344.7	13236.8	11740.1	10230.3
17.5°	9952.5	10161.7	10893.7	12315.3	13158.4	13460.7	13624.1	13728.7	13236.8	12163.3	10612.7
20°	10810.4	11035.9	11810.4	12663.3	12717.2	12604.5	12779.3	13147.0	13390.4	12967.2	11531.0
22.5°	11996.6	12261.3	13135.5	13259.7	12501.5	12075.1	12098.0	12674.7	13669.8	13986.8	12805.5
25°	13442.7	13766.2	14655.1	14148.6	12591.4	11759.7	11751.5	12285.9	13942.7	15008.1	14225.4
27.5°	14879.0	15235.2	16016.2	15233.5	12962.3	11702.5	11686.2	12168.2	14209.0	15916.6	15776.0
30°	16083.2	16429.6	17102.8	16019.5	13362.6	11836.5	11758.1	12294.0	14367.5	16506.4	16906.7
32.5°	17063.6	17341.4	17885.5	16560.3	13790.7	12096.3	11926.4	12630.6	14637.1	17004.8	17945.9
35°	18142.0	18434.5	18651.8	17075.0	14271.1	12470.5	12227.0	13164.9	15052.2	17511.3	19084.8
37.5°	19372.4	19663.3	19637.1	17545.6	14880.6	13089.8	12934.5	14011.3	15697.6	18012.9	20356.1
40°	20576.6	20874.0	20661.6	18060.3	15596.3	14111.0	13996.6	15282.6	16562.0	18655.1	21846.2
42.5°	21704.1	22026.0	21571.7	18547.3	16449.2	15398.6	15594.7	16919.8	17643.7	19445.9	23130.6
45°	22612.6	22941.0	22334.8	19021.1	17347.9	16960.7	17550.5	18733.5	18944.3	20114.2	23998.2
47.5°	23272.7	23583.2	22864.2	19495.0	18498.2	18870.8	19898.5	20635.5	20119.1	20694.3	24614.2
50°	23694.3	23936.1	23019.4	20088.1	20008.0	21099.5	22344.6	22704.1	21225.3	21217.2	25362.6
52.5°	23962.2	24071.7	23133.8	20707.4	21583.2	23526.0	24740.0	24852.8	22364.2	21792.3	26370.7
55°	24885.4	24973.7	23944.3	21457.4	22885.5	25651.8	26906.7	26802.1	23653.4	22918.1	27560.3
57.5°	26460.6	26553.7	25619.1	22535.8	23939.4	26965.5	28476.9	28664.8	25164.9	24499.8	28834.8
60°	27251.4	27424.6	27091.3	23901.8	24960.6	27805.4	29547.2	30146.8	27053.7	26584.8	30070.0
62.5°	26534.1	26785.8	27269.4	25416.5	25975.3	28267.8	29880.5	30677.9	28988.4	29014.5	30831.5
65°	25102.8	25303.7	26124.0	26246.5	26563.5	28210.6	29057.0	29936.1	30173.0	31246.5	30790.6
67.5°	23374.0	23449.2	24145.2	26311.9	25710.6	26491.6	26583.1	27233.5	29236.7	32037.3	29553.7
70°	20885.5	20926.3	21534.2	24124.0	22094.6	22266.2	22130.6	22262.9	25135.4	30110.9	26431.2
72.5°	16808.7	16911.6	17776.0	20034.2	16096.3	15601.2	16666.5	16607.7	19357.7	25439.4	19630.6
75°	12375.7	12553.8	13859.4	16137.1	11297.3	10218.9	10996.7	11204.2	13761.3	19678.0	12276.1
77.5°	8665.0	8797.3	10062.0	11862.7	8176.4	7307.1	7026.1	7272.8	9083.3	14235.2	6184.6
80°	4991.8	5040.8	5848.0	6849.6	5509.8	6303.9	5710.7	5880.7	5442.8	6333.3	2660.1
82.5°	3266.3	3274.5	3589.8	4076.8	3431.3	3986.9	2951.0	3772.8	3348.0	2544.1	866.0
85°	1764.7	1774.5	2081.7	2893.8	1942.8	1098.0	645.4	1325.2	2070.2	583.3	236.9
87.5°	194.4	178.1	627.4	1052.3	539.2	99.7	34.3	148.7	331.7	37.6	0.0
90°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0



REPORT NUMBER: P324123  
 CATALOG NUMBER: GAN-SA9B-730-U-SLL-HSS

**CANDELA DISTRIBUTION (continued):**

	90°	95°	105°	115°	125°	135°	145°	155°	165°	175°	180°
0°	11571.8	11571.8	11571.8	11571.8	11571.8	11571.8	11571.8	11571.8	11571.8	11571.8	11571.8
2.5°	12374.1	12238.5	11900.2	11542.4	11254.8	10985.2	10714.0	10382.3	10125.7	10073.5	9988.5
5°	12109.4	11679.7	10970.5	10258.1	9684.6	8960.7	8501.6	8143.7	7794.1	7772.8	7702.6
7.5°	11184.6	10619.2	9620.8	8635.6	7828.4	7138.8	6442.8	5977.1	5611.1	5482.0	5405.2
10°	10295.7	9660.1	8413.3	7289.2	6568.6	5959.1	5468.9	4982.0	4540.8	4236.9	4099.6
12.5°	9674.8	8972.2	7598.0	6629.0	6112.7	5534.3	4936.2	4328.4	3820.2	3454.2	3230.4
15°	9434.6	8684.6	7325.1	6367.6	5730.4	4998.3	4233.6	3539.2	2975.5	2643.8	2442.8
17.5°	9720.5	8848.0	7303.9	6049.0	5158.5	4248.3	3403.6	2583.3	2052.3	1800.6	1671.6
20°	10446.0	9367.6	7295.7	5658.5	4478.7	3359.5	2305.5	1699.3	1377.4	1236.9	1176.5
22.5°	11472.1	10031.0	7361.1	5272.8	3771.2	2400.3	1591.5	1248.4	1083.3	1008.2	973.8
25°	12792.4	10962.3	7545.7	4923.2	3106.2	1790.8	1240.2	1045.7	929.7	870.9	846.4
27.5°	14199.2	12034.2	7833.3	4619.2	2565.3	1428.1	1062.1	895.4	812.1	771.2	748.4
30°	15359.4	13276.0	8124.1	4281.0	2173.2	1245.1	972.2	817.0	720.6	694.4	673.2
32.5°	16374.1	14215.6	8330.0	3975.5	1916.7	1106.2	879.1	730.4	665.0	614.4	591.5
35°	17424.7	14998.3	8323.5	3761.4	1740.2	1001.6	800.6	653.6	575.2	516.3	498.4
37.5°	18562.0	15882.2	8181.3	3578.4	1663.4	918.3	756.5	612.7	534.3	475.5	452.6
40°	19893.6	16810.3	8035.9	3406.8	1642.1	851.3	725.5	580.1	496.7	439.5	416.7
42.5°	21191.0	17646.9	7908.4	3279.4	1550.6	849.7	697.7	555.6	467.3	411.8	385.6
45°	22228.6	18426.3	7883.9	3202.6	1454.2	879.1	683.0	539.2	444.4	388.9	364.4
47.5°	23091.3	19272.7	8040.8	3148.7	1362.7	802.3	718.9	527.8	423.2	369.3	341.5
50°	24117.5	20311.9	8410.1	3060.4	1266.3	722.2	823.5	531.0	405.2	349.7	320.3
52.5°	25548.8	21749.8	8952.5	2911.7	1134.0	648.7	810.5	534.3	385.6	328.4	299.0
55°	27153.4	23545.6	9535.9	2665.0	949.3	552.3	694.4	511.4	348.0	305.6	277.8
57.5°	28839.7	25174.7	9882.3	2370.9	754.9	477.1	555.6	465.7	307.2	274.5	256.5
60°	29104.4	25793.9	9723.8	2009.8	599.7	415.0	411.8	473.9	274.5	241.8	228.8
62.5°	28445.9	25016.2	8957.5	1687.9	501.6	364.4	338.2	413.4	248.4	215.7	202.6
65°	27179.5	22913.2	7715.6	1521.2	465.7	312.1	281.0	290.8	217.3	187.9	176.5
67.5°	25418.1	20106.1	6334.9	1426.5	460.8	268.0	240.2	220.6	187.9	163.4	153.6
70°	21816.8	16749.9	5053.9	1374.2	447.7	225.5	202.6	179.7	156.9	138.9	130.7
72.5°	16057.1	11869.2	3931.3	1317.0	451.0	179.7	176.5	148.7	125.8	107.8	104.6
75°	9277.7	6781.0	2578.4	1067.0	429.7	138.9	147.1	104.6	88.2	75.2	75.2
77.5°	4944.4	4135.6	982.0	444.4	156.9	88.2	83.3	62.1	55.6	45.8	44.1
80°	2155.2	1820.2	295.7	124.2	86.6	47.4	31.0	27.8	24.5	19.6	18.0
82.5°	763.1	658.5	96.4	60.5	37.6	0.0	0.0	0.0	0.0	0.0	0.0
85°	173.2	124.2	0.0	14.7	0.0	0.0	0.0	0.0	0.0	0.0	0.0
87.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
90°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0





REPORT NUMBER: P324123

CATALOG NUMBER: GAN-SA9B-730-U-SLL-HSS

**CANDELA DISTRIBUTION (continued):**

	185°	195°	205°	215°	225°	235°	245°	255°	265°	270°	275°
0°	11571.8	11571.8	11571.8	11571.8	11571.8	11571.8	11571.8	11571.8	11571.8	11571.8	11571.8
2.5°	9815.3	9779.3	9566.9	9575.1	9612.7	9666.6	9539.1	9598.0	9756.5	9908.4	9965.6
5°	7589.8	7598.0	7468.9	7549.0	7620.9	7669.9	7464.0	7467.3	7593.1	7764.6	7854.5
7.5°	5348.0	5334.9	5341.5	5532.6	5668.3	5570.2	5647.0	5380.7	5397.0	5519.6	5428.1
10°	3975.5	3795.7	3694.4	3838.2	3986.9	3933.0	3800.6	3714.0	3774.5	3910.1	3900.3
12.5°	3124.2	2866.0	2714.0	2611.1	2733.6	2632.3	2629.1	2553.9	2472.2	2486.9	2704.2
15°	2349.7	2161.7	1982.0	1817.0	1813.7	1779.4	1604.6	1408.5	1392.1	1402.0	1514.7
17.5°	1616.0	1552.3	1478.7	1336.6	1299.0	1155.2	985.3	906.9	867.6	885.6	923.2
20°	1135.6	1111.1	1119.3	1042.5	988.6	851.3	751.6	720.6	714.0	732.0	750.0
22.5°	941.2	897.1	892.2	857.8	803.9	704.2	650.3	632.3	624.2	640.5	653.6
25°	823.5	779.4	761.4	740.2	683.0	614.4	581.7	565.4	557.2	567.0	575.2
27.5°	725.5	684.6	668.3	653.6	598.0	549.0	522.9	508.2	501.6	504.9	513.1
30°	652.0	616.0	594.8	576.8	529.4	495.1	472.2	457.5	451.0	451.0	459.1
32.5°	575.2	555.6	535.9	513.1	469.0	446.1	423.2	406.9	400.3	402.0	408.5
35°	478.8	472.2	477.1	455.9	418.3	398.7	375.8	357.8	352.9	354.6	361.1
37.5°	424.8	395.4	413.4	402.0	380.7	354.6	325.2	308.8	300.7	305.6	308.8
40°	390.5	354.6	341.5	352.9	349.7	307.2	281.0	264.7	258.2	259.8	263.1
42.5°	361.1	318.6	289.2	287.6	307.2	268.0	240.2	225.5	217.3	217.3	220.6
45°	333.3	287.6	251.6	223.9	258.2	227.1	201.0	187.9	178.1	178.1	179.7
47.5°	312.1	261.4	219.0	183.0	194.4	186.3	165.0	152.0	142.2	142.2	143.8
50°	292.5	235.3	189.5	153.6	145.4	153.6	134.0	119.3	112.7	111.1	114.4
52.5°	271.2	209.1	161.8	130.7	114.4	116.0	104.6	94.8	86.6	86.6	89.9
55°	250.0	187.9	140.5	111.1	94.8	86.6	83.3	76.8	70.3	70.3	73.5
57.5°	228.8	165.0	119.3	91.5	75.2	68.6	68.6	63.7	58.8	58.8	62.1
60°	209.1	142.2	98.0	75.2	58.8	57.2	58.8	53.9	50.7	50.7	53.9
62.5°	186.3	120.9	80.1	62.1	47.4	45.8	50.7	47.4	44.1	44.1	47.4
65°	158.5	102.9	63.7	47.4	35.9	35.9	42.5	39.2	35.9	35.9	39.2
67.5°	134.0	86.6	49.0	34.3	26.1	27.8	35.9	32.7	31.0	31.0	34.3
70°	111.1	67.0	34.3	21.2	14.7	21.2	27.8	27.8	27.8	27.8	31.0
72.5°	83.3	45.8	19.6	8.2	6.5	14.7	22.9	26.1	24.5	24.5	29.4
75°	53.9	26.1	6.5	0.0	0.0	8.2	18.0	21.2	21.2	19.6	24.5
77.5°	31.0	8.2	0.0	0.0	0.0	0.0	11.4	9.8	8.2	6.5	11.4
80°	8.2	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
82.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
85°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
87.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
90°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0



REPORT NUMBER: P324123  
 CATALOG NUMBER: GAN-SA9B-730-U-SLL-HSS

**CANDELA DISTRIBUTION (continued):**

	285°	295°	305°	315°	325°	335°	345°	355°	359°	360°
0°	11571.8	11571.8	11571.8	11571.8	11571.8	11571.8	11571.8	11571.8	11571.8	11571.8
2.5°	10196.0	10388.8	10660.1	10947.6	11390.4	11741.7	12086.5	12382.3	12496.6	12544.0
5°	8070.2	8352.9	8749.9	9259.7	10058.8	10777.7	11506.5	12240.1	12558.7	12638.8
7.5°	5790.8	6151.9	6656.8	7295.7	8232.0	9163.3	10181.3	11258.1	11751.5	11875.7
10°	4285.9	4727.1	5305.5	5978.7	6872.5	7830.0	8939.5	10169.9	10733.6	10898.6
12.5°	3040.8	3637.2	4411.7	5230.4	6004.9	6859.4	7982.0	9338.2	9929.7	10107.8
15°	1785.9	2362.7	3279.4	4375.8	5367.6	6233.6	7374.1	8911.7	9563.7	9743.4
17.5°	1024.5	1312.1	2004.9	3227.1	4573.5	5772.8	7183.0	9017.9	9785.9	9952.5
20°	782.7	874.2	1155.2	2078.4	3645.4	5320.2	7183.0	9619.2	10565.3	10810.4
22.5°	684.6	751.6	866.0	1240.2	2683.0	4834.9	7266.3	10488.5	11725.4	11996.6
25°	607.8	668.3	766.3	933.0	1830.1	4258.1	7464.0	11555.5	13091.4	13442.7
27.5°	544.1	601.3	689.5	817.0	1251.6	3562.1	7730.3	12807.1	14597.9	14879.0
30°	486.9	540.8	620.9	710.8	965.7	2772.9	7957.5	13986.8	15780.9	16083.2
32.5°	433.0	482.0	553.9	620.9	790.8	2050.6	7982.0	14921.5	16763.0	17063.6
35°	382.4	426.5	491.8	544.1	655.2	1619.3	7601.3	15731.9	17745.0	18142.0
37.5°	333.3	375.8	433.0	472.2	576.8	1320.3	7019.6	16635.5	19004.8	19372.4
40°	287.6	325.2	384.0	410.1	545.7	1014.7	6387.2	17583.2	20240.0	20576.6
42.5°	245.1	281.0	338.2	388.9	478.8	758.2	5704.2	18472.1	21351.2	21704.1
45°	204.2	241.8	299.0	411.8	397.1	567.0	4973.8	19062.0	22228.6	22612.6
47.5°	165.0	207.5	285.9	392.2	317.0	416.7	4395.4	19620.8	22893.6	23272.7
50°	132.4	174.8	321.9	349.7	259.8	318.6	4153.6	20120.8	23329.9	23694.3
52.5°	107.8	147.1	303.9	268.0	217.3	263.1	4284.3	20931.2	23733.5	23962.2
55°	89.9	116.0	183.0	186.3	184.6	223.9	4446.0	22094.6	24777.6	24885.4
57.5°	78.4	93.1	127.5	143.8	155.2	199.3	4449.3	23764.5	26393.6	26460.6
60°	67.0	81.7	106.2	116.0	134.0	178.1	4287.6	24347.9	27029.2	27251.4
62.5°	58.8	71.9	88.2	96.4	112.7	160.1	3908.5	23503.1	26156.7	26534.1
65°	52.3	65.4	73.5	81.7	99.7	143.8	3284.3	21813.6	24709.0	25102.8
67.5°	45.8	57.2	65.4	73.5	89.9	127.5	2418.3	19851.2	23047.2	23374.0
70°	40.8	50.7	58.8	65.4	78.4	107.8	1467.3	16844.6	20749.8	20885.5
72.5°	39.2	45.8	53.9	58.8	68.6	94.8	743.5	12379.0	16588.1	16808.7
75°	34.3	40.8	49.0	52.3	60.5	81.7	302.3	8130.7	12021.2	12375.7
77.5°	27.8	37.6	44.1	47.4	52.3	67.0	153.6	5196.0	8436.2	8665.0
80°	9.8	27.8	37.6	39.2	44.1	49.0	101.3	2844.8	4893.8	4991.8
82.5°	0.0	18.0	29.4	27.8	31.0	37.6	65.4	1352.9	3230.4	3266.3
85°	0.0	8.2	22.9	18.0	13.1	26.1	22.9	295.7	1694.4	1764.7
87.5°	0.0	0.0	1.6	8.2	6.5	9.8	3.3	1.6	153.6	194.4
90°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0

(END OF REPORT)