

Scaled data based on original data using  
LM-79-08 Approved Method: Electrical and Photometric Measurements of Solid-  
State Lighting Products

Test Report Prepared for  
Cooper Lighting Solutions  
(formerly Eaton)

Brand: STREETWORKS

Report Number: P383227

Luminaire Tested: **GAN-SA5C-735-U-SLL**

Issue Date: 3/3/2020

**Test Information**

Test Method: LM-79-08  
Report Number: P383227  
TEST IS SCALED FROM IESNA LM-79-08 TEST DATA (G2-1903-205-26)  
Test Lab: INNOVATION CENTER  
Issue Date: 3/3/2020  
Manufacturer: COOPER LIGHTING SOLUTIONS (FORMERLY EATON)  
Product Line: STREETWORKS  
Catalog Number: GAN-SA5C-735-U-SLL  
Description: GALLEON AREA AND ROADWAY LUMINAIRE  
(5) 70 CRI, 3500K, 1050mA LIGHTSQUARES WITH 16 LEDS EACH AND SPILL LIGHT  
ELIMINATOR LEFT OPTICS  
Light Source: -  
Ballast/Driver: ELECTRONIC DRIVER

**Summary**

Lumens per Lamp: N/A  
Luminaire Lumens: 28940.4 lumens  
Efficiency: N/A  
Efficacy: 103.7 lumens/watt  
Luminous Opening: Rectangular (W 1.5' x L: 1' x H: 0')  
IES Classification: Type III - Medium  
BUG Rating: B3 - U0 - G5


Input Watts (W): 279  
Input Voltage (V): NR  
Input Current (Ain): NR  
Voltage Rise (V): NR  
Power Factor: NR  
Total Harmonic Distortion (THDi): NR  
Frequency (hertz): 60  
Stabilization Time: NR  
Operation Time: NR  
Ambient Temperature (°C): NR  
Test Distance: 24 FT



REPORT NUMBER: P383227  
 CATALOG NUMBER: GAN-SA5C-735-U-SLL

### Iso-Footcandle Lines of Horizontal Illumination


✕ Max cd  
 - - - 1/2 Max cd



Based on 25 foot mounting height. Maximum calculated value = 17.7 fc  
 Type III - Medium - N/A

REPORT NUMBER: P383227  
CATALOG NUMBER: GAN-SA5C-735-U-SLL

### Luminous Intensity Polar Plot



— Vertical Plane Through 75-Deg Lateral      - - - Horizontal Cone Through 67.5-Deg Vertical

REPORT NUMBER: P383227  
 CATALOG NUMBER: GAN-SA5C-735-U-SLL


**FLUX DISTRIBUTION:**

|                    |           | Downward | Upward | Total   |
|--------------------|-----------|----------|--------|---------|
| <b>House Side</b>  | Lumens    | 5097.1   | 0.0    | 5097.1  |
|                    | % Fixture | 17.6     | 0.0    | 17.6    |
| <b>Street Side</b> | Lumens    | 23843.3  | 0.0    | 23843.3 |
|                    | % Fixture | 82.4     | 0.0    | 82.4    |
| <b>Total</b>       | Lumens    | 28940.4  | 0.0    | 28940.4 |
|                    | % Fixture | 100.0    | 0.0    | 100.0   |

**ZONAL LUMENS:**

| Zone      | Lumens  | % Fixture |
|-----------|---------|-----------|
| 0°-10°    | 680.5   | 2.4       |
| 10°-20°   | 1413.6  | 4.9       |
| 20°-30°   | 2010.4  | 6.9       |
| 30°-40°   | 2897.0  | 10.0      |
| 40°-50°   | 4082.7  | 14.1      |
| 50°-60°   | 5675.7  | 19.6      |
| 60°-70°   | 6863.6  | 23.7      |
| 70°-80°   | 4219.0  | 14.6      |
| 80°-90°   | 1097.8  | 3.8       |
| 90°-100°  | 0.0     | 0.0       |
| 100°-110° | 0.0     | 0.0       |
| 110°-120° | 0.0     | 0.0       |
| 120°-130° | 0.0     | 0.0       |
| 130°-140° | 0.0     | 0.0       |
| 140°-150° | 0.0     | 0.0       |
| 150°-160° | 0.0     | 0.0       |
| 160°-170° | 0.0     | 0.0       |
| 170°-180° | 0.0     | 0.0       |
| 0°-90°    | 28940.4 | 100.0     |
| 0°-180°   | 28940.4 | 100.0     |

**Coefficient of Utilization**




REPORT NUMBER: P383227  
 CATALOG NUMBER: GAN-SA5C-735-U-SLL

**LUMINAIRE CLASSIFICATION SYSTEM LUMEN TABLE AND BUG RATING:**

| Zone           | Lumens  | % Fixture | Zone Rating/Lumen Limit |      |          |
|----------------|---------|-----------|-------------------------|------|----------|
|                |         |           | B                       | U    | G        |
| FL (0°-30°)    | 2873.5  | 9.9       |                         |      |          |
| FM (30°-60°)   | 10341.8 | 35.7      |                         |      |          |
| FH (60°-80°)   | 9653.5  | 33.4      |                         |      | G4/12000 |
| FVH (80°-90°)  | 974.5   | 3.4       |                         |      | G5       |
| BL (0°-30°)    | 1231.0  | 4.3       | B3/2500                 |      |          |
| BM (30°-60°)   | 2313.7  | 8.0       | B2/2500                 |      |          |
| BH (60°-80°)   | 1429.0  | 4.9       | B3/2500                 |      | G3/2500  |
| BVH (80°-90°)  | 123.4   | 0.4       |                         |      | G2/225   |
| UL (90°-100°)  | 0.0     | 0.0       |                         | U0/0 |          |
| UH (100°-180°) | 0.0     | 0.0       |                         | U0/0 |          |

**BUG Rating: B3-U0-G5**  
 Type III Medium





REPORT NUMBER: P383227

CATALOG NUMBER: GAN-SA5C-735-U-SLL

**CANDELA DISTRIBUTION (FULL):**

|        | 0°      | 5°      | 10°     | 15°     | 20°     | 25°     | 30°     | 35°     | 40°     | 45°     | 50°     |
|--------|---------|---------|---------|---------|---------|---------|---------|---------|---------|---------|---------|
| 0°     | 8816.8  | 8816.8  | 8816.8  | 8816.8  | 8816.8  | 8816.8  | 8816.8  | 8816.8  | 8816.8  | 8816.8  | 8816.8  |
| 2.5°   | 9397.6  | 9521.4  | 9607.1  | 9691.5  | 9757.5  | 9822.3  | 9917.2  | 10012.1 | 10030.6 | 10048.0 | 10010.9 |
| 5°     | 9342.1  | 9644.1  | 9901.0  | 10156.7 | 10393.9 | 10631.1 | 10773.4 | 10915.8 | 10944.7 | 10973.6 | 10884.5 |
| 7.5°   | 8744.0  | 9189.4  | 9634.9  | 10080.4 | 10488.8 | 10897.2 | 11146.0 | 11393.6 | 11450.3 | 11505.8 | 11360.0 |
| 10°    | 8063.6  | 8582.0  | 9129.3  | 9676.5  | 10214.5 | 10752.6 | 11112.4 | 11472.3 | 11544.0 | 11615.7 | 11434.1 |
| 12.5°  | 7546.4  | 8112.2  | 8696.5  | 9280.8  | 9848.9  | 10415.9 | 10788.4 | 11161.1 | 11250.1 | 11339.3 | 11207.4 |
| 15°    | 7347.4  | 7967.5  | 8517.1  | 9066.8  | 9562.0  | 10056.1 | 10361.5 | 10665.8 | 10702.8 | 10738.7 | 10717.9 |
| 17.5°  | 7546.4  | 8230.2  | 8727.8  | 9224.1  | 9493.7  | 9762.2  | 9884.8  | 10006.3 | 10046.7 | 10086.1 | 10139.3 |
| 20°    | 8128.4  | 8866.6  | 9217.2  | 9566.6  | 9555.1  | 9542.3  | 9483.2  | 9423.2  | 9412.7  | 9402.3  | 9552.7  |
| 22.5°  | 8959.2  | 9816.6  | 9956.6  | 10095.4 | 9770.3  | 9445.1  | 9247.3  | 9048.2  | 9008.9  | 8968.4  | 9128.0  |
| 25°    | 9934.6  | 10847.5 | 10822.0 | 10795.4 | 10176.4 | 9556.2  | 9179.0  | 8801.8  | 8757.9  | 8713.9  | 8850.4  |
| 27.5°  | 10995.6 | 11868.0 | 11701.4 | 11534.8 | 10693.6 | 9852.4  | 9305.1  | 8757.9  | 8713.9  | 8669.9  | 8790.2  |
| 30°    | 11825.2 | 12616.6 | 12349.3 | 12082.1 | 11129.8 | 10177.5 | 9527.2  | 8877.0  | 8805.3  | 8732.3  | 8880.4  |
| 32.5°  | 12527.5 | 13201.0 | 12842.2 | 12483.6 | 11483.8 | 10484.2 | 9780.7  | 9077.2  | 8964.9  | 8852.7  | 9050.5  |
| 35°    | 13258.8 | 13784.1 | 13279.6 | 12773.9 | 11799.7 | 10824.3 | 10080.4 | 9335.2  | 9197.5  | 9059.8  | 9331.7  |
| 37.5°  | 14081.5 | 14517.7 | 13793.3 | 13067.8 | 12154.9 | 11242.0 | 10529.3 | 9815.3  | 9674.2  | 9533.1  | 9880.2  |
| 40°    | 14950.4 | 15313.7 | 14347.6 | 13381.4 | 12543.8 | 11706.0 | 11150.6 | 10594.1 | 10459.9 | 10324.4 | 10745.7 |
| 42.5°  | 15710.6 | 15975.6 | 14863.7 | 13751.7 | 13012.3 | 12271.8 | 11880.8 | 11488.5 | 11487.3 | 11485.1 | 11912.0 |
| 45°    | 16283.4 | 16513.6 | 15294.1 | 14073.4 | 13469.3 | 12864.2 | 12660.6 | 12456.9 | 12620.0 | 12783.3 | 13169.7 |
| 47.5°  | 16758.9 | 16915.1 | 15655.0 | 14393.9 | 13992.4 | 13590.9 | 13621.0 | 13651.0 | 13983.1 | 14315.2 | 14564.0 |
| 50°    | 17302.8 | 17176.6 | 15982.6 | 14787.3 | 14663.5 | 14539.7 | 14810.4 | 15080.0 | 15461.8 | 15842.6 | 16011.4 |
| 52.5°  | 17891.7 | 17557.3 | 16426.8 | 15295.3 | 15434.1 | 15573.0 | 16123.7 | 16674.4 | 17059.7 | 17445.1 | 17508.7 |
| 55°    | 18950.4 | 18437.8 | 17243.7 | 16048.5 | 16315.8 | 16581.9 | 17390.7 | 18198.3 | 18499.1 | 18799.9 | 18823.1 |
| 57.5°  | 20143.3 | 19688.6 | 18388.1 | 17087.5 | 17374.5 | 17661.4 | 18595.2 | 19527.8 | 19852.9 | 20176.9 | 20131.8 |
| 60°    | 20602.7 | 20624.7 | 19474.6 | 18323.3 | 18612.5 | 18901.8 | 19811.2 | 20720.7 | 21094.4 | 21467.0 | 21367.5 |
| 62.5°  | 20139.9 | 20682.5 | 20068.1 | 19452.6 | 19715.2 | 19976.7 | 20867.6 | 21758.6 | 22141.6 | 22524.5 | 22351.0 |
| 65°    | 19224.6 | 19762.7 | 20038.1 | 20313.4 | 20400.1 | 20487.0 | 21318.9 | 22149.7 | 22443.6 | 22736.3 | 22648.3 |
| 67.5°  | 18060.6 | 18495.7 | 19511.5 | 20526.3 | 20351.6 | 20176.9 | 20566.8 | 20956.7 | 21258.8 | 21560.8 | 21510.9 |
| 70°    | 16712.6 | 17231.0 | 18586.0 | 19940.8 | 19082.3 | 18222.6 | 18061.8 | 17900.9 | 18227.2 | 18552.3 | 18351.0 |
| 72.5°  | 14295.5 | 15077.7 | 16522.9 | 17966.9 | 16385.2 | 14803.5 | 14253.9 | 13704.3 | 14117.3 | 14530.4 | 14209.9 |
| 75°    | 10797.8 | 11835.6 | 13432.4 | 15027.9 | 13140.8 | 11253.6 | 10520.1 | 9786.5  | 10141.7 | 10496.9 | 10277.0 |
| 77.5°  | 7509.3  | 8811.0  | 10383.5 | 11955.9 | 10037.5 | 8118.0  | 7573.0  | 7026.8  | 7133.3  | 7238.6  | 7201.6  |
| 80°    | 5120.0  | 5976.3  | 7073.1  | 8168.8  | 6891.5  | 5614.1  | 5656.9  | 5698.6  | 5648.8  | 5597.9  | 5671.9  |
| 82.5°  | 3210.9  | 3813.7  | 4660.6  | 5506.5  | 4828.4  | 4150.4  | 4539.2  | 4928.0  | 4737.0  | 4544.9  | 4616.7  |
| 85°    | 1808.5  | 2176.5  | 3004.9  | 3832.2  | 3571.8  | 3310.3  | 3538.3  | 3765.1  | 3468.9  | 3172.7  | 3303.5  |
| 87.5°  | 344.8   | 573.9   | 1662.7  | 2750.3  | 2496.9  | 2243.5  | 1949.6  | 1655.7  | 1263.6  | 871.3   | 1272.8  |
| 90°    | 0.0     | 0.0     | 0.0     | 0.0     | 0.0     | 0.0     | 0.0     | 0.0     | 0.0     | 0.0     | 0.0     |
| 92.5°  | 0.0     | 0.0     | 0.0     | 0.0     | 0.0     | 0.0     | 0.0     | 0.0     | 0.0     | 0.0     | 0.0     |
| 95°    | 0.0     | 0.0     | 0.0     | 0.0     | 0.0     | 0.0     | 0.0     | 0.0     | 0.0     | 0.0     | 0.0     |
| 97.5°  | 0.0     | 0.0     | 0.0     | 0.0     | 0.0     | 0.0     | 0.0     | 0.0     | 0.0     | 0.0     | 0.0     |
| 100°   | 0.0     | 0.0     | 0.0     | 0.0     | 0.0     | 0.0     | 0.0     | 0.0     | 0.0     | 0.0     | 0.0     |
| 102.5° | 0.0     | 0.0     | 0.0     | 0.0     | 0.0     | 0.0     | 0.0     | 0.0     | 0.0     | 0.0     | 0.0     |
| 105°   | 0.0     | 0.0     | 0.0     | 0.0     | 0.0     | 0.0     | 0.0     | 0.0     | 0.0     | 0.0     | 0.0     |
| 107.5° | 0.0     | 0.0     | 0.0     | 0.0     | 0.0     | 0.0     | 0.0     | 0.0     | 0.0     | 0.0     | 0.0     |
| 110°   | 0.0     | 0.0     | 0.0     | 0.0     | 0.0     | 0.0     | 0.0     | 0.0     | 0.0     | 0.0     | 0.0     |



REPORT NUMBER: P383227  
 CATALOG NUMBER: GAN-SA5C-735-U-SLL

**CANDELA DISTRIBUTION (continued):**

|        | 0°  | 5°  | 10° | 15° | 20° | 25° | 30° | 35° | 40° | 45° | 50° |
|--------|-----|-----|-----|-----|-----|-----|-----|-----|-----|-----|-----|
| 112.5° | 0.0 | 0.0 | 0.0 | 0.0 | 0.0 | 0.0 | 0.0 | 0.0 | 0.0 | 0.0 | 0.0 |
| 115°   | 0.0 | 0.0 | 0.0 | 0.0 | 0.0 | 0.0 | 0.0 | 0.0 | 0.0 | 0.0 | 0.0 |
| 117.5° | 0.0 | 0.0 | 0.0 | 0.0 | 0.0 | 0.0 | 0.0 | 0.0 | 0.0 | 0.0 | 0.0 |
| 120°   | 0.0 | 0.0 | 0.0 | 0.0 | 0.0 | 0.0 | 0.0 | 0.0 | 0.0 | 0.0 | 0.0 |
| 122.5° | 0.0 | 0.0 | 0.0 | 0.0 | 0.0 | 0.0 | 0.0 | 0.0 | 0.0 | 0.0 | 0.0 |
| 125°   | 0.0 | 0.0 | 0.0 | 0.0 | 0.0 | 0.0 | 0.0 | 0.0 | 0.0 | 0.0 | 0.0 |
| 127.5° | 0.0 | 0.0 | 0.0 | 0.0 | 0.0 | 0.0 | 0.0 | 0.0 | 0.0 | 0.0 | 0.0 |
| 130°   | 0.0 | 0.0 | 0.0 | 0.0 | 0.0 | 0.0 | 0.0 | 0.0 | 0.0 | 0.0 | 0.0 |
| 132.5° | 0.0 | 0.0 | 0.0 | 0.0 | 0.0 | 0.0 | 0.0 | 0.0 | 0.0 | 0.0 | 0.0 |
| 135°   | 0.0 | 0.0 | 0.0 | 0.0 | 0.0 | 0.0 | 0.0 | 0.0 | 0.0 | 0.0 | 0.0 |
| 137.5° | 0.0 | 0.0 | 0.0 | 0.0 | 0.0 | 0.0 | 0.0 | 0.0 | 0.0 | 0.0 | 0.0 |
| 140°   | 0.0 | 0.0 | 0.0 | 0.0 | 0.0 | 0.0 | 0.0 | 0.0 | 0.0 | 0.0 | 0.0 |
| 142.5° | 0.0 | 0.0 | 0.0 | 0.0 | 0.0 | 0.0 | 0.0 | 0.0 | 0.0 | 0.0 | 0.0 |
| 145°   | 0.0 | 0.0 | 0.0 | 0.0 | 0.0 | 0.0 | 0.0 | 0.0 | 0.0 | 0.0 | 0.0 |
| 147.5° | 0.0 | 0.0 | 0.0 | 0.0 | 0.0 | 0.0 | 0.0 | 0.0 | 0.0 | 0.0 | 0.0 |
| 150°   | 0.0 | 0.0 | 0.0 | 0.0 | 0.0 | 0.0 | 0.0 | 0.0 | 0.0 | 0.0 | 0.0 |
| 152.5° | 0.0 | 0.0 | 0.0 | 0.0 | 0.0 | 0.0 | 0.0 | 0.0 | 0.0 | 0.0 | 0.0 |
| 155°   | 0.0 | 0.0 | 0.0 | 0.0 | 0.0 | 0.0 | 0.0 | 0.0 | 0.0 | 0.0 | 0.0 |
| 157.5° | 0.0 | 0.0 | 0.0 | 0.0 | 0.0 | 0.0 | 0.0 | 0.0 | 0.0 | 0.0 | 0.0 |
| 160°   | 0.0 | 0.0 | 0.0 | 0.0 | 0.0 | 0.0 | 0.0 | 0.0 | 0.0 | 0.0 | 0.0 |
| 162.5° | 0.0 | 0.0 | 0.0 | 0.0 | 0.0 | 0.0 | 0.0 | 0.0 | 0.0 | 0.0 | 0.0 |
| 165°   | 0.0 | 0.0 | 0.0 | 0.0 | 0.0 | 0.0 | 0.0 | 0.0 | 0.0 | 0.0 | 0.0 |
| 167.5° | 0.0 | 0.0 | 0.0 | 0.0 | 0.0 | 0.0 | 0.0 | 0.0 | 0.0 | 0.0 | 0.0 |
| 170°   | 0.0 | 0.0 | 0.0 | 0.0 | 0.0 | 0.0 | 0.0 | 0.0 | 0.0 | 0.0 | 0.0 |
| 172.5° | 0.0 | 0.0 | 0.0 | 0.0 | 0.0 | 0.0 | 0.0 | 0.0 | 0.0 | 0.0 | 0.0 |
| 175°   | 0.0 | 0.0 | 0.0 | 0.0 | 0.0 | 0.0 | 0.0 | 0.0 | 0.0 | 0.0 | 0.0 |
| 177.5° | 0.0 | 0.0 | 0.0 | 0.0 | 0.0 | 0.0 | 0.0 | 0.0 | 0.0 | 0.0 | 0.0 |
| 180°   | 0.0 | 0.0 | 0.0 | 0.0 | 0.0 | 0.0 | 0.0 | 0.0 | 0.0 | 0.0 | 0.0 |





REPORT NUMBER: P383227

CATALOG NUMBER: GAN-SA5C-735-U-SLL

**CANDELA DISTRIBUTION (continued):**

|        | 55°     | 60°     | 65°     | 70°     | 75°     | 80°     | 85°     | 90°     | 95°     | 100°    | 105°   |
|--------|---------|---------|---------|---------|---------|---------|---------|---------|---------|---------|--------|
| 0°     | 8816.8  | 8816.8  | 8816.8  | 8816.8  | 8816.8  | 8816.8  | 8816.8  | 8816.8  | 8816.8  | 8816.8  | 8816.8 |
| 2.5°   | 9973.9  | 9954.2  | 9934.6  | 9864.0  | 9792.2  | 9685.8  | 9597.8  | 9445.1  | 9361.8  | 9235.6  | 9109.6 |
| 5°     | 10794.2 | 10669.3 | 10544.3 | 10329.1 | 10112.7 | 9872.1  | 9595.5  | 9288.9  | 9057.5  | 8756.6  | 8455.8 |
| 7.5°   | 11214.2 | 10922.7 | 10630.0 | 10216.8 | 9802.7  | 9430.1  | 8992.7  | 8585.4  | 8238.3  | 7847.2  | 7456.1 |
| 10°    | 11252.4 | 10815.1 | 10376.5 | 9839.7  | 9301.6  | 8849.2  | 8345.9  | 7893.5  | 7477.0  | 7028.0  | 6577.9 |
| 12.5°  | 11074.2 | 10609.1 | 10142.8 | 9551.5  | 8959.2  | 8445.4  | 7903.9  | 7397.1  | 6935.5  | 6441.4  | 5946.2 |
| 15°    | 10697.1 | 10325.6 | 9953.0  | 9398.8  | 8844.6  | 8326.3  | 7801.0  | 7200.4  | 6678.5  | 6172.9  | 5666.1 |
| 17.5°  | 10191.4 | 10015.5 | 9838.5  | 9438.2  | 9036.7  | 8587.8  | 8078.7  | 7373.9  | 6763.0  | 6213.4  | 5663.8 |
| 20°    | 9702.0  | 9766.8  | 9830.4  | 9670.8  | 9511.1  | 9151.2  | 8706.9  | 7915.5  | 7135.7  | 6417.1  | 5697.3 |
| 22.5°  | 9286.6  | 9597.8  | 9907.9  | 10031.7 | 10154.4 | 9938.0  | 9590.9  | 8675.7  | 7643.5  | 6705.2  | 5766.8 |
| 25°    | 8985.8  | 9501.8  | 10017.9 | 10429.8 | 10840.5 | 10744.5 | 10477.2 | 9599.0  | 8317.0  | 7120.6  | 5923.0 |
| 27.5°  | 8910.5  | 9543.4  | 10176.4 | 10815.1 | 11452.6 | 11541.7 | 11467.6 | 10572.1 | 9119.9  | 7636.6  | 6152.1 |
| 30°    | 9028.6  | 9669.6  | 10309.4 | 11087.0 | 11863.4 | 12218.6 | 12318.1 | 11383.2 | 10037.5 | 8238.3  | 6437.9 |
| 32.5°  | 9248.4  | 9876.7  | 10505.0 | 11351.9 | 12197.8 | 12734.6 | 13051.6 | 12124.8 | 10677.4 | 8691.9  | 6705.2 |
| 35°    | 9603.6  | 10191.4 | 10779.2 | 11660.9 | 12542.5 | 13236.8 | 13815.3 | 12890.8 | 11245.5 | 9008.9  | 6771.1 |
| 37.5°  | 10226.2 | 10731.8 | 11237.4 | 12052.0 | 12865.4 | 13765.6 | 14634.5 | 13734.4 | 11859.9 | 9314.4  | 6767.7 |
| 40°    | 11166.8 | 11524.4 | 11880.8 | 12569.2 | 13256.5 | 14389.2 | 15562.5 | 14675.0 | 12539.1 | 9645.2  | 6751.5 |
| 42.5°  | 12338.9 | 12522.9 | 12705.8 | 13250.7 | 13795.7 | 15040.7 | 16404.8 | 15594.9 | 13187.1 | 9953.0  | 6719.1 |
| 45°    | 13555.0 | 13603.6 | 13652.2 | 13995.9 | 14338.3 | 15556.8 | 16978.8 | 16285.7 | 13752.9 | 10220.4 | 6686.6 |
| 47.5°  | 14811.6 | 14645.0 | 14478.3 | 14614.9 | 14751.4 | 15952.5 | 17388.4 | 16809.8 | 14321.0 | 10516.5 | 6711.0 |
| 50°    | 16180.4 | 15716.4 | 15252.4 | 15180.7 | 15109.0 | 16348.2 | 17870.8 | 17476.3 | 15003.6 | 10948.1 | 6892.6 |
| 52.5°  | 17571.1 | 16806.3 | 16041.5 | 15758.1 | 15473.4 | 16820.2 | 18510.7 | 18305.9 | 15977.9 | 11617.0 | 7254.8 |
| 55°    | 18846.2 | 17873.1 | 16900.0 | 16518.2 | 16136.5 | 17542.3 | 19291.7 | 19524.3 | 17226.4 | 12472.0 | 7716.5 |
| 57.5°  | 20085.5 | 18982.8 | 17880.1 | 17526.0 | 17172.0 | 18603.3 | 20281.0 | 20617.8 | 18487.6 | 13292.3 | 8096.0 |
| 60°    | 21268.0 | 20176.9 | 19084.6 | 18801.1 | 18516.5 | 19922.4 | 21350.1 | 21104.9 | 19137.8 | 13676.5 | 8214.0 |
| 62.5°  | 22177.4 | 21309.6 | 20441.9 | 20292.6 | 20142.2 | 21256.4 | 22171.7 | 20915.1 | 18724.8 | 13298.1 | 7871.5 |
| 65°    | 22560.4 | 22066.4 | 21571.1 | 21711.1 | 21850.0 | 22265.4 | 22376.4 | 20359.7 | 17426.6 | 12238.3 | 7050.0 |
| 67.5°  | 21460.1 | 21560.8 | 21661.4 | 22249.2 | 22835.8 | 22550.0 | 21767.8 | 19265.1 | 15578.7 | 10736.4 | 5894.1 |
| 70°    | 18148.5 | 18752.5 | 19355.3 | 20746.1 | 22135.8 | 21501.7 | 20137.5 | 17300.4 | 13354.9 | 9006.6  | 4657.2 |
| 72.5°  | 13888.3 | 14567.4 | 15245.4 | 17309.6 | 19372.7 | 18788.4 | 17117.6 | 14209.9 | 10707.5 | 7192.3  | 3676.0 |
| 75°    | 10056.1 | 10823.2 | 11589.1 | 13866.3 | 16143.3 | 15332.2 | 12804.0 | 10174.1 | 8133.0  | 5490.3  | 2846.3 |
| 77.5°  | 7163.4  | 7677.2  | 8190.8  | 10440.2 | 12688.3 | 11367.0 | 8522.9  | 6846.3  | 5629.2  | 3816.0  | 2001.7 |
| 80°    | 5746.0  | 5588.6  | 5431.3  | 6684.3  | 7937.4  | 7717.6  | 5637.3  | 4396.8  | 3895.8  | 2557.1  | 1218.4 |
| 82.5°  | 4687.3  | 4303.1  | 3919.0  | 4509.1  | 5099.2  | 5066.8  | 3912.0  | 3225.9  | 2899.6  | 1777.2  | 654.9  |
| 85°    | 3433.0  | 3279.1  | 3125.2  | 3647.1  | 4168.9  | 3723.4  | 2649.7  | 2050.3  | 2260.9  | 1308.6  | 356.4  |
| 87.5°  | 1674.3  | 1912.7  | 2149.8  | 2765.4  | 3379.7  | 2537.4  | 804.2   | 398.1   | 550.7   | 362.2   | 172.4  |
| 90°    | 0.0     | 0.0     | 0.0     | 0.0     | 0.0     | 0.0     | 0.0     | 0.0     | 0.0     | 0.0     | 0.0    |
| 92.5°  | 0.0     | 0.0     | 0.0     | 0.0     | 0.0     | 0.0     | 0.0     | 0.0     | 0.0     | 0.0     | 0.0    |
| 95°    | 0.0     | 0.0     | 0.0     | 0.0     | 0.0     | 0.0     | 0.0     | 0.0     | 0.0     | 0.0     | 0.0    |
| 97.5°  | 0.0     | 0.0     | 0.0     | 0.0     | 0.0     | 0.0     | 0.0     | 0.0     | 0.0     | 0.0     | 0.0    |
| 100°   | 0.0     | 0.0     | 0.0     | 0.0     | 0.0     | 0.0     | 0.0     | 0.0     | 0.0     | 0.0     | 0.0    |
| 102.5° | 0.0     | 0.0     | 0.0     | 0.0     | 0.0     | 0.0     | 0.0     | 0.0     | 0.0     | 0.0     | 0.0    |
| 105°   | 0.0     | 0.0     | 0.0     | 0.0     | 0.0     | 0.0     | 0.0     | 0.0     | 0.0     | 0.0     | 0.0    |
| 107.5° | 0.0     | 0.0     | 0.0     | 0.0     | 0.0     | 0.0     | 0.0     | 0.0     | 0.0     | 0.0     | 0.0    |
| 110°   | 0.0     | 0.0     | 0.0     | 0.0     | 0.0     | 0.0     | 0.0     | 0.0     | 0.0     | 0.0     | 0.0    |



REPORT NUMBER: P383227  
 CATALOG NUMBER: GAN-SA5C-735-U-SLL

**CANDELA DISTRIBUTION (continued):**

|        | 55° | 60° | 65° | 70° | 75° | 80° | 85° | 90° | 95° | 100° | 105° |
|--------|-----|-----|-----|-----|-----|-----|-----|-----|-----|------|------|
| 112.5° | 0.0 | 0.0 | 0.0 | 0.0 | 0.0 | 0.0 | 0.0 | 0.0 | 0.0 | 0.0  | 0.0  |
| 115°   | 0.0 | 0.0 | 0.0 | 0.0 | 0.0 | 0.0 | 0.0 | 0.0 | 0.0 | 0.0  | 0.0  |
| 117.5° | 0.0 | 0.0 | 0.0 | 0.0 | 0.0 | 0.0 | 0.0 | 0.0 | 0.0 | 0.0  | 0.0  |
| 120°   | 0.0 | 0.0 | 0.0 | 0.0 | 0.0 | 0.0 | 0.0 | 0.0 | 0.0 | 0.0  | 0.0  |
| 122.5° | 0.0 | 0.0 | 0.0 | 0.0 | 0.0 | 0.0 | 0.0 | 0.0 | 0.0 | 0.0  | 0.0  |
| 125°   | 0.0 | 0.0 | 0.0 | 0.0 | 0.0 | 0.0 | 0.0 | 0.0 | 0.0 | 0.0  | 0.0  |
| 127.5° | 0.0 | 0.0 | 0.0 | 0.0 | 0.0 | 0.0 | 0.0 | 0.0 | 0.0 | 0.0  | 0.0  |
| 130°   | 0.0 | 0.0 | 0.0 | 0.0 | 0.0 | 0.0 | 0.0 | 0.0 | 0.0 | 0.0  | 0.0  |
| 132.5° | 0.0 | 0.0 | 0.0 | 0.0 | 0.0 | 0.0 | 0.0 | 0.0 | 0.0 | 0.0  | 0.0  |
| 135°   | 0.0 | 0.0 | 0.0 | 0.0 | 0.0 | 0.0 | 0.0 | 0.0 | 0.0 | 0.0  | 0.0  |
| 137.5° | 0.0 | 0.0 | 0.0 | 0.0 | 0.0 | 0.0 | 0.0 | 0.0 | 0.0 | 0.0  | 0.0  |
| 140°   | 0.0 | 0.0 | 0.0 | 0.0 | 0.0 | 0.0 | 0.0 | 0.0 | 0.0 | 0.0  | 0.0  |
| 142.5° | 0.0 | 0.0 | 0.0 | 0.0 | 0.0 | 0.0 | 0.0 | 0.0 | 0.0 | 0.0  | 0.0  |
| 145°   | 0.0 | 0.0 | 0.0 | 0.0 | 0.0 | 0.0 | 0.0 | 0.0 | 0.0 | 0.0  | 0.0  |
| 147.5° | 0.0 | 0.0 | 0.0 | 0.0 | 0.0 | 0.0 | 0.0 | 0.0 | 0.0 | 0.0  | 0.0  |
| 150°   | 0.0 | 0.0 | 0.0 | 0.0 | 0.0 | 0.0 | 0.0 | 0.0 | 0.0 | 0.0  | 0.0  |
| 152.5° | 0.0 | 0.0 | 0.0 | 0.0 | 0.0 | 0.0 | 0.0 | 0.0 | 0.0 | 0.0  | 0.0  |
| 155°   | 0.0 | 0.0 | 0.0 | 0.0 | 0.0 | 0.0 | 0.0 | 0.0 | 0.0 | 0.0  | 0.0  |
| 157.5° | 0.0 | 0.0 | 0.0 | 0.0 | 0.0 | 0.0 | 0.0 | 0.0 | 0.0 | 0.0  | 0.0  |
| 160°   | 0.0 | 0.0 | 0.0 | 0.0 | 0.0 | 0.0 | 0.0 | 0.0 | 0.0 | 0.0  | 0.0  |
| 162.5° | 0.0 | 0.0 | 0.0 | 0.0 | 0.0 | 0.0 | 0.0 | 0.0 | 0.0 | 0.0  | 0.0  |
| 165°   | 0.0 | 0.0 | 0.0 | 0.0 | 0.0 | 0.0 | 0.0 | 0.0 | 0.0 | 0.0  | 0.0  |
| 167.5° | 0.0 | 0.0 | 0.0 | 0.0 | 0.0 | 0.0 | 0.0 | 0.0 | 0.0 | 0.0  | 0.0  |
| 170°   | 0.0 | 0.0 | 0.0 | 0.0 | 0.0 | 0.0 | 0.0 | 0.0 | 0.0 | 0.0  | 0.0  |
| 172.5° | 0.0 | 0.0 | 0.0 | 0.0 | 0.0 | 0.0 | 0.0 | 0.0 | 0.0 | 0.0  | 0.0  |
| 175°   | 0.0 | 0.0 | 0.0 | 0.0 | 0.0 | 0.0 | 0.0 | 0.0 | 0.0 | 0.0  | 0.0  |
| 177.5° | 0.0 | 0.0 | 0.0 | 0.0 | 0.0 | 0.0 | 0.0 | 0.0 | 0.0 | 0.0  | 0.0  |
| 180°   | 0.0 | 0.0 | 0.0 | 0.0 | 0.0 | 0.0 | 0.0 | 0.0 | 0.0 | 0.0  | 0.0  |



REPORT NUMBER: P383227

CATALOG NUMBER: GAN-SA5C-735-U-SLL

**CANDELA DISTRIBUTION (continued):**

|        | 110°   | 115°   | 120°   | 125°   | 130°   | 135°   | 140°   | 145°   | 150°   | 155°   | 160°   |
|--------|--------|--------|--------|--------|--------|--------|--------|--------|--------|--------|--------|
| 0°     | 8816.8 | 8816.8 | 8816.8 | 8816.8 | 8816.8 | 8816.8 | 8816.8 | 8816.8 | 8816.8 | 8816.8 | 8816.8 |
| 2.5°   | 9015.8 | 8921.0 | 8813.4 | 8705.8 | 8583.1 | 8459.3 | 8386.4 | 8312.4 | 8232.6 | 8152.6 | 8062.5 |
| 5°     | 8256.8 | 8057.8 | 7832.2 | 7606.6 | 7383.3 | 7159.9 | 7039.6 | 6919.3 | 6792.0 | 6663.5 | 6552.4 |
| 7.5°   | 7166.9 | 6876.4 | 6564.1 | 6250.5 | 5972.8 | 5693.9 | 5521.5 | 5347.9 | 5190.6 | 5032.0 | 4899.0 |
| 10°    | 6207.6 | 5837.4 | 5523.8 | 5209.1 | 4999.7 | 4790.2 | 4631.7 | 4473.2 | 4320.5 | 4166.6 | 4019.6 |
| 12.5°  | 5575.9 | 5205.7 | 5006.6 | 4807.6 | 4634.1 | 4460.4 | 4277.7 | 4093.7 | 3884.3 | 3673.7 | 3519.8 |
| 15°    | 5329.5 | 4992.7 | 4771.8 | 4549.6 | 4317.0 | 4083.3 | 3858.8 | 3634.3 | 3386.7 | 3139.1 | 2964.4 |
| 17.5°  | 5223.0 | 4782.1 | 4473.2 | 4163.1 | 3856.5 | 3549.8 | 3289.6 | 3029.2 | 2758.4 | 2487.7 | 2310.6 |
| 20°    | 5110.7 | 4524.2 | 4109.9 | 3694.5 | 3301.1 | 2907.7 | 2612.6 | 2317.6 | 2075.8 | 1833.9 | 1698.6 |
| 22.5°  | 5008.9 | 4249.9 | 3730.4 | 3209.7 | 2744.5 | 2279.4 | 1990.2 | 1699.7 | 1551.6 | 1403.6 | 1349.2 |
| 25°    | 4967.3 | 4010.4 | 3371.6 | 2733.0 | 2242.4 | 1750.7 | 1544.7 | 1338.7 | 1282.0 | 1224.1 | 1196.4 |
| 27.5°  | 4974.2 | 3796.3 | 3069.7 | 2341.9 | 1899.9 | 1457.9 | 1316.7 | 1175.6 | 1140.9 | 1105.0 | 1087.7 |
| 30°    | 5000.8 | 3563.7 | 2785.0 | 2006.4 | 1641.9 | 1277.4 | 1186.0 | 1093.5 | 1056.4 | 1019.4 | 997.4  |
| 32.5°  | 5030.9 | 3355.5 | 2565.2 | 1773.8 | 1476.4 | 1177.8 | 1102.7 | 1026.3 | 990.4  | 954.6  | 932.6  |
| 35°    | 4978.8 | 3185.4 | 2414.8 | 1644.2 | 1369.9 | 1094.6 | 1030.9 | 966.1  | 926.8  | 887.5  | 866.6  |
| 37.5°  | 4890.9 | 3014.1 | 2297.9 | 1580.6 | 1300.5 | 1019.4 | 973.1  | 925.7  | 885.2  | 843.5  | 823.9  |
| 40°    | 4811.1 | 2869.5 | 2211.1 | 1551.6 | 1262.3 | 972.0  | 932.6  | 893.3  | 851.6  | 808.8  | 785.7  |
| 42.5°  | 4746.2 | 2772.3 | 2125.5 | 1478.7 | 1227.7 | 975.4  | 919.9  | 863.2  | 822.6  | 782.2  | 756.7  |
| 45°    | 4697.7 | 2708.7 | 2058.4 | 1408.1 | 1195.3 | 982.3  | 911.8  | 841.2  | 800.7  | 759.0  | 728.9  |
| 47.5°  | 4693.0 | 2675.1 | 2010.9 | 1346.8 | 1133.9 | 919.9  | 890.9  | 862.1  | 803.0  | 742.8  | 708.2  |
| 50°    | 4756.7 | 2620.7 | 1955.4 | 1289.0 | 1074.9 | 860.8  | 900.2  | 938.3  | 837.7  | 735.9  | 692.0  |
| 52.5°  | 4889.8 | 2524.7 | 1867.5 | 1210.3 | 1003.2 | 794.9  | 856.2  | 916.4  | 829.6  | 741.7  | 685.0  |
| 55°    | 5050.6 | 2383.6 | 1734.4 | 1084.1 | 908.3  | 731.3  | 785.7  | 838.9  | 784.5  | 728.9  | 660.7  |
| 57.5°  | 5151.3 | 2205.3 | 1566.7 | 928.0  | 801.9  | 675.7  | 707.0  | 737.0  | 715.1  | 693.1  | 623.7  |
| 60°    | 5091.1 | 1968.2 | 1378.0 | 786.8  | 708.2  | 629.4  | 623.7  | 616.7  | 649.1  | 681.5  | 601.7  |
| 62.5°  | 4797.2 | 1722.9 | 1211.5 | 700.1  | 641.0  | 580.8  | 568.2  | 554.3  | 607.5  | 659.5  | 575.0  |
| 65°    | 4300.8 | 1551.6 | 1106.1 | 660.7  | 594.7  | 528.7  | 514.9  | 501.0  | 517.2  | 533.4  | 494.1  |
| 67.5°  | 3670.2 | 1446.3 | 1045.9 | 645.7  | 565.8  | 484.8  | 468.6  | 452.5  | 448.9  | 445.5  | 431.6  |
| 70°    | 3019.9 | 1381.6 | 1006.6 | 631.8  | 534.5  | 436.2  | 421.2  | 406.2  | 401.5  | 395.7  | 385.3  |
| 72.5°  | 2524.7 | 1373.5 | 1002.0 | 630.6  | 509.1  | 387.6  | 373.7  | 359.9  | 354.1  | 347.1  | 339.0  |
| 75°    | 2067.7 | 1289.0 | 951.1  | 613.2  | 474.4  | 334.4  | 321.7  | 308.9  | 304.3  | 298.6  | 291.6  |
| 77.5°  | 1534.3 | 1066.8 | 799.5  | 532.3  | 406.2  | 280.0  | 267.3  | 253.4  | 252.3  | 249.9  | 244.2  |
| 80°    | 995.1  | 771.8  | 571.6  | 371.4  | 296.2  | 219.8  | 209.4  | 197.9  | 199.0  | 200.2  | 195.5  |
| 82.5°  | 553.1  | 450.1  | 349.4  | 248.7  | 202.5  | 156.2  | 151.6  | 145.8  | 149.2  | 151.6  | 145.8  |
| 85°    | 291.6  | 226.7  | 187.4  | 148.1  | 116.9  | 85.6   | 85.6   | 84.5   | 89.1   | 93.7   | 89.1   |
| 87.5°  | 126.1  | 79.8   | 68.3   | 55.5   | 31.2   | 5.8    | 7.0    | 7.0    | 9.2    | 11.6   | 10.4   |
| 90°    | 0.0    | 0.0    | 0.0    | 0.0    | 0.0    | 0.0    | 0.0    | 0.0    | 0.0    | 0.0    | 0.0    |
| 92.5°  | 0.0    | 0.0    | 0.0    | 0.0    | 0.0    | 0.0    | 0.0    | 0.0    | 0.0    | 0.0    | 0.0    |
| 95°    | 0.0    | 0.0    | 0.0    | 0.0    | 0.0    | 0.0    | 0.0    | 0.0    | 0.0    | 0.0    | 0.0    |
| 97.5°  | 0.0    | 0.0    | 0.0    | 0.0    | 0.0    | 0.0    | 0.0    | 0.0    | 0.0    | 0.0    | 0.0    |
| 100°   | 0.0    | 0.0    | 0.0    | 0.0    | 0.0    | 0.0    | 0.0    | 0.0    | 0.0    | 0.0    | 0.0    |
| 102.5° | 0.0    | 0.0    | 0.0    | 0.0    | 0.0    | 0.0    | 0.0    | 0.0    | 0.0    | 0.0    | 0.0    |
| 105°   | 0.0    | 0.0    | 0.0    | 0.0    | 0.0    | 0.0    | 0.0    | 0.0    | 0.0    | 0.0    | 0.0    |
| 107.5° | 0.0    | 0.0    | 0.0    | 0.0    | 0.0    | 0.0    | 0.0    | 0.0    | 0.0    | 0.0    | 0.0    |
| 110°   | 0.0    | 0.0    | 0.0    | 0.0    | 0.0    | 0.0    | 0.0    | 0.0    | 0.0    | 0.0    | 0.0    |



REPORT NUMBER: P383227  
 CATALOG NUMBER: GAN-SA5C-735-U-SLL

**CANDELA DISTRIBUTION (continued):**

|        | 110° | 115° | 120° | 125° | 130° | 135° | 140° | 145° | 150° | 155° | 160° |
|--------|------|------|------|------|------|------|------|------|------|------|------|
| 112.5° | 0.0  | 0.0  | 0.0  | 0.0  | 0.0  | 0.0  | 0.0  | 0.0  | 0.0  | 0.0  | 0.0  |
| 115°   | 0.0  | 0.0  | 0.0  | 0.0  | 0.0  | 0.0  | 0.0  | 0.0  | 0.0  | 0.0  | 0.0  |
| 117.5° | 0.0  | 0.0  | 0.0  | 0.0  | 0.0  | 0.0  | 0.0  | 0.0  | 0.0  | 0.0  | 0.0  |
| 120°   | 0.0  | 0.0  | 0.0  | 0.0  | 0.0  | 0.0  | 0.0  | 0.0  | 0.0  | 0.0  | 0.0  |
| 122.5° | 0.0  | 0.0  | 0.0  | 0.0  | 0.0  | 0.0  | 0.0  | 0.0  | 0.0  | 0.0  | 0.0  |
| 125°   | 0.0  | 0.0  | 0.0  | 0.0  | 0.0  | 0.0  | 0.0  | 0.0  | 0.0  | 0.0  | 0.0  |
| 127.5° | 0.0  | 0.0  | 0.0  | 0.0  | 0.0  | 0.0  | 0.0  | 0.0  | 0.0  | 0.0  | 0.0  |
| 130°   | 0.0  | 0.0  | 0.0  | 0.0  | 0.0  | 0.0  | 0.0  | 0.0  | 0.0  | 0.0  | 0.0  |
| 132.5° | 0.0  | 0.0  | 0.0  | 0.0  | 0.0  | 0.0  | 0.0  | 0.0  | 0.0  | 0.0  | 0.0  |
| 135°   | 0.0  | 0.0  | 0.0  | 0.0  | 0.0  | 0.0  | 0.0  | 0.0  | 0.0  | 0.0  | 0.0  |
| 137.5° | 0.0  | 0.0  | 0.0  | 0.0  | 0.0  | 0.0  | 0.0  | 0.0  | 0.0  | 0.0  | 0.0  |
| 140°   | 0.0  | 0.0  | 0.0  | 0.0  | 0.0  | 0.0  | 0.0  | 0.0  | 0.0  | 0.0  | 0.0  |
| 142.5° | 0.0  | 0.0  | 0.0  | 0.0  | 0.0  | 0.0  | 0.0  | 0.0  | 0.0  | 0.0  | 0.0  |
| 145°   | 0.0  | 0.0  | 0.0  | 0.0  | 0.0  | 0.0  | 0.0  | 0.0  | 0.0  | 0.0  | 0.0  |
| 147.5° | 0.0  | 0.0  | 0.0  | 0.0  | 0.0  | 0.0  | 0.0  | 0.0  | 0.0  | 0.0  | 0.0  |
| 150°   | 0.0  | 0.0  | 0.0  | 0.0  | 0.0  | 0.0  | 0.0  | 0.0  | 0.0  | 0.0  | 0.0  |
| 152.5° | 0.0  | 0.0  | 0.0  | 0.0  | 0.0  | 0.0  | 0.0  | 0.0  | 0.0  | 0.0  | 0.0  |
| 155°   | 0.0  | 0.0  | 0.0  | 0.0  | 0.0  | 0.0  | 0.0  | 0.0  | 0.0  | 0.0  | 0.0  |
| 157.5° | 0.0  | 0.0  | 0.0  | 0.0  | 0.0  | 0.0  | 0.0  | 0.0  | 0.0  | 0.0  | 0.0  |
| 160°   | 0.0  | 0.0  | 0.0  | 0.0  | 0.0  | 0.0  | 0.0  | 0.0  | 0.0  | 0.0  | 0.0  |
| 162.5° | 0.0  | 0.0  | 0.0  | 0.0  | 0.0  | 0.0  | 0.0  | 0.0  | 0.0  | 0.0  | 0.0  |
| 165°   | 0.0  | 0.0  | 0.0  | 0.0  | 0.0  | 0.0  | 0.0  | 0.0  | 0.0  | 0.0  | 0.0  |
| 167.5° | 0.0  | 0.0  | 0.0  | 0.0  | 0.0  | 0.0  | 0.0  | 0.0  | 0.0  | 0.0  | 0.0  |
| 170°   | 0.0  | 0.0  | 0.0  | 0.0  | 0.0  | 0.0  | 0.0  | 0.0  | 0.0  | 0.0  | 0.0  |
| 172.5° | 0.0  | 0.0  | 0.0  | 0.0  | 0.0  | 0.0  | 0.0  | 0.0  | 0.0  | 0.0  | 0.0  |
| 175°   | 0.0  | 0.0  | 0.0  | 0.0  | 0.0  | 0.0  | 0.0  | 0.0  | 0.0  | 0.0  | 0.0  |
| 177.5° | 0.0  | 0.0  | 0.0  | 0.0  | 0.0  | 0.0  | 0.0  | 0.0  | 0.0  | 0.0  | 0.0  |
| 180°   | 0.0  | 0.0  | 0.0  | 0.0  | 0.0  | 0.0  | 0.0  | 0.0  | 0.0  | 0.0  | 0.0  |



REPORT NUMBER: P383227

CATALOG NUMBER: GAN-SA5C-735-U-SLL

**CANDELA DISTRIBUTION (continued):**

|        | 165°   | 170°   | 175°   | 180°   | 185°   | 190°   | 195°   | 200°   | 205°   | 210°   | 215°   |
|--------|--------|--------|--------|--------|--------|--------|--------|--------|--------|--------|--------|
| 0°     | 8816.8 | 8816.8 | 8816.8 | 8816.8 | 8816.8 | 8816.8 | 8816.8 | 8816.8 | 8816.8 | 8816.8 | 8816.8 |
| 2.5°   | 7971.0 | 7886.6 | 7801.0 | 7707.2 | 7724.6 | 7652.8 | 7581.1 | 7535.9 | 7490.9 | 7477.0 | 7463.1 |
| 5°     | 6441.4 | 6345.3 | 6248.2 | 6161.3 | 6236.6 | 6185.7 | 6134.7 | 6127.8 | 6119.7 | 6119.7 | 6118.6 |
| 7.5°   | 4766.0 | 4663.0 | 4558.8 | 4487.1 | 4561.1 | 4551.9 | 4542.6 | 4592.3 | 4642.2 | 4682.6 | 4722.0 |
| 10°    | 3872.7 | 3747.7 | 3621.6 | 3515.2 | 3496.7 | 3443.5 | 3389.1 | 3400.6 | 3411.0 | 3455.0 | 3499.0 |
| 12.5°  | 3365.9 | 3216.6 | 3067.4 | 2942.4 | 2885.7 | 2797.8 | 2708.7 | 2653.1 | 2597.6 | 2603.4 | 2608.1 |
| 15°    | 2788.5 | 2643.9 | 2498.1 | 2390.5 | 2354.6 | 2286.4 | 2218.1 | 2148.7 | 2078.1 | 2049.1 | 2019.0 |
| 17.5°  | 2132.5 | 2016.8 | 1899.9 | 1828.2 | 1828.2 | 1808.5 | 1788.9 | 1754.1 | 1718.2 | 1689.3 | 1659.3 |
| 20°    | 1563.2 | 1501.8 | 1439.4 | 1409.3 | 1418.6 | 1419.7 | 1419.7 | 1437.1 | 1454.4 | 1445.2 | 1435.9 |
| 22.5°  | 1293.6 | 1271.7 | 1249.7 | 1236.9 | 1241.6 | 1242.7 | 1243.8 | 1260.0 | 1275.1 | 1286.7 | 1297.1 |
| 25°    | 1167.5 | 1153.6 | 1139.7 | 1135.1 | 1145.5 | 1146.6 | 1146.6 | 1157.1 | 1167.5 | 1179.1 | 1190.6 |
| 27.5°  | 1069.1 | 1063.4 | 1057.6 | 1049.5 | 1059.9 | 1059.9 | 1058.7 | 1070.3 | 1080.7 | 1091.1 | 1100.3 |
| 30°    | 975.4  | 977.8  | 978.9  | 976.5  | 983.5  | 988.1  | 991.6  | 999.7  | 1006.6 | 1014.7 | 1022.8 |
| 32.5°  | 909.5  | 906.0  | 902.5  | 900.2  | 915.2  | 923.3  | 931.5  | 939.6  | 946.5  | 950.0  | 953.4  |
| 35°    | 845.8  | 837.7  | 829.6  | 823.9  | 837.7  | 848.2  | 858.5  | 873.6  | 887.5  | 889.8  | 892.0  |
| 37.5°  | 803.0  | 792.6  | 782.2  | 775.2  | 781.0  | 785.7  | 790.2  | 806.4  | 822.6  | 832.0  | 840.1  |
| 40°    | 762.5  | 752.1  | 741.7  | 735.9  | 739.4  | 740.5  | 741.7  | 749.8  | 756.7  | 774.1  | 790.2  |
| 42.5°  | 730.1  | 717.4  | 704.6  | 697.7  | 700.1  | 702.3  | 703.5  | 702.3  | 701.2  | 717.4  | 733.6  |
| 45°    | 697.7  | 683.8  | 670.0  | 661.9  | 663.0  | 663.0  | 663.0  | 660.7  | 657.2  | 665.3  | 673.4  |
| 47.5°  | 672.3  | 656.1  | 639.9  | 631.8  | 629.4  | 627.1  | 624.8  | 623.7  | 621.3  | 627.1  | 631.8  |
| 50°    | 646.8  | 629.4  | 610.9  | 601.7  | 595.9  | 593.6  | 591.3  | 590.1  | 587.8  | 593.6  | 598.2  |
| 52.5°  | 627.1  | 606.3  | 585.5  | 570.4  | 564.6  | 561.2  | 557.7  | 558.8  | 558.8  | 561.2  | 562.4  |
| 55°    | 592.4  | 573.9  | 554.3  | 543.8  | 533.4  | 531.1  | 528.7  | 532.3  | 534.5  | 534.5  | 534.5  |
| 57.5°  | 554.3  | 536.9  | 518.4  | 511.4  | 502.2  | 502.2  | 501.0  | 505.6  | 509.1  | 511.4  | 513.7  |
| 60°    | 520.6  | 501.0  | 481.3  | 475.6  | 472.1  | 470.9  | 469.8  | 475.6  | 480.2  | 484.8  | 489.4  |
| 62.5°  | 489.4  | 468.6  | 447.8  | 440.8  | 439.7  | 440.8  | 440.8  | 446.6  | 451.2  | 455.9  | 460.6  |
| 65°    | 454.7  | 433.9  | 411.9  | 404.9  | 407.3  | 410.7  | 414.3  | 418.8  | 422.4  | 426.9  | 431.6  |
| 67.5°  | 416.6  | 399.2  | 380.6  | 373.7  | 374.9  | 379.5  | 384.2  | 387.6  | 389.9  | 394.6  | 399.2  |
| 70°    | 374.9  | 359.9  | 344.8  | 340.2  | 339.0  | 344.8  | 349.4  | 351.8  | 354.1  | 359.9  | 364.5  |
| 72.5°  | 329.8  | 317.0  | 304.3  | 300.8  | 302.0  | 305.5  | 308.9  | 312.4  | 314.7  | 320.5  | 325.1  |
| 75°    | 283.5  | 271.9  | 260.4  | 258.0  | 260.4  | 263.8  | 267.3  | 269.6  | 271.9  | 278.8  | 284.7  |
| 77.5°  | 238.4  | 225.6  | 211.7  | 210.6  | 214.1  | 217.5  | 219.8  | 223.3  | 226.7  | 236.1  | 245.3  |
| 80°    | 190.9  | 177.0  | 162.0  | 160.9  | 164.3  | 167.8  | 171.2  | 174.8  | 178.2  | 189.8  | 200.2  |
| 82.5°  | 140.0  | 123.8  | 107.6  | 105.3  | 116.9  | 120.4  | 123.8  | 129.6  | 134.2  | 144.7  | 155.0  |
| 85°    | 84.5   | 68.3   | 52.1   | 51.0   | 61.3   | 67.1   | 72.9   | 79.8   | 85.6   | 94.9   | 104.1  |
| 87.5°  | 9.2    | 4.7    | 0.0    | 0.0    | 1.1    | 5.8    | 10.4   | 16.2   | 22.0   | 31.2   | 39.3   |
| 90°    | 0.0    | 0.0    | 0.0    | 0.0    | 0.0    | 0.0    | 0.0    | 0.0    | 0.0    | 0.0    | 0.0    |
| 92.5°  | 0.0    | 0.0    | 0.0    | 0.0    | 0.0    | 0.0    | 0.0    | 0.0    | 0.0    | 0.0    | 0.0    |
| 95°    | 0.0    | 0.0    | 0.0    | 0.0    | 0.0    | 0.0    | 0.0    | 0.0    | 0.0    | 0.0    | 0.0    |
| 97.5°  | 0.0    | 0.0    | 0.0    | 0.0    | 0.0    | 0.0    | 0.0    | 0.0    | 0.0    | 0.0    | 0.0    |
| 100°   | 0.0    | 0.0    | 0.0    | 0.0    | 0.0    | 0.0    | 0.0    | 0.0    | 0.0    | 0.0    | 0.0    |
| 102.5° | 0.0    | 0.0    | 0.0    | 0.0    | 0.0    | 0.0    | 0.0    | 0.0    | 0.0    | 0.0    | 0.0    |
| 105°   | 0.0    | 0.0    | 0.0    | 0.0    | 0.0    | 0.0    | 0.0    | 0.0    | 0.0    | 0.0    | 0.0    |
| 107.5° | 0.0    | 0.0    | 0.0    | 0.0    | 0.0    | 0.0    | 0.0    | 0.0    | 0.0    | 0.0    | 0.0    |
| 110°   | 0.0    | 0.0    | 0.0    | 0.0    | 0.0    | 0.0    | 0.0    | 0.0    | 0.0    | 0.0    | 0.0    |



REPORT NUMBER: P383227  
 CATALOG NUMBER: GAN-SA5C-735-U-SLL

**CANDELA DISTRIBUTION (continued):**

|        | 165° | 170° | 175° | 180° | 185° | 190° | 195° | 200° | 205° | 210° | 215° |
|--------|------|------|------|------|------|------|------|------|------|------|------|
| 112.5° | 0.0  | 0.0  | 0.0  | 0.0  | 0.0  | 0.0  | 0.0  | 0.0  | 0.0  | 0.0  | 0.0  |
| 115°   | 0.0  | 0.0  | 0.0  | 0.0  | 0.0  | 0.0  | 0.0  | 0.0  | 0.0  | 0.0  | 0.0  |
| 117.5° | 0.0  | 0.0  | 0.0  | 0.0  | 0.0  | 0.0  | 0.0  | 0.0  | 0.0  | 0.0  | 0.0  |
| 120°   | 0.0  | 0.0  | 0.0  | 0.0  | 0.0  | 0.0  | 0.0  | 0.0  | 0.0  | 0.0  | 0.0  |
| 122.5° | 0.0  | 0.0  | 0.0  | 0.0  | 0.0  | 0.0  | 0.0  | 0.0  | 0.0  | 0.0  | 0.0  |
| 125°   | 0.0  | 0.0  | 0.0  | 0.0  | 0.0  | 0.0  | 0.0  | 0.0  | 0.0  | 0.0  | 0.0  |
| 127.5° | 0.0  | 0.0  | 0.0  | 0.0  | 0.0  | 0.0  | 0.0  | 0.0  | 0.0  | 0.0  | 0.0  |
| 130°   | 0.0  | 0.0  | 0.0  | 0.0  | 0.0  | 0.0  | 0.0  | 0.0  | 0.0  | 0.0  | 0.0  |
| 132.5° | 0.0  | 0.0  | 0.0  | 0.0  | 0.0  | 0.0  | 0.0  | 0.0  | 0.0  | 0.0  | 0.0  |
| 135°   | 0.0  | 0.0  | 0.0  | 0.0  | 0.0  | 0.0  | 0.0  | 0.0  | 0.0  | 0.0  | 0.0  |
| 137.5° | 0.0  | 0.0  | 0.0  | 0.0  | 0.0  | 0.0  | 0.0  | 0.0  | 0.0  | 0.0  | 0.0  |
| 140°   | 0.0  | 0.0  | 0.0  | 0.0  | 0.0  | 0.0  | 0.0  | 0.0  | 0.0  | 0.0  | 0.0  |
| 142.5° | 0.0  | 0.0  | 0.0  | 0.0  | 0.0  | 0.0  | 0.0  | 0.0  | 0.0  | 0.0  | 0.0  |
| 145°   | 0.0  | 0.0  | 0.0  | 0.0  | 0.0  | 0.0  | 0.0  | 0.0  | 0.0  | 0.0  | 0.0  |
| 147.5° | 0.0  | 0.0  | 0.0  | 0.0  | 0.0  | 0.0  | 0.0  | 0.0  | 0.0  | 0.0  | 0.0  |
| 150°   | 0.0  | 0.0  | 0.0  | 0.0  | 0.0  | 0.0  | 0.0  | 0.0  | 0.0  | 0.0  | 0.0  |
| 152.5° | 0.0  | 0.0  | 0.0  | 0.0  | 0.0  | 0.0  | 0.0  | 0.0  | 0.0  | 0.0  | 0.0  |
| 155°   | 0.0  | 0.0  | 0.0  | 0.0  | 0.0  | 0.0  | 0.0  | 0.0  | 0.0  | 0.0  | 0.0  |
| 157.5° | 0.0  | 0.0  | 0.0  | 0.0  | 0.0  | 0.0  | 0.0  | 0.0  | 0.0  | 0.0  | 0.0  |
| 160°   | 0.0  | 0.0  | 0.0  | 0.0  | 0.0  | 0.0  | 0.0  | 0.0  | 0.0  | 0.0  | 0.0  |
| 162.5° | 0.0  | 0.0  | 0.0  | 0.0  | 0.0  | 0.0  | 0.0  | 0.0  | 0.0  | 0.0  | 0.0  |
| 165°   | 0.0  | 0.0  | 0.0  | 0.0  | 0.0  | 0.0  | 0.0  | 0.0  | 0.0  | 0.0  | 0.0  |
| 167.5° | 0.0  | 0.0  | 0.0  | 0.0  | 0.0  | 0.0  | 0.0  | 0.0  | 0.0  | 0.0  | 0.0  |
| 170°   | 0.0  | 0.0  | 0.0  | 0.0  | 0.0  | 0.0  | 0.0  | 0.0  | 0.0  | 0.0  | 0.0  |
| 172.5° | 0.0  | 0.0  | 0.0  | 0.0  | 0.0  | 0.0  | 0.0  | 0.0  | 0.0  | 0.0  | 0.0  |
| 175°   | 0.0  | 0.0  | 0.0  | 0.0  | 0.0  | 0.0  | 0.0  | 0.0  | 0.0  | 0.0  | 0.0  |
| 177.5° | 0.0  | 0.0  | 0.0  | 0.0  | 0.0  | 0.0  | 0.0  | 0.0  | 0.0  | 0.0  | 0.0  |
| 180°   | 0.0  | 0.0  | 0.0  | 0.0  | 0.0  | 0.0  | 0.0  | 0.0  | 0.0  | 0.0  | 0.0  |



REPORT NUMBER: P383227  
 CATALOG NUMBER: GAN-SA5C-735-U-SLL

**CANDELA DISTRIBUTION (continued):**

|        | 220°   | 225°   | 230°   | 235°   | 240°   | 245°   | 250°   | 255°   | 260°   | 265°   | 270°   |
|--------|--------|--------|--------|--------|--------|--------|--------|--------|--------|--------|--------|
| 0°     | 8816.8 | 8816.8 | 8816.8 | 8816.8 | 8816.8 | 8816.8 | 8816.8 | 8816.8 | 8816.8 | 8816.8 | 8816.8 |
| 2.5°   | 7412.1 | 7360.1 | 7413.3 | 7465.3 | 7487.3 | 7509.3 | 7452.7 | 7394.8 | 7485.1 | 7574.1 | 7597.2 |
| 5°     | 6072.3 | 6024.8 | 6060.7 | 6095.4 | 6017.9 | 5940.4 | 5932.3 | 5923.0 | 5990.1 | 6057.2 | 6067.6 |
| 7.5°   | 4706.9 | 4691.9 | 4725.5 | 4759.0 | 4660.6 | 4561.1 | 4512.5 | 4464.0 | 4480.2 | 4496.4 | 4494.1 |
| 10°    | 3509.4 | 3518.6 | 3560.3 | 3600.8 | 3524.4 | 3448.0 | 3414.5 | 3381.0 | 3417.9 | 3453.8 | 3487.4 |
| 12.5°  | 2628.8 | 2648.5 | 2692.5 | 2735.3 | 2704.1 | 2671.7 | 2675.1 | 2678.6 | 2721.4 | 2763.1 | 2800.1 |
| 15°    | 2042.2 | 2065.3 | 2096.6 | 2126.7 | 2127.8 | 2127.8 | 2157.9 | 2186.8 | 2183.4 | 2179.9 | 2205.3 |
| 17.5°  | 1690.5 | 1720.6 | 1724.0 | 1727.5 | 1728.7 | 1729.8 | 1727.5 | 1725.2 | 1707.8 | 1690.5 | 1710.1 |
| 20°    | 1447.5 | 1457.9 | 1467.2 | 1475.3 | 1464.9 | 1453.3 | 1424.3 | 1395.5 | 1383.8 | 1372.3 | 1390.8 |
| 22.5°  | 1316.7 | 1335.3 | 1326.0 | 1315.6 | 1294.8 | 1272.8 | 1250.8 | 1227.7 | 1226.5 | 1224.1 | 1234.6 |
| 25°    | 1206.8 | 1221.8 | 1205.7 | 1189.5 | 1174.4 | 1159.4 | 1144.3 | 1129.3 | 1128.1 | 1127.0 | 1131.6 |
| 27.5°  | 1115.4 | 1129.3 | 1114.2 | 1099.2 | 1086.5 | 1073.8 | 1062.2 | 1050.6 | 1048.3 | 1045.9 | 1047.2 |
| 30°    | 1036.7 | 1049.5 | 1036.7 | 1022.8 | 1013.6 | 1003.2 | 995.1  | 987.0  | 985.9  | 984.6  | 984.6  |
| 32.5°  | 966.1  | 978.9  | 969.6  | 960.3  | 952.2  | 944.1  | 938.3  | 932.6  | 926.8  | 921.0  | 908.3  |
| 35°    | 904.8  | 917.6  | 911.8  | 904.8  | 895.6  | 886.3  | 875.9  | 864.3  | 849.3  | 833.1  | 826.2  |
| 37.5°  | 852.7  | 865.5  | 859.7  | 853.9  | 841.2  | 828.4  | 810.0  | 790.2  | 785.7  | 779.9  | 778.7  |
| 40°    | 811.1  | 830.8  | 819.2  | 806.4  | 786.8  | 767.1  | 757.9  | 748.6  | 746.3  | 744.0  | 741.7  |
| 42.5°  | 764.8  | 794.9  | 774.1  | 753.2  | 734.7  | 716.3  | 713.9  | 711.6  | 710.4  | 709.3  | 709.3  |
| 45°    | 707.0  | 739.4  | 718.5  | 696.5  | 686.2  | 675.7  | 675.7  | 675.7  | 676.9  | 676.9  | 679.2  |
| 47.5°  | 652.5  | 672.3  | 661.9  | 651.4  | 645.7  | 639.9  | 641.0  | 642.2  | 645.7  | 648.0  | 653.8  |
| 50°    | 606.3  | 613.2  | 615.6  | 616.7  | 613.2  | 609.8  | 612.1  | 613.2  | 616.7  | 619.0  | 623.7  |
| 52.5°  | 572.7  | 583.1  | 583.1  | 582.0  | 582.0  | 582.0  | 584.4  | 586.6  | 590.1  | 593.6  | 598.2  |
| 55°    | 550.7  | 565.8  | 561.2  | 556.5  | 557.7  | 557.7  | 560.0  | 562.4  | 565.8  | 568.2  | 575.0  |
| 57.5°  | 530.0  | 546.2  | 541.5  | 536.9  | 536.9  | 536.9  | 538.1  | 539.2  | 542.6  | 545.0  | 549.6  |
| 60°    | 505.6  | 521.9  | 517.2  | 511.4  | 512.5  | 513.7  | 514.9  | 514.9  | 517.2  | 518.4  | 518.4  |
| 62.5°  | 476.7  | 492.9  | 488.3  | 482.5  | 486.0  | 488.3  | 488.3  | 488.3  | 490.6  | 491.8  | 488.3  |
| 65°    | 446.6  | 461.7  | 457.0  | 452.5  | 457.0  | 460.6  | 462.8  | 464.0  | 462.8  | 461.7  | 458.2  |
| 67.5°  | 414.3  | 429.3  | 424.6  | 418.8  | 424.6  | 429.3  | 433.9  | 437.4  | 433.9  | 430.5  | 425.8  |
| 70°    | 379.5  | 394.6  | 388.7  | 383.0  | 388.7  | 394.6  | 399.2  | 403.8  | 399.2  | 394.6  | 393.4  |
| 72.5°  | 342.5  | 359.9  | 352.9  | 346.0  | 352.9  | 359.9  | 362.2  | 364.5  | 361.0  | 357.5  | 355.2  |
| 75°    | 302.0  | 319.3  | 313.6  | 306.7  | 312.4  | 318.2  | 319.3  | 320.5  | 320.5  | 319.3  | 312.4  |
| 77.5°  | 259.2  | 273.0  | 269.6  | 266.1  | 269.6  | 273.0  | 273.0  | 273.0  | 274.2  | 274.2  | 264.9  |
| 80°    | 208.3  | 216.4  | 217.5  | 218.7  | 219.8  | 221.0  | 219.8  | 218.7  | 216.4  | 214.1  | 208.3  |
| 82.5°  | 155.0  | 155.0  | 164.3  | 172.4  | 172.4  | 171.2  | 170.1  | 167.8  | 163.1  | 157.3  | 144.7  |
| 85°    | 98.4   | 92.6   | 107.6  | 121.5  | 121.5  | 120.4  | 118.0  | 114.6  | 105.3  | 94.9   | 84.5   |
| 87.5°  | 33.5   | 27.8   | 42.9   | 57.8   | 59.0   | 59.0   | 56.7   | 54.4   | 45.1   | 34.7   | 26.6   |
| 90°    | 0.0    | 0.0    | 0.0    | 0.0    | 0.0    | 0.0    | 0.0    | 0.0    | 0.0    | 0.0    | 0.0    |
| 92.5°  | 0.0    | 0.0    | 0.0    | 0.0    | 0.0    | 0.0    | 0.0    | 0.0    | 0.0    | 0.0    | 0.0    |
| 95°    | 0.0    | 0.0    | 0.0    | 0.0    | 0.0    | 0.0    | 0.0    | 0.0    | 0.0    | 0.0    | 0.0    |
| 97.5°  | 0.0    | 0.0    | 0.0    | 0.0    | 0.0    | 0.0    | 0.0    | 0.0    | 0.0    | 0.0    | 0.0    |
| 100°   | 0.0    | 0.0    | 0.0    | 0.0    | 0.0    | 0.0    | 0.0    | 0.0    | 0.0    | 0.0    | 0.0    |
| 102.5° | 0.0    | 0.0    | 0.0    | 0.0    | 0.0    | 0.0    | 0.0    | 0.0    | 0.0    | 0.0    | 0.0    |
| 105°   | 0.0    | 0.0    | 0.0    | 0.0    | 0.0    | 0.0    | 0.0    | 0.0    | 0.0    | 0.0    | 0.0    |
| 107.5° | 0.0    | 0.0    | 0.0    | 0.0    | 0.0    | 0.0    | 0.0    | 0.0    | 0.0    | 0.0    | 0.0    |
| 110°   | 0.0    | 0.0    | 0.0    | 0.0    | 0.0    | 0.0    | 0.0    | 0.0    | 0.0    | 0.0    | 0.0    |



REPORT NUMBER: P383227  
 CATALOG NUMBER: GAN-SA5C-735-U-SLL

**CANDELA DISTRIBUTION (continued):**

|        | 220° | 225° | 230° | 235° | 240° | 245° | 250° | 255° | 260° | 265° | 270° |
|--------|------|------|------|------|------|------|------|------|------|------|------|
| 112.5° | 0.0  | 0.0  | 0.0  | 0.0  | 0.0  | 0.0  | 0.0  | 0.0  | 0.0  | 0.0  | 0.0  |
| 115°   | 0.0  | 0.0  | 0.0  | 0.0  | 0.0  | 0.0  | 0.0  | 0.0  | 0.0  | 0.0  | 0.0  |
| 117.5° | 0.0  | 0.0  | 0.0  | 0.0  | 0.0  | 0.0  | 0.0  | 0.0  | 0.0  | 0.0  | 0.0  |
| 120°   | 0.0  | 0.0  | 0.0  | 0.0  | 0.0  | 0.0  | 0.0  | 0.0  | 0.0  | 0.0  | 0.0  |
| 122.5° | 0.0  | 0.0  | 0.0  | 0.0  | 0.0  | 0.0  | 0.0  | 0.0  | 0.0  | 0.0  | 0.0  |
| 125°   | 0.0  | 0.0  | 0.0  | 0.0  | 0.0  | 0.0  | 0.0  | 0.0  | 0.0  | 0.0  | 0.0  |
| 127.5° | 0.0  | 0.0  | 0.0  | 0.0  | 0.0  | 0.0  | 0.0  | 0.0  | 0.0  | 0.0  | 0.0  |
| 130°   | 0.0  | 0.0  | 0.0  | 0.0  | 0.0  | 0.0  | 0.0  | 0.0  | 0.0  | 0.0  | 0.0  |
| 132.5° | 0.0  | 0.0  | 0.0  | 0.0  | 0.0  | 0.0  | 0.0  | 0.0  | 0.0  | 0.0  | 0.0  |
| 135°   | 0.0  | 0.0  | 0.0  | 0.0  | 0.0  | 0.0  | 0.0  | 0.0  | 0.0  | 0.0  | 0.0  |
| 137.5° | 0.0  | 0.0  | 0.0  | 0.0  | 0.0  | 0.0  | 0.0  | 0.0  | 0.0  | 0.0  | 0.0  |
| 140°   | 0.0  | 0.0  | 0.0  | 0.0  | 0.0  | 0.0  | 0.0  | 0.0  | 0.0  | 0.0  | 0.0  |
| 142.5° | 0.0  | 0.0  | 0.0  | 0.0  | 0.0  | 0.0  | 0.0  | 0.0  | 0.0  | 0.0  | 0.0  |
| 145°   | 0.0  | 0.0  | 0.0  | 0.0  | 0.0  | 0.0  | 0.0  | 0.0  | 0.0  | 0.0  | 0.0  |
| 147.5° | 0.0  | 0.0  | 0.0  | 0.0  | 0.0  | 0.0  | 0.0  | 0.0  | 0.0  | 0.0  | 0.0  |
| 150°   | 0.0  | 0.0  | 0.0  | 0.0  | 0.0  | 0.0  | 0.0  | 0.0  | 0.0  | 0.0  | 0.0  |
| 152.5° | 0.0  | 0.0  | 0.0  | 0.0  | 0.0  | 0.0  | 0.0  | 0.0  | 0.0  | 0.0  | 0.0  |
| 155°   | 0.0  | 0.0  | 0.0  | 0.0  | 0.0  | 0.0  | 0.0  | 0.0  | 0.0  | 0.0  | 0.0  |
| 157.5° | 0.0  | 0.0  | 0.0  | 0.0  | 0.0  | 0.0  | 0.0  | 0.0  | 0.0  | 0.0  | 0.0  |
| 160°   | 0.0  | 0.0  | 0.0  | 0.0  | 0.0  | 0.0  | 0.0  | 0.0  | 0.0  | 0.0  | 0.0  |
| 162.5° | 0.0  | 0.0  | 0.0  | 0.0  | 0.0  | 0.0  | 0.0  | 0.0  | 0.0  | 0.0  | 0.0  |
| 165°   | 0.0  | 0.0  | 0.0  | 0.0  | 0.0  | 0.0  | 0.0  | 0.0  | 0.0  | 0.0  | 0.0  |
| 167.5° | 0.0  | 0.0  | 0.0  | 0.0  | 0.0  | 0.0  | 0.0  | 0.0  | 0.0  | 0.0  | 0.0  |
| 170°   | 0.0  | 0.0  | 0.0  | 0.0  | 0.0  | 0.0  | 0.0  | 0.0  | 0.0  | 0.0  | 0.0  |
| 172.5° | 0.0  | 0.0  | 0.0  | 0.0  | 0.0  | 0.0  | 0.0  | 0.0  | 0.0  | 0.0  | 0.0  |
| 175°   | 0.0  | 0.0  | 0.0  | 0.0  | 0.0  | 0.0  | 0.0  | 0.0  | 0.0  | 0.0  | 0.0  |
| 177.5° | 0.0  | 0.0  | 0.0  | 0.0  | 0.0  | 0.0  | 0.0  | 0.0  | 0.0  | 0.0  | 0.0  |
| 180°   | 0.0  | 0.0  | 0.0  | 0.0  | 0.0  | 0.0  | 0.0  | 0.0  | 0.0  | 0.0  | 0.0  |





REPORT NUMBER: P383227

CATALOG NUMBER: GAN-SA5C-735-U-SLL

**CANDELA DISTRIBUTION (continued):**

|        | 275°   | 280°   | 285°   | 290°   | 295°   | 300°   | 305°   | 310°   | 315°   | 320°   | 325°   |
|--------|--------|--------|--------|--------|--------|--------|--------|--------|--------|--------|--------|
| 0°     | 8816.8 | 8816.8 | 8816.8 | 8816.8 | 8816.8 | 8816.8 | 8816.8 | 8816.8 | 8816.8 | 8816.8 | 8816.8 |
| 2.5°   | 7632.0 | 7647.1 | 7661.0 | 7774.3 | 7886.6 | 8018.5 | 8150.4 | 8251.0 | 8350.5 | 8453.5 | 8556.5 |
| 5°     | 6103.5 | 6122.0 | 6140.6 | 6278.3 | 6414.7 | 6598.7 | 6782.7 | 6941.2 | 7099.7 | 7286.0 | 7472.3 |
| 7.5°   | 4524.2 | 4564.6 | 4604.0 | 4750.9 | 4896.7 | 5094.5 | 5291.3 | 5498.4 | 5704.3 | 5947.3 | 6190.3 |
| 10°    | 3553.4 | 3629.7 | 3705.0 | 3855.3 | 4005.7 | 4201.3 | 4395.7 | 4612.1 | 4828.4 | 5067.9 | 5306.3 |
| 12.5°  | 2876.4 | 2978.3 | 3079.0 | 3259.5 | 3439.9 | 3673.7 | 3906.3 | 4146.9 | 4386.5 | 4597.0 | 4807.6 |
| 15°    | 2272.5 | 2383.6 | 2493.5 | 2684.3 | 2875.3 | 3132.1 | 3387.9 | 3650.5 | 3912.0 | 4164.3 | 4416.5 |
| 17.5°  | 1772.6 | 1864.0 | 1954.3 | 2116.3 | 2277.1 | 2525.9 | 2774.6 | 3050.0 | 3325.4 | 3633.2 | 3939.8 |
| 20°    | 1430.1 | 1468.3 | 1506.5 | 1623.3 | 1739.1 | 1941.5 | 2142.8 | 2424.1 | 2705.2 | 3073.2 | 3441.1 |
| 22.5°  | 1253.1 | 1272.8 | 1291.3 | 1347.9 | 1403.6 | 1534.3 | 1663.8 | 1912.7 | 2160.3 | 2561.8 | 2962.0 |
| 25°    | 1146.6 | 1161.7 | 1176.7 | 1213.7 | 1250.8 | 1313.3 | 1375.7 | 1550.5 | 1725.2 | 2119.7 | 2513.1 |
| 27.5°  | 1050.6 | 1073.8 | 1095.8 | 1113.1 | 1129.3 | 1172.1 | 1213.7 | 1328.3 | 1442.9 | 1810.8 | 2177.6 |
| 30°    | 981.2  | 989.3  | 997.4  | 1024.0 | 1049.5 | 1093.5 | 1137.4 | 1217.3 | 1297.1 | 1608.3 | 1918.4 |
| 32.5°  | 900.2  | 911.8  | 923.3  | 951.1  | 978.9  | 1019.4 | 1059.9 | 1124.7 | 1188.3 | 1454.4 | 1719.4 |
| 35°    | 827.3  | 838.9  | 850.4  | 878.2  | 904.8  | 948.8  | 991.6  | 1045.9 | 1099.2 | 1330.6 | 1562.0 |
| 37.5°  | 782.2  | 793.8  | 805.3  | 829.6  | 852.7  | 896.7  | 939.6  | 982.3  | 1024.0 | 1238.0 | 1452.1 |
| 40°    | 744.0  | 755.6  | 767.1  | 790.2  | 812.2  | 855.1  | 896.7  | 932.6  | 968.4  | 1168.6 | 1368.8 |
| 42.5°  | 710.4  | 723.2  | 735.9  | 759.0  | 781.0  | 819.2  | 857.4  | 904.8  | 951.1  | 1108.4 | 1264.7 |
| 45°    | 682.6  | 695.4  | 707.0  | 732.4  | 757.9  | 794.9  | 832.0  | 897.9  | 963.9  | 1077.2 | 1190.6 |
| 47.5°  | 657.2  | 671.1  | 683.8  | 711.6  | 739.4  | 785.7  | 830.8  | 886.3  | 940.7  | 1052.9 | 1165.2 |
| 50°    | 632.9  | 649.1  | 665.3  | 698.8  | 731.3  | 808.8  | 885.2  | 893.3  | 900.2  | 1033.3 | 1165.2 |
| 52.5°  | 609.8  | 628.3  | 646.8  | 688.4  | 728.9  | 819.2  | 909.5  | 880.5  | 850.4  | 996.2  | 1142.0 |
| 55°    | 586.6  | 602.8  | 617.9  | 668.8  | 719.7  | 785.7  | 851.6  | 813.4  | 774.1  | 926.8  | 1079.6 |
| 57.5°  | 555.4  | 572.7  | 588.9  | 643.3  | 697.7  | 744.0  | 789.1  | 754.4  | 718.5  | 848.2  | 976.5  |
| 60°    | 523.0  | 542.6  | 562.4  | 631.8  | 700.1  | 692.0  | 682.6  | 675.7  | 667.6  | 760.2  | 852.7  |
| 62.5°  | 494.1  | 514.9  | 535.7  | 626.0  | 716.3  | 660.7  | 605.1  | 610.9  | 615.6  | 683.8  | 752.1  |
| 65°    | 465.1  | 486.0  | 505.6  | 550.7  | 595.9  | 573.9  | 551.9  | 561.2  | 569.3  | 636.3  | 703.5  |
| 67.5°  | 432.7  | 451.2  | 468.6  | 483.7  | 498.7  | 501.0  | 503.3  | 512.5  | 521.9  | 601.7  | 680.3  |
| 70°    | 396.8  | 411.9  | 426.9  | 437.4  | 446.6  | 451.2  | 454.7  | 466.3  | 477.9  | 564.6  | 651.4  |
| 72.5°  | 356.4  | 369.1  | 380.6  | 389.9  | 399.2  | 402.6  | 404.9  | 416.6  | 428.1  | 520.6  | 613.2  |
| 75°    | 312.4  | 322.8  | 332.1  | 340.2  | 348.3  | 352.9  | 357.5  | 365.6  | 373.7  | 474.4  | 573.9  |
| 77.5°  | 263.8  | 274.2  | 283.5  | 290.5  | 296.2  | 300.8  | 304.3  | 314.7  | 325.1  | 409.6  | 492.9  |
| 80°    | 206.0  | 218.7  | 230.3  | 236.1  | 240.7  | 241.8  | 241.8  | 251.1  | 260.4  | 320.5  | 379.5  |
| 82.5°  | 145.8  | 159.7  | 172.4  | 177.0  | 181.7  | 181.7  | 181.7  | 192.1  | 202.5  | 242.9  | 282.4  |
| 85°    | 85.6   | 100.7  | 114.6  | 119.1  | 123.8  | 126.1  | 127.2  | 131.9  | 135.4  | 164.3  | 192.1  |
| 87.5°  | 26.6   | 39.3   | 51.0   | 53.2   | 55.5   | 60.2   | 64.8   | 66.0   | 66.0   | 85.6   | 105.3  |
| 90°    | 0.0    | 0.0    | 0.0    | 0.0    | 0.0    | 0.0    | 0.0    | 0.0    | 0.0    | 0.0    | 0.0    |
| 92.5°  | 0.0    | 0.0    | 0.0    | 0.0    | 0.0    | 0.0    | 0.0    | 0.0    | 0.0    | 0.0    | 0.0    |
| 95°    | 0.0    | 0.0    | 0.0    | 0.0    | 0.0    | 0.0    | 0.0    | 0.0    | 0.0    | 0.0    | 0.0    |
| 97.5°  | 0.0    | 0.0    | 0.0    | 0.0    | 0.0    | 0.0    | 0.0    | 0.0    | 0.0    | 0.0    | 0.0    |
| 100°   | 0.0    | 0.0    | 0.0    | 0.0    | 0.0    | 0.0    | 0.0    | 0.0    | 0.0    | 0.0    | 0.0    |
| 102.5° | 0.0    | 0.0    | 0.0    | 0.0    | 0.0    | 0.0    | 0.0    | 0.0    | 0.0    | 0.0    | 0.0    |
| 105°   | 0.0    | 0.0    | 0.0    | 0.0    | 0.0    | 0.0    | 0.0    | 0.0    | 0.0    | 0.0    | 0.0    |
| 107.5° | 0.0    | 0.0    | 0.0    | 0.0    | 0.0    | 0.0    | 0.0    | 0.0    | 0.0    | 0.0    | 0.0    |
| 110°   | 0.0    | 0.0    | 0.0    | 0.0    | 0.0    | 0.0    | 0.0    | 0.0    | 0.0    | 0.0    | 0.0    |



REPORT NUMBER: P383227  
 CATALOG NUMBER: GAN-SA5C-735-U-SLL

**CANDELA DISTRIBUTION (continued):**

|        | 275° | 280° | 285° | 290° | 295° | 300° | 305° | 310° | 315° | 320° | 325° |
|--------|------|------|------|------|------|------|------|------|------|------|------|
| 112.5° | 0.0  | 0.0  | 0.0  | 0.0  | 0.0  | 0.0  | 0.0  | 0.0  | 0.0  | 0.0  | 0.0  |
| 115°   | 0.0  | 0.0  | 0.0  | 0.0  | 0.0  | 0.0  | 0.0  | 0.0  | 0.0  | 0.0  | 0.0  |
| 117.5° | 0.0  | 0.0  | 0.0  | 0.0  | 0.0  | 0.0  | 0.0  | 0.0  | 0.0  | 0.0  | 0.0  |
| 120°   | 0.0  | 0.0  | 0.0  | 0.0  | 0.0  | 0.0  | 0.0  | 0.0  | 0.0  | 0.0  | 0.0  |
| 122.5° | 0.0  | 0.0  | 0.0  | 0.0  | 0.0  | 0.0  | 0.0  | 0.0  | 0.0  | 0.0  | 0.0  |
| 125°   | 0.0  | 0.0  | 0.0  | 0.0  | 0.0  | 0.0  | 0.0  | 0.0  | 0.0  | 0.0  | 0.0  |
| 127.5° | 0.0  | 0.0  | 0.0  | 0.0  | 0.0  | 0.0  | 0.0  | 0.0  | 0.0  | 0.0  | 0.0  |
| 130°   | 0.0  | 0.0  | 0.0  | 0.0  | 0.0  | 0.0  | 0.0  | 0.0  | 0.0  | 0.0  | 0.0  |
| 132.5° | 0.0  | 0.0  | 0.0  | 0.0  | 0.0  | 0.0  | 0.0  | 0.0  | 0.0  | 0.0  | 0.0  |
| 135°   | 0.0  | 0.0  | 0.0  | 0.0  | 0.0  | 0.0  | 0.0  | 0.0  | 0.0  | 0.0  | 0.0  |
| 137.5° | 0.0  | 0.0  | 0.0  | 0.0  | 0.0  | 0.0  | 0.0  | 0.0  | 0.0  | 0.0  | 0.0  |
| 140°   | 0.0  | 0.0  | 0.0  | 0.0  | 0.0  | 0.0  | 0.0  | 0.0  | 0.0  | 0.0  | 0.0  |
| 142.5° | 0.0  | 0.0  | 0.0  | 0.0  | 0.0  | 0.0  | 0.0  | 0.0  | 0.0  | 0.0  | 0.0  |
| 145°   | 0.0  | 0.0  | 0.0  | 0.0  | 0.0  | 0.0  | 0.0  | 0.0  | 0.0  | 0.0  | 0.0  |
| 147.5° | 0.0  | 0.0  | 0.0  | 0.0  | 0.0  | 0.0  | 0.0  | 0.0  | 0.0  | 0.0  | 0.0  |
| 150°   | 0.0  | 0.0  | 0.0  | 0.0  | 0.0  | 0.0  | 0.0  | 0.0  | 0.0  | 0.0  | 0.0  |
| 152.5° | 0.0  | 0.0  | 0.0  | 0.0  | 0.0  | 0.0  | 0.0  | 0.0  | 0.0  | 0.0  | 0.0  |
| 155°   | 0.0  | 0.0  | 0.0  | 0.0  | 0.0  | 0.0  | 0.0  | 0.0  | 0.0  | 0.0  | 0.0  |
| 157.5° | 0.0  | 0.0  | 0.0  | 0.0  | 0.0  | 0.0  | 0.0  | 0.0  | 0.0  | 0.0  | 0.0  |
| 160°   | 0.0  | 0.0  | 0.0  | 0.0  | 0.0  | 0.0  | 0.0  | 0.0  | 0.0  | 0.0  | 0.0  |
| 162.5° | 0.0  | 0.0  | 0.0  | 0.0  | 0.0  | 0.0  | 0.0  | 0.0  | 0.0  | 0.0  | 0.0  |
| 165°   | 0.0  | 0.0  | 0.0  | 0.0  | 0.0  | 0.0  | 0.0  | 0.0  | 0.0  | 0.0  | 0.0  |
| 167.5° | 0.0  | 0.0  | 0.0  | 0.0  | 0.0  | 0.0  | 0.0  | 0.0  | 0.0  | 0.0  | 0.0  |
| 170°   | 0.0  | 0.0  | 0.0  | 0.0  | 0.0  | 0.0  | 0.0  | 0.0  | 0.0  | 0.0  | 0.0  |
| 172.5° | 0.0  | 0.0  | 0.0  | 0.0  | 0.0  | 0.0  | 0.0  | 0.0  | 0.0  | 0.0  | 0.0  |
| 175°   | 0.0  | 0.0  | 0.0  | 0.0  | 0.0  | 0.0  | 0.0  | 0.0  | 0.0  | 0.0  | 0.0  |
| 177.5° | 0.0  | 0.0  | 0.0  | 0.0  | 0.0  | 0.0  | 0.0  | 0.0  | 0.0  | 0.0  | 0.0  |
| 180°   | 0.0  | 0.0  | 0.0  | 0.0  | 0.0  | 0.0  | 0.0  | 0.0  | 0.0  | 0.0  | 0.0  |



REPORT NUMBER: P383227

CATALOG NUMBER: GAN-SA5C-735-U-SLL

**CANDELA DISTRIBUTION (continued):**

|        | 330°   | 335°   | 340°   | 345°   | 350°    | 355°    | 360°    |
|--------|--------|--------|--------|--------|---------|---------|---------|
| 0°     | 8816.8 | 8816.8 | 8816.8 | 8816.8 | 8816.8  | 8816.8  | 8816.8  |
| 2.5°   | 8674.5 | 8792.5 | 8930.2 | 9066.8 | 9183.6  | 9300.5  | 9397.6  |
| 5°     | 7709.5 | 7946.8 | 8237.1 | 8526.4 | 8784.4  | 9042.4  | 9342.1  |
| 7.5°   | 6496.9 | 6803.6 | 7179.6 | 7555.6 | 7920.1  | 8283.4  | 8744.0  |
| 10°    | 5618.7 | 5930.0 | 6328.0 | 6724.8 | 7134.4  | 7542.9  | 8063.6  |
| 12.5°  | 5061.0 | 5313.3 | 5698.6 | 6083.8 | 6565.2  | 7045.4  | 7546.4  |
| 15°    | 4693.0 | 4968.4 | 5343.4 | 5718.2 | 6244.6  | 6771.1  | 7347.4  |
| 17.5°  | 4300.8 | 4660.6 | 5140.8 | 5621.1 | 6244.6  | 6867.2  | 7546.4  |
| 20°    | 3890.0 | 4337.8 | 4960.3 | 5582.9 | 6422.8  | 7261.7  | 8128.4  |
| 22.5°  | 3480.4 | 3998.9 | 4797.2 | 5594.4 | 6692.4  | 7789.3  | 8959.2  |
| 25°    | 3111.4 | 3709.5 | 4697.7 | 5684.7 | 7084.7  | 8483.6  | 9934.6  |
| 27.5°  | 2831.3 | 3483.9 | 4657.2 | 5829.3 | 7582.2  | 9335.2  | 10995.6 |
| 30°    | 2582.5 | 3246.7 | 4608.6 | 5970.5 | 8061.2  | 10150.9 | 11825.2 |
| 32.5°  | 2367.3 | 3015.3 | 4514.8 | 6013.2 | 8395.7  | 10778.0 | 12527.5 |
| 35°    | 2198.5 | 2834.8 | 4357.5 | 5880.2 | 8605.1  | 11329.9 | 13258.8 |
| 37.5°  | 2052.7 | 2653.1 | 4178.2 | 5703.1 | 8791.4  | 11879.6 | 14081.5 |
| 40°    | 1913.8 | 2458.7 | 4024.3 | 5588.6 | 9048.2  | 12507.9 | 14950.4 |
| 42.5°  | 1781.9 | 2299.1 | 3900.5 | 5501.8 | 9286.6  | 13070.2 | 15710.6 |
| 45°    | 1683.5 | 2176.5 | 3790.6 | 5403.4 | 9440.5  | 13477.4 | 16283.4 |
| 47.5°  | 1635.0 | 2103.5 | 3731.5 | 5358.4 | 9594.4  | 13829.2 | 16758.9 |
| 50°    | 1628.0 | 2090.9 | 3798.7 | 5506.5 | 9927.6  | 14347.6 | 17302.8 |
| 52.5°  | 1626.9 | 2111.6 | 3991.9 | 5872.1 | 10546.6 | 15220.0 | 17891.7 |
| 55°    | 1602.5 | 2124.4 | 4222.1 | 6318.7 | 11377.4 | 16434.9 | 18950.4 |
| 57.5°  | 1528.5 | 2080.4 | 4459.3 | 6837.1 | 12255.6 | 17672.9 | 20143.3 |
| 60°    | 1413.9 | 1973.9 | 4654.9 | 7334.6 | 12845.8 | 18355.7 | 20602.7 |
| 62.5°  | 1270.4 | 1787.6 | 4719.7 | 7650.5 | 12829.6 | 18008.6 | 20139.9 |
| 65°    | 1147.9 | 1592.1 | 4506.7 | 7420.2 | 12180.5 | 16939.4 | 19224.6 |
| 67.5°  | 1039.0 | 1396.6 | 3974.5 | 6551.3 | 11012.9 | 15473.4 | 18060.6 |
| 70°    | 960.3  | 1268.1 | 3288.4 | 5308.6 | 9551.5  | 13793.3 | 16712.6 |
| 72.5°  | 910.6  | 1206.8 | 2680.9 | 4153.9 | 7751.1  | 11347.4 | 14295.5 |
| 75°    | 842.3  | 1110.8 | 2103.5 | 3095.2 | 5932.3  | 8769.4  | 10797.8 |
| 77.5°  | 715.1  | 936.0  | 1585.2 | 2234.3 | 4352.8  | 6470.3  | 7509.3  |
| 80°    | 551.9  | 723.2  | 1089.9 | 1456.8 | 2995.7  | 4534.5  | 5120.0  |
| 82.5°  | 393.4  | 504.5  | 660.7  | 816.9  | 1990.2  | 3162.2  | 3210.9  |
| 85°    | 242.9  | 293.9  | 378.4  | 462.8  | 1316.7  | 2170.7  | 1808.5  |
| 87.5°  | 130.8  | 156.2  | 200.2  | 242.9  | 421.2   | 599.4   | 344.8   |
| 90°    | 0.0    | 0.0    | 0.0    | 0.0    | 0.0     | 0.0     | 0.0     |
| 92.5°  | 0.0    | 0.0    | 0.0    | 0.0    | 0.0     | 0.0     | 0.0     |
| 95°    | 0.0    | 0.0    | 0.0    | 0.0    | 0.0     | 0.0     | 0.0     |
| 97.5°  | 0.0    | 0.0    | 0.0    | 0.0    | 0.0     | 0.0     | 0.0     |
| 100°   | 0.0    | 0.0    | 0.0    | 0.0    | 0.0     | 0.0     | 0.0     |
| 102.5° | 0.0    | 0.0    | 0.0    | 0.0    | 0.0     | 0.0     | 0.0     |
| 105°   | 0.0    | 0.0    | 0.0    | 0.0    | 0.0     | 0.0     | 0.0     |
| 107.5° | 0.0    | 0.0    | 0.0    | 0.0    | 0.0     | 0.0     | 0.0     |
| 110°   | 0.0    | 0.0    | 0.0    | 0.0    | 0.0     | 0.0     | 0.0     |



REPORT NUMBER: P383227  
CATALOG NUMBER: GAN-SA5C-735-U-SLL

**CANDELA DISTRIBUTION (continued):**

|        | 330° | 335° | 340° | 345° | 350° | 355° | 360° |
|--------|------|------|------|------|------|------|------|
| 112.5° | 0.0  | 0.0  | 0.0  | 0.0  | 0.0  | 0.0  | 0.0  |
| 115°   | 0.0  | 0.0  | 0.0  | 0.0  | 0.0  | 0.0  | 0.0  |
| 117.5° | 0.0  | 0.0  | 0.0  | 0.0  | 0.0  | 0.0  | 0.0  |
| 120°   | 0.0  | 0.0  | 0.0  | 0.0  | 0.0  | 0.0  | 0.0  |
| 122.5° | 0.0  | 0.0  | 0.0  | 0.0  | 0.0  | 0.0  | 0.0  |
| 125°   | 0.0  | 0.0  | 0.0  | 0.0  | 0.0  | 0.0  | 0.0  |
| 127.5° | 0.0  | 0.0  | 0.0  | 0.0  | 0.0  | 0.0  | 0.0  |
| 130°   | 0.0  | 0.0  | 0.0  | 0.0  | 0.0  | 0.0  | 0.0  |
| 132.5° | 0.0  | 0.0  | 0.0  | 0.0  | 0.0  | 0.0  | 0.0  |
| 135°   | 0.0  | 0.0  | 0.0  | 0.0  | 0.0  | 0.0  | 0.0  |
| 137.5° | 0.0  | 0.0  | 0.0  | 0.0  | 0.0  | 0.0  | 0.0  |
| 140°   | 0.0  | 0.0  | 0.0  | 0.0  | 0.0  | 0.0  | 0.0  |
| 142.5° | 0.0  | 0.0  | 0.0  | 0.0  | 0.0  | 0.0  | 0.0  |
| 145°   | 0.0  | 0.0  | 0.0  | 0.0  | 0.0  | 0.0  | 0.0  |
| 147.5° | 0.0  | 0.0  | 0.0  | 0.0  | 0.0  | 0.0  | 0.0  |
| 150°   | 0.0  | 0.0  | 0.0  | 0.0  | 0.0  | 0.0  | 0.0  |
| 152.5° | 0.0  | 0.0  | 0.0  | 0.0  | 0.0  | 0.0  | 0.0  |
| 155°   | 0.0  | 0.0  | 0.0  | 0.0  | 0.0  | 0.0  | 0.0  |
| 157.5° | 0.0  | 0.0  | 0.0  | 0.0  | 0.0  | 0.0  | 0.0  |
| 160°   | 0.0  | 0.0  | 0.0  | 0.0  | 0.0  | 0.0  | 0.0  |
| 162.5° | 0.0  | 0.0  | 0.0  | 0.0  | 0.0  | 0.0  | 0.0  |
| 165°   | 0.0  | 0.0  | 0.0  | 0.0  | 0.0  | 0.0  | 0.0  |
| 167.5° | 0.0  | 0.0  | 0.0  | 0.0  | 0.0  | 0.0  | 0.0  |
| 170°   | 0.0  | 0.0  | 0.0  | 0.0  | 0.0  | 0.0  | 0.0  |
| 172.5° | 0.0  | 0.0  | 0.0  | 0.0  | 0.0  | 0.0  | 0.0  |
| 175°   | 0.0  | 0.0  | 0.0  | 0.0  | 0.0  | 0.0  | 0.0  |
| 177.5° | 0.0  | 0.0  | 0.0  | 0.0  | 0.0  | 0.0  | 0.0  |
| 180°   | 0.0  | 0.0  | 0.0  | 0.0  | 0.0  | 0.0  | 0.0  |

(END OF REPORT)