

Scaled data based on original data using  
LM-79-08 Approved Method: Electrical and Photometric Measurements of Solid-  
State Lighting Products

Test Report Prepared for  
Cooper Lighting Solutions  
(formerly Eaton)

Brand: STREETWORKS

Report Number: P320304

Luminaire Tested: **GAN-SA0D-730-U-SLL**

Issue Date: 3/3/2020

**Test Information**

Test Method: LM-79-08  
Report Number: P320304  
TEST IS SCALED FROM IESNA LM-79-08 TEST DATA (G2-1903-205-26)  
Test Lab: INNOVATION CENTER  
Issue Date: 3/3/2020  
Manufacturer: COOPER LIGHTING SOLUTIONS (FORMERLY EATON)  
Product Line: STREETWORKS  
Catalog Number: GAN-SA0D-730-U-SLL  
Description: GALLEON AREA AND ROADWAY LUMINAIRE  
(10) 70 CRI, 3000K, 1200mA LIGHTSQUARES WITH 16 LEDS EACH AND SPILL LIGHT  
ELIMINATOR LEFT OPTICS  
Light Source: -  
Ballast/Driver: ELECTRONIC DRIVER

**Summary**

Lumens per Lamp: N/A  
Luminaire Lumens: 61464 lumens  
Efficiency: N/A  
Efficacy: 96.0 lumens/watt  
Luminous Opening: Rectangular (W 2.5' x L: 1' x H: 0')  
IES Classification: Type III - Medium  
BUG Rating: B4 - U0 - G5


Input Watts (W): 640  
Input Voltage (V): NR  
Input Current (Ain): NR  
Voltage Rise (V): NR  
Power Factor: NR  
Total Harmonic Distortion (THDi): NR  
Frequency (hertz): 60  
Stabilization Time: NR  
Operation Time: NR  
Ambient Temperature (°C): NR  
Test Distance: 24 FT



REPORT NUMBER: P320304  
 CATALOG NUMBER: GAN-SA0D-730-U-SLL

### Iso-Footcandle Lines of Horizontal Illumination


✕ Max cd  
 - - - 1/2 Max cd



Based on 25 foot mounting height. Maximum calculated value = 37.7 fc  
 Type III - Medium - N/A

REPORT NUMBER: P320304  
CATALOG NUMBER: GAN-SA0D-730-U-SLL

### Luminous Intensity Polar Plot



— Vertical Plane Through 75-Deg Lateral      - - - Horizontal Cone Through 67.5-Deg Vertical

REPORT NUMBER: P320304  
 CATALOG NUMBER: GAN-SA0D-730-U-SLL


**FLUX DISTRIBUTION:**

|                    |           | Downward | Upward | Total   |
|--------------------|-----------|----------|--------|---------|
| <b>House Side</b>  | Lumens    | 10825.3  | 0.0    | 10825.3 |
|                    | % Fixture | 17.6     | 0.0    | 17.6    |
| <b>Street Side</b> | Lumens    | 50638.7  | 0.0    | 50638.7 |
|                    | % Fixture | 82.4     | 0.0    | 82.4    |
| <b>Total</b>       | Lumens    | 61464.0  | 0.0    | 61464.0 |
|                    | % Fixture | 100.0    | 0.0    | 100.0   |

**ZONAL LUMENS:**

| Zone      | Lumens  | % Fixture |
|-----------|---------|-----------|
| 0°-10°    | 1445.2  | 2.4       |
| 10°-20°   | 3002.2  | 4.9       |
| 20°-30°   | 4269.8  | 6.9       |
| 30°-40°   | 6152.7  | 10.0      |
| 40°-50°   | 8671.0  | 14.1      |
| 50°-60°   | 12054.1 | 19.6      |
| 60°-70°   | 14577.0 | 23.7      |
| 70°-80°   | 8960.3  | 14.6      |
| 80°-90°   | 2331.6  | 3.8       |
| 90°-100°  | 0.0     | 0.0       |
| 100°-110° | 0.0     | 0.0       |
| 110°-120° | 0.0     | 0.0       |
| 120°-130° | 0.0     | 0.0       |
| 130°-140° | 0.0     | 0.0       |
| 140°-150° | 0.0     | 0.0       |
| 150°-160° | 0.0     | 0.0       |
| 160°-170° | 0.0     | 0.0       |
| 170°-180° | 0.0     | 0.0       |
| 0°-90°    | 61464.0 | 100.0     |
| 0°-180°   | 61464.0 | 100.0     |

**Coefficient of Utilization**




REPORT NUMBER: P320304  
 CATALOG NUMBER: GAN-SA0D-730-U-SLL

**LUMINAIRE CLASSIFICATION SYSTEM LUMEN TABLE AND BUG RATING:**

| Zone           | Lumens  | % Fixture | Zone Rating/Lumen Limit |      |         |
|----------------|---------|-----------|-------------------------|------|---------|
|                |         |           | B                       | U    | G       |
| FL (0°-30°)    | 6102.7  | 9.9       |                         |      |         |
| FM (30°-60°)   | 21964.0 | 35.7      |                         |      |         |
| FH (60°-80°)   | 20502.3 | 33.4      |                         |      | G5      |
| FVH (80°-90°)  | 2069.6  | 3.4       |                         |      | G5      |
| BL (0°-30°)    | 2614.4  | 4.3       | B4/5000                 |      |         |
| BM (30°-60°)   | 4913.9  | 8.0       | B3/5000                 |      |         |
| BH (60°-80°)   | 3035.0  | 4.9       | B4/5000                 |      | G4/5000 |
| BVH (80°-90°)  | 262.0   | 0.4       |                         |      | G3/500  |
| UL (90°-100°)  | 0.0     | 0.0       |                         | U0/0 |         |
| UH (100°-180°) | 0.0     | 0.0       |                         | U0/0 |         |

**BUG Rating: B4-U0-G5**  
 Type III Medium





REPORT NUMBER: P320304

CATALOG NUMBER: GAN-SAOD-730-U-SLL

**CANDELA DISTRIBUTION (FULL):**

|        | 0°      | 5°      | 10°     | 15°     | 20°     | 25°     | 30°     | 35°     | 40°     | 45°     | 50°     |
|--------|---------|---------|---------|---------|---------|---------|---------|---------|---------|---------|---------|
| 0°     | 18725.3 | 18725.3 | 18725.3 | 18725.3 | 18725.3 | 18725.3 | 18725.3 | 18725.3 | 18725.3 | 18725.3 | 18725.3 |
| 2.5°   | 19958.9 | 20221.8 | 20403.7 | 20583.1 | 20723.2 | 20860.8 | 21062.3 | 21263.8 | 21303.1 | 21340.0 | 21261.3 |
| 5°     | 19840.9 | 20482.3 | 21027.9 | 21571.0 | 22074.7 | 22578.5 | 22880.7 | 23183.0 | 23244.4 | 23305.9 | 23116.6 |
| 7.5°   | 18570.5 | 19516.6 | 20462.7 | 21408.8 | 22276.2 | 23143.7 | 23672.0 | 24197.9 | 24318.3 | 24436.3 | 24126.6 |
| 10°    | 17125.5 | 18226.4 | 19388.8 | 20551.1 | 21693.8 | 22836.5 | 23600.8 | 24365.0 | 24517.4 | 24669.7 | 24283.9 |
| 12.5°  | 16027.1 | 17228.7 | 18469.7 | 19710.7 | 20917.3 | 22121.4 | 22912.7 | 23704.0 | 23893.2 | 24082.4 | 23802.3 |
| 15°    | 15604.4 | 16921.6 | 18088.8 | 19256.1 | 20307.9 | 21357.2 | 22005.9 | 22652.2 | 22730.8 | 22807.0 | 22762.8 |
| 17.5°  | 16027.1 | 17479.4 | 18536.1 | 19590.3 | 20162.9 | 20733.0 | 20993.5 | 21251.5 | 21337.5 | 21421.1 | 21534.1 |
| 20°    | 17263.1 | 18831.0 | 19575.6 | 20317.7 | 20293.1 | 20266.1 | 20140.8 | 20013.0 | 19990.9 | 19968.7 | 20288.2 |
| 22.5°  | 19027.6 | 20848.5 | 21145.8 | 21440.7 | 20750.2 | 20059.7 | 19639.4 | 19216.8 | 19133.2 | 19047.2 | 19386.3 |
| 25°    | 21099.1 | 23038.0 | 22983.9 | 22927.4 | 21612.7 | 20295.6 | 19494.5 | 18693.3 | 18600.0 | 18506.6 | 18796.6 |
| 27.5°  | 23352.6 | 25205.4 | 24851.6 | 24497.7 | 22711.2 | 20924.7 | 19762.3 | 18600.0 | 18506.6 | 18413.2 | 18668.8 |
| 30°    | 25114.5 | 26795.4 | 26227.7 | 25660.0 | 23637.6 | 21615.2 | 20234.1 | 18853.1 | 18700.7 | 18545.9 | 18860.5 |
| 32.5°  | 26606.1 | 28036.3 | 27274.5 | 26512.8 | 24389.6 | 22266.4 | 20772.3 | 19278.2 | 19039.8 | 18801.5 | 19221.7 |
| 35°    | 28159.2 | 29274.9 | 28203.4 | 27129.6 | 25060.4 | 22988.9 | 21408.8 | 19826.2 | 19533.8 | 19241.3 | 19818.8 |
| 37.5°  | 29906.4 | 30832.8 | 29294.5 | 27753.7 | 25814.9 | 23876.0 | 22362.2 | 20846.0 | 20546.2 | 20246.4 | 20983.6 |
| 40°    | 31751.9 | 32523.5 | 30471.6 | 28419.7 | 26640.5 | 24861.4 | 23681.8 | 22499.8 | 22214.8 | 21927.3 | 22821.8 |
| 42.5°  | 33366.4 | 33929.2 | 31567.6 | 29206.1 | 27635.8 | 26063.1 | 25232.5 | 24399.4 | 24396.9 | 24392.0 | 25298.8 |
| 45°    | 34582.8 | 35071.8 | 32481.8 | 29889.2 | 28606.5 | 27321.2 | 26888.7 | 26456.2 | 26802.7 | 27149.2 | 27970.0 |
| 47.5°  | 35592.8 | 35924.6 | 33248.5 | 30569.9 | 29717.2 | 28864.5 | 28928.4 | 28992.3 | 29697.5 | 30402.8 | 30931.1 |
| 50°    | 36747.8 | 36479.9 | 33943.9 | 31405.4 | 31142.5 | 30879.5 | 31454.6 | 32027.1 | 32838.1 | 33646.6 | 34005.3 |
| 52.5°  | 37998.6 | 37288.4 | 34887.5 | 32484.2 | 32779.1 | 33074.0 | 34243.7 | 35413.4 | 36231.7 | 37050.0 | 37185.2 |
| 55°    | 40247.1 | 39158.5 | 36622.5 | 34084.0 | 34651.6 | 35216.8 | 36934.5 | 38649.8 | 39288.7 | 39927.6 | 39976.8 |
| 57.5°  | 42780.7 | 41814.9 | 39052.8 | 36290.7 | 36900.1 | 37509.6 | 39492.7 | 41473.3 | 42163.9 | 42851.9 | 42756.1 |
| 60°    | 43756.2 | 43802.9 | 41360.3 | 38915.2 | 39529.5 | 40143.9 | 42075.4 | 44006.9 | 44800.6 | 45591.9 | 45380.6 |
| 62.5°  | 42773.3 | 43925.8 | 42620.9 | 41313.6 | 41871.4 | 42426.8 | 44319.0 | 46211.2 | 47024.6 | 47838.0 | 47469.4 |
| 65°    | 40829.5 | 41972.2 | 42557.0 | 43141.9 | 43326.2 | 43510.5 | 45277.4 | 47041.8 | 47666.0 | 48287.7 | 48100.9 |
| 67.5°  | 38357.4 | 39281.3 | 41438.9 | 43594.1 | 43223.0 | 42851.9 | 43680.1 | 44508.2 | 45149.6 | 45791.0 | 45685.3 |
| 70°    | 35494.5 | 36595.4 | 39473.0 | 42350.6 | 40527.2 | 38701.4 | 38359.8 | 38018.2 | 38711.2 | 39401.8 | 38974.2 |
| 72.5°  | 30361.0 | 32022.2 | 35091.5 | 38158.3 | 34799.1 | 31439.8 | 30272.6 | 29105.3 | 29982.6 | 30859.9 | 30179.2 |
| 75°    | 22932.3 | 25136.6 | 28527.8 | 31916.6 | 27908.6 | 23900.6 | 22342.6 | 20784.6 | 21539.0 | 22293.4 | 21826.5 |
| 77.5°  | 15948.4 | 18713.0 | 22052.6 | 25392.2 | 21317.8 | 17241.0 | 16083.6 | 14923.7 | 15149.8 | 15373.4 | 15294.8 |
| 80°    | 10873.9 | 12692.4 | 15022.0 | 17349.2 | 14636.2 | 11923.2 | 12014.2 | 12102.6 | 11997.0 | 11888.8 | 12046.1 |
| 82.5°  | 6819.3  | 8099.6  | 9898.4  | 11694.7 | 10254.7 | 8814.7  | 9640.3  | 10466.0 | 10060.5 | 9652.6  | 9805.0  |
| 85°    | 3840.9  | 4622.3  | 6381.8  | 8138.9  | 7586.0  | 7030.6  | 7514.7  | 7996.3  | 7367.2  | 6738.2  | 7015.8  |
| 87.5°  | 732.3   | 1218.9  | 3531.3  | 5841.2  | 5303.0  | 4764.9  | 4140.7  | 3516.5  | 2683.5  | 1850.4  | 2703.1  |
| 90°    | 0.0     | 0.0     | 0.0     | 0.0     | 0.0     | 0.0     | 0.0     | 0.0     | 0.0     | 0.0     | 0.0     |
| 92.5°  | 0.0     | 0.0     | 0.0     | 0.0     | 0.0     | 0.0     | 0.0     | 0.0     | 0.0     | 0.0     | 0.0     |
| 95°    | 0.0     | 0.0     | 0.0     | 0.0     | 0.0     | 0.0     | 0.0     | 0.0     | 0.0     | 0.0     | 0.0     |
| 97.5°  | 0.0     | 0.0     | 0.0     | 0.0     | 0.0     | 0.0     | 0.0     | 0.0     | 0.0     | 0.0     | 0.0     |
| 100°   | 0.0     | 0.0     | 0.0     | 0.0     | 0.0     | 0.0     | 0.0     | 0.0     | 0.0     | 0.0     | 0.0     |
| 102.5° | 0.0     | 0.0     | 0.0     | 0.0     | 0.0     | 0.0     | 0.0     | 0.0     | 0.0     | 0.0     | 0.0     |
| 105°   | 0.0     | 0.0     | 0.0     | 0.0     | 0.0     | 0.0     | 0.0     | 0.0     | 0.0     | 0.0     | 0.0     |
| 107.5° | 0.0     | 0.0     | 0.0     | 0.0     | 0.0     | 0.0     | 0.0     | 0.0     | 0.0     | 0.0     | 0.0     |
| 110°   | 0.0     | 0.0     | 0.0     | 0.0     | 0.0     | 0.0     | 0.0     | 0.0     | 0.0     | 0.0     | 0.0     |



REPORT NUMBER: P320304  
 CATALOG NUMBER: GAN-SA0D-730-U-SLL

**CANDELA DISTRIBUTION (continued):**

|        | 0°  | 5°  | 10° | 15° | 20° | 25° | 30° | 35° | 40° | 45° | 50° |
|--------|-----|-----|-----|-----|-----|-----|-----|-----|-----|-----|-----|
| 112.5° | 0.0 | 0.0 | 0.0 | 0.0 | 0.0 | 0.0 | 0.0 | 0.0 | 0.0 | 0.0 | 0.0 |
| 115°   | 0.0 | 0.0 | 0.0 | 0.0 | 0.0 | 0.0 | 0.0 | 0.0 | 0.0 | 0.0 | 0.0 |
| 117.5° | 0.0 | 0.0 | 0.0 | 0.0 | 0.0 | 0.0 | 0.0 | 0.0 | 0.0 | 0.0 | 0.0 |
| 120°   | 0.0 | 0.0 | 0.0 | 0.0 | 0.0 | 0.0 | 0.0 | 0.0 | 0.0 | 0.0 | 0.0 |
| 122.5° | 0.0 | 0.0 | 0.0 | 0.0 | 0.0 | 0.0 | 0.0 | 0.0 | 0.0 | 0.0 | 0.0 |
| 125°   | 0.0 | 0.0 | 0.0 | 0.0 | 0.0 | 0.0 | 0.0 | 0.0 | 0.0 | 0.0 | 0.0 |
| 127.5° | 0.0 | 0.0 | 0.0 | 0.0 | 0.0 | 0.0 | 0.0 | 0.0 | 0.0 | 0.0 | 0.0 |
| 130°   | 0.0 | 0.0 | 0.0 | 0.0 | 0.0 | 0.0 | 0.0 | 0.0 | 0.0 | 0.0 | 0.0 |
| 132.5° | 0.0 | 0.0 | 0.0 | 0.0 | 0.0 | 0.0 | 0.0 | 0.0 | 0.0 | 0.0 | 0.0 |
| 135°   | 0.0 | 0.0 | 0.0 | 0.0 | 0.0 | 0.0 | 0.0 | 0.0 | 0.0 | 0.0 | 0.0 |
| 137.5° | 0.0 | 0.0 | 0.0 | 0.0 | 0.0 | 0.0 | 0.0 | 0.0 | 0.0 | 0.0 | 0.0 |
| 140°   | 0.0 | 0.0 | 0.0 | 0.0 | 0.0 | 0.0 | 0.0 | 0.0 | 0.0 | 0.0 | 0.0 |
| 142.5° | 0.0 | 0.0 | 0.0 | 0.0 | 0.0 | 0.0 | 0.0 | 0.0 | 0.0 | 0.0 | 0.0 |
| 145°   | 0.0 | 0.0 | 0.0 | 0.0 | 0.0 | 0.0 | 0.0 | 0.0 | 0.0 | 0.0 | 0.0 |
| 147.5° | 0.0 | 0.0 | 0.0 | 0.0 | 0.0 | 0.0 | 0.0 | 0.0 | 0.0 | 0.0 | 0.0 |
| 150°   | 0.0 | 0.0 | 0.0 | 0.0 | 0.0 | 0.0 | 0.0 | 0.0 | 0.0 | 0.0 | 0.0 |
| 152.5° | 0.0 | 0.0 | 0.0 | 0.0 | 0.0 | 0.0 | 0.0 | 0.0 | 0.0 | 0.0 | 0.0 |
| 155°   | 0.0 | 0.0 | 0.0 | 0.0 | 0.0 | 0.0 | 0.0 | 0.0 | 0.0 | 0.0 | 0.0 |
| 157.5° | 0.0 | 0.0 | 0.0 | 0.0 | 0.0 | 0.0 | 0.0 | 0.0 | 0.0 | 0.0 | 0.0 |
| 160°   | 0.0 | 0.0 | 0.0 | 0.0 | 0.0 | 0.0 | 0.0 | 0.0 | 0.0 | 0.0 | 0.0 |
| 162.5° | 0.0 | 0.0 | 0.0 | 0.0 | 0.0 | 0.0 | 0.0 | 0.0 | 0.0 | 0.0 | 0.0 |
| 165°   | 0.0 | 0.0 | 0.0 | 0.0 | 0.0 | 0.0 | 0.0 | 0.0 | 0.0 | 0.0 | 0.0 |
| 167.5° | 0.0 | 0.0 | 0.0 | 0.0 | 0.0 | 0.0 | 0.0 | 0.0 | 0.0 | 0.0 | 0.0 |
| 170°   | 0.0 | 0.0 | 0.0 | 0.0 | 0.0 | 0.0 | 0.0 | 0.0 | 0.0 | 0.0 | 0.0 |
| 172.5° | 0.0 | 0.0 | 0.0 | 0.0 | 0.0 | 0.0 | 0.0 | 0.0 | 0.0 | 0.0 | 0.0 |
| 175°   | 0.0 | 0.0 | 0.0 | 0.0 | 0.0 | 0.0 | 0.0 | 0.0 | 0.0 | 0.0 | 0.0 |
| 177.5° | 0.0 | 0.0 | 0.0 | 0.0 | 0.0 | 0.0 | 0.0 | 0.0 | 0.0 | 0.0 | 0.0 |
| 180°   | 0.0 | 0.0 | 0.0 | 0.0 | 0.0 | 0.0 | 0.0 | 0.0 | 0.0 | 0.0 | 0.0 |





REPORT NUMBER: P320304

CATALOG NUMBER: GAN-SAOD-730-U-SLL

**CANDELA DISTRIBUTION (continued):**

|        | 55°     | 60°     | 65°     | 70°     | 75°     | 80°     | 85°     | 90°     | 95°     | 100°    | 105°    |
|--------|---------|---------|---------|---------|---------|---------|---------|---------|---------|---------|---------|
| 0°     | 18725.3 | 18725.3 | 18725.3 | 18725.3 | 18725.3 | 18725.3 | 18725.3 | 18725.3 | 18725.3 | 18725.3 | 18725.3 |
| 2.5°   | 21182.7 | 21140.9 | 21099.1 | 20949.2 | 20796.9 | 20570.8 | 20384.0 | 20059.7 | 19882.7 | 19614.9 | 19347.0 |
| 5°     | 22925.0 | 22659.6 | 22394.2 | 21937.1 | 21477.6 | 20966.4 | 20379.1 | 19727.9 | 19236.4 | 18597.5 | 17958.6 |
| 7.5°   | 23817.0 | 23197.7 | 22576.0 | 21698.7 | 20819.0 | 20027.7 | 19098.8 | 18233.8 | 17496.6 | 16666.0 | 15835.4 |
| 10°    | 23898.1 | 22969.2 | 22037.9 | 20897.6 | 19754.9 | 18794.1 | 17725.1 | 16764.3 | 15879.6 | 14926.2 | 13970.3 |
| 12.5°  | 23519.7 | 22531.8 | 21541.5 | 20285.7 | 19027.6 | 17936.5 | 16786.4 | 15710.1 | 14729.6 | 13680.3 | 12628.5 |
| 15°    | 22718.6 | 21929.7 | 21138.5 | 19961.4 | 18784.3 | 17683.4 | 16567.7 | 15292.3 | 14184.0 | 13110.2 | 12033.8 |
| 17.5°  | 21644.7 | 21271.1 | 20895.2 | 20044.9 | 19192.2 | 18238.7 | 17157.5 | 15660.9 | 14363.4 | 13196.2 | 12028.9 |
| 20°    | 20605.2 | 20742.8 | 20878.0 | 20538.8 | 20199.7 | 19435.5 | 18491.8 | 16811.0 | 15154.7 | 13628.7 | 12100.2 |
| 22.5°  | 19723.0 | 20384.0 | 21042.6 | 21305.6 | 21566.0 | 21106.5 | 20369.3 | 18425.5 | 16233.5 | 14240.6 | 12247.6 |
| 25°    | 19084.1 | 20180.1 | 21276.1 | 22150.9 | 23023.3 | 22819.3 | 22251.6 | 20386.5 | 17663.7 | 15122.8 | 12579.4 |
| 27.5°  | 18924.3 | 20268.5 | 21612.7 | 22969.2 | 24323.2 | 24512.4 | 24355.2 | 22453.2 | 19369.1 | 16218.8 | 13065.9 |
| 30°    | 19175.0 | 20536.4 | 21895.3 | 23546.7 | 25195.6 | 25950.0 | 26161.4 | 24175.8 | 21317.8 | 17496.6 | 13672.9 |
| 32.5°  | 19641.9 | 20976.3 | 22310.6 | 24109.4 | 25905.8 | 27046.0 | 27719.3 | 25751.0 | 22676.8 | 18459.9 | 14240.6 |
| 35°    | 20396.3 | 21644.7 | 22893.0 | 24765.6 | 26638.1 | 28112.5 | 29341.2 | 27377.8 | 23883.4 | 19133.2 | 14380.6 |
| 37.5°  | 21718.4 | 22792.3 | 23866.2 | 25596.2 | 27323.7 | 29235.5 | 31081.0 | 29169.2 | 25188.2 | 19782.0 | 14373.3 |
| 40°    | 23716.3 | 24475.6 | 25232.5 | 26694.6 | 28154.3 | 30560.1 | 33051.9 | 31167.1 | 26630.7 | 20484.8 | 14338.9 |
| 42.5°  | 26205.6 | 26596.3 | 26984.6 | 28142.0 | 29299.4 | 31943.6 | 34840.8 | 33120.7 | 28006.8 | 21138.5 | 14270.1 |
| 45°    | 28788.3 | 28891.5 | 28994.7 | 29724.6 | 30452.0 | 33039.6 | 36059.7 | 34587.7 | 29208.5 | 21706.1 | 14201.2 |
| 47.5°  | 31457.0 | 31103.2 | 30749.3 | 31039.3 | 31329.2 | 33880.0 | 36929.6 | 35700.9 | 30415.1 | 22335.2 | 14252.8 |
| 50°    | 34364.1 | 33378.7 | 32393.3 | 32240.9 | 32088.6 | 34720.4 | 37954.4 | 37116.4 | 31864.9 | 23251.8 | 14638.7 |
| 52.5°  | 37317.9 | 35693.6 | 34069.2 | 33467.2 | 32862.6 | 35723.0 | 39313.3 | 38878.3 | 33934.1 | 24672.2 | 15407.8 |
| 55°    | 40025.9 | 37959.3 | 35892.6 | 35081.7 | 34270.7 | 37256.5 | 40972.0 | 41466.0 | 36585.6 | 26488.2 | 16388.3 |
| 57.5°  | 42657.8 | 40315.9 | 37974.0 | 37222.1 | 36470.1 | 39509.9 | 43073.1 | 43788.2 | 39264.1 | 28230.5 | 17194.3 |
| 60°    | 45169.2 | 42851.9 | 40532.2 | 39930.1 | 39325.6 | 42311.3 | 45343.7 | 44822.8 | 40645.2 | 29046.3 | 17445.0 |
| 62.5°  | 47100.8 | 45257.7 | 43414.7 | 43097.7 | 42778.2 | 45144.7 | 47088.5 | 44419.7 | 39767.9 | 28242.8 | 16717.6 |
| 65°    | 47914.1 | 46864.8 | 45813.1 | 46110.4 | 46405.3 | 47287.5 | 47523.4 | 43240.2 | 37010.7 | 25991.8 | 14972.9 |
| 67.5°  | 45577.2 | 45791.0 | 46004.8 | 47253.1 | 48499.0 | 47892.0 | 46230.8 | 40915.5 | 33086.3 | 22802.1 | 12517.9 |
| 70°    | 38544.1 | 39826.9 | 41107.2 | 44061.0 | 47012.3 | 45665.6 | 42768.4 | 36742.9 | 28363.2 | 19128.3 | 9891.0  |
| 72.5°  | 29496.0 | 30938.5 | 32378.5 | 36762.5 | 41144.0 | 39903.1 | 36354.6 | 30179.2 | 22740.7 | 15275.1 | 7807.1  |
| 75°    | 21357.2 | 22986.4 | 24613.2 | 29449.3 | 34285.5 | 32562.8 | 27193.5 | 21607.8 | 17273.0 | 11660.3 | 6045.2  |
| 77.5°  | 15213.7 | 16304.8 | 17395.8 | 22173.0 | 26947.7 | 24141.4 | 18101.1 | 14540.4 | 11955.2 | 8104.5  | 4251.3  |
| 80°    | 12203.4 | 11869.2 | 11535.0 | 14196.3 | 16857.7 | 16390.8 | 11972.4 | 9338.1  | 8274.0  | 5430.8  | 2587.6  |
| 82.5°  | 9954.9  | 9139.0  | 8323.2  | 9576.4  | 10829.7 | 10760.9 | 8308.4  | 6851.2  | 6158.2  | 3774.5  | 1390.9  |
| 85°    | 7291.1  | 6964.2  | 6637.4  | 7745.7  | 8854.0  | 7907.9  | 5627.4  | 4354.5  | 4801.7  | 2779.3  | 756.9   |
| 87.5°  | 3555.8  | 4062.1  | 4565.8  | 5873.2  | 7178.0  | 5389.1  | 1707.9  | 845.3   | 1169.7  | 769.2   | 366.2   |
| 90°    | 0.0     | 0.0     | 0.0     | 0.0     | 0.0     | 0.0     | 0.0     | 0.0     | 0.0     | 0.0     | 0.0     |
| 92.5°  | 0.0     | 0.0     | 0.0     | 0.0     | 0.0     | 0.0     | 0.0     | 0.0     | 0.0     | 0.0     | 0.0     |
| 95°    | 0.0     | 0.0     | 0.0     | 0.0     | 0.0     | 0.0     | 0.0     | 0.0     | 0.0     | 0.0     | 0.0     |
| 97.5°  | 0.0     | 0.0     | 0.0     | 0.0     | 0.0     | 0.0     | 0.0     | 0.0     | 0.0     | 0.0     | 0.0     |
| 100°   | 0.0     | 0.0     | 0.0     | 0.0     | 0.0     | 0.0     | 0.0     | 0.0     | 0.0     | 0.0     | 0.0     |
| 102.5° | 0.0     | 0.0     | 0.0     | 0.0     | 0.0     | 0.0     | 0.0     | 0.0     | 0.0     | 0.0     | 0.0     |
| 105°   | 0.0     | 0.0     | 0.0     | 0.0     | 0.0     | 0.0     | 0.0     | 0.0     | 0.0     | 0.0     | 0.0     |
| 107.5° | 0.0     | 0.0     | 0.0     | 0.0     | 0.0     | 0.0     | 0.0     | 0.0     | 0.0     | 0.0     | 0.0     |
| 110°   | 0.0     | 0.0     | 0.0     | 0.0     | 0.0     | 0.0     | 0.0     | 0.0     | 0.0     | 0.0     | 0.0     |



REPORT NUMBER: P320304  
 CATALOG NUMBER: GAN-SA0D-730-U-SLL

**CANDELA DISTRIBUTION (continued):**

|        | 55° | 60° | 65° | 70° | 75° | 80° | 85° | 90° | 95° | 100° | 105° |
|--------|-----|-----|-----|-----|-----|-----|-----|-----|-----|------|------|
| 112.5° | 0.0 | 0.0 | 0.0 | 0.0 | 0.0 | 0.0 | 0.0 | 0.0 | 0.0 | 0.0  | 0.0  |
| 115°   | 0.0 | 0.0 | 0.0 | 0.0 | 0.0 | 0.0 | 0.0 | 0.0 | 0.0 | 0.0  | 0.0  |
| 117.5° | 0.0 | 0.0 | 0.0 | 0.0 | 0.0 | 0.0 | 0.0 | 0.0 | 0.0 | 0.0  | 0.0  |
| 120°   | 0.0 | 0.0 | 0.0 | 0.0 | 0.0 | 0.0 | 0.0 | 0.0 | 0.0 | 0.0  | 0.0  |
| 122.5° | 0.0 | 0.0 | 0.0 | 0.0 | 0.0 | 0.0 | 0.0 | 0.0 | 0.0 | 0.0  | 0.0  |
| 125°   | 0.0 | 0.0 | 0.0 | 0.0 | 0.0 | 0.0 | 0.0 | 0.0 | 0.0 | 0.0  | 0.0  |
| 127.5° | 0.0 | 0.0 | 0.0 | 0.0 | 0.0 | 0.0 | 0.0 | 0.0 | 0.0 | 0.0  | 0.0  |
| 130°   | 0.0 | 0.0 | 0.0 | 0.0 | 0.0 | 0.0 | 0.0 | 0.0 | 0.0 | 0.0  | 0.0  |
| 132.5° | 0.0 | 0.0 | 0.0 | 0.0 | 0.0 | 0.0 | 0.0 | 0.0 | 0.0 | 0.0  | 0.0  |
| 135°   | 0.0 | 0.0 | 0.0 | 0.0 | 0.0 | 0.0 | 0.0 | 0.0 | 0.0 | 0.0  | 0.0  |
| 137.5° | 0.0 | 0.0 | 0.0 | 0.0 | 0.0 | 0.0 | 0.0 | 0.0 | 0.0 | 0.0  | 0.0  |
| 140°   | 0.0 | 0.0 | 0.0 | 0.0 | 0.0 | 0.0 | 0.0 | 0.0 | 0.0 | 0.0  | 0.0  |
| 142.5° | 0.0 | 0.0 | 0.0 | 0.0 | 0.0 | 0.0 | 0.0 | 0.0 | 0.0 | 0.0  | 0.0  |
| 145°   | 0.0 | 0.0 | 0.0 | 0.0 | 0.0 | 0.0 | 0.0 | 0.0 | 0.0 | 0.0  | 0.0  |
| 147.5° | 0.0 | 0.0 | 0.0 | 0.0 | 0.0 | 0.0 | 0.0 | 0.0 | 0.0 | 0.0  | 0.0  |
| 150°   | 0.0 | 0.0 | 0.0 | 0.0 | 0.0 | 0.0 | 0.0 | 0.0 | 0.0 | 0.0  | 0.0  |
| 152.5° | 0.0 | 0.0 | 0.0 | 0.0 | 0.0 | 0.0 | 0.0 | 0.0 | 0.0 | 0.0  | 0.0  |
| 155°   | 0.0 | 0.0 | 0.0 | 0.0 | 0.0 | 0.0 | 0.0 | 0.0 | 0.0 | 0.0  | 0.0  |
| 157.5° | 0.0 | 0.0 | 0.0 | 0.0 | 0.0 | 0.0 | 0.0 | 0.0 | 0.0 | 0.0  | 0.0  |
| 160°   | 0.0 | 0.0 | 0.0 | 0.0 | 0.0 | 0.0 | 0.0 | 0.0 | 0.0 | 0.0  | 0.0  |
| 162.5° | 0.0 | 0.0 | 0.0 | 0.0 | 0.0 | 0.0 | 0.0 | 0.0 | 0.0 | 0.0  | 0.0  |
| 165°   | 0.0 | 0.0 | 0.0 | 0.0 | 0.0 | 0.0 | 0.0 | 0.0 | 0.0 | 0.0  | 0.0  |
| 167.5° | 0.0 | 0.0 | 0.0 | 0.0 | 0.0 | 0.0 | 0.0 | 0.0 | 0.0 | 0.0  | 0.0  |
| 170°   | 0.0 | 0.0 | 0.0 | 0.0 | 0.0 | 0.0 | 0.0 | 0.0 | 0.0 | 0.0  | 0.0  |
| 172.5° | 0.0 | 0.0 | 0.0 | 0.0 | 0.0 | 0.0 | 0.0 | 0.0 | 0.0 | 0.0  | 0.0  |
| 175°   | 0.0 | 0.0 | 0.0 | 0.0 | 0.0 | 0.0 | 0.0 | 0.0 | 0.0 | 0.0  | 0.0  |
| 177.5° | 0.0 | 0.0 | 0.0 | 0.0 | 0.0 | 0.0 | 0.0 | 0.0 | 0.0 | 0.0  | 0.0  |
| 180°   | 0.0 | 0.0 | 0.0 | 0.0 | 0.0 | 0.0 | 0.0 | 0.0 | 0.0 | 0.0  | 0.0  |



REPORT NUMBER: P320304

CATALOG NUMBER: GAN-SAOD-730-U-SLL

**CANDELA DISTRIBUTION (continued):**

|        | 110°    | 115°    | 120°    | 125°    | 130°    | 135°    | 140°    | 145°    | 150°    | 155°    | 160°    |
|--------|---------|---------|---------|---------|---------|---------|---------|---------|---------|---------|---------|
| 0°     | 18725.3 | 18725.3 | 18725.3 | 18725.3 | 18725.3 | 18725.3 | 18725.3 | 18725.3 | 18725.3 | 18725.3 | 18725.3 |
| 2.5°   | 19148.0 | 18946.5 | 18717.9 | 18489.4 | 18228.9 | 17966.0 | 17811.1 | 17653.9 | 17484.3 | 17314.8 | 17123.1 |
| 5°     | 17535.9 | 17113.2 | 16634.1 | 16154.9 | 15680.6 | 15206.3 | 14950.7 | 14695.2 | 14424.9 | 14152.1 | 13916.2 |
| 7.5°   | 15221.1 | 14604.3 | 13940.8 | 13274.8 | 12685.0 | 12092.8 | 11726.7 | 11358.0 | 11023.8 | 10687.2 | 10404.6 |
| 10°    | 13183.9 | 12397.5 | 11731.6 | 11063.2 | 10618.4 | 10173.6 | 9836.9  | 9500.3  | 9175.9  | 8849.1  | 8537.0  |
| 12.5°  | 11842.2 | 11055.8 | 10633.1 | 10210.4 | 9841.8  | 9473.2  | 9085.0  | 8694.2  | 8249.5  | 7802.2  | 7475.4  |
| 15°    | 11318.7 | 10603.6 | 10134.3 | 9662.4  | 9168.5  | 8672.1  | 8195.4  | 7718.7  | 7192.8  | 6666.9  | 6295.8  |
| 17.5°  | 11092.6 | 10156.4 | 9500.3  | 8841.7  | 8190.5  | 7539.3  | 6986.4  | 6433.4  | 5858.4  | 5283.4  | 4907.4  |
| 20°    | 10854.3 | 9608.4  | 8728.6  | 7846.4  | 7010.9  | 6175.4  | 5548.8  | 4922.1  | 4408.6  | 3895.0  | 3607.4  |
| 22.5°  | 10638.0 | 9026.0  | 7922.6  | 6816.8  | 5828.9  | 4841.1  | 4226.7  | 3609.9  | 3295.4  | 2980.8  | 2865.3  |
| 25°    | 10549.6 | 8517.3  | 7160.8  | 5804.4  | 4762.4  | 3718.0  | 3280.6  | 2843.2  | 2722.8  | 2599.9  | 2540.9  |
| 27.5°  | 10564.3 | 8062.7  | 6519.5  | 4973.8  | 4035.0  | 3096.3  | 2796.5  | 2496.7  | 2423.0  | 2346.8  | 2309.9  |
| 30°    | 10620.8 | 7568.8  | 5914.9  | 4261.1  | 3487.0  | 2713.0  | 2518.8  | 2322.2  | 2243.6  | 2165.0  | 2118.3  |
| 32.5°  | 10684.7 | 7126.4  | 5448.0  | 3767.2  | 3135.6  | 2501.6  | 2341.9  | 2179.7  | 2103.5  | 2027.3  | 1980.7  |
| 35°    | 10574.1 | 6765.2  | 5128.6  | 3491.9  | 2909.5  | 2324.7  | 2189.5  | 2051.9  | 1968.4  | 1884.8  | 1840.6  |
| 37.5°  | 10387.4 | 6401.5  | 4880.4  | 3356.8  | 2762.1  | 2165.0  | 2066.7  | 1965.9  | 1879.9  | 1791.4  | 1749.7  |
| 40°    | 10217.8 | 6094.3  | 4696.1  | 3295.4  | 2681.0  | 2064.2  | 1980.7  | 1897.1  | 1808.6  | 1717.7  | 1668.6  |
| 42.5°  | 10080.2 | 5887.9  | 4514.2  | 3140.5  | 2607.3  | 2071.6  | 1953.6  | 1833.2  | 1747.2  | 1661.2  | 1607.1  |
| 45°    | 9977.0  | 5752.7  | 4371.7  | 2990.6  | 2538.5  | 2086.3  | 1936.4  | 1786.5  | 1700.5  | 1612.0  | 1548.2  |
| 47.5°  | 9967.2  | 5681.5  | 4270.9  | 2860.4  | 2408.2  | 1953.6  | 1892.2  | 1830.8  | 1705.4  | 1577.6  | 1503.9  |
| 50°    | 10102.3 | 5566.0  | 4153.0  | 2737.5  | 2282.9  | 1828.3  | 1911.8  | 1992.9  | 1779.1  | 1562.9  | 1469.5  |
| 52.5°  | 10384.9 | 5362.0  | 3966.2  | 2570.4  | 2130.6  | 1688.2  | 1818.5  | 1946.3  | 1761.9  | 1575.2  | 1454.8  |
| 55°    | 10726.5 | 5062.2  | 3683.6  | 2302.6  | 1929.0  | 1553.1  | 1668.6  | 1781.6  | 1666.1  | 1548.2  | 1403.2  |
| 57.5°  | 10940.3 | 4683.8  | 3327.3  | 1970.8  | 1703.0  | 1435.1  | 1501.5  | 1565.4  | 1518.7  | 1472.0  | 1324.5  |
| 60°    | 10812.5 | 4180.0  | 2926.7  | 1671.0  | 1503.9  | 1336.8  | 1324.5  | 1309.8  | 1378.6  | 1447.4  | 1277.8  |
| 62.5°  | 10188.3 | 3659.1  | 2572.9  | 1486.7  | 1361.4  | 1233.6  | 1206.6  | 1177.1  | 1290.1  | 1400.7  | 1221.3  |
| 65°    | 9134.1  | 3295.4  | 2349.3  | 1403.2  | 1263.1  | 1123.0  | 1093.5  | 1064.0  | 1098.5  | 1132.9  | 1049.3  |
| 67.5°  | 7794.8  | 3071.7  | 2221.5  | 1371.2  | 1201.7  | 1029.6  | 995.2   | 960.8   | 953.5   | 946.1   | 916.6   |
| 70°    | 6413.8  | 2934.1  | 2137.9  | 1341.7  | 1135.3  | 926.4   | 894.5   | 862.5   | 852.7   | 840.4   | 818.3   |
| 72.5°  | 5362.0  | 2916.9  | 2128.1  | 1339.3  | 1081.3  | 823.2   | 793.7   | 764.2   | 752.0   | 737.2   | 720.0   |
| 75°    | 4391.4  | 2737.5  | 2020.0  | 1302.4  | 1007.5  | 710.2   | 683.2   | 656.1   | 646.3   | 634.0   | 619.3   |
| 77.5°  | 3258.5  | 2265.7  | 1698.1  | 1130.4  | 862.5   | 594.7   | 567.7   | 538.2   | 535.7   | 530.8   | 518.5   |
| 80°    | 2113.4  | 1639.1  | 1213.9  | 788.8   | 629.1   | 466.9   | 444.8   | 420.2   | 422.7   | 425.1   | 415.3   |
| 82.5°  | 1174.6  | 955.9   | 742.1   | 528.3   | 430.0   | 331.7   | 321.9   | 309.6   | 317.0   | 321.9   | 309.6   |
| 85°    | 619.3   | 481.6   | 398.1   | 314.5   | 248.2   | 181.8   | 181.8   | 179.4   | 189.2   | 199.0   | 189.2   |
| 87.5°  | 267.9   | 169.6   | 145.0   | 118.0   | 66.3    | 12.3    | 14.7    | 14.7    | 19.7    | 24.6    | 22.1    |
| 90°    | 0.0     | 0.0     | 0.0     | 0.0     | 0.0     | 0.0     | 0.0     | 0.0     | 0.0     | 0.0     | 0.0     |
| 92.5°  | 0.0     | 0.0     | 0.0     | 0.0     | 0.0     | 0.0     | 0.0     | 0.0     | 0.0     | 0.0     | 0.0     |
| 95°    | 0.0     | 0.0     | 0.0     | 0.0     | 0.0     | 0.0     | 0.0     | 0.0     | 0.0     | 0.0     | 0.0     |
| 97.5°  | 0.0     | 0.0     | 0.0     | 0.0     | 0.0     | 0.0     | 0.0     | 0.0     | 0.0     | 0.0     | 0.0     |
| 100°   | 0.0     | 0.0     | 0.0     | 0.0     | 0.0     | 0.0     | 0.0     | 0.0     | 0.0     | 0.0     | 0.0     |
| 102.5° | 0.0     | 0.0     | 0.0     | 0.0     | 0.0     | 0.0     | 0.0     | 0.0     | 0.0     | 0.0     | 0.0     |
| 105°   | 0.0     | 0.0     | 0.0     | 0.0     | 0.0     | 0.0     | 0.0     | 0.0     | 0.0     | 0.0     | 0.0     |
| 107.5° | 0.0     | 0.0     | 0.0     | 0.0     | 0.0     | 0.0     | 0.0     | 0.0     | 0.0     | 0.0     | 0.0     |
| 110°   | 0.0     | 0.0     | 0.0     | 0.0     | 0.0     | 0.0     | 0.0     | 0.0     | 0.0     | 0.0     | 0.0     |



REPORT NUMBER: P320304  
 CATALOG NUMBER: GAN-SA0D-730-U-SLL

**CANDELA DISTRIBUTION (continued):**

|        | 110° | 115° | 120° | 125° | 130° | 135° | 140° | 145° | 150° | 155° | 160° |
|--------|------|------|------|------|------|------|------|------|------|------|------|
| 112.5° | 0.0  | 0.0  | 0.0  | 0.0  | 0.0  | 0.0  | 0.0  | 0.0  | 0.0  | 0.0  | 0.0  |
| 115°   | 0.0  | 0.0  | 0.0  | 0.0  | 0.0  | 0.0  | 0.0  | 0.0  | 0.0  | 0.0  | 0.0  |
| 117.5° | 0.0  | 0.0  | 0.0  | 0.0  | 0.0  | 0.0  | 0.0  | 0.0  | 0.0  | 0.0  | 0.0  |
| 120°   | 0.0  | 0.0  | 0.0  | 0.0  | 0.0  | 0.0  | 0.0  | 0.0  | 0.0  | 0.0  | 0.0  |
| 122.5° | 0.0  | 0.0  | 0.0  | 0.0  | 0.0  | 0.0  | 0.0  | 0.0  | 0.0  | 0.0  | 0.0  |
| 125°   | 0.0  | 0.0  | 0.0  | 0.0  | 0.0  | 0.0  | 0.0  | 0.0  | 0.0  | 0.0  | 0.0  |
| 127.5° | 0.0  | 0.0  | 0.0  | 0.0  | 0.0  | 0.0  | 0.0  | 0.0  | 0.0  | 0.0  | 0.0  |
| 130°   | 0.0  | 0.0  | 0.0  | 0.0  | 0.0  | 0.0  | 0.0  | 0.0  | 0.0  | 0.0  | 0.0  |
| 132.5° | 0.0  | 0.0  | 0.0  | 0.0  | 0.0  | 0.0  | 0.0  | 0.0  | 0.0  | 0.0  | 0.0  |
| 135°   | 0.0  | 0.0  | 0.0  | 0.0  | 0.0  | 0.0  | 0.0  | 0.0  | 0.0  | 0.0  | 0.0  |
| 137.5° | 0.0  | 0.0  | 0.0  | 0.0  | 0.0  | 0.0  | 0.0  | 0.0  | 0.0  | 0.0  | 0.0  |
| 140°   | 0.0  | 0.0  | 0.0  | 0.0  | 0.0  | 0.0  | 0.0  | 0.0  | 0.0  | 0.0  | 0.0  |
| 142.5° | 0.0  | 0.0  | 0.0  | 0.0  | 0.0  | 0.0  | 0.0  | 0.0  | 0.0  | 0.0  | 0.0  |
| 145°   | 0.0  | 0.0  | 0.0  | 0.0  | 0.0  | 0.0  | 0.0  | 0.0  | 0.0  | 0.0  | 0.0  |
| 147.5° | 0.0  | 0.0  | 0.0  | 0.0  | 0.0  | 0.0  | 0.0  | 0.0  | 0.0  | 0.0  | 0.0  |
| 150°   | 0.0  | 0.0  | 0.0  | 0.0  | 0.0  | 0.0  | 0.0  | 0.0  | 0.0  | 0.0  | 0.0  |
| 152.5° | 0.0  | 0.0  | 0.0  | 0.0  | 0.0  | 0.0  | 0.0  | 0.0  | 0.0  | 0.0  | 0.0  |
| 155°   | 0.0  | 0.0  | 0.0  | 0.0  | 0.0  | 0.0  | 0.0  | 0.0  | 0.0  | 0.0  | 0.0  |
| 157.5° | 0.0  | 0.0  | 0.0  | 0.0  | 0.0  | 0.0  | 0.0  | 0.0  | 0.0  | 0.0  | 0.0  |
| 160°   | 0.0  | 0.0  | 0.0  | 0.0  | 0.0  | 0.0  | 0.0  | 0.0  | 0.0  | 0.0  | 0.0  |
| 162.5° | 0.0  | 0.0  | 0.0  | 0.0  | 0.0  | 0.0  | 0.0  | 0.0  | 0.0  | 0.0  | 0.0  |
| 165°   | 0.0  | 0.0  | 0.0  | 0.0  | 0.0  | 0.0  | 0.0  | 0.0  | 0.0  | 0.0  | 0.0  |
| 167.5° | 0.0  | 0.0  | 0.0  | 0.0  | 0.0  | 0.0  | 0.0  | 0.0  | 0.0  | 0.0  | 0.0  |
| 170°   | 0.0  | 0.0  | 0.0  | 0.0  | 0.0  | 0.0  | 0.0  | 0.0  | 0.0  | 0.0  | 0.0  |
| 172.5° | 0.0  | 0.0  | 0.0  | 0.0  | 0.0  | 0.0  | 0.0  | 0.0  | 0.0  | 0.0  | 0.0  |
| 175°   | 0.0  | 0.0  | 0.0  | 0.0  | 0.0  | 0.0  | 0.0  | 0.0  | 0.0  | 0.0  | 0.0  |
| 177.5° | 0.0  | 0.0  | 0.0  | 0.0  | 0.0  | 0.0  | 0.0  | 0.0  | 0.0  | 0.0  | 0.0  |
| 180°   | 0.0  | 0.0  | 0.0  | 0.0  | 0.0  | 0.0  | 0.0  | 0.0  | 0.0  | 0.0  | 0.0  |



REPORT NUMBER: P320304  
 CATALOG NUMBER: GAN-SAOD-730-U-SLL

**CANDELA DISTRIBUTION (continued):**

|        | 165°    | 170°    | 175°    | 180°    | 185°    | 190°    | 195°    | 200°    | 205°    | 210°    | 215°    |
|--------|---------|---------|---------|---------|---------|---------|---------|---------|---------|---------|---------|
| 0°     | 18725.3 | 18725.3 | 18725.3 | 18725.3 | 18725.3 | 18725.3 | 18725.3 | 18725.3 | 18725.3 | 18725.3 | 18725.3 |
| 2.5°   | 16928.9 | 16749.6 | 16567.7 | 16368.7 | 16405.5 | 16253.2 | 16100.8 | 16005.0 | 15909.1 | 15879.6 | 15850.2 |
| 5°     | 13680.3 | 13476.3 | 13269.9 | 13085.6 | 13245.3 | 13137.2 | 13029.1 | 13014.3 | 12997.1 | 12997.1 | 12994.7 |
| 7.5°   | 10122.0 | 9903.3  | 9682.1  | 9529.8  | 9687.0  | 9667.4  | 9647.7  | 9753.4  | 9859.0  | 9945.0  | 10028.6 |
| 10°    | 8224.9  | 7959.5  | 7691.6  | 7465.5  | 7426.2  | 7313.2  | 7197.7  | 7222.3  | 7244.4  | 7337.8  | 7431.1  |
| 12.5°  | 7148.5  | 6831.5  | 6514.5  | 6249.1  | 6128.7  | 5942.0  | 5752.7  | 5634.8  | 5516.8  | 5529.1  | 5539.0  |
| 15°    | 5922.3  | 5615.1  | 5305.5  | 5077.0  | 5000.8  | 4855.8  | 4710.8  | 4563.4  | 4413.5  | 4352.0  | 4288.1  |
| 17.5°  | 4529.0  | 4283.2  | 4035.0  | 3882.7  | 3882.7  | 3840.9  | 3799.1  | 3725.4  | 3649.2  | 3587.8  | 3523.9  |
| 20°    | 3319.9  | 3189.7  | 3057.0  | 2993.1  | 3012.8  | 3015.2  | 3015.2  | 3052.1  | 3088.9  | 3069.3  | 3049.6  |
| 22.5°  | 2747.4  | 2700.7  | 2654.0  | 2626.9  | 2636.8  | 2639.2  | 2641.7  | 2676.1  | 2708.0  | 2732.6  | 2754.7  |
| 25°    | 2479.5  | 2450.0  | 2420.5  | 2410.7  | 2432.8  | 2435.3  | 2435.3  | 2457.4  | 2479.5  | 2504.1  | 2528.7  |
| 27.5°  | 2270.6  | 2258.3  | 2246.1  | 2228.9  | 2251.0  | 2251.0  | 2248.5  | 2273.1  | 2295.2  | 2317.3  | 2337.0  |
| 30°    | 2071.6  | 2076.5  | 2079.0  | 2074.0  | 2088.8  | 2098.6  | 2106.0  | 2123.2  | 2137.9  | 2155.1  | 2172.3  |
| 32.5°  | 1931.5  | 1924.1  | 1916.8  | 1911.8  | 1943.8  | 1961.0  | 1978.2  | 1995.4  | 2010.1  | 2017.5  | 2024.9  |
| 35°    | 1796.4  | 1779.1  | 1761.9  | 1749.7  | 1779.1  | 1801.3  | 1823.4  | 1855.3  | 1884.8  | 1889.7  | 1894.6  |
| 37.5°  | 1705.4  | 1683.3  | 1661.2  | 1646.4  | 1658.7  | 1668.6  | 1678.4  | 1712.8  | 1747.2  | 1766.9  | 1784.1  |
| 40°    | 1619.4  | 1597.3  | 1575.2  | 1562.9  | 1570.3  | 1572.7  | 1575.2  | 1592.4  | 1607.1  | 1644.0  | 1678.4  |
| 42.5°  | 1550.6  | 1523.6  | 1496.5  | 1481.8  | 1486.7  | 1491.6  | 1494.1  | 1491.6  | 1489.2  | 1523.6  | 1558.0  |
| 45°    | 1481.8  | 1452.3  | 1422.8  | 1405.6  | 1408.1  | 1408.1  | 1408.1  | 1403.2  | 1395.8  | 1413.0  | 1430.2  |
| 47.5°  | 1427.7  | 1393.3  | 1358.9  | 1341.7  | 1336.8  | 1331.9  | 1327.0  | 1324.5  | 1319.6  | 1331.9  | 1341.7  |
| 50°    | 1373.7  | 1336.8  | 1297.5  | 1277.8  | 1265.6  | 1260.6  | 1255.7  | 1253.3  | 1248.4  | 1260.6  | 1270.5  |
| 52.5°  | 1331.9  | 1287.7  | 1243.4  | 1211.5  | 1199.2  | 1191.8  | 1184.5  | 1186.9  | 1186.9  | 1191.8  | 1194.3  |
| 55°    | 1258.2  | 1218.9  | 1177.1  | 1155.0  | 1132.9  | 1127.9  | 1123.0  | 1130.4  | 1135.3  | 1135.3  | 1135.3  |
| 57.5°  | 1177.1  | 1140.2  | 1100.9  | 1086.2  | 1066.5  | 1066.5  | 1064.0  | 1073.9  | 1081.3  | 1086.2  | 1091.1  |
| 60°    | 1105.8  | 1064.0  | 1022.3  | 1010.0  | 1002.6  | 1000.2  | 997.7   | 1010.0  | 1019.8  | 1029.6  | 1039.5  |
| 62.5°  | 1039.5  | 995.2   | 951.0   | 936.3   | 933.8   | 936.3   | 936.3   | 948.6   | 958.4   | 968.2   | 978.0   |
| 65°    | 965.8   | 921.5   | 874.8   | 860.1   | 865.0   | 872.4   | 879.7   | 889.6   | 896.9   | 906.8   | 916.6   |
| 67.5°  | 884.7   | 847.8   | 808.5   | 793.7   | 796.2   | 806.0   | 815.9   | 823.2   | 828.1   | 838.0   | 847.8   |
| 70°    | 796.2   | 764.2   | 732.3   | 722.5   | 720.0   | 732.3   | 742.1   | 747.0   | 752.0   | 764.2   | 774.1   |
| 72.5°  | 700.4   | 673.3   | 646.3   | 638.9   | 641.4   | 648.8   | 656.1   | 663.5   | 668.4   | 680.7   | 690.5   |
| 75°    | 602.1   | 577.5   | 552.9   | 548.0   | 552.9   | 560.3   | 567.7   | 572.6   | 577.5   | 592.2   | 604.5   |
| 77.5°  | 506.2   | 479.2   | 449.7   | 447.2   | 454.6   | 462.0   | 466.9   | 474.3   | 481.6   | 501.3   | 521.0   |
| 80°    | 405.5   | 376.0   | 344.0   | 341.6   | 348.9   | 356.3   | 363.7   | 371.1   | 378.4   | 403.0   | 425.1   |
| 82.5°  | 297.3   | 262.9   | 228.5   | 223.6   | 248.2   | 255.6   | 262.9   | 275.2   | 285.1   | 307.2   | 329.3   |
| 85°    | 179.4   | 145.0   | 110.6   | 108.1   | 130.2   | 142.5   | 154.8   | 169.6   | 181.8   | 201.5   | 221.2   |
| 87.5°  | 19.7    | 9.8     | 0.0     | 0.0     | 2.5     | 12.3    | 22.1    | 34.4    | 46.7    | 66.3    | 83.6    |
| 90°    | 0.0     | 0.0     | 0.0     | 0.0     | 0.0     | 0.0     | 0.0     | 0.0     | 0.0     | 0.0     | 0.0     |
| 92.5°  | 0.0     | 0.0     | 0.0     | 0.0     | 0.0     | 0.0     | 0.0     | 0.0     | 0.0     | 0.0     | 0.0     |
| 95°    | 0.0     | 0.0     | 0.0     | 0.0     | 0.0     | 0.0     | 0.0     | 0.0     | 0.0     | 0.0     | 0.0     |
| 97.5°  | 0.0     | 0.0     | 0.0     | 0.0     | 0.0     | 0.0     | 0.0     | 0.0     | 0.0     | 0.0     | 0.0     |
| 100°   | 0.0     | 0.0     | 0.0     | 0.0     | 0.0     | 0.0     | 0.0     | 0.0     | 0.0     | 0.0     | 0.0     |
| 102.5° | 0.0     | 0.0     | 0.0     | 0.0     | 0.0     | 0.0     | 0.0     | 0.0     | 0.0     | 0.0     | 0.0     |
| 105°   | 0.0     | 0.0     | 0.0     | 0.0     | 0.0     | 0.0     | 0.0     | 0.0     | 0.0     | 0.0     | 0.0     |
| 107.5° | 0.0     | 0.0     | 0.0     | 0.0     | 0.0     | 0.0     | 0.0     | 0.0     | 0.0     | 0.0     | 0.0     |
| 110°   | 0.0     | 0.0     | 0.0     | 0.0     | 0.0     | 0.0     | 0.0     | 0.0     | 0.0     | 0.0     | 0.0     |



REPORT NUMBER: P320304  
 CATALOG NUMBER: GAN-SA0D-730-U-SLL

**CANDELA DISTRIBUTION (continued):**

|        | 165° | 170° | 175° | 180° | 185° | 190° | 195° | 200° | 205° | 210° | 215° |
|--------|------|------|------|------|------|------|------|------|------|------|------|
| 112.5° | 0.0  | 0.0  | 0.0  | 0.0  | 0.0  | 0.0  | 0.0  | 0.0  | 0.0  | 0.0  | 0.0  |
| 115°   | 0.0  | 0.0  | 0.0  | 0.0  | 0.0  | 0.0  | 0.0  | 0.0  | 0.0  | 0.0  | 0.0  |
| 117.5° | 0.0  | 0.0  | 0.0  | 0.0  | 0.0  | 0.0  | 0.0  | 0.0  | 0.0  | 0.0  | 0.0  |
| 120°   | 0.0  | 0.0  | 0.0  | 0.0  | 0.0  | 0.0  | 0.0  | 0.0  | 0.0  | 0.0  | 0.0  |
| 122.5° | 0.0  | 0.0  | 0.0  | 0.0  | 0.0  | 0.0  | 0.0  | 0.0  | 0.0  | 0.0  | 0.0  |
| 125°   | 0.0  | 0.0  | 0.0  | 0.0  | 0.0  | 0.0  | 0.0  | 0.0  | 0.0  | 0.0  | 0.0  |
| 127.5° | 0.0  | 0.0  | 0.0  | 0.0  | 0.0  | 0.0  | 0.0  | 0.0  | 0.0  | 0.0  | 0.0  |
| 130°   | 0.0  | 0.0  | 0.0  | 0.0  | 0.0  | 0.0  | 0.0  | 0.0  | 0.0  | 0.0  | 0.0  |
| 132.5° | 0.0  | 0.0  | 0.0  | 0.0  | 0.0  | 0.0  | 0.0  | 0.0  | 0.0  | 0.0  | 0.0  |
| 135°   | 0.0  | 0.0  | 0.0  | 0.0  | 0.0  | 0.0  | 0.0  | 0.0  | 0.0  | 0.0  | 0.0  |
| 137.5° | 0.0  | 0.0  | 0.0  | 0.0  | 0.0  | 0.0  | 0.0  | 0.0  | 0.0  | 0.0  | 0.0  |
| 140°   | 0.0  | 0.0  | 0.0  | 0.0  | 0.0  | 0.0  | 0.0  | 0.0  | 0.0  | 0.0  | 0.0  |
| 142.5° | 0.0  | 0.0  | 0.0  | 0.0  | 0.0  | 0.0  | 0.0  | 0.0  | 0.0  | 0.0  | 0.0  |
| 145°   | 0.0  | 0.0  | 0.0  | 0.0  | 0.0  | 0.0  | 0.0  | 0.0  | 0.0  | 0.0  | 0.0  |
| 147.5° | 0.0  | 0.0  | 0.0  | 0.0  | 0.0  | 0.0  | 0.0  | 0.0  | 0.0  | 0.0  | 0.0  |
| 150°   | 0.0  | 0.0  | 0.0  | 0.0  | 0.0  | 0.0  | 0.0  | 0.0  | 0.0  | 0.0  | 0.0  |
| 152.5° | 0.0  | 0.0  | 0.0  | 0.0  | 0.0  | 0.0  | 0.0  | 0.0  | 0.0  | 0.0  | 0.0  |
| 155°   | 0.0  | 0.0  | 0.0  | 0.0  | 0.0  | 0.0  | 0.0  | 0.0  | 0.0  | 0.0  | 0.0  |
| 157.5° | 0.0  | 0.0  | 0.0  | 0.0  | 0.0  | 0.0  | 0.0  | 0.0  | 0.0  | 0.0  | 0.0  |
| 160°   | 0.0  | 0.0  | 0.0  | 0.0  | 0.0  | 0.0  | 0.0  | 0.0  | 0.0  | 0.0  | 0.0  |
| 162.5° | 0.0  | 0.0  | 0.0  | 0.0  | 0.0  | 0.0  | 0.0  | 0.0  | 0.0  | 0.0  | 0.0  |
| 165°   | 0.0  | 0.0  | 0.0  | 0.0  | 0.0  | 0.0  | 0.0  | 0.0  | 0.0  | 0.0  | 0.0  |
| 167.5° | 0.0  | 0.0  | 0.0  | 0.0  | 0.0  | 0.0  | 0.0  | 0.0  | 0.0  | 0.0  | 0.0  |
| 170°   | 0.0  | 0.0  | 0.0  | 0.0  | 0.0  | 0.0  | 0.0  | 0.0  | 0.0  | 0.0  | 0.0  |
| 172.5° | 0.0  | 0.0  | 0.0  | 0.0  | 0.0  | 0.0  | 0.0  | 0.0  | 0.0  | 0.0  | 0.0  |
| 175°   | 0.0  | 0.0  | 0.0  | 0.0  | 0.0  | 0.0  | 0.0  | 0.0  | 0.0  | 0.0  | 0.0  |
| 177.5° | 0.0  | 0.0  | 0.0  | 0.0  | 0.0  | 0.0  | 0.0  | 0.0  | 0.0  | 0.0  | 0.0  |
| 180°   | 0.0  | 0.0  | 0.0  | 0.0  | 0.0  | 0.0  | 0.0  | 0.0  | 0.0  | 0.0  | 0.0  |



REPORT NUMBER: P320304  
 CATALOG NUMBER: GAN-SAOD-730-U-SLL

**CANDELA DISTRIBUTION (continued):**

|        | 220°    | 225°    | 230°    | 235°    | 240°    | 245°    | 250°    | 255°    | 260°    | 265°    | 270°    |
|--------|---------|---------|---------|---------|---------|---------|---------|---------|---------|---------|---------|
| 0°     | 18725.3 | 18725.3 | 18725.3 | 18725.3 | 18725.3 | 18725.3 | 18725.3 | 18725.3 | 18725.3 | 18725.3 | 18725.3 |
| 2.5°   | 15742.0 | 15631.4 | 15744.5 | 15855.1 | 15901.8 | 15948.4 | 15828.0 | 15705.2 | 15896.8 | 16086.1 | 16135.2 |
| 5°     | 12896.4 | 12795.6 | 12871.8 | 12945.5 | 12780.9 | 12616.2 | 12599.0 | 12579.4 | 12721.9 | 12864.4 | 12886.5 |
| 7.5°   | 9996.7  | 9964.7  | 10036.0 | 10107.2 | 9898.4  | 9687.0  | 9583.8  | 9480.6  | 9515.0  | 9549.4  | 9544.5  |
| 10°    | 7453.3  | 7472.9  | 7561.4  | 7647.4  | 7485.2  | 7323.0  | 7251.8  | 7180.5  | 7259.1  | 7335.3  | 7406.6  |
| 12.5°  | 5583.2  | 5625.0  | 5718.3  | 5809.3  | 5742.9  | 5674.1  | 5681.5  | 5688.9  | 5779.8  | 5868.2  | 5946.9  |
| 15°    | 4337.3  | 4386.4  | 4452.8  | 4516.7  | 4519.1  | 4519.1  | 4583.0  | 4644.5  | 4637.1  | 4629.7  | 4683.8  |
| 17.5°  | 3590.2  | 3654.1  | 3661.5  | 3668.9  | 3671.3  | 3673.8  | 3668.9  | 3664.0  | 3627.1  | 3590.2  | 3632.0  |
| 20°    | 3074.2  | 3096.3  | 3116.0  | 3133.2  | 3111.1  | 3086.5  | 3025.0  | 2963.6  | 2939.0  | 2914.5  | 2953.8  |
| 22.5°  | 2796.5  | 2835.8  | 2816.2  | 2794.1  | 2749.8  | 2703.1  | 2656.4  | 2607.3  | 2604.8  | 2599.9  | 2622.0  |
| 25°    | 2563.1  | 2595.0  | 2560.6  | 2526.2  | 2494.2  | 2462.3  | 2430.4  | 2398.4  | 2396.0  | 2393.5  | 2403.3  |
| 27.5°  | 2368.9  | 2398.4  | 2366.5  | 2334.5  | 2307.5  | 2280.5  | 2255.9  | 2231.3  | 2226.4  | 2221.5  | 2223.9  |
| 30°    | 2201.8  | 2228.9  | 2201.8  | 2172.3  | 2152.7  | 2130.6  | 2113.4  | 2096.2  | 2093.7  | 2091.2  | 2091.2  |
| 32.5°  | 2051.9  | 2079.0  | 2059.3  | 2039.6  | 2022.4  | 2005.2  | 1992.9  | 1980.7  | 1968.4  | 1956.1  | 1929.0  |
| 35°    | 1921.7  | 1948.7  | 1936.4  | 1921.7  | 1902.0  | 1882.4  | 1860.2  | 1835.7  | 1803.7  | 1769.3  | 1754.6  |
| 37.5°  | 1811.1  | 1838.1  | 1825.8  | 1813.6  | 1786.5  | 1759.5  | 1720.2  | 1678.4  | 1668.6  | 1656.3  | 1653.8  |
| 40°    | 1722.6  | 1764.4  | 1739.8  | 1712.8  | 1671.0  | 1629.2  | 1609.6  | 1589.9  | 1585.0  | 1580.1  | 1575.2  |
| 42.5°  | 1624.3  | 1688.2  | 1644.0  | 1599.8  | 1560.4  | 1521.1  | 1516.2  | 1511.3  | 1508.8  | 1506.4  | 1506.4  |
| 45°    | 1501.5  | 1570.3  | 1526.0  | 1479.3  | 1457.2  | 1435.1  | 1435.1  | 1435.1  | 1437.6  | 1437.6  | 1442.5  |
| 47.5°  | 1386.0  | 1427.7  | 1405.6  | 1383.5  | 1371.2  | 1358.9  | 1361.4  | 1363.9  | 1371.2  | 1376.1  | 1388.4  |
| 50°    | 1287.7  | 1302.4  | 1307.3  | 1309.8  | 1302.4  | 1295.0  | 1300.0  | 1302.4  | 1309.8  | 1314.7  | 1324.5  |
| 52.5°  | 1216.4  | 1238.5  | 1238.5  | 1236.1  | 1236.1  | 1236.1  | 1241.0  | 1245.9  | 1253.3  | 1260.6  | 1270.5  |
| 55°    | 1169.7  | 1201.7  | 1191.8  | 1182.0  | 1184.5  | 1184.5  | 1189.4  | 1194.3  | 1201.7  | 1206.6  | 1221.3  |
| 57.5°  | 1125.5  | 1159.9  | 1150.1  | 1140.2  | 1140.2  | 1140.2  | 1142.7  | 1145.1  | 1152.5  | 1157.4  | 1167.3  |
| 60°    | 1073.9  | 1108.3  | 1098.5  | 1086.2  | 1088.6  | 1091.1  | 1093.5  | 1093.5  | 1098.5  | 1100.9  | 1100.9  |
| 62.5°  | 1012.4  | 1046.8  | 1037.0  | 1024.7  | 1032.1  | 1037.0  | 1037.0  | 1037.0  | 1041.9  | 1044.4  | 1037.0  |
| 65°    | 948.6   | 980.5   | 970.7   | 960.8   | 970.7   | 978.0   | 983.0   | 985.4   | 983.0   | 980.5   | 973.1   |
| 67.5°  | 879.7   | 911.7   | 901.9   | 889.6   | 901.9   | 911.7   | 921.5   | 928.9   | 921.5   | 914.1   | 904.3   |
| 70°    | 806.0   | 838.0   | 825.7   | 813.4   | 825.7   | 838.0   | 847.8   | 857.6   | 847.8   | 838.0   | 835.5   |
| 72.5°  | 727.4   | 764.2   | 749.5   | 734.8   | 749.5   | 764.2   | 769.2   | 774.1   | 766.7   | 759.3   | 754.4   |
| 75°    | 641.4   | 678.2   | 666.0   | 651.2   | 663.5   | 675.8   | 678.2   | 680.7   | 680.7   | 678.2   | 663.5   |
| 77.5°  | 550.5   | 579.9   | 572.6   | 565.2   | 572.6   | 579.9   | 579.9   | 579.9   | 582.4   | 582.4   | 562.7   |
| 80°    | 442.3   | 459.5   | 462.0   | 464.4   | 466.9   | 469.4   | 466.9   | 464.4   | 459.5   | 454.6   | 442.3   |
| 82.5°  | 329.3   | 329.3   | 348.9   | 366.2   | 366.2   | 363.7   | 361.2   | 356.3   | 346.5   | 334.2   | 307.2   |
| 85°    | 208.9   | 196.6   | 228.5   | 258.0   | 258.0   | 255.6   | 250.7   | 243.3   | 223.6   | 201.5   | 179.4   |
| 87.5°  | 71.3    | 59.0    | 90.9    | 122.9   | 125.3   | 125.3   | 120.4   | 115.5   | 95.8    | 73.7    | 56.5    |
| 90°    | 0.0     | 0.0     | 0.0     | 0.0     | 0.0     | 0.0     | 0.0     | 0.0     | 0.0     | 0.0     | 0.0     |
| 92.5°  | 0.0     | 0.0     | 0.0     | 0.0     | 0.0     | 0.0     | 0.0     | 0.0     | 0.0     | 0.0     | 0.0     |
| 95°    | 0.0     | 0.0     | 0.0     | 0.0     | 0.0     | 0.0     | 0.0     | 0.0     | 0.0     | 0.0     | 0.0     |
| 97.5°  | 0.0     | 0.0     | 0.0     | 0.0     | 0.0     | 0.0     | 0.0     | 0.0     | 0.0     | 0.0     | 0.0     |
| 100°   | 0.0     | 0.0     | 0.0     | 0.0     | 0.0     | 0.0     | 0.0     | 0.0     | 0.0     | 0.0     | 0.0     |
| 102.5° | 0.0     | 0.0     | 0.0     | 0.0     | 0.0     | 0.0     | 0.0     | 0.0     | 0.0     | 0.0     | 0.0     |
| 105°   | 0.0     | 0.0     | 0.0     | 0.0     | 0.0     | 0.0     | 0.0     | 0.0     | 0.0     | 0.0     | 0.0     |
| 107.5° | 0.0     | 0.0     | 0.0     | 0.0     | 0.0     | 0.0     | 0.0     | 0.0     | 0.0     | 0.0     | 0.0     |
| 110°   | 0.0     | 0.0     | 0.0     | 0.0     | 0.0     | 0.0     | 0.0     | 0.0     | 0.0     | 0.0     | 0.0     |



REPORT NUMBER: P320304  
 CATALOG NUMBER: GAN-SA0D-730-U-SLL

**CANDELA DISTRIBUTION (continued):**

|        | 220° | 225° | 230° | 235° | 240° | 245° | 250° | 255° | 260° | 265° | 270° |
|--------|------|------|------|------|------|------|------|------|------|------|------|
| 112.5° | 0.0  | 0.0  | 0.0  | 0.0  | 0.0  | 0.0  | 0.0  | 0.0  | 0.0  | 0.0  | 0.0  |
| 115°   | 0.0  | 0.0  | 0.0  | 0.0  | 0.0  | 0.0  | 0.0  | 0.0  | 0.0  | 0.0  | 0.0  |
| 117.5° | 0.0  | 0.0  | 0.0  | 0.0  | 0.0  | 0.0  | 0.0  | 0.0  | 0.0  | 0.0  | 0.0  |
| 120°   | 0.0  | 0.0  | 0.0  | 0.0  | 0.0  | 0.0  | 0.0  | 0.0  | 0.0  | 0.0  | 0.0  |
| 122.5° | 0.0  | 0.0  | 0.0  | 0.0  | 0.0  | 0.0  | 0.0  | 0.0  | 0.0  | 0.0  | 0.0  |
| 125°   | 0.0  | 0.0  | 0.0  | 0.0  | 0.0  | 0.0  | 0.0  | 0.0  | 0.0  | 0.0  | 0.0  |
| 127.5° | 0.0  | 0.0  | 0.0  | 0.0  | 0.0  | 0.0  | 0.0  | 0.0  | 0.0  | 0.0  | 0.0  |
| 130°   | 0.0  | 0.0  | 0.0  | 0.0  | 0.0  | 0.0  | 0.0  | 0.0  | 0.0  | 0.0  | 0.0  |
| 132.5° | 0.0  | 0.0  | 0.0  | 0.0  | 0.0  | 0.0  | 0.0  | 0.0  | 0.0  | 0.0  | 0.0  |
| 135°   | 0.0  | 0.0  | 0.0  | 0.0  | 0.0  | 0.0  | 0.0  | 0.0  | 0.0  | 0.0  | 0.0  |
| 137.5° | 0.0  | 0.0  | 0.0  | 0.0  | 0.0  | 0.0  | 0.0  | 0.0  | 0.0  | 0.0  | 0.0  |
| 140°   | 0.0  | 0.0  | 0.0  | 0.0  | 0.0  | 0.0  | 0.0  | 0.0  | 0.0  | 0.0  | 0.0  |
| 142.5° | 0.0  | 0.0  | 0.0  | 0.0  | 0.0  | 0.0  | 0.0  | 0.0  | 0.0  | 0.0  | 0.0  |
| 145°   | 0.0  | 0.0  | 0.0  | 0.0  | 0.0  | 0.0  | 0.0  | 0.0  | 0.0  | 0.0  | 0.0  |
| 147.5° | 0.0  | 0.0  | 0.0  | 0.0  | 0.0  | 0.0  | 0.0  | 0.0  | 0.0  | 0.0  | 0.0  |
| 150°   | 0.0  | 0.0  | 0.0  | 0.0  | 0.0  | 0.0  | 0.0  | 0.0  | 0.0  | 0.0  | 0.0  |
| 152.5° | 0.0  | 0.0  | 0.0  | 0.0  | 0.0  | 0.0  | 0.0  | 0.0  | 0.0  | 0.0  | 0.0  |
| 155°   | 0.0  | 0.0  | 0.0  | 0.0  | 0.0  | 0.0  | 0.0  | 0.0  | 0.0  | 0.0  | 0.0  |
| 157.5° | 0.0  | 0.0  | 0.0  | 0.0  | 0.0  | 0.0  | 0.0  | 0.0  | 0.0  | 0.0  | 0.0  |
| 160°   | 0.0  | 0.0  | 0.0  | 0.0  | 0.0  | 0.0  | 0.0  | 0.0  | 0.0  | 0.0  | 0.0  |
| 162.5° | 0.0  | 0.0  | 0.0  | 0.0  | 0.0  | 0.0  | 0.0  | 0.0  | 0.0  | 0.0  | 0.0  |
| 165°   | 0.0  | 0.0  | 0.0  | 0.0  | 0.0  | 0.0  | 0.0  | 0.0  | 0.0  | 0.0  | 0.0  |
| 167.5° | 0.0  | 0.0  | 0.0  | 0.0  | 0.0  | 0.0  | 0.0  | 0.0  | 0.0  | 0.0  | 0.0  |
| 170°   | 0.0  | 0.0  | 0.0  | 0.0  | 0.0  | 0.0  | 0.0  | 0.0  | 0.0  | 0.0  | 0.0  |
| 172.5° | 0.0  | 0.0  | 0.0  | 0.0  | 0.0  | 0.0  | 0.0  | 0.0  | 0.0  | 0.0  | 0.0  |
| 175°   | 0.0  | 0.0  | 0.0  | 0.0  | 0.0  | 0.0  | 0.0  | 0.0  | 0.0  | 0.0  | 0.0  |
| 177.5° | 0.0  | 0.0  | 0.0  | 0.0  | 0.0  | 0.0  | 0.0  | 0.0  | 0.0  | 0.0  | 0.0  |
| 180°   | 0.0  | 0.0  | 0.0  | 0.0  | 0.0  | 0.0  | 0.0  | 0.0  | 0.0  | 0.0  | 0.0  |





REPORT NUMBER: P320304  
 CATALOG NUMBER: GAN-SAOD-730-U-SLL

**CANDELA DISTRIBUTION (continued):**

|        | 275°    | 280°    | 285°    | 290°    | 295°    | 300°    | 305°    | 310°    | 315°    | 320°    | 325°    |
|--------|---------|---------|---------|---------|---------|---------|---------|---------|---------|---------|---------|
| 0°     | 18725.3 | 18725.3 | 18725.3 | 18725.3 | 18725.3 | 18725.3 | 18725.3 | 18725.3 | 18725.3 | 18725.3 | 18725.3 |
| 2.5°   | 16208.9 | 16240.9 | 16270.4 | 16511.2 | 16749.6 | 17029.7 | 17309.8 | 17523.6 | 17735.0 | 17953.7 | 18172.4 |
| 5°     | 12962.7 | 13002.0 | 13041.4 | 13333.8 | 13623.8 | 14014.5 | 14405.2 | 14741.9 | 15078.5 | 15474.2 | 15869.8 |
| 7.5°   | 9608.4  | 9694.4  | 9777.9  | 10090.0 | 10399.7 | 10819.9 | 11237.6 | 11677.5 | 12114.9 | 12631.0 | 13147.0 |
| 10°    | 7546.6  | 7708.8  | 7868.6  | 8188.0  | 8507.5  | 8922.8  | 9335.6  | 9795.1  | 10254.7 | 10763.4 | 11269.6 |
| 12.5°  | 6109.1  | 6325.3  | 6539.1  | 6922.5  | 7305.8  | 7802.2  | 8296.1  | 8807.3  | 9316.0  | 9763.2  | 10210.4 |
| 15°    | 4826.3  | 5062.2  | 5295.7  | 5701.1  | 6106.6  | 6652.1  | 7195.2  | 7753.1  | 8308.4  | 8844.1  | 9379.8  |
| 17.5°  | 3764.7  | 3958.9  | 4150.5  | 4494.6  | 4836.1  | 5364.5  | 5892.8  | 6477.7  | 7062.5  | 7716.2  | 8367.4  |
| 20°    | 3037.3  | 3118.4  | 3199.5  | 3447.7  | 3693.5  | 4123.5  | 4551.1  | 5148.2  | 5745.4  | 6526.8  | 7308.3  |
| 22.5°  | 2661.4  | 2703.1  | 2742.4  | 2862.9  | 2980.8  | 3258.5  | 3533.7  | 4062.1  | 4587.9  | 5440.7  | 6290.9  |
| 25°    | 2435.3  | 2467.2  | 2499.2  | 2577.8  | 2656.4  | 2789.1  | 2921.8  | 3292.9  | 3664.0  | 4501.9  | 5337.4  |
| 27.5°  | 2231.3  | 2280.5  | 2327.1  | 2364.0  | 2398.4  | 2489.3  | 2577.8  | 2821.1  | 3064.4  | 3845.8  | 4624.8  |
| 30°    | 2083.9  | 2101.1  | 2118.3  | 2174.8  | 2228.9  | 2322.2  | 2415.6  | 2585.2  | 2754.7  | 3415.8  | 4074.3  |
| 32.5°  | 1911.8  | 1936.4  | 1961.0  | 2020.0  | 2079.0  | 2165.0  | 2251.0  | 2388.6  | 2523.7  | 3088.9  | 3651.7  |
| 35°    | 1757.0  | 1781.6  | 1806.2  | 1865.2  | 1921.7  | 2015.1  | 2106.0  | 2221.5  | 2334.5  | 2826.0  | 3317.5  |
| 37.5°  | 1661.2  | 1685.8  | 1710.3  | 1761.9  | 1811.1  | 1904.5  | 1995.4  | 2086.3  | 2174.8  | 2629.4  | 3084.0  |
| 40°    | 1580.1  | 1604.7  | 1629.2  | 1678.4  | 1725.1  | 1816.0  | 1904.5  | 1980.7  | 2056.8  | 2482.0  | 2907.1  |
| 42.5°  | 1508.8  | 1535.9  | 1562.9  | 1612.0  | 1658.7  | 1739.8  | 1820.9  | 1921.7  | 2020.0  | 2354.2  | 2685.9  |
| 45°    | 1449.9  | 1476.9  | 1501.5  | 1555.5  | 1609.6  | 1688.2  | 1766.9  | 1906.9  | 2047.0  | 2287.8  | 2528.7  |
| 47.5°  | 1395.8  | 1425.3  | 1452.3  | 1511.3  | 1570.3  | 1668.6  | 1764.4  | 1882.4  | 1997.9  | 2236.2  | 2474.6  |
| 50°    | 1344.2  | 1378.6  | 1413.0  | 1484.3  | 1553.1  | 1717.7  | 1879.9  | 1897.1  | 1911.8  | 2194.4  | 2474.6  |
| 52.5°  | 1295.0  | 1334.4  | 1373.7  | 1462.1  | 1548.2  | 1739.8  | 1931.5  | 1870.1  | 1806.2  | 2115.8  | 2425.4  |
| 55°    | 1245.9  | 1280.3  | 1312.2  | 1420.4  | 1528.5  | 1668.6  | 1808.6  | 1727.5  | 1644.0  | 1968.4  | 2292.7  |
| 57.5°  | 1179.5  | 1216.4  | 1250.8  | 1366.3  | 1481.8  | 1580.1  | 1675.9  | 1602.2  | 1526.0  | 1801.3  | 2074.0  |
| 60°    | 1110.7  | 1152.5  | 1194.3  | 1341.7  | 1486.7  | 1469.5  | 1449.9  | 1435.1  | 1417.9  | 1614.5  | 1811.1  |
| 62.5°  | 1049.3  | 1093.5  | 1137.8  | 1329.4  | 1521.1  | 1403.2  | 1285.2  | 1297.5  | 1307.3  | 1452.3  | 1597.3  |
| 65°    | 987.9   | 1032.1  | 1073.9  | 1169.7  | 1265.6  | 1218.9  | 1172.2  | 1191.8  | 1209.0  | 1351.6  | 1494.1  |
| 67.5°  | 919.1   | 958.4   | 995.2   | 1027.2  | 1059.1  | 1064.0  | 1069.0  | 1088.6  | 1108.3  | 1277.8  | 1444.9  |
| 70°    | 842.9   | 874.8   | 906.8   | 928.9   | 948.6   | 958.4   | 965.8   | 990.3   | 1014.9  | 1199.2  | 1383.5  |
| 72.5°  | 756.9   | 783.9   | 808.5   | 828.1   | 847.8   | 855.2   | 860.1   | 884.7   | 909.2   | 1105.8  | 1302.4  |
| 75°    | 663.5   | 685.6   | 705.3   | 722.5   | 739.7   | 749.5   | 759.3   | 776.5   | 793.7   | 1007.5  | 1218.9  |
| 77.5°  | 560.3   | 582.4   | 602.1   | 616.8   | 629.1   | 638.9   | 646.3   | 668.4   | 690.5   | 869.9   | 1046.8  |
| 80°    | 437.4   | 464.4   | 489.0   | 501.3   | 511.1   | 513.6   | 513.6   | 533.3   | 552.9   | 680.7   | 806.0   |
| 82.5°  | 309.6   | 339.1   | 366.2   | 376.0   | 385.8   | 385.8   | 385.8   | 407.9   | 430.0   | 516.1   | 599.6   |
| 85°    | 181.8   | 213.8   | 243.3   | 253.1   | 262.9   | 267.9   | 270.3   | 280.1   | 287.5   | 348.9   | 407.9   |
| 87.5°  | 56.5    | 83.6    | 108.1   | 113.0   | 118.0   | 127.8   | 137.6   | 140.1   | 140.1   | 181.8   | 223.6   |
| 90°    | 0.0     | 0.0     | 0.0     | 0.0     | 0.0     | 0.0     | 0.0     | 0.0     | 0.0     | 0.0     | 0.0     |
| 92.5°  | 0.0     | 0.0     | 0.0     | 0.0     | 0.0     | 0.0     | 0.0     | 0.0     | 0.0     | 0.0     | 0.0     |
| 95°    | 0.0     | 0.0     | 0.0     | 0.0     | 0.0     | 0.0     | 0.0     | 0.0     | 0.0     | 0.0     | 0.0     |
| 97.5°  | 0.0     | 0.0     | 0.0     | 0.0     | 0.0     | 0.0     | 0.0     | 0.0     | 0.0     | 0.0     | 0.0     |
| 100°   | 0.0     | 0.0     | 0.0     | 0.0     | 0.0     | 0.0     | 0.0     | 0.0     | 0.0     | 0.0     | 0.0     |
| 102.5° | 0.0     | 0.0     | 0.0     | 0.0     | 0.0     | 0.0     | 0.0     | 0.0     | 0.0     | 0.0     | 0.0     |
| 105°   | 0.0     | 0.0     | 0.0     | 0.0     | 0.0     | 0.0     | 0.0     | 0.0     | 0.0     | 0.0     | 0.0     |
| 107.5° | 0.0     | 0.0     | 0.0     | 0.0     | 0.0     | 0.0     | 0.0     | 0.0     | 0.0     | 0.0     | 0.0     |
| 110°   | 0.0     | 0.0     | 0.0     | 0.0     | 0.0     | 0.0     | 0.0     | 0.0     | 0.0     | 0.0     | 0.0     |



REPORT NUMBER: P320304  
 CATALOG NUMBER: GAN-SA0D-730-U-SLL

**CANDELA DISTRIBUTION (continued):**

|        | 275° | 280° | 285° | 290° | 295° | 300° | 305° | 310° | 315° | 320° | 325° |
|--------|------|------|------|------|------|------|------|------|------|------|------|
| 112.5° | 0.0  | 0.0  | 0.0  | 0.0  | 0.0  | 0.0  | 0.0  | 0.0  | 0.0  | 0.0  | 0.0  |
| 115°   | 0.0  | 0.0  | 0.0  | 0.0  | 0.0  | 0.0  | 0.0  | 0.0  | 0.0  | 0.0  | 0.0  |
| 117.5° | 0.0  | 0.0  | 0.0  | 0.0  | 0.0  | 0.0  | 0.0  | 0.0  | 0.0  | 0.0  | 0.0  |
| 120°   | 0.0  | 0.0  | 0.0  | 0.0  | 0.0  | 0.0  | 0.0  | 0.0  | 0.0  | 0.0  | 0.0  |
| 122.5° | 0.0  | 0.0  | 0.0  | 0.0  | 0.0  | 0.0  | 0.0  | 0.0  | 0.0  | 0.0  | 0.0  |
| 125°   | 0.0  | 0.0  | 0.0  | 0.0  | 0.0  | 0.0  | 0.0  | 0.0  | 0.0  | 0.0  | 0.0  |
| 127.5° | 0.0  | 0.0  | 0.0  | 0.0  | 0.0  | 0.0  | 0.0  | 0.0  | 0.0  | 0.0  | 0.0  |
| 130°   | 0.0  | 0.0  | 0.0  | 0.0  | 0.0  | 0.0  | 0.0  | 0.0  | 0.0  | 0.0  | 0.0  |
| 132.5° | 0.0  | 0.0  | 0.0  | 0.0  | 0.0  | 0.0  | 0.0  | 0.0  | 0.0  | 0.0  | 0.0  |
| 135°   | 0.0  | 0.0  | 0.0  | 0.0  | 0.0  | 0.0  | 0.0  | 0.0  | 0.0  | 0.0  | 0.0  |
| 137.5° | 0.0  | 0.0  | 0.0  | 0.0  | 0.0  | 0.0  | 0.0  | 0.0  | 0.0  | 0.0  | 0.0  |
| 140°   | 0.0  | 0.0  | 0.0  | 0.0  | 0.0  | 0.0  | 0.0  | 0.0  | 0.0  | 0.0  | 0.0  |
| 142.5° | 0.0  | 0.0  | 0.0  | 0.0  | 0.0  | 0.0  | 0.0  | 0.0  | 0.0  | 0.0  | 0.0  |
| 145°   | 0.0  | 0.0  | 0.0  | 0.0  | 0.0  | 0.0  | 0.0  | 0.0  | 0.0  | 0.0  | 0.0  |
| 147.5° | 0.0  | 0.0  | 0.0  | 0.0  | 0.0  | 0.0  | 0.0  | 0.0  | 0.0  | 0.0  | 0.0  |
| 150°   | 0.0  | 0.0  | 0.0  | 0.0  | 0.0  | 0.0  | 0.0  | 0.0  | 0.0  | 0.0  | 0.0  |
| 152.5° | 0.0  | 0.0  | 0.0  | 0.0  | 0.0  | 0.0  | 0.0  | 0.0  | 0.0  | 0.0  | 0.0  |
| 155°   | 0.0  | 0.0  | 0.0  | 0.0  | 0.0  | 0.0  | 0.0  | 0.0  | 0.0  | 0.0  | 0.0  |
| 157.5° | 0.0  | 0.0  | 0.0  | 0.0  | 0.0  | 0.0  | 0.0  | 0.0  | 0.0  | 0.0  | 0.0  |
| 160°   | 0.0  | 0.0  | 0.0  | 0.0  | 0.0  | 0.0  | 0.0  | 0.0  | 0.0  | 0.0  | 0.0  |
| 162.5° | 0.0  | 0.0  | 0.0  | 0.0  | 0.0  | 0.0  | 0.0  | 0.0  | 0.0  | 0.0  | 0.0  |
| 165°   | 0.0  | 0.0  | 0.0  | 0.0  | 0.0  | 0.0  | 0.0  | 0.0  | 0.0  | 0.0  | 0.0  |
| 167.5° | 0.0  | 0.0  | 0.0  | 0.0  | 0.0  | 0.0  | 0.0  | 0.0  | 0.0  | 0.0  | 0.0  |
| 170°   | 0.0  | 0.0  | 0.0  | 0.0  | 0.0  | 0.0  | 0.0  | 0.0  | 0.0  | 0.0  | 0.0  |
| 172.5° | 0.0  | 0.0  | 0.0  | 0.0  | 0.0  | 0.0  | 0.0  | 0.0  | 0.0  | 0.0  | 0.0  |
| 175°   | 0.0  | 0.0  | 0.0  | 0.0  | 0.0  | 0.0  | 0.0  | 0.0  | 0.0  | 0.0  | 0.0  |
| 177.5° | 0.0  | 0.0  | 0.0  | 0.0  | 0.0  | 0.0  | 0.0  | 0.0  | 0.0  | 0.0  | 0.0  |
| 180°   | 0.0  | 0.0  | 0.0  | 0.0  | 0.0  | 0.0  | 0.0  | 0.0  | 0.0  | 0.0  | 0.0  |



REPORT NUMBER: P320304

CATALOG NUMBER: GAN-SAOD-730-U-SLL

**CANDELA DISTRIBUTION (continued):**

|        | 330°    | 335°    | 340°    | 345°    | 350°    | 355°    | 360°    |
|--------|---------|---------|---------|---------|---------|---------|---------|
| 0°     | 18725.3 | 18725.3 | 18725.3 | 18725.3 | 18725.3 | 18725.3 | 18725.3 |
| 2.5°   | 18423.0 | 18673.7 | 18966.1 | 19256.1 | 19504.3 | 19752.5 | 19958.9 |
| 5°     | 16373.6 | 16877.3 | 17494.1 | 18108.5 | 18656.5 | 19204.5 | 19840.9 |
| 7.5°   | 13798.2 | 14449.4 | 15248.1 | 16046.7 | 16820.8 | 17592.4 | 18570.5 |
| 10°    | 11933.1 | 12594.1 | 13439.5 | 14282.3 | 15152.3 | 16019.7 | 17125.5 |
| 12.5°  | 10748.6 | 11284.3 | 12102.6 | 12920.9 | 13943.2 | 14963.0 | 16027.1 |
| 15°    | 9967.2  | 10552.0 | 11348.2 | 12144.4 | 13262.5 | 14380.6 | 15604.4 |
| 17.5°  | 9134.1  | 9898.4  | 10918.2 | 11938.0 | 13262.5 | 14584.6 | 16027.1 |
| 20°    | 8261.7  | 9212.7  | 10534.8 | 11856.9 | 13641.0 | 15422.6 | 17263.1 |
| 22.5°  | 7391.8  | 8492.7  | 10188.3 | 11881.5 | 14213.5 | 16543.1 | 19027.6 |
| 25°    | 6607.9  | 7878.4  | 9977.0  | 12073.1 | 15046.6 | 18017.6 | 21099.1 |
| 27.5°  | 6013.2  | 7399.2  | 9891.0  | 12380.3 | 16103.3 | 19826.2 | 23352.6 |
| 30°    | 5484.9  | 6895.4  | 9787.8  | 12680.1 | 17120.6 | 21558.7 | 25114.5 |
| 32.5°  | 5027.8  | 6404.0  | 9588.7  | 12771.0 | 17830.8 | 22890.6 | 26606.1 |
| 35°    | 4669.0  | 6020.6  | 9254.5  | 12488.4 | 18275.6 | 24062.7 | 28159.2 |
| 37.5°  | 4359.4  | 5634.8  | 8873.6  | 12112.5 | 18671.2 | 25230.0 | 29906.4 |
| 40°    | 4064.5  | 5221.9  | 8546.8  | 11869.2 | 19216.8 | 26564.4 | 31751.9 |
| 42.5°  | 3784.4  | 4882.8  | 8283.9  | 11684.9 | 19723.0 | 27758.7 | 33366.4 |
| 45°    | 3575.5  | 4622.3  | 8050.4  | 11476.0 | 20049.8 | 28623.7 | 34582.8 |
| 47.5°  | 3472.3  | 4467.5  | 7925.1  | 11380.2 | 20376.7 | 29370.7 | 35592.8 |
| 50°    | 3457.5  | 4440.5  | 8067.6  | 11694.7 | 21084.4 | 30471.6 | 36747.8 |
| 52.5°  | 3455.1  | 4484.7  | 8478.0  | 12471.2 | 22399.1 | 32324.5 | 37998.6 |
| 55°    | 3403.5  | 4511.8  | 8967.0  | 13419.8 | 24163.5 | 34904.7 | 40247.1 |
| 57.5°  | 3246.2  | 4418.4  | 9470.8  | 14520.7 | 26028.7 | 37534.1 | 42780.7 |
| 60°    | 3002.9  | 4192.3  | 9886.1  | 15577.4 | 27281.9 | 38984.0 | 43756.2 |
| 62.5°  | 2698.2  | 3796.7  | 10023.7 | 16248.2 | 27247.5 | 38246.8 | 42773.3 |
| 65°    | 2437.7  | 3381.4  | 9571.5  | 15759.2 | 25868.9 | 35976.2 | 40829.5 |
| 67.5°  | 2206.7  | 2966.1  | 8441.1  | 13913.7 | 23389.4 | 32862.6 | 38357.4 |
| 70°    | 2039.6  | 2693.3  | 6983.9  | 11274.5 | 20285.7 | 29294.5 | 35494.5 |
| 72.5°  | 1934.0  | 2563.1  | 5693.8  | 8822.0  | 16462.0 | 24099.6 | 30361.0 |
| 75°    | 1789.0  | 2359.1  | 4467.5  | 6573.5  | 12599.0 | 18624.5 | 22932.3 |
| 77.5°  | 1518.7  | 1988.0  | 3366.6  | 4745.2  | 9244.7  | 13741.7 | 15948.4 |
| 80°    | 1172.2  | 1535.9  | 2314.9  | 3093.9  | 6362.2  | 9630.5  | 10873.9 |
| 82.5°  | 835.5   | 1071.4  | 1403.2  | 1734.9  | 4226.7  | 6716.0  | 6819.3  |
| 85°    | 516.1   | 624.2   | 803.6   | 983.0   | 2796.5  | 4610.1  | 3840.9  |
| 87.5°  | 277.7   | 331.7   | 425.1   | 516.1   | 894.5   | 1272.9  | 732.3   |
| 90°    | 0.0     | 0.0     | 0.0     | 0.0     | 0.0     | 0.0     | 0.0     |
| 92.5°  | 0.0     | 0.0     | 0.0     | 0.0     | 0.0     | 0.0     | 0.0     |
| 95°    | 0.0     | 0.0     | 0.0     | 0.0     | 0.0     | 0.0     | 0.0     |
| 97.5°  | 0.0     | 0.0     | 0.0     | 0.0     | 0.0     | 0.0     | 0.0     |
| 100°   | 0.0     | 0.0     | 0.0     | 0.0     | 0.0     | 0.0     | 0.0     |
| 102.5° | 0.0     | 0.0     | 0.0     | 0.0     | 0.0     | 0.0     | 0.0     |
| 105°   | 0.0     | 0.0     | 0.0     | 0.0     | 0.0     | 0.0     | 0.0     |
| 107.5° | 0.0     | 0.0     | 0.0     | 0.0     | 0.0     | 0.0     | 0.0     |
| 110°   | 0.0     | 0.0     | 0.0     | 0.0     | 0.0     | 0.0     | 0.0     |



REPORT NUMBER: P320304  
CATALOG NUMBER: GAN-SA0D-730-U-SLL

**CANDELA DISTRIBUTION (continued):**

|        | 330° | 335° | 340° | 345° | 350° | 355° | 360° |
|--------|------|------|------|------|------|------|------|
| 112.5° | 0.0  | 0.0  | 0.0  | 0.0  | 0.0  | 0.0  | 0.0  |
| 115°   | 0.0  | 0.0  | 0.0  | 0.0  | 0.0  | 0.0  | 0.0  |
| 117.5° | 0.0  | 0.0  | 0.0  | 0.0  | 0.0  | 0.0  | 0.0  |
| 120°   | 0.0  | 0.0  | 0.0  | 0.0  | 0.0  | 0.0  | 0.0  |
| 122.5° | 0.0  | 0.0  | 0.0  | 0.0  | 0.0  | 0.0  | 0.0  |
| 125°   | 0.0  | 0.0  | 0.0  | 0.0  | 0.0  | 0.0  | 0.0  |
| 127.5° | 0.0  | 0.0  | 0.0  | 0.0  | 0.0  | 0.0  | 0.0  |
| 130°   | 0.0  | 0.0  | 0.0  | 0.0  | 0.0  | 0.0  | 0.0  |
| 132.5° | 0.0  | 0.0  | 0.0  | 0.0  | 0.0  | 0.0  | 0.0  |
| 135°   | 0.0  | 0.0  | 0.0  | 0.0  | 0.0  | 0.0  | 0.0  |
| 137.5° | 0.0  | 0.0  | 0.0  | 0.0  | 0.0  | 0.0  | 0.0  |
| 140°   | 0.0  | 0.0  | 0.0  | 0.0  | 0.0  | 0.0  | 0.0  |
| 142.5° | 0.0  | 0.0  | 0.0  | 0.0  | 0.0  | 0.0  | 0.0  |
| 145°   | 0.0  | 0.0  | 0.0  | 0.0  | 0.0  | 0.0  | 0.0  |
| 147.5° | 0.0  | 0.0  | 0.0  | 0.0  | 0.0  | 0.0  | 0.0  |
| 150°   | 0.0  | 0.0  | 0.0  | 0.0  | 0.0  | 0.0  | 0.0  |
| 152.5° | 0.0  | 0.0  | 0.0  | 0.0  | 0.0  | 0.0  | 0.0  |
| 155°   | 0.0  | 0.0  | 0.0  | 0.0  | 0.0  | 0.0  | 0.0  |
| 157.5° | 0.0  | 0.0  | 0.0  | 0.0  | 0.0  | 0.0  | 0.0  |
| 160°   | 0.0  | 0.0  | 0.0  | 0.0  | 0.0  | 0.0  | 0.0  |
| 162.5° | 0.0  | 0.0  | 0.0  | 0.0  | 0.0  | 0.0  | 0.0  |
| 165°   | 0.0  | 0.0  | 0.0  | 0.0  | 0.0  | 0.0  | 0.0  |
| 167.5° | 0.0  | 0.0  | 0.0  | 0.0  | 0.0  | 0.0  | 0.0  |
| 170°   | 0.0  | 0.0  | 0.0  | 0.0  | 0.0  | 0.0  | 0.0  |
| 172.5° | 0.0  | 0.0  | 0.0  | 0.0  | 0.0  | 0.0  | 0.0  |
| 175°   | 0.0  | 0.0  | 0.0  | 0.0  | 0.0  | 0.0  | 0.0  |
| 177.5° | 0.0  | 0.0  | 0.0  | 0.0  | 0.0  | 0.0  | 0.0  |
| 180°   | 0.0  | 0.0  | 0.0  | 0.0  | 0.0  | 0.0  | 0.0  |

(END OF REPORT)