

Scaled data based on original data using
LM-79-08 Approved Method: Electrical and Photometric Measurements of Solid-
State Lighting Products

Test Report Prepared for
Cooper Lighting Solutions
(formerly Eaton)

Brand: STREETWORKS

Report Number: P320366

Luminaire Tested: **GAN-SA2C-750-U-SLL**

Issue Date: 3/3/2020

Test Information

Test Method: LM-79-08
Report Number: P320366
TEST IS SCALED FROM IESNA LM-79-08 TEST DATA (G2-1903-205-26)
Test Lab: INNOVATION CENTER
Issue Date: 3/3/2020
Manufacturer: COOPER LIGHTING SOLUTIONS (FORMERLY EATON)
Product Line: STREETWORKS
Catalog Number: GAN-SA2C-750-U-SLL
Description: GALLEON AREA AND ROADWAY LUMINAIRE
(2) 70 CRI, 5000K, 1050mA LIGHTSQUARES WITH 16 LEDS EACH AND SPILL LIGHT
ELIMINATOR LEFT OPTICS
Light Source: -
Ballast/Driver: ELECTRONIC DRIVER

Summary

Lumens per Lamp: N/A
Luminaire Lumens: 12718 lumens
Efficiency: N/A
Efficacy: 112.5 lumens/watt
Luminous Opening: Rectangular (W 0.5' x L: 1' x H: 0')
IES Classification: Type III - Medium
BUG Rating: B2 - U0 - G3


Input Watts (W): 113
Input Voltage (V): NR
Input Current (Ain): NR
Voltage Rise (V): NR
Power Factor: NR
Total Harmonic Distortion (THDi): NR
Frequency (hertz): 60
Stabilization Time: NR
Operation Time: NR
Ambient Temperature (°C): NR
Test Distance: 24 FT



REPORT NUMBER: P320366
 CATALOG NUMBER: GAN-SA2C-750-U-SLL

Iso-Footcandle Lines of Horizontal Illumination


✕ Max cd
 - - - 1/2 Max cd



Based on 25 foot mounting height. Maximum calculated value = 7.8 fc
 Type III - Medium - N/A

REPORT NUMBER: P320366
CATALOG NUMBER: GAN-SA2C-750-U-SLL

Luminous Intensity Polar Plot



— Vertical Plane Through 75-Deg Lateral - - - Horizontal Cone Through 67.5-Deg Vertical

REPORT NUMBER: P320366
 CATALOG NUMBER: GAN-SA2C-750-U-SLL

FLUX DISTRIBUTION:

		Downward	Upward	Total
House Side	Lumens	2239.9	0.0	2239.9
	% Fixture	17.6	0.0	17.6
Street Side	Lumens	10478.0	0.0	10478.0
	% Fixture	82.4	0.0	82.4
Total	Lumens	12718.0	0.0	12718.0
	% Fixture	100.0	0.0	100.0

ZONAL LUMENS:

Zone	Lumens	% Fixture
0°-10°	299.0	2.4
10°-20°	621.2	4.9
20°-30°	883.5	6.9
30°-40°	1273.1	10.0
40°-50°	1794.2	14.1
50°-60°	2494.2	19.6
60°-70°	3016.3	23.7
70°-80°	1854.0	14.6
80°-90°	482.5	3.8
90°-100°	0.0	0.0
100°-110°	0.0	0.0
110°-120°	0.0	0.0
120°-130°	0.0	0.0
130°-140°	0.0	0.0
140°-150°	0.0	0.0
150°-160°	0.0	0.0
160°-170°	0.0	0.0
170°-180°	0.0	0.0
0°-90°	12718.0	100.0
0°-180°	12718.0	100.0

Coefficient of Utilization




REPORT NUMBER: P320366
 CATALOG NUMBER: GAN-SA2C-750-U-SLL

LUMINAIRE CLASSIFICATION SYSTEM LUMEN TABLE AND BUG RATING:

Zone	Lumens	% Fixture	Zone Rating/Lumen Limit		
			B	U	G
FL (0°-30°)	1262.8	9.9			
FM (30°-60°)	4544.7	35.7			
FH (60°-80°)	4242.3	33.4			G2/5000
FVH (80°-90°)	428.2	3.4			G3/500
BL (0°-30°)	541.0	4.3	B2/1000		
BM (30°-60°)	1016.8	8.0	B2/2500		
BH (60°-80°)	628.0	4.9	B2/1000		G2/1000
BVH (80°-90°)	54.2	0.4			G1/100
UL (90°-100°)	0.0	0.0		U0/0	
UH (100°-180°)	0.0	0.0		U0/0	

BUG Rating: B2-U0-G3
 Type III Medium





REPORT NUMBER: P320366

CATALOG NUMBER: GAN-SA2C-750-U-SLL

CANDELA DISTRIBUTION (FULL):

	0°	5°	10°	15°	20°	25°	30°	35°	40°	45°	50°
0°	3874.6	3874.6	3874.6	3874.6	3874.6	3874.6	3874.6	3874.6	3874.6	3874.6	3874.6
2.5°	4129.9	4184.3	4221.9	4259.0	4288.0	4316.5	4358.2	4399.9	4408.0	4415.6	4399.3
5°	4105.4	4238.2	4351.0	4463.4	4567.7	4671.9	4734.4	4797.0	4809.7	4822.4	4783.2
7.5°	3842.6	4038.3	4234.1	4429.9	4609.3	4788.8	4898.2	5007.0	5031.9	5056.3	4992.2
10°	3543.6	3771.4	4011.9	4252.4	4488.8	4725.3	4883.4	5041.6	5073.1	5104.6	5024.8
12.5°	3316.3	3564.9	3821.7	4078.5	4328.2	4577.3	4741.0	4904.8	4943.9	4983.1	4925.1
15°	3228.8	3501.4	3742.9	3984.4	4202.1	4419.2	4553.4	4687.1	4703.4	4719.2	4710.0
17.5°	3316.3	3616.8	3835.4	4053.6	4172.1	4290.0	4343.9	4397.3	4415.1	4432.4	4455.8
20°	3572.1	3896.5	4050.5	4204.1	4199.0	4193.4	4167.5	4141.0	4136.5	4131.9	4198.0
22.5°	3937.1	4313.9	4375.4	4436.5	4293.6	4150.7	4063.8	3976.3	3959.0	3941.2	4011.4
25°	4365.8	4767.0	4755.8	4744.1	4472.1	4199.5	4033.8	3868.0	3848.7	3829.3	3889.3
27.5°	4832.1	5215.5	5142.2	5069.0	4699.3	4329.7	4089.2	3848.7	3829.3	3810.0	3862.9
30°	5196.6	5544.4	5427.0	5309.5	4891.0	4472.6	4186.8	3901.0	3869.5	3837.5	3902.6
32.5°	5505.3	5801.2	5643.6	5486.0	5046.6	4607.3	4298.2	3989.0	3939.7	3890.4	3977.3
35°	5826.6	6057.5	5835.8	5613.6	5185.5	4756.8	4429.9	4102.4	4041.9	3981.4	4100.9
37.5°	6188.2	6379.9	6061.6	5742.7	5341.6	4940.4	4627.1	4313.4	4251.4	4189.3	4341.9
40°	6570.0	6729.7	6305.1	5880.5	5512.4	5144.3	4900.2	4655.6	4596.6	4537.1	4722.2
42.5°	6904.1	7020.5	6531.9	6043.3	5718.3	5392.9	5221.0	5048.7	5048.2	5047.1	5234.8
45°	7155.8	7257.0	6721.1	6184.6	5919.2	5653.3	5563.8	5474.3	5546.0	5617.7	5787.5
47.5°	7364.8	7433.4	6879.7	6325.5	6149.0	5972.6	5985.8	5999.0	6145.0	6290.9	6400.2
50°	7603.8	7548.3	7023.6	6498.3	6443.9	6389.5	6508.5	6627.0	6794.8	6962.1	7036.3
52.5°	7862.6	7715.6	7218.9	6721.6	6782.6	6843.6	7085.6	7327.7	7497.0	7666.3	7694.3
55°	8327.8	8102.6	7577.8	7052.6	7170.0	7287.0	7642.4	7997.3	8129.5	8261.7	8271.9
57.5°	8852.1	8652.3	8080.7	7509.2	7635.3	7761.4	8171.7	8581.6	8724.5	8866.8	8847.0
60°	9053.9	9063.6	8558.2	8052.2	8179.4	8306.5	8706.2	9105.8	9270.1	9433.8	9390.1
62.5°	8850.6	9089.0	8819.0	8548.5	8663.9	8778.9	9170.4	9561.9	9730.2	9898.5	9822.3
65°	8448.4	8684.8	8805.8	8926.8	8965.0	9003.1	9368.7	9733.8	9862.9	9991.6	9952.9
67.5°	7936.8	8128.0	8574.5	9020.4	8943.6	8866.8	9038.2	9209.5	9342.3	9475.0	9453.1
70°	7344.4	7572.2	8167.7	8763.1	8385.8	8008.0	7937.3	7866.7	8010.0	8152.9	8064.5
72.5°	6282.2	6626.0	7261.1	7895.6	7200.5	6505.5	6263.9	6022.4	6203.9	6385.5	6244.6
75°	4745.1	5201.2	5902.9	6604.1	5774.8	4945.5	4623.1	4300.7	4456.8	4612.9	4516.3
77.5°	3300.0	3872.1	4563.1	5254.1	4411.0	3567.5	3328.0	3088.0	3134.8	3181.0	3164.8
80°	2250.0	2626.3	3108.3	3589.9	3028.5	2467.1	2485.9	2504.3	2482.4	2460.0	2492.6
82.5°	1411.0	1675.9	2048.1	2419.8	2121.9	1823.9	1994.8	2165.6	2081.7	1997.3	2028.8
85°	794.8	956.4	1320.5	1684.1	1569.7	1454.8	1554.9	1654.6	1524.4	1394.2	1451.7
87.5°	151.5	252.2	730.7	1208.7	1097.3	985.9	856.8	727.6	555.3	382.9	559.3
90°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
92.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
95°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
97.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
100°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
102.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
105°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
107.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
110°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0



REPORT NUMBER: P320366
 CATALOG NUMBER: GAN-SA2C-750-U-SLL

CANDELA DISTRIBUTION (continued):

	0°	5°	10°	15°	20°	25°	30°	35°	40°	45°	50°
112.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
115°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
117.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
120°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
122.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
125°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
127.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
130°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
132.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
135°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
137.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
140°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
142.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
145°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
147.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
150°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
152.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
155°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
157.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
160°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
162.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
165°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
167.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
170°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
172.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
175°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
177.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
180°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0



REPORT NUMBER: P320366

CATALOG NUMBER: GAN-SA2C-750-U-SLL

CANDELA DISTRIBUTION (continued):

	55°	60°	65°	70°	75°	80°	85°	90°	95°	100°	105°
0°	3874.6	3874.6	3874.6	3874.6	3874.6	3874.6	3874.6	3874.6	3874.6	3874.6	3874.6
2.5°	4383.1	4374.4	4365.8	4334.8	4303.2	4256.5	4217.8	4150.7	4114.1	4058.7	4003.2
5°	4743.6	4688.7	4633.8	4539.2	4444.1	4338.3	4216.8	4082.1	3980.4	3848.2	3716.0
7.5°	4928.2	4800.0	4671.4	4489.9	4307.8	4144.1	3951.9	3772.9	3620.4	3448.5	3276.6
10°	4944.9	4752.7	4560.0	4324.1	4087.7	3888.8	3667.6	3468.8	3285.8	3088.5	2890.7
12.5°	4866.6	4662.2	4457.3	4197.5	3937.1	3711.4	3473.4	3250.7	3047.8	2830.7	2613.1
15°	4700.9	4537.7	4373.9	4130.4	3886.8	3659.0	3428.2	3164.3	2934.9	2712.7	2490.0
17.5°	4478.7	4401.4	4323.6	4147.7	3971.2	3773.9	3550.2	3240.5	2972.1	2730.5	2489.0
20°	4263.6	4292.1	4320.0	4249.9	4179.7	4021.5	3826.3	3478.5	3135.8	2820.0	2503.7
22.5°	4081.0	4217.8	4354.1	4408.5	4462.4	4367.3	4214.8	3812.6	3359.0	2946.6	2534.3
25°	3948.8	4175.6	4402.4	4583.4	4763.9	4721.7	4604.3	4218.3	3654.9	3129.2	2602.9
27.5°	3915.8	4193.9	4472.1	4752.7	5032.9	5072.1	5039.5	4646.0	4007.8	3356.0	2703.6
30°	3967.6	4249.3	4530.5	4872.2	5213.4	5369.5	5413.3	5002.4	4411.0	3620.4	2829.2
32.5°	4064.3	4340.4	4616.5	4988.7	5360.4	5596.3	5735.6	5328.3	4692.2	3819.7	2946.6
35°	4220.4	4478.7	4737.0	5124.4	5511.9	5817.0	6071.2	5664.9	4941.9	3959.0	2975.6
37.5°	4493.9	4716.1	4938.3	5296.3	5653.8	6049.4	6431.2	6035.6	5211.9	4093.2	2974.1
40°	4907.3	5064.4	5221.0	5523.6	5825.6	6323.4	6839.0	6449.0	5510.4	4238.7	2967.0
42.5°	5422.4	5503.3	5583.6	5823.1	6062.6	6609.7	7209.2	6853.3	5795.1	4373.9	2952.7
45°	5956.8	5978.2	5999.5	6150.5	6301.1	6836.5	7461.4	7156.8	6043.8	4491.4	2938.5
47.5°	6509.0	6435.8	6362.6	6422.6	6482.6	7010.4	7641.4	7387.2	6293.4	4621.6	2949.2
50°	7110.5	6906.6	6702.7	6671.2	6639.7	7184.3	7853.4	7680.0	6593.4	4811.2	3029.0
52.5°	7721.7	7385.6	7049.5	6925.0	6799.9	7391.7	8134.6	8044.6	7021.6	5105.1	3188.2
55°	8282.1	7854.5	7426.8	7259.0	7091.2	7709.0	8477.8	8580.0	7570.2	5480.9	3391.0
57.5°	8826.7	8342.1	7857.5	7701.9	7546.3	8175.3	8912.6	9060.6	8124.5	5841.4	3557.8
60°	9346.3	8866.8	8386.8	8262.3	8137.2	8755.0	9382.4	9274.6	8410.2	6010.2	3609.7
62.5°	9746.0	9364.6	8983.3	8917.7	8851.6	9341.2	9743.4	9191.2	8228.7	5843.9	3459.2
65°	9914.3	9697.2	9479.5	9541.1	9602.1	9784.6	9833.4	8947.2	7658.2	5378.2	3098.2
67.5°	9430.7	9475.0	9519.2	9777.5	10035.3	9909.7	9566.0	8466.1	6846.1	4718.2	2590.2
70°	7975.5	8240.9	8505.8	9117.0	9727.7	9449.0	8849.5	7602.8	5868.8	3958.0	2046.6
72.5°	6103.3	6401.7	6699.7	7606.8	8513.4	8256.7	7522.4	6244.6	4705.5	3160.7	1615.4
75°	4419.2	4756.3	5092.9	6093.6	7094.3	6737.8	5626.8	4471.0	3574.1	2412.7	1250.9
77.5°	3148.0	3373.7	3599.5	4588.0	5576.0	4995.3	3745.4	3008.7	2473.7	1677.0	879.7
80°	2525.1	2455.9	2386.8	2937.5	3488.2	3391.5	2477.3	1932.2	1712.0	1123.7	535.4
82.5°	2059.8	1891.0	1722.2	1981.5	2240.9	2226.6	1719.2	1417.6	1274.2	781.0	287.8
85°	1508.7	1441.0	1373.4	1602.7	1832.0	1636.3	1164.4	901.0	993.6	575.1	156.6
87.5°	735.8	840.5	944.8	1215.3	1485.3	1115.1	353.4	174.9	242.0	159.2	75.8
90°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
92.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
95°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
97.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
100°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
102.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
105°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
107.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
110°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0



REPORT NUMBER: P320366
 CATALOG NUMBER: GAN-SA2C-750-U-SLL

CANDELA DISTRIBUTION (continued):

	55°	60°	65°	70°	75°	80°	85°	90°	95°	100°	105°
112.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
115°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
117.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
120°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
122.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
125°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
127.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
130°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
132.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
135°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
137.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
140°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
142.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
145°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
147.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
150°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
152.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
155°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
157.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
160°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
162.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
165°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
167.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
170°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
172.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
175°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
177.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
180°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0



REPORT NUMBER: P320366
 CATALOG NUMBER: GAN-SA2C-750-U-SLL

CANDELA DISTRIBUTION (continued):

	110°	115°	120°	125°	130°	135°	140°	145°	150°	155°	160°
0°	3874.6	3874.6	3874.6	3874.6	3874.6	3874.6	3874.6	3874.6	3874.6	3874.6	3874.6
2.5°	3962.1	3920.4	3873.1	3825.8	3771.9	3717.5	3685.4	3652.9	3617.8	3582.7	3543.1
5°	3628.5	3541.0	3441.9	3342.7	3244.6	3146.5	3093.6	3040.7	2984.8	2928.3	2879.5
7.5°	3149.5	3021.9	2884.6	2746.8	2624.8	2502.2	2426.5	2350.2	2281.0	2211.4	2152.9
10°	2728.0	2565.3	2427.5	2289.2	2197.1	2105.1	2035.4	1965.8	1898.7	1831.0	1766.5
12.5°	2450.4	2287.6	2200.2	2112.7	2036.5	1960.2	1879.8	1799.0	1707.0	1614.4	1546.8
15°	2342.0	2194.1	2097.0	1999.3	1897.1	1794.4	1695.8	1597.1	1488.3	1379.5	1302.7
17.5°	2295.3	2101.5	1965.8	1829.5	1694.8	1560.0	1445.6	1331.2	1212.2	1093.2	1015.4
20°	2245.9	1988.1	1806.1	1623.6	1450.7	1277.8	1148.1	1018.5	912.2	805.9	746.4
22.5°	2201.2	1867.6	1639.3	1410.5	1206.1	1001.7	874.6	747.0	681.9	616.8	592.9
25°	2182.9	1762.4	1481.7	1201.0	985.4	769.3	678.8	588.3	563.4	538.0	525.8
27.5°	2185.9	1668.3	1349.0	1029.2	834.9	640.7	578.6	516.6	501.4	485.6	478.0
30°	2197.6	1566.1	1223.9	881.7	721.5	561.4	521.2	480.5	464.2	448.0	438.3
32.5°	2210.9	1474.6	1127.3	779.5	648.8	517.6	484.6	451.0	435.3	419.5	409.8
35°	2188.0	1399.8	1061.2	722.5	602.0	481.0	453.1	424.6	407.3	390.0	380.8
37.5°	2149.3	1324.6	1009.8	694.6	571.5	448.0	427.6	406.8	389.0	370.7	362.0
40°	2114.2	1261.0	971.7	681.9	554.7	427.1	409.8	392.5	374.2	355.4	345.3
42.5°	2085.8	1218.3	934.1	649.8	539.5	428.6	404.2	379.3	361.5	343.7	332.5
45°	2064.4	1190.3	904.6	618.8	525.3	431.7	400.7	369.7	351.9	333.6	320.3
47.5°	2062.4	1175.6	883.7	591.9	498.3	404.2	391.5	378.8	352.9	326.4	311.2
50°	2090.4	1151.7	859.3	566.4	472.4	378.3	395.6	412.4	368.1	323.4	304.1
52.5°	2148.8	1109.5	820.7	531.9	440.8	349.3	376.3	402.7	364.6	325.9	301.0
55°	2219.5	1047.5	762.2	476.4	399.2	321.4	345.3	368.6	344.7	320.3	290.3
57.5°	2263.7	969.2	688.5	407.8	352.4	297.0	310.7	323.9	314.2	304.6	274.1
60°	2237.3	864.9	605.6	345.8	311.2	276.6	274.1	271.0	285.3	299.5	264.4
62.5°	2108.1	757.1	532.4	307.6	281.7	255.3	249.7	243.6	267.0	289.8	252.7
65°	1890.0	681.9	486.1	290.3	261.4	232.4	226.3	220.2	227.3	234.4	217.1
67.5°	1612.9	635.6	459.7	283.7	248.6	213.1	205.9	198.8	197.3	195.8	189.7
70°	1327.1	607.1	442.4	277.6	234.9	191.7	185.1	178.5	176.4	173.9	169.3
72.5°	1109.5	603.6	440.3	277.1	223.7	170.3	164.2	158.1	155.6	152.5	149.0
75°	908.6	566.4	418.0	269.5	208.5	146.9	141.4	135.8	133.7	131.2	128.1
77.5°	674.2	468.8	351.4	233.9	178.5	123.1	117.5	111.4	110.8	109.8	107.3
80°	437.3	339.2	251.2	163.2	130.2	96.6	92.0	86.9	87.5	88.0	85.9
82.5°	243.1	197.8	153.6	109.3	89.0	68.6	66.6	64.1	65.6	66.6	64.1
85°	128.1	99.7	82.4	65.1	51.4	37.6	37.6	37.1	39.2	41.2	39.2
87.5°	55.4	35.1	30.0	24.4	13.7	2.5	3.1	3.1	4.1	5.1	4.6
90°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
92.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
95°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
97.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
100°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
102.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
105°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
107.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
110°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0



REPORT NUMBER: P320366
 CATALOG NUMBER: GAN-SA2C-750-U-SLL

CANDELA DISTRIBUTION (continued):

	110°	115°	120°	125°	130°	135°	140°	145°	150°	155°	160°
112.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
115°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
117.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
120°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
122.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
125°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
127.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
130°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
132.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
135°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
137.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
140°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
142.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
145°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
147.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
150°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
152.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
155°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
157.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
160°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
162.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
165°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
167.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
170°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
172.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
175°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
177.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
180°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0



REPORT NUMBER: P320366
 CATALOG NUMBER: GAN-SA2C-750-U-SLL

CANDELA DISTRIBUTION (continued):

	165°	170°	175°	180°	185°	190°	195°	200°	205°	210°	215°
0°	3874.6	3874.6	3874.6	3874.6	3874.6	3874.6	3874.6	3874.6	3874.6	3874.6	3874.6
2.5°	3502.9	3465.8	3428.2	3387.0	3394.6	3363.1	3331.5	3311.7	3291.9	3285.8	3279.7
5°	2830.7	2788.5	2745.8	2707.6	2740.7	2718.3	2695.9	2692.9	2689.3	2689.3	2688.8
7.5°	2094.4	2049.2	2003.4	1971.9	2004.4	2000.4	1996.3	2018.1	2040.0	2057.8	2075.1
10°	1701.9	1647.0	1591.5	1544.8	1536.6	1513.2	1489.3	1494.4	1499.0	1518.3	1537.6
12.5°	1479.2	1413.6	1348.0	1293.1	1268.1	1229.5	1190.3	1165.9	1141.5	1144.1	1146.1
15°	1225.4	1161.9	1097.8	1050.5	1034.8	1004.8	974.8	944.2	913.2	900.5	887.3
17.5°	937.1	886.3	834.9	803.4	803.4	794.8	786.1	770.9	755.1	742.4	729.2
20°	687.0	660.0	632.5	619.3	623.4	623.9	623.9	631.5	639.2	635.1	631.0
22.5°	568.5	558.8	549.2	543.6	545.6	546.1	546.6	553.7	560.3	565.4	570.0
25°	513.1	507.0	500.9	498.8	503.4	503.9	503.9	508.5	513.1	518.1	523.2
27.5°	469.8	467.3	464.7	461.2	465.8	465.8	465.3	470.3	474.9	479.5	483.6
30°	428.6	429.7	430.2	429.2	432.2	434.2	435.8	439.3	442.4	445.9	449.5
32.5°	399.7	398.1	396.6	395.6	402.2	405.8	409.3	412.9	415.9	417.5	419.0
35°	371.7	368.1	364.6	362.0	368.1	372.7	377.3	383.9	390.0	391.0	392.0
37.5°	352.9	348.3	343.7	340.7	343.2	345.3	347.3	354.4	361.5	365.6	369.2
40°	335.1	330.5	325.9	323.4	324.9	325.4	325.9	329.5	332.5	340.2	347.3
42.5°	320.8	315.3	309.7	306.6	307.6	308.6	309.2	308.6	308.1	315.3	322.4
45°	306.6	300.5	294.4	290.8	291.4	291.4	291.4	290.3	288.8	292.4	295.9
47.5°	295.4	288.3	281.2	277.6	276.6	275.6	274.6	274.1	273.1	275.6	277.6
50°	284.2	276.6	268.5	264.4	261.9	260.8	259.8	259.3	258.3	260.8	262.9
52.5°	275.6	266.4	257.3	250.7	248.1	246.6	245.1	245.6	245.6	246.6	247.1
55°	260.3	252.2	243.6	239.0	234.4	233.4	232.4	233.9	234.9	234.9	234.9
57.5°	243.6	235.9	227.8	224.7	220.7	220.7	220.2	222.2	223.7	224.7	225.8
60°	228.8	220.2	211.5	209.0	207.5	207.0	206.4	209.0	211.0	213.1	215.1
62.5°	215.1	205.9	196.8	193.7	193.2	193.7	193.7	196.3	198.3	200.3	202.4
65°	199.8	190.7	181.0	178.0	179.0	180.5	182.0	184.1	185.6	187.6	189.7
67.5°	183.1	175.4	167.3	164.2	164.7	166.8	168.8	170.3	171.4	173.4	175.4
70°	164.7	158.1	151.5	149.5	149.0	151.5	153.6	154.6	155.6	158.1	160.2
72.5°	144.9	139.3	133.7	132.2	132.7	134.2	135.8	137.3	138.3	140.8	142.9
75°	124.6	119.5	114.4	113.4	114.4	115.9	117.5	118.5	119.5	122.5	125.1
77.5°	104.7	99.2	93.1	92.5	94.1	95.6	96.6	98.1	99.7	103.7	107.8
80°	83.9	77.8	71.2	70.7	72.2	73.7	75.3	76.8	78.3	83.4	88.0
82.5°	61.5	54.4	47.3	46.3	51.4	52.9	54.4	56.9	59.0	63.6	68.1
85°	37.1	30.0	22.9	22.4	26.9	29.5	32.0	35.1	37.6	41.7	45.8
87.5°	4.1	2.0	0.0	0.0	0.5	2.5	4.6	7.1	9.7	13.7	17.3
90°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
92.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
95°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
97.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
100°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
102.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
105°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
107.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
110°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0



REPORT NUMBER: P320366
 CATALOG NUMBER: GAN-SA2C-750-U-SLL

CANDELA DISTRIBUTION (continued):

	165°	170°	175°	180°	185°	190°	195°	200°	205°	210°	215°
112.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
115°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
117.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
120°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
122.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
125°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
127.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
130°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
132.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
135°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
137.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
140°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
142.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
145°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
147.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
150°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
152.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
155°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
157.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
160°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
162.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
165°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
167.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
170°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
172.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
175°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
177.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
180°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0



REPORT NUMBER: P320366
 CATALOG NUMBER: GAN-SA2C-750-U-SLL

CANDELA DISTRIBUTION (continued):

	220°	225°	230°	235°	240°	245°	250°	255°	260°	265°	270°
0°	3874.6	3874.6	3874.6	3874.6	3874.6	3874.6	3874.6	3874.6	3874.6	3874.6	3874.6
2.5°	3257.3	3234.4	3257.8	3280.7	3290.4	3300.0	3275.1	3249.7	3289.3	3328.5	3338.7
5°	2668.5	2647.6	2663.4	2678.7	2644.6	2610.5	2607.0	2602.9	2632.4	2661.9	2666.5
7.5°	2068.5	2061.9	2076.6	2091.4	2048.1	2004.4	1983.1	1961.7	1968.8	1975.9	1974.9
10°	1542.2	1546.3	1564.6	1582.4	1548.8	1515.3	1500.5	1485.8	1502.0	1517.8	1532.6
12.5°	1155.3	1163.9	1183.2	1202.0	1188.3	1174.1	1175.6	1177.1	1195.9	1214.2	1230.5
15°	897.5	907.6	921.4	934.6	935.1	935.1	948.3	961.0	959.5	958.0	969.2
17.5°	742.9	756.1	757.6	759.2	759.7	760.2	759.2	758.1	750.5	742.9	751.5
20°	636.1	640.7	644.7	648.3	643.7	638.6	625.9	613.2	608.1	603.1	611.2
22.5°	578.6	586.8	582.7	578.1	569.0	559.3	549.7	539.5	539.0	538.0	542.5
25°	530.3	537.0	529.8	522.7	516.1	509.5	502.9	496.3	495.8	495.3	497.3
27.5°	490.2	496.3	489.7	483.1	477.5	471.9	466.8	461.7	460.7	459.7	460.2
30°	455.6	461.2	455.6	449.5	445.4	440.8	437.3	433.7	433.2	432.7	432.7
32.5°	424.6	430.2	426.1	422.0	418.5	414.9	412.4	409.8	407.3	404.7	399.2
35°	397.6	403.2	400.7	397.6	393.6	389.5	384.9	379.8	373.2	366.1	363.1
37.5°	374.7	380.3	377.8	375.3	369.7	364.1	355.9	347.3	345.3	342.7	342.2
40°	356.4	365.1	360.0	354.4	345.8	337.1	333.1	329.0	328.0	327.0	325.9
42.5°	336.1	349.3	340.2	331.0	322.9	314.7	313.7	312.7	312.2	311.7	311.7
45°	310.7	324.9	315.8	306.1	301.5	297.0	297.0	297.0	297.5	297.5	298.5
47.5°	286.8	295.4	290.8	286.3	283.7	281.2	281.7	282.2	283.7	284.7	287.3
50°	266.4	269.5	270.5	271.0	269.5	268.0	269.0	269.5	271.0	272.0	274.1
52.5°	251.7	256.3	256.3	255.8	255.8	255.8	256.8	257.8	259.3	260.8	262.9
55°	242.0	248.6	246.6	244.6	245.1	245.1	246.1	247.1	248.6	249.7	252.7
57.5°	232.9	240.0	238.0	235.9	235.9	235.9	236.4	237.0	238.5	239.5	241.5
60°	222.2	229.3	227.3	224.7	225.3	225.8	226.3	226.3	227.3	227.8	227.8
62.5°	209.5	216.6	214.6	212.0	213.6	214.6	214.6	214.6	215.6	216.1	214.6
65°	196.3	202.9	200.8	198.8	200.8	202.4	203.4	203.9	203.4	202.9	201.4
67.5°	182.0	188.6	186.6	184.1	186.6	188.6	190.7	192.2	190.7	189.2	187.1
70°	166.8	173.4	170.8	168.3	170.8	173.4	175.4	177.5	175.4	173.4	172.9
72.5°	150.5	158.1	155.1	152.0	155.1	158.1	159.2	160.2	158.6	157.1	156.1
75°	132.7	140.3	137.8	134.7	137.3	139.8	140.3	140.8	140.8	140.3	137.3
77.5°	113.9	120.0	118.5	116.9	118.5	120.0	120.0	120.0	120.5	120.5	116.4
80°	91.5	95.1	95.6	96.1	96.6	97.1	96.6	96.1	95.1	94.1	91.5
82.5°	68.1	68.1	72.2	75.8	75.8	75.3	74.7	73.7	71.7	69.2	63.6
85°	43.2	40.7	47.3	53.4	53.4	52.9	51.9	50.3	46.3	41.7	37.1
87.5°	14.7	12.2	18.8	25.4	25.9	25.9	24.9	23.9	19.8	15.3	11.7
90°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
92.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
95°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
97.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
100°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
102.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
105°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
107.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
110°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0



REPORT NUMBER: P320366
 CATALOG NUMBER: GAN-SA2C-750-U-SLL

CANDELA DISTRIBUTION (continued):

	220°	225°	230°	235°	240°	245°	250°	255°	260°	265°	270°
112.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
115°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
117.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
120°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
122.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
125°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
127.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
130°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
132.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
135°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
137.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
140°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
142.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
145°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
147.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
150°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
152.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
155°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
157.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
160°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
162.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
165°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
167.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
170°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
172.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
175°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
177.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
180°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0



REPORT NUMBER: P320366
 CATALOG NUMBER: GAN-SA2C-750-U-SLL

CANDELA DISTRIBUTION (continued):

	275°	280°	285°	290°	295°	300°	305°	310°	315°	320°	325°
0°	3874.6	3874.6	3874.6	3874.6	3874.6	3874.6	3874.6	3874.6	3874.6	3874.6	3874.6
2.5°	3353.9	3360.5	3366.6	3416.5	3465.8	3523.7	3581.7	3626.0	3669.7	3714.9	3760.2
5°	2682.2	2690.4	2698.5	2759.0	2819.0	2899.8	2980.7	3050.4	3120.0	3201.9	3283.7
7.5°	1988.1	2005.9	2023.2	2087.8	2151.9	2238.8	2325.3	2416.3	2506.8	2613.6	2720.4
10°	1561.5	1595.1	1628.1	1694.2	1760.3	1846.3	1931.7	2026.8	2121.9	2227.1	2331.9
12.5°	1264.1	1308.8	1353.1	1432.4	1511.7	1614.4	1716.6	1822.4	1927.6	2020.2	2112.7
15°	998.6	1047.5	1095.8	1179.7	1263.6	1376.4	1488.8	1604.2	1719.2	1830.0	1940.9
17.5°	779.0	819.2	858.8	930.0	1000.7	1110.0	1219.3	1340.3	1461.4	1596.6	1731.4
20°	628.5	645.3	662.0	713.4	764.2	853.2	941.7	1065.3	1188.8	1350.5	1512.2
22.5°	550.7	559.3	567.5	592.4	616.8	674.2	731.2	840.5	949.3	1125.8	1301.7
25°	503.9	510.5	517.1	533.4	549.7	577.1	604.6	681.4	758.1	931.5	1104.4
27.5°	461.7	471.9	481.5	489.2	496.3	515.1	533.4	583.7	634.1	795.8	957.0
30°	431.2	434.7	438.3	450.0	461.2	480.5	499.8	534.9	570.0	706.8	843.1
32.5°	395.6	400.7	405.8	418.0	430.2	448.0	465.8	494.2	522.2	639.2	755.6
35°	363.6	368.6	373.7	385.9	397.6	417.0	435.8	459.7	483.1	584.7	686.4
37.5°	343.7	348.8	353.9	364.6	374.7	394.1	412.9	431.7	450.0	544.1	638.1
40°	327.0	332.0	337.1	347.3	357.0	375.8	394.1	409.8	425.6	513.6	601.5
42.5°	312.2	317.8	323.4	333.6	343.2	360.0	376.8	397.6	418.0	487.1	555.8
45°	300.0	305.6	310.7	321.9	333.1	349.3	365.6	394.6	423.6	473.4	523.2
47.5°	288.8	294.9	300.5	312.7	324.9	345.3	365.1	389.5	413.4	462.7	512.0
50°	278.1	285.3	292.4	307.1	321.4	355.4	389.0	392.5	395.6	454.1	512.0
52.5°	268.0	276.1	284.2	302.5	320.3	360.0	399.7	387.0	373.7	437.8	501.9
55°	257.8	264.9	271.5	293.9	316.3	345.3	374.2	357.5	340.2	407.3	474.4
57.5°	244.1	251.7	258.8	282.7	306.6	327.0	346.8	331.5	315.8	372.7	429.2
60°	229.8	238.5	247.1	277.6	307.6	304.1	300.0	297.0	293.4	334.1	374.7
62.5°	217.1	226.3	235.4	275.1	314.7	290.3	265.9	268.5	270.5	300.5	330.5
65°	204.4	213.6	222.2	242.0	261.9	252.2	242.5	246.6	250.2	279.7	309.2
67.5°	190.2	198.3	205.9	212.5	219.2	220.2	221.2	225.3	229.3	264.4	299.0
70°	174.4	181.0	187.6	192.2	196.3	198.3	199.8	204.9	210.0	248.1	286.3
72.5°	156.6	162.2	167.3	171.4	175.4	177.0	178.0	183.1	188.1	228.8	269.5
75°	137.3	141.9	145.9	149.5	153.1	155.1	157.1	160.7	164.2	208.5	252.2
77.5°	115.9	120.5	124.6	127.6	130.2	132.2	133.7	138.3	142.9	180.0	216.6
80°	90.5	96.1	101.2	103.7	105.8	106.3	106.3	110.3	114.4	140.8	166.8
82.5°	64.1	70.2	75.8	77.8	79.8	79.8	79.8	84.4	89.0	106.8	124.1
85°	37.6	44.2	50.3	52.4	54.4	55.4	55.9	58.0	59.5	72.2	84.4
87.5°	11.7	17.3	22.4	23.4	24.4	26.4	28.5	29.0	29.0	37.6	46.3
90°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
92.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
95°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
97.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
100°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
102.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
105°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
107.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
110°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0



REPORT NUMBER: P320366
 CATALOG NUMBER: GAN-SA2C-750-U-SLL

CANDELA DISTRIBUTION (continued):

	275°	280°	285°	290°	295°	300°	305°	310°	315°	320°	325°
112.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
115°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
117.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
120°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
122.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
125°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
127.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
130°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
132.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
135°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
137.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
140°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
142.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
145°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
147.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
150°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
152.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
155°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
157.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
160°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
162.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
165°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
167.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
170°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
172.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
175°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
177.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
180°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0



REPORT NUMBER: P320366

CATALOG NUMBER: GAN-SA2C-750-U-SLL

CANDELA DISTRIBUTION (continued):

	330°	335°	340°	345°	350°	355°	360°
0°	3874.6	3874.6	3874.6	3874.6	3874.6	3874.6	3874.6
2.5°	3812.1	3863.9	3924.4	3984.4	4035.8	4087.1	4129.9
5°	3388.0	3492.2	3619.9	3747.0	3860.4	3973.8	4105.4
7.5°	2855.1	2989.8	3155.1	3320.4	3480.5	3640.2	3842.6
10°	2469.2	2605.9	2780.9	2955.3	3135.3	3314.8	3543.6
12.5°	2224.1	2334.9	2504.3	2673.6	2885.1	3096.1	3316.3
15°	2062.4	2183.4	2348.1	2512.9	2744.3	2975.6	3228.8
17.5°	1890.0	2048.1	2259.2	2470.2	2744.3	3017.8	3316.3
20°	1709.5	1906.3	2179.8	2453.4	2822.6	3191.2	3572.1
22.5°	1529.5	1757.3	2108.1	2458.5	2941.0	3423.1	3937.1
25°	1367.3	1630.2	2064.4	2498.1	3113.4	3728.2	4365.8
27.5°	1244.2	1531.0	2046.6	2561.7	3332.1	4102.4	4832.1
30°	1134.9	1426.8	2025.3	2623.7	3542.6	4460.9	5196.6
32.5°	1040.3	1325.1	1984.1	2642.6	3689.5	4736.5	5505.3
35°	966.1	1245.8	1914.9	2584.1	3781.5	4979.0	5826.6
37.5°	902.0	1165.9	1836.1	2506.3	3863.4	5220.5	6188.2
40°	841.0	1080.5	1768.5	2455.9	3976.3	5496.6	6570.0
42.5°	783.1	1010.3	1714.1	2417.8	4081.0	5743.8	6904.1
45°	739.8	956.4	1665.8	2374.6	4148.7	5922.7	7155.8
47.5°	718.5	924.4	1639.8	2354.8	4216.3	6077.3	7364.8
50°	715.4	918.8	1669.3	2419.8	4362.7	6305.1	7603.8
52.5°	714.9	928.0	1754.2	2580.5	4634.8	6688.5	7862.6
55°	704.2	933.6	1855.4	2776.8	4999.9	7222.4	8327.8
57.5°	671.7	914.2	1959.7	3004.6	5385.8	7766.5	8852.1
60°	621.4	867.5	2045.6	3223.2	5645.1	8066.5	9053.9
62.5°	558.3	785.6	2074.1	3362.1	5638.0	7913.9	8850.6
65°	504.4	699.7	1980.5	3260.9	5352.7	7444.1	8448.4
67.5°	456.6	613.7	1746.6	2879.0	4839.7	6799.9	7936.8
70°	422.0	557.3	1445.1	2332.9	4197.5	6061.6	7344.4
72.5°	400.2	530.3	1178.1	1825.4	3406.3	4986.6	6282.2
75°	370.2	488.1	924.4	1360.2	2607.0	3853.8	4745.1
77.5°	314.2	411.4	696.6	981.9	1912.9	2843.4	3300.0
80°	242.5	317.8	479.0	640.2	1316.4	1992.7	2250.0
82.5°	172.9	221.7	290.3	359.0	874.6	1389.7	1411.0
85°	106.8	129.2	166.3	203.4	578.6	953.9	794.8
87.5°	57.5	68.6	88.0	106.8	185.1	263.4	151.5
90°	0.0	0.0	0.0	0.0	0.0	0.0	0.0
92.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0
95°	0.0	0.0	0.0	0.0	0.0	0.0	0.0
97.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0
100°	0.0	0.0	0.0	0.0	0.0	0.0	0.0
102.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0
105°	0.0	0.0	0.0	0.0	0.0	0.0	0.0
107.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0
110°	0.0	0.0	0.0	0.0	0.0	0.0	0.0



REPORT NUMBER: P320366
CATALOG NUMBER: GAN-SA2C-750-U-SLL

CANDELA DISTRIBUTION (continued):

	330°	335°	340°	345°	350°	355°	360°
112.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0
115°	0.0	0.0	0.0	0.0	0.0	0.0	0.0
117.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0
120°	0.0	0.0	0.0	0.0	0.0	0.0	0.0
122.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0
125°	0.0	0.0	0.0	0.0	0.0	0.0	0.0
127.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0
130°	0.0	0.0	0.0	0.0	0.0	0.0	0.0
132.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0
135°	0.0	0.0	0.0	0.0	0.0	0.0	0.0
137.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0
140°	0.0	0.0	0.0	0.0	0.0	0.0	0.0
142.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0
145°	0.0	0.0	0.0	0.0	0.0	0.0	0.0
147.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0
150°	0.0	0.0	0.0	0.0	0.0	0.0	0.0
152.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0
155°	0.0	0.0	0.0	0.0	0.0	0.0	0.0
157.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0
160°	0.0	0.0	0.0	0.0	0.0	0.0	0.0
162.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0
165°	0.0	0.0	0.0	0.0	0.0	0.0	0.0
167.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0
170°	0.0	0.0	0.0	0.0	0.0	0.0	0.0
172.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0
175°	0.0	0.0	0.0	0.0	0.0	0.0	0.0
177.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0
180°	0.0	0.0	0.0	0.0	0.0	0.0	0.0

(END OF REPORT)