

Scaled data based on original data using
LM-79-08 Approved Method: Electrical and Photometric Measurements of Solid-
State Lighting Products

Test Report Prepared for
Cooper Lighting Solutions
(formerly Eaton)

Brand: STREETWORKS

Report Number: P946272

Luminaire Tested: **GLAN-SB2A-722-U-T2R**

Issue Date: 1/21/2025

Test Information

Test Method: LM-79-08
Report Number: P946272
TEST IS SCALED FROM IESNA LM-79-08 TEST DATA (G2-2411-289-3)
Test Lab: INNOVATION CENTER
Issue Date: 1/21/2025
Manufacturer: COOPER LIGHTING SOLUTIONS (FORMERLY EATON)
Product Line: STREETWORKS
Catalog Number: GLAN-SB2A-722-U-T2R
Description: GALLEON AREA AND ROADWAY HIGH DENSITY LED LUMINAIRE
(2) 70 CRI, 2200K, 350mA LIGHTSQUARES WITH 26 LEDS EACH AND TYPE II
ROADWAY OPTICS
Light Source: -
Ballast/Driver: -

Summary

Lumens per Lamp: N/A
Luminaire Lumens: 7548 lumens
Efficiency: N/A
Efficacy: 131.7 lumens/watt
Luminous Opening: Rectangular (W 0.5' x L: 1' x H: 0')
IES Classification: Type II - Medium
BUG Rating: B1 - U0 - G2

Input Watts (W): 57.3
Input Voltage (V): NR
Input Current (Ain): NR
Voltage Rise (V): NR
Power Factor: NR
Total Harmonic Distortion (THDi): NR
Frequency (hertz): 60
Stabilization Time: NR
Operation Time: NR
Ambient Temperature (°C): NR
Test Distance: 24 FT




REPORT NUMBER: P946272

CATALOG NUMBER: GLAN-SB2A-722-U-T2R


Iso-Footcandle Lines of Horizontal Illumination

✕ Max cd
- - - 1/2 Max cd



Based on 25 foot mounting height. Maximum calculated value = 2.8 fc
Type II - Medium - N/A

REPORT NUMBER: P946272
CATALOG NUMBER: GLAN-SB2A-722-U-T2R



REPORT NUMBER: P946272

CATALOG NUMBER: GLAN-SB2A-722-U-T2R

FLUX DISTRIBUTION:

		Downward	Upward	Total
House Side	Lumens	1427.8	0.0	1427.8
	% Fixture	18.9	0.0	18.9
Street Side	Lumens	6120.2	0.0	6120.2
	% Fixture	81.1	0.0	81.1
Total	Lumens	7548.0	0.0	7548.0
	% Fixture	100.0	0.0	100.0

ZONAL LUMENS:

Zone	Lumens	% Fixture
0°-10°	94.9	1.3
10°-20°	341.0	4.5
20°-30°	643.9	8.5
30°-40°	1037.3	13.7
40°-50°	1418.9	18.8
50°-60°	1600.5	21.2
60°-70°	1493.8	19.8
70°-80°	818.9	10.8
80°-90°	98.8	1.3
90°-100°	0.0	0.0
100°-110°	0.0	0.0
110°-120°	0.0	0.0
120°-130°	0.0	0.0
130°-140°	0.0	0.0
140°-150°	0.0	0.0
150°-160°	0.0	0.0
160°-170°	0.0	0.0
170°-180°	0.0	0.0
0°-90°	7548.0	100.0
0°-180°	7548.0	100.0

Coefficient of Utilization



REPORT NUMBER: P946272


CATALOG NUMBER: GLAN-SB2A-722-U-T2R

LUMINAIRE CLASSIFICATION SYSTEM LUMEN TABLE AND BUG RATING:

Zone		Lumens	% Fixture	Zone Rating/Lumen Limit		
				B	U	G
FL	(0°-30°)	769.4	10.2			
FM	(30°-60°)	3374.6	44.7			
FH	(60°-80°)	1914.4	25.4			G2/5000
FVH	(80°-90°)	61.8	0.8			G1/100
BL	(0°-30°)	310.4	4.1	B1/500		
BM	(30°-60°)	682.0	9.0	B1/1000		
BH	(60°-80°)	398.3	5.3	B1/500		G1/500
BVH	(80°-90°)	37.0	0.5			G1/100
UL	(90°-100°)	0.0	0.0		U0/0	
UH	(100°-180°)	0.0	0.0		U0/0	

BUG Rating: B1-U0-G2

Type II Medium



REPORT NUMBER: P946272

CATALOG NUMBER: GLAN-SB2A-722-U-T2R

CANDELA DISTRIBUTION (FULL):

	0°	5°	15°	25°	35°	45°	55°	65°	75°	77°
0°	885.6	885.6	885.6	885.6	885.6	885.6	885.6	885.6	885.6	885.6
2.5°	1108.9	1116.7	1106.9	1106.9	1074.2	1057.0	1024.3	999.4	954.6	946.8
5°	1310.7	1320.4	1306.8	1301.0	1262.4	1226.9	1172.0	1117.8	1038.0	1029.8
7.5°	1466.9	1479.4	1467.3	1461.1	1426.8	1387.1	1322.8	1247.2	1134.6	1118.6
10°	1594.3	1596.3	1592.4	1594.7	1567.8	1535.1	1469.3	1381.2	1240.6	1218.7
12.5°	1666.4	1675.4	1683.2	1697.2	1692.5	1672.3	1613.0	1507.8	1352.8	1324.7
15°	1700.3	1715.9	1733.4	1765.8	1791.9	1796.9	1751.7	1643.8	1466.9	1433.0
17.5°	1712.4	1727.2	1754.9	1801.6	1857.7	1895.5	1875.3	1775.9	1579.9	1541.0
20°	1773.6	1777.9	1794.6	1839.0	1899.8	1962.5	1977.7	1902.9	1691.7	1647.7
22.5°	1904.5	1895.9	1900.6	1920.8	1964.5	2025.3	2059.9	2015.1	1806.7	1756.0
25°	2120.7	2095.8	2070.9	2047.5	2069.7	2104.0	2143.3	2127.3	1927.1	1862.8
27.5°	2393.8	2363.5	2308.5	2231.8	2204.9	2217.0	2234.5	2231.4	2038.5	1973.4
30°	2662.7	2627.2	2561.8	2450.7	2379.8	2347.9	2334.6	2325.7	2159.7	2090.3
32.5°	2877.4	2849.3	2785.0	2660.7	2557.9	2503.3	2459.3	2427.4	2286.3	2217.0
35°	3065.2	3039.1	2965.4	2829.8	2718.0	2660.0	2602.3	2534.1	2418.0	2347.9
37.5°	3236.6	3210.5	3109.6	2968.5	2855.9	2815.8	2764.4	2648.7	2550.1	2483.9
40°	3344.9	3339.1	3244.8	3085.0	2968.2	2948.3	2931.1	2781.5	2696.6	2635.0
42.5°	3372.6	3385.4	3310.6	3179.3	3067.9	3051.9	3092.1	2931.9	2861.0	2802.2
45°	3306.0	3343.0	3293.9	3204.7	3138.8	3130.2	3234.7	3096.3	3043.0	2989.2
47.5°	3137.3	3200.0	3179.7	3167.3	3157.9	3194.9	3360.1	3270.9	3249.1	3202.3
50°	2796.7	2915.6	2951.0	3029.7	3120.1	3245.2	3474.3	3461.4	3489.9	3442.7
52.5°	2208.0	2371.6	2577.4	2774.5	3004.0	3228.4	3599.7	3734.9	3854.9	3829.2
55°	1822.7	1896.3	2054.5	2416.1	2778.8	3157.9	3656.2	3955.9	4217.3	4194.3
57.5°	1526.5	1592.4	1689.8	1991.8	2438.3	2997.8	3691.3	4090.7	4465.5	4463.1
60°	1209.0	1278.7	1378.5	1592.4	2040.5	2721.1	3683.5	4244.2	4782.2	4801.7
62.5°	850.5	927.3	1038.0	1237.4	1634.1	2362.7	3524.5	4355.2	5155.1	5208.1
65°	559.1	609.8	693.1	865.4	1217.6	1901.8	3221.0	4369.6	5554.1	5643.7
67.5°	392.0	411.4	460.5	554.0	802.6	1458.4	2737.5	4220.4	5820.2	5921.1
70°	305.9	315.6	340.5	377.9	504.2	980.7	2097.7	3832.3	5763.3	5868.5
72.5°	264.2	273.5	282.9	287.5	338.2	605.5	1421.0	3204.3	5227.6	5298.9
75°	239.6	242.0	249.7	248.2	257.9	392.7	820.2	2334.6	4124.6	4100.0
77.5°	201.4	204.6	217.4	215.5	229.1	268.5	425.9	1506.7	2674.0	2507.2
80°	170.7	172.2	186.2	183.9	199.1	194.4	217.4	767.9	1134.2	960.8
82.5°	59.2	73.2	142.2	146.5	152.0	117.7	125.5	313.3	346.4	265.3
85°	28.8	30.8	72.5	102.9	102.5	59.2	61.2	111.8	109.1	85.7
87.5°	4.7	5.8	8.6	40.1	31.9	15.6	21.0	21.8	22.6	19.5
90°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0

REPORT NUMBER: P946272

CATALOG NUMBER: GLAN-SB2A-722-U-T2R

CANDELA DISTRIBUTION (continued):

85°		90°	95°	105°	115°	125°	135°	145°	155°	165°	175°
885.6	0°	885.6	885.6	885.6	885.6	885.6	885.6	885.6	885.6	885.6	885.6
917.2	2.5°	895.4	875.9	835.0	797.2	767.6	739.1	723.1	709.5	701.7	700.2
960.0	5°	919.5	879.4	805.0	742.2	701.3	670.9	655.0	644.8	639.8	636.6
1017.7	7.5°	954.2	895.4	789.4	718.1	675.2	653.4	645.2	643.7	643.3	643.7
1087.4	10°	1002.1	921.5	787.8	712.2	676.4	664.3	663.9	664.3	665.9	666.3
1163.4	12.5°	1053.9	948.3	794.1	717.3	691.2	684.6	683.4	683.0	684.2	685.0
1240.2	15°	1110.4	983.8	804.6	728.2	707.6	700.5	699.4	697.0	696.6	696.3
1320.8	17.5°	1168.5	1018.9	816.3	739.9	718.1	708.3	704.1	698.6	694.3	693.1
1404.2	20°	1227.3	1053.5	824.4	745.7	718.9	705.2	696.6	687.3	679.9	675.6
1488.4	22.5°	1290.0	1089.8	829.5	744.2	711.8	693.1	677.6	666.6	655.3	647.9
1573.3	25°	1351.2	1121.3	829.1	736.0	698.2	674.4	654.6	640.5	625.0	617.2
1661.0	27.5°	1410.0	1149.8	819.4	721.6	678.7	652.2	628.5	611.7	596.5	589.1
1749.4	30°	1470.8	1173.5	804.2	700.5	655.7	626.5	600.4	586.0	572.4	565.3
1842.9	32.5°	1531.2	1195.4	782.8	674.4	629.2	601.2	575.5	562.2	554.0	554.0
1943.4	35°	1595.1	1210.6	754.3	644.0	601.2	574.3	554.0	546.3	545.5	540.8
2049.8	37.5°	1662.5	1220.3	719.6	612.9	573.5	548.2	542.0	532.6	524.8	514.7
2166.7	40°	1733.4	1230.0	677.9	580.5	544.3	530.3	527.6	515.1	492.9	467.9
2299.2	42.5°	1819.5	1236.7	634.7	548.2	513.5	508.8	512.7	491.3	455.9	437.2
2458.9	45°	1919.3	1247.6	595.0	516.3	482.0	482.0	498.3	470.3	441.1	429.4
2641.3	47.5°	2048.6	1272.9	557.9	481.2	452.7	460.5	466.4	445.0	428.6	414.2
2863.3	50°	2235.7	1333.7	519.8	445.7	430.5	446.1	437.9	425.5	406.4	394.7
3216.3	52.5°	2467.9	1369.5	485.9	413.8	411.4	427.0	415.3	403.7	389.2	373.6
3484.0	55°	2626.1	1376.2	457.4	390.4	398.6	397.0	392.7	382.2	374.4	353.8
3748.2	57.5°	2803.0	1389.4	434.0	376.4	390.4	373.3	371.7	362.7	352.6	338.6
4070.4	60°	3014.5	1410.0	413.8	370.9	383.4	357.7	349.9	346.4	336.2	329.2
4458.1	62.5°	3245.2	1428.8	393.1	371.7	375.2	342.5	330.8	329.6	323.4	321.1
4822.0	65°	3402.6	1377.7	367.4	370.9	362.4	326.9	312.1	311.7	306.6	305.9
4979.8	67.5°	3347.6	1216.0	332.7	360.0	349.1	311.3	294.9	293.4	286.8	287.2
4815.0	70°	3072.6	985.4	284.8	333.1	332.7	297.3	277.0	272.0	263.0	264.6
4186.5	72.5°	2556.7	730.2	220.5	288.3	306.6	284.4	256.4	248.2	236.9	238.4
3090.5	75°	1846.4	496.4	160.5	219.4	266.9	269.2	236.1	222.1	208.4	210.8
1720.2	77.5°	944.8	281.3	118.1	151.2	209.6	244.7	217.8	199.1	196.0	217.8
496.0	80°	308.2	141.0	81.8	106.0	137.5	200.3	190.9	169.5	168.7	173.8
104.0	82.5°	92.0	59.6	52.6	69.7	76.0	153.5	164.8	128.2	110.3	116.1
34.7	85°	31.6	28.8	30.0	34.7	36.2	90.0	115.3	84.9	80.3	88.4
7.8	87.5°	7.4	10.1	8.6	7.8	7.8	21.8	44.8	35.5	49.1	32.7
0.0	90°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0

(END O

180°
885.6
700.2
636.3
644.8
666.6
685.3
695.9
694.3
677.2
648.3
617.2
588.7
565.0
554.4
539.6
513.1
464.4
437.5
431.3
413.8
393.5
370.5
354.2
333.9
331.2
321.1
305.5
287.2
266.1
238.1
211.6
214.7
149.2
120.0
87.3
31.6
0.0

F REPORT)