

Scaled data based on original data using
LM-79-08 Approved Method: Electrical and Photometric Measurements of Solid-
State Lighting Products

Test Report Prepared for
Cooper Lighting Solutions
(formerly Eaton)

Brand: STREETWORKS

Report Number: P654119

Luminaire Tested: **GLAN-SA9A-840-U-T3R-GRSBK**

Issue Date: 5/27/2021

Test Information

Test Method: LM-79-08
Report Number: P654119
TEST IS SCALED FROM IESNA LM-79-08 TEST DATA (G3-2011-057-11)
Test Lab: INNOVATION CENTER
Issue Date: 5/27/2021
Manufacturer: COOPER LIGHTING SOLUTIONS (FORMERLY EATON)
Product Line: STREETWORKS
Catalog Number: GLAN-SA9A-840-U-T3R-GRSBK
Description: GALLEON AREA AND ROADWAY LUMINAIRE
(9) 80 CRI, 4000K, 615mA LIGHTSQUARES WITH 16 LEDS EACH AND TYPE III
ROADWAY OPTICS WITH BLACK GLARE REDUCTION SHIELD
Light Source: -
Ballast/Driver: ELECTRONIC DRIVER

Summary

Lumens per Lamp: N/A
Luminaire Lumens: 21204.1 lumens
Efficiency: N/A
Efficacy: 77.4 lumens/watt
Luminous Opening: Rectangular (W 1.5' x L: 1.5' x H: 0')
IES Classification: Type II - Short
BUG Rating: B3 - U0 - G1


Input Watts (W): 274
Input Voltage (V): NR
Input Current (Ain): NR
Voltage Rise (V): NR
Power Factor: NR
Total Harmonic Distortion (THDi): NR
Frequency (hertz): 60
Stabilization Time: NR
Operation Time: NR
Ambient Temperature (°C): NR
Test Distance: 24 FT



REPORT NUMBER: P654119
 CATALOG NUMBER: GLAN-SA9A-840-U-T3R-GRSBK

Iso-Footcandle Lines of Horizontal Illumination


× Max cd
 - - - 1/2 Max cd



Based on 25 foot mounting height. Maximum calculated value = 9.4 fc
 Type II - Short - N/A

REPORT NUMBER: P654119
CATALOG NUMBER: GLAN-SA9A-840-U-T3R-GRSBK

Luminous Intensity Polar Plot



— Vertical Plane Through 78-Deg Lateral - - - Horizontal Cone Through 55-Deg Vertical

REPORT NUMBER: P654119
 CATALOG NUMBER: GLAN-SA9A-840-U-T3R-GRSBK


FLUX DISTRIBUTION:

		Downward	Upward	Total
House Side	Lumens	3938.4	0.0	3938.4
	% Fixture	18.6	0.0	18.6
Street Side	Lumens	17265.7	0.0	17265.7
	% Fixture	81.4	0.0	81.4
Total	Lumens	21204.1	0.0	21204.1
	% Fixture	100.0	0.0	100.0

ZONAL LUMENS:

Zone	Lumens	% Fixture
0°-10°	486.1	2.3
10°-20°	1286.5	6.1
20°-30°	2255.0	10.6
30°-40°	3718.2	17.5
40°-50°	5410.5	25.5
50°-60°	6130.6	28.9
60°-70°	1752.8	8.3
70°-80°	136.1	0.6
80°-90°	28.3	0.1
90°-100°	0.0	0.0
100°-110°	0.0	0.0
110°-120°	0.0	0.0
120°-130°	0.0	0.0
130°-140°	0.0	0.0
140°-150°	0.0	0.0
150°-160°	0.0	0.0
160°-170°	0.0	0.0
170°-180°	0.0	0.0
0°-90°	21204.1	100.0
0°-180°	21204.1	100.0

Coefficient of Utilization




REPORT NUMBER: P654119
 CATALOG NUMBER: GLAN-SA9A-840-U-T3R-GRSBK

LUMINAIRE CLASSIFICATION SYSTEM LUMEN TABLE AND BUG RATING:

Zone	Lumens	% Fixture	Zone Rating/Lumen Limit		
			B	U	G
FL (0°-30°)	2606.6	12.3			
FM (30°-60°)	13043.8	61.5			
FH (60°-80°)	1601.5	7.6			G1/1800
FVH (80°-90°)	13.8	0.1			G1/100
BL (0°-30°)	1421.0	6.7	B3/2500		
BM (30°-60°)	2215.4	10.4	B2/2500		
BH (60°-80°)	287.5	1.4	B1/500		G1/500
BVH (80°-90°)	14.5	0.1			G1/100
UL (90°-100°)	0.0	0.0		U0/0	
UH (100°-180°)	0.0	0.0		U0/0	

BUG Rating: B3-U0-G1
 Type II Short





REPORT NUMBER: P654119

CATALOG NUMBER: GLAN-SA9A-840-U-T3R-GRSBK

CANDELA DISTRIBUTION (FULL):

	0°	5°	15°	25°	35°	45°	55°	65°	75°	78°	85°
0°	5451.6	5451.6	5451.6	5451.6	5451.6	5451.6	5451.6	5451.6	5451.6	5451.6	5451.6
2.5°	5125.6	5174.8	5182.4	5243.0	5239.3	5341.6	5372.0	5375.8	5444.0	5409.9	5497.1
5°	4981.5	4954.9	4943.6	5049.7	5080.1	5171.1	5246.9	5292.3	5432.6	5481.9	5572.9
7.5°	4852.6	4852.6	4860.2	4954.9	4943.6	5061.1	5140.7	5281.0	5485.7	5527.4	5637.4
10°	4727.5	4682.0	4738.9	4837.4	4920.9	4973.9	5140.7	5273.4	5512.3	5633.6	5785.2
12.5°	4663.0	4685.8	4693.4	4765.4	4856.4	5015.6	5106.6	5326.5	5701.8	5773.8	5936.9
15°	5068.7	5023.2	4913.3	4848.8	4924.6	5000.4	5227.9	5451.6	5800.4	5902.7	6084.7
17.5°	5538.8	5500.9	5409.9	5235.5	5064.9	5205.2	5383.3	5588.1	5906.5	6058.1	6327.3
20°	6152.9	6092.3	6001.3	5660.1	5512.3	5360.6	5550.2	5792.8	6080.9	6217.4	6494.1
22.5°	6884.6	6884.6	6679.9	6266.7	5959.6	5815.5	5895.2	6035.4	6274.3	6460.1	6733.0
25°	7646.6	7623.9	7438.1	7009.7	6490.3	6319.8	6410.8	6509.3	6573.8	6676.1	6858.1
27.5°	8518.6	8385.9	8150.9	7677.0	7218.2	6888.4	6987.0	6899.8	6820.2	6873.2	7134.9
30°	9110.0	9193.4	8893.9	8439.0	8006.8	7639.1	7658.0	7582.2	7218.2	7294.1	7449.5
32.5°	9724.1	9777.2	9610.4	9360.2	8928.1	8499.7	8344.2	8279.7	8006.8	8040.9	7889.3
35°	10236.0	10338.3	10190.5	10080.6	9955.4	9610.4	9182.0	9390.5	8950.8	8867.3	8473.1
37.5°	10706.0	10675.7	10850.1	10736.4	10709.9	10467.3	9997.1	10038.8	9743.2	9724.1	9269.2
40°	11126.9	11134.4	11373.3	11426.3	11320.2	10888.0	10205.6	10535.5	10774.3	10797.0	10213.2
42.5°	11475.6	11578.0	11782.7	12211.2	12051.9	11331.5	10421.8	10781.9	11669.0	11809.2	11107.9
45°	11779.0	11987.4	12241.4	12624.3	12533.3	11960.9	10960.1	11289.9	12624.3	12992.1	11949.5
47.5°	11797.9	12070.9	12347.6	12916.2	13030.0	12298.3	11517.3	12093.6	13382.6	13780.6	12563.7
50°	11722.0	11866.1	12419.6	13037.6	13295.4	12848.0	12298.3	12768.4	14118.0	14368.2	12874.5
52.5°	10823.6	10933.5	12044.3	13151.3	13773.1	13469.8	13333.3	13708.6	14868.7	15054.4	13166.4
55°	9022.8	9003.8	10531.7	12578.8	13992.9	14391.0	14307.6	14440.3	15736.9	15903.6	13238.5
57.5°	6171.9	6516.9	7836.2	10474.8	12647.1	14174.9	14262.1	14042.2	14724.6	14789.1	11540.1
60°	3328.6	3472.7	4534.2	6990.8	9629.4	11551.5	11779.0	11380.8	11327.8	11145.9	8238.0
62.5°	1323.1	1395.1	1997.9	3461.3	5246.9	7021.1	7510.1	7347.1	6998.4	6520.7	4265.0
65°	629.3	674.8	993.3	1618.8	2327.7	2926.8	3415.8	3567.4	2631.0	2369.4	1406.5
67.5°	428.4	462.6	724.1	925.0	830.2	868.2	1129.7	1050.2	618.0	527.0	390.5
70°	326.1	348.8	580.0	629.3	371.6	261.6	291.9	273.0	254.0	257.8	254.0
72.5°	231.3	250.2	424.6	371.6	163.0	121.4	155.4	185.8	185.8	185.8	182.0
75°	140.3	159.2	246.4	144.1	64.4	64.4	98.6	125.1	132.7	136.5	128.9
77.5°	72.0	91.0	83.4	41.7	41.7	49.3	72.0	87.2	94.8	94.8	91.0
80°	15.1	15.1	15.1	22.7	41.7	53.1	72.0	79.6	91.0	91.0	83.4
82.5°	0.0	3.8	11.4	22.7	37.9	49.3	68.2	79.6	91.0	94.8	87.2
85°	0.0	3.8	7.6	15.1	26.6	30.4	26.6	22.7	22.7	22.7	22.7
87.5°	0.0	0.0	3.8	3.8	3.8	7.6	7.6	7.6	7.6	7.6	7.6
90°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0



REPORT NUMBER: P654119

CATALOG NUMBER: GLAN-SA9A-840-U-T3R-GRSBK

CANDELA DISTRIBUTION (continued):

	90°	95°	105°	115°	125°	135°	145°	155°	165°	175°	180°
0°	5451.6	5451.6	5451.6	5451.6	5451.6	5451.6	5451.6	5451.6	5451.6	5451.6	5451.6
2.5°	5504.7	5516.0	5497.1	5493.3	5478.1	5523.6	5413.7	5387.1	5455.4	5391.0	5406.1
5°	5576.7	5603.2	5569.1	5512.3	5428.8	5300.0	5190.0	5045.9	4977.7	4928.4	4920.9
7.5°	5629.7	5648.7	5614.6	5432.6	5182.4	4856.4	4613.7	4435.6	4295.3	4253.6	4185.4
10°	5845.9	5849.7	5679.0	5277.2	4788.1	4359.7	3988.3	3715.3	3575.0	3487.8	3449.9
12.5°	5989.9	5982.4	5637.4	4970.1	4318.0	3749.4	3324.8	2995.0	2866.0	2824.3	2797.8
15°	6171.9	6130.2	5538.8	4655.4	3711.5	3097.3	2714.4	2486.9	2475.6	2449.1	2475.6
17.5°	6316.0	6198.4	5394.8	4083.0	3131.5	2551.4	2301.2	2316.4	2346.7	2373.2	2377.0
20°	6551.1	6308.3	5064.9	3582.6	2593.1	2187.4	2183.7	2251.9	2327.7	2358.1	2388.4
22.5°	6729.2	6353.8	4712.3	3048.0	2153.4	2039.6	2104.1	2206.4	2263.3	2293.6	2339.1
25°	6793.7	6228.8	4242.3	2513.5	1941.0	1971.4	2070.0	2138.2	2210.2	2244.3	2225.4
27.5°	6858.1	6164.4	3681.1	2070.0	1827.3	1925.9	2009.3	2077.5	2100.2	2145.7	2176.1
30°	7013.5	5940.7	3177.0	1789.4	1770.5	1895.5	1956.2	1979.0	2039.6	2066.2	2066.2
32.5°	7138.7	5853.4	2642.4	1656.7	1762.8	1910.8	1918.3	1918.3	1925.9	1906.9	1899.3
35°	7396.4	5554.0	2164.7	1577.1	1759.0	1914.5	1933.5	1869.0	1694.6	1626.4	1607.4
37.5°	7714.9	5360.6	1812.1	1558.1	1785.6	1960.0	1990.3	1747.7	1520.2	1410.3	1391.4
40°	8101.6	5224.1	1580.9	1550.6	1846.2	2066.2	1975.2	1652.9	1357.2	1198.0	1190.4
42.5°	8552.7	5099.0	1425.4	1546.8	1922.1	2176.1	1960.0	1573.3	1190.4	1084.2	1099.4
45°	8912.8	5030.8	1319.3	1520.2	1948.6	2240.5	1971.4	1433.1	1122.1	1053.9	1061.5
47.5°	9193.4	4886.7	1232.1	1474.8	1944.8	2263.3	1869.0	1376.1	1088.1	1107.0	1125.9
50°	9201.0	4693.4	1122.1	1376.1	1888.0	2221.6	1751.5	1323.1	1080.4	1160.1	1198.0
52.5°	9098.6	4420.4	1004.7	1235.9	1755.3	2077.5	1645.3	1300.4	1046.4	1038.7	1084.2
55°	8734.7	3908.6	807.5	1000.9	1482.3	1713.5	1550.6	1258.6	944.0	856.8	864.4
57.5°	7059.0	2801.6	595.2	716.5	1050.2	1254.9	1398.9	1239.7	849.2	727.9	731.7
60°	4371.1	1588.5	436.0	489.0	648.2	762.0	1133.5	1152.5	758.2	614.2	606.6
62.5°	2244.3	784.7	337.4	345.0	398.0	447.3	777.2	966.7	686.2	583.8	583.8
65°	750.7	386.7	295.7	265.3	265.3	276.8	470.1	671.0	580.0	489.0	489.0
67.5°	322.3	288.1	257.8	231.3	212.3	200.9	265.3	390.5	432.2	371.6	356.3
70°	250.2	242.6	223.7	193.3	166.8	151.6	155.4	200.9	246.4	238.8	231.3
72.5°	185.8	185.8	178.2	151.6	128.9	109.9	102.3	106.1	117.5	121.4	125.1
75°	128.9	132.7	132.7	117.5	94.8	79.6	68.2	56.9	45.5	37.9	34.1
77.5°	87.2	91.0	98.6	87.2	72.0	53.1	41.7	30.4	18.9	7.6	7.6
80°	75.9	87.2	94.8	87.2	75.9	56.9	41.7	22.7	11.4	0.0	0.0
82.5°	79.6	87.2	98.6	83.4	72.0	53.1	41.7	26.6	11.4	3.8	0.0
85°	18.9	18.9	22.7	26.6	34.1	37.9	30.4	18.9	11.4	3.8	0.0
87.5°	7.6	7.6	7.6	7.6	7.6	3.8	3.8	3.8	3.8	0.0	0.0
90°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0

(END OF REPORT)