

Scaled data based on original data using  
LM-79-08 Approved Method: Electrical and Photometric Measurements of Solid-  
State Lighting Products

Test Report Prepared for  
Cooper Lighting Solutions  
(formerly Eaton)

Brand: STREETWORKS

Report Number: P654265

Luminaire Tested: **GLAN-SA3B-840-U-SLL-GRSWH**

Issue Date: 5/27/2021

**Test Information**

Test Method: LM-79-08  
Report Number: P654265  
TEST IS SCALED FROM IESNA LM-79-08 TEST DATA (G3-2011-057-24)  
Test Lab: INNOVATION CENTER  
Issue Date: 5/27/2021  
Manufacturer: COOPER LIGHTING SOLUTIONS (FORMERLY EATON)  
Product Line: STREETWORKS  
Catalog Number: GLAN-SA3B-840-U-SLL-GRSWH  
Description: GALLEON AREA AND ROADWAY LUMINAIRE  
(3) 80 CRI, 4000K, 800mA LIGHTSQUARES WITH 16 LEDS EACH AND SPILL LIGHT  
ELIMINATOR LEFT OPTICS WITH WHITE GLARE REDUCTION SHIELD  
Light Source: -  
Ballast/Driver: ELECTRONIC DRIVER

**Summary**

Lumens per Lamp: N/A  
Luminaire Lumens: 10639.5 lumens  
Efficiency: N/A  
Efficacy: 87.9 lumens/watt  
Luminous Opening: Rectangular (W 1' x L: 1' x H: 0')  
IES Classification: Type II - Short  
BUG Rating: B2 - U0 - G2


Input Watts (W): 121  
Input Voltage (V): NR  
Input Current (Ain): NR  
Voltage Rise (V): NR  
Power Factor: NR  
Total Harmonic Distortion (THDi): NR  
Frequency (hertz): 60  
Stabilization Time: NR  
Operation Time: NR  
Ambient Temperature (°C): NR  
Test Distance: 24 FT



REPORT NUMBER: P654265  
 CATALOG NUMBER: GLAN-SA3B-840-U-SLL-GRSWH

### Iso-Footcandle Lines of Horizontal Illumination


✕ Max cd  
 - - - 1/2 Max cd



Based on 25 foot mounting height. Maximum calculated value = 8.1 fc  
 Type II - Short - N/A

REPORT NUMBER: P654265  
CATALOG NUMBER: GLAN-SA3B-840-U-SLL-GRSWH

### Luminous Intensity Polar Plot



— Vertical Plane Through 55-Deg Lateral      - - - Horizontal Cone Through 52.5-Deg Vertical

REPORT NUMBER: P654265  
 CATALOG NUMBER: GLAN-SA3B-840-U-SLL-GRSWH


**FLUX DISTRIBUTION:**

		Downward	Upward	Total
<b>House Side</b>	Lumens	3245.6	0.0	3245.6
	% Fixture	30.5	0.0	30.5
<b>Street Side</b>	Lumens	7393.9	0.0	7393.9
	% Fixture	69.5	0.0	69.5
<b>Total</b>	Lumens	10639.5	0.0	10639.5
	% Fixture	100.0	0.0	100.0

**Coefficient of Utilization**

**ZONAL LUMENS:**

Zone	Lumens	% Fixture
0°-10°	362.6	3.4
10°-20°	781.8	7.3
20°-30°	1185.4	11.1
30°-40°	1712.8	16.1
40°-50°	2288.8	21.5
50°-60°	2554.7	24.0
60°-70°	1401.4	13.2
70°-80°	303.0	2.8
80°-90°	49.0	0.5
90°-100°	0.0	0.0
100°-110°	0.0	0.0
110°-120°	0.0	0.0
120°-130°	0.0	0.0
130°-140°	0.0	0.0
140°-150°	0.0	0.0
150°-160°	0.0	0.0
160°-170°	0.0	0.0
170°-180°	0.0	0.0
0°-90°	10639.5	100.0
0°-180°	10639.5	100.0




REPORT NUMBER: P654265  
 CATALOG NUMBER: GLAN-SA3B-840-U-SLL-GRSWH

**LUMINAIRE CLASSIFICATION SYSTEM LUMEN TABLE AND BUG RATING:**

Zone	Lumens	% Fixture	Zone Rating/Lumen Limit		
			B	U	G
FL (0°-30°)	1491.9	14.0			
FM (30°-60°)	4790.4	45.0			
FH (60°-80°)	1093.5	10.3			G1/1800
FVH (80°-90°)	18.1	0.2			G1/100
BL (0°-30°)	838.0	7.9	B2/1000		
BM (30°-60°)	1765.9	16.6	B2/2500		
BH (60°-80°)	610.9	5.7	B2/1000		G2/1000
BVH (80°-90°)	30.9	0.3			G1/100
UL (90°-100°)	0.0	0.0		U0/0	
UH (100°-180°)	0.0	0.0		U0/0	

**BUG Rating: B2-U0-G2**  
 Type II Short





REPORT NUMBER: P654265

CATALOG NUMBER: GLAN-SA3B-840-U-SLL-GRSWH

**CANDELA DISTRIBUTION (FULL):**

	0°	1°	5°	15°	25°	35°	45°	55°	65°	75°	85°
0°	4746.0	4746.0	4746.0	4746.0	4746.0	4746.0	4746.0	4746.0	4746.0	4746.0	4746.0
2.5°	4980.7	4952.6	4977.5	5095.6	5163.9	5210.5	5240.0	5235.4	5123.5	5014.8	5014.8
5°	4834.6	4798.8	4850.1	5117.3	5386.1	5409.4	5448.3	5384.5	5219.8	5021.0	4772.4
7.5°	4412.1	4438.5	4523.9	4874.9	5224.5	5400.1	5446.7	5365.9	5098.6	4727.4	4362.4
10°	4047.0	4109.1	4306.4	4685.5	5007.1	5235.4	5286.7	5173.2	4962.0	4506.8	4180.5
12.5°	3921.1	3882.3	4101.3	4480.3	4788.0	4910.7	4934.0	4941.8	4798.8	4394.9	3997.3
15°	3905.6	3930.4	4101.3	4388.8	4578.2	4584.5	4623.3	4683.9	4702.5	4471.1	4082.7
17.5°	4129.3	4099.8	4275.3	4503.7	4413.6	4323.5	4332.8	4419.8	4573.6	4536.3	4351.4
20°	4460.2	4527.0	4665.3	4642.0	4399.6	4171.2	4172.8	4255.1	4558.1	4806.7	4725.8
22.5°	5010.2	5075.4	5178.0	4896.7	4399.6	4126.2	4073.4	4185.2	4657.5	5128.2	5148.4
25°	5511.9	5631.6	5659.5	5328.6	4620.2	4168.2	4133.9	4244.3	4756.9	5442.0	5633.1
27.5°	5968.7	6012.1	6134.9	5606.7	4742.9	4196.1	4193.0	4334.3	4882.8	5599.0	6066.6
30°	6329.1	6324.4	6394.3	5782.2	4938.7	4353.0	4202.3	4469.5	5047.4	5858.3	6467.4
32.5°	6574.5	6627.3	6774.9	6026.2	5021.0	4502.1	4384.0	4627.9	5247.8	5981.1	6750.1
35°	7006.5	7098.0	6911.7	6161.3	5282.0	4649.7	4511.5	4843.9	5347.2	6114.7	7096.5
37.5°	7413.4	7343.5	7154.0	6234.3	5451.4	4923.1	4794.2	5261.8	5656.4	6405.2	7326.5
40°	7674.5	7672.9	7335.8	6293.4	5571.0	5341.0	5333.3	5685.9	6035.4	6588.6	7584.3
42.5°	7787.8	7896.6	7410.3	6287.1	5822.7	5847.5	6004.4	6319.8	6304.2	6625.8	7578.1
44°	7943.2	8008.4	7539.3	6301.1	5990.4	6189.3	6559.0	6759.5	6538.8	6605.6	7570.3
45°	7937.0	7941.6	7356.0	6319.8	6133.3	6475.1	6806.0	7144.7	6745.4	6562.2	7672.9
47.5°	7755.2	7702.4	7200.6	6181.5	6579.2	7230.2	7536.2	7741.2	7000.2	6468.9	7545.5
50°	7396.3	7335.8	6823.1	6122.5	6672.4	7699.3	8121.9	8196.4	7231.7	6377.2	7419.6
52.5°	7421.2	7404.2	6930.3	6211.0	6765.6	7846.9	8524.2	8542.9	7494.2	6569.9	7421.2
55°	7865.5	7806.5	7237.9	6321.3	6697.3	7674.5	8267.9	8235.2	7405.7	6453.3	7557.9
57.5°	7197.5	7236.4	6812.3	5884.8	5861.4	6239.0	6500.0	6419.2	6179.9	5824.2	7031.3
60°	5807.1	5917.4	5957.8	4921.6	4422.9	4228.7	4151.0	4008.1	4048.5	4784.9	6176.8
62.5°	4980.7	4974.4	5227.7	4461.8	2897.3	2491.9	2454.5	2487.2	2953.3	4710.3	6049.5
65°	3949.1	4054.7	4132.4	3781.3	2293.0	1850.3	1848.7	2055.3	2555.5	3936.6	4884.3
67.5°	2507.4	2645.7	2742.0	2418.9	1533.3	1317.4	1281.7	1530.2	1771.1	2582.0	2940.8
70°	1413.7	1479.0	1522.5	1395.1	975.6	683.6	643.2	702.2	1070.3	1671.6	1743.1
72.5°	545.3	574.8	633.9	638.5	368.2	220.6	178.6	214.4	450.5	661.8	630.8
75°	83.9	90.1	127.4	152.2	105.6	80.8	85.4	88.6	125.8	170.9	142.9
77.5°	40.4	40.4	38.9	45.1	52.8	57.4	62.1	68.4	74.6	82.3	79.2
80°	26.4	26.4	26.4	31.0	38.9	46.6	52.8	55.9	59.0	65.3	62.1
82.5°	17.1	17.1	17.1	23.3	31.0	38.9	42.0	49.7	55.9	65.3	60.6
85°	9.3	9.3	9.3	15.6	23.3	32.6	31.0	24.9	14.0	1.5	3.1
87.5°	3.1	3.1	3.1	3.1	0.0	0.0	0.0	0.0	0.0	0.0	0.0
90°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0



REPORT NUMBER: P654265

CATALOG NUMBER: GLAN-SA3B-840-U-SLL-GRSWH

**CANDELA DISTRIBUTION (continued):**

	90°	95°	105°	115°	125°	135°	145°	155°	165°	175°	180°
0°	4746.0	4746.0	4746.0	4746.0	4746.0	4746.0	4746.0	4746.0	4746.0	4746.0	4746.0
2.5°	4884.3	4812.9	4806.7	4660.6	4530.1	4466.4	4415.2	4272.2	4303.3	4221.0	4219.4
5°	4648.1	4502.1	4266.0	4071.8	3877.6	3838.7	3669.5	3521.9	3526.5	3420.9	3439.5
7.5°	4224.1	4123.1	3835.6	3531.2	3273.3	3090.0	2930.0	2833.7	2710.9	2669.0	2647.2
10°	3955.3	3831.0	3507.9	3125.7	2836.8	2738.9	2585.1	2499.6	2373.8	2311.7	2268.2
12.5°	3837.2	3655.5	3251.6	2863.2	2670.5	2569.5	2439.1	2283.7	2134.5	2077.1	1997.9
15°	3849.7	3632.2	3177.0	2757.6	2526.0	2330.3	2213.8	2041.4	1889.1	1788.1	1730.6
17.5°	4037.6	3773.6	3211.1	2676.7	2344.3	2098.8	1870.5	1684.0	1562.8	1486.7	1468.0
20°	4481.9	4123.1	3268.6	2546.2	2162.5	1856.5	1575.3	1381.1	1287.9	1286.3	1287.9
22.5°	4851.6	4495.9	3385.1	2468.6	1980.7	1545.8	1266.1	1204.0	1185.3	1224.2	1228.9
25°	5350.4	4915.4	3585.5	2428.1	1812.9	1317.4	1144.9	1121.6	1120.1	1169.8	1171.3
27.5°	5861.4	5282.0	3705.2	2310.1	1642.1	1199.4	1071.9	1067.3	1092.1	1144.9	1140.3
30°	6209.4	5589.6	3921.1	2168.7	1440.1	1095.2	1042.4	1048.6	1082.8	1123.2	1129.4
32.5°	6615.0	5892.6	3977.0	2091.1	1315.8	1008.3	970.9	985.0	1028.5	1092.1	1126.4
35°	7079.5	6106.9	4062.5	1985.4	1269.2	941.4	922.8	938.3	991.1	1033.1	1070.3
37.5°	7422.8	6486.0	4078.0	1903.1	1217.9	904.2	874.6	925.9	957.0	1016.0	1034.7
40°	7677.6	6761.0	4118.4	1851.8	1177.6	856.0	856.0	890.2	932.1	986.5	1023.7
42.5°	7840.6	6961.4	4147.9	1805.2	1099.9	842.0	834.3	868.4	924.3	977.2	994.2
44°	7940.1	7046.8	4118.4	1761.7	1078.2	824.9	824.9	854.5	897.9	960.1	980.3
45°	7964.9	7154.0	4053.2	1760.1	1051.8	804.8	801.6	857.6	887.1	963.2	975.6
47.5°	8061.2	7286.1	4060.9	1710.4	988.0	756.6	811.0	835.8	862.2	929.1	970.9
50°	8058.1	7368.4	4043.9	1637.4	941.4	702.2	792.3	820.2	846.6	915.0	932.1
52.5°	8079.9	7676.0	4200.7	1520.9	857.6	632.3	730.2	792.3	824.9	882.4	918.1
55°	8069.1	7851.6	4356.1	1433.9	739.5	590.4	677.3	750.3	796.9	857.6	874.6
57.5°	7369.9	6939.6	4031.4	1270.8	612.1	540.6	602.7	706.9	765.9	828.0	849.7
60°	6021.5	5348.8	3324.6	935.2	503.3	497.1	560.9	692.9	717.7	772.1	809.4
62.5°	5564.7	4691.7	2636.4	714.6	430.3	455.1	517.3	626.0	664.9	731.8	765.9
65°	4354.5	3116.4	1632.8	483.2	379.0	408.6	467.6	548.4	612.1	674.2	714.6
67.5°	2578.8	1702.7	807.9	338.7	330.9	362.0	422.5	483.2	556.2	624.5	644.7
70°	1404.4	837.4	344.9	257.9	281.2	309.2	368.2	410.2	480.0	532.9	567.0
72.5°	450.5	254.7	172.4	191.1	214.4	247.0	282.7	334.0	383.7	414.8	442.8
75°	108.7	107.2	122.7	133.6	155.3	180.2	209.7	236.2	275.0	304.5	329.3
77.5°	76.1	82.3	94.8	110.3	118.1	127.4	146.0	166.3	183.3	205.0	220.6
80°	59.0	63.7	73.0	80.8	88.6	96.3	105.6	113.4	124.3	138.3	146.0
82.5°	55.9	59.0	68.4	73.0	69.9	68.4	74.6	77.7	79.2	83.9	88.6
85°	4.6	0.0	3.1	10.8	26.4	38.9	42.0	42.0	40.4	43.5	43.5
87.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	1.5	6.2	4.6
90°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0





REPORT NUMBER: P654265

CATALOG NUMBER: GLAN-SA3B-840-U-SLL-GRSWH

**CANDELA DISTRIBUTION (continued):**

	185°	195°	205°	215°	225°	235°	245°	255°	265°	270°	275°
0°	4746.0	4746.0	4746.0	4746.0	4746.0	4746.0	4746.0	4746.0	4746.0	4746.0	4746.0
2.5°	4200.7	4147.9	4168.2	4193.0	4157.2	4074.9	4096.7	4087.3	4171.2	4165.1	4248.9
5°	3521.9	3439.5	3448.9	3570.0	3531.2	3573.2	3489.2	3478.4	3493.9	3501.7	3515.6
7.5°	2695.4	2684.5	2777.7	2880.3	2928.4	2878.7	2796.3	2777.7	2760.6	2726.4	2804.1
10°	2199.8	2202.9	2196.7	2274.4	2328.7	2317.9	2268.2	2262.0	2229.3	2216.9	2260.4
12.5°	1963.7	1921.7	1901.5	1876.7	1918.6	1946.6	1924.8	1909.3	1910.8	1926.4	1932.6
15°	1735.3	1708.9	1665.3	1637.4	1657.6	1643.7	1635.8	1666.9	1659.2	1656.1	1693.4
17.5°	1479.0	1500.7	1497.6	1466.5	1492.9	1482.1	1480.5	1458.8	1429.3	1407.5	1419.9
20°	1309.6	1350.1	1381.1	1382.6	1396.6	1395.1	1371.8	1305.0	1283.2	1278.6	1281.7
22.5°	1249.1	1270.8	1308.1	1360.9	1360.9	1336.0	1308.1	1230.4	1210.2	1188.4	1179.2
25°	1200.9	1242.8	1291.0	1297.2	1322.1	1298.8	1253.7	1214.8	1172.9	1143.4	1143.4
27.5°	1176.1	1222.6	1258.4	1269.2	1303.4	1284.8	1238.2	1188.4	1138.7	1137.2	1110.8
30°	1165.1	1208.7	1232.0	1258.4	1273.9	1244.3	1230.4	1177.6	1127.9	1115.4	1071.9
32.5°	1132.5	1194.6	1238.2	1232.0	1244.3	1232.0	1211.7	1168.2	1112.3	1084.4	1079.7
35°	1095.2	1157.4	1204.0	1236.6	1244.3	1217.9	1205.6	1146.5	1070.3	1056.4	1008.3
37.5°	1075.1	1112.3	1169.8	1222.6	1233.5	1219.5	1177.6	1117.0	1040.9	1025.3	983.4
40°	1050.2	1098.3	1143.4	1186.9	1219.5	1185.3	1137.2	1078.2	1043.9	997.3	985.0
42.5°	1031.6	1085.9	1123.2	1171.3	1208.7	1163.6	1107.7	1067.3	1019.1	988.0	952.3
44°	1025.3	1075.1	1099.9	1158.9	1190.0	1155.8	1109.2	1067.3	1011.4	983.4	952.3
45°	1003.6	1071.9	1098.3	1151.2	1177.6	1149.6	1090.6	1048.6	1008.3	974.0	941.4
47.5°	981.9	1028.5	1073.5	1115.4	1134.1	1124.8	1075.1	1023.7	975.6	955.5	924.3
50°	975.6	1022.2	1064.2	1103.0	1124.8	1106.1	1061.1	1011.4	955.5	922.8	896.4
52.5°	944.5	1002.1	1048.6	1061.1	1089.0	1078.2	1043.9	989.6	936.8	908.8	887.1
55°	899.5	960.1	1023.7	1039.3	1079.7	1062.6	1011.4	960.1	915.0	873.1	845.1
57.5°	882.4	941.4	1003.6	1023.7	1048.6	1020.6	1008.3	953.9	882.4	860.7	817.1
60°	838.9	913.5	964.7	1011.4	1012.9	1005.2	983.4	921.2	862.2	821.8	790.7
62.5°	804.8	874.6	915.0	958.5	985.0	963.2	941.4	884.0	820.2	775.2	739.5
65°	755.0	818.7	852.9	879.3	908.8	905.7	868.4	826.5	759.7	723.9	689.8
67.5°	678.9	734.8	781.5	806.3	824.9	820.2	792.3	762.8	694.4	658.7	633.9
70°	587.3	644.7	674.2	688.2	706.9	716.2	694.4	680.5	619.8	573.2	549.9
72.5°	472.3	509.6	553.0	565.5	573.2	579.4	579.4	567.0	504.9	486.3	445.9
75°	348.0	377.5	410.2	410.2	424.1	425.6	428.7	421.0	374.4	349.5	340.2
77.5°	236.2	257.9	284.3	295.2	304.5	302.9	301.4	279.6	254.7	243.9	234.6
80°	153.8	175.5	188.0	201.9	211.3	209.7	212.9	197.3	186.4	167.8	170.9
82.5°	91.7	108.7	121.2	138.3	138.3	142.9	142.9	138.3	127.4	118.1	118.1
85°	43.5	57.4	65.3	76.1	82.3	83.9	74.6	63.7	52.8	48.2	52.8
87.5°	7.7	10.8	15.6	14.0	17.1	15.6	15.6	15.6	15.6	12.4	14.0
90°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0



REPORT NUMBER: P654265

CATALOG NUMBER: GLAN-SA3B-840-U-SLL-GRSWH

**CANDELA DISTRIBUTION (continued):**

	285°	295°	305°	315°	325°	335°	345°	355°	359°	360°
0°	4746.0	4746.0	4746.0	4746.0	4746.0	4746.0	4746.0	4746.0	4746.0	4746.0
2.5°	4217.9	4295.5	4349.9	4440.0	4595.3	4719.6	4847.0	4941.8	4952.6	4980.7
5°	3566.9	3608.8	3747.1	3927.3	4054.7	4264.5	4399.6	4645.1	4736.7	4834.6
7.5°	2785.5	2853.8	3038.7	3159.9	3439.5	3702.1	3973.9	4276.9	4398.0	4412.1
10°	2348.9	2448.4	2574.2	2768.4	2920.6	3212.7	3551.4	3888.4	4023.7	4047.0
12.5°	2063.1	2190.5	2358.2	2498.1	2644.1	2898.9	3223.6	3639.9	3815.4	3921.1
15°	1788.1	1920.2	2105.0	2299.2	2428.1	2732.7	3114.8	3584.0	3812.3	3905.6
17.5°	1505.4	1628.1	1780.3	1990.1	2249.5	2591.3	3097.7	3770.5	4020.6	4129.3
20°	1263.0	1331.4	1508.5	1724.4	2049.1	2446.8	3104.0	4045.4	4412.1	4460.2
22.5°	1168.2	1183.8	1253.7	1452.6	1808.3	2299.2	3214.2	4435.3	4851.6	5010.2
25°	1095.2	1092.1	1110.8	1244.3	1632.8	2241.8	3323.0	4794.2	5339.5	5511.9
27.5°	1054.9	1023.7	1025.3	1151.2	1508.5	2148.5	3462.8	5205.9	5892.6	5968.7
30°	1034.7	1028.5	1009.8	1061.1	1373.4	2008.7	3486.1	5611.3	6218.8	6329.1
32.5°	1022.2	961.6	938.3	957.0	1245.9	1856.5	3573.2	5878.6	6622.7	6574.5
35°	960.1	905.7	890.2	908.8	1155.8	1771.1	3515.6	6111.6	6925.6	7006.5
37.5°	936.8	888.6	857.6	842.0	1071.9	1699.6	3486.1	6470.5	7219.2	7413.4
40°	915.0	863.8	826.5	811.0	1006.7	1604.8	3476.8	6747.0	7557.9	7674.5
42.5°	890.2	857.6	815.6	787.7	927.5	1510.0	3369.6	6832.5	7662.0	7787.8
44°	882.4	832.7	789.2	779.9	896.4	1461.9	3347.9	6910.1	7752.1	7943.2
45°	874.6	828.0	778.3	765.9	885.5	1435.5	3318.3	6928.7	7901.3	7937.0
47.5°	852.9	823.3	775.2	741.0	862.2	1378.0	3229.8	6823.1	7749.0	7755.2
50°	835.8	801.6	751.9	685.1	831.2	1329.8	3270.1	6784.3	7382.4	7396.3
52.5°	817.1	765.9	737.9	622.9	779.9	1289.4	3355.6	6959.8	7424.3	7421.2
55°	795.4	739.5	671.1	570.1	694.4	1238.2	3562.2	7306.3	7812.7	7865.5
57.5°	761.2	713.1	615.2	523.5	596.5	1140.3	3495.4	6642.9	7188.2	7197.5
60°	716.2	671.1	557.8	487.8	489.4	899.5	3125.7	5176.4	5672.0	5807.1
62.5°	672.7	647.8	509.6	436.6	416.4	716.2	2642.6	4301.7	4868.8	4980.7
65°	621.4	560.9	467.6	397.7	357.3	501.8	1872.0	3214.2	3798.4	3949.1
67.5°	556.2	490.9	411.7	349.5	306.0	335.6	966.3	1827.0	2418.9	2507.4
70°	486.3	425.6	346.4	295.2	247.0	231.4	425.6	871.5	1322.1	1413.7
72.5°	399.2	343.3	276.5	233.0	184.9	160.0	142.9	233.0	469.2	545.3
75°	289.0	250.1	208.1	166.3	130.5	102.5	83.9	69.9	77.7	83.9
77.5°	212.9	181.7	153.8	118.1	91.7	73.0	57.4	43.5	42.0	40.4
80°	166.3	147.6	122.7	94.8	71.5	54.4	40.4	29.5	26.4	26.4
82.5°	130.5	121.2	101.0	77.7	59.0	43.5	29.5	20.2	17.1	17.1
85°	49.7	49.7	73.0	63.7	45.1	31.0	20.2	10.8	9.3	9.3
87.5°	12.4	12.4	12.4	12.4	10.8	9.3	9.3	4.6	3.1	3.1
90°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0

(END OF REPORT)