

Scaled data based on original data using
LM-79-08 Approved Method: Electrical and Photometric Measurements of Solid-
State Lighting Products

Test Report Prepared for
Cooper Lighting Solutions
(formerly Eaton)

Brand: STREETWORKS

Report Number: P949837

Luminaire Tested: **GLAN-SB4C-722-U-SLL-HSS**

Issue Date: 1/21/2025

Test Information

Test Method: LM-79-08
Report Number: P949837
TEST IS SCALED FROM IESNA LM-79-08 TEST DATA (G2-2411-289-9)
Test Lab: INNOVATION CENTER
Issue Date: 1/21/2025
Manufacturer: COOPER LIGHTING SOLUTIONS (FORMERLY EATON)
Product Line: STREETWORKS
Catalog Number: GLAN-SB4C-722-U-SLL-HSS
Description: GALLEON AREA AND ROADWAY HIGH DENSITY LED LUMINAIRE
(4) 70 CRI, 2200K, 615mA LIGHTSQUARES WITH 26 LEDS EACH AND SPILL LIGHT
ELIMINATOR LEFT OPTICS WITH HOUSE SIDE SHIELD
Light Source: -
Ballast/Driver: -

Summary

Lumens per Lamp: N/A
Luminaire Lumens: 18923 lumens
Efficiency: N/A
Efficacy: 94.3 lumens/watt
Luminous Opening: Rectangular (W 1' x L: 1' x H: 0')
IES Classification: Type IV - Short
BUG Rating: B2 - U0 - G4

Input Watts (W): 200.7
Input Voltage (V): NR
Input Current (Ain): NR
Voltage Rise (V): NR
Power Factor: NR
Total Harmonic Distortion (THDi): NR
Frequency (hertz): 60
Stabilization Time: NR
Operation Time: NR
Ambient Temperature (°C): NR
Test Distance: 24 FT




REPORT NUMBER: P949837

CATALOG NUMBER: GLAN-SB4C-722-U-SLL-HSS


Iso-Footcandle Lines of Horizontal Illumination

× Max cd
 --- 1/2 Max cd



Based on 25 foot mounting height. Maximum calculated value = 6.9 fc
 Type IV - Short - N/A

REPORT NUMBER: P949837
CATALOG NUMBER: GLAN-SB4C-722-U-SLL-HSS



REPORT NUMBER: P949837

CATALOG NUMBER: GLAN-SB4C-722-U-SLL-HSS

FLUX DISTRIBUTION:

		Downward	Upward	Total
House Side	Lumens	3761.3	0.0	3761.3
	% Fixture	19.9	0.0	19.9
Street Side	Lumens	15161.7	0.0	15161.7
	% Fixture	80.1	0.0	80.1
Total	Lumens	18923.0	0.0	18923.0
	% Fixture	100.0	0.0	100.0

ZONAL LUMENS:

Zone	Lumens	% Fixture
0°-10°	258.0	1.4
10°-20°	773.3	4.1
20°-30°	1139.3	6.0
30°-40°	1463.6	7.7
40°-50°	2367.1	12.5
50°-60°	4151.0	21.9
60°-70°	5194.0	27.4
70°-80°	3035.1	16.0
80°-90°	541.5	2.9
90°-100°	0.0	0.0
100°-110°	0.0	0.0
110°-120°	0.0	0.0
120°-130°	0.0	0.0
130°-140°	0.0	0.0
140°-150°	0.0	0.0
150°-160°	0.0	0.0
160°-170°	0.0	0.0
170°-180°	0.0	0.0
0°-90°	18923.0	100.0
0°-180°	18923.0	100.0

Coefficient of Utilization



REPORT NUMBER: P949837


CATALOG NUMBER: GLAN-SB4C-722-U-SLL-HSS

LUMINAIRE CLASSIFICATION SYSTEM LUMEN TABLE AND BUG RATING:

Zone		Lumens	% Fixture	Zone Rating/Lumen Limit		
				B	U	G
FL	(0°-30°)	1266.2	6.7			
FM	(30°-60°)	5938.3	31.4			
FH	(60°-80°)	7441.1	39.3			G3/7500
FVH	(80°-90°)	516.1	2.7			G4/750
BL	(0°-30°)	904.4	4.8	B2/1000		
BM	(30°-60°)	2043.5	10.8	B2/2500		
BH	(60°-80°)	788.1	4.2	B2/1000		G2/1000
BVH	(80°-90°)	25.4	0.1			G1/100
UL	(90°-100°)	0.0	0.0		U0/0	
UH	(100°-180°)	0.0	0.0		U0/0	

BUG Rating: B2-U0-G4

Type IV Short



REPORT NUMBER: P949837

CATALOG NUMBER: GLAN-SB4C-722-U-SLL-HSS

CANDELA DISTRIBUTION (FULL):

	0°	5°	15°	25°	35°	45°	55°	65°	75°	85°
0°	2620.2	2620.2	2620.2	2620.2	2620.2	2620.2	2620.2	2620.2	2620.2	2620.2
2.5°	2935.7	2957.9	3007.4	3033.5	3073.9	3076.5	3076.5	3041.3	3040.0	2968.3
5°	3281.2	3333.3	3450.6	3571.9	3597.9	3604.4	3591.4	3521.0	3468.9	3329.4
7.5°	3624.0	3724.4	3903.0	4064.6	4116.8	4116.8	4085.5	3970.8	3863.9	3661.8
10°	3908.2	4034.6	4277.1	4458.3	4518.3	4505.2	4441.4	4296.7	4149.3	3904.3
12.5°	4095.9	4238.0	4503.9	4649.9	4711.2	4677.3	4604.3	4463.5	4308.4	4050.3
15°	4189.8	4338.4	4569.1	4646.0	4629.1	4593.9	4584.8	4517.0	4399.6	4158.5
17.5°	4230.2	4368.4	4528.7	4480.5	4337.1	4309.7	4400.9	4487.0	4458.3	4252.3
20°	4268.0	4384.0	4432.2	4218.4	3968.1	3943.4	4118.1	4363.1	4488.3	4339.7
22.5°	4320.1	4391.8	4292.7	3942.1	3672.2	3614.9	3807.8	4176.7	4497.4	4450.5
25°	4391.8	4411.4	4138.9	3680.1	3408.9	3351.5	3531.4	3969.5	4481.8	4570.4
27.5°	4477.9	4437.4	3991.6	3461.1	3199.0	3145.6	3325.5	3770.0	4437.4	4690.3
30°	4590.0	4471.3	3845.6	3291.6	3049.1	3010.0	3183.4	3597.9	4382.7	4842.9
32.5°	4703.4	4485.7	3710.0	3192.5	3015.2	3029.6	3171.7	3505.4	4322.7	4988.9
35°	4825.9	4531.3	3643.6	3290.3	3298.1	3423.2	3481.9	3591.4	4313.6	5187.0
37.5°	4992.8	4633.0	3723.1	3776.5	4047.7	4307.1	4258.9	4012.5	4419.2	5482.9
40°	5232.6	4811.6	4069.8	4604.3	5160.9	5582.0	5398.2	4777.7	4742.5	5909.2
42.5°	5582.0	5095.8	4685.1	5615.9	6559.7	7253.2	6760.5	5764.5	5308.2	6518.0
45°	6098.2	5555.9	5429.5	6683.5	8284.4	9376.8	8352.1	6816.5	6100.8	7439.6
47.5°	6813.9	6232.5	6126.9	7808.5	10380.5	11793.6	10117.2	7791.6	7002.9	8696.3
50°	7764.2	7143.7	6787.8	9039.1	12678.8	14257.4	11881.0	8732.8	8036.7	10231.9
52.5°	9018.3	8414.7	7558.3	10211.1	15042.2	16669.1	13652.6	9559.3	9319.4	12014.0
55°	10728.6	10327.1	8611.6	11329.6	17404.3	19095.1	15355.1	10338.8	11014.1	14131.0
57.5°	12850.9	13137.7	10130.3	12626.6	19527.9	21595.4	17065.4	11428.6	13214.6	16498.3
60°	14219.6	16875.1	13038.6	14544.2	21940.8	24422.9	19409.3	13501.4	15527.1	17347.0
62.5°	13888.5	18063.9	16521.8	16992.4	24159.6	26478.7	21706.2	15583.2	15962.5	16096.8
65°	12873.0	17104.5	15811.3	17468.2	24721.4	26594.7	22320.2	15314.7	13540.5	13141.6
67.5°	11475.6	15966.5	14123.2	16206.3	23705.9	24973.0	21176.9	13547.0	10464.0	9861.7
70°	9967.3	14707.2	13015.1	14790.6	21770.1	22146.8	19233.3	11914.9	7696.4	6660.1
72.5°	8536.0	13395.8	12256.4	13339.7	19187.6	18408.1	16703.0	10471.8	5604.2	4803.8
75°	7072.0	11461.2	11175.7	11616.4	15791.8	14499.9	13878.1	8670.2	4398.3	3475.4
77.5°	5456.9	8955.7	9612.7	9302.5	11115.8	10770.3	10757.3	6515.4	3213.4	2319.1
80°	3734.8	6241.6	7510.0	6562.3	7214.1	7038.1	8101.9	4371.0	2330.8	1396.2
82.5°	2195.3	3800.0	5227.4	3176.9	3989.0	4094.6	4824.6	2126.2	1371.4	322.0
85°	890.4	1500.4	2044.0	1243.6	1924.1	1623.0	1831.6	597.0	382.0	7.8
87.5°	224.2	479.7	336.3	139.5	222.9	204.7	161.6	73.0	15.6	0.0
90°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0

REPORT NUMBER: P949837

CATALOG NUMBER: GLAN-SB4C-722-U-SLL-HSS

CANDELA DISTRIBUTION (continued):

90°		95°	105°	115°	125°	135°	145°	155°	165°	175°	180°
2620.2	0°	2620.2	2620.2	2620.2	2620.2	2620.2	2620.2	2620.2	2620.2	2620.2	2620.2
2960.5	2.5°	2909.6	2879.6	2805.3	2731.0	2671.1	2590.2	2536.8	2472.9	2411.7	2356.9
3299.4	5°	3217.3	3118.2	2982.6	2858.8	2732.3	2609.8	2488.6	2360.8	2243.5	2171.8
3586.2	7.5°	3467.6	3292.9	3113.0	2955.3	2802.7	2659.3	2499.0	2343.9	2160.1	2062.3
3805.2	10°	3654.0	3424.5	3188.6	3007.4	2853.6	2714.1	2578.5	2422.1	2200.5	2077.9
3938.2	12.5°	3776.5	3504.1	3227.7	3020.4	2848.4	2740.2	2680.2	2618.9	2398.6	2255.2
4035.9	15°	3861.3	3560.1	3255.1	2990.5	2779.3	2699.7	2759.7	2830.1	2689.3	2523.8
4137.6	17.5°	3953.8	3633.1	3266.8	2909.6	2645.0	2611.1	2766.2	2929.2	2922.7	2758.4
4234.1	20°	4051.6	3697.0	3259.0	2779.3	2482.0	2512.0	2710.2	2899.2	2978.7	2890.1
4344.9	22.5°	4152.0	3758.3	3229.0	2609.8	2329.5	2423.4	2621.5	2787.1	2880.9	2853.6
4480.5	25°	4278.4	3844.3	3184.7	2427.3	2203.1	2333.4	2518.5	2652.8	2718.0	2716.7
4626.5	27.5°	4429.6	3959.0	3161.2	2280.0	2113.1	2231.8	2396.0	2515.9	2561.6	2561.6
4807.7	30°	4605.6	4094.6	3135.2	2183.5	2061.0	2126.2	2253.9	2371.2	2416.9	2416.9
5005.8	32.5°	4801.1	4225.0	3072.6	2124.9	2021.9	2023.2	2104.0	2210.9	2265.7	2273.5
5253.5	35°	5035.8	4364.4	2935.7	2077.9	1976.3	1922.8	1961.9	2050.6	2115.7	2132.7
5606.8	37.5°	5343.4	4535.2	2740.2	2008.8	1905.9	1817.2	1826.3	1894.1	1965.8	1991.9
6094.3	40°	5756.7	4736.0	2536.8	1909.8	1806.8	1701.2	1697.3	1746.8	1817.2	1845.9
6753.9	42.5°	6302.9	4977.1	2342.6	1814.6	1686.9	1578.7	1572.1	1611.2	1672.5	1702.5
7624.7	45°	7001.6	5273.0	2175.7	1740.3	1569.5	1462.6	1460.0	1492.6	1546.1	1577.4
8739.3	47.5°	7972.8	5569.0	2062.3	1701.2	1477.0	1367.5	1372.7	1401.4	1449.6	1471.8
10182.4	50°	9238.6	5658.9	2004.9	1701.2	1427.4	1282.7	1308.8	1332.3	1368.8	1381.8
11912.3	52.5°	10453.5	5361.7	1952.8	1711.6	1434.0	1211.0	1267.1	1284.0	1315.3	1320.5
13515.7	55°	11049.3	4609.5	1881.1	1714.2	1474.4	1149.8	1233.2	1264.5	1276.2	1274.9
14446.5	57.5°	10844.6	3727.0	1759.9	1703.8	1501.7	1110.7	1191.5	1251.5	1259.3	1247.5
14269.2	60°	10126.3	2744.1	1667.3	1626.9	1491.3	1098.9	1127.6	1222.8	1234.5	1218.9
12903.0	62.5°	8921.8	1904.6	1595.6	1457.4	1445.7	1095.0	1027.2	1160.2	1188.9	1166.7
10371.4	65°	7023.8	1345.3	1374.0	1277.5	1346.6	1074.2	922.9	1084.6	1123.7	1089.8
7524.4	67.5°	4752.9	971.2	1113.3	1157.6	1186.3	1027.2	847.3	998.6	1050.7	1006.4
4828.5	70°	2566.8	681.8	735.2	975.1	1007.7	946.4	779.6	911.2	971.2	922.9
3432.4	72.5°	1516.1	490.2	514.9	783.5	839.5	833.0	703.9	809.5	882.5	825.2
2368.6	75°	835.6	331.1	367.6	568.4	681.8	642.7	604.9	685.7	760.0	703.9
1484.8	77.5°	374.1	198.1	255.5	372.8	535.8	440.6	468.0	534.5	603.6	544.9
826.5	80°	144.7	110.8	169.5	203.4	389.8	243.8	301.1	393.7	443.2	396.3
179.9	82.5°	18.3	49.5	73.0	79.5	226.8	129.1	174.7	247.7	243.8	211.2
0.0	85°	0.0	9.1	10.4	5.2	97.8	46.9	57.4	80.8	75.6	57.4
0.0	87.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	2.6	0.0
0.0	90°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0

REPORT NUMBER: P949837

CATALOG NUMBER: GLAN-SB4C-722-U-SLL-HSS

CANDELA DISTRIBUTION (continued):

185°		195°	205°	215°	225°	235°	245°	255°	265°	270°	275°
2620.2	0°	2620.2	2620.2	2620.2	2620.2	2620.2	2620.2	2620.2	2620.2	2620.2	2620.2
2346.5	2.5°	2282.6	2235.7	2212.2	2192.7	2210.9	2221.3	2221.3	2265.7	2291.7	2302.2
2126.2	5°	2011.5	1924.1	1865.4	1830.3	1842.0	1855.0	1869.4	1925.4	1963.2	1988.0
1973.6	7.5°	1797.7	1664.7	1582.6	1539.5	1546.1	1555.2	1566.9	1621.7	1659.5	1692.1
1945.0	10°	1692.1	1504.4	1396.2	1344.0	1334.9	1329.7	1325.8	1358.3	1387.0	1413.1
2062.3	12.5°	1697.3	1435.3	1303.6	1239.7	1212.3	1181.1	1156.3	1161.5	1179.8	1212.3
2272.2	15°	1763.8	1413.1	1255.4	1175.8	1130.2	1093.7	1063.7	1057.2	1063.7	1068.9
2512.0	17.5°	1853.7	1410.5	1213.6	1114.6	1067.6	1037.7	1010.3	1001.2	1002.5	1009.0
2671.1	20°	1925.4	1402.7	1166.7	1055.9	1014.2	988.1	960.8	951.6	954.2	955.5
2686.7	22.5°	1963.2	1390.9	1114.6	997.3	962.1	936.0	911.2	909.9	909.9	917.7
2602.0	25°	1963.2	1366.2	1067.6	941.2	909.9	886.4	856.5	861.7	864.3	874.7
2470.3	27.5°	1916.3	1319.2	1029.8	893.0	860.4	836.9	809.5	816.1	820.0	831.7
2340.0	30°	1856.3	1263.2	986.8	847.3	809.5	792.6	769.1	771.7	776.9	790.0
2218.7	32.5°	1792.4	1196.7	951.6	801.7	763.9	750.9	724.8	728.7	733.9	748.3
2098.8	35°	1722.1	1118.5	909.9	760.0	722.2	711.8	681.8	684.4	692.2	707.9
1969.7	37.5°	1647.7	1054.6	868.2	719.6	680.5	670.0	638.8	641.4	650.5	668.7
1834.2	40°	1574.7	992.0	823.9	676.6	637.5	628.3	594.4	597.0	607.5	627.0
1697.3	42.5°	1495.2	943.8	766.5	632.2	590.5	581.4	550.1	554.0	565.8	585.3
1570.8	45°	1400.1	912.5	702.6	590.5	543.6	534.5	505.8	513.6	526.7	546.2
1462.6	47.5°	1302.3	899.5	649.2	546.2	495.4	487.5	464.1	477.1	491.5	507.1
1370.1	50°	1208.4	882.5	594.4	504.5	453.7	445.8	430.2	447.1	461.5	475.8
1303.6	52.5°	1101.5	846.0	544.9	468.0	418.5	415.8	408.0	423.7	436.7	449.7
1246.2	55°	990.7	787.4	501.9	435.4	388.5	391.1	387.2	400.2	410.6	422.4
1194.1	57.5°	894.3	713.1	468.0	400.2	362.4	370.2	365.0	371.5	378.0	392.4
1131.5	60°	796.5	624.4	430.2	358.5	336.3	345.5	331.1	329.8	332.4	336.3
1039.0	62.5°	664.8	531.9	383.3	322.0	307.6	311.6	284.2	263.3	263.3	267.2
909.9	65°	534.5	445.8	331.1	280.3	268.5	265.9	226.8	198.1	195.5	207.3
760.0	67.5°	439.3	370.2	279.0	233.3	225.5	228.1	199.5	170.8	168.2	181.2
619.2	70°	363.7	298.5	222.9	179.9	187.7	199.5	170.8	143.4	139.5	151.2
503.2	72.5°	289.4	233.3	170.8	133.0	155.1	169.5	139.5	113.4	110.8	121.2
388.5	75°	212.5	166.9	116.0	96.5	119.9	133.0	101.7	80.8	76.9	86.0
259.4	77.5°	131.7	93.9	73.0	57.4	82.1	88.6	53.4	46.9	45.6	52.1
157.7	80°	61.3	40.4	35.2	19.6	30.0	35.2	22.2	24.8	26.1	31.3
79.5	82.5°	16.9	6.5	1.3	0.0	0.0	10.4	5.2	10.4	13.0	19.6
6.5	85°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	2.6	6.5	11.7
0.0	87.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	5.2
0.0	90°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0

REPORT NUMBER: P949837

CATALOG NUMBER: GLAN-SB4C-722-U-SLL-HSS

CANDELA DISTRIBUTION (continued):

285°		295°	305°	315°	325°	335°	345°	355°	360°
2620.2	0°	2620.2	2620.2	2620.2	2620.2	2620.2	2620.2	2620.2	2620.2
2375.2	2.5°	2429.9	2482.0	2565.5	2651.5	2736.3	2822.3	2905.7	2935.7
2101.4	5°	2204.4	2324.3	2489.9	2667.2	2849.7	3034.8	3204.2	3281.2
1818.5	7.5°	1952.8	2124.9	2373.9	2651.5	2942.2	3232.9	3500.2	3624.0
1538.2	10°	1684.2	1901.9	2186.1	2561.6	2978.7	3380.2	3747.8	3908.2
1291.9	12.5°	1428.7	1656.9	1971.0	2420.8	2950.0	3465.0	3906.9	4095.9
1118.5	15°	1215.0	1417.0	1755.9	2253.9	2857.5	3470.2	3982.5	4189.8
1022.0	17.5°	1054.6	1186.3	1536.9	2068.8	2736.3	3421.9	4008.6	4230.2
969.9	20°	975.1	1011.6	1252.8	1831.6	2622.8	3376.3	4034.6	4268.0
928.2	22.5°	928.2	937.3	1024.6	1525.2	2487.3	3362.0	4080.3	4320.1
890.4	25°	890.4	893.0	916.4	1208.4	2280.0	3352.9	4150.7	4391.8
851.2	27.5°	852.6	852.6	865.6	973.8	1998.4	3313.7	4241.9	4477.9
812.1	30°	814.7	814.7	823.9	861.7	1668.6	3236.8	4351.4	4590.0
773.0	32.5°	775.6	775.6	783.5	810.8	1332.3	3140.4	4451.8	4703.4
732.6	35°	736.5	733.9	744.4	773.0	1059.8	3017.8	4552.2	4825.9
692.2	37.5°	694.8	693.5	703.9	736.5	915.1	2875.7	4627.8	4992.8
651.8	40°	650.5	650.5	662.2	697.4	873.4	2697.1	4747.7	5232.6
610.1	42.5°	610.1	607.5	620.5	663.5	842.1	2526.4	4962.8	5582.0
572.3	45°	571.0	565.8	577.5	630.9	787.4	2466.4	5364.3	6098.2
535.8	47.5°	534.5	521.4	531.9	591.8	737.8	2690.6	6021.3	6813.9
503.2	50°	504.5	479.7	488.8	552.7	700.0	3176.9	6873.9	7764.2
473.2	52.5°	473.2	440.6	445.8	504.5	666.1	3639.6	7798.1	9018.3
443.2	55°	440.6	404.1	406.7	456.3	617.9	3708.7	8700.2	10728.6
409.3	57.5°	404.1	370.2	370.2	411.9	582.7	3214.7	9393.7	12850.9
367.6	60°	363.7	341.5	335.0	376.7	614.0	2268.3	9474.5	14219.6
314.2	62.5°	319.4	307.6	298.5	342.8	637.5	1344.0	8824.0	13888.5
247.7	65°	268.5	265.9	259.4	376.7	537.1	793.9	7575.2	12873.0
211.2	67.5°	225.5	221.6	221.6	395.0	408.0	499.3	5918.3	11475.6
179.9	70°	194.2	179.9	179.9	298.5	247.7	345.5	4132.4	9967.3
148.6	72.5°	162.9	147.3	136.9	238.6	185.1	252.9	2582.4	8536.0
113.4	75°	130.4	118.6	105.6	157.7	138.2	191.6	1500.4	7072.0
71.7	77.5°	93.9	88.6	74.3	116.0	100.4	138.2	893.0	5456.9
44.3	80°	48.2	49.5	46.9	66.5	67.8	93.9	508.4	3734.8
28.7	82.5°	28.7	22.2	24.8	32.6	39.1	53.4	191.6	2195.3
20.9	85°	18.3	11.7	11.7	15.6	19.6	20.9	58.7	890.4
10.4	87.5°	9.1	3.9	5.2	7.8	6.5	5.2	2.6	224.2
0.0	90°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0

(END OF REPORT)