Cooper Lighting Solutions Photometric Lab
1121 Highway 74 South
Peachtree City, GA 30269

Cooper Lighting Solutions Photometric Lab
1121 Highway 74 South
Peachtree City, GA 30269

Scaled data based on original data using

LM-79-08 Approved Method: Electrical and Photometric Measurements of Solid-State Lighting Products

Test Report Prepared for

Cooper Lighting Solutions

(formerly Eaton)

Brand: STREETWORKS

Report Number: P947338

Luminaire Tested: **GLAN-SB2D-722-U-SLL-HSS**

Issue Date: 1/21/2025

Report Generated By 670246001

Cooper Lighting Solutions Photometric Lab
1121 Highway 74 South
Peachtree City, GA 30269

Test Information

Test Method:	LM-79-08
Report Number:	P947338
	TEST IS SCALED FROM IESNA LM-79-08 TEST DATA (G2-2411-289-9)
Test Lab:	INNOVATION CENTER
Issue Date:	1/21/2025
Manufacturer:	COOPER LIGHTING SOLUTIONS (FORMERLY EATON)
Product Line:	STREETWORKS
Catalog Number:	GLAN-SB2D-722-U-SLL-HSS
Description:	GALLEON AREA AND ROADWAY HIGH DENSITY LED LUMINAIRE
	(2) 70 CRI, 2200K, 900mA LIGHTSQUARES WITH 26 LEDS EACH AND SPILL LIGHT ELIMINATOR LEFT OPTICS WITH HOUSE SIDE SHIELD
Light Source:	-
Ballast/Driver:	-

Summary

Lumens per Lamp:	N/A
Luminaire Lumens:	12830 lumens
Efficiency:	N/A
Efficacy:	86.9 lumens/watt
Luminous Opening:	Rectangular (W 0.5' x L: 1' x H: 0')
IES Classification:	Type IV - Short
BUG Rating:	B2 - U0 - G3

Input Watts (W):	147.6
Input Voltage (V):	NR
Input Current (Ain):	NR
Voltage Rise (V):	NR
Power Factor:	NR
Total Harmonic Distortion (THDi):	NR
Frequency (hertz):	60
Stabilization Time:	NR
Operation Time:	NR
Ambient Temperature (°C):	NR
Test Distance:	24 FT

Cooper Lighting Solutions Photometric Lab
1121 Highway 74 South
Peachtree City, GA 30269

REPORT NUMBER: P947338
CATALOG NUMBER: GLAN-SB2D-722-U-SLL-HSS

Iso-Footcandle Lines of Horizontal Illumination



Based on 25 foot mounting height. Maximum calculated value = 4.7 fc
Type IV - Short - N/A

Cooper Lighting Solutions Photometric Lab
1121 Highway 74 South
Peachtree City, GA 30269

REPORT NUMBER: P947338
CATALOG NUMBER: GLAN-SB2D-722-U-SLL-HSS

Luminous Intensity Polar Plot



Cooper Lighting Solutions Photometric Lab
1121 Highway 74 South
Peachtree City, GA 30269

REPORT NUMBER: P947338
CATALOG NUMBER: GLAN-SB2D-722-U-SLL-HSS

FLUX DISTRIBUTION:

		Downward	Upward	Total
House Side	Lumens	2550.2	0.0	2550.2
	% Fixture	19.9	0.0	19.9
Street Side	Lumens	10279.8	0.0	10279.8
	% Fixture	80.1	0.0	80.1
Total	Lumens	12830.0	0.0	12830.0
	% Fixture	100.0	0.0	100.0

ZONAL LUMENS:

Zone	Lumens	% Fixture
0°-10°	174.9	1.4
10°-20°	524.3	4.1
20°-30°	772.4	6.0
30°-40°	992.4	7.7
40°-50°	1604.9	12.5
50°-60°	2814.4	21.9
60°-70°	3521.6	27.4
70°-80°	2057.9	16.0
80°-90°	367.2	2.9
90°-100°	0.0	0.0
100°-110°	0.0	0.0
110°-120°	0.0	0.0
120°-130°	0.0	0.0
130°-140°	0.0	0.0
140°-150°	0.0	0.0
150°-160°	0.0	0.0
160°-170°	0.0	0.0
170°-180°	0.0	0.0
0°-90°	12830.0	100.0
0°-180°	12830.0	100.0



Cooper Lighting Solutions Photometric Lab
1121 Highway 74 South
Peachtree City, GA 30269

REPORT NUMBER: P947338
CATALOG NUMBER: GLAN-SB2D-722-U-SLL-HSS

LUMINAIRE CLASSIFICATION SYSTEM LUMEN TABLE AND BUG RATING:

Zone		Lumens	% Fixture	Zone Rating/Lumen Limit B	U	G
FL	(0°-30°)	858.5	6.7			
FM	(30°-60°)	4026.2	31.4			
FH	(60°-80°)	5045.2	39.3			G3/7500
FVH	(80°-90°)	349.9	2.7			G3/500
BL	(0°-30°)	613.2	4.8	B2/1000		
BM	(30°-60°)	1385.5	10.8	B2/2500		
BH	(60°-80°)	534.3	4.2	B2/1000		G2/1000
BVH	(80°-90°)	17.2	0.1			G1/100
UL	(90°-100°)	0.0	0.0		U0/0	
UH	(100°-180°)	0.0	0.0		U0/0	

BUG Rating: B2-U0-G3
Type IV Short



Cooper Lighting Solutions Photometric Lab
1121 Highway 74 South
Peachtree City, GA 30269

REPORT NUMBER: P947338
CATALOG NUMBER: GLAN-SB2D-722-U-SLL-HSS

CANDELA DISTRIBUTION (FULL):

	0°	5°	15°	25°	35°	45°	55°	65°	75°	85°
0°	1776.5	1776.5	1776.5	1776.5	1776.5	1776.5	1776.5	1776.5	1776.5	1776.5
2.5°	1990.4	2005.5	2039.0	2056.7	2084.1	2085.9	2085.9	2062.0	2061.1	2012.5
5°	2224.7	2260.0	2339.6	2421.8	2439.4	2443.9	2435.0	2387.3	2351.9	2257.4
7.5°	2457.1	2525.2	2646.3	2755.9	2791.2	2791.2	2770.0	2692.2	2619.7	2482.7
10°	2649.8	2735.5	2899.9	3022.8	3063.4	3054.6	3011.3	2913.2	2813.3	2647.1
12.5°	2777.1	2873.4	3053.7	3152.7	3194.2	3171.3	3121.8	3026.3	2921.1	2746.1
15°	2840.7	2941.5	3097.9	3150.1	3138.6	3114.7	3108.5	3062.6	2983.0	2819.5
17.5°	2868.1	2961.8	3070.5	3037.8	2940.6	2922.0	2983.9	3042.2	3022.8	2883.1
20°	2893.7	2972.4	3005.1	2860.1	2690.4	2673.7	2792.1	2958.3	3043.1	2942.3
22.5°	2929.1	2977.7	2910.5	2672.8	2489.8	2450.9	2581.7	2831.9	3049.3	3017.5
25°	2977.7	2991.0	2806.2	2495.1	2311.3	2272.4	2394.4	2691.3	3038.7	3098.8
27.5°	3036.0	3008.6	2706.4	2346.6	2169.0	2132.7	2254.7	2556.1	3008.6	3180.1
30°	3112.0	3031.6	2607.4	2231.7	2067.3	2040.8	2158.4	2439.4	2971.5	3283.5
32.5°	3188.9	3041.3	2515.4	2164.6	2044.4	2054.1	2150.4	2376.7	2930.9	3382.5
35°	3272.0	3072.3	2470.4	2230.8	2236.1	2321.0	2360.8	2435.0	2924.7	3516.9
37.5°	3385.2	3141.2	2524.3	2560.5	2744.4	2920.3	2887.5	2720.5	2996.3	3717.5
40°	3547.8	3262.3	2759.4	3121.8	3499.2	3784.7	3660.0	3239.3	3215.5	4006.5
42.5°	3784.7	3455.0	3176.6	3807.6	4447.5	4917.8	4583.7	3908.4	3599.0	4419.3
45°	4134.7	3767.0	3681.2	4531.5	5616.9	6357.6	5662.8	4621.7	4136.4	5044.1
47.5°	4619.9	4225.7	4154.1	5294.3	7038.1	7996.2	6859.6	5282.8	4748.1	5896.2
50°	5264.2	4843.5	4602.2	6128.6	8596.4	9666.7	8055.4	5920.9	5449.0	6937.4
52.5°	6114.5	5705.3	5124.6	6923.2	10198.8	11301.8	9256.6	6481.3	6318.7	8145.6
55°	7274.1	7001.9	5838.7	7681.6	11800.3	12946.7	10410.9	7009.8	7467.7	9581.0
57.5°	8713.0	8907.5	6868.4	8561.0	13240.1	14641.9	11570.5	7748.7	8959.6	11186.0
60°	9641.1	11441.5	8840.3	9861.1	14876.1	16559.0	13159.7	9154.1	10527.6	11761.4
62.5°	9416.6	12247.6	11202.0	11521.0	16380.4	17952.8	14717.0	10565.6	10822.8	10913.8
65°	8728.0	11597.0	10720.3	11843.6	16761.4	18031.5	15133.3	10383.5	9180.6	8910.1
67.5°	7780.6	10825.4	9575.7	10988.1	16072.9	16932.0	14358.2	9185.0	7094.7	6686.3
70°	6757.9	9971.6	8824.4	10028.2	14760.3	15015.8	13040.4	8078.4	5218.3	4515.6
72.5°	5787.5	9082.5	8310.0	9044.5	13009.4	12480.9	11324.8	7100.0	3799.7	3257.0
75°	4794.9	7770.8	7577.3	7876.0	10707.0	9831.1	9409.5	5878.5	2982.1	2356.4
77.5°	3699.8	6072.1	6517.5	6307.2	7536.6	7302.4	7293.6	4417.5	2178.7	1572.4
80°	2532.2	4231.9	5091.9	4449.3	4891.2	4771.9	5493.1	2963.6	1580.3	946.6
82.5°	1488.4	2576.4	3544.3	2153.9	2704.6	2776.2	3271.1	1441.6	929.8	218.3
85°	603.7	1017.3	1385.9	843.2	1304.6	1100.4	1241.8	404.8	259.0	5.3
87.5°	152.0	325.3	228.0	94.6	151.1	138.8	109.6	49.5	10.6	0.0
90°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0

Cooper Lighting Solutions Photometric Lab
1121 Highway 74 South
Peachtree City, GA 30269

REPORT NUMBER: P947338
CATALOG NUMBER: GLAN-SB2D-722-U-SLL-HSS

CANDELA DISTRIBUTION (continued):

90°		95°	105°	115°	125°	135°	145°	155°	165°	175°	180°
1776.5	0°	1776.5	1776.5	1776.5	1776.5	1776.5	1776.5	1776.5	1776.5	1776.5	1776.5
2007.2	2.5°	1972.8	1952.4	1902.1	1851.7	1811.0	1756.2	1720.0	1676.7	1635.1	1598.0
2237.0	5°	2181.3	2114.2	2022.3	1938.3	1852.6	1769.5	1687.3	1600.7	1521.1	1472.5
2431.5	7.5°	2351.0	2232.6	2110.6	2003.7	1900.3	1803.1	1694.3	1589.2	1464.5	1398.3
2580.0	10°	2477.4	2321.9	2161.9	2039.0	1934.8	1840.2	1748.3	1642.2	1491.9	1408.9
2670.1	12.5°	2560.5	2375.8	2188.4	2047.9	1931.2	1857.9	1817.2	1775.7	1626.3	1529.1
2736.4	15°	2618.0	2413.8	2207.0	2027.6	1884.4	1830.5	1871.1	1918.8	1823.4	1711.1
2805.3	17.5°	2680.7	2463.3	2214.9	1972.8	1793.3	1770.4	1875.5	1986.0	1981.6	1870.2
2870.8	20°	2747.0	2506.6	2209.6	1884.4	1682.9	1703.2	1837.5	1965.7	2019.6	1959.5
2945.9	22.5°	2815.1	2548.1	2189.3	1769.5	1579.4	1643.1	1777.4	1889.7	1953.3	1934.8
3037.8	25°	2900.8	2606.5	2159.3	1645.7	1493.7	1582.1	1707.6	1798.6	1842.8	1841.9
3136.8	27.5°	3003.3	2684.3	2143.3	1545.9	1432.7	1513.2	1624.5	1705.8	1736.8	1736.8
3259.6	30°	3122.7	2776.2	2125.7	1480.5	1397.4	1441.6	1528.2	1607.7	1638.7	1638.7
3394.0	32.5°	3255.2	2864.6	2083.2	1440.7	1370.9	1371.7	1426.5	1499.0	1536.1	1541.4
3561.9	35°	3414.3	2959.1	1990.4	1408.9	1339.9	1303.7	1330.2	1390.3	1434.5	1446.0
3801.5	37.5°	3622.9	3074.9	1857.9	1362.0	1292.2	1232.1	1238.3	1284.2	1332.9	1350.5
4132.0	40°	3903.1	3211.0	1720.0	1294.8	1225.0	1153.4	1150.8	1184.4	1232.1	1251.5
4579.2	42.5°	4273.4	3374.6	1588.3	1230.3	1143.7	1070.3	1065.9	1092.4	1134.0	1154.3
5169.7	45°	4747.2	3575.2	1475.2	1179.9	1064.2	991.7	989.9	1012.0	1048.2	1069.5
5925.4	47.5°	5405.6	3775.8	1398.3	1153.4	1001.4	927.2	930.7	950.1	982.8	997.9
6903.8	50°	6263.9	3836.8	1359.4	1153.4	967.8	869.7	887.4	903.3	928.0	936.9
8076.6	52.5°	7087.6	3635.3	1324.0	1160.5	972.2	821.1	859.1	870.6	891.8	895.3
9163.8	55°	7491.5	3125.3	1275.4	1162.3	999.6	779.6	836.1	857.3	865.3	864.4
9794.9	57.5°	7352.8	2526.9	1193.2	1155.2	1018.2	753.0	807.8	848.5	853.8	845.8
9674.7	60°	6865.8	1860.5	1130.4	1103.0	1011.1	745.1	764.5	829.1	837.0	826.4
8748.4	62.5°	6049.1	1291.3	1081.8	988.1	980.2	742.4	696.5	786.6	806.1	791.0
7031.9	65°	*4762.2*	*912.1*	*931.6*	*866.2*	*913.0*	*728.3*	*625.8*	*735.4*	*761.9*	*738.9*
5101.6	67.5°	3222.5	658.5	754.8	784.9	804.3	696.5	574.5	677.0	712.4	682.3
3273.8	70°	1740.3	462.3	498.5	661.1	683.2	641.7	528.5	617.8	658.5	625.8
2327.2	72.5°	1027.9	332.3	349.1	531.2	569.2	564.8	477.3	548.9	598.4	559.5
1606.0	75°	566.5	224.5	249.2	385.4	462.3	435.7	410.1	464.9	515.3	477.3
1006.7	77.5°	253.7	134.3	173.2	252.8	363.3	298.7	317.3	362.4	409.2	369.5
560.4	80°	98.1	75.1	114.9	137.9	264.3	165.3	204.2	266.9	300.5	268.7
122.0	82.5°	12.4	33.6	49.5	53.9	153.8	87.5	118.4	167.9	165.3	143.2
0.0	85°	0.0	6.2	7.1	3.5	66.3	31.8	38.9	54.8	51.3	38.9
0.0	87.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	1.8	0.0
0.0	90°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0

Cooper Lighting Solutions Photometric Lab
1121 Highway 74 South
Peachtree City, GA 30269

REPORT NUMBER: P947338
CATALOG NUMBER: GLAN-SB2D-722-U-SLL-HSS

CANDELA DISTRIBUTION (continued):

185°		195°	205°	215°	225°	235°	245°	255°	265°	270°	275°
1776.5	0°	1776.5	1776.5	1776.5	1776.5	1776.5	1776.5	1776.5	1776.5	1776.5	1776.5
1590.9	2.5°	1547.6	1515.8	1499.9	1486.6	1499.0	1506.1	1506.1	1536.1	1553.8	1560.9
1441.6	5°	1363.8	1304.6	1264.8	1240.9	1248.9	1257.7	1267.4	1305.5	1331.1	1347.9
1338.2	7.5°	1218.8	1128.7	1073.0	1043.8	1048.2	1054.4	1062.4	1099.5	1125.1	1147.2
1318.7	10°	1147.2	1020.0	946.6	911.3	905.1	901.5	898.9	921.0	940.4	958.1
1398.3	12.5°	1150.8	973.1	883.9	840.5	822.0	800.8	784.0	787.5	799.9	822.0
1540.6	15°	1195.9	958.1	851.2	797.2	766.3	741.6	721.2	716.8	721.2	724.8
1703.2	17.5°	1256.8	956.3	822.9	755.7	723.9	703.5	685.0	678.8	679.7	684.1
1811.0	20°	1305.5	951.0	791.0	715.9	687.6	670.0	651.4	645.2	647.0	647.9
1821.6	22.5°	1331.1	943.1	755.7	676.1	652.3	634.6	617.8	616.9	616.9	622.2
1764.2	25°	1331.1	926.3	723.9	638.1	616.9	601.0	580.7	584.2	586.0	593.1
1674.9	27.5°	1299.3	894.5	698.2	605.4	583.3	567.4	548.9	553.3	555.9	563.9
1586.5	30°	1258.6	856.5	669.1	574.5	548.9	537.4	521.5	523.2	526.8	535.6
1504.3	32.5°	1215.3	811.4	645.2	543.6	517.9	509.1	491.4	494.1	497.6	507.3
1423.0	35°	1167.6	758.3	616.9	515.3	489.7	482.6	462.3	464.0	469.3	479.9
1335.5	37.5°	1117.2	715.0	588.6	487.9	461.4	454.3	433.1	434.9	441.0	453.4
1243.6	40°	1067.7	672.6	558.6	458.7	432.2	426.0	403.0	404.8	411.9	425.1
1150.8	42.5°	1013.8	639.9	519.7	428.7	400.4	394.2	373.0	375.6	383.6	396.8
1065.0	45°	949.3	618.7	476.4	400.4	368.6	362.4	342.9	348.2	357.1	370.3
991.7	47.5°	883.0	609.9	440.2	370.3	335.9	330.6	314.7	323.5	333.2	343.8
928.9	50°	819.3	598.4	403.0	342.1	307.6	302.3	291.7	303.2	312.9	322.6
883.9	52.5°	746.9	573.6	369.5	317.3	283.7	281.9	276.6	287.3	296.1	304.9
845.0	55°	671.7	533.8	340.3	295.2	263.4	265.2	262.5	271.3	278.4	286.4
809.6	57.5°	606.3	483.5	317.3	271.3	245.7	251.0	247.5	251.9	256.3	266.0
767.2	60°	540.0	423.4	291.7	243.1	228.0	234.2	224.5	223.6	225.4	228.0
704.4	62.5°	450.8	360.6	259.9	218.3	208.6	211.2	192.7	178.5	178.5	181.2
616.9	65°	*362.4*	*302.3*	*224.5*	*190.0*	*182.1*	*180.3*	*153.8*	*134.3*	*132.6*	*140.5*
515.3	67.5°	297.9	251.0	189.1	158.2	152.9	154.7	135.2	115.8	114.0	122.9
419.8	70°	246.6	202.4	151.1	122.0	127.3	135.2	115.8	97.2	94.6	102.5
341.2	72.5°	196.2	158.2	115.8	90.2	105.2	114.9	94.6	76.9	75.1	82.2
263.4	75°	144.1	113.1	78.7	65.4	81.3	90.2	68.9	54.8	52.1	58.3
175.9	77.5°	89.3	63.6	49.5	38.9	55.7	60.1	36.2	31.8	30.9	35.4
106.9	80°	41.5	27.4	23.9	13.3	20.3	23.9	15.0	16.8	17.7	21.2
53.9	82.5°	11.5	4.4	0.9	0.0	0.0	7.1	3.5	7.1	8.8	13.3
4.4	85°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	1.8	4.4	8.0
0.0	87.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	3.5
0.0	90°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0

Cooper Lighting Solutions Photometric Lab
1121 Highway 74 South
Peachtree City, GA 30269

REPORT NUMBER: P947338
CATALOG NUMBER: GLAN-SB2D-722-U-SLL-HSS

CANDELA DISTRIBUTION (continued):

285°		295°	305°	315°	325°	335°	345°	355°	360°
1776.5	0°	1776.5	1776.5	1776.5	1776.5	1776.5	1776.5	1776.5	1776.5
1610.4	2.5°	1647.5	1682.9	1739.4	1797.8	1855.2	1913.5	1970.1	1990.4
1424.8	5°	1494.6	1575.9	1688.2	1808.4	1932.1	2057.6	2172.5	2224.7
1233.0	7.5°	1324.0	1440.7	1609.5	1797.8	1994.9	2192.0	2373.1	2457.1
1042.9	10°	1141.9	1289.5	1482.2	1736.8	2019.6	2291.8	2541.1	2649.8
875.9	12.5°	968.7	1123.4	1336.4	1641.3	2000.2	2349.3	2648.9	2777.1
758.3	15°	823.8	960.7	1190.5	1528.2	1937.4	2352.8	2700.2	2840.7
692.9	17.5°	715.0	804.3	1042.1	1402.7	1855.2	2320.1	2717.8	2868.1
657.6	20°	661.1	685.9	849.4	1241.8	1778.3	2289.2	2735.5	2893.7
629.3	22.5°	629.3	635.5	694.7	1034.1	1686.4	2279.5	2766.5	2929.1
603.7	25°	603.7	605.4	621.3	819.3	1545.9	2273.3	2814.2	2977.7
577.2	27.5°	578.0	578.0	586.9	660.2	1354.9	2246.8	2876.1	3036.0
550.6	30°	552.4	552.4	558.6	584.2	1131.3	2194.6	2950.3	3112.0
524.1	32.5°	525.9	525.9	531.2	549.8	903.3	2129.2	3018.4	3188.9
496.7	35°	499.4	497.6	504.7	524.1	718.6	2046.1	3086.4	3272.0
469.3	37.5°	471.1	470.2	477.3	499.4	620.5	1949.8	3137.7	3385.2
441.9	40°	441.0	441.0	449.0	472.9	592.2	1828.7	3219.0	3547.8
413.6	42.5°	413.6	411.9	420.7	449.9	571.0	1712.9	3364.8	3784.7
388.0	45°	387.1	383.6	391.5	427.8	533.8	1672.2	3637.1	4134.7
363.3	47.5°	362.4	353.5	360.6	401.3	500.3	1824.3	4082.5	4619.9
341.2	50°	342.1	325.3	331.4	374.8	474.6	2153.9	4660.6	5264.2
320.8	52.5°	320.8	298.7	302.3	342.1	451.6	2467.7	5287.2	6114.5
300.5	55°	298.7	274.0	275.8	309.3	418.9	2514.6	5898.8	7274.1
277.5	57.5°	274.0	251.0	251.0	279.3	395.1	2179.6	6369.0	8713.0
249.2	60°	246.6	231.6	227.2	255.4	416.3	1537.9	6423.8	9641.1
213.0	62.5°	216.5	208.6	202.4	232.5	432.2	911.3	5982.8	9416.6
167.9	65°	*182.1*	*180.3*	*175.9*	*255.4*	*364.1*	*538.3*	*5136.1*	*8728.0*
143.2	67.5°	152.9	150.3	150.3	267.8	276.6	338.5	4012.7	7780.6
122.0	70°	131.7	122.0	122.0	202.4	167.9	234.2	2801.8	6757.9
100.8	72.5°	110.5	99.9	92.8	161.7	125.5	171.5	1750.9	5787.5
76.9	75°	88.4	80.4	71.6	106.9	93.7	129.9	1017.3	4794.9
48.6	77.5°	63.6	60.1	50.4	78.7	68.1	93.7	605.4	3699.8
30.1	80°	32.7	33.6	31.8	45.1	46.0	63.6	344.7	2532.2
19.4	82.5°	19.4	15.0	16.8	22.1	26.5	36.2	129.9	1488.4
14.1	85°	12.4	8.0	8.0	10.6	13.3	14.1	39.8	603.7
7.1	87.5°	6.2	2.7	3.5	5.3	4.4	3.5	1.8	152.0
0.0	90°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0

(END OF REPORT)