

Scaled data based on original data using
LM-79-08 Approved Method: Electrical and Photometric Measurements of Solid-
State Lighting Products

Test Report Prepared for
Cooper Lighting Solutions
(formerly Eaton)

Brand: STREETWORKS

Report Number: P955194

Luminaire Tested: **GLAN-SB8B-722-U-SLR-HSS**

Issue Date: 1/21/2025

Test Information

Test Method: LM-79-08
Report Number: P955194
TEST IS SCALED FROM IESNA LM-79-08 TEST DATA (G2-2411-289-9)
Test Lab: INNOVATION CENTER
Issue Date: 1/21/2025
Manufacturer: COOPER LIGHTING SOLUTIONS (FORMERLY EATON)
Product Line: STREETWORKS
Catalog Number: GLAN-SB8B-722-U-SLR-HSS
Description: GALLEON AREA AND ROADWAY HIGH DENSITY LED LUMINAIRE
(8) 70 CRI, 2200K, 450mA LIGHTSQUARES WITH 26 LEDS EACH AND SPILL LIGHT
ELIMINATOR RIGHT OPTICS WITH HOUSE SIDE SHIELD
Light Source: -
Ballast/Driver: -


Summary

Lumens per Lamp: N/A
Luminaire Lumens: 28707 lumens
Efficiency: N/A
Efficacy: 98.0 lumens/watt
Luminous Opening: Rectangular (W 1.5' x L: 1.5' x H: 0')
IES Classification: Type IV - Short
BUG Rating: B3 - U0 - G5

Input Watts (W): 292.8
Input Voltage (V): NR
Input Current (Ain): NR
Voltage Rise (V): NR
Power Factor: NR
Total Harmonic Distortion (THDi): NR
Frequency (hertz): 60
Stabilization Time: NR
Operation Time: NR
Ambient Temperature (°C): NR
Test Distance: 24 FT



REPORT NUMBER: P955194
CATALOG NUMBER: GLAN-SB8B-722-U-SLR-HSS




Based on 25 foot mounting height. Maximum calculated value = 8.9 fc
Type IV - Short - N/A

REPORT NUMBER: P955194

CATALOG NUMBER: GLAN-SB8B-722-U-SLR-HSS

Luminous Intensity Polar Plot



REPORT NUMBER: P955194

CATALOG NUMBER: GLAN-SB8B-722-U-SLR-HSS


FLUX DISTRIBUTION:

		Downward	Upward	Total
House Side	Lumens	4020.2	0.0	4020.2
	% Fixture	14.0	0.0	14.0
Street Side	Lumens	24686.8	0.0	24686.8
	% Fixture	86.0	0.0	86.0
Total	Lumens	28707.0	0.0	28707.0
	% Fixture	100.0	0.0	100.0

ZONAL LUMENS:

Zone	Lumens	% Fixture
0°-10°	391.4	1.4
10°-20°	1173.2	4.1
20°-30°	1728.3	6.0
30°-40°	2220.4	7.7
40°-50°	3591.0	12.5
50°-60°	6297.2	21.9
60°-70°	7879.6	27.4
70°-80°	4604.4	16.0
80°-90°	821.5	2.9
90°-100°	0.0	0.0
100°-110°	0.0	0.0
110°-120°	0.0	0.0
120°-130°	0.0	0.0
130°-140°	0.0	0.0
140°-150°	0.0	0.0
150°-160°	0.0	0.0
160°-170°	0.0	0.0
170°-180°	0.0	0.0
0°-90°	28707.0	100.0
0°-180°	28707.0	100.0

Coefficient of Utilization



REPORT NUMBER: P955194


CATALOG NUMBER: GLAN-SB8B-722-U-SLR-HSS

LUMINAIRE CLASSIFICATION SYSTEM LUMEN TABLE AND BUG RATING:

Zone		Lumens	% Fixture	Zone Rating/Lumen Limit		
				B	U	G
FL	(0°-30°)	2239.0	7.8			
FM	(30°-60°)	10061.5	35.0			
FH	(60°-80°)	11596.3	40.4			G4/12000
FVH	(80°-90°)	789.9	2.8			G5
BL	(0°-30°)	1053.8	3.7	B3/2500		
BM	(30°-60°)	2047.2	7.1	B2/2500		
BH	(60°-80°)	887.7	3.1	B2/1000		G2/1000
BVH	(80°-90°)	31.6	0.1			G1/100
UL	(90°-100°)	0.0	0.0		U0/0	
UH	(100°-180°)	0.0	0.0		U0/0	

BUG Rating: B3-U0-G5

Type IV Short



REPORT NUMBER: P955194

CATALOG NUMBER: GLAN-SB8B-722-U-SLR-HSS

CANDELA DISTRIBUTION (FULL):

	0°	5°	15°	25°	35°	45°	55°	65°	75°	85°
0°	3975.0	3975.0	3975.0	3975.0	3975.0	3975.0	3975.0	3975.0	3975.0	3975.0
2.5°	4491.2	4414.0	4368.5	4255.8	4143.1	4052.1	3929.5	3848.4	3751.5	3658.6
5°	5005.3	4880.7	4730.4	4524.8	4336.9	4145.1	3959.2	3775.3	3581.5	3403.5
7.5°	5440.4	5260.4	4995.4	4722.5	4483.2	4251.9	4034.3	3791.1	3555.7	3276.9
10°	5772.7	5543.2	5195.2	4837.2	4562.4	4329.0	4117.4	3911.7	3674.4	3338.2
12.5°	5974.4	5729.1	5315.8	4896.6	4582.1	4321.1	4156.9	4066.0	3973.0	3638.8
15°	6122.7	5857.7	5400.9	4938.1	4536.6	4216.3	4095.6	4186.6	4293.4	4079.8
17.5°	6276.9	5998.1	5511.6	4955.9	4414.0	4012.6	3961.2	4196.5	4443.7	4433.8
20°	6423.3	6146.4	5608.5	4944.0	4216.3	3765.4	3810.9	4111.5	4398.2	4518.8
22.5°	6591.4	6298.7	5701.5	4898.5	3959.2	3534.0	3676.4	3977.0	4228.1	4370.5
25°	6797.1	6490.5	5832.0	4831.3	3682.3	3342.2	3539.9	3820.7	4024.4	4123.3
27.5°	7018.5	6719.9	6006.0	4795.7	3458.8	3205.7	3385.7	3634.9	3816.8	3886.0
30°	7293.4	6986.9	6211.7	4756.2	3312.5	3126.6	3225.5	3419.3	3597.3	3666.5
32.5°	7594.0	7283.5	6409.4	4661.2	3223.5	3067.3	3069.3	3191.9	3354.0	3437.1
35°	7969.8	7639.5	6621.0	4453.6	3152.3	2998.1	2917.0	2976.3	3110.8	3209.7
37.5°	8505.7	8106.2	6880.1	4156.9	3047.5	2891.3	2756.8	2770.6	2873.5	2982.2
40°	9245.3	8733.1	7184.7	3848.4	2897.2	2741.0	2580.8	2574.9	2650.0	2756.8
42.5°	10246.0	9561.8	7550.5	3553.8	2752.8	2559.0	2394.9	2385.0	2444.3	2537.3
45°	11567.1	10621.8	7999.4	3300.6	2640.1	2381.0	2218.9	2214.9	2264.4	2345.4
47.5°	13257.9	12095.1	8448.4	3128.6	2580.8	2240.6	2074.5	2082.4	2125.9	2199.1
50°	15447.1	14015.3	8584.8	3041.6	2580.8	2165.5	1946.0	1985.5	2021.1	2076.5
52.5°	18071.4	15858.5	8133.9	2962.5	2596.6	2175.4	1837.2	1922.2	1947.9	1995.4
55°	20503.9	16762.2	6992.8	2853.7	2600.6	2236.7	1744.3	1870.8	1918.3	1936.1
57.5°	21915.9	16451.8	5654.0	2669.8	2584.7	2278.2	1684.9	1807.5	1898.5	1910.4
60°	21646.9	15362.1	4162.9	2529.4	2468.1	2262.4	1667.1	1710.6	1855.0	1872.8
62.5°	19574.4	13534.8	2889.3	2420.6	2211.0	2193.2	1661.2	1558.4	1760.1	1803.6
65°	15733.9	10655.4	2040.9	2084.4	1938.1	2042.9	1629.6	1400.1	1645.4	1704.7
67.5°	11414.8	7210.4	1473.3	1688.9	1756.1	1799.6	1558.4	1285.4	1514.9	1594.0
70°	7325.1	3893.9	1034.3	1115.4	1479.3	1528.7	1435.7	1182.6	1382.4	1473.3
72.5°	5207.1	2300.0	743.6	781.2	1188.5	1273.6	1263.7	1067.9	1228.1	1338.8
75°	3593.3	1267.6	502.3	557.7	862.2	1034.3	975.0	917.6	1040.2	1152.9
77.5°	2252.5	567.6	300.6	387.6	565.6	812.8	668.4	710.0	810.8	915.6
80°	1253.8	219.5	168.1	257.1	308.5	591.3	369.8	456.8	597.2	672.4
82.5°	272.9	27.7	75.1	110.7	120.6	344.1	195.8	265.0	375.7	369.8
85°	0.0	0.0	13.8	15.8	7.9	148.3	71.2	87.0	122.6	114.7
87.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	4.0
90°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0

REPORT NUMBER: P955194

CATALOG NUMBER: GLAN-SB8B-722-U-SLR-HSS

CANDELA DISTRIBUTION (continued):

90°		95°	105°	115°	125°	135°	145°	155°	165°	175°	180°
3975.0	0°	3975.0	3975.0	3975.0	3975.0	3975.0	3975.0	3975.0	3975.0	3975.0	3975.0
3575.5	2.5°	3559.7	3462.8	3391.6	3356.0	3326.3	3354.0	3369.9	3369.9	3437.1	3476.6
3294.7	5°	3225.5	3051.5	2919.0	2830.0	2776.6	2794.4	2814.1	2835.9	2920.9	2978.3
3128.6	7.5°	2994.1	2727.1	2525.4	2400.8	2335.6	2345.4	2359.3	2377.1	2460.1	2517.5
3152.3	10°	2950.6	2566.9	2282.2	2118.0	2038.9	2025.1	2017.2	2011.2	2060.7	2104.2
3421.3	12.5°	3128.6	2574.9	2177.4	1977.6	1880.7	1839.2	1791.7	1754.1	1762.1	1789.7
3828.7	15°	3447.0	2675.7	2143.7	1904.4	1783.8	1714.6	1659.2	1613.7	1603.8	1613.7
4184.6	17.5°	3810.9	2812.2	2139.8	1841.2	1690.9	1619.7	1574.2	1532.6	1518.8	1520.8
4384.4	20°	4052.1	2920.9	2127.9	1770.0	1601.9	1538.6	1499.0	1457.5	1443.7	1447.6
4329.0	22.5°	4075.9	2978.3	2110.1	1690.9	1512.9	1459.5	1419.9	1382.4	1380.4	1380.4
4121.3	25°	3947.3	2978.3	2072.5	1619.7	1427.8	1380.4	1344.8	1299.3	1307.2	1311.2
3886.0	27.5°	3747.6	2907.1	2001.3	1562.3	1354.7	1305.2	1269.6	1228.1	1238.0	1243.9
3666.5	30°	3549.8	2816.1	1916.3	1497.1	1285.4	1228.1	1202.4	1166.8	1170.7	1178.7
3449.0	32.5°	3365.9	2719.2	1815.4	1443.7	1216.2	1158.9	1139.1	1099.6	1105.5	1113.4
3235.4	35°	3184.0	2612.4	1696.8	1380.4	1152.9	1095.6	1079.8	1034.3	1038.2	1050.1
3021.8	37.5°	2988.2	2499.7	1599.9	1317.1	1091.6	1032.3	1016.5	969.0	973.0	986.8
2800.3	40°	2782.5	2389.0	1505.0	1249.9	1026.4	967.1	953.2	901.8	905.7	921.6
2582.8	42.5°	2574.9	2268.3	1431.8	1162.8	959.1	895.9	882.0	834.6	840.5	858.3
2392.9	45°	2383.0	2124.0	1384.3	1065.9	895.9	824.7	810.8	767.3	779.2	799.0
2232.7	47.5°	2218.9	1975.6	1364.6	984.9	828.6	751.5	739.6	704.0	723.8	745.6
2096.3	50°	2078.5	1833.2	1338.8	901.8	765.3	688.2	676.3	652.6	678.3	700.1
2003.3	52.5°	1977.6	1671.1	1283.5	826.6	710.0	634.8	630.9	619.0	642.7	662.5
1934.1	55°	1890.6	1503.0	1194.5	761.4	660.5	589.3	593.3	587.4	607.1	622.9
1892.6	57.5°	1811.5	1356.6	1081.8	710.0	607.1	549.8	561.6	553.7	563.6	573.5
1849.1	60°	1716.6	1208.3	947.3	652.6	543.8	510.2	524.1	502.3	500.3	504.3
1770.0	62.5°	1576.2	1008.6	806.9	581.4	488.5	466.7	472.6	431.1	399.5	399.5
1653.3	65°	1380.4	810.8	676.3	502.3	425.2	407.4	403.4	344.1	300.6	296.6
1526.7	67.5°	1152.9	666.5	561.6	423.2	354.0	342.1	346.1	302.6	259.1	255.1
1400.1	70°	939.4	551.8	452.9	338.2	272.9	284.8	302.6	259.1	217.5	211.6
1251.8	72.5°	763.4	439.0	354.0	259.1	201.7	235.3	257.1	211.6	172.1	168.1
1067.9	75°	589.3	322.4	253.1	176.0	146.3	181.9	201.7	154.3	122.6	116.7
826.6	77.5°	393.5	199.7	142.4	110.7	87.0	124.6	134.5	81.1	71.2	69.2
601.2	80°	239.3	92.9	61.3	53.4	29.7	45.5	53.4	33.6	37.6	39.6
320.4	82.5°	120.6	25.7	9.9	2.0	0.0	0.0	15.8	7.9	15.8	19.8
87.0	85°	9.9	0.0	0.0	0.0	0.0	0.0	0.0	0.0	4.0	9.9
0.0	87.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
0.0	90°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0

REPORT NUMBER: P955194

CATALOG NUMBER: GLAN-SB8B-722-U-SLR-HSS

CANDELA DISTRIBUTION (continued):

185°		195°	205°	215°	225°	235°	245°	255°	265°	270°	275°
3975.0	0°	3975.0	3975.0	3975.0	3975.0	3975.0	3975.0	3975.0	3975.0	3975.0	3975.0
3492.5	2.5°	3603.2	3686.3	3765.4	3891.9	4022.5	4151.0	4281.5	4408.1	4453.6	4487.2
3015.9	5°	3187.9	3344.1	3526.1	3777.2	4046.2	4323.1	4603.9	4861.0	4977.7	5056.8
2566.9	7.5°	2758.8	2962.5	3223.5	3601.2	4022.5	4463.5	4904.5	5309.9	5497.8	5650.0
2143.7	10°	2333.6	2555.1	2885.3	3316.5	3886.0	4518.8	5127.9	5685.6	5928.9	6120.7
1839.2	12.5°	1959.8	2167.5	2513.5	2990.1	3672.4	4475.3	5256.5	5926.9	6213.7	6429.2
1621.6	15°	1696.8	1843.1	2149.7	2663.8	3419.3	4334.9	5264.4	6041.6	6356.0	6581.5
1530.7	17.5°	1550.4	1599.9	1799.6	2331.6	3138.5	4151.0	5191.2	6081.2	6417.4	6627.0
1449.6	20°	1471.3	1479.3	1534.6	1900.5	2778.5	3979.0	5122.0	6120.7	6474.7	6650.7
1392.2	22.5°	1408.1	1408.1	1421.9	1554.4	2313.8	3773.3	5100.3	6189.9	6553.8	6662.6
1327.0	25°	1350.7	1350.7	1354.7	1390.3	1833.2	3458.8	5086.4	6296.7	6662.6	6692.2
1261.7	27.5°	1291.4	1293.4	1293.4	1313.1	1477.3	3031.7	5027.1	6435.2	6793.1	6731.8
1198.4	30°	1232.1	1236.0	1236.0	1249.9	1307.2	2531.3	4910.4	6601.3	6963.2	6783.2
1135.1	32.5°	1172.7	1176.7	1176.7	1188.5	1230.1	2021.1	4764.1	6753.5	7135.2	6805.0
1073.8	35°	1111.4	1117.4	1113.4	1129.2	1172.7	1607.8	4578.2	6905.8	7321.1	6874.2
1014.5	37.5°	1050.1	1054.1	1052.1	1067.9	1117.4	1388.3	4362.6	7020.5	7574.3	7028.4
951.2	40°	988.8	986.8	986.8	1004.6	1058.0	1325.0	4091.7	7202.5	7938.1	7299.4
887.9	42.5°	925.5	925.5	921.6	941.3	1006.6	1277.5	3832.6	7528.8	8468.1	7730.5
828.6	45°	868.2	866.2	858.3	876.1	957.2	1194.5	3741.6	8137.9	9251.3	8428.6
769.3	47.5°	812.8	810.8	791.0	806.9	897.8	1119.3	4081.8	9134.6	10337.0	9455.0
721.8	50°	763.4	765.3	727.8	741.6	838.5	1062.0	4819.4	10428.0	11778.7	10837.3
682.3	52.5°	717.9	717.9	668.4	676.3	765.3	1010.6	5521.5	11830.1	13681.1	12765.5
640.7	55°	672.4	668.4	613.1	617.0	692.2	937.4	5626.3	13198.6	16275.8	15666.6
595.3	57.5°	621.0	613.1	561.6	561.6	624.9	884.0	4876.8	14250.7	19495.3	19930.4
510.2	60°	557.7	551.8	518.1	508.2	571.5	931.5	3441.0	14373.3	21571.8	25600.2
405.4	62.5°	476.6	484.5	466.7	452.9	520.1	967.1	2038.9	13386.5	21069.5	27403.8
314.4	65°	375.7	407.4	403.4	393.5	571.5	814.8	1204.4	11491.9	19528.9	25948.3
274.9	67.5°	320.4	342.1	336.2	336.2	599.2	619.0	757.4	8978.4	17408.9	24221.8
229.4	70°	272.9	294.7	272.9	272.9	452.9	375.7	524.1	6269.0	15120.8	22311.4
183.9	72.5°	225.4	247.2	223.5	207.6	361.9	280.8	383.7	3917.7	12949.4	20321.9
130.5	75°	172.1	197.8	180.0	160.2	239.3	209.6	290.7	2276.2	10728.5	17387.2
79.1	77.5°	108.8	142.4	134.5	112.7	176.0	152.3	209.6	1354.7	8278.3	13586.2
47.5	80°	67.2	73.2	75.1	71.2	100.9	102.8	142.4	771.3	5665.9	9468.8
29.7	82.5°	43.5	43.5	33.6	37.6	49.4	59.3	81.1	290.7	3330.3	5764.7
17.8	85°	31.6	27.7	17.8	17.8	23.7	29.7	31.6	89.0	1350.7	2276.2
7.9	87.5°	15.8	13.8	5.9	7.9	11.9	9.9	7.9	4.0	340.1	727.8
0.0	90°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0

REPORT NUMBER: P955194

CATALOG NUMBER: GLAN-SB8B-722-U-SLR-HSS

CANDELA DISTRIBUTION (continued):

285°		295°	305°	315°	325°	335°	345°	355°	360°
3975.0	0°	3975.0	3975.0	3975.0	3975.0	3975.0	3975.0	3975.0	3975.0
4562.4	2.5°	4601.9	4663.2	4667.2	4667.2	4613.8	4611.8	4503.0	4491.2
5234.7	5°	5418.7	5458.2	5468.1	5448.3	5341.5	5262.4	5050.8	5005.3
5921.0	7.5°	6166.2	6245.3	6245.3	6197.8	6023.8	5861.6	5555.1	5440.4
6488.5	10°	6763.4	6854.4	6834.6	6737.7	6518.2	6294.7	5922.9	5772.7
6832.7	12.5°	7054.1	7147.1	7095.7	6984.9	6771.3	6536.0	6144.4	5974.4
6931.5	15°	7048.2	7022.5	6969.1	6955.3	6852.4	6674.4	6308.6	6122.7
6870.2	17.5°	6797.1	6579.5	6538.0	6676.4	6806.9	6763.4	6451.0	6276.9
6723.9	20°	6399.6	6019.9	5982.3	6247.3	6619.1	6808.9	6583.5	6423.3
6512.3	22.5°	5980.3	5570.9	5483.9	5776.6	6336.3	6822.8	6751.6	6591.4
6278.9	25°	5582.8	5171.5	5084.4	5357.4	6021.8	6799.0	6933.5	6797.1
6055.4	27.5°	5250.6	4853.1	4772.0	5044.9	5719.3	6731.8	7115.4	7018.5
5834.0	30°	4993.5	4625.6	4566.3	4829.3	5458.2	6648.7	7346.8	7293.4
5628.3	32.5°	4843.2	4574.2	4596.0	4811.5	5317.8	6557.8	7568.3	7594.0
5527.4	35°	4991.5	5003.4	5193.2	5282.2	5448.3	6543.9	7868.9	7969.8
5648.1	37.5°	5729.1	6140.5	6534.0	6460.9	6087.1	6704.1	8317.8	8505.7
6174.1	40°	6984.9	7829.4	8468.1	8189.3	7247.9	7194.6	8964.5	9245.3
7107.5	42.5°	8519.6	9951.3	11003.4	10255.9	8745.0	8052.8	9888.1	10246.0
8236.8	45°	10139.2	12567.7	14225.0	12670.6	10340.9	9255.2	11286.2	11567.1
9294.8	47.5°	11845.9	15747.7	17891.5	15348.2	11820.2	10623.7	13192.7	13257.9
10297.4	50°	13712.8	19234.3	21629.1	18024.0	13248.0	12192.0	15522.3	15447.1
11466.2	52.5°	15490.6	22819.7	25287.7	20711.5	14501.8	14138.0	18225.7	18071.4
13064.1	55°	17187.4	26403.1	28968.1	23294.3	15684.4	16708.8	21437.3	20503.9
15368.0	57.5°	19155.2	29624.6	32761.1	25888.9	17337.7	20047.1	25028.7	21915.9
19780.1	60°	22064.2	33285.2	37050.6	29444.7	20482.1	23555.3	26316.1	21646.9
25064.3	62.5°	25778.2	36651.1	40169.3	32929.2	23640.4	24215.9	24419.6	19574.4
23986.5	65°	26500.0	37503.4	40345.3	33860.7	23233.0	20541.5	19936.3	15733.9
21425.5	67.5°	24585.7	35962.9	37885.1	32126.3	20551.3	15874.3	14960.6	11414.8
19744.5	70°	22438.0	33026.1	33597.7	29177.7	18075.4	11675.8	10103.6	7325.1
18593.5	72.5°	20236.9	29108.5	27925.9	25339.1	15886.2	8501.8	7287.5	5207.1
16954.1	75°	17622.5	23956.8	21997.0	21053.7	13153.1	6672.5	5272.3	3593.3
14582.9	77.5°	14112.2	16863.1	16339.0	16319.3	9884.1	4874.8	3518.2	2252.5
11393.0	80°	9955.3	10944.1	10677.1	12290.9	6630.9	3536.0	2118.0	1253.8
7930.2	82.5°	4819.4	6051.5	6211.7	7319.1	3225.5	2080.4	488.5	272.9
3100.9	85°	1886.6	2919.0	2462.1	2778.5	905.7	579.4	11.9	0.0
510.2	87.5°	211.6	338.2	310.5	245.2	110.7	23.7	0.0	0.0
0.0	90°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0

(END OF REPORT)