

Scaled data based on original data using
LM-79-08 Approved Method: Electrical and Photometric Measurements of Solid-
State Lighting Products

Test Report Prepared for
Cooper Lighting Solutions
(formerly Eaton)

Brand: STREETWORKS

Report Number: P947341

Luminaire Tested: **GLAN-SB2D-722-U-SLR**

Issue Date: 1/21/2025

Test Information

Test Method: LM-79-08
Report Number: P947341
TEST IS SCALED FROM IESNA LM-79-08 TEST DATA (G2-2411-289-8)
Test Lab: INNOVATION CENTER
Issue Date: 1/21/2025
Manufacturer: COOPER LIGHTING SOLUTIONS (FORMERLY EATON)
Product Line: STREETWORKS
Catalog Number: GLAN-SB2D-722-U-SLR
Description: GALLEON AREA AND ROADWAY HIGH DENSITY LED LUMINAIRE
(2) 70 CRI, 2200K, 900mA LIGHTSQUARES WITH 26 LEDS EACH AND SPILL LIGHT
ELIMINATOR RIGHT OPTICS
Light Source: -
Ballast/Driver: -

Summary

Lumens per Lamp: N/A
Luminaire Lumens: 16751 lumens
Efficiency: N/A
Efficacy: 113.5 lumens/watt
Luminous Opening: Rectangular (W 0.5' x L: 1' x H: 0')
IES Classification: Type IV - Short
BUG Rating: B3 - U0 - G4

Input Watts (W): 147.6
Input Voltage (V): NR
Input Current (Ain): NR
Voltage Rise (V): NR
Power Factor: NR
Total Harmonic Distortion (THDi): NR
Frequency (hertz): 60
Stabilization Time: NR
Operation Time: NR
Ambient Temperature (°C): NR
Test Distance: 24 FT




REPORT NUMBER: P947341

CATALOG NUMBER: GLAN-SB2D-722-U-SLR

Iso-Footcandle Lines of Horizontal Illumination


× Max cd
--- 1/2 Max cd



Based on 25 foot mounting height. Maximum calculated value = 4.6 fc
Type IV - Short - N/A

REPORT NUMBER: P947341
CATALOG NUMBER: GLAN-SB2D-722-U-SLR

Luminous Intensity Polar Plot



REPORT NUMBER: P947341

CATALOG NUMBER: GLAN-SB2D-722-U-SLR


FLUX DISTRIBUTION:

		Downward	Upward	Total
House Side	Lumens	4257.3	0.0	4257.3
	% Fixture	25.4	0.0	25.4
Street Side	Lumens	12493.7	0.0	12493.7
	% Fixture	74.6	0.0	74.6
Total	Lumens	16751.0	0.0	16751.0
	% Fixture	100.0	0.0	100.0

ZONAL LUMENS:

Zone	Lumens	% Fixture
0°-10°	228.5	1.4
10°-20°	717.3	4.3
20°-30°	1108.0	6.6
30°-40°	1404.1	8.4
40°-50°	2117.7	12.6
50°-60°	3421.5	20.4
60°-70°	4265.4	25.5
70°-80°	2797.0	16.7
80°-90°	691.5	4.1
90°-100°	0.0	0.0
100°-110°	0.0	0.0
110°-120°	0.0	0.0
120°-130°	0.0	0.0
130°-140°	0.0	0.0
140°-150°	0.0	0.0
150°-160°	0.0	0.0
160°-170°	0.0	0.0
170°-180°	0.0	0.0
0°-90°	16751.0	100.0
0°-180°	16751.0	100.0

Coefficient of Utilization



REPORT NUMBER: P947341


CATALOG NUMBER: GLAN-SB2D-722-U-SLR

LUMINAIRE CLASSIFICATION SYSTEM LUMEN TABLE AND BUG RATING:

Zone		Lumens	% Fixture	Zone Rating/Lumen Limit		
				B	U	G
FL	(0°-30°)	1126.7	6.7			
FM	(30°-60°)	4885.9	29.2			
FH	(60°-80°)	5911.5	35.3			G3/7500
FVH	(80°-90°)	569.6	3.4			G4/750
BL	(0°-30°)	927.1	5.5	B2/1000		
BM	(30°-60°)	2057.4	12.3	B2/2500		
BH	(60°-80°)	1151.0	6.9	B3/2500		G3/2500
BVH	(80°-90°)	121.9	0.7			G2/225
UL	(90°-100°)	0.0	0.0		U0/0	
UH	(100°-180°)	0.0	0.0		U0/0	

BUG Rating: B3-U0-G4

Type IV Short



REPORT NUMBER: P947341

CATALOG NUMBER: GLAN-SB2D-722-U-SLR

CANDELA DISTRIBUTION (FULL):

	0°	5°	10°	15°	20°	25°	30°	35°	40°	45°
0°	2303.4	2303.4	2303.4	2303.4	2303.4	2303.4	2303.4	2303.4	2303.4	2303.4
2.5°	2477.1	2458.1	2439.1	2418.8	2398.7	2378.4	2358.0	2338.6	2319.1	2300.3
5°	2663.6	2621.6	2579.6	2537.7	2495.9	2453.8	2411.7	2372.3	2333.0	2295.9
7.5°	2851.0	2781.7	2712.5	2648.5	2584.5	2522.2	2459.9	2405.0	2350.1	2299.4
10°	2994.6	2907.0	2819.4	2734.8	2650.3	2574.7	2498.9	2434.0	2369.0	2306.5
12.5°	3082.6	2986.3	2890.1	2794.3	2698.5	2609.2	2520.0	2446.5	2373.1	2307.4
15°	3136.0	3035.7	2935.4	2831.4	2727.5	2624.7	2521.9	2436.9	2351.8	2279.1
17.5°	3166.1	3064.3	2962.6	2849.2	2735.8	2616.5	2497.2	2394.9	2292.6	2207.1
20°	3199.2	3093.5	2987.7	2863.1	2738.5	2593.9	2449.2	2322.5	2195.7	2096.1
22.5°	3237.7	3129.7	3021.6	2881.8	2742.0	2566.1	2390.2	2237.6	2084.9	1971.5
25°	3287.2	3181.3	3075.5	2915.8	2756.0	2538.7	2321.5	2142.7	1964.0	1847.8
27.5°	3354.3	3253.4	3152.4	2968.8	2785.1	2520.4	2255.7	2056.0	1856.3	1750.5
30°	3444.9	3347.4	3249.9	3037.5	2825.1	2511.8	2198.4	1983.5	1768.7	1679.8
32.5°	3551.9	3455.3	3358.8	3109.2	2859.5	2501.2	2142.7	1921.0	1699.3	1627.7
35°	3681.8	3589.4	3496.8	3190.8	2884.8	2481.2	2077.8	1859.6	1641.4	1581.7
37.5°	3900.6	3782.7	3664.8	3282.3	2899.9	2447.0	1994.2	1787.3	1580.4	1528.2
40°	4231.2	4059.3	3887.5	3398.5	2909.3	2399.9	1890.6	1701.0	1511.4	1464.2
42.5°	4669.6	4421.6	4173.5	3550.4	2927.3	2351.3	1775.6	1605.8	1436.1	1392.6
45°	5210.9	4876.4	4541.8	3750.3	2958.8	2306.1	1653.6	1504.7	1355.9	1311.7
47.5°	5888.0	5417.2	4946.2	3963.3	2980.5	2268.8	1557.2	1424.7	1292.2	1235.2
50°	6775.4	6065.6	5355.6	4161.0	2966.3	2228.2	1490.1	1371.6	1253.2	1178.2
52.5°	7794.1	6746.7	5699.3	4289.3	2879.3	2159.5	1439.9	1336.6	1233.5	1147.3
55°	8878.6	7350.6	5822.6	4261.0	2699.4	2045.7	1391.9	1311.2	1230.5	1150.4
57.5°	9865.1	7778.5	5692.0	4062.0	2432.0	1885.2	1338.2	1281.2	1224.2	1153.5
60°	10461.2	7885.5	5309.7	3691.5	2073.4	1676.7	1280.0	1235.2	1190.4	1143.7
62.5°	10158.5	7435.2	4711.8	3190.7	1669.5	1427.3	1185.1	1155.3	1125.6	1119.9
65°	9552.6	6798.0	4043.3	2679.6	1315.9	1202.9	1089.8	1075.8	1061.7	1062.4
67.5°	8740.7	6039.7	3338.6	2179.0	1019.3	987.2	955.0	962.9	970.7	968.7
70°	7765.4	5212.3	2659.2	1715.6	772.1	781.3	790.4	826.8	863.1	863.1
72.5°	6603.1	4315.3	2027.6	1311.6	595.6	623.2	651.0	702.6	754.1	762.8
75°	5132.7	3287.1	1441.4	951.9	462.4	487.6	512.7	570.5	628.3	668.2
77.5°	3667.2	2300.7	934.1	645.1	356.0	373.1	390.2	446.4	502.5	568.3
80°	2400.2	1482.3	564.4	415.6	266.9	274.0	281.1	328.6	376.1	454.8
82.5°	1395.2	857.9	320.7	255.6	190.7	192.0	193.4	228.4	263.4	330.6
85°	613.9	385.9	158.0	136.6	115.3	114.7	114.0	139.7	165.3	215.2
87.5°	190.0	126.4	62.8	56.7	50.6	49.9	49.3	59.8	70.3	91.0
90°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0

REPORT NUMBER: P947341

CATALOG NUMBER: GLAN-SB2D-722-U-SLR

CANDELA DISTRIBUTION (continued):

50°		55°	60°	65°	70°	75°	80°	85°	90°	95°	100°
2303.4	0°	2303.4	2303.4	2303.4	2303.4	2303.4	2303.4	2303.4	2303.4	2303.4	2303.4
2279.4	2.5°	2262.4	2245.5	2230.2	2215.0	2201.7	2188.3	2174.9	2161.5	2151.2	2140.8
2259.2	5°	2227.2	2195.1	2168.3	2141.5	2117.8	2094.1	2072.6	2051.1	2034.5	2017.9
2252.0	7.5°	2209.4	2166.8	2131.5	2096.1	2066.3	2036.5	2010.1	1983.9	1964.2	1944.5
2255.5	10°	2210.6	2165.7	2130.3	2095.0	2062.9	2030.7	2001.1	1971.5	1948.0	1924.4
2259.9	12.5°	2223.1	2186.6	2163.0	2139.7	2114.4	2089.3	2058.7	2028.1	1998.0	1968.0
2241.1	15°	2223.5	2206.0	2209.2	2212.4	2205.8	2199.3	2172.7	2146.1	2103.3	2060.5
2183.6	17.5°	2190.1	2196.5	2235.0	2273.5	2294.0	2314.5	2293.0	2271.6	2214.9	2158.3
2089.9	20°	2120.0	2150.1	2217.0	2284.0	2326.8	2369.7	2359.8	2349.8	2285.0	2220.3
1983.6	22.5°	2028.1	2072.5	2148.9	2225.4	2281.2	2337.0	2343.0	2348.9	2287.1	2225.2
1880.5	25°	1931.7	1983.0	2051.7	2120.4	2175.3	2230.2	2250.7	2271.1	2220.4	2169.8
1790.3	27.5°	1839.8	1889.3	1945.8	2002.2	2046.2	2090.2	2113.0	2135.9	2099.8	2063.7
1711.0	30°	1750.3	1789.7	1836.5	1883.4	1919.9	1956.5	1975.0	1993.6	1966.1	1938.5
1641.6	32.5°	1664.8	1688.0	1725.4	1762.9	1797.9	1833.0	1853.6	1874.3	1849.0	1823.6
1576.0	35°	1582.3	1588.8	1617.3	1645.8	1680.4	1715.2	1739.9	1764.7	1746.6	1728.7
1507.2	37.5°	1500.1	1493.1	1513.6	1534.0	1568.5	1603.2	1633.8	1664.4	1656.0	1647.7
1431.9	40°	1415.9	1399.9	1414.7	1429.4	1462.8	1496.2	1531.4	1566.7	1568.7	1570.7
1351.9	42.5°	1330.7	1309.5	1321.5	1333.6	1365.3	1397.0	1435.0	1473.0	1483.2	1493.3
1272.4	45°	1251.7	1231.1	1241.2	1251.4	1281.5	1311.5	1350.9	1390.4	1404.9	1419.5
1201.4	47.5°	1184.1	1166.7	1176.3	1185.7	1215.2	1244.5	1283.4	1322.3	1339.1	1355.9
1138.9	50°	1123.5	1108.2	1123.1	1138.0	1165.8	1193.4	1228.2	1263.1	1284.6	1306.2
1092.3	52.5°	1077.1	1062.0	1084.4	1106.6	1132.1	1157.4	1189.9	1222.4	1248.0	1273.5
1067.6	55°	1043.5	1019.6	1051.3	1082.9	1110.3	1137.7	1166.2	1194.6	1221.6	1248.8
1052.7	57.5°	1017.7	982.7	1016.8	1050.9	1083.1	1115.3	1143.4	1171.6	1198.9	1226.1
1038.7	60°	993.4	948.0	977.9	1007.8	1044.8	1081.7	1110.2	1138.9	1166.3	1193.7
1022.5	62.5°	965.7	909.1	928.1	947.1	990.1	1033.3	1063.8	1094.3	1119.4	1144.5
988.2	65°	927.9	867.5	874.9	882.1	928.3	974.5	1003.7	1032.8	1054.9	1077.0
927.0	67.5°	876.8	826.6	824.3	822.0	864.6	907.3	935.0	962.6	981.6	1000.7
849.4	70°	813.7	778.0	770.0	762.1	799.6	837.0	860.9	884.8	902.0	919.2
763.0	72.5°	738.5	714.0	702.3	690.8	720.3	749.7	771.3	792.8	809.7	826.6
664.9	75°	646.0	627.1	616.0	604.8	626.7	648.6	668.1	687.7	703.0	718.4
566.6	77.5°	551.5	536.3	525.0	513.7	531.6	549.3	566.1	582.9	599.1	615.2
454.5	80°	441.9	429.1	419.7	410.1	425.0	439.7	453.9	468.0	480.3	492.5
334.3	82.5°	328.1	321.9	315.2	308.5	307.2	306.0	301.1	296.1	322.3	348.4
220.1	85°	213.5	206.8	199.3	191.8	185.4	179.0	165.3	151.6	176.1	200.6
97.2	87.5°	94.6	91.9	90.5	89.1	88.8	88.6	78.1	67.6	77.9	88.2
0.0	90°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0

REPORT NUMBER: P947341

CATALOG NUMBER: GLAN-SB2D-722-U-SLR

CANDELA DISTRIBUTION (continued):

105°		110°	115°	120°	125°	130°	135°	140°	145°	150°	155°
2303.4	0°	2303.4	2303.4	2303.4	2303.4	2303.4	2303.4	2303.4	2303.4	2303.4	2303.4
2132.4	2.5°	2124.0	2117.4	2110.9	2104.9	2098.8	2091.3	2098.8	2104.9	2110.9	2117.4
2006.3	5°	1994.8	1986.5	1978.3	1972.0	1965.8	1959.6	1965.8	1972.0	1978.3	1986.5
1930.8	7.5°	1917.0	1907.5	1898.1	1892.5	1886.9	1882.7	1886.9	1892.5	1898.1	1907.5
1909.0	10°	1893.5	1884.5	1875.6	1870.8	1866.1	1864.1	1866.1	1870.8	1875.6	1884.5
1948.1	12.5°	1928.2	1918.2	1908.3	1904.2	1900.2	1899.5	1900.2	1904.2	1908.3	1918.2
2030.3	15°	2000.1	1986.2	1972.4	1967.1	1961.8	1961.3	1961.8	1967.1	1972.4	1986.2
2113.7	17.5°	2069.2	2048.7	2028.1	2021.4	2014.6	2013.5	2014.6	2021.4	2028.1	2048.7
2165.7	20°	2111.2	2084.9	2058.6	2050.2	2041.8	2039.1	2041.8	2050.2	2058.6	2084.9
2169.0	22.5°	2112.7	2085.0	2057.2	2048.0	2038.7	2034.7	2038.7	2048.0	2057.2	2085.0
2119.7	25°	2069.9	2045.8	2021.9	2013.1	2004.5	1999.4	2004.5	2013.1	2021.9	2045.8
2024.9	27.5°	1986.1	1970.0	1953.8	1949.9	1945.9	1944.5	1945.9	1949.9	1953.8	1970.0
1910.8	30°	1882.9	1874.6	1866.3	1866.3	1866.3	1867.7	1866.3	1866.3	1866.3	1874.6
1801.4	32.5°	1779.3	1773.9	1768.5	1769.2	1770.0	1771.3	1770.0	1769.2	1768.5	1773.9
1708.2	35°	1687.8	1679.6	1671.4	1669.7	1667.9	1667.0	1667.9	1669.7	1671.4	1679.6
1628.9	37.5°	1610.0	1595.1	1580.2	1572.3	1564.5	1560.1	1564.5	1572.3	1580.2	1595.1
1554.7	40°	1538.7	1516.9	1495.4	1480.7	1466.2	1457.5	1466.2	1480.7	1495.4	1516.9
1479.8	42.5°	1466.4	1439.4	1412.4	1391.1	1369.8	1355.9	1369.8	1391.1	1412.4	1439.4
1407.3	45°	1395.2	1364.4	1333.6	1308.6	1283.6	1267.5	1283.6	1308.6	1333.6	1364.4
1347.4	47.5°	1338.9	1311.5	1284.1	1261.0	1237.9	1222.4	1237.9	1261.0	1284.1	1311.5
1305.7	50°	1305.3	1283.4	1261.5	1240.1	1218.7	1203.9	1218.7	1240.1	1261.5	1283.4
1278.1	52.5°	1282.7	1264.8	1247.0	1227.8	1208.7	1195.0	1208.7	1227.8	1247.0	1264.8
1255.1	55°	1261.5	1245.9	1230.4	1213.6	1196.8	1184.4	1196.8	1213.6	1230.4	1245.9
1232.6	57.5°	1239.0	1223.3	1207.6	1190.9	1174.2	1161.4	1174.2	1190.9	1207.6	1223.3
1200.8	60°	1207.8	1192.5	1177.2	1160.0	1142.9	1129.6	1142.9	1160.0	1177.2	1192.5
1151.3	62.5°	1158.1	1144.2	1130.3	1112.3	1094.3	1078.3	1094.3	1112.3	1130.3	1144.2
1084.0	65°	1090.9	1077.5	1064.2	1046.7	1029.3	1015.6	1029.3	1046.7	1064.2	1077.5
1007.5	67.5°	1014.3	1002.0	989.8	973.5	957.2	944.9	957.2	973.5	989.8	1002.0
925.8	70°	932.3	922.3	912.3	896.8	881.2	867.1	881.2	896.8	912.3	922.3
834.4	72.5°	842.2	833.9	825.5	810.7	795.9	782.2	795.9	810.7	825.5	833.9
726.6	75°	734.7	730.6	726.6	714.1	701.6	688.5	701.6	714.1	726.6	730.6
622.8	77.5°	630.4	624.7	618.9	606.3	593.8	583.4	593.8	606.3	618.9	624.7
502.6	80°	512.7	510.2	507.8	490.9	473.9	454.3	473.9	490.9	507.8	510.2
365.6	82.5°	382.7	381.7	380.5	366.3	352.0	339.4	352.0	366.3	380.5	381.7
221.9	85°	243.1	241.3	239.5	228.4	217.3	205.9	217.3	228.4	239.5	241.3
96.8	87.5°	105.4	103.2	100.9	95.3	89.4	84.0	89.4	95.3	100.9	103.2
0.0	90°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0

REPORT NUMBER: P947341

CATALOG NUMBER: GLAN-SB2D-722-U-SLR

CANDELA DISTRIBUTION (continued):

160°		165°	170°	175°	180°	185°	190°	195°	200°	205°	210°
2303.4	0°	2303.4	2303.4	2303.4	2303.4	2303.4	2303.4	2303.4	2303.4	2303.4	2303.4
2124.0	2.5°	2132.4	2140.8	2151.2	2161.5	2174.9	2188.3	2201.7	2215.0	2230.2	2245.5
1994.8	5°	2006.3	2017.9	2034.5	2051.1	2072.6	2094.1	2117.8	2141.5	2168.3	2195.1
1917.0	7.5°	1930.8	1944.5	1964.2	1983.9	2010.1	2036.5	2066.3	2096.1	2131.5	2166.8
1893.5	10°	1909.0	1924.4	1948.0	1971.5	2001.1	2030.7	2062.9	2095.0	2130.3	2165.7
1928.2	12.5°	1948.1	1968.0	1998.0	2028.1	2058.7	2089.3	2114.4	2139.7	2163.0	2186.6
2000.1	15°	2030.3	2060.5	2103.3	2146.1	2172.7	2199.3	2205.8	2212.4	2209.2	2206.0
2069.2	17.5°	2113.7	2158.3	2214.9	2271.6	2293.0	2314.5	2294.0	2273.5	2235.0	2196.5
2111.2	20°	2165.7	2220.3	2285.0	2349.8	2359.8	2369.7	2326.8	2284.0	2217.0	2150.1
2112.7	22.5°	2169.0	2225.2	2287.1	2348.9	2343.0	2337.0	2281.2	2225.4	2148.9	2072.5
2069.9	25°	2119.7	2169.8	2220.4	2271.1	2250.7	2230.2	2175.3	2120.4	2051.7	1983.0
1986.1	27.5°	2024.9	2063.7	2099.8	2135.9	2113.0	2090.2	2046.2	2002.2	1945.8	1889.3
1882.9	30°	1910.8	1938.5	1966.1	1993.6	1975.0	1956.5	1919.9	1883.4	1836.5	1789.7
1779.3	32.5°	1801.4	1823.6	1849.0	1874.3	1853.6	1833.0	1797.9	1762.9	1725.4	1688.0
1687.8	35°	1708.2	1728.7	1746.6	1764.7	1739.9	1715.2	1680.4	1645.8	1617.3	1588.8
1610.0	37.5°	1628.9	1647.7	1656.0	1664.4	1633.8	1603.2	1568.5	1534.0	1513.6	1493.1
1538.7	40°	1554.7	1570.7	1568.7	1566.7	1531.4	1496.2	1462.8	1429.4	1414.7	1399.9
1466.4	42.5°	1479.8	1493.3	1483.2	1473.0	1435.0	1397.0	1365.3	1333.6	1321.5	1309.5
1395.2	45°	1407.3	1419.5	1404.9	1390.4	1350.9	1311.5	1281.5	1251.4	1241.2	1231.1
1338.9	47.5°	1347.4	1355.9	1339.1	1322.3	1283.4	1244.5	1215.2	1185.7	1176.3	1166.7
1305.3	50°	1305.7	1306.2	1284.6	1263.1	1228.2	1193.4	1165.8	1138.0	1123.1	1108.2
1282.7	52.5°	1278.1	1273.5	1248.0	1222.4	1189.9	1157.4	1132.1	1106.6	1084.4	1062.0
1261.5	55°	1255.1	1248.8	1221.6	1194.6	1166.2	1137.7	1110.3	1082.9	1051.3	1019.6
1239.0	57.5°	1232.6	1226.1	1198.9	1171.6	1143.4	1115.3	1083.1	1050.9	1016.8	982.7
1207.8	60°	1200.8	1193.7	1166.3	1138.9	1110.2	1081.7	1044.8	1007.8	977.9	948.0
1158.1	62.5°	1151.3	1144.5	1119.4	1094.3	1063.8	1033.3	990.1	947.1	928.1	909.1
1090.9	65°	1084.0	1077.0	1054.9	1032.8	1003.7	974.5	928.3	882.1	874.9	867.5
1014.3	67.5°	1007.5	1000.7	981.6	962.6	935.0	907.3	864.6	822.0	824.3	826.6
932.3	70°	925.8	919.2	902.0	884.8	860.9	837.0	799.6	762.1	770.0	778.0
842.2	72.5°	834.4	826.6	809.7	792.8	771.3	749.7	720.3	690.8	702.3	714.0
734.7	75°	726.6	718.4	703.0	687.7	668.1	648.6	626.7	604.8	616.0	627.1
630.4	77.5°	622.8	615.2	599.1	582.9	566.1	549.3	531.6	513.7	525.0	536.3
512.7	80°	502.6	492.5	480.3	468.0	453.9	439.7	425.0	410.1	419.7	429.1
382.7	82.5°	365.6	348.4	322.3	296.1	301.1	306.0	307.2	308.5	315.2	321.9
243.1	85°	221.9	200.6	176.1	151.6	165.3	179.0	185.4	191.8	199.3	206.8
105.4	87.5°	96.8	88.2	77.9	67.6	78.1	88.6	88.8	89.1	90.5	91.9
0.0	90°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0

REPORT NUMBER: P947341

CATALOG NUMBER: GLAN-SB2D-722-U-SLR

CANDELA DISTRIBUTION (continued):

215°		220°	225°	230°	235°	240°	245°	250°	255°	260°	265°
2303.4	0°	2303.4	2303.4	2303.4	2303.4	2303.4	2303.4	2303.4	2303.4	2303.4	2303.4
2262.4	2.5°	2279.4	2300.3	2319.1	2338.6	2358.0	2378.4	2398.7	2418.8	2439.1	2458.1
2227.2	5°	2259.2	2295.9	2333.0	2372.3	2411.7	2453.8	2495.9	2537.7	2579.6	2621.6
2209.4	7.5°	2252.0	2299.4	2350.1	2405.0	2459.9	2522.2	2584.5	2648.5	2712.5	2781.7
2210.6	10°	2255.5	2306.5	2369.0	2434.0	2498.9	2574.7	2650.3	2734.8	2819.4	2907.0
2223.1	12.5°	2259.9	2307.4	2373.1	2446.5	2520.0	2609.2	2698.5	2794.3	2890.1	2986.3
2223.5	15°	2241.1	2279.1	2351.8	2436.9	2521.9	2624.7	2727.5	2831.4	2935.4	3035.7
2190.1	17.5°	2183.6	2207.1	2292.6	2394.9	2497.2	2616.5	2735.8	2849.2	2962.6	3064.3
2120.0	20°	2089.9	2096.1	2195.7	2322.5	2449.2	2593.9	2738.5	2863.1	2987.7	3093.5
2028.1	22.5°	1983.6	1971.5	2084.9	2237.6	2390.2	2566.1	2742.0	2881.8	3021.6	3129.7
1931.7	25°	1880.5	1847.8	1964.0	2142.7	2321.5	2538.7	2756.0	2915.8	3075.5	3181.3
1839.8	27.5°	1790.3	1750.5	1856.3	2056.0	2255.7	2520.4	2785.1	2968.8	3152.4	3253.4
1750.3	30°	1711.0	1679.8	1768.7	1983.5	2198.4	2511.8	2825.1	3037.5	3249.9	3347.4
1664.8	32.5°	1641.6	1627.7	1699.3	1921.0	2142.7	2501.2	2859.5	3109.2	3358.8	3455.3
1582.3	35°	1576.0	1581.7	1641.4	1859.6	2077.8	2481.2	2884.8	3190.8	3496.8	3589.4
1500.1	37.5°	1507.2	1528.2	1580.4	1787.3	1994.2	2447.0	2899.9	3282.3	3664.8	3782.7
1415.9	40°	1431.9	1464.2	1511.4	1701.0	1890.6	2399.9	2909.3	3398.5	3887.5	4059.3
1330.7	42.5°	1351.9	1392.6	1436.1	1605.8	1775.6	2351.3	2927.3	3550.4	4173.5	4421.6
1251.7	45°	1272.4	1311.7	1355.9	1504.7	1653.6	2306.1	2958.8	3750.3	4541.8	4876.4
1184.1	47.5°	1201.4	1235.2	1292.2	1424.7	1557.2	2268.8	2980.5	3963.3	4946.2	5417.2
1123.5	50°	1138.9	1178.2	1253.2	1371.6	1490.1	2228.2	2966.3	4161.0	5355.6	6065.6
1077.1	52.5°	1092.3	1147.3	1233.5	1336.6	1439.9	2159.5	2879.3	4289.3	5699.3	6746.7
1043.5	55°	1067.6	1150.4	1230.5	1311.2	1391.9	2045.7	2699.4	4261.0	5822.6	7350.6
1017.7	57.5°	1052.7	1153.5	1224.2	1281.2	1338.2	1885.2	2432.0	4062.0	5692.0	7778.5
993.4	60°	1038.7	1143.7	1190.4	1235.2	1280.0	1676.7	2073.4	3691.5	5309.7	7885.5
965.7	62.5°	1022.5	1119.9	1125.6	1155.3	1185.1	1427.3	1669.5	3190.7	4711.8	7435.2
927.9	65°	988.2	1062.4	1061.7	1075.8	1089.8	1202.9	1315.9	2679.6	4043.3	6798.0
876.8	67.5°	927.0	968.7	970.7	962.9	955.0	987.2	1019.3	2179.0	3338.6	6039.7
813.7	70°	849.4	863.1	863.1	826.8	790.4	781.3	772.1	1715.6	2659.2	5212.3
738.5	72.5°	763.0	762.8	754.1	702.6	651.0	623.2	595.6	1311.6	2027.6	4315.3
646.0	75°	664.9	668.2	628.3	570.5	512.7	487.6	462.4	951.9	1441.4	3287.1
551.5	77.5°	566.6	568.3	502.5	446.4	390.2	373.1	356.0	645.1	934.1	2300.7
441.9	80°	454.5	454.8	376.1	328.6	281.1	274.0	266.9	415.6	564.4	1482.3
328.1	82.5°	334.3	330.6	263.4	228.4	193.4	192.0	190.7	255.6	320.7	857.9
213.5	85°	220.1	215.2	165.3	139.7	114.0	114.7	115.3	136.6	158.0	385.9
94.6	87.5°	97.2	91.0	70.3	59.8	49.3	49.9	50.6	56.7	62.8	126.4
0.0	90°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0

REPORT NUMBER: P947341

CATALOG NUMBER: GLAN-SB2D-722-U-SLR

CANDELA DISTRIBUTION (continued):

270°		275°	280°	285°	290°	295°	300°	305°	310°	315°	320°
2303.4	0°	2303.4	2303.4	2303.4	2303.4	2303.4	2303.4	2303.4	2303.4	2303.4	2303.4
2477.1	2.5°	2486.5	2495.9	2509.3	2522.6	2530.6	2538.5	2542.5	2546.5	2544.7	2546.5
2663.6	5°	2696.4	2729.3	2761.8	2794.4	2812.1	2829.8	2840.5	2851.2	2859.4	2851.2
2851.0	7.5°	2904.4	2957.7	3005.7	3053.6	3082.6	3111.5	3127.1	3142.7	3150.2	3142.7
2994.6	10°	3057.7	3120.8	3177.1	3233.4	3267.5	3301.5	3316.7	3331.8	3337.6	3331.8
3082.6	12.5°	3151.0	3219.3	3270.2	3320.9	3345.7	3370.4	3378.7	3387.1	3387.9	3387.1
3136.0	15°	3195.1	3254.0	3285.9	3317.9	3318.8	3319.7	3310.9	3302.0	3291.6	3302.0
3166.1	17.5°	3205.9	3245.8	3246.4	3247.0	3211.2	3175.4	3142.6	3109.7	3086.5	3109.7
3199.2	20°	3213.1	3227.1	3185.1	3143.1	3064.1	2985.1	2927.5	2870.0	2834.6	2870.0
3237.7	22.5°	3219.5	3201.3	3114.3	3027.3	2911.1	2794.8	2722.9	2651.0	2611.9	2651.0
3287.2	25°	3229.7	3172.3	3040.2	2908.2	2767.0	2625.8	2550.2	2474.7	2437.8	2474.7
3354.3	27.5°	3251.6	3148.8	2973.9	2799.1	2642.6	2486.2	2411.8	2337.4	2302.5	2337.4
3444.9	30°	3291.8	3138.7	2923.4	2708.0	2545.1	2382.1	2313.0	2244.0	2211.5	2244.0
3551.9	32.5°	3342.1	3132.5	2888.9	2645.3	2492.1	2338.9	2284.8	2230.5	2207.1	2230.5
3681.8	35°	3425.1	3168.6	2914.7	2660.9	2554.5	2448.2	2435.5	2422.9	2421.0	2422.9
3900.6	37.5°	3598.7	3296.7	3066.0	2835.3	2828.4	2821.5	2879.3	2937.2	2967.2	2937.2
4231.2	40°	3902.8	3574.4	3402.9	3231.3	3352.4	3473.5	3614.0	3754.6	3824.6	3754.6
4669.6	42.5°	4343.8	4018.0	3919.2	3820.3	4084.4	4348.5	4604.2	4859.8	5009.9	4859.8
5210.9	45°	4918.3	4625.6	4582.0	4538.3	4961.4	5384.6	5804.7	6224.8	6479.8	6224.8
5888.0	47.5°	5603.3	5318.5	5309.7	5300.8	5911.3	6521.5	7136.4	7751.2	8112.3	7751.2
6775.4	50°	6423.7	6072.1	6073.6	6075.1	6861.8	7648.4	8460.1	9271.8	9762.5	9271.8
7794.1	52.5°	7368.2	6942.5	6899.4	6856.3	7796.0	8735.6	9739.9	10744.1	11332.3	10744.1
8878.6	55°	8457.9	8037.2	7869.3	7701.5	8747.3	9793.0	10990.2	12187.5	12887.1	12187.5
9865.1	57.5°	9635.9	9406.8	9070.1	8733.5	9789.5	10845.5	12201.5	13557.5	14425.0	13557.5
10461.2	60°	10817.1	11173.0	10754.9	10336.9	11336.2	12335.5	13787.4	15239.3	16176.9	15239.3
10158.5	62.5°	11130.9	12103.2	12056.1	12008.9	12924.4	13839.9	15221.2	16602.5	17469.1	16602.5
9552.6	65°	10465.2	11377.8	11558.4	11738.9	12902.3	14065.7	15405.2	16744.5	17482.4	16744.5
8740.7	67.5°	9608.7	10476.7	10561.4	10646.0	11858.1	13070.2	14415.4	15760.6	16338.6	15760.6
7765.4	70°	8709.5	9653.6	9691.5	9729.4	10813.4	11897.3	13054.9	14212.4	14533.7	14212.4
6603.1	72.5°	7686.4	8769.9	8797.1	8824.3	9672.4	10520.5	11387.5	12254.4	12286.9	12254.4
5132.7	75°	6254.0	7375.3	7476.0	7576.7	8236.5	8896.3	9506.6	10117.0	9953.4	10117.0
3667.2	77.5°	4713.9	5760.7	5904.8	6048.9	6550.5	7052.1	7484.9	7917.9	7636.8	7917.9
2400.2	80°	3280.8	4161.3	4340.4	4519.5	4898.3	5277.0	5504.3	5731.6	5279.5	5731.6
1395.2	82.5°	1997.2	2599.3	2799.4	2999.5	3260.2	3521.0	3615.8	3710.6	3355.2	3710.6
613.9	85°	933.4	1252.9	1423.1	1593.2	1807.5	2021.6	2075.5	2129.3	1844.7	2129.3
190.0	87.5°	297.4	404.8	499.7	594.7	701.8	808.9	813.5	818.0	686.8	818.0
0.0	90°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0

REPORT NUMBER: P947341

CATALOG NUMBER: GLAN-SB2D-722-U-SLR

CANDELA DISTRIBUTION (continued):

325°		330°	335°	340°	345°	350°	355°	360°
2303.4	0°	2303.4	2303.4	2303.4	2303.4	2303.4	2303.4	2303.4
2542.5	2.5°	2538.5	2530.6	2522.6	2509.3	2495.9	2486.5	2477.1
2840.5	5°	2829.8	2812.1	2794.4	2761.8	2729.3	2696.4	2663.6
3127.1	7.5°	3111.5	3082.6	3053.6	3005.7	2957.7	2904.4	2851.0
3316.7	10°	3301.5	3267.5	3233.4	3177.1	3120.8	3057.7	2994.6
3378.7	12.5°	3370.4	3345.7	3320.9	3270.2	3219.3	3151.0	3082.6
3310.9	15°	3319.7	3318.8	3317.9	3285.9	3254.0	3195.1	3136.0
3142.6	17.5°	3175.4	3211.2	3247.0	3246.4	3245.8	3205.9	3166.1
2927.5	20°	2985.1	3064.1	3143.1	3185.1	3227.1	3213.1	3199.2
2722.9	22.5°	2794.8	2911.1	3027.3	3114.3	3201.3	3219.5	3237.7
2550.2	25°	2625.8	2767.0	2908.2	3040.2	3172.3	3229.7	3287.2
2411.8	27.5°	2486.2	2642.6	2799.1	2973.9	3148.8	3251.6	3354.3
2313.0	30°	2382.1	2545.1	2708.0	2923.4	3138.7	3291.8	3444.9
2284.8	32.5°	2338.9	2492.1	2645.3	2888.9	3132.5	3342.1	3551.9
2435.5	35°	2448.2	2554.5	2660.9	2914.7	3168.6	3425.1	3681.8
2879.3	37.5°	2821.5	2828.4	2835.3	3066.0	3296.7	3598.7	3900.6
3614.0	40°	3473.5	3352.4	3231.3	3402.9	3574.4	3902.8	4231.2
4604.2	42.5°	4348.5	4084.4	3820.3	3919.2	4018.0	4343.8	4669.6
5804.7	45°	5384.6	4961.4	4538.3	4582.0	4625.6	4918.3	5210.9
7136.4	47.5°	6521.5	5911.3	5300.8	5309.7	5318.5	5603.3	5888.0
8460.1	50°	7648.4	6861.8	6075.1	6073.6	6072.1	6423.7	6775.4
9739.9	52.5°	8735.6	7796.0	6856.3	6899.4	6942.5	7368.2	7794.1
10990.2	55°	9793.0	8747.3	7701.5	7869.3	8037.2	8457.9	8878.6
12201.5	57.5°	10845.5	9789.5	8733.5	9070.1	9406.8	9635.9	9865.1
13787.4	60°	12335.5	11336.2	10336.9	10754.9	11173.0	10817.1	10461.2
15221.2	62.5°	13839.9	12924.4	12008.9	12056.1	12103.2	11130.9	10158.5
15405.2	65°	14065.7	12902.3	11738.9	11558.4	11377.8	10465.2	9552.6
14415.4	67.5°	13070.2	11858.1	10646.0	10561.4	10476.7	9608.7	8740.7
13054.9	70°	11897.3	10813.4	9729.4	9691.5	9653.6	8709.5	7765.4
11387.5	72.5°	10520.5	9672.4	8824.3	8797.1	8769.9	7686.4	6603.1
9506.6	75°	8896.3	8236.5	7576.7	7476.0	7375.3	6254.0	5132.7
7484.9	77.5°	7052.1	6550.5	6048.9	5904.8	5760.7	4713.9	3667.2
5504.3	80°	5277.0	4898.3	4519.5	4340.4	4161.3	3280.8	2400.2
3615.8	82.5°	3521.0	3260.2	2999.5	2799.4	2599.3	1997.2	1395.2
2075.5	85°	2021.6	1807.5	1593.2	1423.1	1252.9	933.4	613.9
813.5	87.5°	808.9	701.8	594.7	499.7	404.8	297.4	190.0
0.0	90°	0.0	0.0	0.0	0.0	0.0	0.0	0.0

(END OF REPORT)