

Scaled data based on original data using
LM-79-08 Approved Method: Electrical and Photometric Measurements of Solid-
State Lighting Products

Test Report Prepared for
Cooper Lighting Solutions
(formerly Eaton)

Brand: STREETWORKS

Report Number: P948096

Luminaire Tested: **GLAN-SB3B-730-U-SLR-HSS**

Issue Date: 1/21/2025

Test Information

Test Method: LM-79-08
Report Number: P948096
TEST IS SCALED FROM IESNA LM-79-08 TEST DATA (G2-2411-289-9)
Test Lab: INNOVATION CENTER
Issue Date: 1/21/2025
Manufacturer: COOPER LIGHTING SOLUTIONS (FORMERLY EATON)
Product Line: STREETWORKS
Catalog Number: GLAN-SB3B-730-U-SLR-HSS
Description: GALLEON AREA AND ROADWAY HIGH DENSITY LED LUMINAIRE
(3) 70 CRI, 3000K, 450mA LIGHTSQUARES WITH 26 LEDS EACH AND SPILL LIGHT
ELIMINATOR RIGHT OPTICS WITH HOUSE SIDE SHIELD
Light Source: -
Ballast/Driver: -

Summary

Lumens per Lamp: N/A
Luminaire Lumens: 12894 lumens
Efficiency: N/A
Efficacy: 118.1 lumens/watt
Luminous Opening: Rectangular (W 1' x L: 1' x H: 0')
IES Classification: Type IV - Short
BUG Rating: B1 - U0 - G3


Input Watts (W): 109.2
Input Voltage (V): NR
Input Current (Ain): NR
Voltage Rise (V): NR
Power Factor: NR
Total Harmonic Distortion (THDi): NR
Frequency (hertz): 60
Stabilization Time: NR
Operation Time: NR
Ambient Temperature (°C): NR
Test Distance: 24 FT



REPORT NUMBER: P948096
 CATALOG NUMBER: GLAN-SB3B-730-U-SLR-HSS

Iso-Footcandle Lines of Horizontal Illumination


× Max cd
 - - - 1/2 Max cd



Based on 25 foot mounting height. Maximum calculated value = 4 fc
 Type IV - Short - N/A

REPORT NUMBER: P948096
CATALOG NUMBER: GLAN-SB3B-730-U-SLR-HSS

Luminous Intensity Polar Plot



— Vertical Plane Through 315-Deg Lateral - - - Horizontal Cone Through 65-Deg Vertical

REPORT NUMBER: P948096
 CATALOG NUMBER: GLAN-SB3B-730-U-SLR-HSS


FLUX DISTRIBUTION:

		Downward	Upward	Total
House Side	Lumens	1805.7	0.0	1805.7
	% Fixture	14.0	0.0	14.0
Street Side	Lumens	11088.3	0.0	11088.3
	% Fixture	86.0	0.0	86.0
Total	Lumens	12894.0	0.0	12894.0
	% Fixture	100.0	0.0	100.0

ZONAL LUMENS:

Zone	Lumens	% Fixture
0°-10°	175.8	1.4
10°-20°	526.9	4.1
20°-30°	776.3	6.0
30°-40°	997.3	7.7
40°-50°	1612.9	12.5
50°-60°	2828.5	21.9
60°-70°	3539.2	27.4
70°-80°	2068.1	16.0
80°-90°	369.0	2.9
90°-100°	0.0	0.0
100°-110°	0.0	0.0
110°-120°	0.0	0.0
120°-130°	0.0	0.0
130°-140°	0.0	0.0
140°-150°	0.0	0.0
150°-160°	0.0	0.0
160°-170°	0.0	0.0
170°-180°	0.0	0.0
0°-90°	12894.0	100.0
0°-180°	12894.0	100.0

Coefficient of Utilization




REPORT NUMBER: P948096
 CATALOG NUMBER: GLAN-SB3B-730-U-SLR-HSS

LUMINAIRE CLASSIFICATION SYSTEM LUMEN TABLE AND BUG RATING:

Zone	Lumens	% Fixture	Zone Rating/Lumen Limit		
			B	U	G
FL (0°-30°)	1005.7	7.8			
FM (30°-60°)	4519.2	35.0			
FH (60°-80°)	5208.6	40.4			G3/7500
FVH (80°-90°)	354.8	2.8			G3/500
BL (0°-30°)	473.3	3.7	B1/500		
BM (30°-60°)	919.5	7.1	B1/1000		
BH (60°-80°)	398.7	3.1	B1/500		G1/500
BVH (80°-90°)	14.2	0.1			G1/100
UL (90°-100°)	0.0	0.0		U0/0	
UH (100°-180°)	0.0	0.0		U0/0	

BUG Rating: B1-U0-G3

Type IV Short



REPORT NUMBER: P948096
 CATALOG NUMBER: GLAN-SB3B-730-U-SLR-HSS

CANDELA DISTRIBUTION (FULL):

	0°	5°	15°	25°	35°	45°	55°	65°	75°	85°
0°	1785.4	1785.4	1785.4	1785.4	1785.4	1785.4	1785.4	1785.4	1785.4	1785.4
2.5°	2017.2	1982.6	1962.2	1911.5	1860.9	1820.0	1765.0	1728.6	1685.0	1643.3
5°	2248.2	2192.2	2124.7	2032.3	1948.0	1861.8	1778.3	1695.7	1608.6	1528.7
7.5°	2443.6	2362.8	2243.7	2121.2	2013.7	1909.8	1812.1	1702.8	1597.1	1471.8
10°	2592.8	2489.8	2333.5	2172.7	2049.2	1944.4	1849.4	1757.0	1650.4	1499.4
12.5°	2683.4	2573.3	2387.6	2199.3	2058.1	1940.9	1867.1	1826.3	1784.5	1634.4
15°	2750.1	2631.0	2425.8	2218.0	2037.7	1893.8	1839.6	1880.5	1928.4	1832.5
17.5°	2819.3	2694.1	2475.6	2226.0	1982.6	1802.3	1779.2	1884.9	1995.9	1991.5
20°	2885.1	2760.7	2519.1	2220.7	1893.8	1691.3	1711.7	1846.7	1975.5	2029.7
22.5°	2960.6	2829.1	2560.9	2200.2	1778.3	1587.3	1651.3	1786.3	1899.1	1963.1
25°	3053.0	2915.3	2619.5	2170.0	1653.9	1501.2	1590.0	1716.1	1807.6	1852.0
27.5°	3152.4	3018.3	2697.7	2154.0	1553.6	1439.9	1520.7	1632.6	1714.3	1745.4
30°	3275.9	3138.2	2790.0	2136.3	1487.8	1404.3	1448.8	1535.8	1615.7	1646.8
32.5°	3410.9	3271.5	2878.9	2093.6	1447.9	1377.7	1378.6	1433.7	1506.5	1543.8
35°	3579.7	3431.4	2973.9	2000.4	1415.9	1346.6	1310.2	1336.8	1397.2	1441.6
37.5°	3820.4	3641.0	3090.3	1867.1	1368.8	1298.6	1238.2	1244.5	1290.6	1339.5
40°	4152.6	3922.6	3227.1	1728.6	1301.3	1231.1	1159.2	1156.5	1190.3	1238.2
42.5°	4602.1	4294.7	3391.4	1596.2	1236.5	1149.4	1075.7	1071.2	1097.9	1139.6
45°	5195.4	4770.9	3593.0	1482.5	1185.8	1069.5	996.6	994.9	1017.1	1053.5
47.5°	5954.9	5432.6	3794.7	1405.2	1159.2	1006.4	931.8	935.3	954.9	987.7
50°	6938.2	6295.1	3855.9	1366.1	1159.2	972.6	874.0	891.8	907.8	932.7
52.5°	8116.9	7123.0	3653.4	1330.6	1166.3	977.1	825.2	863.4	874.9	896.3
55°	9209.5	7528.9	3140.9	1281.8	1168.1	1004.6	783.4	840.3	861.6	869.6
57.5°	9843.7	7389.5	2539.5	1199.2	1161.0	1023.3	756.8	811.9	852.7	858.1
60°	9722.9	6900.0	1869.8	1136.1	1108.6	1016.2	748.8	768.3	833.2	841.2
62.5°	8792.0	6079.3	1297.8	1087.2	993.1	985.1	746.1	700.0	790.6	810.1
65°	7067.0	4786.0	916.7	936.2	870.5	917.6	731.9	628.9	739.0	765.7
67.5°	5127.0	3238.6	661.8	758.6	788.8	808.3	700.0	577.4	680.4	715.9
70°	3290.1	1749.0	464.6	501.0	664.4	686.6	644.9	531.2	620.9	661.8
72.5°	2338.8	1033.0	334.0	350.9	533.8	572.0	567.6	479.7	551.6	601.4
75°	1614.0	569.4	225.6	250.5	387.3	464.6	437.9	412.2	467.2	517.9
77.5°	1011.7	254.9	135.0	174.1	254.0	365.1	300.2	318.9	364.2	411.3
80°	563.2	98.6	75.5	115.5	138.6	265.6	166.1	205.2	268.3	302.0
82.5°	122.6	12.4	33.8	49.7	54.2	154.6	87.9	119.0	168.8	166.1
85°	0.0	0.0	6.2	7.1	3.6	66.6	32.0	39.1	55.1	51.5
87.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	1.8
90°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0

REPORT NUMBER: P948096
 CATALOG NUMBER: GLAN-SB3B-730-U-SLR-HSS

CANDELA DISTRIBUTION (continued):

90°		95°	105°	115°	125°	135°	145°	155°	165°	175°	180°
1785.4	0°	1785.4	1785.4	1785.4	1785.4	1785.4	1785.4	1785.4	1785.4	1785.4	1785.4
1606.0	2.5°	1598.9	1555.3	1523.4	1507.4	1494.1	1506.5	1513.6	1513.6	1543.8	1561.6
1479.8	5°	1448.8	1370.6	1311.1	1271.1	1247.1	1255.1	1264.0	1273.8	1312.0	1337.7
1405.2	7.5°	1344.8	1224.9	1134.3	1078.3	1049.0	1053.5	1059.7	1067.7	1105.0	1130.8
1415.9	10°	1325.3	1153.0	1025.1	951.3	915.8	909.6	906.0	903.4	925.6	945.1
1536.7	12.5°	1405.2	1156.5	978.0	888.3	844.7	826.1	804.8	787.9	791.4	803.9
1719.7	15°	1548.2	1201.8	962.9	855.4	801.2	770.1	745.3	724.8	720.4	724.8
1879.6	17.5°	1711.7	1263.1	961.1	827.0	759.5	727.5	707.1	688.4	682.2	683.1
1969.3	20°	1820.0	1312.0	955.8	795.0	719.5	691.1	673.3	654.6	648.4	650.2
1944.4	22.5°	1830.7	1337.7	947.8	759.5	679.5	655.5	637.8	620.9	620.0	620.0
1851.1	25°	1773.0	1337.7	930.9	727.5	641.3	620.0	604.0	583.6	587.1	588.9
1745.4	27.5°	1683.3	1305.7	898.9	701.7	608.5	586.3	570.3	551.6	556.1	558.7
1646.8	30°	1594.4	1264.9	860.7	672.4	577.4	551.6	540.1	524.1	525.9	529.4
1549.1	32.5°	1511.8	1221.4	815.4	648.4	546.3	520.5	511.6	493.9	496.5	500.1
1453.2	35°	1430.1	1173.4	762.1	620.0	517.9	492.1	485.0	464.6	466.3	471.7
1357.3	37.5°	1342.2	1122.8	718.6	591.6	490.3	463.7	456.6	435.2	437.0	443.2
1257.8	40°	1249.8	1073.0	676.0	561.4	461.0	434.4	428.1	405.0	406.8	413.9
1160.1	42.5°	1156.5	1018.8	643.1	522.3	430.8	402.4	396.2	374.8	377.5	385.5
1074.8	45°	1070.4	954.0	621.8	478.8	402.4	370.4	364.2	344.6	350.0	358.9
1002.8	47.5°	996.6	887.4	612.9	442.4	372.2	337.5	332.2	316.2	325.1	334.9
941.6	50°	933.6	823.4	601.4	405.0	343.8	309.1	303.8	293.1	304.7	314.4
899.8	52.5°	888.3	750.6	576.5	371.3	318.9	285.1	283.4	278.0	288.7	297.6
868.7	55°	849.2	675.1	536.5	342.0	296.7	264.7	266.5	263.8	272.7	279.8
850.1	57.5°	813.6	609.3	485.9	318.9	272.7	246.9	252.3	248.7	253.2	257.6
830.5	60°	771.0	542.7	425.5	293.1	244.3	229.2	235.4	225.6	224.7	226.5
795.0	62.5°	707.9	453.0	362.4	261.1	219.4	209.6	212.3	193.6	179.4	179.4
742.6	65°	620.0	364.2	303.8	225.6	191.0	183.0	181.2	154.6	135.0	133.2
685.7	67.5°	517.9	299.3	252.3	190.1	159.0	153.7	155.4	135.9	116.4	114.6
628.9	70°	421.9	247.8	203.4	151.9	122.6	127.9	135.9	116.4	97.7	95.0
562.3	72.5°	342.9	197.2	159.0	116.4	90.6	105.7	115.5	95.0	77.3	75.5
479.7	75°	264.7	144.8	113.7	79.1	65.7	81.7	90.6	69.3	55.1	52.4
371.3	77.5°	176.8	89.7	64.0	49.7	39.1	56.0	60.4	36.4	32.0	31.1
270.0	80°	107.5	41.7	27.5	24.0	13.3	20.4	24.0	15.1	16.9	17.8
143.9	82.5°	54.2	11.5	4.4	0.9	0.0	0.0	7.1	3.6	7.1	8.9
39.1	85°	4.4	0.0	0.0	0.0	0.0	0.0	0.0	0.0	1.8	4.4
0.0	87.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
0.0	90°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0

REPORT NUMBER: P948096
 CATALOG NUMBER: GLAN-SB3B-730-U-SLR-HSS

CANDELA DISTRIBUTION (continued):

185°		195°	205°	215°	225°	235°	245°	255°	265°	270°	275°
1785.4	0°	1785.4	1785.4	1785.4	1785.4	1785.4	1785.4	1785.4	1785.4	1785.4	1785.4
1568.7	2.5°	1618.4	1655.7	1691.3	1748.1	1806.7	1864.5	1923.1	1979.9	2000.4	2015.5
1354.6	5°	1431.9	1502.1	1583.8	1696.6	1817.4	1941.7	2067.9	2183.3	2235.8	2271.3
1153.0	7.5°	1239.1	1330.6	1447.9	1617.5	1806.7	2004.8	2202.9	2385.0	2469.4	2537.8
962.9	10°	1048.1	1147.6	1296.0	1489.6	1745.4	2029.7	2303.3	2553.8	2663.0	2749.2
826.1	12.5°	880.3	973.5	1129.0	1343.1	1649.5	2010.1	2361.0	2662.1	2790.9	2887.7
728.4	15°	762.1	827.9	965.5	1196.5	1535.8	1947.1	2364.6	2713.6	2854.9	2956.1
687.5	17.5°	696.4	718.6	808.3	1047.3	1409.7	1864.5	2331.7	2731.4	2882.4	2976.6
651.1	20°	660.9	664.4	689.3	853.6	1248.0	1787.2	2300.6	2749.2	2908.2	2987.2
625.3	22.5°	632.4	632.4	638.7	698.2	1039.3	1694.8	2290.8	2780.3	2943.7	2992.6
596.0	25°	606.7	606.7	608.5	624.4	823.4	1553.6	2284.6	2828.2	2992.6	3005.9
566.7	27.5°	580.0	580.9	580.9	589.8	663.5	1361.7	2258.0	2890.4	3051.2	3023.6
538.3	30°	553.4	555.2	555.2	561.4	587.1	1137.0	2205.6	2965.0	3127.6	3046.7
509.9	32.5°	526.7	528.5	528.5	533.8	552.5	907.8	2139.8	3033.4	3204.8	3056.5
482.3	35°	499.2	501.9	500.1	507.2	526.7	722.2	2056.3	3101.8	3288.3	3087.6
455.7	37.5°	471.7	473.4	472.6	479.7	501.9	623.6	1959.5	3153.3	3402.0	3156.9
427.3	40°	444.1	443.2	443.2	451.2	475.2	595.1	1837.8	3235.0	3565.5	3278.6
398.8	42.5°	415.7	415.7	413.9	422.8	452.1	573.8	1721.5	3381.6	3803.5	3472.2
372.2	45°	389.9	389.1	385.5	393.5	429.9	536.5	1680.6	3655.2	4155.3	3785.8
345.5	47.5°	365.1	364.2	355.3	362.4	403.3	502.8	1833.4	4102.9	4642.9	4246.8
324.2	50°	342.9	343.8	326.9	333.1	376.6	477.0	2164.7	4683.8	5290.5	4867.7
306.5	52.5°	322.4	322.4	300.2	303.8	343.8	453.9	2480.0	5313.6	6145.0	5733.7
287.8	55°	302.0	300.2	275.4	277.1	310.9	421.0	2527.1	5928.3	7310.4	7036.8
267.4	57.5°	278.9	275.4	252.3	252.3	280.7	397.1	2190.5	6400.8	8756.5	8951.9
229.2	60°	250.5	247.8	232.7	228.3	256.7	418.4	1545.6	6455.9	9689.2	11498.6
182.1	62.5°	214.1	217.6	209.6	203.4	233.6	434.4	915.8	6012.6	9463.5	12308.6
141.2	65°	168.8	183.0	181.2	176.8	256.7	366.0	541.0	5161.7	8771.6	11654.9
123.5	67.5°	143.9	153.7	151.0	151.0	269.1	278.0	340.2	4032.7	7819.4	10879.4
103.0	70°	122.6	132.4	122.6	122.6	203.4	168.8	235.4	2815.8	6791.7	10021.4
82.6	72.5°	101.3	111.0	100.4	93.3	162.6	126.1	172.3	1759.6	5816.3	9127.8
58.6	75°	77.3	88.8	80.8	71.9	107.5	94.2	130.6	1022.4	4818.8	7809.6
35.5	77.5°	48.9	64.0	60.4	50.6	79.1	68.4	94.2	608.5	3718.3	6102.4
21.3	80°	30.2	32.9	33.8	32.0	45.3	46.2	64.0	346.4	2544.9	4253.0
13.3	82.5°	19.5	19.5	15.1	16.9	22.2	26.6	36.4	130.6	1495.8	2589.3
8.0	85°	14.2	12.4	8.0	8.0	10.7	13.3	14.2	40.0	606.7	1022.4
3.6	87.5°	7.1	6.2	2.7	3.6	5.3	4.4	3.6	1.8	152.8	326.9
0.0	90°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0

REPORT NUMBER: P948096
 CATALOG NUMBER: GLAN-SB3B-730-U-SLR-HSS

CANDELA DISTRIBUTION (continued):

285°		295°	305°	315°	325°	335°	345°	355°	360°
1785.4	0°	1785.4	1785.4	1785.4	1785.4	1785.4	1785.4	1785.4	1785.4
2049.2	2.5°	2067.0	2094.5	2096.3	2096.3	2072.3	2071.4	2022.6	2017.2
2351.2	5°	2433.8	2451.6	2456.0	2447.2	2399.2	2363.7	2268.6	2248.2
2659.5	7.5°	2769.6	2805.1	2805.1	2783.8	2705.6	2632.8	2495.1	2443.6
2914.4	10°	3037.9	3078.7	3069.8	3026.3	2927.7	2827.3	2660.3	2592.8
3068.9	12.5°	3168.4	3210.2	3187.1	3137.3	3041.4	2935.7	2759.8	2683.4
3113.4	15°	3165.8	3154.2	3130.2	3124.0	3077.8	2997.9	2833.6	2750.1
3085.8	17.5°	3053.0	2955.2	2936.6	2998.8	3057.4	3037.9	2897.5	2819.3
3020.1	20°	2874.4	2703.9	2687.0	2806.0	2973.0	3058.3	2957.0	2885.1
2925.0	22.5°	2686.1	2502.2	2463.2	2594.6	2846.0	3064.5	3032.5	2960.6
2820.2	25°	2507.6	2322.8	2283.7	2406.3	2704.8	3053.8	3114.2	3053.0
2719.9	27.5°	2358.3	2179.8	2143.4	2266.0	2568.9	3023.6	3196.0	3152.4
2620.4	30°	2242.9	2077.6	2051.0	2169.1	2451.6	2986.3	3299.9	3275.9
2528.0	32.5°	2175.4	2054.5	2064.3	2161.1	2388.5	2945.5	3399.4	3410.9
2482.7	35°	2242.0	2247.3	2332.6	2372.5	2447.2	2939.3	3534.4	3579.7
2536.9	37.5°	2573.3	2758.1	2934.8	2902.0	2734.1	3011.2	3736.0	3820.4
2773.2	40°	3137.3	3516.6	3803.5	3678.3	3255.5	3231.5	4026.5	4152.6
3192.4	42.5°	3826.6	4469.7	4942.3	4606.5	3927.9	3617.0	4441.3	4602.1
3699.6	45°	4554.1	5644.9	6389.3	5691.1	4644.7	4157.1	5069.3	5195.4
4174.8	47.5°	5320.7	7073.2	8036.1	6893.8	5309.1	4771.7	5925.6	5954.9
4625.2	50°	6159.2	8639.2	9714.9	8095.6	5950.5	5476.1	6972.0	6938.2
5150.1	52.5°	6957.8	10249.7	11358.2	9302.8	6513.6	6350.2	8186.2	8116.9
5867.9	55°	7719.9	11859.2	13011.3	10462.8	7044.8	7504.9	9628.8	9209.5
6902.7	57.5°	8603.7	13306.2	14714.9	11628.2	7787.4	9004.3	11241.8	9843.7
8884.4	60°	9910.3	14950.3	16641.6	13225.3	9199.7	10580.1	11820.1	9722.9
11257.8	62.5°	11578.5	16462.2	18042.4	14790.4	10618.3	10876.8	10968.3	8792.0
10773.7	65°	11902.7	16845.0	18121.4	15208.8	10435.3	9226.4	8954.6	7067.0
9623.4	67.5°	11042.9	16153.0	17016.4	14429.8	9230.8	7130.1	6719.7	5127.0
8868.4	70°	10078.2	14834.0	15090.7	13105.4	8118.7	5244.3	4538.1	3290.1
8351.4	72.5°	9089.6	13074.3	12543.1	11381.3	7135.4	3818.6	3273.2	2338.8
7615.1	75°	7915.3	10760.4	9880.1	9456.4	5907.8	2997.0	2368.1	1614.0
6550.0	77.5°	6338.6	7574.2	7338.8	7329.9	4439.5	2189.6	1580.2	1011.7
5117.3	80°	4471.5	4915.6	4795.7	5520.5	2978.3	1588.2	951.3	563.2
3561.9	82.5°	2164.7	2718.1	2790.0	3287.5	1448.8	934.5	219.4	122.6
1392.8	85°	847.4	1311.1	1105.9	1248.0	406.8	260.3	5.3	0.0
229.2	87.5°	95.0	151.9	139.5	110.1	49.7	10.7	0.0	0.0
0.0	90°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0

(END OF REPORT)