

Scaled data based on original data using
LM-79-08 Approved Method: Electrical and Photometric Measurements of Solid-
State Lighting Products

Test Report Prepared for
Cooper Lighting Solutions
(formerly Eaton)

Brand: STREETWORKS

Report Number: P949190

Luminaire Tested: **GLAN-SB4A-735-U-T2R-HSS**

Issue Date: 1/21/2025

Test Information

Test Method: LM-79-08
Report Number: P949190
TEST IS SCALED FROM IESNA LM-79-08 TEST DATA (G2-2411-289-4)
Test Lab: INNOVATION CENTER
Issue Date: 1/21/2025
Manufacturer: COOPER LIGHTING SOLUTIONS (FORMERLY EATON)
Product Line: STREETWORKS
Catalog Number: GLAN-SB4A-735-U-T2R-HSS
Description: GALLEON AREA AND ROADWAY HIGH DENSITY LED LUMINAIRE
(4) 70 CRI, 3500K, 350mA LIGHTSQUARES WITH 26 LEDS EACH AND TYPE II
ROADWAY OPTICS WITH HOUSE SIDE SHIELD
Light Source: -
Ballast/Driver: -

Summary

Lumens per Lamp: N/A
Luminaire Lumens: 15222 lumens
Efficiency: N/A
Efficacy: 133.5 lumens/watt
Luminous Opening: Rectangular (W 1' x L: 1' x H: 0')
IES Classification: Type II - Medium
BUG Rating: B1 - U0 - G2


Input Watts (W): 114
Input Voltage (V): NR
Input Current (Ain): NR
Voltage Rise (V): NR
Power Factor: NR
Total Harmonic Distortion (THDi): NR
Frequency (hertz): 60
Stabilization Time: NR
Operation Time: NR
Ambient Temperature (°C): NR
Test Distance: 24 FT



REPORT NUMBER: P949190
 CATALOG NUMBER: GLAN-SB4A-735-U-T2R-HSS

Iso-Footcandle Lines of Horizontal Illumination


✕ Max cd
 - - - 1/2 Max cd



Based on 25 foot mounting height. Maximum calculated value = 6.6 fc
 Type II - Medium - N/A

REPORT NUMBER: P949190
CATALOG NUMBER: GLAN-SB4A-735-U-T2R-HSS

Luminous Intensity Polar Plot



— Vertical Plane Through 77-Deg Lateral - - - Horizontal Cone Through 67.5-Deg Vertical

REPORT NUMBER: P949190
 CATALOG NUMBER: GLAN-SB4A-735-U-T2R-HSS


FLUX DISTRIBUTION:

		Downward	Upward	Total
House Side	Lumens	1119.9	0.0	1119.9
	% Fixture	7.4	0.0	7.4
Street Side	Lumens	14102.1	0.0	14102.1
	% Fixture	92.6	0.0	92.6
Total	Lumens	15222.0	0.0	15222.0
	% Fixture	100.0	0.0	100.0

ZONAL LUMENS:

Zone	Lumens	% Fixture
0°-10°	179.2	1.2
10°-20°	627.4	4.1
20°-30°	1210.7	8.0
30°-40°	2101.8	13.8
40°-50°	3051.8	20.0
50°-60°	3504.6	23.0
60°-70°	3042.6	20.0
70°-80°	1433.1	9.4
80°-90°	70.9	0.5
90°-100°	0.0	0.0
100°-110°	0.0	0.0
110°-120°	0.0	0.0
120°-130°	0.0	0.0
130°-140°	0.0	0.0
140°-150°	0.0	0.0
150°-160°	0.0	0.0
160°-170°	0.0	0.0
170°-180°	0.0	0.0
0°-90°	15222.0	100.0
0°-180°	15222.0	100.0

Coefficient of Utilization




REPORT NUMBER: P949190
 CATALOG NUMBER: GLAN-SB4A-735-U-T2R-HSS

LUMINAIRE CLASSIFICATION SYSTEM LUMEN TABLE AND BUG RATING:

Zone	Lumens	% Fixture	Zone Rating/Lumen Limit		
			B	U	G
FL (0°-30°)	1758.0	11.5			
FM (30°-60°)	8058.1	52.9			
FH (60°-80°)	4216.5	27.7			G2/5000
FVH (80°-90°)	69.6	0.5			G1/100
BL (0°-30°)	259.3	1.7	B1/500		
BM (30°-60°)	600.0	3.9	B1/1000		
BH (60°-80°)	259.3	1.7	B1/500		G1/500
BVH (80°-90°)	1.3	0.0			G0/10
UL (90°-100°)	0.0	0.0		U0/0	
UH (100°-180°)	0.0	0.0		U0/0	

BUG Rating: B1-U0-G2
 Type II Medium



REPORT NUMBER: P949190
 CATALOG NUMBER: GLAN-SB4A-735-U-T2R-HSS

CANDELA DISTRIBUTION (FULL):

	0°	5°	15°	25°	35°	45°	55°	65°	75°	77°
0°	1755.3	1755.3	1755.3	1755.3	1755.3	1755.3	1755.3	1755.3	1755.3	1755.3
2.5°	2430.2	2445.3	2423.6	2382.0	2319.6	2279.0	2179.7	2086.2	1982.2	1949.1
5°	2962.4	2975.6	2951.1	2905.7	2822.5	2743.1	2612.7	2417.0	2213.8	2148.5
7.5°	3356.6	3364.1	3354.7	3313.1	3233.7	3143.9	2998.3	2766.7	2465.2	2393.4
10°	3640.1	3664.7	3661.9	3645.8	3592.9	3520.1	3365.1	3101.3	2746.9	2654.2
12.5°	3828.2	3855.7	3871.7	3907.6	3904.8	3858.5	3722.4	3443.5	3027.6	2918.9
15°	3883.1	3912.4	3973.8	4057.0	4130.7	4154.4	4058.9	3779.1	3336.7	3197.8
17.5°	3851.9	3897.2	3971.0	4102.4	4264.0	4370.8	4360.4	4103.3	3617.5	3458.7
20°	3920.9	3964.4	4022.0	4132.6	4320.7	4514.5	4592.0	4413.3	3896.3	3729.9
22.5°	4302.8	4295.2	4300.9	4318.8	4431.3	4623.2	4782.9	4695.0	4172.3	4002.2
25°	4907.7	4873.7	4816.0	4718.7	4690.3	4782.9	4949.3	4944.6	4463.4	4281.0
27.5°	5601.5	5595.9	5460.7	5226.3	5093.9	5058.0	5137.4	5187.5	4751.7	4557.0
30°	6266.0	6281.2	6098.7	5837.8	5594.9	5454.1	5382.2	5418.1	5044.8	4854.8
32.5°	6844.5	6860.6	6662.1	6356.8	6056.2	5886.0	5734.8	5645.9	5364.3	5157.3
35°	7333.2	7349.3	7121.5	6784.0	6463.6	6309.5	6138.4	5895.5	5685.6	5492.8
37.5°	7769.9	7765.2	7459.9	7119.6	6804.8	6682.9	6593.1	6202.7	6016.5	5830.3
40°	8028.0	8047.8	7786.9	7411.7	7106.4	7017.5	7011.8	6583.6	6398.4	6217.8
42.5°	8103.6	8138.6	7949.5	7641.4	7364.4	7268.0	7416.4	6995.8	6842.6	6666.8
45°	7967.5	8001.5	7915.5	7701.9	7540.2	7477.8	7764.2	7423.0	7317.1	7143.2
47.5°	7570.5	7613.0	7633.8	7588.4	7586.5	7649.9	8076.2	7872.9	7880.5	7702.8
50°	6802.0	6873.8	7064.8	7225.5	7474.1	7786.0	8379.6	8360.7	8515.7	8362.6
52.5°	5404.9	5507.0	6164.9	6604.4	7163.1	7760.5	8713.3	9143.4	9630.2	9406.1
55°	4343.4	4343.4	4878.4	5700.8	6556.2	7592.2	8858.8	9651.9	10389.2	10336.3
57.5°	3540.9	3583.4	3924.7	4651.6	5678.1	7191.4	8948.6	9971.4	11000.8	10962.0
60°	2185.4	2277.1	2921.8	3639.2	4679.0	6477.8	8891.9	10294.7	11742.8	11774.0
62.5°	1230.7	1264.7	1552.1	2618.3	3638.2	5518.3	8458.1	10475.2	12691.8	12824.1
65°	849.8	866.8	977.4	1629.6	2521.9	4393.5	7610.2	10362.7	13642.7	13910.2
67.5°	617.2	625.8	694.8	995.3	1496.3	3185.5	6281.2	9795.6	14146.5	14593.6
70°	474.5	480.2	530.3	654.1	883.8	1966.1	4561.8	8667.9	13781.7	14315.7
72.5°	385.7	391.3	430.1	484.0	586.1	1162.7	2764.8	7039.2	12171.0	12747.6
75°	325.2	332.7	367.7	402.7	459.4	746.7	1296.9	4902.0	9152.8	9530.9
77.5°	180.5	166.4	298.7	333.7	387.6	472.6	606.8	2884.9	5126.1	5231.0
80°	112.5	116.3	237.3	268.4	297.8	238.2	277.9	1110.7	1777.1	1688.2
82.5°	6.6	15.1	182.4	193.8	204.2	102.1	104.9	377.2	428.2	393.2
85°	0.0	0.0	83.2	67.1	70.9	29.3	30.2	87.9	57.7	62.4
87.5°	0.0	0.0	0.0	1.9	0.0	2.8	5.7	7.6	2.8	3.8
90°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0

REPORT NUMBER: P949190
 CATALOG NUMBER: GLAN-SB4A-735-U-T2R-HSS

CANDELA DISTRIBUTION (continued):

85°	90°	95°	105°	115°	125°	135°	145°	155°	165°	175°
1755.3	0°	1755.3	1755.3	1755.3	1755.3	1755.3	1755.3	1755.3	1755.3	1755.3
1845.1	2.5°	1779.0	1712.8	1578.6	1447.2	1340.4	1241.1	1170.2	1103.1	1069.1
1964.2	5°	1832.8	1693.9	1425.4	1188.2	997.2	844.1	744.9	674.0	638.0
2110.7	7.5°	1908.5	1699.6	1291.2	961.3	736.3	605.0	548.2	525.6	518.0
2276.2	10°	2003.9	1712.8	1171.2	774.2	580.4	514.2	491.5	482.1	476.4
2462.4	12.5°	2110.7	1725.1	1052.1	642.8	510.4	476.4	460.3	449.0	441.4
2653.3	15°	2214.7	1732.6	928.2	551.1	474.5	447.1	430.1	417.8	407.4
2840.5	17.5°	2317.7	1743.0	812.0	496.3	445.2	417.8	400.8	385.7	377.2
3037.1	20°	2432.1	1741.1	702.3	457.5	415.9	388.5	370.5	356.4	347.9
3245.0	22.5°	2538.0	1731.7	605.9	424.4	385.7	359.2	339.3	325.2	316.7
3457.7	25°	2659.9	1724.1	525.6	394.2	357.3	330.8	309.1	295.9	286.4
3671.3	27.5°	2777.1	1712.8	467.0	366.8	329.9	304.4	283.6	268.4	259.9
3891.6	30°	2892.5	1709.9	445.2	340.3	305.3	279.8	259.0	244.8	238.2
4133.6	32.5°	3031.4	1717.5	454.7	330.8	282.6	257.1	237.3	226.9	220.2
4403.0	35°	3179.8	1715.6	468.8	339.3	267.5	234.4	219.3	212.7	206.1
4701.6	37.5°	3366.0	1718.5	480.2	353.5	261.8	215.5	207.0	198.5	194.7
5028.7	40°	3643.9	1812.0	474.5	365.8	259.9	202.3	185.3	182.4	179.6
5398.3	42.5°	3984.2	2015.3	482.1	366.8	259.0	192.8	170.1	175.8	169.2
5815.1	45°	4356.6	2237.4	530.3	346.9	258.1	188.1	162.6	169.2	158.8
6298.2	47.5°	4726.2	2457.6	579.4	318.5	255.2	187.2	156.0	152.2	149.3
6927.7	50°	5235.7	2637.2	598.3	279.8	248.6	185.3	143.7	144.6	142.7
7815.3	52.5°	5790.6	2675.0	575.7	236.3	229.7	179.6	135.2	139.0	138.0
8440.1	55°	6136.5	2634.4	475.5	196.6	200.4	156.9	126.7	134.2	134.2
9050.7	57.5°	6493.8	2461.4	337.5	159.7	166.4	128.6	119.1	129.5	128.6
9786.1	60°	6750.9	2181.6	222.1	131.4	132.3	105.9	110.6	121.9	121.0
10544.2	62.5°	6942.8	1872.5	142.7	111.5	101.1	95.5	101.1	110.6	106.8
11187.0	65°	6921.1	1444.3	109.6	95.5	83.2	83.2	87.9	96.4	85.1
11309.9	67.5°	6517.5	977.4	90.7	80.3	69.9	69.0	72.8	80.3	72.8
10680.3	70°	5796.2	639.0	72.8	62.4	55.8	51.0	58.6	69.0	61.4
9092.3	72.5°	4704.5	389.4	54.8	45.4	40.6	33.1	46.3	56.7	49.2
6322.7	75°	3043.7	198.5	37.8	29.3	21.7	19.9	34.0	42.5	34.0
2805.5	77.5°	1164.5	83.2	20.8	13.2	11.3	9.5	18.9	25.5	14.2
543.5	80°	224.0	35.0	10.4	6.6	5.7	3.8	2.8	1.9	0.0
96.4	82.5°	38.8	11.3	3.8	1.9	0.0	0.0	0.0	0.0	0.0
18.9	85°	13.2	1.9	0.0	0.0	0.0	0.0	0.0	0.0	0.0
6.6	87.5°	4.7	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
0.0	90°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0

(END O

180°
<hr/>
1755.3
1065.3
623.9
507.6
468.8
432.9
398.9
367.7
337.5
308.1
278.8
255.2
235.4
220.2
206.1
194.7
179.6
167.3
158.8
150.3
144.6
139.9
134.2
127.6
116.3
94.5
66.2
55.8
44.4
32.1
18.0
3.8
0.0
0.0
0.0
0.0
0.0
0.0

F REPORT)