

Scaled data based on original data using  
LM-79-08 Approved Method: Electrical and Photometric Measurements of Solid-  
State Lighting Products

Test Report Prepared for  
Cooper Lighting Solutions  
(formerly Eaton)

Brand: STREETWORKS

Report Number: P947402

Luminaire Tested: **GLAN-SB2D-735-U-SLL**

Issue Date: 1/21/2025

### Test Information

Test Method: LM-79-08  
Report Number: P947402  
TEST IS SCALED FROM IESNA LM-79-08 TEST DATA (G2-2411-289-8)  
Test Lab: INNOVATION CENTER  
Issue Date: 1/21/2025  
Manufacturer: COOPER LIGHTING SOLUTIONS (FORMERLY EATON)  
Product Line: STREETWORKS  
Catalog Number: GLAN-SB2D-735-U-SLL  
Description: GALLEON AREA AND ROADWAY HIGH DENSITY LED LUMINAIRE  
(2) 70 CRI, 3500K, 900mA LIGHTSQUARES WITH 26 LEDS EACH AND SPILL LIGHT  
ELIMINATOR LEFT OPTICS  
Light Source: -  
Ballast/Driver: -

### Summary

Lumens per Lamp: N/A  
Luminaire Lumens: 20277 lumens  
Efficiency: N/A  
Efficacy: 137.4 lumens/watt  
Luminous Opening: Rectangular (W 0.5' x L: 1' x H: 0')  
IES Classification: Type IV - Short  
BUG Rating: B3 - U0 - G4

Input Watts (W): 147.6  
Input Voltage (V): NR  
Input Current (Ain): NR  
Voltage Rise (V): NR  
Power Factor: NR  
Total Harmonic Distortion (THDi): NR  
Frequency (hertz): 60  
Stabilization Time: NR  
Operation Time: NR  
Ambient Temperature (°C): NR  
Test Distance: 24 FT




REPORT NUMBER: P947402

CATALOG NUMBER: GLAN-SB2D-735-U-SLL

## Iso-Footcandle Lines of Horizontal Illumination

× Max cd  
- - - 1/2 Max cd




Based on 25 foot mounting height. Maximum calculated value = 6.2 fc

Type IV - Short - N/A

REPORT NUMBER: P947402  
CATALOG NUMBER: GLAN-SB2D-735-U-SLL

## Luminous Intensity Polar Plot



REPORT NUMBER: P947402

CATALOG NUMBER: GLAN-SB2D-735-U-SLL


**FLUX DISTRIBUTION:**

|                    |           | Downward | Upward | Total   |
|--------------------|-----------|----------|--------|---------|
| <b>House Side</b>  | Lumens    | 5153.4   | 0.0    | 5153.4  |
|                    | % Fixture | 25.4     | 0.0    | 25.4    |
| <b>Street Side</b> | Lumens    | 15123.6  | 0.0    | 15123.6 |
|                    | % Fixture | 74.6     | 0.0    | 74.6    |
| <b>Total</b>       | Lumens    | 20277.0  | 0.0    | 20277.0 |
|                    | % Fixture | 100.0    | 0.0    | 100.0   |

**ZONAL LUMENS:**

| Zone      | Lumens  | % Fixture |
|-----------|---------|-----------|
| 0°-10°    | 276.6   | 1.4       |
| 10°-20°   | 868.3   | 4.3       |
| 20°-30°   | 1341.2  | 6.6       |
| 30°-40°   | 1699.6  | 8.4       |
| 40°-50°   | 2563.5  | 12.6      |
| 50°-60°   | 4141.7  | 20.4      |
| 60°-70°   | 5163.3  | 25.5      |
| 70°-80°   | 3385.8  | 16.7      |
| 80°-90°   | 837.1   | 4.1       |
| 90°-100°  | 0.0     | 0.0       |
| 100°-110° | 0.0     | 0.0       |
| 110°-120° | 0.0     | 0.0       |
| 120°-130° | 0.0     | 0.0       |
| 130°-140° | 0.0     | 0.0       |
| 140°-150° | 0.0     | 0.0       |
| 150°-160° | 0.0     | 0.0       |
| 160°-170° | 0.0     | 0.0       |
| 170°-180° | 0.0     | 0.0       |
| 0°-90°    | 20277.0 | 100.0     |
| 0°-180°   | 20277.0 | 100.0     |

**Coefficient of Utilization**



REPORT NUMBER: P947402


CATALOG NUMBER: GLAN-SB2D-735-U-SLL

**LUMINAIRE CLASSIFICATION SYSTEM LUMEN TABLE AND BUG RATING:**

| Zone |             | Lumens | % Fixture | Zone Rating/Lumen Limit |      |         |
|------|-------------|--------|-----------|-------------------------|------|---------|
|      |             |        |           | B                       | U    | G       |
| FL   | (0°-30°)    | 1363.9 | 6.7       |                         |      |         |
| FM   | (30°-60°)   | 5914.4 | 29.2      |                         |      |         |
| FH   | (60°-80°)   | 7155.8 | 35.3      |                         |      | G3/7500 |
| FVH  | (80°-90°)   | 689.6  | 3.4       |                         |      | G4/750  |
| BL   | (0°-30°)    | 1122.2 | 5.5       | B3/2500                 |      |         |
| BM   | (30°-60°)   | 2490.4 | 12.3      | B2/2500                 |      |         |
| BH   | (60°-80°)   | 1393.2 | 6.9       | B3/2500                 |      | G3/2500 |
| BVH  | (80°-90°)   | 147.5  | 0.7       |                         |      | G2/225  |
| UL   | (90°-100°)  | 0.0    | 0.0       |                         | U0/0 |         |
| UH   | (100°-180°) | 0.0    | 0.0       |                         | U0/0 |         |

**BUG Rating: B3-U0-G4**

Type IV Short



REPORT NUMBER: P947402

CATALOG NUMBER: GLAN-SB2D-735-U-SLL

**CANDELA DISTRIBUTION (FULL):**

|       | 0°      | 5°      | 10°     | 15°     | 20°     | 25°     | 30°     | 35°     | 40°     | 45°     |
|-------|---------|---------|---------|---------|---------|---------|---------|---------|---------|---------|
| 0°    | 2788.3  | 2788.3  | 2788.3  | 2788.3  | 2788.3  | 2788.3  | 2788.3  | 2788.3  | 2788.3  | 2788.3  |
| 2.5°  | 2998.5  | 3009.8  | 3021.3  | 3037.5  | 3053.6  | 3063.2  | 3072.9  | 3077.7  | 3082.5  | 3080.4  |
| 5°    | 3224.3  | 3264.0  | 3303.8  | 3343.1  | 3382.6  | 3404.0  | 3425.4  | 3438.4  | 3451.4  | 3461.3  |
| 7.5°  | 3451.1  | 3515.7  | 3580.2  | 3638.3  | 3696.4  | 3731.4  | 3766.4  | 3785.3  | 3804.2  | 3813.3  |
| 10°   | 3625.0  | 3701.3  | 3777.7  | 3845.9  | 3914.1  | 3955.4  | 3996.4  | 4014.8  | 4033.1  | 4040.1  |
| 12.5° | 3731.4  | 3814.2  | 3896.9  | 3958.6  | 4020.0  | 4049.9  | 4079.9  | 4090.0  | 4100.0  | 4101.1  |
| 15°   | 3796.1  | 3867.6  | 3939.0  | 3977.6  | 4016.3  | 4017.4  | 4018.5  | 4007.8  | 3997.1  | 3984.5  |
| 17.5° | 3832.5  | 3880.8  | 3929.0  | 3929.8  | 3930.4  | 3887.1  | 3843.8  | 3804.1  | 3764.3  | 3736.2  |
| 20°   | 3872.6  | 3889.4  | 3906.3  | 3855.5  | 3804.7  | 3709.1  | 3613.4  | 3543.7  | 3474.1  | 3431.3  |
| 22.5° | 3919.2  | 3897.1  | 3875.1  | 3769.8  | 3664.5  | 3523.8  | 3383.1  | 3296.1  | 3209.0  | 3161.7  |
| 25°   | 3979.1  | 3909.6  | 3840.0  | 3680.2  | 3520.3  | 3349.4  | 3178.6  | 3087.0  | 2995.6  | 2950.9  |
| 27.5° | 4060.4  | 3936.1  | 3811.7  | 3599.9  | 3388.3  | 3198.9  | 3009.5  | 2919.4  | 2829.5  | 2787.2  |
| 30°   | 4170.1  | 3984.7  | 3799.4  | 3538.7  | 3278.1  | 3080.8  | 2883.5  | 2799.9  | 2716.4  | 2677.0  |
| 32.5° | 4299.6  | 4045.7  | 3791.9  | 3497.0  | 3202.1  | 3016.7  | 2831.3  | 2765.7  | 2700.0  | 2671.6  |
| 35°   | 4456.8  | 4146.1  | 3835.5  | 3528.2  | 3221.1  | 3092.2  | 2963.5  | 2948.2  | 2932.9  | 2930.6  |
| 37.5° | 4721.6  | 4356.2  | 3990.7  | 3711.4  | 3432.2  | 3423.8  | 3415.5  | 3485.4  | 3555.4  | 3591.8  |
| 40°   | 5121.8  | 4724.3  | 4326.8  | 4119.2  | 3911.5  | 4058.1  | 4204.6  | 4374.8  | 4544.9  | 4629.6  |
| 42.5° | 5652.5  | 5258.1  | 4863.7  | 4744.1  | 4624.5  | 4944.2  | 5263.9  | 5573.3  | 5882.7  | 6064.4  |
| 45°   | 6307.8  | 5953.6  | 5599.2  | 5546.5  | 5493.6  | 6005.8  | 6518.1  | 7026.5  | 7535.0  | 7843.7  |
| 47.5° | 7127.4  | 6782.8  | 6438.0  | 6427.3  | 6416.6  | 7155.5  | 7894.2  | 8638.6  | 9382.8  | 9819.9  |
| 50°   | 8201.6  | 7775.9  | 7350.3  | 7352.1  | 7353.9  | 8306.2  | 9258.4  | 10240.9 | 11223.5 | 11817.5 |
| 52.5° | 9434.7  | 8919.2  | 8403.8  | 8351.7  | 8299.5  | 9437.0  | 10574.4 | 11790.1 | 13005.6 | 13717.7 |
| 55°   | 10747.5 | 10238.3 | 9729.0  | 9525.8  | 9322.6  | 10588.5 | 11854.4 | 13303.6 | 14752.9 | 15599.7 |
| 57.5° | 11941.6 | 11664.3 | 11386.8 | 10979.3 | 10571.9 | 11850.1 | 13128.4 | 14769.9 | 16411.3 | 17461.4 |
| 60°   | 12663.3 | 13094.0 | 13524.9 | 13018.8 | 12512.7 | 13722.4 | 14932.1 | 16689.6 | 18447.0 | 19582.0 |
| 62.5° | 12296.8 | 13473.9 | 14650.9 | 14593.9 | 14536.7 | 15644.9 | 16753.1 | 18425.2 | 20097.2 | 21146.3 |
| 65°   | 11563.4 | 12668.1 | 13772.8 | 13991.4 | 14209.9 | 15618.1 | 17026.5 | 18647.9 | 20269.1 | 21162.3 |
| 67.5° | 10580.6 | 11631.3 | 12682.0 | 12784.5 | 12886.9 | 14354.2 | 15821.4 | 17449.7 | 19078.1 | 19777.8 |
| 70°   | 9400.0  | 10542.8 | 11685.7 | 11731.5 | 11777.4 | 13089.5 | 14401.6 | 15802.9 | 17204.1 | 17593.0 |
| 72.5° | 7993.0  | 9304.4  | 10615.9 | 10648.9 | 10681.7 | 11708.3 | 12735.0 | 13784.5 | 14833.9 | 14873.2 |
| 75°   | 6213.1  | 7570.5  | 8927.8  | 9049.7  | 9171.5  | 9970.2  | 10768.9 | 11507.7 | 12246.5 | 12048.6 |
| 77.5° | 4439.2  | 5706.2  | 6973.3  | 7147.7  | 7322.1  | 7929.3  | 8536.5  | 9060.5  | 9584.5  | 9244.3  |
| 80°   | 2905.4  | 3971.4  | 5037.3  | 5254.0  | 5470.8  | 5929.4  | 6387.8  | 6662.9  | 6938.0  | 6390.7  |
| 82.5° | 1688.9  | 2417.6  | 3146.5  | 3388.6  | 3630.8  | 3946.5  | 4262.1  | 4376.9  | 4491.6  | 4061.5  |
| 85°   | 743.1   | 1129.9  | 1516.6  | 1722.6  | 1928.6  | 2187.9  | 2447.2  | 2512.3  | 2577.5  | 2233.0  |
| 87.5° | 230.0   | 360.0   | 490.0   | 604.9   | 719.9   | 849.5   | 979.2   | 984.8   | 990.2   | 831.3   |
| 90°   | 0.0     | 0.0     | 0.0     | 0.0     | 0.0     | 0.0     | 0.0     | 0.0     | 0.0     | 0.0     |

REPORT NUMBER: P947402

CATALOG NUMBER: GLAN-SB2D-735-U-SLL

**CANDELA DISTRIBUTION (continued):**

| 50°     |       | 55°     | 60°     | 65°     | 70°     | 75°     | 80°     | 85°     | 90°     | 95°    | 100°   |
|---------|-------|---------|---------|---------|---------|---------|---------|---------|---------|--------|--------|
| 2788.3  | 0°    | 2788.3  | 2788.3  | 2788.3  | 2788.3  | 2788.3  | 2788.3  | 2788.3  | 2788.3  | 2788.3 | 2788.3 |
| 3082.5  | 2.5°  | 3077.7  | 3072.9  | 3063.2  | 3053.6  | 3037.5  | 3021.3  | 3009.8  | 2998.5  | 2975.5 | 2952.5 |
| 3451.4  | 5°    | 3438.4  | 3425.4  | 3404.0  | 3382.6  | 3343.1  | 3303.8  | 3264.0  | 3224.3  | 3173.4 | 3122.6 |
| 3804.2  | 7.5°  | 3785.3  | 3766.4  | 3731.4  | 3696.4  | 3638.3  | 3580.2  | 3515.7  | 3451.1  | 3367.2 | 3283.4 |
| 4033.1  | 10°   | 4014.8  | 3996.4  | 3955.4  | 3914.1  | 3845.9  | 3777.7  | 3701.3  | 3625.0  | 3518.9 | 3412.9 |
| 4100.0  | 12.5° | 4090.0  | 4079.9  | 4049.9  | 4020.0  | 3958.6  | 3896.9  | 3814.2  | 3731.4  | 3614.9 | 3498.5 |
| 3997.1  | 15°   | 4007.8  | 4018.5  | 4017.4  | 4016.3  | 3977.6  | 3939.0  | 3867.6  | 3796.1  | 3674.7 | 3553.3 |
| 3764.3  | 17.5° | 3804.1  | 3843.8  | 3887.1  | 3930.4  | 3929.8  | 3929.0  | 3880.8  | 3832.5  | 3709.4 | 3586.2 |
| 3474.1  | 20°   | 3543.7  | 3613.4  | 3709.1  | 3804.7  | 3855.5  | 3906.3  | 3889.4  | 3872.6  | 3744.7 | 3616.6 |
| 3209.0  | 22.5° | 3296.1  | 3383.1  | 3523.8  | 3664.5  | 3769.8  | 3875.1  | 3897.1  | 3919.2  | 3788.4 | 3657.6 |
| 2995.6  | 25°   | 3087.0  | 3178.6  | 3349.4  | 3520.3  | 3680.2  | 3840.0  | 3909.6  | 3979.1  | 3850.9 | 3722.9 |
| 2829.5  | 27.5° | 2919.4  | 3009.5  | 3198.9  | 3388.3  | 3599.9  | 3811.7  | 3936.1  | 4060.4  | 3938.2 | 3815.9 |
| 2716.4  | 30°   | 2799.9  | 2883.5  | 3080.8  | 3278.1  | 3538.7  | 3799.4  | 3984.7  | 4170.1  | 4052.0 | 3934.0 |
| 2700.0  | 32.5° | 2765.7  | 2831.3  | 3016.7  | 3202.1  | 3497.0  | 3791.9  | 4045.7  | 4299.6  | 4182.6 | 4065.8 |
| 2932.9  | 35°   | 2948.2  | 2963.5  | 3092.2  | 3221.1  | 3528.2  | 3835.5  | 4146.1  | 4456.8  | 4344.9 | 4232.9 |
| 3555.4  | 37.5° | 3485.4  | 3415.5  | 3423.8  | 3432.2  | 3711.4  | 3990.7  | 4356.2  | 4721.6  | 4578.9 | 4436.2 |
| 4544.9  | 40°   | 4374.8  | 4204.6  | 4058.1  | 3911.5  | 4119.2  | 4326.8  | 4724.3  | 5121.8  | 4913.8 | 4705.8 |
| 5882.7  | 42.5° | 5573.3  | 5263.9  | 4944.2  | 4624.5  | 4744.1  | 4863.7  | 5258.1  | 5652.5  | 5352.3 | 5052.0 |
| 7535.0  | 45°   | 7026.5  | 6518.1  | 6005.8  | 5493.6  | 5546.5  | 5599.2  | 5953.6  | 6307.8  | 5902.9 | 5497.9 |
| 9382.8  | 47.5° | 8638.6  | 7894.2  | 7155.5  | 6416.6  | 6427.3  | 6438.0  | 6782.8  | 7127.4  | 6557.4 | 5987.4 |
| 11223.5 | 50°   | 10240.9 | 9258.4  | 8306.2  | 7353.9  | 7352.1  | 7350.3  | 7775.9  | 8201.6  | 7342.4 | 6483.0 |
| 13005.6 | 52.5° | 11790.1 | 10574.4 | 9437.0  | 8299.5  | 8351.7  | 8403.8  | 8919.2  | 9434.7  | 8166.8 | 6899.0 |
| 14752.9 | 55°   | 13303.6 | 11854.4 | 10588.5 | 9322.6  | 9525.8  | 9729.0  | 10238.3 | 10747.5 | 8897.8 | 7048.2 |
| 16411.3 | 57.5° | 14769.9 | 13128.4 | 11850.1 | 10571.9 | 10979.3 | 11386.8 | 11664.3 | 11941.6 | 9415.9 | 6890.2 |
| 18447.0 | 60°   | 16689.6 | 14932.1 | 13722.4 | 12512.7 | 13018.8 | 13524.9 | 13094.0 | 12663.3 | 9545.4 | 6427.3 |
| 20097.2 | 62.5° | 18425.2 | 16753.1 | 15644.9 | 14536.7 | 14593.9 | 14650.9 | 13473.9 | 12296.8 | 9000.2 | 5703.6 |
| 20269.1 | 65°   | 18647.9 | 17026.5 | 15618.1 | 14209.9 | 13991.4 | 13772.8 | 12668.1 | 11563.4 | 8228.9 | 4894.4 |
| 19078.1 | 67.5° | 17449.7 | 15821.4 | 14354.2 | 12886.9 | 12784.5 | 12682.0 | 11631.3 | 10580.6 | 7311.0 | 4041.4 |
| 17204.1 | 70°   | 15802.9 | 14401.6 | 13089.5 | 11777.4 | 11731.5 | 11685.7 | 10542.8 | 9400.0  | 6309.4 | 3218.9 |
| 14833.9 | 72.5° | 13784.5 | 12735.0 | 11708.3 | 10681.7 | 10648.9 | 10615.9 | 9304.4  | 7993.0  | 5223.7 | 2454.4 |
| 12246.5 | 75°   | 11507.7 | 10768.9 | 9970.2  | 9171.5  | 9049.7  | 8927.8  | 7570.5  | 6213.1  | 3979.0 | 1744.9 |
| 9584.5  | 77.5° | 9060.5  | 8536.5  | 7929.3  | 7322.1  | 7147.7  | 6973.3  | 5706.2  | 4439.2  | 2784.9 | 1130.7 |
| 6938.0  | 80°   | 6662.9  | 6387.8  | 5929.4  | 5470.8  | 5254.0  | 5037.3  | 3971.4  | 2905.4  | 1794.3 | 683.2  |
| 4491.6  | 82.5° | 4376.9  | 4262.1  | 3946.5  | 3630.8  | 3388.6  | 3146.5  | 2417.6  | 1688.9  | 1038.5 | 388.2  |
| 2577.5  | 85°   | 2512.3  | 2447.2  | 2187.9  | 1928.6  | 1722.6  | 1516.6  | 1129.9  | 743.1   | 467.1  | 191.3  |
| 990.2   | 87.5° | 984.8   | 979.2   | 849.5   | 719.9   | 604.9   | 490.0   | 360.0   | 230.0   | 153.0  | 76.0   |
| 0.0     | 90°   | 0.0     | 0.0     | 0.0     | 0.0     | 0.0     | 0.0     | 0.0     | 0.0     | 0.0    | 0.0    |



REPORT NUMBER: P947402

CATALOG NUMBER: GLAN-SB2D-735-U-SLL

**CANDELA DISTRIBUTION (continued):**

| 105°   |       | 110°   | 115°   | 120°   | 125°   | 130°   | 135°   | 140°   | 145°   | 150°   | 155°   |
|--------|-------|--------|--------|--------|--------|--------|--------|--------|--------|--------|--------|
| 2788.3 | 0°    | 2788.3 | 2788.3 | 2788.3 | 2788.3 | 2788.3 | 2788.3 | 2788.3 | 2788.3 | 2788.3 | 2788.3 |
| 2928.0 | 2.5°  | 2903.6 | 2879.0 | 2854.4 | 2830.8 | 2807.3 | 2784.5 | 2759.2 | 2738.6 | 2718.2 | 2699.7 |
| 3071.9 | 5°    | 3021.3 | 2970.3 | 2919.3 | 2871.7 | 2824.1 | 2779.2 | 2734.8 | 2696.0 | 2657.2 | 2624.7 |
| 3206.0 | 7.5°  | 3128.5 | 3053.1 | 2977.6 | 2911.2 | 2844.8 | 2783.4 | 2726.0 | 2674.4 | 2623.0 | 2580.2 |
| 3310.5 | 10°   | 3208.2 | 3116.6 | 3024.9 | 2946.4 | 2867.7 | 2792.0 | 2730.3 | 2675.9 | 2621.6 | 2578.8 |
| 3382.5 | 12.5° | 3266.5 | 3158.5 | 3050.4 | 2961.5 | 2872.6 | 2793.1 | 2735.6 | 2691.1 | 2646.8 | 2618.4 |
| 3427.4 | 15°   | 3301.6 | 3177.2 | 3052.8 | 2949.8 | 2846.9 | 2758.8 | 2712.8 | 2691.5 | 2670.4 | 2674.2 |
| 3448.9 | 17.5° | 3311.7 | 3167.2 | 3022.8 | 2899.0 | 2775.2 | 2671.6 | 2643.3 | 2651.1 | 2658.8 | 2705.4 |
| 3465.7 | 20°   | 3314.9 | 3139.8 | 2964.8 | 2811.4 | 2657.9 | 2537.4 | 2529.9 | 2566.2 | 2602.6 | 2683.6 |
| 3488.4 | 22.5° | 3319.2 | 3106.2 | 2893.3 | 2708.6 | 2523.8 | 2386.5 | 2401.2 | 2455.0 | 2508.8 | 2601.2 |
| 3529.5 | 25°   | 3336.1 | 3073.1 | 2810.2 | 2593.7 | 2377.4 | 2236.7 | 2276.3 | 2338.4 | 2400.4 | 2483.5 |
| 3593.7 | 27.5° | 3371.4 | 3050.9 | 2730.5 | 2488.8 | 2247.1 | 2119.0 | 2167.2 | 2227.1 | 2287.0 | 2355.4 |
| 3676.8 | 30°   | 3419.7 | 3040.6 | 2661.2 | 2401.1 | 2140.9 | 2033.4 | 2071.2 | 2118.7 | 2166.4 | 2223.1 |
| 3763.6 | 32.5° | 3461.5 | 3027.7 | 2593.7 | 2325.4 | 2057.0 | 1970.3 | 1987.1 | 2015.2 | 2043.4 | 2088.6 |
| 3862.5 | 35°   | 3492.1 | 3003.5 | 2515.2 | 2251.0 | 1986.9 | 1914.7 | 1907.7 | 1915.4 | 1923.2 | 1957.8 |
| 3973.2 | 37.5° | 3510.3 | 2962.1 | 2414.0 | 2163.5 | 1913.1 | 1849.9 | 1824.5 | 1815.9 | 1807.3 | 1832.2 |
| 4113.8 | 40°   | 3521.7 | 2905.1 | 2288.6 | 2059.1 | 1829.6 | 1772.4 | 1733.3 | 1713.9 | 1694.6 | 1712.4 |
| 4297.7 | 42.5° | 3543.4 | 2846.3 | 2149.3 | 1943.9 | 1738.4 | 1685.7 | 1636.5 | 1610.8 | 1585.1 | 1599.7 |
| 4539.8 | 45°   | 3581.6 | 2791.6 | 2001.6 | 1821.5 | 1641.3 | 1587.8 | 1540.2 | 1515.1 | 1490.2 | 1502.4 |
| 4797.6 | 47.5° | 3607.8 | 2746.4 | 1885.0 | 1724.6 | 1564.3 | 1495.2 | 1454.3 | 1433.3 | 1412.3 | 1423.9 |
| 5036.8 | 50°   | 3590.7 | 2697.2 | 1803.7 | 1660.3 | 1517.0 | 1426.2 | 1378.6 | 1360.0 | 1341.5 | 1359.5 |
| 5192.2 | 52.5° | 3485.3 | 2614.1 | 1742.9 | 1618.0 | 1493.1 | 1388.8 | 1322.2 | 1303.8 | 1285.5 | 1312.6 |
| 5158.0 | 55°   | 3267.6 | 2476.3 | 1684.9 | 1587.3 | 1489.6 | 1392.5 | 1292.3 | 1263.2 | 1234.2 | 1272.6 |
| 4917.0 | 57.5° | 2943.9 | 2282.0 | 1619.9 | 1550.9 | 1481.9 | 1396.3 | 1274.3 | 1231.9 | 1189.6 | 1230.9 |
| 4468.6 | 60°   | 2509.9 | 2029.7 | 1549.5 | 1495.2 | 1441.0 | 1384.5 | 1257.4 | 1202.5 | 1147.5 | 1183.8 |
| 3862.3 | 62.5° | 2020.9 | 1727.7 | 1434.6 | 1398.5 | 1362.6 | 1355.6 | 1237.7 | 1169.0 | 1100.4 | 1123.4 |
| 3243.6 | 65°   | 1592.9 | 1456.1 | 1319.2 | 1302.2 | 1285.2 | 1286.1 | 1196.2 | 1123.2 | 1050.1 | 1059.0 |
| 2637.6 | 67.5° | 1233.9 | 1195.0 | 1156.1 | 1165.6 | 1175.0 | 1172.7 | 1122.2 | 1061.4 | 1000.6 | 997.8  |
| 2076.8 | 70°   | 934.6  | 945.7  | 956.7  | 1000.8 | 1044.8 | 1044.8 | 1028.2 | 985.0  | 941.8  | 932.1  |
| 1587.7 | 72.5° | 720.9  | 754.4  | 788.0  | 850.5  | 912.9  | 923.4  | 923.6  | 893.9  | 864.3  | 850.2  |
| 1152.3 | 75°   | 559.8  | 590.2  | 620.6  | 690.5  | 760.5  | 808.9  | 804.8  | 782.0  | 759.1  | 745.6  |
| 780.8  | 77.5° | 431.0  | 451.6  | 472.4  | 540.3  | 608.3  | 688.0  | 685.8  | 667.5  | 649.2  | 635.5  |
| 503.1  | 80°   | 323.1  | 331.7  | 340.2  | 397.8  | 455.3  | 550.5  | 550.2  | 534.9  | 519.5  | 508.0  |
| 309.4  | 82.5° | 230.9  | 232.4  | 234.1  | 276.5  | 318.8  | 400.2  | 404.7  | 397.2  | 389.7  | 381.5  |
| 165.4  | 85°   | 139.6  | 138.9  | 138.0  | 169.1  | 200.1  | 260.5  | 266.4  | 258.4  | 250.4  | 241.3  |
| 68.6   | 87.5° | 61.2   | 60.5   | 59.7   | 72.3   | 85.1   | 110.2  | 117.7  | 114.5  | 111.3  | 109.6  |
| 0.0    | 90°   | 0.0    | 0.0    | 0.0    | 0.0    | 0.0    | 0.0    | 0.0    | 0.0    | 0.0    | 0.0    |

REPORT NUMBER: P947402

CATALOG NUMBER: GLAN-SB2D-735-U-SLL

**CANDELA DISTRIBUTION (continued):**

| 160°   |       | 165°   | 170°   | 175°   | 180°   | 185°   | 190°   | 195°   | 200°   | 205°   | 210°   |
|--------|-------|--------|--------|--------|--------|--------|--------|--------|--------|--------|--------|
| 2788.3 | 0°    | 2788.3 | 2788.3 | 2788.3 | 2788.3 | 2788.3 | 2788.3 | 2788.3 | 2788.3 | 2788.3 | 2788.3 |
| 2681.3 | 2.5°  | 2665.1 | 2649.0 | 2632.7 | 2616.5 | 2604.0 | 2591.4 | 2581.2 | 2571.1 | 2563.1 | 2555.2 |
| 2592.2 | 5°    | 2563.6 | 2534.9 | 2508.9 | 2482.8 | 2462.8 | 2442.7 | 2428.7 | 2414.6 | 2404.7 | 2394.7 |
| 2537.4 | 7.5°  | 2501.3 | 2465.1 | 2433.3 | 2401.5 | 2377.6 | 2353.9 | 2337.2 | 2320.5 | 2309.0 | 2297.7 |
| 2536.0 | 10°   | 2497.1 | 2458.2 | 2422.3 | 2386.5 | 2358.0 | 2329.5 | 2310.9 | 2292.0 | 2281.2 | 2270.4 |
| 2590.1 | 12.5° | 2559.5 | 2529.1 | 2492.0 | 2455.0 | 2418.6 | 2382.2 | 2358.1 | 2334.1 | 2322.0 | 2310.0 |
| 2678.1 | 15°   | 2670.1 | 2662.2 | 2630.0 | 2597.8 | 2546.0 | 2494.2 | 2457.7 | 2421.1 | 2404.3 | 2387.6 |
| 2752.1 | 17.5° | 2776.9 | 2801.6 | 2775.6 | 2749.7 | 2681.2 | 2612.6 | 2558.7 | 2504.7 | 2479.9 | 2455.0 |
| 2764.7 | 20°   | 2816.6 | 2868.5 | 2856.5 | 2844.4 | 2766.0 | 2687.7 | 2621.6 | 2555.6 | 2523.8 | 2491.9 |
| 2693.9 | 22.5° | 2761.4 | 2828.9 | 2836.2 | 2843.4 | 2768.5 | 2693.6 | 2625.5 | 2557.4 | 2523.9 | 2490.3 |
| 2566.8 | 25°   | 2633.2 | 2699.7 | 2724.5 | 2749.2 | 2687.8 | 2626.5 | 2565.9 | 2505.6 | 2476.5 | 2447.5 |
| 2423.6 | 27.5° | 2476.9 | 2530.2 | 2557.8 | 2585.5 | 2541.7 | 2498.1 | 2451.1 | 2404.2 | 2384.7 | 2365.1 |
| 2279.8 | 30°   | 2324.0 | 2368.3 | 2390.8 | 2413.2 | 2380.0 | 2346.6 | 2313.0 | 2279.2 | 2269.2 | 2259.2 |
| 2134.0 | 32.5° | 2176.4 | 2218.8 | 2243.8 | 2268.8 | 2238.2 | 2207.5 | 2180.6 | 2153.8 | 2147.3 | 2140.7 |
| 1992.2 | 35°   | 2034.2 | 2076.2 | 2106.2 | 2136.1 | 2114.3 | 2092.6 | 2067.8 | 2043.0 | 2033.1 | 2023.3 |
| 1856.9 | 37.5° | 1898.7 | 1940.7 | 1977.7 | 2014.7 | 2004.6 | 1994.6 | 1971.8 | 1948.9 | 1930.8 | 1912.8 |
| 1730.3 | 40°   | 1770.7 | 1811.2 | 1853.8 | 1896.5 | 1898.9 | 1901.3 | 1881.9 | 1862.6 | 1836.2 | 1810.1 |
| 1614.3 | 42.5° | 1652.6 | 1691.0 | 1737.0 | 1783.1 | 1795.4 | 1807.7 | 1791.3 | 1775.0 | 1742.4 | 1709.8 |
| 1514.8 | 45°   | 1551.2 | 1587.6 | 1635.3 | 1683.0 | 1700.7 | 1718.3 | 1703.6 | 1688.9 | 1651.6 | 1614.3 |
| 1435.3 | 47.5° | 1471.0 | 1506.5 | 1553.6 | 1600.6 | 1621.0 | 1641.3 | 1631.0 | 1620.7 | 1587.6 | 1554.4 |
| 1377.5 | 50°   | 1411.1 | 1444.6 | 1486.8 | 1528.9 | 1555.0 | 1581.2 | 1580.5 | 1580.1 | 1553.6 | 1527.0 |
| 1339.6 | 52.5° | 1370.4 | 1401.1 | 1440.4 | 1479.7 | 1510.6 | 1541.6 | 1547.1 | 1552.7 | 1531.1 | 1509.5 |
| 1310.9 | 55°   | 1344.1 | 1377.2 | 1411.7 | 1446.0 | 1478.8 | 1511.6 | 1519.3 | 1527.0 | 1508.2 | 1489.4 |
| 1272.2 | 57.5° | 1311.1 | 1350.0 | 1384.1 | 1418.2 | 1451.3 | 1484.2 | 1492.0 | 1499.8 | 1480.8 | 1461.8 |
| 1219.9 | 60°   | 1264.7 | 1309.4 | 1344.0 | 1378.6 | 1411.8 | 1445.0 | 1453.5 | 1462.1 | 1443.5 | 1424.9 |
| 1146.4 | 62.5° | 1198.5 | 1250.8 | 1287.7 | 1324.6 | 1355.0 | 1385.4 | 1393.6 | 1401.8 | 1385.0 | 1368.2 |
| 1067.8 | 65°   | 1123.7 | 1179.6 | 1214.9 | 1250.2 | 1277.0 | 1303.7 | 1312.2 | 1320.5 | 1304.4 | 1288.2 |
| 995.0  | 67.5° | 1046.6 | 1098.3 | 1131.8 | 1165.2 | 1188.3 | 1211.4 | 1219.6 | 1227.8 | 1212.9 | 1198.1 |
| 922.5  | 70°   | 967.9  | 1013.2 | 1042.1 | 1071.0 | 1091.9 | 1112.7 | 1120.7 | 1128.6 | 1116.5 | 1104.4 |
| 836.2  | 72.5° | 871.9  | 907.5  | 933.6  | 959.7  | 980.2  | 1000.6 | 1010.0 | 1019.4 | 1009.4 | 999.3  |
| 732.1  | 75°   | 758.6  | 785.1  | 808.8  | 832.4  | 851.0  | 869.6  | 879.5  | 889.3  | 884.4  | 879.5  |
| 621.8  | 77.5° | 643.5  | 665.0  | 685.3  | 705.6  | 725.2  | 744.7  | 753.9  | 763.1  | 756.2  | 749.2  |
| 496.5  | 80°   | 514.4  | 532.3  | 549.4  | 566.5  | 581.4  | 596.2  | 608.4  | 620.6  | 617.6  | 614.7  |
| 373.4  | 82.5° | 371.9  | 370.4  | 364.4  | 358.4  | 390.1  | 421.8  | 442.5  | 463.3  | 462.0  | 460.6  |
| 232.2  | 85°   | 224.5  | 216.7  | 200.1  | 183.5  | 213.1  | 242.9  | 268.6  | 294.2  | 292.1  | 290.0  |
| 107.8  | 87.5° | 107.5  | 107.2  | 94.6   | 81.9   | 94.3   | 106.8  | 117.2  | 127.5  | 125.0  | 122.2  |
| 0.0    | 90°   | 0.0    | 0.0    | 0.0    | 0.0    | 0.0    | 0.0    | 0.0    | 0.0    | 0.0    | 0.0    |

REPORT NUMBER: P947402

CATALOG NUMBER: GLAN-SB2D-735-U-SLL

**CANDELA DISTRIBUTION (continued):**

| 215°   |       | 220°   | 225°   | 230°   | 235°   | 240°   | 245°   | 250°   | 255°   | 260°   | 265°   |
|--------|-------|--------|--------|--------|--------|--------|--------|--------|--------|--------|--------|
| 2788.3 | 0°    | 2788.3 | 2788.3 | 2788.3 | 2788.3 | 2788.3 | 2788.3 | 2788.3 | 2788.3 | 2788.3 | 2788.3 |
| 2548.0 | 2.5°  | 2540.6 | 2531.5 | 2540.6 | 2548.0 | 2555.2 | 2563.1 | 2571.1 | 2581.2 | 2591.4 | 2604.0 |
| 2387.1 | 5°    | 2379.5 | 2372.1 | 2379.5 | 2387.1 | 2394.7 | 2404.7 | 2414.6 | 2428.7 | 2442.7 | 2462.8 |
| 2290.8 | 7.5°  | 2284.1 | 2279.0 | 2284.1 | 2290.8 | 2297.7 | 2309.0 | 2320.5 | 2337.2 | 2353.9 | 2377.6 |
| 2264.6 | 10°   | 2258.9 | 2256.5 | 2258.9 | 2264.6 | 2270.4 | 2281.2 | 2292.0 | 2310.9 | 2329.5 | 2358.0 |
| 2305.1 | 12.5° | 2300.2 | 2299.3 | 2300.2 | 2305.1 | 2310.0 | 2322.0 | 2334.1 | 2358.1 | 2382.2 | 2418.6 |
| 2381.2 | 15°   | 2374.7 | 2374.2 | 2374.7 | 2381.2 | 2387.6 | 2404.3 | 2421.1 | 2457.7 | 2494.2 | 2546.0 |
| 2446.8 | 17.5° | 2438.6 | 2437.3 | 2438.6 | 2446.8 | 2455.0 | 2479.9 | 2504.7 | 2558.7 | 2612.6 | 2681.2 |
| 2481.7 | 20°   | 2471.6 | 2468.4 | 2471.6 | 2481.7 | 2491.9 | 2523.8 | 2555.6 | 2621.6 | 2687.7 | 2766.0 |
| 2479.0 | 22.5° | 2467.8 | 2463.0 | 2467.8 | 2479.0 | 2490.3 | 2523.9 | 2557.4 | 2625.5 | 2693.6 | 2768.5 |
| 2436.9 | 25°   | 2426.4 | 2420.2 | 2426.4 | 2436.9 | 2447.5 | 2476.5 | 2505.6 | 2565.9 | 2626.5 | 2687.8 |
| 2360.3 | 27.5° | 2355.5 | 2353.9 | 2355.5 | 2360.3 | 2365.1 | 2384.7 | 2404.2 | 2451.1 | 2498.1 | 2541.7 |
| 2259.2 | 30°   | 2259.2 | 2260.8 | 2259.2 | 2259.2 | 2259.2 | 2269.2 | 2279.2 | 2313.0 | 2346.6 | 2380.0 |
| 2141.6 | 32.5° | 2142.6 | 2144.2 | 2142.6 | 2141.6 | 2140.7 | 2147.3 | 2153.8 | 2180.6 | 2207.5 | 2238.2 |
| 2021.1 | 35°   | 2019.0 | 2017.9 | 2019.0 | 2021.1 | 2023.3 | 2033.1 | 2043.0 | 2067.8 | 2092.6 | 2114.3 |
| 1903.3 | 37.5° | 1893.8 | 1888.4 | 1893.8 | 1903.3 | 1912.8 | 1930.8 | 1948.9 | 1971.8 | 1994.6 | 2004.6 |
| 1792.4 | 40°   | 1774.8 | 1764.3 | 1774.8 | 1792.4 | 1810.1 | 1836.2 | 1862.6 | 1881.9 | 1901.3 | 1898.9 |
| 1684.0 | 42.5° | 1658.2 | 1641.3 | 1658.2 | 1684.0 | 1709.8 | 1742.4 | 1775.0 | 1791.3 | 1807.7 | 1795.4 |
| 1584.0 | 45°   | 1553.8 | 1534.3 | 1553.8 | 1584.0 | 1614.3 | 1651.6 | 1688.9 | 1703.6 | 1718.3 | 1700.7 |
| 1526.4 | 47.5° | 1498.5 | 1479.7 | 1498.5 | 1526.4 | 1554.4 | 1587.6 | 1620.7 | 1631.0 | 1641.3 | 1621.0 |
| 1501.1 | 50°   | 1475.2 | 1457.3 | 1475.2 | 1501.1 | 1527.0 | 1553.6 | 1580.1 | 1580.5 | 1581.2 | 1555.0 |
| 1486.3 | 52.5° | 1463.1 | 1446.6 | 1463.1 | 1486.3 | 1509.5 | 1531.1 | 1552.7 | 1547.1 | 1541.6 | 1510.6 |
| 1469.0 | 55°   | 1448.7 | 1433.7 | 1448.7 | 1469.0 | 1489.4 | 1508.2 | 1527.0 | 1519.3 | 1511.6 | 1478.8 |
| 1441.6 | 57.5° | 1421.4 | 1405.9 | 1421.4 | 1441.6 | 1461.8 | 1480.8 | 1499.8 | 1492.0 | 1484.2 | 1451.3 |
| 1404.2 | 60°   | 1383.4 | 1367.4 | 1383.4 | 1404.2 | 1424.9 | 1443.5 | 1462.1 | 1453.5 | 1445.0 | 1411.8 |
| 1346.4 | 62.5° | 1324.6 | 1305.3 | 1324.6 | 1346.4 | 1368.2 | 1385.0 | 1401.8 | 1393.6 | 1385.4 | 1355.0 |
| 1267.0 | 65°   | 1245.9 | 1229.4 | 1245.9 | 1267.0 | 1288.2 | 1304.4 | 1320.5 | 1312.2 | 1303.7 | 1277.0 |
| 1178.4 | 67.5° | 1158.7 | 1143.8 | 1158.7 | 1178.4 | 1198.1 | 1212.9 | 1227.8 | 1219.6 | 1211.4 | 1188.3 |
| 1085.6 | 70°   | 1066.7 | 1049.6 | 1066.7 | 1085.6 | 1104.4 | 1116.5 | 1128.6 | 1120.7 | 1112.7 | 1091.9 |
| 981.3  | 72.5° | 963.5  | 946.9  | 963.5  | 981.3  | 999.3  | 1009.4 | 1019.4 | 1010.0 | 1000.6 | 980.2  |
| 864.4  | 75°   | 849.3  | 833.5  | 849.3  | 864.4  | 879.5  | 884.4  | 889.3  | 879.5  | 869.6  | 851.0  |
| 734.0  | 77.5° | 718.8  | 706.2  | 718.8  | 734.0  | 749.2  | 756.2  | 763.1  | 753.9  | 744.7  | 725.2  |
| 594.2  | 80°   | 573.7  | 549.9  | 573.7  | 594.2  | 614.7  | 617.6  | 620.6  | 608.4  | 596.2  | 581.4  |
| 443.4  | 82.5° | 426.0  | 410.9  | 426.0  | 443.4  | 460.6  | 462.0  | 463.3  | 442.5  | 421.8  | 390.1  |
| 276.5  | 85°   | 263.0  | 249.3  | 263.0  | 276.5  | 290.0  | 292.1  | 294.2  | 268.6  | 242.9  | 213.1  |
| 115.3  | 87.5° | 108.3  | 101.6  | 108.3  | 115.3  | 122.2  | 125.0  | 127.5  | 117.2  | 106.8  | 94.3   |
| 0.0    | 90°   | 0.0    | 0.0    | 0.0    | 0.0    | 0.0    | 0.0    | 0.0    | 0.0    | 0.0    | 0.0    |

REPORT NUMBER: P947402  
CATALOG NUMBER: GLAN-SB2D-735-U-SLL

**CANDELA DISTRIBUTION (continued):**

| 270°   |       | 275°   | 280°   | 285°   | 290°   | 295°   | 300°   | 305°   | 310°   | 315°   | 320°   |
|--------|-------|--------|--------|--------|--------|--------|--------|--------|--------|--------|--------|
| 2788.3 | 0°    | 2788.3 | 2788.3 | 2788.3 | 2788.3 | 2788.3 | 2788.3 | 2788.3 | 2788.3 | 2788.3 | 2788.3 |
| 2616.5 | 2.5°  | 2632.7 | 2649.0 | 2665.1 | 2681.3 | 2699.7 | 2718.2 | 2738.6 | 2759.2 | 2784.5 | 2807.3 |
| 2482.8 | 5°    | 2508.9 | 2534.9 | 2563.6 | 2592.2 | 2624.7 | 2657.2 | 2696.0 | 2734.8 | 2779.2 | 2824.1 |
| 2401.5 | 7.5°  | 2433.3 | 2465.1 | 2501.3 | 2537.4 | 2580.2 | 2623.0 | 2674.4 | 2726.0 | 2783.4 | 2844.8 |
| 2386.5 | 10°   | 2422.3 | 2458.2 | 2497.1 | 2536.0 | 2578.8 | 2621.6 | 2675.9 | 2730.3 | 2792.0 | 2867.7 |
| 2455.0 | 12.5° | 2492.0 | 2529.1 | 2559.5 | 2590.1 | 2618.4 | 2646.8 | 2691.1 | 2735.6 | 2793.1 | 2872.6 |
| 2597.8 | 15°   | 2630.0 | 2662.2 | 2670.1 | 2678.1 | 2674.2 | 2670.4 | 2691.5 | 2712.8 | 2758.8 | 2846.9 |
| 2749.7 | 17.5° | 2775.6 | 2801.6 | 2776.9 | 2752.1 | 2705.4 | 2658.8 | 2651.1 | 2643.3 | 2671.6 | 2775.2 |
| 2844.4 | 20°   | 2856.5 | 2868.5 | 2816.6 | 2764.7 | 2683.6 | 2602.6 | 2566.2 | 2529.9 | 2537.4 | 2657.9 |
| 2843.4 | 22.5° | 2836.2 | 2828.9 | 2761.4 | 2693.9 | 2601.2 | 2508.8 | 2455.0 | 2401.2 | 2386.5 | 2523.8 |
| 2749.2 | 25°   | 2724.5 | 2699.7 | 2633.2 | 2566.8 | 2483.5 | 2400.4 | 2338.4 | 2276.3 | 2236.7 | 2377.4 |
| 2585.5 | 27.5° | 2557.8 | 2530.2 | 2476.9 | 2423.6 | 2355.4 | 2287.0 | 2227.1 | 2167.2 | 2119.0 | 2247.1 |
| 2413.2 | 30°   | 2390.8 | 2368.3 | 2324.0 | 2279.8 | 2223.1 | 2166.4 | 2118.7 | 2071.2 | 2033.4 | 2140.9 |
| 2268.8 | 32.5° | 2243.8 | 2218.8 | 2176.4 | 2134.0 | 2088.6 | 2043.4 | 2015.2 | 1987.1 | 1970.3 | 2057.0 |
| 2136.1 | 35°   | 2106.2 | 2076.2 | 2034.2 | 1992.2 | 1957.8 | 1923.2 | 1915.4 | 1907.7 | 1914.7 | 1986.9 |
| 2014.7 | 37.5° | 1977.7 | 1940.7 | 1898.7 | 1856.9 | 1832.2 | 1807.3 | 1815.9 | 1824.5 | 1849.9 | 1913.1 |
| 1896.5 | 40°   | 1853.8 | 1811.2 | 1770.7 | 1730.3 | 1712.4 | 1694.6 | 1713.9 | 1733.3 | 1772.4 | 1829.6 |
| 1783.1 | 42.5° | 1737.0 | 1691.0 | 1652.6 | 1614.3 | 1599.7 | 1585.1 | 1610.8 | 1636.5 | 1685.7 | 1738.4 |
| 1683.0 | 45°   | 1635.3 | 1587.6 | 1551.2 | 1514.8 | 1502.4 | 1490.2 | 1515.1 | 1540.2 | 1587.8 | 1641.3 |
| 1600.6 | 47.5° | 1553.6 | 1506.5 | 1471.0 | 1435.3 | 1423.9 | 1412.3 | 1433.3 | 1454.3 | 1495.2 | 1564.3 |
| 1528.9 | 50°   | 1486.8 | 1444.6 | 1411.1 | 1377.5 | 1359.5 | 1341.5 | 1360.0 | 1378.6 | 1426.2 | 1517.0 |
| 1479.7 | 52.5° | 1440.4 | 1401.1 | 1370.4 | 1339.6 | 1312.6 | 1285.5 | 1303.8 | 1322.2 | 1388.8 | 1493.1 |
| 1446.0 | 55°   | 1411.7 | 1377.2 | 1344.1 | 1310.9 | 1272.6 | 1234.2 | 1263.2 | 1292.3 | 1392.5 | 1489.6 |
| 1418.2 | 57.5° | 1384.1 | 1350.0 | 1311.1 | 1272.2 | 1230.9 | 1189.6 | 1231.9 | 1274.3 | 1396.3 | 1481.9 |
| 1378.6 | 60°   | 1344.0 | 1309.4 | 1264.7 | 1219.9 | 1183.8 | 1147.5 | 1202.5 | 1257.4 | 1384.5 | 1441.0 |
| 1324.6 | 62.5° | 1287.7 | 1250.8 | 1198.5 | 1146.4 | 1123.4 | 1100.4 | 1169.0 | 1237.7 | 1355.6 | 1362.6 |
| 1250.2 | 65°   | 1214.9 | 1179.6 | 1123.7 | 1067.8 | 1059.0 | 1050.1 | 1123.2 | 1196.2 | 1286.1 | 1285.2 |
| 1165.2 | 67.5° | 1131.8 | 1098.3 | 1046.6 | 995.0  | 997.8  | 1000.6 | 1061.4 | 1122.2 | 1172.7 | 1175.0 |
| 1071.0 | 70°   | 1042.1 | 1013.2 | 967.9  | 922.5  | 932.1  | 941.8  | 985.0  | 1028.2 | 1044.8 | 1044.8 |
| 959.7  | 72.5° | 933.6  | 907.5  | 871.9  | 836.2  | 850.2  | 864.3  | 893.9  | 923.6  | 923.4  | 912.9  |
| 832.4  | 75°   | 808.8  | 785.1  | 758.6  | 732.1  | 745.6  | 759.1  | 782.0  | 804.8  | 808.9  | 760.5  |
| 705.6  | 77.5° | 685.3  | 665.0  | 643.5  | 621.8  | 635.5  | 649.2  | 667.5  | 685.8  | 688.0  | 608.3  |
| 566.5  | 80°   | 549.4  | 532.3  | 514.4  | 496.5  | 508.0  | 519.5  | 534.9  | 550.2  | 550.5  | 455.3  |
| 358.4  | 82.5° | 364.4  | 370.4  | 371.9  | 373.4  | 381.5  | 389.7  | 397.2  | 404.7  | 400.2  | 318.8  |
| 183.5  | 85°   | 200.1  | 216.7  | 224.5  | 232.2  | 241.3  | 250.4  | 258.4  | 266.4  | 260.5  | 200.1  |
| 81.9   | 87.5° | 94.6   | 107.2  | 107.5  | 107.8  | 109.6  | 111.3  | 114.5  | 117.7  | 110.2  | 85.1   |
| 0.0    | 90°   | 0.0    | 0.0    | 0.0    | 0.0    | 0.0    | 0.0    | 0.0    | 0.0    | 0.0    | 0.0    |

REPORT NUMBER: P947402

CATALOG NUMBER: GLAN-SB2D-735-U-SLL

**CANDELA DISTRIBUTION (continued):**

| 325°   |       | 330°   | 335°   | 340°   | 345°   | 350°   | 355°   | 360°    |
|--------|-------|--------|--------|--------|--------|--------|--------|---------|
| 2788.3 | 0°    | 2788.3 | 2788.3 | 2788.3 | 2788.3 | 2788.3 | 2788.3 | 2788.3  |
| 2830.8 | 2.5°  | 2854.4 | 2879.0 | 2903.6 | 2928.0 | 2952.5 | 2975.5 | 2998.5  |
| 2871.7 | 5°    | 2919.3 | 2970.3 | 3021.3 | 3071.9 | 3122.6 | 3173.4 | 3224.3  |
| 2911.2 | 7.5°  | 2977.6 | 3053.1 | 3128.5 | 3206.0 | 3283.4 | 3367.2 | 3451.1  |
| 2946.4 | 10°   | 3024.9 | 3116.6 | 3208.2 | 3310.5 | 3412.9 | 3518.9 | 3625.0  |
| 2961.5 | 12.5° | 3050.4 | 3158.5 | 3266.5 | 3382.5 | 3498.5 | 3614.9 | 3731.4  |
| 2949.8 | 15°   | 3052.8 | 3177.2 | 3301.6 | 3427.4 | 3553.3 | 3674.7 | 3796.1  |
| 2899.0 | 17.5° | 3022.8 | 3167.2 | 3311.7 | 3448.9 | 3586.2 | 3709.4 | 3832.5  |
| 2811.4 | 20°   | 2964.8 | 3139.8 | 3314.9 | 3465.7 | 3616.6 | 3744.7 | 3872.6  |
| 2708.6 | 22.5° | 2893.3 | 3106.2 | 3319.2 | 3488.4 | 3657.6 | 3788.4 | 3919.2  |
| 2593.7 | 25°   | 2810.2 | 3073.1 | 3336.1 | 3529.5 | 3722.9 | 3850.9 | 3979.1  |
| 2488.8 | 27.5° | 2730.5 | 3050.9 | 3371.4 | 3593.7 | 3815.9 | 3938.2 | 4060.4  |
| 2401.1 | 30°   | 2661.2 | 3040.6 | 3419.7 | 3676.8 | 3934.0 | 4052.0 | 4170.1  |
| 2325.4 | 32.5° | 2593.7 | 3027.7 | 3461.5 | 3763.6 | 4065.8 | 4182.6 | 4299.6  |
| 2251.0 | 35°   | 2515.2 | 3003.5 | 3492.1 | 3862.5 | 4232.9 | 4344.9 | 4456.8  |
| 2163.5 | 37.5° | 2414.0 | 2962.1 | 3510.3 | 3973.2 | 4436.2 | 4578.9 | 4721.6  |
| 2059.1 | 40°   | 2288.6 | 2905.1 | 3521.7 | 4113.8 | 4705.8 | 4913.8 | 5121.8  |
| 1943.9 | 42.5° | 2149.3 | 2846.3 | 3543.4 | 4297.7 | 5052.0 | 5352.3 | 5652.5  |
| 1821.5 | 45°   | 2001.6 | 2791.6 | 3581.6 | 4539.8 | 5497.9 | 5902.9 | 6307.8  |
| 1724.6 | 47.5° | 1885.0 | 2746.4 | 3607.8 | 4797.6 | 5987.4 | 6557.4 | 7127.4  |
| 1660.3 | 50°   | 1803.7 | 2697.2 | 3590.7 | 5036.8 | 6483.0 | 7342.4 | 8201.6  |
| 1618.0 | 52.5° | 1742.9 | 2614.1 | 3485.3 | 5192.2 | 6899.0 | 8166.8 | 9434.7  |
| 1587.3 | 55°   | 1684.9 | 2476.3 | 3267.6 | 5158.0 | 7048.2 | 8897.8 | 10747.5 |
| 1550.9 | 57.5° | 1619.9 | 2282.0 | 2943.9 | 4917.0 | 6890.2 | 9415.9 | 11941.6 |
| 1495.2 | 60°   | 1549.5 | 2029.7 | 2509.9 | 4468.6 | 6427.3 | 9545.4 | 12663.3 |
| 1398.5 | 62.5° | 1434.6 | 1727.7 | 2020.9 | 3862.3 | 5703.6 | 9000.2 | 12296.8 |
| 1302.2 | 65°   | 1319.2 | 1456.1 | 1592.9 | 3243.6 | 4894.4 | 8228.9 | 11563.4 |
| 1165.6 | 67.5° | 1156.1 | 1195.0 | 1233.9 | 2637.6 | 4041.4 | 7311.0 | 10580.6 |
| 1000.8 | 70°   | 956.7  | 945.7  | 934.6  | 2076.8 | 3218.9 | 6309.4 | 9400.0  |
| 850.5  | 72.5° | 788.0  | 754.4  | 720.9  | 1587.7 | 2454.4 | 5223.7 | 7993.0  |
| 690.5  | 75°   | 620.6  | 590.2  | 559.8  | 1152.3 | 1744.9 | 3979.0 | 6213.1  |
| 540.3  | 77.5° | 472.4  | 451.6  | 431.0  | 780.8  | 1130.7 | 2784.9 | 4439.2  |
| 397.8  | 80°   | 340.2  | 331.7  | 323.1  | 503.1  | 683.2  | 1794.3 | 2905.4  |
| 276.5  | 82.5° | 234.1  | 232.4  | 230.9  | 309.4  | 388.2  | 1038.5 | 1688.9  |
| 169.1  | 85°   | 138.0  | 138.9  | 139.6  | 165.4  | 191.3  | 467.1  | 743.1   |
| 72.3   | 87.5° | 59.7   | 60.5   | 61.2   | 68.6   | 76.0   | 153.0  | 230.0   |
| 0.0    | 90°   | 0.0    | 0.0    | 0.0    | 0.0    | 0.0    | 0.0    | 0.0     |

(END OF REPORT)