

Scaled data based on original data using  
LM-79-08 Approved Method: Electrical and Photometric Measurements of Solid-  
State Lighting Products

Test Report Prepared for  
Cooper Lighting Solutions  
(formerly Eaton)

Brand: STREETWORKS

Report Number: P947425

Luminaire Tested: **GLAN-SB2D-740-U-SLR**

Issue Date: 1/21/2025

### Test Information

Test Method: LM-79-08  
Report Number: P947425  
TEST IS SCALED FROM IESNA LM-79-08 TEST DATA (G2-2411-289-8)  
Test Lab: INNOVATION CENTER  
Issue Date: 1/21/2025  
Manufacturer: COOPER LIGHTING SOLUTIONS (FORMERLY EATON)  
Product Line: STREETWORKS  
Catalog Number: GLAN-SB2D-740-U-SLR  
Description: GALLEON AREA AND ROADWAY HIGH DENSITY LED LUMINAIRE  
(2) 70 CRI, 4000K, 900mA LIGHTSQUARES WITH 26 LEDS EACH AND SPILL LIGHT  
ELIMINATOR RIGHT OPTICS  
Light Source: -  
Ballast/Driver: -

### Summary

Lumens per Lamp: N/A  
Luminaire Lumens: 21453 lumens  
Efficiency: N/A  
Efficacy: 145.3 lumens/watt  
Luminous Opening: Rectangular (W 0.5' x L: 1' x H: 0')  
IES Classification: Type IV - Short  
BUG Rating: B3 - U0 - G4

Input Watts (W): 147.6  
Input Voltage (V): NR  
Input Current (Ain): NR  
Voltage Rise (V): NR  
Power Factor: NR  
Total Harmonic Distortion (THDi): NR  
Frequency (hertz): 60  
Stabilization Time: NR  
Operation Time: NR  
Ambient Temperature (°C): NR  
Test Distance: 24 FT




REPORT NUMBER: P947425

CATALOG NUMBER: GLAN-SB2D-740-U-SLR

## Iso-Footcandle Lines of Horizontal Illumination


× Max cd  
- - - 1/2 Max cd



Based on 25 foot mounting height. Maximum calculated value = 5.8 fc  
Type IV - Short - N/A

REPORT NUMBER: P947425  
CATALOG NUMBER: GLAN-SB2D-740-U-SLR

Luminous Intensity Polar Plot



REPORT NUMBER: P947425

CATALOG NUMBER: GLAN-SB2D-740-U-SLR

**FLUX DISTRIBUTION:**

|                    |           | Downward | Upward | Total   |
|--------------------|-----------|----------|--------|---------|
| <b>House Side</b>  | Lumens    | 5452.3   | 0.0    | 5452.3  |
|                    | % Fixture | 25.4     | 0.0    | 25.4    |
| <b>Street Side</b> | Lumens    | 16000.7  | 0.0    | 16000.7 |
|                    | % Fixture | 74.6     | 0.0    | 74.6    |
| <b>Total</b>       | Lumens    | 21453.0  | 0.0    | 21453.0 |
|                    | % Fixture | 100.0    | 0.0    | 100.0   |

**ZONAL LUMENS:**

| Zone      | Lumens  | % Fixture |
|-----------|---------|-----------|
| 0°-10°    | 292.6   | 1.4       |
| 10°-20°   | 918.6   | 4.3       |
| 20°-30°   | 1419.0  | 6.6       |
| 30°-40°   | 1798.2  | 8.4       |
| 40°-50°   | 2712.2  | 12.6      |
| 50°-60°   | 4381.9  | 20.4      |
| 60°-70°   | 5462.7  | 25.5      |
| 70°-80°   | 3582.2  | 16.7      |
| 80°-90°   | 885.6   | 4.1       |
| 90°-100°  | 0.0     | 0.0       |
| 100°-110° | 0.0     | 0.0       |
| 110°-120° | 0.0     | 0.0       |
| 120°-130° | 0.0     | 0.0       |
| 130°-140° | 0.0     | 0.0       |
| 140°-150° | 0.0     | 0.0       |
| 150°-160° | 0.0     | 0.0       |
| 160°-170° | 0.0     | 0.0       |
| 170°-180° | 0.0     | 0.0       |
| 0°-90°    | 21453.0 | 100.0     |
| 0°-180°   | 21453.0 | 100.0     |

**Coefficient of Utilization**



REPORT NUMBER: P947425


CATALOG NUMBER: GLAN-SB2D-740-U-SLR

**LUMINAIRE CLASSIFICATION SYSTEM LUMEN TABLE AND BUG RATING:**

| Zone |             | Lumens | % Fixture | Zone Rating/Lumen Limit |      |          |
|------|-------------|--------|-----------|-------------------------|------|----------|
|      |             |        |           | B                       | U    | G        |
| FL   | (0°-30°)    | 1443.0 | 6.7       |                         |      |          |
| FM   | (30°-60°)   | 6257.4 | 29.2      |                         |      |          |
| FH   | (60°-80°)   | 7570.9 | 35.3      |                         |      | G4/12000 |
| FVH  | (80°-90°)   | 729.5  | 3.4       |                         |      | G4/750   |
| BL   | (0°-30°)    | 1187.3 | 5.5       | B3/2500                 |      |          |
| BM   | (30°-60°)   | 2634.9 | 12.3      | B3/5000                 |      |          |
| BH   | (60°-80°)   | 1474.0 | 6.9       | B3/2500                 |      | G3/2500  |
| BVH  | (80°-90°)   | 156.1  | 0.7       |                         |      | G2/225   |
| UL   | (90°-100°)  | 0.0    | 0.0       |                         | U0/0 |          |
| UH   | (100°-180°) | 0.0    | 0.0       |                         | U0/0 |          |

**BUG Rating: B3-U0-G4**

Type IV Short



REPORT NUMBER: P947425

CATALOG NUMBER: GLAN-SB2D-740-U-SLR

**CANDELA DISTRIBUTION (FULL):**

|       | 0°      | 5°      | 10°    | 15°    | 20°    | 25°    | 30°    | 35°    | 40°    | 45°    |
|-------|---------|---------|--------|--------|--------|--------|--------|--------|--------|--------|
| 0°    | 2950.0  | 2950.0  | 2950.0 | 2950.0 | 2950.0 | 2950.0 | 2950.0 | 2950.0 | 2950.0 | 2950.0 |
| 2.5°  | 3172.4  | 3148.1  | 3123.7 | 3097.8 | 3072.0 | 3046.0 | 3019.9 | 2995.0 | 2970.1 | 2946.0 |
| 5°    | 3411.3  | 3357.5  | 3303.7 | 3250.1 | 3196.5 | 3142.5 | 3088.6 | 3038.3 | 2987.9 | 2940.4 |
| 7.5°  | 3651.2  | 3562.5  | 3473.9 | 3391.9 | 3309.9 | 3230.1 | 3150.3 | 3080.0 | 3009.7 | 2944.9 |
| 10°   | 3835.2  | 3723.0  | 3610.8 | 3502.5 | 3394.3 | 3297.4 | 3200.4 | 3117.3 | 3034.0 | 2953.9 |
| 12.5° | 3947.8  | 3824.5  | 3701.4 | 3578.7 | 3456.0 | 3341.6 | 3227.3 | 3133.2 | 3039.2 | 2955.1 |
| 15°   | 4016.3  | 3887.8  | 3759.3 | 3626.2 | 3493.1 | 3361.5 | 3229.8 | 3120.9 | 3012.0 | 2918.8 |
| 17.5° | 4054.8  | 3924.5  | 3794.2 | 3649.0 | 3503.7 | 3350.9 | 3198.1 | 3067.1 | 2936.2 | 2826.6 |
| 20°   | 4097.2  | 3961.9  | 3826.4 | 3666.7 | 3507.1 | 3321.9 | 3136.8 | 2974.4 | 2812.1 | 2684.5 |
| 22.5° | 4146.5  | 4008.2  | 3869.7 | 3690.7 | 3511.7 | 3286.4 | 3061.1 | 2865.6 | 2670.1 | 2524.9 |
| 25°   | 4209.9  | 4074.3  | 3938.8 | 3734.2 | 3529.6 | 3251.3 | 2973.2 | 2744.2 | 2515.3 | 2366.4 |
| 27.5° | 4295.9  | 4166.6  | 4037.3 | 3802.1 | 3566.9 | 3227.9 | 2888.8 | 2633.1 | 2377.4 | 2241.9 |
| 30°   | 4411.9  | 4287.0  | 4162.1 | 3890.1 | 3618.1 | 3216.9 | 2815.5 | 2540.3 | 2265.1 | 2151.4 |
| 32.5° | 4548.9  | 4425.2  | 4301.6 | 3981.9 | 3662.2 | 3203.3 | 2744.2 | 2460.3 | 2176.3 | 2084.6 |
| 35°   | 4715.3  | 4596.9  | 4478.4 | 4086.5 | 3694.6 | 3177.7 | 2661.1 | 2381.6 | 2102.1 | 2025.7 |
| 37.5° | 4995.5  | 4844.5  | 4693.5 | 4203.7 | 3713.8 | 3133.9 | 2554.0 | 2289.0 | 2024.0 | 1957.2 |
| 40°   | 5418.8  | 5198.8  | 4978.7 | 4352.4 | 3726.0 | 3073.6 | 2421.3 | 2178.5 | 1935.7 | 1875.1 |
| 42.5° | 5980.3  | 5662.7  | 5345.0 | 4547.0 | 3748.9 | 3011.3 | 2273.9 | 2056.6 | 1839.3 | 1783.5 |
| 45°   | 6673.7  | 6245.2  | 5816.7 | 4803.0 | 3789.3 | 2953.5 | 2117.7 | 1927.1 | 1736.5 | 1679.9 |
| 47.5° | 7540.8  | 6937.8  | 6334.6 | 5075.9 | 3817.1 | 2905.7 | 1994.3 | 1824.7 | 1655.0 | 1582.0 |
| 50°   | 8677.3  | 7768.2  | 6859.0 | 5329.0 | 3799.0 | 2853.6 | 1908.3 | 1756.6 | 1604.9 | 1508.9 |
| 52.5° | 9981.9  | 8640.5  | 7299.1 | 5493.3 | 3687.5 | 2765.7 | 1844.0 | 1711.8 | 1579.7 | 1469.3 |
| 55°   | 11370.9 | 9413.9  | 7457.0 | 5457.1 | 3457.1 | 2619.9 | 1782.7 | 1679.3 | 1576.0 | 1473.3 |
| 57.5° | 12634.2 | 9962.0  | 7289.8 | 5202.2 | 3114.7 | 2414.3 | 1713.8 | 1640.8 | 1567.8 | 1477.3 |
| 60°   | 13397.7 | 10099.0 | 6800.1 | 4727.8 | 2655.4 | 2147.4 | 1639.4 | 1582.0 | 1524.6 | 1464.8 |
| 62.5° | 13010.0 | 9522.2  | 6034.4 | 4086.3 | 2138.1 | 1827.9 | 1517.8 | 1479.6 | 1441.6 | 1434.2 |
| 65°   | 12234.0 | 8706.2  | 5178.3 | 3431.7 | 1685.3 | 1540.5 | 1395.7 | 1377.7 | 1359.7 | 1360.7 |
| 67.5° | 11194.3 | 7735.0  | 4275.8 | 2790.6 | 1305.4 | 1264.3 | 1223.1 | 1233.2 | 1243.2 | 1240.7 |
| 70°   | 9945.1  | 6675.4  | 3405.6 | 2197.2 | 988.8  | 1000.6 | 1012.2 | 1058.9 | 1105.4 | 1105.4 |
| 72.5° | 8456.5  | 5526.6  | 2596.8 | 1679.8 | 762.7  | 798.2  | 833.7  | 899.8  | 965.8  | 976.9  |
| 75°   | 6573.5  | 4209.8  | 1846.1 | 1219.2 | 592.3  | 624.4  | 656.6  | 730.6  | 804.6  | 855.8  |
| 77.5° | 4696.6  | 2946.5  | 1196.3 | 826.1  | 456.0  | 477.8  | 499.8  | 571.7  | 643.5  | 727.9  |
| 80°   | 3073.9  | 1898.4  | 722.8  | 532.3  | 341.9  | 350.9  | 360.0  | 420.9  | 481.7  | 582.4  |
| 82.5° | 1786.9  | 1098.7  | 410.7  | 327.4  | 244.3  | 245.9  | 247.7  | 292.5  | 337.3  | 423.4  |
| 85°   | 786.2   | 494.2   | 202.4  | 175.0  | 147.7  | 146.9  | 146.0  | 178.9  | 211.7  | 275.6  |
| 87.5° | 243.4   | 161.9   | 80.4   | 72.6   | 64.7   | 64.0   | 63.2   | 76.5   | 90.0   | 116.6  |
| 90°   | 0.0     | 0.0     | 0.0    | 0.0    | 0.0    | 0.0    | 0.0    | 0.0    | 0.0    | 0.0    |

REPORT NUMBER: P947425

CATALOG NUMBER: GLAN-SB2D-740-U-SLR

**CANDELA DISTRIBUTION (continued):**

| 50°    |       | 55°    | 60°    | 65°    | 70°    | 75°    | 80°    | 85°    | 90°    | 95°    | 100°   |
|--------|-------|--------|--------|--------|--------|--------|--------|--------|--------|--------|--------|
| 2950.0 | 0°    | 2950.0 | 2950.0 | 2950.0 | 2950.0 | 2950.0 | 2950.0 | 2950.0 | 2950.0 | 2950.0 | 2950.0 |
| 2919.2 | 2.5°  | 2897.4 | 2875.8 | 2856.2 | 2836.8 | 2819.7 | 2802.6 | 2785.4 | 2768.3 | 2755.0 | 2741.7 |
| 2893.4 | 5°    | 2852.4 | 2811.3 | 2776.9 | 2742.6 | 2712.3 | 2681.9 | 2654.4 | 2626.8 | 2605.6 | 2584.3 |
| 2884.1 | 7.5°  | 2829.5 | 2775.1 | 2729.8 | 2684.5 | 2646.4 | 2608.1 | 2574.4 | 2540.8 | 2515.5 | 2490.4 |
| 2888.6 | 10°   | 2831.1 | 2773.6 | 2728.3 | 2683.0 | 2642.0 | 2600.8 | 2562.8 | 2524.9 | 2494.8 | 2464.6 |
| 2894.3 | 12.5° | 2847.2 | 2800.3 | 2770.2 | 2740.3 | 2708.0 | 2675.8 | 2636.5 | 2597.4 | 2558.9 | 2520.4 |
| 2870.2 | 15°   | 2847.6 | 2825.2 | 2829.3 | 2833.4 | 2825.0 | 2816.6 | 2782.6 | 2748.5 | 2693.7 | 2638.9 |
| 2796.6 | 17.5° | 2804.9 | 2813.0 | 2862.4 | 2911.7 | 2938.0 | 2964.1 | 2936.6 | 2909.2 | 2836.7 | 2764.1 |
| 2676.6 | 20°   | 2715.1 | 2753.6 | 2839.3 | 2925.1 | 2980.0 | 3034.9 | 3022.2 | 3009.4 | 2926.4 | 2843.6 |
| 2540.4 | 22.5° | 2597.4 | 2654.3 | 2752.1 | 2850.1 | 2921.6 | 2993.0 | 3000.7 | 3008.3 | 2929.0 | 2849.8 |
| 2408.3 | 25°   | 2474.0 | 2539.6 | 2627.6 | 2715.6 | 2785.9 | 2856.2 | 2882.5 | 2908.7 | 2843.7 | 2778.8 |
| 2292.9 | 27.5° | 2356.2 | 2419.6 | 2492.0 | 2564.2 | 2620.6 | 2676.9 | 2706.1 | 2735.5 | 2689.2 | 2643.0 |
| 2191.3 | 30°   | 2241.6 | 2292.1 | 2352.1 | 2412.0 | 2458.8 | 2505.7 | 2529.4 | 2553.2 | 2518.0 | 2482.7 |
| 2102.3 | 32.5° | 2132.1 | 2161.9 | 2209.8 | 2257.8 | 2302.6 | 2347.5 | 2373.9 | 2400.4 | 2368.0 | 2335.5 |
| 2018.3 | 35°   | 2026.5 | 2034.8 | 2071.3 | 2107.8 | 2152.1 | 2196.6 | 2228.3 | 2260.0 | 2236.9 | 2214.0 |
| 1930.3 | 37.5° | 1921.2 | 1912.2 | 1938.4 | 1964.6 | 2008.8 | 2053.2 | 2092.4 | 2131.5 | 2120.9 | 2110.3 |
| 1833.8 | 40°   | 1813.3 | 1792.8 | 1811.8 | 1830.7 | 1873.4 | 1916.2 | 1961.3 | 2006.5 | 2009.1 | 2011.6 |
| 1731.4 | 42.5° | 1704.2 | 1677.0 | 1692.4 | 1708.0 | 1748.5 | 1789.1 | 1837.8 | 1886.5 | 1899.5 | 1912.5 |
| 1629.5 | 45°   | 1603.0 | 1576.6 | 1589.5 | 1602.7 | 1641.2 | 1679.7 | 1730.1 | 1780.6 | 1799.3 | 1818.0 |
| 1538.6 | 47.5° | 1516.4 | 1494.2 | 1506.5 | 1518.6 | 1556.3 | 1593.8 | 1643.7 | 1693.5 | 1715.0 | 1736.5 |
| 1458.6 | 50°   | 1438.9 | 1419.3 | 1438.3 | 1457.4 | 1493.0 | 1528.4 | 1573.0 | 1617.6 | 1645.2 | 1672.9 |
| 1398.9 | 52.5° | 1379.4 | 1360.1 | 1388.7 | 1417.3 | 1449.9 | 1482.3 | 1523.9 | 1565.5 | 1598.3 | 1631.0 |
| 1367.2 | 55°   | 1336.4 | 1305.8 | 1346.4 | 1386.9 | 1422.0 | 1457.1 | 1493.6 | 1529.9 | 1564.5 | 1599.3 |
| 1348.2 | 57.5° | 1303.4 | 1258.5 | 1302.2 | 1345.9 | 1387.1 | 1428.3 | 1464.3 | 1500.5 | 1535.4 | 1570.3 |
| 1330.3 | 60°   | 1272.2 | 1214.1 | 1252.4 | 1290.7 | 1338.0 | 1385.3 | 1421.9 | 1458.6 | 1493.7 | 1528.8 |
| 1309.5 | 62.5° | 1236.8 | 1164.3 | 1188.6 | 1212.9 | 1268.1 | 1323.3 | 1362.4 | 1401.4 | 1433.6 | 1465.7 |
| 1265.6 | 65°   | 1188.4 | 1111.1 | 1120.4 | 1129.7 | 1188.8 | 1248.0 | 1285.4 | 1322.7 | 1351.0 | 1379.3 |
| 1187.2 | 67.5° | 1122.9 | 1058.6 | 1055.7 | 1052.8 | 1107.3 | 1162.0 | 1197.4 | 1232.7 | 1257.2 | 1281.6 |
| 1087.8 | 70°   | 1042.1 | 996.4  | 986.2  | 976.0  | 1024.0 | 1072.0 | 1102.6 | 1133.1 | 1155.2 | 1177.3 |
| 977.1  | 72.5° | 945.8  | 914.4  | 899.5  | 884.7  | 922.5  | 960.2  | 987.8  | 1015.4 | 1037.0 | 1058.6 |
| 851.5  | 75°   | 827.4  | 803.1  | 788.9  | 774.5  | 802.6  | 830.7  | 855.7  | 880.7  | 900.4  | 920.1  |
| 725.6  | 77.5° | 706.3  | 686.9  | 672.4  | 657.9  | 680.8  | 703.5  | 725.0  | 746.5  | 767.3  | 787.9  |
| 582.1  | 80°   | 565.9  | 549.6  | 537.5  | 525.2  | 544.3  | 563.2  | 581.3  | 599.4  | 615.1  | 630.7  |
| 428.1  | 82.5° | 420.2  | 412.3  | 403.7  | 395.1  | 393.5  | 391.9  | 385.6  | 379.2  | 412.7  | 446.2  |
| 281.9  | 85°   | 273.4  | 264.9  | 255.3  | 245.6  | 237.5  | 229.2  | 211.7  | 194.1  | 225.5  | 257.0  |
| 124.5  | 87.5° | 121.1  | 117.7  | 115.9  | 114.1  | 113.8  | 113.4  | 100.1  | 86.6   | 99.7   | 113.0  |
| 0.0    | 90°   | 0.0    | 0.0    | 0.0    | 0.0    | 0.0    | 0.0    | 0.0    | 0.0    | 0.0    | 0.0    |

REPORT NUMBER: P947425

CATALOG NUMBER: GLAN-SB2D-740-U-SLR

**CANDELA DISTRIBUTION (continued):**

| 105°   |       | 110°   | 115°   | 120°   | 125°   | 130°   | 135°   | 140°   | 145°   | 150°   | 155°   |
|--------|-------|--------|--------|--------|--------|--------|--------|--------|--------|--------|--------|
| 2950.0 | 0°    | 2950.0 | 2950.0 | 2950.0 | 2950.0 | 2950.0 | 2950.0 | 2950.0 | 2950.0 | 2950.0 | 2950.0 |
| 2730.9 | 2.5°  | 2720.2 | 2711.8 | 2703.4 | 2695.7 | 2687.9 | 2678.3 | 2687.9 | 2695.7 | 2703.4 | 2711.8 |
| 2569.5 | 5°    | 2554.7 | 2544.2 | 2533.6 | 2525.6 | 2517.6 | 2509.6 | 2517.6 | 2525.6 | 2533.6 | 2544.2 |
| 2472.7 | 7.5°  | 2455.1 | 2443.0 | 2431.0 | 2423.7 | 2416.6 | 2411.1 | 2416.6 | 2423.7 | 2431.0 | 2443.0 |
| 2444.9 | 10°   | 2425.0 | 2413.5 | 2402.1 | 2396.0 | 2389.9 | 2387.4 | 2389.9 | 2396.0 | 2402.1 | 2413.5 |
| 2494.9 | 12.5° | 2469.4 | 2456.6 | 2444.0 | 2438.8 | 2433.6 | 2432.7 | 2433.6 | 2438.8 | 2444.0 | 2456.6 |
| 2600.2 | 15°   | 2561.5 | 2543.7 | 2526.0 | 2519.2 | 2512.5 | 2511.9 | 2512.5 | 2519.2 | 2526.0 | 2543.7 |
| 2707.0 | 17.5° | 2650.0 | 2623.7 | 2597.4 | 2588.8 | 2580.0 | 2578.7 | 2580.0 | 2588.8 | 2597.4 | 2623.7 |
| 2773.6 | 20°   | 2703.8 | 2670.1 | 2636.4 | 2625.7 | 2614.9 | 2611.5 | 2614.9 | 2625.7 | 2636.4 | 2670.1 |
| 2777.8 | 22.5° | 2705.7 | 2670.3 | 2634.7 | 2622.8 | 2610.9 | 2605.8 | 2610.9 | 2622.8 | 2634.7 | 2670.3 |
| 2714.7 | 25°   | 2650.9 | 2620.1 | 2589.4 | 2578.2 | 2567.1 | 2560.6 | 2567.1 | 2578.2 | 2589.4 | 2620.1 |
| 2593.3 | 27.5° | 2543.6 | 2523.0 | 2502.3 | 2497.2 | 2492.1 | 2490.4 | 2492.1 | 2497.2 | 2502.3 | 2523.0 |
| 2447.1 | 30°   | 2411.4 | 2400.8 | 2390.2 | 2390.2 | 2390.2 | 2391.9 | 2390.2 | 2390.2 | 2390.2 | 2400.8 |
| 2307.1 | 32.5° | 2278.7 | 2271.8 | 2264.9 | 2265.8 | 2266.8 | 2268.5 | 2266.8 | 2265.8 | 2264.9 | 2271.8 |
| 2187.7 | 35°   | 2161.5 | 2151.0 | 2140.6 | 2138.3 | 2136.1 | 2134.9 | 2136.1 | 2138.3 | 2140.6 | 2151.0 |
| 2086.1 | 37.5° | 2061.9 | 2042.8 | 2023.8 | 2013.7 | 2003.6 | 1998.0 | 2003.6 | 2013.7 | 2023.8 | 2042.8 |
| 1991.1 | 40°   | 1970.6 | 1942.7 | 1915.1 | 1896.3 | 1877.7 | 1866.7 | 1877.7 | 1896.3 | 1915.1 | 1942.7 |
| 1895.2 | 42.5° | 1878.0 | 1843.4 | 1808.9 | 1781.6 | 1754.4 | 1736.5 | 1754.4 | 1781.6 | 1808.9 | 1843.4 |
| 1802.4 | 45°   | 1786.9 | 1747.3 | 1708.0 | 1675.9 | 1643.9 | 1623.3 | 1643.9 | 1675.9 | 1708.0 | 1747.3 |
| 1725.6 | 47.5° | 1714.7 | 1679.7 | 1644.6 | 1614.9 | 1585.4 | 1565.5 | 1585.4 | 1614.9 | 1644.6 | 1679.7 |
| 1672.2 | 50°   | 1671.7 | 1643.7 | 1615.6 | 1588.2 | 1560.8 | 1541.8 | 1560.8 | 1588.2 | 1615.6 | 1643.7 |
| 1636.9 | 52.5° | 1642.7 | 1619.9 | 1597.0 | 1572.5 | 1548.0 | 1530.5 | 1548.0 | 1572.5 | 1597.0 | 1619.9 |
| 1607.4 | 55°   | 1615.6 | 1595.7 | 1575.7 | 1554.2 | 1532.7 | 1516.9 | 1532.7 | 1554.2 | 1575.7 | 1595.7 |
| 1578.6 | 57.5° | 1586.8 | 1566.7 | 1546.5 | 1525.2 | 1503.9 | 1487.4 | 1503.9 | 1525.2 | 1546.5 | 1566.7 |
| 1537.8 | 60°   | 1546.9 | 1527.2 | 1507.6 | 1485.6 | 1463.7 | 1446.7 | 1463.7 | 1485.6 | 1507.6 | 1527.2 |
| 1474.4 | 62.5° | 1483.1 | 1465.4 | 1447.6 | 1424.5 | 1401.4 | 1381.0 | 1401.4 | 1424.5 | 1447.6 | 1465.4 |
| 1388.3 | 65°   | 1397.1 | 1380.0 | 1362.9 | 1340.5 | 1318.2 | 1300.7 | 1318.2 | 1340.5 | 1362.9 | 1380.0 |
| 1290.4 | 67.5° | 1299.0 | 1283.2 | 1267.6 | 1246.8 | 1225.9 | 1210.1 | 1225.9 | 1246.8 | 1267.6 | 1283.2 |
| 1185.6 | 70°   | 1194.0 | 1181.2 | 1168.4 | 1148.5 | 1128.6 | 1110.5 | 1128.6 | 1148.5 | 1168.4 | 1181.2 |
| 1068.6 | 72.5° | 1078.6 | 1067.9 | 1057.3 | 1038.3 | 1019.4 | 1001.8 | 1019.4 | 1038.3 | 1057.3 | 1067.9 |
| 930.5  | 75°   | 940.9  | 935.7  | 930.5  | 914.5  | 898.6  | 881.8  | 898.6  | 914.5  | 930.5  | 935.7  |
| 797.6  | 77.5° | 807.3  | 800.1  | 792.6  | 776.5  | 760.5  | 747.1  | 760.5  | 776.5  | 792.6  | 800.1  |
| 643.7  | 80°   | 656.6  | 653.4  | 650.3  | 628.7  | 607.0  | 581.8  | 607.0  | 628.7  | 650.3  | 653.4  |
| 468.2  | 82.5° | 490.2  | 488.8  | 487.3  | 469.1  | 450.8  | 434.7  | 450.8  | 469.1  | 487.3  | 488.8  |
| 284.1  | 85°   | 311.3  | 309.0  | 306.8  | 292.5  | 278.2  | 263.8  | 278.2  | 292.5  | 306.8  | 309.0  |
| 124.0  | 87.5° | 134.9  | 132.2  | 129.3  | 122.0  | 114.6  | 107.5  | 114.6  | 122.0  | 129.3  | 132.2  |
| 0.0    | 90°   | 0.0    | 0.0    | 0.0    | 0.0    | 0.0    | 0.0    | 0.0    | 0.0    | 0.0    | 0.0    |

REPORT NUMBER: P947425

CATALOG NUMBER: GLAN-SB2D-740-U-SLR

**CANDELA DISTRIBUTION (continued):**

| 160°   |       | 165°   | 170°   | 175°   | 180°   | 185°   | 190°   | 195°   | 200°   | 205°   | 210°   |
|--------|-------|--------|--------|--------|--------|--------|--------|--------|--------|--------|--------|
| 2950.0 | 0°    | 2950.0 | 2950.0 | 2950.0 | 2950.0 | 2950.0 | 2950.0 | 2950.0 | 2950.0 | 2950.0 | 2950.0 |
| 2720.2 | 2.5°  | 2730.9 | 2741.7 | 2755.0 | 2768.3 | 2785.4 | 2802.6 | 2819.7 | 2836.8 | 2856.2 | 2875.8 |
| 2554.7 | 5°    | 2569.5 | 2584.3 | 2605.6 | 2626.8 | 2654.4 | 2681.9 | 2712.3 | 2742.6 | 2776.9 | 2811.3 |
| 2455.1 | 7.5°  | 2472.7 | 2490.4 | 2515.5 | 2540.8 | 2574.4 | 2608.1 | 2646.4 | 2684.5 | 2729.8 | 2775.1 |
| 2425.0 | 10°   | 2444.9 | 2464.6 | 2494.8 | 2524.9 | 2562.8 | 2600.8 | 2642.0 | 2683.0 | 2728.3 | 2773.6 |
| 2469.4 | 12.5° | 2494.9 | 2520.4 | 2558.9 | 2597.4 | 2636.5 | 2675.8 | 2708.0 | 2740.3 | 2770.2 | 2800.3 |
| 2561.5 | 15°   | 2600.2 | 2638.9 | 2693.7 | 2748.5 | 2782.6 | 2816.6 | 2825.0 | 2833.4 | 2829.3 | 2825.2 |
| 2650.0 | 17.5° | 2707.0 | 2764.1 | 2836.7 | 2909.2 | 2936.6 | 2964.1 | 2938.0 | 2911.7 | 2862.4 | 2813.0 |
| 2703.8 | 20°   | 2773.6 | 2843.6 | 2926.4 | 3009.4 | 3022.2 | 3034.9 | 2980.0 | 2925.1 | 2839.3 | 2753.6 |
| 2705.7 | 22.5° | 2777.8 | 2849.8 | 2929.0 | 3008.3 | 3000.7 | 2993.0 | 2921.6 | 2850.1 | 2752.1 | 2654.3 |
| 2650.9 | 25°   | 2714.7 | 2778.8 | 2843.7 | 2908.7 | 2882.5 | 2856.2 | 2785.9 | 2715.6 | 2627.6 | 2539.6 |
| 2543.6 | 27.5° | 2593.3 | 2643.0 | 2689.2 | 2735.5 | 2706.1 | 2676.9 | 2620.6 | 2564.2 | 2492.0 | 2419.6 |
| 2411.4 | 30°   | 2447.1 | 2482.7 | 2518.0 | 2553.2 | 2529.4 | 2505.7 | 2458.8 | 2412.0 | 2352.1 | 2292.1 |
| 2278.7 | 32.5° | 2307.1 | 2335.5 | 2368.0 | 2400.4 | 2373.9 | 2347.5 | 2302.6 | 2257.8 | 2209.8 | 2161.9 |
| 2161.5 | 35°   | 2187.7 | 2214.0 | 2236.9 | 2260.0 | 2228.3 | 2196.6 | 2152.1 | 2107.8 | 2071.3 | 2034.8 |
| 2061.9 | 37.5° | 2086.1 | 2110.3 | 2120.9 | 2131.5 | 2092.4 | 2053.2 | 2008.8 | 1964.6 | 1938.4 | 1912.2 |
| 1970.6 | 40°   | 1991.1 | 2011.6 | 2009.1 | 2006.5 | 1961.3 | 1916.2 | 1873.4 | 1830.7 | 1811.8 | 1792.8 |
| 1878.0 | 42.5° | 1895.2 | 1912.5 | 1899.5 | 1886.5 | 1837.8 | 1789.1 | 1748.5 | 1708.0 | 1692.4 | 1677.0 |
| 1786.9 | 45°   | 1802.4 | 1818.0 | 1799.3 | 1780.6 | 1730.1 | 1679.7 | 1641.2 | 1602.7 | 1589.5 | 1576.6 |
| 1714.7 | 47.5° | 1725.6 | 1736.5 | 1715.0 | 1693.5 | 1643.7 | 1593.8 | 1556.3 | 1518.6 | 1506.5 | 1494.2 |
| 1671.7 | 50°   | 1672.2 | 1672.9 | 1645.2 | 1617.6 | 1573.0 | 1528.4 | 1493.0 | 1457.4 | 1438.3 | 1419.3 |
| 1642.7 | 52.5° | 1636.9 | 1631.0 | 1598.3 | 1565.5 | 1523.9 | 1482.3 | 1449.9 | 1417.3 | 1388.7 | 1360.1 |
| 1615.6 | 55°   | 1607.4 | 1599.3 | 1564.5 | 1529.9 | 1493.6 | 1457.1 | 1422.0 | 1386.9 | 1346.4 | 1305.8 |
| 1586.8 | 57.5° | 1578.6 | 1570.3 | 1535.4 | 1500.5 | 1464.3 | 1428.3 | 1387.1 | 1345.9 | 1302.2 | 1258.5 |
| 1546.9 | 60°   | 1537.8 | 1528.8 | 1493.7 | 1458.6 | 1421.9 | 1385.3 | 1338.0 | 1290.7 | 1252.4 | 1214.1 |
| 1483.1 | 62.5° | 1474.4 | 1465.7 | 1433.6 | 1401.4 | 1362.4 | 1323.3 | 1268.1 | 1212.9 | 1188.6 | 1164.3 |
| 1397.1 | 65°   | 1388.3 | 1379.3 | 1351.0 | 1322.7 | 1285.4 | 1248.0 | 1188.8 | 1129.7 | 1120.4 | 1111.1 |
| 1299.0 | 67.5° | 1290.4 | 1281.6 | 1257.2 | 1232.7 | 1197.4 | 1162.0 | 1107.3 | 1052.8 | 1055.7 | 1058.6 |
| 1194.0 | 70°   | 1185.6 | 1177.3 | 1155.2 | 1133.1 | 1102.6 | 1072.0 | 1024.0 | 976.0  | 986.2  | 996.4  |
| 1078.6 | 72.5° | 1068.6 | 1058.6 | 1037.0 | 1015.4 | 987.8  | 960.2  | 922.5  | 884.7  | 899.5  | 914.4  |
| 940.9  | 75°   | 930.5  | 920.1  | 900.4  | 880.7  | 855.7  | 830.7  | 802.6  | 774.5  | 788.9  | 803.1  |
| 807.3  | 77.5° | 797.6  | 787.9  | 767.3  | 746.5  | 725.0  | 703.5  | 680.8  | 657.9  | 672.4  | 686.9  |
| 656.6  | 80°   | 643.7  | 630.7  | 615.1  | 599.4  | 581.3  | 563.2  | 544.3  | 525.2  | 537.5  | 549.6  |
| 490.2  | 82.5° | 468.2  | 446.2  | 412.7  | 379.2  | 385.6  | 391.9  | 393.5  | 395.1  | 403.7  | 412.3  |
| 311.3  | 85°   | 284.1  | 257.0  | 225.5  | 194.1  | 211.7  | 229.2  | 237.5  | 245.6  | 255.3  | 264.9  |
| 134.9  | 87.5° | 124.0  | 113.0  | 99.7   | 86.6   | 100.1  | 113.4  | 113.8  | 114.1  | 115.9  | 117.7  |
| 0.0    | 90°   | 0.0    | 0.0    | 0.0    | 0.0    | 0.0    | 0.0    | 0.0    | 0.0    | 0.0    | 0.0    |

REPORT NUMBER: P947425

CATALOG NUMBER: GLAN-SB2D-740-U-SLR

**CANDELA DISTRIBUTION (continued):**

| 215°   |       | 220°   | 225°   | 230°   | 235°   | 240°   | 245°   | 250°   | 255°   | 260°   | 265°    |
|--------|-------|--------|--------|--------|--------|--------|--------|--------|--------|--------|---------|
| 2950.0 | 0°    | 2950.0 | 2950.0 | 2950.0 | 2950.0 | 2950.0 | 2950.0 | 2950.0 | 2950.0 | 2950.0 | 2950.0  |
| 2897.4 | 2.5°  | 2919.2 | 2946.0 | 2970.1 | 2995.0 | 3019.9 | 3046.0 | 3072.0 | 3097.8 | 3123.7 | 3148.1  |
| 2852.4 | 5°    | 2893.4 | 2940.4 | 2987.9 | 3038.3 | 3088.6 | 3142.5 | 3196.5 | 3250.1 | 3303.7 | 3357.5  |
| 2829.5 | 7.5°  | 2884.1 | 2944.9 | 3009.7 | 3080.0 | 3150.3 | 3230.1 | 3309.9 | 3391.9 | 3473.9 | 3562.5  |
| 2831.1 | 10°   | 2888.6 | 2953.9 | 3034.0 | 3117.3 | 3200.4 | 3297.4 | 3394.3 | 3502.5 | 3610.8 | 3723.0  |
| 2847.2 | 12.5° | 2894.3 | 2955.1 | 3039.2 | 3133.2 | 3227.3 | 3341.6 | 3456.0 | 3578.7 | 3701.4 | 3824.5  |
| 2847.6 | 15°   | 2870.2 | 2918.8 | 3012.0 | 3120.9 | 3229.8 | 3361.5 | 3493.1 | 3626.2 | 3759.3 | 3887.8  |
| 2804.9 | 17.5° | 2796.6 | 2826.6 | 2936.2 | 3067.1 | 3198.1 | 3350.9 | 3503.7 | 3649.0 | 3794.2 | 3924.5  |
| 2715.1 | 20°   | 2676.6 | 2684.5 | 2812.1 | 2974.4 | 3136.8 | 3321.9 | 3507.1 | 3666.7 | 3826.4 | 3961.9  |
| 2597.4 | 22.5° | 2540.4 | 2524.9 | 2670.1 | 2865.6 | 3061.1 | 3286.4 | 3511.7 | 3690.7 | 3869.7 | 4008.2  |
| 2474.0 | 25°   | 2408.3 | 2366.4 | 2515.3 | 2744.2 | 2973.2 | 3251.3 | 3529.6 | 3734.2 | 3938.8 | 4074.3  |
| 2356.2 | 27.5° | 2292.9 | 2241.9 | 2377.4 | 2633.1 | 2888.8 | 3227.9 | 3566.9 | 3802.1 | 4037.3 | 4166.6  |
| 2241.6 | 30°   | 2191.3 | 2151.4 | 2265.1 | 2540.3 | 2815.5 | 3216.9 | 3618.1 | 3890.1 | 4162.1 | 4287.0  |
| 2132.1 | 32.5° | 2102.3 | 2084.6 | 2176.3 | 2460.3 | 2744.2 | 3203.3 | 3662.2 | 3981.9 | 4301.6 | 4425.2  |
| 2026.5 | 35°   | 2018.3 | 2025.7 | 2102.1 | 2381.6 | 2661.1 | 3177.7 | 3694.6 | 4086.5 | 4478.4 | 4596.9  |
| 1921.2 | 37.5° | 1930.3 | 1957.2 | 2024.0 | 2289.0 | 2554.0 | 3133.9 | 3713.8 | 4203.7 | 4693.5 | 4844.5  |
| 1813.3 | 40°   | 1833.8 | 1875.1 | 1935.7 | 2178.5 | 2421.3 | 3073.6 | 3726.0 | 4352.4 | 4978.7 | 5198.8  |
| 1704.2 | 42.5° | 1731.4 | 1783.5 | 1839.3 | 2056.6 | 2273.9 | 3011.3 | 3748.9 | 4547.0 | 5345.0 | 5662.7  |
| 1603.0 | 45°   | 1629.5 | 1679.9 | 1736.5 | 1927.1 | 2117.7 | 2953.5 | 3789.3 | 4803.0 | 5816.7 | 6245.2  |
| 1516.4 | 47.5° | 1538.6 | 1582.0 | 1655.0 | 1824.7 | 1994.3 | 2905.7 | 3817.1 | 5075.9 | 6334.6 | 6937.8  |
| 1438.9 | 50°   | 1458.6 | 1508.9 | 1604.9 | 1756.6 | 1908.3 | 2853.6 | 3799.0 | 5329.0 | 6859.0 | 7768.2  |
| 1379.4 | 52.5° | 1398.9 | 1469.3 | 1579.7 | 1711.8 | 1844.0 | 2765.7 | 3687.5 | 5493.3 | 7299.1 | 8640.5  |
| 1336.4 | 55°   | 1367.2 | 1473.3 | 1576.0 | 1679.3 | 1782.7 | 2619.9 | 3457.1 | 5457.1 | 7457.0 | 9413.9  |
| 1303.4 | 57.5° | 1348.2 | 1477.3 | 1567.8 | 1640.8 | 1713.8 | 2414.3 | 3114.7 | 5202.2 | 7289.8 | 9962.0  |
| 1272.2 | 60°   | 1330.3 | 1464.8 | 1524.6 | 1582.0 | 1639.4 | 2147.4 | 2655.4 | 4727.8 | 6800.1 | 10099.0 |
| 1236.8 | 62.5° | 1309.5 | 1434.2 | 1441.6 | 1479.6 | 1517.8 | 1827.9 | 2138.1 | 4086.3 | 6034.4 | 9522.2  |
| 1188.4 | 65°   | 1265.6 | 1360.7 | 1359.7 | 1377.7 | 1395.7 | 1540.5 | 1685.3 | 3431.7 | 5178.3 | 8706.2  |
| 1122.9 | 67.5° | 1187.2 | 1240.7 | 1243.2 | 1233.2 | 1223.1 | 1264.3 | 1305.4 | 2790.6 | 4275.8 | 7735.0  |
| 1042.1 | 70°   | 1087.8 | 1105.4 | 1105.4 | 1058.9 | 1012.2 | 1000.6 | 988.8  | 2197.2 | 3405.6 | 6675.4  |
| 945.8  | 72.5° | 977.1  | 976.9  | 965.8  | 899.8  | 833.7  | 798.2  | 762.7  | 1679.8 | 2596.8 | 5526.6  |
| 827.4  | 75°   | 851.5  | 855.8  | 804.6  | 730.6  | 656.6  | 624.4  | 592.3  | 1219.2 | 1846.1 | 4209.8  |
| 706.3  | 77.5° | 725.6  | 727.9  | 643.5  | 571.7  | 499.8  | 477.8  | 456.0  | 826.1  | 1196.3 | 2946.5  |
| 565.9  | 80°   | 582.1  | 582.4  | 481.7  | 420.9  | 360.0  | 350.9  | 341.9  | 532.3  | 722.8  | 1898.4  |
| 420.2  | 82.5° | 428.1  | 423.4  | 337.3  | 292.5  | 247.7  | 245.9  | 244.3  | 327.4  | 410.7  | 1098.7  |
| 273.4  | 85°   | 281.9  | 275.6  | 211.7  | 178.9  | 146.0  | 146.9  | 147.7  | 175.0  | 202.4  | 494.2   |
| 121.1  | 87.5° | 124.5  | 116.6  | 90.0   | 76.5   | 63.2   | 64.0   | 64.7   | 72.6   | 80.4   | 161.9   |
| 0.0    | 90°   | 0.0    | 0.0    | 0.0    | 0.0    | 0.0    | 0.0    | 0.0    | 0.0    | 0.0    | 0.0     |

REPORT NUMBER: P947425

CATALOG NUMBER: GLAN-SB2D-740-U-SLR

**CANDELA DISTRIBUTION (continued):**

| 270°    |       | 275°    | 280°    | 285°    | 290°    | 295°    | 300°    | 305°    | 310°    | 315°    | 320°    |
|---------|-------|---------|---------|---------|---------|---------|---------|---------|---------|---------|---------|
| 2950.0  | 0°    | 2950.0  | 2950.0  | 2950.0  | 2950.0  | 2950.0  | 2950.0  | 2950.0  | 2950.0  | 2950.0  | 2950.0  |
| 3172.4  | 2.5°  | 3184.4  | 3196.5  | 3213.6  | 3230.7  | 3240.9  | 3251.1  | 3256.2  | 3261.3  | 3259.0  | 3261.3  |
| 3411.3  | 5°    | 3453.3  | 3495.4  | 3537.0  | 3578.8  | 3601.4  | 3624.1  | 3637.8  | 3651.6  | 3662.0  | 3651.6  |
| 3651.2  | 7.5°  | 3719.6  | 3787.9  | 3849.3  | 3910.8  | 3947.8  | 3984.8  | 4004.9  | 4024.8  | 4034.4  | 4024.8  |
| 3835.2  | 10°   | 3916.0  | 3996.8  | 4068.9  | 4141.1  | 4184.7  | 4228.2  | 4247.7  | 4267.0  | 4274.4  | 4267.0  |
| 3947.8  | 12.5° | 4035.4  | 4122.9  | 4188.1  | 4253.1  | 4284.8  | 4316.5  | 4327.2  | 4337.8  | 4338.9  | 4337.8  |
| 4016.3  | 15°   | 4091.9  | 4167.4  | 4208.3  | 4249.3  | 4250.4  | 4251.5  | 4240.2  | 4228.9  | 4215.5  | 4228.9  |
| 4054.8  | 17.5° | 4105.8  | 4156.9  | 4157.7  | 4158.4  | 4112.5  | 4066.7  | 4024.7  | 3982.6  | 3952.9  | 3982.6  |
| 4097.2  | 20°   | 4115.0  | 4132.9  | 4079.1  | 4025.4  | 3924.2  | 3823.0  | 3749.3  | 3675.6  | 3630.3  | 3675.6  |
| 4146.5  | 22.5° | 4123.2  | 4099.9  | 3988.5  | 3877.1  | 3728.2  | 3579.4  | 3487.2  | 3395.1  | 3345.0  | 3395.1  |
| 4209.9  | 25°   | 4136.3  | 4062.7  | 3893.6  | 3724.5  | 3543.7  | 3362.9  | 3266.0  | 3169.4  | 3122.0  | 3169.4  |
| 4295.9  | 27.5° | 4164.4  | 4032.7  | 3808.7  | 3584.8  | 3384.4  | 3184.1  | 3088.8  | 2993.6  | 2948.8  | 2993.6  |
| 4411.9  | 30°   | 4215.8  | 4019.7  | 3744.0  | 3468.2  | 3259.5  | 3050.7  | 2962.3  | 2873.9  | 2832.2  | 2873.9  |
| 4548.9  | 32.5° | 4280.3  | 4011.8  | 3699.8  | 3387.8  | 3191.7  | 2995.5  | 2926.1  | 2856.6  | 2826.6  | 2856.6  |
| 4715.3  | 35°   | 4386.6  | 4058.0  | 3732.9  | 3407.9  | 3271.6  | 3135.4  | 3119.2  | 3103.0  | 3100.5  | 3103.0  |
| 4995.5  | 37.5° | 4608.8  | 4222.1  | 3926.7  | 3631.2  | 3622.4  | 3613.5  | 3687.6  | 3761.6  | 3800.1  | 3761.6  |
| 5418.8  | 40°   | 4998.3  | 4577.8  | 4358.1  | 4138.3  | 4293.4  | 4448.5  | 4628.5  | 4808.5  | 4898.1  | 4808.5  |
| 5980.3  | 42.5° | 5563.1  | 5145.8  | 5019.3  | 4892.7  | 5230.9  | 5569.2  | 5896.5  | 6223.9  | 6416.1  | 6223.9  |
| 6673.7  | 45°   | 6298.9  | 5923.9  | 5868.1  | 5812.2  | 6354.1  | 6896.1  | 7434.0  | 7972.1  | 8298.6  | 7972.1  |
| 7540.8  | 47.5° | 7176.2  | 6811.4  | 6800.1  | 6788.8  | 7570.5  | 8352.1  | 9139.6  | 9927.0  | 10389.4 | 9927.0  |
| 8677.3  | 50°   | 8226.9  | 7776.6  | 7778.5  | 7780.4  | 8787.9  | 9795.4  | 10834.9 | 11874.4 | 12502.9 | 11874.4 |
| 9981.9  | 52.5° | 9436.5  | 8891.2  | 8836.1  | 8780.9  | 9984.3  | 11187.7 | 12473.9 | 13759.9 | 14513.3 | 13759.9 |
| 11370.9 | 55°   | 10832.0 | 10293.2 | 10078.2 | 9863.3  | 11202.6 | 12541.9 | 14075.2 | 15608.5 | 16504.4 | 15608.5 |
| 12634.2 | 57.5° | 12340.8 | 12047.2 | 11616.1 | 11185.0 | 12537.4 | 13889.8 | 15626.5 | 17363.1 | 18474.1 | 17363.1 |
| 13397.7 | 60°   | 13853.4 | 14309.3 | 13773.9 | 13238.4 | 14518.3 | 15798.1 | 17657.5 | 19516.9 | 20717.7 | 19516.9 |
| 13010.0 | 62.5° | 14255.3 | 15500.6 | 15440.3 | 15379.8 | 16552.2 | 17724.7 | 19493.8 | 21262.8 | 22372.7 | 21262.8 |
| 12234.0 | 65°   | 13402.8 | 14571.6 | 14802.8 | 15034.0 | 16523.9 | 18014.0 | 19729.4 | 21444.7 | 22389.7 | 21444.7 |
| 11194.3 | 67.5° | 12305.9 | 13417.5 | 13526.0 | 13634.3 | 15186.7 | 16739.0 | 18461.8 | 20184.6 | 20924.9 | 20184.6 |
| 9945.1  | 70°   | 11154.2 | 12363.4 | 12411.8 | 12460.4 | 13848.7 | 15236.8 | 16719.4 | 18201.9 | 18613.4 | 18201.9 |
| 8456.5  | 72.5° | 9844.0  | 11231.6 | 11266.5 | 11301.2 | 12387.4 | 13473.5 | 14583.9 | 15694.2 | 15735.8 | 15694.2 |
| 6573.5  | 75°   | 8009.5  | 9445.6  | 9574.5  | 9703.4  | 10548.5 | 11393.5 | 12175.1 | 12956.8 | 12747.4 | 12956.8 |
| 4696.6  | 77.5° | 6037.1  | 7377.8  | 7562.3  | 7746.8  | 8389.2  | 9031.6  | 9585.9  | 10140.4 | 9780.4  | 10140.4 |
| 3073.9  | 80°   | 4201.7  | 5329.4  | 5558.8  | 5788.1  | 6273.3  | 6758.2  | 7049.4  | 7340.4  | 6761.4  | 7340.4  |
| 1786.9  | 82.5° | 2557.9  | 3329.0  | 3585.1  | 3841.4  | 4175.4  | 4509.3  | 4630.8  | 4752.1  | 4297.0  | 4752.1  |
| 786.2   | 85°   | 1195.4  | 1604.6  | 1822.5  | 2040.4  | 2314.8  | 2589.1  | 2658.0  | 2727.0  | 2362.5  | 2727.0  |
| 243.4   | 87.5° | 380.9   | 518.5   | 640.0   | 761.6   | 898.8   | 1036.0  | 1041.9  | 1047.7  | 879.6   | 1047.7  |
| 0.0     | 90°   | 0.0     | 0.0     | 0.0     | 0.0     | 0.0     | 0.0     | 0.0     | 0.0     | 0.0     | 0.0     |

REPORT NUMBER: P947425

CATALOG NUMBER: GLAN-SB2D-740-U-SLR

**CANDELA DISTRIBUTION (continued):**

| 325°    |       | 330°    | 335°    | 340°    | 345°    | 350°    | 355°    | 360°    |
|---------|-------|---------|---------|---------|---------|---------|---------|---------|
| 2950.0  | 0°    | 2950.0  | 2950.0  | 2950.0  | 2950.0  | 2950.0  | 2950.0  | 2950.0  |
| 3256.2  | 2.5°  | 3251.1  | 3240.9  | 3230.7  | 3213.6  | 3196.5  | 3184.4  | 3172.4  |
| 3637.8  | 5°    | 3624.1  | 3601.4  | 3578.8  | 3537.0  | 3495.4  | 3453.3  | 3411.3  |
| 4004.9  | 7.5°  | 3984.8  | 3947.8  | 3910.8  | 3849.3  | 3787.9  | 3719.6  | 3651.2  |
| 4247.7  | 10°   | 4228.2  | 4184.7  | 4141.1  | 4068.9  | 3996.8  | 3916.0  | 3835.2  |
| 4327.2  | 12.5° | 4316.5  | 4284.8  | 4253.1  | 4188.1  | 4122.9  | 4035.4  | 3947.8  |
| 4240.2  | 15°   | 4251.5  | 4250.4  | 4249.3  | 4208.3  | 4167.4  | 4091.9  | 4016.3  |
| 4024.7  | 17.5° | 4066.7  | 4112.5  | 4158.4  | 4157.7  | 4156.9  | 4105.8  | 4054.8  |
| 3749.3  | 20°   | 3823.0  | 3924.2  | 4025.4  | 4079.1  | 4132.9  | 4115.0  | 4097.2  |
| 3487.2  | 22.5° | 3579.4  | 3728.2  | 3877.1  | 3988.5  | 4099.9  | 4123.2  | 4146.5  |
| 3266.0  | 25°   | 3362.9  | 3543.7  | 3724.5  | 3893.6  | 4062.7  | 4136.3  | 4209.9  |
| 3088.8  | 27.5° | 3184.1  | 3384.4  | 3584.8  | 3808.7  | 4032.7  | 4164.4  | 4295.9  |
| 2962.3  | 30°   | 3050.7  | 3259.5  | 3468.2  | 3744.0  | 4019.7  | 4215.8  | 4411.9  |
| 2926.1  | 32.5° | 2995.5  | 3191.7  | 3387.8  | 3699.8  | 4011.8  | 4280.3  | 4548.9  |
| 3119.2  | 35°   | 3135.4  | 3271.6  | 3407.9  | 3732.9  | 4058.0  | 4386.6  | 4715.3  |
| 3687.6  | 37.5° | 3613.5  | 3622.4  | 3631.2  | 3926.7  | 4222.1  | 4608.8  | 4995.5  |
| 4628.5  | 40°   | 4448.5  | 4293.4  | 4138.3  | 4358.1  | 4577.8  | 4998.3  | 5418.8  |
| 5896.5  | 42.5° | 5569.2  | 5230.9  | 4892.7  | 5019.3  | 5145.8  | 5563.1  | 5980.3  |
| 7434.0  | 45°   | 6896.1  | 6354.1  | 5812.2  | 5868.1  | 5923.9  | 6298.9  | 6673.7  |
| 9139.6  | 47.5° | 8352.1  | 7570.5  | 6788.8  | 6800.1  | 6811.4  | 7176.2  | 7540.8  |
| 10834.9 | 50°   | 9795.4  | 8787.9  | 7780.4  | 7778.5  | 7776.6  | 8226.9  | 8677.3  |
| 12473.9 | 52.5° | 11187.7 | 9984.3  | 8780.9  | 8836.1  | 8891.2  | 9436.5  | 9981.9  |
| 14075.2 | 55°   | 12541.9 | 11202.6 | 9863.3  | 10078.2 | 10293.2 | 10832.0 | 11370.9 |
| 15626.5 | 57.5° | 13889.8 | 12537.4 | 11185.0 | 11616.1 | 12047.2 | 12340.8 | 12634.2 |
| 17657.5 | 60°   | 15798.1 | 14518.3 | 13238.4 | 13773.9 | 14309.3 | 13853.4 | 13397.7 |
| 19493.8 | 62.5° | 17724.7 | 16552.2 | 15379.8 | 15440.3 | 15500.6 | 14255.3 | 13010.0 |
| 19729.4 | 65°   | 18014.0 | 16523.9 | 15034.0 | 14802.8 | 14571.6 | 13402.8 | 12234.0 |
| 18461.8 | 67.5° | 16739.0 | 15186.7 | 13634.3 | 13526.0 | 13417.5 | 12305.9 | 11194.3 |
| 16719.4 | 70°   | 15236.8 | 13848.7 | 12460.4 | 12411.8 | 12363.4 | 11154.2 | 9945.1  |
| 14583.9 | 72.5° | 13473.5 | 12387.4 | 11301.2 | 11266.5 | 11231.6 | 9844.0  | 8456.5  |
| 12175.1 | 75°   | 11393.5 | 10548.5 | 9703.4  | 9574.5  | 9445.6  | 8009.5  | 6573.5  |
| 9585.9  | 77.5° | 9031.6  | 8389.2  | 7746.8  | 7562.3  | 7377.8  | 6037.1  | 4696.6  |
| 7049.4  | 80°   | 6758.2  | 6273.3  | 5788.1  | 5558.8  | 5329.4  | 4201.7  | 3073.9  |
| 4630.8  | 82.5° | 4509.3  | 4175.4  | 3841.4  | 3585.1  | 3329.0  | 2557.9  | 1786.9  |
| 2658.0  | 85°   | 2589.1  | 2314.8  | 2040.4  | 1822.5  | 1604.6  | 1195.4  | 786.2   |
| 1041.9  | 87.5° | 1036.0  | 898.8   | 761.6   | 640.0   | 518.5   | 380.9   | 243.4   |
| 0.0     | 90°   | 0.0     | 0.0     | 0.0     | 0.0     | 0.0     | 0.0     | 0.0     |

(END OF REPORT)