

Scaled data based on original data using
LM-79-08 Approved Method: Electrical and Photometric Measurements of Solid-
State Lighting Products

Test Report Prepared for
Cooper Lighting Solutions
(formerly Eaton)

Brand: STREETWORKS

Report Number: P956392

Luminaire Tested: **GLAN-SB9A-760-U-SLR**

Issue Date: 1/21/2025

Test Information

Test Method: LM-79-08
Report Number: P956392
TEST IS SCALED FROM IESNA LM-79-08 TEST DATA (G2-2411-289-8)
Test Lab: INNOVATION CENTER
Issue Date: 1/21/2025
Manufacturer: COOPER LIGHTING SOLUTIONS (FORMERLY EATON)
Product Line: STREETWORKS
Catalog Number: GLAN-SB9A-760-U-SLR
Description: GALLEON AREA AND ROADWAY HIGH DENSITY LED LUMINAIRE
(9) 70 CRI, 5700K, 350mA LIGHTSQUARES WITH 26 LEDS EACH AND SPILL LIGHT
ELIMINATOR RIGHT OPTICS
Light Source: -
Ballast/Driver: -

Summary

Lumens per Lamp: N/A
Luminaire Lumens: 43072 lumens
Efficiency: N/A
Efficacy: 168.6 lumens/watt
Luminous Opening: Rectangular (W 1.5' x L: 1.5' x H: 0')
IES Classification: Type IV - Short
BUG Rating: B4 - U0 - G5

Input Watts (W): 255.5
Input Voltage (V): NR
Input Current (Ain): NR
Voltage Rise (V): NR
Power Factor: NR
Total Harmonic Distortion (THDi): NR
Frequency (hertz): 60
Stabilization Time: NR
Operation Time: NR
Ambient Temperature (°C): NR
Test Distance: 24 FT




REPORT NUMBER: P956392

CATALOG NUMBER: GLAN-SB9A-760-U-SLR

Iso-Footcandle Lines of Horizontal Illumination

× Max cd
- - - 1/2 Max cd




Based on 25 foot mounting height. Maximum calculated value = 11.7 fc

Type IV - Short - N/A

REPORT NUMBER: P956392
CATALOG NUMBER: GLAN-SB9A-760-U-SLR

Luminous Intensity Polar Plot



REPORT NUMBER: P956392

CATALOG NUMBER: GLAN-SB9A-760-U-SLR


FLUX DISTRIBUTION:

		Downward	Upward	Total
House Side	Lumens	10946.7	0.0	10946.7
	% Fixture	25.4	0.0	25.4
Street Side	Lumens	32125.3	0.0	32125.3
	% Fixture	74.6	0.0	74.6
Total	Lumens	43072.0	0.0	43072.0
	% Fixture	100.0	0.0	100.0

ZONAL LUMENS:

Zone	Lumens	% Fixture
0°-10°	587.5	1.4
10°-20°	1844.4	4.3
20°-30°	2848.9	6.6
30°-40°	3610.3	8.4
40°-50°	5445.3	12.6
50°-60°	8797.7	20.4
60°-70°	10967.7	25.5
70°-80°	7192.1	16.7
80°-90°	1778.1	4.1
90°-100°	0.0	0.0
100°-110°	0.0	0.0
110°-120°	0.0	0.0
120°-130°	0.0	0.0
130°-140°	0.0	0.0
140°-150°	0.0	0.0
150°-160°	0.0	0.0
160°-170°	0.0	0.0
170°-180°	0.0	0.0
0°-90°	43072.0	100.0
0°-180°	43072.0	100.0

Coefficient of Utilization



REPORT NUMBER: P956392


CATALOG NUMBER: GLAN-SB9A-760-U-SLR

LUMINAIRE CLASSIFICATION SYSTEM LUMEN TABLE AND BUG RATING:

Zone		Lumens	% Fixture	Zone Rating/Lumen Limit		
				B	U	G
FL	(0°-30°)	2897.1	6.7			
FM	(30°-60°)	12563.2	29.2			
FH	(60°-80°)	15200.3	35.3			G5
FVH	(80°-90°)	1464.7	3.4			G5
BL	(0°-30°)	2383.8	5.5	B3/2500		
BM	(30°-60°)	5290.1	12.3	B4/8500		
BH	(60°-80°)	2959.5	6.9	B4/5000		G4/5000
BVH	(80°-90°)	313.3	0.7			G3/500
UL	(90°-100°)	0.0	0.0		U0/0	
UH	(100°-180°)	0.0	0.0		U0/0	

BUG Rating: B4-U0-G5

Type IV Short



REPORT NUMBER: P956392

CATALOG NUMBER: GLAN-SB9A-760-U-SLR

CANDELA DISTRIBUTION (FULL):

	0°	5°	10°	15°	20°	25°	30°	35°	40°	45°
0°	5922.8	5922.8	5922.8	5922.8	5922.8	5922.8	5922.8	5922.8	5922.8	5922.8
2.5°	6369.4	6320.5	6271.6	6219.6	6167.8	6115.5	6063.2	6013.2	5963.2	5914.8
5°	6848.9	6741.0	6633.0	6525.3	6417.8	6309.4	6201.2	6100.0	5998.9	5903.5
7.5°	7330.7	7152.6	6974.6	6810.1	6645.5	6485.3	6325.0	6183.9	6042.8	5912.5
10°	7700.1	7474.8	7249.6	7032.1	6814.8	6620.3	6425.5	6258.7	6091.4	5930.7
12.5°	7926.2	7678.7	7431.4	7185.1	6938.7	6709.1	6479.6	6290.7	6101.9	5933.0
15°	8063.7	7805.7	7547.8	7280.5	7013.2	6748.9	6484.6	6266.0	6047.3	5860.3
17.5°	8141.0	7879.4	7617.8	7326.2	7034.6	6727.8	6421.0	6158.0	5895.0	5675.0
20°	8226.2	7954.4	7682.3	7361.9	7041.4	6669.6	6297.8	5971.9	5646.0	5389.8
22.5°	8325.1	8047.3	7769.4	7410.1	7050.5	6598.2	6146.0	5753.5	5360.9	5069.4
25°	8452.3	8180.1	7908.0	7497.3	7086.4	6527.8	5969.4	5509.6	5050.0	4751.2
27.5°	8625.1	8365.5	8105.7	7633.7	7161.4	6480.7	5800.0	5286.6	4773.2	4501.2
30°	8858.0	8607.1	8356.4	7810.3	7264.1	6458.7	5652.8	5100.3	4547.8	4319.4
32.5°	9133.0	8884.6	8636.4	7994.6	7352.8	6431.4	5509.6	4939.6	4369.4	4185.3
35°	9467.1	9229.4	8991.4	8204.6	7417.8	6380.0	5342.8	4781.6	4220.5	4067.1
37.5°	10029.6	9726.4	9423.3	8439.8	7456.4	6292.1	5127.8	4595.7	4063.7	3929.6
40°	10879.6	10437.8	9996.0	8738.5	7480.7	6171.0	4861.4	4373.9	3886.4	3764.8
42.5°	12006.9	11369.2	10731.4	9129.2	7526.9	6046.0	4565.5	4129.1	3692.8	3580.7
45°	13399.0	12538.7	11678.5	9643.3	7608.0	5929.8	4251.8	3869.1	3486.4	3372.8
47.5°	15139.9	13929.2	12718.3	10191.0	7663.7	5833.9	4004.1	3663.4	3322.8	3176.2
50°	17421.7	15596.5	13771.0	10699.2	7627.3	5729.4	3831.4	3526.8	3222.3	3029.6
52.5°	20041.1	17347.9	14654.7	11029.2	7403.5	5552.8	3702.3	3436.8	3171.6	2950.0
55°	22829.7	18900.6	14971.7	10956.4	6941.0	5260.0	3579.1	3371.6	3164.1	2958.0
57.5°	25366.1	20001.1	14636.0	10444.6	6253.5	4847.3	3440.9	3294.3	3147.8	2965.9
60°	26899.1	20276.1	13652.8	9492.1	5331.4	4311.4	3291.4	3176.2	3060.9	2940.9
62.5°	26120.6	19118.1	12115.5	8204.2	4292.8	3670.0	3047.3	2970.7	2894.3	2879.6
65°	24562.7	17479.7	10396.7	6890.1	3383.7	3093.0	2802.3	2766.2	2730.0	2731.8
67.5°	22475.2	15529.9	8584.6	5602.8	2620.9	2538.4	2455.7	2475.9	2495.9	2490.9
70°	19967.2	13402.4	6837.6	4411.4	1985.2	2008.9	2032.3	2125.9	2219.3	2219.3
72.5°	16978.5	11096.0	5213.7	3372.5	1531.4	1602.5	1673.9	1806.6	1939.1	1961.4
75°	13197.8	8452.1	3706.4	2447.7	1189.1	1253.6	1318.2	1466.8	1615.5	1718.2
77.5°	9429.6	5915.7	2401.8	1658.6	915.5	959.3	1003.4	1147.7	1292.1	1461.4
80°	6171.6	3811.4	1451.1	1068.6	686.4	704.6	722.7	845.0	967.1	1169.3
82.5°	3587.5	2205.9	824.6	657.3	490.5	493.6	497.3	587.3	677.3	850.0
85°	1578.4	992.3	406.4	351.4	296.6	295.0	293.2	359.1	425.0	553.4
87.5°	488.6	325.0	161.4	145.7	130.0	128.4	126.8	153.6	180.7	234.1
90°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0

REPORT NUMBER: P956392

CATALOG NUMBER: GLAN-SB9A-760-U-SLR

CANDELA DISTRIBUTION (continued):

50°		55°	60°	65°	70°	75°	80°	85°	90°	95°	100°
5922.8	0°	5922.8	5922.8	5922.8	5922.8	5922.8	5922.8	5922.8	5922.8	5922.8	5922.8
5861.0	2.5°	5817.3	5773.9	5734.6	5695.5	5661.2	5626.9	5592.3	5558.0	5531.4	5504.6
5809.1	5°	5726.9	5644.4	5575.3	5506.4	5445.5	5384.6	5329.4	5273.9	5231.4	5188.7
5790.5	7.5°	5681.0	5571.6	5480.7	5389.8	5313.2	5236.4	5168.7	5101.2	5050.5	5000.0
5799.6	10°	5684.1	5568.7	5477.8	5386.9	5304.4	5221.6	5145.5	5069.4	5008.9	4948.2
5811.0	12.5°	5716.4	5622.3	5561.9	5501.9	5436.9	5372.3	5293.4	5214.8	5137.5	5060.3
5762.5	15°	5717.3	5672.3	5680.5	5688.7	5671.9	5655.0	5586.6	5518.2	5408.2	5298.2
5614.8	17.5°	5631.4	5647.8	5746.9	5846.0	5898.7	5951.2	5896.0	5841.0	5695.3	5549.6
5373.9	20°	5451.2	5528.4	5700.5	5872.8	5983.0	6093.2	6067.8	6042.1	5875.5	5709.1
5100.5	22.5°	5214.8	5329.1	5525.5	5722.3	5865.7	6009.1	6024.6	6039.8	5880.7	5721.6
4835.3	25°	4967.1	5098.9	5275.5	5452.3	5593.5	5734.6	5787.3	5839.8	5709.4	5579.1
4603.4	27.5°	4730.7	4858.0	5003.2	5148.2	5261.4	5374.6	5433.2	5492.1	5399.1	5306.4
4399.6	30°	4500.5	4601.9	4722.3	4842.8	4936.6	5030.7	5078.4	5126.2	5055.5	4984.6
4220.9	32.5°	4280.7	4340.5	4436.6	4533.0	4623.0	4713.2	4766.2	4819.4	4754.4	4689.1
4052.3	35°	4068.7	4085.3	4158.7	4231.8	4320.9	4410.3	4473.9	4537.5	4491.2	4445.0
3875.5	37.5°	3857.3	3839.1	3891.8	3944.3	4033.2	4122.3	4200.9	4279.6	4258.2	4236.8
3681.8	40°	3640.7	3599.6	3637.5	3675.5	3761.4	3847.3	3937.8	4028.4	4033.7	4038.7
3476.2	42.5°	3421.6	3367.1	3398.0	3429.1	3510.5	3592.1	3689.8	3787.5	3813.7	3839.8
3271.6	45°	3218.4	3165.5	3191.4	3217.8	3295.0	3372.3	3473.7	3575.0	3612.5	3650.0
3089.1	47.5°	3044.6	3000.0	3024.6	3048.9	3124.6	3200.0	3300.0	3400.0	3443.2	3486.4
2928.4	50°	2888.9	2849.6	2887.7	2926.2	2997.5	3068.7	3158.2	3247.8	3303.2	3358.7
2808.7	52.5°	2769.6	2730.7	2788.2	2845.5	2910.9	2976.2	3059.6	3143.2	3208.9	3274.6
2745.0	55°	2683.2	2621.6	2703.2	2784.6	2855.0	2925.5	2998.7	3071.6	3141.2	3210.9
2706.8	57.5°	2616.8	2526.8	2614.6	2702.3	2785.0	2867.7	2940.0	3012.5	3082.8	3152.8
2670.9	60°	2554.3	2437.5	2514.6	2591.4	2686.4	2781.4	2854.8	2928.4	2998.9	3069.3
2629.1	62.5°	2483.2	2337.5	2386.4	2435.2	2545.9	2656.8	2735.2	2813.7	2878.2	2942.7
2540.9	65°	2385.9	2230.7	2249.6	2268.2	2386.8	2505.7	2580.7	2655.7	2712.5	2769.3
2383.7	67.5°	2254.6	2125.5	2119.6	2113.7	2223.2	2333.0	2404.1	2475.0	2524.1	2573.2
2184.1	70°	2092.3	2000.5	1980.0	1959.6	2055.9	2152.3	2213.7	2275.0	2319.3	2363.7
1961.8	72.5°	1898.9	1835.9	1805.9	1776.1	1852.1	1927.7	1983.2	2038.7	2082.1	2125.5
1709.6	75°	1661.1	1612.5	1583.9	1555.0	1611.4	1667.7	1718.0	1768.2	1807.7	1847.3
1456.8	77.5°	1418.0	1379.1	1350.0	1320.9	1366.8	1412.5	1455.7	1498.9	1540.5	1581.8
1168.6	80°	1136.1	1103.4	1079.1	1054.6	1092.7	1130.7	1167.1	1203.4	1235.0	1266.4
859.6	82.5°	843.6	827.7	810.5	793.2	790.0	786.8	774.1	761.4	828.6	895.9
565.9	85°	548.9	531.8	512.5	493.2	476.8	460.2	425.0	389.8	452.7	515.9
250.0	87.5°	243.2	236.4	232.7	229.1	228.4	227.7	200.9	173.9	200.2	226.8
0.0	90°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0

REPORT NUMBER: P956392

CATALOG NUMBER: GLAN-SB9A-760-U-SLR

CANDELA DISTRIBUTION (continued):

105°		110°	115°	120°	125°	130°	135°	140°	145°	150°	155°
5922.8	0°	5922.8	5922.8	5922.8	5922.8	5922.8	5922.8	5922.8	5922.8	5922.8	5922.8
5483.0	2.5°	5461.4	5444.6	5427.8	5412.3	5396.6	5377.3	5396.6	5412.3	5427.8	5444.6
5158.9	5°	5129.1	5108.0	5086.9	5070.7	5054.6	5038.7	5054.6	5070.7	5086.9	5108.0
4964.6	7.5°	4929.1	4904.8	4880.7	4866.2	4851.9	4840.9	4851.9	4866.2	4880.7	4904.8
4908.7	10°	4868.7	4845.7	4822.8	4810.5	4798.2	4793.2	4798.2	4810.5	4822.8	4845.7
5009.1	12.5°	4958.0	4932.3	4906.9	4896.4	4885.9	4884.1	4885.9	4896.4	4906.9	4932.3
5220.5	15°	5142.8	5107.1	5071.6	5058.0	5044.4	5043.2	5044.4	5058.0	5071.6	5107.1
5435.0	17.5°	5320.5	5267.8	5214.8	5197.5	5180.0	5177.3	5180.0	5197.5	5214.8	5267.8
5568.7	20°	5428.4	5360.9	5293.2	5271.6	5250.0	5243.2	5250.0	5271.6	5293.2	5360.9
5577.1	22.5°	5432.3	5361.2	5289.8	5265.9	5242.1	5231.9	5242.1	5265.9	5289.8	5361.2
5450.5	25°	5322.3	5260.5	5198.9	5176.4	5154.1	5140.9	5154.1	5176.4	5198.9	5260.5
5206.6	27.5°	5106.9	5065.5	5023.9	5013.7	5003.4	5000.0	5003.4	5013.7	5023.9	5065.5
4913.2	30°	4841.4	4820.3	4798.9	4798.9	4798.9	4802.3	4798.9	4798.9	4798.9	4820.3
4632.1	32.5°	4575.0	4561.2	4547.3	4549.1	4551.2	4554.6	4551.2	4549.1	4547.3	4561.2
4392.3	35°	4339.8	4318.7	4297.8	4293.2	4288.7	4286.4	4288.7	4293.2	4297.8	4318.7
4188.4	37.5°	4139.8	4101.4	4063.2	4043.0	4022.8	4011.4	4022.8	4043.0	4063.2	4101.4
3997.5	40°	3956.4	3900.5	3845.0	3807.3	3770.0	3747.8	3770.0	3807.3	3845.0	3900.5
3805.0	42.5°	3770.5	3701.2	3631.8	3577.1	3522.3	3486.4	3522.3	3577.1	3631.8	3701.2
3618.7	45°	3587.5	3508.2	3429.1	3364.8	3300.5	3259.1	3300.5	3364.8	3429.1	3508.2
3464.6	47.5°	3442.8	3372.3	3301.8	3242.3	3183.0	3143.2	3183.0	3242.3	3301.8	3372.3
3357.3	50°	3356.4	3300.0	3243.7	3188.7	3133.7	3095.5	3133.7	3188.7	3243.7	3300.0
3286.4	52.5°	3298.2	3252.3	3206.4	3157.1	3108.0	3072.7	3108.0	3157.1	3206.4	3252.3
3227.3	55°	3243.7	3203.7	3163.7	3120.5	3077.3	3045.5	3077.3	3120.5	3163.7	3203.7
3169.3	57.5°	3185.9	3145.5	3105.0	3062.3	3019.3	2986.4	3019.3	3062.3	3105.0	3145.5
3087.5	60°	3105.7	3066.2	3026.8	2982.7	2938.7	2904.6	2938.7	2982.7	3026.8	3066.2
2960.2	62.5°	2977.7	2942.1	2906.4	2860.0	2813.7	2772.7	2813.7	2860.0	2906.4	2942.1
2787.3	65°	2805.0	2770.7	2736.4	2691.4	2646.6	2611.4	2646.6	2691.4	2736.4	2770.7
2590.7	67.5°	2608.0	2576.4	2545.0	2503.2	2461.4	2429.6	2461.4	2503.2	2545.0	2576.4
2380.5	70°	2397.3	2371.6	2345.9	2305.9	2265.9	2229.6	2265.9	2305.9	2345.9	2371.6
2145.5	72.5°	2165.5	2144.1	2122.7	2084.6	2046.6	2011.4	2046.6	2084.6	2122.7	2144.1
1868.2	75°	1889.1	1878.7	1868.2	1836.1	1804.1	1770.5	1804.1	1836.1	1868.2	1878.7
1601.4	77.5°	1620.9	1606.4	1591.4	1559.1	1526.8	1500.0	1526.8	1559.1	1591.4	1606.4
1292.3	80°	1318.2	1311.8	1305.7	1262.3	1218.6	1168.2	1218.6	1262.3	1305.7	1311.8
940.0	82.5°	984.1	981.4	978.4	941.8	905.0	872.7	905.0	941.8	978.4	981.4
570.5	85°	625.0	620.5	615.9	587.3	558.6	529.5	558.6	587.3	615.9	620.5
248.9	87.5°	270.9	265.5	259.5	245.0	230.0	215.9	230.0	245.0	259.5	265.5
0.0	90°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0

REPORT NUMBER: P956392

CATALOG NUMBER: GLAN-SB9A-760-U-SLR

CANDELA DISTRIBUTION (continued):

160°		165°	170°	175°	180°	185°	190°	195°	200°	205°	210°
5922.8	0°	5922.8	5922.8	5922.8	5922.8	5922.8	5922.8	5922.8	5922.8	5922.8	5922.8
5461.4	2.5°	5483.0	5504.6	5531.4	5558.0	5592.3	5626.9	5661.2	5695.5	5734.6	5773.9
5129.1	5°	5158.9	5188.7	5231.4	5273.9	5329.4	5384.6	5445.5	5506.4	5575.3	5644.4
4929.1	7.5°	4964.6	5000.0	5050.5	5101.2	5168.7	5236.4	5313.2	5389.8	5480.7	5571.6
4868.7	10°	4908.7	4948.2	5008.9	5069.4	5145.5	5221.6	5304.4	5386.9	5477.8	5568.7
4958.0	12.5°	5009.1	5060.3	5137.5	5214.8	5293.4	5372.3	5436.9	5501.9	5561.9	5622.3
5142.8	15°	5220.5	5298.2	5408.2	5518.2	5586.6	5655.0	5671.9	5688.7	5680.5	5672.3
5320.5	17.5°	5435.0	5549.6	5695.3	5841.0	5896.0	5951.2	5898.7	5846.0	5746.9	5647.8
5428.4	20°	5568.7	5709.1	5875.5	6042.1	6067.8	6093.2	5983.0	5872.8	5700.5	5528.4
5432.3	22.5°	5577.1	5721.6	5880.7	6039.8	6024.6	6009.1	5865.7	5722.3	5525.5	5329.1
5322.3	25°	5450.5	5579.1	5709.4	5839.8	5787.3	5734.6	5593.5	5452.3	5275.5	5098.9
5106.9	27.5°	5206.6	5306.4	5399.1	5492.1	5433.2	5374.6	5261.4	5148.2	5003.2	4858.0
4841.4	30°	4913.2	4984.6	5055.5	5126.2	5078.4	5030.7	4936.6	4842.8	4722.3	4601.9
4575.0	32.5°	4632.1	4689.1	4754.4	4819.4	4766.2	4713.2	4623.0	4533.0	4436.6	4340.5
4339.8	35°	4392.3	4445.0	4491.2	4537.5	4473.9	4410.3	4320.9	4231.8	4158.7	4085.3
4139.8	37.5°	4188.4	4236.8	4258.2	4279.6	4200.9	4122.3	4033.2	3944.3	3891.8	3839.1
3956.4	40°	3997.5	4038.7	4033.7	4028.4	3937.8	3847.3	3761.4	3675.5	3637.5	3599.6
3770.5	42.5°	3805.0	3839.8	3813.7	3787.5	3689.8	3592.1	3510.5	3429.1	3398.0	3367.1
3587.5	45°	3618.7	3650.0	3612.5	3575.0	3473.7	3372.3	3295.0	3217.8	3191.4	3165.5
3442.8	47.5°	3464.6	3486.4	3443.2	3400.0	3300.0	3200.0	3124.6	3048.9	3024.6	3000.0
3356.4	50°	3357.3	3358.7	3303.2	3247.8	3158.2	3068.7	2997.5	2926.2	2887.7	2849.6
3298.2	52.5°	3286.4	3274.6	3208.9	3143.2	3059.6	2976.2	2910.9	2845.5	2788.2	2730.7
3243.7	55°	3227.3	3210.9	3141.2	3071.6	2998.7	2925.5	2855.0	2784.6	2703.2	2621.6
3185.9	57.5°	3169.3	3152.8	3082.8	3012.5	2940.0	2867.7	2785.0	2702.3	2614.6	2526.8
3105.7	60°	3087.5	3069.3	2998.9	2928.4	2854.8	2781.4	2686.4	2591.4	2514.6	2437.5
2977.7	62.5°	2960.2	2942.7	2878.2	2813.7	2735.2	2656.8	2545.9	2435.2	2386.4	2337.5
2805.0	65°	2787.3	2769.3	2712.5	2655.7	2580.7	2505.7	2386.8	2268.2	2249.6	2230.7
2608.0	67.5°	2590.7	2573.2	2524.1	2475.0	2404.1	2333.0	2223.2	2113.7	2119.6	2125.5
2397.3	70°	2380.5	2363.7	2319.3	2275.0	2213.7	2152.3	2055.9	1959.6	1980.0	2000.5
2165.5	72.5°	2145.5	2125.5	2082.1	2038.7	1983.2	1927.7	1852.1	1776.1	1805.9	1835.9
1889.1	75°	1868.2	1847.3	1807.7	1768.2	1718.0	1667.7	1611.4	1555.0	1583.9	1612.5
1620.9	77.5°	1601.4	1581.8	1540.5	1498.9	1455.7	1412.5	1366.8	1320.9	1350.0	1379.1
1318.2	80°	1292.3	1266.4	1235.0	1203.4	1167.1	1130.7	1092.7	1054.6	1079.1	1103.4
984.1	82.5°	940.0	895.9	828.6	761.4	774.1	786.8	790.0	793.2	810.5	827.7
625.0	85°	570.5	515.9	452.7	389.8	425.0	460.2	476.8	493.2	512.5	531.8
270.9	87.5°	248.9	226.8	200.2	173.9	200.9	227.7	228.4	229.1	232.7	236.4
0.0	90°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0

REPORT NUMBER: P956392

CATALOG NUMBER: GLAN-SB9A-760-U-SLR

CANDELA DISTRIBUTION (continued):

215°		220°	225°	230°	235°	240°	245°	250°	255°	260°	265°
5922.8	0°	5922.8	5922.8	5922.8	5922.8	5922.8	5922.8	5922.8	5922.8	5922.8	5922.8
5817.3	2.5°	5861.0	5914.8	5963.2	6013.2	6063.2	6115.5	6167.8	6219.6	6271.6	6320.5
5726.9	5°	5809.1	5903.5	5998.9	6100.0	6201.2	6309.4	6417.8	6525.3	6633.0	6741.0
5681.0	7.5°	5790.5	5912.5	6042.8	6183.9	6325.0	6485.3	6645.5	6810.1	6974.6	7152.6
5684.1	10°	5799.6	5930.7	6091.4	6258.7	6425.5	6620.3	6814.8	7032.1	7249.6	7474.8
5716.4	12.5°	5811.0	5933.0	6101.9	6290.7	6479.6	6709.1	6938.7	7185.1	7431.4	7678.7
5717.3	15°	5762.5	5860.3	6047.3	6266.0	6484.6	6748.9	7013.2	7280.5	7547.8	7805.7
5631.4	17.5°	5614.8	5675.0	5895.0	6158.0	6421.0	6727.8	7034.6	7326.2	7617.8	7879.4
5451.2	20°	5373.9	5389.8	5646.0	5971.9	6297.8	6669.6	7041.4	7361.9	7682.3	7954.4
5214.8	22.5°	5100.5	5069.4	5360.9	5753.5	6146.0	6598.2	7050.5	7410.1	7769.4	8047.3
4967.1	25°	4835.3	4751.2	5050.0	5509.6	5969.4	6527.8	7086.4	7497.3	7908.0	8180.1
4730.7	27.5°	4603.4	4501.2	4773.2	5286.6	5800.0	6480.7	7161.4	7633.7	8105.7	8365.5
4500.5	30°	4399.6	4319.4	4547.8	5100.3	5652.8	6458.7	7264.1	7810.3	8356.4	8607.1
4280.7	32.5°	4220.9	4185.3	4369.4	4939.6	5509.6	6431.4	7352.8	7994.6	8636.4	8884.6
4068.7	35°	4052.3	4067.1	4220.5	4781.6	5342.8	6380.0	7417.8	8204.6	8991.4	9229.4
3857.3	37.5°	3875.5	3929.6	4063.7	4595.7	5127.8	6292.1	7456.4	8439.8	9423.3	9726.4
3640.7	40°	3681.8	3764.8	3886.4	4373.9	4861.4	6171.0	7480.7	8738.5	9996.0	10437.8
3421.6	42.5°	3476.2	3580.7	3692.8	4129.1	4565.5	6046.0	7526.9	9129.2	10731.4	11369.2
3218.4	45°	3271.6	3372.8	3486.4	3869.1	4251.8	5929.8	7608.0	9643.3	11678.5	12538.7
3044.6	47.5°	3089.1	3176.2	3322.8	3663.4	4004.1	5833.9	7663.7	10191.0	12718.3	13929.2
2888.9	50°	2928.4	3029.6	3222.3	3526.8	3831.4	5729.4	7627.3	10699.2	13771.0	15596.5
2769.6	52.5°	2808.7	2950.0	3171.6	3436.8	3702.3	5552.8	7403.5	11029.2	14654.7	17347.9
2683.2	55°	2745.0	2958.0	3164.1	3371.6	3579.1	5260.0	6941.0	10956.4	14971.7	18900.6
2616.8	57.5°	2706.8	2965.9	3147.8	3294.3	3440.9	4847.3	6253.5	10444.6	14636.0	20001.1
2554.3	60°	2670.9	2940.9	3060.9	3176.2	3291.4	4311.4	5331.4	9492.1	13652.8	20276.1
2483.2	62.5°	2629.1	2879.6	2894.3	2970.7	3047.3	3670.0	4292.8	8204.2	12115.5	19118.1
2385.9	65°	2540.9	2731.8	2730.0	2766.2	2802.3	3093.0	3383.7	6890.1	10396.7	17479.7
2254.6	67.5°	2383.7	2490.9	2495.9	2475.9	2455.7	2538.4	2620.9	5602.8	8584.6	15529.9
2092.3	70°	2184.1	2219.3	2219.3	2125.9	2032.3	2008.9	1985.2	4411.4	6837.6	13402.4
1898.9	72.5°	1961.8	1961.4	1939.1	1806.6	1673.9	1602.5	1531.4	3372.5	5213.7	11096.0
1661.1	75°	1709.6	1718.2	1615.5	1466.8	1318.2	1253.6	1189.1	2447.7	3706.4	8452.1
1418.0	77.5°	1456.8	1461.4	1292.1	1147.7	1003.4	959.3	915.5	1658.6	2401.8	5915.7
1136.1	80°	1168.6	1169.3	967.1	845.0	722.7	704.6	686.4	1068.6	1451.1	3811.4
843.6	82.5°	859.6	850.0	677.3	587.3	497.3	493.6	490.5	657.3	824.6	2205.9
548.9	85°	565.9	553.4	425.0	359.1	293.2	295.0	296.6	351.4	406.4	992.3
243.2	87.5°	250.0	234.1	180.7	153.6	126.8	128.4	130.0	145.7	161.4	325.0
0.0	90°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0

REPORT NUMBER: P956392

CATALOG NUMBER: GLAN-SB9A-760-U-SLR

CANDELA DISTRIBUTION (continued):

270°		275°	280°	285°	290°	295°	300°	305°	310°	315°	320°
5922.8	0°	5922.8	5922.8	5922.8	5922.8	5922.8	5922.8	5922.8	5922.8	5922.8	5922.8
6369.4	2.5°	6393.5	6417.8	6452.1	6486.4	6506.9	6527.3	6537.5	6547.8	6543.2	6547.8
6848.9	5°	6933.2	7017.8	7101.4	7185.3	7230.7	7276.2	7303.7	7331.4	7352.3	7331.4
7330.7	7.5°	7468.0	7605.1	7728.5	7851.9	7926.2	8000.5	8040.7	8080.7	8100.1	8080.7
7700.1	10°	7862.3	8024.6	8169.4	8314.2	8401.9	8489.2	8528.2	8567.1	8581.9	8567.1
7926.2	12.5°	8102.1	8277.8	8408.7	8539.2	8602.8	8666.4	8687.8	8709.2	8711.4	8709.2
8063.7	15°	8215.5	8367.1	8449.2	8531.4	8533.7	8536.0	8513.2	8490.5	8463.7	8490.5
8141.0	17.5°	8243.5	8346.0	8347.6	8348.9	8256.9	8164.8	8080.5	7996.0	7936.4	7996.0
8226.2	20°	8261.9	8297.8	8189.8	8081.9	7878.7	7675.5	7527.6	7379.6	7288.7	7379.6
8325.1	22.5°	8278.2	8231.4	8007.8	7784.1	7485.3	7186.4	7001.4	6816.4	6716.0	6816.4
8452.3	25°	8304.6	8156.9	7817.3	7477.8	7114.8	6751.9	6557.3	6363.2	6268.2	6363.2
8625.1	27.5°	8361.0	8096.7	7646.9	7197.3	6795.1	6392.8	6201.4	6010.3	5920.5	6010.3
8858.0	30°	8464.2	8070.5	7516.9	6963.2	6544.1	6125.0	5947.5	5770.0	5686.4	5770.0
9133.0	32.5°	8593.7	8054.6	7428.2	6801.9	6408.0	6014.1	5874.8	5735.3	5675.0	5735.3
9467.1	35°	8807.1	8147.3	7494.6	6842.1	6568.5	6295.0	6262.5	6230.0	6225.0	6230.0
10029.6	37.5°	9253.3	8476.9	7883.7	7290.5	7272.8	7255.1	7403.7	7552.3	7629.6	7552.3
10879.6	40°	10035.3	9191.0	8749.8	8308.7	8620.1	8931.4	9292.8	9654.2	9834.2	9654.2
12006.9	42.5°	11169.2	10331.4	10077.3	9823.3	10502.4	11181.4	11838.7	12496.0	12881.9	12496.0
13399.0	45°	12646.5	11893.7	11781.7	11669.4	12757.4	13845.6	14925.6	16005.8	16661.5	16005.8
15139.9	47.5°	14407.8	13675.6	13652.8	13630.1	15199.7	16768.8	18349.9	19930.8	20859.2	19930.8
17421.7	50°	16517.4	15613.3	15617.2	15621.0	17643.8	19666.5	21753.6	23840.6	25102.5	23840.6
20041.1	52.5°	18946.0	17851.3	17740.6	17629.7	20045.8	22462.0	25044.3	27626.3	29138.9	27626.3
22829.7	55°	21747.9	20666.1	20234.5	19802.9	22492.0	25180.9	28259.3	31337.7	33136.6	31337.7
25366.1	57.5°	24777.0	24187.7	23322.0	22456.5	25171.8	27887.0	31373.9	34860.5	37091.2	34860.5
26899.1	60°	27814.1	28729.3	27654.3	26579.3	29148.9	31718.4	35451.6	39184.8	41595.8	39184.8
26120.6	62.5°	28620.9	31121.1	31000.0	30878.6	33232.5	35586.6	39138.5	42690.1	44918.5	42690.1
24562.7	65°	26909.3	29255.9	29720.2	30184.3	33175.7	36167.3	39611.4	43055.3	44952.6	43055.3
22475.2	67.5°	24707.0	26938.8	27156.6	27374.1	30490.9	33607.5	37066.4	40525.3	42011.7	40525.3
19967.2	70°	22394.7	24822.5	24919.7	25017.2	27804.5	30591.6	33568.2	36544.6	37370.7	36544.6
16978.5	72.5°	19764.2	22550.2	22620.2	22689.9	24870.6	27051.3	29280.7	31509.8	31593.4	31509.8
13197.8	75°	16081.0	18964.2	19223.1	19482.0	21178.6	22875.2	24444.5	26013.8	25593.4	26013.8
9429.6	77.5°	12121.0	14812.6	15183.1	15553.5	16843.3	18133.1	19246.1	20359.2	19636.5	20359.2
6171.6	80°	8436.0	10700.1	11160.5	11621.0	12595.1	13568.7	14153.3	14737.6	13575.1	14737.6
3587.5	82.5°	5135.5	6683.7	7198.0	7712.6	8383.0	9053.5	9297.3	9541.0	8627.3	9541.0
1578.4	85°	2400.0	3221.6	3659.1	4096.6	4647.5	5198.2	5336.6	5475.0	4743.2	5475.0
488.6	87.5°	764.8	1040.9	1285.0	1529.1	1804.6	2080.0	2091.8	2103.4	1765.9	2103.4
0.0	90°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0

REPORT NUMBER: P956392

CATALOG NUMBER: GLAN-SB9A-760-U-SLR

CANDELA DISTRIBUTION (continued):

325°		330°	335°	340°	345°	350°	355°	360°
5922.8	0°	5922.8	5922.8	5922.8	5922.8	5922.8	5922.8	5922.8
6537.5	2.5°	6527.3	6506.9	6486.4	6452.1	6417.8	6393.5	6369.4
7303.7	5°	7276.2	7230.7	7185.3	7101.4	7017.8	6933.2	6848.9
8040.7	7.5°	8000.5	7926.2	7851.9	7728.5	7605.1	7468.0	7330.7
8528.2	10°	8489.2	8401.9	8314.2	8169.4	8024.6	7862.3	7700.1
8687.8	12.5°	8666.4	8602.8	8539.2	8408.7	8277.8	8102.1	7926.2
8513.2	15°	8536.0	8533.7	8531.4	8449.2	8367.1	8215.5	8063.7
8080.5	17.5°	8164.8	8256.9	8348.9	8347.6	8346.0	8243.5	8141.0
7527.6	20°	7675.5	7878.7	8081.9	8189.8	8297.8	8261.9	8226.2
7001.4	22.5°	7186.4	7485.3	7784.1	8007.8	8231.4	8278.2	8325.1
6557.3	25°	6751.9	7114.8	7477.8	7817.3	8156.9	8304.6	8452.3
6201.4	27.5°	6392.8	6795.1	7197.3	7646.9	8096.7	8361.0	8625.1
5947.5	30°	6125.0	6544.1	6963.2	7516.9	8070.5	8464.2	8858.0
5874.8	32.5°	6014.1	6408.0	6801.9	7428.2	8054.6	8593.7	9133.0
6262.5	35°	6295.0	6568.5	6842.1	7494.6	8147.3	8807.1	9467.1
7403.7	37.5°	7255.1	7272.8	7290.5	7883.7	8476.9	9253.3	10029.6
9292.8	40°	8931.4	8620.1	8308.7	8749.8	9191.0	10035.3	10879.6
11838.7	42.5°	11181.4	10502.4	9823.3	10077.3	10331.4	11169.2	12006.9
14925.6	45°	13845.6	12757.4	11669.4	11781.7	11893.7	12646.5	13399.0
18349.9	47.5°	16768.8	15199.7	13630.1	13652.8	13675.6	14407.8	15139.9
21753.6	50°	19666.5	17643.8	15621.0	15617.2	15613.3	16517.4	17421.7
25044.3	52.5°	22462.0	20045.8	17629.7	17740.6	17851.3	18946.0	20041.1
28259.3	55°	25180.9	22492.0	19802.9	20234.5	20666.1	21747.9	22829.7
31373.9	57.5°	27887.0	25171.8	22456.5	23322.0	24187.7	24777.0	25366.1
35451.6	60°	31718.4	29148.9	26579.3	27654.3	28729.3	27814.1	26899.1
39138.5	62.5°	35586.6	33232.5	30878.6	31000.0	31121.1	28620.9	26120.6
39611.4	65°	36167.3	33175.7	30184.3	29720.2	29255.9	26909.3	24562.7
37066.4	67.5°	33607.5	30490.9	27374.1	27156.6	26938.8	24707.0	22475.2
33568.2	70°	30591.6	27804.5	25017.2	24919.7	24822.5	22394.7	19967.2
29280.7	72.5°	27051.3	24870.6	22689.9	22620.2	22550.2	19764.2	16978.5
24444.5	75°	22875.2	21178.6	19482.0	19223.1	18964.2	16081.0	13197.8
19246.1	77.5°	18133.1	16843.3	15553.5	15183.1	14812.6	12121.0	9429.6
14153.3	80°	13568.7	12595.1	11621.0	11160.5	10700.1	8436.0	6171.6
9297.3	82.5°	9053.5	8383.0	7712.6	7198.0	6683.7	5135.5	3587.5
5336.6	85°	5198.2	4647.5	4096.6	3659.1	3221.6	2400.0	1578.4
2091.8	87.5°	2080.0	1804.6	1529.1	1285.0	1040.9	764.8	488.6
0.0	90°	0.0	0.0	0.0	0.0	0.0	0.0	0.0

(END OF REPORT)