

Scaled data based on original data using
LM-79-08 Approved Method: Electrical and Photometric Measurements of Solid-
State Lighting Products

Test Report Prepared for
Cooper Lighting Solutions
(formerly Eaton)

Brand: STREETWORKS

Report Number: P940090

Luminaire Tested: **GLAN-SB3A-730-U-5WQ**

Issue Date: 1/21/2025

Test Information

Test Method: LM-79-08
Report Number: P940090
TEST IS SCALED FROM IESNA LM-79-08 TEST DATA (G2-2405-108-1)
Test Lab: INNOVATION CENTER
Issue Date: 1/21/2025
Manufacturer: COOPER LIGHTING SOLUTIONS (FORMERLY EATON)
Product Line: STREETWORKS
Catalog Number: GLAN-SB3A-730-U-5WQ
Description: GALLEON AREA AND ROADWAY HIGH DENSITY LED LUMINAIRE
(3) 70 CRI, 3000K, 350mA LIGHTSQUARES WITH 26 LEDS EACH AND TYPE V WIDE OPTICS
Light Source: -
Ballast/Driver: -

Summary

Lumens per Lamp: N/A
Luminaire Lumens: 13614 lumens
Efficiency: N/A
Efficacy: 160.7 lumens/watt
Luminous Opening: Rectangular (W 1' x L: 1' x H: 0')
IES Classification: Type V - Short
BUG Rating: B4 - U0 - G2

Input Watts (W): 84.7
Input Voltage (V): NR
Input Current (Ain): NR
Voltage Rise (V): NR
Power Factor: NR
Total Harmonic Distortion (THDi): NR
Frequency (hertz): 60
Stabilization Time: NR
Operation Time: NR
Ambient Temperature (°C): NR
Test Distance: 24 FT




REPORT NUMBER: P940090

CATALOG NUMBER: GLAN-SB3A-730-U-5WQ


Iso-Footcandle Lines of Horizontal Illumination

✕ Max cd
--- 1/2 Max cd



Based on 25 foot mounting height. Maximum calculated value = 2 fc
Type V - Short - N/A

REPORT NUMBER: P940090
CATALOG NUMBER: GLAN-SB3A-730-U-5WQ



REPORT NUMBER: P940090

CATALOG NUMBER: GLAN-SB3A-730-U-5WQ


FLUX DISTRIBUTION:

		Downward	Upward	Total
House Side	Lumens	6807.0	0.0	6807.0
	% Fixture	50.0	0.0	50.0
Street Side	Lumens	6807.0	0.0	6807.0
	% Fixture	50.0	0.0	50.0
Total	Lumens	13614.0	0.0	13614.0
	% Fixture	100.0	0.0	100.0

ZONAL LUMENS:

Zone	Lumens	% Fixture
0°-10°	115.5	0.8
10°-20°	339.2	2.5
20°-30°	564.5	4.1
30°-40°	853.7	6.3
40°-50°	1418.6	10.4
50°-60°	2676.8	19.7
60°-70°	4520.0	33.2
70°-80°	2970.1	21.8
80°-90°	155.6	1.1
90°-100°	0.0	0.0
100°-110°	0.0	0.0
110°-120°	0.0	0.0
120°-130°	0.0	0.0
130°-140°	0.0	0.0
140°-150°	0.0	0.0
150°-160°	0.0	0.0
160°-170°	0.0	0.0
170°-180°	0.0	0.0
0°-90°	13614.0	100.0
0°-180°	13614.0	100.0

Coefficient of Utilization



REPORT NUMBER: P940090


CATALOG NUMBER: GLAN-SB3A-730-U-5WQ

LUMINAIRE CLASSIFICATION SYSTEM LUMEN TABLE AND BUG RATING:

Zone		Lumens	% Fixture	Zone Rating/Lumen Limit		
				B	U	G
FL	(0°-30°)	509.6	3.7			
FM	(30°-60°)	2474.6	18.2			
FH	(60°-80°)	3745.0	27.5			G2/5000
FVH	(80°-90°)	77.8	0.6			G1/100
BL	(0°-30°)	509.6	3.7	B2/1000		
BM	(30°-60°)	2474.6	18.2	B2/2500		
BH	(60°-80°)	3745.0	27.5	B4/5000		G2/5000
BVH	(80°-90°)	77.8	0.6			G1/100
UL	(90°-100°)	0.0	0.0		U0/0	
UH	(100°-180°)	0.0	0.0		U0/0	

BUG Rating: B4-U0-G2

Type V Short



REPORT NUMBER: P940090

CATALOG NUMBER: GLAN-SB3A-730-U-5WQ

CANDELA DISTRIBUTION (FULL):

	0°	5°	15°	25°	35°	45°	55°	65°	75°	85°
0°	1241.9	1241.9	1241.9	1241.9	1241.9	1241.9	1241.9	1241.9	1241.9	1241.9
2.5°	1234.1	1237.6	1236.2	1233.4	1233.4	1231.3	1233.4	1234.8	1236.9	1238.3
5°	1217.8	1220.6	1219.9	1217.8	1218.5	1216.4	1217.8	1219.9	1221.3	1222.1
7.5°	1203.7	1206.5	1205.1	1201.5	1201.5	1199.4	1200.1	1202.2	1204.4	1205.1
10°	1200.1	1203.0	1198.7	1193.0	1190.9	1188.1	1188.8	1190.9	1195.2	1197.3
12.5°	1201.5	1203.7	1199.4	1190.9	1188.8	1186.0	1186.0	1188.1	1193.8	1196.6
15°	1205.8	1207.9	1201.5	1192.3	1190.2	1188.1	1187.4	1190.2	1196.6	1201.5
17.5°	1213.6	1215.7	1205.8	1193.0	1190.2	1190.9	1190.2	1192.3	1202.2	1211.4
20°	1220.6	1222.1	1208.6	1193.0	1190.2	1190.9	1190.2	1194.5	1207.2	1219.9
22.5°	1222.8	1224.2	1211.4	1198.0	1195.9	1196.6	1195.9	1200.1	1212.2	1224.9
25°	1223.5	1225.6	1215.7	1205.1	1208.6	1210.0	1208.6	1209.3	1218.5	1229.8
27.5°	1234.1	1236.9	1227.7	1218.5	1220.6	1219.9	1222.1	1224.2	1231.3	1242.6
30°	1256.0	1258.1	1250.4	1241.2	1239.7	1234.8	1241.2	1248.2	1256.0	1265.9
32.5°	1292.1	1296.4	1286.5	1276.5	1270.2	1267.3	1272.3	1284.3	1294.9	1305.6
35°	1352.3	1355.1	1345.9	1327.5	1316.2	1316.2	1320.4	1336.0	1353.0	1366.4
37.5°	1437.2	1440.7	1424.4	1402.5	1385.5	1385.5	1391.2	1407.5	1432.9	1452.0
40°	1540.5	1545.4	1524.9	1502.3	1486.0	1483.2	1490.2	1508.6	1532.7	1556.8
42.5°	1665.0	1670.7	1643.8	1624.0	1611.2	1611.2	1614.8	1631.8	1653.7	1683.4
45°	1824.2	1834.1	1797.4	1777.5	1765.5	1768.3	1770.5	1785.3	1805.1	1839.1
47.5°	2013.9	2023.8	1984.9	1964.3	1962.2	1975.7	1967.2	1977.8	1988.4	2027.3
50°	2229.0	2246.0	2219.1	2217.7	2221.9	2246.7	2226.9	2232.5	2220.5	2245.3
52.5°	2492.2	2517.0	2512.0	2520.5	2567.9	2618.9	2573.6	2553.8	2508.5	2516.3
55°	2811.4	2848.9	2855.9	2906.9	3014.5	3118.5	3022.2	2942.3	2846.0	2828.4
57.5°	3174.4	3204.1	3238.1	3342.1	3543.0	3727.7	3543.0	3366.1	3214.7	3178.6
60°	3565.0	3601.8	3634.3	3787.9	4086.5	4346.2	4080.8	3799.9	3599.7	3550.8
62.5°	3984.6	4032.0	4054.7	4225.2	4573.3	4883.3	4578.3	4237.9	4015.7	3963.4
65°	4387.2	4426.2	4451.6	4633.5	4966.1	5276.7	4988.7	4653.3	4424.7	4356.1
67.5°	4574.8	4596.0	4658.3	4864.2	5215.2	5569.7	5274.6	4886.1	4630.7	4510.4
70°	4300.2	4257.0	4407.0	4736.8	5244.9	5749.4	5312.8	4726.9	4414.1	4218.8
72.5°	3323.0	3248.7	3509.1	4073.1	4905.2	5634.8	4939.2	4104.9	3671.1	3274.9
75°	1808.0	1723.8	2083.2	2796.5	3911.7	4884.0	4001.6	2876.5	2319.6	1794.5
77.5°	510.2	478.4	768.5	1353.0	2352.8	3429.1	2443.4	1382.7	911.4	540.6
80°	156.4	151.4	205.2	407.6	999.2	1642.4	960.2	412.5	261.1	164.9
82.5°	92.7	84.9	101.9	148.6	254.7	515.9	247.7	155.0	124.5	83.5
85°	53.1	49.5	60.1	72.2	85.6	109.7	71.5	73.6	66.5	44.6
87.5°	21.9	19.8	23.4	22.6	19.8	25.5	19.1	22.6	26.9	17.7
90°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0

(END C

90°
1241.9
1237.6
1222.1
1205.1
1197.3
1197.3
1202.2
1211.4
1220.6
1224.9
1229.1
1239.7
1263.8
1301.3
1361.5
1445.0
1549.0
1681.3
1837.7
2016.0
2230.4
2490.1
2800.8
3153.1
3508.4
3920.9
4322.1
4511.8
4265.5
3373.2
1911.3
600.8
174.1
90.6
46.7
16.3
0.0

OF REPORT)