

Scaled data based on original data using
LM-79-08 Approved Method: Electrical and Photometric Measurements of Solid-
State Lighting Products

Test Report Prepared for
Cooper Lighting Solutions
(formerly Eaton)

Brand: STREETWORKS

Report Number: P945240

Luminaire Tested: **GLAN-SB1B-730-U-SLR-HSS**

Issue Date: 1/21/2025

Test Information

Test Method: LM-79-08
Report Number: P945240
TEST IS SCALED FROM IESNA LM-79-08 TEST DATA (G2-2411-289-9)
Test Lab: INNOVATION CENTER
Issue Date: 1/21/2025
Manufacturer: COOPER LIGHTING SOLUTIONS (FORMERLY EATON)
Product Line: STREETWORKS
Catalog Number: GLAN-SB1B-730-U-SLR-HSS
Description: GALLEON AREA AND ROADWAY HIGH DENSITY LED LUMINAIRE
(1) 70 CRI, 3000K, 450mA LIGHTSQUARE WITH 26 LEDS AND SPILL LIGHT
ELIMINATOR RIGHT OPTICS WITH HOUSE SIDE SHIELD
Light Source: -
Ballast/Driver: -

Summary

Lumens per Lamp: N/A
Luminaire Lumens: 4299 lumens
Efficiency: N/A
Efficacy: 108.0 lumens/watt
Luminous Opening: Rectangular (W 0.5' x L: 0.5' x H: 0')
IES Classification: Type IV - Short
BUG Rating: B1 - U0 - G2


Input Watts (W): 39.8
Input Voltage (V): NR
Input Current (Ain): NR
Voltage Rise (V): NR
Power Factor: NR
Total Harmonic Distortion (THDi): NR
Frequency (hertz): 60
Stabilization Time: NR
Operation Time: NR
Ambient Temperature (°C): NR
Test Distance: 24 FT



REPORT NUMBER: P945240
CATALOG NUMBER: GLAN-SB1B-730-U-SLR-HSS


Iso-Footcandle Lines of Horizontal Illumination

× Max cd
- - - 1/2 Max cd



Based on 25 foot mounting height. Maximum calculated value = 1.3 fc
Type IV - Short - N/A

REPORT NUMBER: P945240
CATALOG NUMBER: GLAN-SB1B-730-U-SLR-HSS



REPORT NUMBER: P945240

CATALOG NUMBER: GLAN-SB1B-730-U-SLR-HSS


FLUX DISTRIBUTION:

		Downward	Upward	Total
House Side	Lumens	602.0	0.0	602.0
	% Fixture	14.0	0.0	14.0
Street Side	Lumens	3697.0	0.0	3697.0
	% Fixture	86.0	0.0	86.0
Total	Lumens	4299.0	0.0	4299.0
	% Fixture	100.0	0.0	100.0

ZONAL LUMENS:

Zone	Lumens	% Fixture
0°-10°	58.6	1.4
10°-20°	175.7	4.1
20°-30°	258.8	6.0
30°-40°	332.5	7.7
40°-50°	537.8	12.5
50°-60°	943.0	21.9
60°-70°	1180.0	27.4
70°-80°	689.5	16.0
80°-90°	123.0	2.9
90°-100°	0.0	0.0
100°-110°	0.0	0.0
110°-120°	0.0	0.0
120°-130°	0.0	0.0
130°-140°	0.0	0.0
140°-150°	0.0	0.0
150°-160°	0.0	0.0
160°-170°	0.0	0.0
170°-180°	0.0	0.0
0°-90°	4299.0	100.0
0°-180°	4299.0	100.0

Coefficient of Utilization



REPORT NUMBER: P945240


CATALOG NUMBER: GLAN-SB1B-730-U-SLR-HSS

LUMINAIRE CLASSIFICATION SYSTEM LUMEN TABLE AND BUG RATING:

Zone		Lumens	% Fixture	Zone Rating/Lumen Limit		
				B	U	G
FL	(0°-30°)	335.3	7.8			
FM	(30°-60°)	1506.8	35.0			
FH	(60°-80°)	1736.6	40.4			G1/1800
FVH	(80°-90°)	118.3	2.8			G2/225
BL	(0°-30°)	157.8	3.7	B1/500		
BM	(30°-60°)	306.6	7.1	B1/1000		
BH	(60°-80°)	132.9	3.1	B1/500		G1/500
BVH	(80°-90°)	4.7	0.1			G0/10
UL	(90°-100°)	0.0	0.0		U0/0	
UH	(100°-180°)	0.0	0.0		U0/0	

BUG Rating: B1-U0-G2

Type IV Short



REPORT NUMBER: P945240

CATALOG NUMBER: GLAN-SB1B-730-U-SLR-HSS

CANDELA DISTRIBUTION (FULL):

	0°	5°	15°	25°	35°	45°	55°	65°	75°	85°
0°	595.3	595.3	595.3	595.3	595.3	595.3	595.3	595.3	595.3	595.3
2.5°	672.6	661.0	654.2	637.3	620.4	606.8	588.5	576.3	561.8	547.9
5°	749.6	730.9	708.4	677.6	649.5	620.7	592.9	565.4	536.3	509.7
7.5°	814.7	787.8	748.1	707.2	671.4	636.7	604.2	567.7	532.5	490.7
10°	864.5	830.1	778.0	724.4	683.2	648.3	616.6	585.8	550.3	499.9
12.5°	894.7	858.0	796.1	733.3	686.2	647.1	622.5	608.9	595.0	544.9
15°	916.9	877.2	808.8	739.5	679.4	631.4	613.3	627.0	643.0	611.0
17.5°	940.0	898.2	825.4	742.2	661.0	600.9	593.2	628.4	665.5	664.0
20°	961.9	920.5	839.9	740.4	631.4	563.9	570.7	615.7	658.7	676.7
22.5°	987.1	943.3	853.8	733.6	592.9	529.2	550.6	595.6	633.2	654.5
25°	1017.9	972.0	873.4	723.5	551.4	500.5	530.1	572.2	602.7	617.5
27.5°	1051.1	1006.3	899.4	718.2	518.0	480.1	507.0	544.3	571.6	581.9
30°	1092.2	1046.3	930.2	712.3	496.1	468.2	483.0	512.1	538.7	549.1
32.5°	1137.2	1090.7	959.8	698.0	482.7	459.3	459.6	478.0	502.3	514.7
35°	1193.5	1144.1	991.5	666.9	472.1	449.0	436.8	445.7	465.9	480.7
37.5°	1273.8	1213.9	1030.3	622.5	456.4	433.0	412.8	414.9	430.3	446.6
40°	1384.5	1307.8	1075.9	576.3	433.9	410.5	386.5	385.6	396.8	412.8
42.5°	1534.4	1431.9	1130.7	532.2	412.2	383.2	358.6	357.2	366.0	380.0
45°	1732.2	1590.7	1198.0	494.3	395.4	356.6	332.3	331.7	339.1	351.2
47.5°	1985.4	1811.3	1265.2	468.5	386.5	335.5	310.7	311.9	318.4	329.3
50°	2313.3	2098.9	1285.6	455.5	386.5	324.3	291.4	297.3	302.7	311.0
52.5°	2706.3	2374.9	1218.1	443.6	388.9	325.8	275.1	287.9	291.7	298.8
55°	3070.5	2510.2	1047.2	427.4	389.4	335.0	261.2	280.2	287.3	289.9
57.5°	3282.0	2463.7	846.7	399.8	387.1	341.2	252.3	270.7	284.3	286.1
60°	3241.7	2300.5	623.4	378.8	369.6	338.8	249.7	256.2	277.8	280.5
62.5°	2931.4	2026.9	432.7	362.5	331.1	328.4	248.8	233.4	263.6	270.1
65°	2356.2	1595.7	305.6	312.1	290.2	305.9	244.0	209.7	246.4	255.3
67.5°	1709.4	1079.8	220.6	252.9	263.0	269.5	233.4	192.5	226.9	238.7
70°	1097.0	583.1	154.9	167.0	221.5	228.9	215.0	177.1	207.0	220.6
72.5°	779.8	344.4	111.4	117.0	178.0	190.7	189.2	159.9	183.9	200.5
75°	538.1	189.8	75.2	83.5	129.1	154.9	146.0	137.4	155.8	172.7
77.5°	337.3	85.0	45.0	58.0	84.7	121.7	100.1	106.3	121.4	137.1
80°	187.8	32.9	25.2	38.5	46.2	88.6	55.4	68.4	89.4	100.7
82.5°	40.9	4.1	11.3	16.6	18.1	51.5	29.3	39.7	56.3	55.4
85°	0.0	0.0	2.1	2.4	1.2	22.2	10.7	13.0	18.4	17.2
87.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.6
90°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0

REPORT NUMBER: P945240

CATALOG NUMBER: GLAN-SB1B-730-U-SLR-HSS

CANDELA DISTRIBUTION (continued):

90°		95°	105°	115°	125°	135°	145°	155°	165°	175°	180°
595.3	0°	595.3	595.3	595.3	595.3	595.3	595.3	595.3	595.3	595.3	595.3
535.5	2.5°	533.1	518.6	507.9	502.6	498.1	502.3	504.7	504.7	514.7	520.6
493.4	5°	483.0	457.0	437.1	423.8	415.8	418.5	421.4	424.7	437.4	446.0
468.5	7.5°	448.4	408.4	378.2	359.5	349.8	351.2	353.3	356.0	368.4	377.0
472.1	10°	441.9	384.4	341.8	317.2	305.3	303.3	302.1	301.2	308.6	315.1
512.4	12.5°	468.5	385.6	326.1	296.2	281.6	275.4	268.3	262.7	263.9	268.0
573.4	15°	516.2	400.7	321.0	285.2	267.1	256.8	248.5	241.7	240.2	241.7
626.7	17.5°	570.7	421.1	320.4	275.7	253.2	242.6	235.7	229.5	227.4	227.7
656.6	20°	606.8	437.4	318.7	265.1	239.9	230.4	224.5	218.3	216.2	216.8
648.3	22.5°	610.4	446.0	316.0	253.2	226.6	218.6	212.6	207.0	206.7	206.7
617.2	25°	591.1	446.0	310.4	242.6	213.8	206.7	201.4	194.6	195.8	196.4
581.9	27.5°	561.2	435.3	299.7	234.0	202.9	195.5	190.1	183.9	185.4	186.3
549.1	30°	531.6	421.7	287.0	224.2	192.5	183.9	180.1	174.7	175.3	176.5
516.5	32.5°	504.1	407.2	271.9	216.2	182.1	173.5	170.6	164.7	165.6	166.7
484.5	35°	476.8	391.2	254.1	206.7	172.7	164.1	161.7	154.9	155.5	157.3
452.5	37.5°	447.5	374.3	239.6	197.2	163.5	154.6	152.2	145.1	145.7	147.8
419.4	40°	416.7	357.8	225.4	187.2	153.7	144.8	142.7	135.0	135.6	138.0
386.8	42.5°	385.6	339.7	214.4	174.1	143.6	134.2	132.1	125.0	125.9	128.5
358.3	45°	356.9	318.1	207.3	159.6	134.2	123.5	121.4	114.9	116.7	119.6
334.4	47.5°	332.3	295.9	204.3	147.5	124.1	112.5	110.8	105.4	108.4	111.7
313.9	50°	311.3	274.5	200.5	135.0	114.6	103.1	101.3	97.7	101.6	104.8
300.0	52.5°	296.2	250.3	192.2	123.8	106.3	95.1	94.5	92.7	96.3	99.2
289.6	55°	283.1	225.1	178.9	114.0	98.9	88.3	88.8	88.0	90.9	93.3
283.4	57.5°	271.3	203.2	162.0	106.3	90.9	82.3	84.1	82.9	84.4	85.9
276.9	60°	257.1	181.0	141.9	97.7	81.4	76.4	78.5	75.2	74.9	75.5
265.1	62.5°	236.0	151.0	120.8	87.1	73.2	69.9	70.8	64.6	59.8	59.8
247.6	65°	206.7	121.4	101.3	75.2	63.7	61.0	60.4	51.5	45.0	44.4
228.6	67.5°	172.7	99.8	84.1	63.4	53.0	51.2	51.8	45.3	38.8	38.2
209.7	70°	140.7	82.6	67.8	50.6	40.9	42.6	45.3	38.8	32.6	31.7
187.5	72.5°	114.3	65.7	53.0	38.8	30.2	35.2	38.5	31.7	25.8	25.2
159.9	75°	88.3	48.3	37.9	26.4	21.9	27.2	30.2	23.1	18.4	17.5
123.8	77.5°	58.9	29.9	21.3	16.6	13.0	18.7	20.1	12.1	10.7	10.4
90.0	80°	35.8	13.9	9.2	8.0	4.4	6.8	8.0	5.0	5.6	5.9
48.0	82.5°	18.1	3.9	1.5	0.3	0.0	0.0	2.4	1.2	2.4	3.0
13.0	85°	1.5	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.6	1.5
0.0	87.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
0.0	90°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0

REPORT NUMBER: P945240

CATALOG NUMBER: GLAN-SB1B-730-U-SLR-HSS

CANDELA DISTRIBUTION (continued):

185°		195°	205°	215°	225°	235°	245°	255°	265°	270°	275°
595.3	0°	595.3	595.3	595.3	595.3	595.3	595.3	595.3	595.3	595.3	595.3
523.0	2.5°	539.6	552.0	563.9	582.8	602.4	621.6	641.2	660.1	666.9	672.0
451.6	5°	477.4	500.8	528.0	565.7	605.9	647.4	689.5	728.0	745.4	757.3
384.4	7.5°	413.1	443.6	482.7	539.3	602.4	668.4	734.5	795.2	823.3	846.1
321.0	10°	349.5	382.6	432.1	496.7	581.9	676.7	767.9	851.4	887.9	916.6
275.4	12.5°	293.5	324.6	376.4	447.8	550.0	670.2	787.2	887.6	930.5	962.8
242.8	15°	254.1	276.0	321.9	398.9	512.1	649.2	788.4	904.8	951.8	985.6
229.2	17.5°	232.2	239.6	269.5	349.2	470.0	621.6	777.4	910.7	961.0	992.4
217.1	20°	220.3	221.5	229.8	284.6	416.1	595.9	767.0	916.6	969.6	996.0
208.5	22.5°	210.9	210.9	212.9	232.8	346.5	565.1	763.8	927.0	981.5	997.8
198.7	25°	202.3	202.3	202.9	208.2	274.5	518.0	761.7	943.0	997.8	1002.2
188.9	27.5°	193.4	193.7	193.7	196.6	221.2	454.0	752.8	963.7	1017.3	1008.1
179.5	30°	184.5	185.1	185.1	187.2	195.8	379.1	735.4	988.6	1042.8	1015.8
170.0	32.5°	175.6	176.2	176.2	178.0	184.2	302.7	713.4	1011.4	1068.5	1019.1
160.8	35°	166.4	167.3	166.7	169.1	175.6	240.8	685.6	1034.2	1096.4	1029.4
151.9	37.5°	157.3	157.9	157.6	159.9	167.3	207.9	653.3	1051.4	1134.3	1052.5
142.5	40°	148.1	147.8	147.8	150.4	158.4	198.4	612.7	1078.6	1188.8	1093.1
133.0	42.5°	138.6	138.6	138.0	141.0	150.7	191.3	574.0	1127.5	1268.1	1157.7
124.1	45°	130.0	129.7	128.5	131.2	143.3	178.9	560.3	1218.7	1385.4	1262.2
115.2	47.5°	121.7	121.4	118.5	120.8	134.5	167.6	611.3	1367.9	1548.0	1415.9
108.1	50°	114.3	114.6	109.0	111.1	125.6	159.0	721.7	1561.6	1763.9	1622.9
102.2	52.5°	107.5	107.5	100.1	101.3	114.6	151.3	826.9	1771.6	2048.8	1911.7
96.0	55°	100.7	100.1	91.8	92.4	103.7	140.4	842.6	1976.5	2437.4	2346.1
89.1	57.5°	93.0	91.8	84.1	84.1	93.6	132.4	730.3	2134.1	2919.5	2984.7
76.4	60°	83.5	82.6	77.6	76.1	85.6	139.5	515.3	2152.5	3230.5	3833.7
60.7	62.5°	71.4	72.6	69.9	67.8	77.9	144.8	305.3	2004.7	3155.2	4103.8
47.1	65°	56.3	61.0	60.4	58.9	85.6	122.0	180.4	1721.0	2924.5	3885.9
41.2	67.5°	48.0	51.2	50.3	50.3	89.7	92.7	113.4	1344.5	2607.1	3627.3
34.4	70°	40.9	44.1	40.9	40.9	67.8	56.3	78.5	938.8	2264.4	3341.2
27.5	72.5°	33.8	37.0	33.5	31.1	54.2	42.1	57.5	586.7	1939.2	3043.3
19.5	75°	25.8	29.6	27.0	24.0	35.8	31.4	43.5	340.9	1606.6	2603.8
11.8	77.5°	16.3	21.3	20.1	16.9	26.4	22.8	31.4	202.9	1239.7	2034.6
7.1	80°	10.1	11.0	11.3	10.7	15.1	15.4	21.3	115.5	848.5	1418.0
4.4	82.5°	6.5	6.5	5.0	5.6	7.4	8.9	12.1	43.5	498.7	863.3
2.7	85°	4.7	4.1	2.7	2.7	3.6	4.4	4.7	13.3	202.3	340.9
1.2	87.5°	2.4	2.1	0.9	1.2	1.8	1.5	1.2	0.6	50.9	109.0
0.0	90°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0

REPORT NUMBER: P945240

CATALOG NUMBER: GLAN-SB1B-730-U-SLR-HSS

CANDELA DISTRIBUTION (continued):

285°		295°	305°	315°	325°	335°	345°	355°	360°
595.3	0°	595.3	595.3	595.3	595.3	595.3	595.3	595.3	595.3
683.2	2.5°	689.2	698.3	698.9	698.9	690.9	690.6	674.3	672.6
783.9	5°	811.5	817.4	818.9	815.9	799.9	788.1	756.4	749.6
886.7	7.5°	923.4	935.3	935.3	928.2	902.1	877.8	831.9	814.7
971.7	10°	1012.9	1026.5	1023.5	1009.0	976.1	942.7	887.0	864.5
1023.2	12.5°	1056.4	1070.3	1062.6	1046.0	1014.0	978.8	920.2	894.7
1038.0	15°	1055.5	1051.7	1043.7	1041.6	1026.2	999.5	944.7	916.9
1028.8	17.5°	1017.9	985.3	979.1	999.8	1019.4	1012.9	966.1	940.0
1006.9	20°	958.4	901.5	895.9	935.6	991.2	1019.7	985.9	961.9
975.2	22.5°	895.6	834.3	821.2	865.1	948.9	1021.7	1011.1	987.1
940.3	25°	836.0	774.4	761.4	802.3	901.8	1018.2	1038.3	1017.9
906.8	27.5°	786.3	726.8	714.6	755.5	856.5	1008.1	1065.6	1051.1
873.7	30°	747.8	692.7	683.8	723.2	817.4	995.7	1100.2	1092.2
842.9	32.5°	725.3	685.0	688.3	720.5	796.4	982.1	1133.4	1137.2
827.8	35°	747.5	749.3	777.7	791.0	815.9	980.0	1178.4	1193.5
845.8	37.5°	858.0	919.6	978.5	967.5	911.6	1004.0	1245.6	1273.8
924.6	40°	1046.0	1172.5	1268.1	1226.4	1085.4	1077.4	1342.5	1384.5
1064.4	42.5°	1275.8	1490.3	1647.8	1535.9	1309.6	1205.9	1480.8	1534.4
1233.5	45°	1518.4	1882.1	2130.3	1897.5	1548.6	1386.0	1690.2	1732.2
1391.9	47.5°	1774.0	2358.3	2679.3	2298.5	1770.1	1591.0	1975.7	1985.4
1542.1	50°	2053.5	2880.4	3239.1	2699.2	1984.0	1825.8	2324.5	2313.3
1717.1	52.5°	2319.8	3417.3	3786.9	3101.6	2171.7	2117.2	2729.4	2706.3
1956.4	55°	2573.9	3954.0	4338.1	3488.4	2348.8	2502.2	3210.3	3070.5
2301.4	57.5°	2868.6	4436.4	4906.1	3877.0	2596.4	3002.1	3748.2	3282.0
2962.2	60°	3304.2	4984.6	5548.5	4409.5	3067.3	3527.5	3941.0	3241.7
3753.5	62.5°	3860.4	5488.7	6015.5	4931.3	3540.3	3626.4	3656.9	2931.4
3592.1	65°	3968.5	5616.3	6041.9	5070.8	3479.2	3076.2	2985.6	2356.2
3208.6	67.5°	3681.8	5385.6	5673.5	4811.1	3077.7	2377.2	2240.4	1709.4
2956.8	70°	3360.2	4945.8	5031.4	4369.5	2706.9	1748.5	1513.1	1097.0
2784.5	72.5°	3030.6	4359.1	4182.0	3794.6	2379.0	1273.2	1091.3	779.8
2538.9	75°	2639.0	3587.6	3294.1	3152.9	1969.7	999.2	789.6	538.1
2183.9	77.5°	2113.4	2525.3	2446.8	2443.9	1480.2	730.0	526.9	337.3
1706.2	80°	1490.9	1638.9	1598.9	1840.6	993.0	529.5	317.2	187.8
1187.6	82.5°	721.7	906.2	930.2	1096.1	483.0	311.6	73.2	40.9
464.4	85°	282.5	437.1	368.7	416.1	135.6	86.8	1.8	0.0
76.4	87.5°	31.7	50.6	46.5	36.7	16.6	3.6	0.0	0.0
0.0	90°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0

(END OF REPORT)