

Scaled data based on original data using  
LM-79-08 Approved Method: Electrical and Photometric Measurements of Solid-  
State Lighting Products

Test Report Prepared for  
Cooper Lighting Solutions  
(formerly Eaton)

Brand: STREETWORKS

Report Number: P845931

Luminaire Tested: **GLAN-SB1B-827-U-5WQ**

Issue Date: 6/26/2024

**Test Information**

Test Method: LM-79-08  
Report Number: P845931  
TEST IS SCALED FROM IESNA LM-79-08 TEST DATA (G2-2405-108-1)  
Test Lab: INNOVATION CENTER  
Issue Date: 6/26/2024  
Manufacturer: COOPER LIGHTING SOLUTIONS (FORMERLY EATON)  
Product Line: STREETWORKS  
Catalog Number: GLAN-SB1B-827-U-5WQ  
Description: GALLEON AREA AND ROADWAY HIGH DENSITY LED LUMINAIRE  
(1) 80 CRI, 2700K, 450mA LIGHTSQUARE WITH 26 LEDS AND TYPE V WIDE OPTICS  
Light Source: -  
Ballast/Driver: -

**Summary**

Lumens per Lamp: N/A  
Luminaire Lumens: 4543 lumens  
Efficiency: N/A  
Efficacy: 114.1 lumens/watt  
Luminous Opening: Rectangular (W 0.5' x L: 0.5' x H: 0')  
IES Classification: Type V - Short  
BUG Rating: B3 - U0 - G1


Input Watts (W): 39.8  
Input Voltage (V): NR  
Input Current (Ain): NR  
Voltage Rise (V): NR  
Power Factor: NR  
Total Harmonic Distortion (THDi): NR  
Frequency (hertz): 60  
Stabilization Time: NR  
Operation Time: NR  
Ambient Temperature (°C): NR  
Test Distance: 24 FT



REPORT NUMBER: P845931  
 CATALOG NUMBER: GLAN-SB1B-827-U-5WQ

### Iso-Footcandle Lines of Horizontal Illumination


× Max cd  
 - - - 1/2 Max cd



Based on 25 foot mounting height. Maximum calculated value = 0.7 fc  
 Type V - Short - N/A

REPORT NUMBER: P845931  
CATALOG NUMBER: GLAN-SB1B-827-U-5WQ

### Luminous Intensity Polar Plot



— Vertical Plane Through 45-Deg Lateral    - - - Horizontal Cone Through 70-Deg Vertical

REPORT NUMBER: P845931  
 CATALOG NUMBER: GLAN-SB1B-827-U-5WQ

**FLUX DISTRIBUTION:**

		Downward	Upward	Total
<b>House Side</b>	Lumens	2271.5	0.0	2271.5
	% Fixture	50.0	0.0	50.0
<b>Street Side</b>	Lumens	2271.5	0.0	2271.5
	% Fixture	50.0	0.0	50.0
<b>Total</b>	Lumens	4543.0	0.0	4543.0
	% Fixture	100.0	0.0	100.0

**ZONAL LUMENS:**

Zone	Lumens	% Fixture
0°-10°	38.6	0.8
10°-20°	113.2	2.5
20°-30°	188.4	4.1
30°-40°	284.9	6.3
40°-50°	473.4	10.4
50°-60°	893.3	19.7
60°-70°	1508.3	33.2
70°-80°	991.1	21.8
80°-90°	51.9	1.1
90°-100°	0.0	0.0
100°-110°	0.0	0.0
110°-120°	0.0	0.0
120°-130°	0.0	0.0
130°-140°	0.0	0.0
140°-150°	0.0	0.0
150°-160°	0.0	0.0
160°-170°	0.0	0.0
170°-180°	0.0	0.0
0°-90°	4543.0	100.0
0°-180°	4543.0	100.0

**Coefficient of Utilization**




REPORT NUMBER: P845931  
 CATALOG NUMBER: GLAN-SB1B-827-U-5WQ

**LUMINAIRE CLASSIFICATION SYSTEM LUMEN TABLE AND BUG RATING:**

Zone	Lumens	% Fixture	Zone Rating/Lumen Limit		
			B	U	G
FL (0°-30°)	170.1	3.7			
FM (30°-60°)	825.8	18.2			
FH (60°-80°)	1249.7	27.5			G1/1800
FVH (80°-90°)	26.0	0.6			G1/100
BL (0°-30°)	170.1	3.7	B1/500		
BM (30°-60°)	825.8	18.2	B1/1000		
BH (60°-80°)	1249.7	27.5	B3/2500		G1/1800
BVH (80°-90°)	26.0	0.6			G1/100
UL (90°-100°)	0.0	0.0		U0/0	
UH (100°-180°)	0.0	0.0		U0/0	

**BUG Rating: B3-U0-G1**

Type V Short



REPORT NUMBER: P845931  
 CATALOG NUMBER: GLAN-SB1B-827-U-5WQ

**CANDELA DISTRIBUTION (FULL):**

	0°	5°	15°	25°	35°	45°	55°	65°	75°	85°
0°	414.4	414.4	414.4	414.4	414.4	414.4	414.4	414.4	414.4	414.4
2.5°	411.8	413.0	412.5	411.6	411.6	410.9	411.6	412.1	412.8	413.2
5°	406.4	407.3	407.1	406.4	406.6	405.9	406.4	407.1	407.6	407.8
7.5°	401.7	402.6	402.1	401.0	401.0	400.2	400.5	401.2	401.9	402.1
10°	400.5	401.4	400.0	398.1	397.4	396.5	396.7	397.4	398.8	399.5
12.5°	401.0	401.7	400.2	397.4	396.7	395.8	395.8	396.5	398.4	399.3
15°	402.4	403.1	401.0	397.9	397.2	396.5	396.2	397.2	399.3	401.0
17.5°	405.0	405.7	402.4	398.1	397.2	397.4	397.2	397.9	401.2	404.3
20°	407.3	407.8	403.3	398.1	397.2	397.4	397.2	398.6	402.8	407.1
22.5°	408.0	408.5	404.3	399.8	399.1	399.3	399.1	400.5	404.5	408.7
25°	408.3	409.0	405.7	402.1	403.3	403.8	403.3	403.6	406.6	410.4
27.5°	411.8	412.8	409.7	406.6	407.3	407.1	407.8	408.5	410.9	414.6
30°	419.1	419.8	417.2	414.2	413.7	412.1	414.2	416.5	419.1	422.4
32.5°	431.2	432.6	429.3	426.0	423.9	422.9	424.6	428.6	432.1	435.7
35°	451.2	452.2	449.1	443.0	439.2	439.2	440.6	445.8	451.5	456.0
37.5°	479.6	480.8	475.3	468.0	462.3	462.3	464.2	469.7	478.2	484.5
40°	514.1	515.7	508.9	501.3	495.9	494.9	497.3	503.4	511.5	519.5
42.5°	555.6	557.5	548.5	541.9	537.7	537.7	538.9	544.5	551.8	561.8
45°	608.8	612.1	599.8	593.2	589.2	590.1	590.8	595.8	602.4	613.7
47.5°	672.0	675.3	662.4	655.5	654.8	659.3	656.4	660.0	663.5	676.5
50°	743.8	749.5	740.5	740.0	741.5	749.7	743.1	745.0	741.0	749.2
52.5°	831.7	839.9	838.3	841.1	856.9	873.9	858.8	852.2	837.1	839.7
55°	938.2	950.7	953.0	970.0	1005.9	1040.6	1008.5	981.8	949.7	943.8
57.5°	1059.3	1069.2	1080.5	1115.3	1182.3	1243.9	1182.3	1123.3	1072.8	1060.7
60°	1189.6	1201.9	1212.8	1264.0	1363.7	1450.3	1361.8	1268.0	1201.2	1184.9
62.5°	1329.7	1345.5	1353.0	1409.9	1526.1	1629.6	1527.8	1414.2	1340.1	1322.6
65°	1464.0	1477.0	1485.5	1546.2	1657.2	1760.8	1664.7	1552.8	1476.5	1453.6
67.5°	1526.6	1533.7	1554.5	1623.2	1740.3	1858.6	1760.1	1630.5	1545.3	1505.1
70°	1435.0	1420.6	1470.6	1580.7	1750.2	1918.6	1772.9	1577.4	1473.0	1407.8
72.5°	1108.9	1084.1	1171.0	1359.2	1636.9	1880.3	1648.2	1369.8	1225.1	1092.8
75°	603.3	575.2	695.2	933.2	1305.3	1629.8	1335.3	959.9	774.0	598.8
77.5°	170.3	159.6	256.4	451.5	785.1	1144.3	815.4	461.4	304.1	180.4
80°	52.2	50.5	68.5	136.0	333.4	548.1	320.4	137.7	87.1	55.0
82.5°	30.9	28.3	34.0	49.6	85.0	172.1	82.6	51.7	41.6	27.9
85°	17.7	16.5	20.1	24.1	28.6	36.6	23.8	24.6	22.2	14.9
87.5°	7.3	6.6	7.8	7.6	6.6	8.5	6.4	7.6	9.0	5.9
90°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0

(END C

90°
414.4
413.0
407.8
402.1
399.5
399.5
401.2
404.3
407.3
408.7
410.2
413.7
421.7
434.2
454.3
482.2
516.9
561.1
613.2
672.7
744.3
831.0
934.6
1052.2
1170.7
1308.4
1442.3
1505.6
1423.4
1125.6
637.8
200.5
58.1
30.2
15.6
5.4
0.0

OF REPORT)