

Scaled data based on original data using
LM-79-08 Approved Method: Electrical and Photometric Measurements of Solid-
State Lighting Products

Test Report Prepared for
Cooper Lighting Solutions
(formerly Eaton)

Brand: STREETWORKS

Report Number: P951307

Luminaire Tested: **GLAN-SB5C-730-U-SLL-HSS**

Issue Date: 1/21/2025

Test Information

Test Method: LM-79-08
Report Number: P951307
TEST IS SCALED FROM IESNA LM-79-08 TEST DATA (G2-2411-289-9)
Test Lab: INNOVATION CENTER
Issue Date: 1/21/2025
Manufacturer: COOPER LIGHTING SOLUTIONS (FORMERLY EATON)
Product Line: STREETWORKS
Catalog Number: GLAN-SB5C-730-U-SLL-HSS
Description: GALLEON AREA AND ROADWAY HIGH DENSITY LED LUMINAIRE
(5) 70 CRI, 3000K, 615mA LIGHTSQUARES WITH 26 LEDS EACH AND SPILL LIGHT
ELIMINATOR LEFT OPTICS WITH HOUSE SIDE SHIELD
Light Source: -
Ballast/Driver: -

Summary

Lumens per Lamp: N/A
Luminaire Lumens: 28872 lumens
Efficiency: N/A
Efficacy: 115.7 lumens/watt
Luminous Opening: Rectangular (W 1.5' x L: 1' x H: 0')
IES Classification: Type IV - Short
BUG Rating: B3 - U0 - G5


Input Watts (W): 249.5
Input Voltage (V): NR
Input Current (Ain): NR
Voltage Rise (V): NR
Power Factor: NR
Total Harmonic Distortion (THDi): NR
Frequency (hertz): 60
Stabilization Time: NR
Operation Time: NR
Ambient Temperature (°C): NR
Test Distance: 24 FT



REPORT NUMBER: P951307
 CATALOG NUMBER: GLAN-SB5C-730-U-SLL-HSS

Iso-Footcandle Lines of Horizontal Illumination


✕ Max cd
 - - - 1/2 Max cd



Based on 25 foot mounting height. Maximum calculated value = 10.5 fc
 Type IV - Short - N/A

REPORT NUMBER: P951307
CATALOG NUMBER: GLAN-SB5C-730-U-SLL-HSS

Luminous Intensity Polar Plot



— Vertical Plane Through 45-Deg Lateral - - - Horizontal Cone Through 65-Deg Vertical

REPORT NUMBER: P951307
 CATALOG NUMBER: GLAN-SB5C-730-U-SLL-HSS

FLUX DISTRIBUTION:

		Downward	Upward	Total
House Side	Lumens	5738.9	0.0	5738.9
	% Fixture	19.9	0.0	19.9
Street Side	Lumens	23133.1	0.0	23133.1
	% Fixture	80.1	0.0	80.1
Total	Lumens	28872.0	0.0	28872.0
	% Fixture	100.0	0.0	100.0

ZONAL LUMENS:

Zone	Lumens	% Fixture
0°-10°	393.6	1.4
10°-20°	1179.9	4.1
20°-30°	1738.2	6.0
30°-40°	2233.2	7.7
40°-50°	3611.7	12.5
50°-60°	6333.4	21.9
60°-70°	7924.9	27.4
70°-80°	4630.9	16.0
80°-90°	826.2	2.9
90°-100°	0.0	0.0
100°-110°	0.0	0.0
110°-120°	0.0	0.0
120°-130°	0.0	0.0
130°-140°	0.0	0.0
140°-150°	0.0	0.0
150°-160°	0.0	0.0
160°-170°	0.0	0.0
170°-180°	0.0	0.0
0°-90°	28872.0	100.0
0°-180°	28872.0	100.0

Coefficient of Utilization




REPORT NUMBER: P951307
 CATALOG NUMBER: GLAN-SB5C-730-U-SLL-HSS

LUMINAIRE CLASSIFICATION SYSTEM LUMEN TABLE AND BUG RATING:

Zone	Lumens	% Fixture	Zone Rating/Lumen Limit		
			B	U	G
FL (0°-30°)	1931.9	6.7			
FM (30°-60°)	9060.4	31.4			
FH (60°-80°)	11353.4	39.3			G4/12000
FVH (80°-90°)	787.5	2.7			G5
BL (0°-30°)	1379.9	4.8	B3/2500		
BM (30°-60°)	3117.9	10.8	B3/5000		
BH (60°-80°)	1202.4	4.2	B3/2500		G3/2500
BVH (80°-90°)	38.7	0.1			G1/100
UL (90°-100°)	0.0	0.0		U0/0	
UH (100°-180°)	0.0	0.0		U0/0	

BUG Rating: B3-U0-G5

Type IV Short



REPORT NUMBER: P951307
 CATALOG NUMBER: GLAN-SB5C-730-U-SLL-HSS

CANDELA DISTRIBUTION (FULL):

	0°	5°	15°	25°	35°	45°	55°	65°	75°	85°
0°	3997.8	3997.8	3997.8	3997.8	3997.8	3997.8	3997.8	3997.8	3997.8	3997.8
2.5°	4479.2	4513.0	4588.6	4628.4	4690.0	4694.0	4694.0	4640.3	4638.3	4528.9
5°	5006.3	5085.8	5264.8	5449.8	5489.6	5499.5	5479.6	5372.2	5292.7	5079.9
7.5°	5529.4	5682.5	5955.0	6201.6	6281.2	6281.2	6233.5	6058.4	5895.3	5587.0
10°	5963.0	6155.9	6525.8	6802.3	6893.8	6873.9	6776.5	6555.7	6330.9	5957.0
12.5°	6249.4	6466.2	6871.9	7094.7	7188.2	7136.5	7025.1	6810.3	6573.6	6179.8
15°	6392.6	6619.3	6971.4	7088.7	7062.9	7009.2	6995.2	6891.8	6712.8	6344.8
17.5°	6454.2	6665.1	6909.7	6836.1	6617.3	6575.6	6714.8	6846.1	6802.3	6488.1
20°	6511.9	6688.9	6762.5	6436.3	6054.5	6016.7	6283.2	6657.1	6848.1	6621.3
22.5°	6591.5	6700.9	6549.7	6014.7	5603.0	5515.4	5809.8	6372.7	6862.0	6790.4
25°	6700.9	6730.7	6315.0	5614.9	5201.2	5113.7	5388.1	6056.4	6838.1	6973.4
27.5°	6832.1	6770.5	6090.3	5280.7	4881.0	4799.4	5073.9	5752.1	6770.5	7156.3
30°	7003.2	6822.2	5867.5	5022.2	4652.2	4592.6	4857.1	5489.6	6686.9	7389.1
32.5°	7176.2	6844.1	5660.6	4871.0	4600.5	4622.4	4839.2	5348.4	6595.5	7611.8
35°	7363.2	6913.7	5559.2	5020.2	5032.1	5223.1	5312.6	5479.6	6581.5	7914.1
37.5°	7617.8	7068.8	5680.5	5762.1	6175.8	6571.6	6498.0	6122.1	6742.6	8365.6
40°	7983.8	7341.3	6209.6	7025.1	7874.4	8516.8	8236.4	7289.6	7235.9	9016.0
42.5°	8516.8	7774.9	7148.4	8568.5	10008.5	11066.7	10314.8	8795.3	8099.1	9944.9
45°	9304.4	8477.0	8284.1	10197.5	12640.0	14306.7	12743.4	10400.4	9308.4	11351.1
47.5°	10396.4	9509.3	9348.2	11914.0	15838.2	17994.3	15436.5	11888.1	10684.8	13268.5
50°	11846.4	10899.6	10356.6	13791.6	19344.8	21753.5	18127.6	13324.2	12262.1	15611.5
52.5°	13759.8	12838.9	11532.1	15579.7	22950.8	25433.1	20830.6	14585.2	14219.2	18330.4
55°	16369.3	15756.7	13139.2	17286.2	26554.9	29134.6	23428.2	15774.6	16804.9	21560.5
57.5°	19607.4	20044.9	15456.4	19265.3	29794.9	32949.4	26037.7	17437.4	20162.3	25172.5
60°	21695.8	25747.3	19893.8	22191.0	33476.5	37263.5	29613.9	20599.9	23690.7	26467.3
62.5°	21190.6	27561.3	25208.3	25926.3	36861.8	40400.1	33118.5	23776.3	24355.1	24559.9
65°	19641.2	26097.4	24124.3	26652.3	37719.0	40577.2	34055.3	23366.5	20659.5	20050.9
67.5°	17509.0	24361.0	21548.6	24727.0	36169.6	38102.9	32311.0	20669.5	15965.5	15046.6
70°	15207.7	22439.7	19858.0	22567.0	33216.0	33790.8	29345.4	18179.3	11742.9	10161.7
72.5°	13023.8	20438.8	18700.4	20353.2	29275.8	28086.4	25484.8	15977.5	8550.6	7329.4
75°	10790.2	17487.1	17051.5	17723.8	24094.5	22123.4	21174.7	13228.7	6710.8	5302.6
77.5°	8325.9	13664.3	14666.7	14193.4	16960.0	16432.9	16413.1	9940.9	4902.8	3538.4
80°	5698.4	9523.2	11458.5	10012.5	11007.0	10738.5	12361.5	6669.0	3556.3	2130.2
82.5°	3349.4	5797.9	7975.8	4847.1	6086.3	6247.4	7361.2	3244.0	2092.4	491.3
85°	1358.5	2289.3	3118.7	1897.5	2935.7	2476.3	2794.5	911.0	582.8	11.9
87.5°	342.1	731.9	513.2	212.8	340.1	312.3	246.6	111.4	23.9	0.0
90°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0

REPORT NUMBER: P951307
 CATALOG NUMBER: GLAN-SB5C-730-U-SLL-HSS

CANDELA DISTRIBUTION (continued):

90°		95°	105°	115°	125°	135°	145°	155°	165°	175°	180°
3997.8	0°	3997.8	3997.8	3997.8	3997.8	3997.8	3997.8	3997.8	3997.8	3997.8	3997.8
4517.0	2.5°	4439.4	4393.7	4280.3	4166.9	4075.4	3952.1	3870.6	3773.1	3679.6	3596.1
5034.1	5°	4908.8	4757.6	4550.8	4361.8	4168.9	3981.9	3797.0	3602.0	3423.0	3313.6
5471.7	7.5°	5290.7	5024.2	4749.7	4509.0	4276.3	4057.5	3812.9	3576.2	3295.7	3146.6
5805.8	10°	5575.1	5225.0	4865.0	4588.6	4353.9	4141.1	3934.2	3695.5	3357.4	3170.4
6008.7	12.5°	5762.1	5346.4	4924.7	4608.5	4345.9	4180.8	4089.3	3995.9	3659.7	3440.9
6157.9	15°	5891.4	5431.9	4966.5	4562.7	4240.5	4119.2	4210.7	4318.1	4103.3	3850.7
6313.0	17.5°	6032.6	5543.3	4984.4	4439.4	4035.6	3983.9	4220.6	4469.2	4459.3	4208.7
6460.2	20°	6181.7	5640.7	4972.4	4240.5	3787.0	3832.8	4135.1	4423.5	4544.8	4409.6
6629.3	22.5°	6334.9	5734.2	4926.7	3981.9	3554.3	3697.5	3999.8	4252.4	4395.6	4353.9
6836.1	25°	6527.8	5865.5	4859.1	3703.5	3361.4	3560.3	3842.7	4047.6	4147.0	4145.0
7058.9	27.5°	6758.6	6040.5	4823.3	3478.7	3224.1	3405.1	3655.7	3838.7	3908.3	3908.3
7335.4	30°	7027.1	6247.4	4783.5	3331.5	3144.6	3244.0	3438.9	3618.0	3687.6	3687.6
7637.7	32.5°	7325.4	6446.3	4688.0	3242.0	3084.9	3086.9	3210.2	3373.3	3456.8	3468.8
8015.6	35°	7683.4	6659.1	4479.2	3170.4	3015.3	2933.7	2993.4	3128.7	3228.1	3254.0
8554.6	37.5°	8152.8	6919.7	4180.8	3065.0	2907.9	2772.6	2786.6	2890.0	2999.4	3039.2
9298.5	40°	8783.3	7226.0	3870.6	2913.9	2756.7	2595.6	2589.7	2665.2	2772.6	2816.4
10304.9	42.5°	9616.7	7593.9	3574.2	2768.7	2573.7	2408.7	2398.7	2458.4	2551.9	2597.6
11633.5	45°	10682.8	8045.4	3319.6	2655.3	2394.7	2231.6	2227.7	2277.4	2358.9	2406.7
13334.1	47.5°	12164.6	8496.9	3146.6	2595.6	2253.5	2086.4	2094.4	2138.2	2211.7	2245.6
15535.9	50°	14095.9	8634.2	3059.0	2595.6	2177.9	1957.2	1996.9	2032.7	2088.4	2108.3
18175.3	52.5°	15949.6	8180.7	2979.5	2611.5	2187.9	1847.8	1933.3	1959.1	2006.9	2014.8
20621.7	55°	16858.6	7033.0	2870.1	2615.5	2249.5	1754.3	1881.6	1929.3	1947.2	1945.2
22041.9	57.5°	16546.3	5686.5	2685.1	2599.6	2291.3	1694.6	1817.9	1909.4	1921.4	1903.5
21771.4	60°	15450.4	4186.8	2543.9	2482.2	2275.4	1676.7	1720.5	1865.7	1883.6	1859.7
19686.9	62.5°	13612.6	2905.9	2434.5	2223.7	2205.8	1670.7	1567.3	1770.2	1813.9	1780.1
15824.3	65°	10716.6	2052.6	2096.4	1949.2	2054.6	1638.9	1408.2	1654.8	1714.5	1662.8
11480.4	67.5°	7251.8	1481.8	1698.6	1766.2	1810.0	1567.3	1292.8	1523.6	1603.1	1535.5
7367.2	70°	3916.3	1040.2	1121.8	1487.8	1537.5	1444.0	1189.4	1390.3	1481.8	1408.2
5237.0	72.5°	2313.2	747.9	785.6	1195.4	1280.9	1271.0	1074.0	1235.2	1346.5	1259.0
3614.0	75°	1274.9	505.2	560.9	867.2	1040.2	980.6	922.9	1046.2	1159.6	1074.0
2265.4	77.5°	570.8	302.3	389.8	568.8	817.5	672.3	714.0	815.5	920.9	831.4
1261.0	80°	220.8	169.1	258.6	310.3	594.7	371.9	459.5	600.7	676.3	604.6
274.5	82.5°	27.8	75.6	111.4	121.3	346.1	196.9	266.5	377.9	371.9	322.2
0.0	85°	0.0	13.9	15.9	8.0	149.2	71.6	87.5	123.3	115.4	87.5
0.0	87.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	4.0	0.0
0.0	90°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0

REPORT NUMBER: P951307
 CATALOG NUMBER: GLAN-SB5C-730-U-SLL-HSS

CANDELA DISTRIBUTION (continued):

185°		195°	205°	215°	225°	235°	245°	255°	265°	270°	275°
3997.8	0°	3997.8	3997.8	3997.8	3997.8	3997.8	3997.8	3997.8	3997.8	3997.8	3997.8
3580.2	2.5°	3482.7	3411.1	3375.3	3345.5	3373.3	3389.2	3389.2	3456.8	3496.6	3512.5
3244.0	5°	3069.0	2935.7	2846.2	2792.5	2810.4	2830.3	2852.2	2937.7	2995.4	3033.2
3011.3	7.5°	2742.8	2539.9	2414.6	2349.0	2358.9	2372.9	2390.8	2474.3	2532.0	2581.7
2967.6	10°	2581.7	2295.3	2130.2	2050.6	2036.7	2028.8	2022.8	2072.5	2116.3	2156.1
3146.6	12.5°	2589.7	2189.9	1989.0	1891.5	1849.8	1802.0	1764.2	1772.2	1800.0	1849.8
3466.8	15°	2691.1	2156.1	1915.4	1794.1	1724.4	1668.8	1623.0	1613.1	1623.0	1631.0
3832.8	17.5°	2828.3	2152.1	1851.7	1700.6	1629.0	1583.2	1541.5	1527.5	1529.5	1539.5
4075.4	20°	2937.7	2140.1	1780.1	1611.1	1547.4	1507.6	1465.9	1452.0	1455.9	1457.9
4099.3	22.5°	2995.4	2122.2	1700.6	1521.6	1467.9	1428.1	1390.3	1388.3	1388.3	1400.2
3970.0	25°	2995.4	2084.5	1629.0	1436.0	1388.3	1352.5	1306.8	1314.7	1318.7	1334.6
3769.1	27.5°	2923.8	2012.8	1571.3	1362.5	1312.7	1276.9	1235.2	1245.1	1251.1	1269.0
3570.2	30°	2832.3	1927.3	1505.7	1292.8	1235.2	1209.3	1173.5	1177.5	1185.4	1205.3
3385.2	32.5°	2734.8	1825.9	1452.0	1223.2	1165.5	1145.7	1105.9	1111.8	1119.8	1141.7
3202.3	35°	2627.4	1706.5	1388.3	1159.6	1101.9	1086.0	1040.2	1044.2	1056.1	1080.0
3005.3	37.5°	2514.1	1609.1	1324.7	1097.9	1038.2	1022.3	974.6	978.6	992.5	1020.3
2798.5	40°	2402.7	1513.6	1257.0	1032.3	972.6	958.7	907.0	911.0	926.9	956.7
2589.7	42.5°	2281.4	1440.0	1169.5	964.7	901.0	887.1	839.3	845.3	863.2	893.1
2396.7	45°	2136.2	1392.3	1072.1	901.0	829.4	815.5	771.7	783.7	803.5	833.4
2231.6	47.5°	1987.0	1372.4	990.5	833.4	755.8	743.9	708.1	728.0	749.8	773.7
2090.4	50°	1843.8	1346.5	907.0	769.7	692.2	680.2	656.4	682.2	704.1	726.0
1989.0	52.5°	1680.7	1290.8	831.4	714.0	638.5	634.5	622.6	646.4	666.3	686.2
1901.5	55°	1511.6	1201.3	765.8	664.3	592.7	596.7	590.7	610.6	626.5	644.4
1821.9	57.5°	1364.4	1088.0	714.0	610.6	552.9	564.9	556.9	566.9	576.8	598.7
1726.4	60°	1215.3	952.7	656.4	547.0	513.2	527.1	505.2	503.2	507.2	513.2
1585.2	62.5°	1014.4	811.5	584.8	491.3	469.4	475.4	433.6	401.8	401.8	407.7
1388.3	65°	815.5	680.2	505.2	427.6	409.7	405.8	346.1	302.3	298.3	316.2
1159.6	67.5°	670.3	564.9	425.6	356.0	344.1	348.1	304.3	260.6	256.6	276.5
944.8	70°	554.9	455.5	340.1	274.5	286.4	304.3	260.6	218.8	212.8	230.7
767.7	72.5°	441.6	356.0	260.6	202.9	236.7	258.6	212.8	173.0	169.1	185.0
592.7	75°	324.2	254.6	177.0	147.2	183.0	202.9	155.1	123.3	117.3	131.3
395.8	77.5°	200.9	143.2	111.4	87.5	125.3	135.3	81.5	71.6	69.6	79.6
240.7	80°	93.5	61.7	53.7	29.8	45.7	53.7	33.8	37.8	39.8	47.7
121.3	82.5°	25.9	9.9	2.0	0.0	0.0	15.9	8.0	15.9	19.9	29.8
9.9	85°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	4.0	9.9	17.9
0.0	87.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	8.0
0.0	90°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0

REPORT NUMBER: P951307
 CATALOG NUMBER: GLAN-SB5C-730-U-SLL-HSS

CANDELA DISTRIBUTION (continued):

285°		295°	305°	315°	325°	335°	345°	355°	360°
3997.8	0°	3997.8	3997.8	3997.8	3997.8	3997.8	3997.8	3997.8	3997.8
3623.9	2.5°	3707.5	3787.0	3914.3	4045.6	4174.9	4306.1	4433.4	4479.2
3206.2	5°	3363.4	3546.3	3799.0	4069.5	4347.9	4630.3	4888.9	5006.3
2774.6	7.5°	2979.5	3242.0	3621.9	4045.6	4489.1	4932.7	5340.4	5529.4
2347.0	10°	2569.8	2901.9	3335.5	3908.3	4544.8	5157.4	5718.3	5963.0
1971.1	12.5°	2179.9	2528.0	3007.3	3693.5	4501.1	5286.7	5961.0	6249.4
1706.5	15°	1853.7	2162.0	2679.2	3438.9	4359.8	5294.7	6076.3	6392.6
1559.4	17.5°	1609.1	1810.0	2345.0	3156.5	4174.9	5221.1	6116.1	6454.2
1479.8	20°	1487.8	1543.4	1911.4	2794.5	4001.8	5151.5	6155.9	6511.9
1416.2	22.5°	1416.2	1430.1	1563.3	2327.1	3795.0	5129.6	6225.5	6591.5
1358.5	25°	1358.5	1362.5	1398.3	1843.8	3478.7	5115.7	6332.9	6700.9
1298.8	27.5°	1300.8	1300.8	1320.7	1485.8	3049.1	5056.0	6472.1	6832.1
1239.1	30°	1243.1	1243.1	1257.0	1314.7	2545.9	4938.6	6639.2	7003.2
1179.5	32.5°	1183.4	1183.4	1195.4	1237.1	2032.7	4791.5	6792.4	7176.2
1117.8	35°	1123.8	1119.8	1135.7	1179.5	1617.0	4604.5	6945.5	7363.2
1056.1	37.5°	1060.1	1058.1	1074.0	1123.8	1396.3	4387.7	7060.9	7617.8
994.5	40°	992.5	992.5	1010.4	1064.1	1332.6	4115.2	7243.9	7983.8
930.8	42.5°	930.8	926.9	946.8	1012.4	1284.9	3854.6	7572.0	8516.8
873.2	45°	871.2	863.2	881.1	962.7	1201.3	3763.1	8184.6	9304.4
817.5	47.5°	815.5	795.6	811.5	903.0	1125.8	4105.3	9187.1	10396.4
767.7	50°	769.7	731.9	745.9	843.3	1068.1	4847.1	10487.9	11846.4
722.0	52.5°	722.0	672.3	680.2	769.7	1016.4	5553.2	11898.1	13759.8
676.3	55°	672.3	616.6	620.6	696.1	942.8	5658.6	13274.4	16369.3
624.5	57.5°	616.6	564.9	564.9	628.5	889.1	4904.8	14332.6	19607.4
560.9	60°	554.9	521.1	511.2	574.8	936.8	3460.8	14455.9	21695.8
479.3	62.5°	487.3	469.4	455.5	523.1	972.6	2050.6	13463.4	21190.6
377.9	65°	409.7	405.8	395.8	574.8	819.5	1211.3	11558.0	19641.2
322.2	67.5°	344.1	338.1	338.1	602.7	622.6	761.8	9030.0	17509.0
274.5	70°	296.4	274.5	274.5	455.5	377.9	527.1	6305.1	15207.7
226.7	72.5°	248.6	224.8	208.8	364.0	282.4	385.9	3940.2	13023.8
173.0	75°	198.9	181.0	161.1	240.7	210.8	292.4	2289.3	10790.2
109.4	77.5°	143.2	135.3	113.4	177.0	153.2	210.8	1362.5	8325.9
67.6	80°	73.6	75.6	71.6	101.4	103.4	143.2	775.7	5698.4
43.8	82.5°	43.8	33.8	37.8	49.7	59.7	81.5	292.4	3349.4
31.8	85°	27.8	17.9	17.9	23.9	29.8	31.8	89.5	1358.5
15.9	87.5°	13.9	6.0	8.0	11.9	9.9	8.0	4.0	342.1
0.0	90°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0

(END OF REPORT)