

Scaled data based on original data using
LM-79-08 Approved Method: Electrical and Photometric Measurements of Solid-
State Lighting Products

Test Report Prepared for
Cooper Lighting Solutions
(formerly Eaton)

Brand: STREETWORKS

Report Number: P851662

Luminaire Tested: **GLAN-SB9D-730-U-SL4-HSS**

Issue Date: 6/26/2024

Test Information

Test Method: LM-79-08
Report Number: P851662
TEST IS SCALED FROM IESNA LM-79-08 TEST DATA (G2-2405-108-10)
Test Lab: INNOVATION CENTER
Issue Date: 6/26/2024
Manufacturer: COOPER LIGHTING SOLUTIONS (FORMERLY EATON)
Product Line: STREETWORKS
Catalog Number: GLAN-SB9D-730-U-SL4-HSS
Description: GALLEON AREA AND ROADWAY HIGH DENSITY LED LUMINAIRE
(9) 70 CRI, 3000K, 900mA LIGHTSQUARES WITH 26 LEDS EACH AND TYPE IV SPILL
LIGHT ELIMINATOR OPTICS WITH HOUSE SIDE SHIELD
Light Source: -
Ballast/Driver: -

Summary

Lumens per Lamp: N/A
Luminaire Lumens: 62499 lumens
Efficiency: N/A
Efficacy: 95.0 lumens/watt
Luminous Opening: Rectangular (W 1.5' x L: 1.5' x H: 0')
IES Classification: Type IV - Short
BUG Rating: B3 - U0 - G5


Input Watts (W): 658
Input Voltage (V): NR
Input Current (Ain): NR
Voltage Rise (V): NR
Power Factor: NR
Total Harmonic Distortion (THDi): NR
Frequency (hertz): 60
Stabilization Time: NR
Operation Time: NR
Ambient Temperature (°C): NR
Test Distance: 24 FT



REPORT NUMBER: P851662
 CATALOG NUMBER: GLAN-SB9D-730-U-SL4-HSS

Iso-Footcandle Lines of Horizontal Illumination


✕ Max cd
 - - - 1/2 Max cd



Based on 25 foot mounting height. Maximum calculated value = 15.2 fc
 Type IV - Short - N/A

REPORT NUMBER: P851662
CATALOG NUMBER: GLAN-SB9D-730-U-SL4-HSS

Luminous Intensity Polar Plot



— Vertical Plane Through 40-Deg Lateral - - - Horizontal Cone Through 72.5-Deg Vertical

REPORT NUMBER: P851662
 CATALOG NUMBER: GLAN-SB9D-730-U-SL4-HSS

FLUX DISTRIBUTION:

		Downward	Upward	Total
House Side	Lumens	8071.1	0.0	8071.1
	% Fixture	12.9	0.0	12.9
Street Side	Lumens	54427.9	0.0	54427.9
	% Fixture	87.1	0.0	87.1
Total	Lumens	62499.0	0.0	62499.0
	% Fixture	100.0	0.0	100.0

ZONAL LUMENS:

Zone	Lumens	% Fixture
0°-10°	755.8	1.2
10°-20°	2052.4	3.3
20°-30°	3321.0	5.3
30°-40°	4902.9	7.8
40°-50°	8251.7	13.2
50°-60°	12812.7	20.5
60°-70°	16032.3	25.7
70°-80°	13125.7	21.0
80°-90°	1244.6	2.0
90°-100°	0.0	0.0
100°-110°	0.0	0.0
110°-120°	0.0	0.0
120°-130°	0.0	0.0
130°-140°	0.0	0.0
140°-150°	0.0	0.0
150°-160°	0.0	0.0
160°-170°	0.0	0.0
170°-180°	0.0	0.0
0°-90°	62499.0	100.0
0°-180°	62499.0	100.0

Coefficient of Utilization




REPORT NUMBER: P851662
 CATALOG NUMBER: GLAN-SB9D-730-U-SL4-HSS

LUMINAIRE CLASSIFICATION SYSTEM LUMEN TABLE AND BUG RATING:

Zone		Lumens	% Fixture	Zone Rating/Lumen Limit		
				B	U	G
FL	(0°-30°)	4148.1	6.6			
FM	(30°-60°)	21011.1	33.6			
FH	(60°-80°)	28033.6	44.9			G5
FVH	(80°-90°)	1235.1	2.0			G5
BL	(0°-30°)	1981.0	3.2	B3/2500		
BM	(30°-60°)	4956.2	7.9	B3/5000		
BH	(60°-80°)	1124.4	1.8	B3/2500		G3/2500
BVH	(80°-90°)	9.5	0.0			G0/10
UL	(90°-100°)	0.0	0.0		U0/0	
UH	(100°-180°)	0.0	0.0		U0/0	

BUG Rating: B3-U0-G5

Type IV Short



REPORT NUMBER: P851662
 CATALOG NUMBER: GLAN-SB9D-730-U-SL4-HSS

CANDELA DISTRIBUTION (FULL):

	0°	5°	15°	25°	35°	40°	45°	55°	65°	75°
0°	8275.4	8275.4	8275.4	8275.4	8275.4	8275.4	8275.4	8275.4	8275.4	8275.4
2.5°	8524.9	8557.8	8539.0	8501.3	8491.9	8473.1	8449.5	8440.1	8407.2	8378.9
5°	8764.9	8797.9	8774.3	8722.6	8699.0	8675.5	8642.5	8614.3	8548.4	8487.2
7.5°	9028.5	9056.8	9028.5	8953.2	8915.6	8887.3	8840.2	8797.9	8722.6	8633.1
10°	9320.4	9343.9	9301.6	9202.7	9141.5	9099.1	9056.8	9009.7	8939.1	8840.2
12.5°	9593.4	9621.7	9555.8	9438.1	9367.5	9325.1	9278.0	9240.4	9169.8	9075.6
15°	9842.9	9885.3	9772.3	9645.2	9565.2	9532.2	9485.1	9461.6	9414.5	9348.6
17.5°	10031.2	10059.4	9941.7	9791.1	9701.7	9678.1	9645.2	9659.3	9649.9	9616.9
20°	10191.2	10210.1	10054.7	9871.1	9772.3	9777.0	9767.6	9814.7	9833.5	9833.5
22.5°	10388.9	10393.6	10195.9	9965.3	9847.6	9880.6	9894.7	9946.5	9984.1	10021.8
25°	10647.8	10638.4	10403.1	10087.7	9984.1	10031.2	10064.1	10083.0	10125.3	10186.5
27.5°	11033.8	11005.6	10704.3	10285.4	10163.0	10205.4	10266.5	10257.1	10238.3	10285.4
30°	11523.4	11485.7	11085.6	10563.1	10450.1	10487.8	10506.6	10421.9	10285.4	10327.7
32.5°	12300.1	12234.2	11678.7	10873.8	10699.6	10742.0	10718.4	10544.3	10341.9	10384.2
35°	13651.1	13491.0	12704.9	11523.4	10982.1	10935.0	10878.5	10709.0	10459.5	10417.2
37.5°	16522.5	16240.1	14898.5	12789.6	11622.2	11316.3	11142.1	10972.6	10586.6	10417.2
40°	19761.1	19474.0	17925.3	14907.9	12686.1	12168.3	11754.0	11283.3	10718.4	10478.4
42.5°	23140.9	22825.5	21234.5	17534.6	14206.5	13142.7	12370.7	11532.8	10935.0	10666.7
45°	26916.1	26520.7	24440.1	20274.2	16414.2	14762.0	13363.9	12045.9	11311.6	11000.9
47.5°	30898.5	30385.4	27636.4	22933.8	18791.4	17002.6	15180.9	12963.8	11867.0	11499.9
50°	34428.9	33920.6	30936.2	25715.8	21013.2	19135.0	17252.1	14234.8	12700.2	12205.9
52.5°	36966.2	36580.2	33939.4	28587.2	23324.5	21135.6	19130.3	15712.9	13754.6	13109.7
55°	38665.5	38312.4	36067.1	31308.0	26012.4	23338.6	20980.3	17318.0	15025.6	14192.4
57.5°	39696.4	39494.0	37606.4	33737.0	28676.7	25748.7	23098.6	19083.3	16522.5	15468.1
60°	40063.5	39898.8	38561.9	36053.0	31896.4	28643.7	25588.7	21074.4	18339.5	16917.9
62.5°	39084.4	39117.4	39249.2	38797.3	35290.4	32032.9	28573.1	23465.7	20354.2	18560.8
65°	34476.0	34749.0	37253.3	41838.2	39785.8	36278.9	32371.9	26384.2	22660.8	20429.5
67.5°	28544.9	28940.3	32056.5	43617.5	44577.8	41791.1	37662.8	30103.0	25409.8	22331.3
70°	21851.1	22274.8	26050.0	43245.7	49063.8	47816.4	44205.9	34833.8	28257.7	23649.3
72.5°	15595.2	15811.7	18786.7	39936.4	50904.4	51921.1	49026.2	39315.1	29712.3	22919.7
75°	10958.5	10920.9	12893.2	32160.0	48037.7	51422.2	47336.3	36890.8	26887.9	18207.7
77.5°	4773.2	4782.6	6439.5	19530.4	38340.7	43918.8	39348.0	23108.0	18744.3	9649.9
80°	1238.0	1275.7	2363.0	7776.4	23084.4	28987.3	23997.6	10158.3	8661.4	2353.6
82.5°	437.8	466.0	1087.4	2443.1	8515.4	13293.3	10685.5	3248.0	2259.5	673.1
85°	127.1	150.6	583.7	748.5	1760.5	3756.4	2593.7	630.8	555.5	348.3
87.5°	0.0	18.8	117.7	103.6	103.6	70.6	131.8	70.6	89.4	42.4
90°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0

REPORT NUMBER: P851662
 CATALOG NUMBER: GLAN-SB9D-730-U-SL4-HSS

CANDELA DISTRIBUTION (continued):

85°		90°	95°	105°	115°	125°	135°	145°	155°	165°	175°
8275.4	0°	8275.4	8275.4	8275.4	8275.4	8275.4	8275.4	8275.4	8275.4	8275.4	8275.4
8346.0	2.5°	8317.7	8284.8	8214.2	8138.9	8068.3	8002.4	7983.5	7912.9	7880.0	7884.7
8411.9	5°	8360.1	8298.9	8162.4	7997.6	7828.2	7635.2	7475.1	7249.2	7056.2	7032.7
8539.0	7.5°	8473.1	8374.2	8153.0	7832.9	7409.2	6877.3	6383.1	5893.5	5615.8	5465.1
8727.3	10°	8647.2	8515.4	8176.5	7564.6	6665.5	5714.6	4966.2	4349.5	4034.1	3888.2
8957.9	12.5°	8854.4	8708.4	8214.2	7108.0	5705.2	4457.8	3648.1	3271.6	3205.6	3196.2
9240.4	15°	9146.2	8986.2	8256.5	6491.3	4664.9	3393.9	3022.1	3026.8	3078.6	3106.8
9546.3	17.5°	9471.0	9311.0	8195.4	5738.2	3638.7	2899.7	2890.3	2932.6	3007.9	3036.2
9828.8	20°	9800.5	9649.9	7978.8	4853.2	2942.0	2763.2	2800.8	2847.9	2923.2	2960.9
10106.5	22.5°	10139.5	10007.6	7635.2	3911.7	2654.9	2664.3	2711.4	2758.5	2843.2	2885.6
10379.5	25°	10501.9	10388.9	7178.6	3135.0	2532.5	2560.8	2621.9	2678.4	2767.9	2819.7
10610.2	27.5°	10869.1	10784.3	6660.8	2617.2	2419.5	2452.5	2523.1	2598.4	2687.8	2749.0
10812.6	30°	11269.2	11222.1	6246.5	2424.2	2311.3	2339.5	2419.5	2504.3	2603.1	2678.4
11015.0	32.5°	11678.7	11669.3	6044.1	2565.5	2212.4	2231.2	2301.9	2386.6	2509.0	2603.1
11184.5	35°	12083.6	12102.4	5926.4	2965.6	2179.5	2127.7	2174.8	2250.1	2396.0	2513.7
11377.5	37.5°	12601.4	12648.4	5921.7	3398.6	2259.5	2024.1	2057.1	2108.9	2236.0	2372.5
11678.7	40°	13373.3	13622.8	6223.0	3770.5	2400.7	1930.0	1939.4	1948.8	2014.7	2127.7
12078.8	42.5°	14399.5	15129.2	7310.4	4024.7	2457.2	1845.2	1812.3	1760.5	1751.1	1812.3
12624.9	45°	15675.2	16950.9	9221.5	4165.9	2400.7	1751.1	1661.7	1525.2	1473.4	1515.7
13363.9	47.5°	17176.8	18946.7	11485.7	4198.9	2306.6	1633.4	1473.4	1294.5	1252.1	1266.3
14357.2	50°	18640.8	20443.7	13476.9	3925.9	2151.2	1482.8	1266.3	1115.6	1087.4	1092.1
15529.3	52.5°	19935.3	20956.8	14041.8	3281.0	1944.1	1299.2	1087.4	983.8	965.0	965.0
16823.8	55°	20792.0	20401.3	12521.3	2509.0	1685.2	1110.9	932.0	880.3	870.8	866.1
18268.9	57.5°	20970.9	18593.7	9456.9	1812.3	1318.0	936.7	828.5	800.2	781.4	762.6
19751.7	60°	20330.7	15581.1	6020.6	1266.3	988.5	800.2	734.3	715.5	677.8	640.2
21145.0	62.5°	18946.7	11768.2	3332.7	880.3	795.5	682.6	649.6	626.1	555.5	494.3
22251.2	65°	17087.4	7823.5	1473.4	687.3	649.6	574.3	555.5	522.5	437.8	367.2
22670.2	67.5°	15218.6	4504.9	663.7	550.8	522.5	470.7	456.6	433.1	371.9	306.0
21601.6	70°	13086.2	2283.0	456.6	437.8	404.8	357.8	371.9	367.2	306.0	249.5
17619.3	72.5°	9744.0	1134.5	343.6	329.5	291.9	254.2	306.0	301.3	240.1	188.3
10864.4	75°	5516.9	560.2	249.5	230.7	174.2	188.3	244.8	230.7	164.8	122.4
4584.9	77.5°	2188.9	287.1	164.8	141.2	103.6	127.1	178.9	155.3	84.7	51.8
875.6	80°	503.7	141.2	84.7	61.2	47.1	75.3	94.1	56.5	23.5	4.7
235.4	82.5°	141.2	61.2	28.2	23.5	23.5	28.2	23.5	9.4	0.0	0.0
61.2	85°	47.1	28.2	9.4	4.7	4.7	4.7	4.7	0.0	0.0	0.0
18.8	87.5°	18.8	9.4	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
0.0	90°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0

(END O

180°
8275.4
7880.0
7018.5
5455.7
3860.0
3191.5
3102.1
3031.5
2960.9
2885.6
2819.7
2753.8
2687.8
2612.5
2532.5
2396.0
2165.3
1845.2
1515.7
1261.5
1092.1
960.3
856.7
753.2
626.1
475.4
353.0
296.6
240.1
178.9
113.0
47.1
0.0
0.0
0.0
0.0
0.0

F REPORT)