

Scaled data based on original data using
LM-79-08 Approved Method: Electrical and Photometric Measurements of Solid-
State Lighting Products

Test Report Prepared for
Cooper Lighting Solutions
(formerly Eaton)

Brand: STREETWORKS

Report Number: P951770

Luminaire Tested: **GLAN-SB5D-827-U-SLL**

Issue Date: 1/21/2025

Test Information

Test Method: LM-79-08
Report Number: P951770
TEST IS SCALED FROM IESNA LM-79-08 TEST DATA (G2-2411-289-8)
Test Lab: INNOVATION CENTER
Issue Date: 1/21/2025
Manufacturer: COOPER LIGHTING SOLUTIONS (FORMERLY EATON)
Product Line: STREETWORKS
Catalog Number: GLAN-SB5D-827-U-SLL
Description: GALLEON AREA AND ROADWAY HIGH DENSITY LED LUMINAIRE
(5) 80 CRI, 2700K, 900mA LIGHTSQUARES WITH 26 LEDS EACH AND SPILL LIGHT
ELIMINATOR LEFT OPTICS
Light Source: -
Ballast/Driver: -

Summary

Lumens per Lamp: N/A
Luminaire Lumens: 44539 lumens
Efficiency: N/A
Efficacy: 122.1 lumens/watt
Luminous Opening: Rectangular (W 1.5' x L: 1' x H: 0')
IES Classification: Type IV - Short
BUG Rating: B4 - U0 - G5


Input Watts (W): 364.9
Input Voltage (V): NR
Input Current (Ain): NR
Voltage Rise (V): NR
Power Factor: NR
Total Harmonic Distortion (THDi): NR
Frequency (hertz): 60
Stabilization Time: NR
Operation Time: NR
Ambient Temperature (°C): NR
Test Distance: 24 FT



REPORT NUMBER: P951770
 CATALOG NUMBER: GLAN-SB5D-827-U-SLL

Iso-Footcandle Lines of Horizontal Illumination


✕ Max cd
 - - - 1/2 Max cd



Based on 25 foot mounting height. Maximum calculated value = 13.6 fc
 Type IV - Short - N/A

REPORT NUMBER: P951770
CATALOG NUMBER: GLAN-SB5D-827-U-SLL

Luminous Intensity Polar Plot



— Vertical Plane Through 45-Deg Lateral - - - Horizontal Cone Through 65-Deg Vertical

REPORT NUMBER: P951770
 CATALOG NUMBER: GLAN-SB5D-827-U-SLL

FLUX DISTRIBUTION:

| | | Downward | Upward | Total |
|--------------------|-----------|----------|--------|---------|
| House Side | Lumens | 11319.6 | 0.0 | 11319.6 |
| | % Fixture | 25.4 | 0.0 | 25.4 |
| Street Side | Lumens | 33219.4 | 0.0 | 33219.4 |
| | % Fixture | 74.6 | 0.0 | 74.6 |
| Total | Lumens | 44539.0 | 0.0 | 44539.0 |
| | % Fixture | 100.0 | 0.0 | 100.0 |

ZONAL LUMENS:

| Zone | Lumens | % Fixture |
|-----------|---------|-----------|
| 0°-10° | 607.5 | 1.4 |
| 10°-20° | 1907.2 | 4.3 |
| 20°-30° | 2946.0 | 6.6 |
| 30°-40° | 3733.3 | 8.4 |
| 40°-50° | 5630.8 | 12.6 |
| 50°-60° | 9097.3 | 20.4 |
| 60°-70° | 11341.2 | 25.5 |
| 70°-80° | 7437.0 | 16.7 |
| 80°-90° | 1838.6 | 4.1 |
| 90°-100° | 0.0 | 0.0 |
| 100°-110° | 0.0 | 0.0 |
| 110°-120° | 0.0 | 0.0 |
| 120°-130° | 0.0 | 0.0 |
| 130°-140° | 0.0 | 0.0 |
| 140°-150° | 0.0 | 0.0 |
| 150°-160° | 0.0 | 0.0 |
| 160°-170° | 0.0 | 0.0 |
| 170°-180° | 0.0 | 0.0 |
| 0°-90° | 44539.0 | 100.0 |
| 0°-180° | 44539.0 | 100.0 |

Coefficient of Utilization




REPORT NUMBER: P951770
 CATALOG NUMBER: GLAN-SB5D-827-U-SLL

LUMINAIRE CLASSIFICATION SYSTEM LUMEN TABLE AND BUG RATING:

| Zone | Lumens | % Fixture | Zone Rating/Lumen Limit | | |
|----------------|---------|-----------|-------------------------|------|---------|
| | | | B | U | G |
| FL (0°-30°) | 2995.8 | 6.7 | | | |
| FM (30°-60°) | 12991.1 | 29.2 | | | |
| FH (60°-80°) | 15718.0 | 35.3 | | | G5 |
| FVH (80°-90°) | 1514.6 | 3.4 | | | G5 |
| BL (0°-30°) | 2465.0 | 5.5 | B3/2500 | | |
| BM (30°-60°) | 5470.3 | 12.3 | B4/8500 | | |
| BH (60°-80°) | 3060.3 | 6.9 | B4/5000 | | G4/5000 |
| BVH (80°-90°) | 324.0 | 0.7 | | | G3/500 |
| UL (90°-100°) | 0.0 | 0.0 | | U0/0 | |
| UH (100°-180°) | 0.0 | 0.0 | | U0/0 | |

BUG Rating: B4-U0-G5
 Type IV Short



REPORT NUMBER: P951770
 CATALOG NUMBER: GLAN-SB5D-827-U-SLL

CANDELA DISTRIBUTION (FULL):

| | 0° | 5° | 10° | 15° | 20° | 25° | 30° | 35° | 40° | 45° |
|-------|---------|---------|---------|---------|---------|---------|---------|---------|---------|---------|
| 0° | 6124.5 | 6124.5 | 6124.5 | 6124.5 | 6124.5 | 6124.5 | 6124.5 | 6124.5 | 6124.5 | 6124.5 |
| 2.5° | 6586.3 | 6611.2 | 6636.4 | 6671.8 | 6707.3 | 6728.5 | 6749.6 | 6760.2 | 6770.8 | 6766.1 |
| 5° | 7082.2 | 7169.4 | 7256.8 | 7343.3 | 7430.0 | 7477.0 | 7524.0 | 7552.4 | 7581.1 | 7602.7 |
| 7.5° | 7580.4 | 7722.4 | 7864.1 | 7991.7 | 8119.3 | 8196.2 | 8273.0 | 8314.6 | 8356.0 | 8375.9 |
| 10° | 7962.3 | 8130.1 | 8297.9 | 8447.6 | 8597.3 | 8688.0 | 8778.3 | 8818.7 | 8858.9 | 8874.2 |
| 12.5° | 8196.2 | 8378.1 | 8559.7 | 8695.1 | 8830.0 | 8895.8 | 8961.6 | 8983.7 | 9005.8 | 9008.1 |
| 15° | 8338.3 | 8495.3 | 8652.1 | 8736.9 | 8822.0 | 8824.4 | 8826.7 | 8803.2 | 8779.7 | 8752.0 |
| 17.5° | 8418.2 | 8524.2 | 8630.2 | 8631.9 | 8633.3 | 8538.1 | 8442.9 | 8355.7 | 8268.3 | 8206.7 |
| 20° | 8506.4 | 8543.3 | 8580.4 | 8468.8 | 8357.1 | 8147.0 | 7936.9 | 7783.9 | 7630.9 | 7536.9 |
| 22.5° | 8608.6 | 8560.2 | 8511.8 | 8280.5 | 8049.3 | 7740.2 | 7431.2 | 7239.9 | 7048.6 | 6944.7 |
| 25° | 8740.2 | 8587.5 | 8434.7 | 8083.6 | 7732.5 | 7357.2 | 6981.8 | 6780.7 | 6580.0 | 6481.7 |
| 27.5° | 8918.8 | 8645.7 | 8372.4 | 7907.3 | 7442.5 | 7026.5 | 6610.5 | 6412.6 | 6215.0 | 6122.1 |
| 30° | 9159.7 | 8752.4 | 8345.4 | 7772.9 | 7200.4 | 6767.0 | 6333.7 | 6150.1 | 5966.6 | 5880.1 |
| 32.5° | 9444.1 | 8886.4 | 8328.9 | 7681.2 | 7033.5 | 6626.3 | 6219.0 | 6074.9 | 5930.6 | 5868.3 |
| 35° | 9789.6 | 9107.1 | 8424.8 | 7749.9 | 7075.1 | 6792.2 | 6509.5 | 6475.8 | 6442.2 | 6437.1 |
| 37.5° | 10371.2 | 9568.4 | 8765.6 | 8152.2 | 7538.8 | 7520.5 | 7502.2 | 7655.9 | 7809.6 | 7889.5 |
| 40° | 11250.2 | 10377.1 | 9504.0 | 9047.9 | 8591.7 | 8913.7 | 9235.6 | 9609.3 | 9983.0 | 10169.1 |
| 42.5° | 12415.9 | 11549.6 | 10683.3 | 10420.6 | 10157.8 | 10860.1 | 11562.3 | 12241.9 | 12921.6 | 13320.7 |
| 45° | 13855.3 | 13077.2 | 12298.8 | 12183.0 | 12066.9 | 13191.9 | 14317.1 | 15433.9 | 16550.9 | 17229.0 |
| 47.5° | 15655.5 | 14898.6 | 14141.3 | 14117.8 | 14094.3 | 15717.3 | 17339.9 | 18974.9 | 20609.7 | 21569.7 |
| 50° | 18015.1 | 17080.0 | 16145.1 | 16149.1 | 16153.1 | 18244.7 | 20336.3 | 22494.5 | 24652.6 | 25957.4 |
| 52.5° | 20723.6 | 19591.3 | 18459.3 | 18344.8 | 18230.1 | 20728.6 | 23227.0 | 25897.3 | 28567.3 | 30131.3 |
| 55° | 23607.3 | 22488.6 | 21369.9 | 20923.6 | 20477.3 | 23258.0 | 26038.5 | 29221.8 | 32405.1 | 34265.2 |
| 57.5° | 26230.0 | 25620.9 | 25011.5 | 24116.3 | 23221.4 | 26029.1 | 28836.8 | 32442.4 | 36047.8 | 38354.5 |
| 60° | 27815.2 | 28761.4 | 29707.8 | 28596.2 | 27484.6 | 30141.6 | 32798.7 | 36659.1 | 40519.4 | 43012.5 |
| 62.5° | 27010.3 | 29595.7 | 32181.1 | 32055.8 | 31930.3 | 34364.4 | 36798.7 | 40471.5 | 44144.1 | 46448.4 |
| 65° | 25399.3 | 27825.8 | 30252.3 | 30732.5 | 31212.4 | 34305.6 | 37399.1 | 40960.6 | 44521.7 | 46483.7 |
| 67.5° | 23240.7 | 25548.5 | 27856.4 | 28081.5 | 28306.4 | 31529.4 | 34752.2 | 38328.9 | 41905.6 | 43442.6 |
| 70° | 20647.3 | 23157.5 | 25667.9 | 25768.5 | 25869.3 | 28751.5 | 31633.5 | 34711.5 | 37789.3 | 38643.5 |
| 72.5° | 17556.8 | 20437.4 | 23318.2 | 23390.6 | 23462.7 | 25717.7 | 27972.7 | 30277.9 | 32583.0 | 32669.5 |
| 75° | 13647.3 | 16628.7 | 19610.1 | 19877.8 | 20145.5 | 21899.9 | 23654.3 | 25277.1 | 26899.8 | 26465.1 |
| 77.5° | 9750.8 | 12533.8 | 15317.1 | 15700.2 | 16083.3 | 17417.0 | 18750.7 | 19901.6 | 21052.7 | 20305.3 |
| 80° | 6381.8 | 8723.3 | 11064.5 | 11540.7 | 12016.8 | 13024.1 | 14030.9 | 14635.3 | 15239.6 | 14037.5 |
| 82.5° | 3709.7 | 5310.4 | 6911.3 | 7443.2 | 7975.2 | 8668.5 | 9361.8 | 9614.0 | 9865.9 | 8921.2 |
| 85° | 1632.2 | 2481.8 | 3331.3 | 3783.7 | 4236.1 | 4805.8 | 5375.3 | 5518.4 | 5661.5 | 4904.8 |
| 87.5° | 505.3 | 790.8 | 1076.4 | 1328.8 | 1581.2 | 1866.0 | 2150.9 | 2163.1 | 2175.1 | 1826.1 |
| 90° | 0.0 | 0.0 | 0.0 | 0.0 | 0.0 | 0.0 | 0.0 | 0.0 | 0.0 | 0.0 |

REPORT NUMBER: P951770
 CATALOG NUMBER: GLAN-SB5D-827-U-SLL

CANDELA DISTRIBUTION (continued):

| 50° | | 55° | 60° | 65° | 70° | 75° | 80° | 85° | 90° | 95° | 100° |
|---------|-------|---------|---------|---------|---------|---------|---------|---------|---------|---------|---------|
| 6124.5 | 0° | 6124.5 | 6124.5 | 6124.5 | 6124.5 | 6124.5 | 6124.5 | 6124.5 | 6124.5 | 6124.5 | 6124.5 |
| 6770.8 | 2.5° | 6760.2 | 6749.6 | 6728.5 | 6707.3 | 6671.8 | 6636.4 | 6611.2 | 6586.3 | 6535.8 | 6485.2 |
| 7581.1 | 5° | 7552.4 | 7524.0 | 7477.0 | 7430.0 | 7343.3 | 7256.8 | 7169.4 | 7082.2 | 6970.6 | 6858.9 |
| 8356.0 | 7.5° | 8314.6 | 8273.0 | 8196.2 | 8119.3 | 7991.7 | 7864.1 | 7722.4 | 7580.4 | 7396.2 | 7212.1 |
| 8858.9 | 10° | 8818.7 | 8778.3 | 8688.0 | 8597.3 | 8447.6 | 8297.9 | 8130.1 | 7962.3 | 7729.4 | 7496.5 |
| 9005.8 | 12.5° | 8983.7 | 8961.6 | 8895.8 | 8830.0 | 8695.1 | 8559.7 | 8378.1 | 8196.2 | 7940.2 | 7684.5 |
| 8779.7 | 15° | 8803.2 | 8826.7 | 8824.4 | 8822.0 | 8736.9 | 8652.1 | 8495.3 | 8338.3 | 8071.6 | 7804.9 |
| 8268.3 | 17.5° | 8355.7 | 8442.9 | 8538.1 | 8633.3 | 8631.9 | 8630.2 | 8524.2 | 8418.2 | 8147.7 | 7877.2 |
| 7630.9 | 20° | 7783.9 | 7936.9 | 8147.0 | 8357.1 | 8468.8 | 8580.4 | 8543.3 | 8506.4 | 8225.3 | 7944.0 |
| 7048.6 | 22.5° | 7239.9 | 7431.2 | 7740.2 | 8049.3 | 8280.5 | 8511.8 | 8560.2 | 8608.6 | 8321.4 | 8034.0 |
| 6580.0 | 25° | 6780.7 | 6981.8 | 7357.2 | 7732.5 | 8083.6 | 8434.7 | 8587.5 | 8740.2 | 8458.7 | 8177.4 |
| 6215.0 | 27.5° | 6412.6 | 6610.5 | 7026.5 | 7442.5 | 7907.3 | 8372.4 | 8645.7 | 8918.8 | 8650.4 | 8381.8 |
| 5966.6 | 30° | 6150.1 | 6333.7 | 6767.0 | 7200.4 | 7772.9 | 8345.4 | 8752.4 | 9159.7 | 8900.3 | 8641.0 |
| 5930.6 | 32.5° | 6074.9 | 6219.0 | 6626.3 | 7033.5 | 7681.2 | 8328.9 | 8886.4 | 9444.1 | 9187.2 | 8930.6 |
| 6442.2 | 35° | 6475.8 | 6509.5 | 6792.2 | 7075.1 | 7749.9 | 8424.8 | 9107.1 | 9789.6 | 9543.7 | 9297.7 |
| 7809.6 | 37.5° | 7655.9 | 7502.2 | 7520.5 | 7538.8 | 8152.2 | 8765.6 | 9568.4 | 10371.2 | 10057.7 | 9744.2 |
| 9983.0 | 40° | 9609.3 | 9235.6 | 8913.7 | 8591.7 | 9047.9 | 9504.0 | 10377.1 | 11250.2 | 10793.3 | 10336.4 |
| 12921.6 | 42.5° | 12241.9 | 11562.3 | 10860.1 | 10157.8 | 10420.6 | 10683.3 | 11549.6 | 12415.9 | 11756.4 | 11096.9 |
| 16550.9 | 45° | 15433.9 | 14317.1 | 13191.9 | 12066.9 | 12183.0 | 12298.8 | 13077.2 | 13855.3 | 12965.8 | 12076.3 |
| 20609.7 | 47.5° | 18974.9 | 17339.9 | 15717.3 | 14094.3 | 14117.8 | 14141.3 | 14898.6 | 15655.5 | 14403.6 | 13151.5 |
| 24652.6 | 50° | 22494.5 | 20336.3 | 18244.7 | 16153.1 | 16149.1 | 16145.1 | 17080.0 | 18015.1 | 16127.7 | 14240.0 |
| 28567.3 | 52.5° | 25897.3 | 23227.0 | 20728.6 | 18230.1 | 18344.8 | 18459.3 | 19591.3 | 20723.6 | 17938.7 | 15153.8 |
| 32405.1 | 55° | 29221.8 | 26038.5 | 23258.0 | 20477.3 | 20923.6 | 21369.9 | 22488.6 | 23607.3 | 19544.3 | 15481.6 |
| 36047.8 | 57.5° | 32442.4 | 28836.8 | 26029.1 | 23221.4 | 24116.3 | 25011.5 | 25620.9 | 26230.0 | 20682.3 | 15134.5 |
| 40519.4 | 60° | 36659.1 | 32798.7 | 30141.6 | 27484.6 | 28596.2 | 29707.8 | 28761.4 | 27815.2 | 20966.6 | 14117.8 |
| 44144.1 | 62.5° | 40471.5 | 36798.7 | 34364.4 | 31930.3 | 32055.8 | 32181.1 | 29595.7 | 27010.3 | 19769.2 | 12528.2 |
| 44521.7 | 65° | 40960.6 | 37399.1 | 34305.6 | 31212.4 | 30732.5 | 30252.3 | 27825.8 | 25399.3 | 18075.0 | 10750.8 |
| 41905.6 | 67.5° | 38328.9 | 34752.2 | 31529.4 | 28306.4 | 28081.5 | 27856.4 | 25548.5 | 23240.7 | 16058.8 | 8877.0 |
| 37789.3 | 70° | 34711.5 | 31633.5 | 28751.5 | 25869.3 | 25768.5 | 25667.9 | 23157.5 | 20647.3 | 13858.8 | 7070.4 |
| 32583.0 | 72.5° | 30277.9 | 27972.7 | 25717.7 | 23462.7 | 23390.6 | 23318.2 | 20437.4 | 17556.8 | 11473.9 | 5391.2 |
| 26899.8 | 75° | 25277.1 | 23654.3 | 21899.9 | 20145.5 | 19877.8 | 19610.1 | 16628.7 | 13647.3 | 8740.0 | 3832.6 |
| 21052.7 | 77.5° | 19901.6 | 18750.7 | 17417.0 | 16083.3 | 15700.2 | 15317.1 | 12533.8 | 9750.8 | 6117.2 | 2483.6 |
| 15239.6 | 80° | 14635.3 | 14030.9 | 13024.1 | 12016.8 | 11540.7 | 11064.5 | 8723.3 | 6381.8 | 3941.2 | 1500.6 |
| 9865.9 | 82.5° | 9614.0 | 9361.8 | 8668.5 | 7975.2 | 7443.2 | 6911.3 | 5310.4 | 3709.7 | 2281.1 | 852.6 |
| 5661.5 | 85° | 5518.4 | 5375.3 | 4805.8 | 4236.1 | 3783.7 | 3331.3 | 2481.8 | 1632.2 | 1026.1 | 420.2 |
| 2175.1 | 87.5° | 2163.1 | 2150.9 | 1866.0 | 1581.2 | 1328.8 | 1076.4 | 790.8 | 505.3 | 336.1 | 166.9 |
| 0.0 | 90° | 0.0 | 0.0 | 0.0 | 0.0 | 0.0 | 0.0 | 0.0 | 0.0 | 0.0 | 0.0 |

REPORT NUMBER: P951770
 CATALOG NUMBER: GLAN-SB5D-827-U-SLL

CANDELA DISTRIBUTION (continued):

| 105° | | 110° | 115° | 120° | 125° | 130° | 135° | 140° | 145° | 150° | 155° |
|---------|-------|--------|--------|--------|--------|--------|--------|--------|--------|--------|--------|
| 6124.5 | 0° | 6124.5 | 6124.5 | 6124.5 | 6124.5 | 6124.5 | 6124.5 | 6124.5 | 6124.5 | 6124.5 | 6124.5 |
| 6431.4 | 2.5° | 6377.8 | 6323.8 | 6269.7 | 6218.0 | 6166.3 | 6116.3 | 6060.6 | 6015.4 | 5970.6 | 5929.9 |
| 6747.5 | 5° | 6636.4 | 6524.3 | 6412.4 | 6307.8 | 6203.2 | 6104.5 | 6007.0 | 5921.9 | 5836.6 | 5765.2 |
| 7042.0 | 7.5° | 6871.8 | 6706.2 | 6540.5 | 6394.5 | 6248.6 | 6113.9 | 5987.7 | 5874.4 | 5761.4 | 5667.4 |
| 7271.6 | 10° | 7046.9 | 6845.8 | 6644.3 | 6471.8 | 6298.9 | 6132.7 | 5997.1 | 5877.7 | 5758.3 | 5664.3 |
| 7429.8 | 12.5° | 7175.0 | 6937.6 | 6700.3 | 6505.0 | 6309.7 | 6135.1 | 6008.9 | 5911.1 | 5813.8 | 5751.3 |
| 7528.5 | 15° | 7252.1 | 6978.8 | 6705.5 | 6479.4 | 6253.3 | 6059.9 | 5958.8 | 5912.0 | 5865.5 | 5874.0 |
| 7575.7 | 17.5° | 7274.2 | 6956.9 | 6639.6 | 6367.7 | 6095.8 | 5868.3 | 5806.1 | 5823.2 | 5840.1 | 5942.6 |
| 7612.6 | 20° | 7281.2 | 6896.8 | 6512.3 | 6175.3 | 5838.2 | 5573.4 | 5556.9 | 5636.8 | 5716.7 | 5894.7 |
| 7662.4 | 22.5° | 7290.6 | 6823.0 | 6355.3 | 5949.4 | 5543.5 | 5242.0 | 5274.2 | 5392.4 | 5510.6 | 5713.7 |
| 7752.7 | 25° | 7327.8 | 6750.1 | 6172.7 | 5697.2 | 5222.0 | 4913.0 | 4999.9 | 5136.3 | 5272.6 | 5455.2 |
| 7893.7 | 27.5° | 7405.3 | 6701.5 | 5997.6 | 5466.7 | 4935.8 | 4654.5 | 4760.2 | 4891.8 | 5023.4 | 5173.6 |
| 8076.3 | 30° | 7511.6 | 6678.7 | 5845.3 | 5274.0 | 4702.7 | 4466.5 | 4549.4 | 4653.8 | 4758.6 | 4883.1 |
| 8266.9 | 32.5° | 7603.2 | 6650.5 | 5697.2 | 5107.8 | 4518.2 | 4327.8 | 4364.7 | 4426.5 | 4488.3 | 4587.7 |
| 8484.0 | 35° | 7670.4 | 6597.3 | 5524.7 | 4944.5 | 4364.2 | 4205.6 | 4190.3 | 4207.2 | 4224.4 | 4300.3 |
| 8727.3 | 37.5° | 7710.4 | 6506.4 | 5302.4 | 4752.2 | 4202.1 | 4063.4 | 4007.5 | 3988.7 | 3969.9 | 4024.4 |
| 9036.1 | 40° | 7735.5 | 6381.1 | 5027.0 | 4522.9 | 4018.8 | 3893.0 | 3807.2 | 3764.7 | 3722.2 | 3761.4 |
| 9440.1 | 42.5° | 7783.2 | 6251.9 | 4721.0 | 4269.8 | 3818.5 | 3702.7 | 3594.6 | 3538.2 | 3481.8 | 3513.7 |
| 9971.7 | 45° | 7867.1 | 6131.8 | 4396.7 | 4000.9 | 3605.1 | 3487.6 | 3383.0 | 3328.1 | 3273.3 | 3300.1 |
| 10538.1 | 47.5° | 7924.7 | 6032.6 | 4140.5 | 3788.2 | 3435.9 | 3284.3 | 3194.3 | 3148.3 | 3102.2 | 3127.6 |
| 11063.6 | 50° | 7887.1 | 5924.5 | 3961.9 | 3647.0 | 3332.0 | 3132.8 | 3028.2 | 2987.3 | 2946.6 | 2986.1 |
| 11404.8 | 52.5° | 7655.6 | 5741.9 | 3828.4 | 3553.9 | 3279.6 | 3050.5 | 2904.3 | 2863.9 | 2823.7 | 2883.2 |
| 11329.6 | 55° | 7177.4 | 5439.2 | 3701.0 | 3486.5 | 3271.9 | 3058.7 | 2838.5 | 2774.6 | 2710.9 | 2795.3 |
| 10800.4 | 57.5° | 6466.4 | 5012.4 | 3558.1 | 3406.5 | 3255.0 | 3066.9 | 2799.0 | 2706.0 | 2612.9 | 2703.6 |
| 9815.4 | 60° | 5513.0 | 4458.2 | 3403.5 | 3284.3 | 3165.2 | 3041.1 | 2761.9 | 2641.3 | 2520.5 | 2600.2 |
| 8483.6 | 62.5° | 4439.0 | 3795.0 | 3151.1 | 3071.9 | 2992.9 | 2977.6 | 2718.7 | 2567.8 | 2417.1 | 2467.7 |
| 7124.7 | 65° | 3498.9 | 3198.3 | 2897.7 | 2860.4 | 2823.0 | 2824.9 | 2627.5 | 2467.2 | 2306.7 | 2326.2 |
| 5793.6 | 67.5° | 2710.2 | 2624.9 | 2539.3 | 2560.3 | 2580.9 | 2575.8 | 2464.8 | 2331.4 | 2197.9 | 2191.8 |
| 4561.6 | 70° | 2052.9 | 2077.3 | 2101.5 | 2198.3 | 2294.9 | 2294.9 | 2258.5 | 2163.5 | 2068.6 | 2047.5 |
| 3487.4 | 72.5° | 1583.5 | 1657.1 | 1730.9 | 1868.1 | 2005.1 | 2028.2 | 2028.7 | 1963.6 | 1898.5 | 1867.4 |
| 2531.1 | 75° | 1229.6 | 1296.3 | 1363.1 | 1516.8 | 1670.5 | 1776.7 | 1767.8 | 1717.7 | 1667.4 | 1637.8 |
| 1715.1 | 77.5° | 946.6 | 992.0 | 1037.6 | 1186.8 | 1336.1 | 1511.1 | 1506.4 | 1466.3 | 1426.1 | 1396.0 |
| 1105.0 | 80° | 709.7 | 728.5 | 747.3 | 873.8 | 1000.0 | 1209.2 | 1208.4 | 1174.8 | 1141.0 | 1115.9 |
| 679.7 | 82.5° | 507.2 | 510.5 | 514.2 | 607.3 | 700.3 | 879.0 | 888.8 | 872.4 | 855.9 | 838.1 |
| 363.3 | 85° | 306.7 | 305.0 | 303.2 | 371.3 | 439.5 | 572.3 | 585.2 | 567.6 | 549.9 | 530.0 |
| 150.6 | 87.5° | 134.4 | 132.8 | 131.1 | 158.9 | 186.8 | 242.1 | 258.5 | 251.5 | 244.4 | 240.7 |
| 0.0 | 90° | 0.0 | 0.0 | 0.0 | 0.0 | 0.0 | 0.0 | 0.0 | 0.0 | 0.0 | 0.0 |

REPORT NUMBER: P951770
 CATALOG NUMBER: GLAN-SB5D-827-U-SLL

CANDELA DISTRIBUTION (continued):

| 160° | | 165° | 170° | 175° | 180° | 185° | 190° | 195° | 200° | 205° | 210° |
|--------|-------|--------|--------|--------|--------|--------|--------|--------|--------|--------|--------|
| 6124.5 | 0° | 6124.5 | 6124.5 | 6124.5 | 6124.5 | 6124.5 | 6124.5 | 6124.5 | 6124.5 | 6124.5 | 6124.5 |
| 5889.5 | 2.5° | 5854.0 | 5818.5 | 5782.8 | 5747.3 | 5719.8 | 5692.1 | 5669.7 | 5647.4 | 5630.0 | 5612.6 |
| 5693.9 | 5° | 5631.0 | 5568.0 | 5510.9 | 5453.5 | 5409.6 | 5365.4 | 5334.6 | 5303.8 | 5282.0 | 5260.1 |
| 5573.4 | 7.5° | 5494.2 | 5414.8 | 5344.7 | 5274.9 | 5222.5 | 5170.3 | 5133.7 | 5097.0 | 5071.9 | 5047.0 |
| 5570.3 | 10° | 5485.0 | 5399.5 | 5320.7 | 5242.0 | 5179.5 | 5116.8 | 5075.9 | 5034.5 | 5010.8 | 4987.0 |
| 5689.2 | 12.5° | 5622.0 | 5555.3 | 5473.7 | 5392.4 | 5312.5 | 5232.6 | 5179.7 | 5126.9 | 5100.3 | 5074.0 |
| 5882.4 | 15° | 5865.0 | 5847.6 | 5776.9 | 5706.2 | 5592.4 | 5478.7 | 5398.3 | 5317.9 | 5281.0 | 5244.4 |
| 6045.1 | 17.5° | 6099.6 | 6153.9 | 6096.8 | 6039.9 | 5889.2 | 5738.6 | 5620.2 | 5501.7 | 5447.2 | 5392.4 |
| 6072.8 | 20° | 6186.8 | 6300.8 | 6274.4 | 6247.9 | 6075.6 | 5903.6 | 5758.3 | 5613.3 | 5543.5 | 5473.5 |
| 5917.2 | 22.5° | 6065.5 | 6213.8 | 6229.8 | 6245.5 | 6081.0 | 5916.5 | 5767.0 | 5617.3 | 5543.8 | 5470.0 |
| 5638.0 | 25° | 5784.0 | 5929.9 | 5984.4 | 6038.7 | 5903.8 | 5769.2 | 5636.1 | 5503.6 | 5439.7 | 5376.0 |
| 5323.6 | 27.5° | 5440.6 | 5557.6 | 5618.3 | 5679.1 | 5583.0 | 5487.1 | 5384.0 | 5280.8 | 5238.0 | 5195.0 |
| 5007.7 | 30° | 5104.8 | 5202.1 | 5251.4 | 5300.8 | 5227.7 | 5154.4 | 5080.6 | 5006.3 | 4984.4 | 4962.3 |
| 4687.4 | 32.5° | 4780.4 | 4873.7 | 4928.5 | 4983.5 | 4916.3 | 4848.8 | 4789.8 | 4730.9 | 4716.5 | 4702.2 |
| 4376.0 | 35° | 4468.1 | 4560.5 | 4626.3 | 4692.1 | 4644.1 | 4596.4 | 4541.9 | 4487.6 | 4465.8 | 4444.1 |
| 4078.7 | 37.5° | 4170.6 | 4262.7 | 4344.0 | 4425.3 | 4403.2 | 4381.2 | 4331.1 | 4280.8 | 4241.1 | 4201.6 |
| 3800.7 | 40° | 3889.5 | 3978.3 | 4071.9 | 4165.6 | 4171.0 | 4176.2 | 4133.7 | 4091.1 | 4033.3 | 3976.0 |
| 3545.9 | 42.5° | 3630.0 | 3714.4 | 3815.5 | 3916.5 | 3943.6 | 3970.6 | 3934.6 | 3898.9 | 3827.2 | 3755.5 |
| 3327.3 | 45° | 3407.3 | 3487.2 | 3592.0 | 3696.8 | 3735.6 | 3774.3 | 3741.9 | 3709.7 | 3627.7 | 3545.9 |
| 3152.7 | 47.5° | 3231.0 | 3309.0 | 3412.4 | 3515.8 | 3560.5 | 3605.1 | 3582.6 | 3560.0 | 3487.2 | 3414.3 |
| 3025.8 | 50° | 3099.6 | 3173.2 | 3265.8 | 3358.4 | 3415.7 | 3473.1 | 3471.6 | 3470.7 | 3412.4 | 3354.1 |
| 2942.4 | 52.5° | 3010.1 | 3077.5 | 3163.8 | 3250.3 | 3318.2 | 3386.1 | 3398.3 | 3410.5 | 3363.1 | 3315.6 |
| 2879.4 | 55° | 2952.3 | 3025.1 | 3100.8 | 3176.2 | 3248.1 | 3320.3 | 3337.2 | 3354.1 | 3312.8 | 3271.4 |
| 2794.3 | 57.5° | 2879.9 | 2965.4 | 3040.2 | 3115.1 | 3187.7 | 3260.1 | 3277.3 | 3294.4 | 3252.6 | 3210.8 |
| 2679.6 | 60° | 2777.9 | 2876.1 | 2952.0 | 3028.2 | 3101.0 | 3173.9 | 3192.7 | 3211.5 | 3170.6 | 3129.9 |
| 2518.2 | 62.5° | 2632.6 | 2747.3 | 2828.4 | 2909.5 | 2976.2 | 3043.0 | 3061.1 | 3079.2 | 3042.3 | 3005.4 |
| 2345.5 | 65° | 2468.1 | 2591.0 | 2668.6 | 2746.2 | 2804.9 | 2863.7 | 2882.2 | 2900.6 | 2865.1 | 2829.6 |
| 2185.6 | 67.5° | 2298.9 | 2412.4 | 2486.0 | 2559.3 | 2610.1 | 2660.8 | 2678.9 | 2696.8 | 2664.1 | 2631.7 |
| 2026.3 | 70° | 2125.9 | 2225.6 | 2289.0 | 2352.5 | 2398.3 | 2444.2 | 2461.5 | 2478.9 | 2452.4 | 2425.8 |
| 1836.6 | 72.5° | 1915.1 | 1993.4 | 2050.7 | 2108.1 | 2153.0 | 2197.9 | 2218.5 | 2239.2 | 2217.1 | 2195.0 |
| 1608.0 | 75° | 1666.3 | 1724.5 | 1776.5 | 1828.4 | 1869.3 | 1910.2 | 1931.8 | 1953.4 | 1942.6 | 1931.8 |
| 1365.9 | 77.5° | 1413.4 | 1460.6 | 1505.3 | 1549.9 | 1592.9 | 1635.7 | 1655.9 | 1676.1 | 1661.1 | 1645.6 |
| 1090.5 | 80° | 1130.0 | 1169.2 | 1206.8 | 1244.4 | 1277.1 | 1309.5 | 1336.3 | 1363.1 | 1356.5 | 1350.2 |
| 820.2 | 82.5° | 816.9 | 813.6 | 800.5 | 787.3 | 856.9 | 926.4 | 972.0 | 1017.6 | 1014.8 | 1011.7 |
| 510.0 | 85° | 493.1 | 475.9 | 439.5 | 403.1 | 468.2 | 533.5 | 589.9 | 646.3 | 641.6 | 636.9 |
| 236.9 | 87.5° | 236.2 | 235.5 | 207.8 | 179.8 | 207.0 | 234.5 | 257.3 | 280.1 | 274.5 | 268.4 |
| 0.0 | 90° | 0.0 | 0.0 | 0.0 | 0.0 | 0.0 | 0.0 | 0.0 | 0.0 | 0.0 | 0.0 |

REPORT NUMBER: P951770
 CATALOG NUMBER: GLAN-SB5D-827-U-SLL

CANDELA DISTRIBUTION (continued):

| 215° | | 220° | 225° | 230° | 235° | 240° | 245° | 250° | 255° | 260° | 265° |
|--------|-------|--------|--------|--------|--------|--------|--------|--------|--------|--------|--------|
| 6124.5 | 0° | 6124.5 | 6124.5 | 6124.5 | 6124.5 | 6124.5 | 6124.5 | 6124.5 | 6124.5 | 6124.5 | 6124.5 |
| 5596.7 | 2.5° | 5580.4 | 5560.5 | 5580.4 | 5596.7 | 5612.6 | 5630.0 | 5647.4 | 5669.7 | 5692.1 | 5719.8 |
| 5243.4 | 5° | 5226.7 | 5210.3 | 5226.7 | 5243.4 | 5260.1 | 5282.0 | 5303.8 | 5334.6 | 5365.4 | 5409.6 |
| 5031.9 | 7.5° | 5017.1 | 5005.8 | 5017.1 | 5031.9 | 5047.0 | 5071.9 | 5097.0 | 5133.7 | 5170.3 | 5222.5 |
| 4974.3 | 10° | 4961.6 | 4956.5 | 4961.6 | 4974.3 | 4987.0 | 5010.8 | 5034.5 | 5075.9 | 5116.8 | 5179.5 |
| 5063.2 | 12.5° | 5052.4 | 5050.5 | 5052.4 | 5063.2 | 5074.0 | 5100.3 | 5126.9 | 5179.7 | 5232.6 | 5312.5 |
| 5230.3 | 15° | 5216.2 | 5215.0 | 5216.2 | 5230.3 | 5244.4 | 5281.0 | 5317.9 | 5398.3 | 5478.7 | 5592.4 |
| 5374.6 | 17.5° | 5356.5 | 5353.6 | 5356.5 | 5374.6 | 5392.4 | 5447.2 | 5501.7 | 5620.2 | 5738.6 | 5889.2 |
| 5451.2 | 20° | 5428.9 | 5421.8 | 5428.9 | 5451.2 | 5473.5 | 5543.5 | 5613.3 | 5758.3 | 5903.6 | 6075.6 |
| 5445.3 | 22.5° | 5420.6 | 5410.0 | 5420.6 | 5445.3 | 5470.0 | 5543.8 | 5617.3 | 5767.0 | 5916.5 | 6081.0 |
| 5352.7 | 25° | 5329.7 | 5316.0 | 5329.7 | 5352.7 | 5376.0 | 5439.7 | 5503.6 | 5636.1 | 5769.2 | 5903.8 |
| 5184.4 | 27.5° | 5173.9 | 5170.3 | 5173.9 | 5184.4 | 5195.0 | 5238.0 | 5280.8 | 5384.0 | 5487.1 | 5583.0 |
| 4962.3 | 30° | 4962.3 | 4965.9 | 4962.3 | 4962.3 | 4962.3 | 4984.4 | 5006.3 | 5080.6 | 5154.4 | 5227.7 |
| 4704.1 | 32.5° | 4706.2 | 4709.7 | 4706.2 | 4704.1 | 4702.2 | 4716.5 | 4730.9 | 4789.8 | 4848.8 | 4916.3 |
| 4439.4 | 35° | 4434.7 | 4432.4 | 4434.7 | 4439.4 | 4444.1 | 4465.8 | 4487.6 | 4541.9 | 4596.4 | 4644.1 |
| 4180.7 | 37.5° | 4159.8 | 4148.0 | 4159.8 | 4180.7 | 4201.6 | 4241.1 | 4280.8 | 4331.1 | 4381.2 | 4403.2 |
| 3937.0 | 40° | 3898.4 | 3875.4 | 3898.4 | 3937.0 | 3976.0 | 4033.3 | 4091.1 | 4133.7 | 4176.2 | 4171.0 |
| 3698.9 | 42.5° | 3642.3 | 3605.1 | 3642.3 | 3698.9 | 3755.5 | 3827.2 | 3898.9 | 3934.6 | 3970.6 | 3943.6 |
| 3479.4 | 45° | 3412.9 | 3370.1 | 3412.9 | 3479.4 | 3545.9 | 3627.7 | 3709.7 | 3741.9 | 3774.3 | 3735.6 |
| 3352.7 | 47.5° | 3291.4 | 3250.3 | 3291.4 | 3352.7 | 3414.3 | 3487.2 | 3560.0 | 3582.6 | 3605.1 | 3560.5 |
| 3297.3 | 50° | 3240.4 | 3200.9 | 3240.4 | 3297.3 | 3354.1 | 3412.4 | 3470.7 | 3471.6 | 3473.1 | 3415.7 |
| 3264.6 | 52.5° | 3213.8 | 3177.4 | 3213.8 | 3264.6 | 3315.6 | 3363.1 | 3410.5 | 3398.3 | 3386.1 | 3318.2 |
| 3226.8 | 55° | 3182.1 | 3149.2 | 3182.1 | 3226.8 | 3271.4 | 3312.8 | 3354.1 | 3337.2 | 3320.3 | 3248.1 |
| 3166.6 | 57.5° | 3122.2 | 3088.1 | 3122.2 | 3166.6 | 3210.8 | 3252.6 | 3294.4 | 3277.3 | 3260.1 | 3187.7 |
| 3084.3 | 60° | 3038.7 | 3003.5 | 3038.7 | 3084.3 | 3129.9 | 3170.6 | 3211.5 | 3192.7 | 3173.9 | 3101.0 |
| 2957.4 | 62.5° | 2909.5 | 2867.2 | 2909.5 | 2957.4 | 3005.4 | 3042.3 | 3079.2 | 3061.1 | 3043.0 | 2976.2 |
| 2783.0 | 65° | 2736.8 | 2700.3 | 2736.8 | 2783.0 | 2829.6 | 2865.1 | 2900.6 | 2882.2 | 2863.7 | 2804.9 |
| 2588.5 | 67.5° | 2545.2 | 2512.3 | 2545.2 | 2588.5 | 2631.7 | 2664.1 | 2696.8 | 2678.9 | 2660.8 | 2610.1 |
| 2384.5 | 70° | 2343.1 | 2305.5 | 2343.1 | 2384.5 | 2425.8 | 2452.4 | 2478.9 | 2461.5 | 2444.2 | 2398.3 |
| 2155.6 | 72.5° | 2116.3 | 2079.9 | 2116.3 | 2155.6 | 2195.0 | 2217.1 | 2239.2 | 2218.5 | 2197.9 | 2153.0 |
| 1898.7 | 75° | 1865.6 | 1830.8 | 1865.6 | 1898.7 | 1931.8 | 1942.6 | 1953.4 | 1931.8 | 1910.2 | 1869.3 |
| 1612.2 | 77.5° | 1578.8 | 1551.1 | 1578.8 | 1612.2 | 1645.6 | 1661.1 | 1676.1 | 1655.9 | 1635.7 | 1592.9 |
| 1305.3 | 80° | 1260.2 | 1208.0 | 1260.2 | 1305.3 | 1350.2 | 1356.5 | 1363.1 | 1336.3 | 1309.5 | 1277.1 |
| 973.9 | 82.5° | 935.8 | 902.5 | 935.8 | 973.9 | 1011.7 | 1014.8 | 1017.6 | 972.0 | 926.4 | 856.9 |
| 607.3 | 85° | 577.7 | 547.6 | 577.7 | 607.3 | 636.9 | 641.6 | 646.3 | 589.9 | 533.5 | 468.2 |
| 253.3 | 87.5° | 237.8 | 223.3 | 237.8 | 253.3 | 268.4 | 274.5 | 280.1 | 257.3 | 234.5 | 207.0 |
| 0.0 | 90° | 0.0 | 0.0 | 0.0 | 0.0 | 0.0 | 0.0 | 0.0 | 0.0 | 0.0 | 0.0 |

REPORT NUMBER: P951770
 CATALOG NUMBER: GLAN-SB5D-827-U-SLL

CANDELA DISTRIBUTION (continued):

| 270° | | 275° | 280° | 285° | 290° | 295° | 300° | 305° | 310° | 315° | 320° |
|--------|-------|--------|--------|--------|--------|--------|--------|--------|--------|--------|--------|
| 6124.5 | 0° | 6124.5 | 6124.5 | 6124.5 | 6124.5 | 6124.5 | 6124.5 | 6124.5 | 6124.5 | 6124.5 | 6124.5 |
| 5747.3 | 2.5° | 5782.8 | 5818.5 | 5854.0 | 5889.5 | 5929.9 | 5970.6 | 6015.4 | 6060.6 | 6116.3 | 6166.3 |
| 5453.5 | 5° | 5510.9 | 5568.0 | 5631.0 | 5693.9 | 5765.2 | 5836.6 | 5921.9 | 6007.0 | 6104.5 | 6203.2 |
| 5274.9 | 7.5° | 5344.7 | 5414.8 | 5494.2 | 5573.4 | 5667.4 | 5761.4 | 5874.4 | 5987.7 | 6113.9 | 6248.6 |
| 5242.0 | 10° | 5320.7 | 5399.5 | 5485.0 | 5570.3 | 5664.3 | 5758.3 | 5877.7 | 5997.1 | 6132.7 | 6298.9 |
| 5392.4 | 12.5° | 5473.7 | 5555.3 | 5622.0 | 5689.2 | 5751.3 | 5813.8 | 5911.1 | 6008.9 | 6135.1 | 6309.7 |
| 5706.2 | 15° | 5776.9 | 5847.6 | 5865.0 | 5882.4 | 5874.0 | 5865.5 | 5912.0 | 5958.8 | 6059.9 | 6253.3 |
| 6039.9 | 17.5° | 6096.8 | 6153.9 | 6099.6 | 6045.1 | 5942.6 | 5840.1 | 5823.2 | 5806.1 | 5868.3 | 6095.8 |
| 6247.9 | 20° | 6274.4 | 6300.8 | 6186.8 | 6072.8 | 5894.7 | 5716.7 | 5636.8 | 5556.9 | 5573.4 | 5838.2 |
| 6245.5 | 22.5° | 6229.8 | 6213.8 | 6065.5 | 5917.2 | 5713.7 | 5510.6 | 5392.4 | 5274.2 | 5242.0 | 5543.5 |
| 6038.7 | 25° | 5984.4 | 5929.9 | 5784.0 | 5638.0 | 5455.2 | 5272.6 | 5136.3 | 4999.9 | 4913.0 | 5222.0 |
| 5679.1 | 27.5° | 5618.3 | 5557.6 | 5440.6 | 5323.6 | 5173.6 | 5023.4 | 4891.8 | 4760.2 | 4654.5 | 4935.8 |
| 5300.8 | 30° | 5251.4 | 5202.1 | 5104.8 | 5007.7 | 4883.1 | 4758.6 | 4653.8 | 4549.4 | 4466.5 | 4702.7 |
| 4983.5 | 32.5° | 4928.5 | 4873.7 | 4780.4 | 4687.4 | 4587.7 | 4488.3 | 4426.5 | 4364.7 | 4327.8 | 4518.2 |
| 4692.1 | 35° | 4626.3 | 4560.5 | 4468.1 | 4376.0 | 4300.3 | 4224.4 | 4207.2 | 4190.3 | 4205.6 | 4364.2 |
| 4425.3 | 37.5° | 4344.0 | 4262.7 | 4170.6 | 4078.7 | 4024.4 | 3969.9 | 3988.7 | 4007.5 | 4063.4 | 4202.1 |
| 4165.6 | 40° | 4071.9 | 3978.3 | 3889.5 | 3800.7 | 3761.4 | 3722.2 | 3764.7 | 3807.2 | 3893.0 | 4018.8 |
| 3916.5 | 42.5° | 3815.5 | 3714.4 | 3630.0 | 3545.9 | 3513.7 | 3481.8 | 3538.2 | 3594.6 | 3702.7 | 3818.5 |
| 3696.8 | 45° | 3592.0 | 3487.2 | 3407.3 | 3327.3 | 3300.1 | 3273.3 | 3328.1 | 3383.0 | 3487.6 | 3605.1 |
| 3515.8 | 47.5° | 3412.4 | 3309.0 | 3231.0 | 3152.7 | 3127.6 | 3102.2 | 3148.3 | 3194.3 | 3284.3 | 3435.9 |
| 3358.4 | 50° | 3265.8 | 3173.2 | 3099.6 | 3025.8 | 2986.1 | 2946.6 | 2987.3 | 3028.2 | 3132.8 | 3332.0 |
| 3250.3 | 52.5° | 3163.8 | 3077.5 | 3010.1 | 2942.4 | 2883.2 | 2823.7 | 2863.9 | 2904.3 | 3050.5 | 3279.6 |
| 3176.2 | 55° | 3100.8 | 3025.1 | 2952.3 | 2879.4 | 2795.3 | 2710.9 | 2774.6 | 2838.5 | 3058.7 | 3271.9 |
| 3115.1 | 57.5° | 3040.2 | 2965.4 | 2879.9 | 2794.3 | 2703.6 | 2612.9 | 2706.0 | 2799.0 | 3066.9 | 3255.0 |
| 3028.2 | 60° | 2952.0 | 2876.1 | 2777.9 | 2679.6 | 2600.2 | 2520.5 | 2641.3 | 2761.9 | 3041.1 | 3165.2 |
| 2909.5 | 62.5° | 2828.4 | 2747.3 | 2632.6 | 2518.2 | 2467.7 | 2417.1 | 2567.8 | 2718.7 | 2977.6 | 2992.9 |
| 2746.2 | 65° | 2668.6 | 2591.0 | 2468.1 | 2345.5 | 2326.2 | 2306.7 | 2467.2 | 2627.5 | 2824.9 | 2823.0 |
| 2559.3 | 67.5° | 2486.0 | 2412.4 | 2298.9 | 2185.6 | 2191.8 | 2197.9 | 2331.4 | 2464.8 | 2575.8 | 2580.9 |
| 2352.5 | 70° | 2289.0 | 2225.6 | 2125.9 | 2026.3 | 2047.5 | 2068.6 | 2163.5 | 2258.5 | 2294.9 | 2294.9 |
| 2108.1 | 72.5° | 2050.7 | 1993.4 | 1915.1 | 1836.6 | 1867.4 | 1898.5 | 1963.6 | 2028.7 | 2028.2 | 2005.1 |
| 1828.4 | 75° | 1776.5 | 1724.5 | 1666.3 | 1608.0 | 1637.8 | 1667.4 | 1717.7 | 1767.8 | 1776.7 | 1670.5 |
| 1549.9 | 77.5° | 1505.3 | 1460.6 | 1413.4 | 1365.9 | 1396.0 | 1426.1 | 1466.3 | 1506.4 | 1511.1 | 1336.1 |
| 1244.4 | 80° | 1206.8 | 1169.2 | 1130.0 | 1090.5 | 1115.9 | 1141.0 | 1174.8 | 1208.4 | 1209.2 | 1000.0 |
| 787.3 | 82.5° | 800.5 | 813.6 | 816.9 | 820.2 | 838.1 | 855.9 | 872.4 | 888.8 | 879.0 | 700.3 |
| 403.1 | 85° | 439.5 | 475.9 | 493.1 | 510.0 | 530.0 | 549.9 | 567.6 | 585.2 | 572.3 | 439.5 |
| 179.8 | 87.5° | 207.8 | 235.5 | 236.2 | 236.9 | 240.7 | 244.4 | 251.5 | 258.5 | 242.1 | 186.8 |
| 0.0 | 90° | 0.0 | 0.0 | 0.0 | 0.0 | 0.0 | 0.0 | 0.0 | 0.0 | 0.0 | 0.0 |

REPORT NUMBER: P951770
 CATALOG NUMBER: GLAN-SB5D-827-U-SLL

CANDELA DISTRIBUTION (continued):

| 325° | | 330° | 335° | 340° | 345° | 350° | 355° | 360° |
|--------|-------|--------|--------|--------|---------|---------|---------|---------|
| 6124.5 | 0° | 6124.5 | 6124.5 | 6124.5 | 6124.5 | 6124.5 | 6124.5 | 6124.5 |
| 6218.0 | 2.5° | 6269.7 | 6323.8 | 6377.8 | 6431.4 | 6485.2 | 6535.8 | 6586.3 |
| 6307.8 | 5° | 6412.4 | 6524.3 | 6636.4 | 6747.5 | 6858.9 | 6970.6 | 7082.2 |
| 6394.5 | 7.5° | 6540.5 | 6706.2 | 6871.8 | 7042.0 | 7212.1 | 7396.2 | 7580.4 |
| 6471.8 | 10° | 6644.3 | 6845.8 | 7046.9 | 7271.6 | 7496.5 | 7729.4 | 7962.3 |
| 6505.0 | 12.5° | 6700.3 | 6937.6 | 7175.0 | 7429.8 | 7684.5 | 7940.2 | 8196.2 |
| 6479.4 | 15° | 6705.5 | 6978.8 | 7252.1 | 7528.5 | 7804.9 | 8071.6 | 8338.3 |
| 6367.7 | 17.5° | 6639.6 | 6956.9 | 7274.2 | 7575.7 | 7877.2 | 8147.7 | 8418.2 |
| 6175.3 | 20° | 6512.3 | 6896.8 | 7281.2 | 7612.6 | 7944.0 | 8225.3 | 8506.4 |
| 5949.4 | 22.5° | 6355.3 | 6823.0 | 7290.6 | 7662.4 | 8034.0 | 8321.4 | 8608.6 |
| 5697.2 | 25° | 6172.7 | 6750.1 | 7327.8 | 7752.7 | 8177.4 | 8458.7 | 8740.2 |
| 5466.7 | 27.5° | 5997.6 | 6701.5 | 7405.3 | 7893.7 | 8381.8 | 8650.4 | 8918.8 |
| 5274.0 | 30° | 5845.3 | 6678.7 | 7511.6 | 8076.3 | 8641.0 | 8900.3 | 9159.7 |
| 5107.8 | 32.5° | 5697.2 | 6650.5 | 7603.2 | 8266.9 | 8930.6 | 9187.2 | 9444.1 |
| 4944.5 | 35° | 5524.7 | 6597.3 | 7670.4 | 8484.0 | 9297.7 | 9543.7 | 9789.6 |
| 4752.2 | 37.5° | 5302.4 | 6506.4 | 7710.4 | 8727.3 | 9744.2 | 10057.7 | 10371.2 |
| 4522.9 | 40° | 5027.0 | 6381.1 | 7735.5 | 9036.1 | 10336.4 | 10793.3 | 11250.2 |
| 4269.8 | 42.5° | 4721.0 | 6251.9 | 7783.2 | 9440.1 | 11096.9 | 11756.4 | 12415.9 |
| 4000.9 | 45° | 4396.7 | 6131.8 | 7867.1 | 9971.7 | 12076.3 | 12965.8 | 13855.3 |
| 3788.2 | 47.5° | 4140.5 | 6032.6 | 7924.7 | 10538.1 | 13151.5 | 14403.6 | 15655.5 |
| 3647.0 | 50° | 3961.9 | 5924.5 | 7887.1 | 11063.6 | 14240.0 | 16127.7 | 18015.1 |
| 3553.9 | 52.5° | 3828.4 | 5741.9 | 7655.6 | 11404.8 | 15153.8 | 17938.7 | 20723.6 |
| 3486.5 | 55° | 3701.0 | 5439.2 | 7177.4 | 11329.6 | 15481.6 | 19544.3 | 23607.3 |
| 3406.5 | 57.5° | 3558.1 | 5012.4 | 6466.4 | 10800.4 | 15134.5 | 20682.3 | 26230.0 |
| 3284.3 | 60° | 3403.5 | 4458.2 | 5513.0 | 9815.4 | 14117.8 | 20966.6 | 27815.2 |
| 3071.9 | 62.5° | 3151.1 | 3795.0 | 4439.0 | 8483.6 | 12528.2 | 19769.2 | 27010.3 |
| 2860.4 | 65° | 2897.7 | 3198.3 | 3498.9 | 7124.7 | 10750.8 | 18075.0 | 25399.3 |
| 2560.3 | 67.5° | 2539.3 | 2624.9 | 2710.2 | 5793.6 | 8877.0 | 16058.8 | 23240.7 |
| 2198.3 | 70° | 2101.5 | 2077.3 | 2052.9 | 4561.6 | 7070.4 | 13858.8 | 20647.3 |
| 1868.1 | 72.5° | 1730.9 | 1657.1 | 1583.5 | 3487.4 | 5391.2 | 11473.9 | 17556.8 |
| 1516.8 | 75° | 1363.1 | 1296.3 | 1229.6 | 2531.1 | 3832.6 | 8740.0 | 13647.3 |
| 1186.8 | 77.5° | 1037.6 | 992.0 | 946.6 | 1715.1 | 2483.6 | 6117.2 | 9750.8 |
| 873.8 | 80° | 747.3 | 728.5 | 709.7 | 1105.0 | 1500.6 | 3941.2 | 6381.8 |
| 607.3 | 82.5° | 514.2 | 510.5 | 507.2 | 679.7 | 852.6 | 2281.1 | 3709.7 |
| 371.3 | 85° | 303.2 | 305.0 | 306.7 | 363.3 | 420.2 | 1026.1 | 1632.2 |
| 158.9 | 87.5° | 131.1 | 132.8 | 134.4 | 150.6 | 166.9 | 336.1 | 505.3 |
| 0.0 | 90° | 0.0 | 0.0 | 0.0 | 0.0 | 0.0 | 0.0 | 0.0 |

(END OF REPORT)