

Scaled data based on original data using
LM-79-08 Approved Method: Electrical and Photometric Measurements of Solid-
State Lighting Products

Test Report Prepared for
Cooper Lighting Solutions
(formerly Eaton)

Brand: STREETWORKS

Report Number: P956055

Luminaire Tested: **GLAN-SB8D-827-U-SLR-HSS**

Issue Date: 1/21/2025

Test Information

Test Method: LM-79-08
Report Number: P956055
TEST IS SCALED FROM IESNA LM-79-08 TEST DATA (G2-2411-289-9)
Test Lab: INNOVATION CENTER
Issue Date: 1/21/2025
Manufacturer: COOPER LIGHTING SOLUTIONS (FORMERLY EATON)
Product Line: STREETWORKS
Catalog Number: GLAN-SB8D-827-U-SLR-HSS
Description: GALLEON AREA AND ROADWAY HIGH DENSITY LED LUMINAIRE
(8) 80 CRI, 2700K, 900mA LIGHTSQUARES WITH 26 LEDS EACH AND SPILL LIGHT
ELIMINATOR RIGHT OPTICS WITH HOUSE SIDE SHIELD
Light Source: -
Ballast/Driver: -

Summary

Lumens per Lamp: N/A
Luminaire Lumens: 54608 lumens
Efficiency: N/A
Efficacy: 93.4 lumens/watt
Luminous Opening: Rectangular (W 1.5' x L: 1.5' x H: 0')
IES Classification: Type IV - Short
BUG Rating: B3 - U0 - G5


Input Watts (W): 584.9
Input Voltage (V): NR
Input Current (Ain): NR
Voltage Rise (V): NR
Power Factor: NR
Total Harmonic Distortion (THDi): NR
Frequency (hertz): 60
Stabilization Time: NR
Operation Time: NR
Ambient Temperature (°C): NR
Test Distance: 24 FT



REPORT NUMBER: P956055
CATALOG NUMBER: GLAN-SB8D-827-U-SLR-HSS

Iso-Footcandle Lines of Horizontal Illumination


× Max cd
- - - 1/2 Max cd



Based on 25 foot mounting height. Maximum calculated value = 16.9 fc
Type IV - Short - N/A

REPORT NUMBER: P956055
CATALOG NUMBER: GLAN-SB8D-827-U-SLR-HSS

Luminous Intensity Polar Plot



REPORT NUMBER: P956055

CATALOG NUMBER: GLAN-SB8D-827-U-SLR-HSS


FLUX DISTRIBUTION:

		Downward	Upward	Total
House Side	Lumens	7647.4	0.0	7647.4
	% Fixture	14.0	0.0	14.0
Street Side	Lumens	46960.6	0.0	46960.6
	% Fixture	86.0	0.0	86.0
Total	Lumens	54608.0	0.0	54608.0
	% Fixture	100.0	0.0	100.0

ZONAL LUMENS:

Zone	Lumens	% Fixture
0°-10°	744.5	1.4
10°-20°	2231.6	4.1
20°-30°	3287.7	6.0
30°-40°	4223.8	7.7
40°-50°	6831.1	12.5
50°-60°	11978.9	21.9
60°-70°	14988.9	27.4
70°-80°	8758.8	16.0
80°-90°	1562.7	2.9
90°-100°	0.0	0.0
100°-110°	0.0	0.0
110°-120°	0.0	0.0
120°-130°	0.0	0.0
130°-140°	0.0	0.0
140°-150°	0.0	0.0
150°-160°	0.0	0.0
160°-170°	0.0	0.0
170°-180°	0.0	0.0
0°-90°	54608.0	100.0
0°-180°	54608.0	100.0

Coefficient of Utilization



REPORT NUMBER: P956055


CATALOG NUMBER: GLAN-SB8D-827-U-SLR-HSS

LUMINAIRE CLASSIFICATION SYSTEM LUMEN TABLE AND BUG RATING:

Zone		Lumens	% Fixture	Zone Rating/Lumen Limit		
				B	U	G
FL	(0°-30°)	4259.2	7.8			
FM	(30°-60°)	19139.5	35.0			
FH	(60°-80°)	22059.1	40.4			G5
FVH	(80°-90°)	1502.7	2.8			G5
BL	(0°-30°)	2004.5	3.7	B3/2500		
BM	(30°-60°)	3894.3	7.1	B3/5000		
BH	(60°-80°)	1688.6	3.1	B3/2500		G3/2500
BVH	(80°-90°)	60.0	0.1			G1/100
UL	(90°-100°)	0.0	0.0		U0/0	
UH	(100°-180°)	0.0	0.0		U0/0	

BUG Rating: B3-U0-G5

Type IV Short



REPORT NUMBER: P956055

CATALOG NUMBER: GLAN-SB8D-827-U-SLR-HSS

CANDELA DISTRIBUTION (FULL):

	0°	5°	15°	25°	35°	45°	55°	65°	75°	85°
0°	7561.5	7561.5	7561.5	7561.5	7561.5	7561.5	7561.5	7561.5	7561.5	7561.5
2.5°	8543.3	8396.6	8310.1	8095.7	7881.2	7708.2	7474.9	7320.7	7136.4	6959.6
5°	9521.4	9284.4	8998.5	8607.3	8249.9	7885.0	7531.4	7181.5	6812.8	6474.3
7.5°	10349.0	10006.7	9502.6	8983.5	8528.3	8088.1	7674.3	7211.6	6763.9	6233.5
10°	10981.0	10544.7	9882.6	9201.7	8678.8	8234.8	7832.3	7441.1	6989.6	6350.1
12.5°	11364.8	10898.3	10112.0	9314.5	8716.4	8219.8	7907.6	7734.5	7557.7	6921.9
15°	11646.9	11142.8	10273.8	9393.5	8629.8	8020.4	7790.9	7964.0	8167.1	7760.8
17.5°	11940.3	11409.9	10484.5	9427.4	8396.6	7632.9	7535.1	7982.8	8453.0	8434.2
20°	12218.7	11692.0	10668.8	9404.8	8020.4	7162.7	7249.2	7821.0	8366.5	8596.0
22.5°	12538.5	11981.7	10845.6	9318.3	7531.4	6722.6	6993.4	7565.2	8043.0	8313.8
25°	12929.7	12346.6	11093.9	9190.4	7004.7	6357.6	6733.8	7268.0	7655.5	7843.6
27.5°	13351.1	12783.0	11425.0	9122.7	6579.6	6098.1	6440.4	6914.4	7260.5	7392.2
30°	13874.0	13290.9	11816.2	9047.4	6301.2	5947.6	6135.7	6504.4	6842.9	6974.6
32.5°	14445.8	13855.2	12192.4	8866.8	6131.9	5834.7	5838.5	6071.7	6380.2	6538.2
35°	15160.5	14532.3	12594.9	8471.8	5996.5	5703.1	5548.8	5661.7	5917.5	6105.6
37.5°	16180.0	15420.1	13087.7	7907.6	5797.1	5499.9	5244.1	5270.5	5466.1	5673.0
40°	17587.0	16612.6	13667.1	7320.7	5511.2	5214.0	4909.3	4898.0	5041.0	5244.1
42.5°	19490.5	18188.9	14363.0	6760.2	5236.6	4867.9	4555.7	4536.9	4649.7	4826.5
45°	22003.5	20205.3	15217.0	6278.6	5022.2	4529.4	4220.9	4213.4	4307.4	4461.6
47.5°	25219.9	23007.9	16070.9	5951.4	4909.3	4262.3	3946.3	3961.3	4044.1	4183.3
50°	29384.4	26660.7	16330.5	5785.8	4909.3	4119.3	3701.7	3777.0	3844.7	3950.0
52.5°	34376.4	30166.8	15472.8	5635.4	4939.4	4138.1	3494.8	3656.6	3705.5	3795.8
55°	39003.6	31886.0	13302.2	5428.5	4946.9	4254.7	3318.0	3558.8	3649.1	3682.9
57.5°	41689.6	31295.4	10755.3	5078.6	4916.8	4333.7	3205.2	3438.4	3611.4	3634.0
60°	41178.0	29222.6	7918.8	4811.5	4694.9	4303.6	3171.3	3254.1	3528.7	3562.5
62.5°	37235.5	25746.6	5496.2	4604.6	4205.8	4172.0	3160.0	2964.4	3348.1	3430.9
65°	29929.8	20269.2	3882.3	3965.1	3686.7	3886.1	3099.8	2663.4	3129.9	3242.8
67.5°	21713.8	13716.0	2802.6	3212.7	3340.6	3423.3	2964.4	2445.2	2881.6	3032.1
70°	13934.2	7407.2	1967.5	2121.7	2813.9	2908.0	2731.2	2249.6	2629.6	2802.6
72.5°	9905.1	4375.1	1414.5	1486.0	2260.9	2422.7	2403.9	2031.4	2336.2	2546.8
75°	6835.4	2411.4	955.5	1060.9	1640.2	1967.5	1854.6	1745.5	1978.8	2193.2
77.5°	4284.8	1079.7	571.8	737.3	1075.9	1546.1	1271.5	1350.5	1542.4	1741.8
80°	2385.1	417.6	319.8	489.0	586.9	1124.8	703.5	869.0	1136.1	1279.1
82.5°	519.1	52.7	143.0	210.7	229.5	654.6	372.4	504.1	714.8	703.5
85°	0.0	0.0	26.3	30.1	15.0	282.1	135.4	165.5	233.2	218.2
87.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	7.5
90°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0

REPORT NUMBER: P956055

CATALOG NUMBER: GLAN-SB8D-827-U-SLR-HSS

CANDELA DISTRIBUTION (continued):

90°		95°	105°	115°	125°	135°	145°	155°	165°	175°	180°
7561.5	0°	7561.5	7561.5	7561.5	7561.5	7561.5	7561.5	7561.5	7561.5	7561.5	7561.5
6801.6	2.5°	6771.5	6587.1	6451.7	6384.0	6327.6	6380.2	6410.3	6410.3	6538.2	6613.5
6267.4	5°	6135.7	5804.6	5552.6	5383.3	5281.7	5315.6	5353.2	5394.6	5556.4	5665.5
5951.4	7.5°	5695.5	5187.7	4804.0	4567.0	4442.8	4461.6	4488.0	4521.8	4679.8	4788.9
5996.5	10°	5612.8	4883.0	4341.3	4029.0	3878.5	3852.2	3837.2	3825.9	3919.9	4002.7
6508.1	12.5°	5951.4	4898.0	4141.9	3761.9	3577.6	3498.6	3408.3	3336.8	3351.9	3404.5
7283.1	15°	6557.0	5089.9	4077.9	3622.7	3393.3	3261.6	3156.3	3069.7	3050.9	3069.7
7960.2	17.5°	7249.2	5349.5	4070.4	3502.3	3216.4	3081.0	2994.5	2915.5	2889.2	2892.9
8340.2	20°	7708.2	5556.4	4047.8	3366.9	3047.2	2926.8	2851.5	2772.5	2746.2	2753.7
8234.8	22.5°	7753.3	5665.5	4014.0	3216.4	2877.9	2776.3	2701.1	2629.6	2625.8	2625.8
7839.8	25°	7508.8	5665.5	3942.5	3081.0	2716.1	2625.8	2558.1	2471.6	2486.6	2494.2
7392.2	27.5°	7128.8	5530.0	3807.1	2971.9	2576.9	2482.9	2415.2	2336.2	2355.0	2366.2
6974.6	30°	6752.6	5357.0	3645.3	2847.8	2445.2	2336.2	2287.2	2219.5	2227.1	2242.1
6560.8	32.5°	6402.8	5172.6	3453.4	2746.2	2313.6	2204.5	2166.9	2091.6	2102.9	2118.0
6154.5	35°	6056.7	4969.5	3227.7	2625.8	2193.2	2084.1	2054.0	1967.5	1975.0	1997.6
5748.2	37.5°	5684.3	4755.1	3043.4	2505.4	2076.6	1963.7	1933.6	1843.3	1850.9	1877.2
5326.9	40°	5293.0	4544.4	2862.8	2377.5	1952.4	1839.6	1813.2	1715.4	1723.0	1753.1
4913.1	42.5°	4898.0	4314.9	2723.6	2212.0	1824.5	1704.2	1677.8	1587.5	1598.8	1632.7
4551.9	45°	4533.1	4040.3	2633.3	2027.7	1704.2	1568.7	1542.4	1459.6	1482.2	1519.8
4247.2	47.5°	4220.9	3758.2	2595.7	1873.4	1576.2	1429.5	1407.0	1339.2	1376.9	1418.2
3987.6	50°	3953.8	3487.3	2546.8	1715.4	1455.9	1309.1	1286.6	1241.4	1290.3	1331.7
3810.8	52.5°	3761.9	3178.8	2441.5	1572.5	1350.5	1207.6	1200.1	1177.5	1222.6	1260.2
3679.2	55°	3596.4	2859.1	2272.2	1448.3	1256.5	1121.1	1128.6	1117.3	1154.9	1185.0
3600.2	57.5°	3445.9	2580.7	2057.8	1350.5	1154.9	1045.8	1068.4	1053.3	1072.1	1091.0
3517.4	60°	3265.3	2298.5	1802.0	1241.4	1034.5	970.6	996.9	955.5	951.8	959.3
3366.9	62.5°	2998.3	1918.6	1534.9	1106.0	929.2	887.8	899.1	820.1	759.9	759.9
3145.0	65°	2625.8	1542.4	1286.6	955.5	808.8	775.0	767.4	654.6	571.8	564.3
2904.2	67.5°	2193.2	1267.8	1068.4	805.1	673.4	650.8	658.3	575.6	492.8	485.3
2663.4	70°	1786.9	1049.6	861.5	643.3	519.1	541.7	575.6	492.8	413.8	402.5
2381.3	72.5°	1452.1	835.1	673.4	492.8	383.7	447.7	489.0	402.5	327.3	319.8
2031.4	75°	1121.1	613.2	481.5	334.8	278.4	346.1	383.7	293.4	233.2	222.0
1572.5	77.5°	748.6	380.0	270.9	210.7	165.5	237.0	255.8	154.2	135.4	131.7
1143.6	80°	455.2	176.8	116.6	101.6	56.4	86.5	101.6	64.0	71.5	75.2
609.4	82.5°	229.5	48.9	18.8	3.8	0.0	0.0	30.1	15.0	30.1	37.6
165.5	85°	18.8	0.0	0.0	0.0	0.0	0.0	0.0	0.0	7.5	18.8
0.0	87.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
0.0	90°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0

REPORT NUMBER: P956055

CATALOG NUMBER: GLAN-SB8D-827-U-SLR-HSS

CANDELA DISTRIBUTION (continued):

185°		195°	205°	215°	225°	235°	245°	255°	265°	270°	275°
7561.5	0°	7561.5	7561.5	7561.5	7561.5	7561.5	7561.5	7561.5	7561.5	7561.5	7561.5
6643.6	2.5°	6854.2	7012.2	7162.7	7403.5	7651.7	7896.3	8144.6	8385.3	8471.8	8535.8
5736.9	5°	6064.2	6361.4	6707.5	7185.3	7696.9	8223.6	8757.8	9246.8	9468.8	9619.2
4883.0	7.5°	5247.9	5635.4	6131.9	6850.5	7651.7	8490.7	9329.6	10100.8	10458.1	10747.8
4077.9	10°	4439.1	4860.4	5488.6	6308.7	7392.2	8596.0	9754.7	10815.5	11278.2	11643.1
3498.6	12.5°	3728.1	4123.1	4781.4	5688.0	6985.9	8513.2	9999.2	11274.5	11820.0	12230.0
3084.8	15°	3227.7	3506.1	4089.2	5067.3	6504.4	8246.1	10014.2	11492.7	12090.8	12519.7
2911.7	17.5°	2949.3	3043.4	3423.3	4435.3	5970.2	7896.3	9875.0	11567.9	12207.4	12606.2
2757.5	20°	2798.9	2813.9	2919.3	3615.2	5285.5	7569.0	9743.4	11643.1	12316.5	12651.3
2648.4	22.5°	2678.5	2678.5	2704.8	2956.9	4401.4	7177.7	9702.0	11774.8	12467.0	12673.9
2524.2	25°	2569.4	2569.4	2576.9	2644.6	3487.3	6579.6	9675.7	11978.0	12673.9	12730.3
2400.1	27.5°	2456.5	2460.3	2460.3	2497.9	2810.2	5767.0	9562.8	12241.3	12922.2	12805.6
2279.7	30°	2343.7	2351.2	2351.2	2377.5	2486.6	4815.3	9340.8	12557.3	13245.7	12903.4
2159.3	32.5°	2230.8	2238.3	2238.3	2260.9	2339.9	3844.7	9062.5	12847.0	13573.0	12944.8
2042.7	35°	2114.2	2125.5	2118.0	2148.1	2230.8	3058.4	8708.8	13136.6	13926.6	13076.4
1929.9	37.5°	1997.6	2005.1	2001.3	2031.4	2125.5	2640.9	8298.8	13354.8	14408.2	13369.9
1809.5	40°	1881.0	1877.2	1877.2	1911.1	2012.6	2520.5	7783.4	13700.9	15100.3	13885.2
1689.1	42.5°	1760.6	1760.6	1753.1	1790.7	1914.8	2430.2	7290.6	14321.6	16108.5	14705.3
1576.2	45°	1651.5	1647.7	1632.7	1666.5	1820.8	2272.2	7117.6	15480.3	17598.3	16033.3
1463.4	47.5°	1546.1	1542.4	1504.8	1534.9	1707.9	2129.2	7764.6	17376.3	19663.6	17985.7
1373.1	50°	1452.1	1455.9	1384.4	1410.7	1595.1	2020.2	9167.8	19836.6	22406.0	20615.3
1297.9	52.5°	1365.6	1365.6	1271.5	1286.6	1455.9	1922.3	10503.3	22503.8	26025.0	24283.2
1218.9	55°	1279.1	1271.5	1166.2	1173.7	1316.7	1783.2	10702.7	25107.1	30960.6	29801.9
1132.3	57.5°	1181.2	1166.2	1068.4	1068.4	1188.8	1681.6	9276.9	27108.4	37085.0	37912.6
970.6	60°	1060.9	1049.6	985.6	966.8	1087.2	1771.9	6545.7	27341.6	41035.0	48698.1
771.2	62.5°	906.6	921.7	887.8	861.5	989.4	1839.6	3878.5	25464.4	40079.5	52128.9
598.1	65°	714.8	775.0	767.4	748.6	1087.2	1549.9	2291.0	21860.5	37149.0	49360.2
522.9	67.5°	609.4	650.8	639.5	639.5	1139.9	1177.5	1440.8	17079.1	33116.2	46076.0
436.4	70°	519.1	560.5	519.1	519.1	861.5	714.8	996.9	11925.3	28763.6	42442.0
349.9	72.5°	428.9	470.2	425.1	395.0	688.4	534.2	729.8	7452.4	24633.1	38657.5
248.3	75°	327.3	376.2	342.3	304.7	455.2	398.8	553.0	4330.0	20408.4	33074.8
150.5	77.5°	206.9	270.9	255.8	214.4	334.8	289.7	398.8	2576.9	15747.4	25844.4
90.3	80°	127.9	139.2	143.0	135.4	191.9	195.6	270.9	1467.1	10777.9	18012.1
56.4	82.5°	82.8	82.8	64.0	71.5	94.0	112.9	154.2	553.0	6335.1	10966.0
33.9	85°	60.2	52.7	33.9	33.9	45.1	56.4	60.2	169.3	2569.4	4330.0
15.0	87.5°	30.1	26.3	11.3	15.0	22.6	18.8	15.0	7.5	647.1	1384.4
0.0	90°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0

REPORT NUMBER: P956055

CATALOG NUMBER: GLAN-SB8D-827-U-SLR-HSS

CANDELA DISTRIBUTION (continued):

285°		295°	305°	315°	325°	335°	345°	355°	360°
7561.5	0°	7561.5	7561.5	7561.5	7561.5	7561.5	7561.5	7561.5	7561.5
8678.8	2.5°	8754.0	8870.6	8878.1	8878.1	8776.6	8772.8	8565.9	8543.3
9957.8	5°	10307.7	10382.9	10401.7	10364.1	10160.9	10010.5	9607.9	9521.4
11263.2	7.5°	11729.7	11880.1	11880.1	11789.9	11458.8	11150.3	10567.2	10349.0
12342.9	10°	12865.8	13038.8	13001.2	12816.9	12399.3	11974.2	11267.0	10981.0
12997.4	12.5°	13418.8	13595.6	13497.8	13287.1	12880.8	12433.1	11688.3	11364.8
13185.5	15°	13407.5	13358.6	13257.0	13230.7	13035.1	12696.5	12000.5	11646.9
13068.9	17.5°	12929.7	12515.9	12436.9	12700.2	12948.5	12865.8	12271.4	11940.3
12790.5	20°	12173.6	11451.3	11379.8	11883.9	12591.1	12952.3	12523.4	12218.7
12388.0	22.5°	11376.0	10597.3	10431.8	10988.6	12053.2	12978.6	12843.2	12538.5
11944.1	25°	10619.9	9837.4	9671.9	10191.0	11455.0	12933.5	13189.3	12929.7
11519.0	27.5°	9987.9	9231.8	9077.5	9596.7	10879.5	12805.6	13535.4	13351.1
11097.7	30°	9498.8	8799.1	8686.3	9186.6	10382.9	12647.6	13975.5	13874.0
10706.4	32.5°	9212.9	8701.3	8742.7	9152.8	10115.8	12474.5	14396.9	14445.8
10514.6	35°	9495.1	9517.7	9878.8	10048.1	10364.1	12448.2	14968.7	15160.5
10744.0	37.5°	10898.3	11680.8	12429.4	12290.2	11579.2	12752.9	15822.6	16180.0
11744.7	40°	13287.1	14893.4	16108.5	15578.1	13787.4	13685.9	17052.8	17587.0
13520.3	42.5°	16206.4	18930.0	20931.3	19509.3	16635.2	15318.5	18809.6	19490.5
15668.4	45°	19287.4	23907.0	27059.5	24102.6	19671.1	17605.8	21469.3	22003.5
17681.0	47.5°	22533.9	29956.2	34034.1	29196.3	22485.0	20209.0	25095.8	25219.9
19588.3	50°	26085.2	36588.4	41144.1	34286.1	25201.1	23192.2	29527.3	29384.4
21811.6	52.5°	29467.1	43408.8	48103.7	39398.6	27586.2	26894.0	34669.9	34376.4
24851.2	55°	32694.9	50225.4	55104.6	44311.7	29835.8	31784.5	40779.2	39003.6
29233.9	57.5°	36438.0	56353.6	62320.0	49247.3	32980.8	38134.6	47610.9	41689.6
37626.7	60°	41971.7	63316.9	70479.6	56011.2	38962.2	44808.2	50059.9	41178.0
47678.6	62.5°	49036.6	69719.7	76412.1	62639.7	44970.0	46064.7	46452.2	37235.5
45628.3	65°	50409.7	71341.1	76746.9	64411.6	44195.0	39075.1	37923.9	29929.8
40756.6	67.5°	46768.2	68410.5	72067.1	61112.4	39093.9	30196.9	28458.9	21713.8
37559.0	70°	42682.8	62824.1	63911.3	55503.4	34384.0	22210.4	19219.7	13934.2
35369.6	72.5°	38495.7	55371.7	53122.1	48201.5	30219.5	16172.5	13862.7	9905.1
32250.9	75°	33522.5	45571.9	41843.8	40049.4	25020.5	12692.7	10029.3	6835.4
27740.4	77.5°	26845.1	32077.9	31081.0	31043.4	18802.1	9273.1	6692.5	4284.8
21672.4	80°	18937.5	20818.5	20310.6	23380.3	12613.7	6726.3	4029.0	2385.1
15085.3	82.5°	9167.8	11511.5	11816.2	13922.9	6135.7	3957.5	929.2	519.1
5898.7	85°	3588.9	5552.6	4683.6	5285.5	1723.0	1102.2	22.6	0.0
970.6	87.5°	402.5	643.3	590.6	466.5	210.7	45.1	0.0	0.0
0.0	90°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0

(END OF REPORT)