

Scaled data based on original data using  
LM-79-08 Approved Method: Electrical and Photometric Measurements of Solid-  
State Lighting Products

Test Report Prepared for  
Cooper Lighting Solutions  
(formerly Eaton)

Brand: STREETWORKS

Report Number: P956348

Luminaire Tested: **GLAN-SB9A-740-U-SLL**

Issue Date: 1/21/2025

### Test Information

Test Method: LM-79-08  
Report Number: P956348  
TEST IS SCALED FROM IESNA LM-79-08 TEST DATA (G2-2411-289-8)  
Test Lab: INNOVATION CENTER  
Issue Date: 1/21/2025  
Manufacturer: COOPER LIGHTING SOLUTIONS (FORMERLY EATON)  
Product Line: STREETWORKS  
Catalog Number: GLAN-SB9A-740-U-SLL  
Description: GALLEON AREA AND ROADWAY HIGH DENSITY LED LUMINAIRE  
(9) 70 CRI, 4000K, 350mA LIGHTSQUARES WITH 26 LEDS EACH AND SPILL LIGHT  
ELIMINATOR LEFT OPTICS  
Light Source: -  
Ballast/Driver: -

### Summary

Lumens per Lamp: N/A  
Luminaire Lumens: 43072 lumens  
Efficiency: N/A  
Efficacy: 168.6 lumens/watt  
Luminous Opening: Rectangular (W 1.5' x L: 1.5' x H: 0')  
IES Classification: Type IV - Short  
BUG Rating: B4 - U0 - G5

Input Watts (W): 255.5  
Input Voltage (V): NR  
Input Current (Ain): NR  
Voltage Rise (V): NR  
Power Factor: NR  
Total Harmonic Distortion (THDi): NR  
Frequency (hertz): 60  
Stabilization Time: NR  
Operation Time: NR  
Ambient Temperature (°C): NR  
Test Distance: 24 FT




REPORT NUMBER: P956348

CATALOG NUMBER: GLAN-SB9A-740-U-SLL

## Iso-Footcandle Lines of Horizontal Illumination

× Max cd  
- - - 1/2 Max cd




Based on 25 foot mounting height. Maximum calculated value = 13.1 fc

Type IV - Short - N/A

REPORT NUMBER: P956348  
CATALOG NUMBER: GLAN-SB9A-740-U-SLL

## Luminous Intensity Polar Plot



REPORT NUMBER: P956348

CATALOG NUMBER: GLAN-SB9A-740-U-SLL

**FLUX DISTRIBUTION:**

|                    |           | Downward | Upward | Total   |
|--------------------|-----------|----------|--------|---------|
| <b>House Side</b>  | Lumens    | 10946.7  | 0.0    | 10946.7 |
|                    | % Fixture | 25.4     | 0.0    | 25.4    |
| <b>Street Side</b> | Lumens    | 32125.3  | 0.0    | 32125.3 |
|                    | % Fixture | 74.6     | 0.0    | 74.6    |
| <b>Total</b>       | Lumens    | 43072.0  | 0.0    | 43072.0 |
|                    | % Fixture | 100.0    | 0.0    | 100.0   |

**ZONAL LUMENS:**

| Zone      | Lumens  | % Fixture |
|-----------|---------|-----------|
| 0°-10°    | 587.5   | 1.4       |
| 10°-20°   | 1844.4  | 4.3       |
| 20°-30°   | 2848.9  | 6.6       |
| 30°-40°   | 3610.3  | 8.4       |
| 40°-50°   | 5445.3  | 12.6      |
| 50°-60°   | 8797.7  | 20.4      |
| 60°-70°   | 10967.7 | 25.5      |
| 70°-80°   | 7192.1  | 16.7      |
| 80°-90°   | 1778.1  | 4.1       |
| 90°-100°  | 0.0     | 0.0       |
| 100°-110° | 0.0     | 0.0       |
| 110°-120° | 0.0     | 0.0       |
| 120°-130° | 0.0     | 0.0       |
| 130°-140° | 0.0     | 0.0       |
| 140°-150° | 0.0     | 0.0       |
| 150°-160° | 0.0     | 0.0       |
| 160°-170° | 0.0     | 0.0       |
| 170°-180° | 0.0     | 0.0       |
| 0°-90°    | 43072.0 | 100.0     |
| 0°-180°   | 43072.0 | 100.0     |

**Coefficient of Utilization**



REPORT NUMBER: P956348


CATALOG NUMBER: GLAN-SB9A-740-U-SLL

**LUMINAIRE CLASSIFICATION SYSTEM LUMEN TABLE AND BUG RATING:**

| Zone |             | Lumens  | % Fixture | Zone Rating/Lumen Limit |      |         |
|------|-------------|---------|-----------|-------------------------|------|---------|
|      |             |         |           | B                       | U    | G       |
| FL   | (0°-30°)    | 2897.1  | 6.7       |                         |      |         |
| FM   | (30°-60°)   | 12563.2 | 29.2      |                         |      |         |
| FH   | (60°-80°)   | 15200.3 | 35.3      |                         |      | G5      |
| FVH  | (80°-90°)   | 1464.7  | 3.4       |                         |      | G5      |
| BL   | (0°-30°)    | 2383.8  | 5.5       | B3/2500                 |      |         |
| BM   | (30°-60°)   | 5290.1  | 12.3      | B4/8500                 |      |         |
| BH   | (60°-80°)   | 2959.5  | 6.9       | B4/5000                 |      | G4/5000 |
| BVH  | (80°-90°)   | 313.3   | 0.7       |                         |      | G3/500  |
| UL   | (90°-100°)  | 0.0     | 0.0       |                         | U0/0 |         |
| UH   | (100°-180°) | 0.0     | 0.0       |                         | U0/0 |         |

**BUG Rating: B4-U0-G5**

Type IV Short



REPORT NUMBER: P956348

CATALOG NUMBER: GLAN-SB9A-740-U-SLL

**CANDELA DISTRIBUTION (FULL):**

|       | 0°      | 5°      | 10°     | 15°     | 20°     | 25°     | 30°     | 35°     | 40°     | 45°     |
|-------|---------|---------|---------|---------|---------|---------|---------|---------|---------|---------|
| 0°    | 5922.8  | 5922.8  | 5922.8  | 5922.8  | 5922.8  | 5922.8  | 5922.8  | 5922.8  | 5922.8  | 5922.8  |
| 2.5°  | 6369.4  | 6393.5  | 6417.8  | 6452.1  | 6486.4  | 6506.9  | 6527.3  | 6537.5  | 6547.8  | 6543.2  |
| 5°    | 6848.9  | 6933.2  | 7017.8  | 7101.4  | 7185.3  | 7230.7  | 7276.2  | 7303.7  | 7331.4  | 7352.3  |
| 7.5°  | 7330.7  | 7468.0  | 7605.1  | 7728.5  | 7851.9  | 7926.2  | 8000.5  | 8040.7  | 8080.7  | 8100.1  |
| 10°   | 7700.1  | 7862.3  | 8024.6  | 8169.4  | 8314.2  | 8401.9  | 8489.2  | 8528.2  | 8567.1  | 8581.9  |
| 12.5° | 7926.2  | 8102.1  | 8277.8  | 8408.7  | 8539.2  | 8602.8  | 8666.4  | 8687.8  | 8709.2  | 8711.4  |
| 15°   | 8063.7  | 8215.5  | 8367.1  | 8449.2  | 8531.4  | 8533.7  | 8536.0  | 8513.2  | 8490.5  | 8463.7  |
| 17.5° | 8141.0  | 8243.5  | 8346.0  | 8347.6  | 8348.9  | 8256.9  | 8164.8  | 8080.5  | 7996.0  | 7936.4  |
| 20°   | 8226.2  | 8261.9  | 8297.8  | 8189.8  | 8081.9  | 7878.7  | 7675.5  | 7527.6  | 7379.6  | 7288.7  |
| 22.5° | 8325.1  | 8278.2  | 8231.4  | 8007.8  | 7784.1  | 7485.3  | 7186.4  | 7001.4  | 6816.4  | 6716.0  |
| 25°   | 8452.3  | 8304.6  | 8156.9  | 7817.3  | 7477.8  | 7114.8  | 6751.9  | 6557.3  | 6363.2  | 6268.2  |
| 27.5° | 8625.1  | 8361.0  | 8096.7  | 7646.9  | 7197.3  | 6795.1  | 6392.8  | 6201.4  | 6010.3  | 5920.5  |
| 30°   | 8858.0  | 8464.2  | 8070.5  | 7516.9  | 6963.2  | 6544.1  | 6125.0  | 5947.5  | 5770.0  | 5686.4  |
| 32.5° | 9133.0  | 8593.7  | 8054.6  | 7428.2  | 6801.9  | 6408.0  | 6014.1  | 5874.8  | 5735.3  | 5675.0  |
| 35°   | 9467.1  | 8807.1  | 8147.3  | 7494.6  | 6842.1  | 6568.5  | 6295.0  | 6262.5  | 6230.0  | 6225.0  |
| 37.5° | 10029.6 | 9253.3  | 8476.9  | 7883.7  | 7290.5  | 7272.8  | 7255.1  | 7403.7  | 7552.3  | 7629.6  |
| 40°   | 10879.6 | 10035.3 | 9191.0  | 8749.8  | 8308.7  | 8620.1  | 8931.4  | 9292.8  | 9654.2  | 9834.2  |
| 42.5° | 12006.9 | 11169.2 | 10331.4 | 10077.3 | 9823.3  | 10502.4 | 11181.4 | 11838.7 | 12496.0 | 12881.9 |
| 45°   | 13399.0 | 12646.5 | 11893.7 | 11781.7 | 11669.4 | 12757.4 | 13845.6 | 14925.6 | 16005.8 | 16661.5 |
| 47.5° | 15139.9 | 14407.8 | 13675.6 | 13652.8 | 13630.1 | 15199.7 | 16768.8 | 18349.9 | 19930.8 | 20859.2 |
| 50°   | 17421.7 | 16517.4 | 15613.3 | 15617.2 | 15621.0 | 17643.8 | 19666.5 | 21753.6 | 23840.6 | 25102.5 |
| 52.5° | 20041.1 | 18946.0 | 17851.3 | 17740.6 | 17629.7 | 20045.8 | 22462.0 | 25044.3 | 27626.3 | 29138.9 |
| 55°   | 22829.7 | 21747.9 | 20666.1 | 20234.5 | 19802.9 | 22492.0 | 25180.9 | 28259.3 | 31337.7 | 33136.6 |
| 57.5° | 25366.1 | 24777.0 | 24187.7 | 23322.0 | 22456.5 | 25171.8 | 27887.0 | 31373.9 | 34860.5 | 37091.2 |
| 60°   | 26899.1 | 27814.1 | 28729.3 | 27654.3 | 26579.3 | 29148.9 | 31718.4 | 35451.6 | 39184.8 | 41595.8 |
| 62.5° | 26120.6 | 28620.9 | 31121.1 | 31000.0 | 30878.6 | 33232.5 | 35586.6 | 39138.5 | 42690.1 | 44918.5 |
| 65°   | 24562.7 | 26909.3 | 29255.9 | 29720.2 | 30184.3 | 33175.7 | 36167.3 | 39611.4 | 43055.3 | 44952.6 |
| 67.5° | 22475.2 | 24707.0 | 26938.8 | 27156.6 | 27374.1 | 30490.9 | 33607.5 | 37066.4 | 40525.3 | 42011.7 |
| 70°   | 19967.2 | 22394.7 | 24822.5 | 24919.7 | 25017.2 | 27804.5 | 30591.6 | 33568.2 | 36544.6 | 37370.7 |
| 72.5° | 16978.5 | 19764.2 | 22550.2 | 22620.2 | 22689.9 | 24870.6 | 27051.3 | 29280.7 | 31509.8 | 31593.4 |
| 75°   | 13197.8 | 16081.0 | 18964.2 | 19223.1 | 19482.0 | 21178.6 | 22875.2 | 24444.5 | 26013.8 | 25593.4 |
| 77.5° | 9429.6  | 12121.0 | 14812.6 | 15183.1 | 15553.5 | 16843.3 | 18133.1 | 19246.1 | 20359.2 | 19636.5 |
| 80°   | 6171.6  | 8436.0  | 10700.1 | 11160.5 | 11621.0 | 12595.1 | 13568.7 | 14153.3 | 14737.6 | 13575.1 |
| 82.5° | 3587.5  | 5135.5  | 6683.7  | 7198.0  | 7712.6  | 8383.0  | 9053.5  | 9297.3  | 9541.0  | 8627.3  |
| 85°   | 1578.4  | 2400.0  | 3221.6  | 3659.1  | 4096.6  | 4647.5  | 5198.2  | 5336.6  | 5475.0  | 4743.2  |
| 87.5° | 488.6   | 764.8   | 1040.9  | 1285.0  | 1529.1  | 1804.6  | 2080.0  | 2091.8  | 2103.4  | 1765.9  |
| 90°   | 0.0     | 0.0     | 0.0     | 0.0     | 0.0     | 0.0     | 0.0     | 0.0     | 0.0     | 0.0     |

REPORT NUMBER: P956348

CATALOG NUMBER: GLAN-SB9A-740-U-SLL

**CANDELA DISTRIBUTION (continued):**

| 50°     |       | 55°     | 60°     | 65°     | 70°     | 75°     | 80°     | 85°     | 90°     | 95°     | 100°    |
|---------|-------|---------|---------|---------|---------|---------|---------|---------|---------|---------|---------|
| 5922.8  | 0°    | 5922.8  | 5922.8  | 5922.8  | 5922.8  | 5922.8  | 5922.8  | 5922.8  | 5922.8  | 5922.8  | 5922.8  |
| 6547.8  | 2.5°  | 6537.5  | 6527.3  | 6506.9  | 6486.4  | 6452.1  | 6417.8  | 6393.5  | 6369.4  | 6320.5  | 6271.6  |
| 7331.4  | 5°    | 7303.7  | 7276.2  | 7230.7  | 7185.3  | 7101.4  | 7017.8  | 6933.2  | 6848.9  | 6741.0  | 6633.0  |
| 8080.7  | 7.5°  | 8040.7  | 8000.5  | 7926.2  | 7851.9  | 7728.5  | 7605.1  | 7468.0  | 7330.7  | 7152.6  | 6974.6  |
| 8567.1  | 10°   | 8528.2  | 8489.2  | 8401.9  | 8314.2  | 8169.4  | 8024.6  | 7862.3  | 7700.1  | 7474.8  | 7249.6  |
| 8709.2  | 12.5° | 8687.8  | 8666.4  | 8602.8  | 8539.2  | 8408.7  | 8277.8  | 8102.1  | 7926.2  | 7678.7  | 7431.4  |
| 8490.5  | 15°   | 8513.2  | 8536.0  | 8533.7  | 8531.4  | 8449.2  | 8367.1  | 8215.5  | 8063.7  | 7805.7  | 7547.8  |
| 7996.0  | 17.5° | 8080.5  | 8164.8  | 8256.9  | 8348.9  | 8347.6  | 8346.0  | 8243.5  | 8141.0  | 7879.4  | 7617.8  |
| 7379.6  | 20°   | 7527.6  | 7675.5  | 7878.7  | 8081.9  | 8189.8  | 8297.8  | 8261.9  | 8226.2  | 7954.4  | 7682.3  |
| 6816.4  | 22.5° | 7001.4  | 7186.4  | 7485.3  | 7784.1  | 8007.8  | 8231.4  | 8278.2  | 8325.1  | 8047.3  | 7769.4  |
| 6363.2  | 25°   | 6557.3  | 6751.9  | 7114.8  | 7477.8  | 7817.3  | 8156.9  | 8304.6  | 8452.3  | 8180.1  | 7908.0  |
| 6010.3  | 27.5° | 6201.4  | 6392.8  | 6795.1  | 7197.3  | 7646.9  | 8096.7  | 8361.0  | 8625.1  | 8365.5  | 8105.7  |
| 5770.0  | 30°   | 5947.5  | 6125.0  | 6544.1  | 6963.2  | 7516.9  | 8070.5  | 8464.2  | 8858.0  | 8607.1  | 8356.4  |
| 5735.3  | 32.5° | 5874.8  | 6014.1  | 6408.0  | 6801.9  | 7428.2  | 8054.6  | 8593.7  | 9133.0  | 8884.6  | 8636.4  |
| 6230.0  | 35°   | 6262.5  | 6295.0  | 6568.5  | 6842.1  | 7494.6  | 8147.3  | 8807.1  | 9467.1  | 9229.4  | 8991.4  |
| 7552.3  | 37.5° | 7403.7  | 7255.1  | 7272.8  | 7290.5  | 7883.7  | 8476.9  | 9253.3  | 10029.6 | 9726.4  | 9423.3  |
| 9654.2  | 40°   | 9292.8  | 8931.4  | 8620.1  | 8308.7  | 8749.8  | 9191.0  | 10035.3 | 10879.6 | 10437.8 | 9996.0  |
| 12496.0 | 42.5° | 11838.7 | 11181.4 | 10502.4 | 9823.3  | 10077.3 | 10331.4 | 11169.2 | 12006.9 | 11369.2 | 10731.4 |
| 16005.8 | 45°   | 14925.6 | 13845.6 | 12757.4 | 11669.4 | 11781.7 | 11893.7 | 12646.5 | 13399.0 | 12538.7 | 11678.5 |
| 19930.8 | 47.5° | 18349.9 | 16768.8 | 15199.7 | 13630.1 | 13652.8 | 13675.6 | 14407.8 | 15139.9 | 13929.2 | 12718.3 |
| 23840.6 | 50°   | 21753.6 | 19666.5 | 17643.8 | 15621.0 | 15617.2 | 15613.3 | 16517.4 | 17421.7 | 15596.5 | 13771.0 |
| 27626.3 | 52.5° | 25044.3 | 22462.0 | 20045.8 | 17629.7 | 17740.6 | 17851.3 | 18946.0 | 20041.1 | 17347.9 | 14654.7 |
| 31337.7 | 55°   | 28259.3 | 25180.9 | 22492.0 | 19802.9 | 20234.5 | 20666.1 | 21747.9 | 22829.7 | 18900.6 | 14971.7 |
| 34860.5 | 57.5° | 31373.9 | 27887.0 | 25171.8 | 22456.5 | 23322.0 | 24187.7 | 24777.0 | 25366.1 | 20001.1 | 14636.0 |
| 39184.8 | 60°   | 35451.6 | 31718.4 | 29148.9 | 26579.3 | 27654.3 | 28729.3 | 27814.1 | 26899.1 | 20276.1 | 13652.8 |
| 42690.1 | 62.5° | 39138.5 | 35586.6 | 33232.5 | 30878.6 | 31000.0 | 31121.1 | 28620.9 | 26120.6 | 19118.1 | 12115.5 |
| 43055.3 | 65°   | 39611.4 | 36167.3 | 33175.7 | 30184.3 | 29720.2 | 29255.9 | 26909.3 | 24562.7 | 17479.7 | 10396.7 |
| 40525.3 | 67.5° | 37066.4 | 33607.5 | 30490.9 | 27374.1 | 27156.6 | 26938.8 | 24707.0 | 22475.2 | 15529.9 | 8584.6  |
| 36544.6 | 70°   | 33568.2 | 30591.6 | 27804.5 | 25017.2 | 24919.7 | 24822.5 | 22394.7 | 19967.2 | 13402.4 | 6837.6  |
| 31509.8 | 72.5° | 29280.7 | 27051.3 | 24870.6 | 22689.9 | 22620.2 | 22550.2 | 19764.2 | 16978.5 | 11096.0 | 5213.7  |
| 26013.8 | 75°   | 24444.5 | 22875.2 | 21178.6 | 19482.0 | 19223.1 | 18964.2 | 16081.0 | 13197.8 | 8452.1  | 3706.4  |
| 20359.2 | 77.5° | 19246.1 | 18133.1 | 16843.3 | 15553.5 | 15183.1 | 14812.6 | 12121.0 | 9429.6  | 5915.7  | 2401.8  |
| 14737.6 | 80°   | 14153.3 | 13568.7 | 12595.1 | 11621.0 | 11160.5 | 10700.1 | 8436.0  | 6171.6  | 3811.4  | 1451.1  |
| 9541.0  | 82.5° | 9297.3  | 9053.5  | 8383.0  | 7712.6  | 7198.0  | 6683.7  | 5135.5  | 3587.5  | 2205.9  | 824.6   |
| 5475.0  | 85°   | 5336.6  | 5198.2  | 4647.5  | 4096.6  | 3659.1  | 3221.6  | 2400.0  | 1578.4  | 992.3   | 406.4   |
| 2103.4  | 87.5° | 2091.8  | 2080.0  | 1804.6  | 1529.1  | 1285.0  | 1040.9  | 764.8   | 488.6   | 325.0   | 161.4   |
| 0.0     | 90°   | 0.0     | 0.0     | 0.0     | 0.0     | 0.0     | 0.0     | 0.0     | 0.0     | 0.0     | 0.0     |

REPORT NUMBER: P956348

CATALOG NUMBER: GLAN-SB9A-740-U-SLL

**CANDELA DISTRIBUTION (continued):**

| 105°    |       | 110°   | 115°   | 120°   | 125°   | 130°   | 135°   | 140°   | 145°   | 150°   | 155°   |
|---------|-------|--------|--------|--------|--------|--------|--------|--------|--------|--------|--------|
| 5922.8  | 0°    | 5922.8 | 5922.8 | 5922.8 | 5922.8 | 5922.8 | 5922.8 | 5922.8 | 5922.8 | 5922.8 | 5922.8 |
| 6219.6  | 2.5°  | 6167.8 | 6115.5 | 6063.2 | 6013.2 | 5963.2 | 5914.8 | 5861.0 | 5817.3 | 5773.9 | 5734.6 |
| 6525.3  | 5°    | 6417.8 | 6309.4 | 6201.2 | 6100.0 | 5998.9 | 5903.5 | 5809.1 | 5726.9 | 5644.4 | 5575.3 |
| 6810.1  | 7.5°  | 6645.5 | 6485.3 | 6325.0 | 6183.9 | 6042.8 | 5912.5 | 5790.5 | 5681.0 | 5571.6 | 5480.7 |
| 7032.1  | 10°   | 6814.8 | 6620.3 | 6425.5 | 6258.7 | 6091.4 | 5930.7 | 5799.6 | 5684.1 | 5568.7 | 5477.8 |
| 7185.1  | 12.5° | 6938.7 | 6709.1 | 6479.6 | 6290.7 | 6101.9 | 5933.0 | 5811.0 | 5716.4 | 5622.3 | 5561.9 |
| 7280.5  | 15°   | 7013.2 | 6748.9 | 6484.6 | 6266.0 | 6047.3 | 5860.3 | 5762.5 | 5717.3 | 5672.3 | 5680.5 |
| 7326.2  | 17.5° | 7034.6 | 6727.8 | 6421.0 | 6158.0 | 5895.0 | 5675.0 | 5614.8 | 5631.4 | 5647.8 | 5746.9 |
| 7361.9  | 20°   | 7041.4 | 6669.6 | 6297.8 | 5971.9 | 5646.0 | 5389.8 | 5373.9 | 5451.2 | 5528.4 | 5700.5 |
| 7410.1  | 22.5° | 7050.5 | 6598.2 | 6146.0 | 5753.5 | 5360.9 | 5069.4 | 5100.5 | 5214.8 | 5329.1 | 5525.5 |
| 7497.3  | 25°   | 7086.4 | 6527.8 | 5969.4 | 5509.6 | 5050.0 | 4751.2 | 4835.3 | 4967.1 | 5098.9 | 5275.5 |
| 7633.7  | 27.5° | 7161.4 | 6480.7 | 5800.0 | 5286.6 | 4773.2 | 4501.2 | 4603.4 | 4730.7 | 4858.0 | 5003.2 |
| 7810.3  | 30°   | 7264.1 | 6458.7 | 5652.8 | 5100.3 | 4547.8 | 4319.4 | 4399.6 | 4500.5 | 4601.9 | 4722.3 |
| 7994.6  | 32.5° | 7352.8 | 6431.4 | 5509.6 | 4939.6 | 4369.4 | 4185.3 | 4220.9 | 4280.7 | 4340.5 | 4436.6 |
| 8204.6  | 35°   | 7417.8 | 6380.0 | 5342.8 | 4781.6 | 4220.5 | 4067.1 | 4052.3 | 4068.7 | 4085.3 | 4158.7 |
| 8439.8  | 37.5° | 7456.4 | 6292.1 | 5127.8 | 4595.7 | 4063.7 | 3929.6 | 3875.5 | 3857.3 | 3839.1 | 3891.8 |
| 8738.5  | 40°   | 7480.7 | 6171.0 | 4861.4 | 4373.9 | 3886.4 | 3764.8 | 3681.8 | 3640.7 | 3599.6 | 3637.5 |
| 9129.2  | 42.5° | 7526.9 | 6046.0 | 4565.5 | 4129.1 | 3692.8 | 3580.7 | 3476.2 | 3421.6 | 3367.1 | 3398.0 |
| 9643.3  | 45°   | 7608.0 | 5929.8 | 4251.8 | 3869.1 | 3486.4 | 3372.8 | 3271.6 | 3218.4 | 3165.5 | 3191.4 |
| 10191.0 | 47.5° | 7663.7 | 5833.9 | 4004.1 | 3663.4 | 3322.8 | 3176.2 | 3089.1 | 3044.6 | 3000.0 | 3024.6 |
| 10699.2 | 50°   | 7627.3 | 5729.4 | 3831.4 | 3526.8 | 3222.3 | 3029.6 | 2928.4 | 2888.9 | 2849.6 | 2887.7 |
| 11029.2 | 52.5° | 7403.5 | 5552.8 | 3702.3 | 3436.8 | 3171.6 | 2950.0 | 2808.7 | 2769.6 | 2730.7 | 2788.2 |
| 10956.4 | 55°   | 6941.0 | 5260.0 | 3579.1 | 3371.6 | 3164.1 | 2958.0 | 2745.0 | 2683.2 | 2621.6 | 2703.2 |
| 10444.6 | 57.5° | 6253.5 | 4847.3 | 3440.9 | 3294.3 | 3147.8 | 2965.9 | 2706.8 | 2616.8 | 2526.8 | 2614.6 |
| 9492.1  | 60°   | 5331.4 | 4311.4 | 3291.4 | 3176.2 | 3060.9 | 2940.9 | 2670.9 | 2554.3 | 2437.5 | 2514.6 |
| 8204.2  | 62.5° | 4292.8 | 3670.0 | 3047.3 | 2970.7 | 2894.3 | 2879.6 | 2629.1 | 2483.2 | 2337.5 | 2386.4 |
| 6890.1  | 65°   | 3383.7 | 3093.0 | 2802.3 | 2766.2 | 2730.0 | 2731.8 | 2540.9 | 2385.9 | 2230.7 | 2249.6 |
| 5602.8  | 67.5° | 2620.9 | 2538.4 | 2455.7 | 2475.9 | 2495.9 | 2490.9 | 2383.7 | 2254.6 | 2125.5 | 2119.6 |
| 4411.4  | 70°   | 1985.2 | 2008.9 | 2032.3 | 2125.9 | 2219.3 | 2219.3 | 2184.1 | 2092.3 | 2000.5 | 1980.0 |
| 3372.5  | 72.5° | 1531.4 | 1602.5 | 1673.9 | 1806.6 | 1939.1 | 1961.4 | 1961.8 | 1898.9 | 1835.9 | 1805.9 |
| 2447.7  | 75°   | 1189.1 | 1253.6 | 1318.2 | 1466.8 | 1615.5 | 1718.2 | 1709.6 | 1661.1 | 1612.5 | 1583.9 |
| 1658.6  | 77.5° | 915.5  | 959.3  | 1003.4 | 1147.7 | 1292.1 | 1461.4 | 1456.8 | 1418.0 | 1379.1 | 1350.0 |
| 1068.6  | 80°   | 686.4  | 704.6  | 722.7  | 845.0  | 967.1  | 1169.3 | 1168.6 | 1136.1 | 1103.4 | 1079.1 |
| 657.3   | 82.5° | 490.5  | 493.6  | 497.3  | 587.3  | 677.3  | 850.0  | 859.6  | 843.6  | 827.7  | 810.5  |
| 351.4   | 85°   | 296.6  | 295.0  | 293.2  | 359.1  | 425.0  | 553.4  | 565.9  | 548.9  | 531.8  | 512.5  |
| 145.7   | 87.5° | 130.0  | 128.4  | 126.8  | 153.6  | 180.7  | 234.1  | 250.0  | 243.2  | 236.4  | 232.7  |
| 0.0     | 90°   | 0.0    | 0.0    | 0.0    | 0.0    | 0.0    | 0.0    | 0.0    | 0.0    | 0.0    | 0.0    |

REPORT NUMBER: P956348

CATALOG NUMBER: GLAN-SB9A-740-U-SLL

**CANDELA DISTRIBUTION (continued):**

| 160°   |       | 165°   | 170°   | 175°   | 180°   | 185°   | 190°   | 195°   | 200°   | 205°   | 210°   |
|--------|-------|--------|--------|--------|--------|--------|--------|--------|--------|--------|--------|
| 5922.8 | 0°    | 5922.8 | 5922.8 | 5922.8 | 5922.8 | 5922.8 | 5922.8 | 5922.8 | 5922.8 | 5922.8 | 5922.8 |
| 5695.5 | 2.5°  | 5661.2 | 5626.9 | 5592.3 | 5558.0 | 5531.4 | 5504.6 | 5483.0 | 5461.4 | 5444.6 | 5427.8 |
| 5506.4 | 5°    | 5445.5 | 5384.6 | 5329.4 | 5273.9 | 5231.4 | 5188.7 | 5158.9 | 5129.1 | 5108.0 | 5086.9 |
| 5389.8 | 7.5°  | 5313.2 | 5236.4 | 5168.7 | 5101.2 | 5050.5 | 5000.0 | 4964.6 | 4929.1 | 4904.8 | 4880.7 |
| 5386.9 | 10°   | 5304.4 | 5221.6 | 5145.5 | 5069.4 | 5008.9 | 4948.2 | 4908.7 | 4868.7 | 4845.7 | 4822.8 |
| 5501.9 | 12.5° | 5436.9 | 5372.3 | 5293.4 | 5214.8 | 5137.5 | 5060.3 | 5009.1 | 4958.0 | 4932.3 | 4906.9 |
| 5688.7 | 15°   | 5671.9 | 5655.0 | 5586.6 | 5518.2 | 5408.2 | 5298.2 | 5220.5 | 5142.8 | 5107.1 | 5071.6 |
| 5846.0 | 17.5° | 5898.7 | 5951.2 | 5896.0 | 5841.0 | 5695.3 | 5549.6 | 5435.0 | 5320.5 | 5267.8 | 5214.8 |
| 5872.8 | 20°   | 5983.0 | 6093.2 | 6067.8 | 6042.1 | 5875.5 | 5709.1 | 5568.7 | 5428.4 | 5360.9 | 5293.2 |
| 5722.3 | 22.5° | 5865.7 | 6009.1 | 6024.6 | 6039.8 | 5880.7 | 5721.6 | 5577.1 | 5432.3 | 5361.2 | 5289.8 |
| 5452.3 | 25°   | 5593.5 | 5734.6 | 5787.3 | 5839.8 | 5709.4 | 5579.1 | 5450.5 | 5322.3 | 5260.5 | 5198.9 |
| 5148.2 | 27.5° | 5261.4 | 5374.6 | 5433.2 | 5492.1 | 5399.1 | 5306.4 | 5206.6 | 5106.9 | 5065.5 | 5023.9 |
| 4842.8 | 30°   | 4936.6 | 5030.7 | 5078.4 | 5126.2 | 5055.5 | 4984.6 | 4913.2 | 4841.4 | 4820.3 | 4798.9 |
| 4533.0 | 32.5° | 4623.0 | 4713.2 | 4766.2 | 4819.4 | 4754.4 | 4689.1 | 4632.1 | 4575.0 | 4561.2 | 4547.3 |
| 4231.8 | 35°   | 4320.9 | 4410.3 | 4473.9 | 4537.5 | 4491.2 | 4445.0 | 4392.3 | 4339.8 | 4318.7 | 4297.8 |
| 3944.3 | 37.5° | 4033.2 | 4122.3 | 4200.9 | 4279.6 | 4258.2 | 4236.8 | 4188.4 | 4139.8 | 4101.4 | 4063.2 |
| 3675.5 | 40°   | 3761.4 | 3847.3 | 3937.8 | 4028.4 | 4033.7 | 4038.7 | 3997.5 | 3956.4 | 3900.5 | 3845.0 |
| 3429.1 | 42.5° | 3510.5 | 3592.1 | 3689.8 | 3787.5 | 3813.7 | 3839.8 | 3805.0 | 3770.5 | 3701.2 | 3631.8 |
| 3217.8 | 45°   | 3295.0 | 3372.3 | 3473.7 | 3575.0 | 3612.5 | 3650.0 | 3618.7 | 3587.5 | 3508.2 | 3429.1 |
| 3048.9 | 47.5° | 3124.6 | 3200.0 | 3300.0 | 3400.0 | 3443.2 | 3486.4 | 3464.6 | 3442.8 | 3372.3 | 3301.8 |
| 2926.2 | 50°   | 2997.5 | 3068.7 | 3158.2 | 3247.8 | 3303.2 | 3358.7 | 3357.3 | 3356.4 | 3300.0 | 3243.7 |
| 2845.5 | 52.5° | 2910.9 | 2976.2 | 3059.6 | 3143.2 | 3208.9 | 3274.6 | 3286.4 | 3298.2 | 3252.3 | 3206.4 |
| 2784.6 | 55°   | 2855.0 | 2925.5 | 2998.7 | 3071.6 | 3141.2 | 3210.9 | 3227.3 | 3243.7 | 3203.7 | 3163.7 |
| 2702.3 | 57.5° | 2785.0 | 2867.7 | 2940.0 | 3012.5 | 3082.8 | 3152.8 | 3169.3 | 3185.9 | 3145.5 | 3105.0 |
| 2591.4 | 60°   | 2686.4 | 2781.4 | 2854.8 | 2928.4 | 2998.9 | 3069.3 | 3087.5 | 3105.7 | 3066.2 | 3026.8 |
| 2435.2 | 62.5° | 2545.9 | 2656.8 | 2735.2 | 2813.7 | 2878.2 | 2942.7 | 2960.2 | 2977.7 | 2942.1 | 2906.4 |
| 2268.2 | 65°   | 2386.8 | 2505.7 | 2580.7 | 2655.7 | 2712.5 | 2769.3 | 2787.3 | 2805.0 | 2770.7 | 2736.4 |
| 2113.7 | 67.5° | 2223.2 | 2333.0 | 2404.1 | 2475.0 | 2524.1 | 2573.2 | 2590.7 | 2608.0 | 2576.4 | 2545.0 |
| 1959.6 | 70°   | 2055.9 | 2152.3 | 2213.7 | 2275.0 | 2319.3 | 2363.7 | 2380.5 | 2397.3 | 2371.6 | 2345.9 |
| 1776.1 | 72.5° | 1852.1 | 1927.7 | 1983.2 | 2038.7 | 2082.1 | 2125.5 | 2145.5 | 2165.5 | 2144.1 | 2122.7 |
| 1555.0 | 75°   | 1611.4 | 1667.7 | 1718.0 | 1768.2 | 1807.7 | 1847.3 | 1868.2 | 1889.1 | 1878.7 | 1868.2 |
| 1320.9 | 77.5° | 1366.8 | 1412.5 | 1455.7 | 1498.9 | 1540.5 | 1581.8 | 1601.4 | 1620.9 | 1606.4 | 1591.4 |
| 1054.6 | 80°   | 1092.7 | 1130.7 | 1167.1 | 1203.4 | 1235.0 | 1266.4 | 1292.3 | 1318.2 | 1311.8 | 1305.7 |
| 793.2  | 82.5° | 790.0  | 786.8  | 774.1  | 761.4  | 828.6  | 895.9  | 940.0  | 984.1  | 981.4  | 978.4  |
| 493.2  | 85°   | 476.8  | 460.2  | 425.0  | 389.8  | 452.7  | 515.9  | 570.5  | 625.0  | 620.5  | 615.9  |
| 229.1  | 87.5° | 228.4  | 227.7  | 200.9  | 173.9  | 200.2  | 226.8  | 248.9  | 270.9  | 265.5  | 259.5  |
| 0.0    | 90°   | 0.0    | 0.0    | 0.0    | 0.0    | 0.0    | 0.0    | 0.0    | 0.0    | 0.0    | 0.0    |

REPORT NUMBER: P956348  
CATALOG NUMBER: GLAN-SB9A-740-U-SLL

**CANDELA DISTRIBUTION (continued):**

| 215°   |       | 220°   | 225°   | 230°   | 235°   | 240°   | 245°   | 250°   | 255°   | 260°   | 265°   |
|--------|-------|--------|--------|--------|--------|--------|--------|--------|--------|--------|--------|
| 5922.8 | 0°    | 5922.8 | 5922.8 | 5922.8 | 5922.8 | 5922.8 | 5922.8 | 5922.8 | 5922.8 | 5922.8 | 5922.8 |
| 5412.3 | 2.5°  | 5396.6 | 5377.3 | 5396.6 | 5412.3 | 5427.8 | 5444.6 | 5461.4 | 5483.0 | 5504.6 | 5531.4 |
| 5070.7 | 5°    | 5054.6 | 5038.7 | 5054.6 | 5070.7 | 5086.9 | 5108.0 | 5129.1 | 5158.9 | 5188.7 | 5231.4 |
| 4866.2 | 7.5°  | 4851.9 | 4840.9 | 4851.9 | 4866.2 | 4880.7 | 4904.8 | 4929.1 | 4964.6 | 5000.0 | 5050.5 |
| 4810.5 | 10°   | 4798.2 | 4793.2 | 4798.2 | 4810.5 | 4822.8 | 4845.7 | 4868.7 | 4908.7 | 4948.2 | 5008.9 |
| 4896.4 | 12.5° | 4885.9 | 4884.1 | 4885.9 | 4896.4 | 4906.9 | 4932.3 | 4958.0 | 5009.1 | 5060.3 | 5137.5 |
| 5058.0 | 15°   | 5044.4 | 5043.2 | 5044.4 | 5058.0 | 5071.6 | 5107.1 | 5142.8 | 5220.5 | 5298.2 | 5408.2 |
| 5197.5 | 17.5° | 5180.0 | 5177.3 | 5180.0 | 5197.5 | 5214.8 | 5267.8 | 5320.5 | 5435.0 | 5549.6 | 5695.3 |
| 5271.6 | 20°   | 5250.0 | 5243.2 | 5250.0 | 5271.6 | 5293.2 | 5360.9 | 5428.4 | 5568.7 | 5709.1 | 5875.5 |
| 5265.9 | 22.5° | 5242.1 | 5231.9 | 5242.1 | 5265.9 | 5289.8 | 5361.2 | 5432.3 | 5577.1 | 5721.6 | 5880.7 |
| 5176.4 | 25°   | 5154.1 | 5140.9 | 5154.1 | 5176.4 | 5198.9 | 5260.5 | 5322.3 | 5450.5 | 5579.1 | 5709.4 |
| 5013.7 | 27.5° | 5003.4 | 5000.0 | 5003.4 | 5013.7 | 5023.9 | 5065.5 | 5106.9 | 5206.6 | 5306.4 | 5399.1 |
| 4798.9 | 30°   | 4798.9 | 4802.3 | 4798.9 | 4798.9 | 4798.9 | 4820.3 | 4841.4 | 4913.2 | 4984.6 | 5055.5 |
| 4549.1 | 32.5° | 4551.2 | 4554.6 | 4551.2 | 4549.1 | 4547.3 | 4561.2 | 4575.0 | 4632.1 | 4689.1 | 4754.4 |
| 4293.2 | 35°   | 4288.7 | 4286.4 | 4288.7 | 4293.2 | 4297.8 | 4318.7 | 4339.8 | 4392.3 | 4445.0 | 4491.2 |
| 4043.0 | 37.5° | 4022.8 | 4011.4 | 4022.8 | 4043.0 | 4063.2 | 4101.4 | 4139.8 | 4188.4 | 4236.8 | 4258.2 |
| 3807.3 | 40°   | 3770.0 | 3747.8 | 3770.0 | 3807.3 | 3845.0 | 3900.5 | 3956.4 | 3997.5 | 4038.7 | 4033.7 |
| 3577.1 | 42.5° | 3522.3 | 3486.4 | 3522.3 | 3577.1 | 3631.8 | 3701.2 | 3770.5 | 3805.0 | 3839.8 | 3813.7 |
| 3364.8 | 45°   | 3300.5 | 3259.1 | 3300.5 | 3364.8 | 3429.1 | 3508.2 | 3587.5 | 3618.7 | 3650.0 | 3612.5 |
| 3242.3 | 47.5° | 3183.0 | 3143.2 | 3183.0 | 3242.3 | 3301.8 | 3372.3 | 3442.8 | 3464.6 | 3486.4 | 3443.2 |
| 3188.7 | 50°   | 3133.7 | 3095.5 | 3133.7 | 3188.7 | 3243.7 | 3300.0 | 3356.4 | 3357.3 | 3358.7 | 3303.2 |
| 3157.1 | 52.5° | 3108.0 | 3072.7 | 3108.0 | 3157.1 | 3206.4 | 3252.3 | 3298.2 | 3286.4 | 3274.6 | 3208.9 |
| 3120.5 | 55°   | 3077.3 | 3045.5 | 3077.3 | 3120.5 | 3163.7 | 3203.7 | 3243.7 | 3227.3 | 3210.9 | 3141.2 |
| 3062.3 | 57.5° | 3019.3 | 2986.4 | 3019.3 | 3062.3 | 3105.0 | 3145.5 | 3185.9 | 3169.3 | 3152.8 | 3082.8 |
| 2982.7 | 60°   | 2938.7 | 2904.6 | 2938.7 | 2982.7 | 3026.8 | 3066.2 | 3105.7 | 3087.5 | 3069.3 | 2998.9 |
| 2860.0 | 62.5° | 2813.7 | 2772.7 | 2813.7 | 2860.0 | 2906.4 | 2942.1 | 2977.7 | 2960.2 | 2942.7 | 2878.2 |
| 2691.4 | 65°   | 2646.6 | 2611.4 | 2646.6 | 2691.4 | 2736.4 | 2770.7 | 2805.0 | 2787.3 | 2769.3 | 2712.5 |
| 2503.2 | 67.5° | 2461.4 | 2429.6 | 2461.4 | 2503.2 | 2545.0 | 2576.4 | 2608.0 | 2590.7 | 2573.2 | 2524.1 |
| 2305.9 | 70°   | 2265.9 | 2229.6 | 2265.9 | 2305.9 | 2345.9 | 2371.6 | 2397.3 | 2380.5 | 2363.7 | 2319.3 |
| 2084.6 | 72.5° | 2046.6 | 2011.4 | 2046.6 | 2084.6 | 2122.7 | 2144.1 | 2165.5 | 2145.5 | 2125.5 | 2082.1 |
| 1836.1 | 75°   | 1804.1 | 1770.5 | 1804.1 | 1836.1 | 1868.2 | 1878.7 | 1889.1 | 1868.2 | 1847.3 | 1807.7 |
| 1559.1 | 77.5° | 1526.8 | 1500.0 | 1526.8 | 1559.1 | 1591.4 | 1606.4 | 1620.9 | 1601.4 | 1581.8 | 1540.5 |
| 1262.3 | 80°   | 1218.6 | 1168.2 | 1218.6 | 1262.3 | 1305.7 | 1311.8 | 1318.2 | 1292.3 | 1266.4 | 1235.0 |
| 941.8  | 82.5° | 905.0  | 872.7  | 905.0  | 941.8  | 978.4  | 981.4  | 984.1  | 940.0  | 895.9  | 828.6  |
| 587.3  | 85°   | 558.6  | 529.5  | 558.6  | 587.3  | 615.9  | 620.5  | 625.0  | 570.5  | 515.9  | 452.7  |
| 245.0  | 87.5° | 230.0  | 215.9  | 230.0  | 245.0  | 259.5  | 265.5  | 270.9  | 248.9  | 226.8  | 200.2  |
| 0.0    | 90°   | 0.0    | 0.0    | 0.0    | 0.0    | 0.0    | 0.0    | 0.0    | 0.0    | 0.0    | 0.0    |

REPORT NUMBER: P956348

CATALOG NUMBER: GLAN-SB9A-740-U-SLL

**CANDELA DISTRIBUTION (continued):**

| 270°   |       | 275°   | 280°   | 285°   | 290°   | 295°   | 300°   | 305°   | 310°   | 315°   | 320°   |
|--------|-------|--------|--------|--------|--------|--------|--------|--------|--------|--------|--------|
| 5922.8 | 0°    | 5922.8 | 5922.8 | 5922.8 | 5922.8 | 5922.8 | 5922.8 | 5922.8 | 5922.8 | 5922.8 | 5922.8 |
| 5558.0 | 2.5°  | 5592.3 | 5626.9 | 5661.2 | 5695.5 | 5734.6 | 5773.9 | 5817.3 | 5861.0 | 5914.8 | 5963.2 |
| 5273.9 | 5°    | 5329.4 | 5384.6 | 5445.5 | 5506.4 | 5575.3 | 5644.4 | 5726.9 | 5809.1 | 5903.5 | 5998.9 |
| 5101.2 | 7.5°  | 5168.7 | 5236.4 | 5313.2 | 5389.8 | 5480.7 | 5571.6 | 5681.0 | 5790.5 | 5912.5 | 6042.8 |
| 5069.4 | 10°   | 5145.5 | 5221.6 | 5304.4 | 5386.9 | 5477.8 | 5568.7 | 5684.1 | 5799.6 | 5930.7 | 6091.4 |
| 5214.8 | 12.5° | 5293.4 | 5372.3 | 5436.9 | 5501.9 | 5561.9 | 5622.3 | 5716.4 | 5811.0 | 5933.0 | 6101.9 |
| 5518.2 | 15°   | 5586.6 | 5655.0 | 5671.9 | 5688.7 | 5680.5 | 5672.3 | 5717.3 | 5762.5 | 5860.3 | 6047.3 |
| 5841.0 | 17.5° | 5896.0 | 5951.2 | 5898.7 | 5846.0 | 5746.9 | 5647.8 | 5631.4 | 5614.8 | 5675.0 | 5895.0 |
| 6042.1 | 20°   | 6067.8 | 6093.2 | 5983.0 | 5872.8 | 5700.5 | 5528.4 | 5451.2 | 5373.9 | 5389.8 | 5646.0 |
| 6039.8 | 22.5° | 6024.6 | 6009.1 | 5865.7 | 5722.3 | 5525.5 | 5329.1 | 5214.8 | 5100.5 | 5069.4 | 5360.9 |
| 5839.8 | 25°   | 5787.3 | 5734.6 | 5593.5 | 5452.3 | 5275.5 | 5098.9 | 4967.1 | 4835.3 | 4751.2 | 5050.0 |
| 5492.1 | 27.5° | 5433.2 | 5374.6 | 5261.4 | 5148.2 | 5003.2 | 4858.0 | 4730.7 | 4603.4 | 4501.2 | 4773.2 |
| 5126.2 | 30°   | 5078.4 | 5030.7 | 4936.6 | 4842.8 | 4722.3 | 4601.9 | 4500.5 | 4399.6 | 4319.4 | 4547.8 |
| 4819.4 | 32.5° | 4766.2 | 4713.2 | 4623.0 | 4533.0 | 4436.6 | 4340.5 | 4280.7 | 4220.9 | 4185.3 | 4369.4 |
| 4537.5 | 35°   | 4473.9 | 4410.3 | 4320.9 | 4231.8 | 4158.7 | 4085.3 | 4068.7 | 4052.3 | 4067.1 | 4220.5 |
| 4279.6 | 37.5° | 4200.9 | 4122.3 | 4033.2 | 3944.3 | 3891.8 | 3839.1 | 3857.3 | 3875.5 | 3929.6 | 4063.7 |
| 4028.4 | 40°   | 3937.8 | 3847.3 | 3761.4 | 3675.5 | 3637.5 | 3599.6 | 3640.7 | 3681.8 | 3764.8 | 3886.4 |
| 3787.5 | 42.5° | 3689.8 | 3592.1 | 3510.5 | 3429.1 | 3398.0 | 3367.1 | 3421.6 | 3476.2 | 3580.7 | 3692.8 |
| 3575.0 | 45°   | 3473.7 | 3372.3 | 3295.0 | 3217.8 | 3191.4 | 3165.5 | 3218.4 | 3271.6 | 3372.8 | 3486.4 |
| 3400.0 | 47.5° | 3300.0 | 3200.0 | 3124.6 | 3048.9 | 3024.6 | 3000.0 | 3044.6 | 3089.1 | 3176.2 | 3322.8 |
| 3247.8 | 50°   | 3158.2 | 3068.7 | 2997.5 | 2926.2 | 2887.7 | 2849.6 | 2888.9 | 2928.4 | 3029.6 | 3222.3 |
| 3143.2 | 52.5° | 3059.6 | 2976.2 | 2910.9 | 2845.5 | 2788.2 | 2730.7 | 2769.6 | 2808.7 | 2950.0 | 3171.6 |
| 3071.6 | 55°   | 2998.7 | 2925.5 | 2855.0 | 2784.6 | 2703.2 | 2621.6 | 2683.2 | 2745.0 | 2958.0 | 3164.1 |
| 3012.5 | 57.5° | 2940.0 | 2867.7 | 2785.0 | 2702.3 | 2614.6 | 2526.8 | 2616.8 | 2706.8 | 2965.9 | 3147.8 |
| 2928.4 | 60°   | 2854.8 | 2781.4 | 2686.4 | 2591.4 | 2514.6 | 2437.5 | 2554.3 | 2670.9 | 2940.9 | 3060.9 |
| 2813.7 | 62.5° | 2735.2 | 2656.8 | 2545.9 | 2435.2 | 2386.4 | 2337.5 | 2483.2 | 2629.1 | 2879.6 | 2894.3 |
| 2655.7 | 65°   | 2580.7 | 2505.7 | 2386.8 | 2268.2 | 2249.6 | 2230.7 | 2385.9 | 2540.9 | 2731.8 | 2730.0 |
| 2475.0 | 67.5° | 2404.1 | 2333.0 | 2223.2 | 2113.7 | 2119.6 | 2125.5 | 2254.6 | 2383.7 | 2490.9 | 2495.9 |
| 2275.0 | 70°   | 2213.7 | 2152.3 | 2055.9 | 1959.6 | 1980.0 | 2000.5 | 2092.3 | 2184.1 | 2219.3 | 2219.3 |
| 2038.7 | 72.5° | 1983.2 | 1927.7 | 1852.1 | 1776.1 | 1805.9 | 1835.9 | 1898.9 | 1961.8 | 1961.4 | 1939.1 |
| 1768.2 | 75°   | 1718.0 | 1667.7 | 1611.4 | 1555.0 | 1583.9 | 1612.5 | 1661.1 | 1709.6 | 1718.2 | 1615.5 |
| 1498.9 | 77.5° | 1455.7 | 1412.5 | 1366.8 | 1320.9 | 1350.0 | 1379.1 | 1418.0 | 1456.8 | 1461.4 | 1292.1 |
| 1203.4 | 80°   | 1167.1 | 1130.7 | 1092.7 | 1054.6 | 1079.1 | 1103.4 | 1136.1 | 1168.6 | 1169.3 | 967.1  |
| 761.4  | 82.5° | 774.1  | 786.8  | 790.0  | 793.2  | 810.5  | 827.7  | 843.6  | 859.6  | 850.0  | 677.3  |
| 389.8  | 85°   | 425.0  | 460.2  | 476.8  | 493.2  | 512.5  | 531.8  | 548.9  | 565.9  | 553.4  | 425.0  |
| 173.9  | 87.5° | 200.9  | 227.7  | 228.4  | 229.1  | 232.7  | 236.4  | 243.2  | 250.0  | 234.1  | 180.7  |
| 0.0    | 90°   | 0.0    | 0.0    | 0.0    | 0.0    | 0.0    | 0.0    | 0.0    | 0.0    | 0.0    | 0.0    |

REPORT NUMBER: P956348

CATALOG NUMBER: GLAN-SB9A-740-U-SLL

**CANDELA DISTRIBUTION (continued):**

| 325°   |       | 330°   | 335°   | 340°   | 345°    | 350°    | 355°    | 360°    |
|--------|-------|--------|--------|--------|---------|---------|---------|---------|
| 5922.8 | 0°    | 5922.8 | 5922.8 | 5922.8 | 5922.8  | 5922.8  | 5922.8  | 5922.8  |
| 6013.2 | 2.5°  | 6063.2 | 6115.5 | 6167.8 | 6219.6  | 6271.6  | 6320.5  | 6369.4  |
| 6100.0 | 5°    | 6201.2 | 6309.4 | 6417.8 | 6525.3  | 6633.0  | 6741.0  | 6848.9  |
| 6183.9 | 7.5°  | 6325.0 | 6485.3 | 6645.5 | 6810.1  | 6974.6  | 7152.6  | 7330.7  |
| 6258.7 | 10°   | 6425.5 | 6620.3 | 6814.8 | 7032.1  | 7249.6  | 7474.8  | 7700.1  |
| 6290.7 | 12.5° | 6479.6 | 6709.1 | 6938.7 | 7185.1  | 7431.4  | 7678.7  | 7926.2  |
| 6266.0 | 15°   | 6484.6 | 6748.9 | 7013.2 | 7280.5  | 7547.8  | 7805.7  | 8063.7  |
| 6158.0 | 17.5° | 6421.0 | 6727.8 | 7034.6 | 7326.2  | 7617.8  | 7879.4  | 8141.0  |
| 5971.9 | 20°   | 6297.8 | 6669.6 | 7041.4 | 7361.9  | 7682.3  | 7954.4  | 8226.2  |
| 5753.5 | 22.5° | 6146.0 | 6598.2 | 7050.5 | 7410.1  | 7769.4  | 8047.3  | 8325.1  |
| 5509.6 | 25°   | 5969.4 | 6527.8 | 7086.4 | 7497.3  | 7908.0  | 8180.1  | 8452.3  |
| 5286.6 | 27.5° | 5800.0 | 6480.7 | 7161.4 | 7633.7  | 8105.7  | 8365.5  | 8625.1  |
| 5100.3 | 30°   | 5652.8 | 6458.7 | 7264.1 | 7810.3  | 8356.4  | 8607.1  | 8858.0  |
| 4939.6 | 32.5° | 5509.6 | 6431.4 | 7352.8 | 7994.6  | 8636.4  | 8884.6  | 9133.0  |
| 4781.6 | 35°   | 5342.8 | 6380.0 | 7417.8 | 8204.6  | 8991.4  | 9229.4  | 9467.1  |
| 4595.7 | 37.5° | 5127.8 | 6292.1 | 7456.4 | 8439.8  | 9423.3  | 9726.4  | 10029.6 |
| 4373.9 | 40°   | 4861.4 | 6171.0 | 7480.7 | 8738.5  | 9996.0  | 10437.8 | 10879.6 |
| 4129.1 | 42.5° | 4565.5 | 6046.0 | 7526.9 | 9129.2  | 10731.4 | 11369.2 | 12006.9 |
| 3869.1 | 45°   | 4251.8 | 5929.8 | 7608.0 | 9643.3  | 11678.5 | 12538.7 | 13399.0 |
| 3663.4 | 47.5° | 4004.1 | 5833.9 | 7663.7 | 10191.0 | 12718.3 | 13929.2 | 15139.9 |
| 3526.8 | 50°   | 3831.4 | 5729.4 | 7627.3 | 10699.2 | 13771.0 | 15596.5 | 17421.7 |
| 3436.8 | 52.5° | 3702.3 | 5552.8 | 7403.5 | 11029.2 | 14654.7 | 17347.9 | 20041.1 |
| 3371.6 | 55°   | 3579.1 | 5260.0 | 6941.0 | 10956.4 | 14971.7 | 18900.6 | 22829.7 |
| 3294.3 | 57.5° | 3440.9 | 4847.3 | 6253.5 | 10444.6 | 14636.0 | 20001.1 | 25366.1 |
| 3176.2 | 60°   | 3291.4 | 4311.4 | 5331.4 | 9492.1  | 13652.8 | 20276.1 | 26899.1 |
| 2970.7 | 62.5° | 3047.3 | 3670.0 | 4292.8 | 8204.2  | 12115.5 | 19118.1 | 26120.6 |
| 2766.2 | 65°   | 2802.3 | 3093.0 | 3383.7 | 6890.1  | 10396.7 | 17479.7 | 24562.7 |
| 2475.9 | 67.5° | 2455.7 | 2538.4 | 2620.9 | 5602.8  | 8584.6  | 15529.9 | 22475.2 |
| 2125.9 | 70°   | 2032.3 | 2008.9 | 1985.2 | 4411.4  | 6837.6  | 13402.4 | 19967.2 |
| 1806.6 | 72.5° | 1673.9 | 1602.5 | 1531.4 | 3372.5  | 5213.7  | 11096.0 | 16978.5 |
| 1466.8 | 75°   | 1318.2 | 1253.6 | 1189.1 | 2447.7  | 3706.4  | 8452.1  | 13197.8 |
| 1147.7 | 77.5° | 1003.4 | 959.3  | 915.5  | 1658.6  | 2401.8  | 5915.7  | 9429.6  |
| 845.0  | 80°   | 722.7  | 704.6  | 686.4  | 1068.6  | 1451.1  | 3811.4  | 6171.6  |
| 587.3  | 82.5° | 497.3  | 493.6  | 490.5  | 657.3   | 824.6   | 2205.9  | 3587.5  |
| 359.1  | 85°   | 293.2  | 295.0  | 296.6  | 351.4   | 406.4   | 992.3   | 1578.4  |
| 153.6  | 87.5° | 126.8  | 128.4  | 130.0  | 145.7   | 161.4   | 325.0   | 488.6   |
| 0.0    | 90°   | 0.0    | 0.0    | 0.0    | 0.0     | 0.0     | 0.0     | 0.0     |

(END OF REPORT)