

Scaled data based on original data using  
LM-79-08 Approved Method: Electrical and Photometric Measurements of Solid-  
State Lighting Products

Test Report Prepared for  
Cooper Lighting Solutions  
(formerly Eaton)

Brand: STREETWORKS

Report Number: P949250

Luminaire Tested: **GLAN-SB4A-760-U-SLL**

Issue Date: 1/21/2025

### Test Information

Test Method: LM-79-08  
Report Number: P949250  
TEST IS SCALED FROM IESNA LM-79-08 TEST DATA (G2-2411-289-8)  
Test Lab: INNOVATION CENTER  
Issue Date: 1/21/2025  
Manufacturer: COOPER LIGHTING SOLUTIONS (FORMERLY EATON)  
Product Line: STREETWORKS  
Catalog Number: GLAN-SB4A-760-U-SLL  
Description: GALLEON AREA AND ROADWAY HIGH DENSITY LED LUMINAIRE  
(4) 70 CRI, 5700K, 350mA LIGHTSQUARES WITH 26 LEDS EACH AND SPILL LIGHT  
ELIMINATOR LEFT OPTICS  
Light Source: -  
Ballast/Driver: -

### Summary

Lumens per Lamp: N/A  
Luminaire Lumens: 18952 lumens  
Efficiency: N/A  
Efficacy: 166.2 lumens/watt  
Luminous Opening: Rectangular (W 1' x L: 1' x H: 0')  
IES Classification: Type IV - Short  
BUG Rating: B3 - U0 - G4

Input Watts (W): 114  
Input Voltage (V): NR  
Input Current (Ain): NR  
Voltage Rise (V): NR  
Power Factor: NR  
Total Harmonic Distortion (THDi): NR  
Frequency (hertz): 60  
Stabilization Time: NR  
Operation Time: NR  
Ambient Temperature (°C): NR  
Test Distance: 24 FT




REPORT NUMBER: P949250

CATALOG NUMBER: GLAN-SB4A-760-U-SLL

## Iso-Footcandle Lines of Horizontal Illumination

× Max cd  
- - - 1/2 Max cd




Based on 25 foot mounting height. Maximum calculated value = 5.8 fc

Type IV - Short - N/A

REPORT NUMBER: P949250  
CATALOG NUMBER: GLAN-SB4A-760-U-SLL

Luminous Intensity Polar Plot



REPORT NUMBER: P949250

CATALOG NUMBER: GLAN-SB4A-760-U-SLL


**FLUX DISTRIBUTION:**

|                    |           | Downward | Upward | Total   |
|--------------------|-----------|----------|--------|---------|
| <b>House Side</b>  | Lumens    | 4816.6   | 0.0    | 4816.6  |
|                    | % Fixture | 25.4     | 0.0    | 25.4    |
| <b>Street Side</b> | Lumens    | 14135.3  | 0.0    | 14135.3 |
|                    | % Fixture | 74.6     | 0.0    | 74.6    |
| <b>Total</b>       | Lumens    | 18952.0  | 0.0    | 18952.0 |
|                    | % Fixture | 100.0    | 0.0    | 100.0   |

**ZONAL LUMENS:**

| Zone      | Lumens  | % Fixture |
|-----------|---------|-----------|
| 0°-10°    | 258.5   | 1.4       |
| 10°-20°   | 811.6   | 4.3       |
| 20°-30°   | 1253.6  | 6.6       |
| 30°-40°   | 1588.6  | 8.4       |
| 40°-50°   | 2396.0  | 12.6      |
| 50°-60°   | 3871.0  | 20.4      |
| 60°-70°   | 4825.9  | 25.5      |
| 70°-80°   | 3164.6  | 16.7      |
| 80°-90°   | 782.4   | 4.1       |
| 90°-100°  | 0.0     | 0.0       |
| 100°-110° | 0.0     | 0.0       |
| 110°-120° | 0.0     | 0.0       |
| 120°-130° | 0.0     | 0.0       |
| 130°-140° | 0.0     | 0.0       |
| 140°-150° | 0.0     | 0.0       |
| 150°-160° | 0.0     | 0.0       |
| 160°-170° | 0.0     | 0.0       |
| 170°-180° | 0.0     | 0.0       |
| 0°-90°    | 18952.0 | 100.0     |
| 0°-180°   | 18952.0 | 100.0     |

**Coefficient of Utilization**



REPORT NUMBER: P949250


CATALOG NUMBER: GLAN-SB4A-760-U-SLL

**LUMINAIRE CLASSIFICATION SYSTEM LUMEN TABLE AND BUG RATING:**

| Zone |             | Lumens | % Fixture | Zone Rating/Lumen Limit |      |         |
|------|-------------|--------|-----------|-------------------------|------|---------|
|      |             |        |           | B                       | U    | G       |
| FL   | (0°-30°)    | 1274.8 | 6.7       |                         |      |         |
| FM   | (30°-60°)   | 5527.9 | 29.2      |                         |      |         |
| FH   | (60°-80°)   | 6688.2 | 35.3      |                         |      | G3/7500 |
| FVH  | (80°-90°)   | 644.5  | 3.4       |                         |      | G4/750  |
| BL   | (0°-30°)    | 1048.9 | 5.5       | B3/2500                 |      |         |
| BM   | (30°-60°)   | 2327.7 | 12.3      | B2/2500                 |      |         |
| BH   | (60°-80°)   | 1302.2 | 6.9       | B3/2500                 |      | G3/2500 |
| BVH  | (80°-90°)   | 137.9  | 0.7       |                         |      | G2/225  |
| UL   | (90°-100°)  | 0.0    | 0.0       |                         | U0/0 |         |
| UH   | (100°-180°) | 0.0    | 0.0       |                         | U0/0 |         |

**BUG Rating: B3-U0-G4**

Type IV Short



REPORT NUMBER: P949250

CATALOG NUMBER: GLAN-SB4A-760-U-SLL

**CANDELA DISTRIBUTION (FULL):**

|       | 0°      | 5°      | 10°     | 15°     | 20°     | 25°     | 30°     | 35°     | 40°     | 45°     |
|-------|---------|---------|---------|---------|---------|---------|---------|---------|---------|---------|
| 0°    | 2606.1  | 2606.1  | 2606.1  | 2606.1  | 2606.1  | 2606.1  | 2606.1  | 2606.1  | 2606.1  | 2606.1  |
| 2.5°  | 2802.6  | 2813.2  | 2823.9  | 2839.0  | 2854.1  | 2863.1  | 2872.1  | 2876.6  | 2881.1  | 2879.1  |
| 5°    | 3013.6  | 3050.7  | 3087.9  | 3124.7  | 3161.6  | 3181.6  | 3201.6  | 3213.7  | 3225.9  | 3235.1  |
| 7.5°  | 3225.6  | 3286.0  | 3346.3  | 3400.6  | 3454.9  | 3487.6  | 3520.3  | 3538.0  | 3555.6  | 3564.1  |
| 10°   | 3388.1  | 3459.5  | 3530.9  | 3594.6  | 3658.3  | 3696.9  | 3735.3  | 3752.5  | 3769.6  | 3776.1  |
| 12.5° | 3487.6  | 3565.0  | 3642.3  | 3699.9  | 3757.3  | 3785.3  | 3813.3  | 3822.7  | 3832.1  | 3833.1  |
| 15°   | 3548.1  | 3614.9  | 3681.6  | 3717.7  | 3753.9  | 3754.9  | 3755.9  | 3745.9  | 3735.9  | 3724.1  |
| 17.5° | 3582.1  | 3627.2  | 3672.3  | 3673.0  | 3673.6  | 3633.1  | 3592.6  | 3555.5  | 3518.3  | 3492.1  |
| 20°   | 3619.6  | 3635.3  | 3651.1  | 3603.6  | 3556.1  | 3466.7  | 3377.3  | 3312.2  | 3247.1  | 3207.1  |
| 22.5° | 3663.1  | 3642.5  | 3621.9  | 3523.5  | 3425.1  | 3293.6  | 3162.1  | 3080.7  | 2999.3  | 2955.1  |
| 25°   | 3719.1  | 3654.1  | 3589.1  | 3439.7  | 3290.3  | 3130.6  | 2970.9  | 2885.3  | 2799.9  | 2758.1  |
| 27.5° | 3795.1  | 3678.9  | 3562.6  | 3364.7  | 3166.9  | 2989.9  | 2812.9  | 2728.7  | 2644.6  | 2605.1  |
| 30°   | 3897.6  | 3724.3  | 3551.1  | 3307.5  | 3063.9  | 2879.5  | 2695.1  | 2617.0  | 2538.9  | 2502.1  |
| 32.5° | 4018.6  | 3781.3  | 3544.1  | 3268.5  | 2992.9  | 2819.6  | 2646.3  | 2585.0  | 2523.6  | 2497.1  |
| 35°   | 4165.6  | 3875.2  | 3584.9  | 3297.7  | 3010.6  | 2890.2  | 2769.9  | 2755.6  | 2741.3  | 2739.1  |
| 37.5° | 4413.1  | 4071.5  | 3729.9  | 3468.9  | 3207.9  | 3200.1  | 3192.3  | 3257.7  | 3323.1  | 3357.1  |
| 40°   | 4787.1  | 4415.6  | 4044.1  | 3850.0  | 3655.9  | 3792.9  | 3929.9  | 4088.9  | 4247.9  | 4327.1  |
| 42.5° | 5283.1  | 4914.5  | 4545.9  | 4434.1  | 4322.3  | 4621.1  | 4919.9  | 5209.1  | 5498.3  | 5668.1  |
| 45°   | 5895.6  | 5564.5  | 5233.3  | 5184.0  | 5134.6  | 5613.3  | 6092.1  | 6567.4  | 7042.7  | 7331.2  |
| 47.5° | 6661.7  | 6339.6  | 6017.3  | 6007.3  | 5997.3  | 6688.0  | 7378.4  | 8074.1  | 8769.7  | 9178.2  |
| 50°   | 7665.7  | 7267.8  | 6870.0  | 6871.7  | 6873.4  | 7763.4  | 8653.4  | 9571.7  | 10490.1 | 11045.3 |
| 52.5° | 8818.2  | 8336.4  | 7854.7  | 7806.0  | 7757.2  | 8820.3  | 9883.4  | 11019.7 | 12155.8 | 12821.3 |
| 55°   | 10045.2 | 9569.2  | 9093.2  | 8903.3  | 8713.4  | 9896.6  | 11079.8 | 12434.3 | 13788.8 | 14580.4 |
| 57.5° | 11161.3 | 10902.1 | 10642.8 | 10261.8 | 9881.0  | 11075.8 | 12270.5 | 13804.7 | 15338.9 | 16320.4 |
| 60°   | 11835.8 | 12238.4 | 12641.1 | 12168.1 | 11695.1 | 12825.7 | 13956.3 | 15599.0 | 17241.6 | 18302.4 |
| 62.5° | 11493.3 | 12593.4 | 13693.5 | 13640.2 | 13586.8 | 14622.6 | 15658.4 | 17221.2 | 18784.0 | 19764.5 |
| 65°   | 10807.8 | 11840.3 | 12872.8 | 13077.1 | 13281.3 | 14597.6 | 15913.9 | 17429.3 | 18944.7 | 19779.5 |
| 67.5° | 9889.2  | 10871.3 | 11853.3 | 11949.1 | 12044.8 | 13416.2 | 14787.6 | 16309.5 | 17831.4 | 18485.4 |
| 70°   | 8785.7  | 9853.8  | 10922.1 | 10964.9 | 11007.8 | 12234.2 | 13460.5 | 14770.3 | 16079.9 | 16443.4 |
| 72.5° | 7470.7  | 8696.4  | 9922.2  | 9953.0  | 9983.7  | 10943.3 | 11902.8 | 12883.7 | 13864.5 | 13901.3 |
| 75°   | 5807.1  | 7075.8  | 8344.4  | 8458.3  | 8572.2  | 9318.7  | 10065.2 | 10755.8 | 11446.3 | 11261.3 |
| 77.5° | 4149.1  | 5333.3  | 6517.7  | 6680.7  | 6843.7  | 7411.2  | 7978.7  | 8468.4  | 8958.2  | 8640.2  |
| 80°   | 2715.6  | 3711.9  | 4708.1  | 4910.7  | 5113.3  | 5541.9  | 5970.3  | 6227.6  | 6484.7  | 5973.1  |
| 82.5° | 1578.5  | 2259.7  | 2940.9  | 3167.2  | 3393.6  | 3688.6  | 3983.6  | 4090.9  | 4198.1  | 3796.1  |
| 85°   | 694.5   | 1056.0  | 1417.5  | 1610.0  | 1802.5  | 2044.9  | 2287.3  | 2348.2  | 2409.1  | 2087.1  |
| 87.5° | 215.0   | 336.5   | 458.0   | 565.4   | 672.8   | 794.0   | 915.2   | 920.4   | 925.5   | 777.0   |
| 90°   | 0.0     | 0.0     | 0.0     | 0.0     | 0.0     | 0.0     | 0.0     | 0.0     | 0.0     | 0.0     |

REPORT NUMBER: P949250

CATALOG NUMBER: GLAN-SB4A-760-U-SLL

**CANDELA DISTRIBUTION (continued):**

| 50°     |       | 55°     | 60°     | 65°     | 70°     | 75°     | 80°     | 85°     | 90°     | 95°    | 100°   |
|---------|-------|---------|---------|---------|---------|---------|---------|---------|---------|--------|--------|
| 2606.1  | 0°    | 2606.1  | 2606.1  | 2606.1  | 2606.1  | 2606.1  | 2606.1  | 2606.1  | 2606.1  | 2606.1 | 2606.1 |
| 2881.1  | 2.5°  | 2876.6  | 2872.1  | 2863.1  | 2854.1  | 2839.0  | 2823.9  | 2813.2  | 2802.6  | 2781.1 | 2759.6 |
| 3225.9  | 5°    | 3213.7  | 3201.6  | 3181.6  | 3161.6  | 3124.7  | 3087.9  | 3050.7  | 3013.6  | 2966.1 | 2918.6 |
| 3555.6  | 7.5°  | 3538.0  | 3520.3  | 3487.6  | 3454.9  | 3400.6  | 3346.3  | 3286.0  | 3225.6  | 3147.2 | 3068.9 |
| 3769.6  | 10°   | 3752.5  | 3735.3  | 3696.9  | 3658.3  | 3594.6  | 3530.9  | 3459.5  | 3388.1  | 3289.0 | 3189.9 |
| 3832.1  | 12.5° | 3822.7  | 3813.3  | 3785.3  | 3757.3  | 3699.9  | 3642.3  | 3565.0  | 3487.6  | 3378.7 | 3269.9 |
| 3735.9  | 15°   | 3745.9  | 3755.9  | 3754.9  | 3753.9  | 3717.7  | 3681.6  | 3614.9  | 3548.1  | 3434.6 | 3321.1 |
| 3518.3  | 17.5° | 3555.5  | 3592.6  | 3633.1  | 3673.6  | 3673.0  | 3672.3  | 3627.2  | 3582.1  | 3467.0 | 3351.9 |
| 3247.1  | 20°   | 3312.2  | 3377.3  | 3466.7  | 3556.1  | 3603.6  | 3651.1  | 3635.3  | 3619.6  | 3500.0 | 3380.3 |
| 2999.3  | 22.5° | 3080.7  | 3162.1  | 3293.6  | 3425.1  | 3523.5  | 3621.9  | 3642.5  | 3663.1  | 3540.9 | 3418.6 |
| 2799.9  | 25°   | 2885.3  | 2970.9  | 3130.6  | 3290.3  | 3439.7  | 3589.1  | 3654.1  | 3719.1  | 3599.3 | 3479.6 |
| 2644.6  | 27.5° | 2728.7  | 2812.9  | 2989.9  | 3166.9  | 3364.7  | 3562.6  | 3678.9  | 3795.1  | 3680.9 | 3566.6 |
| 2538.9  | 30°   | 2617.0  | 2695.1  | 2879.5  | 3063.9  | 3307.5  | 3551.1  | 3724.3  | 3897.6  | 3787.2 | 3676.9 |
| 2523.6  | 32.5° | 2585.0  | 2646.3  | 2819.6  | 2992.9  | 3268.5  | 3544.1  | 3781.3  | 4018.6  | 3909.3 | 3800.1 |
| 2741.3  | 35°   | 2755.6  | 2769.9  | 2890.2  | 3010.6  | 3297.7  | 3584.9  | 3875.2  | 4165.6  | 4061.0 | 3956.3 |
| 3323.1  | 37.5° | 3257.7  | 3192.3  | 3200.1  | 3207.9  | 3468.9  | 3729.9  | 4071.5  | 4413.1  | 4279.7 | 4146.3 |
| 4247.9  | 40°   | 4088.9  | 3929.9  | 3792.9  | 3655.9  | 3850.0  | 4044.1  | 4415.6  | 4787.1  | 4592.7 | 4398.3 |
| 5498.3  | 42.5° | 5209.1  | 4919.9  | 4621.1  | 4322.3  | 4434.1  | 4545.9  | 4914.5  | 5283.1  | 5002.5 | 4721.9 |
| 7042.7  | 45°   | 6567.4  | 6092.1  | 5613.3  | 5134.6  | 5184.0  | 5233.3  | 5564.5  | 5895.6  | 5517.1 | 5138.6 |
| 8769.7  | 47.5° | 8074.1  | 7378.4  | 6688.0  | 5997.3  | 6007.3  | 6017.3  | 6339.6  | 6661.7  | 6128.9 | 5596.1 |
| 10490.1 | 50°   | 9571.7  | 8653.4  | 7763.4  | 6873.4  | 6871.7  | 6870.0  | 7267.8  | 7665.7  | 6862.6 | 6059.3 |
| 12155.8 | 52.5° | 11019.7 | 9883.4  | 8820.3  | 7757.2  | 7806.0  | 7854.7  | 8336.4  | 8818.2  | 7633.2 | 6448.2 |
| 13788.8 | 55°   | 12434.3 | 11079.8 | 9896.6  | 8713.4  | 8903.3  | 9093.2  | 9569.2  | 10045.2 | 8316.4 | 6587.7 |
| 15338.9 | 57.5° | 13804.7 | 12270.5 | 11075.8 | 9881.0  | 10261.8 | 10642.8 | 10902.1 | 11161.3 | 8800.6 | 6440.0 |
| 17241.6 | 60°   | 15599.0 | 13956.3 | 12825.7 | 11695.1 | 12168.1 | 12641.1 | 12238.4 | 11835.8 | 8921.6 | 6007.3 |
| 18784.0 | 62.5° | 17221.2 | 15658.4 | 14622.6 | 13586.8 | 13640.2 | 13693.5 | 12593.4 | 11493.3 | 8412.1 | 5330.9 |
| 18944.7 | 65°   | 17429.3 | 15913.9 | 14597.6 | 13281.3 | 13077.1 | 12872.8 | 11840.3 | 10807.8 | 7691.2 | 4574.6 |
| 17831.4 | 67.5° | 16309.5 | 14787.6 | 13416.2 | 12044.8 | 11949.1 | 11853.3 | 10871.3 | 9889.2  | 6833.3 | 3777.3 |
| 16079.9 | 70°   | 14770.3 | 13460.5 | 12234.2 | 11007.8 | 10964.9 | 10922.1 | 9853.8  | 8785.7  | 5897.1 | 3008.6 |
| 13864.5 | 72.5° | 12883.7 | 11902.8 | 10943.3 | 9983.7  | 9953.0  | 9922.2  | 8696.4  | 7470.7  | 4882.3 | 2294.1 |
| 11446.3 | 75°   | 10755.8 | 10065.2 | 9318.7  | 8572.2  | 8458.3  | 8344.4  | 7075.8  | 5807.1  | 3719.0 | 1630.8 |
| 8958.2  | 77.5° | 8468.4  | 7978.7  | 7411.2  | 6843.7  | 6680.7  | 6517.7  | 5333.3  | 4149.1  | 2603.0 | 1056.8 |
| 6484.7  | 80°   | 6227.6  | 5970.3  | 5541.9  | 5113.3  | 4910.7  | 4708.1  | 3711.9  | 2715.6  | 1677.0 | 638.5  |
| 4198.1  | 82.5° | 4090.9  | 3983.6  | 3688.6  | 3393.6  | 3167.2  | 2940.9  | 2259.7  | 1578.5  | 970.6  | 362.8  |
| 2409.1  | 85°   | 2348.2  | 2287.3  | 2044.9  | 1802.5  | 1610.0  | 1417.5  | 1056.0  | 694.5   | 436.6  | 178.8  |
| 925.5   | 87.5° | 920.4   | 915.2   | 794.0   | 672.8   | 565.4   | 458.0   | 336.5   | 215.0   | 143.0  | 71.0   |
| 0.0     | 90°   | 0.0     | 0.0     | 0.0     | 0.0     | 0.0     | 0.0     | 0.0     | 0.0     | 0.0    | 0.0    |

REPORT NUMBER: P949250

CATALOG NUMBER: GLAN-SB4A-760-U-SLL

**CANDELA DISTRIBUTION (continued):**

| 105°   |       | 110°   | 115°   | 120°   | 125°   | 130°   | 135°   | 140°   | 145°   | 150°   | 155°   |
|--------|-------|--------|--------|--------|--------|--------|--------|--------|--------|--------|--------|
| 2606.1 | 0°    | 2606.1 | 2606.1 | 2606.1 | 2606.1 | 2606.1 | 2606.1 | 2606.1 | 2606.1 | 2606.1 | 2606.1 |
| 2736.7 | 2.5°  | 2713.9 | 2690.9 | 2667.9 | 2645.9 | 2623.9 | 2602.6 | 2578.9 | 2559.7 | 2540.6 | 2523.3 |
| 2871.2 | 5°    | 2823.9 | 2776.2 | 2728.6 | 2684.1 | 2639.6 | 2597.6 | 2556.1 | 2519.9 | 2483.6 | 2453.2 |
| 2996.5 | 7.5°  | 2924.1 | 2853.6 | 2783.1 | 2721.0 | 2658.9 | 2601.6 | 2547.9 | 2499.7 | 2451.6 | 2411.6 |
| 3094.2 | 10°   | 2998.6 | 2913.0 | 2827.3 | 2753.9 | 2680.3 | 2609.6 | 2551.9 | 2501.1 | 2450.3 | 2410.3 |
| 3161.5 | 12.5° | 3053.1 | 2952.1 | 2851.1 | 2768.0 | 2684.9 | 2610.6 | 2556.9 | 2515.3 | 2473.9 | 2447.3 |
| 3203.5 | 15°   | 3085.9 | 2969.6 | 2853.3 | 2757.1 | 2660.9 | 2578.6 | 2535.6 | 2515.7 | 2495.9 | 2499.5 |
| 3223.6 | 17.5° | 3095.3 | 2960.3 | 2825.3 | 2709.6 | 2593.9 | 2497.1 | 2470.6 | 2477.9 | 2485.1 | 2528.7 |
| 3239.3 | 20°   | 3098.3 | 2934.7 | 2771.1 | 2627.7 | 2484.3 | 2371.6 | 2364.6 | 2398.6 | 2432.6 | 2508.3 |
| 3260.5 | 22.5° | 3102.3 | 2903.3 | 2704.3 | 2531.6 | 2358.9 | 2230.6 | 2244.3 | 2294.6 | 2344.9 | 2431.3 |
| 3298.9 | 25°   | 3118.1 | 2872.3 | 2626.6 | 2424.3 | 2222.1 | 2090.6 | 2127.6 | 2185.6 | 2243.6 | 2321.3 |
| 3358.9 | 27.5° | 3151.1 | 2851.6 | 2552.1 | 2326.2 | 2100.3 | 1980.5 | 2025.5 | 2081.6 | 2137.6 | 2201.5 |
| 3436.6 | 30°   | 3196.3 | 2841.9 | 2487.3 | 2244.2 | 2001.0 | 1900.5 | 1935.8 | 1980.2 | 2024.8 | 2077.9 |
| 3517.7 | 32.5° | 3235.3 | 2829.9 | 2424.3 | 2173.5 | 1922.5 | 1841.5 | 1857.2 | 1883.5 | 1909.8 | 1952.1 |
| 3610.1 | 35°   | 3263.9 | 2807.3 | 2350.9 | 2104.0 | 1857.0 | 1789.5 | 1783.0 | 1790.2 | 1797.5 | 1829.8 |
| 3713.6 | 37.5° | 3280.9 | 2768.6 | 2256.3 | 2022.1 | 1788.0 | 1729.0 | 1705.2 | 1697.2 | 1689.2 | 1712.4 |
| 3845.0 | 40°   | 3291.6 | 2715.3 | 2139.1 | 1924.5 | 1710.0 | 1656.5 | 1620.0 | 1601.9 | 1583.8 | 1600.5 |
| 4016.9 | 42.5° | 3311.9 | 2660.3 | 2008.8 | 1816.8 | 1624.8 | 1575.5 | 1529.5 | 1505.5 | 1481.5 | 1495.1 |
| 4243.1 | 45°   | 3347.6 | 2609.2 | 1870.8 | 1702.4 | 1534.0 | 1484.0 | 1439.5 | 1416.1 | 1392.8 | 1404.2 |
| 4484.1 | 47.5° | 3372.1 | 2567.0 | 1761.8 | 1611.9 | 1462.0 | 1397.5 | 1359.2 | 1339.6 | 1320.0 | 1330.8 |
| 4707.7 | 50°   | 3356.1 | 2521.0 | 1685.8 | 1551.8 | 1417.8 | 1333.0 | 1288.5 | 1271.1 | 1253.8 | 1270.6 |
| 4852.9 | 52.5° | 3257.6 | 2443.3 | 1629.0 | 1512.2 | 1395.5 | 1298.0 | 1235.8 | 1218.6 | 1201.5 | 1226.8 |
| 4820.9 | 55°   | 3054.1 | 2314.5 | 1574.8 | 1483.5 | 1392.2 | 1301.5 | 1207.8 | 1180.6 | 1153.5 | 1189.4 |
| 4595.7 | 57.5° | 2751.6 | 2132.9 | 1514.0 | 1449.5 | 1385.0 | 1305.0 | 1191.0 | 1151.4 | 1111.8 | 1150.4 |
| 4176.6 | 60°   | 2345.9 | 1897.0 | 1448.2 | 1397.5 | 1346.8 | 1294.0 | 1175.2 | 1123.9 | 1072.5 | 1106.4 |
| 3609.9 | 62.5° | 1888.8 | 1614.8 | 1340.8 | 1307.1 | 1273.5 | 1267.0 | 1156.8 | 1092.6 | 1028.5 | 1050.0 |
| 3031.7 | 65°   | 1488.8 | 1360.9 | 1233.0 | 1217.1 | 1201.2 | 1202.0 | 1118.0 | 1049.8 | 981.5  | 989.8  |
| 2465.3 | 67.5° | 1153.2 | 1116.9 | 1080.5 | 1089.4 | 1098.2 | 1096.0 | 1048.8 | 992.0  | 935.2  | 932.6  |
| 1941.0 | 70°   | 873.5  | 883.9  | 894.2  | 935.4  | 976.5  | 976.5  | 961.0  | 920.6  | 880.2  | 871.2  |
| 1483.9 | 72.5° | 673.8  | 705.1  | 736.5  | 794.9  | 853.2  | 863.0  | 863.2  | 835.5  | 807.8  | 794.6  |
| 1077.0 | 75°   | 523.2  | 551.6  | 580.0  | 645.4  | 710.8  | 756.0  | 752.2  | 730.9  | 709.5  | 696.9  |
| 729.8  | 77.5° | 402.8  | 422.1  | 441.5  | 505.0  | 568.5  | 643.0  | 641.0  | 623.9  | 606.8  | 594.0  |
| 470.2  | 80°   | 302.0  | 310.0  | 318.0  | 371.8  | 425.5  | 514.5  | 514.2  | 499.9  | 485.5  | 474.8  |
| 289.2  | 82.5° | 215.8  | 217.2  | 218.8  | 258.4  | 298.0  | 374.0  | 378.2  | 371.2  | 364.2  | 356.6  |
| 154.6  | 85°   | 130.5  | 129.8  | 129.0  | 158.0  | 187.0  | 243.5  | 249.0  | 241.5  | 234.0  | 225.5  |
| 64.1   | 87.5° | 57.2   | 56.5   | 55.8   | 67.6   | 79.5   | 103.0  | 110.0  | 107.0  | 104.0  | 102.4  |
| 0.0    | 90°   | 0.0    | 0.0    | 0.0    | 0.0    | 0.0    | 0.0    | 0.0    | 0.0    | 0.0    | 0.0    |

REPORT NUMBER: P949250  
CATALOG NUMBER: GLAN-SB4A-760-U-SLL

**CANDELA DISTRIBUTION (continued):**

| 160°   |       | 165°   | 170°   | 175°   | 180°   | 185°   | 190°   | 195°   | 200°   | 205°   | 210°   |
|--------|-------|--------|--------|--------|--------|--------|--------|--------|--------|--------|--------|
| 2606.1 | 0°    | 2606.1 | 2606.1 | 2606.1 | 2606.1 | 2606.1 | 2606.1 | 2606.1 | 2606.1 | 2606.1 | 2606.1 |
| 2506.1 | 2.5°  | 2491.0 | 2475.9 | 2460.7 | 2445.6 | 2433.9 | 2422.1 | 2412.6 | 2403.1 | 2395.7 | 2388.3 |
| 2422.9 | 5°    | 2396.1 | 2369.3 | 2345.0 | 2320.6 | 2301.9 | 2283.1 | 2270.0 | 2256.9 | 2247.6 | 2238.3 |
| 2371.6 | 7.5°  | 2337.9 | 2304.1 | 2274.3 | 2244.6 | 2222.3 | 2200.1 | 2184.5 | 2168.9 | 2158.2 | 2147.6 |
| 2370.3 | 10°   | 2334.0 | 2297.6 | 2264.1 | 2230.6 | 2204.0 | 2177.3 | 2159.9 | 2142.3 | 2132.2 | 2122.1 |
| 2420.9 | 12.5° | 2392.3 | 2363.9 | 2329.2 | 2294.6 | 2260.6 | 2226.6 | 2204.1 | 2181.6 | 2170.3 | 2159.1 |
| 2503.1 | 15°   | 2495.7 | 2488.3 | 2458.2 | 2428.1 | 2379.7 | 2331.3 | 2297.1 | 2262.9 | 2247.2 | 2231.6 |
| 2572.3 | 17.5° | 2595.5 | 2618.6 | 2594.3 | 2570.1 | 2506.0 | 2441.9 | 2391.5 | 2341.1 | 2317.9 | 2294.6 |
| 2584.1 | 20°   | 2632.6 | 2681.1 | 2669.9 | 2658.6 | 2585.3 | 2512.1 | 2450.3 | 2388.6 | 2358.9 | 2329.1 |
| 2517.9 | 22.5° | 2581.0 | 2644.1 | 2650.9 | 2657.6 | 2587.6 | 2517.6 | 2454.0 | 2390.3 | 2359.0 | 2327.6 |
| 2399.1 | 25°   | 2461.2 | 2523.3 | 2546.5 | 2569.6 | 2512.2 | 2454.9 | 2398.3 | 2341.9 | 2314.7 | 2287.6 |
| 2265.3 | 27.5° | 2315.1 | 2364.9 | 2390.7 | 2416.6 | 2375.7 | 2334.9 | 2291.0 | 2247.1 | 2228.9 | 2210.6 |
| 2130.9 | 30°   | 2172.2 | 2213.6 | 2234.6 | 2255.6 | 2224.5 | 2193.3 | 2161.9 | 2130.3 | 2121.0 | 2111.6 |
| 1994.5 | 32.5° | 2034.1 | 2073.9 | 2097.2 | 2120.6 | 2092.0 | 2063.3 | 2038.1 | 2013.0 | 2006.9 | 2000.8 |
| 1862.0 | 35°   | 1901.2 | 1940.5 | 1968.5 | 1996.5 | 1976.1 | 1955.8 | 1932.6 | 1909.5 | 1900.2 | 1891.0 |
| 1735.5 | 37.5° | 1774.6 | 1813.8 | 1848.4 | 1883.0 | 1873.6 | 1864.2 | 1842.9 | 1821.5 | 1804.6 | 1787.8 |
| 1617.2 | 40°   | 1655.0 | 1692.8 | 1732.6 | 1772.5 | 1774.8 | 1777.0 | 1758.9 | 1740.8 | 1716.2 | 1691.8 |
| 1508.8 | 42.5° | 1544.6 | 1580.5 | 1623.5 | 1666.5 | 1678.0 | 1689.5 | 1674.2 | 1659.0 | 1628.5 | 1598.0 |
| 1415.8 | 45°   | 1449.8 | 1483.8 | 1528.4 | 1573.0 | 1589.5 | 1606.0 | 1592.2 | 1578.5 | 1543.6 | 1508.8 |
| 1341.5 | 47.5° | 1374.8 | 1408.0 | 1452.0 | 1496.0 | 1515.0 | 1534.0 | 1524.4 | 1514.8 | 1483.8 | 1452.8 |
| 1287.5 | 50°   | 1318.9 | 1350.2 | 1389.6 | 1429.0 | 1453.4 | 1477.8 | 1477.2 | 1476.8 | 1452.0 | 1427.2 |
| 1252.0 | 52.5° | 1280.8 | 1309.5 | 1346.2 | 1383.0 | 1411.9 | 1440.8 | 1446.0 | 1451.2 | 1431.0 | 1410.8 |
| 1225.2 | 55°   | 1256.2 | 1287.2 | 1319.4 | 1351.5 | 1382.1 | 1412.8 | 1420.0 | 1427.2 | 1409.6 | 1392.0 |
| 1189.0 | 57.5° | 1225.4 | 1261.8 | 1293.6 | 1325.5 | 1356.4 | 1387.2 | 1394.5 | 1401.8 | 1384.0 | 1366.2 |
| 1140.2 | 60°   | 1182.0 | 1223.8 | 1256.1 | 1288.5 | 1319.5 | 1350.5 | 1358.5 | 1366.5 | 1349.1 | 1331.8 |
| 1071.5 | 62.5° | 1120.2 | 1169.0 | 1203.5 | 1238.0 | 1266.4 | 1294.8 | 1302.5 | 1310.2 | 1294.5 | 1278.8 |
| 998.0  | 65°   | 1050.2 | 1102.5 | 1135.5 | 1168.5 | 1193.5 | 1218.5 | 1226.4 | 1234.2 | 1219.1 | 1204.0 |
| 930.0  | 67.5° | 978.2  | 1026.5 | 1057.8 | 1089.0 | 1110.6 | 1132.2 | 1139.9 | 1147.5 | 1133.6 | 1119.8 |
| 862.2  | 70°   | 904.6  | 947.0  | 974.0  | 1001.0 | 1020.5 | 1040.0 | 1047.4 | 1054.8 | 1043.5 | 1032.2 |
| 781.5  | 72.5° | 814.9  | 848.2  | 872.6  | 897.0  | 916.1  | 935.2  | 944.0  | 952.8  | 943.4  | 934.0  |
| 684.2  | 75°   | 709.0  | 733.8  | 755.9  | 778.0  | 795.4  | 812.8  | 822.0  | 831.2  | 826.6  | 822.0  |
| 581.2  | 77.5° | 601.4  | 621.5  | 640.5  | 659.5  | 677.8  | 696.0  | 704.6  | 713.2  | 706.8  | 700.2  |
| 464.0  | 80°   | 480.8  | 497.5  | 513.5  | 529.5  | 543.4  | 557.2  | 568.6  | 580.0  | 577.2  | 574.5  |
| 349.0  | 82.5° | 347.6  | 346.2  | 340.6  | 335.0  | 364.6  | 394.2  | 413.6  | 433.0  | 431.8  | 430.5  |
| 217.0  | 85°   | 209.8  | 202.5  | 187.0  | 171.5  | 199.2  | 227.0  | 251.0  | 275.0  | 273.0  | 271.0  |
| 100.8  | 87.5° | 100.5  | 100.2  | 88.4   | 76.5   | 88.1   | 99.8   | 109.5  | 119.2  | 116.8  | 114.2  |
| 0.0    | 90°   | 0.0    | 0.0    | 0.0    | 0.0    | 0.0    | 0.0    | 0.0    | 0.0    | 0.0    | 0.0    |

REPORT NUMBER: P949250

CATALOG NUMBER: GLAN-SB4A-760-U-SLL

**CANDELA DISTRIBUTION (continued):**

| 215°   |       | 220°   | 225°   | 230°   | 235°   | 240°   | 245°   | 250°   | 255°   | 260°   | 265°   |
|--------|-------|--------|--------|--------|--------|--------|--------|--------|--------|--------|--------|
| 2606.1 | 0°    | 2606.1 | 2606.1 | 2606.1 | 2606.1 | 2606.1 | 2606.1 | 2606.1 | 2606.1 | 2606.1 | 2606.1 |
| 2381.5 | 2.5°  | 2374.6 | 2366.1 | 2374.6 | 2381.5 | 2388.3 | 2395.7 | 2403.1 | 2412.6 | 2422.1 | 2433.9 |
| 2231.2 | 5°    | 2224.1 | 2217.1 | 2224.1 | 2231.2 | 2238.3 | 2247.6 | 2256.9 | 2270.0 | 2283.1 | 2301.9 |
| 2141.2 | 7.5°  | 2134.9 | 2130.1 | 2134.9 | 2141.2 | 2147.6 | 2158.2 | 2168.9 | 2184.5 | 2200.1 | 2222.3 |
| 2116.7 | 10°   | 2111.3 | 2109.1 | 2111.3 | 2116.7 | 2122.1 | 2132.2 | 2142.3 | 2159.9 | 2177.3 | 2204.0 |
| 2154.5 | 12.5° | 2149.9 | 2149.1 | 2149.9 | 2154.5 | 2159.1 | 2170.3 | 2181.6 | 2204.1 | 2226.6 | 2260.6 |
| 2225.6 | 15°   | 2219.6 | 2219.1 | 2219.6 | 2225.6 | 2231.6 | 2247.2 | 2262.9 | 2297.1 | 2331.3 | 2379.7 |
| 2287.0 | 17.5° | 2279.3 | 2278.1 | 2279.3 | 2287.0 | 2294.6 | 2317.9 | 2341.1 | 2391.5 | 2441.9 | 2506.0 |
| 2319.6 | 20°   | 2310.1 | 2307.1 | 2310.1 | 2319.6 | 2329.1 | 2358.9 | 2388.6 | 2450.3 | 2512.1 | 2585.3 |
| 2317.1 | 22.5° | 2306.6 | 2302.1 | 2306.6 | 2317.1 | 2327.6 | 2359.0 | 2390.3 | 2454.0 | 2517.6 | 2587.6 |
| 2277.7 | 25°   | 2267.9 | 2262.1 | 2267.9 | 2277.7 | 2287.6 | 2314.7 | 2341.9 | 2398.3 | 2454.9 | 2512.2 |
| 2206.1 | 27.5° | 2201.6 | 2200.1 | 2201.6 | 2206.1 | 2210.6 | 2228.9 | 2247.1 | 2291.0 | 2334.9 | 2375.7 |
| 2111.6 | 30°   | 2111.6 | 2113.1 | 2111.6 | 2111.6 | 2111.6 | 2121.0 | 2130.3 | 2161.9 | 2193.3 | 2224.5 |
| 2001.6 | 32.5° | 2002.5 | 2004.0 | 2002.5 | 2001.6 | 2000.8 | 2006.9 | 2013.0 | 2038.1 | 2063.3 | 2092.0 |
| 1889.0 | 35°   | 1887.0 | 1886.0 | 1887.0 | 1889.0 | 1891.0 | 1900.2 | 1909.5 | 1932.6 | 1955.8 | 1976.1 |
| 1778.9 | 37.5° | 1770.0 | 1765.0 | 1770.0 | 1778.9 | 1787.8 | 1804.6 | 1821.5 | 1842.9 | 1864.2 | 1873.6 |
| 1675.2 | 40°   | 1658.8 | 1649.0 | 1658.8 | 1675.2 | 1691.8 | 1716.2 | 1740.8 | 1758.9 | 1777.0 | 1774.8 |
| 1573.9 | 42.5° | 1549.8 | 1534.0 | 1549.8 | 1573.9 | 1598.0 | 1628.5 | 1659.0 | 1674.2 | 1689.5 | 1678.0 |
| 1480.5 | 45°   | 1452.2 | 1434.0 | 1452.2 | 1480.5 | 1508.8 | 1543.6 | 1578.5 | 1592.2 | 1606.0 | 1589.5 |
| 1426.6 | 47.5° | 1400.5 | 1383.0 | 1400.5 | 1426.6 | 1452.8 | 1483.8 | 1514.8 | 1524.4 | 1534.0 | 1515.0 |
| 1403.0 | 50°   | 1378.8 | 1362.0 | 1378.8 | 1403.0 | 1427.2 | 1452.0 | 1476.8 | 1477.2 | 1477.8 | 1453.4 |
| 1389.1 | 52.5° | 1367.5 | 1352.0 | 1367.5 | 1389.1 | 1410.8 | 1431.0 | 1451.2 | 1446.0 | 1440.8 | 1411.9 |
| 1373.0 | 55°   | 1354.0 | 1340.0 | 1354.0 | 1373.0 | 1392.0 | 1409.6 | 1427.2 | 1420.0 | 1412.8 | 1382.1 |
| 1347.4 | 57.5° | 1328.5 | 1314.0 | 1328.5 | 1347.4 | 1366.2 | 1384.0 | 1401.8 | 1394.5 | 1387.2 | 1356.4 |
| 1312.4 | 60°   | 1293.0 | 1278.0 | 1293.0 | 1312.4 | 1331.8 | 1349.1 | 1366.5 | 1358.5 | 1350.5 | 1319.5 |
| 1258.4 | 62.5° | 1238.0 | 1220.0 | 1238.0 | 1258.4 | 1278.8 | 1294.5 | 1310.2 | 1302.5 | 1294.8 | 1266.4 |
| 1184.2 | 65°   | 1164.5 | 1149.0 | 1164.5 | 1184.2 | 1204.0 | 1219.1 | 1234.2 | 1226.4 | 1218.5 | 1193.5 |
| 1101.4 | 67.5° | 1083.0 | 1069.0 | 1083.0 | 1101.4 | 1119.8 | 1133.6 | 1147.5 | 1139.9 | 1132.2 | 1110.6 |
| 1014.6 | 70°   | 997.0  | 981.0  | 997.0  | 1014.6 | 1032.2 | 1043.5 | 1054.8 | 1047.4 | 1040.0 | 1020.5 |
| 917.2  | 72.5° | 900.5  | 885.0  | 900.5  | 917.2  | 934.0  | 943.4  | 952.8  | 944.0  | 935.2  | 916.1  |
| 807.9  | 75°   | 793.8  | 779.0  | 793.8  | 807.9  | 822.0  | 826.6  | 831.2  | 822.0  | 812.8  | 795.4  |
| 686.0  | 77.5° | 671.8  | 660.0  | 671.8  | 686.0  | 700.2  | 706.8  | 713.2  | 704.6  | 696.0  | 677.8  |
| 555.4  | 80°   | 536.2  | 514.0  | 536.2  | 555.4  | 574.5  | 577.2  | 580.0  | 568.6  | 557.2  | 543.4  |
| 414.4  | 82.5° | 398.2  | 384.0  | 398.2  | 414.4  | 430.5  | 431.8  | 433.0  | 413.6  | 394.2  | 364.6  |
| 258.4  | 85°   | 245.8  | 233.0  | 245.8  | 258.4  | 271.0  | 273.0  | 275.0  | 251.0  | 227.0  | 199.2  |
| 107.8  | 87.5° | 101.2  | 95.0   | 101.2  | 107.8  | 114.2  | 116.8  | 119.2  | 109.5  | 99.8   | 88.1   |
| 0.0    | 90°   | 0.0    | 0.0    | 0.0    | 0.0    | 0.0    | 0.0    | 0.0    | 0.0    | 0.0    | 0.0    |

REPORT NUMBER: P949250

CATALOG NUMBER: GLAN-SB4A-760-U-SLL

**CANDELA DISTRIBUTION (continued):**

| 270°   |       | 275°   | 280°   | 285°   | 290°   | 295°   | 300°   | 305°   | 310°   | 315°   | 320°   |
|--------|-------|--------|--------|--------|--------|--------|--------|--------|--------|--------|--------|
| 2606.1 | 0°    | 2606.1 | 2606.1 | 2606.1 | 2606.1 | 2606.1 | 2606.1 | 2606.1 | 2606.1 | 2606.1 | 2606.1 |
| 2445.6 | 2.5°  | 2460.7 | 2475.9 | 2491.0 | 2506.1 | 2523.3 | 2540.6 | 2559.7 | 2578.9 | 2602.6 | 2623.9 |
| 2320.6 | 5°    | 2345.0 | 2369.3 | 2396.1 | 2422.9 | 2453.2 | 2483.6 | 2519.9 | 2556.1 | 2597.6 | 2639.6 |
| 2244.6 | 7.5°  | 2274.3 | 2304.1 | 2337.9 | 2371.6 | 2411.6 | 2451.6 | 2499.7 | 2547.9 | 2601.6 | 2658.9 |
| 2230.6 | 10°   | 2264.1 | 2297.6 | 2334.0 | 2370.3 | 2410.3 | 2450.3 | 2501.1 | 2551.9 | 2609.6 | 2680.3 |
| 2294.6 | 12.5° | 2329.2 | 2363.9 | 2392.3 | 2420.9 | 2447.3 | 2473.9 | 2515.3 | 2556.9 | 2610.6 | 2684.9 |
| 2428.1 | 15°   | 2458.2 | 2488.3 | 2495.7 | 2503.1 | 2499.5 | 2495.9 | 2515.7 | 2535.6 | 2578.6 | 2660.9 |
| 2570.1 | 17.5° | 2594.3 | 2618.6 | 2595.5 | 2572.3 | 2528.7 | 2485.1 | 2477.9 | 2470.6 | 2497.1 | 2593.9 |
| 2658.6 | 20°   | 2669.9 | 2681.1 | 2632.6 | 2584.1 | 2508.3 | 2432.6 | 2398.6 | 2364.6 | 2371.6 | 2484.3 |
| 2657.6 | 22.5° | 2650.9 | 2644.1 | 2581.0 | 2517.9 | 2431.3 | 2344.9 | 2294.6 | 2244.3 | 2230.6 | 2358.9 |
| 2569.6 | 25°   | 2546.5 | 2523.3 | 2461.2 | 2399.1 | 2321.3 | 2243.6 | 2185.6 | 2127.6 | 2090.6 | 2222.1 |
| 2416.6 | 27.5° | 2390.7 | 2364.9 | 2315.1 | 2265.3 | 2201.5 | 2137.6 | 2081.6 | 2025.5 | 1980.5 | 2100.3 |
| 2255.6 | 30°   | 2234.6 | 2213.6 | 2172.2 | 2130.9 | 2077.9 | 2024.8 | 1980.2 | 1935.8 | 1900.5 | 2001.0 |
| 2120.6 | 32.5° | 2097.2 | 2073.9 | 2034.1 | 1994.5 | 1952.1 | 1909.8 | 1883.5 | 1857.2 | 1841.5 | 1922.5 |
| 1996.5 | 35°   | 1968.5 | 1940.5 | 1901.2 | 1862.0 | 1829.8 | 1797.5 | 1790.2 | 1783.0 | 1789.5 | 1857.0 |
| 1883.0 | 37.5° | 1848.4 | 1813.8 | 1774.6 | 1735.5 | 1712.4 | 1689.2 | 1697.2 | 1705.2 | 1729.0 | 1788.0 |
| 1772.5 | 40°   | 1732.6 | 1692.8 | 1655.0 | 1617.2 | 1600.5 | 1583.8 | 1601.9 | 1620.0 | 1656.5 | 1710.0 |
| 1666.5 | 42.5° | 1623.5 | 1580.5 | 1544.6 | 1508.8 | 1495.1 | 1481.5 | 1505.5 | 1529.5 | 1575.5 | 1624.8 |
| 1573.0 | 45°   | 1528.4 | 1483.8 | 1449.8 | 1415.8 | 1404.2 | 1392.8 | 1416.1 | 1439.5 | 1484.0 | 1534.0 |
| 1496.0 | 47.5° | 1452.0 | 1408.0 | 1374.8 | 1341.5 | 1330.8 | 1320.0 | 1339.6 | 1359.2 | 1397.5 | 1462.0 |
| 1429.0 | 50°   | 1389.6 | 1350.2 | 1318.9 | 1287.5 | 1270.6 | 1253.8 | 1271.1 | 1288.5 | 1333.0 | 1417.8 |
| 1383.0 | 52.5° | 1346.2 | 1309.5 | 1280.8 | 1252.0 | 1226.8 | 1201.5 | 1218.6 | 1235.8 | 1298.0 | 1395.5 |
| 1351.5 | 55°   | 1319.4 | 1287.2 | 1256.2 | 1225.2 | 1189.4 | 1153.5 | 1180.6 | 1207.8 | 1301.5 | 1392.2 |
| 1325.5 | 57.5° | 1293.6 | 1261.8 | 1225.4 | 1189.0 | 1150.4 | 1111.8 | 1151.4 | 1191.0 | 1305.0 | 1385.0 |
| 1288.5 | 60°   | 1256.1 | 1223.8 | 1182.0 | 1140.2 | 1106.4 | 1072.5 | 1123.9 | 1175.2 | 1294.0 | 1346.8 |
| 1238.0 | 62.5° | 1203.5 | 1169.0 | 1120.2 | 1071.5 | 1050.0 | 1028.5 | 1092.6 | 1156.8 | 1267.0 | 1273.5 |
| 1168.5 | 65°   | 1135.5 | 1102.5 | 1050.2 | 998.0  | 989.8  | 981.5  | 1049.8 | 1118.0 | 1202.0 | 1201.2 |
| 1089.0 | 67.5° | 1057.8 | 1026.5 | 978.2  | 930.0  | 932.6  | 935.2  | 992.0  | 1048.8 | 1096.0 | 1098.2 |
| 1001.0 | 70°   | 974.0  | 947.0  | 904.6  | 862.2  | 871.2  | 880.2  | 920.6  | 961.0  | 976.5  | 976.5  |
| 897.0  | 72.5° | 872.6  | 848.2  | 814.9  | 781.5  | 794.6  | 807.8  | 835.5  | 863.2  | 863.0  | 853.2  |
| 778.0  | 75°   | 755.9  | 733.8  | 709.0  | 684.2  | 696.9  | 709.5  | 730.9  | 752.2  | 756.0  | 710.8  |
| 659.5  | 77.5° | 640.5  | 621.5  | 601.4  | 581.2  | 594.0  | 606.8  | 623.9  | 641.0  | 643.0  | 568.5  |
| 529.5  | 80°   | 513.5  | 497.5  | 480.8  | 464.0  | 474.8  | 485.5  | 499.9  | 514.2  | 514.5  | 425.5  |
| 335.0  | 82.5° | 340.6  | 346.2  | 347.6  | 349.0  | 356.6  | 364.2  | 371.2  | 378.2  | 374.0  | 298.0  |
| 171.5  | 85°   | 187.0  | 202.5  | 209.8  | 217.0  | 225.5  | 234.0  | 241.5  | 249.0  | 243.5  | 187.0  |
| 76.5   | 87.5° | 88.4   | 100.2  | 100.5  | 100.8  | 102.4  | 104.0  | 107.0  | 110.0  | 103.0  | 79.5   |
| 0.0    | 90°   | 0.0    | 0.0    | 0.0    | 0.0    | 0.0    | 0.0    | 0.0    | 0.0    | 0.0    | 0.0    |

REPORT NUMBER: P949250

CATALOG NUMBER: GLAN-SB4A-760-U-SLL

**CANDELA DISTRIBUTION (continued):**

| 325°   |       | 330°   | 335°   | 340°   | 345°   | 350°   | 355°   | 360°    |
|--------|-------|--------|--------|--------|--------|--------|--------|---------|
| 2606.1 | 0°    | 2606.1 | 2606.1 | 2606.1 | 2606.1 | 2606.1 | 2606.1 | 2606.1  |
| 2645.9 | 2.5°  | 2667.9 | 2690.9 | 2713.9 | 2736.7 | 2759.6 | 2781.1 | 2802.6  |
| 2684.1 | 5°    | 2728.6 | 2776.2 | 2823.9 | 2871.2 | 2918.6 | 2966.1 | 3013.6  |
| 2721.0 | 7.5°  | 2783.1 | 2853.6 | 2924.1 | 2996.5 | 3068.9 | 3147.2 | 3225.6  |
| 2753.9 | 10°   | 2827.3 | 2913.0 | 2998.6 | 3094.2 | 3189.9 | 3289.0 | 3388.1  |
| 2768.0 | 12.5° | 2851.1 | 2952.1 | 3053.1 | 3161.5 | 3269.9 | 3378.7 | 3487.6  |
| 2757.1 | 15°   | 2853.3 | 2969.6 | 3085.9 | 3203.5 | 3321.1 | 3434.6 | 3548.1  |
| 2709.6 | 17.5° | 2825.3 | 2960.3 | 3095.3 | 3223.6 | 3351.9 | 3467.0 | 3582.1  |
| 2627.7 | 20°   | 2771.1 | 2934.7 | 3098.3 | 3239.3 | 3380.3 | 3500.0 | 3619.6  |
| 2531.6 | 22.5° | 2704.3 | 2903.3 | 3102.3 | 3260.5 | 3418.6 | 3540.9 | 3663.1  |
| 2424.3 | 25°   | 2626.6 | 2872.3 | 3118.1 | 3298.9 | 3479.6 | 3599.3 | 3719.1  |
| 2326.2 | 27.5° | 2552.1 | 2851.6 | 3151.1 | 3358.9 | 3566.6 | 3680.9 | 3795.1  |
| 2244.2 | 30°   | 2487.3 | 2841.9 | 3196.3 | 3436.6 | 3676.9 | 3787.2 | 3897.6  |
| 2173.5 | 32.5° | 2424.3 | 2829.9 | 3235.3 | 3517.7 | 3800.1 | 3909.3 | 4018.6  |
| 2104.0 | 35°   | 2350.9 | 2807.3 | 3263.9 | 3610.1 | 3956.3 | 4061.0 | 4165.6  |
| 2022.1 | 37.5° | 2256.3 | 2768.6 | 3280.9 | 3713.6 | 4146.3 | 4279.7 | 4413.1  |
| 1924.5 | 40°   | 2139.1 | 2715.3 | 3291.6 | 3845.0 | 4398.3 | 4592.7 | 4787.1  |
| 1816.8 | 42.5° | 2008.8 | 2660.3 | 3311.9 | 4016.9 | 4721.9 | 5002.5 | 5283.1  |
| 1702.4 | 45°   | 1870.8 | 2609.2 | 3347.6 | 4243.1 | 5138.6 | 5517.1 | 5895.6  |
| 1611.9 | 47.5° | 1761.8 | 2567.0 | 3372.1 | 4484.1 | 5596.1 | 6128.9 | 6661.7  |
| 1551.8 | 50°   | 1685.8 | 2521.0 | 3356.1 | 4707.7 | 6059.3 | 6862.6 | 7665.7  |
| 1512.2 | 52.5° | 1629.0 | 2443.3 | 3257.6 | 4852.9 | 6448.2 | 7633.2 | 8818.2  |
| 1483.5 | 55°   | 1574.8 | 2314.5 | 3054.1 | 4820.9 | 6587.7 | 8316.4 | 10045.2 |
| 1449.5 | 57.5° | 1514.0 | 2132.9 | 2751.6 | 4595.7 | 6440.0 | 8800.6 | 11161.3 |
| 1397.5 | 60°   | 1448.2 | 1897.0 | 2345.9 | 4176.6 | 6007.3 | 8921.6 | 11835.8 |
| 1307.1 | 62.5° | 1340.8 | 1614.8 | 1888.8 | 3609.9 | 5330.9 | 8412.1 | 11493.3 |
| 1217.1 | 65°   | 1233.0 | 1360.9 | 1488.8 | 3031.7 | 4574.6 | 7691.2 | 10807.8 |
| 1089.4 | 67.5° | 1080.5 | 1116.9 | 1153.2 | 2465.3 | 3777.3 | 6833.3 | 9889.2  |
| 935.4  | 70°   | 894.2  | 883.9  | 873.5  | 1941.0 | 3008.6 | 5897.1 | 8785.7  |
| 794.9  | 72.5° | 736.5  | 705.1  | 673.8  | 1483.9 | 2294.1 | 4882.3 | 7470.7  |
| 645.4  | 75°   | 580.0  | 551.6  | 523.2  | 1077.0 | 1630.8 | 3719.0 | 5807.1  |
| 505.0  | 77.5° | 441.5  | 422.1  | 402.8  | 729.8  | 1056.8 | 2603.0 | 4149.1  |
| 371.8  | 80°   | 318.0  | 310.0  | 302.0  | 470.2  | 638.5  | 1677.0 | 2715.6  |
| 258.4  | 82.5° | 218.8  | 217.2  | 215.8  | 289.2  | 362.8  | 970.6  | 1578.5  |
| 158.0  | 85°   | 129.0  | 129.8  | 130.5  | 154.6  | 178.8  | 436.6  | 694.5   |
| 67.6   | 87.5° | 55.8   | 56.5   | 57.2   | 64.1   | 71.0   | 143.0  | 215.0   |
| 0.0    | 90°   | 0.0    | 0.0    | 0.0    | 0.0    | 0.0    | 0.0    | 0.0     |

(END OF REPORT)