

Scaled data based on original data using  
LM-79-08 Approved Method: Electrical and Photometric Measurements of Solid-  
State Lighting Products

Test Report Prepared for  
Cooper Lighting Solutions  
(formerly Eaton)

Brand: STREETWORKS

Report Number: P957164

Luminaire Tested: **GLAN-SB9C-835-U-SL3-HSS**

Issue Date: 1/21/2025

**Test Information**

Test Method: LM-79-08  
Report Number: P957164  
TEST IS SCALED FROM IESNA LM-79-08 TEST DATA (G2-2411-289-13)  
Test Lab: INNOVATION CENTER  
Issue Date: 1/21/2025  
Manufacturer: COOPER LIGHTING SOLUTIONS (FORMERLY EATON)  
Product Line: STREETWORKS  
Catalog Number: GLAN-SB9C-835-U-SL3-HSS  
Description: GALLEON AREA AND ROADWAY HIGH DENSITY LED LUMINAIRE  
(9) 80 CRI, 3500K, 615mA LIGHTSQUARES WITH 26 LEDS EACH AND TYPE III  
SPILL LIGHT ELIMINATOR OPTICS WITH HOUSE SIDE SHIELD  
Light Source: -  
Ballast/Driver: -

**Summary**

Lumens per Lamp: N/A  
Luminaire Lumens: 50952 lumens  
Efficiency: N/A  
Efficacy: 113.3 lumens/watt  
Luminous Opening: Rectangular (W 1.5' x L: 1.5' x H: 0')  
IES Classification: Type III - Medium  
BUG Rating: B3 - U0 - G5


Input Watts (W): 449.8  
Input Voltage (V): NR  
Input Current (Ain): NR  
Voltage Rise (V): NR  
Power Factor: NR  
Total Harmonic Distortion (THDi): NR  
Frequency (hertz): 60  
Stabilization Time: NR  
Operation Time: NR  
Ambient Temperature (°C): NR  
Test Distance: 24 FT



REPORT NUMBER: P957164  
 CATALOG NUMBER: GLAN-SB9C-835-U-SL3-HSS

### Iso-Footcandle Lines of Horizontal Illumination


✕ Max cd  
 - - - 1/2 Max cd



Based on 25 foot mounting height. Maximum calculated value = 14.9 fc  
 Type III - Medium - N/A

REPORT NUMBER: P957164  
CATALOG NUMBER: GLAN-SB9C-835-U-SL3-HSS

### Luminous Intensity Polar Plot



— Vertical Plane Through 59-Deg Lateral    - - - Horizontal Cone Through 72.5-Deg Vertical

REPORT NUMBER: P957164  
 CATALOG NUMBER: GLAN-SB9C-835-U-SL3-HSS


**FLUX DISTRIBUTION:**

		Downward	Upward	Total
<b>House Side</b>	Lumens	5381.6	0.0	5381.6
	% Fixture	10.6	0.0	10.6
<b>Street Side</b>	Lumens	45570.4	0.0	45570.4
	% Fixture	89.4	0.0	89.4
<b>Total</b>	Lumens	50952.0	0.0	50952.0
	% Fixture	100.0	0.0	100.0

**ZONAL LUMENS:**

Zone	Lumens	% Fixture
0°-10°	681.7	1.3
10°-20°	1810.6	3.6
20°-30°	2869.6	5.6
30°-40°	4605.2	9.0
40°-50°	7355.4	14.4
50°-60°	10649.6	20.9
60°-70°	12638.4	24.8
70°-80°	9382.2	18.4
80°-90°	959.2	1.9
90°-100°	0.0	0.0
100°-110°	0.0	0.0
110°-120°	0.0	0.0
120°-130°	0.0	0.0
130°-140°	0.0	0.0
140°-150°	0.0	0.0
150°-160°	0.0	0.0
160°-170°	0.0	0.0
170°-180°	0.0	0.0
0°-90°	50952.0	100.0
0°-180°	50952.0	100.0

**Coefficient of Utilization**



REPORT NUMBER: P957164


CATALOG NUMBER: GLAN-SB9C-835-U-SL3-HSS

**LUMINAIRE CLASSIFICATION SYSTEM LUMEN TABLE AND BUG RATING:**

Zone	Lumens	% Fixture	Zone Rating/Lumen Limit		
			B	U	G
FL (0°-30°)	3983.3	7.8			
FM (30°-60°)	20115.1	39.5			
FH (60°-80°)	20536.6	40.3			G5
FVH (80°-90°)	935.4	1.8			G5
BL (0°-30°)	1378.6	2.7	B3/2500		
BM (30°-60°)	2495.1	4.9	B2/2500		
BH (60°-80°)	1484.1	2.9	B3/2500		G3/2500
BVH (80°-90°)	23.9	0.0			G1/100
UL (90°-100°)	0.0	0.0		U0/0	
UH (100°-180°)	0.0	0.0		U0/0	

**BUG Rating: B3-U0-G5**

Type III Medium



REPORT NUMBER: P957164  
 CATALOG NUMBER: GLAN-SB9C-835-U-SL3-HSS

**CANDELA DISTRIBUTION (FULL):**

	0°	5°	15°	25°	35°	45°	55°	59°	65°	75°
0°	7534.6	7534.6	7534.6	7534.6	7534.6	7534.6	7534.6	7534.6	7534.6	7534.6
2.5°	8359.6	8313.0	8319.6	8239.8	8183.3	8123.4	8007.0	7990.3	7907.2	7760.8
5°	9088.1	9058.1	9031.5	8941.7	8825.3	8678.9	8482.6	8412.8	8259.8	8007.0
7.5°	9620.3	9583.7	9597.0	9507.2	9414.1	9251.1	8981.6	8851.9	8649.0	8263.1
10°	9723.4	9703.5	9790.0	9823.2	9823.2	9720.1	9457.3	9327.6	9031.5	8539.2
12.5°	9144.6	9148.0	9364.2	9623.6	9963.0	10059.4	9883.1	9743.4	9450.7	8831.9
15°	8469.3	8472.7	8682.2	9014.9	9570.4	10126.0	10265.7	10175.9	9873.1	9148.0
17.5°	8063.5	8046.9	8186.6	8459.4	9041.5	9823.2	10498.5	10558.4	10312.2	9497.2
20°	8007.0	7977.0	8050.2	8186.6	8602.4	9444.0	10525.1	10807.9	10764.6	9893.1
22.5°	8352.9	8306.3	8266.4	8273.1	8449.4	9128.0	10458.6	10947.6	11230.4	10368.8
25°	9038.2	8965.0	8835.3	8668.9	8632.3	9061.5	10412.0	11100.6	11662.8	10977.5
27.5°	9876.5	9773.3	9523.9	9274.4	9061.5	9247.7	10508.5	11343.5	12151.8	11686.1
30°	10797.9	10671.5	10422.0	9949.6	9610.3	9663.6	10738.0	11662.8	12777.2	12487.8
32.5°	12151.8	11859.1	11423.3	10701.4	10252.4	10112.6	11084.0	12068.6	13552.3	13555.6
35°	13312.8	13149.8	12710.7	11812.5	10891.1	10708.1	11539.7	12640.8	14626.7	14969.4
37.5°	14074.5	13851.7	13465.8	12790.5	11882.4	11320.2	12148.5	13342.7	15764.4	16579.4
40°	14926.1	14706.6	14194.3	13558.9	13033.3	12371.4	12916.9	14151.1	17011.9	18232.7
42.5°	15954.0	15667.9	15062.5	14377.3	13828.4	13755.2	13921.5	15159.0	18292.6	20029.0
45°	17161.6	16892.1	16196.9	15332.0	14849.6	14719.9	15185.6	16333.3	19719.7	21998.3
47.5°	18292.6	17979.9	17231.4	16443.0	15907.5	15498.3	16529.5	17720.4	21336.4	24057.5
50°	19253.9	18934.6	18249.3	17407.7	17045.1	16509.6	17850.2	19267.3	22939.7	26149.8
52.5°	19912.6	19629.8	18824.8	18252.7	18006.5	17737.1	19397.0	20907.2	24536.5	28065.9
55°	19762.9	19510.1	18801.5	18761.6	18745.0	19027.7	21246.5	22766.8	26163.1	29878.9
57.5°	19287.2	19001.1	18116.3	18725.0	19313.8	20178.7	23249.1	24965.6	27946.2	31588.7
60°	17886.7	17786.9	17248.1	18655.2	19553.3	21306.4	25537.8	27174.4	29875.6	33092.3
62.5°	14922.8	15009.3	15006.0	18801.5	19985.8	22590.5	27616.8	29409.8	31761.7	34539.3
65°	11173.8	11473.2	11855.7	17484.2	20564.6	24882.4	30101.8	31834.9	33677.8	36222.6
67.5°	7508.0	7747.5	8007.0	14344.0	18841.5	27290.8	34230.0	35158.1	35973.1	38088.8
70°	4297.9	4374.4	4737.0	8958.3	14523.6	26625.5	40952.9	41288.9	39396.1	40387.4
72.5°	2408.4	2381.8	2860.8	4251.3	8116.7	22800.0	43308.1	46584.7	42459.8	40350.8
75°	1610.0	1613.4	1969.3	2681.2	3163.5	15960.7	37320.3	43195.0	40623.6	35780.1
77.5°	1097.8	1134.3	1447.0	2072.4	1463.7	7787.4	24689.5	30258.1	32889.4	27630.1
80°	475.7	479.0	954.7	1487.0	988.0	2478.3	12800.5	16210.2	20627.8	15514.9
82.5°	246.2	279.4	608.8	961.4	622.1	868.2	6047.6	7082.2	8655.6	4554.0
85°	86.5	103.1	375.9	472.4	312.7	309.4	2105.7	2145.6	1832.9	685.3
87.5°	0.0	16.6	146.4	116.4	39.9	36.6	249.5	209.6	166.3	96.5
90°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0

REPORT NUMBER: P957164  
 CATALOG NUMBER: GLAN-SB9C-835-U-SL3-HSS

**CANDELA DISTRIBUTION (continued):**

85°		90°	95°	105°	115°	125°	135°	145°	155°	165°	175°
7534.6	0°	7534.6	7534.6	7534.6	7534.6	7534.6	7534.6	7534.6	7534.6	7534.6	7534.6
7611.1	2.5°	7541.2	7451.4	7305.1	7125.4	6915.9	6802.8	6639.8	6540.0	6450.1	6453.5
7714.2	5°	7551.2	7401.5	7029.0	6633.1	6194.0	5871.3	5512.1	5259.2	5066.3	5019.7
7820.7	7.5°	7581.2	7328.3	6719.6	6060.9	5329.1	4786.9	4291.2	3978.5	3802.2	3755.7
7930.4	10°	7621.1	7248.5	6370.3	5362.4	4454.2	3802.2	3389.7	3190.1	3110.3	3050.4
8070.2	12.5°	7654.3	7165.3	5931.2	4640.5	3675.8	3166.9	2854.2	2687.8	2618.0	2574.7
8233.2	15°	7710.9	7055.6	5455.5	3968.5	3150.2	2734.4	2438.3	2315.3	2295.3	2302.0
8412.8	17.5°	7767.4	6949.1	4923.3	3443.0	2764.3	2355.2	2175.5	2155.6	2182.2	2208.8
8619.0	20°	7830.6	6796.1	4384.4	3047.1	2408.4	2092.4	2045.8	2059.1	2072.4	2119.0
8901.8	22.5°	7923.8	6603.2	3912.0	2711.1	2112.3	1966.0	1942.7	1952.7	1962.7	2009.2
9274.4	25°	8056.9	6396.9	3529.4	2401.8	1926.1	1862.9	1839.6	1839.6	1852.9	1896.1
9706.8	27.5°	8196.6	6104.2	3220.1	2115.7	1816.3	1749.8	1709.8	1709.8	1726.5	1776.4
10249.0	30°	8352.9	5838.1	2977.2	1902.8	1723.1	1636.7	1583.4	1570.1	1590.1	1653.3
11034.1	32.5°	8635.7	5665.1	2804.3	1803.0	1640.0	1533.5	1460.3	1423.8	1443.7	1516.9
12131.8	35°	9064.8	5625.2	2684.5	1753.1	1560.1	1440.4	1337.3	1280.7	1297.3	1373.9
13485.7	37.5°	9567.1	5708.3	2568.1	1686.5	1483.6	1350.6	1214.2	1141.0	1167.6	1237.5
15032.6	40°	10289.0	6054.3	2478.3	1636.7	1407.1	1244.1	1091.1	1017.9	1061.2	1121.0
16642.6	42.5°	11160.5	6669.7	2455.0	1590.1	1314.0	1131.0	978.0	924.8	958.0	1014.6
18269.3	45°	12241.6	7454.8	2561.4	1530.2	1210.9	1021.2	888.2	858.2	868.2	924.8
19806.2	47.5°	13402.6	8259.8	2854.2	1477.0	1121.0	931.4	818.3	791.7	785.1	838.3
21209.9	50°	14576.8	8975.0	3200.1	1437.1	1057.8	858.2	765.1	731.8	715.2	748.5
22597.1	52.5°	15737.8	9543.8	3426.3	1370.5	994.6	785.1	718.5	668.6	638.7	655.3
23977.6	55°	16915.4	10042.8	3439.6	1270.7	934.8	738.5	672.0	615.4	578.8	578.8
25308.2	57.5°	18016.5	10481.9	3243.4	1137.7	851.6	695.2	608.8	562.2	522.3	509.0
26489.1	60°	18991.2	10807.9	2917.4	988.0	778.4	638.7	545.6	509.0	459.1	432.4
27540.3	62.5°	19859.4	10967.6	2471.6	835.0	688.6	572.2	485.7	445.8	379.2	346.0
28608.1	65°	20594.5	10804.6	2005.9	691.9	612.1	499.0	415.8	375.9	302.7	262.8
29809.0	67.5°	21323.0	10059.4	1516.9	582.1	532.2	419.1	342.6	306.0	252.8	219.6
30683.9	70°	21416.2	8492.6	1061.2	489.0	442.4	322.7	276.1	252.8	206.2	176.3
28731.2	72.5°	19064.3	6110.8	645.3	399.2	346.0	229.5	219.6	199.6	153.0	133.1
23475.3	75°	15238.8	3745.7	379.2	299.4	229.5	163.0	163.0	143.0	103.1	86.5
16206.8	77.5°	10531.8	1959.3	222.9	192.9	136.4	96.5	106.4	86.5	49.9	39.9
6420.2	80°	4218.0	745.1	119.8	89.8	63.2	43.2	36.6	20.0	10.0	6.7
1317.3	82.5°	841.6	196.3	39.9	23.3	23.3	10.0	0.0	0.0	0.0	0.0
362.6	85°	216.2	43.2	10.0	6.7	6.7	0.0	0.0	0.0	0.0	0.0
119.8	87.5°	66.5	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
0.0	90°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0

(END O



<u>180°</u>
7534.6
6526.6
5089.6
3802.2
3087.0
2598.0
2311.9
2218.8
2132.3
2022.5
1912.8
1796.3
1669.9
1536.9
1397.1
1257.4
1131.0
1024.6
951.4
871.6
761.8
668.6
585.5
512.3
425.8
342.6
262.8
219.6
173.0
129.7
86.5
39.9
10.0
0.0
0.0
0.0
0.0

F REPORT)