

Scaled data based on original data using  
LM-79-08 Approved Method: Electrical and Photometric Measurements of Solid-  
State Lighting Products

Test Report Prepared for  
Cooper Lighting Solutions  
(formerly Eaton)

Brand: STREETWORKS

Report Number: P948895

Luminaire Tested: **GLAN-SB3D-760-U-SLR**

Issue Date: 1/21/2025

### Test Information

Test Method: LM-79-08  
Report Number: P948895  
TEST IS SCALED FROM IESNA LM-79-08 TEST DATA (G2-2411-289-8)  
Test Lab: INNOVATION CENTER  
Issue Date: 1/21/2025  
Manufacturer: COOPER LIGHTING SOLUTIONS (FORMERLY EATON)  
Product Line: STREETWORKS  
Catalog Number: GLAN-SB3D-760-U-SLR  
Description: GALLEON AREA AND ROADWAY HIGH DENSITY LED LUMINAIRE  
(3) 70 CRI, 5700K, 900mA LIGHTSQUARES WITH 26 LEDS EACH AND SPILL LIGHT  
ELIMINATOR RIGHT OPTICS  
Light Source: -  
Ballast/Driver: -

### Summary

Lumens per Lamp: N/A  
Luminaire Lumens: 32186 lumens  
Efficiency: N/A  
Efficacy: 147.6 lumens/watt  
Luminous Opening: Rectangular (W 1' x L: 1' x H: 0')  
IES Classification: Type IV - Short  
BUG Rating: B3 - U0 - G5

Input Watts (W): 218.1  
Input Voltage (V): NR  
Input Current (Ain): NR  
Voltage Rise (V): NR  
Power Factor: NR  
Total Harmonic Distortion (THDi): NR  
Frequency (hertz): 60  
Stabilization Time: NR  
Operation Time: NR  
Ambient Temperature (°C): NR  
Test Distance: 24 FT




REPORT NUMBER: P948895

CATALOG NUMBER: GLAN-SB3D-760-U-SLR

## Iso-Footcandle Lines of Horizontal Illumination

× Max cd

--- 1/2 Max cd




Based on 25 foot mounting height. Maximum calculated value = 8.7 fc

Type IV - Short - N/A

REPORT NUMBER: P948895  
CATALOG NUMBER: GLAN-SB3D-760-U-SLR

## Luminous Intensity Polar Plot



REPORT NUMBER: P948895

CATALOG NUMBER: GLAN-SB3D-760-U-SLR


**FLUX DISTRIBUTION:**

|                    |           | Downward | Upward | Total   |
|--------------------|-----------|----------|--------|---------|
| <b>House Side</b>  | Lumens    | 8180.1   | 0.0    | 8180.1  |
|                    | % Fixture | 25.4     | 0.0    | 25.4    |
| <b>Street Side</b> | Lumens    | 24005.9  | 0.0    | 24005.9 |
|                    | % Fixture | 74.6     | 0.0    | 74.6    |
| <b>Total</b>       | Lumens    | 32186.0  | 0.0    | 32186.0 |
|                    | % Fixture | 100.0    | 0.0    | 100.0   |

**ZONAL LUMENS:**

| Zone      | Lumens  | % Fixture |
|-----------|---------|-----------|
| 0°-10°    | 439.0   | 1.4       |
| 10°-20°   | 1378.2  | 4.3       |
| 20°-30°   | 2128.9  | 6.6       |
| 30°-40°   | 2697.9  | 8.4       |
| 40°-50°   | 4069.0  | 12.6      |
| 50°-60°   | 6574.2  | 20.4      |
| 60°-70°   | 8195.7  | 25.5      |
| 70°-80°   | 5374.3  | 16.7      |
| 80°-90°   | 1328.7  | 4.1       |
| 90°-100°  | 0.0     | 0.0       |
| 100°-110° | 0.0     | 0.0       |
| 110°-120° | 0.0     | 0.0       |
| 120°-130° | 0.0     | 0.0       |
| 130°-140° | 0.0     | 0.0       |
| 140°-150° | 0.0     | 0.0       |
| 150°-160° | 0.0     | 0.0       |
| 160°-170° | 0.0     | 0.0       |
| 170°-180° | 0.0     | 0.0       |
| 0°-90°    | 32186.0 | 100.0     |
| 0°-180°   | 32186.0 | 100.0     |

**Coefficient of Utilization**



REPORT NUMBER: P948895


CATALOG NUMBER: GLAN-SB3D-760-U-SLR

**LUMINAIRE CLASSIFICATION SYSTEM LUMEN TABLE AND BUG RATING:**

| Zone |             | Lumens  | % Fixture | Zone Rating/Lumen Limit |      |          |
|------|-------------|---------|-----------|-------------------------|------|----------|
|      |             |         |           | B                       | U    | G        |
| FL   | (0°-30°)    | 2164.9  | 6.7       |                         |      |          |
| FM   | (30°-60°)   | 9388.0  | 29.2      |                         |      |          |
| FH   | (60°-80°)   | 11358.6 | 35.3      |                         |      | G4/12000 |
| FVH  | (80°-90°)   | 1094.5  | 3.4       |                         |      | G5       |
| BL   | (0°-30°)    | 1781.3  | 5.5       | B3/2500                 |      |          |
| BM   | (30°-60°)   | 3953.1  | 12.3      | B3/5000                 |      |          |
| BH   | (60°-80°)   | 2211.5  | 6.9       | B3/2500                 |      | G3/2500  |
| BVH  | (80°-90°)   | 234.1   | 0.7       |                         |      | G3/500   |
| UL   | (90°-100°)  | 0.0     | 0.0       |                         | U0/0 |          |
| UH   | (100°-180°) | 0.0     | 0.0       |                         | U0/0 |          |

**BUG Rating: B3-U0-G5**

Type IV Short



REPORT NUMBER: P948895

CATALOG NUMBER: GLAN-SB3D-760-U-SLR

**CANDELA DISTRIBUTION (FULL):**

|       | 0°      | 5°      | 10°     | 15°    | 20°    | 25°    | 30°    | 35°    | 40°    | 45°    |
|-------|---------|---------|---------|--------|--------|--------|--------|--------|--------|--------|
| 0°    | 4425.9  | 4425.9  | 4425.9  | 4425.9 | 4425.9 | 4425.9 | 4425.9 | 4425.9 | 4425.9 | 4425.9 |
| 2.5°  | 4759.6  | 4723.1  | 4686.5  | 4647.7 | 4608.9 | 4569.9 | 4530.8 | 4493.4 | 4456.1 | 4419.9 |
| 5°    | 5117.9  | 5037.3  | 4956.6  | 4876.1 | 4795.7 | 4714.7 | 4633.9 | 4558.3 | 4482.7 | 4411.4 |
| 7.5°  | 5478.0  | 5344.8  | 5211.8  | 5088.9 | 4965.9 | 4846.2 | 4726.5 | 4621.0 | 4515.5 | 4418.2 |
| 10°   | 5753.9  | 5585.6  | 5417.3  | 5254.8 | 5092.4 | 4947.1 | 4801.5 | 4676.9 | 4551.9 | 4431.8 |
| 12.5° | 5922.9  | 5738.0  | 5553.2  | 5369.1 | 5185.0 | 5013.5 | 4841.9 | 4700.8 | 4559.7 | 4433.5 |
| 15°   | 6025.7  | 5832.9  | 5640.2  | 5440.4 | 5240.7 | 5043.2 | 4845.7 | 4682.3 | 4518.9 | 4379.1 |
| 17.5° | 6083.4  | 5887.9  | 5692.5  | 5474.6 | 5256.7 | 5027.4 | 4798.1 | 4601.6 | 4405.1 | 4240.7 |
| 20°   | 6147.1  | 5944.0  | 5740.7  | 5501.2 | 5261.8 | 4983.9 | 4706.1 | 4462.5 | 4219.0 | 4027.6 |
| 22.5° | 6221.0  | 6013.5  | 5805.7  | 5537.2 | 5268.6 | 4930.6 | 4592.6 | 4299.3 | 4006.0 | 3788.1 |
| 25°   | 6316.1  | 6112.6  | 5909.3  | 5602.5 | 5295.4 | 4877.9 | 4460.7 | 4117.1 | 3773.7 | 3550.4 |
| 27.5° | 6445.2  | 6251.2  | 6057.1  | 5704.4 | 5351.4 | 4842.8 | 4334.1 | 3950.5 | 3566.8 | 3363.5 |
| 30°   | 6619.2  | 6431.8  | 6244.4  | 5836.3 | 5428.2 | 4826.3 | 4224.1 | 3811.2 | 3398.4 | 3227.7 |
| 32.5° | 6824.7  | 6639.1  | 6453.7  | 5974.1 | 5494.4 | 4805.9 | 4117.1 | 3691.2 | 3265.0 | 3127.5 |
| 35°   | 7074.4  | 6896.8  | 6718.9  | 6131.0 | 5543.0 | 4767.6 | 3992.4 | 3573.1 | 3153.8 | 3039.2 |
| 37.5° | 7494.7  | 7268.2  | 7041.6  | 6306.8 | 5571.9 | 4701.8 | 3831.8 | 3434.2 | 3036.6 | 2936.4 |
| 40°   | 8129.9  | 7799.8  | 7469.6  | 6529.9 | 5590.1 | 4611.3 | 3632.7 | 3268.4 | 2904.1 | 2813.3 |
| 42.5° | 8972.3  | 8495.7  | 8019.2  | 6821.9 | 5624.5 | 4517.9 | 3411.6 | 3085.5 | 2759.4 | 2675.7 |
| 45°   | 10012.5 | 9369.7  | 8726.9  | 7206.0 | 5685.2 | 4431.1 | 3177.2 | 2891.2 | 2605.2 | 2520.3 |
| 47.5° | 11313.4 | 10408.7 | 9503.9  | 7615.3 | 5726.8 | 4359.4 | 2992.1 | 2737.5 | 2483.0 | 2373.4 |
| 50°   | 13018.6 | 11654.6 | 10290.5 | 7995.1 | 5699.6 | 4281.3 | 2863.0 | 2635.5 | 2407.9 | 2263.9 |
| 52.5° | 14975.9 | 12963.4 | 10950.8 | 8241.7 | 5532.3 | 4149.4 | 2766.6 | 2568.2 | 2370.0 | 2204.4 |
| 55°   | 17059.7 | 14123.7 | 11187.8 | 8187.3 | 5186.7 | 3930.6 | 2674.5 | 2519.5 | 2364.4 | 2210.4 |
| 57.5° | 18955.1 | 14946.0 | 10936.9 | 7804.9 | 4673.0 | 3622.2 | 2571.3 | 2461.7 | 2352.2 | 2216.3 |
| 60°   | 20100.6 | 15151.5 | 10202.2 | 7093.1 | 3983.9 | 3221.7 | 2459.5 | 2373.4 | 2287.3 | 2197.6 |
| 62.5° | 19518.9 | 14286.2 | 9053.5  | 6130.6 | 3207.8 | 2742.5 | 2277.1 | 2219.9 | 2162.8 | 2151.8 |
| 65°   | 18354.7 | 13061.9 | 7769.0  | 5148.7 | 2528.5 | 2311.3 | 2094.0 | 2067.0 | 2040.0 | 2041.4 |
| 67.5° | 16794.8 | 11604.9 | 6414.9  | 4186.7 | 1958.5 | 1896.9 | 1835.0 | 1850.2 | 1865.1 | 1861.4 |
| 70°   | 14920.7 | 10015.1 | 5109.4  | 3296.5 | 1483.5 | 1501.2 | 1518.6 | 1588.6 | 1658.4 | 1658.4 |
| 72.5° | 12687.4 | 8291.6  | 3896.0  | 2520.2 | 1144.3 | 1197.5 | 1250.8 | 1350.0 | 1449.0 | 1465.7 |
| 75°   | 9862.2  | 6315.9  | 2769.6  | 1829.1 | 888.6  | 936.8  | 985.0  | 1096.1 | 1207.2 | 1283.9 |
| 77.5° | 7046.4  | 4420.6  | 1794.8  | 1239.4 | 684.1  | 716.9  | 749.8  | 857.7  | 965.5  | 1092.0 |
| 80°   | 4611.8  | 2848.1  | 1084.4  | 798.6  | 512.9  | 526.5  | 540.1  | 631.4  | 722.6  | 873.8  |
| 82.5° | 2680.8  | 1648.4  | 616.2   | 491.2  | 366.5  | 368.9  | 371.6  | 438.8  | 506.1  | 635.2  |
| 85°   | 1179.5  | 741.5   | 303.7   | 262.6  | 221.6  | 220.4  | 219.1  | 268.3  | 317.6  | 413.5  |
| 87.5° | 365.1   | 242.9   | 120.6   | 108.9  | 97.1   | 96.0   | 94.8   | 114.8  | 135.0  | 174.9  |
| 90°   | 0.0     | 0.0     | 0.0     | 0.0    | 0.0    | 0.0    | 0.0    | 0.0    | 0.0    | 0.0    |

REPORT NUMBER: P948895

CATALOG NUMBER: GLAN-SB3D-760-U-SLR

**CANDELA DISTRIBUTION (continued):**

| 50°    |       | 55°    | 60°    | 65°    | 70°    | 75°    | 80°    | 85°    | 90°    | 95°    | 100°   |
|--------|-------|--------|--------|--------|--------|--------|--------|--------|--------|--------|--------|
| 4425.9 | 0°    | 4425.9 | 4425.9 | 4425.9 | 4425.9 | 4425.9 | 4425.9 | 4425.9 | 4425.9 | 4425.9 | 4425.9 |
| 4379.7 | 2.5°  | 4347.0 | 4314.6 | 4285.2 | 4256.0 | 4230.4 | 4204.7 | 4178.9 | 4153.3 | 4133.4 | 4113.4 |
| 4340.9 | 5°    | 4279.5 | 4217.8 | 4166.2 | 4114.7 | 4069.2 | 4023.7 | 3982.4 | 3941.0 | 3909.2 | 3877.3 |
| 4327.0 | 7.5°  | 4245.1 | 4163.5 | 4095.5 | 4027.6 | 3970.4 | 3913.0 | 3862.3 | 3811.9 | 3774.0 | 3736.3 |
| 4333.8 | 10°   | 4247.5 | 4161.3 | 4093.3 | 4025.4 | 3963.7 | 3901.9 | 3845.0 | 3788.1 | 3743.0 | 3697.6 |
| 4342.3 | 12.5° | 4271.6 | 4201.3 | 4156.2 | 4111.3 | 4062.7 | 4014.5 | 3955.6 | 3896.8 | 3839.1 | 3781.3 |
| 4306.1 | 15°   | 4272.3 | 4238.7 | 4244.8 | 4250.9 | 4238.4 | 4225.8 | 4174.7 | 4123.5 | 4041.3 | 3959.2 |
| 4195.7 | 17.5° | 4208.1 | 4220.4 | 4294.4 | 4368.4 | 4407.8 | 4447.1 | 4405.8 | 4364.7 | 4255.8 | 4147.0 |
| 4015.7 | 20°   | 4073.4 | 4131.2 | 4259.8 | 4388.5 | 4470.9 | 4553.2 | 4534.2 | 4515.0 | 4390.5 | 4266.2 |
| 3811.4 | 22.5° | 3896.8 | 3982.2 | 4129.0 | 4276.1 | 4383.2 | 4490.4 | 4501.9 | 4513.3 | 4394.4 | 4275.5 |
| 3613.2 | 25°   | 3711.7 | 3810.2 | 3942.2 | 4074.3 | 4179.8 | 4285.2 | 4324.6 | 4363.9 | 4266.4 | 4169.1 |
| 3440.0 | 27.5° | 3535.1 | 3630.2 | 3738.7 | 3847.1 | 3931.6 | 4016.2 | 4060.0 | 4104.0 | 4034.6 | 3965.3 |
| 3287.6 | 30°   | 3363.0 | 3438.8 | 3528.8 | 3618.8 | 3688.9 | 3759.3 | 3794.9 | 3830.6 | 3777.8 | 3724.8 |
| 3154.1 | 32.5° | 3198.8 | 3243.5 | 3315.3 | 3387.3 | 3454.6 | 3522.0 | 3561.6 | 3601.3 | 3552.7 | 3504.0 |
| 3028.1 | 35°   | 3040.4 | 3052.8 | 3107.6 | 3162.3 | 3228.9 | 3295.6 | 3343.2 | 3390.7 | 3356.1 | 3321.6 |
| 2896.0 | 37.5° | 2882.4 | 2868.8 | 2908.2 | 2947.5 | 3013.9 | 3080.4 | 3139.2 | 3198.0 | 3182.0 | 3166.0 |
| 2751.3 | 40°   | 2720.6 | 2689.8 | 2718.2 | 2746.5 | 2810.7 | 2874.9 | 2942.5 | 3010.3 | 3014.2 | 3017.9 |
| 2597.6 | 42.5° | 2556.8 | 2516.1 | 2539.2 | 2562.4 | 2623.2 | 2684.2 | 2757.2 | 2830.3 | 2849.8 | 2869.3 |
| 2444.7 | 45°   | 2405.0 | 2365.4 | 2384.8 | 2404.5 | 2462.2 | 2520.0 | 2595.7 | 2671.5 | 2699.5 | 2727.5 |
| 2308.4 | 47.5° | 2275.1 | 2241.8 | 2260.1 | 2278.3 | 2334.9 | 2391.3 | 2466.0 | 2540.7 | 2573.0 | 2605.2 |
| 2188.3 | 50°   | 2158.7 | 2129.4 | 2157.9 | 2186.6 | 2239.9 | 2293.1 | 2360.0 | 2426.9 | 2468.4 | 2509.8 |
| 2098.8 | 52.5° | 2069.6 | 2040.5 | 2083.5 | 2126.3 | 2175.2 | 2224.0 | 2286.3 | 2348.8 | 2397.9 | 2447.0 |
| 2051.2 | 55°   | 2005.1 | 1959.0 | 2020.0 | 2080.8 | 2133.4 | 2186.1 | 2240.8 | 2295.3 | 2347.3 | 2399.4 |
| 2022.7 | 57.5° | 1955.5 | 1888.2 | 1953.8 | 2019.3 | 2081.1 | 2143.0 | 2197.0 | 2251.1 | 2303.6 | 2355.9 |
| 1995.9 | 60°   | 1908.8 | 1821.5 | 1879.0 | 1936.4 | 2007.4 | 2078.4 | 2133.3 | 2188.3 | 2240.9 | 2293.6 |
| 1964.6 | 62.5° | 1855.6 | 1746.7 | 1783.2 | 1819.8 | 1902.5 | 1985.3 | 2043.9 | 2102.5 | 2150.8 | 2199.0 |
| 1898.7 | 65°   | 1782.9 | 1666.9 | 1681.0 | 1694.9 | 1783.6 | 1872.4 | 1928.5 | 1984.5 | 2027.0 | 2069.4 |
| 1781.2 | 67.5° | 1684.7 | 1588.3 | 1583.9 | 1579.4 | 1661.3 | 1743.3 | 1796.5 | 1849.5 | 1886.2 | 1922.9 |
| 1632.1 | 70°   | 1563.5 | 1494.9 | 1479.6 | 1464.3 | 1536.3 | 1608.3 | 1654.2 | 1700.0 | 1733.1 | 1766.3 |
| 1466.0 | 72.5° | 1419.0 | 1371.9 | 1349.5 | 1327.2 | 1384.0 | 1440.5 | 1482.0 | 1523.4 | 1555.8 | 1588.3 |
| 1277.5 | 75°   | 1241.3 | 1205.0 | 1183.6 | 1162.0 | 1204.1 | 1246.2 | 1283.8 | 1321.3 | 1350.9 | 1380.4 |
| 1088.6 | 77.5° | 1059.6 | 1030.5 | 1008.8 | 987.1  | 1021.4 | 1055.5 | 1087.8 | 1120.0 | 1151.1 | 1182.0 |
| 873.3  | 80°   | 849.0  | 824.5  | 806.4  | 788.0  | 816.6  | 844.9  | 872.1  | 899.3  | 922.9  | 946.3  |
| 642.3  | 82.5° | 630.4  | 618.5  | 605.6  | 592.7  | 590.3  | 588.0  | 578.5  | 568.9  | 619.2  | 669.5  |
| 422.9  | 85°   | 410.1  | 397.4  | 383.0  | 368.5  | 356.3  | 343.9  | 317.6  | 291.3  | 338.3  | 385.5  |
| 186.8  | 87.5° | 181.7  | 176.6  | 173.9  | 171.2  | 170.7  | 170.2  | 150.1  | 129.9  | 149.6  | 169.5  |
| 0.0    | 90°   | 0.0    | 0.0    | 0.0    | 0.0    | 0.0    | 0.0    | 0.0    | 0.0    | 0.0    | 0.0    |



REPORT NUMBER: P948895

CATALOG NUMBER: GLAN-SB3D-760-U-SLR

**CANDELA DISTRIBUTION (continued):**

| 105°   |       | 110°   | 115°   | 120°   | 125°   | 130°   | 135°   | 140°   | 145°   | 150°   | 155°   |
|--------|-------|--------|--------|--------|--------|--------|--------|--------|--------|--------|--------|
| 4425.9 | 0°    | 4425.9 | 4425.9 | 4425.9 | 4425.9 | 4425.9 | 4425.9 | 4425.9 | 4425.9 | 4425.9 | 4425.9 |
| 4097.2 | 2.5°  | 4081.1 | 4068.5 | 4056.0 | 4044.4 | 4032.7 | 4018.3 | 4032.7 | 4044.4 | 4056.0 | 4068.5 |
| 3855.0 | 5°    | 3832.8 | 3817.0 | 3801.2 | 3789.1 | 3777.1 | 3765.2 | 3777.1 | 3789.1 | 3801.2 | 3817.0 |
| 3709.8 | 7.5°  | 3683.3 | 3665.2 | 3647.2 | 3636.3 | 3625.6 | 3617.4 | 3625.6 | 3636.3 | 3647.2 | 3665.2 |
| 3668.1 | 10°   | 3638.2 | 3621.0 | 3603.9 | 3594.7 | 3585.5 | 3581.8 | 3585.5 | 3594.7 | 3603.9 | 3621.0 |
| 3743.1 | 12.5° | 3704.9 | 3685.7 | 3666.7 | 3658.9 | 3651.1 | 3649.7 | 3651.1 | 3658.9 | 3666.7 | 3685.7 |
| 3901.1 | 15°   | 3843.0 | 3816.3 | 3789.8 | 3779.6 | 3769.4 | 3768.6 | 3769.4 | 3779.6 | 3789.8 | 3816.3 |
| 4061.4 | 17.5° | 3975.8 | 3936.4 | 3896.8 | 3883.9 | 3870.8 | 3868.8 | 3870.8 | 3883.9 | 3896.8 | 3936.4 |
| 4161.3 | 20°   | 4056.5 | 4006.0 | 3955.4 | 3939.3 | 3923.1 | 3918.1 | 3923.1 | 3939.3 | 3955.4 | 4006.0 |
| 4167.5 | 22.5° | 4059.4 | 4006.2 | 3952.9 | 3935.0 | 3917.2 | 3909.6 | 3917.2 | 3935.0 | 3952.9 | 4006.2 |
| 4072.9 | 25°   | 3977.2 | 3931.0 | 3884.9 | 3868.1 | 3851.5 | 3841.6 | 3851.5 | 3868.1 | 3884.9 | 3931.0 |
| 3890.7 | 27.5° | 3816.2 | 3785.2 | 3754.2 | 3746.5 | 3738.9 | 3736.3 | 3738.9 | 3746.5 | 3754.2 | 3785.2 |
| 3671.5 | 30°   | 3617.8 | 3602.0 | 3586.0 | 3586.0 | 3586.0 | 3588.6 | 3586.0 | 3586.0 | 3586.0 | 3602.0 |
| 3461.4 | 32.5° | 3418.7 | 3408.4 | 3398.0 | 3399.4 | 3400.9 | 3403.5 | 3400.9 | 3399.4 | 3398.0 | 3408.4 |
| 3282.2 | 35°   | 3243.0 | 3227.2 | 3211.5 | 3208.1 | 3204.8 | 3203.1 | 3204.8 | 3208.1 | 3211.5 | 3227.2 |
| 3129.9 | 37.5° | 3093.5 | 3064.8 | 3036.3 | 3021.2 | 3006.0 | 2997.6 | 3006.0 | 3021.2 | 3036.3 | 3064.8 |
| 2987.2 | 40°   | 2956.5 | 2914.7 | 2873.2 | 2845.0 | 2817.2 | 2800.5 | 2817.2 | 2845.0 | 2873.2 | 2914.7 |
| 2843.3 | 42.5° | 2817.5 | 2765.7 | 2713.9 | 2673.0 | 2632.1 | 2605.2 | 2632.1 | 2673.0 | 2713.9 | 2765.7 |
| 2704.1 | 45°   | 2680.8 | 2621.5 | 2562.4 | 2514.4 | 2466.3 | 2435.4 | 2466.3 | 2514.4 | 2562.4 | 2621.5 |
| 2588.9 | 47.5° | 2572.6 | 2520.0 | 2467.3 | 2422.8 | 2378.5 | 2348.8 | 2378.5 | 2422.8 | 2467.3 | 2520.0 |
| 2508.8 | 50°   | 2508.1 | 2466.0 | 2423.9 | 2382.8 | 2341.7 | 2313.1 | 2341.7 | 2382.8 | 2423.9 | 2466.0 |
| 2455.8 | 52.5° | 2464.6 | 2430.3 | 2396.0 | 2359.2 | 2322.5 | 2296.1 | 2322.5 | 2359.2 | 2396.0 | 2430.3 |
| 2411.6 | 55°   | 2423.9 | 2394.0 | 2364.1 | 2331.8 | 2299.5 | 2275.8 | 2299.5 | 2331.8 | 2364.1 | 2394.0 |
| 2368.3 | 57.5° | 2380.7 | 2350.5 | 2320.3 | 2288.3 | 2256.2 | 2231.6 | 2256.2 | 2288.3 | 2320.3 | 2350.5 |
| 2307.2 | 60°   | 2320.8 | 2291.2 | 2261.8 | 2228.9 | 2195.9 | 2170.5 | 2195.9 | 2228.9 | 2261.8 | 2291.2 |
| 2212.1 | 62.5° | 2225.2 | 2198.5 | 2171.8 | 2137.2 | 2102.5 | 2072.0 | 2102.5 | 2137.2 | 2171.8 | 2198.5 |
| 2082.8 | 65°   | 2096.1 | 2070.4 | 2044.8 | 2011.2 | 1977.7 | 1951.4 | 1977.7 | 2011.2 | 2044.8 | 2070.4 |
| 1935.9 | 67.5° | 1948.8 | 1925.2 | 1901.8 | 1870.5 | 1839.3 | 1815.5 | 1839.3 | 1870.5 | 1901.8 | 1925.2 |
| 1778.8 | 70°   | 1791.4 | 1772.2 | 1753.0 | 1723.1 | 1693.2 | 1666.1 | 1693.2 | 1723.1 | 1753.0 | 1772.2 |
| 1603.2 | 72.5° | 1618.2 | 1602.2 | 1586.2 | 1557.7 | 1529.3 | 1503.0 | 1529.3 | 1557.7 | 1586.2 | 1602.2 |
| 1396.0 | 75°   | 1411.7 | 1403.8 | 1396.0 | 1372.1 | 1348.1 | 1323.0 | 1348.1 | 1372.1 | 1396.0 | 1403.8 |
| 1196.6 | 77.5° | 1211.3 | 1200.4 | 1189.2 | 1165.1 | 1140.9 | 1120.9 | 1140.9 | 1165.1 | 1189.2 | 1200.4 |
| 965.7  | 80°   | 985.0  | 980.3  | 975.7  | 943.3  | 910.6  | 872.9  | 910.6  | 943.3  | 975.7  | 980.3  |
| 702.4  | 82.5° | 735.4  | 733.3  | 731.1  | 703.8  | 676.3  | 652.2  | 676.3  | 703.8  | 731.1  | 733.3  |
| 426.3  | 85°   | 467.0  | 463.6  | 460.2  | 438.8  | 417.4  | 395.7  | 417.4  | 438.8  | 460.2  | 463.6  |
| 186.0  | 87.5° | 202.4  | 198.4  | 193.9  | 183.1  | 171.9  | 161.3  | 171.9  | 183.1  | 193.9  | 198.4  |
| 0.0    | 90°   | 0.0    | 0.0    | 0.0    | 0.0    | 0.0    | 0.0    | 0.0    | 0.0    | 0.0    | 0.0    |

REPORT NUMBER: P948895

CATALOG NUMBER: GLAN-SB3D-760-U-SLR

**CANDELA DISTRIBUTION (continued):**

| 160°   |       | 165°   | 170°   | 175°   | 180°   | 185°   | 190°   | 195°   | 200°   | 205°   | 210°   |
|--------|-------|--------|--------|--------|--------|--------|--------|--------|--------|--------|--------|
| 4425.9 | 0°    | 4425.9 | 4425.9 | 4425.9 | 4425.9 | 4425.9 | 4425.9 | 4425.9 | 4425.9 | 4425.9 | 4425.9 |
| 4081.1 | 2.5°  | 4097.2 | 4113.4 | 4133.4 | 4153.3 | 4178.9 | 4204.7 | 4230.4 | 4256.0 | 4285.2 | 4314.6 |
| 3832.8 | 5°    | 3855.0 | 3877.3 | 3909.2 | 3941.0 | 3982.4 | 4023.7 | 4069.2 | 4114.7 | 4166.2 | 4217.8 |
| 3683.3 | 7.5°  | 3709.8 | 3736.3 | 3774.0 | 3811.9 | 3862.3 | 3913.0 | 3970.4 | 4027.6 | 4095.5 | 4163.5 |
| 3638.2 | 10°   | 3668.1 | 3697.6 | 3743.0 | 3788.1 | 3845.0 | 3901.9 | 3963.7 | 4025.4 | 4093.3 | 4161.3 |
| 3704.9 | 12.5° | 3743.1 | 3781.3 | 3839.1 | 3896.8 | 3955.6 | 4014.5 | 4062.7 | 4111.3 | 4156.2 | 4201.3 |
| 3843.0 | 15°   | 3901.1 | 3959.2 | 4041.3 | 4123.5 | 4174.7 | 4225.8 | 4238.4 | 4250.9 | 4244.8 | 4238.7 |
| 3975.8 | 17.5° | 4061.4 | 4147.0 | 4255.8 | 4364.7 | 4405.8 | 4447.1 | 4407.8 | 4368.4 | 4294.4 | 4220.4 |
| 4056.5 | 20°   | 4161.3 | 4266.2 | 4390.5 | 4515.0 | 4534.2 | 4553.2 | 4470.9 | 4388.5 | 4259.8 | 4131.2 |
| 4059.4 | 22.5° | 4167.5 | 4275.5 | 4394.4 | 4513.3 | 4501.9 | 4490.4 | 4383.2 | 4276.1 | 4129.0 | 3982.2 |
| 3977.2 | 25°   | 4072.9 | 4169.1 | 4266.4 | 4363.9 | 4324.6 | 4285.2 | 4179.8 | 4074.3 | 3942.2 | 3810.2 |
| 3816.2 | 27.5° | 3890.7 | 3965.3 | 4034.6 | 4104.0 | 4060.0 | 4016.2 | 3931.6 | 3847.1 | 3738.7 | 3630.2 |
| 3617.8 | 30°   | 3671.5 | 3724.8 | 3777.8 | 3830.6 | 3794.9 | 3759.3 | 3688.9 | 3618.8 | 3528.8 | 3438.8 |
| 3418.7 | 32.5° | 3461.4 | 3504.0 | 3552.7 | 3601.3 | 3561.6 | 3522.0 | 3454.6 | 3387.3 | 3315.3 | 3243.5 |
| 3243.0 | 35°   | 3282.2 | 3321.6 | 3356.1 | 3390.7 | 3343.2 | 3295.6 | 3228.9 | 3162.3 | 3107.6 | 3052.8 |
| 3093.5 | 37.5° | 3129.9 | 3166.0 | 3182.0 | 3198.0 | 3139.2 | 3080.4 | 3013.9 | 2947.5 | 2908.2 | 2868.8 |
| 2956.5 | 40°   | 2987.2 | 3017.9 | 3014.2 | 3010.3 | 2942.5 | 2874.9 | 2810.7 | 2746.5 | 2718.2 | 2689.8 |
| 2817.5 | 42.5° | 2843.3 | 2869.3 | 2849.8 | 2830.3 | 2757.2 | 2684.2 | 2623.2 | 2562.4 | 2539.2 | 2516.1 |
| 2680.8 | 45°   | 2704.1 | 2727.5 | 2699.5 | 2671.5 | 2595.7 | 2520.0 | 2462.2 | 2404.5 | 2384.8 | 2365.4 |
| 2572.6 | 47.5° | 2588.9 | 2605.2 | 2573.0 | 2540.7 | 2466.0 | 2391.3 | 2334.9 | 2278.3 | 2260.1 | 2241.8 |
| 2508.1 | 50°   | 2508.8 | 2509.8 | 2468.4 | 2426.9 | 2360.0 | 2293.1 | 2239.9 | 2186.6 | 2157.9 | 2129.4 |
| 2464.6 | 52.5° | 2455.8 | 2447.0 | 2397.9 | 2348.8 | 2286.3 | 2224.0 | 2175.2 | 2126.3 | 2083.5 | 2040.5 |
| 2423.9 | 55°   | 2411.6 | 2399.4 | 2347.3 | 2295.3 | 2240.8 | 2186.1 | 2133.4 | 2080.8 | 2020.0 | 1959.0 |
| 2380.7 | 57.5° | 2368.3 | 2355.9 | 2303.6 | 2251.1 | 2197.0 | 2143.0 | 2081.1 | 2019.3 | 1953.8 | 1888.2 |
| 2320.8 | 60°   | 2307.2 | 2293.6 | 2240.9 | 2188.3 | 2133.3 | 2078.4 | 2007.4 | 1936.4 | 1879.0 | 1821.5 |
| 2225.2 | 62.5° | 2212.1 | 2199.0 | 2150.8 | 2102.5 | 2043.9 | 1985.3 | 1902.5 | 1819.8 | 1783.2 | 1746.7 |
| 2096.1 | 65°   | 2082.8 | 2069.4 | 2027.0 | 1984.5 | 1928.5 | 1872.4 | 1783.6 | 1694.9 | 1681.0 | 1666.9 |
| 1948.8 | 67.5° | 1935.9 | 1922.9 | 1886.2 | 1849.5 | 1796.5 | 1743.3 | 1661.3 | 1579.4 | 1583.9 | 1588.3 |
| 1791.4 | 70°   | 1778.8 | 1766.3 | 1733.1 | 1700.0 | 1654.2 | 1608.3 | 1536.3 | 1464.3 | 1479.6 | 1494.9 |
| 1618.2 | 72.5° | 1603.2 | 1588.3 | 1555.8 | 1523.4 | 1482.0 | 1440.5 | 1384.0 | 1327.2 | 1349.5 | 1371.9 |
| 1411.7 | 75°   | 1396.0 | 1380.4 | 1350.9 | 1321.3 | 1283.8 | 1246.2 | 1204.1 | 1162.0 | 1183.6 | 1205.0 |
| 1211.3 | 77.5° | 1196.6 | 1182.0 | 1151.1 | 1120.0 | 1087.8 | 1055.5 | 1021.4 | 987.1  | 1008.8 | 1030.5 |
| 985.0  | 80°   | 965.7  | 946.3  | 922.9  | 899.3  | 872.1  | 844.9  | 816.6  | 788.0  | 806.4  | 824.5  |
| 735.4  | 82.5° | 702.4  | 669.5  | 619.2  | 568.9  | 578.5  | 588.0  | 590.3  | 592.7  | 605.6  | 618.5  |
| 467.0  | 85°   | 426.3  | 385.5  | 338.3  | 291.3  | 317.6  | 343.9  | 356.3  | 368.5  | 383.0  | 397.4  |
| 202.4  | 87.5° | 186.0  | 169.5  | 149.6  | 129.9  | 150.1  | 170.2  | 170.7  | 171.2  | 173.9  | 176.6  |
| 0.0    | 90°   | 0.0    | 0.0    | 0.0    | 0.0    | 0.0    | 0.0    | 0.0    | 0.0    | 0.0    | 0.0    |

REPORT NUMBER: P948895

CATALOG NUMBER: GLAN-SB3D-760-U-SLR

**CANDELA DISTRIBUTION (continued):**

| 215°   |       | 220°   | 225°   | 230°   | 235°   | 240°   | 245°   | 250°   | 255°   | 260°    | 265°    |
|--------|-------|--------|--------|--------|--------|--------|--------|--------|--------|---------|---------|
| 4425.9 | 0°    | 4425.9 | 4425.9 | 4425.9 | 4425.9 | 4425.9 | 4425.9 | 4425.9 | 4425.9 | 4425.9  | 4425.9  |
| 4347.0 | 2.5°  | 4379.7 | 4419.9 | 4456.1 | 4493.4 | 4530.8 | 4569.9 | 4608.9 | 4647.7 | 4686.5  | 4723.1  |
| 4279.5 | 5°    | 4340.9 | 4411.4 | 4482.7 | 4558.3 | 4633.9 | 4714.7 | 4795.7 | 4876.1 | 4956.6  | 5037.3  |
| 4245.1 | 7.5°  | 4327.0 | 4418.2 | 4515.5 | 4621.0 | 4726.5 | 4846.2 | 4965.9 | 5088.9 | 5211.8  | 5344.8  |
| 4247.5 | 10°   | 4333.8 | 4431.8 | 4551.9 | 4676.9 | 4801.5 | 4947.1 | 5092.4 | 5254.8 | 5417.3  | 5585.6  |
| 4271.6 | 12.5° | 4342.3 | 4433.5 | 4559.7 | 4700.8 | 4841.9 | 5013.5 | 5185.0 | 5369.1 | 5553.2  | 5738.0  |
| 4272.3 | 15°   | 4306.1 | 4379.1 | 4518.9 | 4682.3 | 4845.7 | 5043.2 | 5240.7 | 5440.4 | 5640.2  | 5832.9  |
| 4208.1 | 17.5° | 4195.7 | 4240.7 | 4405.1 | 4601.6 | 4798.1 | 5027.4 | 5256.7 | 5474.6 | 5692.5  | 5887.9  |
| 4073.4 | 20°   | 4015.7 | 4027.6 | 4219.0 | 4462.5 | 4706.1 | 4983.9 | 5261.8 | 5501.2 | 5740.7  | 5944.0  |
| 3896.8 | 22.5° | 3811.4 | 3788.1 | 4006.0 | 4299.3 | 4592.6 | 4930.6 | 5268.6 | 5537.2 | 5805.7  | 6013.5  |
| 3711.7 | 25°   | 3613.2 | 3550.4 | 3773.7 | 4117.1 | 4460.7 | 4877.9 | 5295.4 | 5602.5 | 5909.3  | 6112.6  |
| 3535.1 | 27.5° | 3440.0 | 3363.5 | 3566.8 | 3950.5 | 4334.1 | 4842.8 | 5351.4 | 5704.4 | 6057.1  | 6251.2  |
| 3363.0 | 30°   | 3287.6 | 3227.7 | 3398.4 | 3811.2 | 4224.1 | 4826.3 | 5428.2 | 5836.3 | 6244.4  | 6431.8  |
| 3198.8 | 32.5° | 3154.1 | 3127.5 | 3265.0 | 3691.2 | 4117.1 | 4805.9 | 5494.4 | 5974.1 | 6453.7  | 6639.1  |
| 3040.4 | 35°   | 3028.1 | 3039.2 | 3153.8 | 3573.1 | 3992.4 | 4767.6 | 5543.0 | 6131.0 | 6718.9  | 6896.8  |
| 2882.4 | 37.5° | 2896.0 | 2936.4 | 3036.6 | 3434.2 | 3831.8 | 4701.8 | 5571.9 | 6306.8 | 7041.6  | 7268.2  |
| 2720.6 | 40°   | 2751.3 | 2813.3 | 2904.1 | 3268.4 | 3632.7 | 4611.3 | 5590.1 | 6529.9 | 7469.6  | 7799.8  |
| 2556.8 | 42.5° | 2597.6 | 2675.7 | 2759.4 | 3085.5 | 3411.6 | 4517.9 | 5624.5 | 6821.9 | 8019.2  | 8495.7  |
| 2405.0 | 45°   | 2444.7 | 2520.3 | 2605.2 | 2891.2 | 3177.2 | 4431.1 | 5685.2 | 7206.0 | 8726.9  | 9369.7  |
| 2275.1 | 47.5° | 2308.4 | 2373.4 | 2483.0 | 2737.5 | 2992.1 | 4359.4 | 5726.8 | 7615.3 | 9503.9  | 10408.7 |
| 2158.7 | 50°   | 2188.3 | 2263.9 | 2407.9 | 2635.5 | 2863.0 | 4281.3 | 5699.6 | 7995.1 | 10290.5 | 11654.6 |
| 2069.6 | 52.5° | 2098.8 | 2204.4 | 2370.0 | 2568.2 | 2766.6 | 4149.4 | 5532.3 | 8241.7 | 10950.8 | 12963.4 |
| 2005.1 | 55°   | 2051.2 | 2210.4 | 2364.4 | 2519.5 | 2674.5 | 3930.6 | 5186.7 | 8187.3 | 11187.8 | 14123.7 |
| 1955.5 | 57.5° | 2022.7 | 2216.3 | 2352.2 | 2461.7 | 2571.3 | 3622.2 | 4673.0 | 7804.9 | 10936.9 | 14946.0 |
| 1908.8 | 60°   | 1995.9 | 2197.6 | 2287.3 | 2373.4 | 2459.5 | 3221.7 | 3983.9 | 7093.1 | 10202.2 | 15151.5 |
| 1855.6 | 62.5° | 1964.6 | 2151.8 | 2162.8 | 2219.9 | 2277.1 | 2742.5 | 3207.8 | 6130.6 | 9053.5  | 14286.2 |
| 1782.9 | 65°   | 1898.7 | 2041.4 | 2040.0 | 2067.0 | 2094.0 | 2311.3 | 2528.5 | 5148.7 | 7769.0  | 13061.9 |
| 1684.7 | 67.5° | 1781.2 | 1861.4 | 1865.1 | 1850.2 | 1835.0 | 1896.9 | 1958.5 | 4186.7 | 6414.9  | 11604.9 |
| 1563.5 | 70°   | 1632.1 | 1658.4 | 1658.4 | 1588.6 | 1518.6 | 1501.2 | 1483.5 | 3296.5 | 5109.4  | 10015.1 |
| 1419.0 | 72.5° | 1466.0 | 1465.7 | 1449.0 | 1350.0 | 1250.8 | 1197.5 | 1144.3 | 2520.2 | 3896.0  | 8291.6  |
| 1241.3 | 75°   | 1277.5 | 1283.9 | 1207.2 | 1096.1 | 985.0  | 936.8  | 888.6  | 1829.1 | 2769.6  | 6315.9  |
| 1059.6 | 77.5° | 1088.6 | 1092.0 | 965.5  | 857.7  | 749.8  | 716.9  | 684.1  | 1239.4 | 1794.8  | 4420.6  |
| 849.0  | 80°   | 873.3  | 873.8  | 722.6  | 631.4  | 540.1  | 526.5  | 512.9  | 798.6  | 1084.4  | 2848.1  |
| 630.4  | 82.5° | 642.3  | 635.2  | 506.1  | 438.8  | 371.6  | 368.9  | 366.5  | 491.2  | 616.2   | 1648.4  |
| 410.1  | 85°   | 422.9  | 413.5  | 317.6  | 268.3  | 219.1  | 220.4  | 221.6  | 262.6  | 303.7   | 741.5   |
| 181.7  | 87.5° | 186.8  | 174.9  | 135.0  | 114.8  | 94.8   | 96.0   | 97.1   | 108.9  | 120.6   | 242.9   |
| 0.0    | 90°   | 0.0    | 0.0    | 0.0    | 0.0    | 0.0    | 0.0    | 0.0    | 0.0    | 0.0     | 0.0     |

REPORT NUMBER: P948895

CATALOG NUMBER: GLAN-SB3D-760-U-SLR

**CANDELA DISTRIBUTION (continued):**

| 270°    |       | 275°    | 280°    | 285°    | 290°    | 295°    | 300°    | 305°    | 310°    | 315°    | 320°    |
|---------|-------|---------|---------|---------|---------|---------|---------|---------|---------|---------|---------|
| 4425.9  | 0°    | 4425.9  | 4425.9  | 4425.9  | 4425.9  | 4425.9  | 4425.9  | 4425.9  | 4425.9  | 4425.9  | 4425.9  |
| 4759.6  | 2.5°  | 4777.6  | 4795.7  | 4821.4  | 4847.0  | 4862.3  | 4877.6  | 4885.3  | 4892.9  | 4889.5  | 4892.9  |
| 5117.9  | 5°    | 5180.9  | 5244.1  | 5306.6  | 5369.3  | 5403.2  | 5437.2  | 5457.8  | 5478.5  | 5494.1  | 5478.5  |
| 5478.0  | 7.5°  | 5580.5  | 5683.0  | 5775.2  | 5867.4  | 5922.9  | 5978.5  | 6008.5  | 6038.4  | 6052.9  | 6038.4  |
| 5753.9  | 10°   | 5875.2  | 5996.5  | 6104.7  | 6212.8  | 6278.4  | 6343.6  | 6372.8  | 6401.9  | 6412.9  | 6401.9  |
| 5922.9  | 12.5° | 6054.4  | 6185.7  | 6283.5  | 6381.0  | 6428.5  | 6476.1  | 6492.0  | 6508.0  | 6509.7  | 6508.0  |
| 6025.7  | 15°   | 6139.1  | 6252.4  | 6313.7  | 6375.2  | 6376.9  | 6378.6  | 6361.6  | 6344.6  | 6324.6  | 6344.6  |
| 6083.4  | 17.5° | 6160.0  | 6236.6  | 6237.8  | 6238.8  | 6170.0  | 6101.3  | 6038.2  | 5975.1  | 5930.6  | 5975.1  |
| 6147.1  | 20°   | 6173.8  | 6200.6  | 6119.9  | 6039.3  | 5887.4  | 5735.6  | 5625.0  | 5514.5  | 5446.5  | 5514.5  |
| 6221.0  | 22.5° | 6186.0  | 6151.0  | 5983.9  | 5816.8  | 5593.5  | 5370.1  | 5231.9  | 5093.6  | 5018.6  | 5093.6  |
| 6316.1  | 25°   | 6205.7  | 6095.3  | 5841.6  | 5587.9  | 5316.6  | 5045.4  | 4900.0  | 4755.0  | 4684.0  | 4755.0  |
| 6445.2  | 27.5° | 6247.8  | 6050.3  | 5714.2  | 5378.3  | 5077.7  | 4777.1  | 4634.1  | 4491.2  | 4424.2  | 4491.2  |
| 6619.2  | 30°   | 6324.9  | 6030.8  | 5617.1  | 5203.3  | 4890.2  | 4577.0  | 4444.4  | 4311.7  | 4249.2  | 4311.7  |
| 6824.7  | 32.5° | 6421.7  | 6018.9  | 5550.8  | 5082.8  | 4788.4  | 4494.1  | 4390.0  | 4285.7  | 4240.7  | 4285.7  |
| 7074.4  | 35°   | 6581.2  | 6088.2  | 5600.4  | 5112.8  | 4908.3  | 4704.0  | 4679.8  | 4655.5  | 4651.7  | 4655.5  |
| 7494.7  | 37.5° | 6914.6  | 6334.4  | 5891.2  | 5447.9  | 5434.7  | 5421.4  | 5532.5  | 5643.6  | 5701.3  | 5643.6  |
| 8129.9  | 40°   | 7499.0  | 6868.1  | 6538.4  | 6208.8  | 6441.4  | 6674.1  | 6944.1  | 7214.2  | 7348.7  | 7214.2  |
| 8972.3  | 42.5° | 8346.3  | 7720.3  | 7530.4  | 7340.5  | 7848.0  | 8355.5  | 8846.6  | 9337.8  | 9626.1  | 9337.8  |
| 10012.5 | 45°   | 9450.2  | 8887.7  | 8804.0  | 8720.1  | 9533.1  | 10346.2 | 11153.3 | 11960.5 | 12450.5 | 11960.5 |
| 11313.4 | 47.5° | 10766.4 | 10219.2 | 10202.2 | 10185.2 | 11358.1 | 12530.6 | 13712.2 | 14893.5 | 15587.3 | 14893.5 |
| 13018.6 | 50°   | 12342.8 | 11667.2 | 11670.1 | 11673.0 | 13184.5 | 14696.0 | 16255.6 | 17815.2 | 18758.1 | 17815.2 |
| 14975.9 | 52.5° | 14157.6 | 13339.5 | 13256.8 | 13174.0 | 14979.5 | 16785.0 | 18714.6 | 20644.1 | 21774.3 | 20644.1 |
| 17059.7 | 55°   | 16251.3 | 15442.9 | 15120.4 | 14797.9 | 16807.4 | 18816.7 | 21117.1 | 23417.4 | 24761.7 | 23417.4 |
| 18955.1 | 57.5° | 18514.9 | 18074.5 | 17427.6 | 16780.9 | 18809.9 | 20838.9 | 23444.4 | 26049.9 | 27716.8 | 26049.9 |
| 20100.6 | 60°   | 20784.4 | 21468.3 | 20665.0 | 19861.6 | 21781.8 | 23701.9 | 26491.6 | 29281.3 | 31082.9 | 29281.3 |
| 19518.9 | 62.5° | 21387.3 | 23255.6 | 23165.1 | 23074.4 | 24833.3 | 26592.5 | 29246.6 | 31900.6 | 33565.8 | 31900.6 |
| 18354.7 | 65°   | 20108.2 | 21861.8 | 22208.7 | 22555.5 | 24790.9 | 27026.4 | 29600.1 | 32173.5 | 33591.3 | 32173.5 |
| 16794.8 | 67.5° | 18462.6 | 20130.3 | 20293.0 | 20455.6 | 22784.6 | 25113.6 | 27698.3 | 30283.0 | 31393.7 | 30283.0 |
| 14920.7 | 70°   | 16734.7 | 18548.8 | 18621.5 | 18694.4 | 20777.2 | 22859.9 | 25084.2 | 27308.3 | 27925.7 | 27308.3 |
| 12687.4 | 72.5° | 14769.0 | 16850.8 | 16903.2 | 16955.3 | 18584.8 | 20214.4 | 21880.3 | 23546.0 | 23608.5 | 23546.0 |
| 9862.2  | 75°   | 12016.7 | 14171.2 | 14364.7 | 14558.1 | 15825.9 | 17093.7 | 18266.4 | 19439.1 | 19124.9 | 19439.1 |
| 7046.4  | 77.5° | 9057.5  | 11068.9 | 11345.7 | 11622.5 | 12586.3 | 13550.1 | 14381.8 | 15213.7 | 14673.6 | 15213.7 |
| 4611.8  | 80°   | 6303.9  | 7995.7  | 8339.8  | 8683.9  | 9411.8  | 10139.4 | 10576.2 | 11012.8 | 10144.1 | 11012.8 |
| 2680.8  | 82.5° | 3837.6  | 4994.5  | 5378.8  | 5763.3  | 6264.3  | 6765.3  | 6947.5  | 7129.6  | 6446.9  | 7129.6  |
| 1179.5  | 85°   | 1793.4  | 2407.4  | 2734.3  | 3061.2  | 3472.9  | 3884.4  | 3987.9  | 4091.3  | 3544.4  | 4091.3  |
| 365.1   | 87.5° | 571.5   | 777.8   | 960.2   | 1142.6  | 1348.5  | 1554.3  | 1563.1  | 1571.8  | 1319.6  | 1571.8  |
| 0.0     | 90°   | 0.0     | 0.0     | 0.0     | 0.0     | 0.0     | 0.0     | 0.0     | 0.0     | 0.0     | 0.0     |

REPORT NUMBER: P948895

CATALOG NUMBER: GLAN-SB3D-760-U-SLR

**CANDELA DISTRIBUTION (continued):**

| 325°    |       | 330°    | 335°    | 340°    | 345°    | 350°    | 355°    | 360°    |
|---------|-------|---------|---------|---------|---------|---------|---------|---------|
| 4425.9  | 0°    | 4425.9  | 4425.9  | 4425.9  | 4425.9  | 4425.9  | 4425.9  | 4425.9  |
| 4885.3  | 2.5°  | 4877.6  | 4862.3  | 4847.0  | 4821.4  | 4795.7  | 4777.6  | 4759.6  |
| 5457.8  | 5°    | 5437.2  | 5403.2  | 5369.3  | 5306.6  | 5244.1  | 5180.9  | 5117.9  |
| 6008.5  | 7.5°  | 5978.5  | 5922.9  | 5867.4  | 5775.2  | 5683.0  | 5580.5  | 5478.0  |
| 6372.8  | 10°   | 6343.6  | 6278.4  | 6212.8  | 6104.7  | 5996.5  | 5875.2  | 5753.9  |
| 6492.0  | 12.5° | 6476.1  | 6428.5  | 6381.0  | 6283.5  | 6185.7  | 6054.4  | 5922.9  |
| 6361.6  | 15°   | 6378.6  | 6376.9  | 6375.2  | 6313.7  | 6252.4  | 6139.1  | 6025.7  |
| 6038.2  | 17.5° | 6101.3  | 6170.0  | 6238.8  | 6237.8  | 6236.6  | 6160.0  | 6083.4  |
| 5625.0  | 20°   | 5735.6  | 5887.4  | 6039.3  | 6119.9  | 6200.6  | 6173.8  | 6147.1  |
| 5231.9  | 22.5° | 5370.1  | 5593.5  | 5816.8  | 5983.9  | 6151.0  | 6186.0  | 6221.0  |
| 4900.0  | 25°   | 5045.4  | 5316.6  | 5587.9  | 5841.6  | 6095.3  | 6205.7  | 6316.1  |
| 4634.1  | 27.5° | 4777.1  | 5077.7  | 5378.3  | 5714.2  | 6050.3  | 6247.8  | 6445.2  |
| 4444.4  | 30°   | 4577.0  | 4890.2  | 5203.3  | 5617.1  | 6030.8  | 6324.9  | 6619.2  |
| 4390.0  | 32.5° | 4494.1  | 4788.4  | 5082.8  | 5550.8  | 6018.9  | 6421.7  | 6824.7  |
| 4679.8  | 35°   | 4704.0  | 4908.3  | 5112.8  | 5600.4  | 6088.2  | 6581.2  | 7074.4  |
| 5532.5  | 37.5° | 5421.4  | 5434.7  | 5447.9  | 5891.2  | 6334.4  | 6914.6  | 7494.7  |
| 6944.1  | 40°   | 6674.1  | 6441.4  | 6208.8  | 6538.4  | 6868.1  | 7499.0  | 8129.9  |
| 8846.6  | 42.5° | 8355.5  | 7848.0  | 7340.5  | 7530.4  | 7720.3  | 8346.3  | 8972.3  |
| 11153.3 | 45°   | 10346.2 | 9533.1  | 8720.1  | 8804.0  | 8887.7  | 9450.2  | 10012.5 |
| 13712.2 | 47.5° | 12530.6 | 11358.1 | 10185.2 | 10202.2 | 10219.2 | 10766.4 | 11313.4 |
| 16255.6 | 50°   | 14696.0 | 13184.5 | 11673.0 | 11670.1 | 11667.2 | 12342.8 | 13018.6 |
| 18714.6 | 52.5° | 16785.0 | 14979.5 | 13174.0 | 13256.8 | 13339.5 | 14157.6 | 14975.9 |
| 21117.1 | 55°   | 18816.7 | 16807.4 | 14797.9 | 15120.4 | 15442.9 | 16251.3 | 17059.7 |
| 23444.4 | 57.5° | 20838.9 | 18809.9 | 16780.9 | 17427.6 | 18074.5 | 18514.9 | 18955.1 |
| 26491.6 | 60°   | 23701.9 | 21781.8 | 19861.6 | 20665.0 | 21468.3 | 20784.4 | 20100.6 |
| 29246.6 | 62.5° | 26592.5 | 24833.3 | 23074.4 | 23165.1 | 23255.6 | 21387.3 | 19518.9 |
| 29600.1 | 65°   | 27026.4 | 24790.9 | 22555.5 | 22208.7 | 21861.8 | 20108.2 | 18354.7 |
| 27698.3 | 67.5° | 25113.6 | 22784.6 | 20455.6 | 20293.0 | 20130.3 | 18462.6 | 16794.8 |
| 25084.2 | 70°   | 22859.9 | 20777.2 | 18694.4 | 18621.5 | 18548.8 | 16734.7 | 14920.7 |
| 21880.3 | 72.5° | 20214.4 | 18584.8 | 16955.3 | 16903.2 | 16850.8 | 14769.0 | 12687.4 |
| 18266.4 | 75°   | 17093.7 | 15825.9 | 14558.1 | 14364.7 | 14171.2 | 12016.7 | 9862.2  |
| 14381.8 | 77.5° | 13550.1 | 12586.3 | 11622.5 | 11345.7 | 11068.9 | 9057.5  | 7046.4  |
| 10576.2 | 80°   | 10139.4 | 9411.8  | 8683.9  | 8339.8  | 7995.7  | 6303.9  | 4611.8  |
| 6947.5  | 82.5° | 6765.3  | 6264.3  | 5763.3  | 5378.8  | 4994.5  | 3837.6  | 2680.8  |
| 3987.9  | 85°   | 3884.4  | 3472.9  | 3061.2  | 2734.3  | 2407.4  | 1793.4  | 1179.5  |
| 1563.1  | 87.5° | 1554.3  | 1348.5  | 1142.6  | 960.2   | 777.8   | 571.5   | 365.1   |
| 0.0     | 90°   | 0.0     | 0.0     | 0.0     | 0.0     | 0.0     | 0.0     | 0.0     |

(END OF REPORT)