

Scaled data based on original data using  
LM-79-08 Approved Method: Electrical and Photometric Measurements of Solid-  
State Lighting Products

Test Report Prepared for  
Cooper Lighting Solutions  
(formerly Eaton)

Brand: STREETWORKS

Report Number: P948200

Luminaire Tested: **GLAN-SB3B-827-U-SLL**

Issue Date: 1/21/2025

### Test Information

Test Method: LM-79-08  
Report Number: P948200  
TEST IS SCALED FROM IESNA LM-79-08 TEST DATA (G2-2411-289-8)  
Test Lab: INNOVATION CENTER  
Issue Date: 1/21/2025  
Manufacturer: COOPER LIGHTING SOLUTIONS (FORMERLY EATON)  
Product Line: STREETWORKS  
Catalog Number: GLAN-SB3B-827-U-SLL  
Description: GALLEON AREA AND ROADWAY HIGH DENSITY LED LUMINAIRE  
(3) 80 CRI, 2700K, 450mA LIGHTSQUARES WITH 26 LEDS EACH AND SPILL LIGHT  
ELIMINATOR LEFT OPTICS  
Light Source: -  
Ballast/Driver: -

### Summary

Lumens per Lamp: N/A  
Luminaire Lumens: 14639 lumens  
Efficiency: N/A  
Efficacy: 134.1 lumens/watt  
Luminous Opening: Rectangular (W 1' x L: 1' x H: 0')  
IES Classification: Type IV - Short  
BUG Rating: B3 - U0 - G3

Input Watts (W): 109.2  
Input Voltage (V): NR  
Input Current (Ain): NR  
Voltage Rise (V): NR  
Power Factor: NR  
Total Harmonic Distortion (THDi): NR  
Frequency (hertz): 60  
Stabilization Time: NR  
Operation Time: NR  
Ambient Temperature (°C): NR  
Test Distance: 24 FT




REPORT NUMBER: P948200

CATALOG NUMBER: GLAN-SB3B-827-U-SLL

## Iso-Footcandle Lines of Horizontal Illumination

× Max cd

--- 1/2 Max cd




Based on 25 foot mounting height. Maximum calculated value = 4.5 fc

Type IV - Short - N/A

REPORT NUMBER: P948200  
CATALOG NUMBER: GLAN-SB3B-827-U-SLL

Luminous Intensity Polar Plot



REPORT NUMBER: P948200

CATALOG NUMBER: GLAN-SB3B-827-U-SLL

**FLUX DISTRIBUTION:**

|                    |           | Downward | Upward | Total   |
|--------------------|-----------|----------|--------|---------|
| <b>House Side</b>  | Lumens    | 3720.5   | 0.0    | 3720.5  |
|                    | % Fixture | 25.4     | 0.0    | 25.4    |
| <b>Street Side</b> | Lumens    | 10918.5  | 0.0    | 10918.5 |
|                    | % Fixture | 74.6     | 0.0    | 74.6    |
| <b>Total</b>       | Lumens    | 14639.0  | 0.0    | 14639.0 |
|                    | % Fixture | 100.0    | 0.0    | 100.0   |

**ZONAL LUMENS:**

| Zone      | Lumens  | % Fixture |
|-----------|---------|-----------|
| 0°-10°    | 199.7   | 1.4       |
| 10°-20°   | 626.9   | 4.3       |
| 20°-30°   | 968.3   | 6.6       |
| 30°-40°   | 1227.1  | 8.4       |
| 40°-50°   | 1850.7  | 12.6      |
| 50°-60°   | 2990.1  | 20.4      |
| 60°-70°   | 3727.6  | 25.5      |
| 70°-80°   | 2444.4  | 16.7      |
| 80°-90°   | 604.3   | 4.1       |
| 90°-100°  | 0.0     | 0.0       |
| 100°-110° | 0.0     | 0.0       |
| 110°-120° | 0.0     | 0.0       |
| 120°-130° | 0.0     | 0.0       |
| 130°-140° | 0.0     | 0.0       |
| 140°-150° | 0.0     | 0.0       |
| 150°-160° | 0.0     | 0.0       |
| 160°-170° | 0.0     | 0.0       |
| 170°-180° | 0.0     | 0.0       |
| 0°-90°    | 14639.0 | 100.0     |
| 0°-180°   | 14639.0 | 100.0     |

**Coefficient of Utilization**



REPORT NUMBER: P948200


CATALOG NUMBER: GLAN-SB3B-827-U-SLL

**LUMINAIRE CLASSIFICATION SYSTEM LUMEN TABLE AND BUG RATING:**

| Zone |             | Lumens | % Fixture | Zone Rating/Lumen Limit |      |         |
|------|-------------|--------|-----------|-------------------------|------|---------|
|      |             |        |           | B                       | U    | G       |
| FL   | (0°-30°)    | 984.6  | 6.7       |                         |      |         |
| FM   | (30°-60°)   | 4269.9 | 29.2      |                         |      |         |
| FH   | (60°-80°)   | 5166.2 | 35.3      |                         |      | G3/7500 |
| FVH  | (80°-90°)   | 497.8  | 3.4       |                         |      | G3/500  |
| BL   | (0°-30°)    | 810.2  | 5.5       | B2/1000                 |      |         |
| BM   | (30°-60°)   | 1798.0 | 12.3      | B2/2500                 |      |         |
| BH   | (60°-80°)   | 1005.8 | 6.9       | B3/2500                 |      | G3/2500 |
| BVH  | (80°-90°)   | 106.5  | 0.7       |                         |      | G2/225  |
| UL   | (90°-100°)  | 0.0    | 0.0       |                         | U0/0 |         |
| UH   | (100°-180°) | 0.0    | 0.0       |                         | U0/0 |         |

**BUG Rating: B3-U0-G3**

Type IV Short



REPORT NUMBER: P948200

CATALOG NUMBER: GLAN-SB3B-827-U-SLL

**CANDELA DISTRIBUTION (FULL):**

|       | 0°     | 5°     | 10°     | 15°     | 20°     | 25°     | 30°     | 35°     | 40°     | 45°     |
|-------|--------|--------|---------|---------|---------|---------|---------|---------|---------|---------|
| 0°    | 2013.0 | 2013.0 | 2013.0  | 2013.0  | 2013.0  | 2013.0  | 2013.0  | 2013.0  | 2013.0  | 2013.0  |
| 2.5°  | 2164.8 | 2173.0 | 2181.2  | 2192.9  | 2204.6  | 2211.5  | 2218.5  | 2221.9  | 2225.4  | 2223.9  |
| 5°    | 2327.8 | 2356.4 | 2385.2  | 2413.6  | 2442.1  | 2457.5  | 2473.0  | 2482.3  | 2491.7  | 2498.9  |
| 7.5°  | 2491.5 | 2538.2 | 2584.8  | 2626.7  | 2668.6  | 2693.9  | 2719.2  | 2732.8  | 2746.4  | 2753.0  |
| 10°   | 2617.0 | 2672.2 | 2727.3  | 2776.5  | 2825.8  | 2855.6  | 2885.2  | 2898.5  | 2911.7  | 2916.7  |
| 12.5° | 2693.9 | 2753.7 | 2813.4  | 2857.9  | 2902.2  | 2923.9  | 2945.5  | 2952.7  | 2960.0  | 2960.8  |
| 15°   | 2740.6 | 2792.2 | 2843.8  | 2871.6  | 2899.6  | 2900.4  | 2901.1  | 2893.4  | 2885.7  | 2876.6  |
| 17.5° | 2766.9 | 2801.7 | 2836.6  | 2837.1  | 2837.6  | 2806.3  | 2775.0  | 2746.3  | 2717.6  | 2697.4  |
| 20°   | 2795.9 | 2808.0 | 2820.2  | 2783.5  | 2746.8  | 2677.8  | 2608.7  | 2558.4  | 2508.1  | 2477.2  |
| 22.5° | 2829.5 | 2813.5 | 2797.6  | 2721.6  | 2645.6  | 2544.0  | 2442.5  | 2379.6  | 2316.7  | 2282.6  |
| 25°   | 2872.7 | 2822.5 | 2772.3  | 2656.9  | 2541.5  | 2418.1  | 2294.8  | 2228.7  | 2162.7  | 2130.4  |
| 27.5° | 2931.4 | 2841.7 | 2751.8  | 2599.0  | 2446.2  | 2309.5  | 2172.7  | 2107.7  | 2042.7  | 2012.2  |
| 30°   | 3010.6 | 2876.7 | 2742.9  | 2554.8  | 2366.6  | 2224.2  | 2081.7  | 2021.4  | 1961.1  | 1932.7  |
| 32.5° | 3104.1 | 2920.8 | 2737.5  | 2524.7  | 2311.8  | 2177.9  | 2044.0  | 1996.7  | 1949.3  | 1928.8  |
| 35°   | 3217.6 | 2993.3 | 2769.1  | 2547.2  | 2325.4  | 2232.4  | 2139.5  | 2128.5  | 2117.4  | 2115.7  |
| 37.5° | 3408.8 | 3144.9 | 2881.1  | 2679.5  | 2477.8  | 2471.8  | 2465.8  | 2516.3  | 2566.8  | 2593.1  |
| 40°   | 3697.7 | 3410.7 | 3123.8  | 2973.8  | 2823.9  | 2929.7  | 3035.5  | 3158.4  | 3281.2  | 3342.4  |
| 42.5° | 4080.8 | 3796.1 | 3511.4  | 3425.0  | 3338.7  | 3569.5  | 3800.3  | 4023.7  | 4247.1  | 4378.2  |
| 45°   | 4553.9 | 4298.2 | 4042.4  | 4004.3  | 3966.1  | 4335.9  | 4705.7  | 5072.8  | 5439.9  | 5662.8  |
| 47.5° | 5145.6 | 4896.8 | 4647.9  | 4640.2  | 4632.5  | 5165.9  | 5699.2  | 6236.6  | 6773.9  | 7089.5  |
| 50°   | 5921.2 | 5613.8 | 5306.5  | 5307.8  | 5309.2  | 5996.6  | 6684.1  | 7393.4  | 8102.8  | 8531.6  |
| 52.5° | 6811.4 | 6439.2 | 6067.2  | 6029.5  | 5991.8  | 6813.0  | 7634.2  | 8511.9  | 9389.4  | 9903.5  |
| 55°   | 7759.2 | 7391.5 | 7023.8  | 6877.1  | 6730.5  | 7644.4  | 8558.3  | 9604.6  | 10650.8 | 11262.2 |
| 57.5° | 8621.2 | 8421.0 | 8220.7  | 7926.5  | 7632.4  | 8555.2  | 9478.0  | 10663.1 | 11848.1 | 12606.3 |
| 60°   | 9142.3 | 9453.2 | 9764.3  | 9398.9  | 9033.6  | 9906.9  | 10780.2 | 12049.0 | 13317.9 | 14137.3 |
| 62.5° | 8877.7 | 9727.5 | 10577.2 | 10536.1 | 10494.8 | 11294.8 | 12094.9 | 13302.1 | 14509.2 | 15266.6 |
| 65°   | 8348.2 | 9145.7 | 9943.3  | 10101.1 | 10258.8 | 11275.5 | 12292.3 | 13462.8 | 14633.3 | 15278.2 |
| 67.5° | 7638.7 | 8397.2 | 9155.8  | 9229.8  | 9303.7  | 10363.0 | 11422.3 | 12597.9 | 13773.4 | 14278.6 |
| 70°   | 6786.3 | 7611.4 | 8436.5  | 8469.5  | 8502.7  | 9450.0  | 10397.2 | 11408.9 | 12420.5 | 12701.3 |
| 72.5° | 5770.5 | 6717.3 | 7664.2  | 7688.0  | 7711.7  | 8452.9  | 9194.0  | 9951.7  | 10709.3 | 10737.7 |
| 75°   | 4485.6 | 5465.5 | 6445.4  | 6533.4  | 6621.4  | 7198.0  | 7774.6  | 8308.0  | 8841.4  | 8698.5  |
| 77.5° | 3204.9 | 4119.6 | 5034.4  | 5160.3  | 5286.2  | 5724.6  | 6162.9  | 6541.2  | 6919.6  | 6673.9  |
| 80°   | 2097.6 | 2867.2 | 3636.7  | 3793.2  | 3949.7  | 4280.7  | 4611.6  | 4810.3  | 5008.9  | 4613.8  |
| 82.5° | 1219.3 | 1745.4 | 2271.6  | 2446.4  | 2621.3  | 2849.2  | 3077.0  | 3159.9  | 3242.7  | 2932.2  |
| 85°   | 536.5  | 815.7  | 1094.9  | 1243.6  | 1392.3  | 1579.6  | 1766.7  | 1813.8  | 1860.8  | 1612.1  |
| 87.5° | 166.1  | 259.9  | 353.8   | 436.7   | 519.7   | 613.3   | 706.9   | 711.0   | 714.9   | 600.2   |
| 90°   | 0.0    | 0.0    | 0.0     | 0.0     | 0.0     | 0.0     | 0.0     | 0.0     | 0.0     | 0.0     |

REPORT NUMBER: P948200

CATALOG NUMBER: GLAN-SB3B-827-U-SLL

**CANDELA DISTRIBUTION (continued):**

| 50°     |       | 55°     | 60°     | 65°     | 70°     | 75°     | 80°     | 85°    | 90°    | 95°    | 100°   |
|---------|-------|---------|---------|---------|---------|---------|---------|--------|--------|--------|--------|
| 2013.0  | 0°    | 2013.0  | 2013.0  | 2013.0  | 2013.0  | 2013.0  | 2013.0  | 2013.0 | 2013.0 | 2013.0 | 2013.0 |
| 2225.4  | 2.5°  | 2221.9  | 2218.5  | 2211.5  | 2204.6  | 2192.9  | 2181.2  | 2173.0 | 2164.8 | 2148.2 | 2131.6 |
| 2491.7  | 5°    | 2482.3  | 2473.0  | 2457.5  | 2442.1  | 2413.6  | 2385.2  | 2356.4 | 2327.8 | 2291.1 | 2254.4 |
| 2746.4  | 7.5°  | 2732.8  | 2719.2  | 2693.9  | 2668.6  | 2626.7  | 2584.8  | 2538.2 | 2491.5 | 2431.0 | 2370.5 |
| 2911.7  | 10°   | 2898.5  | 2885.2  | 2855.6  | 2825.8  | 2776.5  | 2727.3  | 2672.2 | 2617.0 | 2540.5 | 2463.9 |
| 2960.0  | 12.5° | 2952.7  | 2945.5  | 2923.9  | 2902.2  | 2857.9  | 2813.4  | 2753.7 | 2693.9 | 2609.8 | 2525.7 |
| 2885.7  | 15°   | 2893.4  | 2901.1  | 2900.4  | 2899.6  | 2871.6  | 2843.8  | 2792.2 | 2740.6 | 2653.0 | 2565.3 |
| 2717.6  | 17.5° | 2746.3  | 2775.0  | 2806.3  | 2837.6  | 2837.1  | 2836.6  | 2801.7 | 2766.9 | 2678.0 | 2589.1 |
| 2508.1  | 20°   | 2558.4  | 2608.7  | 2677.8  | 2746.8  | 2783.5  | 2820.2  | 2808.0 | 2795.9 | 2703.5 | 2611.0 |
| 2316.7  | 22.5° | 2379.6  | 2442.5  | 2544.0  | 2645.6  | 2721.6  | 2797.6  | 2813.5 | 2829.5 | 2735.1 | 2640.6 |
| 2162.7  | 25°   | 2228.7  | 2294.8  | 2418.1  | 2541.5  | 2656.9  | 2772.3  | 2822.5 | 2872.7 | 2780.2 | 2687.7 |
| 2042.7  | 27.5° | 2107.7  | 2172.7  | 2309.5  | 2446.2  | 2599.0  | 2751.8  | 2841.7 | 2931.4 | 2843.2 | 2754.9 |
| 1961.1  | 30°   | 2021.4  | 2081.7  | 2224.2  | 2366.6  | 2554.8  | 2742.9  | 2876.7 | 3010.6 | 2925.3 | 2840.1 |
| 1949.3  | 32.5° | 1996.7  | 2044.0  | 2177.9  | 2311.8  | 2524.7  | 2737.5  | 2920.8 | 3104.1 | 3019.6 | 2935.3 |
| 2117.4  | 35°   | 2128.5  | 2139.5  | 2232.4  | 2325.4  | 2547.2  | 2769.1  | 2993.3 | 3217.6 | 3136.8 | 3055.9 |
| 2566.8  | 37.5° | 2516.3  | 2465.8  | 2471.8  | 2477.8  | 2679.5  | 2881.1  | 3144.9 | 3408.8 | 3305.8 | 3202.7 |
| 3281.2  | 40°   | 3158.4  | 3035.5  | 2929.7  | 2823.9  | 2973.8  | 3123.8  | 3410.7 | 3697.7 | 3547.5 | 3397.4 |
| 4247.1  | 42.5° | 4023.7  | 3800.3  | 3569.5  | 3338.7  | 3425.0  | 3511.4  | 3796.1 | 4080.8 | 3864.1 | 3647.3 |
| 5439.9  | 45°   | 5072.8  | 4705.7  | 4335.9  | 3966.1  | 4004.3  | 4042.4  | 4298.2 | 4553.9 | 4261.6 | 3969.2 |
| 6773.9  | 47.5° | 6236.6  | 5699.2  | 5165.9  | 4632.5  | 4640.2  | 4647.9  | 4896.8 | 5145.6 | 4734.2 | 4322.6 |
| 8102.8  | 50°   | 7393.4  | 6684.1  | 5996.6  | 5309.2  | 5307.8  | 5306.5  | 5613.8 | 5921.2 | 5300.8 | 4680.4 |
| 9389.4  | 52.5° | 8511.9  | 7634.2  | 6813.0  | 5991.8  | 6029.5  | 6067.2  | 6439.2 | 6811.4 | 5896.1 | 4980.7 |
| 10650.8 | 55°   | 9604.6  | 8558.3  | 7644.4  | 6730.5  | 6877.1  | 7023.8  | 7391.5 | 7759.2 | 6423.8 | 5088.5 |
| 11848.1 | 57.5° | 10663.1 | 9478.0  | 8555.2  | 7632.4  | 7926.5  | 8220.7  | 8421.0 | 8621.2 | 6797.8 | 4974.4 |
| 13317.9 | 60°   | 12049.0 | 10780.2 | 9906.9  | 9033.6  | 9398.9  | 9764.3  | 9453.2 | 9142.3 | 6891.3 | 4640.2 |
| 14509.2 | 62.5° | 13302.1 | 12094.9 | 11294.8 | 10494.8 | 10536.1 | 10577.2 | 9727.5 | 8877.7 | 6497.7 | 4117.7 |
| 14633.3 | 65°   | 13462.8 | 12292.3 | 11275.5 | 10258.8 | 10101.1 | 9943.3  | 9145.7 | 8348.2 | 5940.9 | 3533.5 |
| 13773.4 | 67.5° | 12597.9 | 11422.3 | 10363.0 | 9303.7  | 9229.8  | 9155.8  | 8397.2 | 7638.7 | 5278.2 | 2917.7 |
| 12420.5 | 70°   | 11408.9 | 10397.2 | 9450.0  | 8502.7  | 8469.5  | 8436.5  | 7611.4 | 6786.3 | 4555.1 | 2323.9 |
| 10709.3 | 72.5° | 9951.7  | 9194.0  | 8452.9  | 7711.7  | 7688.0  | 7664.2  | 6717.3 | 5770.5 | 3771.2 | 1772.0 |
| 8841.4  | 75°   | 8308.0  | 7774.6  | 7198.0  | 6621.4  | 6533.4  | 6445.4  | 5465.5 | 4485.6 | 2872.6 | 1259.7 |
| 6919.6  | 77.5° | 6541.2  | 6162.9  | 5724.6  | 5286.2  | 5160.3  | 5034.4  | 4119.6 | 3204.9 | 2010.6 | 816.3  |
| 5008.9  | 80°   | 4810.3  | 4611.6  | 4280.7  | 3949.7  | 3793.2  | 3636.7  | 2867.2 | 2097.6 | 1295.4 | 493.2  |
| 3242.7  | 82.5° | 3159.9  | 3077.0  | 2849.2  | 2621.3  | 2446.4  | 2271.6  | 1745.4 | 1219.3 | 749.7  | 280.2  |
| 1860.8  | 85°   | 1813.8  | 1766.7  | 1579.6  | 1392.3  | 1243.6  | 1094.9  | 815.7  | 536.5  | 337.2  | 138.1  |
| 714.9   | 87.5° | 711.0   | 706.9   | 613.3   | 519.7   | 436.7   | 353.8   | 259.9  | 166.1  | 110.5  | 54.8   |
| 0.0     | 90°   | 0.0     | 0.0     | 0.0     | 0.0     | 0.0     | 0.0     | 0.0    | 0.0    | 0.0    | 0.0    |

REPORT NUMBER: P948200

CATALOG NUMBER: GLAN-SB3B-827-U-SLL

**CANDELA DISTRIBUTION (continued):**

| 105°   |       | 110°   | 115°   | 120°   | 125°   | 130°   | 135°   | 140°   | 145°   | 150°   | 155°   |
|--------|-------|--------|--------|--------|--------|--------|--------|--------|--------|--------|--------|
| 2013.0 | 0°    | 2013.0 | 2013.0 | 2013.0 | 2013.0 | 2013.0 | 2013.0 | 2013.0 | 2013.0 | 2013.0 | 2013.0 |
| 2113.9 | 2.5°  | 2096.3 | 2078.5 | 2060.7 | 2043.7 | 2026.7 | 2010.3 | 1992.0 | 1977.1 | 1962.4 | 1949.0 |
| 2217.8 | 5°    | 2181.2 | 2144.4 | 2107.6 | 2073.2 | 2038.9 | 2006.4 | 1974.4 | 1946.4 | 1918.4 | 1894.9 |
| 2314.6 | 7.5°  | 2258.6 | 2204.2 | 2149.7 | 2101.7 | 2053.8 | 2009.5 | 1968.0 | 1930.8 | 1893.6 | 1862.7 |
| 2390.0 | 10°   | 2316.2 | 2250.1 | 2183.9 | 2127.2 | 2070.3 | 2015.7 | 1971.1 | 1931.9 | 1892.6 | 1861.7 |
| 2442.0 | 12.5° | 2358.3 | 2280.3 | 2202.2 | 2138.0 | 2073.9 | 2016.5 | 1975.0 | 1942.9 | 1910.9 | 1890.3 |
| 2474.4 | 15°   | 2383.6 | 2293.8 | 2203.9 | 2129.6 | 2055.3 | 1991.7 | 1958.5 | 1943.2 | 1927.9 | 1930.6 |
| 2490.0 | 17.5° | 2390.9 | 2286.6 | 2182.3 | 2092.9 | 2003.6 | 1928.8 | 1908.3 | 1914.0 | 1919.5 | 1953.2 |
| 2502.1 | 20°   | 2393.2 | 2266.8 | 2140.4 | 2029.7 | 1918.9 | 1831.9 | 1826.4 | 1852.7 | 1879.0 | 1937.4 |
| 2518.5 | 22.5° | 2396.3 | 2242.6 | 2088.8 | 1955.4 | 1822.0 | 1722.9 | 1733.5 | 1772.4 | 1811.2 | 1878.0 |
| 2548.1 | 25°   | 2408.5 | 2218.6 | 2028.8 | 1872.6 | 1716.4 | 1614.8 | 1643.4 | 1688.2 | 1733.0 | 1793.0 |
| 2594.5 | 27.5° | 2434.0 | 2202.6 | 1971.3 | 1796.8 | 1622.3 | 1529.8 | 1564.6 | 1607.8 | 1651.1 | 1700.5 |
| 2654.5 | 30°   | 2468.9 | 2195.1 | 1921.2 | 1733.4 | 1545.7 | 1468.0 | 1495.3 | 1529.6 | 1564.0 | 1605.0 |
| 2717.1 | 32.5° | 2499.0 | 2185.9 | 1872.6 | 1678.8 | 1485.0 | 1422.5 | 1434.6 | 1454.9 | 1475.2 | 1507.9 |
| 2788.5 | 35°   | 2521.1 | 2168.4 | 1815.9 | 1625.1 | 1434.4 | 1382.3 | 1377.3 | 1382.8 | 1388.5 | 1413.4 |
| 2868.5 | 37.5° | 2534.2 | 2138.5 | 1742.8 | 1562.0 | 1381.1 | 1335.6 | 1317.2 | 1311.0 | 1304.8 | 1322.7 |
| 2970.0 | 40°   | 2542.5 | 2097.3 | 1652.3 | 1486.6 | 1320.9 | 1279.6 | 1251.4 | 1237.4 | 1223.4 | 1236.3 |
| 3102.8 | 42.5° | 2558.2 | 2054.9 | 1551.7 | 1403.4 | 1255.1 | 1217.0 | 1181.5 | 1162.9 | 1144.4 | 1154.9 |
| 3277.5 | 45°   | 2585.8 | 2015.4 | 1445.1 | 1315.0 | 1184.9 | 1146.3 | 1111.9 | 1093.9 | 1075.9 | 1084.7 |
| 3463.6 | 47.5° | 2604.7 | 1982.8 | 1360.9 | 1245.1 | 1129.3 | 1079.5 | 1049.9 | 1034.8 | 1019.6 | 1028.0 |
| 3636.4 | 50°   | 2592.3 | 1947.3 | 1302.2 | 1198.7 | 1095.2 | 1029.7 | 995.3  | 981.9  | 968.5  | 981.5  |
| 3748.5 | 52.5° | 2516.2 | 1887.2 | 1258.3 | 1168.1 | 1077.9 | 1002.6 | 954.6  | 941.3  | 928.1  | 947.6  |
| 3723.8 | 55°   | 2359.0 | 1787.7 | 1216.4 | 1145.9 | 1075.4 | 1005.3 | 933.0  | 911.9  | 891.0  | 918.7  |
| 3549.8 | 57.5° | 2125.4 | 1647.5 | 1169.5 | 1119.7 | 1069.8 | 1008.0 | 920.0  | 889.4  | 858.8  | 888.6  |
| 3226.1 | 60°   | 1812.0 | 1465.3 | 1118.7 | 1079.5 | 1040.3 | 999.5  | 907.8  | 868.1  | 828.4  | 854.6  |
| 2788.4 | 62.5° | 1459.0 | 1247.3 | 1035.7 | 1009.7 | 983.7  | 978.7  | 893.6  | 844.0  | 794.5  | 811.1  |
| 2341.7 | 65°   | 1150.0 | 1051.2 | 952.4  | 940.1  | 927.9  | 928.5  | 863.6  | 810.9  | 758.2  | 764.6  |
| 1904.2 | 67.5° | 890.8  | 862.7  | 834.6  | 841.5  | 848.3  | 846.6  | 810.1  | 766.3  | 722.4  | 720.4  |
| 1499.3 | 70°   | 674.7  | 682.8  | 690.7  | 722.5  | 754.3  | 754.3  | 742.3  | 711.1  | 679.9  | 673.0  |
| 1146.2 | 72.5° | 520.5  | 544.7  | 568.9  | 614.0  | 659.0  | 666.6  | 666.8  | 645.4  | 624.0  | 613.8  |
| 831.9  | 75°   | 404.1  | 426.1  | 448.0  | 498.5  | 549.1  | 584.0  | 581.0  | 564.6  | 548.0  | 538.3  |
| 563.7  | 77.5° | 311.1  | 326.0  | 341.0  | 390.1  | 439.1  | 496.7  | 495.1  | 481.9  | 468.7  | 458.8  |
| 363.2  | 80°   | 233.3  | 239.5  | 245.6  | 287.2  | 328.7  | 397.4  | 397.2  | 386.1  | 375.0  | 366.8  |
| 223.4  | 82.5° | 166.7  | 167.8  | 169.0  | 199.6  | 230.2  | 288.9  | 292.1  | 286.7  | 281.3  | 275.5  |
| 119.4  | 85°   | 100.8  | 100.3  | 99.6   | 122.0  | 144.4  | 188.1  | 192.3  | 186.5  | 180.8  | 174.2  |
| 49.5   | 87.5° | 44.2   | 43.6   | 43.1   | 52.2   | 61.4   | 79.6   | 85.0   | 82.7   | 80.3   | 79.1   |
| 0.0    | 90°   | 0.0    | 0.0    | 0.0    | 0.0    | 0.0    | 0.0    | 0.0    | 0.0    | 0.0    | 0.0    |

REPORT NUMBER: P948200

CATALOG NUMBER: GLAN-SB3B-827-U-SLL

**CANDELA DISTRIBUTION (continued):**

| 160°   |       | 165°   | 170°   | 175°   | 180°   | 185°   | 190°   | 195°   | 200°   | 205°   | 210°   |
|--------|-------|--------|--------|--------|--------|--------|--------|--------|--------|--------|--------|
| 2013.0 | 0°    | 2013.0 | 2013.0 | 2013.0 | 2013.0 | 2013.0 | 2013.0 | 2013.0 | 2013.0 | 2013.0 | 2013.0 |
| 1935.7 | 2.5°  | 1924.1 | 1912.4 | 1900.7 | 1889.0 | 1880.0 | 1870.9 | 1863.5 | 1856.2 | 1850.5 | 1844.8 |
| 1871.5 | 5°    | 1850.8 | 1830.1 | 1811.3 | 1792.5 | 1778.0 | 1763.5 | 1753.4 | 1743.3 | 1736.1 | 1728.9 |
| 1831.9 | 7.5°  | 1805.8 | 1779.7 | 1756.7 | 1733.8 | 1716.5 | 1699.4 | 1687.3 | 1675.3 | 1667.0 | 1658.8 |
| 1830.8 | 10°   | 1802.8 | 1774.7 | 1748.8 | 1722.9 | 1702.4 | 1681.8 | 1668.3 | 1654.7 | 1646.9 | 1639.1 |
| 1869.9 | 12.5° | 1847.8 | 1825.9 | 1799.1 | 1772.4 | 1746.1 | 1719.8 | 1702.5 | 1685.1 | 1676.4 | 1667.7 |
| 1933.4 | 15°   | 1927.7 | 1922.0 | 1898.7 | 1875.5 | 1838.1 | 1800.7 | 1774.3 | 1747.9 | 1735.8 | 1723.7 |
| 1986.9 | 17.5° | 2004.8 | 2022.6 | 2003.9 | 1985.2 | 1935.7 | 1886.2 | 1847.2 | 1808.3 | 1790.4 | 1772.4 |
| 1996.0 | 20°   | 2033.5 | 2070.9 | 2062.3 | 2053.5 | 1996.9 | 1940.4 | 1892.6 | 1845.0 | 1822.0 | 1799.0 |
| 1944.9 | 22.5° | 1993.6 | 2042.3 | 2047.6 | 2052.8 | 1998.7 | 1944.6 | 1895.5 | 1846.3 | 1822.1 | 1797.9 |
| 1853.1 | 25°   | 1901.1 | 1949.0 | 1967.0 | 1984.8 | 1940.5 | 1896.2 | 1852.5 | 1808.9 | 1787.9 | 1767.0 |
| 1749.7 | 27.5° | 1788.2 | 1826.7 | 1846.6 | 1866.6 | 1835.0 | 1803.5 | 1769.6 | 1735.7 | 1721.6 | 1707.5 |
| 1645.9 | 30°   | 1677.8 | 1709.8 | 1726.0 | 1742.2 | 1718.2 | 1694.1 | 1669.9 | 1645.5 | 1638.3 | 1631.0 |
| 1540.6 | 32.5° | 1571.2 | 1601.9 | 1619.9 | 1638.0 | 1615.9 | 1593.7 | 1574.3 | 1554.9 | 1550.2 | 1545.5 |
| 1438.3 | 35°   | 1468.6 | 1498.9 | 1520.6 | 1542.2 | 1526.4 | 1510.7 | 1492.8 | 1475.0 | 1467.8 | 1460.7 |
| 1340.6 | 37.5° | 1370.8 | 1401.1 | 1427.8 | 1454.5 | 1447.3 | 1440.0 | 1423.5 | 1407.0 | 1394.0 | 1381.0 |
| 1249.2 | 40°   | 1278.4 | 1307.6 | 1338.3 | 1369.2 | 1370.9 | 1372.6 | 1358.7 | 1344.7 | 1325.7 | 1306.8 |
| 1165.5 | 42.5° | 1193.1 | 1220.8 | 1254.1 | 1287.3 | 1296.2 | 1305.0 | 1293.2 | 1281.5 | 1257.9 | 1234.4 |
| 1093.6 | 45°   | 1119.9 | 1146.2 | 1180.6 | 1215.1 | 1227.8 | 1240.5 | 1229.9 | 1219.3 | 1192.3 | 1165.5 |
| 1036.2 | 47.5° | 1062.0 | 1087.6 | 1121.6 | 1155.6 | 1170.3 | 1184.9 | 1177.5 | 1170.1 | 1146.2 | 1122.2 |
| 994.5  | 50°   | 1018.8 | 1043.0 | 1073.4 | 1103.8 | 1122.7 | 1141.5 | 1141.1 | 1140.7 | 1121.6 | 1102.4 |
| 967.1  | 52.5° | 989.3  | 1011.5 | 1039.9 | 1068.3 | 1090.6 | 1112.9 | 1117.0 | 1121.0 | 1105.4 | 1089.8 |
| 946.4  | 55°   | 970.3  | 994.3  | 1019.2 | 1044.0 | 1067.6 | 1091.3 | 1096.9 | 1102.4 | 1088.8 | 1075.2 |
| 918.4  | 57.5° | 946.6  | 974.7  | 999.2  | 1023.9 | 1047.7 | 1071.5 | 1077.2 | 1082.8 | 1069.1 | 1055.3 |
| 880.7  | 60°   | 913.0  | 945.3  | 970.3  | 995.3  | 1019.2 | 1043.2 | 1049.4 | 1055.5 | 1042.1 | 1028.7 |
| 827.7  | 62.5° | 865.3  | 903.0  | 929.6  | 956.3  | 978.2  | 1000.2 | 1006.1 | 1012.1 | 999.9  | 987.8  |
| 770.9  | 65°   | 811.2  | 851.6  | 877.1  | 902.6  | 921.9  | 941.2  | 947.3  | 953.4  | 941.7  | 930.0  |
| 718.4  | 67.5° | 755.6  | 792.9  | 817.1  | 841.2  | 857.9  | 874.6  | 880.5  | 886.4  | 875.6  | 865.0  |
| 666.0  | 70°   | 698.8  | 731.5  | 752.4  | 773.2  | 788.3  | 803.3  | 809.1  | 814.8  | 806.0  | 797.3  |
| 603.7  | 72.5° | 629.5  | 655.2  | 674.0  | 692.9  | 707.6  | 722.4  | 729.2  | 736.0  | 728.7  | 721.5  |
| 528.5  | 75°   | 547.7  | 566.8  | 583.9  | 601.0  | 614.4  | 627.8  | 634.9  | 642.1  | 638.5  | 634.9  |
| 448.9  | 77.5° | 464.5  | 480.1  | 494.8  | 509.4  | 523.6  | 537.6  | 544.3  | 550.9  | 546.0  | 540.9  |
| 358.4  | 80°   | 371.4  | 384.3  | 396.6  | 409.0  | 419.7  | 430.4  | 439.2  | 448.0  | 445.9  | 443.8  |
| 269.6  | 82.5° | 268.5  | 267.4  | 263.1  | 258.8  | 281.6  | 304.5  | 319.5  | 334.5  | 333.5  | 332.5  |
| 167.6  | 85°   | 162.1  | 156.4  | 144.4  | 132.5  | 153.9  | 175.3  | 193.9  | 212.4  | 210.9  | 209.3  |
| 77.9   | 87.5° | 77.6   | 77.4   | 68.3   | 59.1   | 68.1   | 77.1   | 84.6   | 92.1   | 90.2   | 88.2   |
| 0.0    | 90°   | 0.0    | 0.0    | 0.0    | 0.0    | 0.0    | 0.0    | 0.0    | 0.0    | 0.0    | 0.0    |

REPORT NUMBER: P948200

CATALOG NUMBER: GLAN-SB3B-827-U-SLL

**CANDELA DISTRIBUTION (continued):**

| 215°   |       | 220°   | 225°   | 230°   | 235°   | 240°   | 245°   | 250°   | 255°   | 260°   | 265°   |
|--------|-------|--------|--------|--------|--------|--------|--------|--------|--------|--------|--------|
| 2013.0 | 0°    | 2013.0 | 2013.0 | 2013.0 | 2013.0 | 2013.0 | 2013.0 | 2013.0 | 2013.0 | 2013.0 | 2013.0 |
| 1839.5 | 2.5°  | 1834.2 | 1827.6 | 1834.2 | 1839.5 | 1844.8 | 1850.5 | 1856.2 | 1863.5 | 1870.9 | 1880.0 |
| 1723.4 | 5°    | 1717.9 | 1712.5 | 1717.9 | 1723.4 | 1728.9 | 1736.1 | 1743.3 | 1753.4 | 1763.5 | 1778.0 |
| 1653.9 | 7.5°  | 1649.0 | 1645.3 | 1649.0 | 1653.9 | 1658.8 | 1667.0 | 1675.3 | 1687.3 | 1699.4 | 1716.5 |
| 1635.0 | 10°   | 1630.8 | 1629.1 | 1630.8 | 1635.0 | 1639.1 | 1646.9 | 1654.7 | 1668.3 | 1681.8 | 1702.4 |
| 1664.2 | 12.5° | 1660.6 | 1660.0 | 1660.6 | 1664.2 | 1667.7 | 1676.4 | 1685.1 | 1702.5 | 1719.8 | 1746.1 |
| 1719.1 | 15°   | 1714.4 | 1714.1 | 1714.4 | 1719.1 | 1723.7 | 1735.8 | 1747.9 | 1774.3 | 1800.7 | 1838.1 |
| 1766.5 | 17.5° | 1760.6 | 1759.6 | 1760.6 | 1766.5 | 1772.4 | 1790.4 | 1808.3 | 1847.2 | 1886.2 | 1935.7 |
| 1791.7 | 20°   | 1784.3 | 1782.0 | 1784.3 | 1791.7 | 1799.0 | 1822.0 | 1845.0 | 1892.6 | 1940.4 | 1996.9 |
| 1789.8 | 22.5° | 1781.6 | 1778.2 | 1781.6 | 1789.8 | 1797.9 | 1822.1 | 1846.3 | 1895.5 | 1944.6 | 1998.7 |
| 1759.3 | 25°   | 1751.7 | 1747.3 | 1751.7 | 1759.3 | 1767.0 | 1787.9 | 1808.9 | 1852.5 | 1896.2 | 1940.5 |
| 1704.0 | 27.5° | 1700.5 | 1699.4 | 1700.5 | 1704.0 | 1707.5 | 1721.6 | 1735.7 | 1769.6 | 1803.5 | 1835.0 |
| 1631.0 | 30°   | 1631.0 | 1632.2 | 1631.0 | 1631.0 | 1631.0 | 1638.3 | 1645.5 | 1669.9 | 1694.1 | 1718.2 |
| 1546.1 | 32.5° | 1546.8 | 1548.0 | 1546.8 | 1546.1 | 1545.5 | 1550.2 | 1554.9 | 1574.3 | 1593.7 | 1615.9 |
| 1459.1 | 35°   | 1457.6 | 1456.8 | 1457.6 | 1459.1 | 1460.7 | 1467.8 | 1475.0 | 1492.8 | 1510.7 | 1526.4 |
| 1374.1 | 37.5° | 1367.2 | 1363.4 | 1367.2 | 1374.1 | 1381.0 | 1394.0 | 1407.0 | 1423.5 | 1440.0 | 1447.3 |
| 1294.0 | 40°   | 1281.3 | 1273.8 | 1281.3 | 1294.0 | 1306.8 | 1325.7 | 1344.7 | 1358.7 | 1372.6 | 1370.9 |
| 1215.7 | 42.5° | 1197.1 | 1184.9 | 1197.1 | 1215.7 | 1234.4 | 1257.9 | 1281.5 | 1293.2 | 1305.0 | 1296.2 |
| 1143.6 | 45°   | 1121.7 | 1107.7 | 1121.7 | 1143.6 | 1165.5 | 1192.3 | 1219.3 | 1229.9 | 1240.5 | 1227.8 |
| 1102.0 | 47.5° | 1081.8 | 1068.3 | 1081.8 | 1102.0 | 1122.2 | 1146.2 | 1170.1 | 1177.5 | 1184.9 | 1170.3 |
| 1083.7 | 50°   | 1065.0 | 1052.1 | 1065.0 | 1083.7 | 1102.4 | 1121.6 | 1140.7 | 1141.1 | 1141.5 | 1122.7 |
| 1073.0 | 52.5° | 1056.3 | 1044.3 | 1056.3 | 1073.0 | 1089.8 | 1105.4 | 1121.0 | 1117.0 | 1112.9 | 1090.6 |
| 1060.6 | 55°   | 1045.9 | 1035.1 | 1045.9 | 1060.6 | 1075.2 | 1088.8 | 1102.4 | 1096.9 | 1091.3 | 1067.6 |
| 1040.8 | 57.5° | 1026.2 | 1015.0 | 1026.2 | 1040.8 | 1055.3 | 1069.1 | 1082.8 | 1077.2 | 1071.5 | 1047.7 |
| 1013.8 | 60°   | 998.8  | 987.2  | 998.8  | 1013.8 | 1028.7 | 1042.1 | 1055.5 | 1049.4 | 1043.2 | 1019.2 |
| 972.0  | 62.5° | 956.3  | 942.4  | 956.3  | 972.0  | 987.8  | 999.9  | 1012.1 | 1006.1 | 1000.2 | 978.2  |
| 914.7  | 65°   | 899.5  | 887.5  | 899.5  | 914.7  | 930.0  | 941.7  | 953.4  | 947.3  | 941.2  | 921.9  |
| 850.8  | 67.5° | 836.6  | 825.7  | 836.6  | 850.8  | 865.0  | 875.6  | 886.4  | 880.5  | 874.6  | 857.9  |
| 783.7  | 70°   | 770.1  | 757.8  | 770.1  | 783.7  | 797.3  | 806.0  | 814.8  | 809.1  | 803.3  | 788.3  |
| 708.5  | 72.5° | 695.6  | 683.6  | 695.6  | 708.5  | 721.5  | 728.7  | 736.0  | 729.2  | 722.4  | 707.6  |
| 624.1  | 75°   | 613.2  | 601.7  | 613.2  | 624.1  | 634.9  | 638.5  | 642.1  | 634.9  | 627.8  | 614.4  |
| 529.9  | 77.5° | 518.9  | 509.8  | 518.9  | 529.9  | 540.9  | 546.0  | 550.9  | 544.3  | 537.6  | 523.6  |
| 429.0  | 80°   | 414.2  | 397.0  | 414.2  | 429.0  | 443.8  | 445.9  | 448.0  | 439.2  | 430.4  | 419.7  |
| 320.1  | 82.5° | 307.6  | 296.6  | 307.6  | 320.1  | 332.5  | 333.5  | 334.5  | 319.5  | 304.5  | 281.6  |
| 199.6  | 85°   | 189.9  | 180.0  | 189.9  | 199.6  | 209.3  | 210.9  | 212.4  | 193.9  | 175.3  | 153.9  |
| 83.3   | 87.5° | 78.2   | 73.4   | 78.2   | 83.3   | 88.2   | 90.2   | 92.1   | 84.6   | 77.1   | 68.1   |
| 0.0    | 90°   | 0.0    | 0.0    | 0.0    | 0.0    | 0.0    | 0.0    | 0.0    | 0.0    | 0.0    | 0.0    |

REPORT NUMBER: P948200

CATALOG NUMBER: GLAN-SB3B-827-U-SLL

**CANDELA DISTRIBUTION (continued):**

| 270°   |       | 275°   | 280°   | 285°   | 290°   | 295°   | 300°   | 305°   | 310°   | 315°   | 320°   |
|--------|-------|--------|--------|--------|--------|--------|--------|--------|--------|--------|--------|
| 2013.0 | 0°    | 2013.0 | 2013.0 | 2013.0 | 2013.0 | 2013.0 | 2013.0 | 2013.0 | 2013.0 | 2013.0 | 2013.0 |
| 1889.0 | 2.5°  | 1900.7 | 1912.4 | 1924.1 | 1935.7 | 1949.0 | 1962.4 | 1977.1 | 1992.0 | 2010.3 | 2026.7 |
| 1792.5 | 5°    | 1811.3 | 1830.1 | 1850.8 | 1871.5 | 1894.9 | 1918.4 | 1946.4 | 1974.4 | 2006.4 | 2038.9 |
| 1733.8 | 7.5°  | 1756.7 | 1779.7 | 1805.8 | 1831.9 | 1862.7 | 1893.6 | 1930.8 | 1968.0 | 2009.5 | 2053.8 |
| 1722.9 | 10°   | 1748.8 | 1774.7 | 1802.8 | 1830.8 | 1861.7 | 1892.6 | 1931.9 | 1971.1 | 2015.7 | 2070.3 |
| 1772.4 | 12.5° | 1799.1 | 1825.9 | 1847.8 | 1869.9 | 1890.3 | 1910.9 | 1942.9 | 1975.0 | 2016.5 | 2073.9 |
| 1875.5 | 15°   | 1898.7 | 1922.0 | 1927.7 | 1933.4 | 1930.6 | 1927.9 | 1943.2 | 1958.5 | 1991.7 | 2055.3 |
| 1985.2 | 17.5° | 2003.9 | 2022.6 | 2004.8 | 1986.9 | 1953.2 | 1919.5 | 1914.0 | 1908.3 | 1928.8 | 2003.6 |
| 2053.5 | 20°   | 2062.3 | 2070.9 | 2033.5 | 1996.0 | 1937.4 | 1879.0 | 1852.7 | 1826.4 | 1831.9 | 1918.9 |
| 2052.8 | 22.5° | 2047.6 | 2042.3 | 1993.6 | 1944.9 | 1878.0 | 1811.2 | 1772.4 | 1733.5 | 1722.9 | 1822.0 |
| 1984.8 | 25°   | 1967.0 | 1949.0 | 1901.1 | 1853.1 | 1793.0 | 1733.0 | 1688.2 | 1643.4 | 1614.8 | 1716.4 |
| 1866.6 | 27.5° | 1846.6 | 1826.7 | 1788.2 | 1749.7 | 1700.5 | 1651.1 | 1607.8 | 1564.6 | 1529.8 | 1622.3 |
| 1742.2 | 30°   | 1726.0 | 1709.8 | 1677.8 | 1645.9 | 1605.0 | 1564.0 | 1529.6 | 1495.3 | 1468.0 | 1545.7 |
| 1638.0 | 32.5° | 1619.9 | 1601.9 | 1571.2 | 1540.6 | 1507.9 | 1475.2 | 1454.9 | 1434.6 | 1422.5 | 1485.0 |
| 1542.2 | 35°   | 1520.6 | 1498.9 | 1468.6 | 1438.3 | 1413.4 | 1388.5 | 1382.8 | 1377.3 | 1382.3 | 1434.4 |
| 1454.5 | 37.5° | 1427.8 | 1401.1 | 1370.8 | 1340.6 | 1322.7 | 1304.8 | 1311.0 | 1317.2 | 1335.6 | 1381.1 |
| 1369.2 | 40°   | 1338.3 | 1307.6 | 1278.4 | 1249.2 | 1236.3 | 1223.4 | 1237.4 | 1251.4 | 1279.6 | 1320.9 |
| 1287.3 | 42.5° | 1254.1 | 1220.8 | 1193.1 | 1165.5 | 1154.9 | 1144.4 | 1162.9 | 1181.5 | 1217.0 | 1255.1 |
| 1215.1 | 45°   | 1180.6 | 1146.2 | 1119.9 | 1093.6 | 1084.7 | 1075.9 | 1093.9 | 1111.9 | 1146.3 | 1184.9 |
| 1155.6 | 47.5° | 1121.6 | 1087.6 | 1062.0 | 1036.2 | 1028.0 | 1019.6 | 1034.8 | 1049.9 | 1079.5 | 1129.3 |
| 1103.8 | 50°   | 1073.4 | 1043.0 | 1018.8 | 994.5  | 981.5  | 968.5  | 981.9  | 995.3  | 1029.7 | 1095.2 |
| 1068.3 | 52.5° | 1039.9 | 1011.5 | 989.3  | 967.1  | 947.6  | 928.1  | 941.3  | 954.6  | 1002.6 | 1077.9 |
| 1044.0 | 55°   | 1019.2 | 994.3  | 970.3  | 946.4  | 918.7  | 891.0  | 911.9  | 933.0  | 1005.3 | 1075.4 |
| 1023.9 | 57.5° | 999.2  | 974.7  | 946.6  | 918.4  | 888.6  | 858.8  | 889.4  | 920.0  | 1008.0 | 1069.8 |
| 995.3  | 60°   | 970.3  | 945.3  | 913.0  | 880.7  | 854.6  | 828.4  | 868.1  | 907.8  | 999.5  | 1040.3 |
| 956.3  | 62.5° | 929.6  | 903.0  | 865.3  | 827.7  | 811.1  | 794.5  | 844.0  | 893.6  | 978.7  | 983.7  |
| 902.6  | 65°   | 877.1  | 851.6  | 811.2  | 770.9  | 764.6  | 758.2  | 810.9  | 863.6  | 928.5  | 927.9  |
| 841.2  | 67.5° | 817.1  | 792.9  | 755.6  | 718.4  | 720.4  | 722.4  | 766.3  | 810.1  | 846.6  | 848.3  |
| 773.2  | 70°   | 752.4  | 731.5  | 698.8  | 666.0  | 673.0  | 679.9  | 711.1  | 742.3  | 754.3  | 754.3  |
| 692.9  | 72.5° | 674.0  | 655.2  | 629.5  | 603.7  | 613.8  | 624.0  | 645.4  | 666.8  | 666.6  | 659.0  |
| 601.0  | 75°   | 583.9  | 566.8  | 547.7  | 528.5  | 538.3  | 548.0  | 564.6  | 581.0  | 584.0  | 549.1  |
| 509.4  | 77.5° | 494.8  | 480.1  | 464.5  | 448.9  | 458.8  | 468.7  | 481.9  | 495.1  | 496.7  | 439.1  |
| 409.0  | 80°   | 396.6  | 384.3  | 371.4  | 358.4  | 366.8  | 375.0  | 386.1  | 397.2  | 397.4  | 328.7  |
| 258.8  | 82.5° | 263.1  | 267.4  | 268.5  | 269.6  | 275.5  | 281.3  | 286.7  | 292.1  | 288.9  | 230.2  |
| 132.5  | 85°   | 144.4  | 156.4  | 162.1  | 167.6  | 174.2  | 180.8  | 186.5  | 192.3  | 188.1  | 144.4  |
| 59.1   | 87.5° | 68.3   | 77.4   | 77.6   | 77.9   | 79.1   | 80.3   | 82.7   | 85.0   | 79.6   | 61.4   |
| 0.0    | 90°   | 0.0    | 0.0    | 0.0    | 0.0    | 0.0    | 0.0    | 0.0    | 0.0    | 0.0    | 0.0    |

REPORT NUMBER: P948200

CATALOG NUMBER: GLAN-SB3B-827-U-SLL

**CANDELA DISTRIBUTION (continued):**

| 325°   |       | 330°   | 335°   | 340°   | 345°   | 350°   | 355°   | 360°   |
|--------|-------|--------|--------|--------|--------|--------|--------|--------|
| 2013.0 | 0°    | 2013.0 | 2013.0 | 2013.0 | 2013.0 | 2013.0 | 2013.0 | 2013.0 |
| 2043.7 | 2.5°  | 2060.7 | 2078.5 | 2096.3 | 2113.9 | 2131.6 | 2148.2 | 2164.8 |
| 2073.2 | 5°    | 2107.6 | 2144.4 | 2181.2 | 2217.8 | 2254.4 | 2291.1 | 2327.8 |
| 2101.7 | 7.5°  | 2149.7 | 2204.2 | 2258.6 | 2314.6 | 2370.5 | 2431.0 | 2491.5 |
| 2127.2 | 10°   | 2183.9 | 2250.1 | 2316.2 | 2390.0 | 2463.9 | 2540.5 | 2617.0 |
| 2138.0 | 12.5° | 2202.2 | 2280.3 | 2358.3 | 2442.0 | 2525.7 | 2609.8 | 2693.9 |
| 2129.6 | 15°   | 2203.9 | 2293.8 | 2383.6 | 2474.4 | 2565.3 | 2653.0 | 2740.6 |
| 2092.9 | 17.5° | 2182.3 | 2286.6 | 2390.9 | 2490.0 | 2589.1 | 2678.0 | 2766.9 |
| 2029.7 | 20°   | 2140.4 | 2266.8 | 2393.2 | 2502.1 | 2611.0 | 2703.5 | 2795.9 |
| 1955.4 | 22.5° | 2088.8 | 2242.6 | 2396.3 | 2518.5 | 2640.6 | 2735.1 | 2829.5 |
| 1872.6 | 25°   | 2028.8 | 2218.6 | 2408.5 | 2548.1 | 2687.7 | 2780.2 | 2872.7 |
| 1796.8 | 27.5° | 1971.3 | 2202.6 | 2434.0 | 2594.5 | 2754.9 | 2843.2 | 2931.4 |
| 1733.4 | 30°   | 1921.2 | 2195.1 | 2468.9 | 2654.5 | 2840.1 | 2925.3 | 3010.6 |
| 1678.8 | 32.5° | 1872.6 | 2185.9 | 2499.0 | 2717.1 | 2935.3 | 3019.6 | 3104.1 |
| 1625.1 | 35°   | 1815.9 | 2168.4 | 2521.1 | 2788.5 | 3055.9 | 3136.8 | 3217.6 |
| 1562.0 | 37.5° | 1742.8 | 2138.5 | 2534.2 | 2868.5 | 3202.7 | 3305.8 | 3408.8 |
| 1486.6 | 40°   | 1652.3 | 2097.3 | 2542.5 | 2970.0 | 3397.4 | 3547.5 | 3697.7 |
| 1403.4 | 42.5° | 1551.7 | 2054.9 | 2558.2 | 3102.8 | 3647.3 | 3864.1 | 4080.8 |
| 1315.0 | 45°   | 1445.1 | 2015.4 | 2585.8 | 3277.5 | 3969.2 | 4261.6 | 4553.9 |
| 1245.1 | 47.5° | 1360.9 | 1982.8 | 2604.7 | 3463.6 | 4322.6 | 4734.2 | 5145.6 |
| 1198.7 | 50°   | 1302.2 | 1947.3 | 2592.3 | 3636.4 | 4680.4 | 5300.8 | 5921.2 |
| 1168.1 | 52.5° | 1258.3 | 1887.2 | 2516.2 | 3748.5 | 4980.7 | 5896.1 | 6811.4 |
| 1145.9 | 55°   | 1216.4 | 1787.7 | 2359.0 | 3723.8 | 5088.5 | 6423.8 | 7759.2 |
| 1119.7 | 57.5° | 1169.5 | 1647.5 | 2125.4 | 3549.8 | 4974.4 | 6797.8 | 8621.2 |
| 1079.5 | 60°   | 1118.7 | 1465.3 | 1812.0 | 3226.1 | 4640.2 | 6891.3 | 9142.3 |
| 1009.7 | 62.5° | 1035.7 | 1247.3 | 1459.0 | 2788.4 | 4117.7 | 6497.7 | 8877.7 |
| 940.1  | 65°   | 952.4  | 1051.2 | 1150.0 | 2341.7 | 3533.5 | 5940.9 | 8348.2 |
| 841.5  | 67.5° | 834.6  | 862.7  | 890.8  | 1904.2 | 2917.7 | 5278.2 | 7638.7 |
| 722.5  | 70°   | 690.7  | 682.8  | 674.7  | 1499.3 | 2323.9 | 4555.1 | 6786.3 |
| 614.0  | 72.5° | 568.9  | 544.7  | 520.5  | 1146.2 | 1772.0 | 3771.2 | 5770.5 |
| 498.5  | 75°   | 448.0  | 426.1  | 404.1  | 831.9  | 1259.7 | 2872.6 | 4485.6 |
| 390.1  | 77.5° | 341.0  | 326.0  | 311.1  | 563.7  | 816.3  | 2010.6 | 3204.9 |
| 287.2  | 80°   | 245.6  | 239.5  | 233.3  | 363.2  | 493.2  | 1295.4 | 2097.6 |
| 199.6  | 82.5° | 169.0  | 167.8  | 166.7  | 223.4  | 280.2  | 749.7  | 1219.3 |
| 122.0  | 85°   | 99.6   | 100.3  | 100.8  | 119.4  | 138.1  | 337.2  | 536.5  |
| 52.2   | 87.5° | 43.1   | 43.6   | 44.2   | 49.5   | 54.8   | 110.5  | 166.1  |
| 0.0    | 90°   | 0.0    | 0.0    | 0.0    | 0.0    | 0.0    | 0.0    | 0.0    |

(END OF REPORT)