

Scaled data based on original data using
LM-79-08 Approved Method: Electrical and Photometric Measurements of Solid-
State Lighting Products

Test Report Prepared for
Cooper Lighting Solutions
(formerly Eaton)

Brand: STREETWORKS

Report Number: P953661

Luminaire Tested: **GLAN-SB7A-927-U-SLR-HSS**

Issue Date: 1/21/2025

Test Information

Test Method: LM-79-08
Report Number: P953661
TEST IS SCALED FROM IESNA LM-79-08 TEST DATA (G2-2411-289-9)
Test Lab: INNOVATION CENTER
Issue Date: 1/21/2025
Manufacturer: COOPER LIGHTING SOLUTIONS (FORMERLY EATON)
Product Line: STREETWORKS
Catalog Number: GLAN-SB7A-927-U-SLR-HSS
Description: GALLEON AREA AND ROADWAY HIGH DENSITY LED LUMINAIRE
(7) 90 CRI, 2700K, 350mA LIGHTSQUARES WITH 26 LEDS EACH AND SPILL LIGHT
ELIMINATOR RIGHT OPTICS WITH HOUSE SIDE SHIELD
Light Source: -
Ballast/Driver: -

Summary

Lumens per Lamp: N/A
Luminaire Lumens: 14820 lumens
Efficiency: N/A
Efficacy: 74.4 lumens/watt
Luminous Opening: Rectangular (W 1.5' x L: 1.5' x H: 0')
IES Classification: Type IV - Short
BUG Rating: B2 - U0 - G3

Input Watts (W): 199.1
Input Voltage (V): NR
Input Current (Ain): NR
Voltage Rise (V): NR
Power Factor: NR
Total Harmonic Distortion (THDi): NR
Frequency (hertz): 60
Stabilization Time: NR
Operation Time: NR
Ambient Temperature (°C): NR
Test Distance: 24 FT




REPORT NUMBER: P953661

CATALOG NUMBER: GLAN-SB7A-927-U-SLR-HSS

Iso-Footcandle Lines of Horizontal Illumination

× Max cd

--- 1/2 Max cd




Based on 25 foot mounting height. Maximum calculated value = 4.6 fc

Type IV - Short - N/A

REPORT NUMBER: P953661
CATALOG NUMBER: GLAN-SB7A-927-U-SLR-HSS

Luminous Intensity Polar Plot



REPORT NUMBER: P953661

CATALOG NUMBER: GLAN-SB7A-927-U-SLR-HSS


FLUX DISTRIBUTION:

		Downward	Upward	Total
House Side	Lumens	2075.4	0.0	2075.4
	% Fixture	14.0	0.0	14.0
Street Side	Lumens	12744.6	0.0	12744.6
	% Fixture	86.0	0.0	86.0
Total	Lumens	14820.0	0.0	14820.0
	% Fixture	100.0	0.0	100.0

ZONAL LUMENS:

Zone	Lumens	% Fixture
0°-10°	202.0	1.4
10°-20°	605.6	4.1
20°-30°	892.2	6.0
30°-40°	1146.3	7.7
40°-50°	1853.9	12.5
50°-60°	3250.9	21.9
60°-70°	4067.8	27.4
70°-80°	2377.0	16.0
80°-90°	424.1	2.9
90°-100°	0.0	0.0
100°-110°	0.0	0.0
110°-120°	0.0	0.0
120°-130°	0.0	0.0
130°-140°	0.0	0.0
140°-150°	0.0	0.0
150°-160°	0.0	0.0
160°-170°	0.0	0.0
170°-180°	0.0	0.0
0°-90°	14820.0	100.0
0°-180°	14820.0	100.0

Coefficient of Utilization



REPORT NUMBER: P953661


CATALOG NUMBER: GLAN-SB7A-927-U-SLR-HSS

LUMINAIRE CLASSIFICATION SYSTEM LUMEN TABLE AND BUG RATING:

Zone		Lumens	% Fixture	Zone Rating/Lumen Limit		
				B	U	G
FL	(0°-30°)	1155.9	7.8			
FM	(30°-60°)	5194.2	35.0			
FH	(60°-80°)	5986.6	40.4			G3/7500
FVH	(80°-90°)	407.8	2.8			G3/500
BL	(0°-30°)	544.0	3.7	B2/1000		
BM	(30°-60°)	1056.9	7.1	B2/2500		
BH	(60°-80°)	458.3	3.1	B1/500		G1/500
BVH	(80°-90°)	16.3	0.1			G1/100
UL	(90°-100°)	0.0	0.0		U0/0	
UH	(100°-180°)	0.0	0.0		U0/0	

BUG Rating: B2-U0-G3

Type IV Short



REPORT NUMBER: P953661

CATALOG NUMBER: GLAN-SB7A-927-U-SLR-HSS

CANDELA DISTRIBUTION (FULL):

	0°	5°	15°	25°	35°	45°	55°	65°	75°	85°
0°	2052.1	2052.1	2052.1	2052.1	2052.1	2052.1	2052.1	2052.1	2052.1	2052.1
2.5°	2318.6	2278.7	2255.3	2197.1	2138.9	2091.9	2028.6	1986.8	1936.7	1888.7
5°	2584.0	2519.7	2442.1	2335.9	2238.9	2139.9	2043.9	1949.0	1848.9	1757.0
7.5°	2808.6	2715.7	2578.9	2438.0	2314.5	2195.0	2082.7	1957.1	1835.7	1691.7
10°	2980.1	2861.7	2682.0	2497.2	2355.3	2234.8	2125.6	2019.4	1896.9	1723.4
12.5°	3084.3	2957.7	2744.3	2527.9	2365.5	2230.8	2146.0	2099.1	2051.1	1878.5
15°	3160.8	3024.0	2788.2	2549.3	2342.0	2176.7	2114.4	2161.3	2216.5	2106.2
17.5°	3240.5	3096.5	2845.4	2558.5	2278.7	2071.5	2044.9	2166.4	2294.1	2289.0
20°	3316.0	3173.1	2895.4	2552.4	2176.7	1943.9	1967.4	2122.5	2270.6	2332.9
22.5°	3402.8	3251.7	2943.4	2528.9	2043.9	1824.4	1897.9	2053.1	2182.8	2256.3
25°	3509.0	3350.7	3010.8	2494.2	1901.0	1725.4	1827.5	1972.5	2077.6	2128.7
27.5°	3623.3	3469.2	3100.6	2475.8	1785.6	1654.9	1747.9	1876.5	1970.4	2006.2
30°	3765.2	3607.0	3206.8	2455.4	1710.1	1614.1	1665.2	1765.2	1857.1	1892.8
32.5°	3920.4	3760.1	3308.9	2406.4	1664.1	1583.5	1584.5	1647.8	1731.5	1774.4
35°	4114.4	3943.9	3418.1	2299.2	1627.4	1547.7	1505.9	1536.5	1605.9	1657.0
37.5°	4391.1	4184.8	3551.9	2146.0	1573.3	1492.6	1423.2	1430.3	1483.4	1539.6
40°	4772.9	4508.5	3709.1	1986.8	1495.7	1415.0	1332.3	1329.3	1368.1	1423.2
42.5°	5289.5	4936.3	3898.0	1834.6	1421.2	1321.1	1236.4	1231.3	1261.9	1309.9
45°	5971.5	5483.5	4129.7	1704.0	1363.0	1229.2	1145.5	1143.5	1169.0	1210.8
47.5°	6844.4	6244.1	4361.5	1615.1	1332.3	1156.7	1071.0	1075.1	1097.5	1135.3
50°	7974.6	7235.4	4431.9	1570.2	1332.3	1117.9	1004.6	1025.0	1043.4	1072.0
52.5°	9329.4	8186.9	4199.1	1529.4	1340.5	1123.0	948.5	992.4	1005.6	1030.1
55°	10585.1	8653.5	3610.1	1473.2	1342.5	1154.7	900.5	965.8	990.3	999.5
57.5°	11314.1	8493.2	2918.9	1378.3	1334.4	1176.1	869.8	933.1	980.1	986.2
60°	11175.2	7930.7	2149.1	1305.8	1274.1	1168.0	860.7	883.1	957.6	966.8
62.5°	10105.3	6987.3	1491.6	1249.6	1141.4	1132.2	857.6	804.5	908.6	931.1
65°	8122.6	5500.8	1053.6	1076.1	1000.5	1054.6	841.3	722.8	849.4	880.1
67.5°	5892.9	3722.4	760.6	871.9	906.6	929.1	804.5	663.6	782.0	822.9
70°	3781.6	2010.2	534.0	575.8	763.7	789.2	741.2	610.5	713.6	760.6
72.5°	2688.1	1187.4	383.9	403.3	613.6	657.5	652.4	551.3	634.0	691.2
75°	1855.1	654.4	259.3	287.9	445.1	534.0	503.3	473.7	537.0	595.2
77.5°	1162.9	293.0	155.2	200.1	292.0	419.6	345.1	366.5	418.6	472.7
80°	647.3	113.3	86.8	132.7	159.3	305.3	190.9	235.8	308.3	347.1
82.5°	140.9	14.3	38.8	57.2	62.3	177.6	101.1	136.8	194.0	190.9
85°	0.0	0.0	7.1	8.2	4.1	76.6	36.8	44.9	63.3	59.2
87.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	2.0
90°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0

REPORT NUMBER: P953661

CATALOG NUMBER: GLAN-SB7A-927-U-SLR-HSS

CANDELA DISTRIBUTION (continued):

90°		95°	105°	115°	125°	135°	145°	155°	165°	175°	180°
2052.1	0°	2052.1	2052.1	2052.1	2052.1	2052.1	2052.1	2052.1	2052.1	2052.1	2052.1
1845.9	2.5°	1837.7	1787.7	1750.9	1732.5	1717.2	1731.5	1739.7	1739.7	1774.4	1794.8
1700.9	5°	1665.2	1575.3	1506.9	1461.0	1433.4	1442.6	1452.8	1464.0	1507.9	1537.5
1615.1	7.5°	1545.7	1407.9	1303.7	1239.4	1205.7	1210.8	1218.0	1227.2	1270.1	1299.7
1627.4	10°	1523.2	1325.2	1178.2	1093.4	1052.6	1045.4	1041.4	1038.3	1063.8	1086.3
1766.2	12.5°	1615.1	1329.3	1124.1	1020.9	970.9	949.5	925.0	905.6	909.7	924.0
1976.5	15°	1779.5	1381.3	1106.7	983.2	920.9	885.2	856.6	833.1	828.0	833.1
2160.3	17.5°	1967.4	1451.8	1104.7	950.5	872.9	836.2	812.7	791.2	784.1	785.1
2263.4	20°	2091.9	1507.9	1098.5	913.7	827.0	794.3	773.9	752.4	745.3	747.3
2234.8	22.5°	2104.2	1537.5	1089.3	872.9	781.0	753.5	733.0	713.6	712.6	712.6
2127.6	25°	2037.8	1537.5	1069.9	836.2	737.1	712.6	694.2	670.8	674.8	676.9
2006.2	27.5°	1934.7	1500.8	1033.2	806.5	699.3	673.8	655.4	634.0	639.1	642.2
1892.8	30°	1832.6	1453.8	989.3	772.9	663.6	634.0	620.7	602.4	604.4	608.5
1780.5	32.5°	1737.6	1403.8	937.2	745.3	627.9	598.3	588.1	567.6	570.7	574.8
1670.3	35°	1643.7	1348.7	876.0	712.6	595.2	565.6	557.4	534.0	536.0	542.1
1560.0	37.5°	1542.6	1290.5	825.9	679.9	563.6	532.9	524.8	500.3	502.3	509.5
1445.7	40°	1436.5	1233.3	776.9	645.2	529.9	499.2	492.1	465.6	467.6	475.8
1333.4	42.5°	1329.3	1171.0	739.2	600.3	495.2	462.5	455.3	430.8	433.9	443.1
1235.3	45°	1230.2	1096.5	714.7	550.3	462.5	425.7	418.6	396.1	402.3	412.5
1152.6	47.5°	1145.5	1019.9	704.5	508.4	427.8	388.0	381.8	363.5	373.7	384.9
1082.2	50°	1073.0	946.4	691.2	465.6	395.1	355.3	349.2	336.9	350.2	361.4
1034.2	52.5°	1020.9	862.7	662.6	426.8	366.5	327.7	325.7	319.6	331.8	342.0
998.5	55°	976.0	775.9	616.6	393.1	341.0	304.2	306.3	303.2	313.4	321.6
977.0	57.5°	935.2	700.4	558.5	366.5	313.4	283.8	289.9	285.9	291.0	296.1
954.6	60°	886.2	623.8	489.0	336.9	280.8	263.4	270.5	259.3	258.3	260.3
913.7	62.5°	813.7	520.7	416.5	300.2	252.2	240.9	244.0	222.6	206.2	206.2
853.5	65°	712.6	418.6	349.2	259.3	219.5	210.3	208.3	177.6	155.2	153.1
788.2	67.5°	595.2	344.1	289.9	218.5	182.7	176.6	178.7	156.2	133.7	131.7
722.8	70°	484.9	284.8	233.8	174.6	140.9	147.0	156.2	133.7	112.3	109.2
646.3	72.5°	394.1	226.6	182.7	133.7	104.1	121.5	132.7	109.2	88.8	86.8
551.3	75°	304.2	166.4	130.7	90.9	75.5	93.9	104.1	79.6	63.3	60.2
426.8	77.5°	203.2	103.1	73.5	57.2	44.9	64.3	69.4	41.9	36.8	35.7
310.4	80°	123.5	48.0	31.6	27.6	15.3	23.5	27.6	17.4	19.4	20.4
165.4	82.5°	62.3	13.3	5.1	1.0	0.0	0.0	8.2	4.1	8.2	10.2
44.9	85°	5.1	0.0	0.0	0.0	0.0	0.0	0.0	0.0	2.0	5.1
0.0	87.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
0.0	90°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0

REPORT NUMBER: P953661

CATALOG NUMBER: GLAN-SB7A-927-U-SLR-HSS

CANDELA DISTRIBUTION (continued):

185°		195°	205°	215°	225°	235°	245°	255°	265°	270°	275°
2052.1	0°	2052.1	2052.1	2052.1	2052.1	2052.1	2052.1	2052.1	2052.1	2052.1	2052.1
1803.0	2.5°	1860.2	1903.0	1943.9	2009.2	2076.6	2143.0	2210.3	2275.7	2299.2	2316.5
1556.9	5°	1645.8	1726.4	1820.3	1950.0	2088.8	2231.8	2376.8	2509.5	2569.7	2610.6
1325.2	7.5°	1424.2	1529.4	1664.1	1859.1	2076.6	2304.3	2531.9	2741.2	2838.2	2916.8
1106.7	10°	1204.7	1319.1	1489.6	1712.1	2006.2	2332.9	2647.3	2935.2	3060.8	3159.8
949.5	12.5°	1011.8	1119.0	1297.6	1543.7	1895.9	2310.4	2713.7	3059.8	3207.8	3319.1
837.2	15°	876.0	951.5	1109.8	1375.2	1765.2	2237.9	2717.8	3119.0	3281.3	3397.7
790.2	17.5°	800.4	825.9	929.1	1203.7	1620.2	2143.0	2680.0	3139.4	3313.0	3421.2
748.4	20°	759.6	763.7	792.3	981.1	1434.4	2054.1	2644.2	3159.8	3342.6	3433.4
718.7	22.5°	726.9	726.9	734.1	802.5	1194.5	1948.0	2633.0	3195.6	3383.4	3439.6
685.1	25°	697.3	697.3	699.3	717.7	946.4	1785.6	2625.9	3250.7	3439.6	3454.9
651.4	27.5°	666.7	667.7	667.7	677.9	762.6	1565.1	2595.2	3322.1	3506.9	3475.3
618.7	30°	636.0	638.1	638.1	645.2	674.8	1306.8	2535.0	3407.9	3594.7	3501.8
586.0	32.5°	605.4	607.5	607.5	613.6	635.0	1043.4	2459.5	3486.5	3683.6	3513.1
554.4	35°	573.8	576.8	574.8	583.0	605.4	830.0	2363.5	3565.1	3779.5	3548.8
523.7	37.5°	542.1	544.2	543.1	551.3	576.8	716.7	2252.2	3624.3	3910.2	3628.4
491.1	40°	510.5	509.5	509.5	518.6	546.2	684.0	2112.3	3718.3	4098.1	3768.3
458.4	42.5°	477.8	477.8	475.8	486.0	519.7	659.5	1978.6	3886.7	4371.7	3990.9
427.8	45°	448.2	447.2	443.1	452.3	494.1	616.6	1931.6	4201.2	4776.0	4351.3
397.1	47.5°	419.6	418.6	408.4	416.5	463.5	577.9	2107.2	4715.7	5336.5	4881.1
372.6	50°	394.1	395.1	375.7	382.9	432.9	548.2	2488.0	5383.4	6080.7	5594.8
352.2	52.5°	370.6	370.6	345.1	349.2	395.1	521.7	2850.5	6107.3	7062.9	6590.2
330.8	55°	347.1	345.1	316.5	318.5	357.3	483.9	2904.6	6813.8	8402.4	8087.9
307.3	57.5°	320.6	316.5	289.9	289.9	322.6	456.4	2517.6	7356.9	10064.5	10289.1
263.4	60°	287.9	284.8	267.5	262.4	295.1	480.9	1776.4	7420.2	11136.4	13216.1
209.3	62.5°	246.0	250.1	240.9	233.8	268.5	499.2	1052.6	6910.8	10877.1	14147.2
162.3	65°	194.0	210.3	208.3	203.2	295.1	420.6	621.8	5932.7	10081.8	13395.8
141.9	67.5°	165.4	176.6	173.6	173.6	309.3	319.6	391.0	4635.1	8987.4	12504.5
118.4	70°	140.9	152.1	140.9	140.9	233.8	194.0	270.5	3236.4	7806.1	11518.3
94.9	72.5°	116.4	127.6	115.4	107.2	186.8	145.0	198.1	2022.5	6685.1	10491.2
67.4	75°	88.8	102.1	92.9	82.7	123.5	108.2	150.1	1175.1	5538.6	8976.1
40.8	77.5°	56.2	73.5	69.4	58.2	90.9	78.6	108.2	699.3	4273.7	7013.9
24.5	80°	34.7	37.8	38.8	36.8	52.1	53.1	73.5	398.2	2925.0	4888.3
15.3	82.5°	22.5	22.5	17.4	19.4	25.5	30.6	41.9	150.1	1719.3	2976.0
9.2	85°	16.3	14.3	9.2	9.2	12.3	15.3	16.3	45.9	697.3	1175.1
4.1	87.5°	8.2	7.1	3.1	4.1	6.1	5.1	4.1	2.0	175.6	375.7
0.0	90°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0

REPORT NUMBER: P953661

CATALOG NUMBER: GLAN-SB7A-927-U-SLR-HSS

CANDELA DISTRIBUTION (continued):

285°		295°	305°	315°	325°	335°	345°	355°	360°
2052.1	0°	2052.1	2052.1	2052.1	2052.1	2052.1	2052.1	2052.1	2052.1
2355.3	2.5°	2375.7	2407.4	2409.4	2409.4	2381.9	2380.8	2324.7	2318.6
2702.4	5°	2797.4	2817.8	2822.9	2812.7	2757.6	2716.7	2607.5	2584.0
3056.7	7.5°	3183.3	3224.1	3224.1	3199.6	3109.8	3026.1	2867.8	2808.6
3349.7	10°	3491.6	3538.6	3528.4	3478.4	3365.0	3249.7	3057.7	2980.1
3527.4	12.5°	3641.7	3689.7	3663.1	3606.0	3495.7	3374.2	3172.1	3084.3
3578.4	15°	3638.6	3625.4	3597.8	3590.7	3537.6	3445.7	3256.8	3160.8
3546.8	17.5°	3509.0	3396.7	3375.2	3446.7	3514.1	3491.6	3330.3	3240.5
3471.2	20°	3303.8	3107.8	3088.4	3225.2	3417.1	3515.1	3398.7	3316.0
3362.0	22.5°	3087.3	2876.0	2831.1	2982.2	3271.1	3522.3	3485.5	3402.8
3241.5	25°	2882.1	2669.8	2624.8	2765.7	3108.8	3510.0	3579.4	3509.0
3126.1	27.5°	2710.6	2505.4	2463.5	2604.4	2952.6	3475.3	3673.4	3623.3
3011.8	30°	2577.9	2388.0	2357.4	2493.1	2817.8	3432.4	3792.8	3765.2
2905.6	32.5°	2500.3	2361.4	2372.7	2484.0	2745.3	3385.4	3907.1	3920.4
2853.5	35°	2576.9	2583.0	2681.0	2726.9	2812.7	3378.3	4062.3	4114.4
2915.8	37.5°	2957.7	3170.0	3373.2	3335.4	3142.5	3461.0	4294.1	4391.1
3187.4	40°	3606.0	4041.9	4371.7	4227.7	3741.8	3714.2	4627.9	4772.9
3669.3	42.5°	4398.2	5137.4	5680.5	5294.6	4514.6	4157.3	5104.7	5289.5
4252.2	45°	5234.4	6488.1	7343.6	6541.2	5338.5	4778.0	5826.5	5971.5
4798.4	47.5°	6115.4	8129.8	9236.5	7923.5	6102.2	5484.5	6810.7	6844.4
5316.1	50°	7079.2	9929.7	11166.1	9304.9	6839.3	6294.1	8013.4	7974.6
5919.4	52.5°	7997.0	11780.7	13054.8	10692.3	7486.6	7298.7	9409.0	9329.4
6744.4	55°	8873.0	13630.6	14954.8	12025.7	8097.1	8625.9	11067.0	10585.1
7933.7	57.5°	9888.9	15293.7	16912.9	13365.2	8950.6	10349.3	12921.1	11314.1
10211.5	60°	11390.7	17183.5	19127.4	15200.8	10573.9	12160.5	13585.7	11175.2
12939.4	62.5°	13308.0	18921.1	20737.4	16999.7	12204.4	12501.4	12606.6	10105.3
12383.0	65°	13680.6	19361.2	20828.3	17480.6	11994.0	10604.5	10292.1	8122.6
11060.9	67.5°	12692.4	18565.9	19558.2	16585.2	10609.6	8195.1	7723.4	5892.9
10193.1	70°	11583.6	17049.8	17344.8	15063.0	9331.4	6027.6	5216.0	3781.6
9598.9	72.5°	10447.3	15027.3	14416.7	13081.3	8201.2	4389.0	3762.2	2688.1
8752.5	75°	9097.6	12367.7	11356.0	10869.0	6790.3	3444.7	2721.8	1855.1
7528.4	77.5°	7285.5	8705.6	8435.0	8424.8	5102.7	2516.6	1816.3	1162.9
5881.7	80°	5139.4	5649.9	5512.1	6345.2	3423.2	1825.4	1093.4	647.3
4094.0	82.5°	2488.0	3124.1	3206.8	3778.5	1665.2	1074.0	252.2	140.9
1600.8	85°	974.0	1506.9	1271.1	1434.4	467.6	299.1	6.1	0.0
263.4	87.5°	109.2	174.6	160.3	126.6	57.2	12.3	0.0	0.0
0.0	90°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0

(END OF REPORT)