

Scaled data based on original data using
LM-79-08 Approved Method: Electrical and Photometric Measurements of Solid-
State Lighting Products

Test Report Prepared for
Cooper Lighting Solutions
(formerly Eaton)

Brand: STREETWORKS

Report Number: P954291

Luminaire Tested: **GLAN-SB7C-830-U-SLR-HSS**

Issue Date: 1/21/2025

Test Information

Test Method: LM-79-08
Report Number: P954291
TEST IS SCALED FROM IESNA LM-79-08 TEST DATA (G2-2411-289-9)
Test Lab: INNOVATION CENTER
Issue Date: 1/21/2025
Manufacturer: COOPER LIGHTING SOLUTIONS (FORMERLY EATON)
Product Line: STREETWORKS
Catalog Number: GLAN-SB7C-830-U-SLR-HSS
Description: GALLEON AREA AND ROADWAY HIGH DENSITY LED LUMINAIRE
(7) 80 CRI, 3000K, 615mA LIGHTSQUARES WITH 26 LEDS EACH AND SPILL LIGHT
ELIMINATOR RIGHT OPTICS WITH HOUSE SIDE SHIELD
Light Source: -
Ballast/Driver: -


Summary

Lumens per Lamp: N/A
Luminaire Lumens: 36524 lumens
Efficiency: N/A
Efficacy: 104.2 lumens/watt
Luminous Opening: Rectangular (W 1.5' x L: 1.5' x H: 0')
IES Classification: Type IV - Short
BUG Rating: B3 - U0 - G5

Input Watts (W): 350.5
Input Voltage (V): NR
Input Current (Ain): NR
Voltage Rise (V): NR
Power Factor: NR
Total Harmonic Distortion (THDi): NR
Frequency (hertz): 60
Stabilization Time: NR
Operation Time: NR
Ambient Temperature (°C): NR
Test Distance: 24 FT




REPORT NUMBER: P954291
CATALOG NUMBER: GLAN-SB7C-830-U-SLR-HSS



REPORT NUMBER: P954291
CATALOG NUMBER: GLAN-SB7C-830-U-SLR-HSS

Luminous Intensity Polar Plot



REPORT NUMBER: P954291

CATALOG NUMBER: GLAN-SB7C-830-U-SLR-HSS

FLUX DISTRIBUTION:

		Downward	Upward	Total
House Side	Lumens	5114.9	0.0	5114.9
	% Fixture	14.0	0.0	14.0
Street Side	Lumens	31409.1	0.0	31409.1
	% Fixture	86.0	0.0	86.0
Total	Lumens	36524.0	0.0	36524.0
	% Fixture	100.0	0.0	100.0

ZONAL LUMENS:

Zone	Lumens	% Fixture
0°-10°	497.9	1.4
10°-20°	1492.6	4.1
20°-30°	2198.9	6.0
30°-40°	2825.0	7.7
40°-50°	4568.9	12.5
50°-60°	8012.0	21.9
60°-70°	10025.2	27.4
70°-80°	5858.3	16.0
80°-90°	1045.2	2.9
90°-100°	0.0	0.0
100°-110°	0.0	0.0
110°-120°	0.0	0.0
120°-130°	0.0	0.0
130°-140°	0.0	0.0
140°-150°	0.0	0.0
150°-160°	0.0	0.0
160°-170°	0.0	0.0
170°-180°	0.0	0.0
0°-90°	36524.0	100.0
0°-180°	36524.0	100.0

Coefficient of Utilization



REPORT NUMBER: P954291


CATALOG NUMBER: GLAN-SB7C-830-U-SLR-HSS

LUMINAIRE CLASSIFICATION SYSTEM LUMEN TABLE AND BUG RATING:

Zone		Lumens	% Fixture	Zone Rating/Lumen Limit		
				B	U	G
FL	(0°-30°)	2848.7	7.8			
FM	(30°-60°)	12801.3	35.0			
FH	(60°-80°)	14754.0	40.4			G5
FVH	(80°-90°)	1005.1	2.8			G5
BL	(0°-30°)	1340.7	3.7	B3/2500		
BM	(30°-60°)	2604.6	7.1	B3/5000		
BH	(60°-80°)	1129.4	3.1	B3/2500		G3/2500
BVH	(80°-90°)	40.2	0.1			G1/100
UL	(90°-100°)	0.0	0.0		U0/0	
UH	(100°-180°)	0.0	0.0		U0/0	

BUG Rating: B3-U0-G5

Type IV Short



REPORT NUMBER: P954291

CATALOG NUMBER: GLAN-SB7C-830-U-SLR-HSS

CANDELA DISTRIBUTION (FULL):

	0°	5°	15°	25°	35°	45°	55°	65°	75°	85°
0°	5057.4	5057.4	5057.4	5057.4	5057.4	5057.4	5057.4	5057.4	5057.4	5057.4
2.5°	5714.1	5616.0	5558.1	5414.7	5271.3	5155.5	4999.5	4896.4	4773.1	4654.8
5°	6368.3	6209.8	6018.6	5756.9	5517.9	5273.8	5037.3	4803.3	4556.7	4330.2
7.5°	6921.9	6692.9	6355.7	6008.5	5704.0	5409.7	5132.9	4823.4	4524.0	4169.2
10°	7344.6	7052.7	6609.9	6154.4	5804.7	5507.8	5238.6	4976.9	4675.0	4247.2
12.5°	7601.2	7289.2	6763.3	6229.9	5829.9	5497.7	5288.9	5173.1	5054.9	4629.7
15°	7789.9	7452.8	6871.5	6282.8	5772.0	5364.4	5210.9	5326.6	5462.5	5190.8
17.5°	7986.2	7631.4	7012.4	6305.4	5616.0	5105.2	5039.8	5339.2	5653.7	5641.1
20°	8172.4	7820.1	7135.7	6290.3	5364.4	4790.7	4848.6	5231.0	5595.9	5749.3
22.5°	8386.2	8013.8	7254.0	6232.4	5037.3	4496.3	4677.5	5059.9	5379.5	5560.6
25°	8647.9	8257.9	7420.0	6146.9	4685.0	4252.2	4503.9	4861.1	5120.3	5246.1
27.5°	8929.7	8549.8	7641.5	6101.6	4400.7	4078.6	4307.6	4624.6	4856.1	4944.2
30°	9279.5	8889.5	7903.1	6051.3	4214.5	3978.0	4103.8	4350.4	4576.8	4664.9
32.5°	9661.9	9266.9	8154.8	5930.5	4101.3	3902.5	3905.0	4061.0	4267.3	4373.0
35°	10140.0	9719.8	8424.0	5666.3	4010.7	3814.4	3711.3	3786.8	3957.9	4083.7
37.5°	10821.8	10313.6	8753.6	5288.9	3877.3	3678.6	3507.5	3525.1	3655.9	3794.3
40°	11762.9	11111.2	9141.1	4896.4	3686.1	3487.3	3283.5	3276.0	3371.6	3507.5
42.5°	13036.0	12165.5	9606.6	4521.5	3502.4	3255.9	3047.0	3034.4	3109.9	3228.2
45°	14716.8	13514.1	10177.7	4199.4	3359.0	3029.4	2823.1	2818.1	2881.0	2984.1
47.5°	16868.1	15388.6	10748.9	3980.5	3283.5	2850.8	2639.4	2649.5	2704.8	2797.9
50°	19653.4	17831.8	10922.5	3869.8	3283.5	2755.2	2475.9	2526.2	2571.5	2641.9
52.5°	22992.3	20176.8	10348.8	3769.2	3303.7	2767.7	2337.5	2445.7	2478.4	2538.8
55°	26087.2	21326.7	8897.0	3630.8	3308.7	2845.7	2219.2	2380.3	2440.6	2463.3
57.5°	27883.7	20931.6	7193.6	3396.8	3288.6	2898.6	2143.7	2299.7	2415.5	2430.6
60°	27541.5	19545.2	5296.4	3218.1	3140.1	2878.4	2121.1	2176.4	2360.1	2382.8
62.5°	24904.6	17220.3	3676.1	3079.7	2813.0	2790.4	2113.5	1982.7	2239.3	2294.7
65°	20018.3	13556.9	2596.6	2652.0	2465.8	2599.2	2073.3	1781.4	2093.4	2168.9
67.5°	14523.1	9173.8	1874.5	2148.8	2234.3	2289.7	1982.7	1635.5	1927.3	2028.0
70°	9319.7	4954.2	1315.9	1419.1	1882.1	1945.0	1826.7	1504.6	1758.8	1874.5
72.5°	6624.9	2926.2	946.1	993.9	1512.2	1620.4	1607.8	1358.7	1562.5	1703.4
75°	4571.8	1612.8	639.1	709.5	1097.0	1315.9	1240.4	1167.5	1323.5	1466.9
77.5°	2865.9	722.1	382.5	493.2	719.6	1034.1	850.4	903.3	1031.6	1165.0
80°	1595.2	279.3	213.9	327.1	392.5	752.3	470.5	581.2	759.9	855.5
82.5°	347.2	35.2	95.6	140.9	153.5	437.8	249.1	337.2	478.1	470.5
85°	0.0	0.0	17.6	20.1	10.1	188.7	90.6	110.7	156.0	145.9
87.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	5.0
90°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0

REPORT NUMBER: P954291

CATALOG NUMBER: GLAN-SB7C-830-U-SLR-HSS

CANDELA DISTRIBUTION (continued):

90°		95°	105°	115°	125°	135°	145°	155°	165°	175°	180°
5057.4	0°	5057.4	5057.4	5057.4	5057.4	5057.4	5057.4	5057.4	5057.4	5057.4	5057.4
4549.1	2.5°	4529.0	4405.7	4315.1	4269.9	4232.1	4267.3	4287.5	4287.5	4373.0	4423.3
4191.9	5°	4103.8	3882.4	3713.8	3600.6	3532.6	3555.3	3580.4	3608.1	3716.3	3789.3
3980.5	7.5°	3809.4	3469.7	3213.1	3054.6	2971.5	2984.1	3001.7	3024.4	3130.1	3203.0
4010.7	10°	3754.1	3265.9	2903.6	2694.8	2594.1	2576.5	2566.4	2558.9	2621.8	2677.2
4352.9	12.5°	3980.5	3276.0	2770.3	2516.1	2392.8	2340.0	2279.6	2231.8	2241.9	2277.1
4871.2	15°	4385.6	3404.3	2727.5	2423.0	2269.5	2181.5	2111.0	2053.2	2040.6	2053.2
5324.1	17.5°	4848.6	3577.9	2722.4	2342.5	2151.3	2060.7	2002.8	1950.0	1932.4	1934.9
5578.2	20°	5155.5	3716.3	2707.3	2251.9	2038.1	1957.5	1907.2	1854.4	1836.8	1841.8
5507.8	22.5°	5185.7	3789.3	2684.7	2151.3	1924.8	1856.9	1806.6	1758.8	1756.3	1756.3
5243.6	25°	5022.2	3789.3	2636.9	2060.7	1816.6	1756.3	1711.0	1653.1	1663.2	1668.2
4944.2	27.5°	4768.1	3698.7	2546.3	1987.7	1723.5	1660.6	1615.4	1562.5	1575.1	1582.6
4664.9	30°	4516.4	3583.0	2438.1	1904.7	1635.5	1562.5	1529.8	1484.5	1489.5	1499.6
4388.1	32.5°	4282.4	3459.7	2309.8	1836.8	1547.4	1474.4	1449.3	1399.0	1406.5	1416.6
4116.4	35°	4051.0	3323.8	2158.8	1756.3	1466.9	1393.9	1373.8	1315.9	1321.0	1336.1
3844.6	37.5°	3801.9	3180.4	2035.5	1675.7	1388.9	1313.4	1293.3	1232.9	1237.9	1255.5
3562.8	40°	3540.2	3039.5	1914.8	1590.2	1305.9	1230.4	1212.8	1147.4	1152.4	1172.5
3286.1	42.5°	3276.0	2886.0	1821.7	1479.5	1220.3	1139.8	1122.2	1061.8	1069.4	1092.0
3044.5	45°	3031.9	2702.3	1761.3	1356.2	1139.8	1049.2	1031.6	976.3	991.4	1016.5
2840.7	47.5°	2823.1	2513.6	1736.1	1253.0	1054.3	956.1	941.0	895.7	920.9	948.6
2667.1	50°	2644.4	2332.4	1703.4	1147.4	973.7	875.6	860.5	830.3	863.0	890.7
2548.8	52.5°	2516.1	2126.1	1633.0	1051.7	903.3	807.7	802.6	787.5	817.7	842.9
2460.8	55°	2405.4	1912.3	1519.7	968.7	840.4	749.8	754.8	747.3	772.4	792.6
2407.9	57.5°	2304.8	1726.1	1376.3	903.3	772.4	699.5	714.6	704.5	717.1	729.7
2352.6	60°	2184.0	1537.4	1205.2	830.3	691.9	649.2	666.8	639.1	636.6	641.6
2251.9	62.5°	2005.3	1283.2	1026.6	739.7	621.5	593.8	601.4	548.5	508.3	508.3
2103.5	65°	1756.3	1031.6	860.5	639.1	541.0	518.3	513.3	437.8	382.5	377.4
1942.4	67.5°	1466.9	847.9	714.6	538.5	450.4	435.3	440.3	385.0	329.6	324.6
1781.4	70°	1195.2	702.0	576.2	430.3	347.2	362.3	385.0	329.6	276.8	269.2
1592.7	72.5°	971.2	558.6	450.4	329.6	256.6	299.4	327.1	269.2	218.9	213.9
1358.7	75°	749.8	410.1	322.1	223.9	186.2	231.5	256.6	196.3	156.0	148.5
1051.7	77.5°	500.7	254.1	181.2	140.9	110.7	158.5	171.1	103.2	90.6	88.1
764.9	80°	304.5	118.3	78.0	67.9	37.7	57.9	67.9	42.8	47.8	50.3
407.6	82.5°	153.5	32.7	12.6	2.5	0.0	0.0	20.1	10.1	20.1	25.2
110.7	85°	12.6	0.0	0.0	0.0	0.0	0.0	0.0	0.0	5.0	12.6
0.0	87.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
0.0	90°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0

REPORT NUMBER: P954291

CATALOG NUMBER: GLAN-SB7C-830-U-SLR-HSS

CANDELA DISTRIBUTION (continued):

185°		195°	205°	215°	225°	235°	245°	255°	265°	270°	275°
5057.4	0°	5057.4	5057.4	5057.4	5057.4	5057.4	5057.4	5057.4	5057.4	5057.4	5057.4
4443.5	2.5°	4584.4	4690.1	4790.7	4951.7	5117.8	5281.3	5447.4	5608.4	5666.3	5709.1
3837.1	5°	4056.0	4254.8	4486.2	4805.8	5148.0	5500.2	5857.5	6184.6	6333.1	6433.7
3265.9	7.5°	3510.0	3769.2	4101.3	4581.9	5117.8	5678.9	6240.0	6755.8	6994.8	7188.6
2727.5	10°	2969.0	3250.8	3671.0	4219.5	4944.2	5749.3	6524.3	7233.9	7543.3	7787.4
2340.0	12.5°	2493.5	2757.7	3198.0	3804.4	4672.4	5694.0	6687.9	7540.8	7905.7	8179.9
2063.2	15°	2158.8	2345.0	2735.0	3389.2	4350.4	5515.3	6697.9	7686.8	8086.8	8373.7
1947.5	17.5°	1972.6	2035.5	2289.7	2966.5	3993.1	5281.3	6604.8	7737.1	8164.8	8431.5
1844.3	20°	1872.0	1882.1	1952.5	2418.0	3535.2	5062.4	6516.8	7787.4	8237.8	8461.7
1771.3	22.5°	1791.5	1791.5	1809.1	1977.7	2943.9	4800.8	6489.1	7875.5	8338.4	8476.8
1688.3	25°	1718.5	1718.5	1723.5	1768.8	2332.4	4400.7	6471.5	8011.3	8476.8	8514.6
1605.3	27.5°	1643.0	1645.5	1645.5	1670.7	1879.5	3857.2	6396.0	8187.5	8642.9	8564.9
1524.8	30°	1567.5	1572.6	1572.6	1590.2	1663.2	3220.6	6247.5	8398.8	8859.3	8630.3
1444.3	32.5°	1492.1	1497.1	1497.1	1512.2	1565.0	2571.5	6061.3	8592.6	9078.2	8658.0
1366.3	35°	1414.1	1421.6	1416.6	1436.7	1492.1	2045.6	5824.8	8786.3	9314.7	8746.0
1290.8	37.5°	1336.1	1341.1	1338.6	1358.7	1421.6	1766.3	5550.6	8932.2	9636.7	8942.3
1210.3	40°	1258.1	1255.5	1255.5	1278.2	1346.1	1685.8	5205.9	9163.7	10099.7	9287.0
1129.7	42.5°	1177.5	1177.5	1172.5	1197.7	1280.7	1625.4	4876.2	9578.9	10774.0	9835.5
1054.3	45°	1104.6	1102.1	1092.0	1114.6	1217.8	1519.7	4760.5	10353.8	11770.4	10723.7
978.8	47.5°	1034.1	1031.6	1006.4	1026.6	1142.3	1424.1	5193.3	11622.0	13151.8	12029.6
918.4	50°	971.2	973.7	925.9	943.5	1066.8	1351.2	6131.8	13267.5	14986.0	13788.3
868.1	52.5°	913.4	913.4	850.4	860.5	973.7	1285.7	7025.0	15051.4	17406.5	16241.6
815.2	55°	855.5	850.4	780.0	785.0	880.6	1192.6	7158.4	16792.6	20707.7	19932.7
757.4	57.5°	790.1	780.0	714.6	714.6	795.1	1124.7	6204.8	18131.2	24803.9	25357.5
649.2	60°	709.5	702.0	659.2	646.6	727.2	1185.1	4378.1	18287.2	27445.9	32571.2
515.8	62.5°	606.4	616.4	593.8	576.2	661.7	1230.4	2594.1	17031.6	26806.8	34865.9
400.1	65°	478.1	518.3	513.3	500.7	727.2	1036.6	1532.3	14621.2	24846.7	33014.0
349.7	67.5°	407.6	435.3	427.7	427.7	762.4	787.5	963.7	11423.2	22149.4	30817.5
291.9	70°	347.2	374.9	347.2	347.2	576.2	478.1	666.8	7976.1	19238.3	28386.9
234.0	72.5°	286.8	314.5	284.3	264.2	460.5	357.3	488.1	4984.4	16475.6	25855.7
166.1	75°	218.9	251.6	229.0	203.8	304.5	266.7	369.9	2896.1	13650.0	22121.7
100.6	77.5°	138.4	181.2	171.1	143.4	223.9	193.7	266.7	1723.5	10532.5	17285.8
60.4	80°	85.5	93.1	95.6	90.6	128.3	130.8	181.2	981.3	7208.7	12047.2
37.7	82.5°	55.4	55.4	42.8	47.8	62.9	75.5	103.2	369.9	4237.1	7334.5
22.6	85°	40.3	35.2	22.6	22.6	30.2	37.7	40.3	113.2	1718.5	2896.1
10.1	87.5°	20.1	17.6	7.5	10.1	15.1	12.6	10.1	5.0	432.8	925.9
0.0	90°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0

REPORT NUMBER: P954291

CATALOG NUMBER: GLAN-SB7C-830-U-SLR-HSS

CANDELA DISTRIBUTION (continued):

285°		295°	305°	315°	325°	335°	345°	355°	360°
5057.4	0°	5057.4	5057.4	5057.4	5057.4	5057.4	5057.4	5057.4	5057.4
5804.7	2.5°	5855.0	5933.0	5938.0	5938.0	5870.1	5867.6	5729.2	5714.1
6660.2	5°	6894.2	6944.5	6957.1	6931.9	6796.0	6695.4	6426.2	6368.3
7533.3	7.5°	7845.3	7945.9	7945.9	7885.5	7664.1	7457.8	7067.8	6921.9
8255.4	10°	8605.1	8720.9	8695.7	8572.4	8293.1	8008.8	7535.8	7344.6
8693.2	12.5°	8975.0	9093.3	9027.8	8886.9	8615.2	8315.8	7817.6	7601.2
8819.0	15°	8967.5	8934.7	8866.8	8849.2	8718.4	8491.9	8026.4	7789.9
8741.0	17.5°	8647.9	8371.1	8318.3	8494.4	8660.5	8605.1	8207.6	7986.2
8554.8	20°	8142.2	7659.1	7611.3	7948.4	8421.5	8663.0	8376.2	8172.4
8285.6	22.5°	7608.8	7087.9	6977.2	7349.6	8061.7	8680.6	8590.0	8386.2
7988.7	25°	7103.0	6579.7	6468.9	6816.2	7661.6	8650.4	8821.5	8647.9
7704.4	27.5°	6680.3	6174.6	6071.4	6418.6	7276.6	8564.9	9053.0	8929.7
7422.6	30°	6353.2	5885.2	5809.7	6144.4	6944.5	8459.2	9347.4	9279.5
7160.9	32.5°	6162.0	5819.8	5847.5	6121.7	6765.9	8343.5	9629.2	9661.9
7032.6	35°	6350.7	6365.8	6607.3	6720.6	6931.9	8325.8	10011.6	10140.0
7186.0	37.5°	7289.2	7812.6	8313.3	8220.2	7744.6	8529.7	10582.8	10821.8
7855.3	40°	8886.9	9961.3	10774.0	10419.3	9221.6	9153.7	11405.6	11762.9
9042.9	42.5°	10839.5	12661.1	13999.7	13048.6	11126.3	10245.6	12580.6	13036.0
10479.6	45°	12900.2	15990.0	18098.5	16120.8	13156.8	11775.5	14359.5	14716.8
11825.8	47.5°	15071.6	20035.9	22763.4	19527.6	15038.9	13516.6	16785.1	16868.1
13101.4	50°	17446.8	24471.8	27518.8	22931.9	16855.5	15511.9	19749.0	19653.4
14588.5	52.5°	19708.8	29033.5	32173.7	26351.3	18450.7	17987.8	23188.6	22992.3
16621.5	55°	21867.6	33592.7	36856.2	29637.4	19955.4	21258.7	27274.8	26087.2
19552.8	57.5°	24371.2	37691.5	41682.1	32938.6	22058.8	25505.9	31844.0	27883.7
25166.3	60°	28072.4	42348.9	47139.5	37462.5	26059.5	29969.5	33482.0	27541.5
31889.3	62.5°	32797.7	46631.3	51107.5	41895.9	30077.7	30809.9	31069.1	24904.6
30518.0	65°	33716.0	47715.7	51331.4	43081.0	29559.4	26135.0	25365.0	20018.3
27259.7	67.5°	31280.4	45755.7	48201.4	40874.4	26147.5	20196.9	19034.5	14523.1
25121.0	70°	28547.9	42019.2	42746.4	37122.9	22997.4	14855.2	12854.9	9319.7
23656.6	72.5°	25747.5	37034.8	35530.2	32239.1	20212.0	10816.8	9271.9	6624.9
21570.7	75°	22421.2	30480.3	27986.8	26786.6	16734.7	8489.4	6708.0	4571.8
18553.9	77.5°	17955.0	21455.0	20788.2	20763.0	12575.6	6202.2	4476.2	2865.9
14495.4	80°	12666.2	13924.2	13584.5	15637.7	8436.6	4498.8	2694.8	1595.2
10089.6	82.5°	6131.8	7699.3	7903.1	9312.2	4103.8	2647.0	621.5	347.2
3945.3	85°	2400.4	3713.8	3132.6	3535.2	1152.4	737.2	15.1	0.0
649.2	87.5°	269.2	430.3	395.0	312.0	140.9	30.2	0.0	0.0
0.0	90°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0

(END OF REPORT)