

Scaled data based on original data using  
LM-79-08 Approved Method: Electrical and Photometric Measurements of Solid-  
State Lighting Products

Test Report Prepared for  
Cooper Lighting Solutions  
(formerly Eaton)

Brand: STREETWORKS

Report Number: P954017

Luminaire Tested: **GLAN-SB7B-927-U-SLL**

Issue Date: 1/21/2025

**Test Information**

Test Method: LM-79-08  
Report Number: P954017  
TEST IS SCALED FROM IESNA LM-79-08 TEST DATA (G2-2411-289-8)  
Test Lab: INNOVATION CENTER  
Issue Date: 1/21/2025  
Manufacturer: COOPER LIGHTING SOLUTIONS (FORMERLY EATON)  
Product Line: STREETWORKS  
Catalog Number: GLAN-SB7B-927-U-SLL  
Description: GALLEON AREA AND ROADWAY HIGH DENSITY LED LUMINAIRE  
(7) 90 CRI, 2700K, 450mA LIGHTSQUARES WITH 26 LEDS EACH AND SPILL LIGHT  
ELIMINATOR LEFT OPTICS  
Light Source: -  
Ballast/Driver: -

**Summary**

Lumens per Lamp: N/A  
Luminaire Lumens: 24289 lumens  
Efficiency: N/A  
Efficacy: 94.6 lumens/watt  
Luminous Opening: Rectangular (W 1.5' x L: 1.5' x H: 0')  
IES Classification: Type IV - Short  
BUG Rating: B3 - U0 - G5

Input Watts (W): 256.7  
Input Voltage (V): NR  
Input Current (Ain): NR  
Voltage Rise (V): NR  
Power Factor: NR  
Total Harmonic Distortion (THDi): NR  
Frequency (hertz): 60  
Stabilization Time: NR  
Operation Time: NR  
Ambient Temperature (°C): NR  
Test Distance: 24 FT




REPORT NUMBER: P954017

CATALOG NUMBER: GLAN-SB7B-927-U-SLL

## Iso-Footcandle Lines of Horizontal Illumination

× Max cd

--- 1/2 Max cd




Based on 25 foot mounting height. Maximum calculated value = 7.4 fc

Type IV - Short - N/A

REPORT NUMBER: P954017  
CATALOG NUMBER: GLAN-SB7B-927-U-SLL

## Luminous Intensity Polar Plot



REPORT NUMBER: P954017

CATALOG NUMBER: GLAN-SB7B-927-U-SLL

**FLUX DISTRIBUTION:**

|                    |           | Downward | Upward | Total   |
|--------------------|-----------|----------|--------|---------|
| <b>House Side</b>  | Lumens    | 6173.0   | 0.0    | 6173.0  |
|                    | % Fixture | 25.4     | 0.0    | 25.4    |
| <b>Street Side</b> | Lumens    | 18116.0  | 0.0    | 18116.0 |
|                    | % Fixture | 74.6     | 0.0    | 74.6    |
| <b>Total</b>       | Lumens    | 24289.0  | 0.0    | 24289.0 |
|                    | % Fixture | 100.0    | 0.0    | 100.0   |

**ZONAL LUMENS:**

| Zone      | Lumens  | % Fixture |
|-----------|---------|-----------|
| 0°-10°    | 331.3   | 1.4       |
| 10°-20°   | 1040.1  | 4.3       |
| 20°-30°   | 1606.6  | 6.6       |
| 30°-40°   | 2035.9  | 8.4       |
| 40°-50°   | 3070.7  | 12.6      |
| 50°-60°   | 4961.2  | 20.4      |
| 60°-70°   | 6184.9  | 25.5      |
| 70°-80°   | 4055.7  | 16.7      |
| 80°-90°   | 1002.7  | 4.1       |
| 90°-100°  | 0.0     | 0.0       |
| 100°-110° | 0.0     | 0.0       |
| 110°-120° | 0.0     | 0.0       |
| 120°-130° | 0.0     | 0.0       |
| 130°-140° | 0.0     | 0.0       |
| 140°-150° | 0.0     | 0.0       |
| 150°-160° | 0.0     | 0.0       |
| 160°-170° | 0.0     | 0.0       |
| 170°-180° | 0.0     | 0.0       |
| 0°-90°    | 24289.0 | 100.0     |
| 0°-180°   | 24289.0 | 100.0     |

**Coefficient of Utilization**



REPORT NUMBER: P954017


CATALOG NUMBER: GLAN-SB7B-927-U-SLL

**LUMINAIRE CLASSIFICATION SYSTEM LUMEN TABLE AND BUG RATING:**

| Zone |             | Lumens | % Fixture | Zone Rating/Lumen Limit |      |          |
|------|-------------|--------|-----------|-------------------------|------|----------|
|      |             |        |           | B                       | U    | G        |
| FL   | (0°-30°)    | 1633.7 | 6.7       |                         |      |          |
| FM   | (30°-60°)   | 7084.6 | 29.2      |                         |      |          |
| FH   | (60°-80°)   | 8571.7 | 35.3      |                         |      | G4/12000 |
| FVH  | (80°-90°)   | 826.0  | 3.4       |                         |      | G5       |
| BL   | (0°-30°)    | 1344.3 | 5.5       | B3/2500                 |      |          |
| BM   | (30°-60°)   | 2983.2 | 12.3      | B3/5000                 |      |          |
| BH   | (60°-80°)   | 1668.9 | 6.9       | B3/2500                 |      | G3/2500  |
| BVH  | (80°-90°)   | 176.7  | 0.7       |                         |      | G2/225   |
| UL   | (90°-100°)  | 0.0    | 0.0       |                         | U0/0 |          |
| UH   | (100°-180°) | 0.0    | 0.0       |                         | U0/0 |          |

**BUG Rating: B3-U0-G5**

Type IV Short



REPORT NUMBER: P954017

CATALOG NUMBER: GLAN-SB7B-927-U-SLL

**CANDELA DISTRIBUTION (FULL):**

|       | 0°      | 5°      | 10°     | 15°     | 20°     | 25°     | 30°     | 35°     | 40°     | 45°     |
|-------|---------|---------|---------|---------|---------|---------|---------|---------|---------|---------|
| 0°    | 3339.9  | 3339.9  | 3339.9  | 3339.9  | 3339.9  | 3339.9  | 3339.9  | 3339.9  | 3339.9  | 3339.9  |
| 2.5°  | 3591.8  | 3605.4  | 3619.1  | 3638.4  | 3657.8  | 3669.3  | 3680.9  | 3686.6  | 3692.4  | 3689.8  |
| 5°    | 3862.2  | 3909.8  | 3957.4  | 4004.6  | 4051.9  | 4077.5  | 4103.2  | 4118.7  | 4134.3  | 4146.1  |
| 7.5°  | 4133.9  | 4211.3  | 4288.6  | 4358.2  | 4427.8  | 4469.7  | 4511.6  | 4534.3  | 4556.9  | 4567.8  |
| 10°   | 4342.2  | 4433.7  | 4525.2  | 4606.8  | 4688.5  | 4738.0  | 4787.2  | 4809.2  | 4831.1  | 4839.5  |
| 12.5° | 4469.7  | 4568.9  | 4668.0  | 4741.8  | 4815.4  | 4851.3  | 4887.1  | 4899.2  | 4911.2  | 4912.5  |
| 15°   | 4547.2  | 4632.9  | 4718.3  | 4764.6  | 4811.0  | 4812.3  | 4813.6  | 4800.8  | 4787.9  | 4772.8  |
| 17.5° | 4590.8  | 4648.6  | 4706.4  | 4707.3  | 4708.1  | 4656.2  | 4604.3  | 4556.7  | 4509.1  | 4475.5  |
| 20°   | 4638.9  | 4659.0  | 4679.3  | 4618.4  | 4557.5  | 4442.9  | 4328.3  | 4244.9  | 4161.5  | 4110.2  |
| 22.5° | 4694.6  | 4668.2  | 4641.8  | 4515.7  | 4389.6  | 4221.1  | 4052.5  | 3948.2  | 3843.9  | 3787.2  |
| 25°   | 4766.4  | 4683.1  | 4599.8  | 4408.3  | 4216.8  | 4012.2  | 3807.5  | 3697.8  | 3588.3  | 3534.8  |
| 27.5° | 4863.8  | 4714.9  | 4565.8  | 4312.2  | 4058.7  | 3831.8  | 3605.0  | 3497.1  | 3389.3  | 3338.7  |
| 30°   | 4995.2  | 4773.1  | 4551.1  | 4238.9  | 3926.7  | 3690.3  | 3454.0  | 3353.9  | 3253.8  | 3206.7  |
| 32.5° | 5150.3  | 4846.1  | 4542.1  | 4188.9  | 3835.7  | 3613.6  | 3391.5  | 3312.9  | 3234.2  | 3200.2  |
| 35°   | 5338.7  | 4966.5  | 4594.4  | 4226.3  | 3858.4  | 3704.1  | 3549.9  | 3531.6  | 3513.2  | 3510.4  |
| 37.5° | 5655.9  | 5218.1  | 4780.3  | 4445.7  | 4111.2  | 4101.2  | 4091.2  | 4175.1  | 4258.9  | 4302.5  |
| 40°   | 6135.2  | 5659.1  | 5182.9  | 4934.2  | 4685.4  | 4861.0  | 5036.6  | 5240.4  | 5444.1  | 5545.6  |
| 42.5° | 6770.9  | 6298.5  | 5826.1  | 5682.8  | 5539.5  | 5922.4  | 6305.4  | 6676.0  | 7046.7  | 7264.3  |
| 45°   | 7555.9  | 7131.5  | 6707.1  | 6643.9  | 6580.6  | 7194.1  | 7807.7  | 8416.8  | 9025.9  | 9395.7  |
| 47.5° | 8537.6  | 8124.8  | 7711.9  | 7699.1  | 7686.2  | 8571.3  | 9456.2  | 10347.8 | 11239.3 | 11762.9 |
| 50°   | 9824.4  | 9314.4  | 8804.6  | 8806.8  | 8808.9  | 9949.6  | 11090.3 | 12267.2 | 13444.1 | 14155.7 |
| 52.5° | 11301.5 | 10684.0 | 10066.6 | 10004.2 | 9941.7  | 11304.2 | 12666.7 | 14122.9 | 15578.9 | 16431.9 |
| 55°   | 12874.0 | 12264.0 | 11653.9 | 11410.5 | 11167.2 | 12683.6 | 14199.9 | 15935.9 | 17671.9 | 18686.3 |
| 57.5° | 14304.4 | 13972.2 | 13639.8 | 13151.6 | 12663.6 | 14194.8 | 15725.9 | 17692.2 | 19658.4 | 20916.3 |
| 60°   | 15168.8 | 15684.8 | 16200.9 | 15594.7 | 14988.5 | 16437.5 | 17886.5 | 19991.7 | 22097.0 | 23456.5 |
| 62.5° | 14729.9 | 16139.8 | 17549.7 | 17481.4 | 17413.0 | 18740.4 | 20067.9 | 22070.8 | 24073.6 | 25330.3 |
| 65°   | 13851.3 | 15174.6 | 16497.9 | 16759.7 | 17021.4 | 18708.3 | 20395.3 | 22337.5 | 24279.6 | 25349.5 |
| 67.5° | 12674.1 | 13932.7 | 15191.2 | 15314.0 | 15436.7 | 17194.3 | 18951.8 | 20902.4 | 22852.9 | 23691.1 |
| 70°   | 11259.8 | 12628.7 | 13997.8 | 14052.6 | 14107.6 | 15679.4 | 17251.1 | 18929.7 | 20608.1 | 21074.0 |
| 72.5° | 9574.5  | 11145.4 | 12716.4 | 12755.9 | 12795.2 | 14025.0 | 15254.7 | 16511.8 | 17768.9 | 17816.0 |
| 75°   | 7442.5  | 9068.4  | 10694.2 | 10840.2 | 10986.2 | 11942.9 | 12899.7 | 13784.6 | 14669.6 | 14432.5 |
| 77.5° | 5317.5  | 6835.2  | 8353.1  | 8562.0  | 8770.9  | 9498.2  | 10225.5 | 10853.2 | 11480.9 | 11073.3 |
| 80°   | 3480.3  | 4757.2  | 6033.9  | 6293.6  | 6553.3  | 7102.6  | 7651.6  | 7981.3  | 8310.8  | 7655.2  |
| 82.5° | 2023.1  | 2896.0  | 3769.0  | 4059.1  | 4349.2  | 4727.3  | 5105.4  | 5242.9  | 5380.3  | 4865.1  |
| 85°   | 890.1   | 1353.4  | 1816.7  | 2063.4  | 2310.2  | 2620.8  | 2931.4  | 3009.4  | 3087.5  | 2674.8  |
| 87.5° | 275.6   | 431.3   | 587.0   | 724.6   | 862.3   | 1017.6  | 1173.0  | 1179.6  | 1186.2  | 995.8   |
| 90°   | 0.0     | 0.0     | 0.0     | 0.0     | 0.0     | 0.0     | 0.0     | 0.0     | 0.0     | 0.0     |

REPORT NUMBER: P954017

CATALOG NUMBER: GLAN-SB7B-927-U-SLL

**CANDELA DISTRIBUTION (continued):**

| 50°     |       | 55°     | 60°     | 65°     | 70°     | 75°     | 80°     | 85°     | 90°     | 95°     | 100°   |
|---------|-------|---------|---------|---------|---------|---------|---------|---------|---------|---------|--------|
| 3339.9  | 0°    | 3339.9  | 3339.9  | 3339.9  | 3339.9  | 3339.9  | 3339.9  | 3339.9  | 3339.9  | 3339.9  | 3339.9 |
| 3692.4  | 2.5°  | 3686.6  | 3680.9  | 3669.3  | 3657.8  | 3638.4  | 3619.1  | 3605.4  | 3591.8  | 3564.2  | 3536.7 |
| 4134.3  | 5°    | 4118.7  | 4103.2  | 4077.5  | 4051.9  | 4004.6  | 3957.4  | 3909.8  | 3862.2  | 3801.3  | 3740.5 |
| 4556.9  | 7.5°  | 4534.3  | 4511.6  | 4469.7  | 4427.8  | 4358.2  | 4288.6  | 4211.3  | 4133.9  | 4033.4  | 3933.1 |
| 4831.1  | 10°   | 4809.2  | 4787.2  | 4738.0  | 4688.5  | 4606.8  | 4525.2  | 4433.7  | 4342.2  | 4215.2  | 4088.2 |
| 4911.2  | 12.5° | 4899.2  | 4887.1  | 4851.3  | 4815.4  | 4741.8  | 4668.0  | 4568.9  | 4469.7  | 4330.1  | 4190.7 |
| 4787.9  | 15°   | 4800.8  | 4813.6  | 4812.3  | 4811.0  | 4764.6  | 4718.3  | 4632.9  | 4547.2  | 4401.8  | 4256.3 |
| 4509.1  | 17.5° | 4556.7  | 4604.3  | 4656.2  | 4708.1  | 4707.3  | 4706.4  | 4648.6  | 4590.8  | 4443.3  | 4295.8 |
| 4161.5  | 20°   | 4244.9  | 4328.3  | 4442.9  | 4557.5  | 4618.4  | 4679.3  | 4659.0  | 4638.9  | 4485.6  | 4332.2 |
| 3843.9  | 22.5° | 3948.2  | 4052.5  | 4221.1  | 4389.6  | 4515.7  | 4641.8  | 4668.2  | 4694.6  | 4538.0  | 4381.3 |
| 3588.3  | 25°   | 3697.8  | 3807.5  | 4012.2  | 4216.8  | 4408.3  | 4599.8  | 4683.1  | 4766.4  | 4612.9  | 4459.5 |
| 3389.3  | 27.5° | 3497.1  | 3605.0  | 3831.8  | 4058.7  | 4312.2  | 4565.8  | 4714.9  | 4863.8  | 4717.5  | 4571.0 |
| 3253.8  | 30°   | 3353.9  | 3454.0  | 3690.3  | 3926.7  | 4238.9  | 4551.1  | 4773.1  | 4995.2  | 4853.7  | 4712.3 |
| 3234.2  | 32.5° | 3312.9  | 3391.5  | 3613.6  | 3835.7  | 4188.9  | 4542.1  | 4846.1  | 5150.3  | 5010.2  | 4870.2 |
| 3513.2  | 35°   | 3531.6  | 3549.9  | 3704.1  | 3858.4  | 4226.3  | 4594.4  | 4966.5  | 5338.7  | 5204.6  | 5070.4 |
| 4258.9  | 37.5° | 4175.1  | 4091.2  | 4101.2  | 4111.2  | 4445.7  | 4780.3  | 5218.1  | 5655.9  | 5484.9  | 5313.9 |
| 5444.1  | 40°   | 5240.4  | 5036.6  | 4861.0  | 4685.4  | 4934.2  | 5182.9  | 5659.1  | 6135.2  | 5886.0  | 5636.9 |
| 7046.7  | 42.5° | 6676.0  | 6305.4  | 5922.4  | 5539.5  | 5682.8  | 5826.1  | 6298.5  | 6770.9  | 6411.3  | 6051.6 |
| 9025.9  | 45°   | 8416.8  | 7807.7  | 7194.1  | 6580.6  | 6643.9  | 6707.1  | 7131.5  | 7555.9  | 7070.8  | 6585.7 |
| 11239.3 | 47.5° | 10347.8 | 9456.2  | 8571.3  | 7686.2  | 7699.1  | 7711.9  | 8124.8  | 8537.6  | 7854.9  | 7172.0 |
| 13444.1 | 50°   | 12267.2 | 11090.3 | 9949.6  | 8808.9  | 8806.8  | 8804.6  | 9314.4  | 9824.4  | 8795.1  | 7765.7 |
| 15578.9 | 52.5° | 14122.9 | 12666.7 | 11304.2 | 9941.7  | 10004.2 | 10066.6 | 10684.0 | 11301.5 | 9782.7  | 8264.0 |
| 17671.9 | 55°   | 15935.9 | 14199.9 | 12683.6 | 11167.2 | 11410.5 | 11653.9 | 12264.0 | 12874.0 | 10658.4 | 8442.8 |
| 19658.4 | 57.5° | 17692.2 | 15725.9 | 14194.8 | 12663.6 | 13151.6 | 13639.8 | 13972.2 | 14304.4 | 11278.9 | 8253.5 |
| 22097.0 | 60°   | 19991.7 | 17886.5 | 16437.5 | 14988.5 | 15594.7 | 16200.9 | 15684.8 | 15168.8 | 11434.0 | 7699.1 |
| 24073.6 | 62.5° | 22070.8 | 20067.9 | 18740.4 | 17413.0 | 17481.4 | 17549.7 | 16139.8 | 14729.9 | 10781.0 | 6832.2 |
| 24279.6 | 65°   | 22337.5 | 20395.3 | 18708.3 | 17021.4 | 16759.7 | 16497.9 | 15174.6 | 13851.3 | 9857.1  | 5862.8 |
| 22852.9 | 67.5° | 20902.4 | 18951.8 | 17194.3 | 15436.7 | 15314.0 | 15191.2 | 13932.7 | 12674.1 | 8757.6  | 4841.0 |
| 20608.1 | 70°   | 18929.7 | 17251.1 | 15679.4 | 14107.6 | 14052.6 | 13997.8 | 12628.7 | 11259.8 | 7557.8  | 3855.8 |
| 17768.9 | 72.5° | 16511.8 | 15254.7 | 14025.0 | 12795.2 | 12755.9 | 12716.4 | 11145.4 | 9574.5  | 6257.2  | 2940.1 |
| 14669.6 | 75°   | 13784.6 | 12899.7 | 11942.9 | 10986.2 | 10840.2 | 10694.2 | 9068.4  | 7442.5  | 4766.3  | 2090.1 |
| 11480.9 | 77.5° | 10853.2 | 10225.5 | 9498.2  | 8770.9  | 8562.0  | 8353.1  | 6835.2  | 5317.5  | 3336.0  | 1354.4 |
| 8310.8  | 80°   | 7981.3  | 7651.6  | 7102.6  | 6553.3  | 6293.6  | 6033.9  | 4757.2  | 3480.3  | 2149.3  | 818.3  |
| 5380.3  | 82.5° | 5242.9  | 5105.4  | 4727.3  | 4349.2  | 4059.1  | 3769.0  | 2896.0  | 2023.1  | 1244.0  | 465.0  |
| 3087.5  | 85°   | 3009.4  | 2931.4  | 2620.8  | 2310.2  | 2063.4  | 1816.7  | 1353.4  | 890.1   | 559.6   | 229.2  |
| 1186.2  | 87.5° | 1179.6  | 1173.0  | 1017.6  | 862.3   | 724.6   | 587.0   | 431.3   | 275.6   | 183.3   | 91.0   |
| 0.0     | 90°   | 0.0     | 0.0     | 0.0     | 0.0     | 0.0     | 0.0     | 0.0     | 0.0     | 0.0     | 0.0    |

REPORT NUMBER: P954017

CATALOG NUMBER: GLAN-SB7B-927-U-SLL

**CANDELA DISTRIBUTION (continued):**

| 105°   |       | 110°   | 115°   | 120°   | 125°   | 130°   | 135°   | 140°   | 145°   | 150°   | 155°   |
|--------|-------|--------|--------|--------|--------|--------|--------|--------|--------|--------|--------|
| 3339.9 | 0°    | 3339.9 | 3339.9 | 3339.9 | 3339.9 | 3339.9 | 3339.9 | 3339.9 | 3339.9 | 3339.9 | 3339.9 |
| 3507.3 | 2.5°  | 3478.1 | 3448.6 | 3419.2 | 3391.0 | 3362.8 | 3335.5 | 3305.1 | 3280.5 | 3256.0 | 3233.8 |
| 3679.7 | 5°    | 3619.1 | 3558.0 | 3496.9 | 3439.9 | 3382.9 | 3329.1 | 3275.9 | 3229.5 | 3182.9 | 3144.0 |
| 3840.3 | 7.5°  | 3747.5 | 3657.2 | 3566.8 | 3487.2 | 3407.6 | 3334.2 | 3265.4 | 3203.6 | 3141.9 | 3090.7 |
| 3965.5 | 10°   | 3843.0 | 3733.3 | 3623.4 | 3529.4 | 3435.0 | 3344.4 | 3270.5 | 3205.4 | 3140.3 | 3089.0 |
| 4051.8 | 12.5° | 3912.8 | 3783.4 | 3653.9 | 3547.4 | 3440.9 | 3345.7 | 3276.9 | 3223.6 | 3170.5 | 3136.4 |
| 4105.6 | 15°   | 3954.9 | 3805.8 | 3656.8 | 3533.5 | 3410.2 | 3304.7 | 3249.6 | 3224.1 | 3198.7 | 3203.3 |
| 4131.4 | 17.5° | 3966.9 | 3793.9 | 3620.9 | 3472.6 | 3324.3 | 3200.2 | 3166.3 | 3175.6 | 3184.9 | 3240.7 |
| 4151.5 | 20°   | 3970.8 | 3761.1 | 3551.4 | 3367.6 | 3183.8 | 3039.4 | 3030.4 | 3074.0 | 3117.6 | 3214.6 |
| 4178.7 | 22.5° | 3975.9 | 3720.8 | 3465.8 | 3244.5 | 3023.1 | 2858.7 | 2876.3 | 2940.7 | 3005.2 | 3115.9 |
| 4227.9 | 25°   | 3996.1 | 3681.1 | 3366.2 | 3106.9 | 2847.8 | 2679.3 | 2726.7 | 2801.0 | 2875.4 | 2974.9 |
| 4304.8 | 27.5° | 4038.4 | 3654.6 | 3270.7 | 2981.2 | 2691.7 | 2538.3 | 2596.0 | 2667.7 | 2739.5 | 2821.4 |
| 4404.3 | 30°   | 4096.4 | 3642.2 | 3187.7 | 2876.1 | 2564.6 | 2435.8 | 2481.0 | 2537.9 | 2595.1 | 2663.0 |
| 4508.3 | 32.5° | 4146.4 | 3626.8 | 3106.9 | 2785.5 | 2463.9 | 2360.1 | 2380.3 | 2414.0 | 2447.7 | 2501.9 |
| 4626.7 | 35°   | 4183.0 | 3597.8 | 3012.9 | 2696.4 | 2380.0 | 2293.5 | 2285.2 | 2294.4 | 2303.7 | 2345.1 |
| 4759.4 | 37.5° | 4204.8 | 3548.2 | 2891.6 | 2591.6 | 2291.6 | 2216.0 | 2185.4 | 2175.2 | 2164.9 | 2194.7 |
| 4927.8 | 40°   | 4218.5 | 3479.9 | 2741.4 | 2466.5 | 2191.6 | 2123.0 | 2076.3 | 2053.1 | 2029.9 | 2051.3 |
| 5148.1 | 42.5° | 4244.5 | 3409.4 | 2574.6 | 2328.5 | 2082.4 | 2019.2 | 1960.3 | 1929.5 | 1898.7 | 1916.2 |
| 5438.0 | 45°   | 4290.3 | 3343.9 | 2397.7 | 2181.9 | 1966.0 | 1901.9 | 1844.9 | 1814.9 | 1785.1 | 1799.7 |
| 5746.9 | 47.5° | 4321.7 | 3289.8 | 2258.0 | 2065.9 | 1873.8 | 1791.1 | 1742.0 | 1716.9 | 1691.8 | 1705.6 |
| 6033.4 | 50°   | 4301.2 | 3230.9 | 2160.6 | 1988.8 | 1817.1 | 1708.4 | 1651.4 | 1629.1 | 1606.9 | 1628.4 |
| 6219.5 | 52.5° | 4174.9 | 3131.3 | 2087.8 | 1938.1 | 1788.5 | 1663.6 | 1583.8 | 1561.8 | 1539.9 | 1572.3 |
| 6178.5 | 55°   | 3914.1 | 2966.2 | 2018.3 | 1901.3 | 1784.3 | 1668.1 | 1548.0 | 1513.1 | 1478.4 | 1524.4 |
| 5889.9 | 57.5° | 3526.4 | 2733.5 | 1940.4 | 1857.7 | 1775.1 | 1672.5 | 1526.4 | 1475.7 | 1424.9 | 1474.4 |
| 5352.8 | 60°   | 3006.5 | 2431.3 | 1856.1 | 1791.1 | 1726.1 | 1658.4 | 1506.2 | 1440.4 | 1374.6 | 1418.0 |
| 4626.5 | 62.5° | 2420.8 | 2069.6 | 1718.4 | 1675.2 | 1632.2 | 1623.8 | 1482.6 | 1400.3 | 1318.2 | 1345.7 |
| 3885.4 | 65°   | 1908.1 | 1744.2 | 1580.3 | 1559.9 | 1539.5 | 1540.5 | 1432.9 | 1345.5 | 1257.9 | 1268.6 |
| 3159.5 | 67.5° | 1478.0 | 1431.5 | 1384.8 | 1396.2 | 1407.5 | 1404.7 | 1344.2 | 1271.4 | 1198.6 | 1195.3 |
| 2487.7 | 70°   | 1119.5 | 1132.8 | 1146.0 | 1198.8 | 1251.5 | 1251.5 | 1231.7 | 1179.9 | 1128.1 | 1116.6 |
| 1901.8 | 72.5° | 863.6  | 903.7  | 943.9  | 1018.8 | 1093.5 | 1106.1 | 1106.3 | 1070.8 | 1035.3 | 1018.4 |
| 1380.3 | 75°   | 670.6  | 707.0  | 743.3  | 827.2  | 911.0  | 968.9  | 964.0  | 936.7  | 909.3  | 893.2  |
| 935.3  | 77.5° | 516.2  | 541.0  | 565.8  | 647.2  | 728.6  | 824.1  | 821.5  | 799.6  | 777.7  | 761.3  |
| 602.6  | 80°   | 387.1  | 397.3  | 407.6  | 476.5  | 545.3  | 659.4  | 659.0  | 640.7  | 622.2  | 608.5  |
| 370.6  | 82.5° | 276.6  | 278.4  | 280.4  | 331.2  | 381.9  | 479.3  | 484.7  | 475.7  | 466.8  | 457.0  |
| 198.1  | 85°   | 167.3  | 166.4  | 165.3  | 202.5  | 239.7  | 312.1  | 319.1  | 309.5  | 299.9  | 289.0  |
| 82.2   | 87.5° | 73.3   | 72.4   | 71.5   | 86.6   | 101.9  | 132.0  | 141.0  | 137.1  | 133.3  | 131.2  |
| 0.0    | 90°   | 0.0    | 0.0    | 0.0    | 0.0    | 0.0    | 0.0    | 0.0    | 0.0    | 0.0    | 0.0    |

REPORT NUMBER: P954017

CATALOG NUMBER: GLAN-SB7B-927-U-SLL

**CANDELA DISTRIBUTION (continued):**

| 160°   |       | 165°   | 170°   | 175°   | 180°   | 185°   | 190°   | 195°   | 200°   | 205°   | 210°   |
|--------|-------|--------|--------|--------|--------|--------|--------|--------|--------|--------|--------|
| 3339.9 | 0°    | 3339.9 | 3339.9 | 3339.9 | 3339.9 | 3339.9 | 3339.9 | 3339.9 | 3339.9 | 3339.9 | 3339.9 |
| 3211.8 | 2.5°  | 3192.4 | 3173.1 | 3153.6 | 3134.2 | 3119.2 | 3104.1 | 3091.9 | 3079.8 | 3070.3 | 3060.8 |
| 3105.2 | 5°    | 3070.8 | 3036.5 | 3005.3 | 2974.0 | 2950.1 | 2926.0 | 2909.2 | 2892.4 | 2880.5 | 2868.6 |
| 3039.4 | 7.5°  | 2996.2 | 2952.9 | 2914.7 | 2876.6 | 2848.1 | 2819.6 | 2799.6 | 2779.6 | 2765.9 | 2752.3 |
| 3037.7 | 10°   | 2991.2 | 2944.6 | 2901.6 | 2858.7 | 2824.6 | 2790.4 | 2768.1 | 2745.5 | 2732.6 | 2719.6 |
| 3102.6 | 12.5° | 3065.9 | 3029.5 | 2985.1 | 2940.7 | 2897.1 | 2853.6 | 2824.7 | 2795.9 | 2781.4 | 2767.1 |
| 3207.9 | 15°   | 3198.5 | 3189.0 | 3150.4 | 3111.8 | 3049.8 | 2987.8 | 2943.9 | 2900.1 | 2880.0 | 2860.0 |
| 3296.6 | 17.5° | 3326.4 | 3356.0 | 3324.8 | 3293.8 | 3211.7 | 3129.5 | 3064.9 | 3000.3 | 2970.6 | 2940.7 |
| 3311.8 | 20°   | 3373.9 | 3436.1 | 3421.7 | 3407.2 | 3313.3 | 3219.5 | 3140.3 | 3061.2 | 3023.1 | 2984.9 |
| 3226.9 | 22.5° | 3307.8 | 3388.6 | 3397.4 | 3406.0 | 3316.2 | 3226.5 | 3145.0 | 3063.4 | 3023.3 | 2983.0 |
| 3074.6 | 25°   | 3154.2 | 3233.8 | 3263.6 | 3293.2 | 3219.6 | 3146.2 | 3073.6 | 3001.3 | 2966.5 | 2931.7 |
| 2903.2 | 27.5° | 2967.0 | 3030.8 | 3063.9 | 3097.1 | 3044.7 | 2992.4 | 2936.1 | 2879.8 | 2856.5 | 2833.1 |
| 2730.9 | 30°   | 2783.8 | 2836.9 | 2863.8 | 2890.7 | 2850.9 | 2810.9 | 2770.6 | 2730.1 | 2718.2 | 2706.2 |
| 2556.2 | 32.5° | 2607.0 | 2657.9 | 2687.7 | 2717.7 | 2681.1 | 2644.3 | 2612.1 | 2579.9 | 2572.1 | 2564.3 |
| 2386.4 | 35°   | 2436.6 | 2487.0 | 2522.9 | 2558.8 | 2532.6 | 2506.6 | 2476.9 | 2447.3 | 2435.4 | 2423.6 |
| 2224.3 | 37.5° | 2274.4 | 2324.6 | 2369.0 | 2413.3 | 2401.3 | 2389.2 | 2361.9 | 2334.5 | 2312.8 | 2291.3 |
| 2072.7 | 40°   | 2121.1 | 2169.6 | 2220.6 | 2271.7 | 2274.6 | 2277.5 | 2254.3 | 2231.1 | 2199.5 | 2168.3 |
| 1933.7 | 42.5° | 1979.6 | 2025.6 | 2080.7 | 2135.8 | 2150.6 | 2165.3 | 2145.7 | 2126.2 | 2087.1 | 2048.1 |
| 1814.5 | 45°   | 1858.1 | 1901.7 | 1958.9 | 2016.0 | 2037.2 | 2058.3 | 2040.6 | 2023.1 | 1978.3 | 1933.7 |
| 1719.3 | 47.5° | 1762.0 | 1804.5 | 1860.9 | 1917.3 | 1941.7 | 1966.0 | 1953.7 | 1941.4 | 1901.7 | 1862.0 |
| 1650.1 | 50°   | 1690.4 | 1730.5 | 1781.0 | 1831.5 | 1862.7 | 1894.0 | 1893.2 | 1892.7 | 1860.9 | 1829.2 |
| 1604.6 | 52.5° | 1641.5 | 1678.3 | 1725.3 | 1772.5 | 1809.5 | 1846.6 | 1853.2 | 1859.9 | 1834.0 | 1808.1 |
| 1570.3 | 55°   | 1610.0 | 1649.7 | 1691.0 | 1732.1 | 1771.4 | 1810.7 | 1819.9 | 1829.2 | 1806.6 | 1784.0 |
| 1523.9 | 57.5° | 1570.5 | 1617.2 | 1657.9 | 1698.8 | 1738.4 | 1777.9 | 1787.2 | 1796.6 | 1773.8 | 1751.0 |
| 1461.3 | 60°   | 1514.9 | 1568.5 | 1609.9 | 1651.4 | 1691.1 | 1730.9 | 1741.1 | 1751.4 | 1729.1 | 1706.9 |
| 1373.3 | 62.5° | 1435.7 | 1498.2 | 1542.5 | 1586.7 | 1623.1 | 1659.5 | 1669.3 | 1679.2 | 1659.1 | 1639.0 |
| 1279.1 | 65°   | 1346.0 | 1413.0 | 1455.3 | 1497.6 | 1529.6 | 1561.7 | 1571.8 | 1581.8 | 1562.4 | 1543.1 |
| 1191.9 | 67.5° | 1253.7 | 1315.6 | 1355.7 | 1395.7 | 1423.4 | 1451.1 | 1460.9 | 1470.7 | 1452.9 | 1435.2 |
| 1105.0 | 70°   | 1159.4 | 1213.7 | 1248.3 | 1282.9 | 1307.9 | 1332.9 | 1342.4 | 1351.9 | 1337.4 | 1322.9 |
| 1001.6 | 72.5° | 1044.4 | 1087.1 | 1118.4 | 1149.6 | 1174.1 | 1198.6 | 1209.9 | 1221.1 | 1209.1 | 1197.0 |
| 876.9  | 75°   | 908.7  | 940.5  | 968.8  | 997.1  | 1019.4 | 1041.7 | 1053.5 | 1065.3 | 1059.4 | 1053.5 |
| 744.9  | 77.5° | 770.8  | 796.5  | 820.9  | 845.2  | 868.7  | 892.0  | 903.0  | 914.1  | 905.9  | 897.4  |
| 594.7  | 80°   | 616.2  | 637.6  | 658.1  | 678.6  | 696.4  | 714.1  | 728.7  | 743.3  | 739.8  | 736.3  |
| 447.3  | 82.5° | 445.5  | 443.7  | 436.5  | 429.3  | 467.3  | 505.2  | 530.1  | 554.9  | 553.4  | 551.7  |
| 278.1  | 85°   | 268.9  | 259.5  | 239.7  | 219.8  | 255.3  | 290.9  | 321.7  | 352.5  | 349.9  | 347.3  |
| 129.2  | 87.5° | 128.8  | 128.4  | 113.3  | 98.0   | 112.9  | 127.9  | 140.3  | 152.8  | 149.7  | 146.4  |
| 0.0    | 90°   | 0.0    | 0.0    | 0.0    | 0.0    | 0.0    | 0.0    | 0.0    | 0.0    | 0.0    | 0.0    |

REPORT NUMBER: P954017

CATALOG NUMBER: GLAN-SB7B-927-U-SLL

**CANDELA DISTRIBUTION (continued):**

| 215°   |       | 220°   | 225°   | 230°   | 235°   | 240°   | 245°   | 250°   | 255°   | 260°   | 265°   |
|--------|-------|--------|--------|--------|--------|--------|--------|--------|--------|--------|--------|
| 3339.9 | 0°    | 3339.9 | 3339.9 | 3339.9 | 3339.9 | 3339.9 | 3339.9 | 3339.9 | 3339.9 | 3339.9 | 3339.9 |
| 3052.1 | 2.5°  | 3043.2 | 3032.4 | 3043.2 | 3052.1 | 3060.8 | 3070.3 | 3079.8 | 3091.9 | 3104.1 | 3119.2 |
| 2859.5 | 5°    | 2850.4 | 2841.4 | 2850.4 | 2859.5 | 2868.6 | 2880.5 | 2892.4 | 2909.2 | 2926.0 | 2950.1 |
| 2744.1 | 7.5°  | 2736.0 | 2729.9 | 2736.0 | 2744.1 | 2752.3 | 2765.9 | 2779.6 | 2799.6 | 2819.6 | 2848.1 |
| 2712.7 | 10°   | 2705.8 | 2703.0 | 2705.8 | 2712.7 | 2719.6 | 2732.6 | 2745.5 | 2768.1 | 2790.4 | 2824.6 |
| 2761.2 | 12.5° | 2755.3 | 2754.2 | 2755.3 | 2761.2 | 2767.1 | 2781.4 | 2795.9 | 2824.7 | 2853.6 | 2897.1 |
| 2852.3 | 15°   | 2844.6 | 2844.0 | 2844.6 | 2852.3 | 2860.0 | 2880.0 | 2900.1 | 2943.9 | 2987.8 | 3049.8 |
| 2931.0 | 17.5° | 2921.1 | 2919.6 | 2921.1 | 2931.0 | 2940.7 | 2970.6 | 3000.3 | 3064.9 | 3129.5 | 3211.7 |
| 2972.8 | 20°   | 2960.6 | 2956.7 | 2960.6 | 2972.8 | 2984.9 | 3023.1 | 3061.2 | 3140.3 | 3219.5 | 3313.3 |
| 2969.6 | 22.5° | 2956.1 | 2950.3 | 2956.1 | 2969.6 | 2983.0 | 3023.3 | 3063.4 | 3145.0 | 3226.5 | 3316.2 |
| 2919.1 | 25°   | 2906.5 | 2899.1 | 2906.5 | 2919.1 | 2931.7 | 2966.5 | 3001.3 | 3073.6 | 3146.2 | 3219.6 |
| 2827.3 | 27.5° | 2821.5 | 2819.6 | 2821.5 | 2827.3 | 2833.1 | 2856.5 | 2879.8 | 2936.1 | 2992.4 | 3044.7 |
| 2706.2 | 30°   | 2706.2 | 2708.1 | 2706.2 | 2706.2 | 2706.2 | 2718.2 | 2730.1 | 2770.6 | 2810.9 | 2850.9 |
| 2565.3 | 32.5° | 2566.5 | 2568.4 | 2566.5 | 2565.3 | 2564.3 | 2572.1 | 2579.9 | 2612.1 | 2644.3 | 2681.1 |
| 2421.0 | 35°   | 2418.4 | 2417.2 | 2418.4 | 2421.0 | 2423.6 | 2435.4 | 2447.3 | 2476.9 | 2506.6 | 2532.6 |
| 2279.9 | 37.5° | 2268.5 | 2262.1 | 2268.5 | 2279.9 | 2291.3 | 2312.8 | 2334.5 | 2361.9 | 2389.2 | 2401.3 |
| 2147.0 | 40°   | 2126.0 | 2113.4 | 2126.0 | 2147.0 | 2168.3 | 2199.5 | 2231.1 | 2254.3 | 2277.5 | 2274.6 |
| 2017.2 | 42.5° | 1986.3 | 1966.0 | 1986.3 | 2017.2 | 2048.1 | 2087.1 | 2126.2 | 2145.7 | 2165.3 | 2150.6 |
| 1897.5 | 45°   | 1861.2 | 1837.9 | 1861.2 | 1897.5 | 1933.7 | 1978.3 | 2023.1 | 2040.6 | 2058.3 | 2037.2 |
| 1828.4 | 47.5° | 1794.9 | 1772.5 | 1794.9 | 1828.4 | 1862.0 | 1901.7 | 1941.4 | 1953.7 | 1966.0 | 1941.7 |
| 1798.1 | 50°   | 1767.1 | 1745.6 | 1767.1 | 1798.1 | 1829.2 | 1860.9 | 1892.7 | 1893.2 | 1894.0 | 1862.7 |
| 1780.3 | 52.5° | 1752.6 | 1732.8 | 1752.6 | 1780.3 | 1808.1 | 1834.0 | 1859.9 | 1853.2 | 1846.6 | 1809.5 |
| 1759.7 | 55°   | 1735.3 | 1717.4 | 1735.3 | 1759.7 | 1784.0 | 1806.6 | 1829.2 | 1819.9 | 1810.7 | 1771.4 |
| 1726.9 | 57.5° | 1702.7 | 1684.1 | 1702.7 | 1726.9 | 1751.0 | 1773.8 | 1796.6 | 1787.2 | 1777.9 | 1738.4 |
| 1682.0 | 60°   | 1657.2 | 1637.9 | 1657.2 | 1682.0 | 1706.9 | 1729.1 | 1751.4 | 1741.1 | 1730.9 | 1691.1 |
| 1612.8 | 62.5° | 1586.7 | 1563.6 | 1586.7 | 1612.8 | 1639.0 | 1659.1 | 1679.2 | 1669.3 | 1659.5 | 1623.1 |
| 1517.7 | 65°   | 1492.5 | 1472.6 | 1492.5 | 1517.7 | 1543.1 | 1562.4 | 1581.8 | 1571.8 | 1561.7 | 1529.6 |
| 1411.6 | 67.5° | 1388.0 | 1370.1 | 1388.0 | 1411.6 | 1435.2 | 1452.9 | 1470.7 | 1460.9 | 1451.1 | 1423.4 |
| 1300.3 | 70°   | 1277.8 | 1257.3 | 1277.8 | 1300.3 | 1322.9 | 1337.4 | 1351.9 | 1342.4 | 1332.9 | 1307.9 |
| 1175.5 | 72.5° | 1154.1 | 1134.2 | 1154.1 | 1175.5 | 1197.0 | 1209.1 | 1221.1 | 1209.9 | 1198.6 | 1174.1 |
| 1035.4 | 75°   | 1017.4 | 998.4  | 1017.4 | 1035.4 | 1053.5 | 1059.4 | 1065.3 | 1053.5 | 1041.7 | 1019.4 |
| 879.2  | 77.5° | 861.0  | 845.9  | 861.0  | 879.2  | 897.4  | 905.9  | 914.1  | 903.0  | 892.0  | 868.7  |
| 711.8  | 80°   | 687.2  | 658.8  | 687.2  | 711.8  | 736.3  | 739.8  | 743.3  | 728.7  | 714.1  | 696.4  |
| 531.1  | 82.5° | 510.3  | 492.1  | 510.3  | 531.1  | 551.7  | 553.4  | 554.9  | 530.1  | 505.2  | 467.3  |
| 331.2  | 85°   | 315.0  | 298.6  | 315.0  | 331.2  | 347.3  | 349.9  | 352.5  | 321.7  | 290.9  | 255.3  |
| 138.2  | 87.5° | 129.7  | 121.8  | 129.7  | 138.2  | 146.4  | 149.7  | 152.8  | 140.3  | 127.9  | 112.9  |
| 0.0    | 90°   | 0.0    | 0.0    | 0.0    | 0.0    | 0.0    | 0.0    | 0.0    | 0.0    | 0.0    | 0.0    |

REPORT NUMBER: P954017

CATALOG NUMBER: GLAN-SB7B-927-U-SLL

**CANDELA DISTRIBUTION (continued):**

| 270°   |       | 275°   | 280°   | 285°   | 290°   | 295°   | 300°   | 305°   | 310°   | 315°   | 320°   |
|--------|-------|--------|--------|--------|--------|--------|--------|--------|--------|--------|--------|
| 3339.9 | 0°    | 3339.9 | 3339.9 | 3339.9 | 3339.9 | 3339.9 | 3339.9 | 3339.9 | 3339.9 | 3339.9 | 3339.9 |
| 3134.2 | 2.5°  | 3153.6 | 3173.1 | 3192.4 | 3211.8 | 3233.8 | 3256.0 | 3280.5 | 3305.1 | 3335.5 | 3362.8 |
| 2974.0 | 5°    | 3005.3 | 3036.5 | 3070.8 | 3105.2 | 3144.0 | 3182.9 | 3229.5 | 3275.9 | 3329.1 | 3382.9 |
| 2876.6 | 7.5°  | 2914.7 | 2952.9 | 2996.2 | 3039.4 | 3090.7 | 3141.9 | 3203.6 | 3265.4 | 3334.2 | 3407.6 |
| 2858.7 | 10°   | 2901.6 | 2944.6 | 2991.2 | 3037.7 | 3089.0 | 3140.3 | 3205.4 | 3270.5 | 3344.4 | 3435.0 |
| 2940.7 | 12.5° | 2985.1 | 3029.5 | 3065.9 | 3102.6 | 3136.4 | 3170.5 | 3223.6 | 3276.9 | 3345.7 | 3440.9 |
| 3111.8 | 15°   | 3150.4 | 3189.0 | 3198.5 | 3207.9 | 3203.3 | 3198.7 | 3224.1 | 3249.6 | 3304.7 | 3410.2 |
| 3293.8 | 17.5° | 3324.8 | 3356.0 | 3326.4 | 3296.6 | 3240.7 | 3184.9 | 3175.6 | 3166.3 | 3200.2 | 3324.3 |
| 3407.2 | 20°   | 3421.7 | 3436.1 | 3373.9 | 3311.8 | 3214.6 | 3117.6 | 3074.0 | 3030.4 | 3039.4 | 3183.8 |
| 3406.0 | 22.5° | 3397.4 | 3388.6 | 3307.8 | 3226.9 | 3115.9 | 3005.2 | 2940.7 | 2876.3 | 2858.7 | 3023.1 |
| 3293.2 | 25°   | 3263.6 | 3233.8 | 3154.2 | 3074.6 | 2974.9 | 2875.4 | 2801.0 | 2726.7 | 2679.3 | 2847.8 |
| 3097.1 | 27.5° | 3063.9 | 3030.8 | 2967.0 | 2903.2 | 2821.4 | 2739.5 | 2667.7 | 2596.0 | 2538.3 | 2691.7 |
| 2890.7 | 30°   | 2863.8 | 2836.9 | 2783.8 | 2730.9 | 2663.0 | 2595.1 | 2537.9 | 2481.0 | 2435.8 | 2564.6 |
| 2717.7 | 32.5° | 2687.7 | 2657.9 | 2607.0 | 2556.2 | 2501.9 | 2447.7 | 2414.0 | 2380.3 | 2360.1 | 2463.9 |
| 2558.8 | 35°   | 2522.9 | 2487.0 | 2436.6 | 2386.4 | 2345.1 | 2303.7 | 2294.4 | 2285.2 | 2293.5 | 2380.0 |
| 2413.3 | 37.5° | 2369.0 | 2324.6 | 2274.4 | 2224.3 | 2194.7 | 2164.9 | 2175.2 | 2185.4 | 2216.0 | 2291.6 |
| 2271.7 | 40°   | 2220.6 | 2169.6 | 2121.1 | 2072.7 | 2051.3 | 2029.9 | 2053.1 | 2076.3 | 2123.0 | 2191.6 |
| 2135.8 | 42.5° | 2080.7 | 2025.6 | 1979.6 | 1933.7 | 1916.2 | 1898.7 | 1929.5 | 1960.3 | 2019.2 | 2082.4 |
| 2016.0 | 45°   | 1958.9 | 1901.7 | 1858.1 | 1814.5 | 1799.7 | 1785.1 | 1814.9 | 1844.9 | 1901.9 | 1966.0 |
| 1917.3 | 47.5° | 1860.9 | 1804.5 | 1762.0 | 1719.3 | 1705.6 | 1691.8 | 1716.9 | 1742.0 | 1791.1 | 1873.8 |
| 1831.5 | 50°   | 1781.0 | 1730.5 | 1690.4 | 1650.1 | 1628.4 | 1606.9 | 1629.1 | 1651.4 | 1708.4 | 1817.1 |
| 1772.5 | 52.5° | 1725.3 | 1678.3 | 1641.5 | 1604.6 | 1572.3 | 1539.9 | 1561.8 | 1583.8 | 1663.6 | 1788.5 |
| 1732.1 | 55°   | 1691.0 | 1649.7 | 1610.0 | 1570.3 | 1524.4 | 1478.4 | 1513.1 | 1548.0 | 1668.1 | 1784.3 |
| 1698.8 | 57.5° | 1657.9 | 1617.2 | 1570.5 | 1523.9 | 1474.4 | 1424.9 | 1475.7 | 1526.4 | 1672.5 | 1775.1 |
| 1651.4 | 60°   | 1609.9 | 1568.5 | 1514.9 | 1461.3 | 1418.0 | 1374.6 | 1440.4 | 1506.2 | 1658.4 | 1726.1 |
| 1586.7 | 62.5° | 1542.5 | 1498.2 | 1435.7 | 1373.3 | 1345.7 | 1318.2 | 1400.3 | 1482.6 | 1623.8 | 1632.2 |
| 1497.6 | 65°   | 1455.3 | 1413.0 | 1346.0 | 1279.1 | 1268.6 | 1257.9 | 1345.5 | 1432.9 | 1540.5 | 1539.5 |
| 1395.7 | 67.5° | 1355.7 | 1315.6 | 1253.7 | 1191.9 | 1195.3 | 1198.6 | 1271.4 | 1344.2 | 1404.7 | 1407.5 |
| 1282.9 | 70°   | 1248.3 | 1213.7 | 1159.4 | 1105.0 | 1116.6 | 1128.1 | 1179.9 | 1231.7 | 1251.5 | 1251.5 |
| 1149.6 | 72.5° | 1118.4 | 1087.1 | 1044.4 | 1001.6 | 1018.4 | 1035.3 | 1070.8 | 1106.3 | 1106.1 | 1093.5 |
| 997.1  | 75°   | 968.8  | 940.5  | 908.7  | 876.9  | 893.2  | 909.3  | 936.7  | 964.0  | 968.9  | 911.0  |
| 845.2  | 77.5° | 820.9  | 796.5  | 770.8  | 744.9  | 761.3  | 777.7  | 799.6  | 821.5  | 824.1  | 728.6  |
| 678.6  | 80°   | 658.1  | 637.6  | 616.2  | 594.7  | 608.5  | 622.2  | 640.7  | 659.0  | 659.4  | 545.3  |
| 429.3  | 82.5° | 436.5  | 443.7  | 445.5  | 447.3  | 457.0  | 466.8  | 475.7  | 484.7  | 479.3  | 381.9  |
| 219.8  | 85°   | 239.7  | 259.5  | 268.9  | 278.1  | 289.0  | 299.9  | 309.5  | 319.1  | 312.1  | 239.7  |
| 98.0   | 87.5° | 113.3  | 128.4  | 128.8  | 129.2  | 131.2  | 133.3  | 137.1  | 141.0  | 132.0  | 101.9  |
| 0.0    | 90°   | 0.0    | 0.0    | 0.0    | 0.0    | 0.0    | 0.0    | 0.0    | 0.0    | 0.0    | 0.0    |

REPORT NUMBER: P954017

CATALOG NUMBER: GLAN-SB7B-927-U-SLL

**CANDELA DISTRIBUTION (continued):**

| 325°   |       | 330°   | 335°   | 340°   | 345°   | 350°   | 355°    | 360°    |
|--------|-------|--------|--------|--------|--------|--------|---------|---------|
| 3339.9 | 0°    | 3339.9 | 3339.9 | 3339.9 | 3339.9 | 3339.9 | 3339.9  | 3339.9  |
| 3391.0 | 2.5°  | 3419.2 | 3448.6 | 3478.1 | 3507.3 | 3536.7 | 3564.2  | 3591.8  |
| 3439.9 | 5°    | 3496.9 | 3558.0 | 3619.1 | 3679.7 | 3740.5 | 3801.3  | 3862.2  |
| 3487.2 | 7.5°  | 3566.8 | 3657.2 | 3747.5 | 3840.3 | 3933.1 | 4033.4  | 4133.9  |
| 3529.4 | 10°   | 3623.4 | 3733.3 | 3843.0 | 3965.5 | 4088.2 | 4215.2  | 4342.2  |
| 3547.4 | 12.5° | 3653.9 | 3783.4 | 3912.8 | 4051.8 | 4190.7 | 4330.1  | 4469.7  |
| 3533.5 | 15°   | 3656.8 | 3805.8 | 3954.9 | 4105.6 | 4256.3 | 4401.8  | 4547.2  |
| 3472.6 | 17.5° | 3620.9 | 3793.9 | 3966.9 | 4131.4 | 4295.8 | 4443.3  | 4590.8  |
| 3367.6 | 20°   | 3551.4 | 3761.1 | 3970.8 | 4151.5 | 4332.2 | 4485.6  | 4638.9  |
| 3244.5 | 22.5° | 3465.8 | 3720.8 | 3975.9 | 4178.7 | 4381.3 | 4538.0  | 4694.6  |
| 3106.9 | 25°   | 3366.2 | 3681.1 | 3996.1 | 4227.9 | 4459.5 | 4612.9  | 4766.4  |
| 2981.2 | 27.5° | 3270.7 | 3654.6 | 4038.4 | 4304.8 | 4571.0 | 4717.5  | 4863.8  |
| 2876.1 | 30°   | 3187.7 | 3642.2 | 4096.4 | 4404.3 | 4712.3 | 4853.7  | 4995.2  |
| 2785.5 | 32.5° | 3106.9 | 3626.8 | 4146.4 | 4508.3 | 4870.2 | 5010.2  | 5150.3  |
| 2696.4 | 35°   | 3012.9 | 3597.8 | 4183.0 | 4626.7 | 5070.4 | 5204.6  | 5338.7  |
| 2591.6 | 37.5° | 2891.6 | 3548.2 | 4204.8 | 4759.4 | 5313.9 | 5484.9  | 5655.9  |
| 2466.5 | 40°   | 2741.4 | 3479.9 | 4218.5 | 4927.8 | 5636.9 | 5886.0  | 6135.2  |
| 2328.5 | 42.5° | 2574.6 | 3409.4 | 4244.5 | 5148.1 | 6051.6 | 6411.3  | 6770.9  |
| 2181.9 | 45°   | 2397.7 | 3343.9 | 4290.3 | 5438.0 | 6585.7 | 7070.8  | 7555.9  |
| 2065.9 | 47.5° | 2258.0 | 3289.8 | 4321.7 | 5746.9 | 7172.0 | 7854.9  | 8537.6  |
| 1988.8 | 50°   | 2160.6 | 3230.9 | 4301.2 | 6033.4 | 7765.7 | 8795.1  | 9824.4  |
| 1938.1 | 52.5° | 2087.8 | 3131.3 | 4174.9 | 6219.5 | 8264.0 | 9782.7  | 11301.5 |
| 1901.3 | 55°   | 2018.3 | 2966.2 | 3914.1 | 6178.5 | 8442.8 | 10658.4 | 12874.0 |
| 1857.7 | 57.5° | 1940.4 | 2733.5 | 3526.4 | 5889.9 | 8253.5 | 11278.9 | 14304.4 |
| 1791.1 | 60°   | 1856.1 | 2431.3 | 3006.5 | 5352.8 | 7699.1 | 11434.0 | 15168.8 |
| 1675.2 | 62.5° | 1718.4 | 2069.6 | 2420.8 | 4626.5 | 6832.2 | 10781.0 | 14729.9 |
| 1559.9 | 65°   | 1580.3 | 1744.2 | 1908.1 | 3885.4 | 5862.8 | 9857.1  | 13851.3 |
| 1396.2 | 67.5° | 1384.8 | 1431.5 | 1478.0 | 3159.5 | 4841.0 | 8757.6  | 12674.1 |
| 1198.8 | 70°   | 1146.0 | 1132.8 | 1119.5 | 2487.7 | 3855.8 | 7557.8  | 11259.8 |
| 1018.8 | 72.5° | 943.9  | 903.7  | 863.6  | 1901.8 | 2940.1 | 6257.2  | 9574.5  |
| 827.2  | 75°   | 743.3  | 707.0  | 670.6  | 1380.3 | 2090.1 | 4766.3  | 7442.5  |
| 647.2  | 77.5° | 565.8  | 541.0  | 516.2  | 935.3  | 1354.4 | 3336.0  | 5317.5  |
| 476.5  | 80°   | 407.6  | 397.3  | 387.1  | 602.6  | 818.3  | 2149.3  | 3480.3  |
| 331.2  | 82.5° | 280.4  | 278.4  | 276.6  | 370.6  | 465.0  | 1244.0  | 2023.1  |
| 202.5  | 85°   | 165.3  | 166.4  | 167.3  | 198.1  | 229.2  | 559.6   | 890.1   |
| 86.6   | 87.5° | 71.5   | 72.4   | 73.3   | 82.2   | 91.0   | 183.3   | 275.6   |
| 0.0    | 90°   | 0.0    | 0.0    | 0.0    | 0.0    | 0.0    | 0.0     | 0.0     |

(END OF REPORT)