

Scaled data based on original data using  
LM-79-08 Approved Method: Electrical and Photometric Measurements of Solid-  
State Lighting Products

Test Report Prepared for  
Cooper Lighting Solutions  
(formerly Eaton)

Brand: STREETWORKS

Report Number: P948664

Luminaire Tested: **GLAN-SB3C-927-U-SLR**

Issue Date: 1/21/2025

### Test Information

Test Method: LM-79-08  
Report Number: P948664  
TEST IS SCALED FROM IESNA LM-79-08 TEST DATA (G2-2411-289-8)  
Test Lab: INNOVATION CENTER  
Issue Date: 1/21/2025  
Manufacturer: COOPER LIGHTING SOLUTIONS (FORMERLY EATON)  
Product Line: STREETWORKS  
Catalog Number: GLAN-SB3C-927-U-SLR  
Description: GALLEON AREA AND ROADWAY HIGH DENSITY LED LUMINAIRE  
(3) 90 CRI, 2700K, 615mA LIGHTSQUARES WITH 26 LEDS EACH AND SPILL LIGHT  
ELIMINATOR RIGHT OPTICS  
Light Source: -  
Ballast/Driver: -

### Summary

Lumens per Lamp: N/A  
Luminaire Lumens: 13628 lumens  
Efficiency: N/A  
Efficacy: 91.4 lumens/watt  
Luminous Opening: Rectangular (W 1' x L: 1' x H: 0')  
IES Classification: Type IV - Short  
BUG Rating: B2 - U0 - G3

Input Watts (W): 149.1  
Input Voltage (V): NR  
Input Current (Ain): NR  
Voltage Rise (V): NR  
Power Factor: NR  
Total Harmonic Distortion (THDi): NR  
Frequency (hertz): 60  
Stabilization Time: NR  
Operation Time: NR  
Ambient Temperature (°C): NR  
Test Distance: 24 FT




REPORT NUMBER: P948664

CATALOG NUMBER: GLAN-SB3C-927-U-SLR


## Iso-Footcandle Lines of Horizontal Illumination

× Max cd  
- - - 1/2 Max cd



Based on 25 foot mounting height. Maximum calculated value = 3.7 fc  
Type IV - Short - N/A

REPORT NUMBER: P948664  
CATALOG NUMBER: GLAN-SB3C-927-U-SLR



REPORT NUMBER: P948664

CATALOG NUMBER: GLAN-SB3C-927-U-SLR

**FLUX DISTRIBUTION:**

|                    |           | Downward | Upward | Total   |
|--------------------|-----------|----------|--------|---------|
| <b>House Side</b>  | Lumens    | 3463.6   | 0.0    | 3463.6  |
|                    | % Fixture | 25.4     | 0.0    | 25.4    |
| <b>Street Side</b> | Lumens    | 10164.4  | 0.0    | 10164.4 |
|                    | % Fixture | 74.6     | 0.0    | 74.6    |
| <b>Total</b>       | Lumens    | 13628.0  | 0.0    | 13628.0 |
|                    | % Fixture | 100.0    | 0.0    | 100.0   |

**ZONAL LUMENS:**

| Zone      | Lumens  | % Fixture |
|-----------|---------|-----------|
| 0°-10°    | 185.9   | 1.4       |
| 10°-20°   | 583.6   | 4.3       |
| 20°-30°   | 901.4   | 6.6       |
| 30°-40°   | 1142.3  | 8.4       |
| 40°-50°   | 1722.9  | 12.6      |
| 50°-60°   | 2783.6  | 20.4      |
| 60°-70°   | 3470.2  | 25.5      |
| 70°-80°   | 2275.6  | 16.7      |
| 80°-90°   | 562.6   | 4.1       |
| 90°-100°  | 0.0     | 0.0       |
| 100°-110° | 0.0     | 0.0       |
| 110°-120° | 0.0     | 0.0       |
| 120°-130° | 0.0     | 0.0       |
| 130°-140° | 0.0     | 0.0       |
| 140°-150° | 0.0     | 0.0       |
| 150°-160° | 0.0     | 0.0       |
| 160°-170° | 0.0     | 0.0       |
| 170°-180° | 0.0     | 0.0       |
| 0°-90°    | 13628.0 | 100.0     |
| 0°-180°   | 13628.0 | 100.0     |

**Coefficient of Utilization**



REPORT NUMBER: P948664


CATALOG NUMBER: GLAN-SB3C-927-U-SLR

**LUMINAIRE CLASSIFICATION SYSTEM LUMEN TABLE AND BUG RATING:**

| Zone |             | Lumens | % Fixture | Zone Rating/Lumen Limit |      |         |
|------|-------------|--------|-----------|-------------------------|------|---------|
|      |             |        |           | B                       | U    | G       |
| FL   | (0°-30°)    | 916.6  | 6.7       |                         |      |         |
| FM   | (30°-60°)   | 3975.0 | 29.2      |                         |      |         |
| FH   | (60°-80°)   | 4809.4 | 35.3      |                         |      | G2/5000 |
| FVH  | (80°-90°)   | 463.4  | 3.4       |                         |      | G3/500  |
| BL   | (0°-30°)    | 754.2  | 5.5       | B2/1000                 |      |         |
| BM   | (30°-60°)   | 1673.8 | 12.3      | B2/2500                 |      |         |
| BH   | (60°-80°)   | 936.4  | 6.9       | B2/1000                 |      | G2/1000 |
| BVH  | (80°-90°)   | 99.1   | 0.7       |                         |      | G1/100  |
| UL   | (90°-100°)  | 0.0    | 0.0       |                         | U0/0 |         |
| UH   | (100°-180°) | 0.0    | 0.0       |                         | U0/0 |         |

**BUG Rating: B2-U0-G3**

Type IV Short



REPORT NUMBER: P948664

CATALOG NUMBER: GLAN-SB3C-927-U-SLR

**CANDELA DISTRIBUTION (FULL):**

|       | 0°     | 5°     | 10°    | 15°    | 20°    | 25°    | 30°    | 35°    | 40°    | 45°    |
|-------|--------|--------|--------|--------|--------|--------|--------|--------|--------|--------|
| 0°    | 1874.0 | 1874.0 | 1874.0 | 1874.0 | 1874.0 | 1874.0 | 1874.0 | 1874.0 | 1874.0 | 1874.0 |
| 2.5°  | 2015.3 | 1999.8 | 1984.3 | 1967.9 | 1951.5 | 1934.9 | 1918.4 | 1902.6 | 1886.8 | 1871.5 |
| 5°    | 2167.0 | 2132.8 | 2098.7 | 2064.6 | 2030.6 | 1996.3 | 1962.1 | 1930.1 | 1898.1 | 1867.9 |
| 7.5°  | 2319.4 | 2263.1 | 2206.8 | 2154.7 | 2102.6 | 2051.9 | 2001.2 | 1956.6 | 1911.9 | 1870.7 |
| 10°   | 2436.3 | 2365.0 | 2293.8 | 2225.0 | 2156.2 | 2094.7 | 2033.0 | 1980.2 | 1927.3 | 1876.5 |
| 12.5° | 2507.9 | 2429.5 | 2351.3 | 2273.4 | 2195.4 | 2122.8 | 2050.1 | 1990.4 | 1930.6 | 1877.2 |
| 15°   | 2551.4 | 2469.7 | 2388.1 | 2303.6 | 2219.0 | 2135.4 | 2051.7 | 1982.6 | 1913.4 | 1854.2 |
| 17.5° | 2575.8 | 2493.0 | 2410.3 | 2318.0 | 2225.7 | 2128.7 | 2031.6 | 1948.4 | 1865.2 | 1795.6 |
| 20°   | 2602.8 | 2516.8 | 2430.7 | 2329.3 | 2227.9 | 2110.3 | 1992.6 | 1889.5 | 1786.4 | 1705.3 |
| 22.5° | 2634.1 | 2546.2 | 2458.2 | 2344.5 | 2230.8 | 2087.7 | 1944.6 | 1820.4 | 1696.2 | 1603.9 |
| 25°   | 2674.3 | 2588.2 | 2502.1 | 2372.2 | 2242.1 | 2065.4 | 1888.7 | 1743.2 | 1597.8 | 1503.3 |
| 27.5° | 2729.0 | 2646.9 | 2564.7 | 2415.3 | 2265.9 | 2050.5 | 1835.1 | 1672.7 | 1510.2 | 1424.2 |
| 30°   | 2802.7 | 2723.3 | 2644.0 | 2471.2 | 2298.4 | 2043.5 | 1788.5 | 1613.7 | 1438.9 | 1366.6 |
| 32.5° | 2889.7 | 2811.1 | 2732.6 | 2529.5 | 2326.4 | 2034.9 | 1743.2 | 1562.9 | 1382.5 | 1324.2 |
| 35°   | 2995.4 | 2920.2 | 2844.9 | 2595.9 | 2347.0 | 2018.6 | 1690.5 | 1512.9 | 1335.4 | 1286.8 |
| 37.5° | 3173.4 | 3077.4 | 2981.5 | 2670.4 | 2359.2 | 1990.8 | 1622.4 | 1454.1 | 1285.7 | 1243.3 |
| 40°   | 3442.3 | 3302.5 | 3162.7 | 2764.9 | 2366.9 | 1952.5 | 1538.1 | 1383.9 | 1229.7 | 1191.2 |
| 42.5° | 3799.0 | 3597.2 | 3395.4 | 2888.5 | 2381.5 | 1912.9 | 1444.5 | 1306.5 | 1168.4 | 1132.9 |
| 45°   | 4239.4 | 3967.3 | 3695.1 | 3051.1 | 2407.2 | 1876.2 | 1345.3 | 1224.2 | 1103.1 | 1067.1 |
| 47.5° | 4790.3 | 4407.2 | 4024.1 | 3224.4 | 2424.8 | 1845.9 | 1266.9 | 1159.1 | 1051.3 | 1004.9 |
| 50°   | 5512.2 | 4934.7 | 4357.2 | 3385.2 | 2413.3 | 1812.8 | 1212.3 | 1115.9 | 1019.5 | 958.6  |
| 52.5° | 6341.0 | 5488.9 | 4636.7 | 3489.6 | 2342.5 | 1756.9 | 1171.4 | 1087.4 | 1003.5 | 933.4  |
| 55°   | 7223.3 | 5980.2 | 4737.1 | 3466.6 | 2196.1 | 1664.3 | 1132.4 | 1066.8 | 1001.1 | 935.9  |
| 57.5° | 8025.8 | 6328.3 | 4630.8 | 3304.7 | 1978.6 | 1533.7 | 1088.7 | 1042.3 | 995.9  | 938.4  |
| 60°   | 8510.9 | 6415.4 | 4319.8 | 3003.3 | 1686.9 | 1364.1 | 1041.4 | 1004.9 | 968.5  | 930.5  |
| 62.5° | 8264.6 | 6049.0 | 3833.4 | 2595.8 | 1358.2 | 1161.2 | 964.2  | 939.9  | 915.8  | 911.1  |
| 65°   | 7771.6 | 5530.6 | 3289.5 | 2180.0 | 1070.6 | 978.6  | 886.6  | 875.2  | 863.8  | 864.4  |
| 67.5° | 7111.2 | 4913.7 | 2716.2 | 1772.7 | 829.3  | 803.2  | 777.0  | 783.4  | 789.7  | 788.1  |
| 70°   | 6317.6 | 4240.5 | 2163.4 | 1395.8 | 628.1  | 635.6  | 643.0  | 672.6  | 702.2  | 702.2  |
| 72.5° | 5372.0 | 3510.8 | 1649.6 | 1067.1 | 484.5  | 507.0  | 529.6  | 571.6  | 613.5  | 620.6  |
| 75°   | 4175.8 | 2674.3 | 1172.7 | 774.5  | 376.2  | 396.7  | 417.1  | 464.1  | 511.1  | 543.6  |
| 77.5° | 2983.5 | 1871.7 | 759.9  | 524.8  | 289.7  | 303.5  | 317.5  | 363.1  | 408.8  | 462.4  |
| 80°   | 1952.7 | 1205.9 | 459.1  | 338.1  | 217.2  | 222.9  | 228.7  | 267.4  | 306.0  | 370.0  |
| 82.5° | 1135.1 | 698.0  | 260.9  | 208.0  | 155.2  | 156.2  | 157.3  | 185.8  | 214.3  | 268.9  |
| 85°   | 499.4  | 314.0  | 128.6  | 111.2  | 93.8   | 93.3   | 92.8   | 113.6  | 134.5  | 175.1  |
| 87.5° | 154.6  | 102.8  | 51.1   | 46.1   | 41.1   | 40.6   | 40.1   | 48.6   | 57.2   | 74.1   |
| 90°   | 0.0    | 0.0    | 0.0    | 0.0    | 0.0    | 0.0    | 0.0    | 0.0    | 0.0    | 0.0    |

REPORT NUMBER: P948664

CATALOG NUMBER: GLAN-SB3C-927-U-SLR

**CANDELA DISTRIBUTION (continued):**

| 50°    |       | 55°    | 60°    | 65°    | 70°    | 75°    | 80°    | 85°    | 90°    | 95°    | 100°   |
|--------|-------|--------|--------|--------|--------|--------|--------|--------|--------|--------|--------|
| 1874.0 | 0°    | 1874.0 | 1874.0 | 1874.0 | 1874.0 | 1874.0 | 1874.0 | 1874.0 | 1874.0 | 1874.0 | 1874.0 |
| 1854.4 | 2.5°  | 1840.6 | 1826.9 | 1814.4 | 1802.1 | 1791.2 | 1780.3 | 1769.4 | 1758.6 | 1750.1 | 1741.7 |
| 1838.0 | 5°    | 1812.0 | 1785.9 | 1764.0 | 1742.2 | 1723.0 | 1703.7 | 1686.2 | 1668.7 | 1655.2 | 1641.7 |
| 1832.1 | 7.5°  | 1797.5 | 1762.9 | 1734.1 | 1705.3 | 1681.1 | 1656.8 | 1635.4 | 1614.0 | 1598.0 | 1582.0 |
| 1835.0 | 10°   | 1798.5 | 1761.9 | 1733.2 | 1704.4 | 1678.3 | 1652.1 | 1628.0 | 1603.9 | 1584.8 | 1565.6 |
| 1838.6 | 12.5° | 1808.7 | 1778.9 | 1759.8 | 1740.8 | 1720.2 | 1699.8 | 1674.8 | 1650.0 | 1625.5 | 1601.1 |
| 1823.3 | 15°   | 1809.0 | 1794.7 | 1797.3 | 1799.9 | 1794.6 | 1789.3 | 1767.6 | 1746.0 | 1711.2 | 1676.4 |
| 1776.5 | 17.5° | 1781.8 | 1787.0 | 1818.3 | 1849.7 | 1866.3 | 1883.0 | 1865.5 | 1848.1 | 1802.0 | 1755.9 |
| 1700.3 | 20°   | 1724.8 | 1749.2 | 1803.6 | 1858.1 | 1893.0 | 1927.9 | 1919.8 | 1911.7 | 1859.0 | 1806.4 |
| 1613.8 | 22.5° | 1650.0 | 1686.1 | 1748.3 | 1810.5 | 1855.9 | 1901.3 | 1906.2 | 1911.0 | 1860.7 | 1810.3 |
| 1529.9 | 25°   | 1571.6 | 1613.3 | 1669.2 | 1725.1 | 1769.8 | 1814.4 | 1831.1 | 1847.7 | 1806.4 | 1765.2 |
| 1456.5 | 27.5° | 1496.8 | 1537.1 | 1583.0 | 1628.9 | 1664.7 | 1700.5 | 1719.1 | 1737.7 | 1708.3 | 1678.9 |
| 1392.0 | 30°   | 1424.0 | 1456.0 | 1494.1 | 1532.3 | 1562.0 | 1591.7 | 1606.8 | 1621.9 | 1599.6 | 1577.1 |
| 1335.5 | 32.5° | 1354.4 | 1373.3 | 1403.7 | 1434.2 | 1462.7 | 1491.3 | 1508.0 | 1524.8 | 1504.3 | 1483.6 |
| 1282.2 | 35°   | 1287.3 | 1292.6 | 1315.8 | 1339.0 | 1367.1 | 1395.4 | 1415.5 | 1435.7 | 1421.0 | 1406.4 |
| 1226.2 | 37.5° | 1220.5 | 1214.7 | 1231.4 | 1248.0 | 1276.1 | 1304.3 | 1329.2 | 1354.1 | 1347.3 | 1340.5 |
| 1164.9 | 40°   | 1151.9 | 1138.9 | 1150.9 | 1162.9 | 1190.1 | 1217.3 | 1245.9 | 1274.6 | 1276.3 | 1277.8 |
| 1099.9 | 42.5° | 1082.6 | 1065.3 | 1075.1 | 1085.0 | 1110.7 | 1136.5 | 1167.5 | 1198.4 | 1206.6 | 1214.9 |
| 1035.1 | 45°   | 1018.3 | 1001.6 | 1009.8 | 1018.1 | 1042.5 | 1067.0 | 1099.1 | 1131.1 | 1143.0 | 1154.9 |
| 977.4  | 47.5° | 963.3  | 949.2  | 957.0  | 964.7  | 988.6  | 1012.5 | 1044.1 | 1075.8 | 1089.4 | 1103.1 |
| 926.6  | 50°   | 914.0  | 901.6  | 913.7  | 925.8  | 948.4  | 970.9  | 999.3  | 1027.6 | 1045.1 | 1062.7 |
| 888.7  | 52.5° | 876.3  | 864.0  | 882.2  | 900.3  | 921.0  | 941.7  | 968.0  | 994.5  | 1015.3 | 1036.1 |
| 868.5  | 55°   | 849.0  | 829.5  | 855.3  | 881.0  | 903.3  | 925.6  | 948.8  | 971.9  | 993.9  | 1015.9 |
| 856.4  | 57.5° | 828.0  | 799.5  | 827.2  | 855.0  | 881.2  | 907.4  | 930.2  | 953.2  | 975.4  | 997.5  |
| 845.1  | 60°   | 808.2  | 771.2  | 795.6  | 819.9  | 850.0  | 880.0  | 903.3  | 926.6  | 948.8  | 971.1  |
| 831.9  | 62.5° | 785.7  | 739.6  | 755.1  | 770.5  | 805.5  | 840.6  | 865.4  | 890.2  | 910.7  | 931.1  |
| 804.0  | 65°   | 754.9  | 705.8  | 711.8  | 717.7  | 755.2  | 792.8  | 816.5  | 840.3  | 858.2  | 876.2  |
| 754.2  | 67.5° | 713.3  | 672.5  | 670.6  | 668.8  | 703.4  | 738.2  | 760.7  | 783.1  | 798.6  | 814.2  |
| 691.1  | 70°   | 662.0  | 632.9  | 626.5  | 620.0  | 650.5  | 681.0  | 700.4  | 719.8  | 733.8  | 747.9  |
| 620.7  | 72.5° | 600.8  | 580.9  | 571.4  | 562.0  | 586.0  | 609.9  | 627.5  | 645.0  | 658.8  | 672.5  |
| 540.9  | 75°   | 525.6  | 510.2  | 501.1  | 492.0  | 509.8  | 527.7  | 543.6  | 559.5  | 572.0  | 584.5  |
| 460.9  | 77.5° | 448.6  | 436.3  | 427.1  | 417.9  | 432.5  | 446.9  | 460.6  | 474.2  | 487.4  | 500.5  |
| 369.8  | 80°   | 359.5  | 349.1  | 341.4  | 333.7  | 345.7  | 357.8  | 369.3  | 380.8  | 390.8  | 400.7  |
| 272.0  | 82.5° | 266.9  | 261.9  | 256.4  | 251.0  | 250.0  | 249.0  | 244.9  | 240.9  | 262.2  | 283.5  |
| 179.1  | 85°   | 173.7  | 168.3  | 162.2  | 156.0  | 150.9  | 145.6  | 134.5  | 123.3  | 143.2  | 163.2  |
| 79.1   | 87.5° | 76.9   | 74.8   | 73.6   | 72.5   | 72.3   | 72.1   | 63.6   | 55.0   | 63.4   | 71.8   |
| 0.0    | 90°   | 0.0    | 0.0    | 0.0    | 0.0    | 0.0    | 0.0    | 0.0    | 0.0    | 0.0    | 0.0    |

REPORT NUMBER: P948664

CATALOG NUMBER: GLAN-SB3C-927-U-SLR

**CANDELA DISTRIBUTION (continued):**

| 105°   |       | 110°   | 115°   | 120°   | 125°   | 130°   | 135°   | 140°   | 145°   | 150°   | 155°   |
|--------|-------|--------|--------|--------|--------|--------|--------|--------|--------|--------|--------|
| 1874.0 | 0°    | 1874.0 | 1874.0 | 1874.0 | 1874.0 | 1874.0 | 1874.0 | 1874.0 | 1874.0 | 1874.0 | 1874.0 |
| 1734.8 | 2.5°  | 1728.0 | 1722.7 | 1717.3 | 1712.5 | 1707.5 | 1701.4 | 1707.5 | 1712.5 | 1717.3 | 1722.7 |
| 1632.3 | 5°    | 1622.9 | 1616.2 | 1609.5 | 1604.4 | 1599.3 | 1594.2 | 1599.3 | 1604.4 | 1609.5 | 1616.2 |
| 1570.8 | 7.5°  | 1559.6 | 1551.9 | 1544.3 | 1539.7 | 1535.1 | 1531.7 | 1535.1 | 1539.7 | 1544.3 | 1551.9 |
| 1553.1 | 10°   | 1540.5 | 1533.2 | 1525.9 | 1522.0 | 1518.2 | 1516.6 | 1518.2 | 1522.0 | 1525.9 | 1533.2 |
| 1584.9 | 12.5° | 1568.7 | 1560.6 | 1552.5 | 1549.2 | 1545.9 | 1545.3 | 1545.9 | 1549.2 | 1552.5 | 1560.6 |
| 1651.8 | 15°   | 1627.2 | 1615.9 | 1604.7 | 1600.4 | 1596.0 | 1595.7 | 1596.0 | 1600.4 | 1604.7 | 1615.9 |
| 1719.6 | 17.5° | 1683.4 | 1666.7 | 1650.0 | 1644.5 | 1639.0 | 1638.1 | 1639.0 | 1644.5 | 1650.0 | 1666.7 |
| 1761.9 | 20°   | 1717.6 | 1696.2 | 1674.8 | 1667.9 | 1661.1 | 1659.0 | 1661.1 | 1667.9 | 1674.8 | 1696.2 |
| 1764.6 | 22.5° | 1718.8 | 1696.3 | 1673.7 | 1666.1 | 1658.6 | 1655.4 | 1658.6 | 1666.1 | 1673.7 | 1696.3 |
| 1724.5 | 25°   | 1684.0 | 1664.4 | 1644.9 | 1637.8 | 1630.8 | 1626.6 | 1630.8 | 1637.8 | 1644.9 | 1664.4 |
| 1647.4 | 27.5° | 1615.8 | 1602.7 | 1589.6 | 1586.3 | 1583.1 | 1582.0 | 1583.1 | 1586.3 | 1589.6 | 1602.7 |
| 1554.5 | 30°   | 1531.8 | 1525.1 | 1518.4 | 1518.4 | 1518.4 | 1519.5 | 1518.4 | 1518.4 | 1518.4 | 1525.1 |
| 1465.6 | 32.5° | 1447.5 | 1443.2 | 1438.8 | 1439.3 | 1440.0 | 1441.1 | 1440.0 | 1439.3 | 1438.8 | 1443.2 |
| 1389.7 | 35°   | 1373.1 | 1366.4 | 1359.8 | 1358.4 | 1356.9 | 1356.2 | 1356.9 | 1358.4 | 1359.8 | 1366.4 |
| 1325.2 | 37.5° | 1309.8 | 1297.7 | 1285.6 | 1279.2 | 1272.8 | 1269.2 | 1272.8 | 1279.2 | 1285.6 | 1297.7 |
| 1264.8 | 40°   | 1251.8 | 1234.1 | 1216.6 | 1204.6 | 1192.8 | 1185.8 | 1192.8 | 1204.6 | 1216.6 | 1234.1 |
| 1203.9 | 42.5° | 1193.0 | 1171.0 | 1149.1 | 1131.8 | 1114.5 | 1103.1 | 1114.5 | 1131.8 | 1149.1 | 1171.0 |
| 1144.9 | 45°   | 1135.1 | 1110.0 | 1085.0 | 1064.6 | 1044.3 | 1031.2 | 1044.3 | 1064.6 | 1085.0 | 1110.0 |
| 1096.2 | 47.5° | 1089.3 | 1067.0 | 1044.7 | 1025.9 | 1007.1 | 994.5  | 1007.1 | 1025.9 | 1044.7 | 1067.0 |
| 1062.3 | 50°   | 1062.0 | 1044.1 | 1026.3 | 1008.9 | 991.5  | 979.4  | 991.5  | 1008.9 | 1026.3 | 1044.1 |
| 1039.8 | 52.5° | 1043.6 | 1029.0 | 1014.5 | 998.9  | 983.4  | 972.2  | 983.4  | 998.9  | 1014.5 | 1029.0 |
| 1021.1 | 55°   | 1026.3 | 1013.6 | 1001.0 | 987.3  | 973.7  | 963.6  | 973.7  | 987.3  | 1001.0 | 1013.6 |
| 1002.8 | 57.5° | 1008.0 | 995.2  | 982.4  | 968.9  | 955.3  | 944.9  | 955.3  | 968.9  | 982.4  | 995.2  |
| 976.9  | 60°   | 982.6  | 970.1  | 957.7  | 943.7  | 929.8  | 919.0  | 929.8  | 943.7  | 957.7  | 970.1  |
| 936.6  | 62.5° | 942.2  | 930.9  | 919.6  | 904.9  | 890.2  | 877.3  | 890.2  | 904.9  | 919.6  | 930.9  |
| 881.9  | 65°   | 887.5  | 876.7  | 865.8  | 851.6  | 837.4  | 826.2  | 837.4  | 851.6  | 865.8  | 876.7  |
| 819.7  | 67.5° | 825.2  | 815.2  | 805.2  | 792.0  | 778.8  | 768.7  | 778.8  | 792.0  | 805.2  | 815.2  |
| 753.2  | 70°   | 758.5  | 750.4  | 742.3  | 729.6  | 716.9  | 705.4  | 716.9  | 729.6  | 742.3  | 750.4  |
| 678.8  | 72.5° | 685.2  | 678.4  | 671.6  | 659.6  | 647.5  | 636.4  | 647.5  | 659.6  | 671.6  | 678.4  |
| 591.1  | 75°   | 597.7  | 594.4  | 591.1  | 581.0  | 570.8  | 560.2  | 570.8  | 581.0  | 591.1  | 594.4  |
| 506.7  | 77.5° | 512.9  | 508.3  | 503.5  | 493.3  | 483.1  | 474.6  | 483.1  | 493.3  | 503.5  | 508.3  |
| 408.9  | 80°   | 417.1  | 415.1  | 413.1  | 399.4  | 385.6  | 369.6  | 385.6  | 399.4  | 413.1  | 415.1  |
| 297.4  | 82.5° | 311.4  | 310.5  | 309.6  | 298.0  | 286.3  | 276.1  | 286.3  | 298.0  | 309.6  | 310.5  |
| 180.5  | 85°   | 197.8  | 196.3  | 194.9  | 185.8  | 176.8  | 167.5  | 176.8  | 185.8  | 194.9  | 196.3  |
| 78.7   | 87.5° | 85.7   | 84.0   | 82.1   | 77.5   | 72.8   | 68.3   | 72.8   | 77.5   | 82.1   | 84.0   |
| 0.0    | 90°   | 0.0    | 0.0    | 0.0    | 0.0    | 0.0    | 0.0    | 0.0    | 0.0    | 0.0    | 0.0    |

REPORT NUMBER: P948664

CATALOG NUMBER: GLAN-SB3C-927-U-SLR

**CANDELA DISTRIBUTION (continued):**

| 160°   |       | 165°   | 170°   | 175°   | 180°   | 185°   | 190°   | 195°   | 200°   | 205°   | 210°   |
|--------|-------|--------|--------|--------|--------|--------|--------|--------|--------|--------|--------|
| 1874.0 | 0°    | 1874.0 | 1874.0 | 1874.0 | 1874.0 | 1874.0 | 1874.0 | 1874.0 | 1874.0 | 1874.0 | 1874.0 |
| 1728.0 | 2.5°  | 1734.8 | 1741.7 | 1750.1 | 1758.6 | 1769.4 | 1780.3 | 1791.2 | 1802.1 | 1814.4 | 1826.9 |
| 1622.9 | 5°    | 1632.3 | 1641.7 | 1655.2 | 1668.7 | 1686.2 | 1703.7 | 1723.0 | 1742.2 | 1764.0 | 1785.9 |
| 1559.6 | 7.5°  | 1570.8 | 1582.0 | 1598.0 | 1614.0 | 1635.4 | 1656.8 | 1681.1 | 1705.3 | 1734.1 | 1762.9 |
| 1540.5 | 10°   | 1553.1 | 1565.6 | 1584.8 | 1603.9 | 1628.0 | 1652.1 | 1678.3 | 1704.4 | 1733.2 | 1761.9 |
| 1568.7 | 12.5° | 1584.9 | 1601.1 | 1625.5 | 1650.0 | 1674.8 | 1699.8 | 1720.2 | 1740.8 | 1759.8 | 1778.9 |
| 1627.2 | 15°   | 1651.8 | 1676.4 | 1711.2 | 1746.0 | 1767.6 | 1789.3 | 1794.6 | 1799.9 | 1797.3 | 1794.7 |
| 1683.4 | 17.5° | 1719.6 | 1755.9 | 1802.0 | 1848.1 | 1865.5 | 1883.0 | 1866.3 | 1849.7 | 1818.3 | 1787.0 |
| 1717.6 | 20°   | 1761.9 | 1806.4 | 1859.0 | 1911.7 | 1919.8 | 1927.9 | 1893.0 | 1858.1 | 1803.6 | 1749.2 |
| 1718.8 | 22.5° | 1764.6 | 1810.3 | 1860.7 | 1911.0 | 1906.2 | 1901.3 | 1855.9 | 1810.5 | 1748.3 | 1686.1 |
| 1684.0 | 25°   | 1724.5 | 1765.2 | 1806.4 | 1847.7 | 1831.1 | 1814.4 | 1769.8 | 1725.1 | 1669.2 | 1613.3 |
| 1615.8 | 27.5° | 1647.4 | 1678.9 | 1708.3 | 1737.7 | 1719.1 | 1700.5 | 1664.7 | 1628.9 | 1583.0 | 1537.1 |
| 1531.8 | 30°   | 1554.5 | 1577.1 | 1599.6 | 1621.9 | 1606.8 | 1591.7 | 1562.0 | 1532.3 | 1494.1 | 1456.0 |
| 1447.5 | 32.5° | 1465.6 | 1483.6 | 1504.3 | 1524.8 | 1508.0 | 1491.3 | 1462.7 | 1434.2 | 1403.7 | 1373.3 |
| 1373.1 | 35°   | 1389.7 | 1406.4 | 1421.0 | 1435.7 | 1415.5 | 1395.4 | 1367.1 | 1339.0 | 1315.8 | 1292.6 |
| 1309.8 | 37.5° | 1325.2 | 1340.5 | 1347.3 | 1354.1 | 1329.2 | 1304.3 | 1276.1 | 1248.0 | 1231.4 | 1214.7 |
| 1251.8 | 40°   | 1264.8 | 1277.8 | 1276.3 | 1274.6 | 1245.9 | 1217.3 | 1190.1 | 1162.9 | 1150.9 | 1138.9 |
| 1193.0 | 42.5° | 1203.9 | 1214.9 | 1206.6 | 1198.4 | 1167.5 | 1136.5 | 1110.7 | 1085.0 | 1075.1 | 1065.3 |
| 1135.1 | 45°   | 1144.9 | 1154.9 | 1143.0 | 1131.1 | 1099.1 | 1067.0 | 1042.5 | 1018.1 | 1009.8 | 1001.6 |
| 1089.3 | 47.5° | 1096.2 | 1103.1 | 1089.4 | 1075.8 | 1044.1 | 1012.5 | 988.6  | 964.7  | 957.0  | 949.2  |
| 1062.0 | 50°   | 1062.3 | 1062.7 | 1045.1 | 1027.6 | 999.3  | 970.9  | 948.4  | 925.8  | 913.7  | 901.6  |
| 1043.6 | 52.5° | 1039.8 | 1036.1 | 1015.3 | 994.5  | 968.0  | 941.7  | 921.0  | 900.3  | 882.2  | 864.0  |
| 1026.3 | 55°   | 1021.1 | 1015.9 | 993.9  | 971.9  | 948.8  | 925.6  | 903.3  | 881.0  | 855.3  | 829.5  |
| 1008.0 | 57.5° | 1002.8 | 997.5  | 975.4  | 953.2  | 930.2  | 907.4  | 881.2  | 855.0  | 827.2  | 799.5  |
| 982.6  | 60°   | 976.9  | 971.1  | 948.8  | 926.6  | 903.3  | 880.0  | 850.0  | 819.9  | 795.6  | 771.2  |
| 942.2  | 62.5° | 936.6  | 931.1  | 910.7  | 890.2  | 865.4  | 840.6  | 805.5  | 770.5  | 755.1  | 739.6  |
| 887.5  | 65°   | 881.9  | 876.2  | 858.2  | 840.3  | 816.5  | 792.8  | 755.2  | 717.7  | 711.8  | 705.8  |
| 825.2  | 67.5° | 819.7  | 814.2  | 798.6  | 783.1  | 760.7  | 738.2  | 703.4  | 668.8  | 670.6  | 672.5  |
| 758.5  | 70°   | 753.2  | 747.9  | 733.8  | 719.8  | 700.4  | 681.0  | 650.5  | 620.0  | 626.5  | 632.9  |
| 685.2  | 72.5° | 678.8  | 672.5  | 658.8  | 645.0  | 627.5  | 609.9  | 586.0  | 562.0  | 571.4  | 580.9  |
| 597.7  | 75°   | 591.1  | 584.5  | 572.0  | 559.5  | 543.6  | 527.7  | 509.8  | 492.0  | 501.1  | 510.2  |
| 512.9  | 77.5° | 506.7  | 500.5  | 487.4  | 474.2  | 460.6  | 446.9  | 432.5  | 417.9  | 427.1  | 436.3  |
| 417.1  | 80°   | 408.9  | 400.7  | 390.8  | 380.8  | 369.3  | 357.8  | 345.7  | 333.7  | 341.4  | 349.1  |
| 311.4  | 82.5° | 297.4  | 283.5  | 262.2  | 240.9  | 244.9  | 249.0  | 250.0  | 251.0  | 256.4  | 261.9  |
| 197.8  | 85°   | 180.5  | 163.2  | 143.2  | 123.3  | 134.5  | 145.6  | 150.9  | 156.0  | 162.2  | 168.3  |
| 85.7   | 87.5° | 78.7   | 71.8   | 63.4   | 55.0   | 63.6   | 72.1   | 72.3   | 72.5   | 73.6   | 74.8   |
| 0.0    | 90°   | 0.0    | 0.0    | 0.0    | 0.0    | 0.0    | 0.0    | 0.0    | 0.0    | 0.0    | 0.0    |

REPORT NUMBER: P948664

CATALOG NUMBER: GLAN-SB3C-927-U-SLR

**CANDELA DISTRIBUTION (continued):**

| 215°   |       | 220°   | 225°   | 230°   | 235°   | 240°   | 245°   | 250°   | 255°   | 260°   | 265°   |
|--------|-------|--------|--------|--------|--------|--------|--------|--------|--------|--------|--------|
| 1874.0 | 0°    | 1874.0 | 1874.0 | 1874.0 | 1874.0 | 1874.0 | 1874.0 | 1874.0 | 1874.0 | 1874.0 | 1874.0 |
| 1840.6 | 2.5°  | 1854.4 | 1871.5 | 1886.8 | 1902.6 | 1918.4 | 1934.9 | 1951.5 | 1967.9 | 1984.3 | 1999.8 |
| 1812.0 | 5°    | 1838.0 | 1867.9 | 1898.1 | 1930.1 | 1962.1 | 1996.3 | 2030.6 | 2064.6 | 2098.7 | 2132.8 |
| 1797.5 | 7.5°  | 1832.1 | 1870.7 | 1911.9 | 1956.6 | 2001.2 | 2051.9 | 2102.6 | 2154.7 | 2206.8 | 2263.1 |
| 1798.5 | 10°   | 1835.0 | 1876.5 | 1927.3 | 1980.2 | 2033.0 | 2094.7 | 2156.2 | 2225.0 | 2293.8 | 2365.0 |
| 1808.7 | 12.5° | 1838.6 | 1877.2 | 1930.6 | 1990.4 | 2050.1 | 2122.8 | 2195.4 | 2273.4 | 2351.3 | 2429.5 |
| 1809.0 | 15°   | 1823.3 | 1854.2 | 1913.4 | 1982.6 | 2051.7 | 2135.4 | 2219.0 | 2303.6 | 2388.1 | 2469.7 |
| 1781.8 | 17.5° | 1776.5 | 1795.6 | 1865.2 | 1948.4 | 2031.6 | 2128.7 | 2225.7 | 2318.0 | 2410.3 | 2493.0 |
| 1724.8 | 20°   | 1700.3 | 1705.3 | 1786.4 | 1889.5 | 1992.6 | 2110.3 | 2227.9 | 2329.3 | 2430.7 | 2516.8 |
| 1650.0 | 22.5° | 1613.8 | 1603.9 | 1696.2 | 1820.4 | 1944.6 | 2087.7 | 2230.8 | 2344.5 | 2458.2 | 2546.2 |
| 1571.6 | 25°   | 1529.9 | 1503.3 | 1597.8 | 1743.2 | 1888.7 | 2065.4 | 2242.1 | 2372.2 | 2502.1 | 2588.2 |
| 1496.8 | 27.5° | 1456.5 | 1424.2 | 1510.2 | 1672.7 | 1835.1 | 2050.5 | 2265.9 | 2415.3 | 2564.7 | 2646.9 |
| 1424.0 | 30°   | 1392.0 | 1366.6 | 1438.9 | 1613.7 | 1788.5 | 2043.5 | 2298.4 | 2471.2 | 2644.0 | 2723.3 |
| 1354.4 | 32.5° | 1335.5 | 1324.2 | 1382.5 | 1562.9 | 1743.2 | 2034.9 | 2326.4 | 2529.5 | 2732.6 | 2811.1 |
| 1287.3 | 35°   | 1282.2 | 1286.8 | 1335.4 | 1512.9 | 1690.5 | 2018.6 | 2347.0 | 2595.9 | 2844.9 | 2920.2 |
| 1220.5 | 37.5° | 1226.2 | 1243.3 | 1285.7 | 1454.1 | 1622.4 | 1990.8 | 2359.2 | 2670.4 | 2981.5 | 3077.4 |
| 1151.9 | 40°   | 1164.9 | 1191.2 | 1229.7 | 1383.9 | 1538.1 | 1952.5 | 2366.9 | 2764.9 | 3162.7 | 3302.5 |
| 1082.6 | 42.5° | 1099.9 | 1132.9 | 1168.4 | 1306.5 | 1444.5 | 1912.9 | 2381.5 | 2888.5 | 3395.4 | 3597.2 |
| 1018.3 | 45°   | 1035.1 | 1067.1 | 1103.1 | 1224.2 | 1345.3 | 1876.2 | 2407.2 | 3051.1 | 3695.1 | 3967.3 |
| 963.3  | 47.5° | 977.4  | 1004.9 | 1051.3 | 1159.1 | 1266.9 | 1845.9 | 2424.8 | 3224.4 | 4024.1 | 4407.2 |
| 914.0  | 50°   | 926.6  | 958.6  | 1019.5 | 1115.9 | 1212.3 | 1812.8 | 2413.3 | 3385.2 | 4357.2 | 4934.7 |
| 876.3  | 52.5° | 888.7  | 933.4  | 1003.5 | 1087.4 | 1171.4 | 1756.9 | 2342.5 | 3489.6 | 4636.7 | 5488.9 |
| 849.0  | 55°   | 868.5  | 935.9  | 1001.1 | 1066.8 | 1132.4 | 1664.3 | 2196.1 | 3466.6 | 4737.1 | 5980.2 |
| 828.0  | 57.5° | 856.4  | 938.4  | 995.9  | 1042.3 | 1088.7 | 1533.7 | 1978.6 | 3304.7 | 4630.8 | 6328.3 |
| 808.2  | 60°   | 845.1  | 930.5  | 968.5  | 1004.9 | 1041.4 | 1364.1 | 1686.9 | 3003.3 | 4319.8 | 6415.4 |
| 785.7  | 62.5° | 831.9  | 911.1  | 915.8  | 939.9  | 964.2  | 1161.2 | 1358.2 | 2595.8 | 3833.4 | 6049.0 |
| 754.9  | 65°   | 804.0  | 864.4  | 863.8  | 875.2  | 886.6  | 978.6  | 1070.6 | 2180.0 | 3289.5 | 5530.6 |
| 713.3  | 67.5° | 754.2  | 788.1  | 789.7  | 783.4  | 777.0  | 803.2  | 829.3  | 1772.7 | 2716.2 | 4913.7 |
| 662.0  | 70°   | 691.1  | 702.2  | 702.2  | 672.6  | 643.0  | 635.6  | 628.1  | 1395.8 | 2163.4 | 4240.5 |
| 600.8  | 72.5° | 620.7  | 620.6  | 613.5  | 571.6  | 529.6  | 507.0  | 484.5  | 1067.1 | 1649.6 | 3510.8 |
| 525.6  | 75°   | 540.9  | 543.6  | 511.1  | 464.1  | 417.1  | 396.7  | 376.2  | 774.5  | 1172.7 | 2674.3 |
| 448.6  | 77.5° | 460.9  | 462.4  | 408.8  | 363.1  | 317.5  | 303.5  | 289.7  | 524.8  | 759.9  | 1871.7 |
| 359.5  | 80°   | 369.8  | 370.0  | 306.0  | 267.4  | 228.7  | 222.9  | 217.2  | 338.1  | 459.1  | 1205.9 |
| 266.9  | 82.5° | 272.0  | 268.9  | 214.3  | 185.8  | 157.3  | 156.2  | 155.2  | 208.0  | 260.9  | 698.0  |
| 173.7  | 85°   | 179.1  | 175.1  | 134.5  | 113.6  | 92.8   | 93.3   | 93.8   | 111.2  | 128.6  | 314.0  |
| 76.9   | 87.5° | 79.1   | 74.1   | 57.2   | 48.6   | 40.1   | 40.6   | 41.1   | 46.1   | 51.1   | 102.8  |
| 0.0    | 90°   | 0.0    | 0.0    | 0.0    | 0.0    | 0.0    | 0.0    | 0.0    | 0.0    | 0.0    | 0.0    |

REPORT NUMBER: P948664

CATALOG NUMBER: GLAN-SB3C-927-U-SLR

**CANDELA DISTRIBUTION (continued):**

| 270°   |       | 275°   | 280°   | 285°   | 290°   | 295°    | 300°    | 305°    | 310°    | 315°    | 320°    |
|--------|-------|--------|--------|--------|--------|---------|---------|---------|---------|---------|---------|
| 1874.0 | 0°    | 1874.0 | 1874.0 | 1874.0 | 1874.0 | 1874.0  | 1874.0  | 1874.0  | 1874.0  | 1874.0  | 1874.0  |
| 2015.3 | 2.5°  | 2022.9 | 2030.6 | 2041.4 | 2052.3 | 2058.8  | 2065.2  | 2068.5  | 2071.7  | 2070.3  | 2071.7  |
| 2167.0 | 5°    | 2193.7 | 2220.4 | 2246.9 | 2273.4 | 2287.8  | 2302.2  | 2310.9  | 2319.7  | 2326.3  | 2319.7  |
| 2319.4 | 7.5°  | 2362.9 | 2406.2 | 2445.3 | 2484.3 | 2507.9  | 2531.4  | 2544.1  | 2556.8  | 2562.9  | 2556.8  |
| 2436.3 | 10°   | 2487.6 | 2539.0 | 2584.8 | 2630.6 | 2658.4  | 2686.0  | 2698.3  | 2710.6  | 2715.3  | 2710.6  |
| 2507.9 | 12.5° | 2563.5 | 2619.1 | 2660.5 | 2701.8 | 2721.9  | 2742.1  | 2748.8  | 2755.6  | 2756.3  | 2755.6  |
| 2551.4 | 15°   | 2599.4 | 2647.4 | 2673.3 | 2699.3 | 2700.1  | 2700.8  | 2693.6  | 2686.4  | 2677.9  | 2686.4  |
| 2575.8 | 17.5° | 2608.2 | 2640.7 | 2641.2 | 2641.6 | 2612.5  | 2583.4  | 2556.7  | 2529.9  | 2511.1  | 2529.9  |
| 2602.8 | 20°   | 2614.1 | 2625.4 | 2591.3 | 2557.1 | 2492.8  | 2428.5  | 2381.7  | 2334.9  | 2306.1  | 2334.9  |
| 2634.1 | 22.5° | 2619.2 | 2604.4 | 2533.7 | 2462.9 | 2368.3  | 2273.8  | 2215.3  | 2156.7  | 2124.9  | 2156.7  |
| 2674.3 | 25°   | 2627.6 | 2580.8 | 2473.4 | 2366.0 | 2251.1  | 2136.3  | 2074.7  | 2013.3  | 1983.3  | 2013.3  |
| 2729.0 | 27.5° | 2645.4 | 2561.8 | 2419.5 | 2277.2 | 2150.0  | 2022.7  | 1962.1  | 1901.7  | 1873.2  | 1901.7  |
| 2802.7 | 30°   | 2678.1 | 2553.5 | 2378.3 | 2203.2 | 2070.6  | 1938.0  | 1881.8  | 1825.6  | 1799.2  | 1825.6  |
| 2889.7 | 32.5° | 2719.1 | 2548.5 | 2350.3 | 2152.1 | 2027.5  | 1902.9  | 1858.8  | 1814.6  | 1795.6  | 1814.6  |
| 2995.4 | 35°   | 2786.6 | 2577.8 | 2371.3 | 2164.8 | 2078.3  | 1991.8  | 1981.5  | 1971.2  | 1969.6  | 1971.2  |
| 3173.4 | 37.5° | 2927.7 | 2682.1 | 2494.4 | 2306.7 | 2301.1  | 2295.5  | 2342.5  | 2389.6  | 2414.0  | 2389.6  |
| 3442.3 | 40°   | 3175.2 | 2908.0 | 2768.5 | 2628.9 | 2727.4  | 2825.9  | 2940.2  | 3054.6  | 3111.5  | 3054.6  |
| 3799.0 | 42.5° | 3533.9 | 3268.9 | 3188.5 | 3108.1 | 3322.9  | 3537.8  | 3745.8  | 3953.7  | 4075.8  | 3953.7  |
| 4239.4 | 45°   | 4001.3 | 3763.2 | 3727.7 | 3692.2 | 4036.4  | 4380.7  | 4722.5  | 5064.2  | 5271.7  | 5064.2  |
| 4790.3 | 47.5° | 4558.6 | 4327.0 | 4319.8 | 4312.6 | 4809.2  | 5305.6  | 5805.9  | 6306.1  | 6599.9  | 6306.1  |
| 5512.2 | 50°   | 5226.1 | 4940.1 | 4941.3 | 4942.5 | 5582.5  | 6222.5  | 6882.8  | 7543.2  | 7942.4  | 7543.2  |
| 6341.0 | 52.5° | 5994.5 | 5648.1 | 5613.1 | 5578.0 | 6342.5  | 7107.0  | 7924.0  | 8741.0  | 9219.5  | 8741.0  |
| 7223.3 | 55°   | 6881.0 | 6538.8 | 6402.2 | 6265.6 | 7116.5  | 7967.2  | 8941.3  | 9915.3  | 10484.4 | 9915.3  |
| 8025.8 | 57.5° | 7839.5 | 7653.0 | 7379.1 | 7105.3 | 7964.4  | 8823.5  | 9926.7  | 11029.9 | 11735.7 | 11029.9 |
| 8510.9 | 60°   | 8800.4 | 9090.0 | 8749.8 | 8409.7 | 9222.7  | 10035.7 | 11216.9 | 12398.1 | 13160.9 | 12398.1 |
| 8264.6 | 62.5° | 9055.7 | 9846.7 | 9808.4 | 9770.0 | 10514.8 | 11259.6 | 12383.4 | 13507.2 | 14212.2 | 13507.2 |
| 7771.6 | 65°   | 8514.1 | 9256.6 | 9403.5 | 9550.3 | 10496.8 | 11443.4 | 12533.1 | 13622.7 | 14223.0 | 13622.7 |
| 7111.2 | 67.5° | 7817.3 | 8523.5 | 8592.3 | 8661.2 | 9647.3  | 10633.4 | 11727.8 | 12822.2 | 13292.5 | 12822.2 |
| 6317.6 | 70°   | 7085.7 | 7853.8 | 7884.6 | 7915.5 | 8797.4  | 9679.2  | 10621.0 | 11562.7 | 11824.1 | 11562.7 |
| 5372.0 | 72.5° | 6253.4 | 7134.9 | 7157.0 | 7179.1 | 7869.1  | 8559.1  | 9264.4  | 9969.7  | 9996.2  | 9969.7  |
| 4175.8 | 75°   | 5088.0 | 6000.3 | 6082.2 | 6164.1 | 6700.9  | 7237.7  | 7734.3  | 8230.8  | 8097.8  | 8230.8  |
| 2983.5 | 77.5° | 3835.1 | 4686.7 | 4803.9 | 4921.1 | 5329.2  | 5737.3  | 6089.5  | 6441.7  | 6213.0  | 6441.7  |
| 1952.7 | 80°   | 2669.1 | 3385.5 | 3531.2 | 3676.9 | 3985.1  | 4293.2  | 4478.1  | 4663.0  | 4295.2  | 4663.0  |
| 1135.1 | 82.5° | 1624.9 | 2114.7 | 2277.5 | 2440.3 | 2652.4  | 2864.5  | 2941.7  | 3018.8  | 2729.7  | 3018.8  |
| 499.4  | 85°   | 759.4  | 1019.3 | 1157.7 | 1296.2 | 1470.5  | 1644.7  | 1688.5  | 1732.3  | 1500.8  | 1732.3  |
| 154.6  | 87.5° | 242.0  | 329.3  | 406.6  | 483.8  | 571.0   | 658.1   | 661.9   | 665.5   | 558.7   | 665.5   |
| 0.0    | 90°   | 0.0    | 0.0    | 0.0    | 0.0    | 0.0     | 0.0     | 0.0     | 0.0     | 0.0     | 0.0     |

REPORT NUMBER: P948664

CATALOG NUMBER: GLAN-SB3C-927-U-SLR

**CANDELA DISTRIBUTION (continued):**

| 325°    |       | 330°    | 335°    | 340°   | 345°   | 350°   | 355°   | 360°   |
|---------|-------|---------|---------|--------|--------|--------|--------|--------|
| 1874.0  | 0°    | 1874.0  | 1874.0  | 1874.0 | 1874.0 | 1874.0 | 1874.0 | 1874.0 |
| 2068.5  | 2.5°  | 2065.2  | 2058.8  | 2052.3 | 2041.4 | 2030.6 | 2022.9 | 2015.3 |
| 2310.9  | 5°    | 2302.2  | 2287.8  | 2273.4 | 2246.9 | 2220.4 | 2193.7 | 2167.0 |
| 2544.1  | 7.5°  | 2531.4  | 2507.9  | 2484.3 | 2445.3 | 2406.2 | 2362.9 | 2319.4 |
| 2698.3  | 10°   | 2686.0  | 2658.4  | 2630.6 | 2584.8 | 2539.0 | 2487.6 | 2436.3 |
| 2748.8  | 12.5° | 2742.1  | 2721.9  | 2701.8 | 2660.5 | 2619.1 | 2563.5 | 2507.9 |
| 2693.6  | 15°   | 2700.8  | 2700.1  | 2699.3 | 2673.3 | 2647.4 | 2599.4 | 2551.4 |
| 2556.7  | 17.5° | 2583.4  | 2612.5  | 2641.6 | 2641.2 | 2640.7 | 2608.2 | 2575.8 |
| 2381.7  | 20°   | 2428.5  | 2492.8  | 2557.1 | 2591.3 | 2625.4 | 2614.1 | 2602.8 |
| 2215.3  | 22.5° | 2273.8  | 2368.3  | 2462.9 | 2533.7 | 2604.4 | 2619.2 | 2634.1 |
| 2074.7  | 25°   | 2136.3  | 2251.1  | 2366.0 | 2473.4 | 2580.8 | 2627.6 | 2674.3 |
| 1962.1  | 27.5° | 2022.7  | 2150.0  | 2277.2 | 2419.5 | 2561.8 | 2645.4 | 2729.0 |
| 1881.8  | 30°   | 1938.0  | 2070.6  | 2203.2 | 2378.3 | 2553.5 | 2678.1 | 2802.7 |
| 1858.8  | 32.5° | 1902.9  | 2027.5  | 2152.1 | 2350.3 | 2548.5 | 2719.1 | 2889.7 |
| 1981.5  | 35°   | 1991.8  | 2078.3  | 2164.8 | 2371.3 | 2577.8 | 2786.6 | 2995.4 |
| 2342.5  | 37.5° | 2295.5  | 2301.1  | 2306.7 | 2494.4 | 2682.1 | 2927.7 | 3173.4 |
| 2940.2  | 40°   | 2825.9  | 2727.4  | 2628.9 | 2768.5 | 2908.0 | 3175.2 | 3442.3 |
| 3745.8  | 42.5° | 3537.8  | 3322.9  | 3108.1 | 3188.5 | 3268.9 | 3533.9 | 3799.0 |
| 4722.5  | 45°   | 4380.7  | 4036.4  | 3692.2 | 3727.7 | 3763.2 | 4001.3 | 4239.4 |
| 5805.9  | 47.5° | 5305.6  | 4809.2  | 4312.6 | 4319.8 | 4327.0 | 4558.6 | 4790.3 |
| 6882.8  | 50°   | 6222.5  | 5582.5  | 4942.5 | 4941.3 | 4940.1 | 5226.1 | 5512.2 |
| 7924.0  | 52.5° | 7107.0  | 6342.5  | 5578.0 | 5613.1 | 5648.1 | 5994.5 | 6341.0 |
| 8941.3  | 55°   | 7967.2  | 7116.5  | 6265.6 | 6402.2 | 6538.8 | 6881.0 | 7223.3 |
| 9926.7  | 57.5° | 8823.5  | 7964.4  | 7105.3 | 7379.1 | 7653.0 | 7839.5 | 8025.8 |
| 11216.9 | 60°   | 10035.7 | 9222.7  | 8409.7 | 8749.8 | 9090.0 | 8800.4 | 8510.9 |
| 12383.4 | 62.5° | 11259.6 | 10514.8 | 9770.0 | 9808.4 | 9846.7 | 9055.7 | 8264.6 |
| 12533.1 | 65°   | 11443.4 | 10496.8 | 9550.3 | 9403.5 | 9256.6 | 8514.1 | 7771.6 |
| 11727.8 | 67.5° | 10633.4 | 9647.3  | 8661.2 | 8592.3 | 8523.5 | 7817.3 | 7111.2 |
| 10621.0 | 70°   | 9679.2  | 8797.4  | 7915.5 | 7884.6 | 7853.8 | 7085.7 | 6317.6 |
| 9264.4  | 72.5° | 8559.1  | 7869.1  | 7179.1 | 7157.0 | 7134.9 | 6253.4 | 5372.0 |
| 7734.3  | 75°   | 7237.7  | 6700.9  | 6164.1 | 6082.2 | 6000.3 | 5088.0 | 4175.8 |
| 6089.5  | 77.5° | 5737.3  | 5329.2  | 4921.1 | 4803.9 | 4686.7 | 3835.1 | 2983.5 |
| 4478.1  | 80°   | 4293.2  | 3985.1  | 3676.9 | 3531.2 | 3385.5 | 2669.1 | 1952.7 |
| 2941.7  | 82.5° | 2864.5  | 2652.4  | 2440.3 | 2277.5 | 2114.7 | 1624.9 | 1135.1 |
| 1688.5  | 85°   | 1644.7  | 1470.5  | 1296.2 | 1157.7 | 1019.3 | 759.4  | 499.4  |
| 661.9   | 87.5° | 658.1   | 571.0   | 483.8  | 406.6  | 329.3  | 242.0  | 154.6  |
| 0.0     | 90°   | 0.0     | 0.0     | 0.0    | 0.0    | 0.0    | 0.0    | 0.0    |

(END OF REPORT)