

Scaled data based on original data using
LM-79-08 Approved Method: Electrical and Photometric Measurements of Solid-
State Lighting Products

Test Report Prepared for
Cooper Lighting Solutions
(formerly Eaton)

Brand: STREETWORKS

Report Number: P950735

Luminaire Tested: **GLAN-SB5A-835-U-RW**

Issue Date: 1/21/2025

Test Information

Test Method: LM-79-08
Report Number: P950735
TEST IS SCALED FROM IESNA LM-79-08 TEST DATA (G2-2411-289-19)
Test Lab: INNOVATION CENTER
Issue Date: 1/21/2025
Manufacturer: COOPER LIGHTING SOLUTIONS (FORMERLY EATON)
Product Line: STREETWORKS
Catalog Number: GLAN-SB5A-835-U-RW
Description: GALLEON AREA AND ROADWAY HIGH DENSITY LED LUMINAIRE
(5) 80 CRI, 3500K, 350mA LIGHTSQUARES WITH 26 LEDS EACH AND RECTANGULAR
WIDE OPTICS
Light Source: -
Ballast/Driver: -

Summary

Lumens per Lamp: N/A
Luminaire Lumens: 21643 lumens
Efficiency: N/A
Efficacy: 152.7 lumens/watt
Luminous Opening: Rectangular (W 1.5' x L: 1' x H: 0')
IES Classification: Type III - Medium
BUG Rating: B4 - U0 - G4

Input Watts (W): 141.7
Input Voltage (V): NR
Input Current (Ain): NR
Voltage Rise (V): NR
Power Factor: NR
Total Harmonic Distortion (THDi): NR
Frequency (hertz): 60
Stabilization Time: NR
Operation Time: NR
Ambient Temperature (°C): NR
Test Distance: 24 FT




REPORT NUMBER: P950735

CATALOG NUMBER: GLAN-SB5A-835-U-RW

Iso-Footcandle Lines of Horizontal Illumination

× Max cd


--- 1/2 Max cd



Based on 25 foot mounting height. Maximum calculated value = 4.1 fc
Type III - Medium - N/A

REPORT NUMBER: P950735
CATALOG NUMBER: GLAN-SB5A-835-U-RW

Luminous Intensity Polar Plot



REPORT NUMBER: P950735

CATALOG NUMBER: GLAN-SB5A-835-U-RW


FLUX DISTRIBUTION:

		Downward	Upward	Total
House Side	Lumens	10821.5	0.0	10821.5
	% Fixture	50.0	0.0	50.0
Street Side	Lumens	10821.5	0.0	10821.5
	% Fixture	50.0	0.0	50.0
Total	Lumens	21643.0	0.0	21643.0
	% Fixture	100.0	0.0	100.0

ZONAL LUMENS:

Zone	Lumens	% Fixture
0°-10°	227.1	1.0
10°-20°	749.0	3.5
20°-30°	1447.3	6.7
30°-40°	2443.9	11.3
40°-50°	3875.8	17.9
50°-60°	5189.2	24.0
60°-70°	4938.5	22.8
70°-80°	2577.0	11.9
80°-90°	195.1	0.9
90°-100°	0.0	0.0
100°-110°	0.0	0.0
110°-120°	0.0	0.0
120°-130°	0.0	0.0
130°-140°	0.0	0.0
140°-150°	0.0	0.0
150°-160°	0.0	0.0
160°-170°	0.0	0.0
170°-180°	0.0	0.0
0°-90°	21643.0	100.0
0°-180°	21643.0	100.0

Coefficient of Utilization



REPORT NUMBER: P950735


CATALOG NUMBER: GLAN-SB5A-835-U-RW

LUMINAIRE CLASSIFICATION SYSTEM LUMEN TABLE AND BUG RATING:

Zone		Lumens	% Fixture	Zone Rating/Lumen Limit		
				B	U	G
FL	(0°-30°)	1211.7	5.6			
FM	(30°-60°)	5754.5	26.6			
FH	(60°-80°)	3757.7	17.4			G2/5000
FVH	(80°-90°)	97.5	0.5			G1/100
BL	(0°-30°)	1211.7	5.6	B3/2500		
BM	(30°-60°)	5754.5	26.6	B4/8500		
BH	(60°-80°)	3757.7	17.4	B4/5000		G4/5000
BVH	(80°-90°)	97.5	0.5			G1/100
UL	(90°-100°)	0.0	0.0		U0/0	
UH	(100°-180°)	0.0	0.0		U0/0	

BUG Rating: B4-U0-G4

Type III Medium



REPORT NUMBER: P950735

CATALOG NUMBER: GLAN-SB5A-835-U-RW

CANDELA DISTRIBUTION (FULL):

	0°	5°	15°	25°	35°	45°	55°	65°	75°	85°
0°	2318.4	2318.4	2318.4	2318.4	2318.4	2318.4	2318.4	2318.4	2318.4	2318.4
2.5°	2318.4	2316.1	2318.4	2320.6	2319.5	2319.5	2325.0	2328.3	2334.9	2333.8
5°	2302.9	2301.8	2310.6	2320.6	2328.3	2341.6	2358.1	2370.3	2385.8	2389.1
7.5°	2295.1	2291.8	2307.3	2325.0	2349.3	2382.4	2414.5	2447.6	2474.2	2483.0
10°	2300.7	2301.8	2322.8	2355.9	2394.6	2441.0	2486.3	2542.7	2580.2	2589.1
12.5°	2326.1	2323.9	2359.2	2412.3	2465.3	2523.9	2576.9	2638.8	2679.7	2700.7
15°	2372.5	2368.1	2417.8	2496.3	2573.6	2642.1	2685.2	2743.8	2791.3	2817.8
17.5°	2427.8	2430.0	2495.2	2596.8	2698.5	2775.8	2816.7	2846.6	2883.0	2906.2
20°	2525.0	2529.4	2602.3	2722.8	2838.8	2927.2	2960.4	2949.3	2959.3	2977.0
22.5°	2655.4	2657.6	2739.4	2869.8	2991.3	3088.6	3110.7	3065.4	3037.7	3049.9
25°	2806.8	2821.1	2902.9	3036.6	3161.5	3254.3	3264.3	3195.7	3127.2	3130.5
27.5°	2991.3	3004.6	3087.5	3220.1	3347.1	3427.8	3426.7	3335.0	3234.4	3209.0
30°	3191.3	3205.7	3290.8	3427.8	3546.0	3616.8	3601.3	3491.9	3348.2	3300.7
32.5°	3428.9	3437.7	3523.9	3661.0	3770.4	3826.7	3794.7	3659.9	3480.8	3426.7
35°	3716.2	3729.5	3793.6	3922.9	4019.0	4065.4	4011.3	3852.1	3651.0	3590.2
37.5°	4044.4	4035.6	4108.5	4223.4	4303.0	4331.7	4257.7	4068.7	3845.5	3773.7
40°	4387.0	4382.5	4462.1	4572.6	4615.7	4633.4	4524.0	4317.4	4069.8	3992.5
42.5°	4697.5	4694.2	4801.4	4924.0	4975.9	4956.1	4817.9	4581.5	4329.5	4241.1
45°	4946.1	4941.7	5073.2	5245.6	5347.2	5314.1	5128.4	4873.2	4592.5	4500.8
47.5°	5137.3	5139.5	5280.9	5494.2	5672.1	5684.3	5445.6	5170.4	4882.0	4778.1
50°	5275.4	5282.0	5433.4	5669.9	5913.0	6020.2	5769.4	5475.4	5181.5	5064.4
52.5°	5309.7	5321.8	5504.2	5781.5	6067.7	6272.1	6098.7	5768.3	5465.5	5353.9
55°	5127.3	5151.6	5382.6	5772.7	6162.8	6437.9	6388.2	6065.5	5751.7	5636.8
57.5°	4708.5	4742.8	5012.4	5521.8	6141.8	6551.7	6612.5	6350.6	6037.9	5927.4
60°	4121.8	4162.6	4421.2	4977.1	5845.6	6593.7	6770.5	6628.0	6300.9	6193.7
62.5°	3236.6	3289.7	3599.1	4251.1	5220.2	6398.1	6905.3	6878.8	6537.4	6403.6
65°	2076.4	2132.7	2458.7	3228.9	4385.9	5799.2	6947.3	7123.0	6787.1	6600.3
67.5°	1252.0	1277.4	1438.7	1957.0	3205.7	4896.4	6591.5	7393.8	7078.8	6846.8
70°	801.1	815.5	911.6	1149.2	1812.2	3572.6	5709.7	7444.6	7432.4	7099.8
72.5°	543.7	548.1	573.5	680.7	1025.5	2029.9	4211.3	6739.6	7653.4	7425.8
75°	397.8	422.1	463.0	481.8	582.4	1014.4	2413.4	4735.1	6450.1	6549.5
77.5°	296.1	297.3	353.6	375.7	415.5	540.4	1021.0	2643.2	4004.6	4204.6
80°	250.8	237.6	236.5	302.8	312.7	337.0	456.4	912.8	1434.3	869.7
82.5°	208.9	194.5	175.7	236.5	213.3	206.6	197.8	371.3	456.4	224.3
85°	145.9	139.2	132.6	154.7	121.6	103.9	95.0	173.5	192.3	95.0
87.5°	63.0	65.2	66.3	68.5	50.8	36.5	36.5	48.6	48.6	37.6
90°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0

(END C

90°
2318.4
2332.7
2389.1
2485.2
2597.9
2709.5
2827.8
2917.3
2990.2
3058.7
3136.1
3216.7
3306.2
3440.0
3599.1
3786.9
4017.9
4263.2
4521.8
4809.1
5099.7
5382.6
5668.8
5952.8
6216.9
6419.1
6623.5
6864.4
7097.6
7390.4
6308.6
3750.5
657.5
191.2
84.0
27.6
0.0