

Scaled data based on original data using
LM-79-08 Approved Method: Electrical and Photometric Measurements of Solid-
State Lighting Products

Test Report Prepared for
Cooper Lighting Solutions
(formerly Eaton)

Brand: STREETWORKS

Report Number: P846636

Luminaire Tested: **GLAN-SB2B-835-U-T2**

Issue Date: 6/26/2024

Test Information

Test Method: LM-79-08
Report Number: P846636
TEST IS SCALED FROM IESNA LM-79-08 TEST DATA (G2-2405-108-3)
Test Lab: INNOVATION CENTER
Issue Date: 6/26/2024
Manufacturer: COOPER LIGHTING SOLUTIONS (FORMERLY EATON)
Product Line: STREETWORKS
Catalog Number: GLAN-SB2B-835-U-T2
Description: GALLEON AREA AND ROADWAY HIGH DENSITY LED LUMINAIRE
(2) 80 CRI, 3500K, 450mA LIGHTSQUARES WITH 26 LEDS EACH AND TYPE II OPTICS
Light Source: -
Ballast/Driver: -

Summary

Lumens per Lamp: N/A
Luminaire Lumens: 9239 lumens
Efficiency: N/A
Efficacy: 125.0 lumens/watt
Luminous Opening: Rectangular (W 0.5' x L: 1' x H: 0')
IES Classification: Type II - Medium
BUG Rating: B2 - U0 - G2


Input Watts (W): 73.9
Input Voltage (V): NR
Input Current (Ain): NR
Voltage Rise (V): NR
Power Factor: NR
Total Harmonic Distortion (THDi): NR
Frequency (hertz): 60
Stabilization Time: NR
Operation Time: NR
Ambient Temperature (°C): NR
Test Distance: 24 FT



REPORT NUMBER: P846636
 CATALOG NUMBER: GLAN-SB2B-835-U-T2

Iso-Footcandle Lines of Horizontal Illumination


✕ Max cd
 - - - 1/2 Max cd



Based on 25 foot mounting height. Maximum calculated value = 2.5 fc
 Type II - Medium - N/A

REPORT NUMBER: P846636
CATALOG NUMBER: GLAN-SB2B-835-U-T2

Luminous Intensity Polar Plot



— Vertical Plane Through 82-Deg Lateral - - - Horizontal Cone Through 70-Deg Vertical

REPORT NUMBER: P846636
 CATALOG NUMBER: GLAN-SB2B-835-U-T2

FLUX DISTRIBUTION:

		Downward	Upward	Total
House Side	Lumens	2277.6	0.0	2277.6
	% Fixture	24.7	0.0	24.7
Street Side	Lumens	6961.4	0.0	6961.4
	% Fixture	75.3	0.0	75.3
Total	Lumens	9239.0	0.0	9239.0
	% Fixture	100.0	0.0	100.0

ZONAL LUMENS:

Zone	Lumens	% Fixture
0°-10°	127.9	1.4
10°-20°	367.4	4.0
20°-30°	614.7	6.7
30°-40°	960.3	10.4
40°-50°	1529.4	16.6
50°-60°	2128.4	23.0
60°-70°	2226.4	24.1
70°-80°	1163.6	12.6
80°-90°	120.8	1.3
90°-100°	0.0	0.0
100°-110°	0.0	0.0
110°-120°	0.0	0.0
120°-130°	0.0	0.0
130°-140°	0.0	0.0
140°-150°	0.0	0.0
150°-160°	0.0	0.0
160°-170°	0.0	0.0
170°-180°	0.0	0.0
0°-90°	9239.0	100.0
0°-180°	9239.0	100.0

Coefficient of Utilization




REPORT NUMBER: P846636
 CATALOG NUMBER: GLAN-SB2B-835-U-T2

LUMINAIRE CLASSIFICATION SYSTEM LUMEN TABLE AND BUG RATING:

Zone	Lumens	% Fixture	Zone Rating/Lumen Limit		
			B	U	G
FL (0°-30°)	636.2	6.9			
FM (30°-60°)	3616.1	39.1			
FH (60°-80°)	2641.5	28.6			G2/5000
FVH (80°-90°)	67.6	0.7			G1/100
BL (0°-30°)	473.8	5.1	B1/500		
BM (30°-60°)	1002.1	10.8	B2/2500		
BH (60°-80°)	748.6	8.1	B2/1000		G2/1000
BVH (80°-90°)	53.2	0.6			G1/100
UL (90°-100°)	0.0	0.0		U0/0	
UH (100°-180°)	0.0	0.0		U0/0	

BUG Rating: B2-U0-G2
 Type II Medium



REPORT NUMBER: P846636
 CATALOG NUMBER: GLAN-SB2B-835-U-T2

CANDELA DISTRIBUTION (FULL):

	0°	5°	15°	25°	35°	45°	55°	65°	75°	82°
0°	1354.6	1354.6	1354.6	1354.6	1354.6	1354.6	1354.6	1354.6	1354.6	1354.6
2.5°	1386.9	1394.8	1392.3	1389.9	1389.9	1386.4	1385.9	1381.0	1377.1	1370.7
5°	1404.6	1412.9	1411.9	1413.9	1420.2	1421.7	1423.2	1420.2	1412.4	1404.6
7.5°	1388.9	1398.2	1401.1	1412.9	1432.5	1450.2	1463.4	1468.8	1461.4	1450.2
10°	1335.9	1346.2	1356.5	1384.5	1419.3	1460.9	1496.2	1517.3	1515.8	1505.1
12.5°	1228.6	1239.3	1261.4	1315.8	1379.6	1453.1	1518.8	1562.9	1578.1	1570.3
15°	1142.8	1152.1	1168.7	1224.6	1307.5	1419.3	1527.1	1612.9	1651.6	1647.2
17.5°	1140.3	1144.2	1154.5	1181.0	1244.7	1366.3	1518.3	1661.9	1736.0	1735.5
20°	1183.5	1184.9	1190.8	1196.2	1232.5	1326.1	1495.7	1702.6	1830.6	1830.6
22.5°	1243.3	1242.3	1248.2	1243.3	1260.9	1322.7	1481.5	1738.4	1936.0	1943.8
25°	1333.0	1328.1	1326.6	1315.3	1318.8	1354.6	1497.2	1779.1	2061.0	2077.2
27.5°	1452.6	1444.8	1439.4	1413.4	1404.6	1420.2	1545.3	1828.1	2200.2	2228.2
30°	1608.5	1594.3	1586.4	1541.3	1509.5	1511.9	1617.8	1893.3	2345.8	2390.9
32.5°	1821.3	1799.2	1778.1	1704.1	1645.8	1626.6	1711.5	1983.5	2503.7	2575.8
35°	2059.5	2041.9	2019.3	1905.1	1815.4	1771.3	1837.9	2109.5	2688.5	2802.7
37.5°	2289.0	2273.8	2284.6	2130.6	2014.9	1950.7	2003.6	2278.7	2916.5	3085.1
40°	2526.2	2514.5	2515.9	2368.9	2234.1	2162.0	2204.6	2490.9	3177.8	3420.9
42.5°	2784.1	2775.3	2745.9	2615.5	2464.0	2396.8	2436.0	2736.1	3458.2	3803.3
45°	3072.9	3067.5	3040.0	2890.5	2716.9	2641.5	2694.4	3006.7	3740.1	4163.2
47.5°	3322.4	3326.8	3323.4	3197.4	3017.5	2906.7	2969.9	3289.1	4002.4	4501.4
50°	3442.5	3465.6	3499.4	3460.2	3348.4	3235.6	3247.9	3561.6	4252.4	4818.6
52.5°	3379.8	3423.4	3515.6	3578.3	3621.5	3597.9	3565.1	3832.3	4487.7	5104.9
55°	3145.9	3207.2	3360.2	3511.6	3731.8	3902.9	3946.0	4132.3	4717.2	5356.9
57.5°	2719.9	2819.4	2956.7	3263.1	3633.7	4050.4	4390.2	4548.5	4960.3	5626.1
60°	1989.4	2122.8	2293.4	2749.3	3290.5	3971.5	4768.1	5187.8	5305.9	5974.6
62.5°	1273.2	1355.5	1512.4	1941.9	2564.0	3567.0	4883.8	5986.9	5891.8	6546.3
65°	871.7	924.6	1068.2	1309.5	1657.5	2655.2	4574.0	6586.0	6822.3	7452.2
67.5°	633.4	673.6	796.2	1007.5	1080.0	1571.2	3549.4	6558.5	7726.8	8385.7
70°	461.8	490.2	593.2	796.2	831.0	874.1	2150.2	5575.1	7707.2	8633.7
72.5°	342.2	361.8	430.9	617.7	672.6	590.3	1064.3	4051.9	6622.7	7809.1
75°	247.6	262.3	313.3	472.6	538.3	449.6	530.9	2367.9	4619.6	5493.2
77.5°	189.2	200.5	233.8	346.1	430.9	337.3	329.4	1089.3	2190.4	2201.2
80°	152.0	159.3	177.5	243.7	330.4	252.5	214.7	439.8	692.2	585.8
82.5°	111.8	124.0	150.0	171.1	236.3	174.0	130.9	222.1	263.3	226.5
85°	63.7	72.1	90.7	122.6	151.0	106.4	75.0	98.5	122.6	100.5
87.5°	22.6	29.4	31.9	48.0	65.7	44.1	28.9	28.4	40.2	29.9
90°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0

REPORT NUMBER: P846636
 CATALOG NUMBER: GLAN-SB2B-835-U-T2

CANDELA DISTRIBUTION (continued):

85°		90°	95°	105°	115°	125°	135°	145°	155°	165°	175°
1354.6	0°	1354.6	1354.6	1354.6	1354.6	1354.6	1354.6	1354.6	1354.6	1354.6	1354.6
1369.3	2.5°	1364.4	1361.9	1352.1	1338.9	1325.1	1311.9	1307.5	1298.2	1291.8	1288.4
1401.1	5°	1391.8	1384.0	1360.9	1331.5	1300.6	1267.3	1243.8	1222.2	1206.5	1191.8
1444.8	7.5°	1431.0	1417.3	1377.6	1326.1	1271.2	1215.8	1174.6	1143.3	1122.2	1108.4
1495.7	10°	1476.6	1455.5	1394.8	1317.8	1233.0	1153.6	1105.0	1078.1	1064.8	1057.5
1554.1	12.5°	1529.1	1499.2	1412.4	1298.7	1174.6	1083.9	1050.6	1042.8	1043.2	1043.7
1627.6	15°	1593.8	1552.1	1426.6	1257.0	1098.6	1030.5	1024.6	1037.4	1050.6	1057.0
1711.0	17.5°	1666.8	1608.0	1429.1	1188.4	1024.1	996.2	1014.8	1042.3	1062.4	1071.2
1804.1	20°	1745.3	1664.9	1411.4	1091.3	962.8	968.2	1001.6	1036.9	1058.9	1070.2
1910.5	22.5°	1835.0	1725.7	1369.3	989.3	912.8	937.8	977.1	1011.4	1034.4	1045.7
2035.5	25°	1937.5	1793.8	1303.1	903.5	869.7	903.5	942.7	971.2	989.8	1000.1
2175.2	27.5°	2051.2	1864.9	1214.8	835.4	831.9	868.2	900.6	922.6	932.5	940.3
2323.8	30°	2165.4	1929.6	1108.0	783.9	799.1	833.4	856.5	866.3	869.2	870.7
2489.5	32.5°	2289.0	1985.5	995.7	741.3	767.7	799.6	813.3	817.7	804.0	794.7
2690.5	35°	2438.5	2045.3	885.9	707.4	736.8	764.3	768.7	764.8	748.6	729.5
2942.5	37.5°	2623.3	2119.8	798.1	683.4	707.9	726.1	720.7	719.7	721.2	698.6
3245.4	40°	2849.8	2216.9	733.9	664.8	684.4	688.3	673.1	681.4	688.8	654.5
3577.8	42.5°	3101.3	2334.1	693.2	652.0	664.8	655.5	631.9	641.2	640.3	595.2
3911.7	45°	3357.7	2461.5	679.0	642.7	646.6	628.0	602.0	604.5	583.9	543.2
4231.8	47.5°	3612.6	2598.3	687.8	634.9	624.1	603.0	582.9	572.1	541.7	511.3
4538.7	50°	3862.7	2742.0	720.2	619.2	593.2	580.9	566.2	547.1	514.8	488.8
4828.9	52.5°	4094.5	2886.6	756.5	593.2	554.5	561.8	552.5	530.4	498.6	472.1
5103.5	55°	4314.2	3031.2	770.7	557.4	518.2	545.2	539.8	499.1	460.8	439.3
5390.8	57.5°	4553.4	3205.2	755.0	511.8	488.8	526.0	505.4	460.3	438.3	422.1
5764.8	60°	4884.8	3478.3	721.2	455.4	460.8	497.6	462.3	443.7	419.7	401.5
6325.7	62.5°	5435.4	3987.7	666.7	399.6	428.0	455.4	441.7	423.1	398.6	380.9
7284.6	65°	6249.2	4695.6	564.3	355.9	391.2	414.3	419.7	401.0	375.5	356.9
8124.9	67.5°	6935.5	5139.8	427.0	319.6	353.5	380.9	396.1	378.0	351.0	332.9
8321.5	70°	6897.8	4817.2	326.0	283.9	320.1	348.1	367.7	353.5	324.5	307.4
7558.6	72.5°	6126.6	4029.8	263.8	247.6	286.3	313.8	337.3	326.5	297.1	280.4
5537.3	75°	4501.0	2860.6	210.8	210.8	244.1	278.0	304.0	297.1	270.1	258.4
2324.8	77.5°	1897.3	1200.1	165.2	175.0	203.0	238.8	271.1	273.6	250.0	264.7
614.8	80°	504.5	330.9	126.0	137.8	159.3	197.1	235.8	234.8	209.3	195.6
228.5	82.5°	192.2	130.4	89.7	97.1	115.2	151.0	186.8	192.7	167.2	144.6
89.7	85°	74.0	55.9	55.4	58.3	67.2	100.0	141.2	146.1	126.0	106.9
25.0	87.5°	19.1	16.7	20.6	19.6	30.9	53.4	80.9	83.8	77.0	44.6
0.0	90°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0

(END O

180°
1354.6
1292.3
1197.7
1111.4
1059.4
1044.7
1056.5
1073.2
1073.2
1048.6
1003.0
943.2
874.1
797.6
730.5
700.1
655.5
594.7
544.7
511.3
486.8
472.6
437.3
420.6
400.5
380.9
357.9
333.4
308.9
280.4
254.9
240.2
181.9
144.6
110.3
63.7
0.0

F REPORT)