

Scaled data based on original data using  
LM-79-08 Approved Method: Electrical and Photometric Measurements of Solid-  
State Lighting Products

Test Report Prepared for  
Cooper Lighting Solutions  
(formerly Eaton)

Brand: STREETWORKS

Report Number: P948368

Luminaire Tested: **GLAN-SB3B-940-U-SLL**

Issue Date: 1/21/2025

**Test Information**

Test Method: LM-79-08  
Report Number: P948368  
TEST IS SCALED FROM IESNA LM-79-08 TEST DATA (G2-2411-289-8)  
Test Lab: INNOVATION CENTER  
Issue Date: 1/21/2025  
Manufacturer: COOPER LIGHTING SOLUTIONS (FORMERLY EATON)  
Product Line: STREETWORKS  
Catalog Number: GLAN-SB3B-940-U-SLL  
Description: GALLEON AREA AND ROADWAY HIGH DENSITY LED LUMINAIRE  
(3) 90 CRI, 4000K, 450mA LIGHTSQUARES WITH 26 LEDS EACH AND SPILL LIGHT  
ELIMINATOR LEFT OPTICS  
Light Source: -  
Ballast/Driver: -

**Summary**

Lumens per Lamp: N/A  
Luminaire Lumens: 12199 lumens  
Efficiency: N/A  
Efficacy: 111.7 lumens/watt  
Luminous Opening: Rectangular (W 1' x L: 1' x H: 0')  
IES Classification: Type IV - Short  
BUG Rating: B2 - U0 - G3


Input Watts (W): 109.2  
Input Voltage (V): NR  
Input Current (Ain): NR  
Voltage Rise (V): NR  
Power Factor: NR  
Total Harmonic Distortion (THDi): NR  
Frequency (hertz): 60  
Stabilization Time: NR  
Operation Time: NR  
Ambient Temperature (°C): NR  
Test Distance: 24 FT



REPORT NUMBER: P948368  
 CATALOG NUMBER: GLAN-SB3B-940-U-SLL

### Iso-Footcandle Lines of Horizontal Illumination


✕ Max cd  
 - - - 1/2 Max cd



Based on 25 foot mounting height. Maximum calculated value = 3.7 fc  
 Type IV - Short - N/A

REPORT NUMBER: P948368  
CATALOG NUMBER: GLAN-SB3B-940-U-SLL

### Luminous Intensity Polar Plot



— Vertical Plane Through 45-Deg Lateral      - - - Horizontal Cone Through 65-Deg Vertical

REPORT NUMBER: P948368  
 CATALOG NUMBER: GLAN-SB3B-940-U-SLL


**FLUX DISTRIBUTION:**

|                    |           | Downward | Upward | Total   |
|--------------------|-----------|----------|--------|---------|
| <b>House Side</b>  | Lumens    | 3100.4   | 0.0    | 3100.4  |
|                    | % Fixture | 25.4     | 0.0    | 25.4    |
| <b>Street Side</b> | Lumens    | 9098.6   | 0.0    | 9098.6  |
|                    | % Fixture | 74.6     | 0.0    | 74.6    |
| <b>Total</b>       | Lumens    | 12199.0  | 0.0    | 12199.0 |
|                    | % Fixture | 100.0    | 0.0    | 100.0   |

**ZONAL LUMENS:**

| Zone      | Lumens  | % Fixture |
|-----------|---------|-----------|
| 0°-10°    | 166.4   | 1.4       |
| 10°-20°   | 522.4   | 4.3       |
| 20°-30°   | 806.9   | 6.6       |
| 30°-40°   | 1022.5  | 8.4       |
| 40°-50°   | 1542.2  | 12.6      |
| 50°-60°   | 2491.7  | 20.4      |
| 60°-70°   | 3106.3  | 25.5      |
| 70°-80°   | 2037.0  | 16.7      |
| 80°-90°   | 503.6   | 4.1       |
| 90°-100°  | 0.0     | 0.0       |
| 100°-110° | 0.0     | 0.0       |
| 110°-120° | 0.0     | 0.0       |
| 120°-130° | 0.0     | 0.0       |
| 130°-140° | 0.0     | 0.0       |
| 140°-150° | 0.0     | 0.0       |
| 150°-160° | 0.0     | 0.0       |
| 160°-170° | 0.0     | 0.0       |
| 170°-180° | 0.0     | 0.0       |
| 0°-90°    | 12199.0 | 100.0     |
| 0°-180°   | 12199.0 | 100.0     |

**Coefficient of Utilization**




REPORT NUMBER: P948368  
 CATALOG NUMBER: GLAN-SB3B-940-U-SLL

**LUMINAIRE CLASSIFICATION SYSTEM LUMEN TABLE AND BUG RATING:**

| Zone           | Lumens | % Fixture | Zone Rating/Lumen Limit |      |         |
|----------------|--------|-----------|-------------------------|------|---------|
|                |        |           | B                       | U    | G       |
| FL (0°-30°)    | 820.5  | 6.7       |                         |      |         |
| FM (30°-60°)   | 3558.2 | 29.2      |                         |      |         |
| FH (60°-80°)   | 4305.1 | 35.3      |                         |      | G2/5000 |
| FVH (80°-90°)  | 414.8  | 3.4       |                         |      | G3/500  |
| BL (0°-30°)    | 675.1  | 5.5       | B2/1000                 |      |         |
| BM (30°-60°)   | 1498.3 | 12.3      | B2/2500                 |      |         |
| BH (60°-80°)   | 838.2  | 6.9       | B2/1000                 |      | G2/1000 |
| BVH (80°-90°)  | 88.7   | 0.7       |                         |      | G1/100  |
| UL (90°-100°)  | 0.0    | 0.0       |                         | U0/0 |         |
| UH (100°-180°) | 0.0    | 0.0       |                         | U0/0 |         |

**BUG Rating: B2-U0-G3**

Type IV Short



REPORT NUMBER: P948368  
 CATALOG NUMBER: GLAN-SB3B-940-U-SLL

**CANDELA DISTRIBUTION (FULL):**

|       | 0°     | 5°     | 10°    | 15°    | 20°    | 25°    | 30°     | 35°     | 40°     | 45°     |
|-------|--------|--------|--------|--------|--------|--------|---------|---------|---------|---------|
| 0°    | 1677.5 | 1677.5 | 1677.5 | 1677.5 | 1677.5 | 1677.5 | 1677.5  | 1677.5  | 1677.5  | 1677.5  |
| 2.5°  | 1804.0 | 1810.8 | 1817.7 | 1827.4 | 1837.1 | 1842.9 | 1848.7  | 1851.6  | 1854.5  | 1853.2  |
| 5°    | 1939.8 | 1963.7 | 1987.6 | 2011.3 | 2035.0 | 2047.9 | 2060.8  | 2068.6  | 2076.4  | 2082.4  |
| 7.5°  | 2076.2 | 2115.1 | 2153.9 | 2188.9 | 2223.8 | 2244.9 | 2265.9  | 2277.3  | 2288.7  | 2294.1  |
| 10°   | 2180.8 | 2226.8 | 2272.8 | 2313.8 | 2354.8 | 2379.6 | 2404.3  | 2415.4  | 2426.4  | 2430.6  |
| 12.5° | 2244.9 | 2294.7 | 2344.5 | 2381.5 | 2418.5 | 2436.5 | 2454.5  | 2460.6  | 2466.6  | 2467.3  |
| 15°   | 2283.8 | 2326.8 | 2369.8 | 2393.0 | 2416.3 | 2416.9 | 2417.6  | 2411.2  | 2404.7  | 2397.1  |
| 17.5° | 2305.7 | 2334.7 | 2363.8 | 2364.2 | 2364.6 | 2338.5 | 2312.5  | 2288.6  | 2264.6  | 2247.8  |
| 20°   | 2329.9 | 2340.0 | 2350.1 | 2319.6 | 2289.0 | 2231.4 | 2173.9  | 2132.0  | 2090.1  | 2064.3  |
| 22.5° | 2357.9 | 2344.6 | 2331.3 | 2268.0 | 2204.7 | 2120.0 | 2035.4  | 1983.0  | 1930.6  | 1902.1  |
| 25°   | 2393.9 | 2352.1 | 2310.2 | 2214.1 | 2117.9 | 2015.1 | 1912.3  | 1857.2  | 1802.2  | 1775.3  |
| 27.5° | 2442.8 | 2368.0 | 2293.2 | 2165.8 | 2038.5 | 1924.5 | 1810.6  | 1756.4  | 1702.2  | 1676.8  |
| 30°   | 2508.8 | 2397.2 | 2285.8 | 2129.0 | 1972.2 | 1853.5 | 1734.8  | 1684.5  | 1634.2  | 1610.5  |
| 32.5° | 2586.7 | 2433.9 | 2281.3 | 2103.9 | 1926.4 | 1814.9 | 1703.3  | 1663.9  | 1624.4  | 1607.3  |
| 35°   | 2681.3 | 2494.4 | 2307.5 | 2122.6 | 1937.8 | 1860.3 | 1782.9  | 1773.7  | 1764.5  | 1763.1  |
| 37.5° | 2840.6 | 2620.7 | 2400.9 | 2232.8 | 2064.8 | 2059.8 | 2054.8  | 2096.9  | 2139.0  | 2160.9  |
| 40°   | 3081.4 | 2842.2 | 2603.1 | 2478.2 | 2353.2 | 2441.4 | 2529.6  | 2631.9  | 2734.3  | 2785.3  |
| 42.5° | 3400.6 | 3163.4 | 2926.1 | 2854.1 | 2782.2 | 2974.5 | 3166.8  | 3353.0  | 3539.2  | 3648.5  |
| 45°   | 3794.9 | 3581.8 | 3368.6 | 3336.8 | 3305.0 | 3613.2 | 3921.4  | 4227.3  | 4533.2  | 4718.9  |
| 47.5° | 4288.0 | 4080.6 | 3873.2 | 3866.8 | 3860.4 | 4304.9 | 4749.3  | 5197.1  | 5644.9  | 5907.8  |
| 50°   | 4934.2 | 4678.1 | 4422.1 | 4423.1 | 4424.2 | 4997.1 | 5570.0  | 6161.1  | 6752.2  | 7109.6  |
| 52.5° | 5676.1 | 5366.0 | 5055.9 | 5024.5 | 4993.1 | 5677.4 | 6361.8  | 7093.1  | 7824.4  | 8252.8  |
| 55°   | 6465.9 | 6159.5 | 5853.1 | 5730.9 | 5608.6 | 6370.3 | 7131.8  | 8003.7  | 8875.6  | 9385.1  |
| 57.5° | 7184.3 | 7017.4 | 6850.5 | 6605.3 | 6360.2 | 7129.2 | 7898.3  | 8885.8  | 9873.3  | 10505.1 |
| 60°   | 7618.4 | 7877.6 | 8136.8 | 7832.3 | 7527.9 | 8255.6 | 8983.4  | 10040.7 | 11098.1 | 11780.9 |
| 62.5° | 7398.0 | 8106.1 | 8814.2 | 8779.9 | 8745.6 | 9412.2 | 10079.0 | 11084.9 | 12090.8 | 12722.0 |
| 65°   | 6956.7 | 7621.3 | 8286.0 | 8417.5 | 8548.9 | 9396.1 | 10243.4 | 11218.9 | 12194.3 | 12731.6 |
| 67.5° | 6365.5 | 6997.6 | 7629.7 | 7691.4 | 7753.0 | 8635.7 | 9518.4  | 10498.1 | 11477.7 | 11898.7 |
| 70°   | 5655.2 | 6342.7 | 7030.3 | 7057.9 | 7085.5 | 7874.9 | 8664.3  | 9507.3  | 10350.3 | 10584.3 |
| 72.5° | 4808.7 | 5597.7 | 6386.7 | 6406.6 | 6426.3 | 7043.9 | 7661.6  | 8293.0  | 8924.3  | 8948.0  |
| 75°   | 3737.9 | 4554.5 | 5371.1 | 5444.4 | 5517.7 | 5998.3 | 6478.8  | 6923.3  | 7367.7  | 7248.6  |
| 77.5° | 2670.7 | 3433.0 | 4195.3 | 4300.2 | 4405.1 | 4770.4 | 5135.7  | 5450.9  | 5766.2  | 5561.5  |
| 80°   | 1748.0 | 2389.3 | 3030.5 | 3160.9 | 3291.3 | 3567.2 | 3843.0  | 4008.5  | 4174.0  | 3844.8  |
| 82.5° | 1016.1 | 1454.5 | 1893.0 | 2038.6 | 2184.4 | 2374.3 | 2564.2  | 2633.2  | 2702.2  | 2443.5  |
| 85°   | 447.0  | 679.7  | 912.4  | 1036.3 | 1160.3 | 1316.3 | 1472.3  | 1511.5  | 1550.7  | 1343.4  |
| 87.5° | 138.4  | 216.6  | 294.8  | 363.9  | 433.1  | 511.1  | 589.1   | 592.5   | 595.7   | 500.2   |
| 90°   | 0.0    | 0.0    | 0.0    | 0.0    | 0.0    | 0.0    | 0.0     | 0.0     | 0.0     | 0.0     |

REPORT NUMBER: P948368  
 CATALOG NUMBER: GLAN-SB3B-940-U-SLL

**CANDELA DISTRIBUTION (continued):**

| 50°     |       | 55°     | 60°     | 65°    | 70°    | 75°    | 80°    | 85°    | 90°    | 95°    | 100°   |
|---------|-------|---------|---------|--------|--------|--------|--------|--------|--------|--------|--------|
| 1677.5  | 0°    | 1677.5  | 1677.5  | 1677.5 | 1677.5 | 1677.5 | 1677.5 | 1677.5 | 1677.5 | 1677.5 | 1677.5 |
| 1854.5  | 2.5°  | 1851.6  | 1848.7  | 1842.9 | 1837.1 | 1827.4 | 1817.7 | 1810.8 | 1804.0 | 1790.1 | 1776.3 |
| 2076.4  | 5°    | 2068.6  | 2060.8  | 2047.9 | 2035.0 | 2011.3 | 1987.6 | 1963.7 | 1939.8 | 1909.2 | 1878.6 |
| 2288.7  | 7.5°  | 2277.3  | 2265.9  | 2244.9 | 2223.8 | 2188.9 | 2153.9 | 2115.1 | 2076.2 | 2025.8 | 1975.4 |
| 2426.4  | 10°   | 2415.4  | 2404.3  | 2379.6 | 2354.8 | 2313.8 | 2272.8 | 2226.8 | 2180.8 | 2117.0 | 2053.3 |
| 2466.6  | 12.5° | 2460.6  | 2454.5  | 2436.5 | 2418.5 | 2381.5 | 2344.5 | 2294.7 | 2244.9 | 2174.8 | 2104.8 |
| 2404.7  | 15°   | 2411.2  | 2417.6  | 2416.9 | 2416.3 | 2393.0 | 2369.8 | 2326.8 | 2283.8 | 2210.8 | 2137.7 |
| 2264.6  | 17.5° | 2288.6  | 2312.5  | 2338.5 | 2364.6 | 2364.2 | 2363.8 | 2334.7 | 2305.7 | 2231.6 | 2157.5 |
| 2090.1  | 20°   | 2132.0  | 2173.9  | 2231.4 | 2289.0 | 2319.6 | 2350.1 | 2340.0 | 2329.9 | 2252.9 | 2175.8 |
| 1930.6  | 22.5° | 1983.0  | 2035.4  | 2120.0 | 2204.7 | 2268.0 | 2331.3 | 2344.6 | 2357.9 | 2279.2 | 2200.5 |
| 1802.2  | 25°   | 1857.2  | 1912.3  | 2015.1 | 2117.9 | 2214.1 | 2310.2 | 2352.1 | 2393.9 | 2316.8 | 2239.7 |
| 1702.2  | 27.5° | 1756.4  | 1810.6  | 1924.5 | 2038.5 | 2165.8 | 2293.2 | 2368.0 | 2442.8 | 2369.3 | 2295.7 |
| 1634.2  | 30°   | 1684.5  | 1734.8  | 1853.5 | 1972.2 | 2129.0 | 2285.8 | 2397.2 | 2508.8 | 2437.7 | 2366.7 |
| 1624.4  | 32.5° | 1663.9  | 1703.3  | 1814.9 | 1926.4 | 2103.9 | 2281.3 | 2433.9 | 2586.7 | 2516.3 | 2446.0 |
| 1764.5  | 35°   | 1773.7  | 1782.9  | 1860.3 | 1937.8 | 2122.6 | 2307.5 | 2494.4 | 2681.3 | 2614.0 | 2546.6 |
| 2139.0  | 37.5° | 2096.9  | 2054.8  | 2059.8 | 2064.8 | 2232.8 | 2400.9 | 2620.7 | 2840.6 | 2754.8 | 2668.9 |
| 2734.3  | 40°   | 2631.9  | 2529.6  | 2441.4 | 2353.2 | 2478.2 | 2603.1 | 2842.2 | 3081.4 | 2956.2 | 2831.1 |
| 3539.2  | 42.5° | 3353.0  | 3166.8  | 2974.5 | 2782.2 | 2854.1 | 2926.1 | 3163.4 | 3400.6 | 3220.0 | 3039.4 |
| 4533.2  | 45°   | 4227.3  | 3921.4  | 3613.2 | 3305.0 | 3336.8 | 3368.6 | 3581.8 | 3794.9 | 3551.3 | 3307.6 |
| 5644.9  | 47.5° | 5197.1  | 4749.3  | 4304.9 | 3860.4 | 3866.8 | 3873.2 | 4080.6 | 4288.0 | 3945.1 | 3602.1 |
| 6752.2  | 50°   | 6161.1  | 5570.0  | 4997.1 | 4424.2 | 4423.1 | 4422.1 | 4678.1 | 4934.2 | 4417.3 | 3900.3 |
| 7824.4  | 52.5° | 7093.1  | 6361.8  | 5677.4 | 4993.1 | 5024.5 | 5055.9 | 5366.0 | 5676.1 | 4913.3 | 4150.5 |
| 8875.6  | 55°   | 8003.7  | 7131.8  | 6370.3 | 5608.6 | 5730.9 | 5853.1 | 6159.5 | 6465.9 | 5353.1 | 4240.3 |
| 9873.3  | 57.5° | 8885.8  | 7898.3  | 7129.2 | 6360.2 | 6605.3 | 6850.5 | 7017.4 | 7184.3 | 5664.8 | 4145.3 |
| 11098.1 | 60°   | 10040.7 | 8983.4  | 8255.6 | 7527.9 | 7832.3 | 8136.8 | 7877.6 | 7618.4 | 5742.7 | 3866.8 |
| 12090.8 | 62.5° | 11084.9 | 10079.0 | 9412.2 | 8745.6 | 8779.9 | 8814.2 | 8106.1 | 7398.0 | 5414.7 | 3431.4 |
| 12194.3 | 65°   | 11218.9 | 10243.4 | 9396.1 | 8548.9 | 8417.5 | 8286.0 | 7621.3 | 6956.7 | 4950.7 | 2944.6 |
| 11477.7 | 67.5° | 10498.1 | 9518.4  | 8635.7 | 7753.0 | 7691.4 | 7629.7 | 6997.6 | 6365.5 | 4398.4 | 2431.4 |
| 10350.3 | 70°   | 9507.3  | 8664.3  | 7874.9 | 7085.5 | 7057.9 | 7030.3 | 6342.7 | 5655.2 | 3795.9 | 1936.6 |
| 8924.3  | 72.5° | 8293.0  | 7661.6  | 7043.9 | 6426.3 | 6406.6 | 6386.7 | 5597.7 | 4808.7 | 3142.6 | 1476.6 |
| 7367.7  | 75°   | 6923.3  | 6478.8  | 5998.3 | 5517.7 | 5444.4 | 5371.1 | 4554.5 | 3737.9 | 2393.8 | 1049.7 |
| 5766.2  | 77.5° | 5450.9  | 5135.7  | 4770.4 | 4405.1 | 4300.2 | 4195.3 | 3433.0 | 2670.7 | 1675.5 | 680.3  |
| 4174.0  | 80°   | 4008.5  | 3843.0  | 3567.2 | 3291.3 | 3160.9 | 3030.5 | 2389.3 | 1748.0 | 1079.5 | 411.0  |
| 2702.2  | 82.5° | 2633.2  | 2564.2  | 2374.3 | 2184.4 | 2038.6 | 1893.0 | 1454.5 | 1016.1 | 624.8  | 233.5  |
| 1550.7  | 85°   | 1511.5  | 1472.3  | 1316.3 | 1160.3 | 1036.3 | 912.4  | 679.7  | 447.0  | 281.0  | 115.1  |
| 595.7   | 87.5° | 592.5   | 589.1   | 511.1  | 433.1  | 363.9  | 294.8  | 216.6  | 138.4  | 92.0   | 45.7   |
| 0.0     | 90°   | 0.0     | 0.0     | 0.0    | 0.0    | 0.0    | 0.0    | 0.0    | 0.0    | 0.0    | 0.0    |



REPORT NUMBER: P948368  
 CATALOG NUMBER: GLAN-SB3B-940-U-SLL

**CANDELA DISTRIBUTION (continued):**

| 105°   |       | 110°   | 115°   | 120°   | 125°   | 130°   | 135°   | 140°   | 145°   | 150°   | 155°   |
|--------|-------|--------|--------|--------|--------|--------|--------|--------|--------|--------|--------|
| 1677.5 | 0°    | 1677.5 | 1677.5 | 1677.5 | 1677.5 | 1677.5 | 1677.5 | 1677.5 | 1677.5 | 1677.5 | 1677.5 |
| 1761.5 | 2.5°  | 1746.9 | 1732.1 | 1717.2 | 1703.1 | 1688.9 | 1675.2 | 1660.0 | 1647.6 | 1635.3 | 1624.2 |
| 1848.1 | 5°    | 1817.7 | 1787.0 | 1756.3 | 1727.7 | 1699.0 | 1672.0 | 1645.3 | 1622.0 | 1598.6 | 1579.0 |
| 1928.8 | 7.5°  | 1882.2 | 1836.8 | 1791.4 | 1751.4 | 1711.5 | 1674.6 | 1640.0 | 1609.0 | 1578.0 | 1552.3 |
| 1991.7 | 10°   | 1930.1 | 1875.0 | 1819.9 | 1772.6 | 1725.2 | 1679.7 | 1642.6 | 1609.9 | 1577.2 | 1551.4 |
| 2035.0 | 12.5° | 1965.2 | 1900.2 | 1835.2 | 1781.7 | 1728.2 | 1680.4 | 1645.8 | 1619.0 | 1592.4 | 1575.2 |
| 2062.0 | 15°   | 1986.3 | 1911.5 | 1836.6 | 1774.7 | 1712.7 | 1659.8 | 1632.1 | 1619.3 | 1606.5 | 1608.8 |
| 2074.9 | 17.5° | 1992.4 | 1905.5 | 1818.6 | 1744.1 | 1669.6 | 1607.3 | 1590.2 | 1594.9 | 1599.6 | 1627.6 |
| 2085.1 | 20°   | 1994.3 | 1889.0 | 1783.7 | 1691.4 | 1599.1 | 1526.5 | 1522.0 | 1543.9 | 1565.8 | 1614.5 |
| 2098.7 | 22.5° | 1996.9 | 1868.8 | 1740.7 | 1629.5 | 1518.3 | 1435.8 | 1444.6 | 1477.0 | 1509.3 | 1564.9 |
| 2123.4 | 25°   | 2007.0 | 1848.8 | 1690.7 | 1560.4 | 1430.3 | 1345.6 | 1369.5 | 1406.8 | 1444.1 | 1494.1 |
| 2162.0 | 27.5° | 2028.3 | 1835.5 | 1642.7 | 1497.3 | 1351.9 | 1274.8 | 1303.8 | 1339.8 | 1375.9 | 1417.0 |
| 2212.1 | 30°   | 2057.4 | 1829.3 | 1601.0 | 1444.5 | 1288.0 | 1223.3 | 1246.1 | 1274.6 | 1303.4 | 1337.5 |
| 2264.3 | 32.5° | 2082.5 | 1821.5 | 1560.4 | 1399.0 | 1237.5 | 1185.4 | 1195.5 | 1212.4 | 1229.3 | 1256.6 |
| 2323.7 | 35°   | 2100.9 | 1807.0 | 1513.2 | 1354.3 | 1195.3 | 1151.9 | 1147.7 | 1152.3 | 1157.0 | 1177.8 |
| 2390.4 | 37.5° | 2111.8 | 1782.1 | 1452.3 | 1301.6 | 1150.9 | 1112.9 | 1097.6 | 1092.5 | 1087.3 | 1102.3 |
| 2474.9 | 40°   | 2118.7 | 1747.8 | 1376.9 | 1238.8 | 1100.7 | 1066.3 | 1042.8 | 1031.1 | 1019.5 | 1030.2 |
| 2585.6 | 42.5° | 2131.8 | 1712.4 | 1293.1 | 1169.5 | 1045.9 | 1014.1 | 984.5  | 969.1  | 953.6  | 962.4  |
| 2731.2 | 45°   | 2154.8 | 1679.5 | 1204.2 | 1095.8 | 987.4  | 955.2  | 926.6  | 911.5  | 896.5  | 903.9  |
| 2886.3 | 47.5° | 2170.5 | 1652.3 | 1134.1 | 1037.6 | 941.1  | 899.6  | 874.9  | 862.3  | 849.7  | 856.6  |
| 3030.3 | 50°   | 2160.2 | 1622.7 | 1085.1 | 998.9  | 912.6  | 858.0  | 829.4  | 818.2  | 807.1  | 817.9  |
| 3123.7 | 52.5° | 2096.8 | 1572.7 | 1048.6 | 973.4  | 898.3  | 835.5  | 795.5  | 784.4  | 773.4  | 789.7  |
| 3103.1 | 55°   | 1965.8 | 1489.8 | 1013.7 | 954.9  | 896.2  | 837.8  | 777.5  | 759.9  | 742.5  | 765.6  |
| 2958.2 | 57.5° | 1771.1 | 1372.9 | 974.6  | 933.0  | 891.5  | 840.0  | 766.6  | 741.1  | 715.7  | 740.5  |
| 2688.4 | 60°   | 1510.0 | 1221.1 | 932.2  | 899.6  | 866.9  | 832.9  | 756.5  | 723.4  | 690.4  | 712.2  |
| 2323.6 | 62.5° | 1215.8 | 1039.4 | 863.1  | 841.4  | 819.7  | 815.6  | 744.6  | 703.3  | 662.0  | 675.9  |
| 1951.4 | 65°   | 958.3  | 876.0  | 793.7  | 783.4  | 773.2  | 773.7  | 719.7  | 675.8  | 631.8  | 637.1  |
| 1586.8 | 67.5° | 742.3  | 718.9  | 695.5  | 701.2  | 706.9  | 705.5  | 675.1  | 638.5  | 602.0  | 600.3  |
| 1249.4 | 70°   | 562.3  | 569.0  | 575.6  | 602.1  | 628.6  | 628.6  | 618.6  | 592.6  | 566.6  | 560.8  |
| 955.2  | 72.5° | 433.7  | 453.9  | 474.1  | 511.7  | 549.2  | 555.5  | 555.6  | 537.8  | 520.0  | 511.5  |
| 693.3  | 75°   | 336.8  | 355.1  | 373.3  | 415.4  | 457.5  | 486.6  | 484.2  | 470.5  | 456.7  | 448.6  |
| 469.8  | 77.5° | 259.3  | 271.7  | 284.2  | 325.1  | 365.9  | 413.9  | 412.6  | 401.6  | 390.6  | 382.4  |
| 302.7  | 80°   | 194.4  | 199.5  | 204.7  | 239.3  | 273.9  | 331.2  | 331.0  | 321.8  | 312.5  | 305.6  |
| 186.2  | 82.5° | 138.9  | 139.8  | 140.8  | 166.3  | 191.8  | 240.7  | 243.4  | 238.9  | 234.4  | 229.5  |
| 99.5   | 85°   | 84.0   | 83.6   | 83.0   | 101.7  | 120.4  | 156.7  | 160.3  | 155.5  | 150.6  | 145.2  |
| 41.3   | 87.5° | 36.8   | 36.4   | 35.9   | 43.5   | 51.2   | 66.3   | 70.8   | 68.9   | 66.9   | 65.9   |
| 0.0    | 90°   | 0.0    | 0.0    | 0.0    | 0.0    | 0.0    | 0.0    | 0.0    | 0.0    | 0.0    | 0.0    |

REPORT NUMBER: P948368  
 CATALOG NUMBER: GLAN-SB3B-940-U-SLL

**CANDELA DISTRIBUTION (continued):**

| 160°   |       | 165°   | 170°   | 175°   | 180°   | 185°   | 190°   | 195°   | 200°   | 205°   | 210°   |
|--------|-------|--------|--------|--------|--------|--------|--------|--------|--------|--------|--------|
| 1677.5 | 0°    | 1677.5 | 1677.5 | 1677.5 | 1677.5 | 1677.5 | 1677.5 | 1677.5 | 1677.5 | 1677.5 | 1677.5 |
| 1613.1 | 2.5°  | 1603.4 | 1593.7 | 1583.9 | 1574.2 | 1566.6 | 1559.0 | 1552.9 | 1546.8 | 1542.0 | 1537.3 |
| 1559.5 | 5°    | 1542.3 | 1525.0 | 1509.4 | 1493.7 | 1481.7 | 1469.6 | 1461.1 | 1452.7 | 1446.7 | 1440.7 |
| 1526.5 | 7.5°  | 1504.8 | 1483.1 | 1463.9 | 1444.8 | 1430.4 | 1416.1 | 1406.1 | 1396.0 | 1389.2 | 1382.3 |
| 1525.7 | 10°   | 1502.3 | 1478.9 | 1457.3 | 1435.8 | 1418.6 | 1401.5 | 1390.3 | 1378.9 | 1372.4 | 1365.9 |
| 1558.3 | 12.5° | 1539.8 | 1521.6 | 1499.2 | 1477.0 | 1455.1 | 1433.2 | 1418.7 | 1404.2 | 1396.9 | 1389.7 |
| 1611.2 | 15°   | 1606.4 | 1601.6 | 1582.3 | 1562.9 | 1531.7 | 1500.6 | 1478.6 | 1456.6 | 1446.4 | 1436.4 |
| 1655.7 | 17.5° | 1670.6 | 1685.5 | 1669.9 | 1654.3 | 1613.0 | 1571.8 | 1539.3 | 1506.9 | 1492.0 | 1477.0 |
| 1663.3 | 20°   | 1694.5 | 1725.7 | 1718.5 | 1711.3 | 1664.1 | 1617.0 | 1577.2 | 1537.5 | 1518.3 | 1499.2 |
| 1620.7 | 22.5° | 1661.3 | 1701.9 | 1706.3 | 1710.6 | 1665.6 | 1620.5 | 1579.6 | 1538.6 | 1518.4 | 1498.2 |
| 1544.2 | 25°   | 1584.2 | 1624.2 | 1639.1 | 1654.0 | 1617.0 | 1580.1 | 1543.7 | 1507.4 | 1489.9 | 1472.5 |
| 1458.1 | 27.5° | 1490.2 | 1522.2 | 1538.8 | 1555.5 | 1529.2 | 1502.9 | 1474.6 | 1446.4 | 1434.7 | 1422.9 |
| 1371.6 | 30°   | 1398.2 | 1424.8 | 1438.3 | 1451.9 | 1431.8 | 1411.8 | 1391.5 | 1371.2 | 1365.2 | 1359.2 |
| 1283.8 | 32.5° | 1309.3 | 1334.9 | 1349.9 | 1365.0 | 1346.5 | 1328.1 | 1311.9 | 1295.8 | 1291.8 | 1287.9 |
| 1198.6 | 35°   | 1223.8 | 1249.1 | 1267.1 | 1285.1 | 1272.0 | 1258.9 | 1244.0 | 1229.1 | 1223.1 | 1217.2 |
| 1117.1 | 37.5° | 1142.3 | 1167.5 | 1189.8 | 1212.1 | 1206.0 | 1200.0 | 1186.3 | 1172.5 | 1161.6 | 1150.8 |
| 1041.0 | 40°   | 1065.3 | 1089.6 | 1115.3 | 1140.9 | 1142.4 | 1143.8 | 1132.2 | 1120.5 | 1104.7 | 1089.0 |
| 971.2  | 42.5° | 994.3  | 1017.4 | 1045.0 | 1072.7 | 1080.1 | 1087.5 | 1077.7 | 1067.9 | 1048.3 | 1028.6 |
| 911.3  | 45°   | 933.2  | 955.1  | 983.8  | 1012.5 | 1023.2 | 1033.8 | 1024.9 | 1016.1 | 993.6  | 971.2  |
| 863.5  | 47.5° | 885.0  | 906.3  | 934.6  | 963.0  | 975.2  | 987.4  | 981.2  | 975.1  | 955.1  | 935.2  |
| 828.8  | 50°   | 849.0  | 869.1  | 894.5  | 919.8  | 935.5  | 951.3  | 950.9  | 950.6  | 934.6  | 918.7  |
| 805.9  | 52.5° | 824.4  | 842.9  | 866.5  | 890.2  | 908.8  | 927.4  | 930.8  | 934.1  | 921.1  | 908.1  |
| 788.7  | 55°   | 808.6  | 828.6  | 849.3  | 870.0  | 889.7  | 909.4  | 914.0  | 918.7  | 907.4  | 896.0  |
| 765.4  | 57.5° | 788.8  | 812.2  | 832.7  | 853.2  | 873.1  | 892.9  | 897.6  | 902.3  | 890.9  | 879.4  |
| 733.9  | 60°   | 760.8  | 787.8  | 808.5  | 829.4  | 849.4  | 869.3  | 874.5  | 879.6  | 868.4  | 857.3  |
| 689.7  | 62.5° | 721.1  | 752.5  | 774.7  | 796.9  | 815.2  | 833.5  | 838.4  | 843.4  | 833.3  | 823.2  |
| 642.4  | 65°   | 676.0  | 709.7  | 730.9  | 752.2  | 768.2  | 784.3  | 789.4  | 794.4  | 784.7  | 775.0  |
| 598.6  | 67.5° | 629.7  | 660.8  | 680.9  | 701.0  | 714.9  | 728.8  | 733.7  | 738.6  | 729.7  | 720.8  |
| 555.0  | 70°   | 582.3  | 609.6  | 627.0  | 644.3  | 656.9  | 669.4  | 674.2  | 679.0  | 671.7  | 664.4  |
| 503.0  | 72.5° | 524.5  | 546.0  | 561.7  | 577.4  | 589.7  | 602.0  | 607.6  | 613.3  | 607.3  | 601.2  |
| 440.4  | 75°   | 456.4  | 472.3  | 486.6  | 500.8  | 512.0  | 523.2  | 529.1  | 535.0  | 532.1  | 529.1  |
| 374.1  | 77.5° | 387.1  | 400.1  | 412.3  | 424.5  | 436.3  | 448.0  | 453.5  | 459.1  | 455.0  | 450.7  |
| 298.7  | 80°   | 309.5  | 320.2  | 330.5  | 340.8  | 349.8  | 358.7  | 366.0  | 373.3  | 371.5  | 369.8  |
| 224.6  | 82.5° | 223.7  | 222.8  | 219.2  | 215.6  | 234.7  | 253.7  | 266.2  | 278.7  | 277.9  | 277.1  |
| 139.7  | 85°   | 135.0  | 130.3  | 120.4  | 110.4  | 128.2  | 146.1  | 161.6  | 177.0  | 175.7  | 174.4  |
| 64.9   | 87.5° | 64.7   | 64.5   | 56.9   | 49.2   | 56.7   | 64.2   | 70.5   | 76.7   | 75.2   | 73.5   |
| 0.0    | 90°   | 0.0    | 0.0    | 0.0    | 0.0    | 0.0    | 0.0    | 0.0    | 0.0    | 0.0    | 0.0    |

REPORT NUMBER: P948368  
 CATALOG NUMBER: GLAN-SB3B-940-U-SLL

**CANDELA DISTRIBUTION (continued):**

| 215°   |       | 220°   | 225°   | 230°   | 235°   | 240°   | 245°   | 250°   | 255°   | 260°   | 265°   |
|--------|-------|--------|--------|--------|--------|--------|--------|--------|--------|--------|--------|
| 1677.5 | 0°    | 1677.5 | 1677.5 | 1677.5 | 1677.5 | 1677.5 | 1677.5 | 1677.5 | 1677.5 | 1677.5 | 1677.5 |
| 1532.9 | 2.5°  | 1528.5 | 1523.0 | 1528.5 | 1532.9 | 1537.3 | 1542.0 | 1546.8 | 1552.9 | 1559.0 | 1566.6 |
| 1436.1 | 5°    | 1431.6 | 1427.1 | 1431.6 | 1436.1 | 1440.7 | 1446.7 | 1452.7 | 1461.1 | 1469.6 | 1481.7 |
| 1378.2 | 7.5°  | 1374.2 | 1371.1 | 1374.2 | 1378.2 | 1382.3 | 1389.2 | 1396.0 | 1406.1 | 1416.1 | 1430.4 |
| 1362.4 | 10°   | 1359.0 | 1357.6 | 1359.0 | 1362.4 | 1365.9 | 1372.4 | 1378.9 | 1390.3 | 1401.5 | 1418.6 |
| 1386.8 | 12.5° | 1383.8 | 1383.3 | 1383.8 | 1386.8 | 1389.7 | 1396.9 | 1404.2 | 1418.7 | 1433.2 | 1455.1 |
| 1432.5 | 15°   | 1428.7 | 1428.4 | 1428.7 | 1432.5 | 1436.4 | 1446.4 | 1456.6 | 1478.6 | 1500.6 | 1531.7 |
| 1472.1 | 17.5° | 1467.1 | 1466.3 | 1467.1 | 1472.1 | 1477.0 | 1492.0 | 1506.9 | 1539.3 | 1571.8 | 1613.0 |
| 1493.0 | 20°   | 1486.9 | 1485.0 | 1486.9 | 1493.0 | 1499.2 | 1518.3 | 1537.5 | 1577.2 | 1617.0 | 1664.1 |
| 1491.4 | 22.5° | 1484.7 | 1481.8 | 1484.7 | 1491.4 | 1498.2 | 1518.4 | 1538.6 | 1579.6 | 1620.5 | 1665.6 |
| 1466.1 | 25°   | 1459.8 | 1456.0 | 1459.8 | 1466.1 | 1472.5 | 1489.9 | 1507.4 | 1543.7 | 1580.1 | 1617.0 |
| 1420.0 | 27.5° | 1417.1 | 1416.1 | 1417.1 | 1420.0 | 1422.9 | 1434.7 | 1446.4 | 1474.6 | 1502.9 | 1529.2 |
| 1359.2 | 30°   | 1359.2 | 1360.1 | 1359.2 | 1359.2 | 1359.2 | 1365.2 | 1371.2 | 1391.5 | 1411.8 | 1431.8 |
| 1288.4 | 32.5° | 1289.0 | 1290.0 | 1289.0 | 1288.4 | 1287.9 | 1291.8 | 1295.8 | 1311.9 | 1328.1 | 1346.5 |
| 1215.9 | 35°   | 1214.7 | 1214.0 | 1214.7 | 1215.9 | 1217.2 | 1223.1 | 1229.1 | 1244.0 | 1258.9 | 1272.0 |
| 1145.1 | 37.5° | 1139.3 | 1136.1 | 1139.3 | 1145.1 | 1150.8 | 1161.6 | 1172.5 | 1186.3 | 1200.0 | 1206.0 |
| 1078.3 | 40°   | 1067.8 | 1061.5 | 1067.8 | 1078.3 | 1089.0 | 1104.7 | 1120.5 | 1132.2 | 1143.8 | 1142.4 |
| 1013.1 | 42.5° | 997.6  | 987.4  | 997.6  | 1013.1 | 1028.6 | 1048.3 | 1067.9 | 1077.7 | 1087.5 | 1080.1 |
| 953.0  | 45°   | 934.8  | 923.1  | 934.8  | 953.0  | 971.2  | 993.6  | 1016.1 | 1024.9 | 1033.8 | 1023.2 |
| 918.3  | 47.5° | 901.5  | 890.2  | 901.5  | 918.3  | 935.2  | 955.1  | 975.1  | 981.2  | 987.4  | 975.2  |
| 903.1  | 50°   | 887.5  | 876.7  | 887.5  | 903.1  | 918.7  | 934.6  | 950.6  | 950.9  | 951.3  | 935.5  |
| 894.2  | 52.5° | 880.3  | 870.3  | 880.3  | 894.2  | 908.1  | 921.1  | 934.1  | 930.8  | 927.4  | 908.8  |
| 883.8  | 55°   | 871.6  | 862.6  | 871.6  | 883.8  | 896.0  | 907.4  | 918.7  | 914.0  | 909.4  | 889.7  |
| 867.3  | 57.5° | 855.1  | 845.8  | 855.1  | 867.3  | 879.4  | 890.9  | 902.3  | 897.6  | 892.9  | 873.1  |
| 844.8  | 60°   | 832.3  | 822.6  | 832.3  | 844.8  | 857.3  | 868.4  | 879.6  | 874.5  | 869.3  | 849.4  |
| 810.0  | 62.5° | 796.9  | 785.3  | 796.9  | 810.0  | 823.2  | 833.3  | 843.4  | 838.4  | 833.5  | 815.2  |
| 762.3  | 65°   | 749.6  | 739.6  | 749.6  | 762.3  | 775.0  | 784.7  | 794.4  | 789.4  | 784.3  | 768.2  |
| 709.0  | 67.5° | 697.1  | 688.1  | 697.1  | 709.0  | 720.8  | 729.7  | 738.6  | 733.7  | 728.8  | 714.9  |
| 653.1  | 70°   | 641.8  | 631.5  | 641.8  | 653.1  | 664.4  | 671.7  | 679.0  | 674.2  | 669.4  | 656.9  |
| 590.4  | 72.5° | 579.6  | 569.7  | 579.6  | 590.4  | 601.2  | 607.3  | 613.3  | 607.6  | 602.0  | 589.7  |
| 520.0  | 75°   | 511.0  | 501.4  | 511.0  | 520.0  | 529.1  | 532.1  | 535.0  | 529.1  | 523.2  | 512.0  |
| 441.6  | 77.5° | 432.4  | 424.8  | 432.4  | 441.6  | 450.7  | 455.0  | 459.1  | 453.5  | 448.0  | 436.3  |
| 357.5  | 80°   | 345.1  | 330.9  | 345.1  | 357.5  | 369.8  | 371.5  | 373.3  | 366.0  | 358.7  | 349.8  |
| 266.7  | 82.5° | 256.3  | 247.2  | 256.3  | 266.7  | 277.1  | 277.9  | 278.7  | 266.2  | 253.7  | 234.7  |
| 166.3  | 85°   | 158.2  | 150.0  | 158.2  | 166.3  | 174.4  | 175.7  | 177.0  | 161.6  | 146.1  | 128.2  |
| 69.4   | 87.5° | 65.1   | 61.2   | 65.1   | 69.4   | 73.5   | 75.2   | 76.7   | 70.5   | 64.2   | 56.7   |
| 0.0    | 90°   | 0.0    | 0.0    | 0.0    | 0.0    | 0.0    | 0.0    | 0.0    | 0.0    | 0.0    | 0.0    |

REPORT NUMBER: P948368  
 CATALOG NUMBER: GLAN-SB3B-940-U-SLL

**CANDELA DISTRIBUTION (continued):**

| 270°   |       | 275°   | 280°   | 285°   | 290°   | 295°   | 300°   | 305°   | 310°   | 315°   | 320°   |
|--------|-------|--------|--------|--------|--------|--------|--------|--------|--------|--------|--------|
| 1677.5 | 0°    | 1677.5 | 1677.5 | 1677.5 | 1677.5 | 1677.5 | 1677.5 | 1677.5 | 1677.5 | 1677.5 | 1677.5 |
| 1574.2 | 2.5°  | 1583.9 | 1593.7 | 1603.4 | 1613.1 | 1624.2 | 1635.3 | 1647.6 | 1660.0 | 1675.2 | 1688.9 |
| 1493.7 | 5°    | 1509.4 | 1525.0 | 1542.3 | 1559.5 | 1579.0 | 1598.6 | 1622.0 | 1645.3 | 1672.0 | 1699.0 |
| 1444.8 | 7.5°  | 1463.9 | 1483.1 | 1504.8 | 1526.5 | 1552.3 | 1578.0 | 1609.0 | 1640.0 | 1674.6 | 1711.5 |
| 1435.8 | 10°   | 1457.3 | 1478.9 | 1502.3 | 1525.7 | 1551.4 | 1577.2 | 1609.9 | 1642.6 | 1679.7 | 1725.2 |
| 1477.0 | 12.5° | 1499.2 | 1521.6 | 1539.8 | 1558.3 | 1575.2 | 1592.4 | 1619.0 | 1645.8 | 1680.4 | 1728.2 |
| 1562.9 | 15°   | 1582.3 | 1601.6 | 1606.4 | 1611.2 | 1608.8 | 1606.5 | 1619.3 | 1632.1 | 1659.8 | 1712.7 |
| 1654.3 | 17.5° | 1669.9 | 1685.5 | 1670.6 | 1655.7 | 1627.6 | 1599.6 | 1594.9 | 1590.2 | 1607.3 | 1669.6 |
| 1711.3 | 20°   | 1718.5 | 1725.7 | 1694.5 | 1663.3 | 1614.5 | 1565.8 | 1543.9 | 1522.0 | 1526.5 | 1599.1 |
| 1710.6 | 22.5° | 1706.3 | 1701.9 | 1661.3 | 1620.7 | 1564.9 | 1509.3 | 1477.0 | 1444.6 | 1435.8 | 1518.3 |
| 1654.0 | 25°   | 1639.1 | 1624.2 | 1584.2 | 1544.2 | 1494.1 | 1444.1 | 1406.8 | 1369.5 | 1345.6 | 1430.3 |
| 1555.5 | 27.5° | 1538.8 | 1522.2 | 1490.2 | 1458.1 | 1417.0 | 1375.9 | 1339.8 | 1303.8 | 1274.8 | 1351.9 |
| 1451.9 | 30°   | 1438.3 | 1424.8 | 1398.2 | 1371.6 | 1337.5 | 1303.4 | 1274.6 | 1246.1 | 1223.3 | 1288.0 |
| 1365.0 | 32.5° | 1349.9 | 1334.9 | 1309.3 | 1283.8 | 1256.6 | 1229.3 | 1212.4 | 1195.5 | 1185.4 | 1237.5 |
| 1285.1 | 35°   | 1267.1 | 1249.1 | 1223.8 | 1198.6 | 1177.8 | 1157.0 | 1152.3 | 1147.7 | 1151.9 | 1195.3 |
| 1212.1 | 37.5° | 1189.8 | 1167.5 | 1142.3 | 1117.1 | 1102.3 | 1087.3 | 1092.5 | 1097.6 | 1112.9 | 1150.9 |
| 1140.9 | 40°   | 1115.3 | 1089.6 | 1065.3 | 1041.0 | 1030.2 | 1019.5 | 1031.1 | 1042.8 | 1066.3 | 1100.7 |
| 1072.7 | 42.5° | 1045.0 | 1017.4 | 994.3  | 971.2  | 962.4  | 953.6  | 969.1  | 984.5  | 1014.1 | 1045.9 |
| 1012.5 | 45°   | 983.8  | 955.1  | 933.2  | 911.3  | 903.9  | 896.5  | 911.5  | 926.6  | 955.2  | 987.4  |
| 963.0  | 47.5° | 934.6  | 906.3  | 885.0  | 863.5  | 856.6  | 849.7  | 862.3  | 874.9  | 899.6  | 941.1  |
| 919.8  | 50°   | 894.5  | 869.1  | 849.0  | 828.8  | 817.9  | 807.1  | 818.2  | 829.4  | 858.0  | 912.6  |
| 890.2  | 52.5° | 866.5  | 842.9  | 824.4  | 805.9  | 789.7  | 773.4  | 784.4  | 795.5  | 835.5  | 898.3  |
| 870.0  | 55°   | 849.3  | 828.6  | 808.6  | 788.7  | 765.6  | 742.5  | 759.9  | 777.5  | 837.8  | 896.2  |
| 853.2  | 57.5° | 832.7  | 812.2  | 788.8  | 765.4  | 740.5  | 715.7  | 741.1  | 766.6  | 840.0  | 891.5  |
| 829.4  | 60°   | 808.5  | 787.8  | 760.8  | 733.9  | 712.2  | 690.4  | 723.4  | 756.5  | 832.9  | 866.9  |
| 796.9  | 62.5° | 774.7  | 752.5  | 721.1  | 689.7  | 675.9  | 662.0  | 703.3  | 744.6  | 815.6  | 819.7  |
| 752.2  | 65°   | 730.9  | 709.7  | 676.0  | 642.4  | 637.1  | 631.8  | 675.8  | 719.7  | 773.7  | 773.2  |
| 701.0  | 67.5° | 680.9  | 660.8  | 629.7  | 598.6  | 600.3  | 602.0  | 638.5  | 675.1  | 705.5  | 706.9  |
| 644.3  | 70°   | 627.0  | 609.6  | 582.3  | 555.0  | 560.8  | 566.6  | 592.6  | 618.6  | 628.6  | 628.6  |
| 577.4  | 72.5° | 561.7  | 546.0  | 524.5  | 503.0  | 511.5  | 520.0  | 537.8  | 555.6  | 555.5  | 549.2  |
| 500.8  | 75°   | 486.6  | 472.3  | 456.4  | 440.4  | 448.6  | 456.7  | 470.5  | 484.2  | 486.6  | 457.5  |
| 424.5  | 77.5° | 412.3  | 400.1  | 387.1  | 374.1  | 382.4  | 390.6  | 401.6  | 412.6  | 413.9  | 365.9  |
| 340.8  | 80°   | 330.5  | 320.2  | 309.5  | 298.7  | 305.6  | 312.5  | 321.8  | 331.0  | 331.2  | 273.9  |
| 215.6  | 82.5° | 219.2  | 222.8  | 223.7  | 224.6  | 229.5  | 234.4  | 238.9  | 243.4  | 240.7  | 191.8  |
| 110.4  | 85°   | 120.4  | 130.3  | 135.0  | 139.7  | 145.2  | 150.6  | 155.5  | 160.3  | 156.7  | 120.4  |
| 49.2   | 87.5° | 56.9   | 64.5   | 64.7   | 64.9   | 65.9   | 66.9   | 68.9   | 70.8   | 66.3   | 51.2   |
| 0.0    | 90°   | 0.0    | 0.0    | 0.0    | 0.0    | 0.0    | 0.0    | 0.0    | 0.0    | 0.0    | 0.0    |

REPORT NUMBER: P948368  
 CATALOG NUMBER: GLAN-SB3B-940-U-SLL

**CANDELA DISTRIBUTION (continued):**

| 325°   |       | 330°   | 335°   | 340°   | 345°   | 350°   | 355°   | 360°   |
|--------|-------|--------|--------|--------|--------|--------|--------|--------|
| 1677.5 | 0°    | 1677.5 | 1677.5 | 1677.5 | 1677.5 | 1677.5 | 1677.5 | 1677.5 |
| 1703.1 | 2.5°  | 1717.2 | 1732.1 | 1746.9 | 1761.5 | 1776.3 | 1790.1 | 1804.0 |
| 1727.7 | 5°    | 1756.3 | 1787.0 | 1817.7 | 1848.1 | 1878.6 | 1909.2 | 1939.8 |
| 1751.4 | 7.5°  | 1791.4 | 1836.8 | 1882.2 | 1928.8 | 1975.4 | 2025.8 | 2076.2 |
| 1772.6 | 10°   | 1819.9 | 1875.0 | 1930.1 | 1991.7 | 2053.3 | 2117.0 | 2180.8 |
| 1781.7 | 12.5° | 1835.2 | 1900.2 | 1965.2 | 2035.0 | 2104.8 | 2174.8 | 2244.9 |
| 1774.7 | 15°   | 1836.6 | 1911.5 | 1986.3 | 2062.0 | 2137.7 | 2210.8 | 2283.8 |
| 1744.1 | 17.5° | 1818.6 | 1905.5 | 1992.4 | 2074.9 | 2157.5 | 2231.6 | 2305.7 |
| 1691.4 | 20°   | 1783.7 | 1889.0 | 1994.3 | 2085.1 | 2175.8 | 2252.9 | 2329.9 |
| 1629.5 | 22.5° | 1740.7 | 1868.8 | 1996.9 | 2098.7 | 2200.5 | 2279.2 | 2357.9 |
| 1560.4 | 25°   | 1690.7 | 1848.8 | 2007.0 | 2123.4 | 2239.7 | 2316.8 | 2393.9 |
| 1497.3 | 27.5° | 1642.7 | 1835.5 | 2028.3 | 2162.0 | 2295.7 | 2369.3 | 2442.8 |
| 1444.5 | 30°   | 1601.0 | 1829.3 | 2057.4 | 2212.1 | 2366.7 | 2437.7 | 2508.8 |
| 1399.0 | 32.5° | 1560.4 | 1821.5 | 2082.5 | 2264.3 | 2446.0 | 2516.3 | 2586.7 |
| 1354.3 | 35°   | 1513.2 | 1807.0 | 2100.9 | 2323.7 | 2546.6 | 2614.0 | 2681.3 |
| 1301.6 | 37.5° | 1452.3 | 1782.1 | 2111.8 | 2390.4 | 2668.9 | 2754.8 | 2840.6 |
| 1238.8 | 40°   | 1376.9 | 1747.8 | 2118.7 | 2474.9 | 2831.1 | 2956.2 | 3081.4 |
| 1169.5 | 42.5° | 1293.1 | 1712.4 | 2131.8 | 2585.6 | 3039.4 | 3220.0 | 3400.6 |
| 1095.8 | 45°   | 1204.2 | 1679.5 | 2154.8 | 2731.2 | 3307.6 | 3551.3 | 3794.9 |
| 1037.6 | 47.5° | 1134.1 | 1652.3 | 2170.5 | 2886.3 | 3602.1 | 3945.1 | 4288.0 |
| 998.9  | 50°   | 1085.1 | 1622.7 | 2160.2 | 3030.3 | 3900.3 | 4417.3 | 4934.2 |
| 973.4  | 52.5° | 1048.6 | 1572.7 | 2096.8 | 3123.7 | 4150.5 | 4913.3 | 5676.1 |
| 954.9  | 55°   | 1013.7 | 1489.8 | 1965.8 | 3103.1 | 4240.3 | 5353.1 | 6465.9 |
| 933.0  | 57.5° | 974.6  | 1372.9 | 1771.1 | 2958.2 | 4145.3 | 5664.8 | 7184.3 |
| 899.6  | 60°   | 932.2  | 1221.1 | 1510.0 | 2688.4 | 3866.8 | 5742.7 | 7618.4 |
| 841.4  | 62.5° | 863.1  | 1039.4 | 1215.8 | 2323.6 | 3431.4 | 5414.7 | 7398.0 |
| 783.4  | 65°   | 793.7  | 876.0  | 958.3  | 1951.4 | 2944.6 | 4950.7 | 6956.7 |
| 701.2  | 67.5° | 695.5  | 718.9  | 742.3  | 1586.8 | 2431.4 | 4398.4 | 6365.5 |
| 602.1  | 70°   | 575.6  | 569.0  | 562.3  | 1249.4 | 1936.6 | 3795.9 | 5655.2 |
| 511.7  | 72.5° | 474.1  | 453.9  | 433.7  | 955.2  | 1476.6 | 3142.6 | 4808.7 |
| 415.4  | 75°   | 373.3  | 355.1  | 336.8  | 693.3  | 1049.7 | 2393.8 | 3737.9 |
| 325.1  | 77.5° | 284.2  | 271.7  | 259.3  | 469.8  | 680.3  | 1675.5 | 2670.7 |
| 239.3  | 80°   | 204.7  | 199.5  | 194.4  | 302.7  | 411.0  | 1079.5 | 1748.0 |
| 166.3  | 82.5° | 140.8  | 139.8  | 138.9  | 186.2  | 233.5  | 624.8  | 1016.1 |
| 101.7  | 85°   | 83.0   | 83.6   | 84.0   | 99.5   | 115.1  | 281.0  | 447.0  |
| 43.5   | 87.5° | 35.9   | 36.4   | 36.8   | 41.3   | 45.7   | 92.0   | 138.4  |
| 0.0    | 90°   | 0.0    | 0.0    | 0.0    | 0.0    | 0.0    | 0.0    | 0.0    |

(END OF REPORT)