

Scaled data based on original data using
LM-79-08 Approved Method: Electrical and Photometric Measurements of Solid-
State Lighting Products

Test Report Prepared for
Cooper Lighting Solutions
(formerly Eaton)

Brand: STREETWORKS

Report Number: P957565

Luminaire Tested: **GLAN-SB9D-850-U-SLL-HSS**

Issue Date: 1/21/2025

Test Information

Test Method: LM-79-08
Report Number: P957565
TEST IS SCALED FROM IESNA LM-79-08 TEST DATA (G2-2411-289-9)
Test Lab: INNOVATION CENTER
Issue Date: 1/21/2025
Manufacturer: COOPER LIGHTING SOLUTIONS (FORMERLY EATON)
Product Line: STREETWORKS
Catalog Number: GLAN-SB9D-850-U-SLL-HSS
Description: GALLEON AREA AND ROADWAY HIGH DENSITY LED LUMINAIRE
(9) 80 CRI, 5000K, 900mA LIGHTSQUARES WITH 26 LEDS EACH AND SPILL LIGHT
ELIMINATOR LEFT OPTICS WITH HOUSE SIDE SHIELD
Light Source: -
Ballast/Driver: -

Summary

Lumens per Lamp: N/A
Luminaire Lumens: 67662 lumens
Efficiency: N/A
Efficacy: 102.8 lumens/watt
Luminous Opening: Rectangular (W 1.5' x L: 1.5' x H: 0')
IES Classification: Type IV - Short
BUG Rating: B4 - U0 - G5


Input Watts (W): 658
Input Voltage (V): NR
Input Current (Ain): NR
Voltage Rise (V): NR
Power Factor: NR
Total Harmonic Distortion (THDi): NR
Frequency (hertz): 60
Stabilization Time: NR
Operation Time: NR
Ambient Temperature (°C): NR
Test Distance: 24 FT



REPORT NUMBER: P957565
CATALOG NUMBER: GLAN-SB9D-850-U-SLL-HSS

Iso-Footcandle Lines of Horizontal Illumination


× Max cd
- - - 1/2 Max cd



Based on 25 foot mounting height. Maximum calculated value = 24.6 fc
Type IV - Short - N/A

REPORT NUMBER: P957565
CATALOG NUMBER: GLAN-SB9D-850-U-SLL-HSS

Luminous Intensity Polar Plot



REPORT NUMBER: P957565

CATALOG NUMBER: GLAN-SB9D-850-U-SLL-HSS


FLUX DISTRIBUTION:

		Downward	Upward	Total
House Side	Lumens	13449.1	0.0	13449.1
	% Fixture	19.9	0.0	19.9
Street Side	Lumens	54212.9	0.0	54212.9
	% Fixture	80.1	0.0	80.1
Total	Lumens	67662.0	0.0	67662.0
	% Fixture	100.0	0.0	100.0

ZONAL LUMENS:

Zone	Lumens	% Fixture
0°-10°	922.4	1.4
10°-20°	2765.1	4.1
20°-30°	4073.6	6.0
30°-40°	5233.4	7.7
40°-50°	8464.0	12.5
50°-60°	14842.5	21.9
60°-70°	18572.0	27.4
70°-80°	10852.6	16.0
80°-90°	1936.3	2.9
90°-100°	0.0	0.0
100°-110°	0.0	0.0
110°-120°	0.0	0.0
120°-130°	0.0	0.0
130°-140°	0.0	0.0
140°-150°	0.0	0.0
150°-160°	0.0	0.0
160°-170°	0.0	0.0
170°-180°	0.0	0.0
0°-90°	67662.0	100.0
0°-180°	67662.0	100.0

Coefficient of Utilization



REPORT NUMBER: P957565


CATALOG NUMBER: GLAN-SB9D-850-U-SLL-HSS

LUMINAIRE CLASSIFICATION SYSTEM LUMEN TABLE AND BUG RATING:

Zone		Lumens	% Fixture	Zone Rating/Lumen Limit		
				B	U	G
FL	(0°-30°)	4527.4	6.7			
FM	(30°-60°)	21233.1	31.4			
FH	(60°-80°)	26606.8	39.3			G5
FVH	(80°-90°)	1845.5	2.7			G5
BL	(0°-30°)	3233.7	4.8	B4/5000		
BM	(30°-60°)	7306.8	10.8	B4/8500		
BH	(60°-80°)	2817.8	4.2	B4/5000		G4/5000
BVH	(80°-90°)	90.7	0.1			G1/100
UL	(90°-100°)	0.0	0.0		U0/0	
UH	(100°-180°)	0.0	0.0		U0/0	

BUG Rating: B4-U0-G5

Type IV Short



REPORT NUMBER: P957565

CATALOG NUMBER: GLAN-SB9D-850-U-SLL-HSS

CANDELA DISTRIBUTION (FULL):

	0°	5°	15°	25°	35°	45°	55°	65°	75°	85°
0°	9369.0	9369.0	9369.0	9369.0	9369.0	9369.0	9369.0	9369.0	9369.0	9369.0
2.5°	10497.0	10576.3	10753.4	10846.6	10991.1	11000.4	11000.4	10874.6	10869.9	10613.6
5°	11732.3	11918.7	12338.2	12771.7	12864.9	12888.2	12841.6	12589.9	12403.5	11904.7
7.5°	12958.1	13317.1	13955.6	14533.6	14720.1	14720.1	14608.2	14198.0	13815.8	13093.3
10°	13974.3	14426.4	15293.4	15941.3	16155.7	16109.1	15880.7	15363.3	14836.6	13960.3
12.5°	14645.5	15153.6	16104.5	16626.5	16845.6	16724.4	16463.4	15960.0	15405.3	14482.4
15°	14981.1	15512.5	16337.5	16612.5	16551.9	16426.1	16393.5	16151.1	15731.6	14869.2
17.5°	15125.6	15619.7	16193.0	16020.6	15507.8	15409.9	15736.2	16043.9	15941.3	15204.9
20°	15260.8	15675.6	15848.1	15083.7	14188.7	14100.1	14724.7	15601.1	16048.5	15517.2
22.5°	15447.2	15703.6	15349.3	14095.5	13130.6	12925.5	13615.4	14934.5	16081.2	15913.4
25°	15703.6	15773.5	14799.3	13158.6	12189.1	11984.0	12627.2	14193.4	16025.2	16342.2
27.5°	16011.2	15866.7	14272.6	12375.5	11438.6	11247.5	11890.7	13480.2	15866.7	16771.0
30°	16412.1	15987.9	13750.6	11769.5	10902.6	10762.7	11382.7	12864.9	15671.0	17316.4
32.5°	16817.6	16039.2	13265.8	11415.3	10781.4	10832.6	11340.7	12534.0	15456.6	17838.4
35°	17255.8	16202.3	13028.1	11764.9	11792.8	12240.3	12450.1	12841.6	15423.9	18546.9
37.5°	17852.4	16565.9	13312.4	13503.5	14473.0	15400.6	15228.2	14347.2	15801.5	19605.0
40°	18710.1	17204.5	14552.3	16463.4	18453.7	19959.3	19302.0	17083.3	16957.5	21129.2
42.5°	19959.3	18220.7	16752.4	20080.5	23455.2	25934.9	24173.0	20611.8	18980.4	23306.0
45°	21805.1	19866.1	19413.9	23898.0	29622.0	33528.0	29864.3	24373.4	21814.4	26601.5
47.5°	24364.1	22285.2	21907.7	27920.6	37117.2	42169.9	36175.6	27860.0	25040.0	31094.9
50°	27762.1	25543.4	24270.9	32320.8	45334.9	50979.6	42482.2	31225.4	28736.3	36585.8
52.5°	32246.2	30088.1	27025.7	36511.2	53785.6	59602.8	48816.8	34180.6	33323.0	42957.7
55°	38361.7	36926.1	30791.9	40510.5	62231.7	68277.3	54904.3	36968.0	39382.5	50527.5
57.5°	45950.2	46975.6	36222.2	45148.4	69824.9	77217.5	61019.8	40864.8	47250.6	58992.2
60°	50844.4	60339.3	46621.4	52005.1	78452.7	87327.7	69400.7	48276.1	55519.6	62026.7
62.5°	49660.5	64590.3	59076.1	60758.8	86386.1	94678.4	77613.7	55720.0	57076.5	57556.6
65°	46029.4	61159.7	56535.8	62460.1	88395.1	95093.2	79809.2	54759.8	48415.9	46989.6
67.5°	41032.6	57090.4	50499.5	57948.1	84764.0	89294.7	75721.3	48439.2	37415.5	35262.0
70°	35639.6	52587.7	46537.5	52886.0	77842.1	79189.2	68771.4	42603.4	27519.8	23814.1
72.5°	30521.6	47898.5	43824.6	47698.1	68608.3	65820.9	59724.0	37443.5	20038.5	17176.5
75°	25287.0	40981.3	39960.5	41536.0	56465.8	51846.6	49623.2	31001.7	15726.9	12426.8
77.5°	19511.8	32022.5	34371.7	33262.4	39746.1	38510.9	38464.3	23296.7	11489.9	8292.3
80°	13354.4	22317.8	26853.2	23464.5	25795.1	25165.8	28969.4	15629.0	8334.2	4992.2
82.5°	7849.5	13587.4	18691.4	11359.4	14263.3	14640.8	17251.1	7602.4	4903.6	1151.3
85°	3183.6	5365.0	7308.8	4446.8	6879.9	5803.2	6549.0	2134.8	1365.7	28.0
87.5°	801.7	1715.3	1202.6	498.7	797.1	731.8	578.0	261.0	55.9	0.0
90°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0

REPORT NUMBER: P957565

CATALOG NUMBER: GLAN-SB9D-850-U-SLL-HSS

CANDELA DISTRIBUTION (continued):

90°		95°	105°	115°	125°	135°	145°	155°	165°	175°	180°
9369.0	0°	9369.0	9369.0	9369.0	9369.0	9369.0	9369.0	9369.0	9369.0	9369.0	9369.0
10585.6	2.5°	10403.8	10296.6	10030.9	9765.2	9550.8	9261.8	9070.7	8842.3	8623.2	8427.5
11797.5	5°	11503.9	11149.6	10664.8	10222.0	9769.9	9331.7	8898.2	8441.4	8021.9	7765.6
12823.0	7.5°	12398.8	11774.2	11131.0	10567.0	10021.6	9508.9	8935.5	8380.8	7723.6	7374.0
13606.1	10°	13065.4	12245.0	11401.3	10753.4	10203.4	9704.6	9219.9	8660.5	7868.1	7430.0
14081.5	12.5°	13503.5	12529.3	11541.1	10800.0	10184.7	9797.9	9583.4	9364.4	8576.6	8063.9
14431.1	15°	13806.5	12729.8	11639.0	10692.8	9937.7	9653.4	9867.8	10119.5	9616.1	9024.1
14794.7	17.5°	14137.4	12990.8	11681.0	10403.8	9457.6	9336.4	9891.1	10473.7	10450.4	9863.1
15139.6	20°	14487.0	13219.2	11653.0	9937.7	8874.9	8982.1	9690.6	10366.5	10650.9	10333.9
15535.8	22.5°	14845.9	13438.3	11545.8	9331.7	8329.6	8665.2	9373.7	9965.7	10301.3	10203.4
16020.6	25°	15298.1	13745.9	11387.3	8679.2	7877.4	8343.6	9005.4	9485.6	9718.6	9714.0
16542.6	27.5°	15838.8	14156.1	11303.4	8152.4	7555.8	7980.0	8567.3	8996.1	9159.3	9159.3
17190.5	30°	16468.0	14640.8	11210.2	7807.5	7369.4	7602.4	8059.2	8478.7	8641.9	8641.9
17899.0	32.5°	17167.2	15107.0	10986.5	7597.8	7229.5	7234.2	7523.2	7905.4	8101.2	8129.1
18784.7	35°	18006.2	15605.7	10497.0	7430.0	7066.4	6875.3	7015.1	7332.1	7565.1	7625.7
20047.8	37.5°	19106.3	16216.3	9797.9	7182.9	6814.7	6497.7	6530.3	6772.7	7029.1	7122.3
21791.1	40°	20583.9	16934.2	9070.7	6828.7	6460.4	6082.9	6068.9	6246.0	6497.7	6600.3
24149.7	42.5°	22536.9	17796.5	8376.2	6488.4	6031.6	5644.7	5621.4	5761.2	5980.3	6087.5
27263.4	45°	25035.3	18854.6	7779.6	6222.7	5612.1	5229.9	5220.5	5337.1	5528.2	5640.1
31248.7	47.5°	28507.9	19912.7	7374.0	6082.9	5281.1	4889.6	4908.2	5010.8	5183.3	5262.5
36408.7	50°	33034.0	20234.3	7168.9	6082.9	5104.0	4586.6	4679.8	4763.8	4894.3	4940.9
42594.1	52.5°	37378.2	19171.5	6982.5	6120.2	5127.3	4330.3	4530.7	4591.3	4703.2	4721.8
48327.4	55°	39508.4	16482.0	6726.1	6129.5	5271.8	4111.2	4409.5	4521.4	4563.3	4558.7
51655.5	57.5°	38776.6	13326.4	6292.6	6092.2	5369.7	3971.3	4260.3	4474.8	4502.7	4460.8
51021.5	60°	36208.2	9811.8	5961.7	5817.2	5332.4	3929.4	4031.9	4372.2	4414.2	4358.2
46136.6	62.5°	31901.3	6810.0	5705.3	5211.2	5169.3	3915.4	3673.0	4148.5	4251.0	4171.8
37084.5	65°	25114.6	4810.4	4912.9	4568.0	4815.0	3840.8	3300.1	3878.1	4018.0	3896.8
26904.5	67.5°	16994.8	3472.6	3980.7	4139.2	4241.7	3673.0	3029.8	3570.5	3756.9	3598.5
17265.1	70°	9177.9	2437.8	2628.9	3486.6	3603.1	3384.0	2787.4	3258.2	3472.6	3300.1
12273.0	72.5°	5421.0	1752.6	1841.2	2801.4	3001.8	2978.5	2517.1	2894.6	3155.6	2950.5
8469.4	75°	2987.8	1183.9	1314.5	2032.3	2437.8	2298.0	2162.8	2451.8	2717.5	2517.1
5309.1	77.5°	1337.8	708.5	913.6	1333.1	1915.8	1575.5	1673.4	1911.1	2158.1	1948.4
2955.2	80°	517.4	396.2	606.0	727.1	1393.7	871.6	1076.7	1407.7	1584.8	1417.0
643.2	82.5°	65.3	177.1	261.0	284.3	811.0	461.5	624.6	885.6	871.6	755.1
0.0	85°	0.0	32.6	37.3	18.6	349.6	167.8	205.1	289.0	270.3	205.1
0.0	87.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	9.3	0.0
0.0	90°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0

REPORT NUMBER: P957565

CATALOG NUMBER: GLAN-SB9D-850-U-SLL-HSS

CANDELA DISTRIBUTION (continued):

185°		195°	205°	215°	225°	235°	245°	255°	265°	270°	275°
9369.0	0°	9369.0	9369.0	9369.0	9369.0	9369.0	9369.0	9369.0	9369.0	9369.0	9369.0
8390.2	2.5°	8161.8	7994.0	7910.1	7840.1	7905.4	7942.7	7942.7	8101.2	8194.4	8231.7
7602.4	5°	7192.2	6879.9	6670.2	6544.3	6586.3	6632.9	6684.2	6884.6	7019.8	7108.3
7057.1	7.5°	6427.8	5952.4	5658.7	5504.9	5528.2	5560.8	5602.8	5798.5	5933.7	6050.2
6954.5	10°	6050.2	5379.0	4992.2	4805.7	4773.1	4754.4	4740.4	4857.0	4959.5	5052.7
7374.0	12.5°	6068.9	5132.0	4661.2	4432.8	4334.9	4223.1	4134.5	4153.1	4218.4	4334.9
8124.5	15°	6306.6	5052.7	4488.7	4204.4	4041.3	3910.8	3803.5	3780.2	3803.5	3822.2
8982.1	17.5°	6628.2	5043.4	4339.6	3985.3	3817.5	3710.3	3612.4	3579.8	3584.5	3607.8
9550.8	20°	6884.6	5015.5	4171.8	3775.6	3626.4	3533.2	3435.3	3402.7	3412.0	3416.7
9606.7	22.5°	7019.8	4973.5	3985.3	3565.8	3440.0	3346.7	3258.2	3253.5	3253.5	3281.5
9303.8	25°	7019.8	4884.9	3817.5	3365.4	3253.5	3169.6	3062.4	3081.1	3090.4	3127.7
8833.0	27.5°	6852.0	4717.1	3682.4	3192.9	3076.4	2992.5	2894.6	2917.9	2931.9	2973.8
8366.9	30°	6637.6	4516.7	3528.5	3029.8	2894.6	2834.0	2750.1	2759.4	2778.1	2824.7
7933.4	32.5°	6409.2	4279.0	3402.7	2866.6	2731.5	2684.9	2591.6	2605.6	2624.3	2675.5
7504.5	35°	6157.5	3999.3	3253.5	2717.5	2582.3	2545.0	2437.8	2447.1	2475.1	2531.0
7043.1	37.5°	5891.8	3770.9	3104.4	2573.0	2433.1	2395.9	2284.0	2293.3	2325.9	2391.2
6558.3	40°	5630.7	3547.2	2945.9	2419.2	2279.3	2246.7	2125.5	2134.8	2172.1	2242.0
6068.9	42.5°	5346.4	3374.7	2740.8	2260.7	2111.5	2078.9	1967.0	1981.0	2023.0	2092.9
5616.8	45°	5006.1	3262.8	2512.4	2111.5	1943.7	1911.1	1808.5	1836.5	1883.1	1953.0
5229.9	47.5°	4656.5	3216.2	2321.3	1953.0	1771.3	1743.3	1659.4	1706.0	1757.3	1813.2
4898.9	50°	4320.9	3155.6	2125.5	1803.9	1622.1	1594.1	1538.2	1598.8	1650.1	1701.3
4661.2	52.5°	3938.7	3025.1	1948.4	1673.4	1496.2	1486.9	1459.0	1514.9	1561.5	1608.1
4456.1	55°	3542.5	2815.4	1794.6	1556.8	1389.0	1398.4	1384.4	1431.0	1468.3	1510.2
4269.7	57.5°	3197.6	2549.7	1673.4	1431.0	1295.8	1323.8	1305.1	1328.4	1351.7	1403.0
4045.9	60°	2848.0	2232.7	1538.2	1281.8	1202.6	1235.2	1183.9	1179.3	1188.6	1202.6
3715.0	62.5°	2377.2	1901.8	1370.4	1151.3	1100.0	1114.0	1016.1	941.6	941.6	955.5
3253.5	65°	1911.1	1594.1	1183.9	1002.2	960.2	950.9	811.0	708.5	699.2	741.1
2717.5	67.5°	1570.8	1323.8	997.5	834.4	806.4	815.7	713.2	610.6	601.3	647.9
2214.1	70°	1300.5	1067.4	797.1	643.2	671.2	713.2	610.6	512.7	498.7	540.7
1799.2	72.5°	1034.8	834.4	610.6	475.4	554.7	606.0	498.7	405.5	396.2	433.5
1389.0	75°	759.8	596.6	414.8	344.9	428.8	475.4	363.6	289.0	275.0	307.6
927.6	77.5°	470.8	335.6	261.0	205.1	293.7	317.0	191.1	167.8	163.1	186.4
564.0	80°	219.1	144.5	125.9	69.9	107.2	125.9	79.2	88.6	93.2	111.9
284.3	82.5°	60.6	23.3	4.7	0.0	0.0	37.3	18.6	37.3	46.6	69.9
23.3	85°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	9.3	23.3	42.0
0.0	87.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	18.6
0.0	90°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0

REPORT NUMBER: P957565

CATALOG NUMBER: GLAN-SB9D-850-U-SLL-HSS

CANDELA DISTRIBUTION (continued):

285°		295°	305°	315°	325°	335°	345°	355°	360°
9369.0	0°	9369.0	9369.0	9369.0	9369.0	9369.0	9369.0	9369.0	9369.0
8492.7	2.5°	8688.5	8874.9	9173.3	9480.9	9783.9	10091.5	10389.8	10497.0
7513.9	5°	7882.1	8310.9	8902.9	9536.8	10189.4	10851.3	11457.2	11732.3
6502.4	7.5°	6982.5	7597.8	8488.1	9480.9	10520.3	11559.8	12515.3	12958.1
5500.2	10°	6022.3	6800.7	7816.8	9159.3	10650.9	12086.5	13401.0	13974.3
4619.3	12.5°	5108.7	5924.4	7047.7	8655.9	10548.3	12389.5	13969.6	14645.5
3999.3	15°	4344.2	5066.7	6278.6	8059.2	10217.4	12408.1	14240.0	14981.1
3654.4	17.5°	3770.9	4241.7	5495.6	7397.3	9783.9	12235.7	14333.2	15125.6
3467.9	20°	3486.6	3617.1	4479.4	6549.0	9378.3	12072.5	14426.4	15260.8
3318.8	22.5°	3318.8	3351.4	3663.7	5453.6	8893.6	12021.2	14589.6	15447.2
3183.6	25°	3183.6	3192.9	3276.8	4320.9	8152.4	11988.6	14841.3	15703.6
3043.8	27.5°	3048.4	3048.4	3095.0	3481.9	7145.6	11848.8	15167.6	16011.2
2903.9	30°	2913.3	2913.3	2945.9	3081.1	5966.3	11573.8	15559.1	16412.1
2764.1	32.5°	2773.4	2773.4	2801.4	2899.3	4763.8	11228.8	15918.0	16817.6
2619.6	35°	2633.6	2624.3	2661.5	2764.1	3789.6	10790.7	16276.9	17255.8
2475.1	37.5°	2484.4	2479.8	2517.1	2633.6	3272.2	10282.6	16547.3	17852.4
2330.6	40°	2325.9	2325.9	2367.9	2493.7	3123.0	9644.0	16976.1	18710.1
2181.4	42.5°	2181.4	2172.1	2218.7	2372.6	3011.1	9033.4	17745.2	19959.3
2046.3	45°	2041.6	2023.0	2064.9	2256.0	2815.4	8819.0	19180.9	21805.1
1915.8	47.5°	1911.1	1864.5	1901.8	2116.2	2638.2	9620.7	21530.1	24364.1
1799.2	50°	1803.9	1715.3	1748.0	1976.4	2503.1	11359.4	24578.5	27762.1
1692.0	52.5°	1692.0	1575.5	1594.1	1803.9	2381.9	13014.1	27883.3	32246.2
1584.8	55°	1575.5	1445.0	1454.3	1631.4	2209.4	13261.1	31108.9	38361.7
1463.6	57.5°	1445.0	1323.8	1323.8	1472.9	2083.6	11494.5	33588.6	45950.2
1314.5	60°	1300.5	1221.2	1197.9	1347.1	2195.4	8110.5	33877.6	50844.4
1123.4	62.5°	1142.0	1100.0	1067.4	1225.9	2279.3	4805.7	31551.7	49660.5
885.6	65°	960.2	950.9	927.6	1347.1	1920.4	2838.7	27086.3	46029.4
755.1	67.5°	806.4	792.4	792.4	1412.3	1459.0	1785.2	21161.9	41032.6
643.2	70°	694.5	643.2	643.2	1067.4	885.6	1235.2	14776.0	35639.6
531.4	72.5°	582.7	526.7	489.4	853.0	661.9	904.3	9233.8	30521.6
405.5	75°	466.1	424.2	377.6	564.0	494.1	685.2	5365.0	25287.0
256.4	77.5°	335.6	317.0	265.7	414.8	358.9	494.1	3192.9	19511.8
158.5	80°	172.5	177.1	167.8	237.7	242.4	335.6	1817.9	13354.4
102.5	82.5°	102.5	79.2	88.6	116.5	139.8	191.1	685.2	7849.5
74.6	85°	65.3	42.0	42.0	55.9	69.9	74.6	209.8	3183.6
37.3	87.5°	32.6	14.0	18.6	28.0	23.3	18.6	9.3	801.7
0.0	90°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0

(END OF REPORT)