

Scaled data based on original data using
LM-79-08 Approved Method: Electrical and Photometric Measurements of Solid-
State Lighting Products

Test Report Prepared for
Cooper Lighting Solutions
(formerly Eaton)

Brand: STREETWORKS

Report Number: P951517

Luminaire Tested: **GLAN-SB5C-927-U-SLL-HSS**

Issue Date: 1/21/2025

Test Information

Test Method: LM-79-08
Report Number: P951517
TEST IS SCALED FROM IESNA LM-79-08 TEST DATA (G2-2411-289-9)
Test Lab: INNOVATION CENTER
Issue Date: 1/21/2025
Manufacturer: COOPER LIGHTING SOLUTIONS (FORMERLY EATON)
Product Line: STREETWORKS
Catalog Number: GLAN-SB5C-927-U-SLL-HSS
Description: GALLEON AREA AND ROADWAY HIGH DENSITY LED LUMINAIRE
(5) 90 CRI, 2700K, 615mA LIGHTSQUARES WITH 26 LEDS EACH AND SPILL LIGHT
ELIMINATOR LEFT OPTICS WITH HOUSE SIDE SHIELD
Light Source: -
Ballast/Driver: -

Summary

Lumens per Lamp: N/A
Luminaire Lumens: 17574 lumens
Efficiency: N/A
Efficacy: 70.4 lumens/watt
Luminous Opening: Rectangular (W 1.5' x L: 1' x H: 0')
IES Classification: Type IV - Short
BUG Rating: B2 - U0 - G3

Input Watts (W): 249.5
Input Voltage (V): NR
Input Current (Ain): NR
Voltage Rise (V): NR
Power Factor: NR
Total Harmonic Distortion (THDi): NR
Frequency (hertz): 60
Stabilization Time: NR
Operation Time: NR
Ambient Temperature (°C): NR
Test Distance: 24 FT




REPORT NUMBER: P951517

CATALOG NUMBER: GLAN-SB5C-927-U-SLL-HSS

Iso-Footcandle Lines of Horizontal Illumination

× Max cd

--- 1/2 Max cd




Based on 25 foot mounting height. Maximum calculated value = 6.4 fc

Type IV - Short - N/A

REPORT NUMBER: P951517
CATALOG NUMBER: GLAN-SB5C-927-U-SLL-HSS

Luminous Intensity Polar Plot



REPORT NUMBER: P951517

CATALOG NUMBER: GLAN-SB5C-927-U-SLL-HSS

FLUX DISTRIBUTION:

		Downward	Upward	Total
House Side	Lumens	3493.2	0.0	3493.2
	% Fixture	19.9	0.0	19.9
Street Side	Lumens	14080.8	0.0	14080.8
	% Fixture	80.1	0.0	80.1
Total	Lumens	17574.0	0.0	17574.0
	% Fixture	100.0	0.0	100.0

ZONAL LUMENS:

Zone	Lumens	% Fixture
0°-10°	239.6	1.4
10°-20°	718.2	4.1
20°-30°	1058.0	6.0
30°-40°	1359.3	7.7
40°-50°	2198.4	12.5
50°-60°	3855.1	21.9
60°-70°	4823.7	27.4
70°-80°	2818.8	16.0
80°-90°	502.9	2.9
90°-100°	0.0	0.0
100°-110°	0.0	0.0
110°-120°	0.0	0.0
120°-130°	0.0	0.0
130°-140°	0.0	0.0
140°-150°	0.0	0.0
150°-160°	0.0	0.0
160°-170°	0.0	0.0
170°-180°	0.0	0.0
0°-90°	17574.0	100.0
0°-180°	17574.0	100.0

Coefficient of Utilization



REPORT NUMBER: P951517


CATALOG NUMBER: GLAN-SB5C-927-U-SLL-HSS

LUMINAIRE CLASSIFICATION SYSTEM LUMEN TABLE AND BUG RATING:

Zone		Lumens	% Fixture	Zone Rating/Lumen Limit		
				B	U	G
FL	(0°-30°)	1175.9	6.7			
FM	(30°-60°)	5514.9	31.4			
FH	(60°-80°)	6910.6	39.3			G3/7500
FVH	(80°-90°)	479.3	2.7			G3/500
BL	(0°-30°)	839.9	4.8	B2/1000		
BM	(30°-60°)	1897.8	10.8	B2/2500		
BH	(60°-80°)	731.9	4.2	B2/1000		G2/1000
BVH	(80°-90°)	23.6	0.1			G1/100
UL	(90°-100°)	0.0	0.0		U0/0	
UH	(100°-180°)	0.0	0.0		U0/0	

BUG Rating: B2-U0-G3

Type IV Short



REPORT NUMBER: P951517

CATALOG NUMBER: GLAN-SB5C-927-U-SLL-HSS

CANDELA DISTRIBUTION (FULL):

	0°	5°	15°	25°	35°	45°	55°	65°	75°	85°
0°	2433.4	2433.4	2433.4	2433.4	2433.4	2433.4	2433.4	2433.4	2433.4	2433.4
2.5°	2726.4	2747.0	2793.0	2817.2	2854.7	2857.2	2857.2	2824.5	2823.3	2756.7
5°	3047.2	3095.7	3204.6	3317.2	3341.4	3347.5	3335.4	3270.0	3221.6	3092.0
7.5°	3365.6	3458.9	3624.7	3774.9	3823.3	3823.3	3794.2	3687.7	3588.4	3400.8
10°	3629.6	3747.0	3972.2	4140.5	4196.2	4184.1	4124.7	3990.4	3853.5	3625.9
12.5°	3803.9	3935.9	4182.8	4318.4	4375.3	4343.9	4276.1	4145.3	4001.2	3761.5
15°	3891.1	4029.1	4243.4	4314.8	4299.1	4266.4	4257.9	4195.0	4086.0	3862.0
17.5°	3928.6	4056.9	4205.9	4161.1	4027.9	4002.5	4087.2	4167.1	4140.5	3949.2
20°	3963.7	4071.5	4116.3	3917.7	3685.3	3662.3	3824.5	4052.1	4168.3	4030.3
22.5°	4012.1	4078.7	3986.7	3661.1	3410.4	3357.2	3536.4	3879.0	4176.8	4133.2
25°	4078.7	4096.9	3843.9	3417.7	3165.9	3112.6	3279.7	3686.5	4162.3	4244.6
27.5°	4158.6	4121.1	3707.1	3214.3	2971.0	2921.3	3088.4	3501.2	4121.1	4356.0
30°	4262.8	4152.6	3571.5	3056.9	2831.7	2795.4	2956.4	3341.4	4070.3	4497.6
32.5°	4368.1	4165.9	3445.6	2964.9	2800.3	2813.6	2945.5	3255.5	4014.6	4633.2
35°	4481.9	4208.3	3383.8	3055.7	3063.0	3179.2	3233.7	3335.4	4006.1	4817.2
37.5°	4636.8	4302.7	3457.7	3507.3	3759.1	4000.0	3955.2	3726.4	4104.2	5092.1
40°	4859.6	4468.6	3779.7	4276.1	4793.0	5184.1	5013.4	4437.1	4404.4	5487.9
42.5°	5184.1	4732.5	4351.1	5215.5	6092.1	6736.1	6278.5	5353.6	4929.8	6053.3
45°	5663.5	5159.9	5042.4	6207.1	7693.8	8708.3	7756.7	6330.6	5665.9	6909.3
47.5°	6328.1	5788.2	5690.1	7251.9	9640.5	10952.9	9396.0	7236.1	6503.7	8076.3
50°	7210.7	6634.4	6303.9	8394.8	11774.9	13241.0	11034.0	8110.2	7463.7	9502.5
52.5°	8375.4	7814.8	7019.4	9483.1	13969.9	15480.8	12679.3	8877.8	8655.0	11157.5
55°	9963.8	9590.9	7997.7	10521.9	16163.6	17733.8	14260.4	9601.8	10228.9	13123.6
57.5°	11934.7	12201.1	9408.1	11726.5	18135.8	20055.9	15848.8	10613.9	12272.5	15322.2
60°	13205.9	15672.1	12109.1	13507.4	20376.7	22681.8	18025.6	12538.9	14420.2	16110.3
62.5°	12898.4	16776.2	15344.0	15781.0	22437.3	24591.0	20158.8	14472.3	14824.6	14949.3
65°	11955.3	15885.1	14684.2	16222.9	22959.1	24698.8	20729.0	14222.9	12575.2	12204.7
67.5°	10657.5	14828.2	13116.3	15051.0	22015.9	23192.7	19667.3	12581.2	9718.0	9158.7
70°	9256.7	13658.7	12087.3	13736.2	20218.1	20568.0	17862.2	11065.5	7147.8	6185.3
72.5°	7927.4	12440.8	11382.7	12388.7	17819.8	17095.8	15512.3	9725.3	5204.6	4461.3
75°	6567.9	10644.2	10379.0	10788.2	14666.0	13466.2	12888.7	8052.1	4084.8	3227.6
77.5°	5067.8	8317.3	8927.4	8639.3	10323.3	10002.5	9990.4	6050.9	2984.3	2153.8
80°	3468.6	5796.7	6974.6	6094.5	6699.8	6536.4	7524.3	4059.4	2164.7	1296.6
82.5°	2038.8	3529.1	4854.8	2950.4	3704.6	3802.7	4480.7	1974.6	1273.6	299.0
85°	826.9	1393.5	1898.3	1155.0	1786.9	1507.3	1701.0	554.5	354.7	7.3
87.5°	208.2	445.5	312.4	129.5	207.0	190.1	150.1	67.8	14.5	0.0
90°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0

REPORT NUMBER: P951517

CATALOG NUMBER: GLAN-SB5C-927-U-SLL-HSS

CANDELA DISTRIBUTION (continued):

90°		95°	105°	115°	125°	135°	145°	155°	165°	175°	180°
2433.4	0°	2433.4	2433.4	2433.4	2433.4	2433.4	2433.4	2433.4	2433.4	2433.4	2433.4
2749.4	2.5°	2702.2	2674.4	2605.4	2536.3	2480.7	2405.6	2356.0	2296.6	2239.7	2188.9
3064.2	5°	2987.9	2895.9	2770.0	2655.0	2537.6	2423.8	2311.2	2192.5	2083.6	2017.0
3330.5	7.5°	3220.4	3058.1	2891.1	2744.6	2602.9	2469.8	2320.8	2176.8	2006.1	1915.3
3533.9	10°	3393.5	3180.4	2961.3	2793.0	2650.1	2520.6	2394.7	2249.4	2043.6	1929.8
3657.4	12.5°	3507.3	3254.3	2997.6	2805.1	2645.3	2544.8	2489.1	2432.2	2227.6	2094.5
3748.2	15°	3586.0	3306.3	3023.0	2777.3	2581.1	2507.3	2563.0	2628.4	2497.6	2343.8
3842.7	17.5°	3671.9	3374.1	3033.9	2702.2	2456.4	2425.0	2569.0	2720.4	2714.3	2561.8
3932.2	20°	3762.7	3433.4	3026.7	2581.1	2305.1	2333.0	2517.0	2692.5	2766.4	2684.0
4035.1	22.5°	3856.0	3490.3	2998.8	2423.8	2163.5	2250.6	2434.6	2588.4	2675.6	2650.1
4161.1	25°	3973.4	3570.3	2957.7	2254.3	2046.0	2167.1	2339.0	2463.7	2524.2	2523.0
4296.7	27.5°	4113.8	3676.8	2935.9	2117.5	1962.5	2072.7	2225.2	2336.6	2379.0	2379.0
4464.9	30°	4277.3	3802.7	2911.6	2027.9	1914.1	1974.6	2093.2	2202.2	2244.6	2244.6
4649.0	32.5°	4458.9	3923.8	2853.5	1973.4	1877.7	1879.0	1954.0	2053.3	2104.1	2111.4
4879.0	35°	4676.8	4053.3	2726.4	1929.8	1835.4	1785.7	1822.1	1904.4	1964.9	1980.6
5207.1	37.5°	4962.5	4211.9	2544.8	1865.6	1770.0	1687.7	1696.1	1759.1	1825.7	1849.9
5659.9	40°	5346.3	4398.3	2356.0	1773.6	1678.0	1579.9	1576.3	1622.3	1687.7	1714.3
6272.5	42.5°	5853.6	4622.3	2175.6	1685.2	1566.6	1466.1	1460.1	1496.4	1553.3	1581.1
7081.2	45°	6502.5	4897.1	2020.6	1616.2	1457.6	1358.4	1355.9	1386.2	1435.8	1464.9
8116.3	47.5°	7404.4	5172.0	1915.3	1579.9	1371.7	1270.0	1274.8	1301.5	1346.3	1366.8
9456.5	50°	8580.0	5255.5	1862.0	1579.9	1325.7	1191.3	1215.5	1237.3	1271.2	1283.3
11063.1	52.5°	9708.3	4979.5	1813.6	1589.6	1331.7	1124.7	1176.8	1192.5	1221.6	1226.4
12552.2	55°	10261.6	4280.9	1747.0	1592.0	1369.3	1067.8	1145.3	1174.3	1185.2	1184.0
13416.6	57.5°	10071.5	3461.3	1634.4	1582.3	1394.7	1031.5	1106.5	1162.2	1169.5	1158.6
13251.9	60°	9404.4	2548.4	1548.4	1510.9	1385.0	1020.6	1047.2	1135.6	1146.5	1132.0
11983.2	62.5°	8285.8	1768.8	1481.9	1353.5	1342.6	1017.0	954.0	1077.5	1104.1	1083.5
9632.1	65°	6523.1	1249.4	1276.0	1186.5	1250.6	997.6	857.2	1007.3	1043.6	1012.1
6988.0	67.5°	4414.1	901.9	1033.9	1075.1	1101.7	954.0	786.9	927.4	975.8	934.6
4484.3	70°	2383.8	633.2	682.8	905.6	935.8	878.9	724.0	846.3	901.9	857.2
3187.7	72.5°	1408.0	455.2	478.2	727.6	779.7	773.6	653.8	751.8	819.6	766.4
2199.8	75°	776.0	307.5	341.4	527.8	633.2	596.9	561.7	636.8	705.8	653.8
1378.9	77.5°	347.5	184.0	237.3	346.3	497.6	409.2	434.6	496.4	560.5	506.1
767.6	80°	134.4	102.9	157.4	188.9	362.0	226.4	279.7	365.6	411.6	368.0
167.1	82.5°	16.9	46.0	67.8	73.9	210.7	119.9	162.2	230.0	226.4	196.1
0.0	85°	0.0	8.5	9.7	4.8	90.8	43.6	53.3	75.1	70.2	53.3
0.0	87.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	2.4	0.0
0.0	90°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0

REPORT NUMBER: P951517
CATALOG NUMBER: GLAN-SB5C-927-U-SLL-HSS

CANDELA DISTRIBUTION (continued):

185°		195°	205°	215°	225°	235°	245°	255°	265°	270°	275°
2433.4	0°	2433.4	2433.4	2433.4	2433.4	2433.4	2433.4	2433.4	2433.4	2433.4	2433.4
2179.2	2.5°	2119.9	2076.3	2054.5	2036.3	2053.3	2063.0	2063.0	2104.1	2128.3	2138.0
1974.6	5°	1868.1	1786.9	1732.5	1699.8	1710.7	1722.8	1736.1	1788.2	1823.3	1846.3
1832.9	7.5°	1669.5	1546.0	1469.7	1429.8	1435.8	1444.3	1455.2	1506.1	1541.2	1571.4
1806.3	10°	1571.4	1397.1	1296.6	1248.2	1239.7	1234.9	1231.2	1261.5	1288.1	1312.4
1915.3	12.5°	1576.3	1332.9	1210.7	1151.3	1125.9	1096.9	1073.9	1078.7	1095.7	1125.9
2110.2	15°	1638.0	1312.4	1165.9	1092.0	1049.6	1015.7	987.9	981.8	987.9	992.7
2333.0	17.5°	1721.6	1309.9	1127.1	1035.1	991.5	963.7	938.3	929.8	931.0	937.1
2480.7	20°	1788.2	1302.7	1083.5	980.6	941.9	917.7	892.3	883.8	886.2	887.4
2495.2	22.5°	1823.3	1291.8	1035.1	926.2	893.5	869.3	846.3	845.0	845.0	852.3
2416.5	25°	1823.3	1268.8	991.5	874.1	845.0	823.3	795.4	800.2	802.7	812.4
2294.2	27.5°	1779.7	1225.2	956.4	829.3	799.0	777.2	751.8	757.9	761.5	772.4
2173.1	30°	1724.0	1173.1	916.5	786.9	751.8	736.1	714.3	716.7	721.6	733.7
2060.6	32.5°	1664.7	1111.4	883.8	744.6	709.4	697.3	673.1	676.8	681.6	694.9
1949.2	35°	1599.3	1038.8	845.0	705.8	670.7	661.0	633.2	635.6	642.9	657.4
1829.3	37.5°	1530.3	979.4	806.3	668.3	632.0	622.3	593.2	595.6	604.1	621.1
1703.4	40°	1462.5	921.3	765.1	628.3	592.0	583.5	552.1	554.5	564.2	582.3
1576.3	42.5°	1388.6	876.5	711.9	587.2	548.4	540.0	510.9	514.5	525.4	543.6
1458.9	45°	1300.3	847.5	652.5	548.4	504.8	496.4	469.7	477.0	489.1	507.3
1358.4	47.5°	1209.5	835.4	602.9	507.3	460.1	452.8	431.0	443.1	456.4	470.9
1272.4	50°	1122.3	819.6	552.1	468.5	421.3	414.0	399.5	415.3	428.6	441.9
1210.7	52.5°	1023.0	785.7	506.1	434.6	388.6	386.2	378.9	393.5	405.6	417.7
1157.4	55°	920.1	731.2	466.1	404.4	360.8	363.2	359.6	371.7	381.4	392.3
1109.0	57.5°	830.5	662.2	434.6	371.7	336.6	343.8	339.0	345.0	351.1	364.4
1050.9	60°	739.7	579.9	399.5	332.9	312.4	320.8	307.5	306.3	308.7	312.4
964.9	62.5°	617.4	494.0	355.9	299.0	285.7	289.3	263.9	244.6	244.6	248.2
845.0	65°	496.4	414.0	307.5	260.3	249.4	247.0	210.7	184.0	181.6	192.5
705.8	67.5°	408.0	343.8	259.1	216.7	209.4	211.9	185.2	158.6	156.2	168.3
575.1	70°	337.8	277.2	207.0	167.1	174.3	185.2	158.6	133.2	129.5	140.4
467.3	72.5°	268.8	216.7	158.6	123.5	144.1	157.4	129.5	105.3	102.9	112.6
360.8	75°	197.3	155.0	107.7	89.6	111.4	123.5	94.4	75.1	71.4	79.9
240.9	77.5°	122.3	87.2	67.8	53.3	76.3	82.3	49.6	43.6	42.4	48.4
146.5	80°	56.9	37.5	32.7	18.2	27.8	32.7	20.6	23.0	24.2	29.1
73.9	82.5°	15.7	6.1	1.2	0.0	0.0	9.7	4.8	9.7	12.1	18.2
6.1	85°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	2.4	6.1	10.9
0.0	87.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	4.8
0.0	90°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0

REPORT NUMBER: P951517

CATALOG NUMBER: GLAN-SB5C-927-U-SLL-HSS

CANDELA DISTRIBUTION (continued):

285°		295°	305°	315°	325°	335°	345°	355°	360°
2433.4	0°	2433.4	2433.4	2433.4	2433.4	2433.4	2433.4	2433.4	2433.4
2205.8	2.5°	2256.7	2305.1	2382.6	2462.5	2541.2	2621.1	2698.6	2726.4
1951.6	5°	2047.2	2158.6	2312.4	2477.0	2646.5	2818.4	2975.8	3047.2
1688.9	7.5°	1813.6	1973.4	2204.6	2462.5	2732.5	3002.4	3250.6	3365.6
1428.6	10°	1564.2	1766.4	2030.3	2379.0	2766.4	3139.3	3480.7	3629.6
1199.8	12.5°	1326.9	1538.8	1830.5	2248.2	2739.7	3217.9	3628.4	3803.9
1038.8	15°	1128.3	1316.0	1630.8	2093.2	2653.8	3222.8	3698.6	3891.1
949.2	17.5°	979.4	1101.7	1427.4	1921.3	2541.2	3178.0	3722.8	3928.6
900.7	20°	905.6	939.5	1163.4	1701.0	2435.9	3135.6	3747.0	3963.7
862.0	22.5°	862.0	870.5	951.6	1416.5	2309.9	3122.3	3789.4	4012.1
826.9	25°	826.9	829.3	851.1	1122.3	2117.5	3113.8	3854.8	4078.7
790.6	27.5°	791.8	791.8	803.9	904.4	1855.9	3077.5	3939.5	4158.6
754.2	30°	756.7	756.7	765.1	800.2	1549.7	3006.1	4041.2	4262.8
717.9	32.5°	720.3	720.3	727.6	753.0	1237.3	2916.5	4134.4	4368.1
680.4	35°	684.0	681.6	691.3	717.9	984.3	2802.7	4227.6	4481.9
642.9	37.5°	645.3	644.1	653.8	684.0	849.9	2670.7	4297.9	4636.8
605.3	40°	604.1	604.1	615.0	647.7	811.1	2504.9	4409.2	4859.6
566.6	42.5°	566.6	564.2	576.3	616.2	782.1	2346.3	4609.0	5184.1
531.5	45°	530.3	525.4	536.3	586.0	731.2	2290.6	4981.9	5663.5
497.6	47.5°	496.4	484.3	494.0	549.6	685.2	2498.8	5592.1	6328.1
467.3	50°	468.5	445.5	454.0	513.3	650.1	2950.4	6383.8	7210.7
439.5	52.5°	439.5	409.2	414.0	468.5	618.6	3380.2	7242.2	8375.4
411.6	55°	409.2	375.3	377.7	423.7	573.9	3444.3	8080.0	9963.8
380.1	57.5°	375.3	343.8	343.8	382.6	541.2	2985.5	8724.1	11934.7
341.4	60°	337.8	317.2	311.1	349.9	570.2	2106.6	8799.1	13205.9
291.8	62.5°	296.6	285.7	277.2	318.4	592.0	1248.2	8195.0	12898.4
230.0	65°	249.4	247.0	240.9	349.9	498.8	737.3	7035.2	11955.3
196.1	67.5°	209.4	205.8	205.8	366.8	378.9	463.7	5496.4	10657.5
167.1	70°	180.4	167.1	167.1	277.2	230.0	320.8	3837.8	9256.7
138.0	72.5°	151.3	136.8	127.1	221.6	171.9	234.9	2398.3	7927.4
105.3	75°	121.1	110.2	98.1	146.5	128.3	178.0	1393.5	6567.9
66.6	77.5°	87.2	82.3	69.0	107.7	93.2	128.3	829.3	5067.8
41.2	80°	44.8	46.0	43.6	61.7	63.0	87.2	472.2	3468.6
26.6	82.5°	26.6	20.6	23.0	30.3	36.3	49.6	178.0	2038.8
19.4	85°	16.9	10.9	10.9	14.5	18.2	19.4	54.5	826.9
9.7	87.5°	8.5	3.6	4.8	7.3	6.1	4.8	2.4	208.2
0.0	90°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0

(END OF REPORT)