

Scaled data based on original data using  
LM-79-08 Approved Method: Electrical and Photometric Measurements of Solid-  
State Lighting Products

Test Report Prepared for  
Cooper Lighting Solutions  
(formerly Eaton)

Brand: STREETWORKS

Report Number: P954374

Luminaire Tested: **GLAN-SB7C-927-U-SLL**

Issue Date: 1/21/2025

**Test Information**

Test Method: LM-79-08  
Report Number: P954374  
TEST IS SCALED FROM IESNA LM-79-08 TEST DATA (G2-2411-289-8)  
Test Lab: INNOVATION CENTER  
Issue Date: 1/21/2025  
Manufacturer: COOPER LIGHTING SOLUTIONS (FORMERLY EATON)  
Product Line: STREETWORKS  
Catalog Number: GLAN-SB7C-927-U-SLL  
Description: GALLEON AREA AND ROADWAY HIGH DENSITY LED LUMINAIRE  
(7) 90 CRI, 2700K, 615mA LIGHTSQUARES WITH 26 LEDS EACH AND SPILL LIGHT  
ELIMINATOR LEFT OPTICS  
Light Source: -  
Ballast/Driver: -

**Summary**

Lumens per Lamp: N/A  
Luminaire Lumens: 32303 lumens  
Efficiency: N/A  
Efficacy: 92.2 lumens/watt  
Luminous Opening: Rectangular (W 1.5' x L: 1.5' x H: 0')  
IES Classification: Type IV - Short  
BUG Rating: B3 - U0 - G5


Input Watts (W): 350.5  
Input Voltage (V): NR  
Input Current (Ain): NR  
Voltage Rise (V): NR  
Power Factor: NR  
Total Harmonic Distortion (THDi): NR  
Frequency (hertz): 60  
Stabilization Time: NR  
Operation Time: NR  
Ambient Temperature (°C): NR  
Test Distance: 24 FT



REPORT NUMBER: P954374  
 CATALOG NUMBER: GLAN-SB7C-927-U-SLL

### Iso-Footcandle Lines of Horizontal Illumination


✕ Max cd  
 - - - 1/2 Max cd



Based on 25 foot mounting height. Maximum calculated value = 9.8 fc  
 Type IV - Short - N/A

REPORT NUMBER: P954374  
CATALOG NUMBER: GLAN-SB7C-927-U-SLL

### Luminous Intensity Polar Plot



— Vertical Plane Through 45-Deg Lateral      - - - Horizontal Cone Through 65-Deg Vertical

REPORT NUMBER: P954374  
 CATALOG NUMBER: GLAN-SB7C-927-U-SLL

**FLUX DISTRIBUTION:**

|                    |           | Downward | Upward | Total   |
|--------------------|-----------|----------|--------|---------|
| <b>House Side</b>  | Lumens    | 8209.8   | 0.0    | 8209.8  |
|                    | % Fixture | 25.4     | 0.0    | 25.4    |
| <b>Street Side</b> | Lumens    | 24093.2  | 0.0    | 24093.2 |
|                    | % Fixture | 74.6     | 0.0    | 74.6    |
| <b>Total</b>       | Lumens    | 32303.0  | 0.0    | 32303.0 |
|                    | % Fixture | 100.0    | 0.0    | 100.0   |

**ZONAL LUMENS:**

| Zone      | Lumens  | % Fixture |
|-----------|---------|-----------|
| 0°-10°    | 440.6   | 1.4       |
| 10°-20°   | 1383.3  | 4.3       |
| 20°-30°   | 2136.6  | 6.6       |
| 30°-40°   | 2707.7  | 8.4       |
| 40°-50°   | 4083.8  | 12.6      |
| 50°-60°   | 6598.0  | 20.4      |
| 60°-70°   | 8225.5  | 25.5      |
| 70°-80°   | 5393.9  | 16.7      |
| 80°-90°   | 1333.5  | 4.1       |
| 90°-100°  | 0.0     | 0.0       |
| 100°-110° | 0.0     | 0.0       |
| 110°-120° | 0.0     | 0.0       |
| 120°-130° | 0.0     | 0.0       |
| 130°-140° | 0.0     | 0.0       |
| 140°-150° | 0.0     | 0.0       |
| 150°-160° | 0.0     | 0.0       |
| 160°-170° | 0.0     | 0.0       |
| 170°-180° | 0.0     | 0.0       |
| 0°-90°    | 32303.0 | 100.0     |
| 0°-180°   | 32303.0 | 100.0     |

**Coefficient of Utilization**



REPORT NUMBER: P954374


CATALOG NUMBER: GLAN-SB7C-927-U-SLL

**LUMINAIRE CLASSIFICATION SYSTEM LUMEN TABLE AND BUG RATING:**

| Zone           | Lumens  | % Fixture | Zone Rating/Lumen Limit |      |          |
|----------------|---------|-----------|-------------------------|------|----------|
|                |         |           | B                       | U    | G        |
| FL (0°-30°)    | 2172.7  | 6.7       |                         |      |          |
| FM (30°-60°)   | 9422.1  | 29.2      |                         |      |          |
| FH (60°-80°)   | 11399.9 | 35.3      |                         |      | G4/12000 |
| FVH (80°-90°)  | 1098.5  | 3.4       |                         |      | G5       |
| BL (0°-30°)    | 1787.8  | 5.5       | B3/2500                 |      |          |
| BM (30°-60°)   | 3967.5  | 12.3      | B3/5000                 |      |          |
| BH (60°-80°)   | 2219.5  | 6.9       | B3/2500                 |      | G3/2500  |
| BVH (80°-90°)  | 235.0   | 0.7       |                         |      | G3/500   |
| UL (90°-100°)  | 0.0     | 0.0       |                         | U0/0 |          |
| UH (100°-180°) | 0.0     | 0.0       |                         | U0/0 |          |

**BUG Rating: B3-U0-G5**

Type IV Short



REPORT NUMBER: P954374

CATALOG NUMBER: GLAN-SB7C-927-U-SLL

**CANDELA DISTRIBUTION (FULL):**

|       | 0°      | 5°      | 10°     | 15°     | 20°     | 25°     | 30°     | 35°     | 40°     | 45°     |
|-------|---------|---------|---------|---------|---------|---------|---------|---------|---------|---------|
| 0°    | 4441.9  | 4441.9  | 4441.9  | 4441.9  | 4441.9  | 4441.9  | 4441.9  | 4441.9  | 4441.9  | 4441.9  |
| 2.5°  | 4776.9  | 4794.9  | 4813.2  | 4838.9  | 4864.7  | 4880.0  | 4895.3  | 4903.0  | 4910.7  | 4907.3  |
| 5°    | 5136.5  | 5199.8  | 5263.2  | 5325.9  | 5388.8  | 5422.9  | 5457.0  | 5477.6  | 5498.4  | 5514.1  |
| 7.5°  | 5497.9  | 5600.8  | 5703.6  | 5796.2  | 5888.7  | 5944.5  | 6000.2  | 6030.4  | 6060.4  | 6074.9  |
| 10°   | 5774.9  | 5896.6  | 6018.3  | 6126.8  | 6235.4  | 6301.2  | 6366.7  | 6396.0  | 6425.1  | 6436.2  |
| 12.5° | 5944.5  | 6076.4  | 6208.1  | 6306.3  | 6404.2  | 6451.9  | 6499.6  | 6515.6  | 6531.7  | 6533.4  |
| 15°   | 6047.6  | 6161.4  | 6275.1  | 6336.7  | 6398.4  | 6400.1  | 6401.8  | 6384.7  | 6367.7  | 6347.6  |
| 17.5° | 6105.5  | 6182.4  | 6259.3  | 6260.5  | 6261.5  | 6192.5  | 6123.4  | 6060.2  | 5996.8  | 5952.1  |
| 20°   | 6169.5  | 6196.2  | 6223.1  | 6142.2  | 6061.2  | 5908.8  | 5756.5  | 5645.5  | 5534.5  | 5466.3  |
| 22.5° | 6243.6  | 6208.5  | 6173.4  | 6005.7  | 5837.9  | 5613.8  | 5389.6  | 5250.9  | 5112.2  | 5036.8  |
| 25°   | 6339.1  | 6228.3  | 6117.5  | 5862.8  | 5608.2  | 5336.0  | 5063.7  | 4917.8  | 4772.3  | 4701.0  |
| 27.5° | 6468.6  | 6270.5  | 6072.3  | 5735.0  | 5397.8  | 5096.1  | 4794.4  | 4650.9  | 4507.6  | 4440.2  |
| 30°   | 6643.3  | 6347.9  | 6052.7  | 5637.5  | 5222.3  | 4908.0  | 4593.6  | 4460.5  | 4327.4  | 4264.7  |
| 32.5° | 6849.6  | 6445.1  | 6040.8  | 5571.0  | 5101.2  | 4805.9  | 4510.5  | 4406.0  | 4301.3  | 4256.1  |
| 35°   | 7100.1  | 6605.1  | 6110.3  | 5620.8  | 5131.4  | 4926.2  | 4721.1  | 4696.8  | 4672.4  | 4668.6  |
| 37.5° | 7522.0  | 6939.7  | 6357.5  | 5912.6  | 5467.7  | 5454.4  | 5441.1  | 5552.6  | 5664.1  | 5722.0  |
| 40°   | 8159.5  | 7526.2  | 6893.0  | 6562.2  | 6231.3  | 6464.8  | 6698.4  | 6969.4  | 7240.4  | 7375.4  |
| 42.5° | 9004.9  | 8376.6  | 7748.3  | 7557.8  | 7367.2  | 7876.5  | 8385.8  | 8878.8  | 9371.7  | 9661.1  |
| 45°   | 10048.9 | 9484.5  | 8920.0  | 8836.0  | 8751.8  | 9567.7  | 10383.8 | 11193.8 | 12004.0 | 12495.7 |
| 47.5° | 11354.6 | 10805.5 | 10256.3 | 10239.3 | 10222.3 | 11399.4 | 12576.2 | 13762.0 | 14947.7 | 15643.9 |
| 50°   | 13065.9 | 12387.7 | 11709.6 | 11712.5 | 11715.4 | 13232.4 | 14749.4 | 16314.7 | 17879.9 | 18826.3 |
| 52.5° | 15030.3 | 14209.1 | 13388.0 | 13305.0 | 13221.8 | 15033.9 | 16846.0 | 18782.6 | 20719.1 | 21853.5 |
| 55°   | 17121.8 | 16310.4 | 15499.1 | 15175.4 | 14851.7 | 16868.5 | 18885.1 | 21193.8 | 23502.6 | 24851.7 |
| 57.5° | 19024.0 | 18582.2 | 18140.2 | 17491.0 | 16841.9 | 18878.2 | 20914.6 | 23529.7 | 26144.6 | 27817.5 |
| 60°   | 20173.7 | 20859.9 | 21546.3 | 20740.1 | 19933.8 | 21861.0 | 23788.1 | 26587.9 | 29387.7 | 31195.9 |
| 62.5° | 19589.9 | 21465.0 | 23340.1 | 23249.3 | 23158.3 | 24923.6 | 26689.1 | 29352.9 | 32016.6 | 33687.8 |
| 65°   | 18421.4 | 20181.3 | 21941.2 | 22289.5 | 22637.5 | 24881.0 | 27124.6 | 29707.7 | 32290.5 | 33713.4 |
| 67.5° | 16855.9 | 18529.7 | 20203.5 | 20366.8 | 20529.9 | 22867.5 | 25204.9 | 27798.9 | 30393.0 | 31507.8 |
| 70°   | 14974.9 | 16795.5 | 18616.3 | 18689.2 | 18762.3 | 20852.7 | 22943.0 | 25175.4 | 27407.6 | 28027.2 |
| 72.5° | 12733.5 | 14822.7 | 16912.1 | 16964.6 | 17016.9 | 18652.4 | 20287.9 | 21959.8 | 23631.6 | 23694.3 |
| 75°   | 9898.1  | 12060.4 | 14222.7 | 14416.9 | 14611.0 | 15883.4 | 17155.8 | 18332.8 | 19509.8 | 19194.4 |
| 77.5° | 7072.0  | 9090.5  | 11109.1 | 11386.9 | 11664.8 | 12632.1 | 13599.4 | 14434.1 | 15269.0 | 14726.9 |
| 80°   | 4628.6  | 6326.8  | 8024.8  | 8370.1  | 8715.5  | 9446.0  | 10176.2 | 10614.6 | 11052.9 | 10181.0 |
| 82.5° | 2690.6  | 3851.5  | 5012.6  | 5398.3  | 5784.2  | 6287.1  | 6789.9  | 6972.8  | 7155.5  | 6470.3  |
| 85°   | 1183.8  | 1800.0  | 2416.1  | 2744.3  | 3072.4  | 3485.5  | 3898.5  | 4002.3  | 4106.2  | 3557.3  |
| 87.5° | 366.5   | 573.6   | 780.7   | 963.7   | 1146.8  | 1353.4  | 1560.0  | 1568.8  | 1577.5  | 1324.4  |
| 90°   | 0.0     | 0.0     | 0.0     | 0.0     | 0.0     | 0.0     | 0.0     | 0.0     | 0.0     | 0.0     |

REPORT NUMBER: P954374  
 CATALOG NUMBER: GLAN-SB7C-927-U-SLL

**CANDELA DISTRIBUTION (continued):**

| 50°     |       | 55°     | 60°     | 65°     | 70°     | 75°     | 80°     | 85°     | 90°     | 95°     | 100°    |
|---------|-------|---------|---------|---------|---------|---------|---------|---------|---------|---------|---------|
| 4441.9  | 0°    | 4441.9  | 4441.9  | 4441.9  | 4441.9  | 4441.9  | 4441.9  | 4441.9  | 4441.9  | 4441.9  | 4441.9  |
| 4910.7  | 2.5°  | 4903.0  | 4895.3  | 4880.0  | 4864.7  | 4838.9  | 4813.2  | 4794.9  | 4776.9  | 4740.2  | 4703.6  |
| 5498.4  | 5°    | 5477.6  | 5457.0  | 5422.9  | 5388.8  | 5325.9  | 5263.2  | 5199.8  | 5136.5  | 5055.6  | 4974.6  |
| 6060.4  | 7.5°  | 6030.4  | 6000.2  | 5944.5  | 5888.7  | 5796.2  | 5703.6  | 5600.8  | 5497.9  | 5364.2  | 5230.8  |
| 6425.1  | 10°   | 6396.0  | 6366.7  | 6301.2  | 6235.4  | 6126.8  | 6018.3  | 5896.6  | 5774.9  | 5605.9  | 5437.0  |
| 6531.7  | 12.5° | 6515.6  | 6499.6  | 6451.9  | 6404.2  | 6306.3  | 6208.1  | 6076.4  | 5944.5  | 5758.8  | 5573.4  |
| 6367.7  | 15°   | 6384.7  | 6401.8  | 6400.1  | 6398.4  | 6336.7  | 6275.1  | 6161.4  | 6047.6  | 5854.1  | 5660.7  |
| 5996.8  | 17.5° | 6060.2  | 6123.4  | 6192.5  | 6261.5  | 6260.5  | 6259.3  | 6182.4  | 6105.5  | 5909.3  | 5713.2  |
| 5534.5  | 20°   | 5645.5  | 5756.5  | 5908.8  | 6061.2  | 6142.2  | 6223.1  | 6196.2  | 6169.5  | 5965.6  | 5761.6  |
| 5112.2  | 22.5° | 5250.9  | 5389.6  | 5613.8  | 5837.9  | 6005.7  | 6173.4  | 6208.5  | 6243.6  | 6035.3  | 5826.9  |
| 4772.3  | 25°   | 4917.8  | 5063.7  | 5336.0  | 5608.2  | 5862.8  | 6117.5  | 6228.3  | 6339.1  | 6134.9  | 5930.8  |
| 4507.6  | 27.5° | 4650.9  | 4794.4  | 5096.1  | 5397.8  | 5735.0  | 6072.3  | 6270.5  | 6468.6  | 6273.9  | 6079.1  |
| 4327.4  | 30°   | 4460.5  | 4593.6  | 4908.0  | 5222.3  | 5637.5  | 6052.7  | 6347.9  | 6643.3  | 6455.1  | 6267.1  |
| 4301.3  | 32.5° | 4406.0  | 4510.5  | 4805.9  | 5101.2  | 5571.0  | 6040.8  | 6445.1  | 6849.6  | 6663.3  | 6477.1  |
| 4672.4  | 35°   | 4696.8  | 4721.1  | 4926.2  | 5131.4  | 5620.8  | 6110.3  | 6605.1  | 7100.1  | 6921.8  | 6743.4  |
| 5664.1  | 37.5° | 5552.6  | 5441.1  | 5454.4  | 5467.7  | 5912.6  | 6357.5  | 6939.7  | 7522.0  | 7294.6  | 7067.2  |
| 7240.4  | 40°   | 6969.4  | 6698.4  | 6464.8  | 6231.3  | 6562.2  | 6893.0  | 7526.2  | 8159.5  | 7828.1  | 7496.8  |
| 9371.7  | 42.5° | 8878.8  | 8385.8  | 7876.5  | 7367.2  | 7557.8  | 7748.3  | 8376.6  | 9004.9  | 8526.6  | 8048.3  |
| 12004.0 | 45°   | 11193.8 | 10383.8 | 9567.7  | 8751.8  | 8836.0  | 8920.0  | 9484.5  | 10048.9 | 9403.8  | 8758.6  |
| 14947.7 | 47.5° | 13762.0 | 12576.2 | 11399.4 | 10222.3 | 10239.3 | 10256.3 | 10805.5 | 11354.6 | 10446.6 | 9538.4  |
| 17879.9 | 50°   | 16314.7 | 14749.4 | 13232.4 | 11715.4 | 11712.5 | 11709.6 | 12387.7 | 13065.9 | 11697.0 | 10327.9 |
| 20719.1 | 52.5° | 18782.6 | 16846.0 | 15033.9 | 13221.8 | 13305.0 | 13388.0 | 14209.1 | 15030.3 | 13010.5 | 10990.6 |
| 23502.6 | 55°   | 21193.8 | 18885.1 | 16868.5 | 14851.7 | 15175.4 | 15499.1 | 16310.4 | 17121.8 | 14175.0 | 11228.4 |
| 26144.6 | 57.5° | 23529.7 | 20914.6 | 18878.2 | 16841.9 | 17491.0 | 18140.2 | 18582.2 | 19024.0 | 15000.3 | 10976.7 |
| 29387.7 | 60°   | 26587.9 | 23788.1 | 21861.0 | 19933.8 | 20740.1 | 21546.3 | 20859.9 | 20173.7 | 15206.6 | 10239.3 |
| 32016.6 | 62.5° | 29352.9 | 26689.1 | 24923.6 | 23158.3 | 23249.3 | 23340.1 | 21465.0 | 19589.9 | 14338.1 | 9086.4  |
| 32290.5 | 65°   | 29707.7 | 27124.6 | 24881.0 | 22637.5 | 22289.5 | 21941.2 | 20181.3 | 18421.4 | 13109.3 | 7797.3  |
| 30393.0 | 67.5° | 27798.9 | 25204.9 | 22867.5 | 20529.9 | 20366.8 | 20203.5 | 18529.7 | 16855.9 | 11647.1 | 6438.3  |
| 27407.6 | 70°   | 25175.4 | 22943.0 | 20852.7 | 18762.3 | 18689.2 | 18616.3 | 16795.5 | 14974.9 | 10051.5 | 5128.0  |
| 23631.6 | 72.5° | 21959.8 | 20287.9 | 18652.4 | 17016.9 | 16964.6 | 16912.1 | 14822.7 | 12733.5 | 8321.7  | 3910.1  |
| 19509.8 | 75°   | 18332.8 | 17155.8 | 15883.4 | 14611.0 | 14416.9 | 14222.7 | 12060.4 | 9898.1  | 6338.9  | 2779.7  |
| 15269.0 | 77.5° | 14434.1 | 13599.4 | 12632.1 | 11664.8 | 11386.9 | 11109.1 | 9090.5  | 7072.0  | 4436.7  | 1801.3  |
| 11052.9 | 80°   | 10614.6 | 10176.2 | 9446.0  | 8715.5  | 8370.1  | 8024.8  | 6326.8  | 4628.6  | 2858.5  | 1088.3  |
| 7155.5  | 82.5° | 6972.8  | 6789.9  | 6287.1  | 5784.2  | 5398.3  | 5012.6  | 3851.5  | 2690.6  | 1654.4  | 618.4   |
| 4106.2  | 85°   | 4002.3  | 3898.5  | 3485.5  | 3072.4  | 2744.3  | 2416.1  | 1800.0  | 1183.8  | 744.2   | 304.8   |
| 1577.5  | 87.5° | 1568.8  | 1560.0  | 1353.4  | 1146.8  | 963.7   | 780.7   | 573.6   | 366.5   | 243.7   | 121.0   |
| 0.0     | 90°   | 0.0     | 0.0     | 0.0     | 0.0     | 0.0     | 0.0     | 0.0     | 0.0     | 0.0     | 0.0     |



REPORT NUMBER: P954374  
 CATALOG NUMBER: GLAN-SB7C-927-U-SLL

**CANDELA DISTRIBUTION (continued):**

| 105°   |       | 110°   | 115°   | 120°   | 125°   | 130°   | 135°   | 140°   | 145°   | 150°   | 155°   |
|--------|-------|--------|--------|--------|--------|--------|--------|--------|--------|--------|--------|
| 4441.9 | 0°    | 4441.9 | 4441.9 | 4441.9 | 4441.9 | 4441.9 | 4441.9 | 4441.9 | 4441.9 | 4441.9 | 4441.9 |
| 4664.5 | 2.5°  | 4625.7 | 4586.5 | 4547.3 | 4509.8 | 4472.3 | 4436.0 | 4395.6 | 4362.9 | 4330.3 | 4300.8 |
| 4893.8 | 5°    | 4813.2 | 4731.9 | 4650.7 | 4574.9 | 4499.0 | 4427.5 | 4356.7 | 4295.0 | 4233.1 | 4181.3 |
| 5107.4 | 7.5°  | 4984.0 | 4863.8 | 4743.6 | 4637.8 | 4531.9 | 4434.3 | 4342.7 | 4260.6 | 4178.6 | 4110.4 |
| 5273.9 | 10°   | 5111.0 | 4965.1 | 4819.0 | 4693.9 | 4568.4 | 4447.9 | 4349.6 | 4263.0 | 4176.4 | 4108.2 |
| 5388.6 | 12.5° | 5203.9 | 5031.7 | 4859.5 | 4717.9 | 4576.3 | 4449.6 | 4358.1 | 4287.2 | 4216.6 | 4171.3 |
| 5460.2 | 15°   | 5259.8 | 5061.5 | 4863.3 | 4699.3 | 4535.3 | 4395.1 | 4321.8 | 4287.9 | 4254.1 | 4260.2 |
| 5494.5 | 17.5° | 5275.8 | 5045.7 | 4815.6 | 4618.4 | 4421.1 | 4256.1 | 4211.0 | 4223.4 | 4235.7 | 4310.0 |
| 5521.2 | 20°   | 5280.9 | 5002.0 | 4723.2 | 4478.8 | 4234.3 | 4042.2 | 4030.3 | 4088.3 | 4146.2 | 4275.2 |
| 5557.4 | 22.5° | 5287.7 | 4948.5 | 4609.3 | 4315.0 | 4020.6 | 3801.9 | 3825.3 | 3911.0 | 3996.7 | 4144.0 |
| 5622.8 | 25°   | 5314.6 | 4895.7 | 4476.9 | 4132.1 | 3787.4 | 3563.3 | 3626.3 | 3725.2 | 3824.1 | 3956.5 |
| 5725.1 | 27.5° | 5370.9 | 4860.4 | 4349.9 | 3964.8 | 3579.8 | 3375.8 | 3452.5 | 3547.9 | 3643.4 | 3752.3 |
| 5857.5 | 30°   | 5447.9 | 4843.9 | 4239.4 | 3825.1 | 3410.7 | 3239.4 | 3299.6 | 3375.3 | 3451.3 | 3541.6 |
| 5995.8 | 32.5° | 5514.4 | 4823.4 | 4132.1 | 3704.6 | 3276.9 | 3138.8 | 3165.6 | 3210.4 | 3255.3 | 3327.4 |
| 6153.3 | 35°   | 5563.2 | 4784.9 | 4007.0 | 3586.1 | 3165.3 | 3050.2 | 3039.1 | 3051.4 | 3063.8 | 3118.9 |
| 6329.7 | 37.5° | 5592.1 | 4718.9 | 3845.7 | 3446.7 | 3047.7 | 2947.1 | 2906.5 | 2892.9 | 2879.3 | 2918.8 |
| 6553.7 | 40°   | 5610.4 | 4628.1 | 3645.9 | 3280.3 | 2914.7 | 2823.5 | 2761.3 | 2730.4 | 2699.6 | 2728.1 |
| 6846.7 | 42.5° | 5645.0 | 4534.3 | 3424.0 | 3096.7 | 2769.5 | 2685.4 | 2607.0 | 2566.1 | 2525.2 | 2548.4 |
| 7232.2 | 45°   | 5705.8 | 4447.2 | 3188.8 | 2901.7 | 2614.7 | 2529.5 | 2453.6 | 2413.7 | 2374.0 | 2393.5 |
| 7643.0 | 47.5° | 5747.6 | 4375.3 | 3003.0 | 2747.5 | 2492.0 | 2382.0 | 2316.8 | 2283.4 | 2249.9 | 2268.4 |
| 8024.1 | 50°   | 5720.3 | 4296.9 | 2873.5 | 2645.1 | 2416.6 | 2272.1 | 2196.3 | 2166.6 | 2137.1 | 2165.7 |
| 8271.6 | 52.5° | 5552.4 | 4164.4 | 2776.6 | 2577.6 | 2378.6 | 2212.4 | 2106.4 | 2077.1 | 2048.0 | 2091.1 |
| 8217.1 | 55°   | 5205.6 | 3944.9 | 2684.3 | 2528.6 | 2373.0 | 2218.4 | 2058.7 | 2012.3 | 1966.1 | 2027.3 |
| 7833.2 | 57.5° | 4689.9 | 3635.4 | 2580.6 | 2470.7 | 2360.7 | 2224.4 | 2030.1 | 1962.6 | 1895.1 | 1960.9 |
| 7118.9 | 60°   | 3998.4 | 3233.4 | 2468.5 | 2382.0 | 2295.6 | 2205.6 | 2003.1 | 1915.7 | 1828.1 | 1885.9 |
| 6152.9 | 62.5° | 3219.5 | 2752.4 | 2285.4 | 2228.0 | 2170.7 | 2159.6 | 1971.8 | 1862.3 | 1753.1 | 1789.7 |
| 5167.4 | 65°   | 2537.7 | 2319.7 | 2101.7 | 2074.6 | 2047.5 | 2048.8 | 1905.6 | 1789.4 | 1673.0 | 1687.1 |
| 4201.9 | 67.5° | 1965.6 | 1903.8 | 1841.7 | 1856.9 | 1871.9 | 1868.1 | 1787.7 | 1690.9 | 1594.1 | 1589.6 |
| 3308.4 | 70°   | 1488.9 | 1506.6 | 1524.2 | 1594.4 | 1664.4 | 1664.4 | 1638.0 | 1569.2 | 1500.3 | 1485.0 |
| 2529.3 | 72.5° | 1148.5 | 1201.8 | 1255.4 | 1354.9 | 1454.3 | 1471.0 | 1471.3 | 1424.1 | 1376.9 | 1354.4 |
| 1835.8 | 75°   | 891.8  | 940.2  | 988.6  | 1100.1 | 1211.6 | 1288.6 | 1282.1 | 1245.8 | 1209.3 | 1187.9 |
| 1243.9 | 77.5° | 686.6  | 719.5  | 752.5  | 860.8  | 969.0  | 1096.0 | 1092.6 | 1063.4 | 1034.3 | 1012.5 |
| 801.5  | 80°   | 514.8  | 528.4  | 542.0  | 633.7  | 725.3  | 877.0  | 876.5  | 852.1  | 827.5  | 809.3  |
| 492.9  | 82.5° | 367.8  | 370.2  | 372.9  | 440.4  | 507.9  | 637.5  | 644.6  | 632.7  | 620.8  | 607.8  |
| 263.5  | 85°   | 222.4  | 221.2  | 219.9  | 269.3  | 318.7  | 415.0  | 424.4  | 411.6  | 398.9  | 384.4  |
| 109.3  | 87.5° | 97.5   | 96.3   | 95.1   | 115.2  | 135.5  | 175.6  | 187.5  | 182.4  | 177.3  | 174.5  |
| 0.0    | 90°   | 0.0    | 0.0    | 0.0    | 0.0    | 0.0    | 0.0    | 0.0    | 0.0    | 0.0    | 0.0    |

REPORT NUMBER: P954374  
 CATALOG NUMBER: GLAN-SB7C-927-U-SLL

**CANDELA DISTRIBUTION (continued):**

| 160°   |       | 165°   | 170°   | 175°   | 180°   | 185°   | 190°   | 195°   | 200°   | 205°   | 210°   |
|--------|-------|--------|--------|--------|--------|--------|--------|--------|--------|--------|--------|
| 4441.9 | 0°    | 4441.9 | 4441.9 | 4441.9 | 4441.9 | 4441.9 | 4441.9 | 4441.9 | 4441.9 | 4441.9 | 4441.9 |
| 4271.5 | 2.5°  | 4245.8 | 4220.0 | 4194.1 | 4168.4 | 4148.4 | 4128.3 | 4112.1 | 4095.9 | 4083.3 | 4070.7 |
| 4129.7 | 5°    | 4084.0 | 4038.3 | 3996.9 | 3955.3 | 3923.4 | 3891.4 | 3869.1 | 3846.7 | 3830.9 | 3815.0 |
| 4042.2 | 7.5°  | 3984.8 | 3927.2 | 3876.4 | 3825.8 | 3787.8 | 3749.9 | 3723.3 | 3696.7 | 3678.5 | 3660.4 |
| 4040.0 | 10°   | 3978.1 | 3916.1 | 3859.0 | 3801.9 | 3756.6 | 3711.0 | 3681.4 | 3651.4 | 3634.2 | 3617.0 |
| 4126.3 | 12.5° | 4077.5 | 4029.1 | 3970.0 | 3911.0 | 3853.0 | 3795.1 | 3756.7 | 3718.4 | 3699.1 | 3680.0 |
| 4266.4 | 15°   | 4253.8 | 4241.1 | 4189.8 | 4138.5 | 4056.0 | 3973.5 | 3915.2 | 3857.0 | 3830.2 | 3803.6 |
| 4384.3 | 17.5° | 4423.9 | 4463.2 | 4421.8 | 4380.6 | 4271.3 | 4162.1 | 4076.2 | 3990.2 | 3950.7 | 3911.0 |
| 4404.4 | 20°   | 4487.1 | 4569.8 | 4550.7 | 4531.4 | 4406.5 | 4281.7 | 4176.4 | 4071.2 | 4020.6 | 3969.8 |
| 4291.6 | 22.5° | 4399.2 | 4506.7 | 4518.3 | 4529.7 | 4410.4 | 4291.1 | 4182.7 | 4074.1 | 4020.8 | 3967.2 |
| 4089.1 | 25°   | 4195.0 | 4300.8 | 4340.4 | 4379.7 | 4281.9 | 4184.2 | 4087.7 | 3991.6 | 3945.2 | 3899.1 |
| 3861.0 | 27.5° | 3945.9 | 4030.8 | 4074.8 | 4118.9 | 4049.2 | 3979.7 | 3904.9 | 3830.0 | 3799.0 | 3767.8 |
| 3632.0 | 30°   | 3702.4 | 3772.9 | 3808.7 | 3844.5 | 3791.5 | 3738.3 | 3684.8 | 3630.9 | 3615.1 | 3599.1 |
| 3399.6 | 32.5° | 3467.1 | 3534.8 | 3574.5 | 3614.4 | 3565.7 | 3516.7 | 3474.0 | 3431.2 | 3420.8 | 3410.4 |
| 3173.8 | 35°   | 3240.6 | 3307.6 | 3355.3 | 3403.0 | 3368.3 | 3333.7 | 3294.1 | 3254.8 | 3238.9 | 3223.2 |
| 2958.2 | 37.5° | 3024.8 | 3091.6 | 3150.6 | 3209.6 | 3193.6 | 3177.5 | 3141.2 | 3104.8 | 3076.0 | 3047.3 |
| 2756.5 | 40°   | 2821.0 | 2885.4 | 2953.2 | 3021.2 | 3025.2 | 3028.9 | 2998.1 | 2967.2 | 2925.3 | 2883.7 |
| 2571.8 | 42.5° | 2632.8 | 2694.0 | 2767.3 | 2840.6 | 2860.2 | 2879.8 | 2853.7 | 2827.8 | 2775.8 | 2723.8 |
| 2413.2 | 45°   | 2471.2 | 2529.1 | 2605.2 | 2681.2 | 2709.3 | 2737.4 | 2713.9 | 2690.6 | 2631.1 | 2571.8 |
| 2286.6 | 47.5° | 2343.4 | 2399.9 | 2474.9 | 2549.9 | 2582.3 | 2614.7 | 2598.3 | 2582.0 | 2529.1 | 2476.3 |
| 2194.6 | 50°   | 2248.1 | 2301.4 | 2368.6 | 2435.7 | 2477.3 | 2518.9 | 2517.9 | 2517.2 | 2474.9 | 2432.7 |
| 2134.0 | 52.5° | 2183.1 | 2232.0 | 2294.6 | 2357.3 | 2406.6 | 2455.9 | 2464.7 | 2473.6 | 2439.1 | 2404.7 |
| 2088.4 | 55°   | 2141.2 | 2194.0 | 2248.9 | 2303.6 | 2355.8 | 2408.1 | 2420.4 | 2432.7 | 2402.7 | 2372.7 |
| 2026.7 | 57.5° | 2088.7 | 2150.7 | 2204.9 | 2259.3 | 2312.0 | 2364.5 | 2376.9 | 2389.4 | 2359.0 | 2328.7 |
| 1943.5 | 60°   | 2014.7 | 2086.0 | 2141.0 | 2196.3 | 2249.1 | 2301.9 | 2315.6 | 2329.2 | 2299.5 | 2270.1 |
| 1826.4 | 62.5° | 1909.4 | 1992.6 | 2051.4 | 2110.2 | 2158.6 | 2207.0 | 2220.1 | 2233.2 | 2206.5 | 2179.7 |
| 1701.1 | 65°   | 1790.1 | 1879.2 | 1935.5 | 1991.7 | 2034.3 | 2076.9 | 2090.4 | 2103.7 | 2078.0 | 2052.2 |
| 1585.2 | 67.5° | 1667.3 | 1749.7 | 1803.0 | 1856.2 | 1893.0 | 1929.8 | 1943.0 | 1955.9 | 1932.2 | 1908.7 |
| 1469.6 | 70°   | 1541.9 | 1614.2 | 1660.2 | 1706.2 | 1739.4 | 1772.7 | 1785.3 | 1797.9 | 1778.7 | 1759.4 |
| 1332.1 | 72.5° | 1389.0 | 1445.8 | 1487.4 | 1528.9 | 1561.5 | 1594.1 | 1609.1 | 1624.1 | 1608.0 | 1592.0 |
| 1166.2 | 75°   | 1208.5 | 1250.8 | 1288.4 | 1326.1 | 1355.8 | 1385.4 | 1401.1 | 1416.8 | 1408.9 | 1401.1 |
| 990.7  | 77.5° | 1025.1 | 1059.4 | 1091.7 | 1124.1 | 1155.3 | 1186.3 | 1201.0 | 1215.7 | 1204.7 | 1193.5 |
| 790.9  | 80°   | 819.5  | 848.0  | 875.3  | 902.5  | 926.2  | 949.8  | 969.2  | 988.6  | 983.8  | 979.2  |
| 594.9  | 82.5° | 592.5  | 590.1  | 580.6  | 571.0  | 621.5  | 671.9  | 705.0  | 738.1  | 736.0  | 733.8  |
| 369.9  | 85°   | 357.6  | 345.2  | 318.7  | 292.3  | 339.5  | 386.9  | 427.8  | 468.7  | 465.3  | 461.9  |
| 171.8  | 87.5° | 171.3  | 170.8  | 150.7  | 130.4  | 150.2  | 170.1  | 186.6  | 203.2  | 199.1  | 194.7  |
| 0.0    | 90°   | 0.0    | 0.0    | 0.0    | 0.0    | 0.0    | 0.0    | 0.0    | 0.0    | 0.0    | 0.0    |

REPORT NUMBER: P954374  
 CATALOG NUMBER: GLAN-SB7C-927-U-SLL

**CANDELA DISTRIBUTION (continued):**

| 215°   |       | 220°   | 225°   | 230°   | 235°   | 240°   | 245°   | 250°   | 255°   | 260°   | 265°   |
|--------|-------|--------|--------|--------|--------|--------|--------|--------|--------|--------|--------|
| 4441.9 | 0°    | 4441.9 | 4441.9 | 4441.9 | 4441.9 | 4441.9 | 4441.9 | 4441.9 | 4441.9 | 4441.9 | 4441.9 |
| 4059.1 | 2.5°  | 4047.3 | 4032.9 | 4047.3 | 4059.1 | 4070.7 | 4083.3 | 4095.9 | 4112.1 | 4128.3 | 4148.4 |
| 3802.9 | 5°    | 3790.8 | 3778.9 | 3790.8 | 3802.9 | 3815.0 | 3830.9 | 3846.7 | 3869.1 | 3891.4 | 3923.4 |
| 3649.5 | 7.5°  | 3638.8 | 3630.6 | 3638.8 | 3649.5 | 3660.4 | 3678.5 | 3696.7 | 3723.3 | 3749.9 | 3787.8 |
| 3607.8 | 10°   | 3598.6 | 3594.8 | 3598.6 | 3607.8 | 3617.0 | 3634.2 | 3651.4 | 3681.4 | 3711.0 | 3756.6 |
| 3672.2 | 12.5° | 3664.3 | 3663.0 | 3664.3 | 3672.2 | 3680.0 | 3699.1 | 3718.4 | 3756.7 | 3795.1 | 3853.0 |
| 3793.4 | 15°   | 3783.1 | 3782.3 | 3783.1 | 3793.4 | 3803.6 | 3830.2 | 3857.0 | 3915.2 | 3973.5 | 4056.0 |
| 3898.0 | 17.5° | 3884.9 | 3882.9 | 3884.9 | 3898.0 | 3911.0 | 3950.7 | 3990.2 | 4076.2 | 4162.1 | 4271.3 |
| 3953.6 | 20°   | 3937.4 | 3932.3 | 3937.4 | 3953.6 | 3969.8 | 4020.6 | 4071.2 | 4176.4 | 4281.7 | 4406.5 |
| 3949.3 | 22.5° | 3931.4 | 3923.8 | 3931.4 | 3949.3 | 3967.2 | 4020.8 | 4074.1 | 4182.7 | 4291.1 | 4410.4 |
| 3882.2 | 25°   | 3865.5 | 3855.6 | 3865.5 | 3882.2 | 3899.1 | 3945.2 | 3991.6 | 4087.7 | 4184.2 | 4281.9 |
| 3760.1 | 27.5° | 3752.5 | 3749.9 | 3752.5 | 3760.1 | 3767.8 | 3799.0 | 3830.0 | 3904.9 | 3979.7 | 4049.2 |
| 3599.1 | 30°   | 3599.1 | 3601.6 | 3599.1 | 3599.1 | 3599.1 | 3615.1 | 3630.9 | 3684.8 | 3738.3 | 3791.5 |
| 3411.7 | 32.5° | 3413.3 | 3415.8 | 3413.3 | 3411.7 | 3410.4 | 3420.8 | 3431.2 | 3474.0 | 3516.7 | 3565.7 |
| 3219.8 | 35°   | 3216.4 | 3214.7 | 3216.4 | 3219.8 | 3223.2 | 3238.9 | 3254.8 | 3294.1 | 3333.7 | 3368.3 |
| 3032.1 | 37.5° | 3017.0 | 3008.5 | 3017.0 | 3032.1 | 3047.3 | 3076.0 | 3104.8 | 3141.2 | 3177.5 | 3193.6 |
| 2855.4 | 40°   | 2827.4 | 2810.7 | 2827.4 | 2855.4 | 2883.7 | 2925.3 | 2967.2 | 2998.1 | 3028.9 | 3025.2 |
| 2682.7 | 42.5° | 2641.6 | 2614.7 | 2641.6 | 2682.7 | 2723.8 | 2775.8 | 2827.8 | 2853.7 | 2879.8 | 2860.2 |
| 2523.5 | 45°   | 2475.3 | 2444.3 | 2475.3 | 2523.5 | 2571.8 | 2631.1 | 2690.6 | 2713.9 | 2737.4 | 2709.3 |
| 2431.6 | 47.5° | 2387.2 | 2357.3 | 2387.2 | 2431.6 | 2476.3 | 2529.1 | 2582.0 | 2598.3 | 2614.7 | 2582.3 |
| 2391.4 | 50°   | 2350.2 | 2321.5 | 2350.2 | 2391.4 | 2432.7 | 2474.9 | 2517.2 | 2517.9 | 2518.9 | 2477.3 |
| 2367.7 | 52.5° | 2330.9 | 2304.5 | 2330.9 | 2367.7 | 2404.7 | 2439.1 | 2473.6 | 2464.7 | 2455.9 | 2406.6 |
| 2340.3 | 55°   | 2307.9 | 2284.0 | 2307.9 | 2340.3 | 2372.7 | 2402.7 | 2432.7 | 2420.4 | 2408.1 | 2355.8 |
| 2296.7 | 57.5° | 2264.4 | 2239.7 | 2264.4 | 2296.7 | 2328.7 | 2359.0 | 2389.4 | 2376.9 | 2364.5 | 2312.0 |
| 2237.0 | 60°   | 2203.9 | 2178.4 | 2203.9 | 2237.0 | 2270.1 | 2299.5 | 2329.2 | 2315.6 | 2301.9 | 2249.1 |
| 2144.9 | 62.5° | 2110.2 | 2079.5 | 2110.2 | 2144.9 | 2179.7 | 2206.5 | 2233.2 | 2220.1 | 2207.0 | 2158.6 |
| 2018.5 | 65°   | 1984.9 | 1958.5 | 1984.9 | 2018.5 | 2052.2 | 2078.0 | 2103.7 | 2090.4 | 2076.9 | 2034.3 |
| 1877.3 | 67.5° | 1846.0 | 1822.1 | 1846.0 | 1877.3 | 1908.7 | 1932.2 | 1955.9 | 1943.0 | 1929.8 | 1893.0 |
| 1729.4 | 70°   | 1699.4 | 1672.1 | 1699.4 | 1729.4 | 1759.4 | 1778.7 | 1797.9 | 1785.3 | 1772.7 | 1739.4 |
| 1563.4 | 72.5° | 1534.9 | 1508.5 | 1534.9 | 1563.4 | 1592.0 | 1608.0 | 1624.1 | 1609.1 | 1594.1 | 1561.5 |
| 1377.1 | 75°   | 1353.0 | 1327.8 | 1353.0 | 1377.1 | 1401.1 | 1408.9 | 1416.8 | 1401.1 | 1385.4 | 1355.8 |
| 1169.3 | 77.5° | 1145.1 | 1125.0 | 1145.1 | 1169.3 | 1193.5 | 1204.7 | 1215.7 | 1201.0 | 1186.3 | 1155.3 |
| 946.7  | 80°   | 914.0  | 876.1  | 914.0  | 946.7  | 979.2  | 983.8  | 988.6  | 969.2  | 949.8  | 926.2  |
| 706.3  | 82.5° | 678.7  | 654.5  | 678.7  | 706.3  | 733.8  | 736.0  | 738.1  | 705.0  | 671.9  | 621.5  |
| 440.4  | 85°   | 419.0  | 397.1  | 419.0  | 440.4  | 461.9  | 465.3  | 468.7  | 427.8  | 386.9  | 339.5  |
| 183.7  | 87.5° | 172.5  | 161.9  | 172.5  | 183.7  | 194.7  | 199.1  | 203.2  | 186.6  | 170.1  | 150.2  |
| 0.0    | 90°   | 0.0    | 0.0    | 0.0    | 0.0    | 0.0    | 0.0    | 0.0    | 0.0    | 0.0    | 0.0    |

REPORT NUMBER: P954374  
 CATALOG NUMBER: GLAN-SB7C-927-U-SLL

**CANDELA DISTRIBUTION (continued):**

| 270°   |       | 275°   | 280°   | 285°   | 290°   | 295°   | 300°   | 305°   | 310°   | 315°   | 320°   |
|--------|-------|--------|--------|--------|--------|--------|--------|--------|--------|--------|--------|
| 4441.9 | 0°    | 4441.9 | 4441.9 | 4441.9 | 4441.9 | 4441.9 | 4441.9 | 4441.9 | 4441.9 | 4441.9 | 4441.9 |
| 4168.4 | 2.5°  | 4194.1 | 4220.0 | 4245.8 | 4271.5 | 4300.8 | 4330.3 | 4362.9 | 4395.6 | 4436.0 | 4472.3 |
| 3955.3 | 5°    | 3996.9 | 4038.3 | 4084.0 | 4129.7 | 4181.3 | 4233.1 | 4295.0 | 4356.7 | 4427.5 | 4499.0 |
| 3825.8 | 7.5°  | 3876.4 | 3927.2 | 3984.8 | 4042.2 | 4110.4 | 4178.6 | 4260.6 | 4342.7 | 4434.3 | 4531.9 |
| 3801.9 | 10°   | 3859.0 | 3916.1 | 3978.1 | 4040.0 | 4108.2 | 4176.4 | 4263.0 | 4349.6 | 4447.9 | 4568.4 |
| 3911.0 | 12.5° | 3970.0 | 4029.1 | 4077.5 | 4126.3 | 4171.3 | 4216.6 | 4287.2 | 4358.1 | 4449.6 | 4576.3 |
| 4138.5 | 15°   | 4189.8 | 4241.1 | 4253.8 | 4266.4 | 4260.2 | 4254.1 | 4287.9 | 4321.8 | 4395.1 | 4535.3 |
| 4380.6 | 17.5° | 4421.8 | 4463.2 | 4423.9 | 4384.3 | 4310.0 | 4235.7 | 4223.4 | 4211.0 | 4256.1 | 4421.1 |
| 4531.4 | 20°   | 4550.7 | 4569.8 | 4487.1 | 4404.4 | 4275.2 | 4146.2 | 4088.3 | 4030.3 | 4042.2 | 4234.3 |
| 4529.7 | 22.5° | 4518.3 | 4506.7 | 4399.2 | 4291.6 | 4144.0 | 3996.7 | 3911.0 | 3825.3 | 3801.9 | 4020.6 |
| 4379.7 | 25°   | 4340.4 | 4300.8 | 4195.0 | 4089.1 | 3956.5 | 3824.1 | 3725.2 | 3626.3 | 3563.3 | 3787.4 |
| 4118.9 | 27.5° | 4074.8 | 4030.8 | 3945.9 | 3861.0 | 3752.3 | 3643.4 | 3547.9 | 3452.5 | 3375.8 | 3579.8 |
| 3844.5 | 30°   | 3808.7 | 3772.9 | 3702.4 | 3632.0 | 3541.6 | 3451.3 | 3375.3 | 3299.6 | 3239.4 | 3410.7 |
| 3614.4 | 32.5° | 3574.5 | 3534.8 | 3467.1 | 3399.6 | 3327.4 | 3255.3 | 3210.4 | 3165.6 | 3138.8 | 3276.9 |
| 3403.0 | 35°   | 3355.3 | 3307.6 | 3240.6 | 3173.8 | 3118.9 | 3063.8 | 3051.4 | 3039.1 | 3050.2 | 3165.3 |
| 3209.6 | 37.5° | 3150.6 | 3091.6 | 3024.8 | 2958.2 | 2918.8 | 2879.3 | 2892.9 | 2906.5 | 2947.1 | 3047.7 |
| 3021.2 | 40°   | 2953.2 | 2885.4 | 2821.0 | 2756.5 | 2728.1 | 2699.6 | 2730.4 | 2761.3 | 2823.5 | 2914.7 |
| 2840.6 | 42.5° | 2767.3 | 2694.0 | 2632.8 | 2571.8 | 2548.4 | 2525.2 | 2566.1 | 2607.0 | 2685.4 | 2769.5 |
| 2681.2 | 45°   | 2605.2 | 2529.1 | 2471.2 | 2413.2 | 2393.5 | 2374.0 | 2413.7 | 2453.6 | 2529.5 | 2614.7 |
| 2549.9 | 47.5° | 2474.9 | 2399.9 | 2343.4 | 2286.6 | 2268.4 | 2249.9 | 2283.4 | 2316.8 | 2382.0 | 2492.0 |
| 2435.7 | 50°   | 2368.6 | 2301.4 | 2248.1 | 2194.6 | 2165.7 | 2137.1 | 2166.6 | 2196.3 | 2272.1 | 2416.6 |
| 2357.3 | 52.5° | 2294.6 | 2232.0 | 2183.1 | 2134.0 | 2091.1 | 2048.0 | 2077.1 | 2106.4 | 2212.4 | 2378.6 |
| 2303.6 | 55°   | 2248.9 | 2194.0 | 2141.2 | 2088.4 | 2027.3 | 1966.1 | 2012.3 | 2058.7 | 2218.4 | 2373.0 |
| 2259.3 | 57.5° | 2204.9 | 2150.7 | 2088.7 | 2026.7 | 1960.9 | 1895.1 | 1962.6 | 2030.1 | 2224.4 | 2360.7 |
| 2196.3 | 60°   | 2141.0 | 2086.0 | 2014.7 | 1943.5 | 1885.9 | 1828.1 | 1915.7 | 2003.1 | 2205.6 | 2295.6 |
| 2110.2 | 62.5° | 2051.4 | 1992.6 | 1909.4 | 1826.4 | 1789.7 | 1753.1 | 1862.3 | 1971.8 | 2159.6 | 2170.7 |
| 1991.7 | 65°   | 1935.5 | 1879.2 | 1790.1 | 1701.1 | 1687.1 | 1673.0 | 1789.4 | 1905.6 | 2048.8 | 2047.5 |
| 1856.2 | 67.5° | 1803.0 | 1749.7 | 1667.3 | 1585.2 | 1589.6 | 1594.1 | 1690.9 | 1787.7 | 1868.1 | 1871.9 |
| 1706.2 | 70°   | 1660.2 | 1614.2 | 1541.9 | 1469.6 | 1485.0 | 1500.3 | 1569.2 | 1638.0 | 1664.4 | 1664.4 |
| 1528.9 | 72.5° | 1487.4 | 1445.8 | 1389.0 | 1332.1 | 1354.4 | 1376.9 | 1424.1 | 1471.3 | 1471.0 | 1454.3 |
| 1326.1 | 75°   | 1288.4 | 1250.8 | 1208.5 | 1166.2 | 1187.9 | 1209.3 | 1245.8 | 1282.1 | 1288.6 | 1211.6 |
| 1124.1 | 77.5° | 1091.7 | 1059.4 | 1025.1 | 990.7  | 1012.5 | 1034.3 | 1063.4 | 1092.6 | 1096.0 | 969.0  |
| 902.5  | 80°   | 875.3  | 848.0  | 819.5  | 790.9  | 809.3  | 827.5  | 852.1  | 876.5  | 877.0  | 725.3  |
| 571.0  | 82.5° | 580.6  | 590.1  | 592.5  | 594.9  | 607.8  | 620.8  | 632.7  | 644.6  | 637.5  | 507.9  |
| 292.3  | 85°   | 318.7  | 345.2  | 357.6  | 369.9  | 384.4  | 398.9  | 411.6  | 424.4  | 415.0  | 318.7  |
| 130.4  | 87.5° | 150.7  | 170.8  | 171.3  | 171.8  | 174.5  | 177.3  | 182.4  | 187.5  | 175.6  | 135.5  |
| 0.0    | 90°   | 0.0    | 0.0    | 0.0    | 0.0    | 0.0    | 0.0    | 0.0    | 0.0    | 0.0    | 0.0    |

REPORT NUMBER: P954374  
 CATALOG NUMBER: GLAN-SB7C-927-U-SLL

**CANDELA DISTRIBUTION (continued):**

| 325°   |       | 330°   | 335°   | 340°   | 345°   | 350°    | 355°    | 360°    |
|--------|-------|--------|--------|--------|--------|---------|---------|---------|
| 4441.9 | 0°    | 4441.9 | 4441.9 | 4441.9 | 4441.9 | 4441.9  | 4441.9  | 4441.9  |
| 4509.8 | 2.5°  | 4547.3 | 4586.5 | 4625.7 | 4664.5 | 4703.6  | 4740.2  | 4776.9  |
| 4574.9 | 5°    | 4650.7 | 4731.9 | 4813.2 | 4893.8 | 4974.6  | 5055.6  | 5136.5  |
| 4637.8 | 7.5°  | 4743.6 | 4863.8 | 4984.0 | 5107.4 | 5230.8  | 5364.2  | 5497.9  |
| 4693.9 | 10°   | 4819.0 | 4965.1 | 5111.0 | 5273.9 | 5437.0  | 5605.9  | 5774.9  |
| 4717.9 | 12.5° | 4859.5 | 5031.7 | 5203.9 | 5388.6 | 5573.4  | 5758.8  | 5944.5  |
| 4699.3 | 15°   | 4863.3 | 5061.5 | 5259.8 | 5460.2 | 5660.7  | 5854.1  | 6047.6  |
| 4618.4 | 17.5° | 4815.6 | 5045.7 | 5275.8 | 5494.5 | 5713.2  | 5909.3  | 6105.5  |
| 4478.8 | 20°   | 4723.2 | 5002.0 | 5280.9 | 5521.2 | 5761.6  | 5965.6  | 6169.5  |
| 4315.0 | 22.5° | 4609.3 | 4948.5 | 5287.7 | 5557.4 | 5826.9  | 6035.3  | 6243.6  |
| 4132.1 | 25°   | 4476.9 | 4895.7 | 5314.6 | 5622.8 | 5930.8  | 6134.9  | 6339.1  |
| 3964.8 | 27.5° | 4349.9 | 4860.4 | 5370.9 | 5725.1 | 6079.1  | 6273.9  | 6468.6  |
| 3825.1 | 30°   | 4239.4 | 4843.9 | 5447.9 | 5857.5 | 6267.1  | 6455.1  | 6643.3  |
| 3704.6 | 32.5° | 4132.1 | 4823.4 | 5514.4 | 5995.8 | 6477.1  | 6663.3  | 6849.6  |
| 3586.1 | 35°   | 4007.0 | 4784.9 | 5563.2 | 6153.3 | 6743.4  | 6921.8  | 7100.1  |
| 3446.7 | 37.5° | 3845.7 | 4718.9 | 5592.1 | 6329.7 | 7067.2  | 7294.6  | 7522.0  |
| 3280.3 | 40°   | 3645.9 | 4628.1 | 5610.4 | 6553.7 | 7496.8  | 7828.1  | 8159.5  |
| 3096.7 | 42.5° | 3424.0 | 4534.3 | 5645.0 | 6846.7 | 8048.3  | 8526.6  | 9004.9  |
| 2901.7 | 45°   | 3188.8 | 4447.2 | 5705.8 | 7232.2 | 8758.6  | 9403.8  | 10048.9 |
| 2747.5 | 47.5° | 3003.0 | 4375.3 | 5747.6 | 7643.0 | 9538.4  | 10446.6 | 11354.6 |
| 2645.1 | 50°   | 2873.5 | 4296.9 | 5720.3 | 8024.1 | 10327.9 | 11697.0 | 13065.9 |
| 2577.6 | 52.5° | 2776.6 | 4164.4 | 5552.4 | 8271.6 | 10990.6 | 13010.5 | 15030.3 |
| 2528.6 | 55°   | 2684.3 | 3944.9 | 5205.6 | 8217.1 | 11228.4 | 14175.0 | 17121.8 |
| 2470.7 | 57.5° | 2580.6 | 3635.4 | 4689.9 | 7833.2 | 10976.7 | 15000.3 | 19024.0 |
| 2382.0 | 60°   | 2468.5 | 3233.4 | 3998.4 | 7118.9 | 10239.3 | 15206.6 | 20173.7 |
| 2228.0 | 62.5° | 2285.4 | 2752.4 | 3219.5 | 6152.9 | 9086.4  | 14338.1 | 19589.9 |
| 2074.6 | 65°   | 2101.7 | 2319.7 | 2537.7 | 5167.4 | 7797.3  | 13109.3 | 18421.4 |
| 1856.9 | 67.5° | 1841.7 | 1903.8 | 1965.6 | 4201.9 | 6438.3  | 11647.1 | 16855.9 |
| 1594.4 | 70°   | 1524.2 | 1506.6 | 1488.9 | 3308.4 | 5128.0  | 10051.5 | 14974.9 |
| 1354.9 | 72.5° | 1255.4 | 1201.8 | 1148.5 | 2529.3 | 3910.1  | 8321.7  | 12733.5 |
| 1100.1 | 75°   | 988.6  | 940.2  | 891.8  | 1835.8 | 2779.7  | 6338.9  | 9898.1  |
| 860.8  | 77.5° | 752.5  | 719.5  | 686.6  | 1243.9 | 1801.3  | 4436.7  | 7072.0  |
| 633.7  | 80°   | 542.0  | 528.4  | 514.8  | 801.5  | 1088.3  | 2858.5  | 4628.6  |
| 440.4  | 82.5° | 372.9  | 370.2  | 367.8  | 492.9  | 618.4   | 1654.4  | 2690.6  |
| 269.3  | 85°   | 219.9  | 221.2  | 222.4  | 263.5  | 304.8   | 744.2   | 1183.8  |
| 115.2  | 87.5° | 95.1   | 96.3   | 97.5   | 109.3  | 121.0   | 243.7   | 366.5   |
| 0.0    | 90°   | 0.0    | 0.0    | 0.0    | 0.0    | 0.0     | 0.0     | 0.0     |

(END OF REPORT)