

LM-79-08 Approved Method: Electrical and Photometric Measurements of Solid-State  
Lighting Products

Test Report Prepared for  
Cooper Lighting Solutions  
(formerly Eaton)

Brand: STREETWORKS

Report Number: P599564

Luminaire Tested: **IFLD-L-SA7A-760-U-SLL-HSS**

Issue Date: 05/04/2022

Tested By:

Approved By:



Cooper Lighting Solutions laboratories have been accredited by National Voluntary Laboratory Accreditation Program (NVLAP) that it adheres to the requirements of ISO/IEC 17025:2005 and appropriate IESNA test methods. This report must not be used to claim product certification, approval or endorsement by NVLAP, NIST or any agency of the Federal Government. Results contained in this report are valid for luminaire sample tested, as supplied by requestor. Information related to the luminaire tested has been supplied by requestor and can affect the validity of the test results. Report shall not be reproduced except in full without approval of Cooper Lighting Solutions Lighting Laboratory. Test performed at address noted above.

**Test Information**

Test Method: LM-79-08  
 Report Number: P599564  
 Test Lab: INNOVATION CENTER(G1)  
 Issue Date: 05/04/2022  
 Manufacturer: COOPER LIGHTING SOLUTIONS (FORMERLY EATON)  
 Product Line: STREETWORKS  
 Catalog Number: IFLD-L-SA7A-760-U-SLL-HSS  
 Description: Infrastructure Flood – Middle Tier Light Square Luminaire w/ SLL distribution lens with House Side Shield  
 Light Source: (112) 5700K CCT, 70 CRI LEDS  
 Ballast/Driver: ELECTRONIC DRIVER

**Summary**


Lumens per Lamp: N/A  
 Luminaire Lumens: 23319.5 lumens  
 Efficiency: N/A  
 Efficacy: 107.2 lumens/watt  
 Spacing Criteria (0/90/45): 0.53 / 0.46 / 0.63  
 Luminous Opening: Rectangular (W 2' x L: 1' x H: 0')  
 CIE Type: Direct

Input Watts (W): 217.6  
 Input Voltage (V): 120  
 Input Current (Ain): NR  
 Voltage Rise (V): NR  
 Power Factor: NR  
 Total Harmonic Distortion (THDi): NR  
 Frequency (hertz): 60  
 Stabilization Time: NR  
 Operation Time: NR  
 Ambient Temperature (°C): NR  
 Test Distance: 25 FT

Measurement and Test Equipment			
Instrument	Identification Number	Calibration Date	Calibration Due Date
Photometer	GONIO 1 IN0055	4/22/2021	10/22/2021
Power Meter	XITRON 2801 IN0197	12/1/2020	12/1/2021
AC Power Source	CHROMA 61505 IN0196	12/1/2020	12/1/2021
DC Power Supply	AGILENT E3634A IN0198	11/30/2020	11/30/2021
Room Thermometer	ONSET IN0143	12/1/2020	12/1/2021

TEST NUMBER: P599564  
CATALOG NUMBER: IFLD-L-SA7A-760-U-SLL-HSS

### Luminous Intensity Polar Plot



— 0°-180°    - - 45°-225°    ··· 90°-270°    - · 135°-315°

TEST NUMBER: P599564  
 CATALOG NUMBER: IFLD-L-SA7A-760-U-SLL-HSS

**COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:**

RF	20					20					20					20					20	
RC	80					70					50					30					10	0
RW	70	50	30	10	70	50	30	10	50	30	10	50	30	10	50	30	10	50	30	10	0	
RCR																						
0	119	119	119	119	116	116	116	116	111	111	111	106	106	106	102	102	102	100			100	
1	106	100	95	90	103	98	93	89	94	90	86	90	86	83	86	83	81	79			79	
2	94	84	76	69	91	82	75	68	78	72	66	75	70	65	72	67	63	61			61	
3	84	72	62	54	81	70	61	53	67	59	52	64	57	51	61	55	50	48			48	
4	76	62	51	44	73	60	51	43	58	49	43	55	48	42	53	46	41	39			39	
5	69	54	44	36	67	53	43	36	51	42	35	48	41	35	46	40	34	32			32	
6	63	48	38	30	61	47	37	30	45	36	30	43	35	30	41	35	29	27			27	
7	58	43	33	26	56	42	33	26	40	32	26	39	31	26	37	31	25	23			23	
8	54	39	29	23	52	38	29	23	37	28	23	35	28	22	34	27	22	20			20	
9	50	35	26	20	49	35	26	20	34	26	20	32	25	20	31	25	20	18			18	
10	47	33	24	18	46	32	24	18	31	23	18	30	23	18	29	23	18	16			16	

**AVERAGE LUMINANCE (cd/sqm):**

	0°	90°	180°	270°
0°	47189	47189	47189	47189
5°	49590	47201	34484	34686
10°	42642	41008	18854	18411
15°	41463	39416	12248	9229
20°	47792	45795	6562	3281
25°	60092	56209	4252	2552
30°	72175	67259	3444	2090
35°	85469	80191	2823	1677
40°	103120	97082	2494	1269
45°	117403	112283	2322	853
50°	131705	126595	2294	522
55°	148941	148415	2279	234
60°	183795	188152	2077	67
65°	205076	226171	1904	0
70°	209111	255266	1764	0
75°	170151	188280	1684	0
80°	123717	78745	1736	0
85°	79986	33068	2309	0

TEST NUMBER: P599564  
 CATALOG NUMBER: IFLD-L-SA7A-760-U-SLL-HSS

**ZONAL LUMENS:**

Zone	Lumens	% Fixture
0°-10°	666.1	2.9
10°-20°	1306.2	5.6
20°-30°	1807.6	7.8
30°-40°	2554.5	11.0
40°-50°	3478.0	14.9
50°-60°	4606.4	19.8
60°-70°	5348.4	22.9
70°-80°	3028.8	13.0
80°-90°	523.3	2.2
90°-100°	0.0	0.0
100°-110°	0.0	0.0
110°-120°	0.0	0.0
120°-130°	0.0	0.0
130°-140°	0.0	0.0
140°-150°	0.0	0.0
150°-160°	0.0	0.0
160°-170°	0.0	0.0
170°-180°	0.0	0.0
0°-30°	3779.8	16.2
0°-40°	6334.4	27.2
0°-60°	14418.9	61.8
0°-90°	23319.5	100.0
90°-120°	0.0	0.0
90°-150°	0.0	0.0
90°-180°	0.0	0.0
0°-180°	23319.5	100.0

**CANDELA DISTRIBUTION:**

	0°	90°	180°	270°	360°	Flux
0°	8768	8768	8768	8768	8768	
5°	9179	8737	6383	6420	9179	824
15°	7442	7074	2198	1656	7442	2183
25°	10119	9465	716	430	10119	4720
35°	13009	12205	430	255	13009	8201
45°	15425	14752	305	112	15425	11959
55°	15873	15817	243	25	15873	14381
65°	16104	17760	150	0	16104	15698
75°	8183	9054	81	0	8183	8930
85°	1295	536	37	0	1295	1556
90°	0	0	0	0	0	

TEST NUMBER: P599564  
 CATALOG NUMBER: IFLD-L-SA7A-760-U-SLL-HSS

**CANDELA DISTRIBUTION (FULL):**

	0°	2°	5°	15°	25°	35°	45°	55°	65°	75°	85°
0°	8768.0	8768.0	8768.0	8768.0	8768.0	8768.0	8768.0	8768.0	8768.0	8768.0	8768.0
2.5°	9110.5	9303.5	9309.7	9396.9	9484.1	9484.1	9689.6	9639.8	9459.2	9428.0	9297.3
5°	9179.0	9247.5	9297.3	9739.4	10113.0	10075.7	10187.8	10113.0	9764.3	9316.0	9010.8
7.5°	8587.4	8662.1	8861.4	9614.9	10119.3	10287.4	10499.1	10032.1	9664.7	8855.1	8269.8
10°	7802.7	7946.0	8313.4	9172.7	9795.5	10331.0	10331.0	9957.4	9247.5	8456.6	7740.5
12.5°	7366.8	7653.3	7852.6	8724.4	9533.9	9901.3	9888.9	9689.6	9228.8	8232.4	7422.9
15°	7441.6	7522.5	7946.0	8624.7	9160.3	9141.6	9365.8	9303.5	8979.7	8431.7	7541.2
17.5°	7784.1	7908.6	8276.0	8624.7	8880.0	8805.3	8799.1	9098.0	9116.7	8768.0	7983.3
20°	8344.5	8711.9	8886.3	8992.1	8680.8	8363.2	8325.8	8743.0	9066.9	9197.6	8512.6
22.5°	9241.2	9484.1	9839.0	9297.3	8487.7	8089.2	8014.5	8475.3	9129.1	9708.3	9197.6
25°	10119.3	10306.1	10648.6	9951.1	8705.7	8033.1	7902.4	8300.9	9365.8	10418.2	10025.9
27.5°	11047.1	11209.0	11246.4	10430.6	8824.0	7921.1	7765.4	8300.9	9565.0	10791.8	11016.0
30°	11613.8	11806.9	11844.2	10854.1	9017.0	8014.5	7939.7	8338.3	9702.0	11109.4	11725.9
32.5°	12249.0	12298.8	12267.7	10928.8	9228.8	8288.5	7977.1	8587.4	9857.7	11489.3	12373.5
35°	13008.7	13095.9	12778.3	11271.3	9702.0	8462.8	8350.7	8892.5	10125.5	11663.6	13158.2
37.5°	13587.8	13861.8	13145.7	11402.1	9795.5	8830.2	8848.9	9527.7	10312.3	11875.4	14023.7
40°	14677.6	14216.8	13768.4	11850.4	10150.4	9453.0	9353.3	10181.5	10941.3	12012.3	14590.4
42.5°	15275.4	15032.6	14011.3	11894.0	10698.4	10312.3	10337.2	10922.6	11271.3	12398.4	14746.1
45°	15424.9	15169.6	14341.3	11925.2	11240.2	11327.4	11757.0	11869.1	11757.0	12653.8	15038.8
47.5°	15804.7	15250.5	14304.0	12342.4	12118.2	12454.5	13002.5	13245.3	12417.1	12560.3	15175.8
50°	15730.0	15412.4	14223.0	12516.8	13189.3	14079.8	14447.2	14347.6	13151.9	12367.3	15026.3
52.5°	15418.7	15076.2	14472.1	12990.0	14191.9	15269.2	15779.8	15530.7	13805.8	12803.2	14926.7
55°	15873.2	15611.7	14795.9	13631.4	14945.4	16315.4	16676.6	16489.7	14609.1	13208.0	15493.4
57.5°	16365.2	16309.1	15674.0	14384.9	15835.9	17392.7	17392.7	17162.3	15306.6	13793.3	16334.1
60°	17075.1	17199.6	16321.6	14883.1	16141.0	17330.4	18233.4	17965.6	16010.2	14820.8	17286.8
62.5°	16844.7	17243.2	17156.1	15954.2	16489.7	17635.5	18127.5	18326.8	16882.1	16072.5	18557.2
65°	16103.6	16527.1	17149.8	16657.9	16228.2	16894.5	17143.6	17747.6	17318.0	17249.5	19080.3
67.5°	15219.4	15680.2	16066.3	17131.1	15698.9	16141.0	15923.1	16116.1	16844.7	18538.5	19379.2
70°	13288.9	13731.1	14341.3	16078.7	14297.7	13899.2	13843.2	13749.8	14883.1	18077.7	18021.6
72.5°	10928.8	11134.3	12143.1	13071.0	10580.1	10505.4	10592.5	10486.7	11800.6	16365.2	15437.3
75°	8182.6	8388.1	8961.0	10038.3	7204.9	6775.2	7273.4	7765.4	9010.8	12703.6	11090.7
77.5°	6152.5	6414.1	6775.2	7510.1	5286.9	4614.4	4682.9	5149.9	6513.7	10175.3	6214.8
80°	3991.7	3960.5	4658.0	5168.6	3979.2	4103.8	3929.4	4271.9	4720.2	5442.6	3175.9
82.5°	2304.1	2335.2	2627.9	2964.2	2771.1	3169.7	2285.4	3817.3	3368.9	2216.9	1183.2
85°	1295.3	1351.3	1619.1	2055.0	1737.4	1164.5	952.8	1893.1	2117.3	909.2	572.9
87.5°	130.8	112.1	218.0	778.4	473.3	193.0	286.5	454.6	510.6	342.5	168.1
90°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0

TEST NUMBER: P599564  
 CATALOG NUMBER: IFLD-L-SA7A-760-U-SLL-HSS

**CANDELA DISTRIBUTION (continued):**

	90°	95°	105°	115°	125°	135°	145°	155°	165°	175°	180°
0°	8768.0	8768.0	8768.0	8768.0	8768.0	8768.0	8768.0	8768.0	8768.0	8768.0	8768.0
2.5°	9110.5	9110.5	8954.8	8693.2	8587.4	8400.5	8145.2	8226.2	8139.0	7821.4	7740.5
5°	8736.8	8437.9	8114.1	7715.6	7485.1	7011.9	6862.4	6594.6	6638.2	6370.5	6382.9
7.5°	7958.4	7721.8	7173.8	6650.7	6196.1	5785.1	5206.0	4988.0	4776.3	4670.4	4795.0
10°	7503.8	7061.7	6314.4	5629.4	5025.4	4658.0	4271.9	3973.0	3699.0	3493.5	3449.9
12.5°	7173.8	6781.5	5878.5	5044.1	4570.8	4271.9	3916.9	3505.9	3238.2	2883.2	2777.3
15°	7074.1	6594.6	5641.9	4813.7	4352.8	3860.9	3456.1	3051.3	2702.6	2329.0	2198.2
17.5°	7416.6	6862.4	5635.7	4626.8	3979.2	3449.9	2889.4	2434.9	2079.9	1737.4	1656.4
20°	7995.8	7148.9	5816.2	4514.8	3624.3	2914.3	2279.2	1824.6	1426.0	1201.9	1145.8
22.5°	8655.9	7634.6	5834.9	4215.8	3269.3	2378.8	1662.7	1201.9	977.7	871.8	840.7
25°	9465.4	8413.0	6059.1	3973.0	2852.1	1805.9	1183.2	921.6	790.9	728.6	716.1
27.5°	10131.7	8954.8	6302.0	3717.7	2441.1	1338.9	927.9	753.5	685.0	622.7	616.5
30°	10822.9	9577.5	6370.5	3562.0	2086.1	1102.2	797.1	666.3	591.6	560.5	554.2
32.5°	11427.0	10256.3	6588.4	3306.7	1749.9	971.4	722.4	597.8	548.0	498.2	492.0
35°	12205.4	10648.6	6694.3	3169.7	1625.3	878.0	660.1	548.0	473.3	442.1	429.7
37.5°	13039.8	11028.4	6762.8	3063.8	1519.4	822.0	622.7	516.9	448.4	404.8	392.3
40°	13818.3	11564.0	6663.1	2933.0	1438.5	753.5	597.8	479.5	417.2	373.6	355.0
42.5°	14416.1	12087.1	6632.0	2808.5	1351.3	728.6	566.7	460.8	392.3	342.5	336.3
45°	14752.3	12442.0	6414.1	2708.9	1282.8	741.0	554.2	435.9	373.6	330.0	305.1
47.5°	14671.4	12716.0	6470.1	2677.7	1189.4	691.2	548.0	417.2	342.5	305.1	286.5
50°	15119.7	13270.3	6376.7	2578.1	1120.9	622.7	597.8	417.2	336.3	292.7	274.0
52.5°	15194.5	13774.7	6576.0	2397.5	1015.0	572.9	591.6	411.0	323.8	280.2	255.3
55°	15817.2	14360.0	6962.1	2297.9	927.9	498.2	541.8	398.5	292.7	255.3	242.9
57.5°	16664.1	15574.3	7211.1	2204.4	809.5	435.9	454.6	392.3	267.8	236.6	218.0
60°	17479.9	16060.1	7229.8	2036.3	697.5	392.3	355.0	392.3	249.1	211.7	193.0
62.5°	18090.1	16060.1	7105.3	1893.1	610.3	348.7	311.4	373.6	224.2	186.8	174.4
65°	17760.1	15630.4	6781.5	1774.8	554.2	305.1	267.8	286.5	199.3	161.9	149.5
67.5°	17168.5	14291.5	6065.3	1631.5	548.0	267.8	230.4	211.7	174.4	143.2	130.8
70°	16222.0	12485.6	5050.3	1469.6	535.5	242.9	205.5	180.6	155.7	124.5	112.1
72.5°	13071.0	10312.3	4147.3	1376.2	523.1	211.7	174.4	155.7	130.8	105.9	93.4
75°	9054.4	6588.4	3194.6	1176.9	510.6	193.0	161.9	137.0	112.1	87.2	81.0
77.5°	5430.2	4402.7	2061.2	884.3	336.3	155.7	137.0	105.9	93.4	74.7	68.5
80°	2540.7	2079.9	834.5	342.5	161.9	112.1	93.4	81.0	74.7	62.3	56.0
82.5°	996.4	878.0	404.8	199.3	130.8	87.2	74.7	68.5	62.3	49.8	43.6
85°	535.5	473.3	193.0	137.0	93.4	62.3	62.3	56.0	49.8	43.6	37.4
87.5°	118.3	87.2	81.0	81.0	68.5	49.8	49.8	43.6	37.4	31.1	24.9
90°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0

TEST NUMBER: P599564  
 CATALOG NUMBER: IFLD-L-SA7A-760-U-SLL-HSS

**CANDELA DISTRIBUTION (continued):**

	185°	195°	205°	215°	225°	235°	245°	255°	265°	270°	275°
0°	8768.0	8768.0	8768.0	8768.0	8768.0	8768.0	8768.0	8768.0	8768.0	8768.0	8768.0
2.5°	7696.9	7790.3	7640.8	7734.2	7603.5	7703.1	7715.6	7622.1	7647.1	7771.6	7827.6
5°	6557.3	6495.0	6358.0	6314.4	6320.7	6239.7	6270.8	6314.4	6382.9	6420.3	6532.4
7.5°	4726.5	4869.7	4863.5	4969.3	4975.6	4963.1	4875.9	4689.1	4751.4	4701.6	4763.8
10°	3381.4	3443.7	3562.0	3630.5	3755.0	3686.5	3487.3	3412.5	3375.2	3368.9	3431.2
12.5°	2702.6	2553.2	2540.7	2565.6	2627.9	2546.9	2447.3	2360.1	2403.7	2490.9	2559.4
15°	2092.4	1967.8	1805.9	1781.0	1793.4	1756.1	1650.2	1538.1	1569.3	1656.4	1706.3
17.5°	1606.6	1463.4	1351.3	1276.6	1251.7	1120.9	965.2	871.8	846.9	840.7	884.3
20°	1083.5	1058.6	1039.9	946.5	946.5	759.7	629.0	560.5	560.5	572.9	579.1
22.5°	809.5	778.4	784.6	766.0	716.1	566.7	498.2	479.5	479.5	492.0	492.0
25°	703.7	660.1	647.6	641.4	591.6	485.7	435.9	417.2	417.2	429.7	429.7
27.5°	597.8	585.4	566.7	541.8	498.2	417.2	386.1	367.4	373.6	379.9	373.6
30°	548.0	516.9	492.0	492.0	442.1	373.6	348.7	336.3	323.8	336.3	342.5
32.5°	485.7	467.0	454.6	435.9	379.9	330.0	305.1	292.7	286.5	286.5	292.7
35°	417.2	417.2	404.8	379.9	330.0	298.9	267.8	255.3	249.1	255.3	255.3
37.5°	373.6	355.0	361.2	336.3	292.7	261.5	230.4	218.0	218.0	211.7	218.0
40°	348.7	317.6	298.9	286.5	261.5	224.2	199.3	186.8	180.6	180.6	180.6
42.5°	311.4	286.5	249.1	242.9	236.6	193.0	161.9	155.7	149.5	143.2	143.2
45°	292.7	255.3	224.2	193.0	193.0	161.9	137.0	124.5	118.3	112.1	118.3
47.5°	267.8	230.4	193.0	161.9	155.7	130.8	105.9	93.4	87.2	87.2	87.2
50°	255.3	205.5	168.1	137.0	118.3	105.9	81.0	68.5	62.3	62.3	62.3
52.5°	236.6	193.0	149.5	118.3	93.4	81.0	62.3	49.8	43.6	43.6	43.6
55°	211.7	174.4	130.8	99.6	81.0	62.3	43.6	31.1	24.9	24.9	24.9
57.5°	199.3	155.7	112.1	87.2	62.3	43.6	24.9	18.7	18.7	12.5	18.7
60°	180.6	137.0	93.4	68.5	49.8	31.1	18.7	6.2	6.2	6.2	6.2
62.5°	155.7	118.3	81.0	56.0	37.4	18.7	6.2	0.0	0.0	0.0	0.0
65°	130.8	93.4	62.3	43.6	24.9	6.2	0.0	0.0	0.0	0.0	0.0
67.5°	112.1	81.0	49.8	31.1	18.7	0.0	0.0	0.0	0.0	0.0	0.0
70°	99.6	68.5	37.4	24.9	6.2	0.0	0.0	0.0	0.0	0.0	0.0
72.5°	81.0	56.0	31.1	12.5	0.0	0.0	0.0	0.0	0.0	0.0	0.0
75°	68.5	43.6	18.7	6.2	0.0	0.0	0.0	0.0	0.0	0.0	0.0
77.5°	56.0	31.1	12.5	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
80°	43.6	24.9	6.2	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
82.5°	37.4	18.7	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
85°	24.9	6.2	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
87.5°	18.7	6.2	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
90°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0



TEST NUMBER: P599564  
 CATALOG NUMBER: IFLD-L-SA7A-760-U-SLL-HSS

**CANDELA DISTRIBUTION (continued):**

	285°	295°	305°	315°	325°	335°	345°	355°	358°	360°
0°	8768.0	8768.0	8768.0	8768.0	8768.0	8768.0	8768.0	8768.0	8768.0	8768.0
2.5°	7908.6	7871.2	8058.1	8363.2	8518.9	8824.0	8898.7	9091.8	9042.0	9110.5
5°	6544.8	6619.6	6893.6	7341.9	7503.8	7946.0	8363.2	8780.4	9048.2	9179.0
7.5°	4857.2	5106.3	5442.6	5853.6	6270.8	6850.0	7559.9	8045.6	8307.1	8587.4
10°	3618.0	3885.8	4271.9	4676.7	5355.4	6003.1	6713.0	7317.0	7541.2	7802.7
12.5°	2845.8	3263.1	3711.4	4147.3	4552.1	5168.6	6046.7	6924.7	7167.6	7366.8
15°	1980.3	2490.9	3132.3	3699.0	4265.7	4801.2	5710.4	6775.2	7105.3	7441.6
17.5°	1096.0	1500.8	2235.6	3032.7	3867.1	4689.1	5822.5	7049.2	7547.4	7784.1
20°	635.2	797.1	1320.2	2266.7	3368.9	4446.3	5878.5	7566.1	8226.2	8344.5
22.5°	523.1	579.1	747.3	1419.8	2758.7	4290.6	6165.0	8288.5	8961.0	9241.2
25°	448.4	492.0	579.1	853.1	2086.1	3960.5	6345.6	9191.4	9814.1	10119.3
27.5°	398.5	442.1	510.6	629.0	1419.8	3505.9	6644.5	10007.2	10629.9	11047.1
30°	348.7	386.1	454.6	535.5	983.9	2995.3	6899.8	10605.0	11483.0	11613.8
32.5°	311.4	342.5	392.3	460.8	728.6	2272.9	7105.3	11221.5	11962.5	12249.0
35°	267.8	305.1	336.3	392.3	554.2	1712.5	6980.7	11701.0	12666.2	13008.7
37.5°	236.6	261.5	292.7	330.0	467.0	1338.9	6725.4	12273.9	13270.3	13587.8
40°	199.3	218.0	255.3	292.7	423.5	1033.7	6432.7	12965.1	14117.2	14677.6
42.5°	168.1	186.8	211.7	274.0	348.7	766.0	5841.2	13500.7	14802.2	15275.4
45°	130.8	155.7	193.0	274.0	280.2	566.7	5230.9	13899.2	15188.2	15424.9
47.5°	99.6	124.5	186.8	236.6	224.2	392.3	4508.5	14353.8	15586.8	15804.7
50°	74.7	99.6	211.7	205.5	186.8	298.9	4053.9	14671.4	15611.7	15730.0
52.5°	49.8	74.7	174.4	155.7	155.7	261.5	3929.4	14658.9	15674.0	15418.7
55°	37.4	56.0	99.6	112.1	137.0	230.4	3817.3	15126.0	15692.6	15873.2
57.5°	24.9	43.6	68.5	87.2	118.3	199.3	3586.9	15686.4	16271.8	16365.2
60°	12.5	31.1	49.8	68.5	99.6	174.4	3263.1	16097.4	16975.5	17075.1
62.5°	6.2	18.7	37.4	56.0	81.0	137.0	2926.8	15443.6	16670.3	16844.7
65°	0.0	12.5	24.9	37.4	49.8	99.6	2378.8	13942.8	15462.2	16103.6
67.5°	0.0	0.0	12.5	24.9	31.1	74.7	1793.4	12684.9	14347.6	15219.4
70°	0.0	0.0	6.2	6.2	18.7	56.0	1145.8	10505.4	12809.4	13288.9
72.5°	0.0	0.0	0.0	0.0	6.2	37.4	666.3	7802.7	10038.3	10928.8
75°	0.0	0.0	0.0	0.0	0.0	31.1	336.3	5019.2	6987.0	8182.6
77.5°	0.0	0.0	0.0	0.0	0.0	24.9	180.6	3238.2	5149.9	6152.5
80°	0.0	0.0	0.0	0.0	0.0	6.2	105.9	1880.6	3294.2	3991.7
82.5°	0.0	0.0	0.0	0.0	0.0	0.0	43.6	921.6	1967.8	2304.1
85°	0.0	0.0	0.0	0.0	0.0	0.0	12.5	492.0	983.9	1295.3
87.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	18.7	68.5	130.8
90°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0

(END OF REPORT)