

LM-79-08 Approved Method: Electrical and Photometric Measurements of Solid-State  
Lighting Products

Test Report Prepared for  
Cooper Lighting Solutions  
(formerly Eaton)

Brand: STREETWORKS

Report Number: P599567

Luminaire Tested: **IFLD-L-SA7D-760-U-SLL-HSS**

Issue Date: 05/04/2022

Tested By:

Approved By:



Cooper Lighting Solutions laboratories have been accredited by National Voluntary Laboratory Accreditation Program (NVLAP) that it adheres to the requirements of ISO/IEC 17025:2005 and appropriate IESNA test methods. This report must not be used to claim product certification, approval or endorsement by NVLAP, NIST or any agency of the Federal Government. Results contained in this report are valid for luminaire sample tested, as supplied by requestor. Information related to the luminaire tested has been supplied by requestor and can affect the validity of the test results. Report shall not be reproduced except in full without approval of Cooper Lighting Solutions Lighting Laboratory. Test performed at address noted above.

**Test Information**

Test Method: LM-79-08  
 Report Number: P599567  
 Test Lab: INNOVATION CENTER(G1)  
 Issue Date: 05/04/2022  
 Manufacturer: COOPER LIGHTING SOLUTIONS (FORMERLY EATON)  
 Product Line: STREETWORKS  
 Catalog Number: IFLD-L-SA7D-760-U-SLL-HSS  
 Description: Infrastructure Flood – Middle Tier Light Square Luminaire w/ SLL distribution lens with House Side Shield  
 Light Source: (112) 5700K CCT, 70 CRI LEDS  
 Ballast/Driver: ELECTRONIC DRIVER

**Summary**


Lumens per Lamp: N/A  
 Luminaire Lumens: 36341.3 lumens  
 Efficiency: N/A  
 Efficacy: 86.0 lumens/watt  
 Spacing Criteria (0/90/45): 0.53 / 0.46 / 0.63  
 Luminous Opening: Rectangular (W 2' x L: 1' x H: 0')  
 CIE Type: Direct

Input Watts (W): 422.6  
 Input Voltage (V): 120  
 Input Current (Ain): NR  
 Voltage Rise (V): NR  
 Power Factor: NR  
 Total Harmonic Distortion (THDi): NR  
 Frequency (hertz): 60  
 Stabilization Time: NR  
 Operation Time: NR  
 Ambient Temperature (°C): NR  
 Test Distance: 25 FT

Measurement and Test Equipment			
Instrument	Identification Number	Calibration Date	Calibration Due Date
Photometer	GONIO 1 IN0055	4/22/2021	10/22/2021
Power Meter	XITRON 2801 IN0197	12/1/2020	12/1/2021
AC Power Source	CHROMA 61505 IN0196	12/1/2020	12/1/2021
DC Power Supply	AGILENT E3634A IN0198	11/30/2020	11/30/2021
Room Thermometer	ONSET IN0143	12/1/2020	12/1/2021

TEST NUMBER: P599567  
CATALOG NUMBER: IFLD-L-SA7D-760-U-SLL-HSS

### Luminous Intensity Polar Plot



— 0°-180°    - - 45°-225°    - - - 90°-270°    - - - 135°-315°

TEST NUMBER: P599567

CATALOG NUMBER: IFLD-L-SA7D-760-U-SLL-HSS

**COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:**

RF	20				20				20				20				20				
RC	80				70				50				30				10			0	
RW	70	50	30	10	70	50	30	10	50	30	10	50	30	10	50	30	10	50	30	10	0
RCR																					
0	119	119	119	119	116	116	116	116	111	111	111	106	106	106	102	102	102	100	100	100	100
1	106	100	95	90	103	98	93	89	94	90	86	90	86	83	86	83	81	79	79	79	79
2	94	84	76	69	91	82	75	68	78	72	66	75	70	65	72	67	63	61	61	61	61
3	84	72	62	54	81	70	61	53	67	59	52	64	57	51	61	55	50	48	48	48	48
4	76	62	51	44	73	60	51	43	58	49	43	55	48	42	53	46	41	39	39	39	39
5	69	54	44	36	67	53	43	36	51	42	35	48	41	35	46	40	34	32	32	32	32
6	63	48	38	30	61	47	37	30	45	36	30	43	35	30	41	35	29	27	27	27	27
7	58	43	33	26	56	42	33	26	40	32	26	39	31	26	37	31	25	23	23	23	23
8	54	39	29	23	52	38	29	23	37	28	23	35	28	22	34	27	22	20	20	20	20
9	50	35	26	20	49	35	26	20	34	26	20	32	25	20	31	25	20	18	18	18	18
10	47	33	24	18	46	32	24	18	31	23	18	30	23	18	29	23	18	16	16	16	16

**AVERAGE LUMINANCE (cd/sqm):**

	0°	90°	180°	270°
0°	73540	73540	73540	73540
5°	77281	73558	53740	54054
10°	66454	63908	29381	28692
15°	64616	61426	19087	14383
20°	74480	71367	10227	5113
25°	93648	87596	6627	3976
30°	112478	104818	5368	3256
35°	133196	124971	4399	2614
40°	160703	151294	3887	1977
45°	182961	174984	3619	1330
50°	205250	197288	3575	812
55°	232111	231292	3552	364
60°	286428	293218	3238	104
65°	319594	352467	2966	0
70°	325882	397809	2749	0
75°	265165	293418	2624	0
80°	192798	122719	2706	0
85°	124651	51537	3594	0

TEST NUMBER: P599567  
 CATALOG NUMBER: IFLD-L-SA7D-760-U-SLL-HSS

**ZONAL LUMENS:**

Zone	Lumens	% Fixture
0°-10°	1038.0	2.9
10°-20°	2035.6	5.6
20°-30°	2816.9	7.8
30°-40°	3981.0	11.0
40°-50°	5420.2	14.9
50°-60°	7178.7	19.8
60°-70°	8335.0	22.9
70°-80°	4720.2	13.0
80°-90°	815.6	2.2
90°-100°	0.0	0.0
100°-110°	0.0	0.0
110°-120°	0.0	0.0
120°-130°	0.0	0.0
130°-140°	0.0	0.0
140°-150°	0.0	0.0
150°-160°	0.0	0.0
160°-170°	0.0	0.0
170°-180°	0.0	0.0
0°-30°	5890.5	16.2
0°-40°	9871.5	27.2
0°-60°	22470.5	61.8
0°-90°	36341.3	100.0
90°-120°	0.0	0.0
90°-150°	0.0	0.0
90°-180°	0.0	0.0
0°-180°	36341.3	100.0

**CANDELA DISTRIBUTION:**

	0°	90°	180°	270°	360°	Flux
0°	13664	13664	13664	13664	13664	
5°	14305	13616	9947	10005	14305	1285
15°	11597	11024	3426	2581	11597	3401
25°	15770	14751	1116	670	15770	7355
35°	20273	19021	670	398	20273	12780
45°	24038	22990	476	175	24038	18637
55°	24737	24650	378	39	24737	22412
65°	25096	27678	233	0	25096	24464
75°	12752	14110	126	0	12752	13917
85°	2019	835	58	0	2019	2425
90°	0	0	0	0	0	

TEST NUMBER: P599567  
 CATALOG NUMBER: IFLD-L-SA7D-760-U-SLL-HSS

**CANDELA DISTRIBUTION (FULL):**

	0°	2°	5°	15°	25°	35°	45°	55°	65°	75°	85°
0°	13664.1	13664.1	13664.1	13664.1	13664.1	13664.1	13664.1	13664.1	13664.1	13664.1	13664.1
2.5°	14197.8	14498.7	14508.4	14644.2	14780.1	14780.1	15100.4	15022.7	14741.3	14692.8	14489.0
5°	14304.6	14411.3	14489.0	15178.0	15760.3	15702.0	15876.7	15760.3	15216.8	14518.1	14042.6
7.5°	13382.6	13499.1	13809.6	14983.9	15770.0	16032.0	16362.0	15634.1	15061.5	13799.9	12887.7
10°	12159.9	12383.1	12955.6	14294.9	15265.3	16099.9	16099.9	15517.7	14411.3	13178.8	12062.8
12.5°	11480.5	11927.0	12237.5	13596.1	14857.7	15430.3	15410.9	15100.4	14382.2	12829.5	11567.9
15°	11597.0	11723.2	12383.1	13440.9	14275.5	14246.4	14595.7	14498.7	13994.0	13140.0	11752.3
17.5°	12130.8	12324.8	12897.4	13440.9	13838.8	13722.3	13712.6	14178.4	14207.5	13664.1	12441.3
20°	13004.2	13576.7	13848.5	14013.4	13528.2	13033.3	12975.1	13625.3	14129.9	14333.7	13266.2
22.5°	14401.6	14780.1	15333.3	14489.0	13227.4	12606.3	12489.8	13208.0	14226.9	15129.5	14333.7
25°	15770.0	16061.1	16594.9	15508.0	13567.0	12518.9	12315.1	12936.2	14595.7	16235.8	15624.4
27.5°	17216.0	17468.3	17526.5	16255.2	13751.4	12344.3	12101.6	12936.2	14906.3	16818.1	17167.4
30°	18099.1	18399.9	18458.2	16915.1	14052.3	12489.8	12373.4	12994.5	15119.8	17313.0	18273.8
32.5°	19089.0	19166.6	19118.1	17031.6	14382.2	12916.8	12431.6	13382.6	15362.4	17905.0	19283.0
35°	20272.9	20408.8	19913.8	17565.3	15119.8	13188.6	13013.9	13858.2	15779.7	18176.7	20505.8
37.5°	21175.4	21602.4	20486.4	17769.1	15265.3	13761.1	13790.2	14848.0	16070.8	18506.7	21854.8
40°	22873.7	22155.6	21456.9	18467.9	15818.5	14731.6	14576.3	15867.0	17051.0	18720.2	22737.9
42.5°	23805.4	23426.9	21835.4	18535.8	16672.5	16070.8	16109.6	17021.9	17565.3	19321.9	22980.5
45°	24038.3	23640.4	22349.7	18584.3	17516.8	17652.7	18322.3	18497.0	18322.3	19719.7	23436.6
47.5°	24630.3	23766.6	22291.5	19234.5	18885.2	19409.2	20263.2	20641.7	19351.0	19574.2	23650.1
50°	24513.8	24018.9	22165.3	19506.2	20554.3	21942.1	22514.7	22359.4	20496.1	19273.3	23417.2
52.5°	24028.6	23494.8	22553.5	20243.8	22116.8	23795.7	24591.5	24203.3	21515.1	19952.7	23261.9
55°	24737.0	24329.4	23058.1	21243.4	23291.0	25426.1	25988.9	25697.8	22767.0	20583.5	24145.0
57.5°	25503.7	25416.4	24426.5	22417.6	24678.8	27105.0	27105.0	26745.9	23853.9	21495.7	25455.2
60°	26610.0	26804.1	25435.8	23194.0	25154.3	27007.9	28415.1	27997.8	24950.5	23097.0	26940.0
62.5°	26250.9	26872.0	26736.2	24863.2	25697.8	27483.4	28250.1	28560.6	26309.2	25047.6	28919.7
65°	25096.1	25756.0	26726.5	25959.8	25290.2	26328.6	26716.8	27658.1	26988.5	26881.7	29734.9
67.5°	23718.0	24436.2	25037.9	26697.4	24465.3	25154.3	24814.7	25115.5	26250.9	28890.6	30200.7
70°	20709.6	21398.6	22349.7	25057.3	22281.8	21660.7	21573.3	21427.8	23194.0	28172.5	28085.1
72.5°	17031.6	17351.8	18924.0	20370.0	16488.1	16371.7	16507.5	16342.5	18390.2	25503.7	24057.7
75°	12751.8	13072.1	13964.9	15643.8	11228.2	10558.6	11335.0	12101.6	14042.6	19797.4	17283.9
77.5°	9588.1	9995.7	10558.6	11703.7	8239.2	7191.1	7297.9	8025.7	10151.0	15857.3	9685.2
80°	6220.6	6172.1	7259.0	8054.8	6201.2	6395.3	6123.6	6657.4	7356.1	8481.8	4949.3
82.5°	3590.7	3639.2	4095.3	4619.4	4318.5	4939.6	3561.6	5948.9	5250.2	3454.8	1843.9
85°	2018.6	2105.9	2523.2	3202.5	2707.6	1814.8	1484.8	2950.2	3299.6	1416.9	892.8
87.5°	203.8	174.7	339.7	1213.1	737.5	300.8	446.4	708.4	795.8	533.8	262.0
90°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0

TEST NUMBER: P599567  
 CATALOG NUMBER: IFLD-L-SA7D-760-U-SLL-HSS

**CANDELA DISTRIBUTION (continued):**

	90°	95°	105°	115°	125°	135°	145°	155°	165°	175°	180°
0°	13664.1	13664.1	13664.1	13664.1	13664.1	13664.1	13664.1	13664.1	13664.1	13664.1	13664.1
2.5°	14197.8	14197.8	13955.2	13547.6	13382.6	13091.5	12693.6	12819.8	12683.9	12189.0	12062.8
5°	13615.6	13149.7	12645.1	12024.0	11664.9	10927.4	10694.5	10277.2	10345.1	9927.8	9947.2
7.5°	12402.5	12033.7	11179.7	10364.5	9656.1	9015.6	8113.0	7773.4	7443.4	7278.5	7472.5
10°	11694.0	11005.0	9840.5	8773.0	7831.6	7259.0	6657.4	6191.5	5764.5	5444.3	5376.3
12.5°	11179.7	10568.3	9161.1	7860.7	7123.2	6657.4	6104.2	5463.7	5046.4	4493.2	4328.3
15°	11024.4	10277.2	8792.4	7501.7	6783.5	6016.9	5386.1	4755.3	4211.8	3629.5	3425.7
17.5°	11558.2	10694.5	8782.7	7210.5	6201.2	5376.3	4502.9	3794.5	3241.3	2707.6	2581.4
20°	12460.7	11140.9	9064.1	7035.8	5648.1	4541.8	3551.9	2843.4	2222.4	1873.0	1785.6
22.5°	13489.4	11897.8	9093.2	6570.0	5094.9	3707.2	2591.1	1873.0	1523.6	1358.6	1310.1
25°	14751.0	13110.9	9442.6	6191.5	4444.7	2814.3	1843.9	1436.3	1232.5	1135.4	1116.0
27.5°	15789.4	13955.2	9821.1	5793.6	3804.2	2086.5	1446.0	1174.3	1067.5	970.5	960.8
30°	16866.6	14925.7	9927.8	5551.0	3251.0	1717.7	1242.2	1038.4	921.9	873.4	863.7
32.5°	17807.9	15983.5	10267.5	5153.1	2727.0	1513.9	1125.7	931.6	854.0	776.4	766.7
35°	19021.0	16594.9	10432.4	4939.6	2532.9	1368.3	1028.7	854.0	737.5	689.0	669.6
37.5°	20321.4	17186.8	10539.2	4774.7	2367.9	1281.0	970.5	805.5	698.7	630.8	611.4
40°	21534.5	18021.4	10383.9	4570.9	2241.8	1174.3	931.6	747.3	650.2	582.3	553.2
42.5°	22466.2	18836.6	10335.4	4376.8	2105.9	1135.4	883.1	718.1	611.4	533.8	524.0
45°	22990.2	19389.8	9995.7	4221.5	1999.1	1154.8	863.7	679.3	582.3	514.3	475.5
47.5°	22864.0	19816.8	10083.1	4173.0	1853.6	1077.2	854.0	650.2	533.8	475.5	446.4
50°	23562.8	20680.5	9937.5	4017.7	1746.8	970.5	931.6	650.2	524.0	456.1	427.0
52.5°	23679.2	21466.6	10248.1	3736.3	1581.8	892.8	921.9	640.5	504.6	436.7	397.9
55°	24649.7	22378.8	10849.7	3581.0	1446.0	776.4	844.3	621.1	456.1	397.9	378.5
57.5°	25969.5	24271.2	11237.9	3435.4	1261.6	679.3	708.4	611.4	417.3	368.8	339.7
60°	27240.8	25028.2	11267.0	3173.4	1086.9	611.4	553.2	611.4	388.2	330.0	300.8
62.5°	28191.9	25028.2	11072.9	2950.2	951.1	543.5	485.2	582.3	349.4	291.1	271.7
65°	27677.5	24358.5	10568.3	2765.8	863.7	475.5	417.3	446.4	310.5	252.3	232.9
67.5°	26755.6	22272.1	9452.3	2542.6	854.0	417.3	359.1	330.0	271.7	223.2	203.8
70°	25280.5	19457.7	7870.4	2290.3	834.6	378.5	320.3	281.4	242.6	194.1	174.7
72.5°	20370.0	16070.8	6463.3	2144.7	815.2	330.0	271.7	242.6	203.8	165.0	145.6
75°	14110.5	10267.5	4978.5	1834.2	795.8	300.8	252.3	213.5	174.7	135.9	126.2
77.5°	8462.4	6861.2	3212.2	1378.1	524.0	242.6	213.5	165.0	145.6	116.5	106.8
80°	3959.5	3241.3	1300.4	533.8	252.3	174.7	145.6	126.2	116.5	97.0	87.3
82.5°	1552.7	1368.3	630.8	310.5	203.8	135.9	116.5	106.8	97.0	77.6	67.9
85°	834.6	737.5	300.8	213.5	145.6	97.0	97.0	87.3	77.6	67.9	58.2
87.5°	184.4	135.9	126.2	126.2	106.8	77.6	77.6	67.9	58.2	48.5	38.8
90°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0

TEST NUMBER: P599567  
 CATALOG NUMBER: IFLD-L-SA7D-760-U-SLL-HSS

**CANDELA DISTRIBUTION (continued):**

	185°	195°	205°	215°	225°	235°	245°	255°	265°	270°	275°
0°	13664.1	13664.1	13664.1	13664.1	13664.1	13664.1	13664.1	13664.1	13664.1	13664.1	13664.1
2.5°	11994.9	12140.5	11907.5	12053.1	11849.3	12004.6	12024.0	11878.4	11917.3	12111.3	12198.7
5°	10218.9	10121.9	9908.4	9840.5	9850.2	9724.0	9772.5	9840.5	9947.2	10005.4	10180.1
7.5°	7365.8	7589.0	7579.3	7744.3	7754.0	7734.6	7598.7	7307.6	7404.6	7327.0	7424.0
10°	5269.6	5366.6	5551.0	5657.8	5851.9	5745.1	5434.6	5318.1	5259.9	5250.2	5347.2
12.5°	4211.8	3978.9	3959.5	3998.3	4095.3	3969.2	3813.9	3678.0	3746.0	3881.8	3988.6
15°	3260.7	3066.7	2814.3	2775.5	2794.9	2736.7	2571.7	2397.0	2445.6	2581.4	2659.1
17.5°	2503.8	2280.6	2105.9	1989.4	1950.6	1746.8	1504.2	1358.6	1319.8	1310.1	1378.1
20°	1688.6	1649.8	1620.7	1475.1	1475.1	1184.0	980.2	873.4	873.4	892.8	902.5
22.5°	1261.6	1213.1	1222.8	1193.7	1116.0	883.1	776.4	747.3	747.3	766.7	766.7
25°	1096.6	1028.7	1009.3	999.6	921.9	757.0	679.3	650.2	650.2	669.6	669.6
27.5°	931.6	912.2	883.1	844.3	776.4	650.2	601.7	572.6	582.3	592.0	582.3
30°	854.0	805.5	766.7	766.7	689.0	582.3	543.5	524.0	504.6	524.0	533.8
32.5°	757.0	727.8	708.4	679.3	592.0	514.3	475.5	456.1	446.4	446.4	456.1
35°	650.2	650.2	630.8	592.0	514.3	465.8	417.3	397.9	388.2	397.9	397.9
37.5°	582.3	553.2	562.9	524.0	456.1	407.6	359.1	339.7	339.7	330.0	339.7
40°	543.5	494.9	465.8	446.4	407.6	349.4	310.5	291.1	281.4	281.4	281.4
42.5°	485.2	446.4	388.2	378.5	368.8	300.8	252.3	242.6	232.9	223.2	223.2
45°	456.1	397.9	349.4	300.8	300.8	252.3	213.5	194.1	184.4	174.7	184.4
47.5°	417.3	359.1	300.8	252.3	242.6	203.8	165.0	145.6	135.9	135.9	135.9
50°	397.9	320.3	262.0	213.5	184.4	165.0	126.2	106.8	97.0	97.0	97.0
52.5°	368.8	300.8	232.9	184.4	145.6	126.2	97.0	77.6	67.9	67.9	67.9
55°	330.0	271.7	203.8	155.3	126.2	97.0	67.9	48.5	38.8	38.8	38.8
57.5°	310.5	242.6	174.7	135.9	97.0	67.9	38.8	29.1	29.1	19.4	29.1
60°	281.4	213.5	145.6	106.8	77.6	48.5	29.1	9.7	9.7	9.7	9.7
62.5°	242.6	184.4	126.2	87.3	58.2	29.1	9.7	0.0	0.0	0.0	0.0
65°	203.8	145.6	97.0	67.9	38.8	9.7	0.0	0.0	0.0	0.0	0.0
67.5°	174.7	126.2	77.6	48.5	29.1	0.0	0.0	0.0	0.0	0.0	0.0
70°	155.3	106.8	58.2	38.8	9.7	0.0	0.0	0.0	0.0	0.0	0.0
72.5°	126.2	87.3	48.5	19.4	0.0	0.0	0.0	0.0	0.0	0.0	0.0
75°	106.8	67.9	29.1	9.7	0.0	0.0	0.0	0.0	0.0	0.0	0.0
77.5°	87.3	48.5	19.4	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
80°	67.9	38.8	9.7	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
82.5°	58.2	29.1	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
85°	38.8	9.7	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
87.5°	29.1	9.7	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
90°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0





TEST NUMBER: P599567  
 CATALOG NUMBER: IFLD-L-SA7D-760-U-SLL-HSS

**CANDELA DISTRIBUTION (continued):**

	285°	295°	305°	315°	325°	335°	345°	355°	358°	360°
0°	13664.1	13664.1	13664.1	13664.1	13664.1	13664.1	13664.1	13664.1	13664.1	13664.1
2.5°	12324.8	12266.6	12557.8	13033.3	13275.9	13751.4	13867.9	14168.7	14091.1	14197.8
5°	10199.5	10316.0	10743.0	11441.7	11694.0	12383.1	13033.3	13683.5	14100.8	14304.6
7.5°	7569.6	7957.8	8481.8	9122.3	9772.5	10675.1	11781.4	12538.3	12945.9	13382.6
10°	5638.4	6055.7	6657.4	7288.2	8346.0	9355.2	10461.6	11402.9	11752.3	12159.9
12.5°	4435.0	5085.2	5783.9	6463.3	7094.1	8054.8	9423.2	10791.5	11170.0	11480.5
15°	3086.1	3881.8	4881.4	5764.5	6647.7	7482.2	8899.1	10558.6	11072.9	11597.0
17.5°	1708.0	2338.8	3484.0	4726.1	6026.6	7307.6	9073.8	10985.6	11762.0	12130.8
20°	989.9	1242.2	2057.4	3532.5	5250.2	6929.1	9161.1	11791.1	12819.8	13004.2
22.5°	815.2	902.5	1164.6	2212.6	4299.1	6686.5	9607.6	12916.8	13964.9	14401.6
25°	698.7	766.7	902.5	1329.5	3251.0	6172.1	9889.0	14324.0	15294.5	15770.0
27.5°	621.1	689.0	795.8	980.2	2212.6	5463.7	10354.8	15595.3	16565.8	17216.0
30°	543.5	601.7	708.4	834.6	1533.3	4667.9	10752.7	16526.9	17895.3	18099.1
32.5°	485.2	533.8	611.4	718.1	1135.4	3542.2	11072.9	17487.7	18642.5	19089.0
35°	417.3	475.5	524.0	611.4	863.7	2668.8	10878.9	18234.9	19739.2	20272.9
37.5°	368.8	407.6	456.1	514.3	727.8	2086.5	10481.0	19127.8	20680.5	21175.4
40°	310.5	339.7	397.9	456.1	659.9	1611.0	10024.9	20205.0	22000.3	22873.7
42.5°	262.0	291.1	330.0	427.0	543.5	1193.7	9102.9	21039.6	23067.8	23805.4
45°	203.8	242.6	300.8	427.0	436.7	883.1	8151.9	21660.7	23669.5	24038.3
47.5°	155.3	194.1	291.1	368.8	349.4	611.4	7026.1	22369.1	24290.6	24630.3
50°	116.5	155.3	330.0	320.3	291.1	465.8	6317.7	22864.0	24329.4	24513.8
52.5°	77.6	116.5	271.7	242.6	242.6	407.6	6123.6	22844.6	24426.5	24028.6
55°	58.2	87.3	155.3	174.7	213.5	359.1	5948.9	23572.5	24455.6	24737.0
57.5°	38.8	67.9	106.8	135.9	184.4	310.5	5589.9	24445.9	25358.1	25503.7
60°	19.4	48.5	77.6	106.8	155.3	271.7	5085.2	25086.4	26454.7	26610.0
62.5°	9.7	29.1	58.2	87.3	126.2	213.5	4561.2	24067.4	25979.2	26250.9
65°	0.0	19.4	38.8	58.2	77.6	155.3	3707.2	21728.6	24096.5	25096.1
67.5°	0.0	0.0	19.4	38.8	48.5	116.5	2794.9	19768.3	22359.4	23718.0
70°	0.0	0.0	9.7	9.7	29.1	87.3	1785.6	16371.7	19962.4	20709.6
72.5°	0.0	0.0	0.0	0.0	9.7	58.2	1038.4	12159.9	15643.8	17031.6
75°	0.0	0.0	0.0	0.0	0.0	48.5	524.0	7821.9	10888.6	12751.8
77.5°	0.0	0.0	0.0	0.0	0.0	38.8	281.4	5046.4	8025.7	9588.1
80°	0.0	0.0	0.0	0.0	0.0	9.7	165.0	2930.8	5133.7	6220.6
82.5°	0.0	0.0	0.0	0.0	0.0	0.0	67.9	1436.3	3066.7	3590.7
85°	0.0	0.0	0.0	0.0	0.0	0.0	19.4	766.7	1533.3	2018.6
87.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	29.1	106.8	203.8
90°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0

(END OF REPORT)